NX3DV2567

Low-ohmic four-pole double-throw analog switch

Rev. 2.1 — 4 October 2023

Product data sheet

1 General description

The NX3DV2567 is a four-pole double-throw analog switch (4PDT) optimized for switching WLAN-SIM supply, data and control signals. It has one digital select input (S) and four switches each with two independent input/outputs (nY0 and nY1) and a common input/output (nZ). Schmitt trigger action at S makes the circuit tolerant to slower input rise and fall times across the entire V_{CC} range from 1.4 V to 4.3 V.

A low input voltage threshold allows pin S to be driven by lower level logic signals without significant increase in supply current I_{CC} . This makes it possible for the NX3DV2567 to switch 4.3 V signals with a 1.8 V digital controller, eliminating the need for logic level translation.

The NX3DV2567 allows signals with amplitude up to V_{CC} to be transmitted from nZ to nY0 or nY1; or from nY0 or nY1 to nZ.

2 Features and benefits

- Wide supply voltage range from 1.4 V to 4.3 V
- · Very low ON resistance for supply path:
 - -0.5Ω (typical) at $V_{CC} = 1.8 V$
 - 0.45 Ω (typical) at V_{CC} = 2.7 V
- · Low ON resistance for data path:
 - -7Ω (typical) at $V_{CC} = 1.8 V$
 - -6Ω (typical) at $V_{CC} = 2.7 V$
- · Low ON capacitance for data path
- Wide -3 db bandwidth > 160 MHz
- · Break-before-make switching
- · High noise immunity
- ESD protection:
 - HBM JESD22-A114F Class 3A exceeds 4000 V
 - HBM JESD22-A114F Class 3A I/O to GND exceeds 7000 V
 - CDM AEC-Q100-011 revision B exceeds 1000 V
- CMOS low-power consumption
- Latch-up performance exceeds 100 mA per JESD 78B Class II Level A
- 1.8 V control logic at V_{CC} = 3.6 V
- · Control input accepts voltages above supply voltage
- ullet Very low supply current, even when input is below V_{CC}
- High current handling capability (350 mA continuous current under 3.3 V supply for supply path switch)
- Specified from -40 °C to +85 °C and from -40 °C to +125 °C

3 Applications

- · Cell phone, PDA, digital camera, printer and notebook
- · LCD monitor, TV and set-top box



4 Ordering information

Table 1. Ordering information

Type number	Topside	Package	Package							
	marking	Name	Description Ve							
NX3DV2567HR	D60		plastic thermal enhanced extremely thin quad flat package; no leads; 16 terminals; body 3 x 3 x 0.5 mm	SOT1039-2						
NX3DV2567GU	D60		plastic, extremely thin quad flat package; no leads; 16 terminals; body 1.80 x $2.60 \times 0.50 \text{ mm}$	SOT1161-1						

4.1 Ordering options

Table 2. Ordering options

Type number	Orderable part number	Package	Packing method	Minimum order qty	Temperature
NX3DV2567HR	NX3DV2567HR,115	HXQFN16(U)	REEL 7" Q1/T1 NDP	1500	T _{amb} = -40 °C to +125 °C
NX3DV2567GU	NX3DV2567GU,115	XQFN16	REEL 7" Q1/T1 NDP	4000	T _{amb} = -40 °C to +125 °C

5 Functional diagram




Figure 1. Logic symbol




Figure 2. Logic diagram (one switch)

6 Pinning information

6.1 Pinning




Figure 4. Pin configuration SOT1161-1 (XQFN16)

6.2 Pin description

Table 3. Pin description

Symbol	Pin	Description
- Cyllison	• • • • • • • • • • • • • • • • • • • •	Becomption
1Y0	1	independent input or output (supply switch)
2Y0, 3Y0, 4Y0	5, 9, 13	independent input or output (data switch)
S	2	select input
1Y1	15	independent input or output (supply switch)
2Y1, 3Y1, 4Y1	3, 7, 11	independent input or output (data switch)
1Z	16	common output or input (supply switch)
2Z, 3Z, 4Z	4, 8, 12	common output or input (data switch)
GND	6	ground (0 V)

32

001aam598

Transparent top view

NX3DV2567

All information provided in this document is subject to legal disclaimers.

Low-ohmic four-pole double-throw analog switch

Table 3. Pin description...continued

Symbol	Pin	Description
n.c.	10	not connected
V _{CC}	14	supply voltage

Functional description

Table 4. Function table^[1]

Input S	Channel on
L	nY0
Н	nY1

H = HIGH voltage level; L = LOW voltage level.

Limiting values

Table 5. Limiting values

In accordance with the Absolute Maximum Rating System (IEC 60134). Voltages are referenced to GND (ground = 0 V).

Symbol	Parameter	Conditions		Min	Max	Unit
V _{CC}	supply voltage			-0.5	+4.6	V
VI	input voltage	select input S	[1]	-0.5	+4.6	V
V _{SW}	switch voltage		[2]	-0.5	V _{CC} + 0.5	V
I _{IK}	input clamping current	V _I < -0.5 V		-50	-	mA
I _{SK}	switch clamping current	$V_{I} < -0.5 \text{ V or } V_{I} > V_{CC} + 0.5 \text{ V}$		-	±50	mA
I _{SW}	switch current	supply path switch				
		V_{SW} > -0.5 V or V_{SW} < V_{CC} + 0.5 V; source or sink current		-	±350	mA
		V_{SW} > -0.5 V or V_{SW} < V_{CC} + 0.5 V; pulsed at 1 ms duration, < 10 % duty cycle; peak current		-	±500	mA
		data path switch				
		V_{SW} > -0.5 V or V_{SW} < V_{CC} + 0.5 V; source or sink current		-	±128	mA
T _{stg}	storage temperature			-65	+150	°C
P _{tot}	total power dissipation	T _{amb} = -40 °C to +125 °C	[3] [4]	-	250	mW

The minimum input voltage rating may be exceeded if the input current rating is observed.

The minimum and maximum switch voltage ratings may be exceeded if the switch clamping current rating is observed but may not exceed 4.6 V. For HXQFN16(U) package: above 135 °C the value of P_{tot} derates linearly with 16.9 mW/K.

For XQFN16 package: above 133 °C the value of Ptot derates linearly with 14.5 mW/K.

9 Recommended operating conditions

Table 6. Recommended operating conditions

Symbol	Parameter	Conditions		Min	Max	Unit
V _{CC}	supply voltage			1.4	4.3	V
VI	input voltage	select input S		0	4.3	V
V _{SW}	switch voltage		[1]	0	V _{CC}	V
T _{amb}	ambient temperature			-40	+125	°C
Δt/ΔV	input transition rise and fall rate	V _{CC} = 1.4 V to 4.3 V	[2]	-	200	ns/V

^[1] To avoid sinking GND current from terminal nZ when switch current flows in terminal nYn, the voltage drop across the bidirectional switch must not exceed 0.4 V. If the switch current flows into terminal nZ, no GND current will flow from terminal nYn. In this case, there is no limit for the voltage drop across the switch.

10 Static characteristics

Table 7. Static characteristics

At recommended operating conditions; voltages are referenced to GND (ground 0 V).

Symbol	Parameter	Conditions		Tai	_{mb} = 25	°C	T _{amb} =	Unit		
				Min	Тур	Max	Min	Max (85 °C)	Max (125 °C)	
V _{IH}	HIGH-level	V _{CC} = 1.4 V to 1.6 V		0.9	-	-	0.9	-	-	V
	input voltage	V _{CC} = 1.65 V to 1.95 V		0.9	-	-	0.9	-	-	V
		V _{CC} = 2.3 V to 2.7 V		1.1	-	-	1.1	-	-	V
		V _{CC} = 2.7 V to 3.6 V		1.3	-	-	1.3	-	-	V
		V _{CC} = 3.6 V to 4.3 V		1.4	-	-	1.4	-	-	V
V _{IL}	LOW-level input voltage	V _{CC} = 1.4 V to 1.6 V		-	-	0.3	-	0.3	0.3	V
		V _{CC} = 1.65 V to 1.95 V		-	-	0.4	-	0.4	0.3	V
		V _{CC} = 2.3 V to 2.7 V		-	-	0.4	-	0.4	0.4	V
		V _{CC} = 2.7 V to 3.6 V		-	-	0.5	-	0.5	0.5	V
		V _{CC} = 3.6 V to 4.3 V		-	-	0.6	-	0.6	0.6	V
I _I	input leakage current	select input S; V_I = GND to 4.3 V; V_{CC} = 1.4 V to 4.3 V		-	-	-	-	±0.5	±1	μА
I _{S(OFF)}	OFF-state leakage	nY0 and nY1 port; see Figure 5								
	current	V _{CC} = 1.4 V to 3.6 V		-	-	±5	-	±50	±500	nA
		V _{CC} = 3.6 V to 4.3 V		-	-	±10	-	±50	±500	nA
I _{S(ON)}	ON-state leakage	nZ port; V _{CC} = 1.4 V to 3.6 V; see <u>Figure 6</u>								
	current	V _{CC} = 1.4 V to 3.6 V		-	-	±5	-	±50	±500	nA
		V _{CC} = 3.6 V to 4.3 V		-	-	±10	-	±50	±500	nA
I _{CC}	supply current	$V_1 = V_{CC}$ or GND; $V_{SW} = GND$ or V_{CC}								

NX3DV2567

All information provided in this document is subject to legal disclaimers.

^[2] Applies to control signal levels.


Low-ohmic four-pole double-throw analog switch

Table 7. Static characteristics...continued

At recommended operating conditions; voltages are referenced to GND (ground 0 V).


Symbol	Parameter	Conditions	Ta	_{imb} = 25	°C	T _{amb} =	-40 °C to	+125 °C	Unit
			Min	Тур	Max	Min	Max (85 °C)	Max (125 °C)	
		V _{CC} = 3.6 V	-	-	100	-	500	5000	nA
		V _{CC} = 4.3 V	-	-	150	-	800	6000	nA
ΔI_{CC}	additional	V _{SW} = GND or V _{CC}							
su	supply current	V _I = 2.6 V; V _{CC} = 4.3 V	-	2.0	4.0	-	7	7	μΑ
		V _I = 2.6 V; V _{CC} = 3.6 V	-	0.35	0.7	-	1	1	μΑ
		V _I = 1.8 V; V _{CC} = 4.3 V	-	7.0	10.0	-	15	15	μΑ
		V _I = 1.8 V; V _{CC} = 3.6 V	-	2.5	4.0	-	5	5	μΑ
		V _I = 1.8 V; V _{CC} = 2.5 V	-	50	200	-	300	500	nA
Cı	input capacitance		-	1	-	-	-	-	pF
C _{S(OFF)}	OFF-state	supply path switch	-	35	-	-	-	-	pF
	capacitance	data path switch	-	3	-	-	-	-	pF
C _{S(ON)}	ON-state	supply path switch	-	130	-	-	-	-	pF
сара	capacitance	data path switch	-	16	-	-	-	-	pF

10.1 Test circuits



 V_I = 0.3 V or V_{CC} - 0.3 V; V_O = V_{CC} - 0.3 V or 0.3 V.

Figure 5. Test circuit for measuring OFF-state leakage current



 $V_1 = 0.3 \text{ V or } V_{CC} - 0.3 \text{ V}; V_O = V_{CC} - 0.3 \text{ V or } 0.3 \text{ V}.$

Figure 6. Test circuit for measuring ON-state leakage current

NX3DV2567

All information provided in this document is subject to legal disclaimers.

Low-ohmic four-pole double-throw analog switch

10.2 ON resistance


Table 8. ON resistance

At recommended operating conditions; voltages are referenced to GND (ground = 0 V); for graphs see Figure 8 to Figure 13.

Symbol	Parameter	Conditions		T _{amb} =	-40 °C t	o +85 °C	T _{amb} = -40 °	°C to +125 °C	Unit
				Min	Typ ^[1]	Max	Min	Max	
Supply p	oath switch								
R _{ON}	ON resistance	V_I = GND to V_{CC} ; I_{SW} = 100 mA; see Figure 7							
		V _{CC} = 1.8 V; V _{SW} = 0 V, 1.8 V		-	0.5	0.75	-	0.85	Ω
		V _{CC} = 2.7 V; V _{SW} = 0 V, 2.3 V		-	0.45	0.7	-	0.8	Ω
ΔR _{ON}	ON resistance mismatch between channels	V_I = GND to V_{CC} ; I_{SW} = 100 mA	[2]						
		V _{CC} = 2.7 V; V _{SW} = 0 V		-	0.1	-	-	-	Ω
Data pat	h switches			ı	·		I	1	
R _{ON}	ON resistance	V_I = GND to V_{CC} ; I_{SW} = 20 mA; see <u>Figure 7</u>							
		V _{CC} = 1.8 V; V _{SW} = 0 V, 1.8 V		-	7.0	10.0	-	11.0	Ω
		V _{CC} = 2.7 V; V _{SW} = 0 V, 2.3 V		-	6.0	9.5	-	10.5	Ω
ΔR _{ON}	ON resistance	V_I = GND to V_{CC} ; I_{SW} = 20 mA	[2]						
	mismatch between channels	V _{CC} = 2.7 V; V _{SW} = 0 V		-	0.2	-	-	-	Ω

^[1] Typical values are measured at T_{amb} = 25 °C.


10.3 ON resistance test circuit and graphs



NX3DV2567


^[2] Measured at identical V_{CC}, temperature and input voltage.

Low-ohmic four-pole double-throw analog switch



- 1. V_{CC} = 1.8 V.
- 2. $V_{CC} = 2.7 \text{ V}.$


Figure 8. Typical ON resistance as a function of input voltage (supply path switch)



- 1. $T_{amb} = 125 \, ^{\circ}C$.
- 2. T_{amb} = 85 °C.
- 3. $T_{amb} = 25 \, ^{\circ}C$.
- 4. $T_{amb} = -40$ °C.


Figure 9. ON resistance as a function of input voltage; V_{CC} = 1.8 V (supply path switch)

Low-ohmic four-pole double-throw analog switch



- 1. T_{amb} = 125 °C.
- 2. $T_{amb} = 85 \,^{\circ}C$.
- 3. $T_{amb} = 25 \,^{\circ}C$.
- 4. T_{amb} = -40 °C.


Figure 10. ON resistance as a function of input voltage; V_{CC} = 2.7 V (supply path switch)



- 1. $V_{CC} = 1.8 V$.
- 2. $V_{CC} = 2.7 \text{ V}.$


Figure 11. Typical ON resistance as a function of input voltage (data path switch)

Low-ohmic four-pole double-throw analog switch



- 1. T_{amb} = 125 °C.
- 2. T_{amb} = 85 °C.
- 3. $T_{amb} = 25 \,^{\circ}C$.
- 4. $T_{amb} = -40$ °C.

Figure 12. ON resistance as a function of input voltage; $V_{CC} = 1.8 \text{ V}$ (data path switch)



- 1. $T_{amb} = 125 \, ^{\circ}C$.
- 2. T_{amb} = 85 °C.
- 3. $T_{amb} = 25 \,^{\circ}C$.
- 4. $T_{amb} = -40$ °C.

Figure 13. ON resistance as a function of input voltage; V_{CC} = 2.7 V (data path switch)

11 Dynamic characteristics

Table 9. Dynamic characteristics

At recommended operating conditions; voltages are referenced to GND (ground = 0 V); for load circuit see Figure 16.

Symbol	Parameter	Conditions			25 °C		-40	°C to +12	5 °C	Unit
				Min	Typ ^[1]	Max	Min	Max (85 °C)	Max (125 °C)	
Supply p	ath switch							1		
t _{en}	enable time	S to 1Z or 1Y0, 1Y1; see Figure 14								
		V _{CC} = 1.4 V to 1.6 V		-	41	90	-	120	120	ns
		V _{CC} = 1.65 V to 1.95 V		-	30	70	-	80	90	ns
		V _{CC} = 2.3 V to 2.7 V		-	20	45	-	50	55	ns
		V _{CC} = 2.7 V to 3.6 V		-	19	40	-	45	50	ns
		V _{CC} = 3.6 V to 4.3 V		-	19	40	-	45	50	ns
t _{dis}	disable time	S to 1Z or 1Y0, 1Y1; see Figure 14								
		V _{CC} = 1.4 V to 1.6 V		-	24	70	-	80	90	ns
		V _{CC} = 1.65 V to 1.95 V		-	15	55	-	60	65	ns
		V _{CC} = 2.3 V to 2.7 V		-	9	25	-	30	35	ns
		V _{CC} = 2.7 V to 3.6 V		-	8	20	-	25	30	ns
		V _{CC} = 3.6 V to 4.3 V		-	8	20	-	25	30	ns
t _{b-m}	break-before-make	see Figure 15	[2]							
	time	V _{CC} = 1.4 V to 1.6 V		-	20	-	9	-	-	ns
		V _{CC} = 1.65 V to 1.95 V		-	17	-	7	-	-	ns
		V _{CC} = 2.3 V to 2.7 V		-	13	-	4	-	-	ns
		V _{CC} = 2.7 V to 3.6 V		-	11	-	3	-	-	ns
		V _{CC} = 3.6 V to 4.3 V		-	11	-	2	-	-	ns
Data pat	h switch							'		
t _{en}	enable time	S to nZ or nYn; see Figure 14								
		V _{CC} = 1.4 V to 1.6 V		-	40	90	-	120	120	ns
		V _{CC} = 1.65 V to 1.95 V		-	29	70	-	80	90	ns
		V _{CC} = 2.3 V to 2.7 V		-	20	45	-	50	55	ns
		V _{CC} = 2.7 V to 3.6 V		-	19	40	-	45	50	ns
		V _{CC} = 3.6 V to 4.3 V		-	19	40	-	45	50	ns
t _{dis}	disable time	S to nZ or nYn; see Figure 14								

NX3DV2567

All information provided in this document is subject to legal disclaimers.

Low-ohmic four-pole double-throw analog switch


Table 9. Dynamic characteristics...continued

At recommended operating conditions; voltages are referenced to GND (ground = 0 V); for load circuit see Figure 16.

Symbol	Parameter	Conditions			25 °C		-40	°C to +12	5 °C	Unit
				Min	Typ ^[1]	Max	Min	Max (85 °C)	Max (125 °C)	-
		V _{CC} = 1.4 V to 1.6 V		-	21	70	-	80	90	ns
		V _{CC} = 1.65 V to 1.95 V		-	13	55	-	60	65	ns
		V _{CC} = 2.3 V to 2.7 V		-	8	25	-	30	35	ns
		V _{CC} = 2.7 V to 3.6 V		-	7	20	-	25	30	ns
		V _{CC} = 3.6 V to 4.3 V		-	7	20	-	25	30	ns
t _{b-m}	break-before-make	see Figure 15	[2]							
	time	V _{CC} = 1.4 V to 1.6 V		-	23	-	9	-	-	ns
		V _{CC} = 1.65 V to 1.95 V		-	19	-	7	-	-	ns
		V _{CC} = 2.3 V to 2.7 V		-	15	-	4	-	-	ns
		V _{CC} = 2.7 V to 3.6 V		-	13	-	3	-	-	ns
		V _{CC} = 3.6 V to 4.3 V		-	12	-	2	-	-	ns

Typical values are measured at T_{amb} = 25 °C and V_{CC} = 1.5 V, 1.8 V, 2.5 V, 3.3 V and 4.3 V respectively. Break-before-make guaranteed by design.

11.1 Waveform and test circuits



Measurement points are given in Table 10.

Logic level: V_{OH} is typical output voltage level that occurs with the output load.

Figure 14. Enable and disable times

Table 10. Measurement points


Supply voltage	Input	Output
V _{cc}	V _M	V _X
1.4 V to 4.3 V	0.5V _{CC}	0.9V _{OH}

NX3DV2567

All information provided in this document is subject to legal disclaimers.


^[2]

Low-ohmic four-pole double-throw analog switch




a. Test circuit





b. Input and output measurement points

Figure 15. Test circuit for measuring break-before-make timing



Test data is given in Table 11.

Definitions test circuit:

R_L = Load resistance.

 C_L = Load capacitance including jig and probe capacitance.

V_{EXT} = External voltage for measuring switching times.

Figure 16. Test circuit for measuring switching times

Table 11. Test data

Supply voltage	Input		Load	
V _{CC}	VI	t _r , t _f	CL	R _L
1.4 V to 4.3 V	V _{CC}	≤ 2.5 ns	35 pF	50 Ω

11.2 Additional dynamic characteristics


Table 12. Additional dynamic characteristics

At recommended operating conditions; voltages are referenced to GND (ground = 0 V); V_I = GND or V_{CC} (unless otherwise specified); t_r = t_f \leq 2.5 ns; T_{amb} = 25 °C.

Symbol	Parameter	Conditions		Min	Тур	Max	Unit
Data pat	h switch						
f _(-3dB)	-3 dB frequency response	R_L = 50 Ω; see <u>Figure 17</u>	[1]				
		V _{CC} = 2.7 V to 3.6 V		-	330	-	MHz
α_{iso}	isolation (OFF-state)	f_i = 10 MHz; R_L = 50 Ω; see <u>Figure 18</u>	[1]				
		V _{CC} = 2.7 V to 3.6 V		-	-60	-	dB
Xtalk	crosstalk	between switches; f_i = 10 MHz; R_L = 50 Ω ; see Figure 19	[1]				
		V _{CC} = 2.7 V to 3.6 V		-	-60	-	dB
Q _{inj}	charge injection	f_i = 1 MHz; C_L = 0.1 nF; R_L = 1 M Ω ; V_{gen} = 0 V; R_{gen} = 0 Ω ; see <u>Figure 20</u>					
		V _{CC} = 2.7 V to 3.6 V		-	10	-	рС


[1] f_i is biased at 0.5V_{CC}.

11.3 Test circuits



Adjust f_i voltage to obtain 0 dBm level at output. Increase f_i frequency until dB meter reads -3 dB.

Figure 17. Test circuit for measuring the frequency response when channel is in ON-state




Adjust fi voltage to obtain 0 dBm level at input.

Figure 18. Test circuit for measuring isolation (OFF-state)

NX3DV2567


All information provided in this document is subject to legal disclaimers.

Low-ohmic four-pole double-throw analog switch




20 \log_{10} (V_{O2} / V_{O1}) or 20 \log_{10} (V_{O1} / V_{O2}).

Figure 19. Test circuit for measuring crosstalk between switches



a. Test circuit



Definition: $Q_{inj} = \Delta V_O \times C_L$.

 ΔV_{O} = output voltage variation.

 R_{gen} = generator resistance.


V_{gen} = generator voltage.

b. Input and output pulse definitions


Figure 20. Test circuit for measuring charge injection

Low-ohmic four-pole double-throw analog switch

12 Package outline



Low-ohmic four-pole double-throw analog switch



NX3DV2567

Low-ohmic four-pole double-throw analog switch

13 Abbreviations

Table 13. Abbreviations

Acronym	Description
CDM	Charged Device Model
CMOS	Complementary Metal-Oxide Semiconductor
ESD	ElectroStatic Discharge
НВМ	Human Body Model
MM	Machine Model
PDA	Personal Digital Assistant
TTL	Transistor-Transistor Logic

14 Revision history

Table 14. Revision history

Document ID	Release date	Data sheet status	Change notice	Supersedes
NX3DV2567 v.2.1	20231004	Product data sheet	-	NX3DV2567 v.2
Modifications:	Replaced SOT1	039-1 with SOT1039-2.		
NX3DV2567 v.2	20111109	Product data sheet	-	NX3DV2567 v.1
NX3DV2567 v.1	20100928	Product data sheet	-	-

15 Legal information

15.1 Data sheet status

Document status ^{[1][2]}	Product status ^[3]	Definition
Objective [short] data sheet	Development	This document contains data from the objective specification for product development.
Preliminary [short] data sheet	Qualification	This document contains data from the preliminary specification.
Product [short] data sheet	Production	This document contains the product specification.

- [1] Please consult the most recently issued document before initiating or completing a design.
- [2] The term 'short data sheet' is explained in section "Definitions".
- [3] The product status of device(s) described in this document may have changed since this document was published and may differ in case of multiple devices. The latest product status information is available on the Internet at URL https://www.nxp.com.

15.2 Definitions

Draft — A draft status on a document indicates that the content is still under internal review and subject to formal approval, which may result in modifications or additions. NXP Semiconductors does not give any representations or warranties as to the accuracy or completeness of information included in a draft version of a document and shall have no liability for the consequences of use of such information.

Short data sheet — A short data sheet is an extract from a full data sheet with the same product type number(s) and title. A short data sheet is intended for quick reference only and should not be relied upon to contain detailed and full information. For detailed and full information see the relevant full data sheet, which is available on request via the local NXP Semiconductors sales office. In case of any inconsistency or conflict with the short data sheet, the full data sheet shall prevail.

Product specification — The information and data provided in a Product data sheet shall define the specification of the product as agreed between NXP Semiconductors and its customer, unless NXP Semiconductors and customer have explicitly agreed otherwise in writing. In no event however, shall an agreement be valid in which the NXP Semiconductors product is deemed to offer functions and qualities beyond those described in the Product data sheet.

15.3 Disclaimers

Limited warranty and liability — Information in this document is believed to be accurate and reliable. However, NXP Semiconductors does not give any representations or warranties, expressed or implied, as to the accuracy or completeness of such information and shall have no liability for the consequences of use of such information. NXP Semiconductors takes no responsibility for the content in this document if provided by an information source outside of NXP Semiconductors.

In no event shall NXP Semiconductors be liable for any indirect, incidental, punitive, special or consequential damages (including - without limitation - lost profits, lost savings, business interruption, costs related to the removal or replacement of any products or rework charges) whether or not such damages are based on tort (including negligence), warranty, breach of contract or any other legal theory.

Notwithstanding any damages that customer might incur for any reason whatsoever, NXP Semiconductors' aggregate and cumulative liability towards customer for the products described herein shall be limited in accordance with the Terms and conditions of commercial sale of NXP Semiconductors.

Right to make changes — NXP Semiconductors reserves the right to make changes to information published in this document, including without limitation specifications and product descriptions, at any time and without notice. This document supersedes and replaces all information supplied prior to the publication hereof.

Suitability for use — NXP Semiconductors products are not designed, authorized or warranted to be suitable for use in life support, life-critical or safety-critical systems or equipment, nor in applications where failure or malfunction of an NXP Semiconductors product can reasonably be expected to result in personal injury, death or severe property or environmental damage. NXP Semiconductors and its suppliers accept no liability for inclusion and/or use of NXP Semiconductors products in such equipment or applications and therefore such inclusion and/or use is at the customer's own risk

Applications — Applications that are described herein for any of these products are for illustrative purposes only. NXP Semiconductors makes no representation or warranty that such applications will be suitable for the specified use without further testing or modification.

Customers are responsible for the design and operation of their applications and products using NXP Semiconductors products, and NXP Semiconductors accepts no liability for any assistance with applications or customer product design. It is customer's sole responsibility to determine whether the NXP Semiconductors product is suitable and fit for the customer's applications and products planned, as well as for the planned application and use of customer's third party customer(s). Customers should provide appropriate design and operating safeguards to minimize the risks associated with their applications and products.

NXP Semiconductors does not accept any liability related to any default, damage, costs or problem which is based on any weakness or default in the customer's applications or products, or the application or use by customer's third party customer(s). Customer is responsible for doing all necessary testing for the customer's applications and products using NXP Semiconductors products in order to avoid a default of the applications and the products or of the application or use by customer's third party customer(s). NXP does not accept any liability in this respect.

Limiting values — Stress above one or more limiting values (as defined in the Absolute Maximum Ratings System of IEC 60134) will cause permanent damage to the device. Limiting values are stress ratings only and (proper) operation of the device at these or any other conditions above those given in the Recommended operating conditions section (if present) or the Characteristics sections of this document is not warranted. Constant or repeated exposure to limiting values will permanently and irreversibly affect the quality and reliability of the device.

Terms and conditions of commercial sale — NXP Semiconductors products are sold subject to the general terms and conditions of commercial sale, as published at http://www.nxp.com/profile/terms, unless otherwise agreed in a valid written individual agreement. In case an individual agreement is concluded only the terms and conditions of the respective agreement shall apply. NXP Semiconductors hereby expressly objects to applying the customer's general terms and conditions with regard to the purchase of NXP Semiconductors products by customer.

No offer to sell or license — Nothing in this document may be interpreted or construed as an offer to sell products that is open for acceptance or the grant, conveyance or implication of any license under any copyrights, patents or other industrial or intellectual property rights.

NX3DV2567

All information provided in this document is subject to legal disclaimers.

Low-ohmic four-pole double-throw analog switch

Quick reference data — The Quick reference data is an extract of the product data given in the Limiting values and Characteristics sections of this document, and as such is not complete, exhaustive or legally binding.

Export control — This document as well as the item(s) described herein may be subject to export control regulations. Export might require a prior authorization from competent authorities.

Suitability for use in non-automotive qualified products — Unless this document expressly states that this specific NXP Semiconductors product is automotive qualified, the product is not suitable for automotive use. It is neither qualified nor tested in accordance with automotive testing or application requirements. NXP Semiconductors accepts no liability for inclusion and/or use of non-automotive qualified products in automotive equipment or applications.

In the event that customer uses the product for design-in and use in automotive applications to automotive specifications and standards, customer (a) shall use the product without NXP Semiconductors' warranty of the product for such automotive applications, use and specifications, and (b) whenever customer uses the product for automotive applications beyond NXP Semiconductors' specifications such use shall be solely at customer's own risk, and (c) customer fully indemnifies NXP Semiconductors for any liability, damages or failed product claims resulting from customer design and use of the product for automotive applications beyond NXP Semiconductors' standard warranty and NXP Semiconductors' product specifications.

Translations — A non-English (translated) version of a document, including the legal information in that document, is for reference only. The English version shall prevail in case of any discrepancy between the translated and English versions.

Security — Customer understands that all NXP products may be subject to unidentified vulnerabilities or may support established security standards or specifications with known limitations. Customer is responsible for the design and operation of its applications and products throughout their lifecycles to reduce the effect of these vulnerabilities on customer's applications and products. Customer's responsibility also extends to other open and/or proprietary technologies supported by NXP products for use in customer's applications. NXP accepts no liability for any vulnerability. Customer should regularly check security updates from NXP and follow up appropriately. Customer shall select products with security features that best meet rules, regulations, and standards of the intended application and make the ultimate design decisions regarding its products and is solely responsible for compliance with all legal, regulatory, and security related requirements concerning its products, regardless of any information or support that may be provided by NXP.

NXP has a Product Security Incident Response Team (PSIRT) (reachable at PSIRT@nxp.com) that manages the investigation, reporting, and solution release to security vulnerabilities of NXP products.

15.4 Trademarks

Notice: All referenced brands, product names, service names, and trademarks are the property of their respective owners.

NXP — wordmark and logo are trademarks of NXP B.V.

Low-ohmic four-pole double-throw analog switch

Tables

Tab. 1. Tab. 2. Tab. 3. Tab. 4. Tab. 5. Tab. 6. Tab. 7.	Ordering information2Ordering options2Pin description3Function table4Limiting values4Recommended operating conditions5Static characteristics5	Tab. 8. Tab. 9. Tab. 10. Tab. 11. Tab. 12. Tab. 13. Tab. 14.	ON resistance Dynamic characteristics Measurement points Test data Additional dynamic characteristics Abbreviations Revision history	11 12 13 14 18
Figur			•	
Fig. 1.	Logic symbol2	Fig. 12.	ON resistance as a function of input	
Fig. 2.	Logic diagram (one switch)2		voltage; VCC = 1.8 V (data path switch)	. 10
Fig. 3.	Pin configuration SOT1039-2	Fig. 13.	ON resistance as a function of input	
	(HXQFN16(U))3		voltage; VCC = 2.7 V (data path switch)	
Fig. 4.	Pin configuration SOT1161-1 (XQFN16)3	Fig. 14.	Enable and disable times	12
Fig. 5.	Test circuit for measuring OFF-state	Fig. 15.	Test circuit for measuring break-before-	
	leakage current6		make timing	13
Fig. 6.	Test circuit for measuring ON-state leakage	Fig. 16.	Test circuit for measuring switching times	13
	current6	Fig. 17.	Test circuit for measuring the frequency	
Fig. 7.	Test circuit for measuring ON resistance7		response when channel is in ON-state	14
Fig. 8.	Typical ON resistance as a function of input	Fig. 18.	Test circuit for measuring isolation (OFF-	
	voltage (supply path switch)8		state)	14
Fig. 9.	ON resistance as a function of input	Fig. 19.	Test circuit for measuring crosstalk	
	voltage; VCC = 1.8 V (supply path switch)8		between switches	
Fig. 10.	ON resistance as a function of input	Fig. 20.	Test circuit for measuring charge injection	15
	voltage; VCC = 2.7 V (supply path switch)9	Fig. 21.	Package outline SOT1039-2	
Fig. 11.	Typical ON resistance as a function of input		(HXQFN16(U))	
	voltage (data path switch)9	Fig. 22.	Package outline SOT1161-1 (XQFN16)	. 17

Contents

1	General description	1
2	Features and benefits	
3	Applications	
4	Ordering information	
4.1	Ordering options	2
5	Functional diagram	2
6	Pinning information	
6.1	Pinning	
6.2	Pin description	
7	Functional description	4
8	Limiting values	
9	Recommended operating conditions	
10	Static characteristics	
10.1	Test circuits	
10.2	ON resistance	7
10.3	ON resistance test circuit and graphs	7
11	Dynamic characteristics	
11.1	Waveform and test circuits	
11.2	Additional dynamic characteristics	14
11.3	Test circuits	
12	Package outline	16
13	Abbreviations	
14	Revision history	18
15	Legal information	

Please be aware that important notices concerning this document and the product(s) described herein, have been included in section 'Legal information'.