

# 74AUP2G157

## Low-power 2-input multiplexer

Rev. 03 — 2 July 2008

Product data sheet

## 1. General description

The 74AUP2G157 is a high-performance, low-power, low-voltage, Si-gate CMOS device, superior to most advanced CMOS compatible TTL families.

Schmitt trigger action at all inputs makes the circuit tolerant to slower input rise and fall times across the entire  $V_{CC}$  range from 0.8 V to 3.6 V. This device ensures a very low static and dynamic power consumption across the entire  $V_{CC}$  range from 0.8 V to 3.6 V.

This device is fully specified for partial power-down applications using  $I_{OFF}$ . The  $I_{OFF}$  circuitry disables the output, preventing the damaging backflow current through the device when it is powered down.

The 74AUP2G157 is a single 2-input multiplexer which select data from two data inputs (I0 and I1) under control of a common data select input (S). The state of the common data select input determines the particular register from which the data comes. The output (Y,  $\bar{Y}$ ) presents the selected data in the true (non-inverted) and complement form. The enable input ( $\bar{E}$ ) is active LOW. When  $\bar{E}$  is HIGH, the output Y is forced LOW and the output  $\bar{Y}$  is forced HIGH regardless of all other input conditions.

## 2. Features

- Wide supply voltage range from 0.8 V to 3.6 V
- High noise immunity
- Complies with JEDEC standards:
  - ◆ JESD8-12 (0.8 V to 1.3 V)
  - ◆ JESD8-11 (0.9 V to 1.65 V)
  - ◆ JESD8-7 (1.2 V to 1.95 V)
  - ◆ JESD8-5 (1.8 V to 2.7 V)
  - ◆ JESD8-B (2.7 V to 3.6 V)
- ESD protection:
  - ◆ HBM JESD22-A114E Class 3A exceeds 5000 V
  - ◆ MM JESD22-A115-A exceeds 200 V
  - ◆ CDM JESD22-C101C exceeds 1000 V
- Low static power consumption;  $I_{CC} = 0.9 \mu\text{A}$  (maximum)
- Latch-up performance exceeds 100 mA per JESD 78 Class II
- Inputs accept voltages up to 3.6 V
- Low noise overshoot and undershoot < 10 % of  $V_{CC}$
- $I_{OFF}$  circuitry provides partial Power-down mode operation
- Multiple package options
- Specified from  $-40 \text{ }^\circ\text{C}$  to  $+85 \text{ }^\circ\text{C}$  and  $-40 \text{ }^\circ\text{C}$  to  $+125 \text{ }^\circ\text{C}$

### 3. Ordering information

Table 1. Ordering information

| Type number  | Package           |        |  | Version  |
|--------------|-------------------|--------|--|----------|
|              | Temperature range | Name   | Description  |          |
| 74AUP2G157DC | -40 °C to +125 °C | VSSOP8 | plastic very thin shrink small outline package; 8 leads; body width 2.3 mm                           | SOT765-1 |
| 74AUP2G157GT | -40 °C to +125 °C | XSON8  | plastic extremely thin small outline package; no leads; 8 terminals; body 1 × 1.95 × 0.5 mm          | SOT833-1 |
| 74AUP2G157GD | -40 °C to +125 °C | XSON8U | plastic extremely thin small outline package; no leads; 8 terminals; UTLP based; body 3 × 2 × 0.5 mm | SOT996-2 |
| 74AUP2G157GM | -40 °C to +125 °C | XQFN8U | plastic extremely thin quad flat package; no leads; 8 terminals; UTLP based; body 1.6 × 1.6 × 0.5 mm | SOT902-1 |

### 4. Marking

Table 2. Marking codes

| Type number  | Marking code |
|--------------|--------------|
| 74AUP2G157DC | a2P          |
| 74AUP2G157GT | a2P          |
| 74AUP2G157GD | a2P          |
| 74AUP2G157GM | a2P          |

### 5. Functional diagram




Fig 1. Logic symbol




Fig 2. IEC logic symbol




Fig 3. Logic diagram






Fig 4. Functional diagram

## 6. Pinning information

### 6.1 Pinning



### 6.2 Pin description

**Table 3. Pin description**

| Symbol    | Pin                             |          | Description                   |
|-----------|---------------------------------|----------|-------------------------------|
|           | SOT765-1, SOT833-1 and SOT996-2 | SOT902-1 |                               |
| I0        | 1                               | 7        | data input from source 0      |
| I1        | 2                               | 6        | data input from source 1      |
| $\bar{Y}$ | 3                               | 5        | complement multiplexer output |
| GND       | 4                               | 4        | ground (0 V)                  |
| Y         | 5                               | 3        | true multiplexer output       |

Table 3. Pin description ...continued

| Symbol          | Pin                             |          | Description               |
|-----------------|---------------------------------|----------|---------------------------|
|                 | SOT765-1, SOT833-1 and SOT996-2 | SOT902-1 |                           |
| S               | 6                               | 2        | data select input         |
| $\bar{E}$       | 7                               | 1        | enable input (active LOW) |
| V <sub>CC</sub> | 8                               | 8        | supply voltage            |

## 7. Functional description

Table 4. Function table<sup>[1]</sup>

| Input     |   |    |    | Output |           |
|-----------|---|----|----|--------|-----------|
| $\bar{E}$ | S | I0 | I1 | Y      | $\bar{Y}$ |
| H         | X | X  | X  | L      | H         |
| L         | L | L  | X  | L      | H         |
| L         | L | H  | X  | H      | L         |
| L         | H | X  | L  | L      | H         |
| L         | H | X  | H  | H      | L         |

[1] H = HIGH voltage level; L = LOW voltage level; X = don't care.

## 8. Limiting values

Table 5. Limiting values

In accordance with the Absolute Maximum Rating System (IEC 60134). Voltages are referenced to GND (ground = 0 V).

| Symbol           | Parameter               | Conditions                              | Min                 | Max  | Unit |
|------------------|-------------------------|---|---------------------|------|------|
| V <sub>CC</sub>  | supply voltage          |   | -0.5                | +4.6 | V    |
| I <sub>IK</sub>  | input clamping current  | V <sub>I</sub> < 0 V                    | -50                 | -    | mA   |
| V <sub>I</sub>   | input voltage           |   | <sup>[1]</sup> -0.5 | +4.6 | V    |
| I <sub>OK</sub>  | output clamping current | V <sub>O</sub> < 0 V                    | -50                 | -    | mA   |
| V <sub>O</sub>   | output voltage          | Active mode and Power-down mode         | <sup>[1]</sup> -0.5 | +4.6 | V    |
| I <sub>O</sub>   | output current          | V <sub>O</sub> = 0 V to V <sub>CC</sub> | -                   | ±20  | mA   |
| I <sub>CC</sub>  | supply current          |   | -                   | 50   | mA   |
| I <sub>GND</sub> | ground current          |   | -50                 | -    | mA   |
| T <sub>stg</sub> | storage temperature     |   | -65                 | +150 | °C   |
| P <sub>tot</sub> | total power dissipation | T <sub>amb</sub> = -40 °C to +125 °C    | <sup>[2]</sup> -    | 250  | mW   |

[1] The minimum input and output voltage ratings may be exceeded if the input and output current ratings are observed.

[2] For VSSOP8 packages: above 110 °C the value of P<sub>tot</sub> derates linearly with 8.0 mW/K.

For XSON8, XSON8U and XQFN8U packages: above 45 °C the value of P<sub>tot</sub> derates linearly with 2.4 mW/K.

## 9. Recommended operating conditions

**Table 6. Operating conditions**

| Symbol              | Parameter                           | Conditions                      | Min | Max      | Unit |
|---------------------|-------------------------------------|---------------------------------|-----|----------|------|
| $V_{CC}$            | supply voltage                      |                                 | 0.8 | 3.6      | V    |
| $V_I$               | input voltage                       |                                 | 0   | 3.6      | V    |
| $V_O$               | output voltage                      | Active mode                     | 0   | $V_{CC}$ | V    |
|                     |                                     | Power-down mode; $V_{CC} = 0$ V | 0   | 3.6      | V    |
| $T_{amb}$           | ambient temperature                 |                                 | -40 | +125     | °C   |
| $\Delta t/\Delta V$ | input transition rise and fall rate | $V_{CC} = 0.8$ V to 3.6 V       | 0   | 200      | ns/V |

## 10. Static characteristics

**Table 7. Static characteristics**

At recommended operating conditions; voltages are referenced to GND (ground = 0 V).

| Symbol                              | Parameter                        | Conditions                                     | Min                  | Typ  | Max                  | Unit |
|-------------------------------------|----------------------------------|--|----------------------|------|----------------------|------|
| <b><math>T_{amb} = 25</math> °C</b> |                                  |  |                      |      |                      |      |
| $V_{IH}$                            | HIGH-level input voltage         | $V_{CC} = 0.8$ V                               | $0.70 \times V_{CC}$ | -    | -                    | V    |
|                                     |                                  | $V_{CC} = 0.9$ V to 1.95 V                     | $0.65 \times V_{CC}$ | -    | -                    | V    |
|                                     |                                  | $V_{CC} = 2.3$ V to 2.7 V                      | 1.6                  | -    | -                    | V    |
|                                     |                                  | $V_{CC} = 3.0$ V to 3.6 V                      | 2.0                  | -    | -                    | V    |
| $V_{IL}$                            | LOW-level input voltage          | $V_{CC} = 0.8$ V                               | -                    | -    | $0.30 \times V_{CC}$ | V    |
|                                     |                                  | $V_{CC} = 0.9$ V to 1.95 V                     | -                    | -    | $0.35 \times V_{CC}$ | V    |
|                                     |                                  | $V_{CC} = 2.3$ V to 2.7 V                      | -                    | -    | 0.7                  | V    |
|                                     |                                  | $V_{CC} = 3.0$ V to 3.6 V                      | -                    | -    | 0.9                  | V    |
| $V_{OH}$                            | HIGH-level output voltage        | $V_I = V_{IH}$ or $V_{IL}$                     |                      |      |                      |      |
|                                     |                                  | $I_O = -20$ $\mu$ A; $V_{CC} = 0.8$ V to 3.6 V | $V_{CC} - 0.1$       | -    | -                    | V    |
|                                     |                                  | $I_O = -1.1$ mA; $V_{CC} = 1.1$ V              | $0.75 \times V_{CC}$ | -    | -                    | V    |
|                                     |                                  | $I_O = -1.7$ mA; $V_{CC} = 1.4$ V              | 1.11                 | -    | -                    | V    |
|                                     |                                  | $I_O = -1.9$ mA; $V_{CC} = 1.65$ V             | 1.32                 | -    | -                    | V    |
|                                     |                                  | $I_O = -2.3$ mA; $V_{CC} = 2.3$ V              | 2.05                 | -    | -                    | V    |
|                                     |                                  | $I_O = -3.1$ mA; $V_{CC} = 2.3$ V              | 1.9                  | -    | -                    | V    |
|                                     |                                  | $I_O = -2.7$ mA; $V_{CC} = 3.0$ V              | 2.72                 | -    | -                    | V    |
| $V_{OL}$                            | LOW-level output voltage         | $V_I = V_{IH}$ or $V_{IL}$                     |                      |      |                      |      |
|                                     |                                  | $I_O = 20$ $\mu$ A; $V_{CC} = 0.8$ V to 3.6 V  | -                    | -    | 0.1                  | V    |
|                                     |                                  | $I_O = 1.1$ mA; $V_{CC} = 1.1$ V               | -                    | -    | $0.3 \times V_{CC}$  | V    |
|                                     |                                  | $I_O = 1.7$ mA; $V_{CC} = 1.4$ V               | -                    | -    | 0.31                 | V    |
|                                     |                                  | $I_O = 1.9$ mA; $V_{CC} = 1.65$ V              | -                    | -    | 0.31                 | V    |
|                                     |                                  | $I_O = 2.3$ mA; $V_{CC} = 2.3$ V               | -                    | -    | 0.31                 | V    |
|                                     |                                  | $I_O = 3.1$ mA; $V_{CC} = 2.3$ V               | -                    | -    | 0.44                 | V    |
|                                     |                                  | $I_O = 2.7$ mA; $V_{CC} = 3.0$ V               | -                    | -    | 0.31                 | V    |
|                                     | $I_O = 4.0$ mA; $V_{CC} = 3.0$ V | -  | -                    | 0.44 | V                    |      |

**Table 7. Static characteristics ...continued**

At recommended operating conditions; voltages are referenced to GND (ground = 0 V).

| Symbol                  | Parameter                            | Conditions  | Min | Typ | Max       | Unit          |
|-------------------------|--------------------------------------|---|-----|-----|-----------|---------------|
| $I_I$                   | input leakage current                | $V_I = \text{GND to } 3.6 \text{ V}; V_{CC} = 0 \text{ V to } 3.6 \text{ V}$                  | -   | -   | $\pm 0.1$ | $\mu\text{A}$ |
| $I_{\text{OFF}}$        | power-off leakage current            | $V_I \text{ or } V_O = 0 \text{ V to } 3.6 \text{ V}; V_{CC} = 0 \text{ V}$                   | -   | -   | $\pm 0.2$ | $\mu\text{A}$ |
| $\Delta I_{\text{OFF}}$ | additional power-off leakage current | $V_I \text{ or } V_O = 0 \text{ V to } 3.6 \text{ V}; V_{CC} = 0 \text{ V to } 0.2 \text{ V}$ | -   | -   | $\pm 0.2$ | $\mu\text{A}$ |
| $I_{CC}$                | supply current                       | $V_I = \text{GND or } V_{CC}; I_O = 0 \text{ A}; V_{CC} = 0.8 \text{ V to } 3.6 \text{ V}$    | -   | -   | 0.5       | $\mu\text{A}$ |
| $\Delta I_{CC}$         | additional supply current            | $V_I = V_{CC} - 0.6 \text{ V}; I_O = 0 \text{ A}; V_{CC} = 3.3 \text{ V}$                     | [1] | -   | 40        | $\mu\text{A}$ |
| $C_I$                   | input capacitance                    | $V_{CC} = 0 \text{ V to } 3.6 \text{ V}; V_I = \text{GND or } V_{CC}$                         | -   | 0.6 | -         | pF            |
| $C_O$                   | output capacitance                   | $V_O = \text{GND}; V_{CC} = 0 \text{ V}$  | -   | 1.3 | -         | pF            |

**$T_{\text{amb}} = -40 \text{ }^\circ\text{C to } +85 \text{ }^\circ\text{C}$**

|   |                                      |   |                      |   |                      |               |
|---|--------------------------------------|---|----------------------|---|----------------------|---------------|
| $V_{IH}$  | HIGH-level input voltage             | $V_{CC} = 0.8 \text{ V}$  | $0.70 \times V_{CC}$ | - | -                    | V             |
|   |                                      | $V_{CC} = 0.9 \text{ V to } 1.95 \text{ V}$   | $0.65 \times V_{CC}$ | - | -                    | V             |
|   |                                      | $V_{CC} = 2.3 \text{ V to } 2.7 \text{ V}$  | 1.6                  | - | -                    | V             |
|   |                                      | $V_{CC} = 3.0 \text{ V to } 3.6 \text{ V}$  | 2.0                  | - | -                    | V             |
| $V_{IL}$  | LOW-level input voltage              | $V_{CC} = 0.8 \text{ V}$  | -                    | - | $0.30 \times V_{CC}$ | V             |
|   |                                      | $V_{CC} = 0.9 \text{ V to } 1.95 \text{ V}$   | -                    | - | $0.35 \times V_{CC}$ | V             |
|   |                                      | $V_{CC} = 2.3 \text{ V to } 2.7 \text{ V}$  | -                    | - | 0.7                  | V             |
|   |                                      | $V_{CC} = 3.0 \text{ V to } 3.6 \text{ V}$  | -                    | - | 0.9                  | V             |
| $V_{OH}$  | HIGH-level output voltage            | $V_I = V_{IH} \text{ or } V_{IL}$   |                      |   |                      |               |
|   |                                      | $I_O = -20 \mu\text{A}; V_{CC} = 0.8 \text{ V to } 3.6 \text{ V}$                             | $V_{CC} - 0.1$       | - | -                    | V             |
|   |                                      | $I_O = -1.1 \text{ mA}; V_{CC} = 1.1 \text{ V}$   | $0.7 \times V_{CC}$  | - | -                    | V             |
|   |                                      | $I_O = -1.7 \text{ mA}; V_{CC} = 1.4 \text{ V}$   | 1.03                 | - | -                    | V             |
|   |                                      | $I_O = -1.9 \text{ mA}; V_{CC} = 1.65 \text{ V}$  | 1.30                 | - | -                    | V             |
|   |                                      | $I_O = -2.3 \text{ mA}; V_{CC} = 2.3 \text{ V}$   | 1.97                 | - | -                    | V             |
|   |                                      | $I_O = -3.1 \text{ mA}; V_{CC} = 2.3 \text{ V}$   | 1.85                 | - | -                    | V             |
|   |                                      | $I_O = -2.7 \text{ mA}; V_{CC} = 3.0 \text{ V}$   | 2.67                 | - | -                    | V             |
| $I_O = -4.0 \text{ mA}; V_{CC} = 3.0 \text{ V}$ | 2.55                                 | -   | -                    | V |                      |               |
| $V_{OL}$  | LOW-level output voltage             | $V_I = V_{IH} \text{ or } V_{IL}$   |                      |   |                      |               |
|   |                                      | $I_O = 20 \mu\text{A}; V_{CC} = 0.8 \text{ V to } 3.6 \text{ V}$                              | -                    | - | 0.1                  | V             |
|   |                                      | $I_O = 1.1 \text{ mA}; V_{CC} = 1.1 \text{ V}$  | -                    | - | $0.3 \times V_{CC}$  | V             |
|   |                                      | $I_O = 1.7 \text{ mA}; V_{CC} = 1.4 \text{ V}$  | -                    | - | 0.37                 | V             |
|   |                                      | $I_O = 1.9 \text{ mA}; V_{CC} = 1.65 \text{ V}$   | -                    | - | 0.35                 | V             |
|   |                                      | $I_O = 2.3 \text{ mA}; V_{CC} = 2.3 \text{ V}$  | -                    | - | 0.33                 | V             |
|   |                                      | $I_O = 3.1 \text{ mA}; V_{CC} = 2.3 \text{ V}$  | -                    | - | 0.45                 | V             |
|   |                                      | $I_O = 2.7 \text{ mA}; V_{CC} = 3.0 \text{ V}$  | -                    | - | 0.33                 | V             |
| $I_O = 4.0 \text{ mA}; V_{CC} = 3.0 \text{ V}$  | -                                    | -   | 0.45                 | V |                      |               |
| $I_I$   | input leakage current                | $V_I = \text{GND to } 3.6 \text{ V}; V_{CC} = 0 \text{ V to } 3.6 \text{ V}$                  | -                    | - | $\pm 0.5$            | $\mu\text{A}$ |
| $I_{\text{OFF}}$                                | power-off leakage current            | $V_I \text{ or } V_O = 0 \text{ V to } 3.6 \text{ V}; V_{CC} = 0 \text{ V}$                   | -                    | - | $\pm 0.5$            | $\mu\text{A}$ |
| $\Delta I_{\text{OFF}}$                         | additional power-off leakage current | $V_I \text{ or } V_O = 0 \text{ V to } 3.6 \text{ V}; V_{CC} = 0 \text{ V to } 0.2 \text{ V}$ | -                    | - | $\pm 0.6$            | $\mu\text{A}$ |

**Table 7. Static characteristics ...continued**

At recommended operating conditions; voltages are referenced to GND (ground = 0 V).

| Symbol                                     | Parameter                            | Conditions  | Min                    | Typ | Max                    | Unit |
|--|--------------------------------------|---|------------------------|-----|------------------------|------|
| I <sub>CC</sub>                            | supply current                       | V <sub>I</sub> = GND or V <sub>CC</sub> ; I <sub>O</sub> = 0 A;<br>V <sub>CC</sub> = 0.8 V to 3.6 V | -                      | -   | 0.9                    | μA   |
| ΔI <sub>CC</sub>                           | additional supply current            | V <sub>I</sub> = V <sub>CC</sub> - 0.6 V; I <sub>O</sub> = 0 A;<br>V <sub>CC</sub> = 3.3 V          | [1]                    | -   | 50                     | μA   |
| <b>T<sub>amb</sub> = -40 °C to +125 °C</b> |                                      |   |                        |     |                        |      |
| V <sub>IH</sub>                            | HIGH-level input voltage             | V <sub>CC</sub> = 0.8 V   | 0.75 × V <sub>CC</sub> | -   | -                      | V    |
|  |                                      | V <sub>CC</sub> = 0.9 V to 1.95 V   | 0.70 × V <sub>CC</sub> | -   | -                      | V    |
|  |                                      | V <sub>CC</sub> = 2.3 V to 2.7 V  | 1.6                    | -   | -                      | V    |
|  |                                      | V <sub>CC</sub> = 3.0 V to 3.6 V  | 2.0                    | -   | -                      | V    |
| V <sub>IL</sub>                            | LOW-level input voltage              | V <sub>CC</sub> = 0.8 V   | -                      | -   | 0.25 × V <sub>CC</sub> | V    |
|  |                                      | V <sub>CC</sub> = 0.9 V to 1.95 V   | -                      | -   | 0.30 × V <sub>CC</sub> | V    |
|  |                                      | V <sub>CC</sub> = 2.3 V to 2.7 V  | -                      | -   | 0.7                    | V    |
|  |                                      | V <sub>CC</sub> = 3.0 V to 3.6 V  | -                      | -   | 0.9                    | V    |
| V <sub>OH</sub>                            | HIGH-level output voltage            | V <sub>I</sub> = V <sub>IH</sub> or V <sub>IL</sub>   |                        |     |                        |      |
|  |                                      | I <sub>O</sub> = -20 μA; V <sub>CC</sub> = 0.8 V to 3.6 V   | V <sub>CC</sub> - 0.11 | -   | -                      | V    |
|  |                                      | I <sub>O</sub> = -1.1 mA; V <sub>CC</sub> = 1.1 V   | 0.6 × V <sub>CC</sub>  | -   | -                      | V    |
|  |                                      | I <sub>O</sub> = -1.7 mA; V <sub>CC</sub> = 1.4 V   | 0.93                   | -   | -                      | V    |
|  |                                      | I <sub>O</sub> = -1.9 mA; V <sub>CC</sub> = 1.65 V  | 1.17                   | -   | -                      | V    |
|  |                                      | I <sub>O</sub> = -2.3 mA; V <sub>CC</sub> = 2.3 V   | 1.77                   | -   | -                      | V    |
|  |                                      | I <sub>O</sub> = -3.1 mA; V <sub>CC</sub> = 2.3 V   | 1.67                   | -   | -                      | V    |
|  |                                      | I <sub>O</sub> = -2.7 mA; V <sub>CC</sub> = 3.0 V   | 2.40                   | -   | -                      | V    |
| V <sub>OL</sub>                            | LOW-level output voltage             | V <sub>I</sub> = V <sub>IH</sub> or V <sub>IL</sub>   |                        |     |                        |      |
|  |                                      | I <sub>O</sub> = 20 μA; V <sub>CC</sub> = 0.8 V to 3.6 V  | -                      | -   | 0.11                   | V    |
|  |                                      | I <sub>O</sub> = 1.1 mA; V <sub>CC</sub> = 1.1 V  | -                      | -   | 0.33 × V <sub>CC</sub> | V    |
|  |                                      | I <sub>O</sub> = 1.7 mA; V <sub>CC</sub> = 1.4 V  | -                      | -   | 0.41                   | V    |
|  |                                      | I <sub>O</sub> = 1.9 mA; V <sub>CC</sub> = 1.65 V   | -                      | -   | 0.39                   | V    |
|  |                                      | I <sub>O</sub> = 2.3 mA; V <sub>CC</sub> = 2.3 V  | -                      | -   | 0.36                   | V    |
|  |                                      | I <sub>O</sub> = 3.1 mA; V <sub>CC</sub> = 2.3 V  | -                      | -   | 0.50                   | V    |
|  |                                      | I <sub>O</sub> = 2.7 mA; V <sub>CC</sub> = 3.0 V  | -                      | -   | 0.36                   | V    |
| I <sub>I</sub>                             | input leakage current                | V <sub>I</sub> = GND to 3.6 V; V <sub>CC</sub> = 0 V to 3.6 V                                       | -                      | -   | ±0.75                  | μA   |
|  |                                      |   |                        |     |                        |      |
| I <sub>OFF</sub>                           | power-off leakage current            | V <sub>I</sub> or V <sub>O</sub> = 0 V to 3.6 V; V <sub>CC</sub> = 0 V                              | -                      | -   | ±0.75                  | μA   |
| ΔI <sub>OFF</sub>                          | additional power-off leakage current | V <sub>I</sub> or V <sub>O</sub> = 0 V to 3.6 V;<br>V <sub>CC</sub> = 0 V to 0.2 V                  | -                      | -   | ±0.75                  | μA   |
| I <sub>CC</sub>                            | supply current                       | V <sub>I</sub> = GND or V <sub>CC</sub> ; I <sub>O</sub> = 0 A;<br>V <sub>CC</sub> = 0.8 V to 3.6 V | -                      | -   | 1.4                    | μA   |
| ΔI <sub>CC</sub>                           | additional supply current            | V <sub>I</sub> = V <sub>CC</sub> - 0.6 V; I <sub>O</sub> = 0 A;<br>V <sub>CC</sub> = 3.3 V          | [1]                    | -   | 75                     | μA   |

[1] One input at V<sub>CC</sub> - 0.6 V, other input at V<sub>CC</sub> or GND.

## 11. Dynamic characteristics

**Table 8. Dynamic characteristics**

Voltages are referenced to GND (ground = 0 V); for test circuit see [Figure 11](#).

| Symbol                      | Parameter         | Conditions   | T <sub>amb</sub> = 25 °C |                    |      | T <sub>amb</sub> = -40 °C to +125 °C |             |              | Unit |
|-----------------------------|-------------------|--|--------------------------|--------------------|------|--------------------------------------|-------------|--------------|------|
|                             |                   |  | Min                      | Typ <sup>[1]</sup> | Max  | Min                                  | Max (85 °C) | Max (125 °C) |      |
| <b>C<sub>L</sub> = 5 pF</b> |                   |  |                          |                    |      |                                      |             |              |      |
| t <sub>pd</sub>             | propagation delay | I0, I1 to Y, $\bar{Y}$ ; see <a href="#">Figure 9</a> <sup>[2]</sup>     |                          |                    |      |                                      |             |              |      |
|                             |                   | V <sub>CC</sub> = 0.8 V  | -                        | 21.2               | -    | -                                    | -           | -            | ns   |
|                             |                   | V <sub>CC</sub> = 1.1 V to 1.3 V   | 2.5                      | 6.1                | 13.3 | 2.2                                  | 13.8        | 13.9         | ns   |
|                             |                   | V <sub>CC</sub> = 1.4 V to 1.6 V   | 1.9                      | 4.2                | 7.8  | 2.0                                  | 8.4         | 8.8          | ns   |
|                             |                   | V <sub>CC</sub> = 1.65 V to 1.95 V                                       | 1.7                      | 3.4                | 6.2  | 1.6                                  | 6.9         | 7.3          | ns   |
|                             |                   | V <sub>CC</sub> = 2.3 V to 2.7 V   | 1.5                      | 2.7                | 4.3  | 1.2                                  | 4.9         | 5.2          | ns   |
|                             |                   | V <sub>CC</sub> = 3.0 V to 3.6 V   | 1.3                      | 2.4                | 3.7  | 1.0                                  | 4.0         | 4.2          | ns   |
|                             |                   | S to Y, $\bar{Y}$ ; see <a href="#">Figure 9</a> <sup>[2]</sup>          |                          |                    |      |                                      |             |              |      |
|                             |                   | V <sub>CC</sub> = 0.8 V  | -                        | 23.6               | -    | -                                    | -           | -            | ns   |
|                             |                   | V <sub>CC</sub> = 1.1 V to 1.3 V   | 2.6                      | 6.6                | 13.8 | 2.2                                  | 14.3        | 14.5         | ns   |
|                             |                   | V <sub>CC</sub> = 1.4 V to 1.6 V   | 1.9                      | 4.5                | 8.0  | 2.1                                  | 8.7         | 9.1          | ns   |
|                             |                   | V <sub>CC</sub> = 1.65 V to 1.95 V                                       | 1.7                      | 3.6                | 6.3  | 1.6                                  | 7.0         | 7.4          | ns   |
|                             |                   | V <sub>CC</sub> = 2.3 V to 2.7 V   | 1.6                      | 2.8                | 4.4  | 1.2                                  | 5.0         | 5.3          | ns   |
|                             |                   | V <sub>CC</sub> = 3.0 V to 3.6 V   | 1.3                      | 2.5                | 3.7  | 1.0                                  | 4.0         | 4.2          | ns   |
|                             |                   | $\bar{E}$ to Y, $\bar{Y}$ ; see <a href="#">Figure 10</a> <sup>[2]</sup> |                          |                    |      |                                      |             |              |      |
|                             |                   | V <sub>CC</sub> = 0.8 V  | -                        | 22.6               | -    | -                                    | -           | -            | ns   |
|                             |                   | V <sub>CC</sub> = 1.1 V to 1.3 V   | 2.7                      | 6.4                | 13.7 | 2.5                                  | 14.3        | 14.5         | ns   |
|                             |                   | V <sub>CC</sub> = 1.4 V to 1.6 V   | 2.1                      | 4.4                | 8.0  | 2.1                                  | 8.7         | 9.1          | ns   |
|                             |                   | V <sub>CC</sub> = 1.65 V to 1.95 V                                       | 1.8                      | 3.6                | 6.3  | 1.6                                  | 7.0         | 7.4          | ns   |
|                             |                   | V <sub>CC</sub> = 2.3 V to 2.7 V   | 1.6                      | 2.8                | 4.2  | 1.4                                  | 4.8         | 5.1          | ns   |
|                             |                   | V <sub>CC</sub> = 3.0 V to 3.6 V   | 1.4                      | 2.5                | 3.6  | 1.1                                  | 3.9         | 4.2          | ns   |

**Table 8. Dynamic characteristics ...continued**

Voltages are referenced to GND (ground = 0 V); for test circuit see [Figure 11](#).

| Symbol                       | Parameter         | Conditions   | T <sub>amb</sub> = 25 °C |                    |      | T <sub>amb</sub> = -40 °C to +125 °C |             |              | Unit |
|------------------------------|-------------------|--|--------------------------|--------------------|------|--------------------------------------|-------------|--------------|------|
|                              |                   |  | Min                      | Typ <sup>[1]</sup> | Max  | Min                                  | Max (85 °C) | Max (125 °C) |      |
| <b>C<sub>L</sub> = 10 pF</b> |                   |  |                          |                    |      |                                      |             |              |      |
| t <sub>pd</sub>              | propagation delay | I0, I1 to Y, $\bar{Y}$ ; see <a href="#">Figure 9</a> <sup>[2]</sup>     |                          |                    |      |                                      |             |              |      |
|                              |                   | V <sub>CC</sub> = 0.8 V  | -                        | 24.5               | -    | -                                    | -           | -            | ns   |
|                              |                   | V <sub>CC</sub> = 1.1 V to 1.3 V   | 2.9                      | 6.9                | 15.1 | 2.5                                  | 15.6        | 15.8         | ns   |
|                              |                   | V <sub>CC</sub> = 1.4 V to 1.6 V   | 2.2                      | 4.8                | 8.9  | 2.4                                  | 9.6         | 10.0         | ns   |
|                              |                   | V <sub>CC</sub> = 1.65 V to 1.95 V                                       | 2.1                      | 4.0                | 7.1  | 1.9                                  | 7.9         | 8.3          | ns   |
|                              |                   | V <sub>CC</sub> = 2.3 V to 2.7 V   | 1.9                      | 3.2                | 5.0  | 1.6                                  | 5.7         | 6.0          | ns   |
|                              |                   | V <sub>CC</sub> = 3.0 V to 3.6 V   | 1.7                      | 2.9                | 4.4  | 1.3                                  | 4.7         | 5.0          | ns   |
|                              |                   | S to Y, $\bar{Y}$ ; see <a href="#">Figure 9</a> <sup>[2]</sup>          |                          |                    |      |                                      |             |              |      |
|                              |                   | V <sub>CC</sub> = 0.8 V  | -                        | 27.2               | -    | -                                    | -           | -            | ns   |
|                              |                   | V <sub>CC</sub> = 1.1 V to 1.3 V   | 3.0                      | 7.4                | 15.5 | 2.6                                  | 16.1        | 16.4         | ns   |
|                              |                   | V <sub>CC</sub> = 1.4 V to 1.6 V   | 2.3                      | 5.1                | 9.0  | 2.4                                  | 9.8         | 10.3         | ns   |
|                              |                   | V <sub>CC</sub> = 1.65 V to 1.95 V                                       | 2.1                      | 4.2                | 7.2  | 1.9                                  | 8.0         | 8.4          | ns   |
|                              |                   | V <sub>CC</sub> = 2.3 V to 2.7 V   | 1.9                      | 3.4                | 5.1  | 1.6                                  | 5.7         | 6.1          | ns   |
|                              |                   | V <sub>CC</sub> = 3.0 V to 3.6 V   | 1.7                      | 3.0                | 4.4  | 1.4                                  | 4.7         | 5.0          | ns   |
|                              |                   | $\bar{E}$ to Y, $\bar{Y}$ ; see <a href="#">Figure 10</a> <sup>[2]</sup> |                          |                    |      |                                      |             |              |      |
|                              |                   | V <sub>CC</sub> = 0.8 V  | -                        | 25.9               | -    | -                                    | -           | -            | ns   |
|                              |                   | V <sub>CC</sub> = 1.1 V to 1.3 V   | 3.1                      | 7.2                | 15.5 | 2.8                                  | 16.1        | 16.4         | ns   |
|                              |                   | V <sub>CC</sub> = 1.4 V to 1.6 V   | 2.5                      | 5.0                | 9.0  | 2.4                                  | 9.8         | 10.3         | ns   |
|                              |                   | V <sub>CC</sub> = 1.65 V to 1.95 V                                       | 2.2                      | 4.1                | 7.1  | 1.9                                  | 8.0         | 8.4          | ns   |
|                              |                   | V <sub>CC</sub> = 2.3 V to 2.7 V   | 1.9                      | 3.3                | 4.9  | 1.7                                  | 5.5         | 5.9          | ns   |
|                              |                   | V <sub>CC</sub> = 3.0 V to 3.6 V   | 1.7                      | 3.0                | 4.2  | 1.5                                  | 4.6         | 4.8          | ns   |

**Table 8. Dynamic characteristics ...continued**

Voltages are referenced to GND (ground = 0 V); for test circuit see [Figure 11](#).

| Symbol                       | Parameter         | Conditions   | T <sub>amb</sub> = 25 °C |                    |      | T <sub>amb</sub> = -40 °C to +125 °C |             |              | Unit |
|------------------------------|-------------------|--|--------------------------|--------------------|------|--------------------------------------|-------------|--------------|------|
|                              |                   |  | Min                      | Typ <sup>[1]</sup> | Max  | Min                                  | Max (85 °C) | Max (125 °C) |      |
| <b>C<sub>L</sub> = 15 pF</b> |                   |  |                          |                    |      |                                      |             |              |      |
| t <sub>pd</sub>              | propagation delay | I0, I1 to Y, $\bar{Y}$ ; see <a href="#">Figure 9</a> <sup>[2]</sup>     |                          |                    |      |                                      |             |              |      |
|                              |                   | V <sub>CC</sub> = 0.8 V  | -                        | 27.8               | -    | -                                    | -           | -            | ns   |
|                              |                   | V <sub>CC</sub> = 1.1 V to 1.3 V   | 3.3                      | 7.7                | 16.8 | 2.8                                  | 17.4        | 17.6         | ns   |
|                              |                   | V <sub>CC</sub> = 1.4 V to 1.6 V   | 2.5                      | 5.4                | 9.8  | 2.7                                  | 10.6        | 11.2         | ns   |
|                              |                   | V <sub>CC</sub> = 1.65 V to 1.95 V                                       | 2.4                      | 4.4                | 7.8  | 2.2                                  | 8.7         | 9.2          | ns   |
|                              |                   | V <sub>CC</sub> = 2.3 V to 2.7 V   | 2.2                      | 3.7                | 5.6  | 1.9                                  | 6.4         | 6.7          | ns   |
|                              |                   | V <sub>CC</sub> = 3.0 V to 3.6 V   | 2.0                      | 3.4                | 4.9  | 1.6                                  | 5.3         | 5.6          | ns   |
|                              |                   | S to Y, $\bar{Y}$ ; see <a href="#">Figure 9</a> <sup>[2]</sup>          |                          |                    |      |                                      |             |              |      |
|                              |                   | V <sub>CC</sub> = 0.8 V  | -                        | 30.7               | -    | -                                    | -           | -            | ns   |
|                              |                   | V <sub>CC</sub> = 1.1 V to 1.3 V   | 3.3                      | 8.2                | 17.2 | 2.9                                  | 17.9        | 18.2         | ns   |
|                              |                   | V <sub>CC</sub> = 1.4 V to 1.6 V   | 2.6                      | 5.7                | 10.0 | 2.7                                  | 10.9        | 11.4         | ns   |
|                              |                   | V <sub>CC</sub> = 1.65 V to 1.95 V                                       | 2.4                      | 4.7                | 7.9  | 2.2                                  | 8.9         | 9.4          | ns   |
|                              |                   | V <sub>CC</sub> = 2.3 V to 2.7 V   | 2.2                      | 3.8                | 5.7  | 1.9                                  | 6.5         | 6.8          | ns   |
|                              |                   | V <sub>CC</sub> = 3.0 V to 3.6 V   | 2.0                      | 3.5                | 5.0  | 1.6                                  | 5.4         | 5.7          | ns   |
|                              |                   | $\bar{E}$ to Y, $\bar{Y}$ ; see <a href="#">Figure 10</a> <sup>[2]</sup> |                          |                    |      |                                      |             |              |      |
|                              |                   | V <sub>CC</sub> = 0.8 V  | -                        | 29.1               | -    | -                                    | -           | -            | ns   |
|                              |                   | V <sub>CC</sub> = 1.1 V to 1.3 V   | 3.5                      | 8.0                | 17.2 | 3.1                                  | 17.9        | 18.2         | ns   |
|                              |                   | V <sub>CC</sub> = 1.4 V to 1.6 V   | 2.8                      | 5.6                | 9.9  | 2.7                                  | 10.9        | 11.4         | ns   |
|                              |                   | V <sub>CC</sub> = 1.65 V to 1.95 V                                       | 2.4                      | 4.6                | 7.9  | 2.2                                  | 8.9         | 9.4          | ns   |
|                              |                   | V <sub>CC</sub> = 2.3 V to 2.7 V   | 2.2                      | 3.8                | 5.5  | 2.0                                  | 6.2         | 6.6          | ns   |
|                              |                   | V <sub>CC</sub> = 3.0 V to 3.6 V   | 2.0                      | 3.4                | 4.7  | 1.8                                  | 5.1         | 5.4          | ns   |

**Table 8. Dynamic characteristics ...continued**

Voltages are referenced to GND (ground = 0 V); for test circuit see [Figure 11](#).

| Symbol                       | Parameter         | Conditions   | T <sub>amb</sub> = 25 °C |                    |      | T <sub>amb</sub> = -40 °C to +125 °C |             |              | Unit |
|------------------------------|-------------------|--|--------------------------|--------------------|------|--------------------------------------|-------------|--------------|------|
|                              |                   |  | Min                      | Typ <sup>[1]</sup> | Max  | Min                                  | Max (85 °C) | Max (125 °C) |      |
| <b>C<sub>L</sub> = 30 pF</b> |                   |  |                          |                    |      |                                      |             |              |      |
| t <sub>pd</sub>              | propagation delay | I0, I1 to Y, $\bar{Y}$ ; see <a href="#">Figure 9</a> <sup>[2]</sup>     |                          |                    |      |                                      |             |              |      |
|                              |                   | V <sub>CC</sub> = 0.8 V  | -                        | 35.4               | -    | -                                    | -           | -            | ns   |
|                              |                   | V <sub>CC</sub> = 1.1 V to 1.3 V   | 4.3                      | 9.8                | 21.6 | 3.7                                  | 22.5        | 22.8         | ns   |
|                              |                   | V <sub>CC</sub> = 1.4 V to 1.6 V   | 3.3                      | 6.9                | 12.4 | 3.4                                  | 13.6        | 14.4         | ns   |
|                              |                   | V <sub>CC</sub> = 1.65 V to 1.95 V                                       | 3.1                      | 5.7                | 10.0 | 2.8                                  | 11.3        | 11.9         | ns   |
|                              |                   | V <sub>CC</sub> = 2.3 V to 2.7 V   | 2.9                      | 4.8                | 7.2  | 2.6                                  | 8.2         | 8.7          | ns   |
|                              |                   | V <sub>CC</sub> = 3.0 V to 3.6 V   | 2.8                      | 4.4                | 6.4  | 2.3                                  | 6.9         | 7.3          | ns   |
|                              |                   | S to Y, $\bar{Y}$ ; see <a href="#">Figure 9</a> <sup>[2]</sup>          |                          |                    |      |                                      |             |              |      |
|                              |                   | V <sub>CC</sub> = 0.8 V  | -                        | 38.8               | -    | -                                    | -           | -            | ns   |
|                              |                   | V <sub>CC</sub> = 1.1 V to 1.3 V   | 4.4                      | 10.5               | 22.0 | 3.7                                  | 23.0        | 23.4         | ns   |
|                              |                   | V <sub>CC</sub> = 1.4 V to 1.6 V   | 3.3                      | 7.2                | 12.6 | 3.5                                  | 13.9        | 14.6         | ns   |
|                              |                   | V <sub>CC</sub> = 1.65 V to 1.95 V                                       | 3.1                      | 5.9                | 10.1 | 2.8                                  | 11.4        | 12.0         | ns   |
|                              |                   | V <sub>CC</sub> = 2.3 V to 2.7 V   | 2.9                      | 4.9                | 7.3  | 2.6                                  | 8.3         | 8.7          | ns   |
|                              |                   | V <sub>CC</sub> = 3.0 V to 3.6 V   | 2.7                      | 4.5                | 6.4  | 2.3                                  | 6.9         | 7.3          | ns   |
|                              |                   | $\bar{E}$ to Y, $\bar{Y}$ ; see <a href="#">Figure 10</a> <sup>[2]</sup> |                          |                    |      |                                      |             |              |      |
|                              |                   | V <sub>CC</sub> = 0.8 V  | -                        | 36.8               | -    | -                                    | -           | -            | ns   |
|                              |                   | V <sub>CC</sub> = 1.1 V to 1.3 V   | 4.4                      | 10.1               | 22.1 | 3.9                                  | 23.0        | 23.4         | ns   |
|                              |                   | V <sub>CC</sub> = 1.4 V to 1.6 V   | 3.6                      | 7.1                | 12.6 | 3.5                                  | 13.8        | 14.6         | ns   |
|                              |                   | V <sub>CC</sub> = 1.65 V to 1.95 V                                       | 3.1                      | 5.8                | 10.0 | 2.8                                  | 11.3        | 12.0         | ns   |
|                              |                   | V <sub>CC</sub> = 2.3 V to 2.7 V   | 2.9                      | 4.9                | 7.1  | 2.7                                  | 8.0         | 8.5          | ns   |
|                              |                   | V <sub>CC</sub> = 3.0 V to 3.6 V   | 2.7                      | 4.5                | 6.2  | 2.4                                  | 6.7         | 7.0          | ns   |


**Table 8. Dynamic characteristics ...continued**


*Voltages are referenced to GND (ground = 0 V); for test circuit see Figure 11.*

| Symbol  | Parameter                     | Conditions   | T <sub>amb</sub> = 25 °C |                    |     | T <sub>amb</sub> = -40 °C to +125 °C |             |              | Unit |
|---|-------------------------------|--|--------------------------|--------------------|-----|--------------------------------------|-------------|--------------|------|
|   |                               |  | Min                      | Typ <sup>[1]</sup> | Max | Min                                  | Max (85 °C) | Max (125 °C) |      |
| <b>C<sub>L</sub> = 5 pF, 10 pF, 15 pF and 30 pF</b> |                               |  |                          |                    |     |                                      |             |              |      |
| C <sub>PD</sub>                                     | power dissipation capacitance | f <sub>i</sub> = 1 MHz;<br>V <sub>I</sub> = GND to V <sub>CC</sub> |                          | [3]                |     |                                      |             |              |      |
|   |                               | V <sub>CC</sub> = 0.8 V  | -                        | 5.2                | -   | -                                    | -           | -            | pF   |
|   |                               | V <sub>CC</sub> = 1.1 V to 1.3 V                                   | -                        | 5.5                | -   | -                                    | -           | -            | pF   |
|   |                               | V <sub>CC</sub> = 1.4 V to 1.6 V                                   | -                        | 5.7                | -   | -                                    | -           | -            | pF   |
|   |                               | V <sub>CC</sub> = 1.65 V to 1.95 V                                 | -                        | 6.0                | -   | -                                    | -           | -            | pF   |
|   |                               | V <sub>CC</sub> = 2.3 V to 2.7 V                                   | -                        | 6.9                | -   | -                                    | -           | -            | pF   |
|   |                               | V <sub>CC</sub> = 3.0 V to 3.6 V                                   | -                        | 7.9                | -   | -                                    | -           | -            | pF   |

- [1] All typical values are measured at nominal V<sub>CC</sub>.
- [2] t<sub>pd</sub> is the same as t<sub>PLH</sub> and t<sub>PHL</sub>
- [3] C<sub>PD</sub> is used to determine the dynamic power dissipation (P<sub>D</sub> in μW).  
 $P_D = C_{PD} \times V_{CC}^2 \times f_i \times N + \Sigma(C_L \times V_{CC}^2 \times f_o)$  where:  
 f<sub>i</sub> = input frequency in MHz;  
 f<sub>o</sub> = output frequency in MHz;  
 C<sub>L</sub> = output load capacitance in pF;  
 V<sub>CC</sub> = supply voltage in V;  
 N = number of inputs switching;  
 Σ(C<sub>L</sub> × V<sub>CC</sub><sup>2</sup> × f<sub>o</sub>) = sum of the outputs.

## 12. Waveforms






Measurement points are given in [Table 9](#).  
 Logic levels:  $V_{OL}$  and  $V_{OH}$  are typical output voltage drop that occur with the output load.

**Fig 10. The enable input ( $\bar{E}$ ) to output ( $Y, \bar{Y}$ ) propagation delays**

**Table 9. Measurement points**

| Supply voltage | Output              | Input               |          |               |
|----------------|---------------------|---------------------|----------|---------------|
| $V_{CC}$       | $V_M$               | $V_M$               | $V_I$    | $t_r = t_f$   |
| 0.8 V to 3.6 V | $0.5 \times V_{CC}$ | $0.5 \times V_{CC}$ | $V_{CC}$ | $\leq 3.0$ ns |



Test data is given in [Table 10](#).  
 Definitions for test circuit:  
 $R_L$  = Load resistance.  
 $C_L$  = Load capacitance including jig and probe capacitance.  
 $R_T$  = Termination resistance should be equal to the output impedance  $Z_o$  of the pulse generator.  
 $V_{EXT}$  = External voltage for measuring switching times.

**Fig 11. Load circuitry for switching times**

**Table 10. Test data**

| Supply voltage | Load                         |              | $V_{EXT}$          |                    |                    |
|----------------|------------------------------|--------------|--------------------|--------------------|--------------------|
| $V_{CC}$       | $C_L$                        | $R_L$ [1]    | $t_{PLH}, t_{PHL}$ | $t_{PZH}, t_{PHZ}$ | $t_{PZL}, t_{PLZ}$ |
| 0.8 V to 3.6 V | 5 pF, 10 pF, 15 pF and 30 pF | 5 kΩ or 1 MΩ | open               | GND                | $2 \times V_{CC}$  |

[1] For measuring enable and disable times  $R_L = 5$  kΩ, for measuring propagation delays, setup and hold times and pulse width  $R_L = 1$  MΩ.

13. Package outline

VSSOP8: plastic very thin shrink small outline package; 8 leads; body width 2.3 mm

SOT765-1




Fig 12. Package outline SOT765-1 (VSSOP8)

XSON8: plastic extremely thin small outline package; no leads; 8 terminals; body 1 x 1.95 x 0.5 mm

SOT833-1




Fig 13. Package outline SOT833-1 (XSON8)

XSON8U: plastic extremely thin small outline package; no leads;  
8 terminals; UTLP based; body 3 x 2 x 0.5 mm

SOT996-2




Fig 14. Package outline SOT996-2 (XSON8U)

XQFN8U: plastic extremely thin quad flat package; no leads; 8 terminals; UTLP based; body 1.6 x 1.6 x 0.5 mm

SOT902-1




Fig 15. Package outline SOT902-1 (XQFN8U)

## 14. Abbreviations

Table 11. Abbreviations

| Acronym | Description                             |
|---------|---|
| CDM     | Charged Device Model                    |
| CMOS    | Complementary Metal-Oxide Semiconductor |
| DUT     | Device Under Test                       |
| ESD     | ElectroStatic Discharge                 |
| HBM     | Human Body Model                        |
| MM      | Machine Model                           |
| TTL     | Transistor-Transistor Logic             |

## 15. Revision history

Table 12. Revision history

| Document ID    | Release date                                      | Data sheet status  | Change notice | Supersedes   |
|----------------|---|--------------------|---------------|--------------|
| 74AUP2G157_3   | 20080702  | Product data sheet | -             | 74AUP2G157_2 |
| Modifications: | • Added type number 74AUP2G157GD (XSON8U package) |                    |               |              |
| 74AUP2G157_2   | 20080219  | Product data sheet | -             | 74AUP2G157_1 |
| 74AUP2G157_1   | 20061006  | Product data sheet | -             | -            |

## 16. Legal information

### 16.1 Data sheet status

| Document status <sup>[1][2]</sup> | Product status <sup>[3]</sup> | Definition  |
|-----------------------------------|-------------------------------|---|
| Objective [short] data sheet      | Development                   | This document contains data from the objective specification for product development. |
| Preliminary [short] data sheet    | Qualification                 | This document contains data from the preliminary specification.                       |
| Product [short] data sheet        | Production                    | This document contains the product specification.                                     |

[1] Please consult the most recently issued document before initiating or completing a design.

[2] The term 'short data sheet' is explained in section "Definitions".

[3] The product status of device(s) described in this document may have changed since this document was published and may differ in case of multiple devices. The latest product status information is available on the Internet at URL <http://www.nxp.com>.

### 16.2 Definitions

**Draft** — The document is a draft version only. The content is still under internal review and subject to formal approval, which may result in modifications or additions. NXP Semiconductors does not give any representations or warranties as to the accuracy or completeness of information included herein and shall have no liability for the consequences of use of such information.

**Short data sheet** — A short data sheet is an extract from a full data sheet with the same product type number(s) and title. A short data sheet is intended for quick reference only and should not be relied upon to contain detailed and full information. For detailed and full information see the relevant full data sheet, which is available on request via the local NXP Semiconductors sales office. In case of any inconsistency or conflict with the short data sheet, the full data sheet shall prevail.

### 16.3 Disclaimers

**General** — Information in this document is believed to be accurate and reliable. However, NXP Semiconductors does not give any representations or warranties, expressed or implied, as to the accuracy or completeness of such information and shall have no liability for the consequences of use of such information.

**Right to make changes** — NXP Semiconductors reserves the right to make changes to information published in this document, including without limitation specifications and product descriptions, at any time and without notice. This document supersedes and replaces all information supplied prior to the publication hereof.

**Suitability for use** — NXP Semiconductors products are not designed, authorized or warranted to be suitable for use in medical, military, aircraft, space or life support equipment, nor in applications where failure or

malfunction of an NXP Semiconductors product can reasonably be expected to result in personal injury, death or severe property or environmental damage. NXP Semiconductors accepts no liability for inclusion and/or use of NXP Semiconductors products in such equipment or applications and therefore such inclusion and/or use is at the customer's own risk.

**Applications** — Applications that are described herein for any of these products are for illustrative purposes only. NXP Semiconductors makes no representation or warranty that such applications will be suitable for the specified use without further testing or modification.

**Limiting values** — Stress above one or more limiting values (as defined in the Absolute Maximum Ratings System of IEC 60134) may cause permanent damage to the device. Limiting values are stress ratings only and operation of the device at these or any other conditions above those given in the Characteristics sections of this document is not implied. Exposure to limiting values for extended periods may affect device reliability.

**Terms and conditions of sale** — NXP Semiconductors products are sold subject to the general terms and conditions of commercial sale, as published at <http://www.nxp.com/profile/terms>, including those pertaining to warranty, intellectual property rights infringement and limitation of liability, unless explicitly otherwise agreed to in writing by NXP Semiconductors. In case of any inconsistency or conflict between information in this document and such terms and conditions, the latter will prevail.

**No offer to sell or license** — Nothing in this document may be interpreted or construed as an offer to sell products that is open for acceptance or the grant, conveyance or implication of any license under any copyrights, patents or other industrial or intellectual property rights.

### 16.4 Trademarks

Notice: All referenced brands, product names, service names and trademarks are the property of their respective owners.

## 17. Contact information

For more information, please visit: <http://www.nxp.com>

For sales office addresses, please send an email to: [salesaddresses@nxp.com](mailto:salesaddresses@nxp.com)

**18. Contents**

1 **General description** . . . . . 1

2 **Features** . . . . . 1

3 **Ordering information** . . . . . 2

4 **Marking** . . . . . 2

5 **Functional diagram** . . . . . 2

6 **Pinning information** . . . . . 3

6.1 Pinning . . . . . 3

6.2 Pin description . . . . . 3

7 **Functional description** . . . . . 4

8 **Limiting values** . . . . . 4

9 **Recommended operating conditions** . . . . . 5

10 **Static characteristics** . . . . . 5

11 **Dynamic characteristics** . . . . . 8

12 **Waveforms** . . . . . 12

13 **Package outline** . . . . . 14

14 **Abbreviations** . . . . . 18

15 **Revision history** . . . . . 18

16 **Legal information** . . . . . 19

16.1 Data sheet status . . . . . 19

16.2 Definitions . . . . . 19

16.3 Disclaimers . . . . . 19

16.4 Trademarks . . . . . 19

17 **Contact information** . . . . . 19

18 **Contents** . . . . . 20

Please be aware that important notices concerning this document and the product(s) described herein, have been included in section 'Legal information'.



© NXP B.V. 2008.

All rights reserved.

For more information, please visit: <http://www.nxp.com>

For sales office addresses, please send an email to: [salesaddresses@nxp.com](mailto:salesaddresses@nxp.com)

Date of release: 2 July 2008

Document identifier: 74AUP2G157\_3