# MF0ICU2

# MIFARE Ultralight C - Contactless ticket IC

Rev. 3.4 — 20 March 2024 137634 Product data sheet

# 1 General description

NXP Semiconductors has developed the MIFARE Ultralight C - Contactless ticket IC MF0ICU2 to be used in a contactless smart ticket or smart card in combination with Proximity Coupling Devices (PCD). The communication layer (MIFARE RF Interface) complies to parts 2 and 3 of the ISO/IEC 14443 Type A standard (see Ref. 1 and Ref. 2).

The MF0ICU2 is primarily designed for limited use applications such as public transportation, event ticketing and loyalty applications.

### 1.1 Contactless energy and data transfer

In the MIFARE system, the MF0ICU2 is connected to a coil with a few turns. The MF0ICU2 fits for the TFC.0 (Edmonson) and TFC.1 ticket formats as defined in EN 753-2.


TFC.1 ticket formats are supported by the MF0xxU20 chip featuring an on-chip resonance capacitor of 16 pF.

The smaller TFC.0 tickets are supported by the MFxxU21 chip holding an on-chip resonance capacitor of 50 pF.

When the ticket is positioned in the proximity of the coupling device (PCD) antenna, the high speed RF communication interface allows the transmission of the data with a baud rate of 106 kbit/s.

### 1.2 Anticollision

An intelligent anticollision function allows to operate more than one card in the field simultaneously. The anticollision algorithm selects each card individually and ensures that the execution of a transaction with a selected card is performed correctly without interference from another card in the field.



The anticollision function is based on an IC individual serial number called Unique IDentification. The UID of the MF0ICU2 is 7 bytes long and supports cascade level 2 according to ISO/IEC 14443-3.



MIFARE Ultralight C - Contactless ticket IC

# 1.3 Security

- · 3DES Authentication
- · Anti-cloning support by unique 7-byte serial number for each device
- 32-bit user programmable OTP area
- Field programmable read-only locking function per page for first 512-bit
- · Read-only locking per block for the memory above 512 bit

## 1.4 Naming conventions

Table 1. Naming conventions

MF0xxU2w01Dyy	Description	
MF	MIFARE family	
0	Ultralight product family	
xx	Two character identifier for the package type IC bare die MO contactless module	
U2	Product: Ultralight C	
w	One character identifier for input capacitance 0 16 pF 1 50 pF	
01D	Fixed	
уу	This is a two character identifier for the package type UF bare die, 75 µm thickness UD bare die, 120 µm thickness A8 MOA8 contactless module	

## 2 Features and benefits

### 2.1 MIFARE RF Interface (ISO/IEC 14443 A)

- Contactless transmission of data and supply energy
- Data integrity of 16-bit CRC, parity, bit coding, bit counting
- 7 byte serial number (cascade level 2 according to ISO/ IEC 14443-3)
- Fast counter transaction: < 10 ms

· Operating frequency of 13.56 MHz

- Operating distance up to 100 mm depending on antenna geometry and reader configuration
- Data transfer of 106 kbit/s
- · True anticollision
- Typical ticketing transaction: < 35 ms

### 2.2 EEPROM

- · 1536-bit total memory
- 36 pages, 1152-bit user r/w area
- Field programmable read-only locking function per page for first 512-bit
- 512-bit compatible to MF0ICU1
- Field programmable read-only locking function per block
- 16-bit one-way counter

MF0ICU2

All information provided in this document is subject to legal disclaimers.

MIFARE Ultralight C - Contactless ticket IC

- 32-bit user definable One-Time Programmable (OTP) area Write endurance 100000 cycles
- Data retention of 10 years

# 3 Quick reference data

Table 2. Characteristics

Symbol	Parameter	Conditions	Min	Тур	Max	Unit
f <sub>i</sub>	input frequency		-	13.56	-	MHz
C <sub>i</sub>	input capacitance	16 pF version (bare silicon [1] and MOA8)	14.08	16	17.92	pF
		50 pF version [1]	44	50	56	pF
EEPROM o	characteristics					
t <sub>cy(W)</sub>	write cycle time		-	4.1	-	ms
t <sub>ret</sub>	retention time	T <sub>amb</sub> = 22 °C	10	-	-	year
N <sub>endu(W)</sub>	write endurance	T <sub>amb</sub> = 22 °C	100000	-	-	cycle

<sup>[1]</sup>  $T_{amb}$  = 22 °C, f = 13.56 MHz,  $V_{LaLb}$  = 1.5 V RMS


# 4 Ordering information

Table 3. Ordering information

Type number	Package		
	Name	Description	Version
MF0ICU2001DUF	-	8 inch wafer (laser diced; 75 µm thickness, on film frame carrier; electronic fail die marking according to SECSII format); 16 pF input capacitance	-
MF0ICU2001DUD	-	8 inch wafer (laser diced; 120 µm thickness, on film frame carrier; electronic fail die marking according to SECSII format); 16 pF input capacitance	-
MF0MOU2001DA8	PLLMC	MOA8 plastic leadless module carrier package; 35 mm wide tape; 16 pF input capacitance	SOT500-4
MF0ICU2101DUF	-	8 inch wafer (laser diced; 75 µm thickness, on film frame carrier; electronic fail die marking according to SECSII format), 50 pF input capacitance	-
MF0ICU2101DUD	-	8 inch wafer (laser diced; 120 µm thickness, on film frame carrier; electronic fail die marking according to SECSII format), 50 pF input capacitance	-
MF0MOU2101DA8	PLLMC	MOA8 plastic leadless module carrier package; 35 mm wide tape; 50 pF input capacitance	SOT500-4

MIFARE Ultralight C - Contactless ticket IC

# 5 Block diagram



# 6 Pinning information

### 6.1 Smart card contactless module




Table 4. Pin allocation table

Antenna contacts Symbol		Description
LA	LA	Antenna coil connection LA
LB	LB	Antenna coil connection LB

MIFARE Ultralight C - Contactless ticket IC

# 7 Functional description

### 7.1 Block description

The MF0ICU2 chip consists of a 1536-bit EEPROM, an RF-Interface and the Digital Control Unit. Energy and data are transferred via an antenna, which consists of a coil with a few turns directly connected to the MF0ICU2. No further external components are necessary. For details on antenna design please refer to the document Ref. 7.


- · RF-Interface:
  - Modulator/Demodulator
  - Rectifier
  - Clock Regenerator
  - Power On Reset
  - Voltage Regulator
- Crypto coprocessor: Triple Data Encryption Standard (3DES) coprocessor
- · Crypto control unit: controls Crypto coprocessor operations
- Command Interpreter: Handles the commands supported by the MF0ICU2 in order to access the memory
- EEPROM-Interface
- EEPROM: The 1536 bits are organized in 48 pages with 32 bits each. 80 bits are reserved for manufacturer data. 32 bits are used for the read-only locking mechanism. 32 bits are available as OTP area. 1152 bits are user programmable read/write memory.

## 7.2 State diagram and logical states description

The commands are initiated by the PCD and controlled by the Command Interpreter of the MF0ICU2. It handles the internal states (as shown in Figure 4) and generates the appropriate response.

For a correct implementation of an anticollision procedure please refer to the documents in Section 14.

MIFARE Ultralight C - Contactless ticket IC



**Remark:** In each state the command interpreter returns to the Idle state if an unexpected command is received or any other error occurs. If the IC has already been in the Halt state before it returns to the Halt state in such a case. Those transitions are not explicitly shown in the state diagram.

Figure 4. State diagram

### 7.2.1 IDLE

After Power On Reset (POR) the MF0ICU2 enters IDLE state. With a REQA or a WUPA command sent from the PCD transits to the READY1 state. Any other data received in this state is interpreted as an error and the MF0ICU2 remains waiting in the Idle state.

Please refer to Ref. 4 for implementation hints for a card polling algorithm that respects relevant timing specifications from ISO/IEC 14443 Type A.

After a correctly executed HLTA command i.e. out of the ACTIVE or AUTHENTICATED state, the default waiting state changes from the IDLE state to the HALT state. This state can then be exited with a WUPA command only.

#### 7.2.2 READY1

In the READY1 state the MF0ICU2 supports the PCD in resolving the first part of its UID (3 bytes) with the ANTICOLLISION or a cascade level 1 SELECT command.

There are two possibilities to leave this state:

• With the cascade level 1 SELECT command the PCD transits the MF0ICU2 into the READY2 state where the second part of the UID can be resolved

MF0ICU2

All information provided in this document is subject to legal disclaimers

MIFARE Ultralight C - Contactless ticket IC

 With the READ (from page address 00h) command the complete anticollision mechanism may be skipped and the MF0ICU2 changes directly into the ACTIVE state

**Remark:** If more than one MF0ICU2 is in the field of the PCD, a read from address 0 will cause a collision because of the different serial numbers, but all MF0ICU2 devices will be selected.

**Remark:** Any other data received in state READY1 state is interpreted as an error and the MF0ICU2 falls back to its waiting state (IDLE or HALT, depending on its previous state).

The response of the MF0ICU2 to the cascade level 1 SELECT command is the SAK byte with value 04h. It indicates that the UID has not been complete received by the PCD yet and another anticollision level is required.

#### 7.2.3 READY2

In the READY2 state the MF0ICU2 supports the PCD in resolving the second part of its UID (4 bytes) with the ANTICOLLISION command of cascade level 2. This state is left with the cascade level 2 SELECT command.

Alternatively, state READY2 state may be skipped via a READ (from block address 00h) command as described in state READY1.

**Remark:** If more than one MF0ICU2 is in the field of the PCD, a read from address 00h will cause a collision because of the different serial numbers, but all MF0ICU2 devices will be selected.

**Remark:** The response of the MF0ICU2 to the cascade level 2 SELECT command is the SAK byte with value 00h. According to ISO/IEC14443 this byte indicates whether the anticollision cascade procedure is finished (see Ref. 6). In addition it defines for the MIFARE architecture platform the type of the selected device. At this stage the MF0ICU2 is uniquely selected and only a single device will continue communication with the PCD even if other contactless devices are in the field of the PCD.

Any other command received in this state is interpreted as an error and the MF0ICU2 falls back to its waiting state (IDLE or HALT, depending on its previous state).

### **7.2.4 ACTIVE**

In the ACTIVE state READ (16 bytes), WRITE (4 bytes), COMPATIBILITY WRITE (16 bytes) commands or an authentication can be performed.

After a successful authentication the state "AUTHENTICATED" is reached, see Section 7.2.6.

The ACTIVE state is gratefully exited with the HLTA command and upon reception the MF0ICU2 transits to the HALT state.

Any other command received in this state is interpreted as an error and the MF0ICU2 goes back to its waiting state (IDLE or HALT, depending on its previous state).

#### 7.2.5 HALT

Besides the IDLE state the HALT state constitutes the second waiting state implemented in the MF0ICU2. A MF0ICU2 that has already been processed can be set into this state via the HLTA command. This state helps the PCD to distinguish between already processed cards and cards that have not been selected yet. The only way to get the MF0ICU2 out of this state is the WUPA command or a RF reset. Any other data received in this state is interpreted as an error and the MF0ICU2 remains in this state.

### 7.2.6 AUTHENTICATED

In the AUTHENTICATED state either a READ or a WRITE command may be performed to memory areas, which are only readable and/or writeable after authentication.

MF0ICU2

All information provided in this document is subject to legal disclaimers.

MIFARE Ultralight C - Contactless ticket IC

Authentication is performed using the 3DES Authentication described in Section 7.5.5.

## 7.3 Data integrity

The following mechanisms are implemented in the contactless communication link between PCD and MF0ICU2 to ensure a reliable data transmission:

- 16 bits CRC per block
- · Parity bit for each byte
- · Bit count checking
- Bit coding to distinguish between "1", "0", and no information
- · Channel monitoring (protocol sequence and bit stream analysis)

#### 7.4 RF interface

The RF-interface is implemented according to the standard for contactless smart cards ISO/IEC 14443 Type A (see Ref. 1 and Ref. 2).

The RF-field from the PCD is always present (with short modulation pulses when transmitting), because it is used for the power supply of the card.

For both directions of data communication there is one start bit at the beginning of each frame. Each byte is transmitted with a parity bit (odd parity) at the end. The LSBit of the byte with the lowest byte address within selected page is transmitted first. The maximum frame length is 164 bits (16 data bytes + 2 CRC bytes = 16 \* 9 + 2 \* 9 + 1 start bit + 1 end bit).

### 7.5 Memory organization

The 1536-bit EEPROM memory is organized in 48 pages with 32 bits each. In the erased state the EEPROM cells are read as a logical "0", in the written state as a logical "1".


Table 5. Memory organization

Page address	;		Byte number			
Decimal	Hex	0	1	2	3	
0	00h		serial ı	number		
1	01h		serial ı	number		
2	02h	serial number	serial number internal lock bytes loc			
3	03h	OTP	OTP	OTP	OTP	
4 to 39	04h to 27h	user memory	user memory	user memory	user memory	
40	28h	lock bytes	lock bytes	-	-	
41	29h	16-bit counter	16-bit counter	-	-	
42	2Ah		authentication configuration			
43	2Bh		authentication configuration			
44 to 47	2Ch to 2Fh		authentication key			

MIFARE Ultralight C - Contactless ticket IC

### 7.5.1 UID/serial number

The unique 7 byte serial number (UID) and its two Block Check Character Bytes (BCC) are programmed into the first 9 bytes of the memory. It therefore covers page 00h, page 01h and the first byte of page 02h. The second byte of page 02h is reserved for internal data. Due to security and system requirements these bytes are programmed and write-protected in the production test.




SN0 holds the Manufacturer ID for NXP (04h) according to ISO/IEC14443-3 and ISO/IEC 7816-6 AMD.1.

According to ISO/IEC14443-3 BCC0 is defined as CT  $\oplus$  SN0  $\oplus$  SN1  $\oplus$  SN2. Abbreviations CT stays for Cascade Tag byte (88h) and BCC1 is defined as SN3  $\oplus$  SN4  $\oplus$  SN5  $\oplus$  SN6.

### 7.5.2 Lock byte 0 and 1

The bits of byte 2 and byte 3 of page 02h represent the field programmable permanent read-only locking mechanism. Each page from 03h (OTP) to 0Fh can be individually locked by setting the corresponding locking bit Lx to logic 1 to prevent further write access. After locking, the corresponding page becomes read-only memory. To restrict read access to the memory refer to the authentication functionality (see Section 7.5.5).

The three least significant bits of lock byte 0 are the block-locking bits. Bit 2 deals with pages 0Ah to 0Fh, bit 1 deals with pages 04h to 09h and bit 0 deals with page 03h (OTP). Once the block-locking bits are set, the locking configuration for the corresponding memory area is frozen. The functionality of the bits inside the lock bytes 0 and 1 are shown in <u>Table 6</u>.



For example if BL15-10 is set to logic 1, then bits L15 to L10 (lock byte 1, bit[7:2]) can no longer be changed. A WRITE command or COMPATIBILITY\_WRITE command to page 02h, sets the locking and block-locking bits. Byte 2 and byte 3 of the WRITE or COMPATIBILITY\_WRITE command, and the contents of the lock bytes are bit-wise OR'ed and the result then becomes the new content of the lock bytes. This process is irreversible. If a bit is set to logic 1, it cannot be changed back to logic 0. Therefore, before writing the lock bytes, the user has to ensure that the corresponding user memory area and/or configuration bytes to be locked are correctly written.

MF0ICU2

All information provided in this document is subject to legal disclaimers.

MIFARE Ultralight C - Contactless ticket IC

The contents of bytes 0 and 1 of page 02h are unaffected by the corresponding data bytes of the WRITE (see Section 9.3) or COMPATIBILITY WRITE (see Section 9.4) command.

The default value of the static lock bytes is 00 00h.

For compatibility reasons, the first 512 bits of the memory area have the same functionality as the MIFARE Ultralight MF0ICU1 (see also Ref. 8), meaning that the two lock bytes used for the configuration of this memory area have identical functionality. The mapping of single lock bits to memory area for the first 512 bits is shown in Figure 6 and Table 6.

Table 6. Functionality of lock bits in lock byte 0 and 1

Lock Byte	Bit	Function	Block Locking in Lock Byte	Block Locking in Bit
0	3	lock OTP page	0	0
0	4	lock page 4	0	1
0	5	lock page 5	0	1
0	6	lock page 6	0	1
0	7	lock page 7	0	1
1	0	lock page 8	0	1
1	1	lock page 9	0	1
1	2	lock page 10	0	2
1	3	lock page 11	0	2
1	4	lock page 12	0	2
1	5	lock page 13	0	2
1	6	lock page 14	0	2
1	7	lock page 15	0	2

Any write operation to the lock bytes 0 and 1, features anti-tearing support.


Remark: The configuration written in the lock bytes is valid upon the next REQA or WUPA command.

### 7.5.3 Lock byte 2 and 3

To lock the pages of the MF0UL21 starting at page address 10h onwards, the lock bytes 2 and 3 located in page 28h (byte 0 and 1 as shown in <u>Figure 7</u>) are used. Those two lock bytes cover the memory area of 96 data bytes in pages 10h (16d) to 27h (39d) and the configuration area from page address 28h onwards. The granularity is 4 pages, compared to a single page for the first 512 bits as shown in <u>Figure 7</u>. The functionality of the bits inside the lock bytes 2 and 3 are shown in <u>Table 7</u>.

Remark: Set all bits marked with RFUI to 0, when writing to the lock bytes.

### MIFARE Ultralight C - Contactless ticket IC



The default value of lock bytes 2 and 3 is 00 00h. The value of byte 3 on page 28h (see Figure 7) is always BDh when read.

The contents of bytes 2 and 3 of page 28h are unaffected by the corresponding data bytes of the WRITE (see Section 9.3) or COMPATIBILITY\_WRITE (see Section 9.4) command.

Table 7. Functionality of lock bits in lock byte 2 and 3

Lock Byte	Bit	Function	Block Locking in Lock Byte	Block Locking in Bit
2	1	lock page 16-19	2	0
2	2	lock page 20-23	2	0
2	3	lock page 24-27	2	0
2	5	lock page 28-31	2	4
2	6	lock page 32-35	2	4
2	7	lock page 36-39	2	4
3	4	lock Counter	3	0
3	5	lock AUTH0	3	1
3	6	lock AUTH1	3	2
3	7	lock Key	3	3


Any write operation to the lock bytes 2 and 3, features anti-tearing support.

Remark: The configuration written in the lock bytes is valid upon the next REQA or WUPA command.

### 7.5.4 OTP bytes

Page 3 is the OTP page. It is preset to all "0" after production. These bytes may be bit-wise modified by the WRITE or COMPATIBILITY WRITE command.

MIFARE Ultralight C - Contactless ticket IC



The bytes of the WRITE command and the current contents of the OTP bytes are bit-wise "OR-ed" and the result forms the new content of the OTP bytes. This process is irreversible. If a bit is set to "1", it cannot be changed back to "0" again.

The default value of the OTP bytes is 00 00 00 00h.

Any write operation to the OTP bytes features anti-tearing support.

### 7.5.5 3DES Authentication

The 3DES Authentication implemented in the MF0ICU2 proves that two entities hold the same secret and each entity can be seen as a reliable partner for onwards communication. The applied encryption algorithm ek() is the 2 key 3DES encryption (see Ref. 9) in Cipher-Block Chaining (CBC) mode as described in ISO/IEC 10116 (see Ref. 10). The Initial Value (IV) of the first encryption of the protocol is the all zero block. For the subsequent encryptions the IV consists of the last ciphertext block.

The following table shows the communication flow during authentication:

Table 8. 3DES authentication

#	PCD	Data exchanged	PICC	
1	The reader device is always the entity which starts an authentication procedure. This is done by sending the command AUTHENTICATE.	"1Ah" → AUTHENTICATE		Step 1
2		← "AFh"    8 bytes ek(RndB)	The PICC generates a 8 byte random number <i>RndB</i> . This random number is <b>en</b> ciphered with the key, denoted by <i>ek(RndB)</i> , and is then transmitted to the PCD.	
3	The PCD itself generates a 8 byte random number <i>RndA</i> . This <i>RndA</i> is concatenated with <i>RndB</i> ' and <b>en</b> ciphered with the key. <i>RndB</i> ' is generated by rotating the original <i>RndB</i> left by 8 bits. This token <i>ek(RndA</i>    <i>RndB</i> ') is sent to the PICC.	→ "AFh"    16 bytes ek(RndA    RndB')		

MF0ICU2

MIFARE Ultralight C - Contactless ticket IC

Table 8. 3DES authentication...continued

#	PCD	Data exchanged	PICC	
4			The PICC runs an <b>de</b> cipherment on the received token and thus gains <i>RndA</i> + <i>RndB</i> '. The PICC can now verify the sent <i>RndB</i> ' by comparing it with the <i>RndB</i> ' obtained by rotating the original <i>RndB</i> left by 8 bits internally.  A successful verification proves to the PICC that the PICC and the PCD posses the same secret key.  If the verification fails, the PICC stops the authentication procedure and returns an error message.  As the PICC also received the random number <i>RndA</i> , generated by the PCD, it can perform a rotate left operation by 8 bits on <i>RndA</i> to gain <i>RndA'</i> , which is <b>en</b> ciphered again, resulting in <i>ek(RndA')</i> . This token is sent to the PCD.	Step 2
5	The PCD runs a <b>de</b> cipherment on the received <i>ek(RndA')</i> and thus gains <i>RndA'</i> for comparison with the PCD-internally rotated <i>RndA'</i> .  If the comparison fails, the PCD exits the procedure and may halt the PICC.			
6			The PICC sets the state to authenticate.	1

The cryptographic method is based on 3DES in CBC mode.

See command details in <u>Section 9.5</u>. The used key is a double length DES Key; where the parity bits are not checked or used.

# 7.5.6 3DES Authentication example

A numerical example of a 3DES authentication process is shown below in <u>Table 9</u>. The key used in the example has a value of 49454D4B41455242214E4143554F5946h.

Table 9. Numerical 3DES authentication example

1	PCD	Data exchanged	PICC
	start the authentication procedure	$\rightarrow$	
		1Ah	
2		←	generate RndB = 51E764602678DF2B
		AF577293FD2F34CA51	IV = 000000000000000
			ek(RndB) = 577293FD2F34CA51

MIFARE Ultralight C - Contactless ticket IC

Table 9. Numerical 3DES authentication example...continued

#	PCD	Data exchanged	PICC
3	decipher ek(RndB) to retrieve RndB generate RndA = A8AF3B256C75ED40 RndB' = E764602678DF2B51 RndA+RndB' = A8AF3B256C75ED40 E764602678DF2B51 IV = 577293FD2F34CA51 ek(RndA+RndB') = 0A638559FC7737F9F15 D7862EBBE967A	→ AF0A638559FC7737F9 F15D7862EBBE967A	
4		← 003B884FA07C137CE1	decipher ek(RndA+RndB') to retrieve RndA verify RndB' RndA'=AF3B256C75ED40A8 IV = F15D7862EBBE967A ek(RndA')= 3B884FA07C137CE1
5	decipher and verify ek(RndA')		

### 7.5.7 Programming of 3DES key to memory

The 16 bytes of the 3DES key are programmed to memory pages from 2Ch to 2Fh. The keys are stored in memory as shown in <u>Table 10</u>. The key itself can be written during personalization or at any later stage using the WRITE (see <u>Section 9.3</u>) or COMPATIBILITY WRITE (see <u>Section 9.4</u>) command. For both commands, Byte 0 is always sent first.

Table 10. Key memory configuration

D 1 11		•	41		
Byte address		0h	1h	2h	3h
Page address		Byte 0	Byte 1	Byte 2	Byte 3
2Ch	Page 44	Key1 / K0	Key1 / K1	Key1 / K2	Key1 / K3
2Dh	Page 45	Key1 / K4	Key1 / K5	Key1 / K6	Key1 / K7
2Eh	Page 46	Key2 / K0	Key2 / K1	Key2 / K2	Key2 / K3
2Fh	Page 47	Key2 / K4	Key2 / K5	Key2 / K6	Key2 / K7

On example of Key1 = 0001020304050607h and Key2 = 08090A0B0C0D0E0Fh, the command sequence needed for key programming with WRITE command is:

- A2 2C 07 06 05 04 CRC
- A2 2D 03 02 01 00 CRC
- A2 2E 0F 0E 0D 0C CRC
- A2 2F 0B 0A 09 08 CRC

The memory content after those (COMPATIBILITY) WRITE commands is shown in Table 11.

Table 11. Memory content based on example configuration

Byte address		Byte address		0h	1h	2h	3h
Page address		Byte 0	Byte 1	Byte 2	Byte 3		
2Ch	Page 44	07	06	05	04		
2Dh	Page 45	03	02	01	00		
2Eh	Page 46	0F	0E	0D	0C		

MF0ICU2

All information provided in this document is subject to legal disclaimers.

MIFARE Ultralight C - Contactless ticket IC

Table 11. Memory content based on example configuration...continued

Byte address		0h	1h	2h	3h
Page address		Byte 0	Byte 1	Byte 2	Byte 3
2Fh	Page 47	0B	0A	09	08

The memory pages holding the authentication key can never be read, independent of the configuration.

Remark: A re-programmed authentication key is only valid for authentication after a RF reset or a re-activation.

### 7.5.8 Configuration for memory access via 3DES Authentication

The behavior of the memory access rights depending on the authentication is configured with two configuration bytes, AUTH0 and AUTH1, located in pages 2Ah and 2Bh. Both configuration bytes are located in Byte 0 of the respective pages (see also <u>Table 5</u>).

- AUTH0 defines the page address from which the authentication is required. Valid address values for byte AUTH0 are from 03h to 30h.
- Setting AUTH0 to 30h effectively disables memory protection.
- AUTH1 determines if write access is restricted or both read and write access are restricted, see Table 12

Table 12. AUTH1 bit description

Bit	Value	Description
1 to 7	any	ignored
0	1	write access restricted, read access allowed without authentication
	0	read and write access restricted

# 7.5.9 Data pages

The MF0ICU2 features 144 bytes of data memory. The EEPROM memory is organized in pages with 4 bytes per page. The user memory area ranges from page 04h to 27h.

Remark: The default content of the user memory pages 04h to 27h at delivery is not defined.

A write access to data memory is done with a WRITE (see Section 9.3) or a COMPATIBILITY WRITE (see Section 9.4) command. In both cases, 4 bytes of memory - (one page) - will be written. Write access to data memory can be permanently restricted via lock bytes (see Section 7.5.2 and Section 7.5.3) and/or permanently or temporary restricted using an authentication (see Section 7.5.5).

Reading data is done using the READ command (see Section 9.2).

#### 7.5.10 Initial memory configuration

The memory configuration of MF0ICU2 in delivery state is shown in <a>Table 13</a>:

Table 13. Initial memory organization

Page address		Byte number			
dec.	hex.	0	1	2	3
0	00h	SN0	SN1	SN2	BCC0
1	01h	SN3	SN4	SN5	SN6
2	02h	BCC1	internal	00h	00h
3	03h	00h	00h	00h	00h

MF0ICU2

All information provided in this document is subject to legal disclaimers.

MIFARE Ultralight C - Contactless ticket IC

Table 13. Initial memory organization...continued

Page address			Byte number				
dec.	hex.	0	1	2	3		
4 to 39	04h to 27h	not defined	not defined	not defined	not defined		
40	28h	00h	00h	rfu	rfu		
41	29h	00h	00h	rfu	rfu		
42	2Ah	30h	rfu	rfu	rfu		
43	2Bh	00h	rfu	rfu	rfu		
44	2Ch	42h	52h	45h	41h		
45	2Dh	4Bh	4Dh	45h	49h		
46	2Eh	46h	59h	4Fh	55h		
47	2Fh	43h	41h	4Eh	21h		

This configuration ensures that the complete memory area is available for personalization, without knowledge of the authentication key. All lock bytes are set to zero meaning that no page or functionality is locked. The Counter is set to zero.

**Remark:** It is strongly recommended to program the authentication key during personalization in a secure environment and configure the AUTH0 byte at least in a way that the key and the AUTH0 and AUTH1 bytes can only be overwritten with prior authentication. This can be achieved by setting AUTH0 to 2Ah.

### **7.5.11 Counter**

The MF0ICU2 features a 16-bit one-way counter, located at the first two bytes of page 29h. The default counter value is 0000h.

The first valid WRITE or COMPATIBILITY WRITE to address 29h can be performed with any value in the range between 0001h and FFFFh and corresponds to the initial counter value. Every consecutive WRITE command, which represents the increment, can contain values between 0001h and 000Fh. Upon such WRITE command and following mandatory RF reset, the value written to the address 29h is added to the counter content.

After the initial write, only the lower nibble of the first data byte is used for the increment value (0h-Fh) and the remaining part of the data is ignored. Once the counter value reaches FFFFh and an increment is performed via a valid WRITE command, the MF0ICU2 will reply a NAK. If the sum of counter value and increment is higher than FFFFh, MF0ICU2 will reply a NAK and will not increment the counter.

An increment by zero (0000h) is always possible, but does not have any impact to the counter value.


It is recommended to protect the access to the counter functionality by authentication.

An example for the counter functionality is shown in Figure 9.

CU2 All information provided in this document is subject to legal disclaimers.

<sup>1</sup> The first valid write is defined as a write to a counter value of 0000h with an argument different than zero

### MIFARE Ultralight C - Contactless ticket IC



### 8 Command overview

The MIFARE Ultralight C card activation follows the ISO/IEC 14443 Type A. After the MIFARE Ultralight C card has been selected, it can either be deactivated using the ISO/IEC 14443 Halt command, or the MIFARE Ultralight C commands can be performed. For more details about the card activation refer to Ref. 2.

## 8.1 MIFARE Ultralight C command overview

All available commands for the MIFARE Ultralight C are shown in <u>Table 14</u>. All memory access commands are transmitted in plain, only the AUTHENTICATE command uses 3DES encryption, see <u>Section 9.5</u>.

Table 14. Command overview

Command	ISO/IEC 14443	Command code (hexadecimal)
Request	REQA	26h (7 bit)
Wake-up	WUPA	52h (7 bit)
Anticollision CL1	Anticollision CL1	93h 20h
Select CL1	Select CL1	93h 70h
Anticollision CL2	Anticollision CL2	95h 20h
Select CL2	Select CL2	95h 70h
Halt	Halt	50h 00h
READ	-	30h
WRITE	-	A2h
COMPATIBILITY WRITE	-	A0h
AUTHENTICATE	-	1Ah

All commands use the coding and framing as described in Ref. 1 and Ref. 2 if not otherwise specified.

MIFARE Ultralight C - Contactless ticket IC


## 8.2 Timings

The timing shown in this document are not to scale and values are rounded to 1 µs.

All given command and response transmission times refer to the data frames including start of communication and end of communication. A PCD data frame contains the start of communication (1 "start bit") and the end of communication (one logic 0 + 1 bit length of unmodulated carrier). A PICC data frame contains the start of communication (1 "start bit") and the end of communication (1 bit length of no subcarrier).

The minimum command response time is specified according to  $\underline{\text{Ref. 2}}$  as an integer n which specifies the PCD to PICC frame delay time. The frame delay time (FDT) from PICC to PCD is at least 87  $\mu$ s which corresponds to a n=9. The maximum command response time is specified as a time-out value. Depending on the command, the  $T_{ACK}$  value specified for command responses defines the PCD to PICC frame delay time. It does it for either the 4-bit ACK/NAK value specified in Section 8.3 or for a data frame.

All command timings are according to ISO/IEC 14443-3 frame specification as shown for the Frame Delay Time in <u>Figure 10</u>. For more details refer to <u>Ref. 1</u> and <u>Ref. 2</u>.



**Remark:** Due to the coding of commands, the measured timings usually excludes (a part of) the end of communication. Consider this factor when comparing the specified with the measured times.

## 8.3 MIFARE Ultralight C ACK and NAK

The MIFARE Ultralight C - Contactless ticket IC uses, apart from the responses defined in the following sections, two half-byte answers to acknowledge the command received in ACTIVE and AUTHENTICATED state (see Figure 4) abbreviated as ACK and NAK.

The MIFARE Ultralight C - Contactless ticket IC distinguishes between positive (ACK) and negative (NAK) acknowledge. Valid values for ACK and NAK are shown in Table 15.

Table 15. ACK and NAK values

Answer value	Answer explanation			
Ah	positive acknowledge (ACK)			
2h	NAK for EEPROM write error			
1h	NAK for parity or CRC error			

MF0ICU2

All information provided in this document is subject to legal disclaimers

MIFARE Ultralight C - Contactless ticket IC

Table 15. ACK and NAK values...continued

Answer value	Answer explanation
0h	NAK for any other error

After every NAK, the MF0ICU2 performs an internal reset and returns to IDLE or HALT state.

**Remark:** Any 4-bit response different from Ah shall be interpreted as NAK, although not all 4-bit values are detailed in Table 15

## 8.4 Summary of device identification data

For more details on the values below please refer to Ref. 2, Ref. 3 and Ref. 4.

Table 16. Summary of relevant data for device identification

Code	Length	Value	Binary Format	Remark
ATQA	2 Byte	0044h	0000 0000 0100 0100	
СТ	1 Byte	88h	1000 1000	Cascade Tag, ensures collision with cascade level 1 products
SAK (casc. level 1)	1 Byte	04h	0000 0100	'1' indicates additional cascade level
SAK (casc. level 2)	1 Byte	00h	0000 0000	indicates complete UID and MIFARE Ultralight functionality
Manufacturer Byte	1 Byte	04h	0000 0100	indicates NXP Semiconductors as manufacturer

# 9 MIFARE Ultralight C - Contactless ticket IC commands

## 9.1 MIFARE Ultralight C - Contactless ticket IC card activation

The ATQA and SAK values are identical as for MF0ICU1 (see Ref. 8). For information on ISO 14443 card activation, see Ref. 4. Summary of data relevant for device identification is given in Section 8.4.

### **9.2 READ**

The READ command takes the page address as a parameter. Only addresses 00h to 2Bh are decoded. For higher addresses the MF0ICU2 returns a NAK. The MF0ICU2 responds to the READ command by sending 16 bytes starting from the page address defined in the command (e.g. if ADR is 03h, pages 03h, 04h, 05h, 06h are returned). The command structure is shown in Figure 11 and Table 17.

Table 18 shows the required timing.

A roll-over mechanism is implemented to continue reading from page 00h once the end of the accessible memory is reached. For example, reading from address 29h on a MF0ICU2 results in pages 29h, 2Ah, 2Bh and 00h being returned.

The following conditions apply if part of the memory is protected by the 3DES authentication for read access:

- if the MF0ICU2 is in the ACTIVE state
  - addressing a page which is equal or higher than AUTH0 results in a NAK response

MF0ICU2

MIFARE Ultralight C - Contactless ticket IC

- addressing a page lower than AUTH0 results in data being returned with the roll-over mechanism occurring just before the AUTH0 defined page
- if the MF0ICU2 is in the AUTHENTICATED state
  - the READ command behaves like on a MF0ICU2 without access protection




Table 17. READ command

Name	Code	Description	Length
Cmd	30h	read four pages	1 byte
Addr	-	start page address '00h' to '2Bh'	1 byte
CRC	-	CRC according to Ref. 2	2 bytes
Data	-	data content of the addressed pages	16 bytes
NAK	see <u>Table 15</u>	see Section 8.3	4-bit

Table 18. READ timing

These times exclude the end of communication of the PCD.

	T <sub>ACK</sub> min	T <sub>ACK</sub> max	T <sub>NAK min</sub>	T <sub>NAK max</sub>	T <sub>TimeOut</sub>
READ	n=9	T <sub>TimeOut</sub>	n=9	T <sub>TimeOut</sub>	5 ms

### 9.3 WRITE

The WRITE command is used to program the lock bytes in page 02h, the OTP bytes in page 03h, data bytes in pages 04h to 27h, configuration data from page 28h to 2B and keys from page 2Ch to 2Fh. A WRITE command is performed page-wise, programming 4 bytes in a page. The WRITE command is shown in <a href="Figure 12">Figure 12</a> and <a href="Figure 12">Table 19</a>.

Table 20 shows the required timing.

### MIFARE Ultralight C - Contactless ticket IC




Table 19. WRITE command

Name	Code	Description	Length
Cmd	A2h	write one page	1 byte
Addr	-	page address '02h' to '2Fh'	1 byte
CRC	-	CRC according to Ref. 2	2 bytes
Data	-	data	4 bytes
NAK	see <u>Table 15</u>	see Section 8.3	4-bit

Table 20. WRITE timing

These times exclude the end of communication of the PCD.


	T <sub>ACK</sub> min	T <sub>ACK</sub> max	T <sub>NAK min</sub>	T <sub>NAK max</sub>	T <sub>TimeOut</sub>
WRITE	n=9	T <sub>TimeOut</sub>	n=9	T <sub>TimeOut</sub>	10 ms

### 9.4 COMPATIBILITY WRITE

The COMPATIBILITY WRITE command was implemented to accommodate the established MIFARE PCD infrastructure. Even though 16 bytes are transferred to the MF0ICU2, only the least significant 4 bytes (bytes 0 to 3) will be written to the specified address. It is recommended to set the remaining bytes 4 to 15 to all '0'.

Personalization of authentication key: For writing the authentication key, one needs to write the key with four commands. The first command shall have the 4 least significant bytes of the key and shall be written on page 2Ch, the second 4 bytes shall be written on page 2Ch, the next 4 bytes shall be written on page 2Eh, the last 4 bytes shall be written on page 2Fh.

## MIFARE Ultralight C - Contactless ticket IC






Table 21. COMPATIBILITY\_WRITE command

Table 21. Com Anbien Lawring					
Name	Code	Description	Length		
Cmd	A0h	compatibility write	1 byte		
Addr	-	page address '02h' to '2Fh'	1 byte		
CRC	-	CRC according to Ref. 2	2 bytes		
Data	-	16-byte Data, only least significant 4 bytes are written	16 bytes		
NAK	see <u>Table 15</u>	see Section 8.3	4-bit		

## Table 22. COMPATIBILITY\_WRITE timing

These times exclude the end of communication of the PCD.

	T <sub>ACK</sub> min	T <sub>ACK</sub> max	T <sub>NAK min</sub>	T <sub>NAK max</sub>	T <sub>TimeOut</sub>
COMPATIBILITY_WRITE part 1	n=9	T <sub>TimeOut</sub>	n=9	T <sub>TimeOut</sub>	5 ms
COMPATIBILITY_WRITE part 2	n=9	T <sub>TimeOut</sub>	n=9	T <sub>TimeOut</sub>	10 ms

MF0ICU2

All information provided in this document is subject to legal disclaimers.

MIFARE Ultralight C - Contactless ticket IC

### 9.5 AUTHENTICATE

**Description:** The authentication process is detailed <u>Section 7.5.5</u>.

The command is performed in the same protocol as READ, WRITE and COMPATIBILITY WRITE.

Executing a HALT command results in losing the authentication status.




Table 23. AUTHENTICATE part 1 command

Name	Code	Description	Length
Cmd	1Ah	authentication part 1	1 byte
Arg	00h	fixed value 00h as argument	1 byte
CRC	-	CRC according to Ref. 2	2 bytes
AFh	AFh	first response byte indicates that the authentication process needs a second command part	1 bytes
ek(RndB)	-	8-byte encrypted PICC random number RndB	8 bytes
NAK	see <u>Table 15</u>	see Section 8.3	4-bit

## Table 24. AUTHENTICATE part 1 timing

These times exclude the end of communication of the PCD.

	T <sub>ACK</sub> min	T <sub>ACK</sub> max	T <sub>NAK min</sub>	T <sub>NAK max</sub>	T <sub>TimeOut</sub>
AUTHENTICATE part 1	n=9	T <sub>TimeOut</sub>	n=9	T <sub>TimeOut</sub>	5 ms

## Table 25. AUTHENTICATE Step 2

Code	Parameter	Data	Integrity mechanism	Response
AFh	-	ek(RndA+RndB')	Parity, CRC	'00' + ek(RndA')

MF0ICU2

## MIFARE Ultralight C - Contactless ticket IC




Table 26. AUTHENTICATE part 2 command

Name	Code	Description	Length
Cmd	AFh	fixed first byte for the AUTHENTICATE part 2 command	1 byte
ek(RndA    RndB')	-	16-byte encrypted random numbers RNDA concatenated by RndB'	16 bytes
CRC	-	CRC according to Ref. 2	2 bytes
00h	00h	first response byte indicates that the authentication process is finished after this command	1 bytes
ek(RndA')	-	8-byte encrypted, shifted PCD random number RndA'	8 bytes
NAK	see <u>Table 15</u>	see <u>Section 8.3</u>	4-bit

## Table 27. AUTHENTICATE part 2 timing

These times exclude the end of communication of the PCD.

	T <sub>ACK</sub> min	T <sub>ACK</sub> max	T <sub>NAK min</sub>	T <sub>NAK max</sub>	T <sub>TimeOut</sub>
AUTHENTICATE part 2	n=9	T <sub>TimeOut</sub>	n=9	T <sub>TimeOut</sub>	5 ms

MIFARE Ultralight C - Contactless ticket IC

# 10 Limiting values

Stresses exceeding one or more of the limiting values, can cause permanent damage to the device. Exposure to limiting values for extended periods can affect device reliability.

Table 28. Limiting values

In accordance with the Absolute Maximum Rating System (IEC 60134).

Symbol	Parameter	Min	Max	Unit
I <sub>I</sub>	input current	-	30	mA
T <sub>stg</sub>	storage temperature	-55	125	°C
T <sub>amb</sub>	ambient temperature	-25	70	°C
V <sub>ESD</sub>	electrostatic discharge voltage on LA/LB [1]	2	-	kV

<sup>[1]</sup> ANSI/ESDA/JEDEC JS-001; Human body model: C = 100 pF, R = 1.5 k $\Omega$ 

#### **CAUTION**



This device has limited built-in ElectroStatic Discharge (ESD) protection. The leads should be shorted together or the device placed in conductive foam during storage or handling to prevent electrostatic damage to the gates.

## 11 Characteristics

### 11.1 Electrical characteristics

Table 29. Characteristics

Symbol	Parameter	Conditions		Min	Тур	Max	Unit
fi	input frequency			-	13.56	-	MHz
C <sub>i</sub>	input capacitance	16 pF version (bare silicon and MOA8)	[1]	14.08	16	17.92	pF
		50 pF version	[1]	44	50	56	pF
EEPROM ch	naracteristics			1			'
t <sub>cy(W)</sub>	write cycle time			-	4.1	-	ms
t <sub>ret</sub>	retention time	T <sub>amb</sub> = 22 °C		10	-	-	year
N <sub>endu(W)</sub>	write endurance	T <sub>amb</sub> = 22 °C		100000	-	-	cycle

<sup>[1]</sup>  $T_{amb}$  = 22 °C, f = 13.56 MHz,  $V_{LaLb}$  = 1.5 V RMS

MIFARE Ultralight C - Contactless ticket IC

# 12 Wafer specification

Table 30. Wafer specifications MF0ICU2x01DUy

200 mm typical (8 inches)
210 mm
laser dicing
120 μm ± 15 μm
75 μm ± 10 μm
not applicable
61942
Si
ground and stress relieve
$R_a \max = 0.2 \mu m$
R <sub>t</sub> max = 2 μm
x = 710 μm
y = 710 μm
typical = 22 μm
minimum = 5 μm
sandwich structure
PSG / nitride
500 nm / 600 nm
> 99.9 % pure Au
35 to 80 HV 0.005
> 70 MPa
18 µm
within a die = ±2 μm
within a wafer = ±3 μm
wafer to wafer = ±4 μm
minimum = ±1.5 μm
minimum = $\pm 1.5 \mu$ m  LA, LB, VSS, TP1, TP2 <sup>[2]</sup> = $60 \mu$ m × $60 \mu$ m

<sup>[1]</sup> The step size and the gap between chips may vary due to changing foil expansion

MF0ICU2

All information provided in this document is subject to legal disclaimers.

<sup>[2]</sup> Pads VSS and TESTIO are disconnected when wafer is sawn.

MIFARE Ultralight C - Contactless ticket IC

## 12.1 Fail die identification

Electronic wafer mapping covers the electrical test results and additionally the results of mechanical/visual inspection. No ink dots are applied.

# 12.2 Package outline

For more details on the contactless modules MOA8 please refer to Ref. 11 and Ref. 12.

## MIFARE Ultralight C - Contactless ticket IC





Figure 17. Package outline SOT500-2

## MIFARE Ultralight C - Contactless ticket IC




MF0ICU2

MIFARE Ultralight C - Contactless ticket IC

## 12.3 Bare die outline

For more details on the wafer delivery forms see Ref. 13.



MIFARE Ultralight C - Contactless ticket IC

# 13 Abbreviations

## Table 31. Abbreviations

Acronym	Description
3DES	Triple Data Encryption Standard
ACK	Positive Acknowledge
ATQA	Answer To ReQuest, type A
BCC	Block Check Characters byte
CBC	Cipher-Block Chaining
CRC	Cyclic Redundancy Check
СТ	Cascade Tag, Type A
EEPROM	Electrically Erasable Programmable Read-Only Memory
fc	carrier frequency 13.56 MHz
HLTA	Halt A command
IV	Initial Value
LSB	Least Significant Bit
MSB	Most Significant Bit
NAK	Negative AcKnowledge
OTP	One Time Programmable
Passive ACK	Implicit acknowledge without PICC answer
PCD	Proximity Coupling Device
PICC	Proximity Integrated Circuit Card
POR	Power On Reset
REQA	ReQuest Answer, type A
RF	Radio Frequency
SAK	Select AcKnowledge, type A
UID	Unique Identifier
WUPA	Wake-UP command, type A

MIFARE Ultralight C - Contactless ticket IC

## 14 References

[1]

ISO/IEC 14443-2

2001

[2]

ISO/IEC 14443-3

2001

[3]

MIFARE Interface Platform Type Identification Procedure

Application note, BL-ID Doc. No.: 0184\*\* 2

[4]

MIFARE ISO/IEC 14443 PICC Selection

Application note, BU S&C Doc. No.: 1308\*\*

[5]

MIFARE Ultralight Features and Hints

Application note, BU S&C Doc. No.: 0731\*\*

[6]

MIFARE Ultralight as Type 2 Tag

Application note, BU S&C Doc. No.: 1303\*\*

[7]

MIFARE (Card) Coil Design Guide

Application note, BU S&C Doc. No.: 0117\*\*

[8]

MF0ICU1 Functional specification MIFARE Ultralight

Product data sheet, BU S&C Doc. No. 0286\*\*

[9]

NIST SP800-67: Recommendation for the Triple Data Encryption Algorithm (TDEA) Block Cipher, Version 1.1 May 19, 2008

National Institute of Standards and Technology

[10]

ISO/IEC 10116: Information technology - Security techniques - Modes of operation for an n-bit block cipher, February 1, 2006

International Organization for Standardization

[11]

2 \*\* ... document version number

© 2024 NXP B.V. All rights reserved.

Product data sheet

MIFARE Ultralight C - Contactless ticket IC

[12]

# **Contactless smart card module specification MOA8**

Delivery Type Description, BU-ID Document number 1636\*\*<sup>2</sup>

[13]

## General specification for 8" wafer on UV-tape; delivery types

Delivery Type Description, BU-ID Document number 1005\*\*2

MIFARE Ultralight C - Contactless ticket IC

# 15 Revision history

## Table 32. Revision history

Document ID	Release date	Data sheet status	Change notice	Supersedes		
MF0ICU2 v. 3.4	20 March 2024	Product data sheet	-	MF0ICU2 v. 3.3		
Modifications:	Removed MOA4 Type numbers out of the Ordering Information and through the data sheet. Portfolio streamline to MOA8 module.					
MF0ICU2 v. 3.3	30 July 20219	Product data sheet	-	MF0ICU2 v. 3.2		
Modifications:	<ul> <li>Updated descriptive text of the default user memory content, <u>Section 7.5.9</u></li> <li>Update of <u>Table 13</u></li> </ul>					
MF0ICU2 v. 3.2	17 June 2014	Product data sheet		137631		
	<ul> <li>Added 75 µm thin wafer and MOA8 delivery types</li> <li>New bare die outline drawing</li> <li>Corrected descriptive text in delivery forms for the 16 pF input capacitance</li> <li>Extended EEPROM specification with respect to programming cycle endurance and data retention</li> <li>New command descriptions including time-out specification</li> <li>Added descriptions for authentication, counter and lock bytes</li> <li>Removed ISO/IEC 14443-3 anticollision and selection commands and referred to standard</li> </ul>					
	<ul><li>Extended EEPROM sp</li><li>New command descrip</li><li>Added descriptions for</li></ul>	ecification with respect to tions including time-out s authentication, counter a	programming cycle endu pecification nd lock bytes	ırance and data retention		
137631	<ul><li>Extended EEPROM sp</li><li>New command descrip</li><li>Added descriptions for</li></ul>	ecification with respect to tions including time-out s authentication, counter a	programming cycle endu pecification nd lock bytes	ırance and data retention		
137631 Modifications:	<ul> <li>Extended EEPROM sp</li> <li>New command descrip</li> <li>Added descriptions for</li> <li>Removed ISO/IEC 144</li> </ul>	ecification with respect to tions including time-out s authentication, counter a 43-3 anticollision and select	programming cycle endu pecification nd lock bytes	erred to standard		
	<ul> <li>Extended EEPROM sp</li> <li>New command descrip</li> <li>Added descriptions for</li> <li>Removed ISO/IEC 144</li> <li>02 April 2009</li> </ul>	ecification with respect to tions including time-out s authentication, counter a 43-3 anticollision and select	programming cycle endu pecification nd lock bytes	erred to standard		
Modifications:	Extended EEPROM sp     New command descrip     Added descriptions for     Removed ISO/IEC 144      02 April 2009     Section 16 "Legal information of the section of t	ecification with respect to tions including time-out s authentication, counter a 43-3 anticollision and selection	programming cycle endu pecification nd lock bytes	erred to standard		
Modifications:	Extended EEPROM sp     New command descrip     Added descriptions for     Removed ISO/IEC 144     02 April 2009     Section 16 "Legal information of the section of th	ecification with respect to tions including time-out s authentication, counter a 43-3 anticollision and selection	programming cycle endu pecification nd lock bytes	erred to standard		
Modifications: 137630 Modifications:	Extended EEPROM sp     New command descrip     Added descriptions for     Removed ISO/IEC 144     02 April 2009     Section 16 "Legal information 18 February 2009     General update	ecification with respect to tions including time-out s authentication, counter a 43-3 anticollision and selection	programming cycle endu pecification nd lock bytes	erred to standard  137630  137610		

MIFARE Ultralight C - Contactless ticket IC

# Legal information

#### Data sheet status

Document status <sup>[1][2]</sup>	Product status <sup>[3]</sup>	Definition
Objective [short] data sheet	Development	This document contains data from the objective specification for product development.
Preliminary [short] data sheet	Qualification	This document contains data from the preliminary specification.
Product [short] data sheet	Production	This document contains the product specification.

- [1] Please consult the most recently issued document before initiating or completing a design.
- [2] The term 'short data sheet' is explained in section "Definitions".
- [3] The product status of device(s) described in this document may have changed since this document was published and may differ in case of multiple devices. The latest product status information is available on the Internet at URL <a href="https://www.nxp.com">https://www.nxp.com</a>.

### **Definitions**

**Draft** — A draft status on a document indicates that the content is still under internal review and subject to formal approval, which may result in modifications or additions. NXP Semiconductors does not give any representations or warranties as to the accuracy or completeness of information included in a draft version of a document and shall have no liability for the consequences of use of such information.

Short data sheet — A short data sheet is an extract from a full data sheet with the same product type number(s) and title. A short data sheet is intended for quick reference only and should not be relied upon to contain detailed and full information. For detailed and full information see the relevant full data sheet, which is available on request via the local NXP Semiconductors sales office. In case of any inconsistency or conflict with the short data sheet, the full data sheet shall prevail.

**Product specification** — The information and data provided in a Product data sheet shall define the specification of the product as agreed between NXP Semiconductors and its customer, unless NXP Semiconductors and customer have explicitly agreed otherwise in writing. In no event however, shall an agreement be valid in which the NXP Semiconductors product is deemed to offer functions and qualities beyond those described in the Product data sheet.

#### **Disclaimers**

Limited warranty and liability — Information in this document is believed to be accurate and reliable. However, NXP Semiconductors does not give any representations or warranties, expressed or implied, as to the accuracy or completeness of such information and shall have no liability for the consequences of use of such information. NXP Semiconductors takes no responsibility for the content in this document if provided by an information source outside of NXP Semiconductors.

In no event shall NXP Semiconductors be liable for any indirect, incidental, punitive, special or consequential damages (including - without limitation - lost profits, lost savings, business interruption, costs related to the removal or replacement of any products or rework charges) whether or not such damages are based on tort (including negligence), warranty, breach of contract or any other legal theory.

Notwithstanding any damages that customer might incur for any reason whatsoever, NXP Semiconductors' aggregate and cumulative liability towards customer for the products described herein shall be limited in accordance with the Terms and conditions of commercial sale of NXP Semiconductors.

Right to make changes — NXP Semiconductors reserves the right to make changes to information published in this document, including without limitation specifications and product descriptions, at any time and without notice. This document supersedes and replaces all information supplied prior to the publication hereof.

Suitability for use — NXP Semiconductors products are not designed, authorized or warranted to be suitable for use in life support, life-critical or safety-critical systems or equipment, nor in applications where failure or malfunction of an NXP Semiconductors product can reasonably be expected to result in personal injury, death or severe property or environmental damage. NXP Semiconductors and its suppliers accept no liability for inclusion and/or use of NXP Semiconductors products in such equipment or applications and therefore such inclusion and/or use is at the customer's own risk

**Applications** — Applications that are described herein for any of these products are for illustrative purposes only. NXP Semiconductors makes no representation or warranty that such applications will be suitable for the specified use without further testing or modification.

Customers are responsible for the design and operation of their applications and products using NXP Semiconductors products, and NXP Semiconductors accepts no liability for any assistance with applications or customer product design. It is customer's sole responsibility to determine whether the NXP Semiconductors product is suitable and fit for the customer's applications and products planned, as well as for the planned application and use of customer's third party customer(s). Customers should provide appropriate design and operating safeguards to minimize the risks associated with their applications and products.

NXP Semiconductors does not accept any liability related to any default, damage, costs or problem which is based on any weakness or default in the customer's applications or products, or the application or use by customer's third party customer(s). Customer is responsible for doing all necessary testing for the customer's applications and products using NXP Semiconductors products in order to avoid a default of the applications and the products or of the application or use by customer's third party customer(s). NXP does not accept any liability in this respect.

Limiting values — Stress above one or more limiting values (as defined in the Absolute Maximum Ratings System of IEC 60134) will cause permanent damage to the device. Limiting values are stress ratings only and (proper) operation of the device at these or any other conditions above those given in the Recommended operating conditions section (if present) or the Characteristics sections of this document is not warranted. Constant or repeated exposure to limiting values will permanently and irreversibly affect the quality and reliability of the device.

Terms and conditions of commercial sale — NXP Semiconductors products are sold subject to the general terms and conditions of commercial sale, as published at https://www.nxp.com/profile/terms, unless otherwise agreed in a valid written individual agreement. In case an individual agreement is concluded only the terms and conditions of the respective agreement shall apply. NXP Semiconductors hereby expressly objects to applying the customer's general terms and conditions with regard to the purchase of NXP Semiconductors products by customer.

No offer to sell or license — Nothing in this document may be interpreted or construed as an offer to sell products that is open for acceptance or the grant, conveyance or implication of any license under any copyrights, patents or other industrial or intellectual property rights.

MF0ICU2

All information provided in this document is subject to legal disclaimers.

### MIFARE Ultralight C - Contactless ticket IC

**Quick reference data** — The Quick reference data is an extract of the product data given in the Limiting values and Characteristics sections of this document, and as such is not complete, exhaustive or legally binding.

**Export control** — This document as well as the item(s) described herein may be subject to export control regulations. Export might require a prior authorization from competent authorities.

Suitability for use in non-automotive qualified products — Unless this document expressly states that this specific NXP Semiconductors product is automotive qualified, the product is not suitable for automotive use. It is neither qualified nor tested in accordance with automotive testing or application requirements. NXP Semiconductors accepts no liability for inclusion and/or use of non-automotive qualified products in automotive equipment or applications.

In the event that customer uses the product for design-in and use in automotive applications to automotive specifications and standards, customer (a) shall use the product without NXP Semiconductors' warranty of the product for such automotive applications, use and specifications, and (b) whenever customer uses the product for automotive applications beyond NXP Semiconductors' specifications such use shall be solely at customer's own risk, and (c) customer fully indemnifies NXP Semiconductors for any liability, damages or failed product claims resulting from customer design and use of the product for automotive applications beyond NXP Semiconductors' standard warranty and NXP Semiconductors' product specifications.

**Translations** — A non-English (translated) version of a document, including the legal information in that document, is for reference only. The English version shall prevail in case of any discrepancy between the translated and English versions.

Security — Customer understands that all NXP products may be subject to unidentified vulnerabilities or may support established security standards or specifications with known limitations. Customer is responsible for the design and operation of its applications and products throughout their lifecycles to reduce the effect of these vulnerabilities on customer's applications and products. Customer's responsibility also extends to other open and/or proprietary technologies supported by NXP products for use in customer's applications. NXP accepts no liability for any vulnerability. Customer should regularly check security updates from NXP and follow up appropriately. Customer shall select products with security features that best meet rules, regulations, and standards of the intended application and make the ultimate design decisions regarding its products and is solely responsible for compliance with all legal, regulatory, and security related requirements concerning its products, regardless of any information or support that may be provided by NXP.

NXP has a Product Security Incident Response Team (PSIRT) (reachable at <a href="PSIRT@nxp.com">PSIRT@nxp.com</a>) that manages the investigation, reporting, and solution release to security vulnerabilities of NXP products.

**NXP B.V.** — NXP B.V. is not an operating company and it does not distribute or sell products.

#### **Trademarks**

Notice: All referenced brands, product names, service names, and trademarks are the property of their respective owners.

NXP — wordmark and logo are trademarks of NXP B.V.

MIFARE — is a trademark of NXP B.V.

MIFARE Ultralight — is a trademark of NXP B.V.

12.1 12.2 12.3 13 14 15

# MIFARE Ultralight C - Contactless ticket IC

## **Contents**

1	General description	1
1.1	Contactless energy and data transfer	1
1.2	Anticollision	
1.3	Security	2
1.4	Naming conventions	
2	Features and benefits	2
2.1	MIFARE RF Interface (ISO/IEC 14443 A)	
2.2	EEPROM	
3	Quick reference data	3
4	Ordering information	3
5	Block diagram	4
6	Pinning information	
6.1	Smart card contactless module	4
7	Functional description	5
7.1	Block description	5
7.2	State diagram and logical states description .	5
7.2.1	IDLE	
7.2.2	READY1	6
7.2.3	READY2	7
7.2.4	ACTIVE	7
7.2.5	HALT	
7.2.6	AUTHENTICATED	7
7.3	Data integrity	8
7.4	RF interface	8
7.5	Memory organization	
7.5.1	UID/serial number	9
7.5.2	Lock byte 0 and 1	
7.5.3	Lock byte 2 and 3	10
7.5.4	OTP bytes	
7.5.5	3DES Authentication	
7.5.6	3DES Authentication example	13
7.5.7	Programming of 3DES key to memory	14
7.5.8	Configuration for memory access via 3DES	
	Authentication	
7.5.9	Data pages	
7.5.10	Initial memory configuration	
7.5.11	Counter	
8	Command overview	
8.1	MIFARE Ultralight C command overview	
8.2	Timings	
8.3	MIFARE Ultralight C ACK and NAK	
8.4	Summary of device identification data	19
9	MIFARE Ultralight C - Contactless ticket	
	IC commands	19
9.1	MIFARE Ultralight C - Contactless ticket IC	
	card activation	-
9.2	READ	-
9.3	WRITE	
9.4	COMPATIBILITY WRITE	
9.5	AUTHENTICATE	
10	Limiting values	
11	Characteristics	
11.1	Electrical characteristics	25

Wafer specification	26
Fail die identification	27
Package outline	27
Bare die outline	30
Abbreviations	31
References	32
Revision history	34
Legal information	

Please be aware that important notices concerning this document and the product(s) described herein, have been included in section 'Legal information'.