

High Brightness LED Controller using the MC9RS08KA2

Designer Reference Manual

RS08 Microcontrollers

DRM080 Rev. 0 5/2006



freescale.com





High Brightness LED Controller using the MC9RS08KA2

Designer Reference Manual

by: Dennis Lui, Vincent Ko Freescale Semiconductor, Inc. Hong Kong

To provide the most up-to-date information, the revision of our documents on the World Wide Web will be the most current. Your printed copy may be an earlier revision. To verify that you have the latest information available, refer to http://www.freescale.com

The following revision history table summarizes changes contained in this document. For your convenience, the page number designators have been linked to the appropriate location.

Revision History

Date	Revision Level	Description	Page Number(s)
05/2006	0	Initial release	N/A



Revision History



Table of Contents

Chapter 1 Introduction 1.1 1.2 1.3 1.4 Chapter 2 **Control Theory** 2.1 2.2 **Chapter 3 Hardware Implementation** 3.1 3.2 3.3 3.3.1 3.3.2 3.3.3 3.3.4 3.3.5 3.4 3.4.1 3.4.2 3.4.3 3.4.4 3.4.5 3.4.6 3.4.7 3.4.8 Chapter 4 Software Implementation 4.1 4.2 4.2.1 4.2.2 4.2.3 4.2.4 4.2.5



Table of Contents

	Chapter 5 Testing	
5.1	Measurement Data	23
5.2	Customization	24
5.2.1	Hardware	24
	Chapter 6	
	Demo Setup	
6.1	Introduction	25
6.2	Default Settings	25
6.3	Programming and Running the HB-LED Demo	25
6.4	Troubleshooting	26
	Appendix A.	

Schematic

Appendix B. Program Listing

High Brightness LED Controller using the MC9RS08KA2, Rev. 0



Chapter 1 Introduction

1.1 Introduction

This document describes a reference design of a high brightness LED control solution using the MC9RS08KA2 microcontroller.

Recently, light emitting diodes (LEDs) have become very popular in general lighting area as a replacement technology for halogen low-voltage lighting. Customers are quickly recognizing the advantages of using LED lighting, which include long operating life, no fragile glass, no mercury, and low voltage DC operated.

In general, LEDs have a nonlinear I-V behavior and thus current limitation is required to prevent the power dissipation to exceed a maximum limit. Thus, the ideal source for LED driving is a constant current source. The concept of this application is a MCU based LED driver with closed-loop current control. A compact LED light source with dimming control is implemented to demonstrate the advantages of using MCU to drive a high brightness LED with different average current settings.

All hardware schematic diagrams and firmware source codes are available as reference materials.

1.2 Features

- High brightness LED driver with 350mA current driving capability
- Control a buck converter to regulate supply voltage to match with different LED forward voltages
- Up to 80% efficiency
- Internally generated PWM switching frequency
- · Feedback control on LED forward current through a current sense resistor
- Dimming control by a single button

1.3 System Overview

A block diagram of the system is shown in Figure 1-1.



Introduction




Figure 1-1. System Block Diagram

1.4 Freescale's New Generation Ultra Low Cost MCU

The MC9RS08KA2 (KA2) microcontroller unit (MCU) is an extremely low cost, small pin count device for home appliances, toys, small geometry, and LED control applications. This device is composed of standard on-chip modules including a very small and highly efficient RS08 CPU core, 62 bytes RAM, 2K bytes FLASH, an 8-bit modulo timer, keyboard interrupt, and analog comparator. The device is available in small 6- and 8-pin packages.

MC9RS08KA2 Features:

- Simplified S08 instruction set with added high-performance instructions
- 2048 bytes on-chip FLASH EEPROM
- 62 bytes on-chip RAM
- Internal clock source
- Up to 10-MHz internal bus operation
- Background debug system
- Power-saving modes
- Low-voltage detection
- 8-bit modulo timer
- Analog comparator
- Keyboard interrupt ports

Timer system features include:

- 8-bit up-counter
 - Free-running or 8-bit modulo limit
 - Software controllable interrupt on overflow
 - Counter reset bit (TRST)
 - Counter stop bit (TSTP)





- Four software selectable clock sources for input to prescaler:
 - System bus clock rising edge
 - Fixed frequency clock (XCLK) rising edge
 - External clock source on the TCLK pin rising edge
 - External clock source on the TCLK pin falling edge
- Nine selectable clock prescale values:
 - Clock source divide by 1, 2, 4, 8, 16, 32, 64, 128, or 256

The analog comparator has the following features:

- Full rail-to-rail supply operation
- Less than 40 mV of input offset
- Less than 15 mV of hysteresis
- Selectable interrupt on rising edge, falling edge, or either rising or falling edges of comparator output
- Option to compare to fixed internal bandgap reference voltage
- Option to allow comparator output to be visible on a pin, ACMPO
- Remains operational in stop mode

The KBI features include:

- Each keyboard interrupt pin has individual pin enable bit
- Each keyboard interrupt pin is programmable as falling edge (or rising edge) only, or both falling edge and low level (or both rising edge and high level) interrupt sensitivity
- One software-enabled keyboard interrupt
- Exit from low-power modes



Introduction



Chapter 2 Control Theory

2.1 Switching Regulator

A switching regulator regulates a current flow by chopping up the input voltage and controlling the average current by means of the duty cycle. When a higher load current is required by the load, the percentage of on-time is increased to accommodate the change. There are two basic types of switching regulators: forward-mode regulators and flyback-mode regulators. The name of each type is derived from the way the magnetic elements are used within the regulator.

Forward-mode switching regulators have four functional components: a power switch, a rectifier, a series inductor, and a capacitor (see Figure 2-1). The power switch may be a power transistor or a metal oxide semiconductor field-effect transistor (MOSFET) placed directly between the input voltage and the LC filter section. The shunt diode, series inductor, and shunt capacitor form an energy storage tank whose purpose is to store enough energy to maintain the load voltage and current over the entire off-time of the power switch. The power switch serves only to fill up the energy lost to the load during its off-time. Flyback-mode switching regulators have the same four basic elements as the forward-mode regulators except that they have been rearranged in another configuration. In this design, forward-mode switching is used.




Figure 2-1. Forward Mode Switching Regulator

2.2 Buck Converter Basics

A "buck" or step-down converter is the most elementary forward-mode converter. Its basic schematic can be seen in Figure 2-1.

The operation of this regulator topology has two distinct time periods. The first one occurs when the series switch SW1 is on, the input voltage V_{in} is connected to the input of the inductor L. The output of the inductor is the output voltage, and the rectifier (or catch diode) is reverse biased. During this period, since there is a constant voltage source connected across the inductor, the inductor current begins to linearly ramp upwards, as described by the following equation:

$$I_{L(on)} = [(V_{in} - V_{out}) \times t_{on}]/L$$
 (EQ 2-1)

High Brightness LED Controller using the MC9RS08KA2, Rev. 0



Control Theory

During this "on" period, energy is stored within the core material in the form of magnetic flux. If the inductor is properly designed, there is sufficient energy stored to carry the requirements of the load during the "off" period.

The next period is the "off" period of the power switch. When the power switch turns off, the voltage across the inductor reverses its polarity and is clamped at one diode voltage drop below ground by the catch diode. The current now flows through the catch diode thus maintaining the load current loop. This removes the stored energy from the inductor. The inductor current during this time is:

$$I_{L(off)} = [(V_{out} - V_D) \times t_{off}]/L$$
 (EQ 2-2)

This period ends when the power switch is once again turned on. Regulation of the converter is accomplished by varying the duty cycle of the power switch according to the loading conditions. To achieve this, the power switch requires electronic control for proper operation. It is possible to describe the duty cycle as follows:

$$d = t_{on}/T (EQ 2-3)$$

where T is the switching period.

For the buck converter with ideal components, the duty cycle can also be described as:

$$d = V_{out}/V_{in}$$
 (EQ 2-4)



Chapter 3 Hardware Implementation

3.1 Introduction

The system consists of the 8-pin packaged KA2 and external components. There are four major external components: P-channel MOSFET, schottky diode, inductor, and capacitor which are used for switching regulation. The KA2 is used as a PWM controller to control the HB-LED brightness level. A simple DC to DC step-down converter (buck topology) is implemented to convert the 5V input supply to a current regulated output for LED driving. The integrated open source BDM (background debug mode) design allows users to program the MCU FLASH and debug applications via a USB connection.




Figure 3-1. High Brightness LED Control Board

3.2 Functional Pin Assignment

- PA0 Reference Voltage Input
- PA1 Feedback Input
- PA2 Push Button Input
- PA3 Dimming Control DIM0
- PA4 PWM Output
- PA5 Dimming Control DIM1

3.3 Hardware Functions

Figure 3-2 shows a block diagram of the HB-LED reference design. The hardware functions can be divided into the following parts:

- PWM Control
- Feedback Loop
- Reference Voltage
- User Interface
- Background Debug Interface



Hardware Implementation




Figure 3-2. Functional Block Diagram

3.3.1 PWM Control

A fixed frequency step-down (buck) DC to DC converter is implemented with the KA2 for usage in high brightness LED driving applications. The KA2 consists of all active functions required to directly implement a step-down converter with a minimum number of external components. The KA2 enables control of PWM on power switch device to regulate the LED current. The PMOS device ON/OFF switching is controlled by MCU timer module and the frequency is set to around 30kHz. Base the on analog comparator output result, the MCU adjusts the PWM duty cycle in closed-loop to keep the LED driving current as a constant. Since a P-channel MOSFET device is used as the power switch, the PWM control signal should be generated in active low polarity, that means the power switch will turn on if the PWM signal is in LOW level.

A switching cycle is initiated by the falling edge of the PWM signal. At the moment the power switch Q1 is turned on, the inductor is connected to V_{DD} and the inductor current begins to ramp up linearly. When the PWM signal is in HIGH state, the power switch Q1 turns off and the current flows through the diode D to maintain the current loop. The capacitor C_{O} filters the regulated output and provides the converter loop stability. The converter is designed to operate in continuous conduction mode, which means the inductor current will not decrease to zero before the new cycle start. The average inductor current I_{L} is almost equal to the average loading current I_{O} .






Figure 3-3. PWM Control Waveforms

The external pull-up resistor R4 ensures the PMOS device Q1 is in OFF state during power up period, and prevents a high current surge through the LED before MCU controls the system.

3.3.2 Feedback Loop

The KA2 features an analog comparator which can be used to determine the LED current. The inverting input pin and non-inverting input pin are used for current sense feedback input and reference voltage input respectively.

Current limiting is implemented by monitoring the LED forward current, which is one of the key parameters affecting the performance of LED, particularly on the operating life time, so it is important to control and make sure the average current and peak current are also within the limits specified in the LED specification.

The LED forward current is converted to a voltage by using an external resistor connected in series with the LED. The voltage across the current sense resistor R_S is directly proportional to the current through LED. This feedback voltage is compared against a reference by the analog comparator. When the feedback voltage is higher than the level at reference input, the PMOS switch ON time reduces to limit the current accumulated at the inductor L. In contrast, the PMOS switch ON time increases again to pump more current into the inductor when the feedback voltage is lower than the reference level. The upper and lower threshold levels are defined by the hysteresis range of the comparator.




Figure 3-4. Feedback Control Waveforms

High Brightness LED Controller using the MC9RS08KA2, Rev. 0



Hardware Implementation

In steady-state condition, the LED forward current I_{LED} is equal to the reference voltage V_{REF} divided by the current sense resistor R_S .

The LED forward current is determined by the following equation:

$$I_{LED} = \frac{V_{REF}}{R_S}$$
 (EQ 3-1)

A simple low-pass filter is added between the current sense resistor R_S and the feedback path to eliminate any high frequency noises coupling into the feedback pin, However, the response time of the filter should be fast enough to track the deviation of the voltage across the current sense resistor R_S .

In this reference design, the PWM switching frequency is around 30kHz and the filter cut-off frequency is set to 5kHz.

The following equation shows the relationship between the filter cut-off frequency and the RC values:

$$f = \frac{1}{2\pi RC}$$
 (EQ 3-2)

3.3.3 Reference Voltage

The reference voltage in the comparator non-inverting input is determined by a resistor network which consists of three resistors and the connection paths are controlled by the MCU. The pin DIM0 is always configured as output pin and set to output LOW. The resistor R2 connects to ground and generates a reference voltage divided from V_{DD} . This is the default reference voltage and corresponds to 100% brightness level. When the pin DIM1 is set to output LOW, R3 is also connected to ground and in parallel with R2, the reference voltage will be further reduced to a lower level. The DIM1 pin should be configured as input state if it is not used in dimming selection.

The equations for determining the reference voltage with the divider network are:

For High brightness:

$$V_{REF} = V_{DD} \left(\frac{R_2}{R_1 + R_2} \right)$$
 (EQ 3-3)

For Low brightness:

$$V_{REF} = V_{DD} \left(\frac{R_p}{R_1 + R_p} \right)$$
 (EQ 3-4)

where R_p is equal to R2 parallel with R3.



3.3.4 User Interface

A single push button, SW, is used as user interface to toggle the LED brightness level between 100% and 40% (default brightness level is 100%). The dimming control is accomplished by changing the LED forward current which is set by the reference voltage applied at the comparator's non-inverting input.

Table 3-1. Dimming Control

Control Pins	100% Brightness	40% Brightness
DIM0	Output LOW	Output LOW
DIM1	Hi-Z	Output LOW

3.3.5 Background Debug Interface

The on-board open source BDM provides a cost effective debug solution for Freescale RS08 MCUs. The module utilizes the modified version of popular open-source BDM solution from the Internet for in-circuit emulation and device programming. The board comprises a 12V DC-DC converter for RS08 FLASH programming support.

NOTE

In circuit debug can not be used for this application program since the BKGD pin is used for dimming control purpose. Use JP3 to switch between BDM and user mode.

3.4 Design Procedures

This section presents guidelines for selecting external components.

3.4.1 High Brightness LED

The system is designed to drive a high brightness LED with typical 350 mA forward current at 3.5V forward voltage, i.e. the power dissipation on the LED is around 1.2W.

3.4.2 Current Sense Resistor

The value of the current sense resistor R_S is determined by two factors: power dissipation on R_S and the threshold level for comparator input. Smaller R_S reduces power dissipation but the detection of feedback signal in comparator is more difficult.

Base on equation (EQ 3-1), setting R_S to 1Ω , the feedback voltage is equal to 350mV.

Power dissipation on R_S is around 120mW, $I^2R = (350mA)^2 \times 1\Omega$, which is reasonable compared to LED power.

3.4.3 RC Network

Base on equations (EQ 3-3) and (EQ 3-4), set $V_{DD} = 5V$, R1 = $10k\Omega$, R2 = 750Ω , R3 = 500Ω .

The reference voltage for high and low brightness settings are equal to 350mV and 146mV respectively. Low brightness setting is corresponds to around 40% brightness level.

High Brightness LED Controller using the MC9RS08KA2, Rev. 0 Freescale Semiconductor 17



Hardware Implementation

3.4.4 Inductor Value

We can determine the inductor value by using the following equations:

$$V_L = L \times \frac{di}{dt}$$
 (EQ 3-5)

$$L = (V_S - V_O) \times \frac{D \times T}{I_{ripple}}$$
 (EQ 3-6)

$$L = (5 - 3.85) \times \frac{\frac{3.85}{5} \times \frac{1}{30K}}{0.35 \times 0.25} = 337 \mu H$$
 (EQ 3-7)

where: V_L is inductor voltage, V_S is source voltage, V_O is output voltage

D is conduction duty cycle, T is conduction period

 I_{ripple} is inductor peak-to-peak ripple current, set to 25% of output current

The inductor current rating must be higher than the maximum peak current flowing through the inductor.

3.4.5 Output Capacitor

Low ESR (equivalent series resistance) aluminium or solid tantalum capacitor is recommended for low output ripple voltage. The ESR of the output capacitor and the inductor ripple current are two major factors contributing to the output ripple voltage.

3.4.6 P-Channel MOSFET

For superior switching performance, a P-channel MOSFET device with low on-state resistance and low gate charge should be selected. The current rating must be at least 1.2 times greater than the maximum load current and the drain-to-source breakdown voltage should be at least 1.25 times the maximum input voltage. The P-channel MOSFET NTR4502 from On Semiconductor is selected in this design.

3.4.7 Schottky Diode Rating

A diode with a high forward voltage drop or long turn-on delay time should not be used, so a fast switching and low drop schottky diode is selected. The current and reverse voltage rating requirements should be similar to the P-channel MOSFET device. The schottky diode MBR130 from On Semiconductor is used in this design.

3.4.8 PCB Layout Guidelines

The PCB layout is very important for switching converter design and is critical to reduce noise and ensure specified performance. Care should be taken in PCB layout to avoid rapidly switching currents to generate voltage transients and affect the desired operation.

- Minimize inductance and ground loops, the length of the leads indicated by heavy lines should be kept as short as possible. (e.g. PMOS / coil / schottky diode.)
- Minimize the trace from the current sense resistor to the feedback input and keep it away from noise sources to avoid noise pick up.
- Locate the sensitive voltage reference divider network close to MCU.
- Single ground point or ground plane design should be used.


High Brightness LED Controller using the MC9RS08KA2, Rev. 0



Chapter 4 Software Implementation

4.1 Introduction

The software is designed with a main loop to monitor the feedback voltage from the LED and generate a PWM controlled waveform for DC to DC switching operation. The PWM timing is constructed by the modulo timer overflow periods of PWM ON time & OFF time and the software overhead using for user interface detection & feedback loop control (see Figure 4-1). The timing used for each branch routine paths should be keep as constant such that the period of the generated PWM is stable and independent of the executed routine path.



- 1. Set PWM ON; detect KBI, Check ACMP, and adjust ONTime & OFFTime (software overhead)
- 2. MTIMMOD = ONTime
- 3. MTIM overflow; set PWM OFF; MTIMMOD = OFFTime
- 4. MTIM overflow again

Figure 4-1. PWM Timing

4.2 Software Design

This section describes the design of the software blocks. The software description comprises these topics:

- Main Software Flow
- Initialization
- KBI Detection
- Feedback Comparison
- PWM Generation

4.2.1 Main Software Flow

Figure 4-2 shows the flow of the main program, it also indicates the functions that KA2 are to perform. The initialization subroutine initializes the modules of real-time interrupt, modulo timer, analog comparator, and keyboard interrupt.



Software Implementation




Figure 4-2. Main Software Flow

4.2.2 Initialization

The Initialization routine initializes the MCU with following configurations:

- Initializes ICS and sets bus clock to 10MHz
- Initializes page register, disables COP and BKGD
- Enables LVI, and sets RTI to 128ms
- Initializes RAM variables
- Initializes GPIO
- Initializes KBI
- Initializes the ACMP
- Initializes modulo timer
 - Timer prescalar = 1, timer clock = 10MHz
 - Maximum of period = 25.6μs
 - Timer resolution = 100ns

4.2.3 KBI Detection

The state of the user interface is scanned every 128ms to see if any button press event has occurred. When a key press event is detected, it sets the corresponding "Pressed" flag. The output state of DIM1 pin will toggle to setup a new reference voltage for ACMP in the next 128ms period. This is to set up a key debounce period of 128ms.

The real-time interrupt function is used to generate a periodic interrupt for KBI scanning. The RTI is driven from the 1kHz internal clock reference and the wake-up period is set to 128ms.






Figure 4-3. KBI Detection Routine

4.2.4 Feedback Comparison

The function of the feedback comparison routine is to control the PWM duty cycle periodically. When it detects a crossover point between the feedback voltage and the reference voltage, the ONTime and OFFTime variables will be updated according to the result of the analog comparator output that is used as a feedback signal to indicate whether the LED current is higher or lower than the expected level.

These two variables should be adjusted in opposite polarity such the overall period is kept constant (i.e. OFFTime = 255 – ONTime). The PWM duty cycle is determined by the value of ONTime. The variables ONTime and OFFTime should be set in the range of 0 to 255.




Figure 4-4. Feedback Comparison Routine

High Brightness LED Controller using the MC9RS08KA2, Rev. 0



Software Implementation

4.2.5 PWM Generation

The 8-bit modulo timer is configured to generate the PWM signal. The timer is running in modulo mode such that the overflow flag will be set when the count value matches the modulo value in the MTIM module register, MTIMMOD. PWM output is implemented by programming two timer overflow variables, ONTime and OFFTime alternately into the MTIM module register.

The overall PWM period is equal to the sum of PWM ON, PWM OFF and the time used for software looping in KBI detection and feedback comparison routines.




Figure 4-5. PWM Generation Routine



Chapter 5 Testing

The reference design was tested with Lumileds high brightness LED in typical conditions. The LED forward current was regulated with expected performance with 5V supply input. Dimming control was achieved by changing the LED current with a single button user interface.

5.1 Measurement Data

Figure 5-1 shows the voltage waveform measured across the current sense resistor R_S in 100% brightness setting. The LED forward current was determined by this voltage divided by one ($R_S = 1\Omega$), which was equal to around 385mA and the peak-to-peak ripple current was 26mA. The measurements show that the LED forward current was regulated and tracking to the reference input accurately. The difference between the calculated target (350mV) and measured voltage (385mV) showing in Figure 5-2 is due to the tolerance of resistors used.




Figure 5-1. Waveform at R_S

High Brightness LED Controller using the MC9RS08KA2, Rev. 0 Freescale Semiconductor 23



Testing




Figure 5-2. Waveform at Reference Input

The efficiency of the whole converter was measured as:

- 1. Supply input = 5V, supply current = 302mA, DC to DC output voltage = 3.5V
- 2. Voltage across R_S = 385mV, LED forward voltage = 3.115V

$$Efficiency = \frac{Output Power}{InputPower}$$
(EQ 5-1)

Efficiency =
$$\frac{3.115 \times 0.385}{5 \times 0.302}$$
 = 79.4% **(EQ 5-2)**

3. Overall efficiency = 79.4%

5.2 Customization

5.2.1 Hardware

The on-board open source BDM is used for development purposes only. It can be removed to make the design more compact and fit into a smaller housing.

The inductor value can be adjusted to match with new LED forward current requirement.



Chapter 6 Demo Setup

6.1 Introduction

This section shows how to setup the MC9RS08KA2 HB-LED demo board and run the included demo program. Users can use the on-board open source BDM module to program the MCU FLASH and debug new applications via the USB connection.

6.2 Default Settings

Figure 6-1 shows the default settings for the demo board. The black blocks indicate the default position of the jumpers. Please check these settings before continuing.




Figure 6-1. Demo Board Default Settings

6.3 Programming and Running the HB-LED Demo

Further application development and debug for the MC9RS08KA2 is supported through the on-board OS-BDM interface. A USB type B connector (S1) provides the connection between the demo board and your host PC. This tool is tested to run on Windows XP with Freescale CodeWarrior version 5.1. Use the procedure below to operate the HB-LED demo board.

The board must be powered by external 5V supply when HB-LED is turned on. Do not use the USB 5V for powering the HB-LED.

Program:

- 1. Move jumper JP3 to the 1-2 position "BDM" to power up device in background debug mode.
- 2. Programme the device with the corresponding software via the USB connection. Refer to documentation in the CD-ROM that came with the HB-LED demo board.



Demo Setup

NOTE

In-circuit debugging cannot be used for this application program since the BKGD pin is used for dimming control purpose. Use JP3 to switch between BDM and user mode.

Run:

- 1. Move jumper JP3 to the 2-3 position "USER" to isolate the "BDC_BKGD" pin.
- 2. Power up the device for software execution in user mode.

NOTE

All RS08 devices require a power-on-reset to switch between user mode and background debug mode.

6.4 Troubleshooting


The high brightness LED does not turn on:

- Make sure jumper JP3 is set to "USER" (2-3) position.
- Make sure supply input selection (JP1) is selected for external power supply.


Unable to program the MCU using the on-board OS-BDM:

Make sure jumper JP3 is set to "BDM" (1-2) position.











Appendix B. Program Listing

```
; ********************
; (c) Copyright Freescale Semiconductor, Inc. 2006
; ALL RIGHTS RESERVED
; *********************
;* HB LED Coding for 9RS08KA2
; *
;* Author:
        Vincent Ko
;* Date:
        Apr 2006
                   LED Driver
;* PTA0/KBI0/ACMP+
;* PTA1/KBI1/ACMP-
                   Voltage Reference
                   Dimming Button
;* PTA2/KBI2/TCLK/RESETb/VPP
;* PTA3/ACMPO/BKGD/MS
                   DIM0
;* PTA4/KBI4
                   PWM
;* PTA5/KBI5
                   DIM1
; include derivative specific macros
    XDEF
        Entry
    include "MC9RS08KA2.inc"
; ICS Definition
ICS_DIV_1
              $00
        equ
              $40
ICS_DIV_2
        equ
ICS_DIV_4
              $80
        equ
ICS_DIV_8
              $c0
        equ
; MTIM Definition
$00
MTIM_DIV_1
        equ
MTIM_DIV_2
        equ
              $01
MTIM_DIV_4
              $02
        equ
MTIM_DIV_8
              $03
        equ
              $04
MTIM_DIV_16
        equ
MTIM_DIV_32
              $05
        equ
MTIM_DIV_64
        equ
              $06
MTIM_DIV_128
              $07
        equ
MTIM_DIV_256
              $08
        equ
MTIM_BUS_CLK
                  $00
              equ
MTIM_XCLK
              equ
                  $10
```

High Brightness LED Controller using the MC9RS08KA2, Rev. 0



Demo Setup

```
MTIM_TCLK_FALLING
             equ
                 $20
MTIM_TCLK_RISING
             equ
                 $30
; ACMP Definition
ACMP_OUTPUT_FALLING
             equ
                 $00
                 $01
ACMP_OUTPUT_RAISING
             equ
ACMP_OUTPUT_BOTH
                 $03
             equ
; RTI Definition
RTI_DISABLE
              $00
        equ
RTI_8MS
              $01
        equ
RTI_32MS
        equ
              $02
RTI_64MS
              $03
        equ
RTI_128MS
        equ
              $04
              $05
RTI_256MS
        equ
RTI_512MS
              $06
        equ
RTI_1024MS
        equ
              $07
; Application Definition
VREF
        equ
             PTAD PTAD0
mVREF
        equ
             mPTAD_PTAD0
             PTAD_PTAD1
LED
        equ
             mPTAD_PTAD1
mLED
        equ
             PTAD_PTAD2
BUTTON
        equ
mBUTTON
        equ
             mPTAD_PTAD2
             PTAD_PTAD3
DIM0
        equ
mDIM0
        equ
             mPTAD_PTAD3
             PTAD_PTAD4
PWM
        equ
mPWM
             mPTAD_PTAD4
        equ
DIM1
        equ
             PTAD_PTAD5
mDIM1
             mPTAD_PTAD5
        equ
; Application Macro
Delay_1_cycle: macro
             ;1 cycles
    nop
    endm
Delay_2_cycles: macro
             ;2 cycles
    tsta
    endm
Delay_3_cycles: macro
    brn
             ;3 cycles
    endm
Delay_4_cycles: macro
    brn
             ;3 cycles
    nop
             ;1 cycles
```

High Brightness LED Controller using the MC9RS08KA2, Rev. 0



```
endm
Delay_5_cycles: macro
                 ;5 cycles
     tstx
     endm
Delay_10_cycles: macro
     tstx
                 ;5 cycles
     tstx
                 ;5 cycles
     endm
Delay_15_cycles: macro
                 ;5 cycles
     tstx
     tstx
                  ;5 cycles
                  ;5 cycles
     tstx
     endm
           TINY_RAMStart
     org
; variable/data section
ONTime
           ds.b 1
Pressed
           ds.b 1
          RAMStart
     org
; variable/data section
     org
           ROMStart
; code section
main:
Entry:
;-----
; Config ICS
; Device is pre-trim to 20MHz ICLK frequency
; TRIM value are stored in $3FFA:$3FFB
           #HIGH_6_13(NV_ICSTRM), PAGESEL
     mov
           MAP_ADDR_6(NV_FTRIM), ICSSC ; $3FFB
;
     mov
           MAP_ADDR_6(NV_ICSTRM), ICSTRM; $3FFA
     mov
           #ICS_DIV_1, ICSC2
                                   ; Use 10MHz
     mov
;Config System
;-----
           #HIGH_6_13(SOPT), PAGESEL
                                ; Init Page register
     mov
           #(mSOPT_COPT|mSOPT_STOPE), MAP_ADDR_6(SOPT); BKGD disable,COP disabled
     mov
           #(mSPMSC1_LVDE | mSPMSC1_LVDRE), MAP_ADDR_6(SPMSC1); LVI enable
     mov
           #(RTI_128MS), MAP_ADDR_6(SRTISC); 128ms RTI
     mov
;-----
; Init RAM
;-----
clr
     ONTime
clr
     Pressed
;-----
; Config GPIO
; PWM - init H
```

High Brightness LED Controller using the MC9RS08KA2, Rev. 0



Demo Setup

```
;-----
           #(mPWM), PTAD
                                   ; Initial port
     mov
           #(mDIM0|mPWM), PTADD
     mov
                                   ; DIMO and PWM Output pins
;Config KBI
     lda
           #mBUTTON
           MAP_ADDR_6(PTAPE)
     sta
                                   ;Enable Pullup
                                   ;KBI Enable
     sta
           KBIPE
     bset
           KBISC_KBACK, KBISC
;-----
;Config ACMP
;-----
           #(mACMPSC_ACME), ACMPSC
                                   ; Enable ACMP
     mov
;Config MTIM
;Timer prescalar=1 -> Timer clk = 10MHz
; Bus = 10MHz
;Max OF period = 25.6us
;Timer resolution = 100ns
     mov
           #(MTIM_BUS_CLK | MTIM_DIV_1), MTIMCLK
     mov
           #255, MTIMMOD
;-----
;PWM Control Loop
;-----
PWMControlLoop:
     bclr
           PWM, PTAD
                                    ; Switch close
; --- Check Button ---
     brset SRTISC_RTIF, MAP_ADDR_6(SRTISC), CheckPress;5
     Delay_10_cycles
     Delay_10_cycles
     Delay_4_cycles
     bra
           CheckACMP
                                    ; 3
CheckPress:
           SRTISC_RTIACK, MAP_ADDR_6(SRTISC);5
     bset
     brset 0, Pressed, ToggleDim
CheckButton:
     brset KBISC_KBF, KBISC, ButtonPressed;5
     Delay_5_cycles
     Delay_4_cycles
     bra
           CheckACMP
                                   ;3
ButtonPressed:
     bset
           KBISC_KBACK, KBISC
                                   ;5
     inc
           Pressed
                                    ; 4
     bra
           CheckACMP
                                    ;3
ToggleDim:
```

High Brightness LED Controller using the MC9RS08KA2, Rev. 0



```
bset
             KBISC_KBACK, KBISC
                                         ;5
      lda
             PTADD
                          ;3
                          ; 2
             #mDIM1
      eor
                          ; 2
      sta
             PTADD
      clr
             Pressed
                          ; 2
      Delay_3_cycles
; --- Check ACMP ---
CheckACMP:
      lda
             ONTime
                                        ; 3
      brset
             ACMPSC_ACO, ACMPSC, LowerThanRef;5
HigherThanRef:
                                        ; 4
      cbega
             #0, DummyCycles
      deca
                                         ;1
      bra
            PWMGen
                                         ; 3
LowerThanRef:
      cbeqa
            #255, DummyCycles
                                        ; 4
      inca
                                         ;1
                                         ;3
      bra
             PWMGen
DummyCycles:
      nop
                                        ;1
      bra
                                         ; 2
             PWMGen
PWMGen:
             ONTime
                                        ; 2
      sta
             EnableOnTime
                                         ; 3
      Delay_10_cycles
      Delay_3_cycles
      bra
             EnableOffTime
                                        ; 3
EnableOnTime:
                                        ;2 ON period
      sta
             MTIMMOD
      mov
             #(mMTIMSC_TRST|mMTIMSC_TOIE), MTIMSC;4 Reset and Start Timer
      lda
             #255
                          ; 2
      sub
             ONTime
                          ; 3
      wait
                                        ;2+
             ZeroOffTime
                                        ;3 Duty cycle is off
      bea
EnableOffTime:
      bset
             PWM, PTAD
                                        ;5 Switch open
                                        ;2 OFF period
      sta
             MTIMMOD
      mov
             #(mMTIMSC_TRST|mMTIMSC_TOIE), MTIMSC;4 Reset and Start Timer
      wait
                                         ;2+
                                         ; 3
      jmp
            PWMControlLoop
ZeroOffTime:
      Delay_10_cycles
      Delay_3_cycles
             PWMControlLoop
                                        ;3
; Reset Vector
$3ffc
      org
Security:
      dc.b
             $FF
      jmp
             main
```

High Brightness LED Controller using the MC9RS08KA2, Rev. 0



Demo Setup





How to Reach Us:

Home Page:

www.freescale.com

E-mail:

support@freescale.com

USA/Europe or Locations Not Listed:

Freescale Semiconductor Technical Information Center, CH370 1300 N. Alma School Road Chandler, Arizona 85224 +1-800-521-6274 or +1-480-768-2130 support@freescale.com

Europe, Middle East, and Africa:

Freescale Halbleiter Deutschland GmbH Technical Information Center Schatzbogen 7 81829 Muenchen, Germany +44 1296 380 456 (English) +46 8 52200080 (English) +49 89 92103 559 (German) +33 1 69 35 48 48 (French) support@freescale.com

Japan:

Freescale Semiconductor Japan Ltd. Headquarters
ARCO Tower 15F
1-8-1, Shimo-Meguro, Meguro-ku, Tokyo 153-0064
Japan
0120 191014 or +81 3 5437 9125
support.japan@freescale.com

Asia/Pacific:

Freescale Semiconductor Hong Kong Ltd. Technical Information Center 2 Dai King Street Tai Po Industrial Estate Tai Po, N.T., Hong Kong +800 2666 8080 support.asia@freescale.com

For Literature Requests Only:

Freescale Semiconductor Literature Distribution Center P.O. Box 5405
Denver, Colorado 80217
1-800-441-2447 or 303-675-2140
Fax: 303-675-2150
LDCForFreescaleSemiconductor@hibbertgroup.com

RoHS-compliant and/or Pb-free versions of Freescale products have the functionality and electrical characteristics of their non-RoHS-compliant and/or non-Pb-free counterparts. For further information, see http://www.freescale.com or contact your Freescale sales representative.

For information on Freescale's Environmental Products program, go to http://www.freescale.com/epp.

Information in this document is provided solely to enable system and software implementers to use Freescale Semiconductor products. There are no express or implied copyright licenses granted hereunder to design or fabricate any integrated circuits or integrated circuits based on the information in this document.

Freescale Semiconductor reserves the right to make changes without further notice to any products herein. Freescale Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does Freescale Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation consequential or incidental damages. "Typical" parameters that may be provided in Freescale Semiconductor data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals", must be validated for each customer application by customer's technical experts. Freescale Semiconductor does not convey any license under its patent rights nor the rights of others. Freescale Semiconductor products are not designed, intended, or authorized for use as components in systems intended for surgical implant into the body, or other applications intended to support or sustain life, or for any other application in which the failure of the Freescale Semiconductor product could create a situation where personal injury or death may occur. Should Buyer purchase or use Freescale Semiconductor products for any such unintended or unauthorized application, Buyer shall indemnify and hold Freescale Semiconductor and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that Freescale Semiconductor was negligent regarding the design or manufacture of the part.

Freescale[™] and the Freescale logo are trademarks of Freescale Semiconductor, Inc. All other product or service names are the property of their respective owners.

© Freescale Semiconductor, Inc. 2006. All rights reserved.

