



USB-IF 2.0 Compliance Test Report for Embedded Host

Company Name: NXP Semiconductors

VID (Dec): 8137 The VID for the company who apply the USB-IF logo.

Model Name: LPC55S69

Product Type: Embedded Host

Report Date: 05/17/2019

Test Result: **PASS**

Tester: Sofiya Mayevskiy

Authorized Signature: Kayla Seliner

Company Information:

Company

Company Name: NXP Semiconductors
Company Address: 411 E Plumeria Dr. San Jose, CA 95134

Technical Contact

Name: Dezheng Tang (Tom)
Phone Number: N/A
E-Mail: dezheng.tang@nxp.com
FAX Number: N/A

Product Information:

Information Obtained From Checklist or Vendor			
Input	Type	Purpose	Checklist Ref
Uses Micro-AB	<input type="checkbox"/>	Check this box for an EH which uses a Micro-AB receptacle instead of a Standard-A receptacle. It will be automatically selected for OTG devices.	P15a
Supports Sessions	<input type="checkbox"/>	Check this box if the OTG A-UUT or EH with Micro-AB receptacle does not keep V BUS enabled all the time that the ID pin is held low. Check this box for an EH with Standard-A receptacle which does not keep V BUS high all the time it is powered up. In either case it is assumed that SRP or ADP is available to detect the presence of a device.	PI10

Input	Type	Purpose	Checklist Ref
SRP as A-device	<input type="checkbox"/>	Check this box if the UUT, as an A-device, supports detecting, and acting on, an SRP pulse generated by a connected device.	PI13
HNP as A-device	<input type="checkbox"/>	Check this box if the UUT, as an A-device, supports HNP to enable the connected B-device to become host if it so requires.	PI13
HNP Polling as A-device	<input type="checkbox"/>	Check this box if the UUT, as an A-device, supports HNP polling. If it does it is allowed to remain as host, for as long as the other device does not set its Host Request Flag.	PI13
ADP as A-device	<input type="checkbox"/>	Check this box if the UUT, as an A-device, supports ADP probing to detect the presence or otherwise of a connected device.	PI13
SRP as B-device	<input type="checkbox"/>	Check this box if the UUT, as a B-device, supports generating an SRP pulse in order to start a session (cause the connected A-device to turn on V BUS).	PI20
HNP as B-device	<input type="checkbox"/>	Check this box if the UUT, as a B-device, supports HNP to allow it to become host if it so requires.	PI20
ADP as B-device	<input type="checkbox"/>	Check this box if the UUT, as a B-device, supports ADP sensing and probing to detect the presence or otherwise of a connected device.	PI20
FS Not Available	<input type="checkbox"/>	Check this box if UUT does not fully support full-speed operation. This is not permitted for an OTG device, but may be for an Embedded Host.	PI11, PI18

Input	Type	Purpose	Checklist Ref
IA_VBUS_RATED	100 mA	The rated output current of an A-device in mA units.	PI8
bMaxPower	100 mA	bMaxPower (sic) is the highest current, in mA, declared in any of the device's Configuration Descriptors. This value ignores current drawn under the Battery Charging provisions.	PI17
TPWRUP_RDY	30 S	Maximum time, in seconds, specified by vendor from powering on the UUT until it is ready to perform USB functionality. By default this is set to 30 seconds, but a vendor is permitted to specify a longer time.	PI24
TA_WAIT_BCON max	30 S	The maximum time, in seconds, that V BUS is left on for by an A-device, in the absence of a B-device connecting. The default value is thirty seconds. A vendor is permitted to specify a longer time, but should be aware that this will have an impact on the time taken for, and therefore possibly the cost of, compliance testing.	PI10

Input	Type	Purpose	Checklist Ref
Unknown Dev (No HNP)	VID: 1A0A PID: 0201	The test will use the VID/PID combination specified during tests for error messages, when an unknown B-device, not capable of HNP, is connected. A default value (1A0A/0201) is used, but any other device not on the UUT's TPL may be defined here.	-
Unknown Dev (HNP)	VID: 1A0A PID: 0202	The test will use the VID/PID combination specified during tests for error messages, when an unknown B-device, capable of HNP, is connected. A default value (1A0A/0202) is used, but any other device not on the UUT's TPL may be defined here.	-

Test Cable Information:

Information Obtained From PET Test Cables			
Input	Type	Purpose	
Cable A	<u>175</u> mΩ	Test Cable A loop resistance in mΩ.	
Cable B	<u>587</u> mΩ	Test Cable B loop resistance in mΩ.	

High Speed & Full Speed Compliance Tests

Host High-speed Signal Quality

☒ Pass ☐ Fail ☐ N/A

These tests measure the ability of transmitters to do valid high speed signaling. High speed signal quality is measured on upstream ports. A high speed scope with differential probes is used. Signaling data is captured with the scope and then translated to an eye pattern. The signal quality eye patterns obtained from the measurements must agree with the transmit eye patterns in the USB 2.0 Specification.

Port	1
EL_2: Data Rate	Pass
EL_3: Eye Pattern	Pass
EL_6: Rise and Fall Time	Pass
EL_7: Monotonic	Pass

Host Controller Packet Parameters

☒ Pass ☐ Fail ☐ N/A

This test measures the amount of time it takes hosts and devices to respond. It also verifies Host generated SYNCs and EOPs.

EL_21: (32bit)	32bit/32bit	<input checked="" type="checkbox"/> Pass	<input type="checkbox"/> Fail	<input type="checkbox"/> N/A
EL_25: (8bit)	8bit	<input checked="" type="checkbox"/> Pass	<input type="checkbox"/> Fail	<input type="checkbox"/> N/A
EL_23: (>=88bit and <=192bit)	119bit	<input checked="" type="checkbox"/> Pass	<input type="checkbox"/> Fail	<input type="checkbox"/> N/A
EL_22: (>=8bit and <=192bit)	126bit	<input checked="" type="checkbox"/> Pass	<input type="checkbox"/> Fail	<input type="checkbox"/> N/A
EL_55: (40bit)	40bit	<input checked="" type="checkbox"/> Pass	<input type="checkbox"/> Fail	<input type="checkbox"/> N/A

Host CHIRP Timing☒ Pass ☐ Fail ☐ N/A

This test examines the basic timings and voltages of both upstream ports during the speed detection protocol. (Device reset from Full Speed)

EL_33: ($\leq 100\mu\text{s}$)	50.018us	<input checked="" type="checkbox"/> Pass	<input type="checkbox"/> Fail	<input type="checkbox"/> N/A
EL_34: ($> 40\mu\text{s}$ and $\leq 60\mu\text{s}$)	50.018us	<input checked="" type="checkbox"/> Pass	<input type="checkbox"/> Fail	<input type="checkbox"/> N/A
EL_35: ($100\mu\text{s}$ and $\leq 500\mu\text{s}$)	343.750us	<input checked="" type="checkbox"/> Pass	<input type="checkbox"/> Fail	<input type="checkbox"/> N/A

Host Suspend/Resume/Reset timing☒ Pass ☐ Fail ☐ N/A

This test verifies that a Host can be suspended and resumed while operating in high speed and also that the device can be reset from the suspended state.

EL_39:		<input checked="" type="checkbox"/> Pass	<input type="checkbox"/> Fail	<input type="checkbox"/> N/A
EL_41: ($\leq 3\text{ms}$)	122us	<input checked="" type="checkbox"/> Pass	<input type="checkbox"/> Fail	<input type="checkbox"/> N/A

Host Test J/K, SE0_NAK (EL_9)☒ Pass ☐ Fail ☐ N/A

The USB-IF no longer requires EL_8: Test_J and Test_K to be performed as a condition for USB Certification. Measurement of EL_9: Test_J, Test_K and SE0_NAK is still a requirement for certification. EL_9 is defined in the USB 2.0 Test Specification and measures the data line voltage when not driven.

EL_9

Port	1
SE0_NAK D+	0.5mV
SE0_NAK D-	0.6mV
Test J D-	2.2mV
Test K D+	2.1mV

(-20mV to 20mV)

Full Speed Signal Quality Test Result☒ Pass☐ FailFull Speed Downstream Signal Quality: ☒ Pass☐ Fail

Port 1
Pass

Low Speed Downstream Signal Quality: ☐ Pass☐ Fail☒ N/A

Port 1
N/A

Drop/ Droop Test Result☒ Pass☐ Fail**500mA**

Port	1
V _{non-load} ($\geq 4.75V$ and $\leq 5.5V$)	5.203V
V _{load} ($\geq 4.75V$ and $\leq 5.5V$)	4.822V
V _{drop} ($\leq 500mV$)	381mV
V _{droop} ($\leq 330mV$)	N/A

BC 1.2 Implemented Check:☐ Supported ☒ Not Supported

If any one of exposed ports has BC 1.2 capability, all items of BC 1.2 specific category(s) should be tested under this port(s) for USB-IF certification.

Port 1
N/A

Embedded Host PET Automated Test (CH 6)

A-UUT

Only tested when Embedded Host A-Port is applied.

Test Item	Result
6.7.2 A-UUT Initial Power-up Test	Pass
6.7.4 A-UUT V _{BUS} Voltage and Current Measurements	Pass
6.7.5 A-UUT Bypass Capacitance	N/A
6.7.6 A-UUT SRP	N/A
6.7.8 A-UUT ADP	N/A
6.7.9 A-UUT Leakage	N/A
6.7.14 EH, Capable of ADP and SRP, State Transition Test (Standard-A)	N/A
6.7.15 EH, Capable of ADP but not SRP, State Transition Test (Standard-A)	N/A
6.7.16 EH, Capable of SRP but not ADP, State Transition Test (Standard-A)	N/A
6.7.17 EH with no Session Support State Transition Test (Standard-A)	Pass
6.7.18 EH, Capable of ADP and SRP, (Micro-AB) or OTG-A , Capable of ADP and SRP but not HNP, State Transition Test	N/A
6.7.19 EH, Capable of ADP but not SRP, (Micro-AB) or OTG-A , Capable of ADP but not SRP or HNP, State Transition Test	N/A
6.7.20 EH, Capable of SRP but not ADP, (Micro-AB) or OTG-A , Capable of SRP but not ADP or HNP, State Transition Test	N/A
6.7.21 EH with no Session Support State Transition Test (Micro-AB), or OTG-A with no Session or HNP Support	N/A
6.7.22 A-UUT “Device No Response” for connection timeout	Pass
6.7.23 A-UUT “Unsupported Device” Message	Pass
6.7.24 A-UUT “Device No Response” for HNP enable	N/A
6.7.25 EH using Micro-AB “Incorrect Connection”	N/A

B-UUT

Only tested when Embedded Host B-Port is applied.

Test Item	Result
6.8.1 B-UUT Initial Power-up Test	N/A
6.8.2 B-UUT V_{BUS} Voltage and Current Measurements	N/A
6.8.3 B-UUT Bypass Capacitance	N/A
6.8.4 B-UUT SRP	N/A
6.8.6 B-UUT ADP	N/A
6.8.7 B-UUT Leakage	N/A
6.8.13 ADP-Capable Peripheral Only B-device State Transition Test	N/A
6.8.14 SRP Only Capable Peripheral Only B-device State Transition Test	N/A
6.8.15 Peripheral Only B-device, Capable of No Protocols, State Transition Test	N/A
6.8.16 B-UUT “Device no response” for SRP	N/A

Embedded Host Manual Interoperability Tests (CH 7)

This section will perform DUT interoperability with peripherals that are on the vendor's Target Peripheral List.

Test Item	Result
7.3.1 A-UUT Functionality B-device	Pass
7.3.2 A-UUT Category Functionality B-device	Pass
7.3.3 A-UUT Boot test	Pass
7.3.4 A-UUT Legacy Speed test	N/A
7.3.5 A-UUT Concurrent and Independently test	N/A
7.3.6 A-UUT Unsupported device Message test	Pass
7.3.7 A-UUT Hub Error message test	Pass
7.3.8 A-UUT Hub Functionality test	N/A
7.3.9 A-UUT Hub maximum tier test	N/A
7.3.10 A-UUT Hub Concurrent and Independent test	N/A
7.3.11 A-UUT Bus powered hub power exceeded test	N/A
7.3.12 A-UUT Maximum concurrently device exceed message test	N/A
7.3.13 A-UUT Standby test	N/A
7.3.14 A-UUT Standby Disconnect test	N/A
7.3.15 A-UUT Standby Attach test	N/A
7.3.16 A-UUT Standby Topology Change test	N/A
7.3.17 A-UUT Standby Remote Wakeup test	N/A

Battery Charging 1.2 Compliance Test

Dedicated Charging Port (DCP)

☐ Pass

☐ Fail

☒ N/A

Test Items \ Port	Port 1
DCP Overshoot and Undershoot Voltage Test	N/A
DCP Handshaking Test	N/A
DCP Resistance and Capacitance Tests	N/A
DCP Voltage and Current	N/A

Charging Downstream Port (CDP)

☐ Pass

☐ Fail

☒ N/A

Test Items \ Port	Port 1
CDP Overshoot and Undershoot Voltage Test	N/A
CDP Voltage and Current Test	N/A
CDP Handshaking Test	N/A
CDP Ground Offset Test – Full Speed	N/A
CDP Ground Offset Test – High Speed	N/A

Standard Downstream Port (SDP)☐ Pass☐ Fail☒ N/A

Port	
Test Items	Port 1
SDP Handshaking Test	N/A

Multiple Role Port (MRP)☐ Pass☐ Fail☒ N/A

Port	
Test Items	Port 1
MRP Functional Test	N/A

More Detailed Test Results:



1. Full Speed Downstream Signal Quality: Pass

- Overall result: pass!
- Signal eye:
eye passes
- EOP width: 165.72 ns
EOP width passes
- Measured signaling rate: 12.0004 MHz
signal rate passes
- Edge Monotonicity: 97 mV
Monotonic Edge passes
- Crossover voltage range: 1.60 V to 1.68 V, mean crossover 1.64 V
(first crossover at 1.67 V, 19 other differential crossovers checked)
crossover voltages pass
- Consecutive jitter range: -386.821 ps to 338.124 ps, RMS jitter 206.175 ps
- Paired JK jitter range: -533.607 ps to 373.306 ps, RMS jitter 320.547 ps
- Paired KJ jitter range: -549.984 ps to 400.399 ps, RMS jitter 309.545 ps
jitter passes

Additional Information

- Rising Edge Rate: 162.18 V/us (Equivalent risetime = 16.28 ns)
- Falling Edge Rate: 163.71 V/us (Equivalent falltime = 16.13 ns)
- Edge Rate Match: 0.94% (limit +/-10%)
- Margin Above eye: 0.7367 V
- Margin Below eye: 0.6079 V
- Maximum Voltage: 3.7774 V
- Margin Below Top: 0.6226 V
- Minimum Voltage: -0.6008 V
- Margin Above Bottom: 0.2992 V

Signal Data and Eye





2. High Speed Downstream Signal Quality: Pass

- Overall result: pass!
- Signal eye:
eye passes
- EOP width: 7.92 bits
EOP width passes
- Measured signaling rate: 479.9906 MHz
signal rate passes
- Edge Monotonicity: 0 mV
Monotonic Edge passes
- Rising Edge Rate: 1463.39 V/us (437.34 ps equivalent risetime)
passes
- Falling Edge Rate: 1414.21 V/us (452.55 ps equivalent falltime)
passes

Additional Information

- Consecutive jitter range: -47.988 ps to 46.506 ps, RMS jitter 15.981 ps
- Paired JK jitter range: -43.683 ps to 35.260 ps, RMS jitter 13.267 ps
- Paired KJ jitter range: -41.964 ps to 33.763 ps, RMS jitter 14.301 ps
- Margin Above eye: 0.0795 V
- Margin Below eye: 0.0810 V
- Maximum Voltage: 0.4327 V
- Margin Below Top: 0.0923 V
- Minimum Voltage: -0.4318 V
- Margin Above Bottom: 0.0932 V

Signal Data and Eye



Test Procedure Reference:

1. USB On-The-Go and Embedded Host Automated Compliance Plan for the On-The-Go & Embedded Host Supplement Revision 2.0, Version 1.2
2. Keysight N5416A/N5416B USB 2.0 Compliance Test Application, Version 3.96
3. Universal Serial Bus Implementers Forum Full and Low Speed Electrical and Interoperability Compliance Test Procedure, Version: 1.3
4. USB Battery Charging 1.2 Compliance Plan, Revision: 1.1

Notice: Test result is valid only to the original tested device model.