
RF MILITARY

MMRF2010N | MMRF1312H
MMRF1314H | MMRF1317H
HIGH POWER LDMOS AVIONICS DEVICES



APRIL 2016





NXP RF Military Overview

- NXP RF (formerly Freescale) is #1 in RF power for cellular infrastructure*
- Strong presence in ISM, mobile radio, broadcast and avionics
- June 2013: Freescale RF announced new focus supporting U.S. defense industry

NXP RF Military Value Proposition

- Products and Technology
 - Leveraging 20 years of innovation in RF power
 - Highest performing RF portfolio
- Support
 - U.S. LDMOS fabrication and dedicated internal manufacturing
 - NXP product longevity program (10 or 15 years)
 - Dedicated U.S.-based applications & systems engineering support
- Compliance
 - ITAR compliant, secure technical data handling

*Source: ABI 2013 Report






MMRF2010N: 250 W Peak – L-Band Transistor



- 1030 to 1090 MHz
- 250 W Peak, 50 V
 - Gain: 32.1 dB @ 1090 MHz, Drain Efficiency: 61.4%
- Housed in TO-270WB plastic package
- Ruggedness: > 10:1 VSWR
- Product Longevity Program: warranted availability until 2029
- Typical Applications
 - IFF and secondary radar



Available Reference Circuits:

- 1. 1090 MHz
- 2. 1030-1090 MHz



MMRF2010N: Featured Device

Features


- Characterized over 1030–1090 MHz
- On-chip input (50 ohm) and interstage matching
- Single ended
- Integrated ESD protection
- Low thermal resistance
- Integrated quiescent current temperature compensation with enable/disable function

Competitive Advantages

- Suitable for use in pulse applications with large duty cycles and long pulses
- Device in NXP 15 year Product Longevity Program
- Able to replace multiple RF amplifiers with one wideband PA
- Application circuit support
- Dedicated RF Military team
- Availability: Device is in production as earless and gull winged. Orderable part number is MMRF2010NR1.





MMRF2010N Applications Circuit: 1030 to 1090 MHz





MMRF1312H: 1200 W Peak – L-Band Transistor





- High power 1200 W Peak @ P3dB across 900 to 1215 MHz in one circuit
 - Gain: 17.3 dB @ 960–1215 MHz, Drain Efficiency: 54%
- Housed in NI-1230 air-cavity ceramic package
- High Ruggedness: > 20:1 VSWR
- Product Longevity Program: warranted availability until 2030
- Typical Applications
 - High power L-Band radar applications
 - Avionics navigation applications
 - Commercial aviation secondary surveillance radar

Available Reference Circuits:

- 1. 1030 MHz
- 2. 900-1215 MHz



MMRF1312H: Featured Device

Features


- Internally input and output matched for broadband operation and ease of use
- Device can be used in a single-ended, push-pull or quadrature configuration
- High ruggedness, handles > 20:1 VSWR
- Integrated ESD protection with greater negative voltage range for improved
 Class C operation and gate voltage pulsing
- Characterized with series equivalent large-signal impedance parameters

Competitive Advantages

- Suitable for use in pulse applications with large duty cycles and long pulses
- Device in NXP 15 year Product Longevity Program
- Able to replace multiple RF amplifiers with one wideband PA
- Application circuit support
- Dedicated RF Military team
- Availability: Device is in production as eared, earless and gull winged. Orderable part number is MMRF1312HR5.




MMRF1312H Applications Circuit: 900 to 1215 MHz






MMRF1312H: Gain, Efficiency and IRL versus Frequency






MMRF1312H: Gain and Efficiency versus Power






MMRF1312H: Power and Efficiency versus Frequency





MMRF1314H: 1000 W Peak - L-Band Transistor





- High power 1000 W Peak across 1200 to 1400 MHz in one circuit
 - Gain: 15.5 dB @ 1200-1400 MHz, Drain Efficiency: 46.5%
- Housed in NI-1230 air-cavity ceramic package
- High Ruggedness: > 20:1 VSWR
- Product Longevity Program: warranted availability until 2030
- Typical Applications
 - High power L-Band radar applications

Available Reference Circuits:

- 1. 1400 MHz
- 2. 1200-1400 MHz



MMRF1314H: Featured Device

Features


- Internally input and output matched for broadband operation and ease of use
- Device can be used in a single-ended, push-pull or quadrature configuration
- High ruggedness, handles > 20:1 VSWR
- Integrated ESD protection with greater negative voltage range for improved Class C operation and gate voltage pulsing
- Characterized with series equivalent large-signal impedance parameters

Competitive Advantages

- Device in NXP 15 year Product Longevity Program
- Able to replace multiple RF amplifiers with one wideband PA
- Application circuit support
- Dedicated RF Military team
- Availability: Device is in production as eared, earless and gull winged. Orderable part number is MMRF1314HR5.




MMRF1314H Applications Circuit: 1200 to 1400 MHz






MMRF1314H: Gain, Efficiency and IRL versus Frequency






MMRF1314H: Power and Efficiency versus Frequency






MMRF1314H: Gain and Efficiency versus Power





MMRF1317H: 1500 W Peak – IFF Transistor





- High power 1500 W Peak @ P3dB
 - Gain: 18.9 dB @ 1030 MHz, Drain Efficiency: 56%
- Housed in NI-1230 air-cavity ceramic package
- High Ruggedness: > 10:1 VSWR
- Product Longevity Program: warranted availability until 2030
- Typical Applications
 - Defense and commercial pulse applications, such as IFF and secondary surveillance radars

Available Reference Circuit:
1. 1030 to 1090 MHz



MMRF1317H: Featured Device

Features


- Internally input and output matched for broadband operation and ease of use
- Device can be used in a single-ended, push-pull or quadrature configuration
- High ruggedness, handles > 10:1 VSWR
- Integrated ESD protection with greater negative voltage range for improved Class C operation and gate voltage pulsing
- Characterized with series equivalent large-signal impedance parameters

Competitive Advantages

- Device in NXP 15 year Product Longevity Program
- Able to replace multiple RF amplifiers with one wideband PA
- Application circuit support
- Dedicated RF Military team
- Availability: Device is in production as eared, earless and gull winged. Orderable part number is MMRF1317HR5.




MMRF1317H Applications Circuit: 1030 to 1090 MHz





MMRF1317H: Gain and Efficiency versus Power







SECURE CONNECTIONS FOR A SMARTER WORLD