

UM10561

UBA2017AT reference design for 420 V (DC)

Rev. 1 — 13 August 2012

User manual

Document information

Info	Content
Keywords	UBA2017AT, dimmable, 2 x T5 35 W ballast
Abstract	This user manual describes the performance, technical data and wiring of the 420 V (DC) UBA2017AT reference design. This dimmable design drives two 35 W T5 lamps.



Revision history

Rev	Date	Description
v.1	20120813	first issue

Contact information

For more information, please visit: <http://www.nxp.com>

For sales office addresses, please send an email to: salesaddresses@nxp.com

1. Introduction

WARNING

Lethal voltage and fire ignition hazard




The non-insulated high voltages that are present when operating this product, constitute a risk of electric shock, personal injury, death and/or ignition of fire.

This product is intended for evaluation purposes only. It shall be operated in a designated test area by personnel qualified according to local requirements and labor laws to work with non-insulated mains voltages and high-voltage circuits. This product shall never be operated unattended.

The UBA2017AT reference design is intended to serve as an example of a dimmable two lamp ballast. This user manual describes the specification and use of the UBA2017AT board. This reference ballast design is intended to drive two T5 35 W lamps.



a. Top view.



b. Bottom view.

Fig 1. Photograph of the UBA2017AT reference design

2. Safety warning

Connected the board to the DC voltage. Avoid touching the board while it is connected to the mains voltage. An isolated housing is mandatory when used in uncontrolled, non-laboratory environments.

3. Specifications

Table 1. Specifications for the reference board

Parameter	Comment
ballast type	electronic
starting method	programmed start with preheat
starting time	< 1 s
lamp terminals	7
line voltage	420 V(DC); in the range 400 V(DC) to 440 V(DC)
lamp type	T5 35 W
number of lamps	2
dimming interface	1 V to 10 V

Table 2. Ballast performance

Lamp type	Number of lamps	Lamp power (W)	I _{lamp}	maximum crest factor	nominal (A)	minimum (mA)
T5 35 W	2	35	1.7		0.17	5




Fig 2. Wiring diagram

Remark: Connected the ballast as shown in [Figure 2](#). When no dimming is needed, do not connect the (floating) DIM input.

Remark: The chassis connection must connect to the earth using mounting hole MH1.


3.1 Dimming without using an external voltage source

The ballast is dimmed using a voltage source of 1 V (DC) to 10 V (DC) connected to connector X1.


It is also possible to dim using an external logarithmic potentiometer of 470 k Ω (for example, no external voltage supply is available). The potentiometer must connect pins 5 (gray wire, DIM-) and 4 (violet wire, DIM+) of connector X1.

4. Performance data

4.1 Dimming curve



4.2 Sum of Squares (SoS) and maximum lead current curves



5. Board Information

The input section includes:

- the fuse
- surge protection against fast AC transients

The DC voltage connects to a buffer capacitor to supply the half-bridge circuit. The lamp connects to the half-bridge circuit. The UBA2017AT IC controls the half-bridge circuit. A low-voltage control input is present to control the dimming of the lamp light output.

The half-bridge consists of two NMOST transistors which provide the voltage to power the resonant circuit. The resonant circuit includes a transformer for electrode preheating and heating.





Fig 5. Block diagram

The type of ballast presented here is used for most ballast for lamp powers above 25 W. It is a cost-effective application.

5.1 Half-bridge operating principle

This topology supports dimming and preheat times below 1 s for T5 lamps. It uses an additional transformer for preheating/heating the filaments.



When the lamp is off, two resonant frequencies can be distinguished. A main resonant frequency f_{res} and a second frequency f_{sec} . Approaching f_{res} ignites the lamp:

$$f_{res} = \frac{1}{2\pi\sqrt{L_{res} \cdot C_{res}}} \rightarrow f_{res} = 51.9 \text{ kHz} \quad (1)$$


Preheating the electrodes near f_{sec} increases the preheat current without increasing the filament current during normal operation. In dimmable applications, this aids compliance with the lamp sum of squares requirement.

$$f_{sec} = \frac{1}{2\pi\sqrt{\frac{L_{TxA} \cdot L_{TyA}}{L_{TxA} + L_{TyA}} \cdot C_x}} \rightarrow f_{sec} = 84.8 \text{ kHz} \quad (2)$$

Rx is used to limit the voltage when both lamps are removed.

An equalizer transformer Teq is used to equalize the lamp current which is needed in deep dim settings.

The UBA2017AT controller starts at 100 kHz and sweeps down until the preheat frequency is reached. The resistor on pin PH/EN sets the preheat frequency. During preheat, the LC tank voltage remains below 200 V to prevent early ignition and glow.



5.2 Schematic diagrams

See [Figure 8](#) for a detailed overview of the application.

UBA2017AT reference design for 420 V (DC)

aaa-004390




Fig 8. Schematic diagram

5.3 Functional description

The DC supply voltage is applied to the board and current flows through R3 and R4 to the supply of the controller (VDD pin). When the current through R3 and R4 is higher than $240 \mu\text{A}$ ($I_{\text{stb(VDD)}}$) of the controller the VDD voltage rises. When the VDD voltage is above 4.2 V ($V_{\text{rst(VDD)}}$), the half-bridge circuit low-side MOSFET switches on and the floating supply capacitor C32 is pre-charged.

The controller starts oscillating when the VDD voltage is above the 12.4 V ($V_{\text{startup(VDD)}}$). The HB gate drivers start oscillating at 100 kHz ($f_{\text{sw(high)}}$). The dV/dt supply using capacitor C8 takes over the VDD supply to supply the IC with enough energy for the gate drivers. The preheat timer starts and the controller sweeps down the frequency from 100 kHz to the preheat frequency. The PH/EN pin sets the preheat frequency level. The oscillator remains at the preheat frequency until the preheat timer has ended.

When the preheat ends, the controller sweeps down the half-bridge switching frequency. The lamp ignites when the LC tank voltage reaches the lamp ignition voltage. The ignition frequency is typically 60 kHz. The lamp current increases and the LC tank voltage decreases. The controller senses the lamp current and LC tank voltage. The controller assumes that the lamp is on when the lamp current is high enough and the LC tank voltage is low enough for 3 ms. The representation of the states is $V_{\text{IFB}} > V_{\text{th(lod)}}_{\text{IFB}}$ and $V_{\text{VFB}} < V_{\text{th(lod)}}_{\text{VFB}}$ for $t_{\text{d(lod)}}$. The controller enters burn state.

In burn state, all the protective features are activated. The controller closes the lamp current control loop and the oscillator regulates the half-bridge switching frequency. The half-bridge frequency is controlled. It reaches the set point when the average absolute IFB pin voltage equals the DIM pin voltage.

5.3.1 Start-up current and relamp function

The VDD supply of the IC is charged using a start-up current derived from the rectified mains voltage. Resistors R3 and R4 provide the current path and determines the start-up voltage level.

When the lamp is removed while set to deep dimming, the protection must trigger the controller to shut down. In this board, transistor Q7 pulls down the VDD voltage. The signals Lamp1 and Lamp2 sense the filaments of the lamps and control transistor Q7. The pull down by Q7 is released when all lamps are inserted.

6. Waveforms





Fig 9. Normal start-up operation



7. Board layouts




Fig 11. Evaluation board (top view)




Fig 12. Evaluation board (bottom view)

8. Bill of materials

Table 3. Bill of materials

Part reference	Description/Value	Part number	Manufacturer
1	PCB	7022-001-21961	NXP Semiconductors
C3	2.2 nF; 20 %; 250 V	DE2E3KH222MA3B	Murata
C4	100 nF; 10 %; 630 V	R75PI3100AA30K	KEMET
C6	10 µF; 20 %; 450 V	EEUEE2W100U	Panasonic
C7	22 pF; 5 %; 500 V	D220J25C0GL63L6R	Vishay
C8	1 nF; 10 %; 1 kV	F102K39Y5RN6UK5R	Vishay
C9	220 nF; 10 %; 400 V	146-MEF2G224K	Xicon
C10	4.7 nF; 5 % 2 kV	BFC238560472	Vishay
C11	100 nF; 5 %; 100 V	R82EC3100DQ70J	KEMET
C12	56 nF; 10 %; 400 V	DME4S56K-F	Cornell Dubilier
C13	150 nF; 5 %; 250 V	BFC230342154	Vishay
C14	150 nF; 5 %; 250 V	BFC230342154	Vishay
C15	150 nF; 5 %; 250 V	BFC230342154	Vishay
C16	150 nF; 5 %; 250 V	BFC230342154	Vishay
C17	100 nF; 10 %; 50 V	CC0805KRX7R9BB104	Yageo
C18	100 nF; 10 %; 50 V	CC0805KRX7R9BB104	Yageo
C19	100 nF; 10 %; 50 V	CC0805KRX7R9BB103	Yageo
C21	100 nF; 10 %; 50 V	CC0805KRX7R9BB104	Yageo
C22	68 nF; 10 %; 50 V	C0805C683K5RACTU	KEMET
C24	200 pF; 1 %; 50 V	GRM2165C1H201FA01D	Murata
C25	10 nF; 10 %/50 V	CC0805KRX7R9BB103	Yageo
C28	10 nF; 10 %; 50 V	CC0805KRX7R9BB103	Yageo
C29	150 nF; 10 %; 25 V	C0805C154K3RACTU	KEMET
C30	470 nF; 10 %; 25 V	C0805X474K3RACTU	KEMET
C31	100 nF; 10 %; 50 V	CC0805KRX7R9BB104	Yageo
C32	100 nF; 10 %; 50 V	CC0805KRX7R9BB104	Yageo
C33	470 nF; 10 %; 25 V	C0805X474K3RACTU	KEMET
C34	100 pF; 2 %; 50 V	VJ0805A101GXAMC	Vishay
C35	100 nF; 10 %; 50 V	CC0805KRX7R9BB104	Yageo
C36	10 nF; 5 %; 50 V (DC)	C0805C103J5GAC	KEMET
D1	PMBD914	PMBD914	NXP Semiconductors
D2	BZX79-C12	BZX79-C12,133	NXP Semiconductors
D3	PMBD914	PMBD914	NXP Semiconductors
D12	PMBD914	PMBD914	NXP Semiconductors
D13	1N5244B	1N5244B	Fairchild Semiconductor
D14	1N4148	1N4148,133	NXP Semiconductors
D15	1N4148	1N4148,133	NXP Semiconductors
D16	1N4937/54; 600 V; 1 A	1N4937-E3/54	Vishay

Table 3. Bill of materials ...continued

Part reference	Description/Value	Part number	Manufacturer
D17	PMBD6100; 85 V; 0.2152 A	PMBD6100.215	NXP Semiconductors
D18	1N5062; 800 V; 2 A	1N5062-TR	Vishay
D19	1N4148	1N4148,133	NXP Semiconductors
D20	1N4148	1N4148,133	NXP Semiconductors
F1	ceramic fuse; 1 A	0001.2504	SCHURTER
L1	transformer 2 mH	760801080	Würth Elektronik
Q2	TK10A60D(STA4,Q,M)	TK10A60D(STA4,Q,M)	Toshiba
Q3	TK10A60D(STA4,Q,M)	TK10A60D(STA4,Q,M)	Toshiba
Q4	BC847A	BC847A	NXP Semiconductors
Q5	BC847A	BC847A	NXP Semiconductors
Q7	BC847CW	BC847CW,115	NXP Semiconductors
R1	4.7 kΩ; 1 %; 350 V; 0.6 W	MRS25000C4701FCT00	Vishay
R3	330 kΩ; 1 %; 350 V; 0.6 W	MRS25000C3303FCT00	Vishay
R4	330 kΩ; 1 %; 350 V; 0.6 W	MRS25000C3303FCT00	Vishay
R5	8.2 kΩ; 1 %; 350 V; 0.6 W	MRS25000C8201FCT00	Vishay
R7	4.7 kΩ; 1 %; 350 V; 0.6 W	MRS25000C4701FCT00	Vishay
R9	1 Ω; 5 %; 350 V; 1 W	PR01000101008JR500	Vishay
R10	100 Ω; 1 %; 350 V; 0.6 W	MRS25000C1000FCT00	Vishay
R11	22 Ω; 1 %; 350 V; 0.6 W	MRS25000C2209FCT00	Vishay
R12	1.1 MΩ; 1 %; 350 V; 0.6 W	MRS25000C1104FCT00	Vishay
R13	140 kΩ; 1 %; 350 V; 0.6 W	MRS25000C1403FCT00	Vishay
R14	510 kΩ; 1 %; 350 V; 0.6 W	MRS25000C5103FCT00	Vishay
R15	1.6 Ω; 1 %; 350 V; 0.6 W	MRS25000C1608FCT00	Vishay
R16	2 Ω; 1 %; 350 V; 0.6 W	MRS25000C2008FCT00	Vishay
R17	10 kΩ; 1 %; 350 V; 0.6 W	MRS25000C1002FCT00	Vishay
R18	10 kΩ; 5 %; 500 V; 2 W	PR02000201002JR500	Vishay
R19	150 Ω; 1 %; 350 V; 0.6 W	MRS25000C1503FCT00	Vishay
R20	4.7 kΩ; 1 %; 150 V; 0.125 W	RC0805FR-074K7L	Yageo
R21	1 MΩ; 1 %; 150 V; 0.125 W	RC0805FR-071ML	Yageo
R22	200 kΩ; 1 %; 150 V; 0.125 W	RC0805FR-07200KL	Yageo
R23	1 kΩ; 1 %; 150 V; 0.125 W	RC0805FR-071KL	Yageo
R29	68 kΩ; 1 %; 150 V; 0.125 W	RC0805FR-0768KL	Yageo
R32	22 kΩ/ 1 %; 0.125 W	RC0805FR-0722KL	Yageo
R33	33 kΩ; 1 %; 150 V; 0.125 W	RC0805FR-0733KL	Yageo
R34	390 Ω; 1 %; 150 V; 0.125 W	RC0805FR-07330RL	Yageo
R35	22 Ω; 1 %; 150 V; 0.125 W	RC0805FR-0722RL	Yageo
R36	470 Ω; 1 %; 150 V; 0.125 W	RC0805FR-07470RL	Yageo
R37	4.7 kΩ; 1 %; 150 V; 0.125 W	RC0805FR-074K7L	Yageo
R38	33 Ω; 1 %; 150 V; 0.125 W	RC0805FR-0733RL	Yageo
R39	6.8Ω; 1 %; 150 V; 0.1 W	MC 0.1W 0805 1 % 6K8	Multicomp

Table 3. Bill of materials ...continued

Part reference	Description/Value	Part number	Manufacturer
R40	100 Ω; 1 %; 150 V; 0.125 W	RC0805FR-07100RL	Yageo
R41	150 kΩ; 1 %; 150 V; 0.125 W	RC0805FR-07150KL	Yageo
R42	150 kΩ; 1 %; 150 V; 0.125 W	RC0805FR-07150KL	Yageo
R43	150 kΩ; 1 %; 150 V; 0.125 W	RC0805FR-07150KL	Yageo
R44	wire bridge; 10 mm		Vishay
R46	0 Ω; 5 %; 150 V; 0.1 W	MC 0.1W 0805 0R	Multicomp
RT1	150 Ω; 25 %; 0.2 A; +85 °C	PTGL05AR151H8P52B0	Murata
RT2	4.7 Ω; 20 %; 265 V; 1.4 W	B57153S479M	EPCOS
T1	transformer	750311081	Würth Elektronik
T4	transformer 2 × 33 mH	7448640405	Würth Elektronik
T5	transformer	760800001	Würth Elektronik
T6	transformer	760800001	Würth Elektronik
U1	UBA2017AT	UBA2017AT	NXP Semiconductors
V1	BFT46	BFT46	NXP Semiconductors
V2	BAT85	BAT85	NXP Semiconductors
WB1	wire bridge; 3E	923345-03-C	3M
WB2	wire bridge; 3E	923345-03-C	3M
WB4	wire bridge; 2E	923345-02-C	3M
WB5	wire bridge; 3E	923345-03-C	3M
WB6	wire bridge; 3E	923345-03-C	3M
X1	PCB mounted screw terminal MKDSN1.5; 5-5.08	1729157	Phoenix Contact
X3	PCB mounted screw terminal MKDS 1; 7-3.81	1727065	Phoenix Contact
X21	jumper link	LB 03 G	Fischer Elektronik

9. Inductor appearance and dimensions

9.1 Half-bridge inductor

Wurth Electronics Midcom Inc.; part number: 760801080.




Fig 13. Half-bridge inductor appearance and dimensions

Table 4. Half-bridge inductor electrical specifications

Parameter	Value
Inductance (5 to 2)	2 mH
Saturation current (5 to 2)	2.6 A
DC resistance (5 to 2)	2.15 Ω
Operating temperature	-40 °C to +125 °C

9.2 Heater transformer

Wurth Electronics Midcom Inc.; part number: 760800001




Fig 14. Heater transformer appearance and dimensions

Table 5. Heater transformer electrical specifications

Parameter	Value
Inductance (1 to 2)	127 μ H
Inductance (3 to 4) and (8 to 6)	4.1 μ H
Saturation current (1 to 2)	2.5 A
Rated current (1 to 2)	0.7 A
Dielectric rating (5 to 9)	2 kV (AC)
DC resistance (1 to 2)	0.30 Ω
DC resistance (3 to 4) and (8 to 6)	0.11 Ω
Operating temperature	-40 °C to +125 °C

9.3 Dim transformer

Wurth Electronics Midcom Inc.; part number: 750311081.




Fig 15. Dim transformer appearance and dimensions

Table 6. Dim transformer electrical specifications

Parameter	Value
Inductance (1 to 2) and (6 to 4)	10 mH
Turns ratio (1 to 2) : (6 to 4)	1
Leakage inductance	10 μ H
Dielectric rating (5 to 9)	1.5 kV (AC)
DC resistance (1 to 2)	2.30 Ω
DC resistance (6 to 4)	2.70 Ω
Operating temperature	-40 °C to +125 °C

9.4 Equalizing transformer

Wurth Electronics Midcom Inc.; part number: 7448640405




Fig 16. Equalizing transformer appearance and dimensions

Table 7. Equalizing transformer electrical specifications

Parameter	Value
Inductance L0	33 mH
Turns ratio (1 to 2) : (6 to 4)	1
Rated current	0.3 A
Dielectric rating	2 kV; 50 Hz
DC resistance	2 Ω
Operating temperature	-25 °C to +125 °C

10. Abbreviations

Table 8. Abbreviations

Acronym	Description
EMI	ElectroMagnetic Interference
MOSFET	Metal-Oxide Semiconductor Field-Effect Transistor
OLP	Open-Loop Protection
PCB	Printed-Circuit Board
PFC	Power Factor Correction
SoS	Sum of Squares
THD	Total Harmonic Distortion

11. Legal information

11.1 Definitions

Draft — The document is a draft version only. The content is still under internal review and subject to formal approval, which may result in modifications or additions. NXP Semiconductors does not give any representations or warranties as to the accuracy or completeness of information included herein and shall have no liability for the consequences of use of such information.

11.2 Disclaimers

Limited warranty and liability — Information in this document is believed to be accurate and reliable. However, NXP Semiconductors does not give any representations or warranties, expressed or implied, as to the accuracy or completeness of such information and shall have no liability for the consequences of use of such information. NXP Semiconductors takes no responsibility for the content in this document if provided by an information source outside of NXP Semiconductors.

In no event shall NXP Semiconductors be liable for any indirect, incidental, punitive, special or consequential damages (including - without limitation - lost profits, lost savings, business interruption, costs related to the removal or replacement of any products or rework charges) whether or not such damages are based on tort (including negligence), warranty, breach of contract or any other legal theory.

Notwithstanding any damages that customer might incur for any reason whatsoever, NXP Semiconductors' aggregate and cumulative liability towards customer for the products described herein shall be limited in accordance with the *Terms and conditions of commercial sale* of NXP Semiconductors.

Right to make changes — NXP Semiconductors reserves the right to make changes to information published in this document, including without limitation specifications and product descriptions, at any time and without notice. This document supersedes and replaces all information supplied prior to the publication hereof.

Suitability for use — NXP Semiconductors products are not designed, authorized or warranted to be suitable for use in life support, life-critical or safety-critical systems or equipment, nor in applications where failure or malfunction of an NXP Semiconductors product can reasonably be expected to result in personal injury, death or severe property or environmental damage. NXP Semiconductors and its suppliers accept no liability for inclusion and/or use of NXP Semiconductors products in such equipment or applications and therefore such inclusion and/or use is at the customer's own risk.

Applications — Applications that are described herein for any of these products are for illustrative purposes only. NXP Semiconductors makes no representation or warranty that such applications will be suitable for the specified use without further testing or modification.

Customers are responsible for the design and operation of their applications and products using NXP Semiconductors products, and NXP Semiconductors accepts no liability for any assistance with applications or customer product

design. It is customer's sole responsibility to determine whether the NXP Semiconductors product is suitable and fit for the customer's applications and products planned, as well as for the planned application and use of customer's third party customer(s). Customers should provide appropriate design and operating safeguards to minimize the risks associated with their applications and products.

NXP Semiconductors does not accept any liability related to any default, damage, costs or problem which is based on any weakness or default in the customer's applications or products, or the application or use by customer's third party customer(s). Customer is responsible for doing all necessary testing for the customer's applications and products using NXP Semiconductors products in order to avoid a default of the applications and the products or of the application or use by customer's third party customer(s). NXP does not accept any liability in this respect.

Export control — This document as well as the item(s) described herein may be subject to export control regulations. Export might require a prior authorization from competent authorities.

Evaluation products — This product is provided on an "as is" and "with all faults" basis for evaluation purposes only. NXP Semiconductors, its affiliates and their suppliers expressly disclaim all warranties, whether express, implied or statutory, including but not limited to the implied warranties of non-infringement, merchantability and fitness for a particular purpose. The entire risk as to the quality, or arising out of the use or performance, of this product remains with customer.

In no event shall NXP Semiconductors, its affiliates or their suppliers be liable to customer for any special, indirect, consequential, punitive or incidental damages (including without limitation damages for loss of business, business interruption, loss of use, loss of data or information, and the like) arising out the use of or inability to use the product, whether or not based on tort (including negligence), strict liability, breach of contract, breach of warranty or any other theory, even if advised of the possibility of such damages.

Notwithstanding any damages that customer might incur for any reason whatsoever (including without limitation, all damages referenced above and all direct or general damages), the entire liability of NXP Semiconductors, its affiliates and their suppliers and customer's exclusive remedy for all of the foregoing shall be limited to actual damages incurred by customer based on reasonable reliance up to the greater of the amount actually paid by customer for the product or five dollars (US\$5.00). The foregoing limitations, exclusions and disclaimers shall apply to the maximum extent permitted by applicable law, even if any remedy fails of its essential purpose.

Translations — A non-English (translated) version of a document is for reference only. The English version shall prevail in case of any discrepancy between the translated and English versions.

11.3 Trademarks

Notice: All referenced brands, product names, service names and trademarks are the property of their respective owners.

12. Contents

1	Introduction	3
2	Safety warning	3
3	Specifications	4
3.1	Dimming without using an external voltage source	5
4	Performance data	5
4.1	Dimming curve	5
4.2	Sum of Squares (SoS) and maximum lead current curves	6
5	Board Information	7
5.1	Half-bridge operating principle	7
5.2	Schematic diagrams	9
5.3	Functional description	11
5.3.1	Start-up current and relamp function	11
6	Waveforms	12
7	Board layouts	14
8	Bill of materials	15
9	Inductor appearance and dimensions	18
9.1	Half-bridge inductor	18
9.2	Heater transformer	19
9.3	Dim transformer	20
9.4	Equalizing transformer	21
10	Abbreviations	22
11	Legal information	23
11.1	Definitions	23
11.2	Disclaimers	23
11.3	Trademarks	23
12	Contents	24

Please be aware that important notices concerning this document and the product(s) described herein, have been included in section 'Legal information'.

© NXP B.V. 2012.

All rights reserved.

For more information, please visit: <http://www.nxp.com>

For sales office addresses, please send an email to: salesaddresses@nxp.com

Date of release: 13 August 2012

Document identifier: UM10561