# AN11010 Single stage Ku band LNA using BFU730F Rev. 1.0 — 11 January 2011

**Application note** 

### **Document information**

Info	Content
Keywords	BFU730F, LNA, Ku band, LNB
Abstract	The document provides circuit, layout, BOM and performance information on Ku band LNA equipped with NXP's BFU730F wide band transistor.



# Ku band LNA using BFU730F

### **Revision history**

Rev	Date	Description
1.0	20110111	Initial document

# **Contact information**

For additional information, please visit: <a href="http://www.nxp.com">http://www.nxp.com</a>

For sales office addresses, please send an email to: <a href="mailto:salesaddresses@nxp.com">salesaddresses@nxp.com</a>

Ku band LNA using BFU730F

### 1. Introduction

BFU730F is a discrete HBT produced in NXP's SiGeC QuBIC4x BiCmos process. SiGeC is a normal silicon germanium process with the addition of Carbon in the base layer of the NPN transistor. The presence of carbon in the base layer suppresses the boron diffusion during wafer processing. This allows steeper and narrower SiGe HBT base and a heavier doped base. As a result, lower base resistance, lower noise and higher cut off frequency can be achieved.

# 2. Requirements for Ku band LNA

The typical application for a Ku band LNA consists of amplification stage in the MW preamplifier chain of a satellite LNB.

The noise figure requirements for LNBs may vary from standard to standard, however most of them will set a figure of:

BFU730F typical values for the minimum noise figure and maximum stable gain at Ku band frequency of 12GHz and bias of 2V / 10mA are:

NFmin = 1.1dB and Gmax = 12.5dB

This recommends the device as an alternative solution to replace pHemts in Ku band LNA applications.

IF the target spec for the BFU730F LNA noise and gain is:

NF= 1.4dB and Gain = 11.5dB

The LNB system performance is as it shows up in <u>Table 1</u>:

Table 1. BFU730F vs pHemt NF and Gain performance comparison

Preamplifier	1 <sup>st</sup> stage NF/Gain (dB)	2 <sup>nd</sup> stage NF/Gain (dB)	3 <sup>rd</sup> stage NF/Gain (dB)	Mixer stage NF/Gain (dB)	LNB NF/Gain (dB)
2 stage	pHemt 0.8 / 12	pHemt 1 / 12	N/U	active 8 / 2	0.93 / 26
	pHemt 0.8 / 12	BFU730F 1.4 / 11.5	N/U	active 8 / 2	0.97 / 25.5
3 stage	pHemt 0.8 / 12	pHemt 1 / 12	pHemt 1 / 12	diode 12 / -12	0.88 / 24
	pHemt 0.8 / 12	pHemt 1 / 12	BFU730F 1.4 / 11.5	diode 12 / -12	0.88 / 23.5
	pHemt 0.8 / 12	BFU730F 1.4 / 11.5	BFU730F 1.4 / 11.5	diode 12 / -12	0.91 / 23

The performance of the stand-alone BFU730F amplifier is slightly worse compare to the pHemt one, however in an LNB chain it gives almost no performance change when used as LNA3, or minor acceptable degradation when used as LNA2.

Ku band LNA using BFU730F

# 3. Design

The Ku band LNA consists of one stage BFU730F amplifier. It is aimed to replace more costly pHemt transistors in the second and / or third stage of the LNB preamplifier. These stages have to compensate the higher noise of the following mixer stage, thus their gain has to be as high as possible. The driving designs criteria for the LNA is the maximization of its gain. Secondly the noise figure has to be as good as possible, with a very small compromise on gain. Due to the gain criteria, the input and output match are also optimized. Stability wise the LNA has to be unconditionally stable over very broad frequency range. In terms of linearity, the system analysis does not impose stringent requirements.

The design has been conducted using Agilent's Advanced Design System (ADS). The 2D EM Momentum tool has been used to design the microwave section and the PCB. The linear and harmonic balanced circuit tools have been used to simulate the gain, noise, match, stability and linearity performances of the LNA.

### 3.1 BFU730F Ku LNA - ADS simulation circuit






Fig 1. ADS simulation circuit for BFU730F Ku band LNA

Ku band LNA using BFU730F


### 3.2 BFU730F Ku LNA - ADS Gain and match simulation results




### 3.3 BFU730F Ku LNA - ADS NF simulation results



# 3.4 BFU730F Ku band LNA - ADS stability simulation results




# 3.5 BFU730F Ku band LNA - ADS linearity simulation results



Ku band LNA using BFU730F

# 4. Implementation

### 4.1 Schematic



AN11010 **NXP Semiconductors** 

Ku band LNA using BFU730F

# 4.2 Layout and assembly




Table 2. **Bill of materials** 

Designator	Description	Size	Value	Туре	Note
Q1	BFU730F	2X2mm		NXP Semiconductors	HBT
РСВ		30X30mm			
C1, C6	Capacitor	0402	2X 0.1pF (0.2pF)	Murata GRM1555C1HR10BA01 GRM1555C1HR20BA01	Input match
C2, C3	Capacitor	0402	220pF		Decoupling
C4	Capacitor	0402	47nF		Decoupling
R1	Resistor	0402	47R		Stability
R2	Resistor	0402	10R		Stability
R3	Resistor	0402	27k		Bias
R4	Resistor	0402	300R		Bias
X1, X2	SMA RF connector			Giga Lane PSF-S01	RF connector
Х3	DC connector			Molex, PCB header 2way	Bias

### Ku band LNA using BFU730F

### 4.3 Printed Circuit Board details

The PCB material used for this LNA Evaluation Board is Rogers RO4003. The PC board consists of: 0.35um top metal layer, 0.5mm thickness low loss dielectric layer with  $\epsilon_R$  = 3.38 and TanD=0.0024 and 0.35um bottom metal layer

### 4.4 LNA view





Fig 8. BFU730F Ku LNA EvB

### 4.5 Measurement results

### 4.5.1 Gain and match - typical values



- (1) No gain correction has been applied / see  $\S 5.3$  to apply correction
- (2) Blue S11, red S22

Fig 9. BFU730F Ku band LNA - Gain and match measurement plots

# 4.5.2 NF and Gain - typical values




(1) NF and Gain correction applied / see § 5.3 for value

Fig 10. BFU730F Ku band LNA – NF and Gain measurement plots

Ku band LNA using BFU730F

## 4.5.3 Linearity / OIP3 – typical values



### 4.5.4 Gain, NF, Current vs temperature

BFU730F Ku LNA exhibits less than 1dB gain variation for temperature varying in the range of: -40°C to +85°C

**Table 3. Gain / NF vs Temp**BFU730F EvB4 tested for Gain and NF variation over temperature [11]

Temperature (°C)	Icc (mA)	NF (dB)	Gain (dB)
+25	11.6	1.45	10.7
+50	11.4	1.6	10.65
+70	11.1	1.75	10.6
+85	11.0	1.8	10.55
-10	11.8	1.2	11.2
-25	11.9	1.15	11.2
-40	12	1.1	11.25

<sup>[1]</sup> Measurements have been focused on relative variation of the Gain and NF vs. temperature, however the absolute numbers might not be accurate. NF and Gain plots are available by request.

### Ku band LNA using BFU730F

### 4.5.5 Summary

Measurements results averaged over nine EvBs are presented in Table 4

Table 4. Typical results measured on the BFU730F Ku band LNA Evaluation Boards

Operating frequency is f=11.5GHz unless otherwise specified: Temp = 25 °C

Parameter		Symbol	Min	Тур	Max	Unit
Supply Voltage		$V_{CC}$	4.75	5	5.25	V
Supply Current		I <sub>CC</sub>	10.8	11.5	12.1	mA
	10.75GHz			10.55		dB
	11.25GHz			10.9		dB
Power gain	11.75GHz	G <sub>p</sub> [2] [3]		11.15		dB
	12.25GHz			11		dB
	12.75GHz			10.4		dB
	10.75GHz			1.4		dB
	11.25GHz			1.25		dB
Noise Figure	11.75GHz	NF <sup>[4] [5]</sup>		1.2		dB
	12.25GHz			1.2		dB
	12.75GHz			1.35		dB
Input Return Loss		RLin		12		dB
Output Return Loss		RL <sub>out</sub>		12		dB
Input 1dB Gain Compression		P <sub>i</sub> 1dB		0.5		dBm
Input third order intercept point		IP3 <sub>i</sub>		10		dBm

<sup>[2]</sup> No gain correction has been applied. To apply gain correction see § 5.3

<sup>[3]</sup> Average Gain = 10.85dB

<sup>[4]</sup> NF correction applied, see § 5.3

<sup>[5]</sup> Average NF = 1.3dB


Ku band LNA using BFU730F

# 5. NF and Gain measurement corrections

There are two types of errors and losses that have been taken into account to correct the NF and Gain measurement results: (1) Own system error for NF measurement and (2) insertion losses accounted to RF IN and RF OUT connectors, microstrip feed lines and the DC block used at the output of the LNA in NF measurements.

### 5.1 NF measurement system error

A Miteq professional amplifier, rated as NF=1dB, Gain=24dB, has been used as reference for NF measurement system correction. Its manufacturer data is in Fig 12:



Miteq 062 amplifier measured with the NF setup used to qualify the BFU730F Ku band LNA has the NF performances listed in <u>Fig 13</u>. The system correction factor, NFsys, is the difference between the measured NF and the 1dB reference value from the catalog

RBW:	1 MHz	RF Atten.	O dB	2nd Stage Corr.	. On
Average:	3	Auto Ref Level	On	Image Rejection	n
					2
RF:	10 GHz	ENR	5.29 dB	NF.	1.47 dB
LO:	***	Loss In	O dB	Noise Temp.	116.84 K
(F:	***	Loss Out	O dB	Gain	23.46 dB
		Frequency	List Results		
12	RF	NF	Nois	e Temp	Gain
	10.000 GHz	1.470 d	3	116.845 K	23.464 dB
	10.250 GHz	1.500 d	3	119.623 K	23.809 d8
	10.500 GHz	1.510 d	3	120.626 K	24.469 d8
7.	10.750 GHZ	1.539 d	3	123.332 K	24.663 dB
	11,000 GHz	1.540 d	3	123.445 K	24.427 dB
	11.250 GHz	1.557 d	3	125.018 K	24.138 d8
	11.500 GHz	1.535 d	)	122.928 K	24.126 dB
	11.750 GHZ	1.552 d	3	124.553 K	24.437 dB
	12,000 GHz	1.570 d	3	126.271 K	24.902 d8
	12.250 GHz	1.538 d	3	123.270 K	24.992 d8
	12.500 GHz	1.572 d	3	126.448 K	24.500 dB
	12.750 GHz	1.535 d	3	122.929 K	23.952 d8
	13.000 GH2	1.570 d	3	126.280 K	23.682 d8
					019aab365
<b>Fsys</b> = NFta .5dB	ble13 – 1dB re	epresents the N	F system	correction fac	ctor: average valu

### Ku band LNA using BFU730F

### 5.2 Insertion losses

The losses that have to be taken into account are: (1) RF connectors and micro strip lines for Gain-match measurement and RF connectors and microstrip lines plus output DC block for the NF-Gain measurement.

Fig 14 and Fig 15 below plot the two losses:






Fig 14. Insertion loss for 2 RF connector and 27mm uStrip line on Rogers4003 PCB



Ku band LNA using BFU730F

Fig 16 shows the on board loss spitted between the input and the output:



### 5.3 Correction factors for Gain-match and NF-Gain measurements

Table 5. Correction factors / values

Measurement type	Correction on	Corrected for	Correction value	Correction applied
Gain-match on Network Analyzer	Gain	RFin + RFout total loss	RF_IL=RFin + RFout = 0.75dB	N
NF-Gain on	NF	NF System error + RFin loss	NFsys+RFin = 0.5dB+0.15dB ≈0.65dB	Y
NF Analyzer	Gain	RFout loss + DC block loss	RF_IL_DC -NFsys-RFin=0.95dB-0.65dB = 0.3dB	Υ

# Ku band LNA using BFU730F

# 6. Abbreviations / explanations

Table 6. List of abbreviation within text

Abbreviation	Stands for
LNA	Low Noise Amplifier
LNB	Low Noise Block
Ku band LNB	LNB in the frequency band of 10.7 ~ 12.75GHz
NF	Noise Figure
PCB	Printed Circuit Board
ВОМ	Bill of materials
ABS-S LNB	LNB for China Satellite System
MW	Microwave
EM	Electromagnetic

### Ku band LNA using BFU730F

# 7. Legal information

### 7.1 Definitions

Draft — The document is a draft version only. The content is still under internal review and subject to formal approval, which may result in modifications or additions. NXP Semiconductors does not give any representations or warranties as to the accuracy or completeness of information included herein and shall have no liability for the consequences of use of such information.

### 7.2 Disclaimers

Limited warranty and liability — Information in this document is believed to be accurate and reliable. However, NXP Semiconductors does not give any representations or warranties, expressed or implied, as to the accuracy or completeness of such information and shall have no liability for the consequences of use of such information.

In no event shall NXP Semiconductors be liable for any indirect, incidental, punitive, special or consequential damages (including - without limitation - lost profits, lost savings, business interruption, costs related to the removal or replacement of any products or rework charges) whether or not such damages are based on tort (including negligence), warranty, breach of contract or any other legal theory.

Notwithstanding any damages that customer might incur for any reason whatsoever, NXP Semiconductors' aggregate and cumulative liability towards customer for the products described herein shall be limited in accordance with the Terms and conditions of commercial sale of NXP Semiconductors.

Right to make changes — NXP Semiconductors reserves the right to make changes to information published in this document, including without limitation specifications and product descriptions, at any time and without notice. This document supersedes and replaces all information supplied prior to the publication hereof.

Suitability for use — NXP Semiconductors products are not designed, authorized or warranted to be suitable for use in life support, life-critical or safety-critical systems or equipment, nor in applications where failure or malfunction of an NXP Semiconductors product can reasonably be expected to result in personal injury, death or severe property or environmental damage. NXP Semiconductors accepts no liability for inclusion and/or use of NXP Semiconductors products in such equipment or applications and therefore such inclusion and/or use is at the customer's own risk.

**Applications** — Applications that are described herein for any of these products are for illustrative purposes only. NXP Semiconductors makes no representation or warranty that such applications will be suitable for the specified use without further testing or modification.

Customers are responsible for the design and operation of their applications and products using NXP Semiconductors products, and NXP Semiconductors accepts no liability for any assistance with applications or customer product design. It is customer's sole responsibility to determine whether the NXP Semiconductors product is suitable and fit for the

customer's applications and products planned, as well as for the planned application and use of customer's third party customer(s). Customers should provide appropriate design and operating safeguards to minimize the risks associated with their applications and products.

NXP Semiconductors does not accept any liability related to any default, damage, costs or problem which is based on any weakness or default in the customer's applications or products, or the application or use by customer's third party customer(s). Customer is responsible for doing all necessary testing for the customer's applications and products using NXP Semiconductors products in order to avoid a default of the applications and the products or of the application or use by customer's third party customer(s). NXP does not accept any liability in this respect.

**Export control** — This document as well as the item(s) described herein may be subject to export control regulations. Export might require a prior authorization from national authorities.

**Evaluation products** — This product is provided on an "as is" and "with all faults" basis for evaluation purposes only. NXP Semiconductors, its affiliates and their suppliers expressly disclaim all warranties, whether express, implied or statutory, including but not limited to the implied warranties of non-infringement, merchantability and fitness for a particular purpose. The entire risk as to the quality, or arising out of the use or performance, of this product remains with customer.

In no event shall NXP Semiconductors, its affiliates or their suppliers be liable to customer for any special, indirect, consequential, punitive or incidental damages (including without limitation damages for loss of business, business interruption, loss of use, loss of data or information, and the like) arising out the use of or inability to use the product, whether or not based on tort (including negligence), strict liability, breach of contract, breach of warranty or any other theory, even if advised of the possibility of such damages.

Notwithstanding any damages that customer might incur for any reason whatsoever (including without limitation, all damages referenced above and all direct or general damages), the entire liability of NXP Semiconductors, its affiliates and their suppliers and customer's exclusive remedy for all of the foregoing shall be limited to actual damages incurred by customer based on reasonable reliance up to the greater of the amount actually paid by customer for the product or five dollars (US\$5.00). The foregoing limitations, exclusions and disclaimers shall apply to the maximum extent permitted by applicable law, even if any remedy fails of its essential purpose.

### 7.3 Trademarks

Notice: All referenced brands, product names, service names and trademarks are property of their respective owners.

<Name> — is a trademark of NXP B.V.

# Ku band LNA using BFU730F

# 8. List of figures

Fig 1.	ADS simulation circuit for BFU730F Ku band LNA4
Fig 2.	ADS Gain and match simulation results for BFU730F Ku band LNA5
Fig 3.	ADS Noise Figure simulation results for Ku band LNA5
Fig 4.	ADS stability simulation results for Ku band LNA
Fig 5.	ADS linearity simulation results for Ku band LNA
Fig 6.	Schematic for BFU730F Ku band LNA EvB7
Fig 7.	Layout and assembly information for BFU730F Ku band LNA EvB8
Fig 8.	BFU730F Ku LNA EvB9
Fig 9.	BFU730F Ku band LNA – Gain and match measurement plots10
Fig 10.	BFU730F Ku band LNA – NF and Gain measurement plots10
Fig 11.	BFU730F Ku band LNA – Linearity measurement plot11
Fig 12.	Miteq amp 06213
Fig 13.	Miteq 062 amplifier NF and Gain13
Fig 14.	Insertion loss for 2 RF connector and 27mm uStrip line on Rogers4003 PCB14
Fig 15.	Insertion loss for a RO4003 27mm SMA_SMA thru + Agilent DC block14
Fig 16.	Insertion loss distribution15

# Ku band LNA using BFU730F

# 9. List of tables

Table 1.	BFU730F vs pHemt NF and Gain performa	ance
	comparison	3
Table 2.	Bill of materials	8
Table 3.	Gain / NF vs Temp	11
Table 4.	Typical results measured on the BFU730F	Ku
	band LNA Evaluation Boards	12
Table 5.	Correction factors / values	15
Table 6.	List of abbreviation within text	16

NXP Semiconductors

AN11010

Ku band LNA using BFU730F

# 10. Contents

1.	Introduction	3
2.	Requirements for Ku band LNA	3
3.	Design	4
3.1	BFU730F Ku LNA - ADS simulation circuit	4
3.2	BFU730F Ku LNA - ADS Gain and match	
	simulation results	
3.3	BFU730F Ku LNA - ADS NF simulation results	
3.4	BFU730F Ku band LNA - ADS stability simulation results	
3.5	BFU730F Ku band LNA - ADS linearity simulatio	U n
5.5	results	
4.	Implementation	
4.1	Schematic	
4.2	Layout and assembly	8
4.3	Printed Circuit Board details	9
4.4	LNA view	
4.5	Measurement results	
4.5.1	Gain and match – typical values	
4.5.2	NF and Gain – typical values	
4.5.3	Linearity / OIP3 – typical values	
4.5.4	Gain, NF, Current vs temperature	
4.5.5	Summary	
5.	NF and Gain measurement corrections	_
5.1	NF measurement system error	
5.2	Insertion losses	14
5.3	Correction factors for Gain-match and NF-Gain	
	measurements	
6.	Abbreviations / explanations	
7.	Legal information	17
7.1	Definitions	17
7.2	Disclaimers	17
7.3	Trademarks	17
8.	List of figures	18
9.	List of tables	19
10.	Contents	20

Please be aware that important notices concerning this document and the product(s) described herein, have been included in the section 'Legal information'.

© NXP B.V. 2010.

All rights reserved.