

# AN12976

## Wi-Fi Alliance Derivative Certification Process

Rev. 3 — 29 January 2021

Application note

### Document information

Information	Content
Keywords	Wi-Fi Alliance (WFA), certificate qualification, certification process, derivative
Abstract	Overview of Wi-Fi Alliance certification program and step-by-step procedure of the Wi-Fi derivative certification process



## Revision history

### Revision history

Rev	Date	Description
v.1	20200930	Initial version
v.2	20201106	<b>Modifications</b> <ul style="list-style-type: none"><li>• <a href="#">Section 4.1 "Log on and start a new application"</a>: added the screenshot showing the CID option for 88W8987-based products and Android operating system</li><li>• <a href="#">Section 4.2 "Capture the product information"</a>: added the screenshot showing 88W8987 product information with Android operating system</li></ul>
v.3	20210129	<b>Modifications</b> <ul style="list-style-type: none"><li>• <a href="#">Section 1 "About this document"</a>: updated</li><li>• <a href="#">Section 4 "Step by step procedure"</a>: updated per the latest certification system from Wi-Fi Alliance</li></ul>

## 1 About this document

### 1.1 Purpose and scope

This document presents the overall Wi-Fi Alliance derivative certification process with the steps to follow for the derivative certification of your products.

### 1.2 References

Table 1. Reference documents

Document type	Description
Overview	Wi-Fi Alliance - <i>Wi-Fi_CERTIFIED_Derivative_Certifications_Overview_v3.2_0.pdf</i>
Policy	Wi-Fi Alliance - <i>Wi-Fi_Alliance_Derivative_Certifications_Policy_v4.2.pdf</i>

## 2 Wi-Fi certification program

### 2.1 Overview

Wi-Fi CERTIFIED™ is an internationally recognized logo of approval for products indicating that they meet the industry agreed standard for interoperability, security, quality and a range of application specific protocols. It ensures the product delivers best user experience.

The Wi-Fi certification program assures tested and proven interoperability among Wi-Fi devices. This certification gives confidence that Wi-Fi product bearing Wi-Fi Certified logo have passed rigorous interoperability requirements.

Authorized Test Labs(ATL) certification is important and most of the time it is the last milestone before the product launch.

For more information, refer to <https://www.wi-fi.org/>.

### 2.2 Certificate qualification

#### 2.2.1 88W8987 (AW-CM358MA)

- STA | 802.11n (Test Plan version)
- STA | 802.11ac (Test Plan version)
- STA | WPS2.0 (Test Plan version)
- STA | PMF (Test Plan version)
- STA | WMM-PS (Test Plan version)

### 2.3 Roles and responsibilities

#### Wi-Fi Alliance

- Owner of the certification program
- Maintain policies and requirements
- Review ATLs results
- Final authority for the approval of Wi-Fi CERTIFIED products


#### Authorized Test Labs (ATL)

- Operate as independent testing facilities
- Submit results to WFA
- Help in getting the approval for ASD

#### WFA members

- Membership is needed to those who wish to obtain certification of products
- Only members can submit products to ATLs and choose any ATL

## 2.4 Certification process



**Note:** When applying for a derivative certification, some steps of the certification process are skipped as you provide a reference to an already certified product. The process is explained in the following section.

### 3 Derivative certification

#### 3.1 Overview

A derivative certification is a cost-effective way to utilize test results of a Wi-Fi CERTIFIED source product that has undergone ATL testing and Wi-Fi certification.

Multiple derivative certifications can be created from the same source product.

The new product must have the same chipset, operating system (OS), and firmware as tested in the Wi-Fi CERTIFIED source product.

The new product must operate in the same manner as the Wi-Fi CERTIFIED source product.

Any changes in the new product **MUST NOT** affect the wireless functionality.

A derivative certification cannot be designated as a source, and as a result, a derivative certification cannot be used to create another derivative.

#### 3.2 Derivative certification process




Figure 2. Derivative certification process

Please refer to [Section 4 "Step by step procedure"](#).

## 4 Step by step procedure

### 4.1 Log on and start a new application

Log on to [www.wi-fi.org](http://www.wi-fi.org) site as a member. The site opens on the **Applications** page. Click on the **New Application** tab.




Figure 3. Logon screen

On the New Application page, go to **Please select the certification type**, and select the third item on the list: **A derivative of Existing Product**.




Figure 4. New Application screen



- Click on the icon on the right of the first field to open the list and select **NXP Semiconductors** as the source company.
- Click on the icon on the right of the second field and select the CID for your product and operating system.

[Figure 5](#) shows the CID for 88W8987-based wireless module and Linux OS.




Figure 5. Selecting 88W8987-based products and Linux OS

Figure 6 shows the CID for 88W8987-based wireless module and Android OS.




Figure 6. Selecting 88W8987-based products and Android OS

- Click on **Next**

## 4.2 Capture the product information

The next **New Application** page is for **Step 1. Product Information**.

**Caution:** Make sure to capture the exact information about your product as the Wi-Fi components cannot be modified once you have submitted the application.

- Capture the **Product Name** and **Variant Name**
- Capture the **Model Number** and **Product URL**
- Click on the icon to view the list of **Primary Category of Product** and select the category for your product




Figure 7. Capturing the product information

- Verify the Wi-Fi component details.  
[Figure 8](#) shows the Wi-Fi component details for a product based on 88W8987-based product and Linux OS.




Figure 8. 88W8987-based product information (Linux operating system)

- [Figure 9](#) shows the Wi-Fi component details for a product based on 88W8987-based product and Android OS.




Figure 9. 88W8987-based product information (Android operating system)

- Click on **Next Step**

### 4.3 Submit the application

The last **New Application** page is for **Step 2. Submit**.

- Capture optional information such as the PO number and/or CTIA number
- Go to the **Wi-Fi Alliance Terms and Agreements** section on the page
- Check the two boxes to confirm you acknowledge *Wi-Fi Alliance Certification Terms and Conditions* and that you agree to the *Wi-Fi Alliance Certification Mark License Agreement*
- Click on **Submit**




Figure 10. Submit Application Screen

## 5 Obligations and outcomes for derivative certifications

- A member holding the source certification shall be informed of all approved derivative certifications.
- The member holding the source certification and the member holding the derivative certification shall both be accountable for addressing interoperability concerns.
- If interoperability concerns are found with a Derivative Certification and/or Source Certification then both certifications shall be subject to additional verification.
- If identified interoperability concern has not been resolved, the associated certifications shall be revoked.
- If information provided in the certification application(s) is found to be inaccurate, the associated certifications shall be revoked.
- If a Source Certification is revoked, all Derivative Certifications based on that Source Certification shall be revoked.
- A Member holding a Source Certification or a Derivative Certification shall be responsible for responding to Wi-Fi Alliance requests for information in support of these activities.

## 6 Acronyms and abbreviations

Table 2. Acronyms and abbreviations

Terms	Definition
ATL	Authorized Test Labs
CID	Certification Identification Number
CTIA	Cellular Telecommunications and Internet Association

## 7 Legal information

### 7.1 Definitions

**Draft** — A draft status on a document indicates that the content is still under internal review and subject to formal approval, which may result in modifications or additions. NXP Semiconductors does not give any representations or warranties as to the accuracy or completeness of information included in a draft version of a document and shall have no liability for the consequences of use of such information.

### 7.2 Disclaimers

**Limited warranty and liability** — Information in this document is believed to be accurate and reliable. However, NXP Semiconductors does not give any representations or warranties, expressed or implied, as to the accuracy or completeness of such information and shall have no liability for the consequences of use of such information. NXP Semiconductors takes no responsibility for the content in this document if provided by an information source outside of NXP Semiconductors. In no event shall NXP Semiconductors be liable for any indirect, incidental, punitive, special or consequential damages (including - without limitation - lost profits, lost savings, business interruption, costs related to the removal or replacement of any products or rework charges) whether or not such damages are based on tort (including negligence), warranty, breach of contract or any other legal theory. Notwithstanding any damages that customer might incur for any reason whatsoever, NXP Semiconductors' aggregate and cumulative liability towards customer for the products described herein shall be limited in accordance with the Terms and conditions of commercial sale of NXP Semiconductors.

**Right to make changes** — NXP Semiconductors reserves the right to make changes to information published in this document, including without limitation specifications and product descriptions, at any time and without notice. This document supersedes and replaces all information supplied prior to the publication hereof.

**Suitability for use** — NXP Semiconductors products are not designed, authorized or warranted to be suitable for use in life support, life-critical or safety-critical systems or equipment, nor in applications where failure or malfunction of an NXP Semiconductors product can reasonably be expected to result in personal injury, death or severe property or environmental damage. NXP Semiconductors and its suppliers accept no liability for inclusion and/or use of NXP Semiconductors products in such equipment or applications and therefore such inclusion and/or use is at the customer's own risk.

**Applications** — Applications that are described herein for any of these products are for illustrative purposes only. NXP Semiconductors makes no representation or warranty that such applications will be suitable for the specified use without further testing or modification. Customers are responsible for the design and operation of their applications and products using NXP Semiconductors products, and NXP Semiconductors

accepts no liability for any assistance with applications or customer product design. It is customer's sole responsibility to determine whether the NXP Semiconductors product is suitable and fit for the customer's applications and products planned, as well as for the planned application and use of customer's third party customer(s). Customers should provide appropriate design and operating safeguards to minimize the risks associated with their applications and products. NXP Semiconductors does not accept any liability related to any default, damage, costs or problem which is based on any weakness or default in the customer's applications or products, or the application or use by customer's third party customer(s). Customer is responsible for doing all necessary testing for the customer's applications and products using NXP Semiconductors products in order to avoid a default of the applications and the products or of the application or use by customer's third party customer(s). NXP does not accept any liability in this respect.

**Export control** — This document as well as the item(s) described herein may be subject to export control regulations. Export might require a prior authorization from competent authorities.

**Evaluation products** — This product is provided on an "as is" and "with all faults" basis for evaluation purposes only. NXP Semiconductors, its affiliates and their suppliers expressly disclaim all warranties, whether express, implied or statutory, including but not limited to the implied warranties of non-infringement, merchantability and fitness for a particular purpose. The entire risk as to the quality, or arising out of the use or performance, of this product remains with customer. In no event shall NXP Semiconductors, its affiliates or their suppliers be liable to customer for any special, indirect, consequential, punitive or incidental damages (including without limitation damages for loss of business, business interruption, loss of use, loss of data or information, and the like) arising out of the use of or inability to use the product, whether or not based on tort (including negligence), strict liability, breach of contract, breach of warranty or any other theory, even if advised of the possibility of such damages. Notwithstanding any damages that customer might incur for any reason whatsoever (including without limitation, all damages referenced above and all direct or general damages), the entire liability of NXP Semiconductors, its affiliates and their suppliers and customer's exclusive remedy for all of the foregoing shall be limited to actual damages incurred by customer based on reasonable reliance up to the greater of the amount actually paid by customer for the product or five dollars (US\$5.00). The foregoing limitations, exclusions and disclaimers shall apply to the maximum extent permitted by applicable law, even if any remedy fails of its essential purpose.

**Translations** — A non-English (translated) version of a document is for reference only. The English version shall prevail in case of any discrepancy between the translated and English versions.

### 7.3 Trademarks

Notice: All referenced brands, product names, service names and trademarks are the property of their respective owners.

**Tables**

Tab. 1. Reference documents ..... 3	Tab. 2. Acronyms and abbreviations ..... 14
-------------------------------------	---

**Figures**

Fig. 1. Certification process .....5	Fig. 7. Capturing the product information ..... 11
Fig. 2. Derivative certification process .....6	Fig. 8. 88W8987-based product information (Linux operating system) ..... 12
Fig. 3. Logon screen ..... 7	Fig. 9. 88W8987-based product information (Android operating system) ..... 12
Fig. 4. New Application screen .....8	Fig. 10. Submit Application Screen ..... 13
Fig. 5. Selecting 88W8987-based products and Linux OS ..... 9	
Fig. 6. Selecting 88W8987-based products and Android OS .....10	



---

## Contents

---

<b>1</b>	<b>About this document</b> .....	<b>3</b>
1.1	Purpose and scope .....	3
1.2	References .....	3
<b>2</b>	<b>Wi-Fi certification program</b> .....	<b>4</b>
2.1	Overview .....	4
2.2	Certificate qualification .....	4
2.2.1	88W8987 (AW-CM358MA) .....	4
2.3	Roles and responsibilities .....	4
2.4	Certification process .....	5
<b>3</b>	<b>Derivative certification</b> .....	<b>6</b>
3.1	Overview .....	6
3.2	Derivative certification process .....	6
<b>4</b>	<b>Step by step procedure</b> .....	<b>7</b>
4.1	Log on and start a new application .....	7
4.2	Capture the product information .....	11
4.3	Submit the application .....	13
<b>5</b>	<b>Obligations and outcomes for derivative certifications</b> .....	<b>14</b>
<b>6</b>	<b>Acronyms and abbreviations</b> .....	<b>14</b>
<b>7</b>	<b>Legal information</b> .....	<b>15</b>

---

Please be aware that important notices concerning this document and the product(s) described herein, have been included in section 'Legal information'.

---

© NXP B.V. 2021.

All rights reserved.

For more information, please visit: <http://www.nxp.com>

For sales office addresses, please send an email to: [salesaddresses@nxp.com](mailto:salesaddresses@nxp.com)

Date of release: 29 January 2021  
Document identifier: AN12976