# **MPC5775E**

# MPC5775E/MPC5775B Microcontroller Data Sheet

#### Features

- This document provides electrical specifications, pin assignments, and package diagram information for the MPC5775E series of microcontroller units (MCUs).
- For functional characteristics and the programming model, see the MPC5775E Reference Manual.

NXP reserves the right to change the proudction detail specifications as may be required to permit improvements in the design of its products.



# **Table of Contents**

| 1 | Introc | luction    | 3  |
|---|--------|------------|--|
|   | 1.1    | Features   | s summary3                                   |
|   | 1.2    | Block dia  | agram4                                       |
| 2 | Pinou  | ıts        | 5  |
|   | 2.1    | 416-ball   | MAPBGA pin assignments5                      |
| 3 | Electi | rical char | acteristics6                                 |
|   | 3.1    | Absolute   | e maximum ratings6                           |
|   | 3.2    | Electron   | nagnetic interference (EMI) characteristics8 |
|   | 3.3    | Electros   | tatic discharge (ESD) characteristics8       |
|   | 3.4    | Operatir   | ng conditions8                               |
|   | 3.5    | DC elec    | trical specifications11                      |
|   | 3.6    | I/O pad    | specifications12                             |
|   |        | 3.6.1      | Input pad specifications12                   |
|   |        | 3.6.2      | Output pad specifications14                  |
|   |        | 3.6.3      | I/O pad current specifications17             |
|   | 3.7    | Oscillato  | or and PLL electrical specifications17       |
|   |        | 3.7.1      | PLL electrical specifications18              |
|   |        | 3.7.2      | Oscillator electrical specifications19       |
|   | 3.8    | Analog-t   | o-Digital Converter (ADC) electrical         |
|   |        | specifica  | ations21                                     |
|   |        | 3.8.1      | Enhanced Queued Analog-to-Digital            |
|   |        |            | Converter (eQADC)21                          |
|   |        | 3.8.2      | Sigma-Delta ADC (SDADC)23                    |
|   | 3.9    | Tempera    | ature Sensor                                 |
|   | 3.10   | LVDS pa    | ad electrical characteristics                |
|   |        | 3.10.1     | MSC/DSPI LVDS interface timing diagrams32    |
|   |        | 3.10.2     | MSC/DSPI LVDS interface electrical           |
|   |        |            | characteristics                              |
|   | 3.11   | Power n    | nanagement: PMC, POR/LVD, power              |
|   |        | sequenc    | ing36  |

|   |       | 3.11.1      | Power management electrical characteristics37 |
|---|-------|-------------|---|
|   |       | 3.11.2      | Power management integration39                |
|   |       | 3.11.3      | Device voltage monitoring41                   |
|   |       | 3.11.4      | Power sequencing requirements43               |
|   | 3.12  | Flash m     | emory specifications44                        |
|   |       | 3.12.1      | Flash memory program and erase                |
|   |       |             | specifications45                              |
|   |       | 3.12.2      | Flash memory Array Integrity and Margin       |
|   |       |             | Read specifications45                         |
|   |       | 3.12.3      | Flash memory module life specifications46     |
|   |       | 3.12.4      | Data retention vs program/erase cycles47      |
|   |       | 3.12.5      | Flash memory AC timing specifications47       |
|   |       | 3.12.6      | Flash memory read wait-state and address-     |
|   |       |             | pipeline control settings48                   |
|   | 3.13  | AC timin    | ng49  |
|   |       | 3.13.1      | Generic timing diagrams49                     |
|   |       | 3.13.2      | Reset and configuration pin timing50          |
|   |       | 3.13.3      | IEEE 1149.1 interface timing51                |
|   |       | 3.13.4      | Nexus timing54                                |
|   |       | 3.13.5      | External interrupt timing (IRQ/NMI pin)56     |
|   |       | 3.13.6      | eTPU timing57                                 |
|   |       | 3.13.7      | eMIOS timing57                                |
|   |       | 3.13.8      | DSPI timing with CMOS and LVDS pads58         |
|   |       | 3.13.9      | FEC timing70                                  |
| 4 | Packa | age inforr  | nation75                                      |
|   | 4.1   | Thermal     | characteristics75                             |
|   |       | 4.1.1       | General notes for thermal characteristics76   |
| 5 | Orde  | ring inforr | mation79                                      |
| 6 | Docu  | ment revi   | ision history79                               |

# **1** Introduction

# **1.1 Features summary**

On-chip modules available within the family include the following features:

- Three dual issue, 32-bit CPU core complexes (e200z7), two of which run in lockstep
  - Power Architecture embedded specification compliance
  - Instruction set enhancement allowing variable length encoding (VLE), optional encoding of mixed 16-bit and 32-bit instructions, for code size footprint reduction
  - On the two computational cores: Signal processing extension (SPE1.1) instruction support for digital signal processing (DSP)
  - Single-precision floating point operations
  - On the two computational cores: 16 KB I-Cache and 16 KB D-Cache
  - Hardware cache coherency between cores
- 16 hardware semaphores
- 3-channel CRC module
- 4 MB on-chip flash memory
  - Supports read during program and erase operations, and multiple blocks allowing EEPROM emulation
- 512 KB on-chip general-purpose SRAM including 64 KB standby RAM
- Two multichannel direct memory access controllers (eDMA)
  - 64 channels per eDMA
- Dual core Interrupt Controller (INTC)
- Dual phase-locked loops (PLLs) with stable clock domain for peripherals and frequency modulation (FM) domain for computational shell
- Crossbar Switch architecture for concurrent access to peripherals, flash memory, or RAM from multiple bus masters with End-To-End ECC
- System Integration Unit (SIU)
- Error Injection Module (EIM) and Error Reporting Module (ERM)
- Four protected port output (PPO) pins
- Boot Assist Module (BAM) supports serial bootload via CAN or SCI
- Up to three second-generation Enhanced Time Processor Units (eTPUs)
  - 32 channels per eTPU
  - Total of 36 KB code RAM
  - Total of 9 KB parameter RAM

#### Introduction

- Enhanced Modular Input/Output System (eMIOS) supporting 32 unified channels with each channel capable of single action, double action, pulse width modulation (PWM) and modulus counter operation
- Up to two Enhanced Queued Analog-to-Digital Converter (eQADC) modules with:
  - Two separate analog converters per eQADC module
  - Support for a total of 70 analog input pins, expandable to 182 inputs with offchip multiplexers
- Up to four independent 16-bit Sigma-Delta ADCs (SDADCs)
- Ethernet (FEC)
- Two SENT Receiver (SRX) modules supporting 12 channels
- Five Deserial Serial Peripheral Interface (DSPI) modules
- Five Enhanced Serial Communication Interface (eSCI) modules
- Four Controller Area Network (FlexCAN) modules
- Two M\_CAN modules that support FD
- Fault Collection and Control Unit (FCCU)
- Clock Monitor Units (CMUs)
- Tamper Detection Module (TDM)
- Cryptographic Services Engine (CSE)
  - Complies with Secure Hardware Extension (SHE) Functional Specification Version 1.1 security functions
  - Includes software selectable enhancement to key usage flag for MAC verification and increase in number of memory slots for security keys
- PASS module to support security features
- Nexus development interface (NDI) per IEEE-ISTO 5001-2003 standard, with some support for 2010 standard
- Device and board test support per Joint Test Action Group (JTAG) IEEE 1149.1 and 1149.7
- On-chip voltage regulator controller (VRC) that derives the core logic supply voltage from the high-voltage supply
- On-chip voltage regulator for flash memory
- Self Test capability

# 1.2 Block diagram

The following figure shows a top-level block diagram of the MPC5777E. The purpose of the block diagram is to show the general interconnection of functional modules through the crossbar switch.

#### Pinouts




Figure 1. MPC5775E block diagram

# 2 Pinouts

# 2.1 416-ball MAPBGA pin assignments

Figure 2 shows the 416-ball MAPBGA pin assignments.

Electrical characteristics

| A   |         | 2            | 3             | 4               | 5                    | 6             | 7     | 8     | 9              | 10             | 11             | 12             | 13      | 14      | 15      | 16          | 17             | 18             | 19            | 20            | 21     | 22     | 23                 | 24                 | 25                 | 26      | _ |
|-----|---------|--------------|---------------|-----------------|----------------------|---------------|-------|-------|----------------|----------------|----------------|----------------|---------|---------|---------|-------------|----------------|----------------|---------------|---------------|--------|--------|--------------------|--------------------|--------------------|---------|---|
|     | VSS     | VDD          | RSTOUT        | ANAO_SDA<br>O   | ANA4                 | ANA8          | ANA11 | ANA15 | VDDA_SD        | REFBYPCA<br>25 | VRL_SD         | VRH_SD         | AN28    | AN32    | AN36    | VDDA_E<br>Q | REFBYPCB<br>25 | VRL_EQ         | VRH_EQ        | ANB7_SDD<br>7 | ANB11  | ANB14  | ANB17              | ANB21              | ANB23              | VSS     |   |
| в   | VDDEH1  | VSS          | VDD           | TEST            | ANA1_SDA<br>1        | ANA5          | ANA10 | ANA14 | -              | VSSA_SD        | REFBYPCA<br>75 | AN24           | AN27    | AN29    | AN33    | VDDA_E<br>Q | VSSA_EQ        | REFBYPCB<br>75 | 6             | ANB8          | ANB10  | ANB15  | ANB18              | ANB22              | VSS                | TCRCLKC |   |
| c I | ETPUA30 | ETPUA31      | VSS           | VDD             | ANA2_SDA<br>2        | ANA6          | ANA9  | ANA13 | ANA17_SDB<br>1 | B3             | ANA21_SD<br>C1 | C3             | AN26    | AN30    | AN34    | AN37        | AN38           | 0              | ANB4_SDD<br>4 | ANB5_SDD<br>5 | ANB12  | ANB16  | ANB19              | VSS                | ETPUCO             | ETPUC1  |   |
|     | ETPUA27 | ETPUA28      | ETPUA29       | VSS             | VDD                  | ANA3_SDA<br>3 | ANA7  | ANA12 | ANA16_SDB<br>0 | ANA18_SD<br>B2 | ANA20_SD<br>CO | ANA22_SD<br>C2 | AN25    | AN31    | AN35    | AN39        | ANB1_SDD<br>1  | ANB2_SDD<br>2  | ANB3_SDD<br>3 | ANB9          | ANB13  | ANB20  | VSS                | SENT2_A            | ETPUC2             | ETPUC3  |   |
| E   | ETPUA23 | ETPUA24      | ETPUA25       | ETPUA26         |                      |               |       |       |                |                |                |                |         |         |         |             |                |                |               |               |        |        | VDDEH7             | ETPUC4             | ETPUC5             | ETPUC6  |   |
| F   | ETPUA19 | ETPUA20      | ETPUA21       | ETPUA22         |                      |               |       |       |                |                |                |                |         |         |         |             |                |                |               |               |        |        | ETPUC7             | ETPUC8             | ETPUC9             | ETPUC10 | - |
| -   | ETPUA15 | ETPUA16      |               | ETPUA18         |                      |               |       |       |                |                |                |                |         |         |         |             |                |                |               |               |        |        | ETPUC11            | ETPUC12            | ETPUC13            | ETPUC14 |   |
| -   |         | ETPUA12      |               | ETPUA13         |                      |               |       |       |                |                |                |                |         |         |         |             |                |                |               |               |        |        | ETPUC15            | ETPUC16            | ETPUC17            | ETPUC18 |   |
| · - | ETPUA7  | ETPUA8       | ETPUA9        | ETPUA10         |                      |               |       |       |                |                |                |                |         |         |         |             |                | 1              |               |               |        |        | ETPUC19            | ETPUC20            | ETPUC21            | ETPUC22 | - |
| -   | ETPUA3  | ETPUA4       | ETPUAS        | ETPUA6          |                      |               |       |       |                | VSS            | VSS            | VSS            | VSS     | VSS     | VSS     | VSS         | VSS            |                |               |               |        |        | ETPUC23            | ETPUC24            | ETPUC25            | ETPUC26 | - |
| L I | NC      | TXDA         | RXDA          | ETPUA2<br>VSTBY |                      |               |       |       |                | VSS            | VSS            | VSS            | VSS     | VSS     | VSS     | VSS         | VSS            |                |               |               |        |        | ETPUC27<br>ETPUC31 | ETPUC28<br>ETPUB15 | ETPUC29<br>ETPUB14 | ETPUC30 |   |
|     | RXDB    | BOOTCFG      | WKPCFG        | VDD             |                      |               |       |       |                | VDDE2          | VSS            | VSS            | VSS     | VSS     | VSS     | VSS         | VSS            |                |               |               |        |        | VDDEH6             | ETPUB11            | ETPUB12            | ETPUB13 |   |
|     | тхов    | 1<br>PLLCFG1 | PLLCFG2       | VDDEH1          |                      |               |       |       |                | VDDE2          | VDDE2          | VSS            | VSS     | VSS     | VSS     | vss         | VSS            |                |               |               |        |        | ETPUB7             | ETPUB8             | ETPUB9             | ETPUB10 |   |
| R   | JCOMP   | RESET        | PLLCFG0       | RDY             |                      |               |       |       |                | VDDE2          | VDDE2          | VSS            | VSS     | VSS     | VSS     | VSS         | VSS            |                |               |               |        |        | ETPUBS             | ETPUB4             | ETPUB5             | ETPUB6  |   |
| т   | VDDE2   | мско         | MSEO1         | EVTI            |                      |               |       |       |                | VDDE2          | VDDE2          | VDDE2          | VSS     | VSS     | VSS     | VSS         | VSS            |                |               |               |        |        | TCRCLKB            | ETPUBO             | ETPUB1             | ETPUB2  |   |
| U   | EVTO    | MSEOO        | MDO0          | MD01            |                      |               |       |       |                | VDDE2          | VDDE2          | VDDE2          | VSS     | VSS     | VSS     | VSS         | VSS            |                |               |               |        |        | ETPUB19            | ETPUB18            | ETPUB17            | ETPUB16 |   |
| , T | MDO2    | MDO3         | MDO4          | MDO5            |                      |               |       |       |                |                |                |                |         |         |         |             |                | 1              |               |               |        |        | ETPUB26            | ETPUB22            | ETPUB21            | ETPUB20 |   |
| N   | MDO6    | MDO7         | MDO8          | VDDE2           |                      |               |       |       |                |                |                |                |         |         |         |             |                |                |               |               |        |        | REGSEL             | ETPUB25            | ETPUB24            | ETPUB23 |   |
| Y   | MDO9    | MDO10        | MDO11         | MDO15           |                      |               |       |       |                |                |                |                |         |         |         |             |                |                |               |               |        |        | ETPUB29            | ETPUB28            | ETPUB27            | REGCTL  |   |
| A   | MDO12   | MDO13        | MDO14         | NC              |                      |               |       |       |                |                |                |                |         |         |         |             |                |                |               |               |        |        | VDDPMC             | ETPUB30            | VDDPWR             | VSSSYN  |   |
| в   | TDO     | тск          | TMS           | VDD             |                      |               |       |       |                |                |                |                |         |         |         |             |                |                |               |               |        |        | VDD                | ETPUB31            | VSSPWR             | EXTAL   |   |
| NC  | VDDE2   | TDI          | VDD           | VSS             | FEC_TXCLK<br>_REFCLK | PCSA1         | PCSA2 | PCSB4 | PCSB1          | VDDEH3         | VDDEH4         | VDD            | EMIOS8  | EMIOS14 | EMIOS18 | EMIOS22     | EMIOS27        | EMIOS31        | CNRXB         | CNRXD         | VDDEH5 | PCSC1  | VSSPMC             | VDD                | VDDEH6             | XTAL    |   |
| D   | ENGCLK  | VDD          | VSS           | FEC_TXD0        | FEC_TXD1             | PCSA5         | SOUTA | SCKA  | PCSBO          | PCSB3          | EMIOS2         | EMIOS5         | EMIOS9  | EMIOS15 | EMIOS19 | EMIOS23     | EMIOS26        | EMIOS30        | CNTXB         | CNTXD         | SCKC   | RXDC   | PCSC3              | VSS                | VDD                | VDDFLA  |   |
| E   | VDD     | VSS          | FEC_RX_D<br>V | FEC_TX_EN       | PCSA4                | PCSAO         | PCSA3 | SCKB  | SINB           | EMIOSO         | EMIOS3         | EMIOS6         | EMIOS10 | EMIOS13 | EMIOS17 | EMIOS21     | EMIOS25        | EMIOS29        | CNRXA         | CNRXC         | PCSCO  | SINC   | PCSC2              | PCSC5              | VSS                | VDD     |   |
| F   | VSS     | VDDE2A       | FEC_RXD0      | FEC_RXD1        | VDDEH3A              | PCSB5         | SINA  | PCSB2 | SOUTB          | EMIOS1         | EMIOS4         | EMIOS7         | EMIOS11 | EMIOS12 | EMIOS16 | EMIOS20     | EMIOS24        | EMIOS28        | CNTXA         | CNTXC         | SOUTC  | VDDEH4 | TXDC               | PCSC4              | VDDEH5             | VSS     |   |
|     | 1       | 2            | 3             | 4               | 5                    | 6             | 7     | 8     | 9              | 10             | 11             | 12             | 13      | 14      | 15      | 16          | 17             | 18             | 19            | 20            | 21     | 22     | 23                 | 24                 | 25                 | 26      |   |

Figure 2. MPC5775E 416-ball MAPBGA (full diagram)

The following information includes details about power considerations, DC/AC electrical characteristics, and AC timing specifications.

# 3.1 Absolute maximum ratings

Absolute maximum specifications are stress ratings only. Functional operation at these maxima is not guaranteed.

## CAUTION

Stress beyond listed maxima may affect device reliability or cause permanent damage to the device.

See Operating conditions for functional operation specifications.

| Symbol                                | Parameter   | Conditions <sup>1</sup>                                 | Va   | lue   | Unit |  |
|---------------------------------------|---|---|------|-------|------|--|
| Symbol                                | Falameter   | Conditions  | Min  | Max   | Unit |  |
| Cycle                                 | Lifetime power cycles                                   | —   | —    | 1000k | _    |  |
| V <sub>DD</sub>                       | 1.2 V core supply voltage <sup>2, 3, 4</sup>            |   | -0.3 | 1.5   | V    |  |
| V <sub>DDEHx</sub>                    | I/O supply voltage (medium I/O pads) <sup>5</sup>       |   | -0.3 | 6.0   | V    |  |
| V <sub>DDEx</sub>                     | I/O supply voltage (fast I/O pads) <sup>5</sup>         | _   | -0.3 | 6.0   | V    |  |
| V <sub>DDPMC</sub>                    | Power Management Controller supply voltage <sup>5</sup> | _   | -0.3 | 6.0   | V    |  |
| V <sub>DDFLA</sub>                    | Decoupling pin for flash regulator <sup>6</sup>         | _   | -0.3 | 4.5   | V    |  |
| V <sub>STBY</sub>                     | RAM standby supply voltage <sup>5</sup>                 |   | -0.3 | 6.0   | V    |  |
| V <sub>SSA_SD</sub>                   | SDADC ground voltage                                    | Reference to V <sub>SS</sub>                            | -0.3 | 0.3   | V    |  |
| V <sub>SSA_EQ</sub>                   | eQADC ground voltage                                    | Reference to V <sub>SS</sub>                            | -0.3 | 0.3   | V    |  |
| V <sub>DDA_EQA/B</sub>                | eQADC supply voltage                                    | Reference to V <sub>SSA_EQ</sub>                        | -0.3 | 6.0   | V    |  |
| V <sub>DDA_SD</sub>                   | SDADC supply voltage                                    | Reference to V <sub>SSA_SD</sub>                        | -0.3 | 6.0   | V    |  |
| V <sub>RL_SD</sub>                    | SDADC ground reference                                  | Reference to V <sub>SS</sub>                            | -0.3 | 0.3   | V    |  |
| V <sub>RL_EQ</sub>                    | eQADC ground reference                                  | Reference to V <sub>SS</sub>                            | -0.3 | 0.3   | V    |  |
| V <sub>RH_EQ</sub>                    | eQADC alternate reference                               | Reference to V <sub>RL_EQ</sub>                         | -0.3 | 6.0   | V    |  |
| V <sub>RH_SD</sub>                    | SDADC alternate reference                               | Reference to V <sub>RL_SD</sub>                         | -0.3 | 6.0   | V    |  |
| V <sub>REFBYPC</sub>                  | eQADC reference decoupling capacitor pins               | REFBYPCA25, REFBYPCA75,<br>REFBYPCB25, REFBYPC75        | -0.3 | 6.0   | V    |  |
| V <sub>DDA_MISC</sub>                 | TRNG and IRC supply voltage                             |   | -0.3 | 6.0   | V    |  |
| V <sub>DDPWR</sub>                    | SMPS driver supply pin                                  |   | -0.3 | 6.0   | V    |  |
| V <sub>SSPWR</sub>                    | SMPS driver supply pin                                  | Reference to V <sub>SS</sub>                            | -0.3 | 0.3   | V    |  |
| V <sub>SS</sub> – V <sub>SSA_EQ</sub> | V <sub>SSA_EQ</sub> differential voltage                | —   | -0.3 | 0.3   | V    |  |
| $V_{SS} - V_{SSA_SD}$                 | V <sub>SSA_SD</sub> differential voltage                | —   | -0.3 | 0.3   | V    |  |
| $V_{SS} - V_{RL_{EQ}}$                | V <sub>RL_EQ</sub> differential voltage                 |   | -0.3 | 0.3   | V    |  |
| $V_{SS} - V_{RL_{SD}}$                | V <sub>RL_SD</sub> differential voltage                 |   | -0.3 | 0.3   | V    |  |
| V <sub>IN</sub>                       | I/O input voltage range <sup>7</sup>                    |   | -0.3 | 6.0   | V    |  |
|                                       |   | Relative to V <sub>DDEx</sub> /V <sub>DDEHx</sub>       |      | 0.3   | V    |  |
|                                       |   | Relative to V <sub>SS</sub>                             | -0.3 | _     | V    |  |
| I <sub>INJD</sub>                     | Maximum DC injection current for digital pad            | Per pin, applies to all digital pins                    | -5   | 5     | mA   |  |
| I <sub>INJA</sub>                     | Maximum DC injection current for analog pad             | Per pin, applies to all analog pins                     | -5   | 5     | mA   |  |
| I <sub>MAXSEG</sub> <sup>8, 9</sup>   | Maximum current per I/O power segment                   | _   | -120 | 120   | mA   |  |
| T <sub>STG</sub>                      | Storage temperature range and non-<br>operating times   | _   | -55  | 175   | °C   |  |
| STORAGE                               | Maximum storage time, assembled part programmed in ECU  | No supply; storage temperature in range –40 °C to 60 °C | -    | 20    | year |  |
| T <sub>SDR</sub>                      | Maximum solder temperature <sup>10</sup>                | —   |      | 260   | °C   |  |

## Table 1. Absolute maximum ratings

Table continues on the next page ...

| Table 1. | Absolute | maximum | ratings | (continued) |
|----------|----------|---------|---------|-------------|
|----------|----------|---------|---------|-------------|

| Symbol | Parameter                                | Conditions <sup>1</sup> | Va  | lue | Unit |
|--------|--|-------------------------|-----|-----|------|
| Symbol | Faranieter                               | Conditions              | Min | Max |      |
| MSL    | Moisture sensitivity level <sup>11</sup> | —                       |     | 3   | —    |

- 1. Voltages are referred to  $V_{SS}$  if not specified otherwise
- Allowed 1.45 V 1.5 V for 60 seconds cumulative time at maximum T<sub>J</sub> = 150 °C; remaining time as defined in note 3 and note 4
- 3. Allowed 1.375 V 1.45 V for 10 hours cumulative time at maximum  $T_J$  = 150 °C; remaining time as defined in note 4
- 4. 1.32 V 1.375 V range allowed periodically for supply with sinusoidal shape and average supply value below 1.275 V at maximum T<sub>J</sub> = 150 °C
- 5. Allowed 5.5 V 6.0 V for 60 seconds cumulative time with no restrictions, for 10 hours cumulative time device in reset,  $T_J$  = 150 °C; remaining time at or below 5.5 V
- 6. Allowed 3.6 V 4.5 V for 60 seconds cumulative time with no restrictions, for 10 hours cumulative time device in reset,  $T_J$  = 150 °C; remaining time at or below 3.6 V
- 7. The maximum input voltage on an I/O pin tracks with the associated I/P supply maximum. For the injection current condition on a pin, the voltage will be equal to the supply plus the voltage drop across the internal ESD diode from I/O pin to supply. The diode voltage varies greatly across process and temperature, but a value of 0.3V can be used for nominal calculations.
- The sum of all controller pins (including both digital and analog) must not exceed 200 mA. A V<sub>DDEx</sub>/V<sub>DDEHx</sub> power segment is defined as one or more GPIO pins located between two V<sub>DDEx</sub>/V<sub>DDEHx</sub> supply pins.
- 9. The average current values given in I/O pad current specifications should be used to calculate total I/O segment current.
- 10. Solder profile per IPC/JEDEC J-STD-020D
- 11. Moisture sensitivity per JEDEC test method A112

# 3.2 Electromagnetic interference (EMI) characteristics

Test reports with EMC measurements to IC-level IEC standards are available on request.

To find application notes that provide guidance on designing your system to minimize interference from radiated emissions, go to nxp.com and perform a keyword search for "radiated emissions."

# 3.3 Electrostatic discharge (ESD) characteristics

| Symbol           | Parameter                          | Conditions      | Value | Unit |
|------------------|------------------------------------|-----------------|-------|------|
| V <sub>HBM</sub> | ESD for Human Body Model (HBM)     | All pins        | 2000  | V    |
| V <sub>CDM</sub> | ESD for Charged Device Model (CDM) | Corner pins     | 750   | V    |
|                  |                                    | Non-corner pins | 500   |      |

### Table 2. ESD Ratings<sup>1, 2</sup>

1. All ESD testing is in conformity with CDF-AEC-Q100 Stress Test Qualification for Automotive Grade Integrated Circuits.

2. A device will be defined as a failure if after exposure to ESD pulses the device no longer meets the device specification requirements.

# 3.4 Operating conditions

The following table describes the operating conditions for the device, and for which all specifications in the data sheet are valid, except where explicitly noted.

If the device operating conditions are exceeded, the functionality of the device is not guaranteed.

| Symbol   | Parameter  | Conditions                              |                    | Value |                      | Uni |
|--|--|---|--------------------|-------|----------------------|-----|
| Symbol   | Parameter  | Conditions                              | Min                | Тур   | Max                  |     |
|  |  | Frequency                               |                    |       | •                    |     |
| f <sub>SYS</sub>                                   | Device operating frequency <sup>1</sup>  | —                                       | —                  | _     | 264 <sup>2</sup>     | MHz |
| f <sub>PLATF</sub>                                 | Platform operating frequency   | —                                       | —                  | —     | 132 <sup>3</sup>     | MHz |
| f <sub>ETPU</sub>                                  | eTPU operating frequency   | —                                       | —                  | _     | 200                  | MHz |
| f <sub>PER</sub>                                   | Peripheral block operating<br>frequency  | —                                       | —                  | —     | 132 <sup>3</sup>     | MHz |
| f <sub>FM_PER</sub>                                | Frequency-modulated peripheral block operating frequency                             | —                                       | —                  | —     | 132 <sup>3</sup>     | MHz |
| t <sub>CYC</sub>                                   | Platform clock period  | —                                       | —                  | _     | 1/f <sub>PLATF</sub> | ns  |
| t <sub>CYC_ETPU</sub>                              | eTPU clock period  | —                                       | _                  | _     | 1/f <sub>ETPU</sub>  | ns  |
| t <sub>CYC_PER</sub>                               | Peripheral clock period  | —                                       | _                  | _     | 1/f <sub>PER</sub>   | ns  |
|  |  | Temperature                             | -11                |       |                      |     |
| TJ   | Junction operating temperature range   | Packaged devices                        | -40.0              |       | 150.0                | °C  |
| T <sub>A</sub> (T <sub>L</sub> to T <sub>H</sub> ) | Ambient operating temperature range  | Packaged devices                        | -40.0              | —     | 125.0 <sup>4</sup>   | °C  |
|  |  | Voltage                                 | -1 1               |       |                      |     |
| V <sub>DD</sub>                                    | External core supply voltage <sup>5, 6</sup>   | LVD/HVD enabled                         | 1.2                | _     | 1.32                 | V   |
|  |  | LVD/HVD disabled <sup>7, 8, 9, 10</sup> | 1.2                | _     | 1.38                 | 1   |
| V <sub>DDA_MISC</sub>                              | TRNG and IRC supply voltage  | —                                       | 3.5                | —     | 5.5                  | V   |
| V <sub>DDEx</sub>                                  | I/O supply voltage (fast I/O pads)   | 5 V range                               | 4.5                | _     | 5.5                  | V   |
|  |  | 3.3 V range                             | 3.0                | _     | 3.6                  |     |
| V <sub>DDEHx</sub> <sup>10</sup>                   | I/O supply voltage (medium I/O   | 5 V range                               | 4.5                | —     | 5.5                  | V   |
|  | pads)  | 3.3 V range                             | 3.0                | _     | 3.6                  |     |
| V <sub>DDEH1</sub>                                 | eTPU_A, eSCI_A, eSCI_B, and<br>configuration I/O supply voltage<br>(medium I/O pads) | 5 V range                               | 4.5                | _     | 5.5                  | V   |
| V <sub>DDPMC</sub> <sup>11</sup>                   | Power Management Controller<br>(PMC) supply voltage                                  | Full functionality                      | 3.15               |       | 5.5                  | V   |
| V <sub>DDPWR</sub>                                 | SMPS driver supply voltage   | Reference to V <sub>SSPWR</sub>         | 3.0                | _     | 5.5                  | V   |
| V <sub>DDFLA</sub>                                 | Flash core voltage   | —                                       | 3.15               | _     | 3.6                  | V   |
| V <sub>STBY</sub>                                  | RAM standby supply voltage   | —                                       | 0.95 <sup>12</sup> | _     | 5.5                  | V   |
| V <sub>STBY_BO</sub>                               | Standby RAM brownout flag trip point voltage   | _                                       | -                  | _     | 0.9 <sup>13</sup>    | V   |

Table 3. Device operating conditions

Table continues on the next page ...

| Symbol   | Parameter   | Conditions                   |      | Value               |      | Unit |
|--|---|------------------------------|------|---------------------|------|------|
| Symbol   | Parameter   | Conditions                   | Min  | Тур                 | Max  |      |
| V <sub>RL_SD</sub>                             | SDADC ground reference voltage                          | -                            |      | V <sub>SSA_SD</sub> |      | V    |
| V <sub>DDA_SD</sub>                            | SDADC supply voltage <sup>14</sup>                      | -                            | 4.5  | —                   | 5.5  | V    |
| V <sub>DDA_EQA/B</sub>                         | eQADC supply voltage                                    | -                            | 4.75 | —                   | 5.25 | V    |
| V <sub>RH_SD</sub>                             | SDADC reference   | -                            | 4.5  | V <sub>DDA_SD</sub> | 5.5  | V    |
| $V_{DDA_SD} - V_{RH_SD}$                       | SDADC reference differential voltage                    | -                            | _    | _                   | 25   | mV   |
| $V_{SSA\_SD} - V_{RL\_SD}$                     | V <sub>RL_SD</sub> differential voltage                 | -                            | -25  | —                   | 25   | mV   |
| V <sub>RH_EQ</sub>                             | eQADC reference   | -                            | 4.75 | _                   | 5.25 | V    |
| V <sub>DDA_EQA/B</sub> –<br>V <sub>RH_EQ</sub> | eQADC reference differential voltage                    | -                            | -    | _                   | 25   | mV   |
| $V_{SSA_{EQ}} - V_{RL_{EQ}}$                   | V <sub>RL_EQ</sub> differential voltage                 | -                            | -25  | _                   | 25   | mV   |
| $V_{SSA_{EQ}} - V_{SS}$                        | V <sub>SSA_EQ</sub> differential voltage                | -                            | -25  |                     | 25   | mV   |
| $V_{SSA\_SD} - V_{SS}$                         | V <sub>SSA_SD</sub> differential voltage                | -                            | -25  | —                   | 25   | mV   |
| V <sub>RAMP</sub>                              | Slew rate on power supply pins                          | -                            | —    | _                   | 100  | V/ms |
|  |   | Current                      |      |                     |      |      |
| l <sub>iC</sub>                                | DC injection current (per pin) <sup>15,</sup><br>16, 17 | Digital pins and analog pins | -3.0 | —                   | 3.0  | mA   |
| I <sub>MAXSEG</sub>                            | Maximum current per power segment <sup>18, 19</sup>     | -                            | -80  | —                   | 80   | mA   |

Table 3. Device operating conditions (continued)

- 1. Maximum operating frequency is applicable to the computational cores and platform for the device. See the Clocking chapter in the MPC5775E Microcontroller Reference Manual for more information on the clock limitations for the various IP blocks on the device.
- 2. MPC5775B Max value is 220 MHz.
- 3. MPC5775B Max value is 110 MHz
- 4. The maximum specification for operating junction temperature T<sub>J</sub> must be respected. Thermal characteristics provides details.
- 5. Core voltage as measured on device pin to guarantee published silicon performance
- 6. During power ramp, voltage measured on silicon might be lower. Maximum performance is not guaranteed, but correct silicon operation is guaranteed. See power management and reset management for description.
- 7. Maximum core voltage is not permitted for entire product life. See absolute maximum rating.
- 8. When internal LVD/HVDs are disabled, external monitoring is required to guarantee device operation. Failure to monitor externally supply voltage may result in erroneous operation of the device.
- 9. This LVD/HVD disabled supply voltage condition only applies after LVD/HVD are disabled by the application during the reset sequence, and the LVD/HVD are active until that point.
- 10. This spec does not apply to  $V_{\text{DDEH1}}$ .
- 11. When internal flash memory regulator is used:
  - Flash memory read operation is supported for a minimum  $V_{\text{DDPMC}}$  value of 3.15 V.
  - Flash memory read, program, and erase operations are supported for a minimum V<sub>DDPMC</sub> value of 3.5 V.

When flash memory power is supplied externally ( $V_{DDPMC}$  shorted to  $V_{DDFLA}$ ): The  $V_{DDPMC}$  range must be within the limits specified for LVD\_FLASH and HVD\_FLASH monitoring. Table 26 provides the monitored LVD\_FLASH and HVD\_FLASH limits.

- 12. If the standby RAM regulator is not used, the  $V_{STBY}$  supply input pin must be tied to ground.
- 13. V<sub>STBY\_BO</sub> is the maximum voltage that sets the standby RAM brownout flag in the device logic. The minimum voltage for RAM data retention is guaranteed always to be less than the V<sub>STBY\_BO</sub> maximum value.
- 14. For supply voltages between 3.0 V and 4.0 V there will be no guaranteed precision of ADC (accuracy/linearity). ADC will recover to a fully functional state when the voltage rises above 4.0 V.

- 15. Full device lifetime without performance degradation
- 16. I/O and analog input specifications are only valid if the injection current on adjacent pins is within these limits. See the absolute maximum ratings table for maximum input current for reliability requirements.
- 17. The I/O pins on the device are clamped to the I/O supply rails for ESD protection. When the voltage of the input pin is above the supply rail, current will be injected through the clamp diode to the supply rail. For external RC network calculation, assume a typical 0.3 V drop across the active diode. The diode voltage drop varies with temperature.
- 18. The sum of all controller pins (including both digital and analog) must not exceed 200 mA. A V<sub>DDEx</sub>/V<sub>DDEHx</sub> power segment is defined as one or more GPIO pins located between two V<sub>DDEx</sub>/V<sub>DDEHx</sub> supply pins.
- 19. The average current values given in I/O pad current specifications should be used to calculate total I/O segment current.

## 3.5 DC electrical specifications

### NOTE

 $I_{DDA\_MISC}$  is the sum of current consumption of IRC,  $I_{TRNG}$ , and  $I_{STBY}$  in the 5 V domain. IRC current is provided in the IRC specifications.

### NOTE

I/O, XOSC, EQADC, SDADC, and Temperature Sensor current specifications are in those components' dedicated sections.

| Symbol              | Parameter  | Conditions   | $\begin{array}{c ccccccccccccccccccccccccccccccccccc$ |      | Unit |    |
|---------------------|--|--|---|------|------|----|
| Symbol              | Farameter  | Conditions   | Min   | Тур  | Max  |    |
| I <sub>DD</sub>     | Operating current on the V <sub>DD</sub> core logic supply <sup>1</sup>        | LVD/HVD enabled, $V_{DD} = 1.2 V$ to 1.32 V          | _   | 0.65 | 1.35 | A  |
|                     |  | LVD/HVD disabled, $V_{DD} = 1.2 \text{ V}$ to 1.38 V | _   | 0.65 | 1.4  |    |
| I <sub>DD_PE</sub>  | Operating current on the V <sub>DD</sub> supply for flash memory program/erase | -  | _   | _    | 85   | mA |
| I <sub>DDPMC</sub>  | Operating current on the V <sub>DDPMC</sub> supply <sup>2</sup>                | Flash memory read                                    | _   | —    | 40   | mA |
|                     |  | Flash memory program/erase                           |   | _    | 70   |    |
|                     |  | PMC only   |   | —    | 35   | 1  |
|                     | Operating current on the V <sub>DDPMC</sub> supply                             | Flash memory read                                    |   | —    | 10   | mA |
|                     | (internal core regulator bypassed)   | Flash memory program/erase                           |   | —    | 40   | 1  |
|                     |  | PMC only   | _   | —    | 5    | 1  |
| I <sub>REGCTL</sub> | Core regulator DC current output on V <sub>REGCTL</sub> pin                    | -  | _   | _    | 25   | mA |
| I <sub>STBY</sub>   | Standby RAM supply current   | 1.08 V, T <sub>J</sub> = 150°C                       |   | —    | 1140 | μA |
|                     |  | 1.25 V to 5.5 V, T <sub>J</sub> = 150°C              |   |      | 1170 |    |
|                     |  | 1.25 V to 5.5 V, T <sub>J</sub> = 85°C               |   |      | 360  | 1  |
|                     |  | 1.25 V to 5.5 V, T <sub>J</sub> = 40°C               | _   | —    | 120  | 1  |
| I <sub>DD_PWR</sub> | Operating current on the V <sub>DDPWR</sub> supply                             | -  | —   | —    | 50   | mA |
| I <sub>BG_REF</sub> | Bandgap reference current consumption <sup>3</sup>                             |  |   | —    | 600  | μA |
| I <sub>TRNG</sub>   | True Random Number Generator current   | -  | _   | _    | 2.1  | mA |

#### Table 4. DC electrical specifications

- 1.  $I_{DD}$  measured on an application-specific pattern with all cores enabled at full frequency,  $T_J = 40^{\circ}$ C to 150°C. Flash memory program/erase current on the V<sub>DD</sub> supply not included.
- 2. This value is considering the use of the internal core regulator with the simulation of an external transistor with the minimum value of  $h_{FE}$  of 60.
- 3. This bandgap reference is for EQADC calibration and Temperature Sensors.

# 3.6 I/O pad specifications

The following table describes the different pad types on the chip.

#### Table 5. I/O pad specification descriptions

| Pad type                 | Description   |
|--------------------------|---|
| General-purpose I/O pads | General-purpose I/O with four selectable output slew rate settings; also called SR pads |
| LVDS pads                | Low Voltage Differential Signal interface pads  |
| Input-only pads          | Low-input-leakage pads that are associated with the ADC channels                        |

### NOTE

Each I/O pin on the device supports specific drive configurations. See the signal description table in the device reference manual for the available drive configurations for each I/O pin.

### NOTE

Throughout the I/O pad specifications, the symbol  $V_{DDEx}$  represents all  $V_{DDEx}$  and  $V_{DDEHx}$  segments.

## 3.6.1 Input pad specifications

Table 6 provides input DC electrical characteristics as described in Figure 3.




Figure 3. I/O input DC electrical characteristics definition

| Symbol                | Parameter                            | Conditions   |                          | Value                           |  | Unit |
|-----------------------|--------------------------------------|--|--------------------------|---------------------------------|--|------|
| Symbol                | Parameter                            | Conditions   | Min                      | Тур                             | Max           V <sub>DDEx</sub> + 0.3           V <sub>DDEx</sub> + 0.3           0.35 * V <sub>DDEx</sub> 0.4 * V <sub>DDEx</sub> | Unit |
| V <sub>IHCMOS_H</sub> | Input high level CMOS (with          | 3.0 V < V <sub>DDEx</sub> < 3.6 V and  | 0.65 * V <sub>DDEx</sub> |                                 | V <sub>DDEx</sub> + 0.3  | V    |
|                       | hysteresis)                          | 4.5 V < V <sub>DDEx</sub> < 5.5 V  |                          |                                 |  |      |
| VIHCMOS               | Input high level CMOS (without       | 3.0 V < V <sub>DDEx</sub> < 3.6 V and  | 0.55 * V <sub>DDEx</sub> |                                 | V <sub>DDEx</sub> + 0.3  | V    |
|                       | hysteresis)                          | 4.5 V < V <sub>DDEx</sub> < 5.5 V  |                          |                                 |  |      |
| V <sub>ILCMOS_H</sub> | Input low level CMOS (with           | 3.0 V < V <sub>DDEx</sub> < 3.6 V and  | -0.3                     | -0.3 — 0.35 * V <sub>DDEx</sub> | V  |      |
|                       | hysteresis)                          | 4.5 V < V <sub>DDEx</sub> < 5.5 V  |                          |                                 |  |      |
| VILCMOS               | Input low level CMOS (without        | 3.0 V < V <sub>DDEx</sub> < 3.6 V and  | -0.3                     |                                 | 0.4 * V <sub>DDEx</sub>  | V    |
|                       | hysteresis)                          | 4.5 V < V <sub>DDEx</sub> < 5.5 V  |                          |                                 |  |      |
| V <sub>HYSCMOS</sub>  | Input hysteresis CMOS                | 3.0 V < V <sub>DDEx</sub> < 3.6 V and  | 0.1 * V <sub>DDEx</sub>  | _                               | —  | V    |
|                       |                                      | 4.5 V < V <sub>DDEx</sub> < 5.5 V  |                          |                                 |  |      |
|                       |                                      | Input Characteristics  |                          |                                 |  |      |
| I <sub>LKG</sub>      | Digital input leakage                | $V_{SS} < V_{IN} < V_{DDEx}/V_{DDEHx}$   | —                        | _                               | 2.5  | μA   |
| I <sub>LKGA</sub>     | Analog pin input leakage (5 V range) | $V_{SSA\_SD} < V_{IN} < V_{DDA\_SD},$<br>$V_{SSA\_EQ} < V_{IN} < V_{DDA\_EQA/B}$ | —                        | —                               | 220  | nA   |
| C <sub>IN</sub>       | Digital input capacitance            | GPIO input pins  | —                        |                                 | 7  | pF   |

| Table 6. | I/O input DC electrical characteristics |
|----------|---|
|----------|---|

Table 7 provides current specifications for weak pullup and pulldown.

| Symbol           | Parameter             | Conditions                                 | Value |     |     | Unit |
|------------------|-----------------------|--|-------|-----|-----|------|
| Symbol           | Farameter             | Conditions                                 |       | Тур | Max |      |
| I <sub>WPU</sub> | Weak pullup current   | V <sub>IN</sub> = 0.35 * V <sub>DDEx</sub> | 40    | —   | 120 | μA   |
|                  |                       | 4.5 V < V <sub>DDEx</sub> < 5.5 V          |       |     |     |      |
|                  |                       | V <sub>IN</sub> = 0.35 * V <sub>DDEx</sub> | 25    | —   | 80  | 1    |
|                  |                       | 3.0 V < V <sub>DDEx</sub> < 3.6 V          |       |     |     |      |
| I <sub>WPD</sub> | Weak pulldown current | V <sub>IN</sub> = 0.65 * V <sub>DDEx</sub> | 40    | —   | 120 | μA   |
|                  |                       | 4.5 V < V <sub>DDEx</sub> < 5.5 V          |       |     |     |      |
|                  |                       | V <sub>IN</sub> = 0.65 * V <sub>DDEx</sub> | 25    | —   | 80  |      |
|                  |                       | 3.0 V < V <sub>DDEx</sub> < 3.6 V          |       |     |     |      |

#### Table 7. I/O pullup/pulldown DC electrical characteristics

The specifications in Table 8 apply to the pins ANA0\_SDA0 to ANA7, ANA16\_SDB0 to ANA23\_SDC3, and ANB0\_SDD0 to ANB7\_SDD7.

 Table 8.
 I/O pullup/pulldown resistance electrical characteristics

| Symbol            | Parameter   | Conditions |     | Unit |     |      |
|-------------------|---|------------|-----|------|-----|------|
| Symbol            |   |            | Min | Тур  | Мах | Unit |
| R <sub>PUPD</sub> |   | 200 kΩ     | 130 | 200  | 280 | kΩ   |
|                   | pulldown resistance                                   | 100 kΩ     | 65  | 100  | 140 |      |
|                   |   | 5 kΩ       | 1.4 | 5    | 7.5 |      |
| $\Delta_{PUPD}$   | R <sub>PUPD</sub> pullup/pulldown resistance mismatch | —          |     |      | 5   | %    |

# 3.6.2 Output pad specifications

Figure 4 shows output DC electrical characteristics.

**Electrical characteristics** 




Figure 4. I/O output DC electrical characteristics definition

The following tables specify output DC electrical characteristics.

| Table 9. | GPIO data pac | l output buffer electrica | I characteristics (SR pads) <sup>1</sup> |
|----------|---------------|---------------------------|--|
|----------|---------------|---------------------------|--|

| Symbol          | Parameter            | Conditions <sup>2</sup>                   |                       |      | Unit |     |    |
|-----------------|----------------------|---|-----------------------|------|------|-----|----|
| Symbol          | Parameter            | Conditions                                |                       | Min  | Тур  | Max |    |
| I <sub>ОН</sub> | GPIO pad output high | V <sub>OH</sub> = 0.8 * V <sub>DDEx</sub> | PCR[SRC] = 11b or 01b | 25   | —    | —   | mA |
|                 | current              | 4.5 V < V <sub>DDEx</sub> < 5.5 V         | PCR[SRC] = 10b or 00b | 15   | —    |     |    |
|                 |                      | $V_{OH} = 0.8 * V_{DDEx}$                 | PCR[SRC] = 11b or 01b | 13   | —    | —   |    |
|                 |                      | 3.0 V < V <sub>DDEx</sub> < 3.6 V         | PCR[SRC] = 10b or 00b | 8    | —    |     |    |
| I <sub>OL</sub> | GPIO pad output low  | $V_{OL} = 0.2 * V_{DDEx}$                 | PCR[SRC] = 11b or 01b | 48   | —    |     | mA |
|                 | current              | 4.5 V < V <sub>DDEx</sub> < 5.5 V         | PCR[SRC] = 10b or 00b | 22   | —    | _   |    |
|                 |                      | $V_{OL} = 0.2 * V_{DDEx}$                 | PCR[SRC] = 11b or 01b | 17   | —    | _   |    |
|                 |                      | 3.0 V < V <sub>DDEx</sub> < 3.6 V         | PCR[SRC] = 10b or 00b | 10.5 | —    | _   |    |

Table continues on the next page ...

| Table 9. | . GPIO data pad output buffer electrical characteristics (SR p | ads) <sup>1</sup> (continued) |
|----------|--|-------------------------------|
|----------|--|-------------------------------|

|                  |                                       |                                   |                         |     | Value <sup>3</sup> |      |     |
|------------------|---------------------------------------|-----------------------------------|-------------------------|-----|--------------------|------|-----|
| Symbol           | Parameter                             | Conditions <sup>2</sup>           |                         | Min | Тур                | Max  | Uni |
| t <sub>R_F</sub> | GPIO pad output                       | PCR[SRC] = 11b                    | C <sub>L</sub> = 25 pF  |     |                    | 1.2  | ns  |
|                  | transition time (rise/fall)           | 4.5 V < V <sub>DDEx</sub> < 5.5 V | $C_{L} = 50  \text{pF}$ |     |                    | 2.5  | 1   |
|                  |                                       | <b>DDE</b>                        | C <sub>L</sub> = 200 pF |     |                    | 8    | 1   |
|                  |                                       | PCR[SRC] = 11b                    | C <sub>L</sub> = 25 pF  |     | _                  | 1.7  |     |
|                  |                                       | 3.0 V < V <sub>DDEx</sub> < 3.6 V | C <sub>L</sub> = 50 pF  |     |                    | 3.25 | 1   |
|                  |                                       |                                   | C <sub>L</sub> = 200 pF |     |                    | 12   | 1   |
|                  |                                       | PCR[SRC] = 10b                    | C <sub>L</sub> = 50 pF  |     | _                  | 5    | 1   |
|                  |                                       | 4.5 V < V <sub>DDEx</sub> < 5.5 V | C <sub>L</sub> = 200 pF | _   | _                  | 18   | 1   |
|                  |                                       | PCR[SRC] = 10b                    | C <sub>L</sub> = 50 pF  | _   |                    | 7    | 1   |
|                  |                                       | 3.0 V < V <sub>DDEx</sub> < 3.6 V | C <sub>L</sub> = 200 pF |     |                    | 25   | 1   |
|                  |                                       | PCR[SRC] = 01b                    | C <sub>L</sub> = 50 pF  |     | _                  | 13   |     |
|                  |                                       | 4.5 V < V <sub>DDEx</sub> < 5.5 V | C <sub>L</sub> = 200 pF |     |                    | 24   | 1   |
|                  |                                       |                                   | C <sub>L</sub> = 50 pF  |     | _                  | 25   | -   |
|                  |                                       | 3.0 V < V <sub>DDEx</sub> < 3.6 V | C <sub>L</sub> = 200 pF |     |                    | 30   | -   |
|                  |                                       |                                   | C <sub>L</sub> = 50 pF  |     | _                  | 24   | 1   |
|                  |                                       | 4.5 V < V <sub>DDEx</sub> < 5.5 V | C <sub>L</sub> = 200 pF |     |                    | 50   | -   |
|                  |                                       |                                   | C <sub>L</sub> = 50 pF  |     | _                  | 40   | 1   |
|                  |                                       | 3.0 V < V <sub>DDEx</sub> < 3.6 V | C <sub>L</sub> = 200 pF |     |                    | 51   | -   |
| t <sub>PD</sub>  | GPIO pad output                       |                                   | C <sub>L</sub> = 50 pF  |     | _                  | 6    | ns  |
|                  | propagation delay time                | 4.5 V < V <sub>DDEx</sub> < 5.5 V | C <sub>L</sub> = 200 pF |     | _                  | 13   | -   |
|                  |                                       | PCR[SRC] = 11b                    | C <sub>L</sub> = 50 pF  |     | _                  | 8.25 |     |
|                  |                                       | 3.0 V < V <sub>DDEx</sub> < 3.6 V | C <sub>L</sub> = 200 pF |     | _                  | 19.5 | -   |
|                  |                                       | PCR[SRC] = 10b                    | C <sub>L</sub> = 50 pF  |     |                    | 9    | 1   |
|                  |                                       | 4.5 V < V <sub>DDEx</sub> < 5.5 V | C <sub>L</sub> = 200 pF |     | _                  | 22   |     |
|                  |                                       |                                   | C <sub>L</sub> = 50 pF  |     |                    | 12.5 | 1   |
|                  |                                       | 3.0 V < V <sub>DDEx</sub> < 3.6 V | C <sub>L</sub> = 200 pF |     | _                  | 35   |     |
|                  |                                       | PCR[SRC] = 01b                    | C <sub>L</sub> = 50 pF  |     |                    | 27   | 1   |
|                  |                                       | 4.5 V < V <sub>DDEx</sub> < 5.5 V | C <sub>L</sub> = 200 pF |     |                    | 40   | 1   |
|                  |                                       |                                   | C <sub>L</sub> = 50 pF  |     |                    | 45   | 1   |
|                  |                                       | 3.0 V < V <sub>DDEx</sub> < 3.6 V |                         |     |                    | 65   | 1   |
|                  |                                       |                                   | C <sub>L</sub> = 50 pF  |     |                    | 40   | 1   |
|                  |                                       | 4.5 V < V <sub>DDEx</sub> < 5.5 V |                         |     |                    | 65   | 1   |
|                  |                                       |                                   | C <sub>L</sub> = 50 pF  |     |                    | 75   | 1   |
|                  |                                       | 3.0 V < V <sub>DDEx</sub> < 3.6 V |                         |     |                    | 100  | 1   |
| skew_wl          | Difference between rise and fall time |                                   |                         |     |                    | 25   | %   |

1. All GPIO pad output specifications are valid for  $3.0 \text{ V} < \text{V}_{\text{DDEx}} < 5.5 \text{ V}$ , except where explicitly stated. 2. PCR[SRC] values refer to the setting of that register field in the SIU.

- 3. All values to be confirmed during device validation.

The following table shows the, address, and control signal pad electrical characteristics. These pads can also be used for GPIO.

## 3.6.3 I/O pad current specifications

The I/O pads are distributed across the I/O supply segments. Each I/O supply segment is associated with a  $V_{DDEx}$  supply segment.

 Table 10 provides I/O consumption figures.

To ensure device reliability, the average current of the I/O on a single segment should remain below the  $I_{MAXSEG}$  value given in Table 1.

To ensure device functionality, the average current of the I/O on a single segment should remain below the  $I_{MAXSEG}$  value given in Table 3.

### NOTE

The MPC5775E I/O Signal Description and Input Multiplexing Tables are contained in a Microsoft Excel® file attached to the Reference Manual. In the spreadsheet, select the I/O Signal Table tab.

 Table 10.
 I/O consumption

| Symbol                | Parameter                         | Conditions                    |     | Value |      | Unit |
|-----------------------|-----------------------------------|-------------------------------|-----|-------|------|------|
| Symbol                | Farameter                         | Conditions                    | Min | Тур   | Max  |      |
| I <sub>AVG_GPIO</sub> | Average I/O current for GPIO pads | C <sub>L</sub> = 25 pF, 2 MHz | —   | —     | 0.42 | mA   |
|                       | (per pad)                         | $V_{DDEx} = 5.0 V \pm 10\%$   |     |       |      |      |
|                       |                                   | C <sub>L</sub> = 50 pF, 1 MHz | —   | _     | 0.35 |      |
|                       |                                   | $V_{DDEx} = 5.0 V \pm 10\%$   |     |       |      |      |

# 3.7 Oscillator and PLL electrical specifications

The on-chip dual PLL—consisting of the peripheral clock and reference PLL (PLL0) and the frequency-modulated system PLL (PLL1)—generates the system and auxiliary clocks from the main oscillator driver.




Figure 5. PLL integration

# 3.7.1 PLL electrical specifications

### Table 11. PLL0 electrical characteristics

| Symbol                   | Parameter                                 | Conditions   | Value |     |                  | Unit |
|--------------------------|---|--|-------|-----|------------------|------|
| Symbol                   | Farameter                                 | Conditions   | Min   | Тур | Max              |      |
| f <sub>PLLOIN</sub>      | PLL0 input clock <sup>1, 2</sup>          | —  | 8     |     | 44               | MHz  |
| Δ <sub>PLL0IN</sub>      | PLL0 input clock duty cycle <sup>2</sup>  | —  | 40    | _   | 60               | %    |
| f <sub>PLL0VCO</sub>     | PLL0 VCO frequency                        | —  | 600   | _   | 1250             | MHz  |
| f <sub>PLL0PHI</sub>     | PLL0 output frequency                     | —  | 4.762 | _   | 200              | MHz  |
| t <sub>PLL0LOCK</sub>    | PLL0 lock time                            | —  | -     | _   | 110              | μs   |
| Δ <sub>PLL0PHISPJ</sub>  | PLL0_PHI single period jitter             | f <sub>PLL0PHI</sub> = 200 MHz, 6-sigma                                    | _     |     | 200              | ps   |
|                          | f <sub>PLL0IN</sub> = 20 MHz (resonator)  |  |       |     |                  |      |
| Δ <sub>PLL0PHI1SPJ</sub> | PLL0_PHI1 single period jitter            | f <sub>PLL0PHI1</sub> = 40 MHz, 6-sigma                                    |       | _   | 300 <sup>3</sup> | ps   |
|                          | f <sub>PLL0IN</sub> = 20 MHz (resonator)  |  |       |     |                  |      |
| Δ <sub>PLL0LTJ</sub>     | PLL0 output long term jitter <sup>3</sup> | 10 periods accumulated jitter (80 MHz                                      |       | _   | ±250             | ps   |
|                          | f <sub>PLLOIN</sub> = 20 MHz (resonator), | equivalent frequency), 6-sigma pk-pk                                       |       |     |                  |      |
|                          | VCO frequency = 800 MHz                   | 16 periods accumulated jitter (50 MHz equivalent frequency), 6-sigma pk-pk | —     | _   | ±300             | ps   |
|                          |   | long term jitter (< 1 MHz equivalent frequency), 6-sigma pk-pk)            | _     | _   | ±500             | ps   |
| I <sub>PLL0</sub>        | PLL0 consumption                          | FINE LOCK state  | _     | —   | 7.5              | mA   |

- 1. Ensure that the f<sub>PLL0IN</sub> frequency divided by PLLDIG\_PLL0DV[PREDIV] is in the range 8 MHz to 20 MHz.
- 2. PLLOIN clock retrieved directly from either internal IRC or external XOSC clock. Input characteristics are granted when using internal IRC or external oscillator is used in functional mode.
- 3. Noise on the V<sub>DD</sub> supply with frequency content below 40 kHz and above 50 MHz is filtered by the PLL. Noise on the V<sub>DD</sub> supply with frequency content in the range of 40 kHz 50 MHz must be filtered externally to the device.

| Table 12. | PLL1 | electrical | characteristics |
|-----------|------|------------|-----------------|
|-----------|------|------------|-----------------|

| ſ | Symbol              | Parameter                     | Conditions | Value |     | Unit |      |
|---|---------------------|-------------------------------|------------|-------|-----|------|------|
|   | Symbol              | Falanielei                    | Conditions | Min   | Тур | Max  | Unit |
|   | f <sub>PLL1IN</sub> | PLL1 input clock <sup>1</sup> | —          | 38    | _   | 78   | MHz  |

Table continues on the next page ...

| Symphol                 | Parameter                                      | Conditions                                  | Value |     | Unit             |     |
|-------------------------|--|---|-------|-----|------------------|-----|
| Symbol                  | Farameter                                      | Conditions                                  | Min   | Тур | Max              |     |
| $\Delta_{PLL1IN}$       | PLL1 input clock duty cycle <sup>1</sup>       | —   | 35    | —   | 65               | %   |
| f <sub>PLL1VCO</sub>    | PLL1 VCO frequency                             | —   | 600   | —   | 1250             | MHz |
| f <sub>PLL1PHI</sub>    | PLL1 output clock PHI                          | —   | 4.762 | —   | 264 <sup>2</sup> | MHz |
| t <sub>PLL1LOCK</sub>   | PLL1 lock time                                 | —   | _     | —   | 100              | μs  |
| $ \Delta_{PLL1PHISPJ} $ | PLL1_PHI single period peak-to-<br>peak jitter | f <sub>PLL1PHI</sub> = 200 MHz, 6-<br>sigma | _     |     | 500 <sup>3</sup> | ps  |
| f <sub>PLL1MOD</sub>    | PLL1 modulation frequency                      | —   | _     | —   | 250              | kHz |
| δ <sub>PLL1MOD</sub>    | PLL1 modulation depth (when                    | Center spread                               | 0.25  | —   | 2                | %   |
|                         | enabled)                                       | Down spread                                 | 0.5   | —   | 4                | %   |
| I <sub>PLL1</sub>       | PLL1 consumption                               | FINE LOCK state                             | —     | —   | 6                | mA  |

Table 12. PLL1 electrical characteristics (continued)

1. PLL1IN clock retrieved directly from either internal PLL0 or external XOSC clock. Input characteristics are granted when using internal PLL0 or external oscillator in functional mode.

2. MPC5775B Max value is 220MHz.

3. Noise on the V<sub>DD</sub> supply with frequency content below 40 kHz and above 50 MHz is filtered by the PLL. Noise on the V<sub>DD</sub> supply with frequency content in the range of 40 kHz – 50 MHz must be filtered externally to the device.

# 3.7.2 Oscillator electrical specifications

### NOTE

All oscillator specifications in Table 13 are valid for  $V_{DDEH6} = 3.0 \text{ V}$  to 5.5 V.

Table 13. External oscillator (XOSC) electrical specifications

| Sumbol             | Parameter   | Conditions                                   | Va                     | 11                     |      |
|--------------------|---|--|------------------------|------------------------|------|
| Symbol             | Parameter   | Conditions                                   | Min                    | Max                    | Unit |
| f <sub>XTAL</sub>  | Crystal frequency range   | —  | 8                      | 40                     | MHz  |
| t <sub>cst</sub>   | Crystal start-up time <sup>1, 2</sup>                             | T <sub>J</sub> = 150 °C                      | —                      | 5                      | ms   |
| t <sub>rec</sub>   | Crystal recovery time <sup>3</sup>                                | —  | —                      | 0.5                    | ms   |
| V <sub>IHEXT</sub> | EXTAL input high voltage (external reference)                     | V <sub>REF</sub> = 0.28 * V <sub>DDEH6</sub> | V <sub>REF</sub> + 0.6 | _                      | V    |
| V <sub>ILEXT</sub> | EXTAL input low voltage (external reference)                      | V <sub>REF</sub> = 0.28 * V <sub>DDEH6</sub> | —                      | V <sub>REF</sub> – 0.6 | V    |
| $C_{S\_EXTAL}$     | Total on-chip stray capacitance on EXTAL pin <sup>4</sup>         | 416-ball MAPBGA                              | 2.3                    | 3.0                    | pF   |
| $C_{S_XTAL}$       | Total on-chip stray capacitance on XTAL pin <sup>4</sup>          | 416-ball MAPBGA                              | 2.3                    | 3.0                    | pF   |
| 9 <sub>m</sub>     | Oscillator transconductance <sup>5</sup>                          | Low  | 3                      | 10                     | mA/V |
|                    |   | Medium                                       | 10                     | 27                     |      |
|                    |   | High   | 12                     | 35                     | -    |
| V <sub>EXTAL</sub> | Oscillation amplitude on the EXTAL pin after startup <sup>6</sup> | —  | 0.5                    | 1.6                    | V    |
| V <sub>HYS</sub>   | Comparator hysteresis   | —  | 0.1                    | 1.0                    | V    |
| I <sub>XTAL</sub>  | XTAL current <sup>6, 7</sup>                                      | —  | -                      | 14                     | mA   |

- 1. This value is determined by the crystal manufacturer and board design.
- 2. Proper PC board layout procedures must be followed to achieve specifications.
- 3. Crystal recovery time is the time for the oscillator to settle to the correct frequency after adjustment of the integrated load capacitor value.
- 4. See crystal manufacturer's specification for recommended load capacitor (C<sub>L</sub>) values. The external oscillator requires external load capacitors when operating in a "low" transconductance range. Account for on-chip stray capacitance (C<sub>S\_EXTAL</sub>/C<sub>S\_XTAL</sub>) and PCB capacitance when selecting a load capacitor value. When operating in a "medium" or "high" transconductance range, the integrated load capacitor value is selected via software to match the crystal manufacturer's specification, while accounting for on-chip and PCB capacitance.
- 5. Select a "low," "medium," or "high" setting using the UTEST Miscellaneous DCF client's XOSC\_LF\_EN and XOSC\_EN\_HIGH fields. "Low" is the setting commonly used for crystals at 8 MHz, "medium" is commonly used for crystals greater than 8 MHz to 20 MHz, and "high" is commonly used for crystals greater than 20 MHz to 40 MHz. However, the user must characterize carefully to determine the best g<sub>m</sub> setting for the intended application because crystal load capacitance, board layout, and other factors affect the g<sub>m</sub> value that is needed. The user may need an additional Rshunt to optimize g<sub>m</sub> depending on the system environment. Use of overtone crystals is not recommended.
- 6. Amplitude on the EXTAL pin after startup is determined by the ALC block (that is, the Automatic Level Control Circuit). The function of the ALC is to provide high drive current during oscillator startup, while reducing current after oscillation to reduce power, distortion, and RFI, and to avoid over-driving the crystal. The operating point of the ALC is dependent on the crystal value and loading conditions.
- I<sub>XTAL</sub> is the oscillator bias current out of the XTAL pin with both EXTAL and XTAL pins grounded. This is the maximum current during startup of the oscillator. The current after oscillation is typically in the 2–3 mA range and is dependent on the load and series resistance of the crystal. Test circuit is shown in Figure 6.

| load_cap_sel[4:0] from DCF record | Load capacitance <sup>1, 2</sup> (pF) |
|-----------------------------------|---------------------------------------|
| 00000                             | 1.8                                   |
| 00001                             | 2.8                                   |
| 00010                             | 3.7                                   |
| 00011                             | 4.6                                   |
| 00100                             | 5.6                                   |
| 00101                             | 6.5                                   |
| 00110                             | 7.4                                   |
| 00111                             | 8.4                                   |
| 01000                             | 9.3                                   |
| 01001                             | 10.2                                  |
| 01010                             | 11.2                                  |
| 01011                             | 12.1                                  |
| 01100                             | 13.0                                  |
| 01101                             | 13.9                                  |
| 01110                             | 14.9                                  |
| 01111                             | 15.8                                  |

### Table 14. Selectable load capacitance

- 1. Values are determined from simulation across process corners and voltage and temperature variation. Capacitance values vary ±12% across process, 0.25% across voltage, and no variation across temperature.
- 2. Values in this table do not include the die and package capacitances given by  $C_{S_XTAL}/C_{S_EXTAL}$  in Table 13.




Figure 6. Test circuit

| Table 15. | Internal RC (IRC) | ) oscillator electrical | specifications |
|-----------|-------------------|-------------------------|----------------|
|-----------|-------------------|-------------------------|----------------|

| Symbol              | Parameter               | Conditions | Value |     |     | Unit |
|---------------------|-------------------------|------------|-------|-----|-----|------|
| Symbol              | Falanetei               | Conditions | Min   | Тур | Max | Onit |
| f <sub>Target</sub> | IRC target frequency    | _          | _     | 16  |     | MHz  |
| δf <sub>var_T</sub> | IRC frequency variation | T < 150 °C | -8    | _   | 8   | %    |

# 3.8 Analog-to-Digital Converter (ADC) electrical specifications

### 3.8.1 Enhanced Queued Analog-to-Digital Converter (eQADC) Table 16. eQADC conversion specifications (operating)

| Symbol             | Parameter                              | Va     | Unit                  |                  |
|--------------------|--|--------|-----------------------|------------------|
| Symbol             |  | Min    | Мах                   | Onit             |
| f <sub>ADCLK</sub> | ADC Clock (ADCLK) Frequency            | 2      | 33                    | MHz              |
| CC                 | Conversion Cycles                      | 2 + 13 | 128 + 15 <sup>1</sup> | ADCLK cycles     |
| T <sub>SR</sub>    | Stop Mode Recovery Time <sup>2</sup>   | 10     | _                     | μs               |
| —                  | Resolution <sup>3</sup>                | 1.25   | _                     | mV               |
| INL                | INL: 16.5 MHz eQADC clock <sup>4</sup> | -4     | 4                     | LSB <sup>5</sup> |
|                    | INL: 33 MHz eQADC clock <sup>4</sup>   | -6     | 6                     | LSB              |

Table continues on the next page...

| Symbol           | Devemeter  | Va               | Value           |                      |  |
|------------------|--|------------------|-----------------|----------------------|--|
| Symbol           | Parameter  | Min              | Max             | - Unit               |  |
| DNL              | DNL: 16.5 MHz eQADC clock <sup>4</sup>                       | -3               | 3               | LSB                  |  |
|                  | DNL: 33 MHz eQADC clock <sup>4</sup>                         | -3               | 3               | LSB                  |  |
| OFFNC            | Offset Error without Calibration                             | 0                | 140             | LSB                  |  |
| OFFWC            | Offset Error with Calibration                                | -8               | 8               | LSB                  |  |
| GAINNC           | Full Scale Gain Error without Calibration                    | -150             | 0               | LSB                  |  |
| GAINWC           | Full Scale Gain Error with Calibration                       | -8               | 8               | LSB                  |  |
| I <sub>INJ</sub> | Disruptive Input Injection Current <sup>6, 7, 8, 9</sup>     | -3               | 3               | mA                   |  |
| E <sub>INJ</sub> | Incremental Error due to injection current <sup>10, 11</sup> | _                | +4              | Counts               |  |
| TUE              | TUE value <sup>12, 13</sup> (with calibration)               | _                | ±8              | Counts               |  |
| GAINVGA1         | Variable gain amplifier accuracy (gain = 1) <sup>14</sup>    | -                | -               | Counts <sup>16</sup> |  |
|                  | INL, 16.5 MHz ADC  | -4               | 4               |                      |  |
|                  | INL, 33 MHz ADC  | -8               | 8               |                      |  |
|                  | DNL, 16.5 MHz ADC  | -3 <sup>15</sup> | 3 <sup>15</sup> |                      |  |
|                  | DNL, 33 MHz ADC  | -3 <sup>15</sup> | 3 <sup>15</sup> |                      |  |
| GAINVGA2         | Variable gain amplifier accuracy (gain = 2) <sup>14</sup>    | -                | -               | Counts               |  |
|                  | INL, 16.5 MHz ADC  | -5               | 5               |                      |  |
|                  | INL, 33 MHz ADC  | 8                | 8               |                      |  |
|                  | DNL, 16.5 MHz ADC  | -3               | 3               |                      |  |
|                  | DNL, 33 MHz ADC  | -3               | 3               |                      |  |
| GAINVGA4         | Variable gain amplifier accuracy (gain = 4) <sup>14</sup>    | -                | -               | Counts               |  |
|                  | INL, 16.5 MHz ADC  | -7               | 7               |                      |  |
|                  | INL, 33 MHz ADC  | -8               | 8               |                      |  |
|                  | DNL, 16.5 MHz ADC  | -4               | 4               |                      |  |
|                  | DNL, 33 MHz ADC  | -4               | 4               |                      |  |
| I <sub>ADC</sub> | Current consumption per ADC (two ADCs per EQADC)             |                  | 10              | mA                   |  |
| I <sub>ADR</sub> | Reference voltage current consumption per EQADC              | _                | 200             | μA                   |  |

Table 16. eQADC conversion specifications (operating) (continued)

1. 128 sampling cycles (LST=128), differential conversion, pregain of x4

- Stop mode recovery time is the time from the setting of either of the enable bits in the ADC Control Register to the time that the ADC is ready to perform conversions. Delay from power up to full accuracy = 8 ms.
- At V<sub>RH\_EQ</sub> V<sub>RL\_EQ</sub> = 5.12 V, one count = 1.25 mV without using pregain. Based on 12-bit conversion result; does not account for AC and DC errors
- 4. INL and DNL are tested from V<sub>RL</sub> + 50 LSB to V<sub>RH</sub> 50 LSB.
- 5. At  $V_{RH_{EQ}} V_{RL_{EQ}} = 5.12$  V, one LSB = 1.25 mV.
- Below disruptive current conditions, the channel being stressed has conversion values of \$3FF for analog inputs greater than V<sub>RH</sub> and \$000 for values less than V<sub>RL</sub>. Other channels are not affected by non-disruptive conditions.
- 7. Exceeding limit may cause conversion error on stressed channels and on unstressed channels. Transitions within the limit do not affect device reliability or cause permanent damage.
- Input must be current limited to the value specified. To determine the value of the required current-limiting resistor, calculate resistance values using V<sub>POSCLAMP</sub> = V<sub>DDA</sub> + 0.5 V and V<sub>NEGCLAMP</sub> = -0.3 V, then use the larger of the calculated values.
- 9. Condition applies to two adjacent pins at injection limits.
- 10. Performance expected with production silicon.

- 11. All channels have same 10 k $\Omega$  < Rs < 100 k $\Omega$  Channel under test has Rs = 10 k $\Omega$ ,  $I_{INJ}=I_{INJMAX}$ ,  $I_{INJMIN}$ .
- 12. The TUE specification is always less than the sum of the INL, DNL, offset, and gain errors due to cancelling errors.
- 13. TUE, Gain, and Offset specifications do not apply to differential conversions.
- Variable gain is controlled by setting the PRE\_GAIN bits in the ADC\_ACR1-8 registers to select a gain factor of ×1, ×2, or ×4. Settings are for differential input only. Tested at ×1 gain. Values for other settings are guaranteed as indicated.
- 15. Guaranteed 10-bit monotonicity.
- 16. At  $V_{RH_{EQ}} V_{RL_{EQ}} = 5.12$  V, one LSB = 1.25 mV.

# 3.8.2 Sigma-Delta ADC (SDADC)

The SDADC is a 16-bit Sigma-Delta analog-to-digital converter with a 333 Ksps maximum output conversion rate.

### NOTE

The voltage range is 4.5 V to 5.5 V for SDADC specifications, except where noted otherwise.

| Symbol                  | Parameter                                  | Conditions   |                           | Value                 | e                   | Unit |
|-------------------------|--|--|---------------------------|-----------------------|---------------------|------|
| Symbol                  | Parameter                                  | Conditions   | Min                       | Тур                   | Мах                 |      |
| V <sub>IN</sub>         | ADC input signal                           |  | 0                         | —                     | V <sub>DDA_SD</sub> | V    |
| V <sub>IN_PK2PK</sub> 1 | Input range peak to<br>peak                | Single ended<br>V <sub>INM</sub> = V <sub>RL SD</sub>                                  |                           | V <sub>RH_SD</sub> /G | AIN                 | V    |
|                         | $V_{IN_{PK2PK}} = V_{INP}^2 - V_{INM}^{3}$ | Single ended   |                           | H_SD                  |                     |      |
|                         |  | V <sub>INM</sub> = 0.5*V <sub>RH_SD</sub><br>GAIN = 1                                  |                           |                       |                     |      |
|                         |  | Single ended   | ±V <sub>RH_SD</sub> /GAIN |                       |                     |      |
|                         |  | $V_{INM} = 0.5^* V_{RH\_SD}$   |                           |                       |                     |      |
|                         |  | GAIN = 2,4,8,16  |                           |                       |                     |      |
|                         |  | Differential   | ±V <sub>RH_SD</sub> /GAIN |                       |                     |      |
|                         |  | 0 < V <sub>IN</sub> < V <sub>DDEx</sub>  |                           |                       |                     |      |
| f <sub>ADCD_M</sub>     | SD clock frequency <sup>4</sup>            | —  | 4                         | 14.4                  | 16                  | MHz  |
| f <sub>ADCD_S</sub>     | Conversion rate                            | —  |                           | _                     | 333                 | Ksps |
| —                       | Oversampling ratio                         | Internal modulator   | 24                        | _                     | 256                 | —    |
| RESOLUTION              | SD register resolution <sup>5</sup>        | 2's complement notation  |                           | 16                    |                     | bit  |
| GAIN                    | ADC gain                                   | Defined through<br>SDADC_MCR[PGAN]. Only integer<br>powers of 2 are valid gain values. | 1                         | _                     | 16                  | _    |

### Table 17. SDADC electrical specifications

| Symbol                | Parameter  | Conditions  |     | Value             |     | Un |
|-----------------------|--|---|-----|-------------------|-----|----|
| Symbol                |  | Conditions  | Min | Тур               | Max |    |
| δ <sub>GAIN</sub>     | Absolute value of the ADC gain error <sup>6, 7</sup> | Before calibration (applies to gain setting = 1)                  | —   | —                 | 1.5 | %  |
|                       |  | After calibration   | —   | _                 | 5   | m∖ |
|                       |  | $\Delta V_{RH_{SD}} < 5\%$ , $\Delta V_{DDA_{SD}} < 10\%$         |     |                   |     |    |
|                       |  | ΔT <sub>J</sub> < 50 °C   |     |                   |     |    |
|                       |  | After calibration   | —   | _                 | 7.5 |    |
|                       |  | $\Delta V_{RH_{SD}} < 5\%$ , $\Delta V_{DDA_{SD}} < 10\%$         |     |                   |     |    |
|                       |  | ΔT <sub>J</sub> < 100 °C  |     |                   |     |    |
|                       |  | After calibration   | _   | _                 | 10  |    |
|                       |  | $\Delta V_{RH\_SD} < 5\%$ , $\Delta V_{DDA\_SD} < 10\%$           |     |                   |     |    |
|                       |  | ΔT <sub>J</sub> < 150 °C  |     |                   |     |    |
| V <sub>OFFSET</sub>   | Conversion offset <sup>6, 7</sup>                    | Before calibration (applies to all gain settings: 1, 2, 4, 8, 16) | —   | 10*(1+1/<br>gain) | 20  | m  |
|                       |  | After calibration   | _   | _                 | 5   |    |
|                       |  | $\Delta V_{\text{DDA}SD} < 10\%$                                  |     |                   |     |    |
|                       |  | ΔT <sub>J</sub> < 50 °C   |     |                   |     |    |
|                       |  | After calibration   | _   | _                 | 7.5 |    |
|                       |  | $\Delta V_{\text{DDA}SD} < 10\%$                                  |     |                   |     |    |
|                       |  | ΔT <sub>J</sub> < 100 °C  |     |                   |     |    |
|                       |  | After calibration   | —   | _                 | 10  |    |
|                       |  | $\Delta V_{\text{DDA}SD} < 10\%$                                  |     |                   |     |    |
|                       |  | ΔT <sub>J</sub> < 150 °C  |     |                   |     |    |
| NR <sub>DIFF150</sub> | Signal to noise ratio in                             | $4.5 \text{ V} < \text{V}_{\text{DDA}SD} < 5.5 \text{ V}^{8, 9}$  | 80  | _                 | _   | d  |
|                       | differential mode, 150<br>Ksps output rate           | $V_{RH\_SD} = V_{DDA\_SD}$  |     |                   |     |    |
|                       |  | GAIN = 1  |     |                   |     |    |
|                       |  | $4.5 \text{ V} < \text{V}_{\text{DDA}SD} < 5.5 \text{ V}^{8, 9}$  | 77  | _                 | _   |    |
|                       |  | $V_{RH\_SD} = V_{DDA\_SD}$  |     |                   |     |    |
|                       |  | GAIN = 2  |     |                   |     |    |
|                       |  | $4.5 \text{ V} < \text{V}_{\text{DDA}SD} < 5.5 \text{ V}^{8, 9}$  | 74  | _                 | _   |    |
|                       |  | $V_{RH\_SD} = V_{DDA\_SD}$  |     |                   |     |    |
|                       |  | GAIN = 4  |     |                   |     |    |
|                       |  | $4.5 \text{ V} < \text{V}_{\text{DDA}SD} < 5.5 \text{ V}^{8, 9}$  | 71  | _                 |     |    |
|                       |  | $V_{RH\_SD} = V_{DDA\_SD}$  |     |                   |     |    |
|                       |  | GAIN = 8  |     |                   |     |    |
|                       |  | 4.5 V < V <sub>DDA_SD</sub> < 5.5 V <sup>8, 9</sup>               | 68  | _                 | _   |    |
|                       |  | $V_{RH\_SD} = V_{DDA\_SD}$  |     |                   |     |    |
|                       |  | GAIN = 16   |     |                   |     |    |

## Table 17. SDADC electrical specifications (continued)

| Cumbal                 | Parameter                                  | Conditions   |     | Value |     | — Unit |
|------------------------|--|--|-----|-------|-----|--------|
| Symbol                 |  | Conditions   | Min | Тур   | Max |        |
| SNR <sub>DIFF333</sub> | Signal to noise ratio in                   | 4.5 V < V <sub>DDA_SD</sub> < 5.5 V <sup>8, 9</sup>              | 71  | _     | _   | dB     |
|                        | differential mode, 333<br>Ksps output rate | $V_{RH_SD} = V_{DDA_SD}$   |     |       |     |        |
|                        |  | GAIN = 1   |     |       |     |        |
|                        |  | $4.5 \text{ V} < \text{V}_{\text{DDA}SD} < 5.5 \text{ V}^{8, 9}$ | 70  | _     | _   |        |
|                        |  | $V_{RH_{SD}} = V_{DDA_{SD}}$                                     |     |       |     |        |
|                        |  | GAIN = 2   |     |       |     |        |
|                        |  | $4.5 \text{ V} < \text{V}_{\text{DDA}SD} < 5.5 \text{ V}^{8, 9}$ | 68  | _     | _   |        |
|                        |  | $V_{RH_SD} = V_{DDA_SD}$   |     |       |     |        |
|                        |  | GAIN = 4   |     |       |     |        |
|                        |  | $4.5 \text{ V} < \text{V}_{\text{DDA}SD} < 5.5 \text{ V}^{8, 9}$ | 65  | —     | —   |        |
|                        |  | $V_{RH_SD} = V_{DDA_SD}$   |     |       |     |        |
|                        |  | GAIN = 8   |     |       |     |        |
|                        |  | $4.5 \text{ V} < \text{V}_{\text{DDA}SD} < 5.5 \text{ V}^{8, 9}$ | 62  | —     | —   |        |
|                        |  | $V_{RH_SD} = V_{DDA_SD}$   |     |       |     |        |
|                        |  | GAIN = 16  |     |       |     |        |
| SNR <sub>SE150</sub>   | Signal to noise ratio in                   | $4.5 \text{ V} < \text{V}_{\text{DDA}SD} < 5.5 \text{ V}^{8, 9}$ | 72  | —     | —   | dB     |
|                        | single ended mode,<br>150 Ksps output rate | $V_{RH_{SD}} = V_{DDA_{SD}}$                                     |     |       |     |        |
|                        |  | GAIN = 1   |     |       |     |        |
|                        |  | 4.5 V < V <sub>DDA_SD</sub> < 5.5 V <sup>8, 9</sup>              | 69  | —     | —   |        |
|                        |  | $V_{RH_{SD}} = V_{DDA_{SD}}$                                     |     |       |     |        |
|                        |  | GAIN = 2   |     |       |     |        |
|                        |  | 4.5 V < V <sub>DDA_SD</sub> < 5.5 V <sup>8, 9</sup>              | 66  | —     | —   |        |
|                        |  | $V_{RH_SD} = V_{DDA_SD}$   |     |       |     |        |
|                        |  | GAIN = 4   |     |       |     |        |
|                        |  | 4.5 V < V <sub>DDA_SD</sub> < 5.5 V <sup>8, 9</sup>              | 62  | —     | —   |        |
|                        |  | $V_{RH_{SD}} = V_{DDA_{SD}}$                                     |     |       |     |        |
|                        |  | GAIN = 8   |     |       |     |        |
|                        |  | $4.5 \text{ V} < \text{V}_{\text{DDA}SD} < 5.5 \text{ V}^{8, 9}$ | 54  | -     | _   |        |
|                        |  | $V_{RH\_SD} = V_{DDA\_SD}$                                       |     |       |     |        |
|                        |  | GAIN = 16  |     |       |     |        |

## Table 17. SDADC electrical specifications (continued)

| Gumbal                   | Parameter                                  | Conditions                          |      | Value |     | Unit |
|--------------------------|--|-------------------------------------|------|-------|-----|------|
| Symbol                   |  | Conditions                          | Min  | Тур   | Мах | Unit |
| SINAD <sub>DIFF150</sub> | Signal to noise and                        | Gain = 1                            | 72   | _     | _   | dBFS |
|                          | distortion ratio in differential mode, 150 | 4.5 V < V <sub>DDA_SD</sub> < 5.5 V |      |       |     |      |
|                          | Ksps output rate                           | $V_{RH_SD} = V_{DDA_SD}$            |      |       |     |      |
|                          |  | Gain = 2                            | 72   | _     | —   |      |
|                          |  | 4.5 V < V <sub>DDA_SD</sub> < 5.5 V |      |       |     |      |
|                          |  | $V_{RH\_SD} = V_{DDA\_SD}$          |      |       |     |      |
|                          |  | Gain = 4                            | 69   | _     | _   |      |
|                          |  | 4.5 V < V <sub>DDA_SD</sub> < 5.5 V |      |       |     |      |
|                          |  | $V_{RH\_SD} = V_{DDA\_SD}$          |      |       |     |      |
|                          |  | Gain = 8                            | 68.8 | _     | _   |      |
|                          |  | 4.5 V < V <sub>DDA_SD</sub> < 5.5 V |      |       |     |      |
|                          |  | $V_{RH_{SD}} = V_{DDA_{SD}}$        |      |       |     |      |
|                          |  | Gain = 16                           | 64.8 | _     | _   |      |
|                          |  | 4.5 V < V <sub>DDA_SD</sub> < 5.5 V |      |       |     |      |
|                          |  | $V_{RH\_SD} = V_{DDA\_SD}$          |      |       |     |      |
| SINAD <sub>DIFF333</sub> | Signal to noise and                        | Gain = 1                            | 66   | -     | _   | dBFS |
|                          | distortion ratio in differential mode, 333 | 4.5 V < V <sub>DDA_SD</sub> < 5.5 V |      |       |     |      |
|                          | Ksps output rate                           | $V_{RH\_SD} = V_{DDA\_SD}$          |      |       |     |      |
|                          |  | Gain = 2                            | 66   | _     | _   |      |
|                          |  | 4.5 V < V <sub>DDA_SD</sub> < 5.5 V |      |       |     |      |
|                          |  | $V_{RH\_SD} = V_{DDA\_SD}$          |      |       |     |      |
|                          |  | Gain = 4                            | 63   | _     |     |      |
|                          |  | 4.5 V < V <sub>DDA_SD</sub> < 5.5 V |      |       |     |      |
|                          |  | $V_{RH\_SD} = V_{DDA\_SD}$          |      |       |     |      |
|                          |  | Gain = 8                            | 62   | -     | _   |      |
|                          | 4.5 V < V <sub>DDA_SD</sub> < 5.5 V        |                                     |      |       |     |      |
|                          |  | $V_{RH\_SD} = V_{DDA\_SD}$          |      |       |     |      |
|                          |  | Gain = 16                           | 59   | _     | _   |      |
|                          |  | 4.5 V < V <sub>DDA_SD</sub> < 5.5 V |      |       |     |      |
|                          |  | $V_{RH_{SD}} = V_{DDA_{SD}}$        |      |       |     |      |

## Table 17. SDADC electrical specifications (continued)

| Symbol                 | Parameter  | Conditions                          |     | Value |     |      |
|------------------------|--|-------------------------------------|-----|-------|-----|------|
| Symbol                 |  |                                     | Min | Тур   | Мах | Unit |
| SINAD <sub>SE150</sub> | Signal to noise and distortion ratio in single-ended mode, | Gain = 1                            | 66  | _     |     | dBFS |
|                        |  | 4.5 V < V <sub>DDA_SD</sub> < 5.5 V |     |       |     |      |
|                        | 150 Ksps output rate                                       | $V_{RH_{SD}} = V_{DDA_{SD}}$        |     |       |     |      |
|                        |  | Gain = 2                            | 66  | _     | _   |      |
|                        |  | 4.5 V < V <sub>DDA_SD</sub> < 5.5 V |     |       |     |      |
|                        |  | $V_{RH_{SD}} = V_{DDA_{SD}}$        |     |       |     |      |
|                        |  | Gain = 4                            | 63  | -     | _   |      |
|                        |  | 4.5 V < V <sub>DDA_SD</sub> < 5.5 V |     |       |     |      |
|                        |  | $V_{RH_{SD}} = V_{DDA_{SD}}$        |     |       |     |      |
|                        |  | Gain = 8                            | 62  | _     | —   |      |
|                        |  | 4.5 V < V <sub>DDA_SD</sub> < 5.5 V |     |       |     |      |
|                        |  | $V_{RH_{SD}} = V_{DDA_{SD}}$        |     |       |     |      |
|                        |  | Gain = 16                           | 54  | _     | _   |      |
|                        |  | 4.5 V < V <sub>DDA_SD</sub> < 5.5 V |     |       |     |      |
|                        |  | $V_{RH_{SD}} = V_{DDA_{SD}}$        |     |       |     |      |
| THD <sub>DIFF150</sub> | Total harmonic   | Gain = 1                            | 65  | _     | _   | dBF  |
|                        | distortion in differential mode, 150 Ksps                  | 4.5 V < V <sub>DDA_SD</sub> < 5.5 V |     |       |     |      |
|                        | output rate  | $V_{RH_{SD}} = V_{DDA_{SD}}$        |     |       |     |      |
|                        |  | Gain = 2                            | 68  | _     | _   |      |
|                        |  | 4.5 V < V <sub>DDA_SD</sub> < 5.5 V |     |       |     |      |
|                        |  | $V_{RH_{SD}} = V_{DDA_{SD}}$        |     |       |     |      |
|                        |  | Gain = 4                            | 74  | -     | _   |      |
|                        |  | 4.5 V < V <sub>DDA_SD</sub> < 5.5 V |     |       |     |      |
|                        |  | $V_{RH_{SD}} = V_{DDA_{SD}}$        |     |       |     |      |
|                        |  | Gain = 8                            | 80  | -     | _   |      |
|                        |  | 4.5 V < V <sub>DDA_SD</sub> < 5.5 V |     |       |     |      |
|                        |  | $V_{RH_{SD}} = V_{DDA_{SD}}$        |     |       |     |      |
|                        |  | Gain = 16                           | 80  | _     | _   |      |
|                        |  | 4.5 V < V <sub>DDA_SD</sub> < 5.5 V |     |       |     |      |
|                        |  | $V_{RH_{SD}} = V_{DDA_{SD}}$        |     |       |     |      |

## Table 17. SDADC electrical specifications (continued)

| Symbol                 | Parameter  | Conditions -                        |      | Valu | е    | Uni |
|------------------------|--|-------------------------------------|------|------|------|-----|
| Symbol                 |  |                                     | Min  | Тур  | Max  |     |
| THD <sub>DIFF333</sub> | Total harmonic   | Gain = 1                            | 65   | _    | —    | dBF |
|                        | distortion in differential mode, 333 Ksps                                      | 4.5 V < V <sub>DDA_SD</sub> < 5.5 V |      |      |      |     |
|                        | output rate  | $V_{RH\_SD} = V_{DDA\_SD}$          |      |      |      |     |
|                        |  | Gain = 2                            | 68   |      | _    |     |
|                        |  | 4.5 V < V <sub>DDA_SD</sub> < 5.5 V |      |      |      |     |
|                        |  | $V_{RH\_SD} = V_{DDA\_SD}$          |      |      |      |     |
|                        |  | Gain = 4                            | 74   | _    | —    |     |
|                        |  | 4.5 V < V <sub>DDA_SD</sub> < 5.5 V |      |      |      |     |
|                        |  | $V_{RH_{SD}} = V_{DDA_{SD}}$        |      |      |      |     |
|                        |  | Gain = 8                            | 80   | _    | _    |     |
|                        |  | 4.5 V < V <sub>DDA_SD</sub> < 5.5 V |      |      |      |     |
|                        |  | $V_{RH\_SD} = V_{DDA\_SD}$          |      |      |      |     |
|                        |  | Gain = 16                           | 80   |      | _    |     |
|                        |  | 4.5 V < V <sub>DDA_SD</sub> < 5.5 V |      |      |      |     |
|                        |  | $V_{RH\_SD} = V_{DDA\_SD}$          |      |      |      |     |
| THD <sub>SE150</sub>   | Total harmonic<br>distortion in single-<br>ended mode, 150<br>Ksps output rate | Gain = 1                            | 68   | _    | _    | dBF |
|                        |  | 4.5 V < V <sub>DDA_SD</sub> < 5.5 V |      |      |      |     |
|                        |  | $V_{RH_{SD}} = V_{DDA_{SD}}$        |      |      |      |     |
|                        |  | Gain = 2                            | 68   |      | _    |     |
|                        |  | 4.5 V < V <sub>DDA_SD</sub> < 5.5 V |      |      |      |     |
|                        |  | $V_{RH\_SD} = V_{DDA\_SD}$          |      |      |      |     |
|                        |  | Gain = 4                            | 66   | _    | _    |     |
|                        |  | 4.5 V < V <sub>DDA SD</sub> < 5.5 V |      |      |      |     |
|                        |  | $V_{RH_{SD}} = V_{DDA_{SD}}$        |      |      |      |     |
|                        |  | Gain = 8                            | 68   |      | _    | _   |
|                        |  | 4.5 V < V <sub>DDA_SD</sub> < 5.5 V |      |      |      |     |
|                        |  | $V_{RH_{SD}} = V_{DDA_{SD}}$        |      |      |      |     |
|                        |  | Gain = 16                           | 68   |      | _    |     |
|                        |  | 4.5 V < V <sub>DDA_SD</sub> < 5.5 V |      |      |      |     |
|                        |  | $V_{RH_SD} = V_{DDA_SD}$            |      |      |      |     |
| SFDR                   | Spurious free dynamic range  | Any GAIN                            | 60   |      | -    | dE  |
| Z <sub>DIFF</sub>      | Differential input   | GAIN = 1                            | 1000 | 1250 | 1500 | kΩ  |
|                        | impedance <sup>10, 11</sup>  | GAIN = 2                            | 600  | 800  | 1000 |     |
|                        |  | GAIN = 4                            | 300  | 400  | 500  |     |
|                        |  | GAIN = 8                            | 200  | 250  | 300  |     |
|                        |  | GAIN = 16                           | 200  | 250  | 300  |     |

## Table 17. SDADC electrical specifications (continued)

Table continues on the next page...

| 0                    | Demonstern   |  |      | Value                 |                             |     |  |
|----------------------|--|--|------|-----------------------|-----------------------------|-----|--|
| Symbol               | Parameter  | Conditions   | Min  | Тур                   | Max                         | Uni |  |
| Z <sub>CM</sub>      | Common Mode input                                    | GAIN = 1   | 1400 | 1800                  | 2200                        | kΩ  |  |
|                      | impedance <sup>11, 12</sup>                          | GAIN = 2   | 1000 | 1300                  | 1600                        |     |  |
|                      |  | GAIN = 4   | 700  | 950                   | 1150                        |     |  |
|                      |  | GAIN = 8   | 500  | 650                   | 800                         |     |  |
|                      |  | GAIN = 16  | 500  | 650                   | 800                         |     |  |
| R <sub>BIAS</sub>    | Bare bias resistance                                 | —  | 110  | 144                   | 180                         | kΩ  |  |
| ΔV <sub>INTCM</sub>  | Common Mode input<br>reference voltage <sup>13</sup> | _  | -12  | _                     | +12                         | %   |  |
| V <sub>BIAS</sub>    | Bias voltage   | —  |      | V <sub>RH_SD</sub> /2 | —                           | V   |  |
| $\delta V_{BIAS}$    | Bias voltage accuracy                                | —  | -2.5 | _                     | +2.5                        | %   |  |
| CMRR                 | Common mode rejection ratio                          | _  | 20   | _                     | —                           | dB  |  |
| R <sub>Caaf</sub>    | Anti-aliasing filter                                 | External series resistance                               | _    | _                     | 20                          | kΩ  |  |
|                      |  | Filter capacitances                                      | 220  |                       | —                           | pF  |  |
| PASSBAND             | Pass band <sup>9</sup>                               | —  | 0.01 |                       | 0.333 * f <sub>ADCD_S</sub> | kH: |  |
| δ <sub>RIPPLE</sub>  | Pass band ripple <sup>14</sup>                       | 0.333 * f <sub>ADCD_S</sub>                              | -1   |                       | 1                           | %   |  |
| F <sub>rolloff</sub> | Stop band attenuation                                | [0.5 * f <sub>ADCD_S</sub> , 1.0 * f <sub>ADCD_S</sub> ] | 40   |                       | —                           | dB  |  |
|                      |  | [1.0 * f <sub>ADCD_S</sub> , 1.5 * f <sub>ADCD_S</sub> ] | 45   |                       | —                           |     |  |
|                      |  | [1.5 * f <sub>ADCD_S</sub> , 2.0 * f <sub>ADCD_S</sub> ] | 50   |                       | —                           |     |  |
|                      |  | [2.0 * f <sub>ADCD_S</sub> , 2.5 * f <sub>ADCD_S</sub> ] | 55   | _                     | —                           |     |  |
|                      |  | [2.5 * f <sub>ADCD_S</sub> , f <sub>ADCD_M</sub> /2]     | 60   |                       | _                           |     |  |

| Table 17. SDADC electrical specifications (continu | (bei |
|--|------|
|--|------|

Table continues on the next page...

| Symbol                | Parameter   | er Conditions                                  |                     | Value             |   |     |  |
|-----------------------|---|--|---------------------|-------------------|---|-----|--|
| Symbol                | i arameter  |  | Min                 | Тур               | Max   | Un  |  |
| $\delta_{GROUP}$      | Group delay                                       | Within pass band: Tclk is $2/f_{ADCD_M}$       | _                   | —                 |   |     |  |
|                       |   | OSR = 24                                       | —                   | —                 | 235.5   | Tcl |  |
|                       |   | OSR = 28                                       | _                   |                   | 275   |     |  |
|                       |   | OSR = 32                                       | _                   |                   | 314.5   |     |  |
|                       |   | OSR = 36                                       |                     |                   | 354   |     |  |
|                       |   | OSR = 40                                       |                     |                   | 393.5   |     |  |
|                       |   | OSR = 44                                       | _                   |                   | 433   |     |  |
|                       |   | OSR = 48                                       | _                   | _                 | 472.5   |     |  |
|                       |   | OSR = 56                                       |                     | _                 | 551.5   |     |  |
|                       |   | OSR = 64                                       |                     |                   | 630.5   |     |  |
|                       |   | OSR = 72                                       |                     |                   | 709.5   | -   |  |
|                       |   | OSR = 75                                       |                     |                   | 696   |     |  |
|                       |   | OSR = 80                                       |                     |                   | 788.5   | -   |  |
|                       |   | OSR = 88                                       | _                   |                   | 867.5   | -   |  |
|                       |   | OSR = 96                                       | _                   |                   | 946.5   | -   |  |
|                       |   | OSR = 112                                      |                     |                   | 1104.5  |     |  |
|                       |   | OSR = 128                                      |                     |                   | 1262.5  | -   |  |
|                       |   | OSR = 144                                      |                     |                   | 1420.5  |     |  |
|                       |   | OSR = 160                                      |                     | _                 | 1578.5  |     |  |
|                       |   | OSR = 176                                      |                     |                   | 1736.5  | -   |  |
|                       |   | OSR = 192                                      |                     |                   | 1894.5  |     |  |
|                       |   | OSR = 224                                      |                     |                   | 2210.5  |     |  |
|                       |   | OSR = 256                                      |                     |                   | 2526.5  |     |  |
|                       |   | Distortion within pass band                    | -0.5/               |                   | +0.5/ f <sub>ADCD_S</sub>                       | _   |  |
|                       |   | •  | f <sub>ADCD_S</sub> |                   |   |     |  |
| f <sub>HIGH</sub>     | High pass filter 3 dB<br>frequency                | Enabled  | _                   | 10e–5*<br>fADCD_S | —   | _   |  |
| t <sub>STARTUP</sub>  | Startup time from power down state                |  |                     | _                 | 100   | μs  |  |
| t <sub>LATENCY</sub>  | Latency between input data and converted          | HPF = ON                                       | —                   | _                 | δ <sub>GROUP</sub> +<br>f <sub>ADCD_S</sub>     | _   |  |
|                       | data when input mux does not change <sup>15</sup> | HPF = OFF                                      | —                   | _                 | δ <sub>GROUP</sub>                              | 1   |  |
| t <sub>SETTLING</sub> | Settling time after mux                           | Analog inputs are muxed                        | - ]                 | _                 | 2*δ <sub>GROUP</sub> +                          | -   |  |
|                       | change  | HPF = ON                                       |                     |                   | 3*f <sub>ADCD_S</sub>                           |     |  |
|                       |   | HPF = OFF                                      | -                   | —                 | 2∗δ <sub>GROUP</sub> +<br>2*f <sub>ADCD_S</sub> | ]   |  |
| DDRECOVERY            | Overdrive recovery time                           | After input comes within range from saturation | -                   | —                 | 2∗δ <sub>GROUP</sub> +<br>f <sub>ADCD_S</sub>   | -   |  |
|                       |   | HPF = ON                                       |                     |                   |   |     |  |
|                       |   | HPF = OFF                                      |                     |                   | 2*δ <sub>GROUP</sub>                            | 1   |  |

## Table 17. SDADC electrical specifications (continued)

Table continues on the next page ...

| Symbol             | Parameter                                       | Conditions                 |     | 9   | Unit    |    |
|--------------------|---|----------------------------|-----|-----|---------|----|
| Symbol             | Falameter                                       | Conditions                 | Min | Тур | Max     |    |
| C <sub>S_D</sub>   | SDADC sampling                                  | GAIN = 1, 2, 4, 8          | -   | —   | 75*GAIN | fF |
|                    | capacitance after sampling switch <sup>16</sup> | GAIN = 16                  | —   |     | 600     | fF |
| I <sub>BIAS</sub>  | Bias consumption                                | At least one SDADC enabled | —   |     | 3.5     | mA |
| I <sub>ADV_D</sub> | SDADC supply consumption                        | Per SDADC enabled          | —   | _   | 4.325   | mA |
| I <sub>ADR_D</sub> | SDADC reference<br>current consumption          | Per SDADC enabled          | —   |     | 20      | μA |

#### Table 17. SDADC electrical specifications (continued)

- 1. For input voltage above the maximum and below the clamp voltage of the input pad, there is no latch-up concern, and the signal will only be "clipped."
- 2. VINP is the input voltage applied to the positive terminal of the SDADC
- 3. VINM is the input voltage applied to the negative terminal of the SDADC
- 4. Sampling is generated internally  $f_{SAMPLING} = f_{ADCD_M}/2$
- 5. For Gain = 16, SDADC resolution is 15 bit.
- Calibration of gain is possible when gain = 1. Offset Calibration should be done with respect to 0.5\*V<sub>RH\_SD</sub> for differential mode and single ended mode with negative input = 0.5\*V<sub>RH\_SD</sub>. Offset Calibration should be done with respect to 0 for single ended mode with negative input = 0. Both Offset and Gain Calibration is guaranteed for +/-5% variation of V<sub>RH\_SD</sub>, +/-10% variation of V<sub>DDA SD</sub>, +/-50 C temperature variation.
- 7. Offset and gain error due to temperature drift can occur in either direction (+/-) for each of the SDADCs on the device.
- SDADC is functional in the range 3.6 V < V<sub>DDA\_SD</sub> < 4.0 V: SNR parameter degrades by 3 dB. SDADC is functional in the range 3.0 V < V<sub>RH SD</sub> < 4.0 V: SNR parameter degrades by 9 dB.</li>
- 9. SNR values guaranteed only if external noise on the ADC input pin is attenuated by the required SNR value in the frequency range of f<sub>ADCD\_M</sub> f<sub>ADCD\_S</sub> to f<sub>ADCD\_M</sub> + f<sub>ADCD\_S</sub>, where f<sub>ADCD\_M</sub> is the input sampling frequency and f<sub>ADCD\_S</sub> is the output sample frequency. A proper external input filter should be used to remove any interfering signals in this frequency range.
- 10. Input impedance in differential mode  $Z_{IN} = Z_{DIFF}$
- 11. Input impedance given at  $f_{ADCD_M} = 16$  MHz. Impedance is inversely proportional to SDADC clock frequency.  $Z_{DIFF}$  ( $f_{ADCD_M}$ ) = (16 MHz /  $f_{ADCD_M}$ ) \*  $Z_{DIFF}$ ,  $Z_{CM}$  ( $f_{ADCD_M}$ ) = (16 MHz /  $f_{ADCD_M}$ ) \*  $Z_{CM}$ .
- 12. Input impedance in single-ended mode  $Z_{IN} = (2 * Z_{DIFF} * Z_{CM}) / (Z_{DIFF} + Z_{CM})$
- 13. V<sub>INTCM</sub> is the Common Mode input reference voltage for the SDADC. It has a nominal value of (V<sub>RH\_SD</sub> V<sub>RL\_SD</sub>) / 2.
- 14. The  $\pm 1\%$  passband ripple specification is equivalent to 20 \* log<sub>10</sub> (0.99) = 0.087 dB.
- 15. Propagation of the information from the pin to the register CDR[CDATA] and the flags SFR[DFEF] and SFR[DFFF] is given by the different modules that must be crossed: delta/sigma filters, high pass filter, FIFO module, and clock domain synchronizers. The time elapsed between data availability at the pin and internal SDADC module registers is given by the following formula, where f<sub>ADCD\_S</sub> is the after decimation ADC output data rate, f<sub>ADCD\_M</sub>/2 is the modulator sampling rate and f<sub>FM\_PER\_CLK</sub> is the frequency of the peripheral bridge clock feeds to the ADC S/D module.

REGISTER LATENCY = t<sub>LATENCY</sub> + 0.5/f<sub>ADCD\_S</sub> + 2 (~+1)/f<sub>ADCD\_M</sub> + 2(~+1)/f<sub>FM\_PER\_CLK</sub>

The (~+1) symbol refers to the number of clock cycles uncertainty (from 0 to 1 clock cycle) to be added due to resynchronization of the signal during clock domain crossing.

Some further latency may be added by the target module (core, DMA, interrupt) controller to process the data received from the SDADC module.

16. This capacitance does not include pin capacitance, that can be considered together with external capacitance, before sampling switch.

# 3.9 Temperature Sensor

The following table describes the Temperature Sensor electrical characteristics.

| Symbol                 | Parameter   | Conditions                     |     | Unit |     |       |
|------------------------|---|--------------------------------|-----|------|-----|-------|
| Symbol                 | Farameter   | Conditions                     | Min | Тур  | Max | Onit  |
| —                      | Temperature monitoring range                                  | —                              | -40 | _    | 150 | °C    |
| T <sub>SENS</sub>      | Sensitivity   | —                              | —   | 5.18 | —   | mV/°C |
| T <sub>ACC</sub>       | Accuracy  | –40°C < T <sub>J</sub> < 150°C | -5  | _    | 5   | °C    |
| I <sub>TEMP_SENS</sub> | V <sub>DDA_EQA</sub> power supply current, per Temp<br>Sensor |                                |     | _    | 700 | μA    |

 Table 18.
 Temperature Sensor electrical characteristics

# 3.10 LVDS pad electrical characteristics

The LVDS pad is used for the Microsecond Channel (MSC) and DSPI LVDS interfaces, with different characteristics given in the following tables.

# 3.10.1 MSC/DSPI LVDS interface timing diagrams





Figure 7. MSC/DSPI LVDS timing definition










Figure 9. Rise/fall time

# 3.10.2 MSC/DSPI LVDS interface electrical characteristics

### Table 19. LVDS pad startup and receiver electrical characteristics<sup>1</sup>

| Symbol                              | Parameter   | Conditions   | Value |     |      | Unit |  |
|-------------------------------------|---|--|-------|-----|------|------|--|
| Symbol                              | Faranieler  | Conditions     Min     Typ     Max       STARTUP <sup>2</sup> , <sup>3</sup> —     0.5     4 |       |     |      |      |  |
| STARTUP <sup>2</sup> , <sup>3</sup> |   |  |       |     |      |      |  |
| t <sub>STRT_BIAS</sub>              | Bias current reference startup time <sup>4</sup>                  | _  | —     | 0.5 | 4    | μs   |  |
| tpd2NM_TX                           | Transmitter startup time (power down to Normal mode) <sup>5</sup> | _  | _     | 0.4 | 2.75 | μs   |  |

Table continues on the next page...

### Table 19. LVDS pad startup and receiver electrical characteristics<sup>1</sup> (continued)

| Symbol                 | Parameter   | Demonster Occulture                        | Value             |     |                   | Unit |
|------------------------|---|--|-------------------|-----|-------------------|------|
| Symbol                 | Parameter   | Conditions                                 | Min               | Тур |                   |      |
| t <sub>SM2NM_TX</sub>  | Transmitter startup time (Sleep mode to Normal mode) <sup>6</sup> | Not applicable to the MSC/DSPI<br>LVDS pad | -                 | 0.2 | 0.5               | μs   |
| t <sub>PD2NM_RX</sub>  | Receiver startup time (power down to Normal mode) <sup>7</sup>    | _  | _                 | 20  | 40                | ns   |
| t <sub>PD2SM_RX</sub>  | Receiver startup time (power down to Sleep mode) <sup>8</sup>     | Not applicable to the MSC/DSPI<br>LVDS pad | -                 | 20  | 50                | ns   |
| I <sub>LVDS_BIAS</sub> | LVDS bias current consumption                                     | Tx or Rx enabled                           | —                 | _   | 0.95              | mA   |
|                        | TRANSMISSION LINE   | CHARACTERISTICS (PCB Track)                |                   |     | •                 |      |
| Z <sub>0</sub>         | Transmission line characteristic impedance                        | _  | 47.5              | 50  | 52.5              | Ω    |
| Z <sub>DIFF</sub>      | Transmission line differential impedance                          | —  | 95                | 100 | 105               | Ω    |
|                        |   | RECEIVER                                   |                   |     |                   |      |
| V <sub>ICOM</sub>      | Common mode voltage   | —  | 0.15 <sup>9</sup> | _   | 1.6 <sup>10</sup> | V    |
| ΔVII                   | Differential input voltage  | —  | 100               | _   | _                 | mV   |
| V <sub>HYS</sub>       | Input hysteresis  | —  | 25                | _   | _                 | mV   |
| R <sub>IN</sub>        | Terminating resistance  | V <sub>DDEH</sub> = 3.0 V to 5.5 V         | 80                | 125 | 150               | Ω    |
| C <sub>IN</sub>        | Differential input capacitance <sup>11</sup>                      | —  | —                 | 3.5 | 6.0               | pF   |
| ILVDS RX               | Receiver DC current consumption                                   | Enabled                                    | —                 | _   | 0.5               | mA   |

- 1. The LVDS pad startup and receiver electrical characteristics in this table apply to MSC/DSPI LVDS pad except where noted in the conditions.
- 2. All startup times are defined after a 2 peripheral bridge clock delay from writing to the corresponding enable bit in the LVDS control registers (LCR) of the and High-Speed Debug modules.
- 3. Startup times are valid for the maximum external loads CL defined in HSD and MSC/DSPI transmitter electrical characteristic tables.
- 4. Bias startup time is defined as the time taken by the current reference block to reach the settling bias current after being enabled.
- Total transmitter startup time from power down to normal mode is t<sub>STRT\_BIAS</sub> + t<sub>PD2NM\_TX</sub> + 2 peripheral bridge clock periods.
- Total transmitter startup time from sleep mode to normal mode is t<sub>SM2NM\_TX</sub> + 2 peripheral bridge clock periods. Bias block remains enabled in sleep mode.
- 7. Total receiver startup time from power down to normal mode is t<sub>STRT\_BIAS</sub> + t<sub>PD2NM\_RX</sub> + 2 peripheral bridge clock periods.
- Total receiver startup time from power down to sleep mode is t<sub>PD2SM\_RX</sub> + 2 peripheral bridge clock periods. Bias block remains enabled in sleep mode.
- 9. Absolute min = 0.15 V (285 mV/2) = 0 V
- 10. Absolute max = 1.6 V + (285 mV/2) = 1.743 V
- 11. Total internal capacitance including receiver and termination, co-bonded GPIO pads, and package contributions. For bare die devices, subtract the package value given in Figure 10

### Table 20. MSC/DSPI LVDS transmitter electrical characteristics<sup>1</sup>

| Symbol             | Parameter   | Conditions |      | Value |      | Unit |
|--------------------|---|------------|------|-------|------|------|
| Symbol             | Falanielei  | Conditions | Min  | Тур   | Мах  | Unit |
| f <sub>DATA</sub>  | Data rate   | —          | —    | _     | 80   | Mbps |
| V <sub>OS</sub>    | Common mode voltage   | —          | 1.08 | _     | 1.32 | V    |
| IV <sub>OD</sub> I | Differential output voltage swing (terminated) <sup>2,3</sup> | —          | 150  | 200   | 400  | mV   |

Table continues on the next page...

| Table 20. | MSC/DSPI LVDS transmitter electrical characteristics <sup>1</sup> | (continued) | ) |
|-----------|---|-------------|---|
|           |   |             |   |

| Symbol               | Parameter   | Conditions               |     | Value |     | Unit |
|----------------------|---|--------------------------|-----|-------|-----|------|
| Symbol               | Farameter   | Conditions               | Min | Тур   | Max | Unit |
| t <sub>TR</sub>      | Rise/Fall time (10%–90% of swing) <sup>2</sup> , <sup>3</sup> | —                        | 0.8 | —     | 4.0 | ns   |
| CL                   | External lumped differential load capacitance <sup>2</sup>    | V <sub>DDE</sub> = 4.5 V | —   | —     | 50  | pF   |
|                      |   | V <sub>DDE</sub> = 3.0 V | _   | —     | 39  |      |
| I <sub>LVDS_TX</sub> | Transmitter DC current consumption                            | Enabled                  |     |       | 4.0 | mA   |

- 1. The MSC and DSPI LVDS pad electrical characteristics are based on the application circuit and typical worst-case internal capacitance values given in Figure 10.
- Valid for maximum data rate f<sub>DATA</sub>. Value given is the capacitance on each terminal of the differential pair, as shown in Figure 10.
- 3. Valid for maximum external load CL.




Figure 10. LVDS pad external load diagram

# 3.11 Power management: PMC, POR/LVD, power sequencing

## 3.11.1 Power management electrical characteristics

The power management module monitors the different power supplies. It also generates the internal supplies that are required for correct device functionality. The power management is supplied by the  $V_{DDPMC}$  supply.

### 3.11.1.1 LDO mode recommended power transistors

Only specific orderable part numbers of MPC5775E support LDO regulation mode. See Ordering information for MPC5775E parts that support this regulation mode.

The following NPN transistors are recommended for use with the on-chip LDO voltage regulator controller: ON Semiconductor<sup>TM</sup> NJD2873. The collector of the external transistor is preferably connected to the same voltage supply source as the output stage of the regulator.

The following table describes the characteristics of the power transistors.

| Symbol              | Parameter                               | Value  | Unit |
|---------------------|---|--------|------|
| h <sub>FE</sub>     | DC current gain (Beta)                  | 60-550 | —    |
| PD                  | Absolute minimum power dissipation      | 1.60   | W    |
| I <sub>CMaxDC</sub> | Maximum DC collector current            | 2.0    | A    |
| VCE <sub>SAT</sub>  | Collector to emitter saturation voltage | 300    | mV   |
| V <sub>BE</sub>     | Base to emitter voltage                 | 0.95   | V    |
| Vc                  | Minimum voltage at transistor collector | 2.5    | V    |

Table 21. Recommended operating characteristics

The following table shows the recommended components to be used in LDO regulation mode.

Table 22. Recommended operating characteristics

| Part name | Part type | Nominal               | Description  |
|-----------|-----------|-----------------------|--|
| Q1        | NPN BJT   | h <sub>FE</sub> = 400 | NJD2873: ON Semiconductor LDO voltage regulator controller (VRC)                                 |
| CI        | Capacitor | 4.7 μF - 20 V         | Ceramic capacitor, total ESR < 70 m $\Omega$   |
| CE        | Capacitor | 0.047–0.049 µF - 7 V  | Ceramic—one capacitor for each V <sub>DD</sub> pin   |
| CV        | Capacitor | 22 μF - 20 V          | Ceramic V <sub>DDPMC</sub> (optional 0.1 µF)   |
| CD        | Capacitor | 22 µF - 20 V          | Ceramic supply decoupling capacitor, ESR < 50 m $\Omega$ (as close as possible to NPN collector) |
| СВ        | Capacitor | 0.1 µF - 7 V          | Ceramic V <sub>DDPWR</sub>   |
| R         | Resistor  | Application specific  | Optional; reduces thermal loading on the NPN with high $V_{\text{DDPMC}}$ levels                 |

The following diagram shows the LDO configuration connection.




Figure 11. VRC 1.2 V LDO configuration

# 3.11.1.2 SMPS mode recommended external components and characteristics

The following table shows the recommended components to be used in SMPS regulation mode.

| Part name | Part type | Nominal              | Description  |
|-----------|-----------|----------------------|--|
| Q1        | p-MOS     | 3 A - 20 V           | SQ2301ES / FDC642P or equivalent: low threshold p-MOS, Vth < 2.0 V, Rdson @ 4.5 V < 100 m $\Omega$ , Cg < 5 nF                                 |
| D1        | Schottky  | 2 A - 20 V           | SS8P3L or equivalent: Vishay™ low Vf Schottky diode  |
| L         | Inductor  | 3–4 µH - 1.5 A       | Buck shielded coil low ESR   |
| CI        | Capacitor | 22 µF - 20 V         | Ceramic capacitor, total ESR < 70 m $\Omega$   |
| CE        | Capacitor | 0.1 μ <b>F - 7 V</b> | Ceramic—one capacitor for each V <sub>DD</sub> pin   |
| CV        | Capacitor | 22 µF - 20 V         | Ceramic V <sub>DDPMC</sub> (optional 0.1 µF capacitor in parallel)   |
| CD        | Capacitor | 22 µF - 20 V         | Ceramic supply decoupling capacitor, ESR < 50 m $\Omega$ (as close as possible to the p-MOS source)  |
| R         | Resistor  | 2.0-4.7 kΩ           | Pullup for power p-MOS gate  |
| СВ        | Capacitor | 22 µF - 20 V         | Ceramic, connect 100 nF capacitor in parallel (as close as possible to package to reduce current loop from $V_{\rm DDPWR}$ to $V_{\rm SSPWR})$ |

 Table 23.
 Recommended operating characteristics

The following diagram shows the SMPS configuration connection.




Figure 12. SMPS configuration

### NOTE

The REGSEL pin is tied to  $V_{DDPMC}$  to select SMPS. If REGSEL is 0, the chip boots with the linear regulator.

See Power sequencing requirements for details about  $V_{\text{DDPMC}}$  and  $V_{\text{DDPWR}}.$ 

The SMPS regulator characteristics appear in the following table.

Table 24. SMPS electrical characteristics

| Symbol                | Parameter                  | Conditions |      | Unit  |      |      |
|-----------------------|----------------------------|------------|------|-------|------|------|
| Symbol                | Falanielei                 | Conditions | Min  | Тур   | Max  |      |
| SMPS <sub>CLOCK</sub> | SMPS oscillator frequency  | Trimmed    | 825  | 1000  | 1220 | kHz  |
| SMPS <sub>SLOPE</sub> | SMPS soft-start ramp slope | _          | 0.01 | 0.025 | 0.05 | V/µs |
| SMPS <sub>EFF</sub>   | SMPS typical efficiency    | _          |      | 70    |      | %    |

# 3.11.2 Power management integration

To ensure correct functionality of the device, use the following recommended integration scheme for LDO mode.




Figure 13. Recommended supply pin circuits

The following table describes the supply stability capacitances required on the device for proper operation.

| Symbol                    | Parameter   | Conditions |      |                  | Unit |    |
|---------------------------|---|------------|------|------------------|------|----|
| Symbol                    | Falaniciei  | Conditions | Min  | Тур              | Max  |    |
| C <sub>LV</sub>           | Minimum V <sub>DD</sub> external bulk capacitance <sup>2, 3</sup>               | LDO mode   | 4.7  | —                | _    | μF |
|                           |   | SMPS mode  | 22   | —                | _    | μF |
| C <sub>SMPSPWR</sub>      | Minimum SMPS driver supply capacitance  | —          | 22   | —                | —    | μF |
| C <sub>HV_PMC</sub>       | Minimum V <sub>DDPMC</sub> external bulk capacitance <sup>4, 5</sup>            | LDO mode   | 22   | —                | —    | μF |
|                           |   | SMPS mode  | 22   | —                | _    | μF |
| C <sub>HV_IO</sub>        | Minimum V <sub>DDEx</sub> /V <sub>DDEHx</sub> external capacitance <sup>2</sup> | —          | —    | 4.7 <sup>6</sup> | _    | μF |
| C <sub>HV_FLA</sub>       | Minimum V <sub>DD_FLA</sub> external capacitance <sup>7</sup>                   | —          | 1.0  | 2.0              |      | μF |
| C <sub>HV_ADC_EQA/B</sub> | Minimum V <sub>DDA_EQA/B</sub> external capacitance <sup>8</sup>                | —          | 0.01 |                  |      | μF |

Table 25. Device power supply integration

Table continues on the next page...

| Table 25. | Device p | ower suppl | y integration | (continued) |
|-----------|----------|------------|---------------|-------------|
|-----------|----------|------------|---------------|-------------|

| Symbol             | Parameter  | Conditions |      | Value | 1   | Unit |
|--------------------|--|------------|------|-------|-----|------|
| Symbol             | Falaniciei   | Conditions | Min  | Тур   | Max | Unit |
| C <sub>REFEQ</sub> | Minimum REF <sub>BYPCA/B</sub> external capacitance <sup>9</sup> | —          | 0.01 | _     | —   | μF   |
| $C_{HV\_ADC\_SD}$  | Minimum V <sub>DDA_SD</sub> external capacitance <sup>10</sup>   | —          | 1.0  | 2.2   | _   | μF   |

- 1. See Figure 13 for capacitor integration.
- 2. Recommended X7R or X5R ceramic low ESR capacitors, ±15% variation over process, voltage, temperature, and aging.
- 3. Each V<sub>DD</sub> pin requires both a 47 nF and a 0.01 µF capacitor for high-frequency bypass and EMC requirements.
- 4. Recommended X7R or X5R ceramic low ESR capacitors, ±15% variation over process, voltage, temperature, and aging.
- 5. Each V<sub>DDPMC</sub> pin requires both a 47 nF and a 0.01 µF capacitor for high-frequency bypass and EMC requirements.
- 6. The actual capacitance should be selected based on the I/O usage in order to keep the supply voltage within its operating range.
- 7. The recommended flash regulator composition capacitor is 2.0  $\mu$ F typical X7R or X5R, with -50% and +35% as min and max. This puts the min cap at 0.75  $\mu$ F.
- For noise filtering it is recommended to add a high frequency bypass capacitance of 0.1 μF between V<sub>DDA\_EQA/B</sub> and V<sub>SSA\_EQ</sub>.
- 9. For noise filtering it is recommended to add a high frequency bypass capacitance of 0.1 μF between REF<sub>BYPCA/B</sub> and V<sub>SS</sub>.
- 10. For noise filtering it is recommended to add a high frequency bypass capacitance of 0.1  $\mu$ F between V<sub>DDA\_SD</sub> and V<sub>SSA\_SD</sub>.

## 3.11.3 Device voltage monitoring

The LVD/HVDs for the device and their levels are given in the following table. Voltage monitoring threshold definition is provided in the following figure.






Figure 14. Voltage monitor threshold definition

| Table 26. | Voltage monitor electrical characteristics <sup>1, 2</sup> |
|-----------|--|
|-----------|--|

|                       |                                     |                              | Co           | nfigura      | tion       |      | Value |      |      |
|-----------------------|-------------------------------------|------------------------------|--------------|--------------|------------|------|-------|------|------|
| Symbol                | Parameter                           | Conditions                   | Trim<br>bits | Mask<br>Opt. | Pow.<br>Up | Min  | Тур   | Max  | Unit |
| POR098_c <sup>3</sup> | LV internal supply power            | Rising voltage (powerup)     | N/A          | No           | Enab.      | 960  | 1010  | 1060 | mV   |
|                       | on reset                            | Falling voltage (power down) |              |              |            | 940  | 990   | 1040 |      |
| LVD_core_hot          | LV internal <sup>4</sup> supply low | Rising voltage (untrimmed)   | 4bit         | No           | Enab.      | 1100 | 1140  | 1183 | mV   |
|                       | voltage monitoring                  | Falling voltage (untrimmed)  |              |              |            | 1080 | 1120  | 1163 |      |
|                       |                                     | Rising voltage (trimmed)     |              |              |            | 1142 | 1165  | 1183 |      |
|                       |                                     | Falling voltage (trimmed)    |              |              |            | 1122 | 1145  | 1163 |      |
| LVD_core_cold         | LV external <sup>5</sup> supply low | Rising voltage               | 4bit         | Yes          | Disab.     | 1165 | 1180  | 1198 | mV   |
|                       | voltage monitoring                  | Falling voltage              |              |              |            | 1136 | 1160  | 1178 |      |
| HVD_core              | LV internal cold supply             | Rising voltage               | 4bit         | Yes          | Disab.     | 1338 | 1365  | 1385 | mV   |
|                       | high voltage monitoring             | Falling voltage              |              |              |            | 1318 | 1345  | 1365 |      |

Table continues on the next page ...

| Table 26. | Voltage monitor | electrical | characteristics <sup>1, 2</sup> | (continued) | ) |
|-----------|-----------------|------------|---------------------------------|-------------|---|
|-----------|-----------------|------------|---------------------------------|-------------|---|

|                         |  |                              | Co           | nfigura      | tion       |      | Value |      |     |
|-------------------------|--|------------------------------|--------------|--------------|------------|------|-------|------|-----|
| Symbol                  | Parameter  | Conditions                   | Trim<br>bits | Mask<br>Opt. | Pow.<br>Up | Min  | Тур   | Max  | Uni |
| POR_HV                  | HV V <sub>DDPMC</sub> supply power               | Rising voltage (powerup)     | N/A          | No           | Enab.      | 2444 | 2600  | 2756 | mV  |
| on reset threshold      |  | Falling voltage (power down) |              |              |            | 2424 | 2580  | 2736 |     |
| LVD_HV                  | HV internal V <sub>DDPMC</sub> supply            | Rising voltage (untrimmed)   | 4bit         | No           | Enab.      | 2935 | 3023  | 3112 | mV  |
|                         | low voltage monitoring                           | Falling voltage (untrimmed)  |              |              |            | 2922 | 3010  | 3099 |     |
|                         |  | Rising voltage (trimmed)     |              |              |            | 2946 | 3010  | 3066 |     |
|                         |  | Falling voltage (trimmed)    |              |              |            | 2934 | 2998  | 3044 |     |
| high voltage menitoring |  | Rising voltage               | 4bit         | Yes          | Disab.     | 5696 | 5860  | 5968 | mV  |
|                         |  | Falling voltage              |              |              |            | 5666 | 5830  | 5938 |     |
| LVD_FLASH               | FLASH supply low voltage monitoring <sup>6</sup> | Rising voltage (untrimmed)   | 4bit         | No           | Enab.      | 2935 | 3023  | 3112 | mV  |
|                         |  | Falling voltage (untrimmed)  |              |              |            | 2922 | 3010  | 3099 | 1   |
|                         |  | Rising voltage (trimmed)     |              |              |            | 2956 | 3010  | 3053 | İ   |
|                         |  | Falling voltage (trimmed)    |              |              |            | 2944 | 2998  | 3041 | 1   |
| HVD_FLASH               | FLASH supply high                                | Rising voltage               | 4bit         | Yes          | Disab.     | 3456 | 3530  | 3584 | mV  |
|                         | voltage monitoring <sup>6</sup>                  | Falling voltage              |              |              |            | 3426 | 3500  | 3554 |     |
| LVD_IO                  | Main I/O V <sub>DDEH1</sub> supply               | Rising voltage (untrimmed)   | 4bit         | No           | Enab.      | 3250 | 3350  | 3488 | mV  |
|                         | low voltage monitoring                           | Falling voltage (untrimmed)  |              |              |            | 3220 | 3320  | 3458 |     |
|                         |  | Rising voltage (trimmed)     |              |              |            | 3347 | 3420  | 3468 |     |
|                         |  | Falling voltage (trimmed)    |              |              |            | 3317 | 3390  | 3438 |     |
| t <sub>VDASSERT</sub>   | Voltage detector threshold crossing assertion    | _                            | _            | _            | —          | 0.1  | _     | 2.0  | μs  |
| t <sub>VDRELEASE</sub>  | Voltage detector threshold crossing de-assertion | _                            | —            | —            | —          | 5    | —     | 20   | μs  |

- 1. LVD is released after t<sub>VDRELEASE</sub> temporization when upper threshold is crossed; LVD is asserted t<sub>VDASSERT</sub> after detection when lower threshold is crossed.
- HVD is released after t<sub>VDRELEASE</sub> temporization when lower threshold is crossed; HVD is asserted t<sub>VDASSERT</sub> after detection when upper threshold is crossed.
- 3. POR098\_c threshold is an untrimmed value, before the completion of the power-up sequence. All other LVD/HVD thresholds are provided after trimming.
- 4. LV internal supply levels are measured on device internal supply grid after internal voltage drop.
- 5. LV external supply levels are measured on the die side of the package bond wire after package voltage drop.
- 6. V<sub>DDFLA</sub> range is guaranteed when internal flash memory regulator is used.

## 3.11.4 Power sequencing requirements

Requirements for power sequencing include the following.

### NOTE

In these descriptions, *star route layout* means a track split as close as possible to the power supply source. Each of the split tracks is routed individually to the intended end connection.

- 1. For both LDO mode and SMPS mode, V<sub>DDPMC</sub> and V<sub>DDPWR</sub> must be connected together (shorted) to ensure aligned voltage ramping up/down. In addition:
  - For SMPS mode, a star route layout of the power track is required to minimize mutual noise. If SMPS mode is not used, the star route layout is not required. V<sub>DDPWR</sub> is the supply pin for the SMPS circuitry.
  - For 3.3 V operation,  $V_{DDFLA}$  must also be star routed and shorted to  $V_{DDPWR}$ and  $V_{DDPMC}$ . This triple connection is required because 3.3 V does not guarantee correct functionality of the internal  $V_{DDFLA}$  regulator. Consequently,  $V_{DDFLA}$  is supplied externally.
- 2. V<sub>DDA\_MISC</sub>: IRC operation is required to provide the clock for chip startup.
  - The V<sub>DDPMC</sub>, V<sub>DD</sub>, and V<sub>DDEH1</sub> (reset pin pad segment) supplies are monitored. They hold IRC until all of them reach operational voltage. In other words, V<sub>DDA\_MISC</sub> must reach its specified minimum operating voltage before or at the same time that all of these monitored voltages reach their respective specified minimum voltages.
  - An alternative is to connect the same supply voltage to both  $V_{DDEH1}$  and  $V_{DDA\_MISC}$ . This alternative approach requires a star route layout to minimize mutual noise.
- 3. Multiple  $V_{DDEx}$  supplies can be powered up in any order.

During any time when  $V_{DD}$  is powered up but  $V_{DDEx}$  is not yet powered up: pad outputs are unpowered.

During any time when  $V_{DDEx}$  is powered up before all other supplies: all pad output buffers are tristated.

- 4. Ramp up  $V_{DDA\_EQ}$  before  $V_{DD}$ . Otherwise, a reset might occur.
- 5. When the device is powering down while using the internal SMPS regulator,  $V_{DDPMC}$  and  $V_{DDPWR}$  supplies must ramp down through the voltage range from 2.5 V to 1.5 V in less than 1 second. Slower ramp-down times might result in reduced lifetime reliability of the device.

# 3.12 Flash memory specifications

# 3.12.1 Flash memory program and erase specifications

NOTE

All timing, voltage, and current numbers specified in this section are defined for a single embedded flash memory within an SoC, and represent average currents for given supplies and operations.

Table 27 shows the estimated Program/Erase times.

| Symbol               | Characteristic <sup>1</sup>        | Typ <sup>2</sup> |                               | tory<br>nming <sup>3, 4</sup>   | Field Update                           |                   | Unit                |    |
|----------------------|------------------------------------|------------------|-------------------------------|---------------------------------|--|-------------------|---------------------|----|
|                      |                                    |                  | Initial<br>Max                | Initial<br>Max, Full<br>Temp    | Typical<br>End of<br>Life <sup>5</sup> | Lifeti            | me Max <sup>6</sup> |    |
|                      |                                    |                  | 20°C ≤T <sub>A</sub><br>≤30°C | -40°C ≤T <sub>J</sub><br>≤150°C | -40°C ≤T <sub>J</sub><br>≤150°C        | ≤ 1,000<br>cycles | ≤ 250,000<br>cycles |    |
| t <sub>dwpgm</sub>   | Doubleword (64 bits) program time  | 43               | 100                           | 150                             | 55                                     | 500               | -                   | μs |
| t <sub>ppgm</sub>    | Page (256 bits) program time       | 73               | 200                           | 300                             | 108                                    | 500               |                     | μs |
| t <sub>qppgm</sub>   | Quad-page (1024 bits) program time | 268              | 800                           | 1,200                           | 396                                    | 2,000             |                     | μs |
| t <sub>16kers</sub>  | 16 KB Block erase time             | 168              | 290                           | 320                             | 250                                    | 1,000             |                     | ms |
| t <sub>16kpgm</sub>  | 16 KB Block program time           | 34               | 45                            | 50                              | 40                                     | 1,000             |                     | ms |
| t <sub>32kers</sub>  | 32 KB Block erase time             | 217              | 360                           | 390                             | 310                                    | 1,200             |                     | ms |
| t <sub>32kpgm</sub>  | 32 KB Block program time           | 69               | 100                           | 110                             | 90                                     | 1,200             |                     | ms |
| t <sub>64kers</sub>  | 64 KB Block erase time             | 315              | 490                           | 590                             | 420                                    | 1,600             |                     | ms |
| t <sub>64kpgm</sub>  | 64 KB Block program time           | 138              | 180                           | 210                             | 170                                    | 1,600             |                     | ms |
| t <sub>256kers</sub> | 256 KB Block erase time            | 884              | 1,520                         | 2,030                           | 1,080                                  | 4,000             | —                   | ms |
| t <sub>256kpgm</sub> | 256 KB Block program time          | 552              | 720                           | 880                             | 650                                    | 4,000             | _                   | ms |

 Table 27.
 Flash memory program and erase specifications

1. Program times are actual hardware programming times and do not include software overhead. Block program times assume quad-page programming.

2. Typical program and erase times represent the median performance and assume nominal supply values and operation at 25 °C. Typical program and erase times may be used for throughput calculations.

- 3. Conditions:  $\leq$  150 cycles, nominal voltage.
- 4. Plant Programing times provide guidance for timeout limits used in the factory.
- 5. Typical End of Life program and erase times represent the median performance and assume nominal supply values. Typical End of Life program and erase values may be used for throughput calculations.
- 6. Conditions:  $-40^{\circ}C \le T_J \le 150^{\circ}C$ , full spec voltage.

### 3.12.2 Flash memory Array Integrity and Margin Read specifications Table 28. Flash memory Array Integrity and Margin Read specifications

| Symbol                 | Characteristic  | Min    | Typical | Max <sup>1</sup>             | Units<br>2 |
|------------------------|---|--------|---------|------------------------------|------------|
| t <sub>ai16kseq</sub>  | Array Integrity time for sequential sequence on 16 KB block.  | -      | _       | 512 x<br>Tperiod x<br>Nread  | _          |
| t <sub>ai32kseq</sub>  | Array Integrity time for sequential sequence on 32 KB block.  | -      | _       | 1024 x<br>Tperiod x<br>Nread | _          |
| t <sub>ai64kseq</sub>  | Array Integrity time for sequential sequence on 64 KB block.  | _      | _       | 2048 x<br>Tperiod x<br>Nread | _          |
| tai256kseq             | Array Integrity time for sequential sequence on 256 KB block. | -      | _       | 8192 x<br>Tperiod x<br>Nread | _          |
| t <sub>mr16kseq</sub>  | Margin Read time for sequential sequence on 16 KB block.      | 73.81  | _       | 110.7                        | μs         |
| t <sub>mr32kseq</sub>  | Margin Read time for sequential sequence on 32 KB block.      | 128.43 | —       | 192.6                        | μs         |
| t <sub>mr64kseq</sub>  | Margin Read time for sequential sequence on 64 KB block.      | 237.65 | —       | 356.5                        | μs         |
| t <sub>mr256kseq</sub> | Margin Read time for sequential sequence on 256 KB block.     | 893.01 | —       | 1,339.5                      | μs         |

- Array Integrity times need to be calculated and is dependent on system frequency and number of clocks per read. The
  equation presented require Tperiod (which is the unit accurate period, thus for 200 MHz, Tperiod would equal 5e-9) and
  Nread (which is the number of clocks required for read, including pipeline contribution. Thus for a read setup that requires
  6 clocks to read with no pipeline, Nread would equal 6. For a read setup that requires 6 clocks to read, and has the
  address pipeline set to 2, Nread would equal 4 (or 6 2).)
- 2. The units for Array Integrity are determined by the period of the system clock. If unit accurate period is used in the equation, the results of the equation are also unit accurate.

# 3.12.3 Flash memory module life specifications


| Symbol              | Characteristic  | Conditions                        | Min     | Typical | Units         |
|---------------------|---|-----------------------------------|---------|---------|---------------|
| Array P/E<br>cycles | Number of program/erase cycles per block<br>for 16 KB, 32 KB and 64 KB blocks. <sup>1</sup> | —                                 | 250,000 | -       | P/E<br>cycles |
|                     | Number of program/erase cycles per block for 256 KB blocks. <sup>2</sup>                    | —                                 | 1,000   | 250,000 | P/E<br>cycles |
| Data retention      | Minimum data retention.   | Blocks with 0 - 1,000 P/E cycles. | 50      | -       | Years         |
|                     |   | Blocks with 100,000 P/E cycles.   | 20      | -       | Years         |
|                     |   | Blocks with 250,000 P/E cycles.   | 10      | -       | Years         |

Table 29. Flash memory module life specifications

- 1. Program and erase supported across standard temperature specs.
- 2. Program and erase supported across standard temperature specs.

## 3.12.4 Data retention vs program/erase cycles

Graphically, Data Retention versus Program/Erase Cycles can be represented by the following figure. The spec window represents qualified limits. The extrapolated dotted line demonstrates technology capability, however is beyond the qualification limits.



### 3.12.5 Flash memory AC timing specifications Table 30. Flash memory AC timing specifications

| Symbol            | Characteristic  | Min | Typical  | Max   | Units |
|-------------------|---|-----|--|---|-------|
| t <sub>psus</sub> | Time from setting the MCR-PSUS bit until MCR-DONE bit is set to a 1.          |     | 9.4<br>plus four<br>system<br>clock<br>periods | 11.5<br>plus four<br>system<br>clock<br>periods | μs    |
| t <sub>esus</sub> | Time from setting the MCR-ESUS bit until MCR-DONE bit is set to a 1.          |     | 16<br>plus four<br>system<br>clock<br>periods  | 20.8<br>plus four<br>system<br>clock<br>periods | μs    |
| t <sub>res</sub>  | Time from clearing the MCR-ESUS or PSUS bit with EHV = 1 until DONE goes low. | _   | _  | 100   | ns    |

Table continues on the next page...

| Symbol               | Characteristic  | Min  | Typical                                       | Max  | Units |
|----------------------|---|--|---|--|-------|
| t <sub>done</sub>    | Time from 0 to 1 transition on the MCR-EHV bit initiating a program/erase until the MCR-DONE bit is cleared.  | _  | _   | 5  | ns    |
| t <sub>dones</sub>   | Time from 1 to 0 transition on the MCR-EHV bit aborting a program/erase until the MCR-DONE bit is set to a 1.   | _  | 16<br>plus four<br>system<br>clock<br>periods | 20.8<br>plus four<br>system<br>clock<br>periods  | μs    |
| t <sub>drcv</sub>    | Time to recover once exiting low power mode.  | 16<br>plus seven<br>system<br>clock<br>periods.  | _   | 45<br>plus seven<br>system<br>clock<br>periods   | μs    |
| t <sub>aistart</sub> | Time from 0 to 1 transition of UT0-AIE initiating a Margin Read<br>or Array Integrity until the UT0-AID bit is cleared. This time also<br>applies to the resuming from a suspend or breakpoint by<br>clearing AISUS or clearing NAIBP |  | _   | 5  | ns    |
| t <sub>aistop</sub>  | Time from 1 to 0 transition of UT0-AIE initiating an Array<br>Integrity abort until the UT0-AID bit is set. This time also applies<br>to the UT0-AISUS to UT0-AID setting in the event of a Array<br>Integrity suspend request.       |  |   | 80<br>plus fifteen<br>system<br>clock<br>periods | ns    |
| t <sub>mrstop</sub>  | Time from 1 to 0 transition of UT0-AIE initiating a Margin Read<br>abort until the UT0-AID bit is set. This time also applies to the<br>UT0-AISUS to UT0-AID setting in the event of a Margin Read<br>suspend request.                | 10.36<br>plus four<br>system<br>clock<br>periods | _   | 20.42<br>plus four<br>system<br>clock<br>periods | μs    |

### Table 30. Flash memory AC timing specifications (continued)

# 3.12.6 Flash memory read wait-state and address-pipeline control settings

The following table describes the recommended settings of the Flash Memory Controller's PFCR1[RWSC] and PFCR1[APC] fields at various flash memory operating frequencies, based on specified intrinsic flash memory access times of the C55FMC array at 150°C.

 Table 31. Flash memory read wait-state and address-pipeline control combinations

| Flash memory frequency                           | RWSC | APC | Flash memory read latency on<br>mini-cache miss (# of f <sub>PLATF</sub><br>clock periods) | Flash memory read latency on<br>mini-cache hit (# of f <sub>PLATF</sub> clock<br>periods) |
|--|------|-----|--|---|
| 0 MHz < f <sub>PLATF</sub> ≤ 33 MHz              | 0    | 0   | 3  | 1   |
| $33 \text{ MHz} < f_{PLATF} \le 100 \text{ MHz}$ | 2    | 1   | 5  | 1   |

Table continues on the next page...

# Table 31. Flash memory read wait-state and address-pipeline control combinations (continued)

| Flash memory frequency                 | RWSC | АРС | Flash memory read latency on<br>mini-cache miss (# of f <sub>PLATF</sub><br>clock periods) | Flash memory read latency on<br>mini-cache hit (# of f <sub>PLATF</sub> clock<br>periods) |
|--|------|-----|--|---|
| 100 MHz < f <sub>PLATE</sub> ≤ 133 MHz | 3    | 1   | 6  | 1   |

# 3.13 AC timing

# 3.13.1 Generic timing diagrams

The generic timing diagrams in Figure 15 and Figure 16 apply to all I/O pins with pad types SR and FC. See the associated MPC5775E Microsoft Excel® file in the Reference Manual for the pad type for each pin.





Figure 15. Generic output delay/hold timing



# 3.13.2 Reset and configuration pin timing

### Table 32. Reset and configuration pin timing<sup>1</sup>

| Spec | Characteristic                                     | Symbol            | Min | Мах | Unit                          |
|------|--|-------------------|-----|-----|-------------------------------|
| 1    | RESET Pulse Width                                  | t <sub>RPW</sub>  | 10  | —   | t <sub>cyc</sub> <sup>2</sup> |
| 2    | RESET Glitch Detect Pulse Width                    | t <sub>GPW</sub>  | 2   | —   | t <sub>cyc</sub> <sup>2</sup> |
| 3    | PLLCFG, BOOTCFG, WKPCFG Setup Time to RSTOUT Valid | t <sub>RCSU</sub> | 10  | —   | t <sub>cyc</sub> <sup>2</sup> |
| 4    | PLLCFG, BOOTCFG, WKPCFG Hold Time to RSTOUT Valid  | t <sub>RCH</sub>  | 0   |     | t <sub>cyc</sub> <sup>2</sup> |

1. Reset timing specified at:  $V_{DDEH}$  = 3.0 V to 5.25 V,  $V_{DD}$  = 1.08 V to 1.32 V, TA = TL to TH.

2. For further information on t<sub>cvc</sub>, see Table 3.

**Electrical characteristics** 




Figure 17. Reset and configuration pin timing

### 3.13.3 IEEE 1149.1 interface timing Table 33. JTAG pin AC electrical characteristics<sup>1</sup>

| #  | Symphol                               | Characteristic   | Va  | lue              | Unit |
|----|---------------------------------------|--|-----|------------------|------|
| #  | Symbol                                | Characteristic   |     | Max              | Unit |
| 1  | t <sub>JCYC</sub>                     | TCK cycle time   | 100 | —                | ns   |
| 2  | t <sub>JDC</sub>                      | TCK clock pulse width                                  | 40  | 60               | %    |
| 3  | t <sub>TCKRISE</sub>                  | TCK rise and fall times (40%–70%)                      | —   | 3                | ns   |
| 4  | t <sub>TMSS</sub> , t <sub>TDIS</sub> | TMS, TDI data setup time                               | 5   | _                | ns   |
| 5  | t <sub>TMSH</sub> , t <sub>TDIH</sub> | TMS, TDI data hold time                                | 5   | _                | ns   |
| 6  | t <sub>TDOV</sub>                     | TCK low to TDO data valid                              | —   | 16 <sup>2</sup>  | ns   |
| 7  | t <sub>TDOI</sub>                     | TCK low to TDO data invalid                            | 0   | _                | ns   |
| 8  | t <sub>TDOHZ</sub>                    | TCK low to TDO high impedance                          | —   | 15               | ns   |
| 9  | t <sub>JCMPPW</sub>                   | JCOMP assertion time                                   | 100 | _                | ns   |
| 10 | t <sub>JCMPS</sub>                    | JCOMP setup time to TCK low                            | 40  | _                | ns   |
| 11 | t <sub>BSDV</sub>                     | TCK falling edge to output valid                       | —   | 600 <sup>3</sup> | ns   |
| 12 | t <sub>BSDVZ</sub>                    | TCK falling edge to output valid out of high impedance | —   | 600              | ns   |
| 13 | t <sub>BSDHZ</sub>                    | TCK falling edge to output high impedance              | —   | 600              | ns   |
| 14 | t <sub>BSDST</sub>                    | Boundary scan input valid to TCK rising edge           | 15  | —                | ns   |
| 15 | t <sub>BSDHT</sub>                    | TCK rising edge to boundary scan input invalid         | 15  | —                | ns   |

1. These specifications apply to JTAG boundary scan only. See Table 34 for functional specifications.

- 2. Timing includes TCK pad delay, clock tree delay, logic delay and TDO output pad delay.
- 3. Applies to all pins, limited by pad slew rate. Refer to I/O delay and transition specification and add 20 ns for JTAG delay.






Figure 18. JTAG test clock input timing




Figure 19. JTAG test access port timing




Figure 20. JTAG JCOMP timing

**Electrical characteristics** 




Figure 21. JTAG boundary scan timing

# 3.13.4 Nexus timing

### Table 34. Nexus debug port timing<sup>1</sup>

| Spec | Characteristic                           | Symbol              | Min            | Max | Unit              |
|------|--|---------------------|----------------|-----|-------------------|
| 1    | MCKO Cycle Time                          | t <sub>MCYC</sub>   | 2              | 8   | t <sub>CYC</sub>  |
| 2    | MCKO Duty Cycle                          | t <sub>MDC</sub>    | 40             | 60  | %                 |
| 3    | MCKO Low to MDO Data Valid <sup>2</sup>  | t <sub>MDOV</sub>   | -0.1           | 0.2 | t <sub>MCYC</sub> |
| 4    | MCKO Low to MSEO Data Valid <sup>2</sup> | t <sub>MSEOV</sub>  | -0.1           | 0.2 | t <sub>MCYC</sub> |
| 5    | MCKO Low to EVTO Data Valid <sup>2</sup> | t <sub>EVTOV</sub>  | -0.1           | 0.2 | t <sub>MCYC</sub> |
| 6    | EVTI Pulse Width                         | t <sub>EVTIPW</sub> | 4.0            | _   | t <sub>TCYC</sub> |
| 7    | EVTO Pulse Width                         | t <sub>EVTOPW</sub> | 1              | —   | t <sub>MCYC</sub> |
| 8    | TCK Cycle Time                           | t <sub>TCYC</sub>   | 2 <sup>3</sup> | _   | t <sub>CYC</sub>  |

Table continues on the next page...

| Table 34. | Nexus c | debug | port ti | ming <sup>1</sup> ( | (continued) |
|-----------|---------|-------|---------|---------------------|-------------|
|-----------|---------|-------|---------|---------------------|-------------|

| Spec | Characteristic   | Symbol                                  | Min             | Max | Unit |
|------|--|---|-----------------|-----|------|
| 8    | Absolute minimum TCK cycle time <sup>4</sup> (TDO sampled on posedge of TCK) | t <sub>TCYC</sub>                       | 40 <sup>5</sup> | _   | ns   |
|      | Absolute minimum TCK cycle time <sup>4</sup> (TDO sampled on negedge of TCK) |   | 20 <sup>5</sup> | _   |      |
| 9    | TCK Duty Cycle   | t <sub>TDC</sub>                        | 40              | 60  | %    |
| 10   | TDI, TMS Data Setup Time <sup>6</sup>  | t <sub>NTDIS</sub> , t <sub>NTMSS</sub> | 8               | —   | ns   |
| 11   | TDI, TMS Data Hold Time <sup>6</sup>   | T <sub>NTDIH</sub> , t <sub>NTMSH</sub> | 5               | —   | ns   |
| 12   | TCK Low to TDO Data Valid <sup>6</sup>                                       | t <sub>NTDOV</sub>                      | 0               | 18  | ns   |
| 13   | RDY Valid to MCKO <sup>7</sup>   | _                                       | —               | —   | _    |
| 14   | TDO hold time after TCLK low <sup>6</sup>                                    | t <sub>NTDOH</sub>                      | 1               | —   | ns   |

1. All Nexus timing relative to MCKO is measured from 50% of MCKO and 50% of the respective signal. Nexus timing specified at  $V_{DD}$  = 1.08 V to 1.32 V,  $V_{DDE}$  = 3.0 V to 3.6 V,  $V_{DD33}$  and  $V_{DDSYN}$  = 3.0 V to 3.6 V,  $T_A$  =  $T_L$  to  $T_H$ , and  $C_L$  = 30 pF with DSC = 0b10.

- 2. MDO, MSEO, and EVTO data is held valid until next MCKO low cycle.
- 3. This is a functionally allowable feature. However, it may be limited by the maximum frequency specified by the absolute minimum TCK period specification.
- 4. This value is TDO propagation time plus 2 ns setup time to sampling edge.
- 5. This may require a maximum clock speed that is less than the maximum functional capability of the design depending on the actual system frequency being used.
- 6. Applies to TMS pin timing for the bit frame when using the 1149.7 advanced protocol.
- 7. The RDY pin timing is asynchronous to MCKO. The timing is guaranteed by design to function correctly.




Figure 22. Nexus timings




Figure 23. Nexus TCK, TDI, TMS, TDO Timing

### 3.13.5 External interrupt timing (IRQ/NMI pin) Table 35. External Interrupt timing<sup>1</sup>

| Spec | Characteristic                         | Symbol            | Min | Max | Unit                          |
|------|--|-------------------|-----|-----|-------------------------------|
| 1    | IRQ/NMI Pulse Width Low                | t <sub>IPWL</sub> | 3   | —   | t <sub>cyc</sub> <sup>2</sup> |
| 2    | IRQ/NMI Pulse Width High               | t <sub>IPWH</sub> | 3   | _   | t <sub>cyc</sub> <sup>2</sup> |
| 3    | IRQ/NMI Edge to Edge Time <sup>3</sup> | t <sub>ICYC</sub> | 6   | —   | t <sub>cyc</sub> <sup>2</sup> |

1. IRQ/NMI timing specified at  $V_{DD}$  = 1.08 V to 1.32 V,  $V_{DDEH}$  = 3.0 V to 5.5 V,  $T_A$  =  $T_L$  to  $T_H$ .

2. For further information on  $t_{cyc}$ , see Table 3.

3. Applies when IRQ/NMI pins are configured for rising edge or falling edge events, but not both.




Figure 24. External interrupt timing

### 3.13.6 eTPU timing Table 36. eTPU timing<sup>1</sup>

| Spec | Characteristic                  | Symbol            | Min            | Max | Unit                               |
|------|---------------------------------|-------------------|----------------|-----|------------------------------------|
| 1    | eTPU Input Channel Pulse Width  | t <sub>ICPW</sub> | 4              | —   | t <sub>CYC_ETPU</sub> <sup>2</sup> |
| 2    | eTPU Output Channel Pulse Width | t <sub>OCPW</sub> | 1 <sup>3</sup> | —   | t <sub>CYC_ETPU</sub> <sup>2</sup> |

- 1. eTPU timing specified at  $V_{DD}$  = 1.08 V to 1.32 V,  $V_{DDEH}$  = 3.0 V to 5.5 V,  $T_A$  =  $T_L$  to  $T_H$ , and  $C_L$  = 200 pF with SRC = 0b00.
- 2. For further information on  $_{tCYC\_ETPU}$ , see Table 3.
- 3. This specification does not include the rise and fall times. When calculating the minimum eTPU pulse width, include the rise and fall times defined in the slew rate control fields (SRC) of the pad configuration registers (PCR).




Figure 25. eTPU timing

### 3.13.7 eMIOS timing Table 37. eMIOS timing<sup>1</sup>

| Spec | Characteristic           | Symbol            | Min            | Max | Unit                              |
|------|--------------------------|-------------------|----------------|-----|-----------------------------------|
| 1    | eMIOS Input Pulse Width  | t <sub>MIPW</sub> | 4              | —   | t <sub>CYC_PER</sub> <sup>2</sup> |
| 2    | eMIOS Output Pulse Width | t <sub>MOPW</sub> | 1 <sup>3</sup> | —   | t <sub>CYC_PER</sub> <sup>2</sup> |

- 1. eMIOS timing specified at  $V_{DD}$  = 1.08 V to 1.32 V,  $V_{DDEH}$  = 3.0 V to 5.5 V,  $T_A$  =  $T_L$  to  $T_H$ , and  $C_L$  = 50 pF with SRC = 0b00.
- 2. For further information on  $t_{CYC_PER}$ , see Table 3.
- 3. This specification does not include the rise and fall times. When calculating the minimum eMIOS pulse width, include the rise and fall times defined in the slew rate control fields (SRC) of the pad configuration registers (PCR).




Figure 26. eMIOS timing

# 3.13.8 DSPI timing with CMOS and LVDS pads

NOTE

The DSPI in TSB mode with LVDS pads can be used to implement the Micro Second Channel (MSC) bus protocol.

DSPI channel frequency support is shown in Table 38. Timing specifications are shown in Table 39, Table 40, Table 41, Table 42, and Table 43.

|                    | DSPI use mode  |    |  |
|--------------------|--|----|--|
| CMOS (Master mode) | CMOS (Master mode) Full duplex – Classic timing (Table 39) |    |  |
|                    | Full duplex – Modified timing (Table 40)                   | 30 |  |
|                    | Output only mode (SCK/SOUT/PCS) (Table 39 and Table 40)    | 30 |  |
|                    | Output only mode TSB mode (SCK/SOUT/PCS) (Table 43)        | 30 |  |

Table 38. DSPI channel frequency support

Table continues on the next page ...

|                    | DSPI use mode   |    |  |
|--------------------|---|----|--|
| LVDS (Master mode) | DS (Master mode) Full duplex – Modified timing (Table 41) |    |  |
|                    | Output only mode TSB mode (SCK/SOUT/PCS) (Table 42)       | 40 |  |

1. Maximum usable frequency can be achieved if used with fastest configuration of the highest drive pads.

2. Maximum usable frequency does not take into account external device propagation delay.

### 3.13.8.1 DSPI master mode full duplex timing with CMOS and LVDS pads

### 3.13.8.1.1 DSPI CMOS Master Mode — Classic Timing Table 39. DSPI CMOS master classic timing (full duplex and output only) – MTFE = 0, CPHA = 0 or 1<sup>1</sup>

| # | Symbol            | Characteristic                    | Condition              | 2                      | Value                             | 3                       | Unit |
|---|-------------------|-----------------------------------|------------------------|------------------------|-----------------------------------|-------------------------|------|
| # | Symbol            | Characteristic                    | Pad drive <sup>4</sup> | Load (C <sub>L</sub> ) | Min                               | Max                     |      |
| 1 | t <sub>SCK</sub>  | SCK cycle time                    | PCR[SRC]=11b           | 25 pF                  | 33.0                              | _                       | ns   |
|   |                   |                                   | PCR[SRC]=10b           | 50 pF                  | 80.0                              | —                       |      |
|   |                   |                                   | PCR[SRC]=01b           | 50 pF                  | 200.0                             | —                       |      |
| 2 | t <sub>CSC</sub>  | PCS to SCK delay                  | PCR[SRC]=11b           | 25 pF                  | $(N^5 \times t_{SYS}^{, 6}) - 16$ | —                       | ns   |
|   |                   |                                   | PCR[SRC]=10b           | 50 pF                  | $(N^5 \times t_{SYS}^{, 6}) - 16$ | _                       |      |
|   |                   |                                   | PCR[SRC]=01b           | 50 pF                  | $(N^5 \times t_{SYS}^{, 6}) - 18$ | —                       |      |
|   |                   |                                   | PCS: PCR[SRC]=01b      | 50 pF                  | $(N^5 \times t_{SYS}^{, 6}) - 45$ | —                       |      |
|   |                   |                                   | SCK: PCR[SRC]=10b      |                        |                                   |                         |      |
| 3 | t <sub>ASC</sub>  | After SCK delay                   | PCR[SRC]=11b           | PCS: 0 pF              | $(M^7 \times t_{SYS}^{, 6}) - 35$ | —                       | ns   |
|   |                   |                                   |                        | SCK: 50 pF             |                                   |                         |      |
|   |                   |                                   | PCR[SRC]=10b           | PCS: 0 pF              | $(M^7 \times t_{SYS}^{, 6}) - 35$ |                         |      |
|   |                   |                                   |                        | SCK: 50 pF             |                                   |                         |      |
|   |                   |                                   | PCR[SRC]=01b           | PCS: 0 pF              | $(M^7 \times t_{SYS}^{, 6}) - 35$ |                         |      |
|   |                   |                                   |                        | SCK: 50 pF             |                                   |                         |      |
|   |                   |                                   | PCS: PCR[SRC]=01b      | PCS: 0 pF              | $(M^7 \times t_{SYS}^{, 6}) - 35$ |                         |      |
|   |                   |                                   | SCK: PCR[SRC]=10b      | SCK: 50 pF             |                                   |                         |      |
| 4 | t <sub>SDC</sub>  | SCK duty cycle <sup>8</sup>       | PCR[SRC]=11b           | 0 pF                   | 1/2t <sub>SCK</sub> – 2           | 1/2t <sub>SCK</sub> + 2 | ns   |
|   |                   |                                   | PCR[SRC]=10b           | 0 pF                   | 1/2t <sub>SCK</sub> – 2           | 1/2t <sub>SCK</sub> + 2 |      |
|   |                   |                                   | PCR[SRC]=01b           | 0 pF                   | 1/2t <sub>SCK</sub> – 5           | 1/2t <sub>SCK</sub> + 5 |      |
|   |                   |                                   | PCS strob              | e timing               |                                   |                         |      |
| 5 | t <sub>PCSC</sub> | PCSx to PCSS<br>time <sup>9</sup> | PCR[SRC]=10b           | 25 pF                  | 13.0                              | _                       | ns   |
| 6 | t <sub>PASC</sub> | PCSS to PCSx time <sup>9</sup>    | PCR[SRC]=10b           | 25 pF                  | 13.0                              | _                       | ns   |
| 1 |                   |                                   | SIN setu               | ip time                | •                                 |                         |      |

Table continues on the next page...

# Table 39. DSPI CMOS master classic timing (full duplex and output only) – MTFE = 0, CPHA = 0 or 1<sup>1</sup> (continued)

| #  | Symbol           | Characteristic                                       | Condition              | 2                      | Value | 9 <sup>3</sup> | Unit |
|----|------------------|--|------------------------|------------------------|-------|----------------|------|
| "  | Symbol           | Characteristic                                       | Pad drive <sup>4</sup> | Load (C <sub>L</sub> ) | Min   | Max            |      |
| 7  | t <sub>SUI</sub> | SIN setup time to                                    | PCR[SRC]=11b           | 25 pF                  | 29.0  | —              | ns   |
|    |                  | SCK <sup>10</sup>                                    | PCR[SRC]=10b           | 50 pF                  | 31.0  | —              |      |
|    |                  |  | PCR[SRC]=01b           | 50 pF                  | 62.0  | _              |      |
|    |                  |  | SIN hol                | d time                 |       | •              |      |
| 8  | t <sub>HI</sub>  | t <sub>HI</sub> SIN hold time from SCK <sup>10</sup> | PCR[SRC]=11b           | 0 pF                   | -1.0  | _              | ns   |
|    |                  |  | PCR[SRC]=10b           | 0 pF                   | -1.0  | _              |      |
|    |                  |  | PCR[SRC]=01b           | 0 pF                   | -1.0  |                |      |
|    |                  |  | SOUT data valid tim    | e (after SCK ed        | dge)  |                |      |
| 9  | t <sub>SUO</sub> | SOUT data valid                                      | PCR[SRC]=11b           | 25 pF                  | _     | 7.0            | ns   |
|    |                  | time from SCK <sup>11</sup>                          | PCR[SRC]=10b           | 50 pF                  | —     | 8.0            |      |
|    |                  |  | PCR[SRC]=01b           | 50 pF                  | _     | 18.0           |      |
|    |                  |  | SOUT data hold tim     | e (after SCK ec        | lge)  | ·              |      |
| 10 | t <sub>HO</sub>  | SOUT data hold                                       | PCR[SRC]=11b           | 25 pF                  | -9.0  | _              | ns   |
|    |                  | time after SCK <sup>11</sup>                         | PCR[SRC]=10b           | 50 pF                  | -10.0 | _              |      |
|    |                  |  | PCR[SRC]=01b           | 50 pF                  | -21.0 |                |      |

1. All output timing is worst case and includes the mismatching of rise and fall times of the output pads.

- 2. When a characteristic involves two signals, the pad drive and load conditions apply to each signal's pad, unless specified otherwise.
- 3. All timing values for output signals in this table are measured to 50% of the output voltage.
- 4. Pad drive is defined as the PCR[SRC] field setting in the SIU. Timing is guaranteed to same drive capabilities for all signals; mixing of pad drives may reduce operating speeds and may cause incorrect operation.
- 5. N is the number of clock cycles added to time between PCS assertion and SCK assertion and is software programmable using DSPI\_CTARx[PSSCK] and DSPI\_CTARx[CSSCK]. The minimum value is 2 cycles unless TSB mode or Continuous SCK clock mode is selected, in which case, N is automatically set to 0 clock cycles (PCS and SCK are driven by the same edge of DSPI\_CLKn).
- t<sub>SYS</sub> is the period of DSPI\_CLKn clock, the input clock to the DSPI module. Maximum frequency is 100 MHz (min t<sub>SYS</sub> = 10 ns).
- 7. M is the number of clock cycles added to time between SCK negation and PCS negation and is software programmable using DSPI\_CTARx[PASC] and DSPI\_CTARx[ASC]. The minimum value is 2 cycles unless TSB mode or Continuous SCK clock mode is selected, in which case, M is automatically set to 0 clock cycles (PCS and SCK are driven by the same edge of DSPI\_CLKn).
- 8. t<sub>SDC</sub> is only valid for even divide ratios. For odd divide ratios the fundamental duty cycle is not 50:50. For these odd divide ratios cases, the absolute spec number is applied as jitter/uncertainty to the nominal high time and low time.
- 9. PCSx and PCSS using same pad configuration.
- 10. Input timing assumes an input slew rate of 1 ns (10% 90%) and uses TTL / Automotive voltage thresholds.
- 11. SOUT Data Valid and Data hold are independent of load capacitance if SCK and SOUT load capacitances are the same value.




Figure 27. DSPI CMOS master mode – classic timing, CPHA = 0




Figure 28. DSPI CMOS master mode – classic timing, CPHA = 1




Figure 29. DSPI PCS strobe (PCSS) timing (master mode)

### 3.13.8.1.2 DSPI CMOS Master Mode – Modified Timing Table 40. DSPI CMOS master modified timing (full duplex and output only) – MTFE = 1, CPHA = 0 or 1<sup>1</sup>

| # | Symbol            | Characteristic                    | Condition              | 2                      | Value                             | 3                       | Unit |
|---|-------------------|-----------------------------------|------------------------|------------------------|-----------------------------------|-------------------------|------|
| # | Symbol            |                                   | Pad drive <sup>4</sup> | Load (C <sub>L</sub> ) | Min                               | Мах                     |      |
| 1 | t <sub>SCK</sub>  | SCK cycle time                    | PCR[SRC]=11b           | 25 pF                  | 33.0                              |                         | ns   |
|   |                   |                                   | PCR[SRC]=10b           | 50 pF                  | 80.0                              | _                       | 1    |
|   |                   |                                   | PCR[SRC]=01b           | 50 pF                  | 200.0                             | _                       | 1    |
| 2 | t <sub>CSC</sub>  | PCS to SCK delay                  | PCR[SRC]=11b           | 25 pF                  | $(N^5 \times t_{SYS}^{, 6}) - 16$ | _                       | ns   |
|   |                   |                                   | PCR[SRC]=10b           | 50 pF                  | $(N^5 \times t_{SYS}^{, 6}) - 16$ | _                       |      |
|   |                   |                                   | PCR[SRC]=01b           | 50 pF                  | $(N^5 \times t_{SYS}^{, 6}) - 18$ | _                       | 1    |
|   |                   |                                   | PCS: PCR[SRC]=01b      | 50 pF                  | $(N^5 \times t_{SYS}^{, 6}) - 45$ |                         |      |
|   |                   |                                   | SCK: PCR[SRC]=10b      |                        |                                   |                         |      |
| 3 | t <sub>ASC</sub>  | After SCK delay                   | PCR[SRC]=11b           | PCS: 0 pF              | $(M^7 \times t_{SYS}, 6) - 35$    | _                       | ns   |
|   |                   |                                   |                        | SCK: 50 pF             |                                   |                         |      |
|   |                   |                                   | PCR[SRC]=10b           | PCS: 0 pF              | $(M^7 \times t_{SYS}^{, 6}) - 35$ |                         |      |
|   |                   |                                   |                        | SCK: 50 pF             |                                   |                         |      |
|   |                   |                                   | PCR[SRC]=01b           | PCS: 0 pF              | $(M^7 \times t_{SYS}^{, 6}) - 35$ |                         | -    |
|   |                   |                                   |                        |                        | SCK: 50 pF                        |                         |      |
|   |                   |                                   | PCS: PCR[SRC]=01b      | PCS: 0 pF              | $(M^7 \times t_{SYS}^{, 6}) - 35$ |                         | -    |
|   |                   |                                   | SCK: PCR[SRC]=10b      | SCK: 50 pF             |                                   |                         |      |
| 4 | t <sub>SDC</sub>  | SCK duty cycle <sup>8</sup>       | PCR[SRC]=11b           | 0 pF                   | 1/2t <sub>SCK</sub> – 2           | 1/2t <sub>SCK</sub> + 2 | ns   |
|   |                   |                                   | PCR[SRC]=10b           | 0 pF                   | 1/2t <sub>SCK</sub> – 2           | 1/2t <sub>SCK</sub> + 2 |      |
|   |                   |                                   | PCR[SRC]=01b           | 0 pF                   | 1/2t <sub>SCK</sub> – 5           | 1/2t <sub>SCK</sub> + 5 |      |
|   |                   |                                   | PCS strob              | e timing               |                                   |                         |      |
| 5 | t <sub>PCSC</sub> | PCSx to PCSS<br>time <sup>9</sup> | PCR[SRC]=10b           | 25 pF                  | 13.0                              |                         | ns   |
| 6 | t <sub>PASC</sub> | PCSS to PCSx time <sup>9</sup>    | PCR[SRC]=10b           | 25 pF                  | 13.0                              |                         | ns   |
|   |                   | 1                                 | SIN setu               | p time                 | ļ                                 |                         | -1   |

Table continues on the next page...

### Table 40. DSPI CMOS master modified timing (full duplex and output only) – MTFE = 1, CPHA = 0 or $1^1$ (continued)

| #  | Cumhal             | Oberesteristic                     | Conditio               | 1 <sup>2</sup>         | Value                                 | 3                                    | Unit |
|----|--------------------|------------------------------------|------------------------|------------------------|---------------------------------------|--------------------------------------|------|
| #  | Symbol             | Characteristic -                   | Pad drive <sup>4</sup> | Load (C <sub>L</sub> ) | Min                                   | Мах                                  |      |
| 7  | t <sub>SUI</sub>   | SIN setup time to                  | PCR[SRC]=11b           | 25 pF                  | $29 - (P^{11} \times t_{SYS}^{, 6})$  |                                      | ns   |
|    |                    | SCK<br>CPHA = 0 <sup>10</sup>      | PCR[SRC]=10b           | 50 pF                  | $31 - (P^{11} \times t_{SYS}, 6)$     |                                      |      |
|    |                    |                                    | PCR[SRC]=01b           | 50 pF                  | $62 - (P^{11} \times t_{SYS}, 6)$     |                                      | 1    |
|    |                    | SIN setup time to                  | PCR[SRC]=11b           | 25 pF                  | 29.0                                  | _                                    | ns   |
|    |                    | SCK                                | PCR[SRC]=10b           | 50 pF                  | 31.0                                  | _                                    | 1    |
|    |                    | CPHA = 1 <sup>10</sup>             | PCR[SRC]=01b           | 50 pF                  | 62.0                                  | _                                    | 1    |
|    |                    | <u> </u>                           | SIN ho                 | ld time                |                                       |                                      |      |
| 8  | t <sub>HI</sub> 12 | SIN hold time from                 | PCR[SRC]=11b           | 0 pF                   | $-1 + (P^{11} \times t_{SYS}, ^{6})$  | _                                    | ns   |
|    |                    | SCK                                | PCR[SRC]=10b           | 0 pF                   | $-1 + (P^{11} \times t_{SYS}^{, 6})$  | _                                    | 1    |
|    |                    | $CPHA = 0^{10}$ SIN hold time from | PCR[SRC]=01b           | 0 pF                   | $-1 + (P^{11} \times t_{SYS}^{, 6})$  | —                                    | 1    |
|    |                    |                                    | PCR[SRC]=11b           | 0 pF                   | -1.0                                  | —                                    | ns   |
|    |                    | SCK                                | PCR[SRC]=10b           | 0 pF                   | -1.0                                  | —                                    | 1    |
|    |                    | CPHA = 1 <sup>10</sup>             | PCR[SRC]=01b           | 0 pF                   | -1.0                                  | —                                    | 1    |
|    |                    | •                                  | SOUT data valid tir    | ne (after SCK e        | dge)                                  |                                      |      |
| 9  | t <sub>SUO</sub>   | SOUT data valid time from SCK      | PCR[SRC]=11b           | 25 pF                  | —                                     | 7.0 + t <sub>SYS</sub> <sup>6</sup>  | ns   |
|    |                    |                                    | PCR[SRC]=10b           | 50 pF                  | —                                     | 8.0 + t <sub>SYS</sub> <sup>6</sup>  |      |
|    |                    | CPHA = 0 <sup>13</sup>             | PCR[SRC]=01b           | 50 pF                  | —                                     | 18.0 + t <sub>SYS</sub> <sup>6</sup> | 1    |
|    |                    | SOUT data valid                    | PCR[SRC]=11b           | 25 pF                  | —                                     | 7.0                                  | ns   |
|    |                    | time from SCK                      | PCR[SRC]=10b           | 50 pF                  | —                                     | 8.0                                  |      |
|    |                    | CPHA = 1 <sup>13</sup>             | PCR[SRC]=01b           | 50 pF                  | —                                     | 18.0                                 | 1    |
|    |                    |                                    | SOUT data hold tin     | ne (after SCK ed       | dge)                                  |                                      |      |
| 10 | t <sub>HO</sub>    | SOUT data hold                     | PCR[SRC]=11b           | 25 pF                  | $-9.0 + t_{SYS}^{6}$                  | _                                    | ns   |
|    |                    | time after SCK                     | PCR[SRC]=10b           | 50 pF                  | $-10.0 + t_{SYS}^{6}$                 | _                                    | 1    |
|    |                    | CPHA = 0 <sup>13</sup>             | PCR[SRC]=01b           | 50 pF                  | -21.0 + t <sub>SYS</sub> <sup>6</sup> | _                                    | 1    |
|    |                    | SOUT data hold                     | PCR[SRC]=11b           | 25 pF                  | -9.0                                  |                                      | ns   |
|    |                    | time after SCK                     | PCR[SRC]=10b           | 50 pF                  | -10.0                                 | —                                    | 1    |
|    |                    | CPHA = 1 <sup>13</sup>             | PCR[SRC]=01b           | 50 pF                  | -21.0                                 |                                      | 1    |

1. All output timing is worst case and includes the mismatching of rise and fall times of the output pads.

2. When a characteristic involves two signals, the pad drive and load conditions apply to each signal's pad, unless specified otherwise.

- 3. All timing values for output signals in this table are measured to 50% of the output voltage.
- 4. Pad drive is defined as the PCR[SRC] field setting in the SIU. Timing is guaranteed to same drive capabilities for all signals; mixing of pad drives may reduce operating speeds and may cause incorrect operation.
- 5. N is the number of clock cycles added to time between PCS assertion and SCK assertion and is software programmable using DSPI\_CTARx[PSSCK] and DSPI\_CTARx[CSSCK]. The minimum value is 2 cycles unless TSB mode or Continuous SCK clock mode is selected, in which case, N is automatically set to 0 clock cycles (PCS and SCK are driven by the same edge of DSPI\_CLKn).
- t<sub>SYS</sub> is the period of DSPI\_CLKn clock, the input clock to the DSPI module. Maximum frequency is 100 MHz (min t<sub>SYS</sub> = 10 ns).
- 7. M is the number of clock cycles added to time between SCK negation and PCS negation and is software programmable using DSPI\_CTARx[PASC] and DSPI\_CTARx[ASC]. The minimum value is 2 cycles unless TSB mode or Continuous SCK

clock mode is selected, in which case, M is automatically set to 0 clock cycles (PCS and SCK are driven by the same edge of DSPI\_CLKn).

- 8. t<sub>SDC</sub> is only valid for even divide ratios. For odd divide ratios the fundamental duty cycle is not 50:50. For these odd divide ratios cases, the absolute spec number is applied as jitter/uncertainty to the nominal high time and low time.
- 9. PCSx and PCSS using same pad configuration.
- 10. Input timing assumes an input slew rate of 1 ns (10% 90%) and uses TTL / Automotive voltage thresholds.
- 11. P is the number of clock cycles added to delay the DSPI input sample point and is software programmable using DSPI\_MCR[SMPL\_PT]. The value must be 0, 1 or 2. If the baud rate divide ratio is /2 or /3, this value is automatically set to 1.
- 12. The 0 pF load condition given in the DSPI AC timing applies to theoretical worst-case hold timing. This guarantees worstcase operation, and additional margin can be achieved in the applications by applying a realistic load.
- 13. SOUT Data Valid and Data hold are independent of load capacitance if SCK and SOUT load capacitances are the same value.




Figure 30. DSPI CMOS master mode – modified timing, CPHA = 0




Figure 31. DSPI CMOS master mode – modified timing, CPHA = 1




Figure 32. DSPI PCS strobe (PCSS) timing (master mode)

### 3.13.8.1.3 DSPI LVDS Master Mode – Modified Timing Table 41. DSPI LVDS master timing – full duplex – modified transfer format (MTFE = 1), CPHA = 0 or 1

| # | Symbol           | Characteristic   | Conditio               | on <sup>1</sup>             | Value                             | 2   | Unit |
|---|------------------|------------------|------------------------|-----------------------------|-----------------------------------|-----|------|
| π | Symbol           | Characteristic   | Pad drive <sup>3</sup> | Load (C <sub>L</sub> )      | Min                               | Max |      |
| 1 | t <sub>SCK</sub> | SCK cycle time   | LVDS                   | 15 pF to 25 pF differential | 33.3                              |     | ns   |
| 2 | t <sub>CSC</sub> | PCS to SCK delay | PCS: PCR[SRC]=11b      | 25 pF                       | $(N^4 \times t_{SYS}, 5) - 10$    |     | ns   |
|   |                  | (LVDS SCK)       | PCS: PCR[SRC]=10b      | 50 pF                       | $(N^4 \times t_{SYS}^{, 5}) - 10$ |     | ns   |
|   |                  |                  | PCS: PCR[SRC]=01b      | 50 pF                       | $(N^4 \times t_{SYS}^{, 5}) - 32$ |     | ns   |

Table continues on the next page ...

### Table 41. DSPI LVDS master timing – full duplex – modified transfer format (MTFE = 1), CPHA = 0 or 1 (continued)

| "  | 0h.al            | Ohanastanistia                | Conditio               | on <sup>1</sup>                | Value                            | ,2                                  | 11   |
|----|------------------|-------------------------------|------------------------|--------------------------------|----------------------------------|-------------------------------------|------|
| #  | Symbol           | Characteristic                | Pad drive <sup>3</sup> | Load (C <sub>L</sub> )         | Min                              | Мах                                 | Unit |
| 3  | t <sub>ASC</sub> | After SCK delay               | PCS: PCR[SRC]=11b      | PCS: 0 pF                      | $(M^6 \times t_{SYS}^{, 5}) - 8$ |                                     | ns   |
|    |                  | (LVDS SCK)                    |                        | SCK: 25 pF                     |                                  |                                     |      |
|    |                  |                               | PCS: PCR[SRC]=10b      | PCS: 0 pF                      | $(M^6 \times t_{SYS}, 5) - 8$    | _                                   | ns   |
|    |                  |                               |                        | SCK: 25 pF                     |                                  |                                     |      |
|    |                  |                               | PCS: PCR[SRC]=01b      | PCS: 0 pF                      | $(M^6 \times t_{SYS}^{, 5}) - 8$ | _                                   | ns   |
|    |                  |                               |                        | SCK: 25 pF                     |                                  |                                     |      |
| 4  | t <sub>SDC</sub> | SCK duty cycle <sup>7</sup>   | LVDS                   | 15 pF to 25 pF<br>differential | 1/2t <sub>SCK</sub> – 2          | 1/2t <sub>SCK</sub> +2              | ns   |
| 7  | t <sub>SUI</sub> |                               |                        | SIN setup time                 |                                  |                                     |      |
|    |                  | SIN setup time to SCK         | LVDS                   | 15 pF to 25 pF<br>differential | $23 - (P^9 \times t_{SYS}, 5)$   |                                     | ns   |
|    |                  | CPHA = 0 <sup>8</sup>         |                        |                                |                                  |                                     |      |
|    |                  | SIN setup time to SCK         | LVDS                   | 15 pF to 25 pF<br>differential | 23                               |                                     | ns   |
|    |                  | CPHA = 1 <sup>8</sup>         |                        |                                |                                  |                                     |      |
| 8  | t <sub>HI</sub>  |                               |                        | SIN hold time                  |                                  |                                     | _!   |
|    |                  | SIN hold time from SCK        | LVDS                   | 0 pF differential              | $-1 + (P^9 \times t_{SYS}, 5)$   |                                     | ns   |
|    |                  | CPHA = 0 <sup>8</sup>         |                        |                                |                                  |                                     |      |
|    |                  | SIN hold time from SCK        | LVDS                   | 0 pF differential              | -1                               |                                     | ns   |
|    |                  | CPHA = 1 <sup>8</sup>         |                        |                                |                                  |                                     |      |
| 9  | t <sub>SUO</sub> |                               | SOUT data              | a valid time (after            | SCK edge)                        |                                     |      |
|    |                  | SOUT data valid time from SCK | LVDS                   | 15 pF to 25 pF<br>differential | _                                | 7.0 + t <sub>SYS</sub> <sup>5</sup> | ns   |
|    |                  | CPHA = 0 <sup>10</sup>        |                        |                                |                                  |                                     |      |
|    |                  | SOUT data valid time from SCK | LVDS                   | 15 pF to 25 pF<br>differential | _                                | 7.0                                 | ns   |
|    |                  | CPHA = 1 <sup>10</sup>        |                        |                                |                                  |                                     |      |
| 10 | t <sub>HO</sub>  |                               | SOUT dat               | a hold time (after             | SCK edge)                        |                                     | -1   |
|    |                  | SOUT data hold time after SCK | LVDS                   | 15 pF to 25 pF<br>differential | $-7.5 + t_{SYS}^{5}$             | _                                   | ns   |
|    |                  | CPHA = 0 <sup>10</sup>        |                        |                                |                                  |                                     |      |
|    |                  | SOUT data hold time after SCK | LVDS                   | 15 pF to 25 pF<br>differential | -7.5                             | _                                   | ns   |
|    |                  | CPHA = 1 <sup>10</sup>        |                        |                                |                                  |                                     |      |

1. When a characteristic involves two signals, the pad drive and load conditions apply to each signal's pad, unless specified otherwise.

2. All timing values for output signals in this table are measured to 50% of the output voltage.

3. Pad drive is defined as the PCR[SRC] field setting in the SIU. Timing is guaranteed to same drive capabilities for all signals; mixing of pad drives may reduce operating speeds and may cause incorrect operation.

- 4. N is the number of clock cycles added to time between PCS assertion and SCK assertion and is software programmable using DSPI\_CTARx[PSSCK] and DSPI\_CTARx[CSSCK]. The minimum value is 2 cycles unless TSB mode or Continuous SCK clock mode is selected, in which case, N is automatically set to 0 clock cycles (PCS and SCK are driven by the same edge of DSPI\_CLKn).
- 5. t<sub>SYS</sub> is the period of DSPI\_CLKn clock, the input clock to the DSPI module. Maximum frequency is 100 MHz (min tSYS = 10 ns).
- 6. M is the number of clock cycles added to time between SCK negation and PCS negation and is software programmable using DSPI\_CTARx[PASC] and DSPI\_CTARx[ASC]. The minimum value is 2 cycles unless TSB mode or Continuous SCK clock mode is selected, in which case, M is automatically set to 0 clock cycles (PCS and SCK are driven by the same edge of DSPI\_CLKn).
- 7. t<sub>SDC</sub> is only valid for even divide ratios. For odd divide ratios the fundamental duty cycle is not 50:50. For these odd divide ratios cases, the absolute spec number is applied as jitter/uncertainty to the nominal high time and low time.
- 8. Input timing assumes an input slew rate of 1 ns (10% 90%) and LVDS differential voltage = ±100 mV.
- P is the number of clock cycles added to delay the DSPI input sample point and is software programmable using DSPI\_MCR[SMPL\_PT]. The value must be 0, 1 or 2. If the baud rate divide ratio is /2 or /3, this value is automatically set to 1.
- 10. SOUT Data Valid and Data hold are independent of load capacitance if SCK and SOUT load capacitances are the same value.




Figure 33. DSPI LVDS master mode – modified timing, CPHA = 0




Figure 34. DSPI LVDS master mode – modified timing, CPHA = 1

### 3.13.8.1.4 DSPI Master Mode – Output Only Table 42. DSPI LVDS master timing — output only — timed serial bus mode TSB = 1 or ITSB = 1, CPOL = 0 or 1, continuous SCK clock<sup>1, 2</sup>

| # | Symbol           | Characteristic   | Condit                 | tion <sup>3</sup>              | Val                     | ue <sup>4</sup>         | Unit |
|---|------------------|--|------------------------|--------------------------------|-------------------------|-------------------------|------|
| # | Symbol           | Characteristic   | Pad drive <sup>5</sup> | Load (C <sub>L</sub> )         | Min                     | Max                     |      |
| 1 | t <sub>SCK</sub> | SCK cycle time   | LVDS                   | 15 pF to 50 pF<br>differential | 25                      | —                       | ns   |
| 2 | t <sub>CSV</sub> | PCS valid after SCK <sup>6</sup>                             | PCR[SRC]=11b           | 25 pF                          | —                       | 8                       | ns   |
|   |                  | (SCK with 50 pF<br>differential load cap.)                   | PCR[SRC]=10b           | 50 pF                          |                         | 12                      | ns   |
| 3 | t <sub>CSH</sub> | PCS hold after SCK <sup>6</sup>                              | PCR[SRC]=11b           | 0 pF                           | -4.0                    |                         | ns   |
|   |                  | (SCK with 50 pF<br>differential load cap.)                   | PCR[SRC]=10b           | 0 pF                           | -4.0                    | _                       | ns   |
| 4 | t <sub>SDC</sub> | SCK duty cycle (SCK<br>with 50 pF differential<br>load cap.) | LVDS                   | 15 pF to 50 pF<br>differential | 1/2t <sub>SCK</sub> – 2 | 1/2t <sub>SCK</sub> + 2 | ns   |
|   |                  | •  | SOUT data valid time   | (after SCK edge)               |                         |                         |      |
| 5 | t <sub>SUO</sub> | SOUT data valid time from SCK <sup>7</sup>                   | LVDS                   | 15 pF to 50 pF<br>differential |                         | 6                       | ns   |
|   |                  |  | SOUT data hold time    | (after SCK edge)               |                         |                         |      |
| 6 | t <sub>HO</sub>  | SOUT data hold time after SCK <sup>7</sup>                   | LVDS                   | 15 pF to 50 pF<br>differential | -7.0                    |                         | ns   |

<sup>1.</sup> All DSPI timing specifications apply to pins when using LVDS pads for SCK and SOUT and CMOS pad for PCS with pad driver strength as defined. Timing may degrade for weaker output drivers.

- 2. TSB = 1 or ITSB = 1 automatically selects MTFE = 1 and CPHA = 1.
- 3. When a characteristic involves two signals, the pad drive and load conditions apply to each signal's pad, unless specified otherwise.

- 4. All timing values for output signals in this table are measured to 50% of the output voltage.
- 5. Pad drive is defined as the PCR[SRC] field setting in the SIU. Timing is guaranteed to same drive capabilities for all signals; mixing of pad drives may reduce operating speeds and may cause incorrect operation.
- 6. With TSB mode or Continuous SCK clock mode selected, PCS and SCK are driven by the same edge of DSPI\_CLKn. This timing value is due to pad delays and signal propagation delays.
- 7. SOUT Data Valid and Data hold are independent of load capacitance if SCK and SOUT load capacitances are the same value.

# Table 43. DSPI CMOS master timing – output only – timed serial bus mode TSB = 1 or ITSB = 1, CPOL = 0 or 1, continuous SCK clock $^{1, 2}$

| #  | Cumbal           | Ohavaataviatia                   | Condition                | 3                      | Va                      | lue <sup>4</sup>        | Unit |
|----|------------------|----------------------------------|--------------------------|------------------------|-------------------------|-------------------------|------|
| #  | Symbol           | Characteristic                   | Pad drive <sup>5</sup>   | Load (C <sub>L</sub> ) | Min                     | Max                     |      |
| 1  | t <sub>SCK</sub> | SCK cycle time                   | PCR[SRC]=11b             | 25 pF                  | 33.0                    | —                       | ns   |
|    |                  |                                  | PCR[SRC]=10b             | 50 pF                  | 80.0                    | —                       | ns   |
|    |                  |                                  | PCR[SRC]=01b             | 50 pF                  | 200.0                   | —                       | ns   |
| 2  | t <sub>CSV</sub> | PCS valid after SCK <sup>6</sup> | PCR[SRC]=11b             | 25 pF                  | 7                       | —                       | ns   |
|    |                  |                                  | PCR[SRC]=10b             | 50 pF                  | 8                       | —                       | ns   |
|    |                  |                                  | PCR[SRC]=01b             | 50 pF                  | 18                      | —                       | ns   |
|    |                  |                                  | PCS: PCR[SRC]=01b        | 50 pF                  | 45                      | —                       | ns   |
|    |                  |                                  | SCK: PCR[SRC]=10b        |                        |                         |                         |      |
| 3  | t <sub>CSH</sub> | PCS hold after SCK <sup>6</sup>  | PCR[SRC]=11b             | PCS: 0 pF              | -14                     | —                       | ns   |
|    |                  |                                  |                          | SCK: 50 pF             |                         |                         |      |
|    |                  |                                  | PCR[SRC]=10b             | PCS: 0 pF              | -14                     | —                       | ns   |
|    |                  |                                  |                          | SCK: 50 pF             |                         |                         |      |
|    |                  |                                  | PCR[SRC]=01b             | PCS: 0 pF              | -33                     | _                       | ns   |
|    |                  |                                  |                          | SCK: 50 pF             |                         |                         |      |
|    |                  |                                  | PCS: PCR[SRC]=01b        | PCS: 0 pF              | -35                     | _                       | ns   |
|    |                  |                                  | SCK: PCR[SRC]=10b        | SCK: 50 pF             |                         |                         |      |
| 4  | t <sub>SDC</sub> | SCK duty cycle <sup>7</sup>      | PCR[SRC]=11b             | 0 pF                   | 1/2t <sub>SCK</sub> – 2 | 1/2t <sub>SCK</sub> + 2 | ns   |
|    |                  |                                  | PCR[SRC]=10b             | 0 pF                   | 1/2t <sub>SCK</sub> – 2 | 1/2t <sub>SCK</sub> + 2 | ns   |
|    |                  |                                  | PCR[SRC]=01b             | 0 pF                   | 1/2t <sub>SCK</sub> – 5 | 1/2t <sub>SCK</sub> + 5 | ns   |
|    |                  |                                  | SOUT data valid time (af | ter SCK edge)          |                         | 1                       |      |
| 9  | t <sub>suo</sub> | SOUT data valid time             | PCR[SRC]=11b             | 25 pF                  | _                       | 7.0                     | ns   |
|    |                  | from SCK                         | PCR[SRC]=10b             | 50 pF                  |                         | 8.0                     | ns   |
|    |                  | CPHA = 1 <sup>8</sup>            | PCR[SRC]=01b             | 50 pF                  | —                       | 18.0                    | ns   |
|    |                  |                                  | SOUT data hold time (aft | er SCK edge)           |                         |                         | ·    |
| 10 | t <sub>HO</sub>  | SOUT data hold time              | PCR[SRC]=11b             | 25 pF                  | -9.0                    | —                       | ns   |
|    |                  | after SCK                        | PCR[SRC]=10b             | 50 pF                  | -10.0                   | —                       | ns   |
|    |                  | CPHA = 1 <sup>8</sup>            | PCR[SRC]=01b             | 50 pF                  | -21.0                   | _                       | ns   |

1. TSB = 1 or ITSB = 1 automatically selects MTFE = 1 and CPHA = 1.

- 2. All output timing is worst case and includes the mismatching of rise and fall times of the output pads.
- 3. When a characteristic involves two signals, the pad drive and load conditions apply to each signal's pad, unless specified otherwise.
- 4. All timing values for output signals in this table are measured to 50% of the output voltage.

- 5. Pad drive is defined as the PCR[SRC] field setting in the SIU. Timing is guaranteed to same drive capabilities for all signals; mixing of pad drives may reduce operating speeds and may cause incorrect operation.
- 6. With TSB mode or Continuous SCK clock mode selected, PCS and SCK are driven by the same edge of DSPI\_CLKn. This timing value is due to pad delays and signal propagation delays.
- t<sub>SDC</sub> is only valid for even divide ratios. For odd divide ratios the fundamental duty cycle is not 50:50. For these odd divide ratios cases, the absolute spec number is applied as jitter/uncertainty to the nominal high time and low time.
- 8. SOUT Data Valid and Data hold are independent of load capacitance if SCK and SOUT load capacitances are the same value.




Figure 35. DSPI LVDS and CMOS master timing – output only – modified transfer format MTFE = 1, CHPA = 1

## 3.13.9 FEC timing

### 3.13.9.1 MII receive signal timing (RXD[3:0], RX\_DV, and RX\_CLK)

The receiver functions correctly up to a RX\_CLK maximum frequency of 25 MHz +1%. There is no minimum frequency requirement. The system clock frequency must be at least equal to or greater than the RX\_CLK frequency.

| Symbol | Characteristic                  | Va  | lue | Unit          |
|--------|---------------------------------|-----|-----|---------------|
| Symbol |                                 | Min | Мах | Onit          |
| M1     | RXD[3:0], RX_DV to RX_CLK setup | 5   | —   | ns            |
| M2     | RX_CLK to RXD[3:0], RX_DV hold  | 5   | —   | ns            |
| M3     | RX_CLK pulse width high         | 35% | 65% | RX_CLK period |
| M4     | RX_CLK pulse width low          | 35% | 65% | RX_CLK period |

 Table 44. MII receive signal timing<sup>1</sup>

1. All timing specifications valid to the pad input levels defined in I/O pad current specifications.




Figure 36. MII receive signal timing diagram

## 3.13.9.2 MII transmit signal timing (TXD[3:0], TX\_EN, and TX\_CLK)

The transmitter functions correctly up to a TX\_CLK maximum frequency of 25 MHz +1%. There is no minimum frequency requirement. The system clock frequency must be at least equal to or greater than the TX\_CLK frequency.

The transmit outputs (TXD[3:0], TX\_EN) can be programmed to transition from either the rising or falling edge of TX\_CLK, and the timing is the same in either case. This options allows the use of noncompliant MII PHYs.

Refer to the *MPC5775E Microcontroller Reference Manual's* Fast Ethernet Controller (FEC) chapter for details of this option and how to enable it.

| Symbol | Characteristic                    | Va  | lue <sup>2</sup> | Unit          |  |
|--------|-----------------------------------|-----|------------------|---------------|--|
| Symbol |                                   | Min | Max              | Unit          |  |
| M5     | TX_CLK to TXD[3:0], TX_EN invalid | 4.5 | _                | ns            |  |
| M6     | TX_CLK to TXD[3:0], TX_EN valid   | _   | 25               | ns            |  |
| M7     | TX_CLK pulse width high           | 35% | 65%              | TX_CLK period |  |
| M8     | TX_CLK pulse width low            | 35% | 65%              | TX_CLK period |  |

 Table 45. MII transmit signal timing<sup>1</sup>

1. All timing specifications valid to the pad input levels defined in I/O pad specifications.

 Output parameters are valid for C<sub>L</sub> = 25 pF, where C<sub>L</sub> is the external load to the device. The internal package capacitance is accounted for, and does not need to be subtracted from the 25 pF value.




Figure 37. MII transmit signal timing diagram

### 3.13.9.3 MII async inputs signal timing (CRS) Table 46. MII async inputs signal timing

| Symbol | Characteristic          |     | Value | Unit          |  |
|--------|-------------------------|-----|-------|---------------|--|
| Symbol |                         | Min | Max   | Onit          |  |
| M9     | CRS minimum pulse width | 1.5 | —     | TX_CLK period |  |



Figure 38. MII async inputs timing diagram

### 3.13.9.4 MII and RMII serial management channel timing (MDIO and MDC)

The FEC functions correctly with a maximum MDC frequency of 2.5 MHz.

 Table 47. MII serial management channel timing<sup>1</sup>

| Symbol | Characteristic  | Va  | lue <sup>2</sup> | Unit       |
|--------|---|-----|------------------|------------|
| Symbol |   | Min | Max              | Onit       |
| M10    | MDC falling edge to MDIO output invalid (minimum propagation delay) | 0   | _                | ns         |
| M11    | MDC falling edge to MDIO output valid (max prop delay)              | —   | 25               | ns         |
| M12    | MDIO (input) to MDC rising edge setup                               | 10  | —                | ns         |
| M13    | MDIO (input) to MDC rising edge hold                                | 0   | —                | ns         |
| M14    | MDC pulse width high  | 40% | 60%              | MDC period |
| M15    | MDC pulse width low   | 40% | 60%              | MDC period |

1. All timing specifications valid to the pad input levels defined in I/O pad specifications.

2. Output parameters are valid for  $C_L = 25 \text{ pF}$ , where  $C_L$  is the external load to the device. The internal package capacitance is accounted for, and does not need to be subtracted from the 25 pF value

**Electrical characteristics** 




Figure 39. MII serial management channel timing diagram

# 3.13.9.5 RMII receive signal timing (RXD[1:0], CRS\_DV)

The receiver functions correctly up to a REF\_CLK maximum frequency of 50 MHz +1%. There is no minimum frequency requirement. The system clock frequency must be at least equal to or greater than the RX\_CLK frequency, which is half that of the REF\_CLK frequency.

| Table 48. | RMII | receive | signal | timing <sup>1</sup> |
|-----------|------|---------|--------|---------------------|
|-----------|------|---------|--------|---------------------|

| Symbol | Characteristic                    | Value |     | Unit           |
|--------|-----------------------------------|-------|-----|----------------|
| Symbol | Characteristic                    | Min   | Мах | Onic           |
| R1     | RXD[1:0], CRS_DV to REF_CLK setup | 4     | —   | ns             |
| R2     | REF_CLK to RXD[1:0], CRS_DV hold  | 2     | _   | ns             |
| R3     | REF_CLK pulse width high          | 35%   | 65% | REF_CLK period |
| R4     | REF_CLK pulse width low           | 35%   | 65% | REF_CLK period |

1. All timing specifications valid to the pad input levels defined in I/O pad specifications.




Figure 40. RMII receive signal timing diagram

### 3.13.9.6 RMII transmit signal timing (TXD[1:0], TX\_EN)

The transmitter functions correctly up to a REF\_CLK maximum frequency of 50 MHz + 1%. There is no minimum frequency requirement. The system clock frequency must be at least equal to or greater than the TX\_CLK frequency, which is half that of the REF\_CLK frequency.

The transmit outputs (TXD[1:0], TX\_EN) can be programmed to transition from either the rising or falling edge of REF\_CLK, and the timing is the same in either case. This options allows the use of non-compliant RMII PHYs.

| Symbol | Characteristic                     | Va  | lue <sup>2</sup> | Unit           |  |
|--------|------------------------------------|-----|------------------|----------------|--|
| Symbol |                                    | Min | Мах              | Unit           |  |
| R5     | REF_CLK to TXD[1:0], TX_EN invalid | 2   | —                | ns             |  |
| R6     | REF_CLK to TXD[1:0], TX_EN valid   | _   | 16               | ns             |  |
| R7     | REF_CLK pulse width high           | 35% | 65%              | REF_CLK period |  |
| R8     | REF_CLK pulse width low            | 35% | 65%              | REF_CLK period |  |

 Table 49. RMII transmit signal timing<sup>1</sup>

1. All timing specifications valid to the pad input levels defined in I/O pad specifications.

 Output parameters are valid for C<sub>L</sub> = 25 pF, where C<sub>L</sub> is the external load to the device. The internal package capacitance is accounted for, and does not need to be subtracted from the 25 pF value.




Figure 41. RMII transmit signal timing diagram

# 4 Package information

To find the package drawing for each package, go to http://www.nxp.com and perform a keyword search for the drawing's document number:

| If you want the drawing for this package | Then use this document number |
|--|-------------------------------|
| 416-ball MAPBGA                          | 98ASA00562D                   |

# 4.1 Thermal characteristics

 Table 50.
 Thermal characteristics, 416-ball MAPBGA package

| Characteristic   | Symbol            | Value | Unit |
|--|-------------------|-------|------|
| Junction to Ambient <sup>1, 2</sup> Natural Convection (Single layer board)    | R <sub>OJA</sub>  | 28.8  | °C/W |
| Junction to Ambient <sup>1, 3</sup> Natural Convection (Four layer board 2s2p) | R <sub>OJA</sub>  | 19.6  | °C/W |
| Junction to Ambient (@200 ft./min., Single layer board)                        | R <sub>OJMA</sub> | 21.3  | °C/W |
| Junction to Ambient (@200 ft./min., Four layer board 2s2p)                     | R <sub>OJMA</sub> | 15.1  | °C/W |
| Junction to Board <sup>4</sup>   | R <sub>OJB</sub>  | 9.5   | °C/W |
| Junction to Case <sup>5</sup>  | R <sub>OJC</sub>  | 4.8   | °C/W |
| Junction to Package Top <sup>6</sup> Natural Convection                        | Ψ <sub>JT</sub>   | 0.2   | °C/W |

- 1. Junction temperature is a function of on-chip power dissipation, package thermal resistance, mounting site (board) temperature, ambient temperature, air flow, power dissipation of other components on the board, and board thermal resistance.
- 2. Per JEDEC JESD51-2 with the single layer board horizontal. Board meets JESD51-9 specification.
- 3. Per JEDEC JESD51-6 with the board horizontal.
- 4. Thermal resistance between the die and the printed circuit board per JEDEC JESD51-8. Board temperature is measured on the top surface of the board near the package.
- 5. Indicates the average thermal resistance between the die and the case top surface as measured by the cold plate method (MIL SPEC-883 Method 1012.1) with the cold plate temperature used for the case temperature.

#### Package information

6. Thermal characterization parameter indicating the temperature difference between package top and the junction temperature per JEDEC JESD51-2.

## 4.1.1 General notes for thermal characteristics

An estimation of the chip junction temperature, T<sub>J</sub>, can be obtained from the equation:

$$T_J = T_A + \left( R_{\theta JA} * P_D \right)$$

where:

 $T_A$  = ambient temperature for the package (°C)

 $R_{\Theta JA}$  = junction-to-ambient thermal resistance (°C/W)

 $P_D$  = power dissipation in the package (W)

The thermal resistance values used are based on the JEDEC JESD51 series of standards to provide consistent values for estimations and comparisons. The difference between the values determined for the single-layer (1s) board compared to a four-layer board that has two signal layers, a power and a ground plane (2s2p), demonstrate that the effective thermal resistance is not a constant. The thermal resistance depends on the:

- Construction of the application board (number of planes)
- Effective size of the board which cools the component
- Quality of the thermal and electrical connections to the planes
- Power dissipated by adjacent components

Connect all the ground and power balls to the respective planes with one via per ball. Using fewer vias to connect the package to the planes reduces the thermal performance. Thinner planes also reduce the thermal performance. When the clearance between the vias leave the planes virtually disconnected, the thermal performance is also greatly reduced.

As a general rule, the value obtained on a single-layer board is within the normal range for the tightly packed printed circuit board. The value obtained on a board with the internal planes is usually within the normal range if the application board has:

- One oz. (35 micron nominal thickness) internal planes
- Components are well separated
- Overall power dissipation on the board is less than  $0.02 \text{ W/cm}^2$

The thermal performance of any component depends on the power dissipation of the surrounding components. In addition, the ambient temperature varies widely within the application. For many natural convection and especially closed box applications, the board temperature at the perimeter (edge) of the package is approximately the same as the local air temperature near the device. Specifying the local ambient conditions explicitly as the board temperature provides a more precise description of the local ambient conditions that determine the temperature of the device.

At a known board temperature, the junction temperature is estimated using the following equation:

$$T_J = T_B + \left( R_{\theta JB} * P_D \right)$$

where:

 $T_B$  = board temperature for the package perimeter (°C)

 $R_{\Theta JB}$  = junction-to-board thermal resistance (°C/W) per JESD51-8

 $P_D$  = power dissipation in the package (W)

When the heat loss from the package case to the air does not factor into the calculation, the junction temperature is predictable if the application board is similar to the thermal test condition, with the component soldered to a board with internal planes.

The thermal resistance is expressed as the sum of a junction-to-case thermal resistance plus a case-to-ambient thermal resistance:

 $R_{\theta JA} = R_{\theta JC} + R_{\theta CA}$ 

where:

 $R_{\Theta JA}$  = junction-to-ambient thermal resistance (°C/W)

 $R_{\Theta JC}$  = junction-to-case thermal resistance (°C/W)

 $R_{\Theta CA}$  = case to ambient thermal resistance (°C/W)

 $R_{\Theta JC}$  is device related and is not affected by other factors. The thermal environment can be controlled to change the case-to-ambient thermal resistance,  $R_{\Theta CA}$ . For example, change the air flow around the device, add a heat sink, change the mounting arrangement on the printed circuit board, or change the thermal dissipation on the printed circuit board surrounding the device. This description is most useful for packages with heat sinks where 90% of the heat flow is through the case to heat sink to ambient. For most packages, a better model is required.

#### Package information

A more accurate two-resistor thermal model can be constructed from the junction-toboard thermal resistance and the junction-to-case thermal resistance. The junction-to-case thermal resistance describes when using a heat sink or where a substantial amount of heat is dissipated from the top of the package. The junction-to-board thermal resistance describes the thermal performance when most of the heat is conducted to the printed circuit board. This model can be used to generate simple estimations and for computational fluid dynamics (CFD) thermal models. More accurate compact Flotherm models can be generated upon request.

To determine the junction temperature of the device in the application on a prototype board, use the thermal characterization parameter ( $\Psi_{JT}$ ) to determine the junction temperature by measuring the temperature at the top center of the package case using the following equation:

$$T_J = T_T + \left(\Psi_{\rm JT} x P_D\right)$$

where:

 $T_T$  = thermocouple temperature on top of the package (°C)

 $\Psi_{JT}$  = thermal characterization parameter (°C/W)

 $P_D$  = power dissipation in the package (W)

The thermal characterization parameter is measured in compliance with the JESD51-2 specification using a 40-gauge type T thermocouple epoxied to the top center of the package case. Position the thermocouple so that the thermocouple junction rests on the package. Place a small amount of epoxy on the thermocouple junction and approximately 1 mm of wire extending from the junction. Place the thermocouple wire flat against the package case to avoid measurement errors caused by the cooling effects of the thermocouple wire.

When board temperature is perfectly defined below the device, it is possible to use the thermal characterization parameter ( $\Psi_{JPB}$ ) to determine the junction temperature by measuring the temperature at the bottom center of the package case (exposed pad) using the following equation:

$$T_J = T_B + \left( \Psi_{\rm JP\,B} x P_D \right)$$

where:


 $T_T$  = thermocouple temperature on bottom of the package (°C)

 $\Psi_{JT}$  = thermal characterization parameter (°C/W)

 $P_D$  = power dissipation in the package (W)

# 5 Ordering information

Figure 42 and Table 51 describe orderable part numbers for the MPC5775B and MPC5775E.



### Figure 42. MPC5775B and MPC5775E Orderable part number description

| Part number     | Package description  | Speed (MHz) | Operating temperature <sup>1</sup> |                       |
|-----------------|----------------------|-------------|------------------------------------|-----------------------|
|                 | Package description  | Speed (MHZ) | Min (T <sub>L</sub> )              | Max (T <sub>H</sub> ) |
| SPC5775BDK3MME2 | SPC5775B 416 package | 220         | –40 °C                             | 125 °C                |
|                 | Lead-free (Pb-free)  |             |                                    |                       |
| SPC5775EDK3MME3 | SPC5775E 416 package | 264         | –40 °C                             | 125 °C                |
|                 | Lead-free (Pb-free)  |             |                                    |                       |

### Table 51. Example orderable part numbers

The lowest ambient operating temperature is referenced by T<sub>L</sub>; the highest ambient operating temperature is referenced by T<sub>H</sub>.

# 6 Document revision history

The following table summarizes revisions to this document since the previous release.

Table 52. Revision history

| Revision | Date    | Description of changes |
|----------|---------|------------------------|
| 1        | 05/2018 | Initial release        |

Table continues on the next page ...

| Revis | sion | Date    | Description of changes  |
|-------|------|---------|---|
| 2     |      | 02/2020 | In Figure 42 added optional feature field S.  |
|       |      |         | In Table 16, updated the footnote from "TUE does not apply to differential conversions" to "TUE, Gain, and Offset specifications do not apply to differential conversions".   |
|       |      |         | In Table 4 added Max value 120 $\mu$ A for 40°C and 360 $\mu$ A for 85°C for I <sub>STBY</sub> .  |
|       |      |         | <ul> <li>In Table 17 :</li> <li>Changed the condition of δ<sub>GROUP</sub> from "Within pass band – Tclk is f<sub>ADCD_M</sub>/ 2" to "Within pass band – Tclk is 2/f<sub>ADCD_M</sub>".</li> <li>In the footnote of t<sub>LATENCY</sub> changed the Register Latency formula from "where f<sub>ADCD_S</sub> is the after-decimation ADC output data rate, f<sub>ADCD_M</sub> is the modulator sampling rate and f<sub>FM_PER_CLK</sub> is the frequency of the peripheral bridge clock feeds to the ADC S/D module. REGISTER LATENCY = t<sub>LATENCY</sub> + 0.5/f<sub>ADCD_S</sub> + 2 (~+1)/f<sub>ADCD_M</sub> + 2(~+1)f<sub>FM_PER_CLK</sub>" to "where f<sub>ADCD_S</sub> is the after-decimation ADC output data rate, f<sub>ADCD_M</sub>/2 is the modulator sampling rate and f<sub>FM_PER_CLK</sub> is the frequency of the peripheral bridge clock feeds to the ADC S/D module. REGISTER LATENCY = t<sub>LATENCY</sub> + 0.5/f<sub>ADCD_S</sub> + 2 (~+1)/f<sub>ADCD_M</sub>/2 is the modulator sampling rate and f<sub>FM_PER_CLK</sub> is the frequency of the peripheral bridge clock feeds to the ADC S/D module.</li> </ul> |

Table 52. Revision history (continued)

#### How to Reach Us:

Home Page: www.nxp.com

Web Support: www.nxp.com/support Information in this document is provided solely to enable system and software implementers to use NXP products. There are no express or implied copyright licenses granted hereunder to design or fabricate any integrated circuits based on the information in this document. NXP reserves the right to make changes without further notice to any products herein.

NXP makes no warranty, representation, or guarantee regarding the suitability of its products for any particular purpose, nor does NXP assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation consequential or incidental damages. "Typical" parameters that may be provided in NXP data sheets and/or specifications can and do vary in different applications, and actual performance may vary over time. All operating parameters, including "typicals," must be validated for each customer application by customer's technical experts. NXP does not convey any license under its patent rights nor the rights of others. NXP sells products pursuant to standard terms and conditions of sale, which can be found at the following address: nxp.com/SalesTermsandConditions.

While NXP has implemented advanced security features, all products may be subject to unidentified vulnerabilities. Customers are responsible for the design and operation of their applications and products to reduce the effect of these vulnerabilities on customer's applications and products, and NXP accepts no liability for any vulnerability that is discovered. Customers should implement appropriate design and operating safeguards to minimize the risks associated with their applications and products.

NXP, the NXP logo, NXP SECURE CONNECTIONS FOR A SMARTER WORLD, COOLFLUX, EMBRACE, GREENCHIP, HITAG, I2C BUS, ICODE, JCOP, LIFE VIBES, MIFARE, MIFARE CLASSIC, MIFARE DESFire, MIFARE PLUS, MIFARE FLEX, MANTIS, MIFARE ULTRALIGHT, MIFARE4MOBILE, MIGLO, NTAG, ROADLINK, SMARTLX, SMARTMX, STARPLUG, TOPFET, TRENCHMOS, UCODE, Freescale, the Freescale logo, AltiVec, C-5, CodeTEST, CodeWarrior, ColdFire, ColdFire+, C-Ware, the Energy Efficient Solutions logo, Kinetis, Layerscape, MagniV, mobileGT, PEG, PowerQUICC, Processor Expert, QorIQ, QorIQ Qonverge, Ready Play, SafeAssure, the SafeAssure logo, StarCore, Symphony, VortiQa, Vybrid, Airfast, BeeKit, BeeStack, CoreNet, Flexis, MXC, Platform in a Package, QUICC Engine, SMARTMOS, Tower, TurboLink, and UMEMS are trademarks of NXP B.V. All other product or service names are the property of their respective owners. AMBA, Arm, Arm7, Arm7TDMI, Arm9, Arm11, Artisan, big.LITTLE, Cordio, CoreLink, CoreSight, Cortex, DesignStart, DynamIQ, Jazelle, Keil, Mali, Mbed, Mbed Enabled, NEON, POP, RealView, SecurCore, Socrates, Thumb, TrustZone, ULINK, ULINK2, ULINK-ME, ULINK-PLUS, ULINKpro, µVision, Versatile are trademarks or registered trademarks of Arm Limited (or its subsidiaries) in the US and/or elsewhere. The related technology may be protected by any or all of patents, copyrights, designs and trade secrets. All rights reserved. Oracle and Java are registered trademarks of Oracle and/or its affiliates. The Power Architecture and Power.org word marks and the Power and Power.org logos and related marks are trademarks and service marks licensed by Power.org.

© 2013-2020 NXP B.V.





Document Number: MPC5775E Rev. 2, 03/2020