

#### Freescale Semiconductor, Inc.

PewerPe

# Advance Information EC603e<sup>™</sup> Embedded RISC Microprocessor Technical Summary

This document provides an overview of the EC603e microprocessor features, including a block diagram showing the major functional components. It also provides an overview of the PowerPC<sup>TM</sup> architecture specification, and information about how the EC603e implementation complies with the architectural definitions.

The EC603e microprocessor for embedded systems is functionally equivalent to the MPC603e with the exception of the floating-point unit which is not supported on the EC603e microprocessor. In this document, the term '603' is an abbreviation for 'PowerPC  $603^{\text{TM}}$ '.

The EC603e microprocessor is implemented in both a 2.5-volt version (PID 0007v EC603e microprocessor, abbreviated as PID7v) and a 3.3-volt version (PID 0006 EC603e microprocessor, abbreviated as PID6). This document discusses both.

This document is divided into two parts:

- Part 1, "Overview," provides an overview of the EC603e microprocessor features, including a block diagram showing the major functional components.
- Part 2, "Implementation-Specific Information," describes the PowerPC architecture in general, as well as providing specific details about the implementation of the EC603e microprocessor as a low-power, 32-bit member of the PowerPC processor family, and an enumeration of the differences from the 603.

To locate any published errata or updates for this document, refer to the website at http://www.mot.com/SPS/PowerPC/.

© Motorola Inc., 1997. All rights reserved.



For More Information On This Product, Go to: www.freescale.com

The PowerPC name, the PowerPC logotype, PowerPC 601, and PowerPC 603 are trademarks of International Business Machines Corporation, used by Motorola under license from International Business Machines Corporation. EC603e is a trademark of Motorola, Inc. This document contains information on a new product under development by Motorola. Motorola reserves the right to change or discontinue this product without notice.

# Part 1 Overview

This section describes the details of the EC603e microprocessor, provides a block diagram showing the major functional units, and describes briefly how those units interact. Any differences between the PID6 and PID7v implementations are noted.

The EC603e microprocessor is a low-power implementation of the PowerPC microprocessor family of reduced instruction set computing (RISC) microprocessors. The EC603e microprocessor implements the 32-bit portion of the PowerPC architecture, which provides 32-bit effective addresses, integer data types of 8, 16, and 32 bits.

The EC603e microprocessor is a superscalar processor that can issue and retire as many as three instructions per clock. Instructions can execute out of order for increased performance; however, the EC603e microprocessor makes completion appear sequential.

The EC603e microprocessor integrates four execution units—an integer unit (IU), a branch processing unit (BPU), a load/store unit (LSU), and a system register unit (SRU). The ability to execute five instructions in parallel and the use of simple instructions with rapid execution times yield high efficiency and throughput for EC603e-based systems. Most integer instructions execute in one clock cycle.

The EC603e microprocessor provides independent on-chip, 16-Kbyte, four-way set-associative, physically addressed caches for instructions and data and on-chip instruction and data memory management units (MMUs). The MMUs contain 64-entry, two-way set-associative, data and instruction translation lookaside buffers (DTLB and ITLB) that provide support for demand-paged virtual memory address translation and variable-sized block translation. The TLBs and caches use a least recently used (LRU) replacement algorithm. The EC603e microprocessor also supports block address translation through the use of two independent instruction and data block address translation (IBAT and DBAT) arrays of four entries each. Effective addresses are compared simultaneously with all four entries in the BAT array during block translation. In accordance with the PowerPC architecture, if an effective address hits in both the TLB and BAT array, the BAT translation takes priority.

The EC603e microprocessor has a selectable 32- or 64-bit data bus and a 32-bit address bus. The EC603e interface protocol allows multiple masters to compete for system resources through a central external arbiter. The EC603e implementation provides a three-state coherency protocol that supports the exclusive, modified, and invalid cache states. This protocol is a compatible subset of the MESI (modified/exclusive/ shared/invalid) four-state protocol and operates coherently in systems that contain four-state caches. The EC603e microprocessor supports single-beat and burst data transfers for memory accesses, and supports memory-mapped I/O operations.

The EC603e processor is fabricated using an advanced CMOS process technology and is fully compatible with TTL devices.

# 1.1 Features

This section describes the major features of the EC603e microprocessor noting where the PID6 and PID7v implementations differ:

- High-performance, superscalar microprocessor
  - As many as three instructions issued and retired per clock
  - As many as five instructions in execution per clock
  - Single-cycle execution for most instructions



- Four independent execution units and two register files
  - BPU featuring static branch prediction
  - A 32-bit IU
  - LSU for data transfer between data cache and GPRs
  - SRU that executes condition register (CR), special-purpose register (SPR), and integer add/ compare instructions
  - Thirty-two GPRs for integer operands
- High instruction and data throughput
  - Zero-cycle branch capability (branch folding)
  - Programmable static branch prediction on unresolved conditional branches
  - Instruction fetch unit capable of fetching two instructions per clock from the instruction cache
  - A six-entry instruction queue that provides lookahead capability
  - Independent pipelines with feed-forwarding that reduces data dependencies in hardware
  - 16-Kbyte data cache—four-way set-associative, physically addressed; LRU replacement algorithm
  - 16-Kbyte instruction cache—four-way set-associative, physically addressed; LRU replacement algorithm
  - Cache write-back or write-through operation programmable on a per page or per block basis
  - BPU that performs CR lookahead operations
  - Address translation facilities for 4-Kbyte page size, variable block size, and 256-Mbyte segment size
  - A 64-entry, two-way set-associative ITLB
  - A 64-entry, two-way set-associative DTLB
  - Four-entry data and instruction BAT arrays providing 128-Kbyte to 256-Mbyte blocks
  - Software table search operations and updates supported through fast trap mechanism
  - 52-bit virtual address; 32-bit physical address
- Facilities for enhanced system performance
  - A 32- or 64-bit split-transaction external data bus with burst transfers
  - Support for one-level address pipelining and out-of-order bus transactions
  - Hardware support for misaligned little-endian accesses (PID7v)
- Integrated power management
  - Low-power 2.5-volt and 3.3-volt designs
  - Internal processor/bus clock multiplier ratios as follows:
    - 1/1, 1.5/1, 2/1, 2.5/1, 3/1, 3.5/1, and 4/1 (PID6)
    - 2/1, 2.5/1, 3/1, 3.5/1, 4/1, 4.5/1, 5/1, 5.5/1, and 6/1 (PID7v)
  - Three power-saving modes: doze, nap, and sleep
  - Automatic dynamic power reduction when internal functional units are idle
- In-system testability and debugging features through JTAG boundary-scan capability



# Freescale Semiconductor, Inc.

New features specific to the PID7v implementation follow:

- Enhancements to the register set
  - The PID7v implementation adds two new bits to the HID0 register:
    - The address bus enable (ABE) bit, bit 28, gives the PID7v microprocessor the ability to broadcast **dcbf**, **dcbi**, and **dcbst** onto the 60x bus.
    - The instruction fetch enable M (IFEM) bit, bit 24, allows the PID7v implementation to reflect the value of the M-bit onto the 60x bus during instruction translation.
  - The Run\_N counter register (Run\_N) has been extended from 16 to 32 bits.
- Enhancements to cache implementation
  - The instruction cache is blocked only until the critical load completes (hit under reloads allowed).
  - The critical double word is simultaneously written to the cache and forwarded to the requesting unit, thus minimizing stalls due to load delays.
  - Provides for an optional data cache operation broadcast feature (enabled by the HID0[ABE] bit) that allows for correct system management utilizing an external copyback L2 cache.
  - All of the cache control instructions (icbi, dcbi, dcbf, and dcbst, excluding dcbz) require that the HID0[ABE] configuration bit be enabled in order to execute.
- Exceptions
  - The PID7v implementation now offers hardware support for misaligned little-endian accesses. Little-endian load/store accesses that are not on a word boundary, with the exception of strings and multiples, generate exceptions under the same circumstances as big-endian accesses.
  - The PID7v implementation removed misalignment support for eciwx and ecowx graphics instructions. These instructions cause an alignment exception if the access is not on a word boundary.
- Bus clock—New bus multipliers of 4.5x, 5x, 5.5x, and 6x that are selected by the unused encodings of the PLL\_CFG[0–3]. Bus multipliers of 1x and 1.5x are not supported by the PID7v implementation.
- Power management—Internal voltage supply changed from 3.3 volts to 2.5 volts. The core logic of the chip now uses a 2.5-volt supply.
- Signals—The Run\_N counter, which affects the JTAG/COP, has been extended from 16 bits to 32 bits.
- Instruction timing
  - The integer divide instructions divwu[o][.] and divw[o][.] execute in 20 clock cycles; execution of these instructions in the PID6 implementation requires 37 clock cycles.
  - Support for single-cycle store
  - An adder/comparator added to system register unit that allows dispatch and execution of multiple integer add and compare instructions on each cycle.

Figure 1 provides a block diagram of the EC603e microprocessor that illustrates how the execution units— IU, BPU, LSU, and SRU—operate independently and in parallel. Note that this is a conceptual diagram and does not attempt to show how these features are physically implemented on the chip. For more information on the execution units, refer to the *MPC603e* & *EC603e RISC Microprocessors User's Manual*.

The EC603e microprocessor provides address translation and protection facilities, including an ITLB, DTLB, and instruction and data BAT arrays. Instruction fetching and issuing is handled in the instruction



unit. Translation of addresses for cache or external memory accesses are handled by the MMUs. Both units are discussed in more detail in Sections 1.2, "Instruction Unit," and 1.4.1, "Memory Management Units (MMUs)."




Figure 1. Block Diagram



# **1.2 Instruction Unit**

As shown in Figure 1, the EC603e microprocessor instruction unit, which contains a fetch unit, instruction queue, dispatch unit, and BPU, provides centralized control of instruction flow to the execution units. The instruction unit determines the address of the next instruction to be fetched based on information from the sequential fetcher and from the BPU.

The instruction unit fetches the instructions from the instruction cache into the instruction queue. The BPU extracts branch instructions from the fetcher and uses static branch prediction on unresolved conditional branches to allow the instruction unit to fetch instructions from a predicted target instruction stream while a conditional branch is evaluated. The BPU folds out branch instructions for unconditional branches or conditional branches unaffected by instructions in progress in the execution pipeline.

Instructions issued beyond a predicted branch do not complete execution until the branch is resolved, preserving the programming model of sequential execution. If any of these instructions are to be executed in the BPU, they are decoded but not issued. Instructions to be executed by the IU, LSU, and SRU are issued and allowed to complete up to the register write-back stage. Write-back is allowed when a correctly predicted branch is resolved, and instruction execution continues without interruption along the predicted path.

If branch prediction is incorrect, the instruction unit flushes all predicted path instructions, and instructions are issued from the correct path.

# 1.2.1 Instruction Queue and Dispatch Unit

The instruction queue (IQ), shown in Figure 1, holds as many as six instructions and loads up to two instructions from the instruction unit during a single cycle. The instruction fetch unit continuously loads as many instructions as space in the IQ allows. Instructions are dispatched to their respective execution units from the dispatch unit at a maximum rate of two instructions per cycle. Dispatching is facilitated to the IU, LSU, and SRU by the provision of a reservation station at each unit. The dispatch unit performs source and destination register dependency checking, determines dispatch serializations, and inhibits subsequent instruction dispatching as required.

For a more detailed overview of instruction dispatch, see Section 2.6, "Instruction Timing."

# 1.2.2 Branch Processing Unit (BPU)

The BPU receives branch instructions from the fetch unit and performs CR lookahead operations on conditional branches to resolve them early, achieving the effect of a zero-cycle branch in many cases.

The BPU uses a bit in the instruction encoding to predict the direction of the conditional branch. Therefore, when an unresolved conditional branch instruction is encountered, the EC603e microprocessor fetches instructions from the predicted target stream until the conditional branch is resolved.

The BPU contains an adder to compute branch target addresses and three user-control registers—the link register (LR), the count register (CTR), and the condition register (CR). The BPU calculates the return pointer for subroutine calls and saves it into the LR for certain types of branch instructions. The LR also contains the branch target address for the Branch Conditional to Link Register (**bclr***x*) instruction. The CTR contains the branch target address for the Branch Conditional to Count Register (**bctr***x*) instruction. The contents of the LR and CTR can be copied to or from any GPR. Because the BPU uses dedicated registers rather than GPRs, execution of branch instructions is largely independent from execution of integer instructions.



# **1.3 Independent Execution Units**

The PowerPC architecture's support for independent execution units allows implementation of processors with out-of-order instruction execution. For example, because branch instructions do not depend on GPRs, branches can often be resolved early, eliminating stalls caused by taken branches.

In addition to the BPU, the EC603e microprocessor provides three other execution units and a completion unit, which are described in the following sections.

# 1.3.1 Integer Unit (IU)

The IU executes all integer instructions. The IU executes one integer instruction at a time, performing computations with its arithmetic logic unit (ALU), multiplier, divider, and XER register. Most integer instructions are single-cycle instructions. Thirty-two general-purpose registers are provided to support integer operations. Stalls due to contention for GPRs are minimized by the automatic allocation of rename registers. The EC603e microprocessor writes the contents of the rename registers to the appropriate GPR when integer instructions are retired by the completion unit.

# 1.3.2 Load/Store Unit (LSU)

The LSU executes all load and store instructions and provides the data transfer interface between the GPRs and the cache/memory subsystem. The LSU calculates effective addresses, performs data alignment, and provides sequencing for load/store string and multiple instructions.

Load and store instructions are issued and translated in program order; however, the actual memory accesses can occur out of order. Synchronizing instructions are provided to enforce strict ordering.

Cacheable loads, when free of data dependencies, execute in an out-of-order manner with a maximum throughput of one per cycle and a two-cycle total latency. Data returned from the cache is held in a rename register until the completion logic commits the value to a GPR. Stores cannot be executed in a predicted manner and are held in the store queue until the completion logic signals that the store operation is to be completed to memory. The EC603e microprocessor executes store instructions with a maximum throughput of one per cycle and a three-cycle total latency. The time required to perform the actual load or store operation varies depending on whether the operation involves the cache, system memory, or an I/O device.

# 1.3.3 System Register Unit (SRU)

The SRU executes various system-level instructions, including condition register logical operations and move to/from special-purpose register instructions, and also executes integer add/compare instructions. In order to maintain system state, most instructions executed by the SRU are completion-serialized; that is, the instruction is held for execution in the SRU until all prior instructions issued have completed. Results from completion-serialized instructions executed by the SRU are not available or forwarded for subsequent instructions until the instruction completes.

# 1.3.4 Completion Unit

The completion unit tracks instructions from dispatch through execution, and then retires, or "completes" them in program order. Completing an instruction commits the EC603e microprocessor to any architectural register changes caused by that instruction. In-order completion ensures the correct architectural state when the EC603e microprocessor must recover from a mispredicted branch or any exception.

Instruction state and other information required for completion is kept in a first-in-first-out (FIFO) queue of five completion buffers. A single completion buffer is allocated for each instruction once it enters the dispatch unit. An available completion buffer is a required resource for instruction dispatch; if no



completion buffers are available, instruction dispatch stalls. A maximum of two instructions per cycle are completed in order from the queue.

# 1.4 Memory Subsystem Support

The EC603e microprocessor provides support for cache and memory management through dual instruction and data memory management units. The EC603e microprocessor also provides dual 16-Kbyte instruction and data caches, and an efficient processor bus interface to facilitate access to main memory and other bus subsystems. The memory subsystem support functions are described in the following subsections.

# 1.4.1 Memory Management Units (MMUs)

The EC603e microprocessor's MMUs support up to 4 Petabytes  $(2^{52})$  of virtual memory and 4 Gigabytes  $(2^{32})$  of physical memory (referred to as real memory in the architecture specification) for instruction and data. The MMUs also control access privileges for these spaces on block and page granularities. Referenced and changed status is maintained by the processor for each page to assist implementation of a demand-paged virtual memory system. A key bit is implemented to provide information about memory protection violations prior to page table search operations.

The LSU calculates effective addresses for data loads and stores, performs data alignment to and from cache memory, and provides the sequencing for load and store string and multiple word instructions. The instruction unit calculates the effective addresses for instruction fetching.

After an address is generated, the higher-order bits of the effective address are translated by the appropriate MMU into physical address bits. Simultaneously, the lower-order address bits (that are untranslated and therefore, considered both logical and physical), are directed to the on-chip caches where they form the index into the four-way set-associative tag array. After translating the address, the MMU passes the higher-order bits of the physical address to the cache, and the cache lookup completes. For caching-inhibited accesses or accesses that miss in the cache, the untranslated lower-order address bits are concatenated with the translated higher-order address bits; the resulting 32-bit physical address is then used by the memory unit and the system interface, which accesses external memory.

The MMU also directs the address translation and enforces the protection hierarchy programmed by the operating system in relation to the supervisor/user privilege level of the access and in relation to whether the access is a load or store.

For instruction accesses, the MMU performs an address lookup in both the 64 entries of the ITLB, and in the IBAT array. If an effective address hits in both the ITLB and the IBAT array, the IBAT array translation takes priority. Data accesses cause a lookup in the DTLB and DBAT array for the physical address translation. In most cases, the physical address translation resides in one of the TLBs and the physical address bits are readily available to the on-chip cache.

When the physical address translation misses in the TLBs, the EC603e microprocessor provides hardware assistance for software to perform a search of the translation tables in memory. The hardware assist consists of the following features:

- Automatic storage of the missed effective address in the IMISS and DMISS registers
- Automatic generation of the primary and secondary hashed real address of the page table entry group (PTEG), which are readable from the HASH1 and HASH2 register locations.

The HASH data is generated from the contents of the IMISS or DMISS register. Which register is selected depends on which miss (instruction or data) was last acknowledged.



- Automatic generation of the first word of the page table entry (PTE) for which the tables are being searched
- A real page address (RPA) register that matches the format of the lower word of the PTE
- Two TLB access instructions (**tlbli** and **tlbld**) that are used to load an address translation into the instruction or data TLBs
- Shadow registers for GPRs 0–3 that allow miss code to execute without corrupting the state of any of the existing GPRs.

These shadow registers are only used for servicing a TLB miss.

See Section 2.5.2, "Implementation-Specific Memory Management," for more information about memory management for the EC603e microprocessor.

# 1.4.2 Cache Units

The EC603e microprocessor provides independent 16-Kbyte, four-way set-associative instruction and data caches. The cache line size is 32 bytes in length. The caches are designed to adhere to a write-back policy, but the EC603e microprocessor allows control of cacheability, write policy, and memory coherency at the page and block levels. The caches use a least recently used (LRU) replacement policy.

As shown in Figure 1, the caches provide a 64-bit interface to the instruction fetch unit and load/store unit. The surrounding logic selects, organizes, and forwards the requested information to the requesting unit. Write operations to the cache can be performed on a byte basis, and a complete read-modify-write operation to the cache can occur in each cycle.

The load/store and instruction fetch units provide the caches with the address of the data or instruction to be fetched. In the case of a cache hit, the cache returns two words to the requesting unit.

Since the EC603e microprocessor data cache tags are single ported, simultaneous load or store and snoop accesses cause resource contention. Snoop accesses have the highest priority and are given first access to the tags, unless the snoop access coincides with a tag write, in which case the snoop is retried and must rearbitrate for access to the cache. Loads or stores that are deferred due to snoop accesses are executed on the clock cycle following the snoop.

# **1.5 Processor Bus Interface**

Because the caches on the EC603e microprocessor are on-chip, write-back caches, the predominant type of transaction for most applications is burst-read memory operations, followed by burst-write memory operations, and single-beat (noncacheable or write-through) memory read and write operations. Additionally, there can be address-only operations, variants of the burst and single-beat operations, (for example, global memory operations that are snooped and atomic memory operations), and address retry activity (for example, when a snooped read access hits a modified line in the cache).

Memory accesses can occur in single-beat (1–8 bytes) and four-beat burst (32 bytes) data transfers when the bus is configured as 64 bits, and in single-beat (1–4 bytes), two-beat (8 bytes), and eight-beat (32 bytes) data transfers when the bus is configured as 32 bits. The address and data buses operate independently to support pipelining and split transactions during memory accesses. The EC603e microprocessor can pipeline its own transactions to a depth of one level.

Access to the system interface is granted through an external arbitration mechanism that allows devices to compete for bus mastership. This arbitration mechanism is flexible, allowing the EC603e microprocessor to be integrated into systems that implement various fairness and bus parking procedures to avoid arbitration overhead.



Typically, memory accesses are weakly ordered—sequences of operations, including load/store string and multiple instructions, do not necessarily complete in the order they begin—maximizing the efficiency of the bus without sacrificing coherency of the data. The EC603e microprocessor allows read operations to precede store operations (except when a dependency exists, or in cases where a non-cacheable access is performed), and provides support for a write operation to proceed a previously queued read data tenure (for example, allowing a snoop push to be enveloped by the address and data tenures of a read operation). Because the processor can dynamically optimize run-time ordering of load/store traffic, overall performance is improved.

# **1.6 System Support Functions**

The EC603e microprocessor implements several support functions that include power management, time base/decrementer registers for system timing tasks, an IEEE 1149.1(JTAG)/common on-chip processor (COP) test interface, and a phase-locked loop (PLL) clock multiplier. These system support functions are described in the following subsections.

### 1.6.1 Power Management

The EC603e microprocessor provides four power modes selectable by setting the appropriate control bits in the machine state register (MSR) and hardware implementation register 0 (HID0) registers. The four power modes are as follows:

- Full-power–This is the default power state of the EC603e microprocessor. The EC603e microprocessor is fully powered and the internal functional units are operating at the full processor clock speed. If the dynamic power management mode is enabled, functional units that are idle will automatically enter a low-power state without affecting performance, software execution, or external hardware.
- Doze–All the functional units of the EC603e microprocessor are disabled except for the time base/ decrementer registers and the bus snooping logic. When the processor is in doze mode, an external asynchronous interrupt, a system management interrupt, a decrementer exception, a hard or soft reset, or machine check brings the EC603e microprocessor into the full-power state. The EC603e microprocessor in doze mode maintains the PLL in a fully powered state and locked to the system external clock input (SYSCLK) so a transition to the full-power state takes only a few processor clock cycles.
- Nap–The nap mode further reduces power consumption by disabling bus snooping, leaving only the time base register and the PLL in a powered state. The EC603e processor returns to the full-power state upon receipt of an external asynchronous interrupt, a system management interrupt, a decrementer exception, a hard or soft reset, or a machine check input (MCP) signal. A return to full-power state from a nap state takes only a few processor clock cycles.
- Sleep–Sleep mode reduces power consumption to a minimum by disabling all internal functional units, after which external system logic may disable the PLL and SYSCLK. Returning the EC603e microprocessor to the full-power state requires the enabling of the PLL and SYSCLK, followed by the assertion of an external asynchronous interrupt, a system management interrupt, a hard or soft reset, or a machine check input (MCP) signal after the time required to relock the PLL.

The PID7v implementation offers the following enhancements to the EC603e microprocessor family:

- Lower-power design
- 2.5-volt core and 3.3-volt I/O



### 1.6.2 Time Base/Decrementer

The time base is a 64-bit register (accessed as two 32-bit registers) that is incremented once every four bus clock cycles; external control of the time base is provided through the time base enable (TBEN) signal. The decrementer is a 32-bit register that generates a decrementer interrupt exception after a programmable delay. The contents of the decrementer register are decremented once every four bus clock cycles, and the decrementer exception is generated as the count passes through zero.

# 1.6.3 IEEE 1149.1 (JTAG)/COP Test Interface

The EC603e microprocessor provides IEEE 1149.1 and COP functions for facilitating board testing and chip debug. The IEEE 1149.1 test interface provides a means for boundary-scan testing the EC603e processor and the board to which it is attached. The COP function shares the IEEE 1149.1 test port, provides a means for executing test routines, and facilitates chip and software debugging.

# 1.6.4 Clock Multiplier

The internal clocking of the EC603e implementation is generated from and synchronized to the external clock signal, SYSCLK, by means of a voltage-controlled oscillator-based PLL. The PLL provides programmable internal processor clock rates of 1x, 1.5x, 2x, 2.5x, 3x, 3.5x, and 4x multiples of the externally supplied clock frequency. The bus clock is the same frequency and is synchronous with SYSCLK. The configuration of the PLL can be read by software from the hardware implementation register 1 (HID1).

# Part 2 Implementation-Specific Information

The PowerPC architecture is derived from the IBM POWER architecture (Performance Optimized with Enhanced RISC architecture). The PowerPC architecture shares the benefits of the POWER architecture optimized for single-chip implementations. The PowerPC architecture design facilitates parallel instruction execution and is scalable to take advantage of future technological gains.

The PowerPC architecture consists of the following layers, and adherence to the PowerPC architecture can be measured in terms of which of the following levels of the architecture is implemented:

- PowerPC user instruction set architecture (UISA)—Defines the base user-level instruction set, user-level registers, data types, floating-point exception model, memory models for a uniprocessor environment, and programming model for a uniprocessor environment.
- PowerPC virtual environment architecture (VEA)—Describes the memory model for a multiprocessor environment, defines cache control instructions, and describes other aspects of virtual environments. Implementations that conform to the VEA also adhere to the UISA, but may not necessarily adhere to the OEA.
- PowerPC operating environment architecture (OEA)—Defines the memory management model, supervisor-level registers, synchronization requirements, and the exception model. Implementations that conform to the OEA also adhere to the UISA and the VEA.

The PowerPC architecture allows a wide range of designs for such features as cache and system interface implementations.



This section describes the PowerPC architecture in general, and specific details about the implementation of the EC603e microprocessor as a low-power, 32-bit member of the PowerPC processor family. Note that the EC603e microprocessor does not support the floating-point unit. The main topics addressed are as follows:

- Section 2.1, "Programming Model," describes the registers for the operating environment architecture common among PowerPC processors and describes the programming model. It also describes the additional registers that are unique to the EC603e microprocessor.
- Section 2.2, "Instruction Set and Addressing Modes," describes the PowerPC instruction set and addressing modes for the PowerPC operating environment architecture, and defines and describes the PowerPC instructions implemented in the EC603e microprocessor.
- Section 2.3, "Cache Implementation," describes the cache model that is defined generally for PowerPC processors by the virtual environment architecture. It also provides specific details about the EC603e cache implementation.
- Section 2.4, "Exception Model," describes the exception model of the PowerPC operating environment architecture and the differences in the EC603e exception model.
- Section 2.5, "Memory Management," describes generally the conventions for memory management among the PowerPC processors. This section also describes the EC603e's implementation of the 32-bit PowerPC memory management specification.
- Section 2.6, "Instruction Timing," provides a general description of the instruction timing provided by the superscalar, parallel execution supported by the PowerPC architecture and the EC603e microprocessor.
- Section 2.7, "System Interface," describes the signals implemented on the EC603e microprocessor.

The EC603e microprocessor is a high-performance, superscalar PowerPC microprocessor. The PowerPC architecture allows optimizing compilers to schedule instructions to maximize performance through efficient use of the PowerPC instruction set and register model. The multiple, independent execution units allow compilers to optimize instruction throughput. Compilers that take advantage of the flexibility of the PowerPC architecture can additionally optimize system performance of the PowerPC processors.

The following sections summarize the features of the EC603e microprocessor, including both those that are defined by the architecture and those that are unique to the various EC603e implementations.

Specific features of the EC603e microprocessor are listed in Section 1.1, "Features."

# 2.1 Programming Model

The PowerPC architecture defines register-to-register operations for most computational instructions. Source operands for these instructions are accessed from the registers or are provided as immediate values embedded in the instruction opcode. The three-register instruction format allows specification of a target register distinct from the two source operands. Load and store instructions transfer data between registers and memory.

PowerPC processors have two levels of privilege—supervisor mode of operation (typically used by the operating system) and user mode of operation (used by the application software). The programming models incorporate 32 GPRs, special-purpose registers (SPRs), and several miscellaneous registers. Each PowerPC microprocessor also has its own unique set of hardware implementation (HID) registers.

Having access to privileged instructions, registers, and other resources allows the operating system to control the application environment (providing virtual memory and protecting operating-system and critical machine resources). Instructions that control the state of the processor, the address translation mechanism, and supervisor registers can be executed only when the processor is operating in supervisor mode.



Figure 2 shows all the EC603e microprocessor registers available at the user and supervisor level. The numbers to the right of the SPRs indicate the number that is used in the syntax of the instruction operands to access the register.

The following subsections describe the PID7v implementation-specific features as they apply to registers.

# 2.1.1 Processor Version Register (PVR)

The processor version number is 6 for the PID6 and 7 for the PID7v. The processor revision level starts at 0x0100 and changes for each chip revision. The revision level is updated on all silicon revisions.

# 2.1.2 Hardware Implementation Register 0 (HID0)

The PID7v (designated by PVR level 0x0200) defines additional bits in the hardware implementation register 0 (HID0), a supervisor-level register that provides the means for enabling the EC603e implementation's checkstops and features, and allows software to read the configuration of the PLL configuration signals.

The HID0 bits with changed bit assignments are shown in Table 1. The HID0 bits that are not shown here are implemented as they are in Section 2.1.2.1, "Hardware Implementation Registers (HID0 and HID1)," in *MPC603e & EC603e RISC Microprocessors User's Manual*.

Bit(s)	Description		
24	Instruction fetch enable M (IFEM) bit—Enables the M bit on the bus. Used for instruction fetches.		
25–26	Reserved		
28	Address broadcast enable (ABE)—This configuration bit allows for the broadcast of <b>dcbf</b> , <b>dcbi</b> , and <b>dcbst</b> on the bus. Note that these cache control instruction broadcasts are not snooped by the PID7v implementation of the EC603e microprocessor. Refer to Section 2.3, "Cache Implementation," for more information.		
29–30	Reserved		

Table 1. Additional/Changed HID0 Bits

# 2.1.3 Run\_N Counter Register (Run\_N)

The 33-bit Run\_N counter register is unique to the PID7v. The Run\_N counter is used by the COP to control the number of processor cycles that the processor runs before halting. The most-significant 32 bits form a 32-bit counter. The function of the least-significant bit remains unchanged.

# 2.1.4 General-Purpose Registers (GPRs)

The PowerPC architecture defines 32 user-level, general-purpose registers (GPRs). These registers are either 32 bits wide in 32-bit PowerPC microprocessors and 64 bits wide in 64-bit PowerPC microprocessors. The GPRs serve as the data source or destination for all integer instructions.

# 2.1.5 Condition Register (CR)

The CR is a 32-bit user-level register that consists of eight four-bit fields that reflect the results of certain operations, such as move, integer compare, arithmetic, and logical instructions, and provide a mechanism for testing and branching.



### 2.1.6 Machine State Register (MSR)

The machine state register (MSR) is a supervisor-level register that defines the state of the processor. The contents of this register are saved when an exception is taken and restored when the exception handling completes. The EC603e microprocessor implements the MSR as a 32-bit register; 64-bit PowerPC processors implement a 64-bit MSR. To ensure proper operation of the EC603e microprocessor, the MSR[FP] bit should remain cleared to zero.

# 2.1.7 Segment Registers (SRs)

For memory management, 32-bit PowerPC microprocessors implement sixteen 32-bit segment registers (SRs). To speed access, the EC603e microprocessor implements the segment registers as two arrays; a main array (for data memory accesses) and a shadow array (for instruction memory accesses). Loading a segment entry with the Move to Segment Register (**mtsr**) instruction loads both arrays.

# 2.1.8 Special-Purpose Registers (SPRs)

The PowerPC operating environment architecture defines numerous special-purpose registers that serve a variety of functions, such as providing controls, indicating status, configuring the processor, and performing special operations. During normal execution, a program can access the registers, shown in Figure 2, depending on the program's access privilege (supervisor or user, determined by the privilege-level (PR) bit in the MSR). Note that registers such as the GPRs are accessed through operands that are part of the instructions. Access to registers can be explicit (that is, through the use of specific instructions for that purpose such as Move to Special-Purpose Register (**mtspr**) and Move from Special-Purpose Register (**mfspr**) instructions) or implicit, as the part of the execution of an instruction. Some registers are accessed both explicitly and implicitly

In the EC603e implementation, all SPRs are 32 bits wide.

#### 2.1.8.1 User-Level SPRs

The following EC603e SPRs are accessible by user-level software:

- Link register (LR)—The link register can be used to provide the branch target address and to hold the return address after branch and link instructions. The LR is 32 bits wide in 32-bit implementations.
- Count register (CTR)—The CTR is decremented and tested automatically as a result of branch-andcount instructions. The CTR is 32 bits wide in 32-bit implementations.
- XER register—The 32-bit XER contains the summary overflow bit, integer carry bit, overflow bit, and a field specifying the number of bytes to be transferred by a Load String Word Indexed (**lswx**) or Store String Word Indexed (**stswx**) instruction.

### 2.1.8.2 Supervisor-Level SPRs

The EC603e microprocessor also contains SPRs that can be accessed only by supervisor-level software. These registers consist of the following:

- The 32-bit DSISR defines the cause of data access and alignment exceptions.
- The data address register (DAR) is a 32-bit register that holds the address of an access after an alignment or DSI exception.
- Decrementer register (DEC) is a 32-bit decrementing counter that provides a mechanism for causing a decrementer exception after a programmable delay.
- The 32-bit SDR1 specifies the page table format used in virtual-to-physical address translation for pages. (Note that physical address is referred to as real address in the architecture specification.)




- The machine status save/restore register 0 (SRR0) is a 32-bit register that is used by the EC603e microprocessor for saving the address of the instruction that caused the exception, and the address to return to when a Return from Interrupt (**rfi**) instruction is executed.
- The machine status save/restore register 1 (SRR1) is a 32-bit register used to save machine status on exceptions and to restore machine status when an **rfi** instruction is executed.
- The 32-bit SPRG0–SPRG3 registers are provided for operating system use.
- The external access register (EAR) is a 32-bit register that controls access to the external control facility through the External Control In Word Indexed (eciwx) and External Control Out Word Indexed (ecowx) instructions.
- The time base register (TB) is a 64-bit register that maintains the time of day and operates interval timers. The TB consists of two 32-bit fields—time base upper (TBU) and time base lower (TBL).
- The processor version register (PVR) is a 32-bit, read-only register that identifies the version (model) and revision level of the PowerPC processor.
- Block address translation (BAT) arrays—The PowerPC architecture defines 16 BAT registers, divided into four pairs of data BATs (DBATs) and four pairs of instruction BATs (IBATs). See Figure 2 for a list of the SPR numbers for the BAT arrays.

The following supervisor-level SPRs are implementation-specific to the EC603e microprocessor:

- The DMISS and IMISS registers are read-only registers that are loaded automatically upon an instruction or data TLB miss.
- The HASH1 and HASH2 registers contain the physical addresses of the primary and secondary page table entry groups (PTEGs).
- The ICMP and DCMP registers contain a duplicate of the first word in the page table entry (PTE) for which the table search is looking.
- The required physical address (RPA) register is loaded by the processor with the second word of the correct PTE during a page table search.
- The hardware implementation (HID0 and HID1) registers provide the means for enabling the EC603e microprocessor's checkstops and features, and allows software to read the configuration of the PLL configuration signals.
- The instruction address breakpoint register (IABR) is loaded with an instruction address that is compared to instruction addresses in the dispatch queue. When an address match occurs, an instruction address breakpoint exception is generated.

Figure 2 shows all the EC603e microprocessor registers available at the user and supervisor level. The numbers to the right of the SPRs indicate the number that is used in the syntax of the instruction operands to access the register.





#### Note:

<sup>1</sup>These registers are EC603e implementation–specific registers (PID6 and PID7v). They may not be supported by other PowerPC processors.

#### Figure 2. Programming Model—Registers



# 2.2 Instruction Set and Addressing Modes

The following subsections describe the PowerPC instruction set and addressing modes in general.

# 2.2.1 PowerPC Instruction Set and Addressing Modes

All PowerPC instructions are encoded as single-word (32-bit) opcodes. Instruction formats are consistent among all instruction types, permitting efficient decoding to occur in parallel with operand accesses. This fixed instruction length and consistent format greatly simplifies instruction pipelining.

### 2.2.1.1 PowerPC Instruction Set

The PowerPC instructions are divided into the following categories:

- Integer instructions—These include computational and logical instructions.
  - Integer arithmetic instructions
  - Integer compare instructions
  - Integer logical instructions
  - Integer rotate and shift instructions
- Floating-point instructions—These include floating-point computational instructions, as well as instructions that affect the FPSCR. Note that these instructions are not supported on the EC603e microprocessor.
  - Floating-point arithmetic instructions
  - Floating-point multiply/add instructions
  - Floating-point rounding and conversion instructions
  - Floating-point compare instructions
  - Floating-point status and control instructions
- Load/store instructions—These include integer load and store instructions.
  - Integer load and store instructions
  - Integer load and store multiple instructions
  - Primitives used to construct atomic memory operations (lwarx and stwcx. instructions)
- Flow control instructions—These include branching instructions, condition register logical instructions, trap instructions, and other instructions that affect the instruction flow.
  - Branch and trap instructions
  - Condition register logical instructions
- Processor control instructions—These instructions are used for synchronizing memory accesses and management of caches, TLBs, and the segment registers.
  - Move to/from SPR instructions
  - Move to/from MSR
  - Synchronize
  - Instruction synchronize
- Memory control instructions—These instructions provide control of caches, TLBs, and segment registers.
  - Supervisor-level cache management instructions
  - User-level cache instructions
  - Segment register manipulation instructions
  - Translation lookaside buffer management instructions



Note that this grouping of the instructions does not indicate which execution unit executes a particular instruction or group of instructions.

Integer instructions operate on byte, half-word, and word operands. The PowerPC architecture uses instructions that are four bytes long and word-aligned. It provides for byte, half-word, and word operand loads and stores between memory and a set of 32 GPRs.

Computational instructions do not modify memory. To use a memory operand in a computation and then modify the same or another memory location, the memory contents must be loaded into a register, modified, and then written back to the target location with distinct instructions.

PowerPC processors follow the program flow when they are in the normal execution state. However, the flow of instructions can be interrupted directly by the execution of an instruction or by an asynchronous event. Either kind of exception may cause one of several components of the system software to be invoked.

#### 2.2.1.2 Calculating Effective Addresses

The effective address (EA) is the 32-bit address computed by the processor when executing a memory access or branch instruction or when fetching the next sequential instruction.

The PowerPC architecture supports two simple memory addressing modes:

- $EA = (\mathbf{r}A|0) + offset (including offset = 0) (register indirect with immediate index)$
- $EA = (\mathbf{r}A|0) + \mathbf{r}B$  (register indirect with index)

These simple addressing modes allow efficient address generation for memory accesses. Calculation of the effective address for aligned transfers occurs in a single clock cycle.

For a memory access instruction, if the sum of the effective address and the operand length exceeds the maximum effective address, the memory operand is considered to wrap around from the maximum effective address to effective address 0.

Effective address computations for both data and instruction accesses use 32-bit unsigned binary arithmetic. A carry from bit 0 is ignored in 32-bit implementations.

# 2.2.2 Implementation-Specific Instruction Set

The EC603e implementation's instruction set is defined as follows:

- The EC603e microprocessor provides hardware support for all 32-bit PowerPC instructions with the exception of floating-point instructions, which, when implemented on the EC603e microprocessor, take a floating-point unavailable exception.
- The EC603e microprocessor provides two implementation-specific instructions used for software table search operations following TLB misses:
  - Load Data TLB Entry (tlbld)
  - Load Instruction TLB Entry (tlbli)
- The EC603e microprocessor implements the following instructions which are defined as optional by the PowerPC architecture:
  - External Control In Word Indexed (eciwx)
  - External Control Out Word Indexed (ecowx)
  - Store Floating-Point as Integer Word (stfiwx)



# 2.3 Cache Implementation

The following subsections describe the general cache characteristics as implemented in the PowerPC architecture, and the EC603e implementation, specifically. PID7v-specific information is noted where applicable.

# 2.3.1 PowerPC Cache Characteristics

The PowerPC architecture does not define hardware aspects of cache implementations. For example, some PowerPC processors, including the EC603e microprocessor, have separate instruction and data caches (Harvard architecture), while others, such as the PowerPC 601<sup>TM</sup> microprocessor, implement a unified cache.

PowerPC microprocessors control the following memory access modes on a page or block basis:

- Write-back/write-through mode
- Caching-inhibited mode
- Memory coherency

Note that in the EC603e microprocessor, a cache block is defined as eight words. The VEA defines cache management instructions that provide a means by which the application programmer can affect the cache contents.

# 2.3.2 Implementation-Specific Cache Implementation

The EC603e microprocessor has two 16-Kbyte, four-way set-associative (instruction and data) caches. The caches are physically addressed, and the data cache can operate in either write-back or write-through mode as specified by the PowerPC architecture.

The data cache is configured as 128 sets of four blocks each. Each block consists of 32 bytes, two state bits, and an address tag. The two state bits implement the three-state MEI (modified/exclusive/invalid) protocol. Each block contains eight 32-bit words. Note that the PowerPC architecture defines the term 'block' as the cacheable unit. For the EC603e microprocessor, the block size is equivalent to a cache line. A block diagram of the data cache organization is shown in Figure 3.

The instruction cache also consists of 128 sets of four blocks, and each block consists of 32 bytes, an address tag, and a valid bit. The instruction cache may not be written to except through a block fill operation. In the PID7v, the instruction cache is blocked only until the critical load completes. The PID7v supports instruction fetching from other instruction cache lines following the forwarding of the critical first double word of a cache line load operation. Successive instruction fetches from the cache line being loaded are forwarded, and accesses to other instruction cache lines can proceed during the cache line load operation. The instruction cache is not snooped, and cache coherency must be maintained by software. A fast hardware invalidation capability is provided to support cache maintenance. The organization of the instruction cache is very similar to the data cache shown in Figure 3.

Each cache block contains eight contiguous words from memory that are loaded from an 8-word boundary (that is, bits A27–A31 of the effective addresses are zero); thus, a cache block never crosses a page boundary. Misaligned accesses across a page boundary can incur a performance penalty.

The EC603e microprocessor's cache blocks are loaded in four beats of 64 bits each when the EC603e microprocessor is configured with a 64-bit data bus; when the EC603e microprocessor is configured with a 32-bit bus, cache block loads are performed with eight beats of 32 bits each. The burst load is performed as critical double word first. The data cache is blocked to internal accesses until the load completes; the instruction cache allows sequential fetching during a cache block load. In the PID7v implementation of the



EC603e microprocessor family, the critical double word is simultaneously written to the cache and forwarded to the requesting unit, thus minimizing stalls due to load delays.

To ensure coherency among caches in a multiprocessor (or multiple caching-device) implementation, the EC603e microprocessor implements the MEI protocol. These three states, modified, exclusive, and invalid, indicate the state of the cache block as follows:

- Modified—The cache block is modified with respect to system memory; that is, data for this address is valid only in the cache and not in system memory.
- Exclusive—This cache block holds valid data that is identical to the data at this address in system memory. No other cache has this data.
- Invalid—This cache block does not hold valid data.

Cache coherency is enforced by on-chip bus snooping logic. Since the EC603e microprocessor's data cache tags are single-ported, a simultaneous load or store and snoop access represent a resource contention. The snoop access is given first access to the tags. The load or store then occurs on the clock following the snoop.




Figure 3. Data Cache Organization

# 2.4 Exception Model

This section describes the PowerPC exception model and the EC603e implementation, specifically. PID7v-specific information is noted where applicable.

# 2.4.1 PowerPC Exception Model

The PowerPC exception mechanism allows the processor to change to supervisor state as a result of external signals, errors, or unusual conditions arising in the execution of instructions, and differ from the arithmetic exceptions defined by the IEEE for floating-point operations which are not supported on the EC603e microprocessor. When exceptions occur, information about the state of the processor is saved to certain registers and the processor begins execution at an address (exception vector) predetermined for each exception. Processing of exceptions occurs in supervisor mode.

Although multiple exception conditions can map to a single exception vector, a more specific condition may be determined by examining a register associated with the exception—for example, the DSISR and the FPSCR. Additionally, some exception conditions can be explicitly enabled or disabled by software.



The PowerPC architecture requires that exceptions be handled in program order; therefore, although a particular implementation may recognize exception conditions out of order, they are presented strictly in order. When an instruction-caused exception is recognized, any unexecuted instructions that appear earlier in the instruction stream, including any that have not yet entered the execute stage, are required to complete before the exception is taken. Any exceptions caused by those instructions are handled first. Likewise, exceptions that are asynchronous and precise are recognized when they occur, but are not handled until the instruction currently in the completion stage successfully completes execution or generates an exception, and the completed store queue is emptied.

Unless a catastrophic condition causes a system reset or machine check exception, only one exception is handled at a time. If, for example, a single instruction encounters multiple exception conditions, those conditions are handled sequentially. After the exception handler handles an exception, the instruction execution continues until the next exception condition is encountered. However, in many cases there is no attempt to re-execute the instruction. This method of recognizing and handling exception conditions sequentially guarantees that exceptions are recoverable.

Exception handlers should save the information stored in SRR0 and SRR1 early to prevent the program state from being lost due to a system reset or machine check exception or to an instruction-caused exception in the exception handler, and before enabling external interrupts.

The PowerPC architecture supports four types of exceptions:

- Synchronous, precise—These are caused by instructions. All instruction-caused exceptions are handled precisely; that is, the machine state at the time the exception occurs is known and can be completely restored. This means that (excluding the trap and system call exceptions) the address of the faulting instruction is provided to the exception handler and that neither the faulting instruction nor subsequent instructions in the code stream will complete execution before the exception is taken. Once the exception is processed, execution resumes at the address of the faulting instruction (or at an alternate address provided by the exception handler). When an exception is taken due to a trap or system call instruction, execution resumes at an address provided by the handler.
- Synchronous, imprecise—The PowerPC architecture defines two imprecise floating-point exception modes, recoverable and nonrecoverable. The EC603e microprocessor does not support the floating-point unit.
- Asynchronous, maskable—The external, system management interrupt (SMI), and decrementer interrupts are maskable asynchronous exceptions. When these exceptions occur, their handling is postponed until the next instruction, and any exceptions associated with that instruction, completes execution. If there are no instructions in the execution units, the exception is taken immediately upon determination of the correct restart address (for loading SRR0).
- Asynchronous, nonmaskable—There are two nonmaskable asynchronous exceptions: system reset and the machine check exception. These exceptions may not be recoverable, or may provide a limited degree of recoverability. All exceptions report recoverability through the MSR[RI] bit.

# 2.4.2 Implementation-Specific Exception Model

As specified by the PowerPC architecture, all EC603e exceptions can be described as either precise or imprecise and either synchronous or asynchronous. Asynchronous exceptions (some of which are maskable) are caused by events external to the processor's execution; synchronous exceptions, which are all handled precisely by the EC603e microprocessor, are caused by instructions. The EC603e exception classes are shown in Table 2.



Synchronous/Asynchronous	Precise/Imprecise	Exception Type
Asynchronous, nonmaskable	Imprecise	Machine check System reset
Asynchronous, maskable	Precise	External interrupt Decrementer System management interrupt
Synchronous	Precise	Instruction-caused exceptions

#### Table 2. Exception Classifications

Although exceptions have other characteristics as well, such as whether they are maskable or nonmaskable, the distinctions shown in Table 2 define categories of exceptions that the EC603e microprocessor handles uniquely. Note that Table 2 includes no synchronous imprecise instructions. While the PowerPC architecture supports imprecise handling of floating-point exceptions, the EC603e microprocessor does not support the floating-point unit.

The EC603e microprocessor's exceptions, and conditions that cause them, are listed in Table 3.

 Table 3. Exceptions and Conditions

Exception Type	Vector Offset (hex)	Causing Conditions
Reserved	00000	_
System reset	00100	A system reset is caused by the assertion of either SRESET or HRESET.
Machine check	00200	A machine check is caused by the assertion of the $\overline{\text{TEA}}$ signal during a data bus transaction, assertion of $\overline{\text{MCP}}$ , or an address or data parity error.
DSI	00300	<ul> <li>The cause of a DSI exception can be determined by the bit settings in the DSISR, listed as follows:</li> <li>1 Set if the translation of an attempted access is not found in the primary hash table entry group (HTEG), or in the rehashed secondary HTEG, or in the range of a DBAT register; otherwise cleared.</li> <li>4 Set if a memory access is not permitted by the page or DBAT protection mechanism; otherwise cleared.</li> <li>5 Set by an eciwx or ecowx instruction if the access is to an address that is marked as write-through, or execution of a load/store instruction that accesses a direct-store segment.</li> <li>6 Set for a store operation and cleared for a load operation.</li> <li>11 Set if eciwx or ecowx is used and EAR[E] is cleared.</li> </ul>
ISI	00400	<ul> <li>An ISI exception is caused when an instruction fetch cannot be performed for any of the following reasons:</li> <li>The effective (logical) address cannot be translated. That is, there is a page fault for this portion of the translation, so an ISI exception must be taken to load the PTE (and possibly the page) into memory.</li> <li>The fetch access is to a direct-store segment (indicated by SRR1[3] set).</li> <li>The fetch access violates memory protection (indicated by SRR1[4] set). If the key bits (Ks and Kp) in the segment register and the PP bits in the PTE are set to prohibit read access, instructions cannot be fetched from this location.</li> </ul>
External interrupt	00500	An external interrupt is caused when MSR[EE] = 1 and the $\overline{INT}$ signal is asserted.



Table 3. Exceptions and Conditions	(Continued)
------------------------------------	-------------

Exception Type	Vector Offset (hex)	Causing Conditions
Alignment	00600	<ul> <li>An alignment exception is caused when the EC603e microprocessor cannot perform a memory access for any of the reasons described below:</li> <li>The operand of a floating-point load or store instruction is not word-aligned.</li> <li>The operand of Imw, stmw, Iwarx, and stwcx. instructions are not aligned.</li> <li>The operand of a single-register load or store operation is not aligned, and the EC603e microprocessor is in little-endian mode (PID6 only).</li> <li>The execution of a floating-point load or store instruction to a direct-store segment.</li> <li>The operand of a load, store, load multiple, store multiple, load string, or store string instruction crosses a segment boundary into a direct-store segment, or crosses a protection boundary.</li> <li>Execution of a misaligned eciwx or ecowx instruction (PID7v only).</li> <li>The instruction is Imw, stmw, Iswi, Iswx, stswi, stswx and the EC603e microprocessor is in little-endian mode.</li> <li>The operand of dcbz is in memory that is write-through-required or caching-inhibited.</li> </ul>
Program	00700	<ul> <li>A program exception is caused by one of the following exception conditions, which correspond to bit settings in SRR1 and arise during execution of an instruction:</li> <li>Illegal instruction—An illegal instruction program exception is generated when execution of an instruction is attempted with an illegal opcode or illegal combination of opcode and extended opcode fields (including PowerPC instructions not implemented in the EC603e microprocessor), or when execution of an optional instruction not provided in the EC603e microprocessor is attempted (these do not include those optional instructions that are treated as no-ops).</li> <li>Privileged instruction—A privileged instruction type program exception is generated when the execution of a privileged instruction is attempted and the MSR register user privilege bit, MSR[PR], is set. In the EC603e microprocessor, this exception is generated for mtspr or mfspr with an invalid SPR field if SPR[0] = 1 and MSR[PR] = 1. This may not be true for all PowerPC processors.</li> <li>Trap—A trap type program exception is generated when any of the conditions specified in a trap instruction is met.</li> </ul>
Floating- point unavailable	00800	A floating-point unavailable exception is caused by an attempt to execute a floating-point instruction (including floating-point load, store, and move instructions) when the floating-point available bit is disabled (MSR[FP] = 0). Note that the EC603e microprocessor takes a floating-point unavailable exception when execution of a floating-point instruction is attempted.
Decrementer	00900	The decrementer exception occurs when the most significant bit of the decrementer (DEC) register transitions from 0 to 1. Must also be enabled with the MSR[EE] bit.
Reserved	00A00-00BFF	_
System call	00C00	A system call exception occurs when a System Call ( <b>sc</b> ) instruction is executed.
Trace	00D00	A trace exception is taken when MSR[SE] =1 or when the currently completing instruction is a branch and MSR[BE] =1.
Reserved	00E00	The EC603e microprocessor does not generate an exception to this vector. Other PowerPC processors may use this vector for floating-point assist exceptions.



Exception Type	Vector Offset (hex)	Causing Conditions
Reserved	00E10-00FFF	—
Instruction translation miss	01000	An instruction translation miss exception is caused when an effective address for an instruction fetch cannot be translated by the ITLB.
Data load translation miss	01100	A data load translation miss exception is caused when an effective address for a data load operation cannot be translated by the DTLB.
Data store translation miss	01200	A data store translation miss exception is caused when an effective address for a data store operation cannot be translated by the DTLB, or where a DTLB hit occurs, and the change bit in the PTE must be set due to a data store operation.
Instruction address breakpoint	01300	An instruction address breakpoint exception occurs when the address (bits 0–29) in the IABR matches the next instruction to complete in the completion unit, and the IABR enable bit (bit 30) is set.
System management interrupt	01400	A system management interrupt is caused when MSR[EE] = 1 and the SMI input signal is asserted.
Reserved	01500–02FFF	—

#### Table 3. Exceptions and Conditions (Continued)

# 2.5 Memory Management

The following subsections describe the memory management features of the PowerPC architecture, and the EC603e implementation, respectively.

# 2.5.1 PowerPC Memory Management

The primary functions of the MMU are to translate logical (effective) addresses to physical addresses for memory accesses, and to provide access protection on blocks and pages of memory.

There are two types of accesses generated by the EC603e microprocessor that require address translation—instruction accesses, and data accesses to memory generated by load and store instructions.

The PowerPC MMU and exception model support demand-paged virtual memory. Virtual memory management permits execution of programs larger than the size of physical memory; demand-paged implies that individual pages are loaded into physical memory from system memory only when they are first accessed by an executing program.

The hashed page table is a variable-sized data structure that defines the mapping between virtual page numbers and physical page numbers. The page table size is a power of 2, and its starting address is a multiple of its size.

The page table contains a number of page table entry groups (PTEGs). A PTEG contains eight page table entries (PTEs) of eight bytes each; therefore, each PTEG is 64 bytes long. PTEG addresses are entry points for table search operations.

Address translations are enabled by setting bits in the MSR—MSR[IR] enables instruction address translations and MSR[DR] enables data address translations.



### 2.5.2 Implementation-Specific Memory Management

The instruction and data memory management units in the EC603e microprocessor provide 4 Gbytes of logical address space accessible to supervisor and user programs with a 4-Kbyte page size and 256-Mbyte segment size. Block sizes range from 128 Kbyte to 256 Mbyte and are software selectable. In addition, the EC603e microprocessor uses an interim 52-bit virtual address and hashed page tables for generating 32-bit physical addresses. The MMUs in the EC603e microprocessor rely on the exception processing mechanism for the implementation of the paged virtual memory environment and for enforcing protection of designated memory areas.

Instruction and data TLBs provide address translation in parallel with the on-chip cache access, incurring no additional time penalty in the event of a TLB hit. A TLB is a cache of the most recently used page table entries. Software is responsible for maintaining the consistency of the TLB with memory. The TLBs are 64-entry, two-way set-associative caches that contain instruction and data address translations. The EC603e microprocessor provides hardware assist for software table search operations through the hashed page table on TLB misses. Supervisor software can invalidate TLB entries selectively.

The EC603e microprocessor also provides independent four-entry BAT arrays for instructions and data that maintain address translations for blocks of memory. These entries define blocks that can vary from 128 Kbytes to 256 Mbytes. The BAT arrays are maintained by system software.

As specified by the PowerPC architecture, the hashed page table is a variable-sized data structure that defines the mapping between virtual page numbers and physical page numbers. The page table size is a power of 2, and its starting address is a multiple of its size.

Also as specified by the PowerPC architecture, the page table contains a number of page table entry groups (PTEGs). A PTEG contains eight page table entries (PTEs) of eight bytes each; therefore, each PTEG is 64 bytes long. PTEG addresses are entry points for table search operations.

# 2.6 Instruction Timing

The EC603e microprocessor is a pipelined superscalar processor. A pipelined processor is one in which the processing of an instruction is reduced into discrete stages. Because the processing of an instruction is broken into a series of stages, an instruction does not require the entire resources of an execution unit. For example, after an instruction completes the decode stage, it can pass on to the next stage, while the subsequent instruction can advance into the decode stage. This improves the throughput of the instruction flow.

The instruction pipeline in the EC603e microprocessor has four major pipeline stages, described as follows:

- The fetch pipeline stage primarily involves retrieving instructions from the memory system and determining the location of the next instruction fetch. Additionally, the BPU decodes branches during the fetch stage and folds out branch instructions before the dispatch stage if possible.
- The dispatch pipeline stage is responsible for decoding the instructions supplied by the instruction fetch stage, and determining which of the instructions are eligible to be dispatched in the current cycle. In addition, the source operands of the instructions are read from the appropriate register file and dispatched with the instruction to the execute pipeline stage. At the end of the dispatch pipeline stage, the dispatched instructions and their operands are latched by the appropriate execution unit.



- During the execute pipeline stage each execution unit that has an executable instruction executes the selected instruction (perhaps over multiple cycles), writes the instruction's result into the appropriate rename register, and notifies the completion stage that the instruction has finished execution. In the case of an internal exception, the execution unit reports the exception to the completion/writeback pipeline stage and discontinues instruction execution until the exception is handled. The exception is not signaled until that instruction is the next to be completed. Execution of most load/store instructions is pipelined. The load/store unit has two pipeline stages. The first stage is for effective address calculation and MMU translation and the second stage is for accessing the data in the cache.
- The complete/writeback pipeline stage maintains the correct architectural machine state and transfers the contents of the rename registers to the GPRs as instructions are retired. If the completion logic detects an instruction causing an exception, all following instructions are cancelled, their execution results in rename registers are discarded, and instructions are fetched from the correct instruction stream.

A superscalar processor is one that issues multiple independent instructions into multiple pipelines allowing instructions to execute in parallel. The EC603e microprocessor has four independent execution units, one each for integer instructions, branch instructions, load/store instructions, and system register instructions. The IU has dedicated register files for maintaining operands (GPRs) allowing integer calculations to occur simultaneously without interference. Integer division performance of the PID7v has been improved, with the **divwu**x and **divw**x instructions executing in 20 clock cycles, instead of the 37 cycles required in the PID6.

The EC603e microprocessor provides support for single-cycle store and it provides an adder/comparator in the system register unit that allows the dispatch and execution of multiple integer add and compare instructions on each cycle. Refer to Chapter 6, "Instruction Timing," in *MPC603e & EC603e RISC Microprocessors User's Manual*. for more information.

Because the PowerPC architecture can be applied to such a wide variety of implementations, instruction timing among various PowerPC processors varies accordingly.

# 2.7 System Interface

The system interface is specific for each PowerPC microprocessor implementation.

The EC603e microprocessor provides a versatile system interface that allows for a wide range of implementations. The interface includes a 32-bit address bus, a 32- or 64-bit data bus, and 56 control and information signals (see Figure 4). The system interface allows for address-only transactions as well as address and data transactions. The EC603e microprocessor control and information signals include the address arbitration, address start, address transfer, transfer attribute, address termination, data arbitration, data transfer, data termination, and processor state signals. Test and control signals provide diagnostics for selected internal circuits.






Figure 4. System Interface

The system interface supports bus pipelining, which allows the address tenure of one transaction to overlap the data tenure of another. The extent of the pipelining depends on external arbitration and control circuitry. Similarly, the EC603e microprocessor supports split-bus transactions for systems with multiple potential bus masters—one device can have mastership of the address bus while another has mastership of the data bus. Allowing multiple bus transactions to occur simultaneously increases the available bus bandwidth for other activity and as a result, improves performance.

The EC603e microprocessor supports multiple masters through a bus arbitration scheme that allows various devices to compete for the shared bus resource. The arbitration logic can implement priority protocols, such as fairness, and can park masters to avoid arbitration overhead. The MEI protocol ensures coherency among multiple devices and system memory. Also, the EC603e microprocessor's on-chip caches and TLBs and optional second-level caches can be controlled externally.

The EC603e microprocessor's clocking structure allows the bus to operate at integer multiples of the processor cycle time.

The following sections describe the EC603e microprocessor bus support for memory operations. Note that some signals perform different functions depending upon the addressing protocol used.

# 2.7.1 Memory Accesses

The EC603e microprocessor's data bus is configured at power-up to either a 32- or 64-bit width. When the EC603e microprocessor is configured with a 32-bit data bus, memory accesses allow transfer sizes of 8, 16, 24, or 32 bits in one bus clock cycle. Data transfers occur in either single-beat transactions, or two-beat or eight-beat burst transactions, with a single-beat transaction transferring as many as 32 bits. Single- or double-beat transactions are caused by noncached accesses that access memory directly (that is, reads and writes when caching is disabled, caching-inhibited accesses, and stores in write-through mode). Eight-beat burst transactions, which always transfer an entire cache line (32 bytes), are initiated when a line is read from or written to memory.

When the EC603e microprocessor is configured with a 64-bit data bus, memory accesses allow transfer sizes of 8, 16, 24, 32, 40, 48, 56, or 64 bits in one bus clock cycle. Data transfers occur in either single-beat transactions or four-beat burst transactions. Single-beat transactions are caused by noncached accesses that access memory directly (that is, reads and writes when caching is disabled, caching-inhibited accesses, and stores in write-through mode). Four-beat burst transactions, which always transfer an entire cache line (32 bytes), are initiated when a line is read from or written to memory.



### 2.7.2 Signals

The EC603e microprocessor signals are grouped as follows:

- Address arbitration signals—The EC603e microprocessor uses these signals to arbitrate for address bus mastership.
- Address transfer start signals—These signals indicate that a bus master has begun a transaction on the address bus.
- Address transfer signals—These signals, which consist of the address bus, address parity, and address parity error signals, are used to transfer the address and to ensure the integrity of the transfer.
- Transfer attribute signals—These signals provide information about the type of transfer, such as the transfer size and whether the transaction is bursted, write-through, or caching-inhibited.
- Address transfer termination signals—These signals are used to acknowledge the end of the address phase of the transaction. They also indicate whether a condition exists that requires the address phase to be repeated.
- Data arbitration signals—The EC603e microprocessor uses these signals to arbitrate for data bus mastership.
- Data transfer signals—These signals, which consist of the data bus, data parity, and data parity error signals, are used to transfer the data and to ensure the integrity of the transfer.
- Data transfer termination signals—Data termination signals are required after each data beat in a data transfer. In a single-beat transaction, the data termination signals also indicate the end of the tenure, while in burst accesses, the data termination signals apply to individual beats and indicate the end of the tenure only after the final data beat. They also indicate whether a condition exists that requires the data phase to be repeated.
- System status signals—These signals include the interrupt signal, checkstop signals, and both softand hard-reset signals. These signals are used to interrupt and, under various conditions, to reset the processor.
- Processor state signals—These signals indicate the state of the reservation coherency bit, enable the time base, provide machine quiesce control, and cause a machine halt on execution of a **tlbsync** instruction.
- IEEE 1149.1(JTAG)/COP interface signals—The IEEE 1149.1 test unit and the common on-chip processor (COP) unit are accessed through a shared set of input, output, and clocking signals. The IEEE 1149.1/COP interface provides a means for boundary scan testing and internal debugging of the EC603e microprocessor.
- Test interface signals—These signals are used for production testing.
- Clock signals—These signals determine the system clock frequency. These signals can also be used to synchronize multiprocessor systems.

#### NOTE

A bar over a signal name indicates that the signal is active low—for example,  $\overline{ARTRY}$  (address retry) and  $\overline{TS}$  (transfer start). Active-low signals are referred to as asserted (active) when they are low and negated when they are high. Signals that are not active low, such as AP[0–3] (address bus parity signals) and TT[0–4] (transfer type signals) are referred to as asserted when they are high and negated when they are low.



# 2.7.3 Signal Configuration

Figure 5 illustrates the EC603e microprocessor's logical pin configuration, showing how the signals are grouped.




Figure 5. Signal Groups

# 1.8 System Design and Programming Considerations

The EC603e microprocessor is built upon the low power consumption, low cost and high performance attributes of the 603 while providing the system designer additional capabilities through higher processor clock speeds (to 100 MHz), increases in cache size (16-Kbyte instruction and data caches) and set associativity (four-way), and greater system clock flexibility. The following subsections describe the differences between the 603 and the EC603e microprocessor that affect the system designer and programmer already familiar with the operation of the 603.

The design enhancements to the EC603e microprocessor are described in the following sections as changes that can require a modification to the hardware or software configuration of a system designed for the 603.



### 1.8.1 Hardware Features

The following hardware features of the EC603e microprocessor may require system designers to modify systems designed for the 603.

### 1.8.1.1 Replacement of XATS Signal by CSE1 Signal

The EC603e microprocessor employs four-way set associativity for both the instruction and data caches, in place of the two-way set associativity used in the 603. This change requires the use of an additional cache set entry (CSE1) signal to indicate which member of the cache set is being loaded during a cache line fill. The CSE1 signal on the EC603e microprocessor is in the same pin location as the  $\overline{XATS}$  signal on the 603. Note that the  $\overline{XATS}$  signal is no longer needed by the EC603e microprocessor because support for access to direct-store segments has been removed.

Table 4 shows the CSE[0–1] signal encoding indicating the cache set element selected during a cache load operation.

CSE[0-1]	Cache Set Element
00	Set 0
01	Set 1
10	Set 2
11	Set 3

Table 4. CSE[0–1] Signals

#### 1.8.1.2 Addition of Half-Clock Bus Multipliers

Some of the reserved clock configuration signal settings of the 603 are redefined to allow more flexible selection of higher internal and bus clock frequencies. The EC603e microprocessor provides programmable internal processor clock rates of 1x, 1.5x, 2x, 2.5x, 3x, 3.5x, and 4x multiples of the externally supplied clock frequency. For additional information, refer to the appropriate device-specific hardware specifications.

# **1.8.2 Software Features**

The features of the EC603e microprocessor described in the following sections affect software originally written for the 603.

#### 1.8.2.1 16-Kbyte Instruction and Data Caches

The instruction and data caches of the EC603e microprocessor are 16 Kbytes in size, compared to the 8-Kbyte instruction and data caches of the 603. The increase in cache size may require modification of cache flush routines. The increase in cache size is also reflected in four-way set associativity of the instruction and data caches in place of the two-way set associativity in the 603.

#### 1.8.2.2 Clock Configuration Available in HID1 Register

Bits 0–3 in the new HID1 register (SPR 1009) provides software read-only access to the configuration of the PLL\_CFG signals. The HID1 register is not implemented in the 603.



#### 1.8.2.3 Performance Enhancements

The following enhancements provide improved performance without any required changes to software (other than compiler optimization) or hardware designed for the 603:

- Support for single-cycle store.
- Addition of adder/comparator in system register unit allows dispatch and execution of multiple integer add and compare instructions on each cycle.
- Addition of a key bit (bit 12) to SRR1 to provide information about memory protection violations prior to page table search operations. This key bit is set when the combination of the settings in the appropriate Kx bit in the segment register and the MSR[PR] bit indicates that when the PP bits in the PTE are set to either 00 or 01, a protection violation exists; if this is the case for a data write operation with a DTLB miss, the changed (C) bit in the page tables should not be updated (see Table 5). This reduces the time required to execute the page table search routine since the software no longer has to explicitly read both the Kx and MSR[PR] bits to determine whether a protection violation exists before updating the C bit.

Segment Register [Ks, Kp]	MSR[PR]	SRR1[Key] Generated on DTLB Misses
0x	0	0
x0	1	0
1x	0	1
x1	1	1

#### Table 5. SRR1 [Key] Bit Generated by the EC603e Microprocessor

Note that this key bit indicates a protection violation if the PTE[pp] bits are either 00 or 01.



Information in this document is provided solely to enable system and software implementers to use PowerPC microprocessors. There are no express or implied copyright licenses granted hereunder to design or fabricate PowerPC integrated circuits or integrated circuits based on the information in this document.

Motorola reserves the right to make changes without further notice to any products herein. Motorola makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does Motorola assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation consequential or incidental damages. "Typical" parameters can and do vary in different applications. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. Motorola does not convey any license under its patent rights nor the rights of others. Motorola products are not designed, intended, or authorized for use as components in systems intended for surgical implant into the body, or other applications intended to support or sustain life, or for any other application in which the failure of the Motorola product could create a situation where personal injury or death may occur. Should Buyer purchase or use Motorola products for any such unintended or unauthorized application, Buyer shall indemnify and hold Motorola and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that Motorola was negligent regarding the design or manufacture of the part.

Motorola and (A) are registered trademarks of Motorola, Inc. Mfax and EC603e are trademarks of Motorola, Inc. Motorola, Inc. is an Equal Opportunity/ Affirmative Action Employer.

The PowerPC name, the PowerPC logotype, PowerPC 601, and PowerPC 603 are trademarks of International Business Machines Corporation used by Motorola under license from International Business Machines Corporation.

#### Motorola Literature Distribution Centers:

USA/EUROPE: Motorola Literature Distribution; P.O. Box 5405; Denver, Colorado 80217; Tel.: 1-800-441-2447 or 1-303-675-2140; World Wide Web Address: http://dc.nmd.com/

JAPAN: Nippon Motorola Ltd SPD, Strategic Planning Office 4-32-1, Nishi-Gotanda Shinagawa-ku, Tokyo 141, Japan Tel.: 81-3-5487-8488 ASIA/PACIFIC: Motorola Semiconductors H.K. Ltd.; 8B Tai Ping Industrial Park, 51 Ting Kok Road, Tai Po, N.T., Hong Kong; Tel.: 852-26629298

Mfax<sup>TM</sup>: RMFAX0@email.sps.mot.com; TOUCHTONE 1-602-244-6609; US & Canada ONLY (800) 774-1848; World Wide Web Address: http://sps.motorola.com/mfax INTERNET: http://motorola.com/sps

Technical Information: Motorola Inc. SPS Customer Support Center 1-800-521-6274; electronic mail address: crc@wmkmail.sps.mot.com. Document Comments: FAX (512) 891-2638, Attn: RISC Applications Engineering. World Wide Web Addresses: http://www.mot.com/SPS/PowerPC/ http://www.mot.com/SPS/RISC/netcomm/

MPE603E/D

(**M**) motorola

For More Information On This Product, Go to: www.freescale.com