

## . . eescale Semiconductor

Technical Data

# **RF Power Field Effect Transistors**

### N-Channel Enhancement-Mode Lateral MOSFETs

Designed for broadband commercial and industrial applications with frequencies up to 470 MHz. The high gain and broadband performance of these devices make them ideal for large-signal, common source amplifier applications in 12.5 volt mobile FM equipment.

Specified Performance @ 470 MHz, 12.5 Volts
 Output Power — 70 Watts
 Power Gain — 11.5 dB
 Efficiency — 60%

• Capable of Handling 20:1 VSWR, @ 15.6 Vdc, 470 MHz, 2 dB Overdrive

#### **Features**

- · Excellent Thermal Stability
- Characterized with Series Equivalent Large-Signal Impedance Parameters
- Broadband-Full Power Across the Band: 135-175 MHz 400-470 MHz
- Broadband Demonstration Amplifier Information Available Upon Request
- 200°C Capable Plastic Package
- N Suffix Indicates Lead-Free Terminations. RoHS Compliant.
- In Tape and Reel. T1 Suffix = 500 Units per 44 mm, 13 inch Reel.

## Document Number: MRF1570N

Rev. 10, 6/2009

**RoHS** 

# MRF1570NT1 MRF1570FNT1

470 MHz, 70 W, 12.5 V LATERAL N-CHANNEL BROADBAND RF POWER MOSFETs



CASE 1366A-03, STYLE 1 TO-272-8 PLASTIC MRF1570FNT1



### **Table 1. Maximum Ratings**

Rating	Symbol	Value	Unit
Drain-Source Voltage	V <sub>DSS</sub>	+0.5, +40	Vdc
Gate-Source Voltage	V <sub>GS</sub>	± 20	Vdc
Total Device Dissipation @ T <sub>C</sub> = 25°C Derate above 25°C	P <sub>D</sub>	165 0.5	W W/°C
Storage Temperature Range	T <sub>stg</sub>	- 65 to +150	°C
Operating Junction Temperature	TJ	200	°C

#### **Table 2. Thermal Characteristics**

Characteristic	Symbol	Value <sup>(1)</sup>	Unit
Thermal Resistance, Junction to Case	$R_{ heta JC}$	0.29	°C/W

#### **Table 3. ESD Protection Characteristics**

Test Conditions	Class
Human Body Model	1 (Minimum)
Machine Model	M2 (Minimum)
Charge Device Model	C2 (Minimum)

### Table 4. Moisture Sensitivity Level

Test Methodology	Rating	Package Peak Temperature	Unit
Per JESD22-A113, IPC/JEDEC J-STD-020	3	260	°C

MTTF calculator available at <a href="http://www.freescale.com/rf">http://www.freescale.com/rf</a>. Select Software & Tools/Development Tools/Calculators to access MTTF calculators by product.






Table 5. Electrical Characteristics ( $T_A = 25^{\circ}C$  unless otherwise noted)

Characteristic	Symbol	Min	Тур	Max	Unit
Off Characteristics				•	
Zero Gate Voltage Drain Current (V <sub>DS</sub> = 60 Vdc, V <sub>GS</sub> = 0 Vdc)	I <sub>DSS</sub>	_	_	1	μΑ
On Characteristics	1		•		
Gate Threshold Voltage (V <sub>DS</sub> = 12.5 Vdc, I <sub>D</sub> = 0.8 mAdc)	V <sub>GS(th)</sub>	1		3	Vdc
Drain-Source On-Voltage (V <sub>GS</sub> = 10 Vdc, I <sub>D</sub> = 2.0 Adc)	V <sub>DS(on)</sub>	_	_	1	Vdc
Dynamic Characteristics					
Input Capacitance (Includes Input Matching Capacitance) (V <sub>DS</sub> = 12.5 Vdc, V <sub>GS</sub> = 0 V, f = 1 MHz)	C <sub>iss</sub>	_	_	500	pF
Output Capacitance (V <sub>DS</sub> = 12.5 Vdc, V <sub>GS</sub> = 0 V, f = 1 MHz)	C <sub>oss</sub>	_	_	250	pF
Reverse Transfer Capacitance (V <sub>DS</sub> = 12.5 Vdc, V <sub>GS</sub> = 0 V, f = 1 MHz)	C <sub>rss</sub>	_	_	35	pF
RF Characteristics (In Freescale Test Fixture)	•		•	•	
Common-Source Amplifier Power Gain $(V_{DD} = 12.5 \text{ Vdc}, P_{out} = 70 \text{ W}, I_{DQ} = 800 \text{ mA})$ f = 470 MHz	G <sub>ps</sub>	_	11.5		dB
Drain Efficiency $(V_{DD} = 12.5 \text{ Vdc}, P_{out} = 70 \text{ W}, I_{DQ} = 800 \text{ mA})$ $f = 470 \text{ MHz}$	η	_	60	_	%






B1, B2, B3, B4, B5,	B6 Long Ferrite Beads, Fair Rite Products	L3, L4	5 nH, 2 Turn Inductors, Coilcraft
C1, C32, C37, C43	270 pF, 100 mil Chip Capacitors	L5, L6, L7, L8	1 Turn, #18 AWG, 0.33" ID Inductors
C2, C20, C21	33 pF, 100 mil Chip Capacitors	L9, L10	3 Turn, #16 AWG, 0.165" ID Inductors
C3	18 pF, 100 mil Chip Capacitor	N1, N2	Type N Flange Mounts
C4, C5	30 pF, 100 mil Chip Capacitors	R1, R2	25.5 Ω Chip Resistors (1206)
C6, C7	180 pF, 100 mil Chip Capacitors	R3, R4	9.3 Ω Chip Resistors (1206)
C8, C9	150 pF, 100 mil Chip Capacitors	Z1	0.32" x 0.080" Microstrip
C10, C15	300 pF, 100 mil Chip Capacitors	Z2, Z3	0.46" x 0.080" Microstrip
C11, C16, C33, C39	10 μF, 50 V Electrolytic Capacitors	Z4, Z5	0.34" x 0.080" Microstrip
C12, C17, C34, C40	0.1 μF, 100 mil Chip Capacitors	Z6, Z7	0.45" x 0.080" Microstrip
C13, C18, C35, C41	1000 pF, 100 mil Chip Capacitors	Z8, Z9, Z10, Z11	0.28" x 0.240" Microstrip
C14, C19, C36, C42	470 pF, 100 mil Chip Capacitors	Z12, Z13	0.39" x 0.080" Microstrip
C22, C23	110 pF, 100 mil Chip Capacitors	Z14, Z15	0.27" x 0.080" Microstrip
C24, C25	68 pF, 100 mil Chip Capacitors	Z16, Z17	0.25" x 0.080" Microstrip
C26, C27	120 pF, 100 mil Chip Capacitors	Z18, Z19	0.29" x 0.080" Microstrip
C28, C29	24 pF, 100 mil Chip Capacitors	Z20, Z21	0.14" x 0.080" Microstrip
C30, C31	27 pF, 100 mil Chip Capacitors	Z22	0.32" x 0.080" Microstrip
C38, C44	240 pF, 100 mil Chip Capacitors	Board	31 mil Glass Teflon <sup>®</sup>
L1, L2	17.5 nH, 6 Turn Inductors, Coilcraft		

Figure 1. 135 - 175 MHz Broadband Test Circuit Schematic






Freescale has begun the transition of marking Printed Circuit Boards (PCBs) with the Freescale Semiconductor signature/logo. PCBs may have either Motorola or Freescale markings during the transition period. These changes will have no impact on form, fit or function of the current product.

Figure 2. 135 - 175 MHz Broadband Test Circuit Component Layout

### TYPICAL CHARACTERISTICS, 135 - 175 MHz








Figure 4. Input Return Loss versus Output Power



### **TYPICAL CHARACTERISTICS, 135 - 175 MHz**




Figure 5. Gain versus Output Power




Figure 6. Drain Efficiency versus Output Power




Figure 7. Output Power versus Biasing Current




Figure 8. Drain Efficiency versus Biasing Current




Figure 9. Output Power versus Supply Voltage





Figure 10. Drain Efficiency versus Supply Voltage






B1, B2, B3, B4, B5, B	6 Long Ferrite Beads, Fair Rite Products	L1, L2, L3, L4	1 Turn, #18 AWG, 0.085" ID Inductors
C1, C9, C15, C32	270 pF, 100 mil Chip Capacitors	L5, L6	2 Turn, #16 AWG, 0.165" ID Inductors
C2, C3	7.5 pF, 100 mil Chip Capacitors	N1, N2	Type N Flange Mounts
C4	5.1 pF, 100 mil Chip Capacitor	R1, R2	25.5 Ω Chip Resistors (1206)
C5, C6	180 pF, 100 mil Chip Capacitors	R3, R4	10 Ω Chip Resistors (1206)
C7, C8	47 pF, 100 mil Chip Capacitors	Z1	0.240" x 0.080" Microstrip
C10, C16, C37, C42	120 pF, 100 mil Chip Capacitors	Z2	0.185" x 0.080" Microstrip
C11, C17, C33, C38	10 μF, 50 V Electrolytic Capacitors	Z3, Z4	1.500" x 0.080" Microstrip
C12, C18, C34, C39	470 pF, 100 mil Chip Capacitors	Z5, Z6	0.150" x 0.240" Microstrip
C13, C19, C35, C40	1200 pF, 100 mil Chip Capacitors	Z7, Z8	0.140" x 0.240" Microstrip
C14, C20, C36, C41	0.1 μF, 100 mil Chip Capacitors	Z9, Z10	0.140" x 0.240" Microstrip
C21, C22	33 pF, 100 mil Chip Capacitors	Z11, Z12	0.150" x 0.240" Microstrip
C23, C24	27 pF, 100 mil Chip Capacitors	Z13, Z14	0.270" x 0.080" Microstrip
C25, C26	15 pF, 100 mil Chip Capacitors	Z15, Z16	0.680" x 0.080" Microstrip
C27, C28	2.2 pF, 100 mil Chip Capacitors	Z17, Z18	0.320" x 0.080" Microstrip
C29, C30	6.2 pF, 100 mil Chip Capacitors	Z19	0.380" x 0.080" Microstrip
C31	1.0 pF, 100 mil Chip Capacitor	Board	31 mil Glass Teflon <sup>®</sup>

Figure 11. 400 - 470 MHz Broadband Test Circuit Schematic





Freescale has begun the transition of marking Printed Circuit Boards (PCBs) with the Freescale Semiconductor signature/logo. PCBs may have either Motorola or Freescale markings during the transition period. These changes will have no impact on form, fit or function of the current product.

Figure 12. 400 - 470 MHz Broadband Test Circuit Component Layout

### TYPICAL CHARACTERISTICS, 400 - 470 MHz




Figure 13. Output Power versus Input Power




Figure 14. Input Return Loss versus Output Power



### **TYPICAL CHARACTERISTICS, 400 - 470 MHz**




Figure 15. Gain versus Output Power




Figure 16. Drain Efficiency versus Output Power




Figure 17. Output Power versus Biasing Current




Figure 18. Drain Efficiency versus Biasing Current




Figure 19. Output Power versus Supply Voltage





Figure 20. Drain Efficiency versus Supply Voltage






B1, B2, B3, B4, B5, B	6 Long Ferrite Beads, Fair Rite Products	N1, N2	Type N Flange Mounts
C1, C8, C14, C28	270 pF, 100 mil Chip Capacitors	R1, R2	1.0 kΩ Chip Resistors (1206)
C2, C3	10 pF, 100 mil Chip Capacitors	R3, R4	10 Ω Chip Resistors (1206)
C4, C5	180 pF, 100 mil Chip Capacitors	Z1	0.40" x 0.080" Microstrip
C6, C7	47 pF, 100 mil Chip Capacitors	Z2, Z3	0.26" x 0.080" Microstrip
C9, C15, C33, C38	120 pF, 100 mil Chip Capacitors	Z4, Z5	1.35" x 0.080" Microstrip
C10, C16, C29, C34	10 μF, 50 V Electrolytic Capacitors	Z6, Z7	0.17" x 0.240" Microstrip
C11, C17, C30, C35	470 pF, 100 mil Chip Capacitors	Z8, Z9	0.12" x 0.240" Microstrip
C12, C18, C31, C36	1200 pF, 100 mil Chip Capacitors	Z10, Z11	0.14" x 0.240" Microstrip
C13, C19, C32, C37	0.1 μF, 100 mil Chip Capacitors	Z12, Z13	0.15" x 0.240" Microstrip
C20, C21	22 pF, 100 mil Chip Capacitors	Z14, Z15	0.18" x 0.172" Microstrip
C22, C23	20 pF, 100 mil Chip Capacitors	Z16, Z17	1.23" x 0.080" Microstrip
C24, C25, C26, C27	5.1 pF, 100 mil Chip Capacitors	Z18, Z19	0.12" x 0.080" Microstrip
L1, L2	1 Turn, #18 AWG, 0.115" ID Inductors	Z20	0.40" x 0.080" Microstrip
L3, L4	2 Turn, #16 AWG, 0.165" ID Inductors	Board	31 mil Glass Teflon®

Figure 21. 450 - 520 MHz Broadband Test Circuit Schematic





Freescale has begun the transition of marking Printed Circuit Boards (PCBs) with the Freescale Semiconductor signature/logo. PCBs may have either Motorola or Freescale markings during the transition period. These changes will have no impact on form, fit or function of the current product.

Figure 22. 450 - 520 MHz Broadband Test Circuit Component Layout

### TYPICAL CHARACTERISTICS, 450 - 520 MHz




Figure 23. Output Power versus Input Power




Figure 24. Input Return Loss versus Output Power



### **TYPICAL CHARACTERISTICS, 450 - 520 MHz**




Figure 25. Gain versus Output Power




Figure 26. Drain Efficiency versus Output Power




Figure 27. Output Power versus Biasing Current




Figure 28. Drain Efficiency versus Biasing Current




Figure 29. Output Power versus Supply Voltage





Figure 30. Drain Efficiency versus Supply Voltage




### **TYPICAL CHARACTERISTICS**



This above graph displays calculated MTTF in hours x ampere<sup>2</sup> drain current. Life tests at elevated temperatures have correlated to better than  $\pm 10\%$  of the theoretical prediction for metal failure. Divide MTTF factor by  $I_D{}^2$  for MTTF in a particular application.

Figure 31. MTTF Factor versus Junction Temperature





$V_{DD} =$	12.5	V.	lno :	= 0.8	Α.	Pout =	70	W
V I )  ) —	12.0	٧,	11)(.) -	- 0.0	л,	– זווח י	. , ,	V V

f MHz	<b>Z</b> <sub>in</sub> Ω	<b>Z<sub>OL</sub>*</b> Ω
135	2.8 +j0.05	0.65 +j0.42
155	3.9 +j0.34	1.01 +j0.63
175	2.4 -j0.47	0.71 +j0.37

Vpp -	12.5 V	lno -	0 8 A	P	70 W
v DD -	12.J V,	ı ı )( ) —	U.U A,	out -	1 O VV

f MHz	<b>Z</b> <sub>in</sub> Ω	<b>Z<sub>OL</sub>*</b> Ω
400	0.92 -j0.71	1.05 -j1.10
440	1.12 -j1.11	0.83 -j1.45
470	0.82 -j0.79	0.59 -j1.43

 $V_{DD}$  = 12.5 V,  $I_{DQ}$  = 0.8 A,  $P_{out}$  = 70 W

f MHz	<b>Z</b> <sub>in</sub> Ω	<b>Z<sub>OL</sub>*</b> Ω
450	0.94 -j1.12	0.61 -j1.14
470	1.03 -j1.17	0.62 -j1.12
500	0.95 -j1.71	0.75 -j1.03
520	0.62 -j1.74	0.77 -j0.97

 $Z_{in}$  = Complex conjugate of source impedance.

 $Z_{OL}^*$  = Complex conjugate of the load impedance at given output power, voltage, frequency, and  $\eta_D > 50$  %.

Notes: Impedance  $Z_{in}$  was measured with input terminated at 50  $\Omega$ . Impedance  $Z_{OL}$  was measured with output terminated at 50  $\Omega$ .




Figure 32. Series Equivalent Input and Output Impedance

MRF1570NT1 MRF1570FNT1



#### APPLICATIONS INFORMATION

#### **DESIGN CONSIDERATIONS**

This device is a common-source, RF power, N-Channel enhancement mode, Lateral Metal-Oxide Semiconductor Eield-Effect Transistor (MOSFET). Freescale Application Note AN211A, "FETs in Theory and Practice", is suggested reading for those not familiar with the construction and characteristics of FETs.

This surface mount packaged device was designed primarily for VHF and UHF mobile power amplifier applications. Manufacturability is improved by utilizing the tape and reel capability for fully automated pick and placement of parts. However, care should be taken in the design process to insure proper heat sinking of the device.


The major advantages of Lateral RF power MOSFETs include high gain, simple bias systems, relative immunity from thermal runaway, and the ability to withstand severely mismatched loads without suffering damage.

#### **MOSFET CAPACITANCES**

The physical structure of a MOSFET results in capacitors between all three terminals. The metal oxide gate structure determines the capacitors from gate-to-drain  $(C_{gd}),\,$  and gate-to-source  $(C_{gs}).$  The PN junction formed during fabrication of the RF MOSFET results in a junction capacitance from drain-to-source  $(C_{ds}).$  These capacitances are characterized as input  $(C_{iss}),\,$  output  $(C_{oss})\,$  and reverse transfer  $(C_{rss})\,$  capacitances on data sheets. The relationships between the inter-terminal capacitances and those given on data sheets are shown below. The  $C_{iss}\,$  can be specified in two ways:

- 1. Drain shorted to source and positive voltage at the gate.
- Positive voltage of the drain in respect to source and zero volts at the gate.

In the latter case, the numbers are lower. However, neither method represents the actual operating conditions in RF applications.



### **DRAIN CHARACTERISTICS**

One critical figure of merit for a FET is its static resistance in the full-on condition. This on-resistance,  $R_{DS(on)}$ , occurs in the linear region of the output characteristic and is specified at a specific gate-source voltage and drain current. The

drain-source voltage under these conditions is termed  $V_{DS(on)}$ . For MOSFETs,  $V_{DS(on)}$  has a positive temperature coefficient at high temperatures because it contributes to the power dissipation within the device.

BV<sub>DSS</sub> values for this device are higher than normally required for typical applications. Measurement of BV<sub>DSS</sub> is not recommended and may result in possible damage to the device.

#### **GATE CHARACTERISTICS**

The gate of the RF MOSFET is a polysilicon material, and is electrically isolated from the source by a layer of oxide. The DC input resistance is very high - on the order of  $10^9 \,\Omega$  — resulting in a leakage current of a few nanoamperes.

Gate control is achieved by applying a positive voltage to the gate greater than the gate-to-source threshold voltage,  $V_{\rm GS(th)}$ .

**Gate Voltage Rating** — Never exceed the gate voltage rating. Exceeding the rated  $V_{\text{GS}}$  can result in permanent damage to the oxide layer in the gate region.

**Gate Termination** — The gates of these devices are essentially capacitors. Circuits that leave the gate open-circuited or floating should be avoided. These conditions can result in turn-on of the devices due to voltage build-up on the input capacitor due to leakage currents or pickup.

Gate Protection — These devices do not have an internal monolithic zener diode from gate-to-source. If gate protection is required, an external zener diode is recommended. Using a resistor to keep the gate-to-source impedance low also helps dampen transients and serves another important function. Voltage transients on the drain can be coupled to the gate through the parasitic gate-drain capacitance. If the gate-to-source impedance and the rate of voltage change on the drain are both high, then the signal coupled to the gate may be large enough to exceed the gate-threshold voltage and turn the device on.

#### DC BIAS

Since this device is an enhancement mode FET, drain current flows only when the gate is at a higher potential than the source. RF power FETs operate optimally with a quiescent drain current ( $I_{DQ}$ ), whose value is application dependent. This device was characterized at  $I_{DQ}$  = 800 mA, which is the suggested value of bias current for typical applications. For special applications such as linear amplification,  $I_{DQ}$  may have to be selected to optimize the critical parameters.

The gate is a dc open circuit and draws no current. Therefore, the gate bias circuit may generally be just a simple resistive divider network. Some special applications may require a more elaborate bias system.

#### **GAIN CONTROL**

Power output of this device may be controlled to some degree with a low power dc control signal applied to the gate, thus facilitating applications such as manual gain control, ALC/AGC and modulation systems. This characteristic is very dependent on frequency and load line.



#### **AMPLIFIER DESIGN**


Impedance matching networks similar to those used with bipolar transistors are suitable for this device. For examples see Freescale Application Note AN721, "Impedance Matching Networks Applied to RF Power Transistors." Large-signal impedances are provided, and will yield a good first pass approximation.

Since RF power MOSFETs are triode devices, they are not unilateral. This coupled with the very high gain of this device yields a device capable of self oscillation. Stability may be

achieved by techniques such as drain loading, input shunt resistive loading, or output to input feedback. The RF test fixture implements a parallel resistor and capacitor in series with the gate, and has a load line selected for a higher efficiency, lower gain, and more stable operating region. See Freescale Application Note AN215A, "RF Small-Signal Design Using Two-Port Parameters" for a discussion of two port network theory and stability.




### **PACKAGE DIMENSIONS**



© FREESCALE SEMICONDUCTOR, INC. ALL RIGHTS RESERVED.	MECHANICA	L OUTLINE	PRINT VERSION NOT TO SCALE	
TITLE:		DOCUMENT NO: 98ASA99295D		REV: E
TO-272, SPLIT LEAD		CASE NUMBER	R: 1366–05	03 AUG 2007
JI LIT LEAD		STANDARD: NO	N-JEDEC	





© FREESCALE SEMICONDUCTOR, INC. ALL RIGHTS RESERVED.		MECHANICAL OUTLINE		PRINT VERSION NOT TO SCALE	
TITLE:	T0-272		DOCUMENT NO	): 98ASA99295D	REV: E
	SPLIT LEAD		CASE NUMBER	R: 1366–05	03 AUG 2007
			STANDARD: NO	N-JEDEC	



#### NOTES:

- 1. CONTROLLING DIMENSION: INCH
- 2. INTERPRET DIMENSIONS AND TOLERANCES PER ASME Y14.5M-1994.
- 3. DATUM PLANE -H- IS LOCATED AT THE TOP OF LEAD AND IS COINCIDENT WITH THE LEAD WHERE THE LEAD EXITS THE PLASTIC BODY AT THE TOP OF THE PARTING LINE.

DIMENSIONS DO NOT INCLUDE MOLD PROTRUSION. ALLOWABLE PROTRUSION IS .006 PER SIDE. DIMENSIONS DO INCLUDE MOLD MISMATCH AND ARE DETERMINED AT DATUM PLANE -H-.

DIMENSIONS DO NOT INCLUDE DAMBAR PROTRUSION. ALLOWABLE
DAMBAR PROTRUSION SHALL BE .005 TOTAL IN EXCESS OF THE DIMENSIONS
AT MAXIMUM MATERIAL CONDITION.

(A) CROSSHATCHING REPRESENTS THE EXPOSED AREA OF THE HEAT SLUG.

STYLE 1:

PIN 1 - SOURCE (COMMON) PIN 5 - SOURCE (COMMON)


PIN 2 — DRAIN PIN 6 — GATE
PIN 3 — DRAIN PIN 7 — GATE

PIN 4 - SOURCE (COMMON)
PIN 8 - SOURCE (COMMON)
PIN 9 - SOURCE (COMMON)

	IN	СН	МІ	LLIMETER			INCH	l N	MILLIMETER
DIM	MIN	MAX	MIN	MAX	DIM	MIN	MAX	MIN	I MAX
Α	.098	.108	2.49	2.74	b1	.088	.094	2.2	4 2.39
A1	.000	.004	0.000	0.10	b2	.066	.072	1.68	B 1.83
A2	.100	.104	2.54	2.64	b3	.067	.073	1.70	0 1.85
D	.928	.932	23.57	23.67	c1	.007	.011	0.17	78 0.279
D1	.810	BSC	20	).57 BSC	е	.1	04 BSC		2.64 BSC
D2	.604		15.34		e1	.2	210 BSC		5.33 BSC
Е	.296	.304	7.52	7.72	9	0.	6.	0.	6.
E1	.248	.252	6.30	6.40	aaa		.004		0.1
E2	.162		4.11						
E3	.241	.245	6.12	6.22					
L	.060	.070	1.52	1.78					
Р	.126	.134	3.20	3.40					
©	© FREESCALE SEMICONDUCTOR, INC. ALL RIGHTS RESERVED.			MECHANICA	L OUT	LINE	PRINT VERS	SION NO	T TO SCALE
TITLE:	TITLE: TO-272				DOCU	MENT NO	): 98ASA99295	D	REV: E
	SPLIT LEAD				CASE	NUMBER	: 1366–05		03 AUG 2007


STANDARD: NON-JEDEC





© FREESCALE SEMICONDUCTOR, INC	. MECHANIC	AL OUTLINE	PRINT VERSION NOT TO SCALE	
TITLE:		DOCUMENT NO: 98ASA10537D		REV: D
TO-272, 8 L PLASTIC		CASE NUMBER	R: 1366A-03	03 AUG 2007
1 2/13/10		STANDARD: NO	ON-JEDEC	





© FREESCALE SEMICONDUCTOR, INC. ALL RIGHTS RESERVED.	MECHANICAL OUTLINE		PRINT VERSION NC	T TO SCALE
TITLE:		DOCUMENT NO	): 98ASA10537D	REV: D
TO-272, 8 LEAD		CASE NUMBER: 1366A-03		03 AUG 2007
PLASTIC		STANDARD: NO	N-JEDEC	



#### NOTES:

- 1. CONTROLLING DIMENSION: INCH
- 2. INTERPRET DIMENSIONS AND TOLERANCES PER ASME Y14.5M-1994.
- 3. DIMENSIONS "D" AND "E1" DO NOT INCLUDE MOLD PROTRUSION. ALLOWABLE PROTRUSION IS .006 PER SIDE. DIMENSIONS "D" AND "E1" DO INCLUDE MOLD MISMATCH AND ARE DETERMINED AT DATUM PLANE -H-.
- 4. DIMENSIONS "b" AND "b1" DO NOT INCLUDE DAMBAR PROTRUSION. ALLOWABLE DAMBAR PROTRUSION SHALL BE .005 TOTAL IN EXCESS OF THE "b1" AND "b2" DIMENSIONS AT MAXIMUM MATERIAL CONDITION.
- 5. CROSSHATCHING REPRESENTS THE EXPOSED AREA OF THE HEAT SLUG.
- 6. DIMENSION A2 APPLIES WITHIN ZONE "J" ONLY.

### STYLE 1:

PIN 1 - SOURCE (COMMON) PIN 5 - SOURCE (COMMON)

PIN 2 - DRAIN PIN 6 - GATE

PIN 3 - DRAIN PIN 7 - GATE

PIN 4 - SOURCE (COMMON) PIN 8 - SOURCE (COMMON) PIN 9 - SOURCE (COMMON)

	INCH MILLIMETER		LLIMETER			INCH	T N	MILLIMETER	
DIM	MIN	MAX	MIN	MAX	DIM	MIN	MAX	MIN	
Α	.098	.106	2.49	2.69	b	.105	.111	2.6	7 2.82
A1	.038	.044	0.96	1.12	b1	.088	.094	2.2	4 2.39
A2	.040	.042	1.02	1.07	b2	.066	.072	1.68	B 1.83
D	.926	.934	23.52	23.72	b3	.067	.073	1.70	1.85
D1	.810	BSC	20	).57 BSC	b4	.077	.083	1.96	5 2.11
D2	.604		15.34		c1	.007	.011	.178	3 .279
E	.492	.500	12.50	12.70	е	.1	.104 BSC		2.64 BSC
E1	.246	.254	6.25	6.45	e1	.2	210 BSC		5.33 BSC
E2	.162		4.11		e2	.2	229 BSC	:	5.82 BSC
E3	.241	.245	6.12	6.22					
F	.025	BSC	0	.64 BSC	aaa		.004		0.1
Р	.126	.134	3.20	3.40	bbb		.008		0.2
© FREESCALE SEMICONDUCTOR, INC. ALL RIGHTS RESERVED.  MECHANICAL OUTLINE PRINT VERSION						SION NO	T TO SCALE		
TITLE:	TITLE:					MENT NO	): 98ASA10537I	D	REV: D
	TO-272, 8 LEAD					CASE NUMBER: 1366A-03 03 AUG 200			03 AUG 2007
	PLASTIC				STANDARD: NON-JEDEC				



### PRODUCT DOCUMENTATION, TOOLS AND SOFTWARE

Refer to the following documents to aid your design process.

#### **Application Notes**

- AN211A: Field Effect Transistors in Theory and Practice
- AN215A: RF Small-Signal Design Using Two-Port Parameters
- AN721: Impedance Matching Networks Applied to RF Power Transistors
- AN1907: Solder Reflow Attach Method for High Power RF Devices in Plastic Packages
- AN3263: Bolt Down Mounting Method for High Power RF Transistors and RFICs in Over-Molded Plastic Packages
- AN3789: Clamping of High Power RF Transistors and RFICs in Over-Molded Plastic Packages
- AN4005: Thermal Management and Mounting Method for the PLD 1.5 RF Power Surface Mount Package

#### **Engineering Bulletins**

• EB212: Using Data Sheet Impedances for RF LDMOS Devices

#### **Software**

• Electromigration MTTF Calculator

For Software and Tools, do a Part Number search at http://www.freescale.com, and select the "Part Number" link. Go to the Software & Tools tab on the part's Product Summary page to download the respective tool.

#### **REVISION HISTORY**

The following table summarizes revisions to this document.

Revision	Date	Description
9	June 2008	Corrected specified performance values for power gain and efficiency on p. 1 to match typical performance values in the functional test table on p. 2
		<ul> <li>Replaced Case Outline 1366-04 with 1366-05, Issue E, p. 1, 16-18. Removed Drain-ID label from View Y-Y. Added Pin 9 designation. Changed dimensions D2 and E2 from basic to .604 Min and .162 Min, respectively.</li> </ul>
		<ul> <li>Replaced Case Outline 1366A-02 with 1366A-03, Issue D, p. 1, 19-21. Removed Drain-ID label from View Y-Y. Removed Surface Alignment tolerance label for cross hatched section on View Y-Y. Added Pin 9 designation. Changed dimensions D2 and E2 from basic to .604 Min and .162 Min, respectively. Added dimension E3. Restored dimensions F and P designators to DIM column on Sheet 3.</li> </ul>
		Added Product Documentation and Revision History, p. 22
10	June 2009	Modified data sheet to reflect MSL rating change from 1 to 3 as a result of the standardization of packing process as described in Product and Process Change Notification number, PCN13516, p. 1
		Added AN3789, Clamping of High Power RF Transistors and RFICs in Over-Molded Plastic Packages to Product Documentation, Application Notes, p. 22
		Added Electromigration MTTF Calculator availability to Product Software, p. 22



#### How to Reach Us:

Home Page:

www.freescale.com

Web Support:

http://www.freescale.com/support

#### **USA/Europe or Locations Not Listed:**

Freescale Semiconductor, Inc.
Technical Information Center, EL516
2100 East Elliot Road
Tempe, Arizona 85284
1-800-521-6274 or +1-480-768-2130
www.freescale.com/support

#### Europe, Middle East, and Africa:

Freescale Halbleiter Deutschland GmbH Technical Information Center Schatzbogen 7 81829 Muenchen, Germany +44 1296 380 456 (English) +46 8 52200080 (English) +49 89 92103 559 (German) +33 1 69 35 48 48 (French) www.freescale.com/support

#### Japan:

Freescale Semiconductor Japan Ltd. Headquarters ARCO Tower 15F 1-8-1, Shimo-Meguro, Meguro-ku, Tokyo 153-0064 Japan 0120 191014 or +81 3 5437 9125 support.japan@freescale.com

#### Asia/Pacific:

Freescale Semiconductor China Ltd. Exchange Building 23F No. 118 Jianguo Road Chaoyang District Beijing 100022 China +86 10 5879 8000 support.asia@freescale.com

### For Literature Requests Only:

Freescale Semiconductor Literature Distribution Center 1-800-441-2447 or +1-303-675-2140 Fax: +1-303-675-2150 LDCForFreescaleSemiconductor@hibbertgroup.com

Information in this document is provided solely to enable system and software implementers to use Freescale Semiconductor products. There are no express or implied copyright licenses granted hereunder to design or fabricate any integrated circuits or integrated circuits based on the information in this document.

Freescale Semiconductor reserves the right to make changes without further notice to any products herein. Freescale Semiconductor makes no warranty, representation or quarantee regarding the suitability of its products for any particular purpose, nor does Freescale Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation consequential or incidental damages. "Typical" parameters that may be provided in Freescale Semiconductor data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals", must be validated for each customer application by customer's technical experts. Freescale Semiconductor does not convey any license under its patent rights nor the rights of others. Freescale Semiconductor products are not designed, intended, or authorized for use as components in systems intended for surgical implant into the body, or other applications intended to support or sustain life, or for any other application in which the failure of the Freescale Semiconductor product could create a situation where personal injury or death may occur. Should Buyer purchase or use Freescale Semiconductor products for any such unintended or unauthorized application, Buyer shall indemnify and hold Freescale Semiconductor and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that Freescale Semiconductor was negligent regarding the design or manufacture of the part.

Freescale <sup>™</sup> and the Freescale logo are trademarks of Freescale Semiconductor, Inc. All other product or service names are the property of their respective owners. © Freescale Semiconductor, Inc. 2008-2009. All rights reserved.

RoHS-compliant and/or Pb-free versions of Freescale products have the functionality and electrical characteristics of their non-RoHS-compliant and/or non-Pb-free counterparts. For further information, see http://www.freescale.com or contact your Freescale sales representative.

For information on Freescale's Environmental Products program, go to http://www.freescale.com/epp.



Document Number: MRF1570N

Rev. 10, 6/2009