

Technical Data

RF LDMOS Wideband Integrated Power Amplifiers

The MW4IC2020N wideband integrated circuit is designed with on-chip matching that makes it usable from 1600 to 2400 MHz. This multi-stage structure is rated for 26 to 28 Volt operation and covers all typical cellular base station modulation formats.


Final Application


Typical Two-Tone Performance: V_{DD} = 26 Volts, I_{DQ1} = 80 mA, I_{DQ2} = 200 mA, I_{DQ3} = 300 mA, P_{out} = 20 Watts PEP, Full Frequency Band Power Gain — 29 dB
 IMD — -32 dBc
 Drain Efficiency — 26% (at 1805 MHz) and 20% (at 1990 MHz)

Driver Applications

- Typical GSM EDGE Performance: $V_{DD} = 26$ Volts, $I_{DQ1} = 80$ mA, $I_{DQ2} = 230$ mA, $I_{DQ3} = 230$ mA, $P_{out} = 5$ Watts Avg., Full Frequency Band Power Gain — 29 dB Spectral Regrowth @ 400 kHz Offset = -66 dBc Spectral Regrowth @ 600 kHz Offset = -77 dBc EVM — 1% rms
- Typical CDMA Performance: V_{DD} = 26 Volts, I_{DQ1} = 80 mA, I_{DQ2} = 240 mA, I_{DQ3} = 250 mA, P_{out} = 1 Watt Avg., Full Frequency Band, IS-95 CDMA (Pilot, Sync, Paging, Traffic Codes 8 Through 13), Channel Bandwidth = 1.2288 MHz. PAR = 9.8 dB @ 0.01% Probability on CCDF. Power Gain 30 dB
 ACPR @ 885 kHz Offset = -61 dBc in 30 kHz Bandwidth ALT1 @ 1.25 MHz Offset = -69 dBc in 12.5 kHz Bandwidth ALT2 @ 2.25 MHz Offset = -59 dBc in 1 MHz Bandwidth
- Capable of Handling 3:1 VSWR, @ 26 Vdc, 1990 MHz, 8 Watts CW Output Power
- Stable into a 3:1 VSWR. All Spurs Below -60 dBc @ 100 mW to 8 W CW Pout.
- Characterized with Series Equivalent Large-Signal Impedance Parameters
- On-Chip Matching (50 Ohm Input, DC Blocked, >5 Ohm Output)
- Integrated Temperature Compensation with Enable/Disable Function
- On-Chip Current Mirror gm Reference FET for Self Biasing Application (1)
- Integrated ESD Protection
- 200°C Capable Plastic Package
- N Suffix Indicates Lead Free Terminations. RoHS Compliant.








 Refer to AN1987, Quiescent Current Control for the RF Integrated Circuit Device Family. Go to <u>http://www.freescale.com/rf.</u> Select Documentation/Application Notes - AN1987.



Document Number: MW4IC2020N

Rev. 9, 5/2006

1805-1990 MHz, 20 W, 26 V GSM/GSM EDGE, CDMA RF LDMOS WIDEBAND INTEGRATED POWER AMPLIFIERS



 $\ensuremath{\textcircled{\sc c}}$ Freescale Semiconductor, Inc., 2006. All rights reserved.



Table 1. Maximum Ratings

Rating	Symbol	Value	Unit
Drain-Source Voltage	V _{DSS}	-0.5, +65	Vdc
Gate-Source Voltage	V _{GS}	-0.5, +15	Vdc
Storage Temperature Range	T _{stg}	-65 to +175	°C
Operating Junction Temperature	Т _Ј	200	°C
Input Power	P _{in}	20	dBm

Table 2. Thermal Characteristics

Characteristic	Symbol	Value ⁽¹⁾	Unit
Thermal Resistance, Junction to Case Stage 1 Stage 2 Stage 3	R _{θJC}	10.5 5.1 2.3	°C/W

Table 3. ESD Protection Characteristics

Test Conditions	Class
Human Body Model	2 (Minimum)
Machine Model	M3 (Minimum)
Charge Device Model	C5 (Minimum)

Table 4. Moisture Sensitivity Level

Test Methodology	Rating	Package Peak Temperature	Unit
Per JESD 22-A113, IPC/JEDEC J-STD-020	3	260	°C

Table 5. Electrical Characteristics (T_C = 25° C unless otherwise noted)

Characteristic		Min	Тур	Max	Unit
Functional Tests (In Freescale Wideband 1805-1990 MHz Test Fixture, 50 ohm system) V _{DD} = 26 Vdc, I _{DQ1} = 80 mA, I _{DQ2} = 200 mA, I _{DQ3} = 300 mA, P _{out} = 20 W PEP, f1 = 1990 MHz, f2 = 1990.1 MHz and f1 = 1805 MHz, f2 = 1805.1 MHz, Two-Tone CW					
Power Gain	G _{ps}	27	29	—	dB
Drain Efficiency f1 = 1805 MHz, f2 = 1805.1 MHz f1 = 1990 MHz, f2 = 1990.1 MHz	η _D	24 18	26 20	—	%
Input Return Loss	IRL	_	—	- 10	dB
Intermodulation Distortion	IMD		-32	-27	dBc

Typical Performances (In Freescale Test Fixture, 50 ohm system) V_{DD} = 26 Vdc, I_{DQ1} = 80 mA, I_{DQ2} = 200 mA, I_{DQ3} = 300 mA, 1805 MHz<Frequency<1990 MHz, 1-Tone

Saturated Pulsed Output Power (f = 1 kHz, Duty Cycle 10%)	P _{sat}	_	33	_	W
Quiescent Current Accuracy over Temperature (-10 to 85°C) (2)	ΔI_{QT}	—	±5	—	%
Gain Flatness in 30 MHz Bandwidth @ Pout = 1 W CW	G _F	—	0.15	—	dB
Deviation from Linear Phase in 30 MHz Bandwidth @ P _{out} = 1 W CW 1805-1880 MHz 1930-1990 MHz	Φ	_	±0.5 ±0.2	—	0
Delay @ P _{out} = 1 W CW Including Output Matching	Delay	—	1.8	—	ns
Part-to-Part Phase Variation @ P _{out} = 1 W CW	$\Phi\Delta$	—	±10	—	0

 Refer to AN1955, Thermal Measurement Methodology of RF Power Amplifiers. Go to <u>http://www.freescale.com/rf</u>. Select Documentation/Application Notes - AN1955.

2. Refer to AN1977, *Quiescent Current Thermal Tracking Circuit in the RF Integrated Circuit Family.* Go to <u>http://www.freescale.com/rf.</u> Select Documentation/Application Notes - AN1977.

(continued)



Table 5. Electrical Characteristics (T_C = 25°C unless otherwise noted) (continued)

Characteristic	Symbol	Min	Тур	Мах	Unit


Typical CDMA Performances (In Modified CDMA Test Fixture, 50 ohm system) V_{DD} = 26 Vdc, _{DQ1} = 80 mA, I_{DQ2} = 240 mA, I_{DQ3} = 250 mA, P_{out} = 1 W Avg., I1930 MHz<Frequency<1990 MHz, 1-Tone, 9 Channel Forward Model (Pilot, Paging, Sync, Traffic Codes 8 through 13). Peak/Avg. Ratio 9.8 dB @ 0.01% Probability on CCDF.

Power Gain	G _{ps}	_	30	_	dB
Drain Efficiency	η _D	—	5	—	%
Adjacent Channel Power Ratio (±885 kHz in 30 kHz Bandwidth)	ACPR	—	-61	—	dBc
Alternate 1 Channel Power Ratio (±1.25 MHz in 12.5 kHz Bandwidth)	ALT1	—	-69	—	dBc
Alternate 2 Channel Power Ratio (±2.25 MHz in 1 MHz Bandwidth)	ALT2	—	-59	—	dBc

Typical GSM EDGE Performances (In Modified GSM EDGE Test Fixture, 50 ohm system) V_{DD} = 26 Vdc, I_{DQ1} = 80 mA, I_{DQ2} = 230 mA, I_{DQ3} = 230 mA, P_{out} = 5 W Ava, 1805 MHz<Frequency<1990 MHz

Power Gain	G _{ps}	_	29	_	dB
Drain Efficiency	η_D	—	15	_	%
Error Vector Magnitude	EVM	—	1	_	% rms
Spectral Regrowth at 400 kHz Offset	SR1	—	-66	_	dBc
Spectral Regrowth at 600 kHz Offset	SR2	_	-77		dBc






Z1	1.820" x 0.087" Microstrip	Z6	0.303" x 0.087" Microstrip
Z2	0.245" x 0.087" Microstrip	Z7	0.640" x 0.087" Microstrip
Z3	0.345" x 0.236" Microstrip	Z8	0.334" x 0.087" Microstrip
Z4	0.327" x 0.087" Microstrip	Z9	1.231" x 0.043" Microstrip
Z5	0.271" x 0.087" Microstrip	PCB	Taconic TLX8-0300, 0.030", $\epsilon_r = 2.55$

Part	Description	Part Number	Manufacturer
C1, C2, C3	10 µF, 35 V Tantalum Capacitors	TAJE226M035	AVX
C4	220 nF Chip Capacitor (1206)	12065C224K28	AVX
C5, C6, C8	6.8 pF 100B Chip Capacitors	100B6R8CW	ATC
C7	0.5 pF 100B Chip Capacitor	100B0R5BW	ATC
C9, C11	1.8 pF 100B Chip Capacitors	100B1R8BW	ATC
C10	2.2 pF 100B Chip Capacitor	100B2R2BW	ATC
C12	1 pF 100B Chip Capacitor	100B1R0BW	ATC
C13	0.3 pF 100B Chip Capacitor	100B0R3BW	ATC
C14	10 pF 100B Chip Capacitor	100B100GW	ATC
R1, R2, R3	1.8 kΩ Chip Resistors (1206)		






Freescale has begun the transition of marking Printed Circuit Boards (PCBs) with the Freescale Semiconductor signature/logo. PCBs may have either Motorola or Freescale markings during the transition period. These changes will have no impact on form, fit or function of the current product.






TYPICAL CHARACTERISTICS









TYPICAL CHARACTERISTICS





Figure 14. Spectral Regrowth at 400 and 600 kHz versus Output Power @ 1840 MHz

MW4IC2020NBR1 MW4IC2020GNBR1


versus Output Power @ 1960 MHz




TYPICAL CHARACTERISTICS



drain current. Life tests at elevated temperatures have correlated to better than $\pm 10\%$ of the theoretical prediction for metal failure. Divide MTTF factor by I_D^2 for MTTF in a particular application.





 V_{DD} = 26 V, I_{DQ1} = 80 mA, I_{DQ2} = 200 mA, I_{DQ3} = 300 mA, P_{out} = 20 W PEP

f MHz	Z _{in} Ω	Z _{load} Ω
1805	40.00 + j6.50	8.75 - j1.42
1842	40.00 + j2.00	7.00 - j2.70
1880	40.00 - j1.50	5.90 - j2.97
1930	40.00 - j1.80	5.46 - j3.20
1960	40.00 - j2.10	4.30 - j3.35
1990	40.00 - j2.60	4.45 - j3.30

- Z_{in} = Device input impedance as measured from gate to ground.
- Z_{load} = Test circuit impedance as measured from drain to ground.






Figure 17. Series Equivalent Input and Load Impedance



PACKAGE DIMENSIONS



© FREESCALE SEMICONDUCTOR, INC. ALL RIGHTS RESERVED.			PRINT VERSION NOT TO SCALE	
TITLE:		NO: 98ARH99164A	REV: L	
TO-272 WIDE BO	CASE NUM	CASE NUMBER: 1329-09 13 MAR 200		
MOETT EEAD	STANDARE	: NON-JEDEC		



VIEW Y-Y


© FREESCALE SEMICONDUCTOR, INC. ALL RIGHTS RESERVED.		LOUTLINE	PRINT VERSION NO	T TO SCALE
TITLE:	DOCUMENT NO): 98ARH99164A	REV: L	
TO-272 WIDE BODY MULTI-LEAD		CASE NUMBER: 1329–09 13 MAR		13 MAR 2006
	STANDARD: NO	N-JEDEC		




NOTES:

- 1. CONTROLLING DIMENSION: INCH
- 2. INTERPRET DIMENSIONS AND TOLERANCES PER ASME Y14.5M-1994.
- 3. DATUM PLANE -H- IS LOCATED AT THE TOP OF LEAD AND IS COINCIDENT WITH THE LEAD WHERE THE LEAD EXITS THE PLASTIC BODY AT THE TOP OF THE PARTING LINE.
- 4. DIMENSIONS "D" AND "E1" DO NOT INCLUDE MOLD PROTRUSION. ALLOWABLE PROTRUSION IS .006 (0.15) PER SIDE. DIMENSIONS "D" AND "E1" DO INCLUDE MOLD MISMATCH AND ARE DETERMINED AT DATUM PLANE -H-.
- 5. DIMENSIONS "b", "b1", "b2" AND "b3" DO NOT INCLUDE DAMBAR PROTRUSION. ALLOWABLE DAMBAR PROTRUSION SHALL BE .005 (0.13) TOTAL IN EXCESS OF THE "b", "b1", "b2" AND "b3" DIMENSIONS AT MAXIMUM MATERIAL CONDITION.
- 6. HATCHING REPRESENTS THE EXPOSED AREA OFTHE HEAT SLUG. HATCHED AREA SHOWN IS ON THE SAME PLANE.
- 7. DIM A2 APPLIES WITHIN ZONE "J" ONLY.

	IN	СН	MIL	LIMETER		INCH		м	ILLIMETER	
DIM	MIN	MAX	MIN	MAX	DIM	MIN	MAX	MIN	MAX	
А	.100	.104	2.54	2.64	b	.011	.017	0.28	3 0.43	
A1	.038	.044	0.96	1.12	b1	.037	.043	0.94	l.09	
A2	.040	.042	1.02	1.07	b2	.037	.043	0.94	1.09	
D	.928	.932	23.57	23.67	b3	.225	.231	5.72	2 5.87	
D1	.810	BSC	20	.57 BSC	c1	.007	.011	.18	.28	
E	.551	.559	14.00	14.20	е	.0	.054 BSC		1.37 BSC	
E1	.353	.357	8.97	9.07	e1	.0	40 BSC	1.02 BSC		
E2	.346	.350	8.79	8.89	e2	.2	.224 BSC		5.69 BSC	
F	.025	BSC	0.	64 BSC	e3	.1:	.150 BSC 3.8		3.81 BSC	
М	.600		15.24		r1	.063	.068	1.6	1.73	
N	.270		6.86							
					aaa		.004	.10		
C	© FREESCALE SEMICONDUCTOR, INC. ALL RIGHTS RESERVED.					LINE	PRINT VERS	SION NC	T TO SCALE	
TITLE	TITLE: TO-272 WIDE BODY MULTI-LEAD			DOCU	IMENT NO): 98ARH99164	A	REV: L		
				CASE	NUMBER	: 1329–09		13 MAR 2006		
					STAN	DARD: NO	N-JEDEC			



© FREESCALE SEMICONDUCTOR, INC. ALL RIGHTS RESERVED.	MECHANICA	LOUTLINE	PRINT VERSION NO	T TO SCALE
TITLE: TO-272WB, 16 LE	DOCUMENT NO	98ASA10532D	REV: E	
GULL WING	CASE NUMBER	: 1329A-03	3 APR 2006	
PLASTIC	STANDARD: NO	N-JEDEC		



© FREESCALE SEMICONDUCTOR, INC. ALL RIGHTS RESERVED.	MECHANICAL O	UTLINE	PRINT VERSION NO	T TO SCALE
TITLE: TO-272WB, 16 LE		CUMENT NO	98ASA10532D	REV: E
GULL WING		SE NUMBER	: 1329A-03	3 APR 2006
PLASTIC	STA	ANDARD: NO	N-JEDEC	



NOTES:

- 1. CONTROLLING DIMENSION: INCH
- 2. INTERPRET DIMENSIONS AND TOLERANCES PER ASME Y14.5M-1994.
- 3. DATUM PLANE -H- IS LOCATED AT THE TOP OF LEAD AND IS COINCIDENT WITH THE LEAD WHERE THE LEAD EXITS THE PLASTIC BODY AT THE TOP OF THE PARTING LINE.
- 4. DIMENSIONS "D" AND "E1" DO NOT INCLUDE MOLD PROTRUSION. ALLOWABLE PROTRUSION IS .006 (0.15) PER SIDE. DIMENSIONS "D" AND "E1" DO INCLUDE MOLD MISMATCH AND ARE DETERMINED AT DATUM PLANE -H-.
- 5. DIMENSIONS "b", "b1", "b2" AND "b3" DO NOT INCLUDE DAMBAR PROTRUSION. ALLOWABLE DAMBAR PROTRUSION SHALL BE .005 (0.13) TOTAL IN EXCESS OF THE "b", "b1", "b2" AND "b3" DIMENSIONS AT MAXIMUM MATERIAL CONDITION.
- 6. HATCHING REPRESENTS EXPOSED AREA OF THE HEAT SLUG. HATCHED AREA SHOWN IS ON THE SAME PLANE.

	II	NCH	MIL	LIMETER		INCH		МІ	LLIMETER	
DIM	MIN	MAX	MIN	MAX	DIM	MIN	MAX	MIN	MAX	
A	.100	.104	2.54	2.64	b	.011	.017	0.28	0.43	
A1	.001	.004	0.02	0.10	b1	.037	.043	0.94	1.09	
A2	.099	.110	2.51	2.79	b2	.037	.043	0.94	1.09	
D	.928	.932	23.57	23.67	b3	.225	.231	5.72	5.87	
D1	.810	BSC	20.	57 BSC	c1	.007	.011	.18	.28	
E	.429	.437	10.9	11.1	е	.05	64 BSC	1.	37 BSC	
E1	.353	.357	8.97	9.07	e1	.04	.040 BSC		1.02 BSC	
E2	.346	.350	8.79	8.89	e2	.22	.224 BSC		5.69 BSC	
L	.018	.024	4.90	5.06	eЗ	.15	0 BSC	3.81 BSC		
L1	.01	BSC	.02	25 BSC	r1	.063	.068	1.6	1.73	
м	.600		15.24		t	2'	8.	2.	8.	
N	.270		6.86							
					aaa		.004		.10	
© FREESCALE SEMICONDUCTOR, INC. ALL RIGHTS RESERVED.				AL OUTLINE PRINT VERSION NOT TO SC			OT TO SCALE			
TITLE: TO-272WB, 16 LEAD				AD	DOCUMENT NO: 98ASA10532D REV: E			REV: E		
GULL WING				CASE NUMBER: 1329A-03 3 APR 2				3 APR 2006		
PLASTIC				STANDARD: NON-JEDEC						

How to Reach Us:

Home Page: www.freescale.com

E-mail: support@freescale.com

USA/Europe or Locations Not Listed: Freescale Semiconductor

Freescale Semiconductor Technical Information Center, CH370 1300 N. Alma School Road Chandler, Arizona 85224 +1-800-521-6274 or +1-480-768-2130 support@freescale.com

Europe, Middle East, and Africa:

Freescale Halbleiter Deutschland GmbH Technical Information Center Schatzbogen 7 81829 Muenchen, Germany +44 1296 380 456 (English) +46 8 52200080 (English) +49 89 92103 559 (German) +33 1 69 35 48 48 (French) support@freescale.com

Japan:

Freescale Semiconductor Japan Ltd. Headquarters ARCO Tower 15F 1-8-1, Shimo-Meguro, Meguro-ku, Tokyo 153-0064 Japan 0120 191014 or +81 3 5437 9125 support.japan@freescale.com

Asia/Pacific:

Freescale Semiconductor Hong Kong Ltd. Technical Information Center 2 Dai King Street Tai Po Industrial Estate Tai Po, N.T., Hong Kong +800 2666 8080 support.asia@freescale.com

For Literature Requests Only:

Freescale Semiconductor Literature Distribution Center P.O. Box 5405 Denver, Colorado 80217 1-800-441-2447 or 303-675-2140 Fax: 303-675-2150 LDCForFreescaleSemiconductor@hibbertgroup.com Information in this document is provided solely to enable system and software implementers to use Freescale Semiconductor products. There are no express or implied copyright licenses granted hereunder to design or fabricate any integrated circuits or integrated circuits based on the information in this document.

Freescale Semiconductor reserves the right to make changes without further notice to any products herein. Freescale Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does Freescale Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation consequential or incidental damages. "Typical" parameters that may be provided in Freescale Semiconductor data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals", must be validated for each customer application by customer's technical experts. Freescale Semiconductor does not convey any license under its patent rights nor the rights of others. Freescale Semiconductor products are not designed, intended, or authorized for use as components in systems intended for surgical implant into the body, or other applications intended to support or sustain life, or for any other application in which the failure of the Freescale Semiconductor product could create a situation where personal injury or death may occur. Should Buyer purchase or use Freescale Semiconductor products for any such unintended or unauthorized application, Buyer shall indemnify and hold Freescale Semiconductor and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that Freescale Semiconductor was negligent regarding the design or manufacture of the part.

Freescale [™] and the Freescale logo are trademarks of Freescale Semiconductor, Inc. All other product or service names are the property of their respective owners. © Freescale Semiconductor, Inc. 2006. All rights reserved.

RoHS-compliant and/or Pb-free versions of Freescale products have the functionality and electrical characteristics of their non-RoHS-compliant and/or non-Pb-free counterparts. For further information, see http://www.freescale.com or contact your Freescale sales representative.

For information on Freescale's Environmental Products program, go to http://www.freescale.com/epp.

