

P89LPC9402

8-bit microcontroller with accelerated two-clock 80C51 core 8 kB 3 V byte-erasable flash with 32 segment 4 LCD driver

Rev. 01 — 22 April 2009

Product data sheet

1. General description

The P89LPC9402 is a multi-chip module consisting of a P89LPC931A1 single-chip microcontroller combined with a PCF8576D universal LCD driver in a low-cost 64-pin package. The LCD driver provides 32 segments and supports from 1 to 4 backplanes. Display overhead is minimized by an on-chip display RAM with auto-increment addressing.

2. Features

2.1 Principal features

- 8 kB byte-erasable flash code memory organized into 1 kB sectors and 64-byte pages. Single-byte erasing allows any byte(s) to be used as non-volatile data storage.
- 256-byte RAM data memory.
- 32 segment × 4 backplane LCD controller supports from 1 to 4 backplanes.
- Two analog comparators with selectable inputs and reference source.
- Two 16-bit counter/timers (each may be configured to toggle a port output upon timer overflow or to become a PWM output).
- A 23-bit system timer that can also be used as real-time clock consisting of a 7-bit prescaler and a programmable and readable 16-bit timer.
- Enhanced UART with a fractional baud rate generator, break detect, framing error detection, and automatic address detection; 400 kHz byte-wide I²C-bus communication port and SPI communication port.
- 2.4 V to 3.6 V V_{DD} operating range. I/O pins are 5 V tolerant (may be pulled up or driven to 5.5 V).
- Enhanced low voltage (brownout) detect allows a graceful system shutdown when power fails.
- 64-pin LQFP package with 20 microcontroller I/O pins minimum and up to 23 microcontroller I/O pins while using on-chip oscillator and reset options.

2.2 Additional features

A high performance 80C51 CPU provides instruction cycle times of 111 ns to 222 ns for all instructions except multiply and divide when executing at 18 MHz. This is six times the performance of the standard 80C51 running at the same clock frequency. A lower clock frequency for the same performance results in power savings and reduced EMI.



8-bit microcontroller with accelerated two-clock 80C51 core

- Serial flash In-Circuit Programming (ICP) allows simple production coding with commercial EPROM programmers. Flash security bits prevent reading of sensitive application programs.
- Serial flash In-System Programming (ISP) allows coding while the device is mounted in the end application.
- In-Application Programming (IAP) of the flash code memory. This allows changing the code in a running application.
- Watchdog timer with separate on-chip oscillator, nominal 400 kHz, calibrated to ±5 %, requiring no external components. The watchdog prescaler is selectable from eight values.
- High-accuracy internal RC oscillator option, with clock doubler option, allows operation without external oscillator components. The RC oscillator option is selectable and fine tunable.
- Switching on the fly among internal RC oscillator, watchdog oscillator, external clock source provides optimal support of minimal power active mode with fast switching to maximum performance.
- Idle and two different power-down reduced power modes. Improved wake-up from Power-down mode (a LOW interrupt input starts execution). Typical power-down current is 1 μA (total power-down with voltage comparators disabled).
- Active-LOW reset. On-chip power-on reset allows operation without external reset components. A software reset function is also available.
- Configurable on-chip oscillator with frequency range options selected by user programmed flash configuration bits. Oscillator options support frequencies from 20 kHz to the maximum operating frequency of 18 MHz.
- Oscillator fail detect. The watchdog timer has a separate fully on-chip oscillator allowing it to perform an oscillator fail detect function.
- Programmable port output configuration options: quasi-bidirectional, open-drain, push-pull, input-only.
- High current sourcing/sinking (20 mA) on eight I/O pins (P0.3 to P0.7, P1.4, P1.6, P1.7). All other port pins have high sinking capability (20 mA). A maximum limit is specified for the entire chip.
- Port 'input pattern match' detect. Port 0 may generate an interrupt when the value of the pins match or do not match a programmable pattern.
- Controlled slew rate port outputs to reduce EMI. Outputs have approximately 10 ns minimum ramp times.
- Only power and ground connections are required to operate the P89LPC9402 when internal reset option is selected.
- Four interrupt priority levels.
- Eight keypad interrupt inputs, plus two additional external interrupt inputs.
- Schmitt trigger port inputs.
- Second data pointer.
- Emulation support.
- LED drive capability (20 mA) on all port pins. A maximum limit is specified for the entire chip.

8-bit microcontroller with accelerated two-clock 80C51 core

3. Ordering information

Table 1. Ordering information

Type number	Package									
	Name	Description	Version							
P89LPC9402FBD	LQFP64	plastic low profile quad flat package; 64 leads; body $14 \times 14 \times 1.4$ mm	SOT791-1							


3.1 Ordering options

Table 2. Part options


Type number	Flash memory	Temperature range	Frequency
P89LPC9402FBD	8 kB	–40 °C to +85 °C	0 MHz to 18 MHz

8-bit microcontroller with accelerated two-clock 80C51 core


4. Block diagram




8-bit microcontroller with accelerated two-clock 80C51 core



8-bit microcontroller with accelerated two-clock 80C51 core




5. Functional diagram



8-bit microcontroller with accelerated two-clock 80C51 core

6. Pinning information

6.1 Pinning



6.2 Pin description

Table 3. Pin description

Symbol	Pin	Туре	Description
P0.0 to P0.7		I/O	Port 0: Port 0 is an 8-bit I/O port with a user-configurable output type. During reset Port 0 latches are configured in the input only mode with the internal pull-up disabled. The operation of Port 0 pins as inputs and outputs depends upon the port configuration selected. Each port pin is configured independently. Refer to Section 7.14.1 "Port configurations" and Table 12 "Static electrical characteristics" for details. The Keypad Interrupt feature operates with Port 0 pins. All pins have Schmitt trigger inputs.
			Port 0 also provides various special functions as described below:
P0.0/CMP2/	8	I/O	P0.0 — Port 0 bit 0.
KBI0		0	CMP2 — Comparator 2 output
		I	KBI0 — Keyboard input 0.

Product data sheet

8-bit microcontroller with accelerated two-clock 80C51 core

Table 3. Pin description ...continued

	Pin description		
Symbol	Pin		Description Pod Port Obit 4
P0.1/CIN2B KBI1	/ 5	I/O	P0.1 — Port 0 bit 1.
		<u> </u>	CIN2B — Comparator 2 positive input B.
Do 0/001104	,	l	KBI1 — Keyboard input 1.
P0.2/CIN2A KBI2	/ 4	I/O	P0.2 — Port 0 bit 2.
NDI2		<u> </u>	CIN2A — Comparator 2 positive input A.
		<u> </u>	KBI2 — Keyboard input 2.
P0.3/CIN1B KBI3	/ 3	I/O	P0.3 — Port 0 bit 3. High current source.
NDIO		<u>l</u>	CIN1B — Comparator 1 positive input B.
		<u> </u>	KBI3 — Keyboard input 3.
P0.4/ CIN1 <i>A</i> KBI4	√ 2	I/O	P0.4 — Port 0 bit 4. High current source.
NDI4		<u> </u>	CIN1A — Comparator 1 positive input A.
		l	KBI4 — Keyboard input 4.
P0.5/ CMPREF/	1	I/O	P0.5 — Port 0 bit 5. High current source.
KBI5		l	CMPREF — Comparator reference (negative) input.
		I	KBI5 — Keyboard input 5.
P0.6/CMP1/	/ 24	I/O	P0.6 — Port 0 bit 6. High current source.
KBI6		0	CMP1 — Comparator 1 output.
		l	KBI6 — Keyboard input 6.
P0.7/T1/KB	17 23	I/O	P0.7 — Port 0 bit 7. High current source.
		I/O	T1 — Timer/counter 1 external count input or overflow output.
		I	KBI7 — Keyboard input 7.
P1.0 to P1.7	7	I/O, I [1]	Port 1: Port 1 is an 8-bit I/O port with a user-configurable output type, except for three pins as noted below. During reset Port 1 latches are configured in the input only mode with the internal pull-up disabled. The operation of the configurable Port 1 pins as inputs and outputs depends upon the port configuration selected. Each of the configurable port pins are programmed independently. Refer to Section 7.14.1 "Port configurations" and Table 12 "Static electrical characteristics" for details. P1.2 to P1.3 are open-drain when used as outputs. P1.5 is input only.
			All pins have Schmitt trigger inputs.
			Port 1 also provides various special functions as described below:
P1.0/TXD	22	I/O	P1.0 — Port 1 bit 0.
		0	TXD — Transmitter output for serial port.
P1.1/RXD	21	I/O	P1.1 — Port 1 bit 1.
		I	RXD — Receiver input for serial port.
P1.2/T0/SC	L 17	I/O	P1.2 — Port 1 bit 2 (open-drain when used as output).
		I/O	T0 — Timer/counter 0 external count input or overflow output (open-drain when used as output).
		I/O	SCL — I ² C-bus serial clock input/output.
P1.3/ INT0 /	16	I/O	P1.3 — Port 1 bit 3 (open-drain when used as output).
SDA		I	INTO — External interrupt 0 input.
		I/O	SDA — I ² C-bus serial data input/output.
P1.4/INT1	15	I	P1.4 — Port 1 bit 4. High current source.
		Ī	INT1 — External interrupt 1 input.

8 of 60

8-bit microcontroller with accelerated two-clock 80C51 core

Table 3. Pin description continued

	Pin description		
Symbol	Pin	Type	Description
P1.5/RST	11	l	P1.5 — Port 1 bit 5 (input only).
		I	RST — External Reset input during power-on or if selected via UCFG1. When functioning as a reset input, a LOW on this pin resets the microcontroller, causing I/O ports and peripherals to take on their default states, and the processor begins execution at address 0. Also used during a power-on sequence to force ISP mode.
P1.6	10	I/O	P1.6 — Port 1 bit 6. High current source.
P1.7	9	I/O	P1.7 — Port 1 bit 7. High current source.
P2.0 to P2.3 P2.5	,	I/O	Port 2: Port 2 is an 5-bit I/O port with a user-configurable output type. During reset Port 2 latches are configured in the input only mode with the internal pull-up disabled. The operation of Port 2 pins as inputs and outputs depends upon the port configuration selected. Each port pin is configured independently. Refer to Section 7.14.1 "Port configurations" and Table 12 "Static electrical characteristics" for details.
			All pins have Schmitt trigger inputs.
			Port 2 also provides various special functions as described below:
P2.0	6	I/O	P2.0 — Port 2 bit 0.
P2.1	7	I/O	P2.1 — Port 2 bit 1.
P2.2/MOSI	18	I/O	P2.2 — Port 2 bit 2.
		I/O	MOSI — SPI master out slave in. When configured as master, this pin is output; when configured as slave, this pin is input.
P2.3/MISO	19	I/O	P2.3 — Port 2 bit 3.
		I/O	MISO — When configured as master, this pin is input, when configured as slave, this pin is output.
P2.5/SPICL	C 20	I/O	P2.5 — Port 2 bit 5.
		I/O	SPICLK — SPI clock. When configured as master, this pin is output; when configured as slave, this pin is input.
P3.0 to P3.1		I/O	Port 3: Port 3 is a 2-bit I/O port with a user-configurable output type. During reset Port 3 latches are configured in the input only mode with the internal pull-up disabled. The operation of Port 3 pins as inputs and outputs depends upon the port configuration selected. Each port pin is configured independently. Refer to Section 7.14.1 "Port configurations" and Table 42 "Static electrical physical relations" for datailer.
			configurations" and <u>Table 12 "Static electrical characteristics"</u> for details.All pins have Schmitt triggered inputs.
			Port 3 also provides various special functions as described below:
P3.0/XTAL2/	14	I/O	P3.0 — Port 3 bit 0.
CLKOUT	14	0	XTAL2 — Output from the oscillator amplifier (when a crystal oscillator option is selected via the flash configuration.
		0	CLKOUT — CPU clock divided by 2 when enabled via SFR bit (ENCLK - TRIM.6). It can be used if the CPU clock is the internal RC oscillator, watchdog oscillator or external clock input, except when XTAL1/XTAL2 are used to generate clock source for the RTC/system timer.
P3.1/XTAL1	13	I/O	P3.1 — Port 3 bit 1.
		I	XTAL1 — Input to the oscillator circuit and internal clock generator circuits (when selected via the flash configuration). It can be a port pin if internal RC oscillator or watchdog oscillator is used as the CPU clock source, and if XTAL1/XTAL2 are not used to generate the clock for the RTC/system timer.
SDA_LCD	63	I/O	SDA LCD — I ² C-bus data signal for the LCD controller.
SCL_LCD	64	I/O	SCL LCD — I ² C-bus clock signal for the LCD controller.
BP0 to BP3	27 to 30	0	BP0 to BP3: LCD backplane outputs.
P89LPC9402_1			© NXP B.V. 2009. All rights rese

8-bit microcontroller with accelerated two-clock 80C51 core

 Table 3.
 Pin description ...continued

Symbol	Pin	Туре	Description
S0 to S31	31 to 62	0	S0 to S31: LCD segment outputs.
V_{SS}	12	ı	Ground: 0 V reference.
V_{DD}	25	ı	Power supply: This is the power supply voltage for normal operation as well as Idle and Power-down modes.
V_{LCD}	26	I	LCD power supply: LCD voltage.

^[1] Input/output for P1.0 to P1.4, P1.6, P1.7. Input for P1.5.

8-bit microcontroller with accelerated two-clock 80C51 core

7. Functional description

Remark: Please refer to the P89LPC9402 *User manual* for a more detailed functional description.

7.1 Special function registers

Remark: Special Function Registers (SFRs) accesses are restricted in the following ways:

- User must **not** attempt to access any SFR locations not defined.
- Accesses to any defined SFR locations must be strictly for the functions for the SFRs.
- SFR bits labeled '-', logic 0 or logic 1 can **only** be written and read as follows:
 - '-' Unless otherwise specified, must be written with logic 0, but can return any value when read (even if it was written with logic 0). It is a reserved bit and may be used in future derivatives.
 - Logic 0 must be written with logic 0, and will return a logic 0 when read.
 - Logic 1 must be written with logic 1, and will return a logic 1 when read.

8-bit microcontroller with accelerated two-clock 80C51 core

NXP

Semiconductors

Table 4. Special function registers
* indicates SFRs that are bit addressable. Table 4.

Name	Description	SFR	Bit function	Reset value								
		addr.	MSB							LSB	Hex	Binary
	Bit a	ddress	E7	E6	E5	E4	E3	E2	E1	E0		
ACC*	Accumulator	E0H									00	0000 0000
AUXR1	Auxiliary function register	A2H	CLKLP	EBRR	ENT1	ENT0	SRST	0	-	DPS	00	0000 00x0
	Bit a	ddress	F7	F6	F5	F4	F3	F2	F1	F0		
B*	B register	F0H									00	0000 0000
BRGR0[1]	Baud rate generator rate low	BEH									00	0000 0000
BRGR1[1]	Baud rate generator rate high	BFH									00	0000 0000
BRGCON	Baud rate generator control	BDH	-	-	-	-	-	-	SBRGS	BRGEN	00[1]	xxxx xx00
CMP1	Comparator 1 control register	ACH	-	-	CE1	CP1	CN1	OE1	CO1	CMF1	00[2]	xx00 0000
CMP2	Comparator 2 control register	ADH	-	-	CE2	CP2	CN2	OE2	CO2	CMF2	00[2]	xx00 0000
DIVM	CPU clock divide-by-M control	95H									00	0000 0000
DPTR	Data pointer (2 bytes)											
DPH	Data pointer high	83H									00	0000 0000
DPL	Data pointer low	82H									00	0000 0000
FMADRH	Program flash address high	E7H									00	0000 0000
FMADRL	Program flash address low	E6H									00	0000 0000
FMCON	Program flash control (Read)	E4H	BUSY	-	-	-	HVA	HVE	SV	OI	70	0111 0000
	Program flash control (Write)	E4H	FMCMD.	FMCMD. 6	FMCMD. 5	FMCMD.	FMCMD.	FMCMD. 2	FMCMD. 1	FMCMD. 0		
FMDATA	Program flash data	E5H									00	0000 0000
I2ADR	I ² C-bus slave address register	DBH	I2ADR.6	I2ADR.5	I2ADR.4	I2ADR.3	I2ADR.2	I2ADR.1	I2ADR.0	GC	00	0000 0000
	Bit a	ddress	DF	DE	DD	DC	DB	DA	D9	D8		
I2CON*	I ² C-bus control register	D8H	-	I2EN	STA	STO	SI	AA	-	CRSEL	00	x000 00x0
I2DAT	I ² C-bus data register	DAH										

8-bit microcontroller with accelerated two-clock 80C51 core

NXP

Semiconductors

Table 4. Special function registers ...continued * indicates SFRs that are bit addressable.

Name	Description	SFR	Bit functi	Bit functions and addresses									
		addr.	MSB							LSB	Hex	Binary	
2SCLH	Serial clock generator/s duty cycle register high										00	0000 0000	
2SCLL	Serial clock generator/s duty cycle register low	SCL DCH									00	0000 0000	
2STAT	I ² C-bus status register	D9H	STA.4	STA.3	STA.2	STA.1	STA.0	0	0	0	F8	1111 1000	
		Bit address	AF	AE	AD	AC	AB	AA	A9	A8			
EN0*	Interrupt enable 0	A8H	EA	EWDRT	EBO	ES/ESR	ET1	EX1	ET0	EX0	00	0000 0000	
		Bit address	EF	EE	ED	EC	EB	EA	E 9	E8			
EN1*	Interrupt enable 1	E8H	-	EST	-	-	ESPI	EC	EKBI	EI2C	00[2]	00x0 0000	
		Bit address	BF	BE	BD	ВС	ВВ	BA	B9	B8			
P0*	Interrupt priority 0	B8H	-	PWDRT	PBO	PS/PSR	PT1	PX1	PT0	PX0	00[2]	x000 0000	
P0H	Interrupt priority 0 high	В7Н	-	PWDRT H	PBOH	PSH/ PSRH	PT1H	PX1H	PT0H	PX0H	00[2]	x000 0000	
		Bit address	FF	FE	FD	FC	FB	FA	F9	F8			
IP1*	Interrupt priority 1	F8H	-	PST	-	-	PSPI	PC	PKBI	PI2C	00[2]	00x0 0000	
IP1H	Interrupt priority 1 high	F7H	-	PSTH	-	-	PSPIH	PCH	PKBIH	PI2CH	00[2]	00x0 0000	
KBCON	Keypad control register	· 94H	-	-	-	-	-	-	PATN _SEL	KBIF	00[2]	xxxx xx00	
KBMASK	Keypad interrupt mask register	86H									00	0000 0000	
KBPATN	Keypad pattern register	r 93H									FF	1111 1111	
		Bit address	87	86	85	84	83	82	81	80			
P0*	Port 0	80H	T1/KB7	CMP1 /KB6	CMPREF /KB5	CIN1A /KB4	CIN1B /KB3	CIN2A /KB2	CIN2B /KB1	CMP2 /KB0		[2]	
		Bit address	97	96	95	94	93	92	91	90			
P1*	Port 1	90H	-	-	RST	ĪNT1	ĪNT0/ SDA	T0/SCL	RXD	TXD		<u>[2]</u>	
		Bit address	97	96	95	94	93	92	91	90			
2*	Port 2	A0H	-	-	SPICLK	\overline{SS}	MISO	MOSI	-	-		[2]	
		Bit address	B7	В6	B5	B4	В3	B2	B1	В0			
P3*	Port 3	ВОН	-	-	-	-	-	-	XTAL1	XTAL2		[2]	

NXP Semiconductors

Table 4. Special function registers ...continued * indicates SFRs that are bit addressable.

Name	Description	SFR	Bit function	Reset value								
		addr.	MSB							LSB	Hex	Binary
P0M1	Port 0 output mode 1	84H	(P0M1.7)	(P0M1.6)	(P0M1.5)	(P0M1.4)	(P0M1.3)	(P0M1.2)	(P0M1.1)	(P0M1.0)	FF[2]	1111 111
P0M2	Port 0 output mode 2	85H	(P0M2.7)	(P0M2.6)	(P0M2.5)	(P0M2.4)	(P0M2.3)	(P0M2.2)	(P0M2.1)	(P0M2.0)	00[2]	0000 0000
P1M1	Port 1 output mode 1	91H	(P1M1.7)	(P1M1.6)	-	(P1M1.4)	(P1M1.3)	(P1M1.2)	(P1M1.1)	(P1M1.0)	D3[2]	11x1 xx11
P1M2	Port 1 output mode 2	92H	(P1M2.7)	(P1M2.6)	-	(P1M2.4)	(P1M2.3)	(P1M2.2)	(P1M2.1)	(P1M2.0)	00[2]	00x0 xx00
P2M1	Port 2 output mode 1	A4H	(P2M1.7)	(P2M1.6)	(P2M1.5)	(P2M1.4)	(P2M1.3)	(P2M1.2)	(P2M1.1)	(P2M1.0)	FF[2]	1111 111
P2M2	Port 2 output mode 2	A5H	(P2M2.7)	(P2M2.6)	(P2M2.5)	(P2M2.4)	(P2M2.3)	(P2M2.2)	(P2M2.1)	(P2M2.0)	00[2]	0000 0000
P3M1	Port 3 output mode 1	В1Н	-	-	-	-	-	-	(P3M1.1)	(P3M1.0)	03[2]	xxxx xx11
P3M2	Port 3 output mode 2	В2Н	-	-	-	-	-	-	(P3M2.1)	(P3M2.0)	00[2]	xxxx xx00
PCON	Power control register	87H	SMOD1	SMOD0	-	BOI	GF1	GF0	PMOD1	PMOD0	00	0000 0000
PCONA	Power control register A	В5Н	RTCPD	-	VCPD	-	I2PD	SPPD	SPD	-	00[2]	0000 0000
	Bit ac	ddress	D7	D6	D5	D4	D3	D2	D1	D0		
PSW*	Program status word	D0H	CY	AC	F0	RS1	RS0	OV	F1	Р	00	0000 0000
PT0AD	Port 0 digital input disable	F6H	-	-	PT0AD.5	PT0AD.4	PT0AD.3	PT0AD.2	PT0AD.1	-	00	xx00 000x
RSTSRC	Reset source register	DFH	-	BOIF	BOF	POF	R_BK	R_WD	R_SF	R_EX		[3]
RTCCON	Real-time clock control	D1H	RTCF	RTCS1	RTCS0	-	-	-	ERTC	RTCEN	60[2][4]	011x xx00
RTCH	Real-time clock register high	D2H									00[4]	0000 0000
RTCL	Real-time clock register low	D3H									00[4]	0000 0000
SADDR	Serial port address register	А9Н									00	0000 0000
SADEN	Serial port address enable	В9Н									00	0000 0000
SBUF	Serial Port data buffer register	99H									xx	XXXX XXXX
	Bit a	ddress	9F	9E	9D	9C	9B	9A	99	98		
SCON*	Serial port control	98H	SM0/FE	SM1	SM2	REN	TB8	RB8	TI	RI	00	0000 0000
SSTAT	Serial port extended status register	BAH	DBMOD	INTLO	CIDIS	DBISEL	FE	BR	OE	STINT	00	0000 0000
SP	Stack pointer	81H									07	0000 011
SPCTL	SPI control register	E2H	SSIG	SPEN	DORD	MSTR	CPOL	СРНА	SPR1	SPR0	04	0000 0100
SPSTAT	SPI status register	E1H	SPIF	WCOL	-	-	-	-	-	-	00	00xx xxxx
SPDAT	SPI data register	ЕЗН									00	0000 0000

NXP

Semiconductors

Table 4.

Name	Description	SFR	Bit function	Reset value								
		addr.	MSB							LSB	Hex	Binary
TAMOD	Timer 0 and 1 auxiliary mode	8FH	-	-	-	T1M2	-	-	-	T0M2	00	xxx0 xxx0
		Bit address	8F	8E	8D	8C	8B	8A	89	88		
TCON*	Timer 0 and 1 control	88H	TF1	TR1	TF0	TR0	IE1	IT1	IE0	IT0	00	0000 0000
TH0	Timer 0 high	8CH									00	0000 0000
TH1	Timer 1 high	8DH									00	0000 0000
TL0	Timer 0 low	8AH									00	0000 0000
TL1	Timer 1 low	8BH									00	0000 0000
TMOD	Timer 0 and 1 mode	89H	T1GATE	T1C/T	T1M1	T1M0	T0GATE	T0C/T	T0M1	T0M0	00	0000 0000
TRIM	Internal oscillator trim register	96H	RCCLK	ENCLK	TRIM.5	TRIM.4	TRIM.3	TRIM.2	TRIM.1	TRIM.0		[4] [5]
WDCON	Watchdog control regis	ter A7H	PRE2	PRE1	PRE0	-	-	WDRUN	WDTOF	WDCLK		[4] [6]
WDL	Watchdog load	C1H									FF	1111 1111
WFEED1	Watchdog feed 1	C2H										
WFEED2	Watchdog feed 2	СЗН										

[1] All ports are in input only (high-impedance) state after power-up.

Special function registers ...continued

* indicates SFRs that are bit addressable.

- [2] BRGR1 and BRGR0 must only be written if BRGEN in BRGCON SFR is logic 0. If any are written while BRGEN = 1, the result is unpredictable.
- [3] The RSTSRC register reflects the cause of the P89LPC9402 reset except BOIF bit. Upon a power-up reset, all reset source flags are cleared except POF and BOF; the power-on reset value is x011 0000.
- [4] After reset, the value is 1110 01x1, i.e., PRE2 to PRE0 are all logic 1, WDRUN = 1 and WDCLK = 1. WDTOF bit is logic 1 after watchdog reset and is logic 0 after power-on reset. Other resets will not affect WDTOF.
- [5] On power-on reset and watchdog reset, the TRIM SFR is initialized with a factory preprogrammed value. Other resets will not cause initialization of the TRIM register.
- [6] The only reset sources that affect these SFRs are power-on reset and watchdog reset.

8-bit microcontroller with accelerated two-clock 80C51 core

NXP

Semiconductors

Name	Description	SFR	Bit functions and addresses									t value
		addr.	MSB							LSB	Hex	Binary
BODCFG	BOD configuration register	FFC8H	-	-	-	-	-	-	BOICFG1	BOICFG0	[2]	
CLKCON	CLOCK Control register	FFDEH	CLKOK	-	-	XTALWD	CLKDBL	FOSC2	FOSC1	FOSC0	[3]	
RTCDATH	Real-time clock data register high	FFBFH									00	0000 0000
RTCDATL	Real-time clock data register low	FFBEH									00	0000 0000
• •	s are physically located these extended SFRs		it logically locate	ed in external da	ıta memo	ory address spa	ce (XDATA).	The MOVX A	A,@DPTR and	d MOVX @DF	PTR,A ir	nstructions are

^[2] The BOICFG1/0 will be copied from UCFG1.5 and UCFG1.3 when power-on reset.

^[3] CLKCON register reset value comes from UCFG1 and UCFG2. The reset value of CLKCON.2 to CLKCON.0 come from UCFG1.2 to UCFG1.0 and reset value of CLKDBL bit comes from UCFG2.7.

8-bit microcontroller with accelerated two-clock 80C51 core

7.2 Enhanced CPU

The P89LPC9402 uses an enhanced 80C51 CPU which runs at six times the speed of standard 80C51 devices. A machine cycle consists of two CPU clock cycles, and most instructions execute in one or two machine cycles.

7.3 Clocks

7.3.1 Clock definitions

The P89LPC9402 device has several internal clocks as defined below:

OSCCLK — Input to the DIVM clock divider. OSCCLK is selected from one of four clock sources (see Figure 6) and can also be optionally divided to a slower frequency (see Section 7.9 "CCLK modification: DIVM register").

Note: f_{osc} is defined as the OSCCLK frequency.

CCLK — CPU clock; output of the clock divider. There are two CCLK cycles per machine cycle, and most instructions are executed in one to two machine cycles (two or four CCLK cycles).

RCCLK — The internal 7.373 MHz RC oscillator output. The clock doubler option, when enabled, provides an output frequency of 14.746 MHz.

PCLK — Clock for the various peripheral devices and is ^{CCLK}/₂.

7.3.2 CPU clock (OSCCLK)

The P89LPC9402 provides several user-selectable oscillator options in generating the CPU clock. This allows optimization for a range of needs from high precision to lowest possible cost. These options are configured when the flash is programmed and include an on-chip watchdog oscillator, an on-chip RC oscillator, an oscillator using an external crystal, or an external clock source.

7.3.3 Crystal oscillator option

The crystal oscillator can be optimized for low, medium, or high frequency crystals covering a range from 20 kHz to 18 MHz. It can be the clock source of OSCCLK, RTC and WDT.

7.3.3.1 Low speed oscillator option

This option supports an external crystal in the range of 20 kHz to 100 kHz. Ceramic resonators are also supported in this configuration.

7.3.3.2 Medium speed oscillator option

This option supports an external crystal in the range of 100 kHz to 4 MHz. Ceramic resonators are also supported in this configuration.

7.3.3.3 High speed oscillator option

This option supports an external crystal in the range of 4 MHz to 18 MHz. Ceramic resonators are also supported in this configuration.

8-bit microcontroller with accelerated two-clock 80C51 core

7.3.4 Clock output

The P89LPC9402 supports a user-selectable clock output function on the XTAL2/CLKOUT pin when crystal oscillator is not being used. This condition occurs if another clock source has been selected (on-chip RC oscillator, watchdog oscillator, external clock input on XTAL1) and if the RTC and WDT are not using the crystal oscillator as their clock source. This allows external devices to synchronize to the P89LPC9402. This output is enabled by the ENCLK bit in the TRIM register.

The frequency of this clock output is $\frac{1}{2}$ that of the CCLK. If the clock output is not needed in Idle mode, it may be turned off prior to entering Idle, saving additional power.

7.4 On-chip RC oscillator option

The P89LPC9402 has a 6-bit TRIM register that can be used to tune the frequency of the RC oscillator. During reset, the TRIM value is initialized to a factory preprogrammed value to adjust the oscillator frequency to 7.373 MHz \pm 1 % at room temperature. End-user applications can write to the TRIM register to adjust the on-chip RC oscillator to other frequencies. When the clock doubler option is enabled (UCFG2.7 = 1), the output frequency is 14.746 MHz. If CCLK is 8 MHz or slower, the CLKLP SFR bit (AUXR1.7) can be set to logic 1 to reduce power consumption. On reset, CLKLP is logic 0 allowing highest performance access. This bit can then be set in software if CCLK is running at 8 MHz or slower. When clock doubler option is enabled, BOE1 bit (UCFG1.5) and BOE0 bit (UCFG1.3) are required to hold the device in reset at power-up until $V_{\rm DD}$ has reached its specified level.

7.5 Watchdog oscillator option

The watchdog has a separate oscillator which has a frequency of 400 kHz, calibrated to \pm 5 % at room temperature. This oscillator can be used to save power when a high clock frequency is not needed.


7.6 External clock input option

In this configuration, the processor clock is derived from an external source driving the P3.1/XTAL1 pin. The rate may be from 0 Hz up to 18 MHz. The P3.0/XTAL2 pin may be used as a standard port pin or a clock output. When using an oscillator frequency above 12 MHz, BOE1 bit (UCFG1.5) and BOE0 bit (UCFG1.3) are required to hold the device in reset at power-up until V_{DD} has reached its specified level.

7.7 Clock sources switch on the fly

P89LPC9402 can implement clock source switch in any sources of watchdog oscillator, 7 MHz/14 MHz IRC oscillator, external clock source (external crystal or external clock input) during code is running. CLKOK bit in CLKCON register is used to indicate the clock switch status. CLKOK is cleared when starting clock source switch and set when completed. Notice that when CLKOK is '0', writing to CLKCON register is not allowed.

8-bit microcontroller with accelerated two-clock 80C51 core



8-bit microcontroller with accelerated two-clock 80C51 core

7.8 CPU Clock (CCLK) wake-up delay

The P89LPC9402 has an internal wake-up timer that delays the clock until it stabilizes depending on the clock source used. If the clock source is any of the three crystal selections (low, medium and high frequencies) the delay is 1024 OSCCLK cycles plus 60 μs to 100 μs . If the clock source is the internal RC oscillator, the delay is 200 μs to 300 μs . If the clock source is watchdog oscillator or external clock, the delay is 32 OSCCLK cycles.

7.9 CCLK modification: DIVM register

The OSCCLK frequency can be divided down up to 510 times by configuring a dividing register, DIVM, to generate CCLK. This feature makes it possible to temporarily run the CPU at a lower rate, reducing power consumption. By dividing the clock, the CPU can retain the ability to respond to events that would not exit Idle mode by executing its normal program at a lower rate. This can also allow bypassing the oscillator start-up time in cases where Power-down mode would otherwise be used. The value of DIVM may be changed by the program at any time without interrupting code execution.

7.10 Low power select

The P89LPC9402 is designed to run at 18 MHz (CCLK) maximum. However, if CCLK is 8 MHz or slower, the CLKLP SFR bit (AUXR1.7) can be set to logic 1 to lower the power consumption further. On any reset, CLKLP is logic 0 allowing highest performance access. This bit can then be set in software if CCLK is running at 8 MHz or slower.

7.11 Memory organization

The various P89LPC9402 memory spaces are as follows:

DATA

128 bytes of internal data memory space (00H:7FH) accessed via direct or indirect addressing, using instructions other than MOVX and MOVC. All or part of the Stack may be in this area.

IDATA

Indirect Data. 256 bytes of internal data memory space (00H:FFH) accessed via indirect addressing using instructions other than MOVX and MOVC. All or part of the Stack may be in this area. This area includes the DATA area and the 128 bytes immediately above it.

• SFR

Special Function Registers. Selected CPU registers and peripheral control and status registers, accessible only via direct addressing.

8-bit microcontroller with accelerated two-clock 80C51 core

• CODE

64 kB of Code memory space, accessed as part of program execution and via the MOVC instruction. The P89LPC9402 has 8 kB of on-chip Code memory.

7.12 Data RAM arrangement

The 768 bytes of on-chip RAM are organized as shown in Table 6.

Table 6. On-chip data memory usages

Туре	Data RAM	Size (bytes)
DATA	Memory that can be addressed directly and indirectly	128
IDATA	Memory that can be addressed indirectly	256

7.13 Interrupts

The P89LPC9402 uses a four priority level interrupt structure. This allows great flexibility in controlling the handling of the many interrupt sources. The P89LPC9402 supports 13 interrupt sources: external interrupts 0 and 1, timers 0 and 1, serial port TX, serial port RX, combined serial port RX/TX, brownout detect, watchdog/RTC, I²C-bus, keyboard, comparators 1 and 2, SPI.

Each interrupt source can be individually enabled or disabled by setting or clearing a bit in the interrupt enable registers IEN0 or IEN1. The IEN0 register also contains a global disable bit, EA, which disables all interrupts.

Each interrupt source can be individually programmed to one of four priority levels by setting or clearing bits in the interrupt priority registers IP0, IP0H, IP1 and IP1H. An interrupt service routine in progress can be interrupted by a higher priority interrupt, but not by another interrupt of the same or lower priority. The highest priority interrupt service cannot be interrupted by any other interrupt source. If two requests of different priority levels are pending at the start of an instruction, the request of higher priority level is serviced.

If requests of the same priority level are pending at the start of an instruction, an internal polling sequence determines which request is serviced. This is called the arbitration ranking. Note that the arbitration ranking is only used to resolve pending requests of the same priority level.

7.13.1 External interrupt inputs


The P89LPC9402 has two external interrupt inputs as well as the Keypad Interrupt function. The two interrupt inputs are identical to those present on the standard 80C51 microcontrollers.

These external interrupts can be programmed to be level-triggered or edge-triggered by setting or clearing bit IT1 or IT0 in Register TCON.

In edge-triggered mode, if successive samples of the $\overline{\text{INTn}}$ pin show a HIGH in one cycle and a LOW in the next cycle, the interrupt request flag IEn in TCON is set, causing an interrupt request.

If an external interrupt is enabled when the P89LPC9402 is put into Power-down or Idle mode, the interrupt will cause the processor to wake-up and resume operation. Refer to Section 7.16 "Power reduction modes" for details.

8-bit microcontroller with accelerated two-clock 80C51 core



7.14 I/O ports

The P89LPC9402 has four I/O ports: Port 0 and Port 1 are 8-bit ports. Port 2 is a 5-bit port. Port 3 is a 2-bit port. The exact number of I/O pins available depends upon the clock and reset options chosen, as shown in Table 7.

Table 7. Number of I/O pins available

Clock source	Reset option	Number of I/O pins (not including LCD pins)
On-chip oscillator or watchdog oscillator	No external reset (except during power-up)	23
	External RST pin supported	22
External clock input	No external reset (except during power-up)	22
	External RST pin supported[1]	21
Low/medium/high speed oscillator (external crystal or resonator)	No external reset (except during power-up)	21
	External RST pin supported[1]	20

^[1] Required for operation above 12 MHz.

8-bit microcontroller with accelerated two-clock 80C51 core

7.14.1 Port configurations

All but three I/O port pins on the P89LPC9402 may be configured by software to one of four types on a bit-by-bit basis. These are: quasi-bidirectional (standard 80C51 port outputs), push-pull, open-drain, and input-only. Two configuration registers for each port select the output type for each port pin.

- 1. P1.5 (RST) can only be an input and cannot be configured.
- 2. P1.2 (SCL/T0) and P1.3 (SDA/INT0) may only be configured to be either input-only or open-drain.

7.14.1.1 Quasi-bidirectional output configuration

Quasi-bidirectional output type can be used as both an input and output without the need to reconfigure the port. This is possible because when the port outputs a logic HIGH, it is weakly driven, allowing an external device to pull the pin LOW. When the pin is driven LOW, it is driven strongly and able to sink a fairly large current. These features are somewhat similar to an open-drain output except that there are three pull-up transistors in the quasi-bidirectional output that serve different purposes.

The P89LPC9402 is a 3 V device, but the pins are 5 V-tolerant. In quasi-bidirectional mode, if a user applies 5 V on the pin, there will be a current flowing from the pin to V_{DD} , causing extra power consumption. Therefore, applying 5 V in quasi-bidirectional mode is discouraged.

A quasi-bidirectional port pin has a Schmitt trigger input that also has a glitch suppression circuit.

7.14.1.2 Open-drain output configuration

The open-drain output configuration turns off all pull-ups and only drives the pull-down transistor of the port driver when the port latch contains a logic 0. To be used as a logic output, a port configured in this manner must have an external pull-up, typically a resistor tied to V_{DD} .

An open-drain port pin has a Schmitt trigger input that also has a glitch suppression circuit.

7.14.1.3 Input-only configuration

The input-only port configuration has no output drivers. It is a Schmitt trigger input that also has a glitch suppression circuit.

7.14.1.4 Push-pull output configuration

The push-pull output configuration has the same pull-down structure as both the open-drain and the quasi-bidirectional output modes, but provides a continuous strong pull-up when the port latch contains a logic 1. The push-pull mode may be used when more source current is needed from a port output. A push-pull port pin has a Schmitt trigger input that also has a glitch suppression circuit. The P89LPC9402 device has high current source on eight pins in push-pull mode. See Table 11 "Limiting values".

7.14.2 Port 0 analog functions

The P89LPC9402 incorporates two analog comparators. In order to give the best analog function performance and to minimize power consumption, pins that are being used for analog functions must have the digital outputs and digital inputs disabled.

8-bit microcontroller with accelerated two-clock 80C51 core

Digital outputs are disabled by putting the port output into the Input-Only (high-impedance) mode.

Digital inputs on Port 0 may be disabled through the use of the PT0AD register, bits 1:5. On any reset, PT0AD[1:5] defaults to logic 0s to enable digital functions.

7.14.3 Additional port features

After power-up, all pins are in Input-Only mode. Please note that this is different from the LPC76x series of devices.

- After power-up, all I/O pins except P1.5, may be configured by software.
- Pin P1.5 is input only. Pins P1.2 and P1.3 and are configurable for either input-only or open-drain.

Every output on the P89LPC9402 has been designed to sink typical LED drive current. However, there is a maximum total output current for all ports which must not be exceeded. Please refer to <u>Table 12 "Static electrical characteristics"</u> for detailed specifications.

All ports pins that can function as an output have slew rate controlled outputs to limit noise generated by quickly switching output signals. The slew rate is factory-set to approximately 10 ns rise and fall times.

7.15 Power monitoring functions

The P89LPC9402 incorporates power monitoring functions designed to prevent incorrect operation during initial power-up and power loss or reduction during operation. This is accomplished with two hardware functions: Power-on detect and brownout detect.

7.15.1 Brownout detection

The brownout detect function determines if the power supply voltage drops below a certain level. Enhanced brownout detection has 3 independent functions: BOD reset, BOD interrupt and BOD FLASH.

BOD reset is always on except in total Power-down mode. It could not be disabled in software. BOD interrupt may be enabled or disabled in software. BOD FLASH is always on, except in Power-down modes and could not be disabled in software.

BOD reset and BOD interrupt, each has four trip voltage levels. BOE1 bit (UCFG1.5) and BOE0 bit (UCFG1.3) are used as trip point configuration bits of BOD reset. BOICFG1 bit and BOICFG0 bit in register BODCFG are used as trip point configuration bits of BOD interrupt. BOD reset voltage should be lower than BOD interrupt trip point. BOD FLASH is used for flash programming/erase protection and has only 1 trip voltage of 2.4 V. Please refer to P89LPC9402 *User manual* for detail configurations.

If brownout detection is enabled the brownout condition occurs when V_{DD} falls below the brownout trip voltage and is negated when V_{DD} rises above the brownout trip voltage.

For correct activation of brownout detect, the V_{DD} rise and fall times must be observed. Please see Table 12 "Static electrical characteristics" for specifications.

8-bit microcontroller with accelerated two-clock 80C51 core

7.15.2 Power-on detection

The Power-on detect has a function similar to the brownout detect, but is designed to work as power comes up initially, before the power supply voltage reaches a level where brownout detect can work. The POF flag in the RSTSRC register is set to indicate an initial power-up condition. The POF flag will remain set until cleared by software.

7.16 Power reduction modes

The P89LPC9402 supports three different power reduction modes. These modes are Idle mode, Power-down mode, and total Power-down mode.

7.16.1 Idle mode

Idle mode leaves peripherals running in order to allow them to activate the processor when an interrupt is generated. Any enabled interrupt source or reset may terminate Idle mode.

7.16.2 Power-down mode

The Power-down mode stops the oscillator in order to minimize power consumption. The P89LPC9402 exits Power-down mode via any reset, or certain interrupts. In Power-down mode, the power supply voltage may be reduced to the data retention voltage V_{DDR} . This retains the RAM contents at the point where Power-down mode was entered. SFR contents are not guaranteed after V_{DD} has been lowered to V_{DDR} , therefore it is highly recommended to wake-up the processor via reset in this case. V_{DD} must be raised to within the operating range before the Power-down mode is exited.

Some chip functions continue to operate and draw power during Power-down mode, increasing the total power used during power-down. These include: Brownout detect, watchdog timer, Comparators (note that Comparators can be powered-down separately), and RTC/System Timer. The internal RC oscillator is disabled unless both the RC oscillator has been selected as the system clock and the RTC is enabled.

7.16.3 Total Power-down mode

This is the same as Power-down mode except that the brownout detection circuitry and the voltage comparators are also disabled to conserve additional power. The internal RC oscillator is disabled unless both the RC oscillator has been selected as the system clock and the RTC is enabled. If the internal RC oscillator is used to clock the RTC during power-down, there will be high power consumption. Please use an external low frequency clock to achieve low power with the RTC running during power-down.

7.17 Reset

The P1.5/RST pin can function as either a LOW-active reset input or as a digital input, P1.5. The Reset Pin Enable (RPE) bit in UCFG1, when set to logic 1, enables the external reset input function on P1.5. When cleared, P1.5 may be used as an input pin.

Remark: During a power-up sequence, the RPE selection is overridden and this pin always functions as a reset input. An external circuit connected to this pin should not hold this pin LOW during a power-on sequence as this will keep the device in reset. After power-up this pin will function as defined by the RPE bit. Only a power-up reset will temporarily override the selection defined by RPE bit. Other sources of reset will not override the RPE bit.

8-bit microcontroller with accelerated two-clock 80C51 core

Note: During a power cycle, V_{DD} must fall below V_{POR} before power is reapplied, in order to ensure a power-on reset (see Table 12 "Static electrical characteristics").

Reset can be triggered from the following sources:

- External reset pin (during power-up or if user configured via UCFG1)
- Power-on detect
- Brownout detect
- Watchdog timer
- Software reset
- UART break character detect reset

For every reset source, there is a flag in the Reset Register, RSTSRC. The user can read this register to determine the most recent reset source. These flag bits can be cleared in software by writing a logic 0 to the corresponding bit. More than one flag bit may be set:

- During a power-on reset, both POF and BOF are set but the other flag bits are cleared.
- A Watchdog reset is similar to a power-on reset, both POF and BOF are set but the other flag bits are cleared.
- For any other reset, previously set flag bits that have not been cleared will remain set.

7.17.1 Reset vector

Following reset, the P89LPC9402 will fetch instructions from either address 0000H or the Boot address. The Boot address is formed by using the Boot Vector as the high byte of the address and the low byte of the address = 00H.

The Boot address will be used if a UART break reset occurs, or the non-volatile Boot Status bit (BOOTSTAT.0) = 1, or the device is forced into ISP mode during power-on (see P89LPC9402 *User manual*). Otherwise, instructions will be fetched from address 0000H.

7.18 Timers/counters 0 and 1

The P89LPC9402 has two general purpose counter/timers which are upward compatible with the standard 80C51 Timer 0 and Timer 1. Both can be configured to operate either as timers or event counter. An option to automatically toggle the T0 and/or T1 pins upon timer overflow has been added.

In the 'Timer' function, the register is incremented every machine cycle.

In the 'Counter' function, the register is incremented in response to a 1-to-0 transition at its corresponding external input pin, T0 or T1. In this function, the external input is sampled once during every machine cycle.

Timer 0 and Timer 1 have five operating modes (modes 0, 1, 2, 3 and 6). Modes 0, 1, 2 and 6 are the same for both Timers/Counters. Mode 3 is different.

7.18.1 Mode 0

Putting either Timer into Mode 0 makes it look like an 8048 Timer, which is an 8-bit Counter with a divide-by-32 prescaler. In this mode, the Timer register is configured as a 13-bit register. Mode 0 operation is the same for Timer 0 and Timer 1.

8-bit microcontroller with accelerated two-clock 80C51 core

7.18.2 Mode 1

Mode 1 is the same as Mode 0, except that all 16 bits of the timer register are used.

7.18.3 Mode 2

Mode 2 configures the Timer register as an 8-bit Counter with automatic reload. Mode 2 operation is the same for Timer 0 and Timer 1.

7.18.4 Mode 3

When Timer 1 is in Mode 3 it is stopped. Timer 0 in Mode 3 forms two separate 8-bit counters and is provided for applications that require an extra 8-bit timer. When Timer 1 is in Mode 3 it can still be used by the serial port as a baud rate generator.

7.18.5 Mode 6

In this mode, the corresponding timer can be changed to a PWM with a full period of 256 timer clocks.

7.18.6 Timer overflow toggle output

Timers 0 and 1 can be configured to automatically toggle a port output whenever a timer overflow occurs. The same device pins that are used for the T0 and T1 count inputs are also used for the timer toggle outputs. The port outputs will be a logic 1 prior to the first timer overflow when this mode is turned on.

7.19 RTC/system timer

The P89LPC9402 has a simple RTC that allows a user to continue running an accurate timer while the rest of the device is powered down. The RTC can be a wake-up or an interrupt source. The RTC is a 23-bit down counter comprised of a 7-bit prescaler and a 16-bit loadable down counter. When it reaches all logic 0s, the counter will be reloaded again and the RTCF flag will be set. The clock source for this counter can be either the CPU clock (CCLK) or the XTAL oscillator. Only power-on reset and watchdog reset will reset the RTC and its associated SFRs to the default state.

The 16-bit loadable counter portion of the RTC is readable by reading the RTCDATL and RTCDATH registers.

7.20 UART

The P89LPC9402 has an enhanced UART that is compatible with the conventional 80C51 UART except that Timer 2 overflow cannot be used as a baud rate source. The P89LPC9402 does include an independent Baud Rate Generator. The baud rate can be selected from the oscillator (divided by a constant), Timer 1 overflow, or the independent Baud Rate Generator. In addition to the baud rate generation, enhancements over the standard 80C51 UART include Framing Error detection, automatic address recognition, selectable double buffering and several interrupt options. The UART can be operated in four modes: shift register, 8-bit UART, 9-bit UART, and CPU clock/32 or CPU clock/16.

7.20.1 Mode 0

Serial data enters and exits through RXD. TXD outputs the shift clock. 8 bits are transmitted or received, LSB first. The baud rate is fixed at $^{1}/_{16}$ of the CPU clock frequency.

8-bit microcontroller with accelerated two-clock 80C51 core

7.20.2 Mode 1

10 bits are transmitted (through TXD) or received (through RXD): a start bit (logic 0), 8 data bits (LSB first), and a stop bit (logic 1). When data is received, the stop bit is stored in RB8 in Special Function Register SCON. The baud rate is variable and is determined by the Timer 1 overflow rate or the Baud Rate Generator (described in Section 7.20.5
"Baud rate generator and selection").

7.20.3 Mode 2

11 bits are transmitted (through TXD) or received (through RXD): start bit (logic 0), 8 data bits (LSB first), a programmable 9^{th} data bit, and a stop bit (logic 1). When data is transmitted, the 9^{th} data bit (TB8 in SCON) can be assigned the value of logic 0 or logic 1. Or, for example, the parity bit (P, in the PSW) could be moved into TB8. When data is received, the 9^{th} data bit goes into RB8 in Special Function Register SCON, while the stop bit is not saved. The baud rate is programmable to either $\frac{1}{16}$ or $\frac{1}{32}$ of the CPU clock frequency, as determined by the SMOD1 bit in PCON.


7.20.4 Mode 3

11 bits are transmitted (through TXD) or received (through RXD): a start bit (logic 0), 8 data bits (LSB first), a programmable 9th data bit, and a stop bit (logic 1). In fact, Mode 3 is the same as Mode 2 in all respects except baud rate. The baud rate in Mode 3 is variable and is determined by the Timer 1 overflow rate or the Baud Rate Generator (described in Section 7.20.5 "Baud rate generator and selection").

7.20.5 Baud rate generator and selection

The P89LPC9402 enhanced UART has an independent Baud Rate Generator. The baud rate is determined by a baud rate preprogrammed into the BRGR1 and BRGR0 SFRs which together form a 16-bit baud rate divisor value that works in a similar manner as Timer 1 but is much more accurate. If the baud rate generator is used, Timer 1 can be used for other timing functions.

The UART can use either Timer 1 or the baud rate generator output (see <u>Figure 8</u>). Note that Timer T1 is further divided by 2 if the SMOD1 bit (PCON.7) is cleared. The independent Baud Rate Generator uses OSCCLK.



7.20.6 Framing error

Framing error is reported in the status register (SSTAT). In addition, if SMOD0 (PCON.6) is logic 1, framing errors can be made available in SCON.7 respectively. If SMOD0 is logic 0, SCON.7 is SM0. It is recommended that SM0 and SM1 (SCON.7:6) are set up when SMOD0 is logic 0.

8-bit microcontroller with accelerated two-clock 80C51 core

7.20.7 Break detect

Break detect is reported in the status register (SSTAT). A break is detected when 11 consecutive bits are sensed LOW. The break detect can be used to reset the device and force the device into ISP mode.

7.20.8 Double buffering

The UART has a transmit double buffer that allows buffering of the next character to be written to SBUF while the first character is being transmitted. Double buffering allows transmission of a string of characters with only one stop bit between any two characters, as long as the next character is written between the start bit and the stop bit of the previous character.

Double buffering can be disabled. If disabled (DBMOD, i.e., SSTAT.7 = 0), the UART is compatible with the conventional 80C51 UART. If enabled, the UART allows writing to SnBUF while the previous data is being shifted out. Double buffering is only allowed in Modes 1, 2 and 3. When operated in Mode 0, double buffering must be disabled (DBMOD = 0).

7.20.9 Transmit interrupts with double buffering enabled (modes 1, 2 and 3)

Unlike the conventional UART, in double buffering mode, the TX interrupt is generated when the double buffer is ready to receive new data.

7.20.10 The 9th bit (bit 8) in double buffering (modes 1, 2 and 3)

If double buffering is disabled TB8 can be written before or after SBUF is written, as long as TB8 is updated some time before that bit is shifted out. TB8 must not be changed until the bit is shifted out, as indicated by the TX interrupt.

If double buffering is enabled, TB8 **must** be updated before SBUF is written, as TB8 will be double-buffered together with SBUF data.


8-bit microcontroller with accelerated two-clock 80C51 core

7.21 I²C-bus serial interface


The I²C-bus uses two wires (SDA and SCL) to transfer information between devices connected to the bus, and it has the following features:

- Bidirectional data transfer between masters and slaves
- Multi master bus (no central master)
- Arbitration between simultaneously transmitting masters without corruption of serial data on the bus
- Serial clock synchronization allows devices with different bit rates to communicate via one serial bus
- Serial clock synchronization can be used as a handshake mechanism to suspend and resume serial transfer
- The I²C-bus may be used for test and diagnostic purposes.

A typical I²C-bus configuration is shown in <u>Figure 9</u>. The P89LPC9402 device provides a byte-oriented I²C-bus interface that supports data transfers up to 400 kHz.




8-bit microcontroller with accelerated two-clock 80C51 core



8-bit microcontroller with accelerated two-clock 80C51 core

7.22 SPI

The P89LPC9402 provides another high-speed serial communication interface, the SPI interface. SPI is a full-duplex, high-speed, synchronous communication bus with two operation modes: Master mode and Slave mode. Up to 4.5 Mbit/s can be supported in Master mode or up to 3 Mbit/s in Slave mode. It has a transfer completion flag and write collision flag protection.




The SPI interface has three pins: SPICLK, MOSI, MISO and SS:


• SPICLK, MOSI and MISO are typically tied together between two or more SPI devices. Data flows from master to slave on MOSI (Master Out Slave In) pin and flows from slave to master on MISO (Master In Slave Out) pin. The SPICLK signal is output in the master mode and is input in the slave mode. If the SPI system is disabled, i.e., SPEN (SPCTL.6) = 0 (reset value), these pins are configured for port functions.

Typical connections are shown in <u>Figure 12</u> through <u>Figure 14</u>.


8-bit microcontroller with accelerated two-clock 80C51 core

7.22.1 Typical SPI configurations





8-bit microcontroller with accelerated two-clock 80C51 core




8-bit microcontroller with accelerated two-clock 80C51 core

7.23 Analog comparators

Two analog comparators are provided on the P89LPC9402. Input and output options allow use of the comparators in a number of different configurations. Comparator operation is such that the output is a logic 1 (which may be read in a register and/or routed to a pin) when the positive input (one of two selectable pins) is greater than the negative input (selectable from a pin or an internal reference voltage). Otherwise the output is a zero. Each comparator may be configured to cause an interrupt when the output value changes.

The overall connections to both comparators are shown in <u>Figure 15</u>. The comparators function to $V_{DD} = 2.4 \text{ V}$.

When each comparator is first enabled, the comparator output and interrupt flag are not guaranteed to be stable for 10 μ s. The corresponding comparator interrupt should not be enabled during that time, and the comparator interrupt flag must be cleared before the interrupt is enabled in order to prevent an immediate interrupt service.



7.23.1 Internal reference voltage

An internal reference voltage generator may supply a default reference when a single comparator input pin is used. The value of the internal reference voltage, referred to as $V_{ref(bg)}$, is 1.23 V \pm 10 %.

7.23.2 Comparator interrupt

Each comparator has an interrupt flag contained in its configuration register. This flag is set whenever the comparator output changes state. The flag may be polled by software or may be used to generate an interrupt. The two comparators use one common interrupt vector. If both comparators enable interrupts, after entering the interrupt service routine, the user needs to read the flags to determine which comparator caused the interrupt.

7.23.3 Comparators and power reduction modes

Either or both comparators may remain enabled when Power-down or Idle mode is activated, but both comparators are disabled automatically in Total Power-down mode.

8-bit microcontroller with accelerated two-clock 80C51 core

If a comparator interrupt is enabled (except in Total Power-down mode), a change of the comparator output state will generate an interrupt and wake-up the processor. If the comparator output to a pin is enabled, the pin should be configured in the push-pull mode in order to obtain fast switching times while in Power-down mode. The reason is that with the **oscillator** stopped, the temporary strong pull-up that normally occurs during switching on a quasi-bidirectional port pin does not take place.

Comparators consume power in Power-down and Idle modes, as well as in the normal operating mode. This fact should be taken into account when system power consumption is an issue. To minimize power consumption, the user can disable the comparators via PCONA.5, or put the device in Total Power-down mode.

7.24 Keypad interrupt

The Keypad Interrupt (KBI) function is intended primarily to allow a single interrupt to be generated when Port 0 is equal to or not equal to a certain pattern. This function can be used for bus address recognition or keypad recognition. The user can configure the port via SFRs for different tasks.

The Keypad Interrupt Mask Register (KBMASK) is used to define which input pins connected to Port 0 can trigger the interrupt. The Keypad Pattern Register (KBPATN) is used to define a pattern that is compared to the value of Port 0. The Keypad Interrupt Flag (KBIF) in the Keypad Interrupt Control Register (KBCON) is set when the condition is matched while the Keypad Interrupt function is active. An interrupt will be generated if enabled. The PATN_SEL bit in the Keypad Interrupt Control Register (KBCON) is used to define equal or not-equal for the comparison.


In order to use the Keypad Interrupt as an original KBI function like in 87LPC76x series, the user needs to set KBPATN = 0FFH and PATN_SEL = 1 (not equal), then any key connected to Port 0 which is enabled by the KBMASK register will cause the hardware to set KBIF and generate an interrupt if it has been enabled. The interrupt may be used to wake-up the CPU from Idle or Power-down modes. This feature is particularly useful in handheld, battery-powered systems that need to carefully manage power consumption yet also need to be convenient to use.

In order to set the flag and cause an interrupt, the pattern on Port 0 must be held longer than six CCLKs.

8-bit microcontroller with accelerated two-clock 80C51 core

7.25 Watchdog timer

The watchdog timer causes a system reset when it underflows as a result of a failure to feed the timer prior to the timer reaching its terminal count. It consists of a programmable 12-bit prescaler, and an 8-bit down counter. The down counter is decremented by a tap taken from the prescaler. The clock source for the prescaler can be the PCLK, the nominal 400 kHz watchdog oscillator or crystal oscillator. The watchdog timer can only be reset by a power-on reset. When the watchdog feature is disabled, it can be used as an interval timer and may generate an interrupt. Figure 16 shows the watchdog timer in Watchdog mode. Feeding the watchdog requires a two-byte sequence. If PCLK is selected as the watchdog clock and the CPU is powered down, the watchdog is disabled. The watchdog timer has a time-out period that ranges from a few µs to a few seconds. Please refer to the P89LPC9402 User manual for more details.



7.26 Additional features

7.26.1 Software reset

The SRST bit in AUXR1 gives software the opportunity to reset the processor completely, as if an external reset or watchdog reset had occurred. Care should be taken when writing to AUXR1 to avoid accidental software resets.

7.26.2 Dual data pointers

The dual Data Pointers (DPTR) provides two different Data Pointers to specify the address used with certain instructions. The DPS bit in the AUXR1 register selects one of the two Data Pointers. Bit 2 of AUXR1 is permanently wired as a logic 0 so that the DPS bit may be toggled (thereby switching Data Pointers) simply by incrementing the AUXR1 register, without the possibility of inadvertently altering other bits in the register.

7.27 LCD driver

7.27.1 General description

The LCD segment driver in the P89LPC9402 can interface to most LCDs using low multiplex rates. It generates the drive signals for static or multiplexed LCDs containing up to four backplanes and up to 32 segments. The LCD controller communicates to a host using the I²C-bus. The I²C-bus clock and data signals for both the microcontroller and the LCD driver are available on the P89LPC9402 providing system flexibility. Communication overhead to manage the display is minimized by an on-chip display RAM with auto-increment addressing, hardware subaddressing, and display memory switching (static and duplex drive modes).

7.27.2 Functional description

The LCD controller is a versatile peripheral device designed to interface microcontrollers to a wide variety of LCDs. It can directly drive any static or multiplexed LCD containing up to four backplanes and up to 32 segments. The display configurations possible with the LCD controller depend on the number of active backplane outputs required. A selection of display configurations is shown in Table 8. All of these configurations can be implemented in a typical system.

The microcontroller communicates to the LCD controller using the I^2C -bus. The appropriate biasing voltages for the multiplexed LCD waveforms are generated internally. The only other connections required to complete the system are to the power supplies $(V_{DD}, V_{SS} \text{ and } V_{LCD})$ and the LCD panel chosen for the application.

Table 8. Selection of display configurations	Table 8.	Selection of	display	configurations
--	----------	--------------	---------	----------------

Number of		7-segments	s numeric	14- segments	alphanumeric	Dot matrix
Backplanes	Segments	Digits	Indicator symbols	Characters	Indicator symbols	
4	128	16	16	8	16	128
3	96	12	12	6	12	96
2	64	8	8	4	8	64
1	32	4	4	2	4	32

7.27.3 LCD bias voltages

LCD biasing voltages are obtained from an internal voltage divider consisting of three series resistors connected between V_{LCD} and V_{SS} . The LCD voltage can be temperature compensated externally via the supply to pin V_{LCD} . A voltage selector drives the multiplexing of the LCD based on programmable configurations.

7.27.4 Oscillator

7.27.4.1 Internal clock

An internal oscillator provides the clock signals for the internal logic of the LCD controller and its LCD drive signals. After power-up, pin SDA must be HIGH to guarantee that the clock starts.

8-bit microcontroller with accelerated two-clock 80C51 core

7.27.5 Timing

The LCD controller timing controls the internal data flow of the device. This includes the transfer of display data from the display RAM to the display segment outputs. The timing also generates the LCD frame signal whose frequency is derived from the clock frequency. The frame signal frequency is a fixed division of the clock frequency from either the internal or an external clock.

Frame frequency = $f_{osc(LCD)}/24$.

7.27.6 Display register

A display latch holds the display data while the corresponding multiplex signals are generated. There is a one-to-one relationship between the data in the display latch, the LCD segment outputs, and each column of the display RAM.

7.27.7 Segment outputs

The LCD drive section includes 32 segment outputs S0 to S31. The segment output signals are generated according to the multiplexed backplane signals and the display latch data. When less than 32 segment outputs are required, the unused segment outputs should be left open-circuit.

7.27.8 Backplane outputs

The LCD drive section has four backplane outputs BP0 to BP3. The backplane output signals are generated in based on the selected LCD drive mode. If less than four backplane outputs are required, the unused outputs can be left open-circuit. In the 1:3 multiplex drive mode, BP3 carries the same signal as BP1, therefore these two adjacent outputs can be tied together to give enhanced drive capabilities. In the 1:2 multiplex drive mode, BP0 and BP2, BP1 and BP3 respectively carry the same signals and may also be paired to increase the drive capabilities. In the static drive mode the same signal is carried by all four backplane outputs and they can be connected in parallel for very high drive requirements.

7.27.9 Display RAM

The display RAM is a static 32×4 -bit RAM which stores LCD data. There is a one-to-one correspondence between the RAM addresses and the segment outputs, and between the individual bits of a RAM word and the backplane outputs. The first RAM column corresponds to the 32 segments for backplane 0 (BP0). In multiplexed LCD applications the segment data of the second, third and fourth column of the display RAM are time-multiplexed with BP1, BP2 and BP3 respectively.

7.27.10 Data pointer

The Display RAM is addressed using the data pointer. Either a single byte or a series of display bytes may be loaded into any location of the display RAM.

7.27.11 Output bank selector

The LCD controller includes a RAM bank switching feature in the static and 1:2 drive modes. In the static drive mode, the BANK SELECT command may request the contents of bit 2 to be selected for display instead of the contents of bit 0. In 1:2 mode, the contents of bits 2 and 3 may be selected instead of bits 0 and 1. This allows display information to be prepared in an alternative bank and then selected for display when it is assembled.

8-bit microcontroller with accelerated two-clock 80C51 core

7.27.12 Input bank selector

The input bank selector loads display data into the display RAM based on the selected LCD drive configuration. The BANK SELECT command can be used to load display data in bit 2 in static drive mode or in bits 2 and 3 in 1:2 mode. The input bank selector functions are independent of the output bank selector.

7.27.13 Blinker

The LCD controller has a very versatile display blinking capability. The whole display can blink at a frequency selected by the BLINK command. Each blink frequency is a multiple integer value of the clock frequency; the ratio between the clock frequency and blink frequency depends on the blink mode selected, as shown in Table 9.

An additional feature allows an arbitrary selection of LCD segments to be blinked in the static and 1:2 drive modes. This is implemented without any communication overheads by the output bank selector which alternates the displayed data between the data in the display RAM bank and the data in an alternative RAM bank at the blink frequency. This mode can also be implemented by the BLINK command.

The entire display can be blinked at a frequency other than the nominal blink frequency by sequentially resetting and setting the display enable bit E at the required rate using the MODE SET command.

Table 9. Blinking frequencies

Blink mode	Normal operating mode ratio	Normal blink frequency
Off	-	Blinking off
2 Hz	f _{osc(LCD)} /768	2 Hz
1 Hz	f _{osc(LCD)} /1536	1 Hz
0.5 Hz	f _{osc(LCD)} /3072	0.5 Hz

Blink modes 0.5 Hz, 1 Hz and 2 Hz, and nominal blink frequencies 0.5 Hz, 1 Hz and 2 Hz correspond to an oscillator frequency ($f_{osc(LCD)}$) of 1536 Hz at pin CLK. The oscillator frequency range is 397 Hz to 3046 Hz.

7.27.13.1 I²C-bus controller

The LCD controller acts as an I^2 C-bus slave receiver. In the P89LPC9402 the hardware subaddress inputs A0, A,1 and A2 are tied to V_{SS} setting the hardware subaddress = 0.

7.27.14 Input filters

To enhance noise immunity in electrically adverse environments, RC low-pass filters are provided on the SDA and SCL lines.

7.27.15 I²C-bus slave addresses

The I^2C -bus slave address is 0111 0000. The LCD controller is a write-only device and will not respond to a read access.

8-bit microcontroller with accelerated two-clock 80C51 core

7.28 Flash program memory

7.28.1 General description

The P89LPC9402 flash memory provides in-circuit electrical erasure and programming. The flash can be erased, read, and written as bytes. The Sector and Page Erase functions can erase any flash sector (1 kB) or page (64 bytes). The Chip Erase operation will erase the entire program memory. ICP using standard commercial programmers is available. In addition, IAP and byte-erase allows code memory to be used for non-volatile data storage. On-chip erase and write timing generation contribute to a user-friendly programming interface. The P89LPC9402 flash reliably stores memory contents even after 100,000 erase and program cycles. The cell is designed to optimize the erase and programming mechanisms. The P89LPC9402 uses V_{DD} as the supply voltage to perform the Program/Erase algorithms. When voltage supply is lower than 2.4 V, the BOD FLASH is tripped and flash erase/program is blocked.

7.28.2 Features

- Programming and erase over the full operating voltage range.
- Byte erase allows code memory to be used for data storage.
- Read/Programming/Erase using ISP/IAP/ICP.
- Internal fixed boot ROM, containing low-level IAP routines available to user code.
- Default loader providing ISP via the serial port, located in upper end of user program memory.
- Boot vector allows user-provided flash loader code to reside anywhere in the flash memory space, providing flexibility to the user.
- Any flash program or erase operation in 2 ms.
- Programming with industry-standard commercial programmers.
- Programmable security for the code in the flash for each sector.
- 100,000 typical erase/program cycles for each byte.
- 10 year minimum data retention.

7.28.3 Flash organization

The program memory consists of eight 1 kB sectors on the P89LPC9402 device. Each sector can be further divided into 64-byte pages. In addition to sector erase, page erase, and byte erase, a 64-byte page register is included which allows from 1 byte to 64 bytes of a given page to be programmed at the same time, substantially reducing overall programming time.

7.28.4 Using flash as data storage

The flash code memory array of this device supports individual byte erasing and programming. Any byte in the code memory array may be read using the MOVC instruction, provided that the sector containing the byte has not been secured (a MOVC instruction is not allowed to read code memory contents of a secured sector). Thus any byte in a non-secured sector may be used for non-volatile data storage.

8-bit microcontroller with accelerated two-clock 80C51 core

7.28.5 Flash programming and erasing

Four different methods of erasing or programming of the flash are available. The flash may be programmed or erased in the end-user application (IAP) under control of the application's firmware. Another option is to use the ICP mechanism. This ICP system provides for programming through a serial clock - serial data interface. As shipped from the factory, the upper 512 bytes of user code space contains a serial ISP routine allowing for the device to be programmed in circuit through the serial port. The flash may also be programmed or erased using a commercially available EPROM programmer which supports this device. This device does not provide for direct verification of code memory contents. Instead, this device provides a 32-bit CRC result on either a sector or the entire user code space.

Remark: When voltage supply is lower than 2.4 V, the BOD FLASH is tripped and flash erase/program is blocked.

7.28.6 In-circuit programming

ICP is performed without removing the microcontroller from the system. The ICP facility consists of internal hardware resources to facilitate remote programming of the P89LPC9402 through a two-wire serial interface. Using commercially available programmers, the NXP ICP facility has made ICP in an embedded application possible with a minimum of additional expense in components and circuit board area. The ICP function uses five pins. Only a small connector needs to be available to interface your application to a commercial programmer in order to use this feature. Additional details may be found in the P89LPC9402 *User manual*.

7.28.7 In-application programming

IAP is performed in the application under the control of the microcontroller's firmware. The IAP facility consists of internal hardware resources to facilitate programming and erasing. The NXP IAP has made IAP in an embedded application possible without additional components. Two methods are available to accomplish IAP. A set of predefined IAP functions are provided in a Boot ROM and can be called through a common interface, PGM_MTP. Several IAP calls are available for use by an application program to permit selective erasing and programming of flash sectors, pages, security bits, configuration bytes, and device ID. These functions are selected by setting up the microcontroller's registers before making a call to PGM_MTP at FF03H. The Boot ROM occupies the program memory space at the top of the address space from FF00H to FEFFH, thereby not conflicting with the user program memory space.

In addition, IAP operations can be accomplished through the use of four SFRs consisting of a control/status register, a data register, and two address registers. Additional details may be found in the P89LPC9402 *User manual*.

7.28.8 In-system programming

ISP is performed without removing the microcontroller from the system. The ISP facility consists of a series of internal hardware resources coupled with internal firmware to facilitate remote programming of the P89LPC9402 through the serial port. This firmware is provided by NXP and embedded within each P89LPC9402 device. The NXP ISP facility has made ISP in an embedded application possible with a minimum of additional expense

8-bit microcontroller with accelerated two-clock 80C51 core

in components and circuit board area. The ISP function uses five pins (V_{DD} , V_{SS} , TXD, RXD, and \overline{RST}). Only a small connector needs to be available to interface your application to an external circuit in order to use this feature.

7.28.9 Power-on reset code execution

The P89LPC9402 contains two special flash elements: the Boot Vector and the Boot Status bit. Following reset, the P89LPC9402 examines the contents of the Boot Status bit. If the Boot Status bit is set to zero, power-up execution starts at location 0000H, which is the normal start address of the user's application code. When the Boot Status bit is set to a value other than zero, the contents of the Boot Vector are used as the high byte of the execution address and the low byte is set to 00H.

<u>Table 10</u> shows the factory default Boot Vector setting for these devices. A factory-provided bootloader is pre-programmed into the address space indicated and uses the indicated bootloader entry point to perform ISP functions. This code can be erased by the user.

Remark: Users who wish to use this loader should take precautions to avoid erasing the 1 kB sector that contains this bootloader. Instead, the page erase function can be used to erase the first eight 64-byte pages located in this sector.

A custom bootloader can be written with the Boot Vector set to the custom bootloader, if desired.

Table 10. Default Boot Vector values and ISP entry points

Device	Default Boot Vector	Default boot loader entry point	Default boot loader code range	1 kB sector range
P89LPC9402	1FH	1F00H	1E00H to 1FFFH	1C00H to 1FFFH

7.28.10 Hardware activation of the bootloader

The bootloader can also be executed by forcing the device into ISP mode during a power-on sequence (see the P89LPC9402 *User manual* for specific information). This has the same effect as having a non-zero status byte. This allows an application to be built that will normally execute user code but can be manually forced into ISP operation. If the factory default setting for the Boot Vector (1FH) is changed, it will no longer point to the factory preprogrammed ISP bootloader code. After programming the flash, the status byte should be programmed to zero in order to allow execution of the user's application code beginning at address 0000H.

7.29 User configuration bytes

Some user-configurable features of the P89LPC9402 must be defined at power-up and therefore cannot be set by the program after start of execution. These features are configured through the use of the flash byte UCFG1 and UCFG2. Please see the P89LPC9402 *User Manual* for additional details.

7.30 User sector security bytes

There are eight User Sector Security Bytes on the P89LPC9402 device. Each byte corresponds to one sector. Please see the P89LPC9402 *User manual* for additional details.

8. Limiting values

Table 11. Limiting values

In accordance with the Absolute Maximum Rating System (IEC 60134).[1]

Symbol	Parameter	Conditions	Min	Max	Unit
T _{amb(bias)}	bias ambient temperature		-55	+125	°C
T _{stg}	storage temperature		-65	+150	°C
I _{OH(I/O)}	HIGH-level output current per input/output pin		-	20	mA
I _{OL(I/O)}	LOW-level output current per input/output pin		-	20	mA
I _{I/Otot(max)}	maximum total input/output current		-	100	mA
V _n	voltage on any other pin	except V_{SS} , with respect to V_{DD}	-	3.5	V
P _{tot(pack)}	total power dissipation (per package)	based on package heat transfer, not device power consumption	-	1.5	W

^[1] The following applies to Table 11:

a) This product includes circuitry specifically designed for the protection of its internal devices from the damaging effects of excessive static charge. Nonetheless, it is suggested that conventional precautions be taken to avoid applying greater than the rated maximum.

b) Parameters are valid over operating temperature range unless otherwise specified. All voltages are with respect to V_{SS} unless otherwise noted.

9. Static characteristics

Table 12. Static electrical characteristics

 V_{DD} = 2.4 V to 3.6 V unless otherwise specified.

 $T_{amb} = -40 \,^{\circ}\text{C}$ to +85 $^{\circ}\text{C}$ for industrial applications, unless otherwise specified.

Symbol	Parameter	Conditions		Min	Typ[1]	Max	Unit
I _{DD(oper)}	operating supply current	$V_{DD} = 3.6 \text{ V}; f_{osc} = 12 \text{ MHz}$	[2]	-	11	15	mA
		$V_{DD} = 3.6 \text{ V}; f_{osc} = 18 \text{ MHz}$	[2]	-	17	23	mA
I _{DD(idle)}	Idle mode supply current	$V_{DD} = 3.6 \text{ V}; f_{osc} = 12 \text{ MHz}$	[2]	-	3.7	5	mA
		$V_{DD} = 3.6 \text{ V}; f_{osc} = 18 \text{ MHz}$	[2]	-	6	8	mA
I _{DD(pd)}	Power-down mode supply current	V _{DD} = 3.6 V; voltage comparators powered down	[2]	-	60	85	μΑ
I _{DD(tpd)}	total Power-down mode supply current	$V_{DD} = 3.6 \text{ V}$	[3]	-	9	25	μΑ
$(dV/dt)_r$	rise rate	of V _{DD}		-	-	2	mV/μs
V_{DDR}	data retention supply voltage			1.5	-	-	V
$V_{th(HL)}$	HIGH-LOW threshold voltage	except SCL, SDA		$0.22V_{DD}$	$0.4V_{DD}$	-	V
V _{IL}	LOW-level input voltage	SCL, SDA only		-0.5	-	$0.3V_{DD}$	V
$V_{th(LH)}$	LOW-HIGH threshold voltage	except SCL, SDA		-	0.6V _{DD}	$0.7V_{DD}$	V
V _{IH}	HIGH-level input voltage	SCL, SDA only		$0.7V_{DD}$	-	5.5	V
V _{hys}	hysteresis voltage	port 1		-	0.2V _{DD}	-	V
V _{OL}	LOW-level output voltage	I_{OL} = 20 mA; V_{DD} = 2.4 V to 3.6 V, all ports, all modes except high-Z	[4]	-	0.6	1.0	V
		I_{OL} = 3.2 mA; V_{DD} = 2.4 V to 3.6 V; all ports; all modes except high-Z	<u>[4]</u>	-	0.2	0.3	V
V _{OH}	HIGH-level output voltage	I_{OH} = -20 μ A; V_{DD} = 2.4 V to 3.6 V; all ports; quasi-bidirectional mode		V _{DD} – 0.3	V _{DD} – 0.2	-	V
		I_{OH} = -3.2 mA; V_{DD} = 2.4 V to 3.6 V; all ports; push-pull mode		$V_{DD} - 0.7$	V _{DD} – 0.4	-	V
V_{xtal}	crystal voltage	with respect to V _{SS}		-0.5	-	+4.0	V
V _n	voltage on any other pin	except XTAL1, XTAL2, V _{DD} , with respect to V _{SS}		-0.5	-	+5.5	V
C _{iss}	input capacitance		<u>[5]</u>	-	-	15	pF
I _{IL}	LOW-level input current	$V_1 = 0.4 \ V$	[6]	-	-	-80	μΑ
I _{LI}	input leakage current	$V_I = V_{IL}$, V_{IH} or $V_{th(HL)}$	[7]	-	-	±10	μΑ
I _{THL}	HIGH-LOW transition current	all ports, $V_I = 1.5 \text{ V}$ at $V_{DD} = 3.6 \text{ V}$	[8]	-30	-	-450	μΑ
R _{RST_N(int)}	internal pull-up resistance on pin $\overline{\text{RST}}$			10	-	30	kΩ



Table 12. Static electrical characteristics ... continued

 V_{DD} = 2.4 V to 3.6 V unless otherwise specified.

 T_{amb} = -40 °C to +85 °C for industrial applications, unless otherwise specified.

Symbol	Parameter	Conditions	Min	Typ[1]	Max	Unit
V_{bo}	brownout trip voltage	$2.4 \text{ V} < \text{V}_{DD} < 3.6 \text{ V}$; with BOV = 1, BOPD = 0	2.40	-	2.70	V
V _{ref(bg)}	band gap reference voltage		1.11	1.23	1.34	V
TC_{bg}	band gap temperature coefficient		-	10	20	ppm/°C

- [1] Typical ratings are not guaranteed. The values listed are at room temperature, $V_{DD} = 3 \text{ V}$.
- [2] The I_{DD(oper)}, I_{DD(idle)}, and I_{DD(pd)} specifications are measured using an external clock with the following functions disabled: comparators, real-time clock, and watchdog timer.
- [3] The I_{DD(tpd)} specification is measured using an external clock with the following functions disabled: comparators, real-time clock, brownout detect, and watchdog timer.
- [4] See Section 8 "Limiting values" on page 44 for steady state (non-transient) limits on I_{OL} or I_{OH}. If I_{OL}/I_{OH} exceeds the test condition, V_{OL}/V_{OH} may exceed the related specification.
- [5] Pin capacitance is characterized but not tested.
- [6] Measured with port in quasi-bidirectional mode.
- [7] Measured with port in high-impedance mode.
- [8] Port pins source a transition current when used in quasi-bidirectional mode and externally driven from logic 1 to logic 0. This current is highest when V_I is approximately 2 V.

10. Dynamic characteristics

Table 13. Dynamic characteristics (12 MHz)

 V_{DD} = 2.4 V to 3.6 V unless otherwise specified.

 $T_{amb} = -40 \,^{\circ}\text{C}$ to +85 $^{\circ}\text{C}$ for industrial applications, unless otherwise specified.[1][2]

Symbol	Parameter	Conditions	Varia	Variable clock			Unit
			Min	Max	Min	Max	
f _{osc(RC)}	internal RC oscillator frequency		7.189	7.557	7.189	7.557	MHz
f _{osc(WD)}	internal watchdog oscillator frequency		320	520	320	520	kHz
f _{osc}	oscillator frequency		0	12	-	-	MHz
T _{cy(clk)}	clock cycle time	see Figure 18	83	-	-	-	ns
f _{CLKLP}	low-power select clock frequency		0	8	-	-	MHz
Glitch filte	er						
t _{gr}	glitch rejection time	P1.5/RST pin	-	50	-	50	ns
		any pin except P1.5/RST	-	15	-	15	ns
t _{sa}	signal acceptance time	P1.5/RST pin	125	-	125	-	ns
		any pin except P1.5/RST	50	-	50	-	ns
External c	lock						
t _{CHCX}	clock HIGH time	see Figure 18	33	$T_{cy(clk)} - t_{CLCX}$	33	-	ns
t _{CLCX}	clock LOW time	see Figure 18	33	$T_{\text{cy(clk)}} - t_{\text{CHCX}}$	33	-	ns
t _{CLCH}	clock rise time	see Figure 18	-	8	-	8	ns
t _{CHCL}	clock fall time	see Figure 18	-	8	-	8	ns
Shift regis	ster (UART mode 0)						
T _{XLXL}	serial port clock cycle time	see Figure 17	16T _{cy(clk)}	-	1333	-	ns
t _{QVXH}	output data set-up to clock rising edge time	see Figure 17	13T _{cy(clk)}	-	1083	-	ns
t _{XHQX}	output data hold after clock rising edge time	see Figure 17	-	$T_{cy(clk)} + 20$	-	103	ns
t _{XHDX}	input data hold after clock rising edge time	see Figure 17	-	0	-	0	ns
t _{XHDV}	input data valid to clock rising edge time	see Figure 17	150	-	150	-	ns
SPI interfa	ace						
f _{SPI}	SPI operating frequency						
	slave		0	CCLK/6	0	2.0	MHz
	master		-	CCLK/4	-	3.0	MHz
T _{SPICYC}	SPI cycle time	see Figure 19,					
	slave	<u>20, 21, 22</u>	⁶ ∕CCLK	-	500	-	ns
	master		⁴∕cclk	-	333	-	ns
t _{SPILEAD}	SPI enable lead time	see Figure 21,					
	slave	22	250	-	250	-	ns

8-bit microcontroller with accelerated two-clock 80C51 core

Table 13. Dynamic characteristics (12 MHz) ...continued

 V_{DD} = 2.4 V to 3.6 V unless otherwise specified.

 $T_{amb} = -40 \,^{\circ}\text{C}$ to +85 $^{\circ}\text{C}$ for industrial applications, unless otherwise specified. [1][2]

Symbol	Parameter	Conditions	Variak	ole clock	f _{osc} = 12 MHz		Unit	
			Min	Max	Min	Max		
t _{SPILAG}	SPI enable lag time	see Figure 21,						
	slave	<u>22</u>	250	-	250	-	ns	
t _{SPICLKH}	SPICLK HIGH time	see Figure 19,						
	master	<u>20, 21, 22</u>	² /CCLK	-	165	-	ns	
	slave		³ /CCLK	-	250	-	ns	
t _{SPICLKL}	SPICLK LOW time	see <u>Figure 19</u> ,						
	master	<u>20, 21, 22</u>	² /CCLK	-	165	-	ns	
	slave		³ /cclk	-	250	-	ns	
t _{SPIDSU}	SPI data set-up time	see <u>Figure 19</u> ,	100	-	100	-	ns	
	master or slave	<u>20, 21, 22</u>						
t _{SPIDH}	SPI data hold time	see Figure 19,	100	-	100	-	ns	
	master or slave	<u>20, 21, 22</u>						
t _{SPIA}	SPI access time	see <u>Figure 21</u> ,						
	slave	<u>22</u>	0	120	0	120	ns	
t _{SPIDIS}	SPI disable time	see <u>Figure 21</u> ,						
	slave	<u>22</u>	0	240	-	240	ns	
t _{SPIDV}	SPI enable to output data valid time	see <u>Figure 19</u> ,						
	slave	<u>20, 21, 22</u>	-	240	-	240	ns	
	master		-	167	-	167	ns	
t _{SPIOH}	SPI output data hold time	see <u>Figure 19,</u> 20, 21, 22	0	-	0	-	ns	
t _{SPIR}	SPI rise time	see Figure 19,						
	SPI outputs (SPICLK, MOSI, MISO)	<u>20, 21, 22</u>	-	100	-	100	ns	
	SPI inputs (SPICLK, MOSI, MISO, \overline{SS})		-	2000	-	2000	ns	
t _{SPIF}	SPI fall time	see Figure 19,						
	SPI outputs (SPICLK, MOSI, MISO)	<u>20, 21, 22</u>	-	100	-	100	ns	
	SPI inputs (SPICLK, MOSI, MISO, \overline{SS})		-	2000	-	2000	ns	

^[1] Parameters are valid over operating temperature range unless otherwise specified.

^[2] Parts are tested to 2 MHz, but are guaranteed to operate down to 0 Hz.

Table 14. Dynamic characteristics (18 MHz)

 V_{DD} = 3.0 V to 3.6 V unless otherwise specified.

 $T_{amb} = -40 \,^{\circ}\text{C}$ to +85 $^{\circ}\text{C}$ for industrial applications, unless otherwise specified.[1][2]

Symbol	Parameter	Conditions	Varia	able clock	f _{osc} = 18 MHz		Unit
			Min	Max	Min	Max	
f _{osc(RC)}	internal RC oscillator frequency		7.189	7.557	7.189	7.557	MHz
f _{osc(WD)}	internal watchdog oscillator frequency		320	520	320	520	kHz
f _{osc}	oscillator frequency		0	18	-	-	MHz
T _{cy(clk)}	clock cycle time	see Figure 18	55	-	-	-	ns
f _{CLKLP}	low-power select clock frequency		0	8	-	-	MHz
Glitch filte	er						
t _{gr}	glitch rejection time	P1.5/RST pin	-	50	-	50	ns
		any pin except P1.5/RST	125	-	125	-	ns
t _{sa}	signal acceptance time	P1.5/RST pin	-	15	-	15	ns
		any pin except P1.5/RST	50	-	50	-	ns
External c	lock						
t _{CHCX}	clock HIGH time	see Figure 18	22	$T_{\text{cy(clk)}} - t_{\text{CLCX}}$	22	-	ns
t _{CLCX}	clock LOW time	see Figure 18	22	$T_{\text{cy(clk)}} - t_{\text{CHCX}}$	22	-	ns
t _{CLCH}	clock rise time	see Figure 18	-	5	-	5	ns
t _{CHCL}	clock fall time	see Figure 18	-	5	-	5	ns
Shift regis	ster (UART mode 0)						
T_{XLXL}	serial port clock cycle time	see Figure 17	$16T_{cy(clk)}$	-	888	-	ns
t _{QVXH}	output data set-up to clock rising edge time	see Figure 17	13T _{cy(clk)}	-	722	-	ns
t _{XHQX}	output data hold after clock rising edge time	see Figure 17	-	$T_{cy(clk)} + 20$	-	75	ns
t _{XHDX}	input data hold after clock rising edge time	see Figure 17	-	0	-	0	ns
t _{XHDV}	input data valid to clock rising edge time	see Figure 17	150	-	150	-	ns
SPI interfa	ace						
f _{SPI}	SPI operating frequency						
	slave		0	CCLK/6	0	3.0	MHz
	master		-	CCLK/4	-	4.5	MHz
T _{SPICYC}	SPI cycle time	see Figure 19,					
	slave	<u>20, 21, 22</u>	⁶ ∕CCLK	-	333	-	ns
	master		⁴∕cclk	-	222	-	ns
t _{SPILEAD}	SPI enable lead time	see Figure 21,					
	slave	<u>22</u>	250	-	250	-	ns
t _{SPILAG}	SPI enable lag time	see Figure 21,					
	slave	<u>22</u>	250	-	250	-	ns

8-bit microcontroller with accelerated two-clock 80C51 core

Table 14. Dynamic characteristics (18 MHz) ...continued

 V_{DD} = 3.0 V to 3.6 V unless otherwise specified.

 $T_{amb} = -40 \,^{\circ}\text{C}$ to +85 $^{\circ}\text{C}$ for industrial applications, unless otherwise specified. [1][2]

Symbol	Parameter	Conditions	Variable clock		f _{osc} = 1	f _{osc} = 18 MHz	
			Min	Max	Min	Max	
SPICLKH	SPICLK HIGH time	see Figure 19,				1	
	master	<u>20, 21, 22</u>	² /cclk	-	111	-	ns
	slave		³ /CCLK	-	167	-	ns
tspiclkl	SPICLK LOW time	see Figure 19,					
	master	<u>20, 21, 22</u>	² /CCLK	-	111	-	ns
	slave		³ /cclk	-	167	-	ns
t _{SPIDSU}	SPI data set-up time	see Figure 19,	100	-	100	111 - r 167 - r 100 - r 100 - r 0 80 r - 160 r	ns
	master or slave	<u>20, 21, 22</u>					
t _{SPIDH}	SPI data hold time	see Figure 19,	100	-	100	-	ns
	master or slave	<u>20, 21, 22</u>					
t _{SPIA}	SPI access time	see Figure 21,					
	slave	<u>22</u>	0	80	0	80	ns
t _{SPIDIS}	SPI disable time	see <u>Figure 21</u> , <u>22</u>					
	slave		0	160	-	160	ns
SPIDV	SPI enable to output data valid time	see Figure 19,					
	slave	<u>20, 21, 22</u>	-	160	-	160	ns
	master		-	111	-	111	ns
t _{SPIOH}	SPI output data hold time	see <u>Figure 19,</u> <u>20, 21, 22</u>	0	-	0	-	ns
SPIR	SPI rise time	see Figure 19,					
	SPI outputs (SPICLK, MOSI, MISO)	<u>20, 21, 22</u>	-	100	-	100	ns
	SPI inputs (SPICLK, MOSI, MISO, \overline{SS})		-	2000	-	2000	ns
SPIF	SPI fall time	see Figure 19,					
	SPI outputs (SPICLK, MOSI, MISO)	<u>20, 21, 22</u>	-	100	-	100	ns
	SPI inputs (SPICLK, MOSI, MISO, SS)		-	2000	-	2000	ns


^[1] Parameters are valid over operating temperature range unless otherwise specified.


^[2] Parts are tested to 2 MHz, but are guaranteed to operate down to 0 Hz.


P89LPC9402


8-bit microcontroller with accelerated two-clock 80C51 core


10.1 Waveforms












P89LPC9402

8-bit microcontroller with accelerated two-clock 80C51 core




10.2 ISP entry mode

Table 15. Dynamic characteristics, ISP entry mode

 V_{DD} = 2.4 V to 3.6 V, unless otherwise specified.

 T_{amb} = -40 °C to +85 °C for industrial applications, unless otherwise specified.

Symbol	Parameter	Conditions	Min	Тур	Max	Unit
t_{VR}	V_{DD} active to \overline{RST} active delay time	е	50	-	-	μs
t _{RH}	RST HIGH time		1	-	32	μs
t _{RL}	RST LOW time		1	-	-	μs



P89LPC9402_1 © NXP B.V. 2009. All rights reserved.

8-bit microcontroller with accelerated two-clock 80C51 core

11. Other characteristics

11.1 Comparator electrical characteristics

Table 16. Comparator electrical characteristics

 V_{DD} = 2.4 V to 3.6 V, unless otherwise specified.

 $T_{amb} = -40 \,^{\circ}C$ to +85 $^{\circ}C$ for industrial applications, unless otherwise specified.


Symbol	Parameter	Conditions	Min	Тур	Max	Unit
V_{IO}	input offset voltage		-	-	±20	mV
V _{IC}	common-mode input voltage		0	-	$V_{DD}-0.3$	V
CMRR	common-mode rejection ratio		<u>[1]</u> _	-	-50	dB
t _{res(tot)}	total response time		-	250	500	ns
t _(CE-OV)	chip enable to output valid time		-	-	10	μs
I _{LI}	input leakage current	$0 V < V_I < V_{DD}$	-	-	±10	μΑ

^[1] This parameter is characterized, but not tested in production.

12. Package outline

LQFP64: plastic low profile quad flat package; 64 leads; body 14 x 14 x 1.4 mm

SOT791-1



UNIT	A max.	A ₁	A ₂	A ₃	bp	С	D ⁽¹⁾	E ⁽¹⁾	е	H _D	HE	L	Lp	v	w	у	Z _D ⁽¹⁾	Z _E ⁽¹⁾	θ
mm	1.6	0.15 0.05	1.45 1.35	0.25	0.45 0.30	0.20 0.09	14.1 13.9	14.1 13.9	0.8	16.15 15.85	16.15 15.85	1	0.75 0.45	0.2	0.2	0.1	1.2 0.8	1.2 0.8	7° 0°

Note

1. Plastic or metal protrusions of 0.25 mm maximum per side are not included.

VERSION IEC JEDEC JEITA PROJECTION SOT791-1 136E18 MS-026 ED-7311EC 02-10-22	OUTLINE		REFER	EUROPEAN	ISSUE DATE		
SOT791-1 136E18 MS-026 ED-7311EC	VERSION	IEC	JEDEC	JEITA		PROJECTION	1330E DATE
	SOT791-1	136E18	MS-026	ED-7311EC			02-10-22

Fig 24. Package outline SOT791-1 (LQFP64)

P89LPC9402_1

8-bit microcontroller with accelerated two-clock 80C51 core

13. Abbreviations

Table 17. Acronym list

Acronym	Description
BOD	Brownout Detect
CPU	Central Processing Unit
EPROM	Erasable Programmable Read-Only Memory
EMI	Electro-Magnetic Interference
LCD	Liquid Crystal Display
LED	Light Emitting Diode
PWM	Pulse Width Modulator
RAM	Random Access Memory
RC	Resistance-Capacitance
RTC	Real-Time Clock
SFR	Special Function Register
SPI	Serial Peripheral Interface
UART	Universal Asynchronous Receiver/Transmitter
WDT	WatchDog Timer

8-bit microcontroller with accelerated two-clock 80C51 core

14. Revision history

Table 18. Revision history

Document ID	Release date	Data sheet status	Change notice	Doc. number	Supersedes
P89LPC9402_1	20090422	Product data sheet	-	-	-

8-bit microcontroller with accelerated two-clock 80C51 core

15. Legal information

15.1 Data sheet status

Document status[1][2]	Product status[3]	Definition
Objective [short] data sheet	Development	This document contains data from the objective specification for product development.
Preliminary [short] data sheet	Qualification	This document contains data from the preliminary specification.
Product [short] data sheet	Production	This document contains the product specification.

- [1] Please consult the most recently issued document before initiating or completing a design.
- [2] The term 'short data sheet' is explained in section "Definitions"
- [3] The product status of device(s) described in this document may have changed since this document was published and may differ in case of multiple devices. The latest product status information is available on the Internet at URL http://www.nxp.com.

15.2 Definitions

Draft — The document is a draft version only. The content is still under internal review and subject to formal approval, which may result in modifications or additions. NXP Semiconductors does not give any representations or warranties as to the accuracy or completeness of information included herein and shall have no liability for the consequences of use of such information.

Short data sheet — A short data sheet is an extract from a full data sheet with the same product type number(s) and title. A short data sheet is intended for quick reference only and should not be relied upon to contain detailed and full information. For detailed and full information see the relevant full data sheet, which is available on request via the local NXP Semiconductors sales office. In case of any inconsistency or conflict with the short data sheet, the full data sheet shall prevail.

15.3 Disclaimers

General — Information in this document is believed to be accurate and reliable. However, NXP Semiconductors does not give any representations or warranties, expressed or implied, as to the accuracy or completeness of such information and shall have no liability for the consequences of use of such information.

Right to make changes — NXP Semiconductors reserves the right to make changes to information published in this document, including without limitation specifications and product descriptions, at any time and without notice. This document supersedes and replaces all information supplied prior to the publication hereof.

Suitability for use — NXP Semiconductors products are not designed, authorized or warranted to be suitable for use in medical, military, aircraft, space or life support equipment, nor in applications where failure or malfunction of an NXP Semiconductors product can reasonably be expected to result in personal injury, death or severe property or environmental

damage. NXP Semiconductors accepts no liability for inclusion and/or use of NXP Semiconductors products in such equipment or applications and therefore such inclusion and/or use is at the customer's own risk.

Applications — Applications that are described herein for any of these products are for illustrative purposes only. NXP Semiconductors makes no representation or warranty that such applications will be suitable for the specified use without further testing or modification.

Limiting values — Stress above one or more limiting values (as defined in the Absolute Maximum Ratings System of IEC 60134) may cause permanent damage to the device. Limiting values are stress ratings only and operation of the device at these or any other conditions above those given in the Characteristics sections of this document is not implied. Exposure to limiting values for extended periods may affect device reliability.

Terms and conditions of sale — NXP Semiconductors products are sold subject to the general terms and conditions of commercial sale, as published at http://www.nxp.com/profile/terms, including those pertaining to warranty, intellectual property rights infringement and limitation of liability, unless explicitly otherwise agreed to in writing by NXP Semiconductors. In case of any inconsistency or conflict between information in this document and such terms and conditions, the latter will prevail.

No offer to sell or license — Nothing in this document may be interpreted or construed as an offer to sell products that is open for acceptance or the grant, conveyance or implication of any license under any copyrights, patents or other industrial or intellectual property rights.

Export control — This document as well as the item(s) described herein may be subject to export control regulations. Export might require a prior authorization from national authorities.

15.4 Trademarks

Notice: All referenced brands, product names, service names and trademarks are the property of their respective owners.

I²C-bus — logo is a trademark of NXP B.V.

16. Contact information

For more information, please visit: http://www.nxp.com

For sales office addresses, please send an email to: salesaddresses@nxp.com

P89LPC9402_1 © NXP B.V. 2009. All rights reserved.

P89LPC9402

8-bit microcontroller with accelerated two-clock 80C51 core

17. Contents

_		_			
1	General description		7.16.3	Total Power-down mode	
2	Features		7.17	Reset	
2.1	Principal features	1	7.17.1	Reset vector	
2.2	Additional features	1	7.18	Timers/counters 0 and 1	
3	Ordering information	3	7.18.1	Mode 0	
3.1	Ordering options		7.18.2	Mode 1	
4	Block diagram		7.18.3	Mode 2	
			7.18.4	Mode 3	
5	Functional diagram		7.18.5	Mode 6	
6	Pinning information		7.18.6	Timer overflow toggle output	
6.1	Pinning		7.19	RTC/system timer	
6.2	Pin description	7	7.20	UART	
7	Functional description	. 11	7.20.1	Mode 0	
7.1	Special function registers	. 11	7.20.2	Mode 1	
7.2	Enhanced CPU		7.20.3	Mode 2	
7.3	Clocks		7.20.4	Mode 3	
7.3.1	Clock definitions	. 17	7.20.5	Baud rate generator and selection	
7.3.2	CPU clock (OSCCLK)	. 17	7.20.6	Framing error	
7.3.3	Crystal oscillator option	. 17	7.20.7	Break detect	
7.3.3.1	Low speed oscillator option		7.20.8	Double buffering	29
7.3.3.2	Medium speed oscillator option	. 17	7.20.9	Transmit interrupts with double buffering	00
7.3.3.3	High speed oscillator option		7.00.40	enabled (modes 1, 2 and 3)	29
7.3.4	Clock output		7.20.10	The 9 th bit (bit 8) in double buffering	00
7.4	On-chip RC oscillator option		7.04	(modes 1, 2 and 3)	
7.5	Watchdog oscillator option		7.21	I ² C-bus serial interface	
7.6	External clock input option		7.22	SPI	
7.7	Clock sources switch on the fly	. 18	7.22.1	Typical SPI configurations	
7.8	CPU Clock (CCLK) wake-up delay	. 20	7.23	Analog comparators	
7.9	CCLK modification: DIVM register	. 20	7.23.1	Internal reference voltage	
7.10	Low power select	. 20	7.23.2	Comparator interrupt	
7.11	Memory organization	. 20	7.23.3	Comparators and power reduction modes	
7.12	Data RAM arrangement	. 21	7.24	Keypad interrupt	
7.13	Interrupts		7.25	Watchdog timer	
7.13.1	External interrupt inputs		7.26	Additional features	
7.14	I/O ports	. 22	7.26.1	Software reset	
7.14.1	Port configurations	. 23	7.26.2	Dual data pointers	
7.14.1.1	Quasi-bidirectional output configuration	. 23	7.27	LCD driver	
7.14.1.2	2 Open-drain output configuration	. 23	7.27.1 7.27.2	General description	
7.14.1.3	B Input-only configuration	. 23		Functional description	
7.14.1.4	Push-pull output configuration	. 23	7.27.3 7.27.4	LCD bias voltages	
7.14.2	Port 0 analog functions	. 23		Oscillator	
7.14.3	Additional port features	. 24	7.27.4.1	Internal clock	
7.15	Power monitoring functions	. 24	7.27.5	Timing	
7.15.1	Brownout detection	. 24	7.27.6	Display register	
7.15.2	Power-on detection	. 25	7.27.7	Segment outputs	
7.16	Power reduction modes	. 25	7.27.8	Backplane outputs	
7.16.1	Idle mode	. 25	7.27.9	Display RAM	
7 16 2	Power-down mode	25	7.27.10	Data pointer	39

continued >>

59 of 60

NXP Semiconductors

P89LPC9402

8-bit microcontroller with accelerated two-clock 80C51 core

7.27.11	Output bank selector	39
7.27.12	Input bank selector	40
7.27.13	Blinker	40
7.27.13.		40
7.27.14	Input filters	40
7.27.15	I ² C-bus slave addresses	40
7.28	Flash program memory	41
7.28.1	General description	41 41
7.28.2	Features	41
7.28.3 7.28.4	Flash organization	41
7.28.5	Using flash as data storage	41
7.28.6	In-circuit programming	42
7.28.7	In-application programming	42
7.28.8	In-system programming	42
7.28.9	Power-on reset code execution	43
7.28.10	Hardware activation of the bootloader	43
7.29	User configuration bytes	43
7.30	User sector security bytes	43
8	Limiting values	44
9	Static characteristics	45
10	Dynamic characteristics	47
10.1	Waveforms	51
10.2	ISP entry mode	53
11	Other characteristics	54
11.1	Comparator electrical characteristics	54
12	Package outline	55
13	Abbreviations	56
14	Revision history	57
15	Legal information	58
15.1	Data sheet status	58
15.2	Definitions	58
15.3	Disclaimers	58
15.4	Trademarks	58
16	Contact information	58
17	Contents	50

Please be aware that important notices concerning this document and the product(s) described herein, have been included in section 'Legal information'.

