NX3L1T5157

Low-ohmic single-pole double-throw analog switch

Rev. 6.2 — 3 December 2019

Product data sheet

1. General description

The NX3L1T5157 is a low-ohmic single-pole double-throw analog switch suitable for use as an analog or digital 2:1 multiplexer/demultiplexer. It has a digital select input (S), two independent inputs/outputs (Y0 and Y1) and a common input/output (Z).

Schmitt trigger action at the digital input makes the circuit tolerant to slower input rise and fall times. Low threshold digital input allows this device to be driven by 1.8 V logic levels in 3.3 V applications without significant increase in supply current I_{CC} . This makes it possible for the NX3L1T5157 to switch 4.3 V signals with a 1.8 V digital controller, eliminating the need for logic level translation. The NX3L1T5157 allows signals with amplitude up to V_{CC} to be transmitted from Z to Y0 or Y1, or from Y0 or Y1 to Z. Its low ON resistance (0.5 Ω) and flatness (0.13 Ω) ensures minimal attenuation and distortion of transmitted signals.

2. Features and benefits

- Wide supply voltage range from 1.4 V to 4.3 V
- Very low ON resistance (peak):
 - 1.6 Ω (typical) at $V_{CC} = 1.4 \text{ V}$
 - 1.0 Ω (typical) at $V_{CC} = 1.65 \text{ V}$
 - 0.55 Ω (typical) at $V_{CC} = 2.3 \text{ V}$
 - 0.50 Ω (typical) at V_{CC} = 2.7 V
 - 0.50 Ω (typical) at $V_{CC} = 4.3 \text{ V}$
- Break-before-make switching
- High noise immunity
- ESD protection:
 - HBM JESD22-A114F Class 3A exceeds 7500 V
 - MM JESD22-A115-A exceeds 200 V
 - ◆ CDM AEC-Q100-011 revision B exceeds 1000 V
 - ◆ IEC61000-4-2 contact discharge exceeds 8000 V for switch ports
- CMOS low-power consumption
- Latch-up performance exceeds 100 mA per JESD78 Class II Level A
- 1.8 V control logic at V_{CC} = 3.6 V
- Control input accepts voltages above supply voltage
- Very low supply current, even when input is below V_{CC}
- High current handling capability (350 mA continuous current under 3.3 V supply)
- Specified from -40 °C to +85 °C and from -40 °C to +125 °C



NX3L1T5157

Low-ohmic single-pole double-throw analog switch

3. Applications

- Cell phone
- PDA
- Portable media player

4. Ordering information

Table 1. Ordering information

Type number	Topside	Package		
	marking[1]	Name	Description	Version
NX3L1T5157GM	DI	XSON6	plastic extremely thin small outline package; no leads; 6 terminals; body 1 x 1.45 x 0.5 mm	SOT886

^[1] The pin 1 indicator is located on the lower left corner of the device, below the marking code.


4.1 Ordering options

Table 2. Ordering options

Type number	Orderable part number	Package	Packing method	Minimum order quantity	Temperature
NX3L1T5157GM	NX3L1T5157GM,115[1]	XSON6	REEL 7" Q1 NDP	5000	$T_{amb} = -40 ^{\circ}\text{C} \text{ to } +125 ^{\circ}\text{C}$
NX3L1T5157GM	NX3L1T5157GM,132[1]	XSON6	REEL 7" Q3 NDP	5000	$T_{amb} = -40 ^{\circ}\text{C} \text{ to } +125 ^{\circ}\text{C}$
NX3L1T5157GM	NX3L1T5157GMZ	XSON6	REEL 7" Q1 NDP SSB[2]	5000	$T_{amb} = -40 ^{\circ}\text{C} \text{ to } +125 ^{\circ}\text{C}$
NX3L1T5157GM	NX3L1T5157GMAZ	XSON6	REEL 7" Q3 NDP SSB[2]	5000	$T_{amb} = -40 ^{\circ}\text{C} \text{ to } +125 ^{\circ}\text{C}$

^[1] Will go EOL - migrate to new leadframe orderable part number.

5. Functional diagram




^[2] This packing method uses a Static Shielding Bag (SSB) solution. Material is to be kept in the sealed bag between uses.

Low-ohmic single-pole double-throw analog switch

6. Pinning information

6.1 Pinning



6.2 Pin description

Table 3. Pin description

Symbol	Pin	Description
S	1	select input
V _{CC}	2	supply voltage
Z	3	common input or output
Y0	4	independent input or output
GND	5	ground (0 V)
Y1	6	independent input or output

7. Functional description

Table 4. Function table[1]

Input S	Channel on
L	Y0
Н	Y1

[1] H = HIGH voltage level; L = LOW voltage level.

8. Limiting values

Table 5. Limiting values

In accordance with the Absolute Maximum Rating System (IEC 60134). Voltages are referenced to GND (ground = 0 V).

Symbol	Parameter	Conditions	Min	Max	Unit
V _{CC}	supply voltage		-0.5	+4.6	V
VI	input voltage	select input S	-0.5	+4.6	V
V_{SW}	switch voltage	[2]	-0.5	$V_{CC} + 0.5$	V
I _{IK}	input clamping current	$V_1 < -0.5 \text{ V}$	-50	-	mA
I _{SK}	switch clamping current	$V_{I} < -0.5 \text{ V or } V_{I} > V_{CC} + 0.5 \text{ V}$	-	±50	mA
I _{SW}	switch current	$V_{SW} > -0.5 \text{ V or } V_{SW} < V_{CC} + 0.5 \text{ V};$ source or sink current	-	±350	mA
		V_{SW} > -0.5 V or V_{SW} < V_{CC} + 0.5 V; pulsed at 1 ms duration, < 10 % duty cycle; peak current	-	±500	mA
T _{stg}	storage temperature		-65	+150	°C
P _{tot}	total power dissipation	$T_{amb} = -40 ^{\circ}\text{C} \text{ to } +125 ^{\circ}\text{C}$	-	250	mW

^[1] The minimum input voltage rating may be exceeded if the input current rating is observed.

9. Recommended operating conditions

Table 6. Recommended operating conditions

Symbol	Parameter	Conditions	Min	Max	Unit
V_{CC}	supply voltage		1.4	4.3	V
VI	input voltage	select input S	0	4.3	V
V_{SW}	switch voltage	[1]	0	V _{CC}	V
T _{amb}	ambient temperature		-40	+125	°C
Δt/ΔV	input transition rise and fall rate	$V_{CC} = 1.4 \text{ V to } 4.3 \text{ V}$ [2]	-	200	ns/V

^[1] To avoid sinking GND current from terminal Z when switch current flows in terminal Yn, the voltage drop across the bidirectional switch must not exceed 0.4 V. If the switch current flows into terminal Z, no GND current will flow from terminal Yn. In this case, there is no limit for the voltage drop across the switch.

^[2] The minimum and maximum switch voltage ratings may be exceeded if the switch clamping current rating is observed but may not exceed 4.6 V.

^[3] For XSON6 package: above 118 °C the value of Ptot derates linearly with 7.8 mW/K.

^[2] Applies to control signal levels.

10. Static characteristics


Table 7. Static characteristics


At recommended operating conditions; voltages are referenced to GND (ground 0 V).

Symbol	Parameter	Conditions	Ta	_{amb} = 25	°C	T _{amb} =	–40 °C to	+125 °C	Unit
			Min	Тур	Max	Min	Max (85 °C)	Max (125 °C)	
V _{IH}	HIGH-level	V _{CC} = 1.4 V to 1.6 V	0.9	-	-	0.9	-	-	V
	input voltage	V _{CC} = 1.65 V to 1.95 V	0.9	-	-	0.9	-	-	V
		V _{CC} = 2.3 V to 2.7 V	1.1	-	-	1.1	-	-	V
		V _{CC} = 2.7 V to 3.6 V	1.3	-	-	1.3	-	-	V
	V _{CC} = 3.6 V to 4.3 V	1.4	-	-	1.4	-	-	V	
V _{IL}	LOW-level	V _{CC} = 1.4 V to 1.6 V	-	-	0.3	-	0.3	0.3	V
	input voltage	V _{CC} = 1.65 V to 1.95 V	-	-	0.4	-	0.4	0.3	V
		V _{CC} = 2.3 V to 2.7 V	-	-	0.4	-	0.4	0.4	V
		V _{CC} = 2.7 V to 3.6 V	-	-	0.5	-	0.5	0.5	V
		V _{CC} = 3.6 V to 4.3 V	-	-	0.6	-	0.6	0.6	V
l _l	input leakage current	select input S; V _I = GND to 4.3 V; V _{CC} = 1.4 V to 4.3 V	-	-	-	-	±0.5	±1	μА
I _{S(OFF)}	OFF-state leakage	Y0 and Y1 port; see Figure 4							
	current	V _{CC} = 1.4 V to 3.6 V	-	-	±5	-	±50	±500	nΑ
		$V_{CC} = 3.6 \text{ V to } 4.3 \text{ V}$	-	-	±10	-	±50	±500	nΑ
I _{S(ON)}	ON-state	Z port; see Figure 5							
	leakage	V _{CC} = 1.4 V to 3.6 V	-	-	±5	-	±50	±500	nΑ
	current	V _{CC} = 3.6 V to 4.3 V	-	-	±10	-	±50	±500	nΑ
I _{CC}	supply current	$V_I = V_{CC}$ or GND; $V_{SW} = GND$ or V_{CC}							
		V _{CC} = 3.6 V	-	-	100	-	690	6000	nΑ
		V _{CC} = 4.3 V	-	-	150	-	800	7000	nΑ
ΔI_{CC}	additional	V_{SW} = GND or V_{CC}							
	supply current	$V_I = 2.6 \text{ V}; V_{CC} = 4.3 \text{ V}$	-	2.0	4.0	-	7	7	μΑ
		V _I = 2.6 V; V _{CC} = 3.6 V	-	0.35	0.7	-	1	1	μΑ
		V _I = 1.8 V; V _{CC} = 4.3 V	-	7.0	10.0	-	15	15	μΑ
		V _I = 1.8 V; V _{CC} = 3.6 V	-	2.5	4.0	-	5	Max (125 °C)	μΑ
		V _I = 1.8 V; V _{CC} = 2.5 V	-	50	200	-	300	500	nΑ
Cı	input capacitance		-	1.0	-	-	-	-	pF
C _{S(OFF)}	OFF-state capacitance		-	35	-	-	-	-	pF
C _{S(ON)}	ON-state capacitance		-	130	-	-	-	-	pF

Low-ohmic single-pole double-throw analog switch

10.1 Test circuits





10.2 ON resistance

Table 8. ON resistance

At recommended operating conditions; voltages are referenced to GND (ground = 0 V); for graphs see Figure 7 to Figure 13.

Symbol	Parameter	Conditions	T _{amb} =	$_{0}$ = -40 °C to +85 °C		T _{amb} = -40 °	Unit	
			Min	Typ[1]	Max	Min	Max	
R _{ON(peak)}	ON resistance (peak)	$V_I = GND \text{ to } V_{CC};$ $I_{SW} = 100 \text{ mA}; \text{ see } \frac{\text{Figure 6}}{\text{MB}}$						
		V _{CC} = 1.4 V	-	1.6	3.7	-	4.1	Ω
		V _{CC} = 1.65 V	-	1.0	1.6	-	1.7	Ω
		V _{CC} = 2.3 V	-	0.55	0.8	-	0.9	Ω
		V _{CC} = 2.7 V	-	0.5	0.75	-	0.9	Ω
		$V_{CC} = 4.3 \text{ V}$	-	0.5	0.75	-	0.9	Ω

Low-ohmic single-pole double-throw analog switch

Table 8. ON resistance ...continued

At recommended operating conditions; voltages are referenced to GND (ground = 0 V); for graphs see Figure 7 to Figure 13.

Symbol Parameter		Conditions	T _{amb} =	$T_{amb} = -40 ^{\circ}\text{C} \text{ to } +85 ^{\circ}\text{C}$ $T_{amb} = -40 ^{\circ}\text{C} \text{ to } +125 ^{\circ}\text{C}$				Unit
			Min	Typ[1]	Max	Min	Max	
ΔR_{ON}	ON resistance mismatch	$V_I = GND \text{ to } V_{CC};$ $I_{SW} = 100 \text{ mA}$						
	between channels	V _{CC} = 1.4 V	-	0.04	0.3	-	0.3	Ω
	Chamileis	V _{CC} = 1.65 V	-	0.04	0.2	-	0.3	Ω
	V _{CC} = 2.3 V	-	0.02	0.08	-	0.1	Ω	
		V _{CC} = 2.7 V	-	0.02	0.075	-	0.1	Ω
		V _{CC} = 4.3 V	-	0.02	0.075	-	0.1	Ω
R _{ON(flat)}	ON resistance (flatness)	$V_I = GND \text{ to } V_{CC};$ $I_{SW} = 100 \text{ mA}$						
		V _{CC} = 1.4 V	-	1.0	3.3	-	3.6	Ω
		V _{CC} = 1.65 V	-	0.5	1.2	-	1.3	Ω
		V _{CC} = 2.3 V	-	0.15	0.3	-	0.35	Ω
		V _{CC} = 2.7 V	-	0.13	0.3	-	0.35	Ω
		V _{CC} = 4.3 V	-	0.2	0.4	-	0.45	Ω

^[1] Typical values are measured at T_{amb} = 25 °C.

^[2] Measured at identical V_{CC}, temperature and input voltage.

^[3] Flatness is defined as the difference between the maximum and minimum value of ON resistance measured at identical V_{CC} and temperature.

1.6

1.2


0.8

0.4

R_{ON} (Ω) 001aag564

V_I (V)

10.3 ON resistance test circuit and graphs



0 1 2

(2) $V_{CC} = 1.8 \text{ V}.$ (3) $V_{CC} = 2.5 \text{ V}.$

(1) $V_{CC} = 1.5 \text{ V}.$

(4) $V_{CC} = 2.7 \text{ V}.$

(5) $V_{CC} = 3.3 \text{ V}.$


(6) $V_{CC} = 4.3 \text{ V}$. Measured at $T_{amb} = 25 \,^{\circ}\text{C}$.



 $R_{ON} = V_{SW} / I_{SW}$.


Fig 7. Typical ON resistance as a function of input voltage

Low-ohmic single-pole double-throw analog switch




- (1) $T_{amb} = 125 \, ^{\circ}C$.
- (2) $T_{amb} = 85 \, ^{\circ}C$.
- (3) $T_{amb} = 25 \, ^{\circ}C$.
- (4) $T_{amb} = -40 \, ^{\circ}C$.

Fig 8. ON resistance as a function of input voltage; $V_{CC} = 1.5 \text{ V}$




- (1) $T_{amb} = 125 \, ^{\circ}C$.
- (2) $T_{amb} = 85 \, ^{\circ}C$.
- (3) $T_{amb} = 25 \, ^{\circ}C$.
- (4) $T_{amb} = -40 \, ^{\circ}C$.

Fig 9. ON resistance as a function of input voltage; $V_{CC} = 1.8 \text{ V}$



- (1) $T_{amb} = 125 \, ^{\circ}C$.
- (2) $T_{amb} = 85 \, ^{\circ}C$.
- (3) $T_{amb} = 25 \, ^{\circ}C$.
- (4) $T_{amb} = -40 \, ^{\circ}C$.


Fig 10. ON resistance as a function of input voltage; $V_{CC} = 2.5 \text{ V}$



- (1) $T_{amb} = 125 \, ^{\circ}C$.
- (2) $T_{amb} = 85 \, ^{\circ}C$.
- (3) $T_{amb} = 25 \, ^{\circ}C$.
- (4) $T_{amb} = -40 \, ^{\circ}C$.


Fig 11. ON resistance as a function of input voltage; $V_{CC} = 2.7 \text{ V}$

Low-ohmic single-pole double-throw analog switch



- (1) $T_{amb} = 125 \, ^{\circ}C$.
- (2) $T_{amb} = 85 \, ^{\circ}C$.
- (3) $T_{amb} = 25 \, ^{\circ}C$.
- (4) $T_{amb} = -40 \, ^{\circ}C$.

Fig 12. ON resistance as a function of input voltage; $V_{CC} = 3.3 \text{ V}$



- (1) $T_{amb} = 125 \, ^{\circ}C$.
- (2) $T_{amb} = 85 \, ^{\circ}C$.
- (3) $T_{amb} = 25 \, ^{\circ}C$.
- (4) $T_{amb} = -40 \, ^{\circ}C$.

Fig 13. ON resistance as a function of input voltage; $V_{CC} = 4.3 \text{ V}$

11. Dynamic characteristics

Table 9. Dynamic characteristics

At recommended operating conditions; voltages are referenced to GND (ground = 0 V); for load circuit see Figure 16.

Symbol	Parameter	Conditions		25 °C		-40	°C to +12	5 °C	Unit
			Min	Typ[1]	Max	Min	Max (85 °C)	Max (125 °C)	
t _{en}	enable time	S to Z or Yn; see Figure 14							
		V _{CC} = 1.4 V to 1.6 V	-	50	90	-	120	120	ns
		V _{CC} = 1.65 V to 1.95 V	-	36	70	-	80	90	ns
		$V_{CC} = 2.3 \text{ V to } 2.7 \text{ V}$	-	24	45	-	50	55	ns
		V _{CC} = 2.7 V to 3.6 V	-	22	40	-	45	50	ns
		V _{CC} = 3.6 V to 4.3 V	-	22	40	-	45	50	ns
t _{dis}	disable time	S to Z or Yn; see Figure 14							
		V _{CC} = 1.4 V to 1.6 V	-	32	70	-	80	90	ns
		V _{CC} = 1.65 V to 1.95 V	-	20	55	-	60	65	ns
		V _{CC} = 2.3 V to 2.7 V	-	12	25	-	30	35	ns
		V _{CC} = 2.7 V to 3.6 V	-	10	20	-	25	30	ns
		V _{CC} = 3.6 V to 4.3 V	-	10	20	-	25	30	ns

Low-ohmic single-pole double-throw analog switch

Table 9. Dynamic characteristics ...continued

At recommended operating conditions; voltages are referenced to GND (ground = 0 V); for load circuit see Figure 16.

Symbol	Parameter	Conditions		25 °C		-40	°C to +12	5 °C	Unit
			Min	Typ[1]	Max	Min	Max (85 °C)	Max (125 °C)	
t _{b-m}	break-before-make	see Figure 15	l						
	time	V _{CC} = 1.4 V to 1.6 V	-	19	-	9	-	-	ns
		V _{CC} = 1.65 V to 1.95 V	-	17	-	7	-	-	ns
		V _{CC} = 2.3 V to 2.7 V	-	13	-	4	-	-	ns
		V _{CC} = 2.7 V to 3.6 V	-	10	-	3	-	-	ns
		V _{CC} = 3.6 V to 4.3 V	-	10	-	2	-	-	ns

^[1] Typical values are measured at $T_{amb} = 25$ °C and $V_{CC} = 1.5$ V, 1.8 V, 2.5 V, 3.3 V and 4.3 V respectively.

11.1 Waveform and test circuits





Table 10. Measurement points

Supply voltage	Input	Output
Vcc	V _M	V _X
1.4 V to 4.3 V	0.5V _{CC}	0.9V _{OH}

^[2] Break-before-make guaranteed by design.

Low-ohmic single-pole double-throw analog switch






Table 11. Test data

Fig 16. Load circuit for switching times

Supply voltage	Input		Load		
V _{CC}	VI	t _r , t _f	CL	R _L	
1.4 V to 4.3 V	V _{CC}	≤ 2.5 ns	35 pF	50 Ω	

11.2 Additional dynamic characteristics


Table 12. Additional dynamic characteristics

At recommended operating conditions; voltages are referenced to GND (ground = 0 V); $V_I = \text{GND}$ or V_{CC} (unless otherwise specified); $t_r = t_f \le 2.5$ ns; $T_{amb} = 25$ °C.


Symbol	Parameter	Conditions		Min	Тур	Max	Unit
THD total harmonic distortion	total harmonic	f_i = 20 Hz to 20 kHz; R_L = 32 Ω ; see Figure 17	[1]				
	distortion	V _{CC} = 1.4 V; V _I = 1 V (p-p)		-	0.15	-	%
	V _{CC} = 1.65 V; V _I = 1.2 V (p-p)		-	0.10	-	%	
	V _{CC} = 2.3 V; V _I = 1.5 V (p-p)		-	0.02	-	%	
		$V_{CC} = 2.7 \text{ V}; V_{I} = 2 \text{ V (p-p)}$		-	0.02	-	%
	$V_{CC} = 4.3 \text{ V}; V_{I} = 2 \text{ V (p-p)}$		-	0.02	-	%	
f _(-3dB)	-3 dB frequency	$R_L = 50 \Omega$; see Figure 18	[1]				
response	response	V _{CC} = 1.4 V to 4.3 V		-	60	-	MHz
α_{iso} isolation (OFF-state)	$f_i = 100 \text{ kHz}$; $R_L = 50 \Omega$; see Figure 19	[1]					
		V _{CC} = 1.4 V to 4.3 V		-	-90	-	dB
V _{ct} crosstalk voltage	between digital inputs and switch; $f_i = 1 \text{ MHz}$; $C_L = 50 \text{ pF}$; $R_L = 50 \Omega$; see Figure 20						
		V _{CC} = 1.4 V to 3.6 V		-	0.2	-	V
	V _{CC} = 3.6 V to 4.3 V		-	0.3	-	V	
Q _{inj} charge injection	f_i = 1 MHz; C_L = 0.1 nF; R_L = 1 M Ω ; V_{gen} = 0 V; R_{gen} = 0 Ω ; see Figure 21						
		V _{CC} = 1.5 V		-	3	-	рС
		V _{CC} = 1.8 V		-	4	-	рС
		V _{CC} = 2.5 V		-	6	-	рС
		V _{CC} = 3.3 V		-	9	-	рС
		V _{CC} = 4.3 V		-	15	-	рС

^[1] f_i is biased at $0.5V_{CC}$.

11.3 Test circuits



Low-ohmic single-pole double-throw analog switch



Adjust f_i voltage to obtain 0 dBm level at output. Increase f_i frequency until dB meter reads -3 dB.

Fig 18. Test circuit for measuring the frequency response when channel is in ON-state






Fig 19. Test circuit for measuring isolation (OFF-state)

Low-ohmic single-pole double-throw analog switch




15 of 21

Low-ohmic single-pole double-throw analog switch



a. Test circuit



b. Input and output pulse definitions

Definition: $Q_{inj} = \Delta V_O \times C_L$.

 ΔV_{O} = output voltage variation.

R_{gen} = generator resistance.

 V_{gen} = generator voltage.

Fig 21. Test circuit for measuring charge injection

12. Package outline




Fig 22. Package outline SOT886 (XSON6)

NX3L1T5157

Low-ohmic single-pole double-throw analog switch

13. Abbreviations

Table 13. Abbreviations

Acronym	Description
CDM	Charged Device Model
CMOS	Complementary Metal-Oxide Semiconductor
ESD	ElectroStatic Discharge
НВМ	Human Body Model
MM	Machine Model
PDA	Personal Digital Assistant

14. Revision history

Table 14. Revision history

Document ID	Release date	Data sheet status	Change notice	Supersedes
NX3L1T5157 v.6.2	20191203	Product data sheet	-	NX3L1T5157 v.6.1
Modifications:		DT886 requiring SSB addedssembly/Test Transfer from		
NX3L1T5157 v.6.1	20161130	Product data sheet	-	NX3L1T5157 v.6
Modifications:	Added <u>Sect</u>	ion 13 "Packing information	<u>""</u>	<u>'</u>
NX3L1T5157 v.6	20111108	Product data sheet	-	NX3L1T5157 v.5
Modifications:	Legal pages	updated.	<u>'</u>	<u>'</u>
NX3L1T5157 v.5	20110728	Product data sheet	-	NX3L1T5157 v.4
NX3L1T5157 v.4	20100324	Product data sheet	-	NX3L1T5157 v.3
NX3L1T5157 v.3	20100208	Product data sheet	-	NX3L1T5157 v.2
NX3L1T5157 v.2	20090417	Product data sheet	-	NX3L1T5157 v.1
NX3L1T5157 v.1	20080916	Product data sheet	-	-

Low-ohmic single-pole double-throw analog switch

15. Legal information

15.1 Data sheet status

Document status[1][2]	Product status[3]	Definition
Objective [short] data sheet	Development	This document contains data from the objective specification for product development.
Preliminary [short] data sheet	Qualification	This document contains data from the preliminary specification.
Product [short] data sheet	Production	This document contains the product specification.

- [1] Please consult the most recently issued document before initiating or completing a design.
- [2] The term 'short data sheet' is explained in section "Definitions".
- [3] The product status of device(s) described in this document may have changed since this document was published and may differ in case of multiple devices. The latest product status information is available on the Internet at URL http://www.nxp.com.

15.2 Definitions

Draft — The document is a draft version only. The content is still under internal review and subject to formal approval, which may result in modifications or additions. NXP Semiconductors does not give any representations or warranties as to the accuracy or completeness of information included herein and shall have no liability for the consequences of use of such information.

Short data sheet — A short data sheet is an extract from a full data sheet with the same product type number(s) and title. A short data sheet is intended for quick reference only and should not be relied upon to contain detailed and full information. For detailed and full information see the relevant full data sheet, which is available on request via the local NXP Semiconductors sales office. In case of any inconsistency or conflict with the short data sheet, the full data sheet shall prevail.

Product specification — The information and data provided in a Product data sheet shall define the specification of the product as agreed between NXP Semiconductors and its customer, unless NXP Semiconductors and customer have explicitly agreed otherwise in writing. In no event however, shall an agreement be valid in which the NXP Semiconductors product is deemed to offer functions and qualities beyond those described in the Product data sheet.

15.3 Disclaimers

Limited warranty and liability — Information in this document is believed to be accurate and reliable. However, NXP Semiconductors does not give any representations or warranties, expressed or implied, as to the accuracy or completeness of such information and shall have no liability for the consequences of use of such information. NXP Semiconductors takes no responsibility for the content in this document if provided by an information source outside of NXP Semiconductors.

In no event shall NXP Semiconductors be liable for any indirect, incidental, punitive, special or consequential damages (including - without limitation - lost profits, lost savings, business interruption, costs related to the removal or replacement of any products or rework charges) whether or not such damages are based on tort (including negligence), warranty, breach of contract or any other legal theory.

Notwithstanding any damages that customer might incur for any reason whatsoever, NXP Semiconductors' aggregate and cumulative liability towards customer for the products described herein shall be limited in accordance with the *Terms and conditions of commercial sale* of NXP Semiconductors.

Right to make changes — NXP Semiconductors reserves the right to make changes to information published in this document, including without limitation specifications and product descriptions, at any time and without notice. This document supersedes and replaces all information supplied prior to the publication hereof.

Suitability for use — NXP Semiconductors products are not designed, authorized or warranted to be suitable for use in life support, life-critical or safety-critical systems or equipment, nor in applications where failure or malfunction of an NXP Semiconductors product can reasonably be expected to result in personal injury, death or severe property or environmental damage. NXP Semiconductors and its suppliers accept no liability for inclusion and/or use of NXP Semiconductors products in such equipment or applications and therefore such inclusion and/or use is at the customer's own risk.

Applications — Applications that are described herein for any of these products are for illustrative purposes only. NXP Semiconductors makes no representation or warranty that such applications will be suitable for the specified use without further testing or modification.

Customers are responsible for the design and operation of their applications and products using NXP Semiconductors products, and NXP Semiconductors accepts no liability for any assistance with applications or customer product design. It is customer's sole responsibility to determine whether the NXP Semiconductors product is suitable and fit for the customer's applications and products planned, as well as for the planned application and use of customer's third party customer(s). Customers should provide appropriate design and operating safeguards to minimize the risks associated with their applications and products.

NXP Semiconductors does not accept any liability related to any default, damage, costs or problem which is based on any weakness or default in the customer's applications or products, or the application or use by customer's third party customer(s). Customer is responsible for doing all necessary testing for the customer's applications and products using NXP Semiconductors products in order to avoid a default of the applications and the products or of the application or use by customer's third party customer(s). NXP does not accept any liability in this respect.

Limiting values — Stress above one or more limiting values (as defined in the Absolute Maximum Ratings System of IEC 60134) will cause permanent damage to the device. Limiting values are stress ratings only and (proper) operation of the device at these or any other conditions above those given in the Recommended operating conditions section (if present) or the Characteristics sections of this document is not warranted. Constant or repeated exposure to limiting values will permanently and irreversibly affect the quality and reliability of the device.

Terms and conditions of commercial sale — NXP Semiconductors products are sold subject to the general terms and conditions of commercial sale, as published at http://www.nxp.com/profile/terms, unless otherwise agreed in a valid written individual agreement. In case an individual agreement is concluded only the terms and conditions of the respective agreement shall apply. NXP Semiconductors hereby expressly objects to applying the customer's general terms and conditions with regard to the purchase of NXP Semiconductors products by customer.

No offer to sell or license — Nothing in this document may be interpreted or construed as an offer to sell products that is open for acceptance or the grant, conveyance or implication of any license under any copyrights, patents or other industrial or intellectual property rights.

Low-ohmic single-pole double-throw analog switch

Export control — This document as well as the item(s) described herein may be subject to export control regulations. Export might require a prior authorization from competent authorities.

Non-automotive qualified products — Unless this data sheet expressly states that this specific NXP Semiconductors product is automotive qualified, the product is not suitable for automotive use. It is neither qualified nor tested in accordance with automotive testing or application requirements. NXP Semiconductors accepts no liability for inclusion and/or use of non-automotive qualified products in automotive equipment or applications.

In the event that customer uses the product for design-in and use in automotive applications to automotive specifications and standards, customer (a) shall use the product without NXP Semiconductors' warranty of the

product for such automotive applications, use and specifications, and (b) whenever customer uses the product for automotive applications beyond NXP Semiconductors' specifications such use shall be solely at customer's own risk, and (c) customer fully indemnifies NXP Semiconductors for any liability, damages or failed product claims resulting from customer design and use of the product for automotive applications beyond NXP Semiconductors' standard warranty and NXP Semiconductors' product specifications.

15.4 Trademarks

Notice: All referenced brands, product names, service names and trademarks are the property of their respective owners.

16. Contact information

For more information, please visit: http://www.nxp.com

For sales office addresses, please send an email to: salesaddresses@nxp.com

NXP Semiconductors

NX3L1T5157

Low-ohmic single-pole double-throw analog switch

17. Contents

1	General description
2	Features and benefits
3	Applications
4	Ordering information
4.1	Ordering options
5	Functional diagram
6	Pinning information 3
6.1	Pinning
6.2	Pin description
7	Functional description 3
8	Limiting values 4
9	Recommended operating conditions 4
10	Static characteristics 5
10.1	Test circuits
10.2	ON resistance6
10.3	ON resistance test circuit and graphs 8
11	Dynamic characteristics 10
11.1	Waveform and test circuits 11
11.2	Additional dynamic characteristics 13
11.3	Test circuits
12	Package outline
13	Abbreviations 18
14	Revision history 18
15	Legal information
15.1	Data sheet status
15.2	Definitions
15.3	Disclaimers
15.4	Trademarks
16	Contact information 20
17	Contents 21

Please be aware that important notices concerning this document and the product(s) described herein, have been included in section 'Legal information'.