PCA9306

Dual bidirectional I²C-bus and SMBus voltage-level translator

Rev. 9.5 — 31 August 2023

Product data sheet



1 General description

The PCA9306 is a dual bidirectional I²C-bus and SMBus voltage-level translator with an enable (EN) input, and is operational from 1.0 V to 3.6 V ($V_{ref(1)}$) and 1.8 V to 5.5 V ($V_{bias(ref)(2)}$).

The PCA9306 allows bidirectional voltage translations between 1.0 V and 5 V without the use of a direction pin. The low ON-state resistance (R_{on}) of the switch allows connections to be made with minimal propagation delay. When EN is HIGH, the translator switch is on, and the SCL1 and SDA1 I/O are connected to the SCL2 and SDA2 I/O, respectively, allowing bidirectional data flow between ports. When EN is LOW, the translator switch is off, and a high-impedance state exists between ports.

The PCA9306 is not a bus buffer like the PCA9509 or PCA9517A that provide both level translation and physically isolate the capacitance to either side of the bus when both sides are connected. The PCA9306 only isolates both sides when the device is disabled and provides voltage level translation when active.

The PCA9306 can also be used to run two buses, one at 400 kHz operating frequency and the other at 100 kHz operating frequency. If the two buses are operating at different frequencies, the 100 kHz bus must be isolated when the 400 kHz operation of the other bus is required. If the controller is running at 400 kHz, the maximum system operating frequency may be less than 400 kHz because of the delays added by the translator.

As with the standard I^2 C-bus system, pull-up resistors are required to provide the logic HIGH levels on the translator's bus. The PCA9306 has a standard open-collector configuration of the I^2 C-bus. The size of these pull-up resistors depends on the system, but each side of the translator must have a pull-up resistor. The device is designed to work with Standard-mode, Fast-mode and Fast-mode Plus I^2 C-bus devices in addition to SMBus devices. The maximum frequency is dependent on the RC time constant, but generally supports > 2 MHz.

When the SDA1 or SDA2 port is LOW, the clamp is in the ON-state and a low resistance connection exists between the SDA1 and SDA2 ports. Assuming the higher voltage is on the SDA2 port when the SDA2 port is HIGH, the voltage on the SDA1 port is limited to the voltage set by VREF1. When the SDA1 port is HIGH, the SDA2 port is pulled to the drain pull-up supply voltage $(V_{pu(D)})$ by the pull-up resistors. This functionality allows a seamless translation between higher and lower voltages selected by the user without the need for directional control. The SCL1/SCL2 channel also functions as the SDA1/SDA2 channel.

All channels have the same electrical characteristics and there is minimal deviation from one output to another in voltage or propagation delay. This is a benefit over discrete transistor voltage translation solutions, since the fabrication of the switch is symmetrical. The translator provides excellent ESD protection to lower voltage devices, and at the same time protects less ESD-resistant devices.

2 Features and benefits

- 2-bit bidirectional translator for SDA and SCL lines in mixed-mode I²C-bus applications
- Standard-mode, Fast-mode, and Fast-mode Plus I²C-bus and SMBus compatible



- Less than 1.5 ns maximum propagation delay to accommodate Standard-mode and Fast-mode I²C-bus devices and multiple controllers
- Allows voltage level translation between:
 - 1.0 V V_{ref(1)} and 1.8 V, 2.5 V, 3.3 V or 5 V V_{bias(ref)(2)}
 - 1.2 V V_{ref(1)} and 1.8 V, 2.5 V, 3.3 V or 5 V V_{bias(ref)(2)}
 - 1.8 V V_{ref(1)} and 3.3 V or 5 V V_{bias(ref)(2)}
 - 2.5 V $V_{ref(1)}$ and 5 V $V_{bias(ref)(2)}$
 - 3.3 V $V_{ref(1)}$ and 5 V $V_{bias(ref)(2)}$
- Provides bidirectional voltage translation with no direction pin
- \bullet Low 3.5 Ω ON-state connection between input and output ports provides less signal distortion
- Open-drain I²C-bus I/O ports (SCL1, SDA1, SCL2 and SDA2)
- 5 V tolerant I²C-bus I/O ports to support mixed-mode signal operation
- High-impedance SCL1, SDA1, SCL2 and SDA2 pins for EN = LOW
- · Lock-up free operation
- · Flow through pinout for ease of printed-circuit board trace routing
- ESD protection exceeds 2000 V HBM per JESD22-A114 and 1000 V CDM per JESD22-C101
- Packages offered: SO8, TSSOP8, VSSOP8, XQFN8, XSON8, X2SON8

Dual bidirectional I²C-bus and SMBus voltage-level translator

3 Ordering information

Table 1. Ordering information

Type number	Topside	Package								
	mark	Name	Description	Version						
PCA9306D	PCA9306	SO8	plastic small outline package; 8 leads; body width 3.9 mm	SOT96-1						
PCA9306DC1 ^[1]	P06	VSSOP8	plastic very thin shrink small outline package; 8 leads; body width 2.3 mm	SOT765-1						
PCA9306DC1/DG ^[2]	P06	VSSOP8	plastic very thin shrink small outline package; 8 leads; body width 2.3 mm	SOT765-1						
PCA9306DP	306P	TSSOP8 ^[3]	plastic thin shrink small outline package; 8 leads; body width 3 mm	SOT505-1						
PCA9306DP1 ^[4]	306T	TSSOP8	plastic thin shrink small outline package; 8 leads; body width 3 mm; lead length 0.5 mm	SOT505-2						
PCA9306GF ^[5]	06	XSON8	extremely thin small outline package; no leads; 8 terminals; body 1.35 x 1 x 0.5 mm	SOT1089						
PCA9306JK	06	X2SON8	extremely thin small outline package; no leads; 8 terminals; body 1.35 x 1 x 0.32 mm	SOT2015-1						
PCA9306GM	P6X ^[6]	XQFN8	plastic extremely thin quad flat package; no leads; 8 terminals; body 1.6 x 1.6 x 0.5 mm	SOT902-2						

- [1] Same footprint and pinout as the Texas Instruments PCA9306DCU. VSSOP8 transfers to ASEN in dark green refer to PCN202103046A.
- PCA9306DC1/DG is functionally the same (electrically and mechanically) as the PCA9306DC1 and the Texas Instruments PCA9306DCU. It is produced in dark green (lead-free and halogen/antimony-free) package material, with a unique orderable part number for customers who desire to order and only receive dark green package material.
- [3] Also known as MSOP8.
- [4] Same footprint and pinout as the Texas Instruments PCA9306DCT.
- [5] PCA9306GF will be phased out and replaced by PCA9306JK with package version SOT2015-1.
- [6] 'X' will change based on date code.

3.1 Ordering options

Table 2. Ordering options

Type number	Orderable part number	Package	Packing method	Minimum order quantity	Temperature
PCA9306D	PCA9306D,118	SO8	Reel 13" Q1/T1 *standard mark SMD	2500	T _{amb} = -40 °C to +105 °C
PCA9306DC1	PCA9306DC1,125 ^[1]	VSSOP8	Reel 7" Q3/T4 *standard mark	3000	T _{amb} = -40 °C to +105 °C
	PCA9306DC1Z	VSSOP8	Reel 7" Q3/T4 *standard mark SSB [2]	3000	T _{amb} = -40 °C to +105 °C
PCA9306DC1/DG	PCA9306DC1/DG,125 ^[1]	VSSOP8	Reel 7" Q3/T4 *standard mark	3000	T _{amb} = -40 °C to +105 °C
PCA9306DP	PCA9306DP,118	TSSOP8	Reel 13" Q1/T1 *standard mark SMD	2500	T _{amb} = -40 °C to +105 °C
PCA9306DP1	PCA9306DP1,125	TSSOP8	Reel 7" Q3/T4 *standard mark	3000	T _{amb} = -40 °C to +105 °C
PCA9306GF	PCA9306GF,115	XSON8	Reel 7" Q1/T1 *standard mark SMD	5000	T _{amb} = -40 °C to +105 °C
PCA9306JK	PCA9306JKZ	X2SON8	Reel 7" Q1/T1	6000	T_{amb} = -40 °C to +105 °C

PCA9306

All information provided in this document is subject to legal disclaimers.

© 2023 NXP B.V. All rights reserved.


Dual bidirectional I²C-bus and SMBus voltage-level translator

Table 2. Ordering options...continued

Type number	Orderable part number	Package	3	Packing method Minimum Temper order quantity	
			*standard mark		
PCA9306GM	PCA9306GM,125	XQFN8	Reel 7" Q3/T4 *standard mark	4000	T _{amb} = -40 °C to +105 °C


- [1] Discontinuation notice 202108009DN move to PCA9306DC1Z.
- [2] This packing method uses a Static Shielding Bag (SSB) solution. Material should be kept in the sealed bag between uses.

4 Functional diagram




5 Pinning information

5.1 Pinning



Dual bidirectional I²C-bus and SMBus voltage-level translator



5.2 Pin description

Table 3. Pin description

Symbol	Pin	Description
	SO8, TSSOP8 (MSOP8), TSSOP8, VSSOP8 (DC1), XQFN8, XSON8, X2SON8	
GND	1	ground (0 V)
VREF1	2	low-voltage side reference supply voltage for SCL1 and SDA1
SCL1	3	serial clock, low-voltage side; connect to VREF1 through a pull-up resistor
SDA1	4	serial data, low-voltage side; connect to VREF1 through a pull-up resistor
SDA2	5	serial data, high-voltage side; connect to VREF2 through a pull-up resistor
SCL2	6	serial clock, high-voltage side; connect to VREF2 through a pull-up resistor
VREF2	7	high-voltage side reference supply voltage for SCL2 and SDA2
EN	8	switch enable input; connect to VREF2 and pull-up through a high resistor

6 Functional description

Refer to Figure 1.

6.1 Function table

Table 4. Function selection (example)

H = HIGH level; L = LOW level.

Input EN ^[1]	Function
Н	SCL1 = SCL2; SDA1 = SDA2

PCA9306

All information provided in this document is subject to legal disclaimers.

© 2023 NXP B.V. All rights reserved.

Dual bidirectional I²C-bus and SMBus voltage-level translator

Table 4. Function selection (example)...continued

H = HIGH level; L = LOW level.

Input EN ^[1]	Function
L	disconnect

[1] EN is controlled by the V_{bias(ref)(2)} logic levels and should be at least 1 V higher than V_{ref(1)} for best translator operation.

7 Limiting values

Table 5. Limiting values

In accordance with the Absolute Maximum Rating System (IEC 60134).

Over operating free-air temperature range.

Symbol	Parameter	Conditions	Min	Max	Unit
V _{ref(1)}	reference voltage (1)		-0.5	+6	V
V _{bias(ref)(2)}	reference bias voltage (2)		-0.5	+6	V
VI	input voltage		-0.5 ^[1]	+6	V
V _{I/O}	voltage on an input/output pin		-0.5 ^[1]	+6	V
I _{ch}	channel current (DC)		-	128	mA
I _{IK}	input clamping current	V _I < 0 V	-	-50	mA
T _{stg}	storage temperature		-65	+150	°C

^[1] The input and input/output negative voltage ratings may be exceeded if the input and input/output clamp current ratings are observed.

8 Recommended operating conditions

Table 6. Operating conditions

Symbol	Parameter	Conditions	Min	Max	Unit
V _{I/O}	voltage on an input/output pin	SCL1, SDA1, SCL2, SDA2	0	5	V
V _{ref(1)} ^[1]	reference voltage (1)	VREF1	0	5	V
V _{bias(ref)(2)} ^[1]	reference bias voltage (2)	VREF2	0	5	V
V _{I(EN)}	input voltage on pin EN		0	5	V
I _{sw(pass)}	pass switch current		-	64	mA
T _{amb}	ambient temperature	operating in free-air	-40	+105	°C

^[1] $V_{ref(1)} \le V_{bias(ref)(2)} - 1 V$ for best results in level shifting applications.

9 Static characteristics

Table 7. Static characteristics

 T_{amb} = -40 °C to +105 °C, unless otherwise specified.

Symbol	Parameter	Conditions		Min	Typ ^[1]	Max	Unit
V _{IK}	input clamping voltage	I _I = -18 mA; V _{I(EN)} = 0 V		-	-	-1.2	V
I _{IH}	HIGH-level input current	$V_{I} = 5 \text{ V}; V_{I(EN)} = 0 \text{ V}$		-	-	5	μΑ

PCA9306

All information provided in this document is subject to legal disclaimers.

© 2023 NXP B.V. All rights reserved.

Dual bidirectional I²C-bus and SMBus voltage-level translator

Table 7. Static characteristics...continued

 T_{amb} = -40 °C to +105 °C, unless otherwise specified.

Symbol	Parameter	Conditions		Min	Typ ^[1]	Max	Unit
C _{i(EN)}	input capacitance on pin EN	V _I = 3 V or 0 V		-	7.1	-	pF
C _{io(off)}	off-state input/output capacitance	SCLn, SDAn; V _O = 3 V or 0 V; V _{I(EN)} = 0 V			4	6	pF
C _{io(on)}	on-state input/output capacitance	SCLn, SDAn; V _O = 3 V or 0 V; V _{I(EN)} = 3 V	V or 0 - 9.3		12.5	pF	
R _{on}	ON-state resistance ^[2]	SCLn, SDAn; V _I = 0 V; I _O = 64 mA	[3]		,	'	-
		V _{I(EN)} = 4.5 V		-	2.4	5.0	Ω
		V _{I(EN)} = 3 V		-	3.0	6.0	Ω
		V _{I(EN)} = 2.3 V		-	3.8	8.0	Ω
		V _{I(EN)} = 1.5 V		-	15	32	Ω
		V _{I(EN)} = 1.5 V	[4]	-	32	80	Ω
		V _I = 2.4 V; I _O = 15 mA			'	'	
		V _{I(EN)} = 4.5 V		-	4.8	7.5	Ω
		V _{I(EN)} = 3 V		-	46	80	Ω
		V _I = 1.7 V; I _O = 15 mA			'		
		V _{I(EN)} = 2.3 V		-	40	80	Ω

Dynamic characteristics

Table 8. Dynamic characteristics (translating down)

 T_{amb} = -40 °C to +105 °C, unless otherwise specified. Values guaranteed by design.

Symbol	Parameter	Conditions	C _L = 5		50 pF	C _L = 3	30 pF	C _L =	15 pF	Unit
				Min	Max	Min	Max	Min	Max	
V _{I(EN)} = 3.	/ _{I(EN)} = 3.3 V; V _{IH} = 3.3 V; V _{IL} = 0 V; V _M = 1.15 V (see <u>Figure 8</u>)									
t _{PLH}	LOW to HIGH propagation delay	from (input) SCL2 or SDA2 to (output) SCL1 or SDA1		0	2.0	0	1.2	0	0.6	ns
t _{PHL}	HIGH to LOW propagation delay	from (input) SCL2 or SDA2 to (output) SCL1 or SDA1		0	2.0	0	1.5	0	0.75	ns
V _{I(EN)} = 2.	5 V; V _{IH} = 2.5 V; V _{IL} =	= 0 V; V _M = 0.75 V (see <u>Figure</u>	<u>8</u>)							
t _{PLH}	LOW to HIGH propagation delay	from (input) SCL2 or SDA2 to (output) SCL1 or SDA1		0	2.0	0	1.2	0	0.6	ns
t _{PHL}	HIGH to LOW propagation delay	from (input) SCL2 or SDA2 to (output) SCL1 or SDA1		0	2.5	0	1.5	0	0.75	ns

All typical values are at T_{amb} = 25 °C. Measured by the voltage drop between the SCL1 and SCL2, or SDA1 and SDA2 terminals at the indicated current through the switch. ON-state resistance [2] is determined by the lowest voltage of the two terminals.


Guaranteed by design.
For DC, DC1 (VSSOP8) and GD1 (XSON8U) packages only.

Dual bidirectional I²C-bus and SMBus voltage-level translator

Table 9. Dynamic characteristics (translating up)

 T_{amb} = -40 °C to +105 °C, unless otherwise specified. Values guaranteed by design.

Symbol	Parameter	Conditions		C _L = 50 pF		C _L = 3	30 pF	C _L = '	15 pF	Unit
				Min	Max	Min	Max	Min	Max	
V _{I(EN)} = 3.	$V_{I(EN)}$ = 3.3 V; V_{IH} = 2.3 V; V_{IL} = 0 V; V_{TT} = 3.3 V; V_{M} = 1.15 V; R_{L} = 300 Ω (see <u>Figure 8</u>)									
t _{PLH}	LOW to HIGH propagation delay	from (input) SCL1 or SDA1 to (output) SCL2 or SDA2		0	1.75	0	1.0	0	0.5	ns
t _{PHL}	HIGH to LOW propagation delay	from (input) SCL1 or SDA1 to (output) SCL2 or SDA2		0	2.75	0	1.65	0	0.8	ns
V _{I(EN)} = 2.	5 V; V _{IH} = 1.5 V; V _{IL} =	0 V; V _{TT} = 2.5 V; V _M = 0.75 V	/; R _L	= 300 Ω	(see Fig	<u>ure 8</u>)				
t _{PLH}	LOW to HIGH propagation delay	from (input) SCL1 or SDA1 to (output) SCL2 or SDA2		0	1.75	0	1.0	0	0.5	ns
t _{PHL}	HIGH to LOW propagation delay	from (input) SCL1 or SDA1 to (output) SCL2 or SDA2		0	3.3	0	2.0	0	1.0	ns



S1 = translating up; S2 = translating down.

 C_L includes probe and jig capacitance.


All input pulses are supplied by generators having the following characteristics: PRR \leq 10 MHz; Z_o = 50 Ω ; $t_r \leq$ 2 ns; $t_f \leq$ 2 ns.

The outputs are measured one at a time, with one transition per measurement.

Figure 8. Load circuit for outputs


Dual bidirectional I²C-bus and SMBus voltage-level translator

11 Application information



translator operation.

Figure 9. Typical application circuit (switch always enabled)



1. In the Enabled mode, the applied enable voltage and the applied voltage at $V_{ref(1)}$ should be such that $V_{bias(ref)(2)}$ is at least 1 V higher than $V_{ref(1)}$ for best translator operation.

Figure 10. Typical application circuit (switch enable control)

11.1 Bidirectional translation

For the bidirectional clamping configuration (higher voltage to lower voltage or lower voltage to higher voltage), the EN input must be connected to VREF2 and both pins pulled to HIGH side $V_{pu(D)}$ through a pull-up resistor (typically 200 k Ω). This allows VREF2 to regulate the EN input. A filter capacitor on VREF2 is recommended. The I²C-bus controller output can be totem pole or open-drain (pull-up resistors may be required) and the I²C-

PCA9306

Dual bidirectional I²C-bus and SMBus voltage-level translator

bus device output can be totem pole or open-drain (pull-up resistors are required to pull the SCL2 and SDA2 outputs to $V_{pu(D)}$). However, if either output is totem pole, data must be unidirectional or the outputs must be 3-stateable and be controlled by some direction-control mechanism to prevent HIGH-to-LOW contentions in either direction. If both outputs are open-drain, no direction control is needed.

The reference supply voltage ($V_{ref(1)}$) is connected to the processor core power supply voltage. When VREF2 is connected through a 200 k Ω resistor to a 3.3 V to 5.5 V $V_{pu(D)}$ power supply, and $V_{ref(1)}$ is set between 1.0 V and ($V_{pu(D)}$ - 1 V), the output of each SCL1 and SDA1 has a maximum output voltage equal to VREF1, and the output of each SCL2 and SDA2 has a maximum output voltage equal to $V_{pu(D)}$.

Table 10. Application operating conditions *Refer to Figure* 9.

Symbol	Parameter	Conditions	Min	Typ ^[1]	Max	Unit
V _{bias(ref)(2)}	reference bias voltage (2)		V _{ref(1)} + 0.6	2.1	5	V
V _{I(EN)}	input voltage on pin EN		V _{ref(1)} + 0.6	2.1	5	V
V _{ref(1)}	reference voltage (1)		0	1.5	4.4	V
I _{sw(pass)}	pass switch current		-	14	-	mA
I _{ref}	reference current	transistor	-	5	-	μA
T _{amb}	ambient temperature	operating in free-air	-40	-	+105	°C

^[1] All typical values are at T_{amb} = 25 °C.

11.2 How to size pull-up resistor value

Sizing the pull-up resistor on an open-drain bus is specific to the individual application and is dependent on the following driver characteristics:

- · The driver sink current
- The V_{OL} of driver
- The V_{IL} of the driver
- · Frequency of operation

The following tables can be used to estimate the pull-up resistor value in different use cases so that the minimum resistance for the pull-up resistor can be found.

Table 11, Table 12 and Table 13 contain suggested minimum values of pull-up resistors for the PCA9306 and NVT20xx devices with typical voltage translation levels and drive currents. The calculated values assume that both drive currents are the same. $V_{OL} = V_{IL} = 0.1 \times V_{CC}$ and accounts for a ±5 % V_{CC} tolerance of the supplies, ±1 % resistor values. It should be noted that the resistor chosen in the final application should be equal to or larger than the values shown in Table 11, Table 12 and Table 13 to ensure that the pass voltage is less than 10 % of the V_{CC} voltage, and the external driver should be able to sink the total current from both pull-up resistors. When selecting the minimum resistor value in Table 11, Table 12 or Table 13, the drive current strength that should be chosen should be the lowest drive current seen in the application and account for any drive strength current scaling with output voltage. For the GTL devices, the resistance table should be recalculated to account for the difference in ON resistance and bias voltage limitations between $V_{CC(B)}$ and $V_{CC(A)}$.

Table 11. Pull-up resistor minimum values, 3 mA driver sink current for PCA9306 and NVT20xx

	A-side	B-side								
		1.2 V	1.5 V	1.8 V	2.5 V	3.3 V	5.0 V			
Ī	1.0 V	R _{pu(A)} = 750 Ω	R _{pu(A)} = 845 Ω	R _{pu(A)} = 976 Ω	R _{pu(A)} = none	R _{pu(A)} = none	R _{pu(A)} = none			

PCA9306

Dual bidirectional I²C-bus and SMBus voltage-level translator

Table 11. Pull-up resistor minimum values, 3 mA driver sink current for PCA9306 and NVT20xx...continued

A-side	B-side					
	1.2 V	1.5 V	1.8 V	2.5 V	3.3 V	5.0 V
	$R_{pu(B)} = 750 \Omega$	$R_{pu(B)} = 845 \Omega$	$R_{pu(B)} = 976 \Omega$	$R_{pu(B)} = 887 \Omega$	$R_{pu(B)} = 1.18 \text{ k}\Omega$	$R_{pu(B)} = 1.82 \text{ k}\Omega$
1.2 V		$R_{pu(A)} = 931 \Omega$ $R_{pu(B)} = 931 \Omega$	$R_{pu(A)} = 1.02 \text{ k}\Omega$ $R_{pu(B)} = 1.02 \text{ k}\Omega$	$R_{pu(A)}$ = none $R_{pu(B)}$ = 887 Ω	$R_{pu(A)}$ = none $R_{pu(B)}$ = 1.18 k Ω	$R_{pu(A)}$ = none $R_{pu(B)}$ = 1.82 k Ω
1.5 V			$R_{pu(A)} = 1.1 \text{ k}\Omega$ $R_{pu(B)} = 1.1 \text{ k}\Omega$	$R_{pu(A)}$ = none $R_{pu(B)}$ = 866 Ω	$R_{pu(A)}$ = none $R_{pu(B)}$ = 1.18 k Ω	$R_{pu(A)}$ = none $R_{pu(B)}$ = 1.78 kΩ
1.8 V				$R_{pu(A)}$ = 1.47 kΩ $R_{pu(B)}$ = 1.47 kΩ	$R_{pu(A)}$ = none $R_{pu(B)}$ = 1.15 k Ω	$R_{pu(A)}$ = none $R_{pu(B)}$ = 1.78 k Ω
2.5 V					$R_{pu(A)}$ = 1.96 kΩ $R_{pu(B)}$ = 1.96 kΩ	$R_{pu(A)}$ = none $R_{pu(B)}$ = 1.78 k Ω
3.3 V						$R_{pu(A)}$ = none $R_{pu(B)}$ = 1.74 k Ω

Table 12. Pull-up resistor minimum values, 10 mA driver sink current for PCA9306 and NVT20xx

A-side	-	B-side						
	1.2 V	1.5 V	1.8 V	2.5 V	3.3 V	5.0 V		
1.0 V	$R_{pu(A)} = 221 \Omega$ $R_{pu(B)} = 221 \Omega$	$R_{pu(A)} = 255 \Omega$ $R_{pu(B)} = 255 \Omega$	$R_{pu(A)} = 287 \Omega$ $R_{pu(B)} = 287 \Omega$	$R_{pu(A)}$ = none $R_{pu(B)}$ = 267 Ω	$R_{pu(A)}$ = none $R_{pu(B)}$ = 357 Ω	$R_{pu(A)}$ = none $R_{pu(B)}$ = 549 Ω		
1.2 V		$R_{pu(A)} = 274 \Omega$ $R_{pu(B)} = 274 \Omega$	$R_{pu(A)} = 309 \Omega$ $R_{pu(B)} = 309 \Omega$	$R_{pu(A)}$ = none $R_{pu(B)}$ = 267 Ω	$R_{pu(A)}$ = none $R_{pu(B)}$ = 357 Ω	$R_{pu(A)}$ = none $R_{pu(B)}$ = 549 Ω		
1.5 V			$R_{pu(A)} = 332 \Omega$ $R_{pu(B)} = 332 \Omega$	$R_{pu(A)}$ = none $R_{pu(B)}$ = 261 Ω	$R_{pu(A)}$ = none $R_{pu(B)}$ = 348 Ω	$R_{pu(A)}$ = none $R_{pu(B)}$ = 536 Ω		
1.8 V				$R_{pu(A)} = 442 \Omega$ $R_{pu(B)} = 442 \Omega$	$R_{pu(A)}$ = none $R_{pu(B)}$ = 348 Ω	$R_{pu(A)}$ = none $R_{pu(B)}$ = 536 Ω		
2.5 V					$R_{pu(A)} = 590 \Omega$ $R_{pu(B)} = 590 \Omega$	$R_{pu(A)}$ = none $R_{pu(B)}$ = 523 Ω		
3.3 V						$R_{pu(A)}$ = none $R_{pu(B)}$ = 523 Ω		

Table 13. Pull-up resistor minimum values, 15 mA driver sink current for PCA9306 and NVT20xx

able 13. Full-up resistor minimum values, 15 mA univer sink current for FCA9306 and NV120XX								
A-side		B-side						
	1.2 V	1.5 V	1.8 V	2.5 V	3.3 V	5.0 V		
1.0 V	$R_{pu(A)}$ = 147 Ω $R_{pu(B)}$ = 147 Ω	$R_{pu(A)} = 169 \Omega$ $R_{pu(B)} = 169 \Omega$	$R_{pu(A)} = 191 \Omega$ $R_{pu(B)} = 191 \Omega$	$R_{pu(A)}$ = none $R_{pu(B)}$ = 178 Ω	$R_{pu(A)}$ = none $R_{pu(B)}$ = 237 Ω	$R_{pu(A)}$ = none $R_{pu(B)}$ = 365 Ω		
1.2 V	F-(-)	$R_{pu(A)} = 182 \Omega$ $R_{pu(B)} = 182 \Omega$	$R_{pu(A)} = 205 \Omega$ $R_{pu(B)} = 205 \Omega$	$R_{pu(A)} = \text{none}$ $R_{pu(B)} = 178 \Omega$	$R_{pu(A)} = \text{none}$ $R_{pu(B)} = 237 \Omega$	$R_{pu(A)} = \text{none}$ $R_{pu(B)} = 365 \Omega$		
1.5 V			$R_{pu(A)} = 221 \Omega$ $R_{pu(B)} = 221 \Omega$	$R_{pu(A)}$ = none $R_{pu(B)}$ = 174 Ω	$R_{pu(A)}$ = none $R_{pu(B)}$ = 232 Ω	$R_{pu(A)}$ = none $R_{pu(B)}$ = 357 Ω		
1.8 V				R _{pu(A)} = 294 Ω	R _{pu(A)} = none	R _{pu(A)} = none		

PCA9306

All information provided in this document is subject to legal disclaimers.

© 2023 NXP B.V. All rights reserved.

Dual bidirectional I²C-bus and SMBus voltage-level translator

10010 10. 1	Table 10. I all apreciotes infillinating values, 10 mix arrest clink carrent for 1 07,0000 and 14 12000commuca									
A-side		B-side								
	1.2 V 1.5 V 1.8 V 2.5 V 3.3 V 5									
				$R_{pu(B)} = 294 \Omega$	$R_{pu(B)} = 232 \Omega$	$R_{pu(B)} = 357 \Omega$				
2.5 V					$R_{pu(A)} = 392 \Omega$	$R_{pu(A)}$ = none				
					$R_{pu(B)} = 392 \Omega$	$R_{pu(B)} = 357 \Omega$				


Table 13. Pull-up resistor minimum values, 15 mA driver sink current for PCA9306 and NVT20xx...continued

11.3 How to design for maximum frequency operation

The maximum frequency is limited by the minimum pulse width LOW and HIGH as well as rise time and fall time. See Equation 1 as an example of the maximum frequency. The rise and fall times are shown in Figure 11.

$$f_{max} = \frac{1}{t_{LOW(min)} + t_{HIGH(min)} + t_{r(actual)} + t_{f(actual)}}$$
(1)

3.3 V



The rise and fall times are dependent upon translation voltages, the drive strength, the total node capacitance (C_{L(tot)}) and the pull-up resistors (R_{PU}) that are present on the bus. The node capacitance is the addition of the PCB trace capacitance and the device capacitance that exists on the bus. Because of the dependency of the external components, PCB layout and the different device operating states the calculation of rise and fall times is complex and has several inflection points along the curve.

The main component of the rise and fall times is the RC time constant of the bus line when the device is in its two primary operating states: when device is in the ON state and it is low-impedance, the other is when the device is OFF isolating the A-side from the B-side.

A description of the fall time applied to either An or Bn output going from HIGH to LOW is as follows. Whichever side is asserted first, the B-side down must discharge to the V_{CC(A)} voltage. The time is determined by the pullup resistor, pull-down driver strength and the capacitance. As the level moves below the V_{CC(A)} voltage, the channel resistance drops so that both A and B sides equal. The capacitance on both sides is connected to form the total capacitance and the pull-up resistors on both sides combine to the parallel equivalent resistance. The Ron of the device is small compared to the pull-up resistor values, so its effect on the pull-up resistance can be neglected and the fall is determined by the driver pulling the combined capacitance and pull-up resistor currents. An estimation of the actual fall time seen by the device is equal to the time it takes for the B-side to fall to the $V_{CC(A)}$ voltage and the time it takes for both sides to fall from the $V_{CC(A)}$ voltage to the V_{IL} level.

A description of the rise time applied to either An or Bn output going from LOW to HIGH is as follows. When the signal level is LOW, the Ron is at its minimum, so the A and B sides are essentially one node. They will rise together with an RC time constant that is the sum of all the capacitance from both sides and the parallel of the resistance from both sides. As the signal approaches the V_{CC(A)} voltage, the channel resistance goes up and the waveforms separate, with the B side finishing its rise with the RC time constant of the B side. The rise to $V_{CC(A)}$ is essentially the same for both sides.

There are some basic guidelines to follow that will help maximize the performance of the device:

 $R_{pu(A)}$ = none $R_{pu(B)} = 348 \Omega$


Dual bidirectional I²C-bus and SMBus voltage-level translator

- Keep trace length to a minimum by placing the NVT device close to the processor.
- The signal round trip time on trace should be shorter than the rise or fall time of signal to reduce reflections.
- The faster the edge of the signal, the higher the chance for ringing.
- The higher drive strength controlled by the pull-up resistor (up to 15 mA), the higher the frequency the device can use.

The system designer must design the pull-up resistor value based on external current drive strength and limit the node capacitance (minimize the wire, stub, connector and trace length) to get the desired operation frequency result.

Dual bidirectional I²C-bus and SMBus voltage-level translator

12 Package outline



Notes

- 1. Plastic or metal protrusions of 0.15 mm (0.006 inch) maximum per side are not included.
- 2. Plastic or metal protrusions of 0.25 mm (0.01 inch) maximum per side are not included.

OUTLINE VERSION		REFER	ENCES	EUROPEAN	ISSUE DATE
	IEC	JEDEC	JEITA	PROJECTION	ISSUE DATE
SOT96-1	076E03	MS-012			99-12-27 03-02-18

Figure 12. Package outline SOT96-1 (SO8)

PCA9306

All information provided in this document is subject to legal disclaimers.

© 2023 NXP B.V. All rights reserved.




Figure 13. Package outline SOT505-1 (TSSOP8)






Figure 14. Package outline SOT505-2 (TSSOP8)


Dual bidirectional I²C-bus and SMBus voltage-level translator




PCA9306




Dual bidirectional I²C-bus and SMBus voltage-level translator




PCA9306



Dual bidirectional I²C-bus and SMBus voltage-level translator



PCA9306



Dual bidirectional I²C-bus and SMBus voltage-level translator

13 Soldering of SMD packages

This text provides a very brief insight into a complex technology. A more in-depth account of soldering ICs can be found in Application Note *AN10365 "Surface mount reflow soldering description"*.

13.1 Introduction to soldering

Soldering is one of the most common methods through which packages are attached to Printed Circuit Boards (PCBs), to form electrical circuits. The soldered joint provides both the mechanical and the electrical connection. There is no single soldering method that is ideal for all IC packages. Wave soldering is often preferred when through-hole and Surface Mount Devices (SMDs) are mixed on one printed wiring board; however, it is not suitable for fine pitch SMDs. Reflow soldering is ideal for the small pitches and high densities that come with increased miniaturization.

13.2 Wave and reflow soldering

Wave soldering is a joining technology in which the joints are made by solder coming from a standing wave of liquid solder. The wave soldering process is suitable for the following:

- Through-hole components
- · Leaded or leadless SMDs, which are glued to the surface of the printed circuit board

Not all SMDs can be wave soldered. Packages with solder balls, and some leadless packages which have solder lands underneath the body, cannot be wave soldered. Also, leaded SMDs with leads having a pitch smaller than ~0.6 mm cannot be wave soldered, due to an increased probability of bridging.

The reflow soldering process involves applying solder paste to a board, followed by component placement and exposure to a temperature profile. Leaded packages, packages with solder balls, and leadless packages are all reflow solderable.

Key characteristics in both wave and reflow soldering are:

- · Board specifications, including the board finish, solder masks and vias
- · Package footprints, including solder thieves and orientation
- · The moisture sensitivity level of the packages
- Package placement
- · Inspection and repair
- · Lead-free soldering versus SnPb soldering

13.3 Wave soldering

Key characteristics in wave soldering are:

- Process issues, such as application of adhesive and flux, clinching of leads, board transport, the solder wave parameters, and the time during which components are exposed to the wave
- Solder bath specifications, including temperature and impurities

13.4 Reflow soldering

Key characteristics in reflow soldering are:

- Lead-free versus SnPb soldering; note that a lead-free reflow process usually leads to higher minimum peak temperatures (see Figure 21) than a SnPb process, thus reducing the process window
- Solder paste printing issues including smearing, release, and adjusting the process window for a mix of large and small components on one board

PCA9306

All information provided in this document is subject to legal disclaimers.

© 2023 NXP B.V. All rights reserved.

Dual bidirectional I²C-bus and SMBus voltage-level translator

Reflow temperature profile; this profile includes preheat, reflow (in which the board is heated to the peak
temperature) and cooling down. It is imperative that the peak temperature is high enough for the solder to
make reliable solder joints (a solder paste characteristic). In addition, the peak temperature must be low
enough that the packages and/or boards are not damaged. The peak temperature of the package depends on
package thickness and volume and is classified in accordance with <u>Table 14</u> and <u>Table 15</u>

Table 14. SnPb eutectic process (from J-STD-020D)


Package thickness (mm)	Package reflow temperature (°C)	ackage reflow temperature (°C)					
	Volume (mm³)	lume (mm³)					
	< 350	≥ 350					
< 2.5	235	220					
≥ 2.5	220	220					

Table 15. Lead-free process (from J-STD-020D)

Package thickness (mm)	Package reflow temperature	Package reflow temperature (°C)					
	Volume (mm³)	olume (mm³)					
	< 350 350 to 2000 > 2000						
< 1.6	260	260	260				
1.6 to 2.5	260	250	245				
> 2.5	250	245	245				

Moisture sensitivity precautions, as indicated on the packing, must be respected at all times.

Studies have shown that small packages reach higher temperatures during reflow soldering, see Figure 21.





For further information on temperature profiles, refer to Application Note AN10365 "Surface mount reflow soldering description".


PCA9306


Dual bidirectional I²C-bus and SMBus voltage-level translator

14 Soldering: PCB footprints













PCA9306




PCA9306







Dual bidirectional I²C-bus and SMBus voltage-level translator




PCB DESIGN GUIDELINES - SOLDER MASK OPENING PATTERN

THIS SHEET SERVES ONLY AS A GUIDELINE TO HELP DEVELOP A USER SPECIFIC SOLUTION. DEVELOPMENT EFFORT WILL STILL BE REQUIRED BY END USERS TO OPTIMIZE PCB MOUNTING PROCESSES AND BOARD DESIGN IN ORDER TO MEET INDIVIDUAL/SPECIFIC REQUIREMENTS.

© NXP B.V.	ALL RIGHTS RESERVED		DATE: 1	1 JUN 20	219_
MECHANICAL OUTLINE	STANDARD:	DRAWING NUMBER:	REVISION:		
PRINT VERSION NOT TO SCALE	MO-287	98ASA01419D	А		

Figure 30. PCB footprint for SOT2015-1 (X2SON8); reflow soldering (1 of 3)

Dual bidirectional I²C-bus and SMBus voltage-level translator




PCB DESIGN GUIDELINES - I/O PADS AND SOLDERABLE AREA

THIS SHEET SERVES ONLY AS A GUIDELINE TO HELP DEVELOP A USER SPECIFIC SOLUTION. DEVELOPMENT EFFORT WILL STILL BE REQUIRED BY END USERS TO OPTIMIZE PCB MOUNTING PROCESSES AND BOARD DESIGN IN ORDER TO MEET INDIVIDUAL/SPECIFIC REQUIREMENTS.

© NXP B.V.	ALL RIGHTS RESERVED		DATE: 1	1 JUN 2019
MECHANICAL OUTLINE	STANDARD:	DRAWING NUMBER:	REVISION:	
PRINT VERSION NOT TO SCALE	MO-287	98ASA01419D	А	

Figure 31. PCB footprint for SOT2015-1 (X2SON8); reflow soldering (2 of 3)

Dual bidirectional I²C-bus and SMBus voltage-level translator



RECOMMENDED STENCIL THICKNESS 0.1

PCB DESIGN GUIDELINES - SOLDER PASTE STENCIL

THIS SHEET SERVES ONLY AS A GUIDELINE TO HELP DEVELOP A USER SPECIFIC SOLUTION. DEVELOPMENT EFFORT WILL STILL BE REQUIRED BY END USERS TO OPTIMIZE PCB MOUNTING PROCESSES AND BOARD DESIGN IN ORDER TO MEET INDIVIDUAL/SPECIFIC REQUIREMENTS.

© NXP B.V.	ALL RIGHTS RESERVED		DATE: 1	1 JUN	2019
MECHANICAL OUTLINE	STANDARD:	DRAWING NUMBER:	REVISION:		
PRINT VERSION NOT TO SCALE	MO-287	98ASA01419D	Α		

Figure 32. PCB footprint for SOT2015-1 (X2SON8); reflow soldering (3 of 3)

Dual bidirectional I²C-bus and SMBus voltage-level translator

NOTES:

- 1. ALL DIMENSIONS ARE IN MILLIMETERS.
- 2. DIMENSIONING AND TOLERANCING PER ASME Y14.5M-1994.

/3.\ PIN 1 FEATURE SHAPE, SIZE AND LOCATION MAY VARY.

4. COPLANARITY APPLIES TO LEADS.

5. MIN METAL GAP SHOULD BE 0.15 MM.

© NXP B.V. ALL RIGHTS RESERVED

DATE: 11 JUN 2019

MECHANICAL OUTLINE	STANDARD:	DRAWING NUMBER:	REVISION:	
PRINT VERSION NOT TO SCALE	MO-287	98ASA01419D	А	

Figure 33. PCB footprint for SOT2015-1 (X2SON8); notes

Dual bidirectional I²C-bus and SMBus voltage-level translator

15 Abbreviations

Table 16. Abbreviations

Table 10. Abbreviations			
Acronym	Description		
CDM	Charged-Device Model		
ESD	ElectroStatic Discharge		
GTL	Gunning Transceiver Logic		
НВМ	Human Body Model		
I ² C-bus	Inter-Integrated Circuit bus		
I/O	Input/Output		
LVTTL	Low Voltage Transistor-Transistor Logic		
MIPI	(Obsolete) Mobile Industry Processor Interface		
PLL	Phase-Locked Loop		
PRR	Pulse Repetition Rate		
RC	Resistor-Capacitor network		
SMBus	System Management Bus		

16 Revision history

Table 17. Revision history

Document ID	Release date	Data sheet status	Change notice	Supersedes	
PCA9306 v9.5	20230831	Product data sheet	-	PCA9306 v.9.4	
Modifications	<u>Section 12</u> : Added <u>Figure 20</u> (height information)				
PCA9306 v9.4	20230705	Product data sheet	-	PCA9306 v.9.3	
PCA9306 v9.3	20221114	Product data sheet	-	PCA9306 v.9.2	
PCA9306 v9.2	20221025	Product data sheet	-	PCA9306 v.9.1	
PCA9306 v9.1	20210831	Product data sheet	PCN202103046A	PCA9306 v.9	
PCA9306 v.9	20191206	Product data sheet	201912004I	PCA9306 v.8	
PCA9306 v.8	20140122	Product data sheet	-	PCA9306 v.7	
PCA9306 v.7	20130517	Product data sheet	-	PCA9306 v.6	
PCA9306 v.6	20101125	Product data sheet	-	PCA9306 v.5	
PCA9306 v.5	20100319	Product data sheet	-	PCA9306 v.4	
PCA9306 v.4	20091026	Product data sheet	-	PCA9306 v.3	
PCA9306 v.3	20080804	Product data sheet	-	PCA9306 v.2	
PCA9306 v.2	20070221	Product data sheet	-	PCA9306 v.1	
PCA9306 v.1	20061020	Product data sheet	-	-	

Dual bidirectional I²C-bus and SMBus voltage-level translator

17 Legal information

17.1 Data sheet status

Document status ^{[1][2]}	Product status ^[3]	Definition
Objective [short] data sheet	Development	This document contains data from the objective specification for product development.
Preliminary [short] data sheet	Qualification	This document contains data from the preliminary specification.
Product [short] data sheet	Production	This document contains the product specification.

- [1] Please consult the most recently issued document before initiating or completing a design.
- [2] The term 'short data sheet' is explained in section "Definitions".
- [3] The product status of device(s) described in this document may have changed since this document was published and may differ in case of multiple devices. The latest product status information is available on the Internet at URL https://www.nxp.com.

17.2 Definitions

Draft — A draft status on a document indicates that the content is still under internal review and subject to formal approval, which may result in modifications or additions. NXP Semiconductors does not give any representations or warranties as to the accuracy or completeness of information included in a draft version of a document and shall have no liability for the consequences of use of such information.

Short data sheet — A short data sheet is an extract from a full data sheet with the same product type number(s) and title. A short data sheet is intended for quick reference only and should not be relied upon to contain detailed and full information. For detailed and full information see the relevant full data sheet, which is available on request via the local NXP Semiconductors sales office. In case of any inconsistency or conflict with the short data sheet, the full data sheet shall prevail.

Product specification — The information and data provided in a Product data sheet shall define the specification of the product as agreed between NXP Semiconductors and its customer, unless NXP Semiconductors and customer have explicitly agreed otherwise in writing. In no event however, shall an agreement be valid in which the NXP Semiconductors product is deemed to offer functions and qualities beyond those described in the Product data sheet

17.3 Disclaimers

17.4 Trademarks

Notice: All referenced brands, product names, service names, and trademarks are the property of their respective owners.

NXP — wordmark and logo are trademarks of NXP B.V.

Dual bidirectional I²C-bus and SMBus voltage-level translator

Tables

Tab. 1. Tab. 2. Tab. 3.	Ordering information Ordering options Pin description	3	Tab. 12.	Pull-up resistor minimum values, 10 mA driver sink current for PCA9306 and NVT20xx	11
Tab. 4. Tab. 5. Tab. 6.	Function selection (example) Limiting values Operating conditions	5 6	Tab. 13.	Pull-up resistor minimum values, 15 mA driver sink current for PCA9306 and NVT20xx	
Tab. 7.	Static characteristics		Tab. 14.	SnPb eutectic process (from J-STD-020D) .	
Tab. 8.	Dynamic characteristics (translating down)		Tab. 15.	Lead-free process (from J-STD-020D)	
Tab. 9.	Dynamic characteristics (translating up)		Tab. 16.	Abbreviations	
Tab. 10.	Application operating conditions		Tab. 17.	Revision history	
Tab. 11.	Pull-up resistor minimum values, 3 mA			,, ,	
	driver sink current for PCA9306 and				
	NVT20xx	.10			
Figur	es				
Fig. 1.	Logic diagram of PCA9306 (positive logic)	4	Fig. 21.	Temperature profiles for large and small	
Fig. 2.	Pin configuration for TSSOP8 (DP1)		1 ig. 2 i.	components	24
Fig. 3.	Pin configuration for TSSOP8 (DP)		Fig. 22.	PCB footprint for SOT96-1 (SO8); reflow	
g. 0.	(MSOP8)	4	· ·g· ==·	soldering	25
Fig. 4.	Pin configuration for VSSOP8 (DC1; DC1/		Fig. 23.	PCB footprint for SOT96-1 (SO8); wave	
	DG)	4	g	soldering	25
Fig. 5.	Pin configuration for SO8	4	Fig. 24.	PCB footprint for SOT505-1 (TSSOP8);	
Fig. 6.	Pin configuration for XQFN8		J	reflow soldering	26
Fig. 7.	Pin configuration for XSON8 and X2SON8		Fig. 25.	PCB footprint for SOT505-2 (TSSOP8);	
•	(GF; JK)	5	· ·	reflow soldering	27
Fig. 8.	Load circuit for outputs	8	Fig. 26.	PCB footprint for SOT765-1 (VSSOP8);	
Fig. 9.	Typical application circuit (switch always			reflow soldering	28
	enabled)	9	Fig. 27.	PCB footprint for SOT1089 (XSON8);	
Fig. 10.	Typical application circuit (switch enable			reflow soldering	29
	control)	9	Fig. 28.	PCB footprint for SOT996-2 (XSON8U);	
Fig. 11.	An example waveform for maximum			reflow soldering	30
	frequency		Fig. 29.	PCB footprint for SOT902-2 (XQFN8);	
Fig. 12.	Package outline SOT96-1 (SO8)			reflow soldering	31
Fig. 13.	Package outline SOT505-1 (TSSOP8)		Fig. 30.	PCB footprint for SOT2015-1 (X2SON8);	
Fig. 14.	Package outline SOT505-2 (TSSOP8)			reflow soldering (1 of 3)	32
Fig. 15.	Package outline SOT765-1 (VSSOP8)		Fig. 31.	PCB footprint for SOT2015-1 (X2SON8);	
Fig. 16.	Package outline SOT902-2 (XQFN8)			reflow soldering (2 of 3)	33
Fig. 17.	Package outline SOT1089 (XSON8)		Fig. 32.	PCB footprint for SOT2015-1 (X2SON8);	
Fig. 18.	Package outline SOT996-2 (XSON8U)	. 20		reflow soldering (3 of 3)	34
Fig. 19.	Package outline SOT2015-1 (X2SON8) 1		Fig. 33.	PCB footprint for SOT2015-1 (X2SON8);	
	of 2	. 21		notes	35
Fig. 20.	Package outline SOT2015-1 (X2SON8) 2				
	of 2	. 22			

Dual bidirectional I²C-bus and SMBus voltage-level translator

Contents

1	General description	1
2	Features and benefits	1
3	Ordering information	3
3.1	Ordering options	3
4	Functional diagram	4
5	Pinning information	4
5.1	Pinning	4
5.2	Pin description	5
6	Functional description	5
6.1	Function table	
7	Limiting values	е
8	Recommended operating conditions	6
9	Static characteristics	6
10	Dynamic characteristics	7
11	Application information	9
11.1	Bidirectional translation	9
11.2	How to size pull-up resistor value	10
11.3	How to design for maximum frequency	
	operation	12
12	Package outline	
13	Soldering of SMD packages	23
13.1	Introduction to soldering	23
13.2	Wave and reflow soldering	23
13.3	Wave soldering	23
13.4	Reflow soldering	23
14	Soldering: PCB footprints	
15	Abbreviations	36
16	Revision history	36
17	Legal information	

Please be aware that important notices concerning this document and the product(s) described herein, have been included in section 'Legal information'.