INTEGRATED CIRCUITS



Preliminary data

2002 Mar 07

IC28 Data Handbook



ENERAL DESCRIPTION	
N CONFIGURATION, 14-PIN TSSOP AND 14-PIN DIP PACKAGES	
JGIC SYMBOL	
LOCK DIAGRAM	
N DESCRIPTIONS	
PECIAL FUNCTION REGISTERS	
JNCTIONAL DESCRIPTION	
Enhanced CPU	
Analog Functions	
Analog Comparators	
Comparator Configuration	
Internal Reference Voltage	
Comparator Interrupt	
Comparators and Power Reduction Modes	
Comparator Configuration Example	
I ² C Serial Interface	
I ² C Interrupts	
Reading I2CON	
Checking ATN and DRDY	
Pegarding Transmit Active	
I/O PORs	
Push-Pull Output Configuration	
Keyboard Interrupt (KBI)	
Oscillator	
Low Frequency Oscillator Option	
Medium Frequency Oscillator Option	
High Frequency Oscillator Option	
On-Chip RC Oscillator Option	
External Clock Input Option	
Clock Output	
CPU Clock Modification: CLKR and DIVM	
Power Monitoring Functions	
Brownout Detection	
Power On Detection	
Power Reduction Modes	
Idle Mode	
Power Down Mode	
Low Voltage EPROM Operation	
Reset	
Timer/Counters	
Mode 0	
Mode 1	
NIOde U	

Mode 1	31
Mode 2	31
Mode 3	31
Serial Port Control Register (SCON)	31
Baud Rates	32
Using Timer 1 to Generate Baud Rates	32
More About UART Mode 0	34
More About UART Mode 1	34
More About UART Modes 2 and 3	37
Multiprocessor Communications	37
Automatic Address Recognition	40
Watchdog Timer	40
Watchdog Feed Sequence	40
Watchdog Reset	41
Additional Features	42
Software Reset	42
Dual Data Pointers	42
EPROM Characteristics	43
32-Byte Customer Code Space	43
System Configuration Bytes	43
Security Bits	44
ABSOLUTE MAXIMUM RATINGS	45
DC ELECTRICAL CHARACTERISTICS	46
COMPARATOR ELECTRICAL CHARACTERISTICS	47
AC ELECTRICAL CHARACTERISTICS	47
REVISION HISTORY	52

P87LPC760



GENERAL DESCRIPTION

The P87LPC760 is a 14-pin single-chip microcontroller designed for low pin count applications demanding high-integration, low cost solutions over a wide range of performance requirements. A member of the Philips low pin count family, the P87LPC760 offers programmable oscillator configurations for high and low speed crystals or RC operation, wide operating voltage range, programmable port output configurations, selectable Schmitt trigger inputs, LED drive outputs, and a built-in watchdog timer. The P87LPC760 is based on an accelerated 80C51 processor architecture that executes instructions at twice the rate of standard 80C51 devices.

FEATURES

- An accelerated 80C51 CPU provides instruction cycle times of 300–600 ns for all instructions except multiply and divide when executing at 20 MHz. Execution at up to 20 MHz when V_{DD} = 4.5 V to 6.0 V, 10 MHz when V_{DD} = 2.7 V to 6.0 V
- 2.7 V to 6.0 V operating range for digital functions
- 1 kbyte EPROM code memory
- 128 byte RAM data memory
- 32 byte customer code EPROM allows serialization of devices, storage of setup parameters, etc
- Two 16-bit counter/timers. One timer may be configured to toggle a port output upon timer overflow
- One analog comparator
- Full duplex UART
- I²C communication port

- Four keypad interrupt inputs, plus one additional external interrupt input
 Four interrupt priority levels
- Watchdog timer with separate on-chip oscillator, requiring no external components. The watchdog timeout time is selectable from 8 values
- Active low reset. On-chip power-on reset allows operation with no external reset components
- Low voltage reset. One of two preset low voltage levels may be selected to allow a graceful system shutdown when power fails. May optionally be configured as an interrupt
- Oscillator Fail Detect. The watchdog timer has a separate fully on-chip oscillator, allowing it to perform an oscillator fail detect function
- Configurable on-chip oscillator with frequency range and RC oscillator options (selected by user programmed EPROM bits). The RC oscillator option allows operation with no external oscillator components
- Programmable port output configuration options: quasi-bidirectional, open drain, push-pull, input-only
- Selectable Schmitt trigger port inputs
- LED drive capability (20 mA) on all port pins
- Controlled slew rate port outputs to reduce EMI. Outputs have approximately 10 ns minimum ramp times
- Nine I/O pins minimum. Up to 12 I/O pins using on-chip oscillator and reset options
- Only power and ground connections are required to operate the P87LPC760 when fully on-chip oscillator and reset options are selected
- Serial EPROM programming allows simple in-circuit production coding. Two EPROM security bits prevent reading of sensitive application programs
- Idle and Power Down reduced power modes. Improved wakeup from Power Down mode (a low interrupt input starts execution). Typical Power Down current is 1 μA
- 14-pin TSSOP and 14-pin DIP packages

ORDERING INFORMATION

Part Number	Temperature Range °C and Package	Frequency	Drawing Number
P87LPC760BDH	0 to +70, plastic thin shrink small outline pack- age; 14 leads; body width 4.4 mm	20 MHz (5 V), 10 MHz (3 V)	SOT402-1
P87LPC760BN	0 to +70, plastic dual in-line package; 14 leads (300 mil)	20 MHz (5 V), 10 MHz (3 V)	SOT27-1

P87LPC760

PIN CONFIGURATION, 14-PIN TSSOP AND 14-PIN DIP PACKAGES



LOGIC SYMBOL



BLOCK DIAGRAM





 The P87LPC760 does not support access to external data memory. However, the User Configuration Bytes are accessed via the MOV2 instruction as if they were in external data memory.

Figure 1. P87LPC760 Program and Data Memory Map

P87LPC760

PIN DESCRIPTIONS

MNEMONIC	PIN NO.	TYPE			NAME AND FUNCTION					
P0.3-P0.6	10, 12–14	I/O	Port 0: Port configured ir during reset, of port 0 pins pin is configu Electrical Ch	0 is an 4-bit I/ the quasi-bic as determine as inputs and ured independ paracteristics f	O port with a user-configurable output type. Port 0 latches are directional mode and have either ones or zeros written to them ad by the PRHI bit in the UCFG1 configuration byte. The operation d outputs depends upon the port configuration selected. Each port lently. Refer to the section on I/O port configuration and the DC or details.					
			The Keyboa	rd Interrupt fea	ature operates with port 0 pins.					
			Port 0 also p	orovides variou	us special functions as described below.					
	14	I	P0.3	CIN1B	Comparator 1 positive input B.					
	13	I	P0.4	CIN1A	Comparator 1 positive input A					
	12	I	P0.5	CMPREF	Comparator reference (negative) input.					
	10	0	P0.6	CMP1	Comparator 1 output					
P1.0–P1.3 P1.5, P1.7	1–2 6–9	I/O	Port 1: Port 1 is an 6-bit I/O port with a user-configurable output type, except for three pi as noted below. Port 1 latches are configured in the quasi-bidirectional mode and have e ther ones or zeros written to them during reset, as determined by the PRHI bit in the UCI configuration byte. The operation of the configurable port 1 pins as inputs and outputs de pends upon the port configuration selected. Each of the configurable port pins are programmed independently. Refer to the section on I/O port configuration and the DC Electric Characteristics for details.							
			Port 1 also p	provides variou	us special functions as described below.					
	9	0	P1.0	TxD	Transmitter output for the serial port.					
	8	I	P1.1	RxD	Receiver input for the serial port.					
	7	I/O	P1.2	Т0	Timer/counter 0 external count input or overflow output.					
		I/O		SCL	I ² C serial clock input/output. When configured as an output, P1.2 is open drain, in order to conform to I ² C specifications.					
	6	I	P1.3	INT0	External interrupt 0 input.					
		I/O		SDA	I^2C serial data input/output. When configured as an output, P1.3 is open drain, in order to conform to I^2C specifications.					
	2	Ι	P1.5	RST	External Reset input (if selected via EPROM configuration). A low on this pin resets the microcontroller, causing I/O ports and peripherals to take on their default states, and the processor begins execution at address 0. When used as a port pin, P1.5 is a Schmitt trigger input only.					
P2.0–P2.1	4, 5	I/O	Port 2: Port figured in the reset, as det 2 pins as inp configured in cal Characte	2 is a 2-bit I/C e quasi-bidirec ermined by th outs and outpundependently. pristics for deta	D port with a user-configurable output type. Port 2 latches are con- ctional mode and have either ones or zeros written to them during e PRHI bit in the UCFG1 configuration byte. The operation of port its depends upon the port configuration selected. Each port pin is Refer to the section on I/O port configuration and the DC Electri- ails.					
			Port 2 also p	provides variou	us special functions as described below.					
	5	0	P2.0	X2	Output from the oscillator amplifier (when a crystal oscillator option is selected via the EPROM configuration).					
				CLKOUT	CPU clock divided by 6 clock output when enabled via SFR bit and in conjunction with internal RC oscillator or external clock input.					
	4	Ι	P2.1	P2.1 X1 Input to the oscillator circuit and internal clock generato (when selected via the EPROM configuration).						
V _{SS}	3	I	Ground: 0 V reference.							
V _{DD}	11	I	Power Supp Power Dowr	bly: This is the modes.	e power supply voltage for normal operation as well as Idle and					

SPECIAL FUNCTION REGISTERS

Name	Description	SFR Address	м	Bit Functions and Addresses MSB							Reset Value
			E7	E6	E5	E4	E3	E2	E1	E0	
ACC*	Accumulator	E0h									00h
AUXR1#	Auxiliary Function Register	A2h	KBF	BOD	BOI	LPEP	SRST	0	-	DPS	02h ¹
			F7	F6	F5	F4	F3	F2	F1	F0	
В*	B register	F0h									00h
CMP1#	Comparator 1 control register	ACh	-	-	CE1	CP1	CN1	OE1	CO1	CMF1	00h ¹
DIVM#	CPU clock divide-by-M control	95h				•	•				00h
DPTR:	Data pointer (2 bytes)										
DPH	Data pointer high byte	83h									00h
DPL	Data pointer low byte	82h									00h
			CF	CE	CD	CC	СВ	CA	C9	C8	
I2CFG#*	I ² C configuration register	C8h/RD	SLAVEN	MASTRQ	0	TIRUN	-	-	CT1	CT0	00h ¹
		C8h/WR	SLAVEN	MASTRQ	CLRTI	TIRUN	-	-	CT1	CT0	
			DF	DE	DD	DC	DB	DA	D9	D8	
I2CON#*	I ² C control register	D8h/RD	RDAT	ATN	DRDY	ARL	STR	STP	MASTER	-	80h ¹
		D8h/WR	CXA	IDLE	CDR	CARL	CSTR	CSTP	XSTR	XSTP	
I2DAT#	I ² C data register	D9h/RD	RDAT	0	0	0	0	0	0	0	80h
		D9h/WR	XDAT	х	х	Х	х	х	х	х	
			AF	AE	AD	AC	AB	AA	A9	A8	
IEN0*	Interrupt enable 0	A8h	EA	EWD	EBO	ES	ET1	-	ET0	EX0	00h
			EF	EE	ED	EC	EB	EA	E9	E8	
IEN1#*	Interrupt enable 1	E8h	ETI	-	EC1	-	-	-	EKB	El2	00h ¹
			BF	BE	BD	BC	BB	BA	B9	B8	
IP0*	Interrupt priority 0	B8h	_	PWD	PBO	PS	PT1	-	PT0	PX0	00h ¹
IP0H#	Interrupt priority 0 high byte	B7h	_	PWDH	РВОН	PSH	PT1H	-	PT0H	PX0H	00h ¹
			FF	FE	FD	FC	FB	FA	F9	F8	
IP1*	Interrupt priority 1	F8h	PTI	-	PC1	-	-	-	PKB	Pl2	00h ¹
IP1H#	Interrupt priority 1 high byte	F7h	PTIH	-	PC1H	-	-	-	РКВН	PI2H	00h ¹
KBI#	Keyboard Interrupt	86h	87	86	85	84	83	82	81	80	00h
P0*	Port 0	80h	_	CMP1	CMPREF	CIN1A	CIN1B	-	-	-	Note 2
			97	96	95	94	93	92	91	90	
P1*	Port 1	90h	(P1.7)	-	RST	-	INT0	T0	RxD	TxD	Note 2
			A7	A6	A5	A4	A3	A2	A1	A0	
P2*	Port 2	A0h	-	-	-	-	-	-	X1	X2	Note 2
P0M1#	Port 0 output mode 1	84h	-	(P0M1.6)	(P0M1.5)	(P0M1.4)	(P0M1.3)	-	-	-	00h
P0M2#	Port 0 output mode 2	85h	-	(P0M2.6)	(P0M2.5)	(P0M2.4)	(P0M2.3)	-	-	-	00h
P1M1#	Port 1 output mode 1	91h	(P1M1.7)	-	-	-	-	-	(P1M1.1)	(P1M1.0)	00h ¹
P1M2#	Port 1 output mode 2	92h	(P1M2.7)	-	-	-	-	-	(P1M2.1)	(P1M2.0)	00h ¹
P2M1#	Port 2 output mode 1	A4h	P2S	P1S	P0S	ENCLK	-	T0OE	(P2M1.1)	(P2M1.0)	00h

News	Description	SFR			Bit Fu	inctions a	nd Addre	esses				
Name	Description	Address	м	SB		-	-	-	L	SB	Value	
P2M2#	Port 2 output mode 2	A5h	-	-	-	-	-	-	(P2M2.1)	(P2M2.0)	00h ¹	
PCON	Power control register	87h	SMOD1	SMOD0	BOF	POF	GF1	GF0	PD	IDL	Note 3	
			D7	D6	D5	D4	D3	D2	D1	D0	1	
PSW*	Program status word	D0h	CY	AC	F0	RS1	RS0	OV	F1	Р	00h	
PT0AD#	Port 0 digital input disable	F6h								-	00h	
			9F	9E	9D	9C	9B	9A	99	98		
SCON*	Serial port control	98h	SM0	SM1	SM2	REN	TB8	RB8	TI	RI	00h	
SBUF	Serial port data buffer register	99h									XXh	
SADDR#	Serial port address register	A9h									00h	
SADEN#	Serial port address enable	B9h									00h	
SP	Stack pointer	81h									07h	
			8F	8E	8D	8C	8B	8A	89	88		
TCON*	Timer 0 and 1 control	88h	TF1	TR1	TF0	TR0	-	-	IE0	IT0	00h	
тно	Timer 0 high byte	8Ch		•						•	00h	
TH1	Timer 1 high byte	8Dh									00h	
TL0	Timer 0 low byte	8Ah									00h	
TL1	Timer 1 low byte	8Bh									00h	
TMOD	Timer 0 and 1 mode	89h	-	-	M1	MO	GATE	C/T	M1	M0	00h	
				·		<u>^</u>				-	1	
WDCON#	Watchdog control register	A7h	_	-	WDOVF	WDRUN	WDCLK	WDS2	WDS1	WDS0	Note 4	
WDRST#	Watchdog reset register	A6h									XXh	

NOTES:

* SFRs are bit addressable.

SFRs are modified from or added to the 80C51 SFRs.

1. Unimplemented bits in SFRs are X (unknown) at all times. Ones should not be written to these bits since they may be used for other Provide the second of the secon

3. The PCON reset value is x x BOF POF-0 0 0 0b. The BOF and POF flags are not affected by reset. The POF flag is set by hardware upon

power up. The BOF flag is set by the occurrence of a brownout reset/interrupt and upon power up. The WDCON reset value is xx11 0000b for a Watchdog reset, xx01 0000b for all other reset causes if the watchdog is enabled, and xx00 0000b for all other reset causes if the watchdog is disabled. 4.

FUNCTIONAL DESCRIPTION

Details of P87LPC760 functions will be described in the following sections.

Enhanced CPU

The P87LPC760 uses an enhanced 80C51 CPU which runs at twice the speed of standard 80C51 devices. This means that the performance of the P87LPC760 running at 5 MHz is exactly the same as that of a standard 80C51 running at 10 MHz. A machine cycle consists of 6 oscillator cycles, and most instructions execute in 6 or 12 clocks. A user configurable option allows restoring standard 80C51 execution timing. In that case, a machine cycle becomes 12 oscillator cycles.

In the following sections, the term "CPU clock" is used to refer to the clock that controls internal instruction execution. This may sometimes be different from the externally applied clock, as in the case where the part is configured for standard 80C51 timing by means of the CLKR configuration bit or in the case where the clock is divided down via the setting of the DIVM register. These features are described in the Oscillator section.

Analog Functions

The P87LPC760 incorporates one Analog Comparator. In order to give the best analog function performance and to minimize power consumption, pins that are actually being used for analog functions must have the digital outputs and the digital inputs disabled.

Digital outputs are disabled by putting the port output into the Input Only (high impedance) mode as described in the I/O Ports section.

Digital inputs on port 0 may be disabled through the use of the PT0AD register. Each bit in this register corresponds to one pin of

Port 0. Setting the corresponding bit in PT0AD disables that pin's digital input. Port bits that have their digital inputs disabled will be read as 0 by any instruction that accesses the port.

Analog Comparators

An analog comparator is provided on the P87LPC760. Input and output options allow use of the comparator in a number of different configurations. Comparator operation is such that the output is a logical one (which may be read in a register and/or routed to a pin) when the positive input (one of two selectable pins) is greater than the negative input (selectable from a pin or an internal reference voltage). Otherwise the output is a zero. The comparator may be configured to cause an interrupt when the output value changes.

Comparator Configuration

The comparator has a control register, CMP1. The control register is shown in Figure 2.

The overall connections to the comparator are shown in Figure 3. There are eight possible configurations for the comparator, as determined by the control bits in the CMP1 register: CP1, CN1, and OE1. These configurations are shown in Figure 4. The comparator functions down to a V_{DD} of 3.0V.

When the comparator is first enabled, the comparator output and interrupt flag are not guaranteed to be stable for 10 microseconds. The comparator interrupt should not be enabled during that time, and the comparator interrupt flag must be cleared before the interrupt is enabled in order to prevent an immediate interrupt service.

CMP1	Addres Not Bit	s: ACh Addressable	e								Reset Value: 00h		
		_	7	6	5	4	3	2	1	0	_		
			_	_	CE1	CP1	CN1	OE1	CO1	CMF1			
	BIT	SYMBOL	FUN	CTION									
	CMP1.7, 6	_	Rese	erved for future use. Should not be set to 1 by user programs.									
	CMP1.5	CE1	Com Com	omparator enable. When set by software, the corresponding comparator function is enabled. omparator output is stable 10 microseconds after CE1 is first set.									
	CMP1.4	CP1	Com 1, Cl	parator po N1B is se	sitive inputed as	ut select. V the positiv	When 0, C ve compar	IN1A is se ator input.	elected as	s the posit	ive comparator input. When		
	CMP1.3	CN1	Com the n nega	parator ne legative co ltive comp	egative inp omparator arator inp	out select. r input. Wh ut.	When 0, t nen 1, the	the compa internal co	arator refe omparator	rence pin reference	CMPREF is selected as V _{ref} is selected as the		
	CMP1.2	OE1	Outp enab	ut enable. led (CE1	. When 1, = 1). This	the compared output is a	arator outp asynchror	out is conr lous to the	nected to CPU clo	the CMP1 ck.	pin if the comparator is		
	CMP1.1	CO1	Com comp	parator ou parator is	utput, synd disabled (chronized $CE1 = 0$).	to the CP	U clock to	allow rea	ding by so	oftware. Cleared when the		
	CMP1.0	CMF1	Com state softw	omparator interrupt flag. This bit is set by hardware whenever the comparator output CO1 changes ate. This bit will cause a hardware interrupt if enabled and of sufficient priority. Cleared by oftware and when the comparator is disabled ($CE1 = 0$).									
											SU01531		

Figure 2. Comparator Control Register (CMP1)

P87LPC760

Low power, low price, low pin count (14 pin) microcontroller with 1 kbyte OTP



Figure 3. Comparator Input and Output Connections



Figure 4. Comparator Configurations

P87LPC760

Internal Reference Voltage

An internal reference voltage generator may supply a default reference when a single comparator input pin is used. The value of the internal reference voltage, referred to as V_{ref}, is 1.23 V \pm 10%.

Comparator Interrupt

The comparator has an interrupt flag CMF1 contained in its configuration register. This flag is set whenever the comparator output changes state. The flag may be polled by software or may be used to generate an interrupt. The interrupt will be generated when the corresponding enable bit EC1 in the IEN1 register is set and the interrupt system is enabled via the EA bit in the IEN0 register.

Comparators and Power Reduction Modes

The comparator may remain enabled when Power Down or Idle mode is activated. The comparator will continue to function in the power reduction mode. If the comparator interrupt is enabled, a change of the comparator output state will generate an interrupt and wake up the processor. If the comparator output to a pin is enabled, the pin should be configured in the push-pull mode in order to obtain fast switching times while in power down mode. The reason is that with the oscillator stopped, the temporary strong pull-up that normally occurs during switching on a quasi-bidirectional port pin does not take place.

The comparator consumes power in Power Down and Idle modes, as well as in the normal operating mode. This fact should be taken into account when system power consumption is an issue.

Comparator Configuration Example

The code shown in Figure 5 is an example of initializing the comparator. If comparator 1 is configured to use the CIN1A and CMPREF inputs, outputs the comparator result to the CMP1 pin, and generates an interrupt when the comparator output changes.

The interrupt routine used for the comparator must clear the interrupt flag (CMF1 in this case) before returning.

CmpInit:		
mov	PT0AD,#30h	; Disable digital inputs on pins that are used
		; for analog functions: CIN1A, CMPREF.
anl	POM2,#0cfh	; Disable digital outputs on pins that are used
orl	P0M1,#30h	; for analog functions: CIN1A, CMPREF.
mov	CMP1,#24h	; Turn on comparator 1 and set up for:
		; - Positive input on CIN1A.
		; - Negative input from CMPREF pin.
		; - Output to CMP1 pin enabled.
call	delay10us	; The comparator has to start up for at
		; least 10 microseconds before use.
anl	CMP1,#0feh	; Clear comparator 1 interrupt flag.
setb	EC1	; Enable the comparator 1 interrupt. The
		; priority is left at the current value.
setb	EA	; Enable the interrupt system (if needed).
ret		; Return to caller.
		SU01189
	<pre>ImpInit: mov anl orl mov call anl setb setb ret</pre>	<pre>ImpInit: mov PTOAD,#30h anl POM2,#0cfh orl POM1,#30h mov CMP1,#24h call delay10us anl CMP1,#0feh setb EC1 setb EA ret</pre>

Figure 5. Example of comparator initialization code

P87LPC760

I²C Serial Interface

The I^2C bus uses two wires (SDA and SCL) to transfer information between devices connected to the bus. The main bus features are:

- Bidirectional data transfer between masters and slaves.
- Serial addressing of slaves (no added wiring).
- Acknowledgment after each transferred byte.
- Multimaster bus.
- Arbitration between simultaneously transmitting masters without corruption of serial data on bus.

The l^2C subsystem includes hardware to simplify the software required to drive the l^2C bus. The hardware is a single bit interface which in addition to including the necessary arbitration and framing error checks, includes clock stretching and a bus timeout timer. The interface is synchronized to software either through polled loops or interrupts.

Refer to the application note AN422, entitled "Using the 8XC751 Microcontroller as an I²C Bus Master" for additional discussion of the 8xC76x I²C interface and sample driver routines.

The P87LPC760 I²C implementation duplicates that of the 87C751 and 87C752 except for the following details:

- The interrupt vector addresses for both the I²C interrupt and the Timer I interrupt.
- The I²C SFR addresses (I2CON, I2CFG, I2DAT).
- The location of the I²C interrupt enable bit and the name of the SFR it is located within (EI2 is Bit 0 in IEN1).
- The location of the Timer I interrupt enable bit and the name of the SFR it is located within (ETI is Bit 7 in IEN1).
- The I²C and Timer I interrupts have a settable priority.

Timer I is used to both control the timing of the I^2C bus and also to detect a "bus locked" condition, by causing an interrupt when nothing happens on the I^2C bus for an inordinately long period of time while a transmission is in progress. If this interrupt occurs, the program has the opportunity to attempt to correct the fault and resume I^2C operation.

Six time spans are important in I²C operation and are insured by timer I:

- The MINIMUM HIGH time for SCL when this device is the master.
- The MINIMUM LOW time for SCL when this device is a master. This is not very important for a single-bit hardware interface like this one, because the SCL low time is stretched until the software responds to the I²C flags. The software response time normally meets or exceeds the MIN LO time. In cases where the software responds within MIN HI + MIN LO time, timer I will ensure that the minimum time is met.
- The MINIMUM SCL HIGH TO SDA HIGH time in a stop condition.
- The MINIMUM SDA HIGH TO SDA LOW time between I²C stop and start conditions (4.7ms, see I²C specification).
- The MINIMUM SDA LOW TO SCL LOW time in a start condition.
- The MAXIMUM SCL CHANGE time while an I²C frame is in progress. A frame is in progress between a start condition and the following stop condition. This time span serves to detect a lack of software response on this device as well as external I²C problems. SCL "stuck low" indicates a faulty master or slave. SCL

"stuck high" may mean a faulty device, or that noise induced onto the I^2C bus caused all masters to withdraw from I^2C arbitration.

The first five of these times are 4.7 ms (see I^2C specification) and are covered by the low order three bits of timer I. Timer I is clocked by the P87LPC760 CPU clock. Timer I can be pre-loaded with one of four values to optimize timing for different oscillator frequencies. At lower frequencies, software response time is increased and will degrade maximum performance of the I^2C bus. See special function register I2CFG description for prescale values (CT0, CT1).

The MAXIMUM SCL CHANGE time is important, but its exact span is not critical. The complete 10 bits of timer I are used to count out the maximum time. When I²C operation is enabled, this counter is cleared by transitions on the SCL pin. The timer does not run between I²C frames (i.e., whenever reset or stop occurred more recently than the last start). When this counter is running, it will carry out after 1020 to 1023 machine cycles have elapsed since a change on SCL. A carry out causes a hardware reset of the I²C interface and generates an interrupt if the Timer I interrupt is enabled. In cases where the bus hang-up is due to a lack of software response by this device, the reset releases SCL and allows I²C operation among other devices to continue.

Timer I is enabled to run, and will reset the I²C interface upon overflow, if the TIRUN bit in the I2CFG register is set. The Timer I interrupt may be enabled via the ETI bit in IEN1, and its priority set by the PTIH and PTI bits in the IP1H and IP1 registers respectively.

I²C Interrupts

If I²C interrupts are enabled (EA and EI2 are both set to 1), an I²C interrupt will occur whenever the ATN flag is set by a start, stop, arbitration loss, or data ready condition (refer to the description of ATN following). In practice, it is not efficient to operate the I²C interface in this fashion because the I²C interrupt service routine would somehow have to distinguish between hundreds of possible conditions. Also, since I²C can operate at a fairly high rate, the software may execute faster if the code simply waits for the I²C interface.

Typically, the l^2C interrupt should only be used to indicate a start condition at an idle slave device, or a stop condition at an idle master device (if it is waiting to use the l^2C bus). This is accomplished by enabling the l^2C interrupt only during the aforementioned conditions.

Reading I2CON

- RDAT The data from SDA is captured into "Receive DATa" whenever a rising edge occurs on SCL. RDAT is also available (with seven low-order zeros) in the I2DAT register. The difference between reading it here and there is that reading I2DAT clears DRDY, allowing the I²C to proceed on to another bit. Typically, the first seven bits of a received byte are read from I2DAT, while the 8th is read here. Then I2DAT can be written to send the Acknowledge bit and clear DRDY.
- ATN "ATteNtion" is 1 when one or more of DRDY, ARL, STR, or STP is 1. Thus, ATN comprises a single bit that can be tested to release the I²C service routine from a "wait loop."
- DRDY "Data ReaDY" (and thus ATN) is set when a rising edge occurs on SCL, except at idle slave. DRDY is cleared by writing CDR = 1, or by writing or reading the I2DAT register. The following low period on SCL is stretched until the program responds by clearing DRDY.

PX/I	PU./60

I2CON	Addres	ss: D8h									Reset Value: 81h		
	Bit Add	dressable ¹	7	6	5	4	3	2	1	0			
		READ	RDAT	ATN	DRDY	ARL	STR	STP	MASTER	_			
		WRITE	CXA	IDLE	CDR	CARL	CSTR	CSTP	XSTR	XSTP			
BI	ΙТ	SYMBOL	FUN	CTION					•		-		
120	CON.7	RDAT	Read	: the mos	t recently	received of	data bit.						
	"	CXA	Write	ite: clears the transmit active flag.									
120	CON.6	ATN	Read	ad: ATN = 1 if any of the flags DRDY, ARL, STR, or STP = 1.									
	**	IDLE	Write	/rite: in the I ² C slave mode, writing a 1 to this bit causes the I ² C hardware to ignore the bus until it sneeded again.									
120	CON.5	DRDY	Read	: Data Re	ady flag,	set when t	there is a	rising edg	e on SCL.				
	"	CDR	Write	: writing a	1 to this I	oit clears t	he DRDY	flag.					
120	CON.4	ARL	Read	: Arbitrati	on Loss fla	ag, set wh	en arbitra	tion is los	t while in the	e transmit	mode.		
	"	CARL	Write	: writing a	1 to this I	oit clears t	he CARL	flag.					
120	CON.3	STR	Read	: Start fla	g, set whe	en a start o	condition is	s detected	d at a maste	r or non-i	dle slave.		
	"	CSTR	Write	: writing a	1 to this I	oit clears t	he STR fl	ag.					
120	CON.2	STP	Read	: Stop flag	g, set whe	n a stop c	ondition is	s detected	l at a maste	r or non-io	dle slave.		
	"	CSTP	Write	: writing a	1 to this I	oit clears t	he STP fla	ag.					
120	CON.1	MASTER	Read	: indicate	s whether	this devic	e is curre	ntly as bu	s master.				
	"	XSTR	Write	: writing a	1 to this I	oit causes	a repeate	ed start co	ndition to be	e generate	ed.		
120	CON.0	_	Read	: undefine	ed.								
	"	XSTP	Write	: writing a	1 to this I	oit causes	a stop co	ndition to	be generate	ed.	SU01155		

1. Due to the manner in which bit addressing is implemented in the 80C51 family, the I2CON register should never be altered by use of the SETB, CLR, CPL, MOV (bit), or JBC instructions. This is due to the fact that read and write functions of this register are different. Testing of I2CON bits via the JB and JNB instructions is supported.

Figure 6. I²C Control Register (I2CON)

I2DAT	Addres	s: D9h									Reset Value: xxh	
	Not Bit	Addressab	ole									
		_	7	6	5	4	3	2	1	0		
		READ	RDAT	—	—	—	_	—	_	—		
		WRITE	XDAT	_	_	_	_	_	_	_		
		_									-	
	BIT	SYMBOL	. FUN	CTION								
	I2DAT.7	RDAT	Read I2DA	l: the mos T also cle	t recently ars DRDY	received	data bit, ca Transmit A	aptured fro	om SDA at e	every risin	ng edge of SCL. Reading	
	"	XDAT	Write Trans	rite: sets the data for the next transmitted bit. Writing I2DAT also clears DRDY and sets the ansmit Active state.								
	I2DAT.6-0	-	Unus	ed.							SU01156	



P87LPC760

Low power, low price, low pin count (14 pin) microcontroller with 1 kbyte OTP

Checking ATN and DRDY

When a program detects ATN = 1, it should next check DRDY. If DRDY = 1, then if it receives the last bit, it should capture the data from RDAT (in I2DAT or I2CON). Next, if the next bit is to be sent, it should be written to I2DAT. One way or another, it should clear DRDY and then return to monitoring ATN. Note that if any of ARL, STR, or STP is set, clearing DRDY will not release SCL to high, so that the I²C will not go on to the next bit. If a program detects ATN = 1, and DRDY = 0, it should go on to examine ARL, STR, and STP.

ARL "Arbitration Loss" is 1 when transmit Active was set, but this device lost arbitration to another transmitter. Transmit Active is cleared when ARL is 1. There are four separate cases in which ARL is set.

1. If the program sent a 1 or repeated start, but another device sent a 0, or a stop, so that SDA is 0 at the rising edge of SCL. (If the other device sent a stop, the setting of ARL will be followed shortly by STP being set.)

2. If the program sent a 1, but another device sent a repeated start, and it drove SDA low before SCL could be driven low. (This type of ARL is always accompanied by STR = 1.)

3. In master mode, if the program sent a repeated start, but another device sent a 1, and it drove SCL low before this device could drive SDA low.

4. In master mode, if the program sent stop, but it could not be sent because another device sent a 0.

- STR "STaRt" is set to a 1 when an I²C start condition is detected at a non-idle slave or at a master. (STR is not set when an idle slave becomes active due to a start bit; the slave has nothing useful to do until the rising edge of SCL sets DRDY.)
- STP "SToP" is set to 1 when an I²C stop condition is detected at a non-idle slave or at a master. (STP is not set for a stop condition at an idle slave.)

MASTER "MASTER" is 1 if this device is currently a master on the I²C. MASTER is set when MASTRQ is 1 and the bus is not busy (i.e., if a start bit hasn't been received since reset or a "Timer I" time-out, or if a stop has been received since the last start). MASTER is cleared when ARL is set, or after the software writes MASTRQ = 0 and then XSTP = 1.

Writing I2CON

Typically, for each bit in an I^2C message, a service routine waits for ATN = 1. Based on DRDY, ARL, STR, and STP, and on the current

bit position in the message, it may then write I2CON with one or more of the following bits, or it may read or write the I2DAT register.

CXA Writing a 1 to "Clear Xmit Active" clears the Transmit Active state. (Reading the I2DAT register also does this.)

Regarding Transmit Active

Transmit Active is set by writing the I2DAT register, or by writing I2CON with XSTR = 1 or XSTP = 1. The I²C interface will only drive the SDA line low when Transmit Active is set, and the ARL bit will only be set to 1 when Transmit Active is set. Transmit Active is cleared by reading the I2DAT register, or by writing I2CON with CXA = 1. Transmit Active is automatically cleared when ARL is 1.

- IDLE Writing 1 to "IDLE" causes a slave's I²C hardware to ignore the I²C until the next start condition (but if MASTRQ is 1, then a stop condition will cause this device to become a master).
- CDR Writing a 1 to "Clear Data Ready" clears DRDY. (Reading or writing the I2DAT register also does this.)
- CARL Writing a 1 to "Clear Arbitration Loss" clears the ARL bit.
- CSTR Writing a 1 to "Clear STaRt" clears the STR bit.
- CSTP Writing a 1 to "Clear SToP" clears the STP bit. Note that if one or more of DRDY, ARL, STR, or STP is 1, the low time of SCL is stretched until the service routine responds by clearing them.
- XSTR Writing 1s to "Xmit repeated STaRt" and CDR tells the I²C hardware to send a repeated start condition. This should only be at a master. Note that XSTR need not and should not be used to send an "initial" (non-repeated) start; it is sent automatically by the I²C hardware. Writing XSTR = 1 includes the effect of writing I2DAT with XDAT = 1; it sets Transmit Active and releases SDA to high during the SCL low time. After SCL goes high, the I²C hardware waits for the suitable minimum time and then drives SDA low to make the start condition.
- XSTP Writing 1s to "Xmit SToP" and CDR tells the I²C hardware to send a stop condition. This should only be done at a master. If there are no more messages to initiate, the service routine should clear the MASTRQ bit in I2CFG to 0 before writing XSTP with 1. Writing XSTP = 1 includes the effect of writing I2DAT with XDAT = 0; it sets Transmit Active and drives SDA low during the SCL low time. After SCL goes high, the I²C hardware waits for the suitable minimum time and then releases SDA to high to make the stop condition.

P87LPC760

Low power, low price, low pin count (14 pin) microcontroller with 1 kbyte OTP

I2CFG	Addres	s: C8h								Reset Value: 00h			
	Bit Add	ressable											
		7	6	5	4	3	2	1	0				
		SLAV	EN MASTRQ	CLRTI	TIRUN	_	_	CT1	СТ0				
									-1	1			
B	IT	SYMBOL	FUNCTION										
12	CFG.7	SLAVEN	Slave Enable. MASTRQ are (time-out.	Slave Enable. Writing a 1 this bit enables the slave functions of the I ² C subsystem. If SLAVEN and MASTRQ are 0, the I ² C hardware is disabled. This bit is cleared to 0 by reset and by an I ² C ime-out.									
12	CFG.6	MASTRQ	Master Reques progress when start condition When a maste MASTRQ is cle	t. Writing this bit is s sent an wishes t eared by a	a 1 to this changed d DRDY is o release an I ² C time	bit reque from 0 to s set (thus mastershi e-out.	ests maste 1, action is making A p status o	rship of the s delayed u ATN = 1 and f the I ² C, it	e I ² C bus. Intil a stop d generatir writes a 1	If a transmission is in condition is detected. A ng an I ² C interrupt). to XSTP in I2CON.			
12	CFG.5	CLRTI	Writing a 1 to t	nis bit clea	ars the Tin	ner I overf	flow flag.	This bit pos	ition alway	vs reads as a 0.			
12	CFG.4	TIRUN	Writing a 1 to the and MASTER,	nis bit lets this bit de	Timer I ru	in; a zero operationa	stops and al modes a	l clears it. T as shown ir	Together w n Table 1.	ith SLAVEN, MASTRQ,			
12	CFG.2, 3	—	Reserved for fu	iture use.	Should no	ot be set t	o 1 by use	er programs	6.				
12	CFG.1, 0	CT1, CT0	These two bits time of SCL wh controls both o	hese two bits are programmed as a function of the CPU clock rate, to optimize the MIN HI and LO ime of SCL when this device is a master on the I ² C. The time value determined by these bits controls both of these parameters, and also the timing for stop and start conditions.									
										SU01552			

Figure 8. I²C Configuration Register (I2CFG)

Regarding Software Response Time

Because the P87LPC760 can run at 20 MHz, and because the I^2C interface is optimized for high-speed operation, it is quite likely that an I^2C service routine will sometimes respond to DRDY (which is set at a rising edge of SCL) and write I2DAT before SCL has gone low again. If XDAT were applied directly to SDA, this situation would produce an I^2C protocol violation. The programmer need not worry about this possibility because XDAT is applied to SDA only when SCL is low.

Conversely, a program that includes an I^2C service routine may take a long time to respond to DRDY. Typically, an I^2C routine operates on a flag-polling basis during a message, with interrupts from other peripheral functions enabled. If an interrupt occurs, it will delay the response of the I^2C service routine. The programmer need not worry about this very much either, because the I^2C hardware stretches the SCL low time until the service routine responds. The only constraint on the response is that it must not exceed the Timer I time-out.

Values to be used in the CT1 and CT0 bits are shown in Table 2. To allow the I²C bus to run at the maximum rate for a particular oscillator frequency, compare the actual oscillator rate to the f OSC

max column in the table. The value for CT1 and CT0 is found in the first line of the table where CPU clock max is greater than or equal to the actual frequency.

Table 2 also shows the machine cycle count for various settings of CT1/CT0. This allows calculation of the actual minimum high and low times for SCL as follows:

SCL min high/low time in microseconds = $\frac{6 * Min Time Count}{CPU clock in MHz}$

For instance, at an 8 MHz frequency, with CT1/CT0 set to 1 0, the minimum SCL high and low times will be 5.25 $\mu s.$

Table 2 also shows the Timer I timeout period (given in machine cycles) for each CT1/CT0 combination. The timeout period varies because of the way in which minimum SCL high and low times are measured. When the l^2C interface is operating, Timer I is pre-loaded at every SCL transition with a value dependent upon CT1/CT0. The pre-load value is chosen such that a minimum SCL high or low time has elapsed when Timer I reaches a count of 008 (the actual value pre-loaded into Timer I is 8 minus the machine cycle count).

P87LPC760

Table 1. Interaction of TIRUN with SLAVEN, MASTRQ, and MASTER

SLAVEN, MASTRQ, MASTER	TIRUN	OPERATING MODE
All 0	0	The I ² C interface is disabled. Timer I is cleared and does not run. This is the state assumed after a reset. If an I ² C application wants to ignore the I ² C at certain times, it should write SLAVEN, MASTRQ, and TIRUN all to zero.
All 0	1	The I ² C interface is disabled.
Any or all 1	0	The I ² C interface is enabled. The 3 low-order bits of Timer I run for min-time generation, but the hi-order bits do not, so that there is no checking for I ² C being "hung." This configuration can be used for very slow I ² C operation.
Any or all 1	1	The I ² C interface is enabled. Timer I runs during frames on the I ² C, and is cleared by transitions on SCL, and by Start and Stop conditions. This is the normal state for I ² C operation.

Table 2. CT1, CT0 Values

СТ1, СТ0	Min Time Count (Machine Cycles)	CPU Clock Max (for 100 kHz I ² C)	Timeout Period (Machine Cycles)
1 0	7	8.4 MHz	1023
0 1	6	7.2 MHz	1022
0 0	5	6.0 MHz	1021
11	4	4.8 MHz	1020

Interrupts

The P87LPC760 uses a four priority level interrupt structure. This allows great flexibility in controlling the handling of the P87LPC760's many interrupt sources. The P87LPC760 supports up to 10 interrupt sources.

Each interrupt source can be individually enabled or disabled by setting or clearing a bit in registers IEN0 or IEN1. The IEN0 register also contains a global disable bit, EA, which disables all interrupts at once.

Each interrupt source can be individually programmed to one of four priority levels by setting or clearing bits in the IPO, IPOH, IP1, and IP1H registers. An interrupt service routine in progress can be interrupted by a higher priority interrupt, but not by another interrupt

of the same or lower priority. The highest priority interrupt service cannot be interrupted by any other interrupt source. So, if two requests of different priority levels are received simultaneously, the request of higher priority level is serviced.

If requests of the same priority level are received simultaneously, an internal polling sequence determines which request is serviced. This is called the arbitration ranking. Note that the arbitration ranking is only used to resolve simultaneous requests of the same priority level.

Table 3 summarizes the interrupt sources, flag bits, vector addresses, enable bits, priority bits, arbitration ranking, and whether each interrupt may wake up the CPU from Power Down mode.

Table 3. Summary of Interrupts

Description	Interrupt Flag Bit(s)	Vector Address	Interrupt Enable Bit(s)	Interrupt Priority	Arbitration Ranking	Power Down Wakeup
External Interrupt 0	IE0	0003h	EX0 (IEN0.0)	IP0H.0, IP0.0	1 (highest)	Yes
Timer 0 Interrupt	TF0	000Bh	ET0 (IEN0.1)	IP0H.1, IP0.1	4	No
Timer 1 Interrupt	TF1	001Bh	ET1 (IEN0.3)	IP0H.3, IP0.3	8	No
Serial Port Tx and Rx	TI & RI	0023h	ES (IEN0.4)	IP0H.4, IP0.4	9	No
Brownout Detect	BOF	002Bh	EBO (IEN0.5)	IP0H.5, IP0.5	2	Yes
I ² C Interrupt	ATN	0033h	EI2 (IEN1.0)	IP1H.0, IP1.0	5	No
KBI Interrupt	KBF	003Bh	EKB (IEN1.1)	IP1H.1, IP1.1	6	Yes
Watchdog Timer	WDOVF	0053h	EWD (IEN0.6)	IP0H.6, IP0.6	3	Yes
Comparator 1 interrupt	CMF1	0063h	EC1 (IEN1.5)	IP1H.5, IP1.5	7	Yes
Timer I interrupt	-	0073h	ETI (IEN1.7)	IP1H.7, IP1.7	10 (lowest)	No

P87LPC760

External Interrupt Inputs

The P87LPC760 has one individual interrupt input as well as the Keyboard Interrupt function. The latter is described separately in this section. The interrupt input are identical to those present on the standard 80C51 microcontroller.

The external source can be programmed to be level-activated or transition-activated by setting or clearing bit IT0 in Register TCON. If IT0 = 0, external interrupt 0 is triggered by a detected low at the INT0 pin. If IT0 = 1, external interrupt 0 is edge triggered. In this mode if successive samples of the INT0 pin show a high in one cycle and a low in the next cycle, interrupt request flag IE0 in TCON is set, causing an interrupt request.

Since the external interrupt pin is sampled once each machine cycle, an input high or low should hold for at least 6 CPU Clocks to ensure proper sampling. If the external interrupt is

transition-activated, the external source has to hold the request pin high for at least one machine cycle, and then hold it low for at least one machine cycle. This is to ensure that the transition is detected and that interrupt request flag IE0 is set. IE0 is automatically cleared by the CPU when the service routine is called.

If the external interrupt is level-activated, the external source must hold the request active until the requested interrupt is actually generated. If the external interrupt is still asserted when the interrupt service routine is completed another interrupt will be generated. It is not necessary to clear the interrupt flag IEO when the interrupt is level sensitive, it simply tracks the input pin level.

If the external interrupt is enabled when the P87LPC760 is put into Power Down or Idle mode, the interrupt will cause the processor to wake up and resume operation. Refer to the section on Power Reduction Modes for details.



Figure 9. Interrupt Sources, Interrupt Enables, and Power Down Wakeup Sources

P87LPC760

I/O Ports

The P87LPC760 has 3 I/O ports, port 0, port 1, and port 2. The exact number of I/O pins available depend upon the oscillator and reset options chosen. At least 9 pins of the P87LPC760 may be used as I/Os when a two-pin external oscillator and an external reset circuit are used. Up to 12 pins may be available if fully on-chip oscillator and reset configurations are chosen.

All but three I/O port pins on the P87LPC760 may be software configured to one of four types on a bit-by-bit basis, as shown in Table 4. These are: quasi-bidirectional (standard 80C51 port outputs), push-pull, open drain, and input only. Two configuration registers for each port choose the output type for each port pin.

Table 4. Torr output configuration octaing.	Table 4	Port	Output	Configuration	Settings
---	---------	------	--------	---------------	----------

PxM1.y	PxM2.y	Port Output Mode
0	0	Quasi-bidirectional
0	1	Push-Pull
1	0	Input Only (High Impedance)
1	1	Open Drain

Quasi-Bidirectional Output Configuration

The default port output configuration for standard P87LPC760 I/O ports is the quasi-bidirectional output that is common on the 80C51 and most of its derivatives. This output type can be used as both an

input and output without the need to reconfigure the port. This is possible because when the port outputs a logic high, it is weakly driven, allowing an external device to pull the pin low. When the pin is pulled low, it is driven strongly and able to sink a fairly large current. These features are somewhat similar to an open drain output except that there are three pull-up transistors in the quasi-bidirectional output that serve different purposes.

One of these pull-ups, called the "very weak" pull-up, is turned on whenever the port latch for the pin contains a logic 1. The very weak pull-up sources a very small current that will pull the pin high if it is left floating.

A second pull-up, called the "weak" pull-up, is turned on when the port latch for the pin contains a logic 1 and the pin itself is also at a logic 1 level. This pull-up provides the primary source current for a quasi-bidirectional pin that is outputting a 1. If a pin that has a logic 1 on it is pulled low by an external device, the weak pull-up turns off, and only the very weak pull-up remains on. In order to pull the pin low under these conditions, the external device has to sink enough current to overpower the weak pull-up and take the voltage on the port pin below its input threshold.

The third pull-up is referred to as the "strong" pull-up. This pull-up is used to speed up low-to-high transitions on a quasi-bidirectional port pin when the port latch changes from a logic 0 to a logic 1. When this occurs, the strong pull-up turns on for a brief time, two CPU clocks, in order to pull the port pin high quickly. Then it turns off again.

The quasi-bidirectional port configuration is shown in Figure 10.



Figure 10. Quasi-Bidirectional Output

P87LPC760

Low power, low price, low pin count (14 pin) microcontroller with 1 kbyte OTP

Open Drain Output Configuration

The open drain output configuration turns off all pull-ups and only drives the pull-down transistor of the port driver when the port latch contains a logic 0. To be used as a logic output, a port configured in this manner must have an external pull-up, typically a resistor tied to V_{DD} . The pull-down for this mode is the same as for the quasi-bidirectional mode.

The open drain port configuration is shown in Figure 11.

Push-Pull Output Configuration

The push-pull output configuration has the same pull-down structure as both the open drain and the quasi-bidirectional output modes, but provides a continuous strong pull-up when the port latch contains a logic 1. The push-pull mode may be used when more source current is needed from a port output.

The push-pull port configuration is shown in Figure 12.

The three port pins that cannot be configured are P1.2, P1.3, and P1.5. The port pins P1.2 and P1.3 are permanently configured as open drain outputs. They may be used as inputs by writing ones to their respective port latches. P1.5 may be used as a Schmitt trigger input if the P87LPC760 has been configured for an internal reset and is not using the external reset input function RST.

Additionally, port pins P2.0 and P2.1 are disabled for both input and output if one of the crystal oscillator options is chosen. Those options are described in the Oscillator section.

The value of port pins at reset is determined by the PRHI bit in the UCFG1 register. Ports may be configured to reset high or low as needed for the application. When port pins are driven high at reset, they are in quasi-bidirectional mode and therefore do not source large amounts of current.

Every output on the P87LPC760 may potentially be used as a 20 mA sink LED drive output. However, there is a maximum total output current for all ports which must not be exceeded.

All ports pins of the P87LPC760 have slew rate controlled outputs. This is to limit noise generated by quickly switching output signals. The slew rate is factory set to approximately 10 ns rise and fall times.

The bits in the P2M1 register that are not used to control configuration of P2.1 and P2.0 are used for other purposes. These bits can enable Schmitt trigger inputs on each I/O port, enable toggle outputs from Timer 0 and Timer 1, and enable a clock output if either the internal RC oscillator or external clock input is being used. The last two functions are described in the Timer/Counters and Oscillator sections respectively. The enable bits for all of these functions are shown in Figure 13.

Each I/O port of the P87LPC760 may be selected to use TTL level inputs or Schmitt inputs with hysteresis. A single configuration bit determines this selection for the entire port. Port pins P1.2, P1.3, and P1.5 always have a Schmitt trigger input.



Figure 11. Open Drain Output



Figure 12. Push-Pull Output

P87LPC760

Low power, low price, low pin count (14 pin) microcontroller with 1 kbyte OTP

P2M1	Address: /	Address: A4h Reset Value: 00h									
	Not Bit Ad	dressable									
		_		_			-				
		7	6	5	4	3	2	1	0	-	
		P2S	P1S	P0S	ENCLK	-	TOOE	(P2M1.1)	(P2M1.0)		
									-		
E	BIT	SYMBOL	FUNCTION	FUNCTION							
F	P2M1.7	P2S	When P2S =	When P2S = 1, this bit enables Schmitt trigger inputs on Port 2.							
F	P2M1.6	P1S	When P1S =	1, this bit	t enables S	chmitt trig	ger inputs	s on Port 1.			
F	P2M1.5	P0S	When P0S =	1, this bit	t enables S	chmitt trig	ger inputs	s on Port 0.			
F	P2M1.4	ENCLK	When ENCL output is ena	K is set a bled on th	nd the 87LF ne X2 pin (F	PC760 is P2.0). Ref	configured er to the C	to use the c Dscillator sec	on-chip RC tion for det	oscillator, a clock ails.	
F	P2M1.2	T0OE	When set, the P1.2 pin is toggled whenever Timer 0 overflows. The output frequency is therefore one half of the Timer 0 overflow rate. Refer to the Timer/Counters section for details.								
F	P2M1.1, P2M1	.0 —	These bits, along with the matching bits in the P2M2 register, control the output configuration of P2.1 and P2.0 respectively ¹ .								
										SU01535	

1. See Table 4, Port Output Configuration Settings.

Figure 13. Port 2 Mode Register 1 (P2M1)

Keyboard Interrupt (KBI)

The Keyboard Interrupt function is intended primarily to allow a single interrupt to be generated when any key is pressed on a keyboard or keypad connected to specific pins of the P87LPC760, as shown in Figure 14. This interrupt may be used to wake up the CPU from Idle or Power Down modes. This feature is particularly useful in handheld, battery powered systems that need to carefully manage power consumption yet also need to be convenient to use.

The P87LPC760 allows any pin of port 0 to be enabled to cause this interrupt. Port pins are enabled by the setting of bits in the KBI register, as shown in Figure 15. The Keyboard Interrupt Flag (KBF) in the AUXR1 register is set when any enabled pin is pulled low while the KBI interrupt function is active. An interrupt will generated if it has been enabled. Note that the KBF bit must be cleared by software.

Due to human time scales and the mechanical delay associated with keyswitch closures, the KBI feature will typically allow the interrupt service routine to poll port 0 in order to determine which key was pressed, even if the processor has to wake up from Power Down mode. Refer to the section on Power Reduction Modes for details.

2002 Mar 07

P87LPC760



Figure 14. Keyboard Interrupt

KBI	Addre	ss: 86h								Reset Value: 00h
	Not Bit Addressable									
		7	6	5	4	3	2	1	0	1
		-	KBI.6	KBI.5	KBI.4	KBI.3	-	-	-	
										1
	BIT	SYMBOL	FUNCTION							
	KBI.6	I.6 KBI.6 When set, enables P0.6 as a cause of a Keyboard Interrupt.								
	KBI.5	KBI.5	When set, ena	bles P0.5	as a caus	e of a Key	board Inte	errupt.		
	KBI.4	KBI.4	When set, ena	bles P0.4	as a caus	e of a Key	board Inte	errupt.		
	KBI.3	KBI.3	When set, ena	When set, enables P0.3 as a cause of a Keyboard Interrupt.						
	Note: the K	Keyboard Inter	rupt must be ena	bled in or	der for the	e settings	of the KBI	register to	be effectiv	ve. The interrupt flag
	(KBF) is loo	cated at bit 7 o	of AUXR1.							
										SU01537

Figure 15. Keyboard Interrupt Register (KBI)

P87LPC760

Oscillator

The P87LPC760 provides several user selectable oscillator options, allowing optimization for a range of needs from high precision to lowest possible cost. These are configured when the EPROM is programmed. Basic oscillator types that are supported include: low, medium, and high speed crystals, covering a range from 20 kHz to 20 MHz; ceramic resonators; and on-chip RC oscillator.

Low Frequency Oscillator Option

This option supports an external crystal in the range of 20 kHz to 100 kHz.

Table 5 shows capacitor values that may be used with a quartz crystal in this mode.

Table 5.	Recommended	oscillator ca	apacitors for	use with the	low frequence	v oscillator o	ption

Oscillator		V_{DD} = 2.7 to 4.5 V		V _{DD} = 4.5 to 6.0 V			
Frequency	Lower Limit	Optimal Value	Upper Limit	Lower Limit	Optimal Value	Upper Limit	
20 kHz	15 pF	15 pF	33 pF	33 pF	33 pF	47 pF	
32 kHz	15 pF	15 pF	33 pF	33 pF	33 pF	47 pF	
100 kHz	15 pF	15 pF	33 pF	15 pF	15 pF	33 pF	

Medium Frequency Oscillator Option

This option supports an external crystal in the range of 100 kHz to 4 MHz. Ceramic resonators are also supported in this configuration.

Table 6 shows capacitor values that may be used with a quartz crystal in this mode.

Table 6. Recommended oscillator capacitors for use with the medium frequency oscillator option

Oscillator Frequency	V _{DD} = 2.7 to 4.5 V							
Oscillator i requeiley	Lower Limit	Optimal Value	Upper Limit					
100 kHz	33 pF	33 pF	47 pF					
1 MHz	15 pF	15 pF	33 pF					
4 MHz	15 pF	15 pF	33 pF					

High Frequency Oscillator Option

This option supports an external crystal in the range of 4 to 20 MHz. Ceramic resonators are also supported in this configuration.

Table 7 shows capacitor values that may be used with a quartz crystal in this mode.

Table 7. Recommended oscillator capacitors for use with the high frequency oscillator option

Oscillator		V_{DD} = 2.7 to 4.5 V		V _{DD} = 4.5 to 6.0 V			
Frequency	Lower Limit	Optimal Value	Upper Limit	Lower Limit	Optimal Value	Upper Limit	
4 MHz	15 pF	33 pF	47 pF	15 pF	33 pF	68 pF	
8 MHz	15 pF	15 pF	33 pF	15 pF	33 pF	47 pF	
16 MHz	-	-	-	15 pF	15 pF	33 pF	
20 MHz	-	-	-	15 pF	15 pF	33 pF	

On-Chip RC Oscillator Option

The on-chip RC oscillator option has a typical frequency of 6 MHz and can be divided down for slower operation through the use of the DIVM register. For on-chip oscillator tolerance see AC Electrical Characteristics table. A clock output on the X2/P2.0 pin may be enabled when the on-chip RC oscillator is used.

External Clock Input Option

In this configuration, the processor clock is input from an external source driving the X1/P2.1 pin. The rate may be from 0 Hz up to 20 MHz when V_{DD} is above 4.5 V and up to 10 MHz when V_{DD} is below 4.5 V. When the external clock input mode is used, the X2/P2.0 pin may be used as a standard port pin. A clock output on

the X2/P2.0 pin may be enabled when the external clock input is used.

Clock Output

The P87LPC760 supports a clock output function when either the on-chip RC oscillator or external clock input options are selected. This allows external devices to synchronize to the P87LPC760. When enabled, via the ENCLK bit in the P2M1 register, the clock output appears on the X2/CLKOUT pin whenever the on-chip oscillator is running, including in Idle mode. The frequency of the clock output is 1/6 of the CPU clock rate. If the clock output is not needed in Idle mode, it may be turned off prior to entering Idle, saving additional power. The clock output may also be enabled when the external clock input option is selected.



Figure 16. Using the Crystal Oscillator



Figure 17. Using an External Clock Input



Figure 18. Block Diagram of Oscillator Control

CPU Clock Modification: CLKR and DIVM

For backward compatibility, the CLKR configuration bit allows setting the P87LPC760 instruction and peripheral timing to match standard 80C51 timing by dividing the CPU clock by two. Default timing for the P87LPC760 is 6 CPU clocks per machine cycle while standard 80C51 timing is 12 clocks per machine cycle. This division also applies to peripheral timing, allowing 80C51 code that is oscillator frequency and/or timer rate dependent. The CLKR bit is located in the EPROM configuration register UCFG1, described under EPROM Characteristics

In addition to this, the CPU clock may be divided down from the oscillator rate by a programmable divider, under program control. This function is controlled by the DIVM register. If the DIVM register is set to zero (the default value), the CPU will be clocked by either the unmodified oscillator rate, or that rate divided by two, as determined by the previously described CLKR function.

When the DIVM register is set to some value N (between 1 and 255), the CPU clock is divided by 2 * (N + 1). Clock division values from 4 through 512 are thus possible. This feature makes it possible to temporarily run the CPU at a lower rate, reducing power consumption, in a manner similar to Idle mode. By dividing the clock, the CPU can retain the ability to respond to events other than those that can cause interrupts (i.e. events that allow exiting the Idle mode) by executing its normal program at a lower rate. This can allow bypassing the oscillator startup time in cases where Power Down mode would otherwise be used. The value of DIVM may be changed by the program at any time without interrupting code execution.

Power Monitoring Functions

The P87LPC760 incorporates power monitoring functions designed to prevent incorrect operation during initial power up and power loss or reduction during operation. This is accomplished with two hardware functions: Power-On Detect and Brownout Detect.

Brownout Detection

The Brownout Detect function allows preventing the processor from failing in an unpredictable manner if the power supply voltage drops below a certain level. The default operation is for a brownout detection to cause a processor reset, however it may alternatively be configured to generate an interrupt by setting the BOI bit in the AUXR1 register (AUXR1.5).

The P87LPC760 allows selection of two Brownout levels: 2.5 V or 3.8 V. When V_{DD} drops below the selected voltage, the brownout detector triggers and remains active until V_{DD} is returns to a level above the Brownout Detect voltage. When Brownout Detect causes a processor reset, that reset remains active as long as V_{DD} remains below the Brownout Detect voltage. When Brownout Detect generates an interrupt, that interrupt occurs once as V_{DD} crosses from above to below the Brownout Detect voltage. For the interrupt to be processed, the interrupt system and the BOI interrupt must both be enabled (via the EA and EBO bits in IEN0).

When Brownout Detect is activated, the BOF flag in the PCON register is set so that the cause of processor reset may be determined by software. This flag will remain set until cleared by software.

P87LPC760

For correct activation of Brownout Detect, the V_{DD} fall time must be no faster than 50 mV/ μ s. When V_{DD} is restored, is should not rise faster than 2 mV/ μ s in order to insure a proper reset.

The brownout voltage (2.5 V or 3.8 V) is selected via the BOV bit in the EPROM configuration register UCFG1. When unprogrammed (BOV = 1), the brownout detect voltage is 2.5 V. When programmed (BOV = 0), the brownout detect voltage is 3.8 V.

If the Brownout Detect function is not required in an application, it may be disabled, thus saving power. Brownout Detect is disabled by setting the control bit BOD in the AUXR1 register (AUXR1.6).

Power On Detection

The Power On Detect has a function similar to the Brownout Detect, but is designed to work as power comes up initially, before the power supply voltage reaches a level where Brownout Detect can work. When this feature is activated, the POF flag in the PCON register is set to indicate an initial power up condition. The POF flag will remain set until cleared by software.

Power Reduction Modes

The P87LPC760 supports Idle and Power Down modes of power reduction.

Idle Mode

The Idle mode leaves peripherals running in order to allow them to activate the processor when an interrupt is generated. Any enabled interrupt source or Reset may terminate Idle mode. Idle mode is entered by setting the IDL bit in the PCON register (see Figure 19).

Power Down Mode

The Power Down mode stops the oscillator in order to absolutely minimize power consumption. Power Down mode is entered by setting the PD bit in the PCON register (see Figure 19).

The processor can be made to exit Power Down mode via Reset or one of the interrupt sources shown in Table 5. This will occur if the interrupt is enabled and its priority is higher than any interrupt currently in progress.

In Power Down mode, the power supply voltage may be reduced to the RAM keep-alive voltage V_{RAM} . This retains the RAM contents at the point where Power Down mode was entered. SFR contents are not guaranteed after V_{DD} has been lowered to V_{RAM} , therefore it is recommended to wake up the processor via Reset in this case. V_{DD} must be raised to within the operating range before the Power Down mode is exited. Since the watchdog timer has a separate oscillator, it may reset the processor upon overflow if it is running during Power Down.

Note that if the Brownout Detect reset is enabled, the processor will be put into reset as soon as V_{DD} drops below the brownout voltage. If Brownout Detect is configured as an interrupt and is enabled, it will wake up the processor from Power Down mode when V_{DD} drops below the brownout voltage.

When the processor wakes up from Power Down mode, it will start the oscillator immediately and begin execution when the oscillator is stable. Oscillator stability is determined by counting 1024 CPU clocks after start-up when one of the crystal oscillator configurations is used, or 256 clocks after start-up for the internal RC or external clock input configurations.

Some chip functions continue to operate and draw power during Power Down mode, increasing the total power used during Power Down. These include the Brownout Detect, Watchdog Timer, and Comparator.

PCON Address: 87h Reset Value: • 30h for a Power On r										for a Power On reset	
	Not Bit	Addre	essable							• 20ł • 00ł	n for a Brownout reset n for other reset sources
	7			6	5	4	3	2	1	0	
			SMOE	1 SMOD0	BOF	POF	GF1	GF0	PD	IDL	
Bľ	т	SYN	IBOL	FUNCTION	FUNCTION						
PC	CON.7	SM	OD1	When set, this	Vhen set, this bit doubles the UART baud rate for modes 1, 2, and 3.						
PC	CON.6	SM	OD0	This bit selects the function of bit 7 of the SCON SFR. When 0, SCON.7 is the SM0 bit. When 1, SCON.7 is the FE (Framing Error) flag. ¹							the SM0 bit. When 1,
PC	CON.5	В	OF	Brown Out Flag. Set automatically when a brownout reset or interrupt has occurred. Also set at power on. Cleared by software. Refer to the Power Monitoring Functions section for additional information.						occurred. Also set at ection for additional	
PC	CON.4	Ρ	OF	Power On Flag to the Power M	g. Set auto Ionitoring	matically Functions	when a po section fo	ower-on re or addition	eset has occ al informati	curred. Cle on.	eared by software. Refer
PC	CON.3	G	F1	General purpo	se flag 1.	May be re	ad or writ	ten by use	er software,	but has no	o effect on operation.
PC	CON.2	G	F0	General purpo	se flag 0.	May be re	ad or writ	ten by use	er software,	but has no	o effect on operation.
PC	CON.1	F	PD	Power Down control bit. Setting this bit activates Power Down mode operation. Cleared when the Power Down mode is terminated (see text).						tion. Cleared when the	
PC	CON.0	II	DL	Idle mode cont terminated (se	de control bit. Setting this bit activates Idle mode operation. Cleared when the Idle mode is sed (see text).					I when the Idle mode is SU01540	

1. See Figure 31 for additional information.

Figure 19. Power Control Register (PCON)

Table 8. Sources of Wakeup from Power Down Mode

Wakeup Source	Conditions
External Interrupt 0	The interrupt must be enabled.
Keyboard Interrupt	The keyboard interrupt feature must be enabled and properly set up. The corresponding interrupt must be enabled.
Comparator 1	The comparator must be enabled and properly set up. The corresponding interrupt must be enabled.
Watchdog Timer Reset	The watchdog timer must be enabled via the WDTE bit in the UCFG1 EPROM configuration byte.
Watchdog Timer Interrupt	The WDTE bit in the UCFG1 EPROM configuration byte must not be set. The corresponding interrupt must be enabled.
Brownout Detect Reset	The BOD bit in AUXR1 must not be set (brownout detect not disabled). The BOI bit in AUXR1 must not be set (brownout interrupt disabled).
Brownout Detect Interrupt	The BOD bit in AUXR1 must not be set (brownout detect not disabled). The BOI bit in AUXR1 must be set (brownout interrupt enabled). The corresponding interrupt must be enabled.
Reset Input	The external reset input must be enabled.

Preliminary data

P87LPC760

Low Voltage EPROM Operation

The EPROM array contains some analog circuits that are not required when V_{DD} is less than 4 V, but are required for a V_{DD} greater than 4 V. The LPEP bit (AUXR.4), when set by software, will power down these analog circuits resulting in a reduced supply current. LPEP is cleared only by power-on reset, so it may be set ONLY for applications that always operate with V_{DD} less than 4 V.

Reset

The P87LPC760 has an integrated power-on reset circuit which always provides a reset when power is initially applied to the device. It is recommended to use the internal reset whenever possible to save external components and to be able to use pin P1.5 as a general-purpose input pin.

The P87LPC760 can additionally be configured to use P1.5 as an external active-low reset pin $\overline{\text{RST}}$ by programming the RPD bit in the User Configuration Register UCFG1 to 0. The internal reset is still active on power-up of the device. While the signal on the $\overline{\text{RST}}$ pin is low, the P87LPC760 is held in reset until the signal goes high.

The watchdog timer on the P87LPC760 can act as an oscillator fail detect because it uses an independent, fully on-chip oscillator.

UCFG1 is described in the System Configuration Bytes section of this datasheet.



Figure 20. Using pin P1.5 as general purpose input pin or as low-active reset pin



Figure 21. Block Diagram Showing Reset Sources

P87LPC760

Timer/Counters

The P87LPC760 has two general purpose counter/timers which are upward compatible with the standard 80C51 Timer 0 and Timer 1. Both can be configured to operate as timers or can be configured to be an event counter (see Figure 22). An option to automatically toggle the T0 pin upon timer overflow has been added.

In the "Timer" function, the register is incremented every machine cycle. Thus, one can think of it as counting machine cycles. Since a machine cycle consists of 6 CPU clock periods, the count rate is 1/6 of the CPU clock frequency. Refer to the section Enhanced CPU for a description of the CPU clock.

In the "Counter" function of Timer 0, the register is incremented in response to a 1-to-0 transition at its corresponding external input pin, T0. In this function, the external input is sampled once during every machine cycle. When the samples of the pin state show a

high in one cycle and a low in the next cycle, the count is incremented. The new count value appears in the register during the cycle following the one in which the transition was detected. Since it takes 2 machine cycles (12 CPU clocks) to recognize a 1-to-0 transition, the maximum count rate is 1/6 of the CPU clock frequency. There are no restrictions on the duty cycle of the external input signal, but to ensure that a given level is sampled at least once before it changes, it should be held for at least one full machine cycle.

The "Timer" or "Counter" function of Timer 0 is selected by control bit C/T in the Special Function Register TMOD. In addition to the "Timer" or "Counter" selection, Timer 0 and Timer 1 have four operating modes, which are selected by bit-pairs (M1, M0) in TMOD. Modes 0, 1, and 2 are the same for both Timers/Counters. Mode 3 is different. The four operating modes are described in the following text.

тмор	Addres	s: 89h								Reset Value: 00h			
	Not Bit	Addressable											
		_											
		-	-	M1	MO	GATE	C/T	M1	MO				
				·					·	,			
				т	1		т	0					
	BIT	SYMBOL	FUNCTION										
	TMOD.7, 6	-	Reserved. Mu	st be writt	en with ze	ros only.							
	TMOD.5, 4	TMOD.5, 4 M1, M0 Mode Select for Timer 1 (see table below).											
	TMOD.3	GATE	Gating control the TR0 control	for Timer ol pin is se	0. When set. When c	set, Timer/ leared, Tir	Counter is ner 0 is ei	s enabled on abled whe	only while t on the TR0	the INTO pin is high and control bit is set.			
	TMOD.2	C/T	Timer or Coun Set for Counte	ter Select r operatio	or for Time n (input fr	er 0. Clear om T0 inpu	ed for Tim ut pin).	ner operatio	on (input fr	om internal system clock.)			
	TMOD.1, 0	M1, M0	Mode Select for	or Timer 0	(see table	e below).							
		<u>M1, M0</u>	Timer Mode										
		0 0	8048 Timer "T	Ln" serves	s as 5-bit j	orescaler.							
		0 1	16-bit Timer/C	ounter "Th	In" and "T	Ln" are ca	scaded; t	here is no	prescaler.				
		10	8-bit auto-relo	ad Timer/0	Counter. T	Hn holds a	a value wł	nich is load	ed into TL	n when it overflows.			
		11	Timer 0 is a du standard Time text). Timer 1 i	ial 8-bit Ti r 0 contro n this moo	mer/Coun l bits. TH0 de is stopp	ter in this is an 8-bi bed.	mode. TL t timer on	0 is an 8-bi ly, controlle	t Timer/Co d by the T	ounter controlled by the imer 1 control bits (see SU01542			

Figure 22. Timer/Counter Mode Control Register (TMOD)

P87LPC760

Mode 0

Putting either Timer into Mode 0 makes it look like an 8048 Timer, which is an 8-bit Counter with a divide-by-32 prescaler. Figures 24 and 25 show Mode 0 operation.

In this mode, the Timer register is configured as a 13-bit register. As the count rolls over from all 1s to all 0s, it sets the Timer interrupt flag TFn. The count input is enabled to Timer 0 when TR0 = 1 and either GATE = 0 or INT0 = 1. (Setting GATE = 1 allows the Timer to be controlled by external input INT0, to facilitate pulse width

measurements). TRn is a control bit in the Special Function Register TCON (Figure 23). The GATE bit is in the TMOD register (TMOD.3).

The 13-bit register consists of all 8 bits of THn and the lower 5 bits of TLn. The upper 3 bits of TLn are indeterminate and should be ignored. Setting the run flag (TRn) does not clear the registers.

Mode 0 operation is slightly different for Timer 0 and Timer 1. See Figures 24 and 25.

TCON	Addres	s: 88h								Reset Value: 00h			
	7 6 5 4 3 2 1 0												
		TF1	TR1	TF0	TR0	-	-	IE0	IT0				
В	ыт	SYMBOL	FUNCTION										
Т	CON.7	TF1	Timer 1 overflo	mer 1 overflow flag. Set by hardware on Timer/Counter overflow. Cleared by hardware when the terrupt is processed, or by software.									
Т	CON.6	TR1	Timer 1 Run co	ontrol bit.	Set/cleare	d by softw	are to tur	n Timer/Co	unter 1 on	/off.			
Т	CON.5	TF0	Timer 0 overflo processor vect	ow flag. Se ors to the	et by hard interrupt	ware on Troutine, or	imer/Cour by softwa	nter overflov are.	w. Cleared	by hardware when the			
Т	CON.4	TR0	Timer 0 Run co	ontrol bit.	Set/cleare	d by softw	are to tur	n Timer/Co	unter 0 on	/off.			
т	CON.3, 2	-	Reserved (mus	st be 0).									
Т	CON.1 IE0 Interrupt 0 Edge flag. Set by hardware when external interrupt 0 edge is detected. Cleared by hardware when the interrupt is processed, or by software.												
Т	CON.0	IT0	Interrupt 0 Type external interru	e control l ipts.	oit. Set/cle	ared by s	oftware to	specify fall	ing edge/l	ow level triggered SU01543			

Figure 23. Timer/Counter Control Register (TCON)



Figure 24. Timer/Counter 0 in Mode 0 (13-Bit Timer/Counter)

P87LPC760





Mode 1

Mode 1 is the same as Mode 0, except that all 16 bits of the timer register (THn and TLn) are used. (See Figures 26 and 27)

Mode 2

Mode 2 configures the Timer register as an 8-bit Counter (TLn) with automatic reload, as shown in Figures 28 and 29. Overflow from TLn not only sets TFn, but also reloads TLn with the contents of THn, which must be preset by software. The reload leaves THn unchanged. Mode 2 operation is slightly different for Timer 0 and Timer 1 (see Figures 28 and 29).

Mode 3

When Timer 1 is in Mode 3 it is stopped. The effect is the same as setting TR1 = 0.

Timer 0 in Mode 3 establishes TL0 and TH0 as two separate 8-bit counters. The logic for Mode 3 on Timer 0 is shown in Figure 30. TL0 uses the Timer 0 control bits: C/T, GATE, TR0, and TF0 as well as the INT0 pin. TH0 is locked into a timer function (counting machine cycles) and takes over the use of TR1 and TF1 from Timer 1. Thus, TH0 now controls the "Timer 1" interrupt.

Mode 3 is provided for applications that require an extra 8-bit timer. With Timer 0 in Mode 3, an P87LPC760 can look like it has three Timer/Counters. When Timer 0 is in Mode 3, Timer 1 can be turned on and off by switching it into and out of its own Mode 3. It can still be used by the serial port as a baud rate generator, or in any application not requiring an interrupt.







Figure 27. Timer 1 in Mode 1 (16-Bit Timer)

P87LPC760

Low power, low price, low pin count (14 pin) microcontroller with 1 kbyte OTP

OSC/6 OR C/T = 0OSC/12 OVERFLOW TI 0 TF0 INTERRUPT 0 (8 BITS) T0 PIN 0 C/T = 1 CONTROL RELOAD TR0 TOGGLE GATE T0 PIN 0 TH0 (8 BITS) INTO PIN T0OE SU01547

Figure 28. Timer/Counter 0 in Mode 2 (8-Bit Auto-Reload)



Figure 29. Timer 1 in Mode 2 (8-Bit Auto-Reload)



Figure 30. Timer/Counter 0 Mode 3 (Two 8-Bit Timer/Counters)

P87LPC760

Timer Overflow Toggle Output

Timer 0 can be configured to automatically toggle a port output whenever a timer overflow occurs. The same device pins that is used for the T0 count inputs are also used for the timer toggle outputs. This function is enabled by control bit T0OE in the P2M1 register. The port outputs will be a logic 1 prior to the first timer overflow when this mode is turned on.

UART

The P87LPC760 includes an enhanced 80C51 UART. The baud rate source for the UART is timer 1 for modes 1 and 3, while the rate is fixed in modes 0 and 2. Because CPU clocking is different on the P87LPC760 than on the standard 80C51, baud rate calculation is somewhat different. Enhancements over the standard 80C51 UART include Framing Error detection and automatic address recognition.

The serial port is full duplex, meaning it can transmit and receive simultaneously. It is also receive-buffered, meaning it can commence reception of a second byte before a previously received byte has been read from the SBUF register. However, if the first byte still hasn't been read by the time reception of the second byte is complete, the first byte will be lost. The serial port receive and transmit registers are both accessed through Special Function Register SBUF. Writing to SBUF loads the transmit register, and reading SBUF accesses a physically separate receive register.

The serial port can be operated in 4 modes:

Mode 0

Serial data enters and exits through RxD. TxD outputs the shift clock. 8 bits are transmitted or received, LSB first. The baud rate is fixed at 1/6 of the CPU clock frequency.

Mode 1

10 bits are transmitted (through TxD) or received (through RxD): a start bit (logical 0), 8 data bits (LSB first), and a stop bit (logical 1). When data is received, the stop bit is stored in RB8 in Special Function Register SCON. The baud rate is variable and is determined by the Timer 1 overflow rate.

Mode 2

11 bits are transmitted (through TxD) or received (through RxD): start bit (logical 0), 8 data bits (LSB first), a programmable 9th data bit, and a stop bit (logical 1). When data is transmitted, the 9th data bit (TB8 in SCON) can be assigned the value of 0 or 1. Or, for example, the parity bit (P, in the PSW) could be moved into TB8. When data is received, the 9th data bit goes into RB8 in Special Function Register SCON, while the stop bit is ignored. The baud rate is programmable to either 1/16 or 1/32 of the CPU clock frequency, as determined by the SMOD1 bit in PCON.

Mode 3

11 bits are transmitted (through TxD) or received (through RxD): a start bit (logical 0), 8 data bits (LSB first), a programmable 9th data bit, and a stop bit (logical 1). In fact, Mode 3 is the same as Mode 2 in all respects except baud rate. The baud rate in Mode 3 is variable and is determined by the Timer 1 overflow rate.

In all four modes, transmission is initiated by any instruction that uses SBUF as a destination register. Reception is initiated in Mode 0 by the condition RI = 0 and REN = 1. Reception is initiated in the other modes by the incoming start bit if REN = 1

Serial Port Control Register (SCON)

The serial port control and status register is the Special Function Register SCON, shown in Figure 31. This register contains not only the mode selection bits, but also the 9th data bit for transmit and receive (TB8 and RB8), and the serial port interrupt bits (TI and RI).

The Framing Error bit (FE) allows detection of missing stop bits in the received data stream. The FE bit shares the bit position SCON.7 with the SM0 bit. Which bit appears in SCON at any particular time is determined by the SMOD0 bit in the PCON register. If SMOD0 = 0, SCON.7 is the SM0 bit. If SMOD0 = 1, SCON.7 is the FE bit. Once set, the FE bit remains set until it is cleared by software. This allows detection of framing errors for a group of characters without the need for monitoring it for every character individually.

P87LPC760

Low power, low price, low pin count (14 pin) microcontroller with 1 kbyte OTP

SCON Addree Bit Ad	ess: 98h Idressable								Reset Value: 00h			
	7	6	5	4	3	2	1	0				
	SM0/	FE SM1	SM2	REN	TB8	RB8	ΤI	RI]			
BIT	SYMBOL	FUNCTION										
SCON.7	FE	Framing Error. cleared by soft See SM0 bit b	This bit is ware. The elow.	s set by the SMOD0	e UART re bit in the	eceiver wh PCON regi	en an inva ister must	alid stop bit be 1 for th	is detected. Must be is bit to be accessible.			
SCON.7	SM0	With SM1, def to be accessib	With SM1, defines the serial port mode. The SMOD0 bit in the PCON register must be 0 for this bit to be accessible. See FE bit above.									
SCON. 6	SM1	With SM0, def	nes the se	erial port r	node (see	e table belo	ow).					
	SM0, SM1	UART Mode		Baud	Rate							
	0 0	0: shift register		CPU	clock/6							
	0 1	1: 8-bit UART		Varia	ble (see t	ext)						
	10	2: 9-bit UART		CPU	clock/32	or CPU clo	ck/16					
	11	3: 9-bit UART		Varia	ble (see t	ext)						
SCON.5	SM2	Enables the m to 1, then RI w will not be acti	ultiproces ill not be a vated if a	sor comm activated if valid stop	unication the recei bit was no	feature in ved 9th da ot received	Modes 2 a ita bit (RB8 I. In Mode	and 3. In M 3) is 0. In N 0, SM2 sh	ode 2 or 3, if SM2 is set /lode 1, if SM2=1 then RI ould be 0.			
SCON.4	REN	Enables serial	reception	. Set by so	oftware to	enable red	ception. Cl	lear by sof	tware to disable reception.			
SCON.3	TB8	The 9th data b	it that will	be transm	itted in M	odes 2 and	d 3. Set or	clear by s	oftware as desired.			
SCON.2	RB8	In Modes 2 an was received.	In Modes 2 and 3, is the 9th data bit that was received. In Mode 1, it SM2=0, RB8 is the stop bit that was received. In Mode 0, RB8 is not used.									
SCON.1	ТІ	Transmit interr of the stop bit	Fransmit interrupt flag. Set by hardware at the end of the 8th bit time in Mode 0, or at the beginning of the stop bit in the other modes, in any serial transmission. Must be cleared by software.									
SCON.0	RI	Receive interru the stop bit tim software.	upt flag. S e in the of	et by hard ther mode	ware at th s, in any s	ne end of th serial recep	ne 8th bit t ption (exce	ime in Moo ept see SM	de 0, or halfway through 12). Must be cleared by SU01550			



Baud Rates

The baud rate in Mode 0 is fixed: Mode 0 Baud Rate = CPU clock/6. The baud rate in Mode 2 depends on the value of bit SMOD1 in Special Function Register PCON. If SMOD1 = 0 (which is the value on reset), the baud rate is 1/32 of the CPU clock frequency. If SMOD1 = 1, the baud rate is 1/16 of the CPU clock frequency.

Mode 2 Baud Rate =
$$\frac{1 + SMOD1}{32}$$
 x CPU clock frequency

Using Timer 1 to Generate Baud Rates

When Timer 1 is used as the baud rate generator, the baud rates in Modes 1 and 3 are determined by the Timer 1 overflow rate and the value of SMOD1. The Timer 1 interrupt should be disabled in this

application. The Timer itself can be configured for either "timer" or "counter" operation, and in any of its 3 running modes. In the most typical applications, it is configured for "timer" operation, in the auto-reload mode (high nibble of TMOD = 0010b). In that case the baud rate is given by the formula:

Mode 1, 3 Baud Rate =
$$\frac{\begin{array}{c} \text{CPU clock frequency/} \\ 192 \text{ (or 96 if SMOD1 = 1)} \\ \hline 256 - \text{ (TH1)} \end{array}$$

Tables 6 and 7 list various commonly used baud rates and how they can be obtained using Timer 1 as the baud rate generator.

P87LPC760

Timor Count	Baud Rate											
Timer Count	2400	4800	9600	19.2k	38.4k	57.6k						
-1	0.4608	0.9216	* 1.8432	* 3.6864	* 7.3728	* 11.0592						
-2	0.9216	1.8432	* 3.6864	* 7.3728	* 14.7456							
-3	1.3824	2.7648	5.5296	* 11.0592	-	-						
-4	* 1.8432	* 3.6864	* 7.3728	* 14.7456	-	-						
-5	2.3040	4.6080	9.2160	* 18.4320	-	-						
-6	2.7648	5.5296	* 11.0592	-	-	-						
-7	3.2256	6.4512	12.9024	-	-	-						
-8	* 3.6864	* 7.3728	* 14.7456	-	-	-						
-9	4.1472	8.2944	16.5888	-	-	-						
-10	4.6080	9.2160	* 18.4320	-	-	_						

Table 9. Baud Rates, Timer Values, and CPU Clock Frequencies for SMOD1 = 0

Table 10. Baud Rates, Timer Values, and CPU Clock Frequencies for SMOD1 = 1

Timer Count	Baud Rate											
Timer Count	2400	4800	9600	19.2 k	38.4 k	57.6 k	115.2 k					
-1	0.2304	0.4608	0.9216	* 1.8432	* 3.6864	5.5296	* 11.0592					
-2	0.4608	0.9216	* 1.8432	* 3.6864	* 7.3728	* 11.0592	-					
-3	0.6912	1.3824	2.7648	5.5296	* 11.0592	16.5888	-					
-4	0.9216	* 1.8432	* 3.6864	* 7.3728	* 14.7456	-	-					
-5	1.1520	2.3040	4.6080	9.2160	* 18.4320	-	-					
-6	1.3824	2.7648	5.5296	* 11.0592	-	-	-					
-7	1.6128	3.2256	6.4512	12.9024	-	-	-					
-8	* 1.8432	* 3.6864	* 7.3728	* 14.7456	-	-	-					
-9	2.0736	4.1472	8.2944	16.5888	-	-	-					
-10	2.3040	4.6080	9.2160	* 18.4320	-	-	-					
-11	2.5344	5.0688	10.1376	-	-	-	-					
-12	2.7648	5.5296	* 11.0592	-	-	-	-					
-13	2.9952	5.9904	11.9808	-	-	-	-					
-14	3.2256	6.4512	12.9024	-	-	-	-					
-15	3.4560	6.9120	13.8240	-	-	-	-					
-16	* 3.6864	* 7.3728	* 14.7456	-	-	-	-					
-17	3.9168	7.8336	15.6672	-	-	-	-					
-18	4.1472	8.2944	16.5888	-	-	-	-					
-19	4.3776	8.7552	17.5104	-	-	-	-					
-20	4.6080	9.2160	* 18.4320	-	-	-	-					
-21	4.8384	9.6768	19.3536	-	-	-	-					

NOTES TO TABLES 9 AND 10:

- 1. Tables 6 and 7 apply to UART modes 1 and 3 (variable rate modes), and show CPU clock rates in MHz for standard baud rates from 2400 to 115.2k baud.
- 2. Table 6 shows timer settings and CPU clock rates with the SMOD1 bit in the PCON register = 0 (the default after reset), while Table 7 reflects the SMOD1 bit = 1.
- 3. The tables show all potential CPU clock frequencies up to 20 MHz that may be used for baud rates from 9600 baud to 115.2 k baud. Other CPU clock frequencies that would give only lower baud rates are not shown.
- 4. Table entries marked with an asterisk (*) indicate standard crystal and ceramic resonator frequencies that may be obtained from many sources without special ordering.

P87LPC760

More About UART Mode 0

Serial data enters and exits through RxD. TxD outputs the shift clock. 8 bits are transmitted/received: 8 data bits (LSB first). The baud rate is fixed at 1/6 the CPU clock frequency. Figure 32 shows a simplified functional diagram of the serial port in Mode 0, and associated timing.

Transmission is initiated by any instruction that uses SBUF as a destination register. The "write to SBUF" signal at S6P2 also loads a 1 into the 9th position of the transmit shift register and tells the TX Control block to commence a transmission. The internal timing is such that one full machine cycle will elapse between "write to SBUF" and activation of SEND.

SEND enables the output of the shift register to the alternate output function line of P1.1 and also enable SHIFT CLOCK to the alternate output function line of P1.0. SHIFT CLOCK is low during S3, S4, and S5 of every machine cycle, and high during S6, S1, and S2. At S6P2 of every machine cycle in which SEND is active, the contents of the transmit shift are shifted to the right one position.

As data bits shift out to the right, zeros come in from the left. When the MSB of the data byte is at the output position of the shift register, then the 1 that was initially loaded into the 9th position, is just to the left of the MSB, and all positions to the left of that contain zeros. This condition flags the TX Control block to do one last shift and then deactivate SEND and set T1. Both of these actions occur at S1P1 of the 10th machine cycle after "write to SBUF." Reception is initiated by the condition REN = 1 and R1 = 0. At S6P2 of the next machine cycle, the RX Control unit writes the bits 1111110 t o the receive shift register, and in the next clock phase activates RECEIVE.

RECEIVE enable SHIFT CLOCK to the alternate output function line of P1.0. SHIFT CLOCK makes transitions at S3P1 and S6P1 of every machine cycle. At S6P2 of every machine cycle in which RECEIVE is active, the contents of the receive shift register are shifted to the left one position. The value that comes in from the right is the value that was sampled at the P1.1 pin at S5P2 of the same machine cycle.

As data bits come in from the right, 1s shift out to the left. When the 0 that was initially loaded into the rightmost position arrives at the leftmost position in the shift register, it flags the RX Control block to do one last shift and load SBUF. At S1P1 of the 10th machine cycle after the write to SCON that cleared RI, RECEIVE is cleared as RI is set.

More About UART Mode 1

Ten bits are transmitted (through TxD), or received (through RxD): a start bit (0), 8 data bits (LSB first), and a stop bit (1). On receive, the stop bit goes into RB8 in SCON. In the P87LPC760 the baud rate is determined by the Timer 1 overflow rate. Figure 33 shows a simplified functional diagram of the serial port in Mode 1, and associated timings for transmit receive.

Transmission is initiated by any instruction that uses SBUF as a destination register. The "write to SBUF" signal also loads a 1 into the 9th bit position of the transmit shift register and flags the TX Control unit that a transmission is requested. Transmission actually commences at S1P1 of the machine cycle following the next rollover in the divide-by-16 counter. (Thus, the bit times are synchronized to the divide-by-16 counter, not to the "write to SBUF" signal.)

The transmission begins with activation of SEND, which puts the start bit at TxD. One bit time later, DATA is activated, which enables the output bit of the transmit shift register to TxD. The first shift pulse occurs one bit time after that.

As data bits shift out to the right, zeros are clocked in from the left. When the MSB of the data byte is at the output position of the shift register, then the 1 that was initially loaded into the 9th position is just to the left of the MSB, and all positions to the left of that contain zeros. This condition flags the TX Control unit to do one last shift and then deactivate SEND and set TI. This occurs at the 10th divide-by-16 rollover after "write to SBUF."

Reception is initiated by a detected 1-to-0 transition at RxD. For this purpose RxD is sampled at a rate of 16 times whatever baud rate has been established. When a transition is detected, the divide-by-16 counter is immediately reset, and 1FFH is written into the input shift register. Resetting the divide-by-16 counter aligns its rollovers with the boundaries of the incoming bit times.

The 16 states of the counter divide each bit time into 16ths. At the 7th, 8th, and 9th counter states of each bit time, the bit detector samples the value of RxD. The value accepted is the value that was seen in at least 2 of the 3 samples. This is done for noise rejection. If the value accepted during the first bit time is not 0, the receive circuits are reset and the unit goes back to looking for another 1-to-0 transition. This is to provide rejection of false start bits. If the start bit proves valid, it is shifted into the input shift register, and reception of the rest of the frame will proceed.

As data bits come in from the right, 1s shift out to the left. When the start bit arrives at the leftmost position in the shift register (which in mode 1 is a 9-bit register), it flags the RX Control block to do one last shift, load SBUF and RB8, and set RI. The signal to load SBUF and RB8, and to set RI, will be generated if, and only if, the following conditions are met at the time the final shift pulse is generated: 1. R1 = 0, and 2. Either SM2 = 0, or the received stop bit = 1.

If either of these two conditions is not met, the received frame is irretrievably lost. If both conditions are met, the stop bit goes into RB8, the 8 data bits go into SBUF, and RI is activated. At this time, whether the above conditions are met or not, the unit goes back to looking for a 1-to-0 transition in RxD.



Figure 32. Serial Port Mode 0





Figure 33. Serial Port Mode 1

More About UART Modes 2 and 3

Eleven bits are transmitted (through TxD), or received (through RxD): a start bit (0), 8 data bits (LSB first), a programmable 9th data bit, and a stop bit (1). On transmit, the 9th data bit (TB8) can be assigned the value of 0 or 1. On receive, the 9the data bit goes into RB8 in SCON. The baud rate is programmable to either 1/16 or 1/32 of the CPU clock frequency in Mode 2. Mode 3 may have a variable baud rate generated from Timer 1.

Figures 34 and 35 show a functional diagram of the serial port in Modes 2 and 3. The receive portion is exactly the same as in Mode 1. The transmit portion differs from Mode 1 only in the 9th bit of the transmit shift register.

Transmission is initiated by any instruction that uses SBUF as a destination register. The "write to SBUF" signal also loads TB8 into the 9th bit position of the transmit shift register and flags the TX Control unit that a transmission is requested. Transmission commences at S1P1 of the machine cycle following the next rollover in the divide-by-16 counter. (Thus, the bit times are synchronized to the divide-by-16 counter, not to the "write to SBUF" signal.)

The transmission begins with activation of SEND, which puts the start bit at TxD. One bit time later, DATA is activated, which enables the output bit of the transmit shift register to TxD. The first shift pulse occurs one bit time after that. The first shift clocks a 1 (the stop bit) into the 9th bit position of the shift register. Thereafter, only zeros are clocked in. Thus, as data bits shift out to the right, zeros are clocked in from the left. When TB8 is at the output position of the shift register, then the stop bit is just to the left of TB8, and all positions to the left of that contain zeros. This condition flags the TX Control unit to do one last shift and then deactivate SEND and set TI. This occurs at the 11th divide-by-16 rollover after "write to SBUF."

Reception is initiated by a detected 1-to-0 transition at RxD. For this purpose RxD is sampled at a rate of 16 times whatever baud rate has been established. When a transition is detected, the divide-by-16 counter is immediately reset, and 1FFH is written to the input shift register.

At the 7th, 8th, and 9th counter states of each bit time, the bit detector samples the value of R–D. The value accepted is the value that was seen in at least 2 of the 3 samples. If the value accepted during the first bit time is not 0, the receive circuits are reset and the unit goes back to looking for another 1-to-0 transition. If the start bit

proves valid, it is shifted into the input shift register, and reception of the rest of the frame will proceed.

As data bits come in from the right, 1s shift out to the left. When the start bit arrives at the leftmost position in the shift register (which in Modes 2 and 3 is a 9-bit register), it flags the RX Control block to do one last shift, load SBUF and RB8, and set RI.

The signal to load SBUF and RB8, and to set RI, will be generated if, and only if, the following conditions are met at the time the final shift pulse is generated. 1. RI = 0, and 2. Either SM2 = 0, or the received 9th data bit = 1.

If either of these conditions is not met, the received frame is irretrievably lost, and RI is not set. If both conditions are met, the received 9th data bit goes into RB8, and the first 8 data bits go into SBUF. One bit time later, whether the above conditions were met or not, the unit goes back to looking for a 1-to-0 transition at the RxD input.

Multiprocessor Communications

UART modes 2 and 3 have a special provision for multiprocessor communications. In these modes, 9 data bits are received or transmitted. When data is received, the 9th bit is stored in RB8. The UART can be programmed such that when the stop bit is received, the serial port interrupt will be activated only if RB8 = 1. This feature is enabled by setting bit SM2 in SCON. One way to use this feature in multiprocessor systems is as follows:

When the master processor wants to transmit a block of data to one of several slaves, it first sends out an address byte which identifies the target slave. An address byte differs from a data byte in that the 9th bit is 1 in an address byte and 0 in a data byte. With SM2 = 1, no slave will be interrupted by a data byte. An address byte, however, will interrupt all slaves, so that each slave can examine the received byte and see if it is being addressed. The addressed slave will clear its SM2 bit and prepare to receive the data bytes that follow. The slaves that weren't being addressed leave their SM2 bits set and go on about their business, ignoring the subsequent data bytes.

SM2 has no effect in Mode 0, and in Mode 1 can be used to check the validity of the stop bit, although this is better done with the Framing Error flag. In a Mode 1 reception, if SM2 = 1, the receive interrupt will not be activated unless a valid stop bit is received.





Figure 34. Serial Port Mode 2



Figure 35. Serial Port Mode 3

Automatic Address Recognition

Automatic Address Recognition is a feature which allows the UART to recognize certain addresses in the serial bit stream by using hardware to make the comparisons. This feature saves a great deal of software overhead by eliminating the need for the software to examine every serial address which passes by the serial port. This feature is enabled by setting the SM2 bit in SCON. In the 9 bit UART modes, mode 2 and mode 3, the Receive Interrupt flag (RI) will be automatically set when the received byte contains either the "Given" address or the "Broadcast" address. The 9 bit mode requires that the 9th information bit is a 1 to indicate that the received information is an address and not data.

Using the Automatic Address Recognition feature allows a master to selectively communicate with one or more slaves by invoking the Given slave address or addresses. All of the slaves may be contacted by using the Broadcast address. Two special Function Registers are used to define the slave's address, SADDR, and the address mask, SADEN. SADEN is used to define which bits in the SADDR are to be used and which bits are "don't care". The SADEN mask can be logically ANDed with the SADDR to create the "Given" address which the master will use for addressing each of the slaves. Use of the Given address allows multiple slaves to be recognized while excluding others. The following examples will help to show the versatility of this scheme:

SADDR	= 1100 0000
SADEN	= <u>1111 1101</u>
Given	= 1100 00X0
SADDR	= 1100 0000
SADEN	= <u>1111 1110</u>
Given	= 1100 000X
	SADDR SADEN Given SADDR SADEN Given

In the above example SADDR is the same and the SADEN data is used to differentiate between the two slaves. Slave 0 requires a 0 in bit 0 and it ignores bit 1. Slave 1 requires a 0 in bit 1 and bit 0 is ignored. A unique address for Slave 0 would be 1100 0010 since slave 1 requires a 0 in bit 1. A unique address for slave 1 would be 1100 0001 since a 1 in bit 0 will exclude slave 0. Both slaves can be selected at the same time by an address which has bit 0 = 0 (for slave 0) and bit 1 = 0 (for slave 1). Thus, both could be addressed with 1100 0000.

In a more complex system the following could be used to select slaves 1 and 2 while excluding slave 0:

Slave 0	SADDR	= 1100 0000
	SADEN	= <u>1111 1001</u>
	Given	= 1100 0XX0
Slave 1	SADDR	= 1110 0000
	SADEN	= <u>1111 1010</u>
	Given	= 1110 0X0X
Slave 2	SADDR	= 1110 0000
	SADEN	= <u>1111 1100</u>
	Given	= 1110 00XX

In the above example the differentiation among the 3 slaves is in the lower 3 address bits. Slave 0 requires that bit 0 = 0 and it can be uniquely addressed by 1110 0110. Slave 1 requires that bit 1 = 0 and it can be uniquely addressed by 1110 and 0101. Slave 2 requires that bit 2 = 0 and its unique address is 1110 0011. To select Slaves 0 and 1 and exclude Slave 2 use address 1110 0100, since it is necessary to make bit 2 = 1 to exclude slave 2. The Broadcast

Address for each slave is created by taking the logical OR of SADDR and SADEN. Zeros in this result are treated as don't-cares. In most cases, interpreting the don't-cares as ones, the broadcast address will be FF hexadecimal. Upon reset SADDR and SADEN are loaded with 0s. This produces a given address of all "don't cares" as well as a Broadcast address of all "don't cares". This effectively disables the Automatic Addressing mode and allows the microcontroller to use standard UART drivers which do not make use of this feature.

Watchdog Timer

When enabled via the WDTE configuration bit, the watchdog timer is operated from an independent, fully on-chip oscillator in order to provide the greatest possible dependability. When the watchdog feature is enabled, the timer must be fed regularly by software in order to prevent it from resetting the CPU, and it <u>cannot</u> be turned off. When disabled as a watchdog timer (via the WDTE bit in the UCFG1 configuration register), it may be used as an interval timer and may generate an interrupt. The watchdog timer is shown in Figure 36.

The watchdog timeout time is selectable from one of eight values, nominal times range from 25 milliseconds to 3.2 seconds. The frequency tolerance of the independent watchdog RC oscillator is \pm 37%. The timeout selections and other control bits are shown in Figure 35. When the watchdog function is enabled, the WDCON register may be written <u>once</u> during chip initialization in order to set the watchdog timeout time. The recommended method of initializing the WDCON register is to first feed the watchdog, then write to WDCON to configure the WDS2–0 bits. Using this method, the watchdog initialization may be done any time within 10 milliseconds after startup without a watchdog overflow occurring before the initialization can be completed.

Since the watchdog timer oscillator is fully on-chip and independent of any external oscillator circuit used by the CPU, it intrinsically serves as an oscillator fail detection function. If the watchdog feature is enabled and the CPU oscillator fails for any reason, the watchdog timer will time out and reset the CPU.

When the watchdog function is enabled, the timer is deactivated temporarily when a chip reset occurs from another source, such as a power on reset, brownout reset, or external reset.

Watchdog Feed Sequence

If the watchdog timer is running, it must be fed before it times out in order to prevent a chip reset from occurring. The watchdog feed sequence consists of first writing the value 1Eh, then the value E1h to the WDRST register. An example of a watchdog feed sequence is shown below.

WDFeed:

mov WDRST,#leh ; First part of watchdog feed sequence. mov WDRST,#0elh ; Second part of watchdog feed sequence.

The two writes to WDRST do not have to occur in consecutive instructions. An incorrect watchdog feed sequence does not cause any immediate response from the watchdog timer, which will still time out at the originally scheduled time if a correct feed sequence does not occur prior to that time.

After a chip reset, the user program has a limited time in which to either feed the watchdog timer or change the timeout period. When a low CPU clock frequency is used in the application, the number of

P87LPC760

Low power, low price, low pin count (14 pin) microcontroller with 1 kbyte OTP

code execution will begin immediately after that. If the processor was in Power Down mode, the watchdog reset will start the oscillator and code execution will resume after the oscillator is

instructions that can be executed before the watchdog overflows may be quite small.

Watchdog Reset

If a watchdog reset occurs, the internal reset is active for approximately one microsecond. If the CPU clock was still running,



stable.

Figure 36. Block Diagram of the Watchdog Timer

WDCON	Address:	A7h		Reset	Value: • 3	0h for a wat	chdog res	et.							
	Not Bit A	ddress	able		• 1	0h for other	rest sourc	es if the w	atchdog is	enabled v	ia the WDTE conf	iguration bit.			
				O0h for other reset sources if the watchdog is disabled via the WDTE configuration bit.											
			7	6	5	4	3	2	1	0					
			-	_	WDOVF	WDRUN	WDCLK	WDS2	WDS1	WDS0					
						1									
BI	г	SYME	BOL	FUNCTION											
WE	DCON.7, 6		-	Reserv	Reserved for future use. Should not be set to 1 by user programs.										
WE	DCON.5	WDO	DVF	Watchdog timer overflow flag. Set when a watchdog reset or timer overflow occurs. Cleared when the watchdog is fed.											
WE	DCON.4	WDR	UN	Watcho WDRU	log run con N = 0. This	trol. The was bit is forced	atchdog tin d to 1 (wate	ner is star chdog run	ted when W ning) if the	/DRUN = ⁻ WDTE co	1 and stopped when the	en			
WE	DCON.3	WDC	CLK	Watchdog clock select. The watchdog timer is clocked by CPU clock/6 when WDCLK = 1 and by the watchdog RC oscillator when WDCLK = 0. This bit is forced to 0 (using the watchdog RC oscillator) if the WDTE configuration bit = 1.											
WE	DCON.2-0	WDS	2–0	Watchdog rate select.											
		WDS:	<u>2–0</u>	Timeo	ut Clocks	Minimur	n Time	No	ominal Time	2	<u>Maximum Time</u>				
		0 0	0	8	,192	10 i	ms		16 ms		23 ms				
		0 0	1	16	6,384	20 ו	ms		32 ms		45 ms				
		0 1	0	32	2,768	41 ı	ms		65 ms		90 ms				
		0 1	1	65	5,536	82 ו	ns		131 ms		180 ms				
	100			13	1,072	165	ms		262 ms		360 ms				
	101		1	26	2,144	330	ms		524 ms		719 ms				
		11	0	52	4,288	660	ms		1.05 sec		1.44 sec				
		11	1	1,04	48,576	1.3 :	sec		2.1 sec		2.9 sec	SU01634			

Figure 37. Watchdog Timer Control Register (WDCON)

P87LPC760

Additional Features

The AUXR1 register contains several special purpose control bits that relate to several chip features. AUXR1 is described in Figure 38.

Software Reset

The SRST bit in AUXR1 allows software the opportunity to reset the processor completely, as if an external reset or watchdog reset had occurred. If a value is written to AUXR1 that contains a 1 at bit position 3, all SFRs will be initialized and execution will resume at program address 0000. Care should be taken when writing to AUXR1 to avoid accidental software resets.

Dual Data Pointers

The dual Data Pointer (DPTR) adds to the ways in which the processor can specify the address used with certain instructions. The DPS bit in the AUXR1 register selects one of the two Data Pointers. The DPTR that is not currently selected is not accessible to software unless the DPS bit is toggled.

Specific instructions affected by the Data Pointer selection are:

• INC DPTR Increments the Data Pointer by 1.

• JMP @A+DPTR Jump indirect relative to DPTR value.

•	MOV	DPTR, #data16	Load the Data Pointer with a 16-bit constant.
•	MOVC	A, @A+DPTR	Move code byte relative to DPTR to the accumulator.
•	MOVX	A, @DPTR	Move data byte the accumulator to data memory relative to DPTR.
•	MOVX	@DPTR, A	Move data byte from data memory relative to DPTR to the accumulator.

Also, any instruction that reads or manipulates the DPH and DPL registers (the upper and lower bytes of the current DPTR) will be affected by the setting of DPS. The MOVX instructions have limited application for the P87LPC760 since the part does not have an external data bus. However, they may be used to access EPROM configuration information (see EPROM Characteristics section).

Bit 2 of AUXR1 is permanently wired as a logic 0. This is so that the DPS bit may be toggled (thereby switching Data Pointers) simply by incrementing the AUXR1 register, without the possibility of inadvertently altering other bits in the register.

AUXR1	Address	s: A2h									Reset Value: 00h
	Not Bit A	Addressable	9								
			7	6	5	4	3	2	1	0	_
			KBF	BOD	BOI	LPEP	SRST	0	_	DPS	
						•			•		
BI	ΙТ	SYMBOL	. FUN	ICTION							
Al	UXR1.7	KBF	Key func	board Int	errupt Flag s low. Must	. Set when a be cleared	any pin of by softwar	port 0 tha e.	t is enabled	for the Ke	yboard Interrupt
Al	UXR1.6	BOD	Brov Mor	wn Out D hitoring Fi	isable. Whe	en set, turns ction for de	s off brown tails.	out detec	tion and sav	ves power	: See Power
AU	UXR1.5	BOI	Brow the sect	wn Out In brownout tion for de	terrupt. Wh detect fun etails.	nen set, pre ction to be u	vents brow used as an	nout dete interrupt.	ection from o See the Po	causing a ower Monit	chip reset and allows toring Functions
Al	UXR1.4	LPEP	Low only	Power E be cleare	PROM con ed by powe	trol bit. Allov r-on or brow	ws power s vnout reset	avings in . See the	low voltage Power Redu	systems. uction Mod	Set by software. Can des section for details.
AL	UXR1.3	SRST	Soft	ware Res	set. When s	set by softw	are, resets	the 87LF	C760 as if	a hardwar	e reset occurred.
Al	UXR1.2	—	This inter	s bit conta rfering wi	ains a hard- th other bit	wired 0. All s in the regi	ows toggliı ster.	ng of the I	OPS bit by i	ncrementi	ng AUXR1, without
AL	UXR1.1	_	Res	erved for	future use	. Should not	t be set to	1 by user	programs.		
AU	UXR1.0	DPS	Data	a Pointer	Select. Ch	ooses one o	of two Data	Pointers	for use by t	the progra	m. See text for details.
											SU01551

Figure 38. AUXR1 Register

P87LPC760

EPROM Characteristics

Programming of the EPROM on the P87LPC760 is accomplished with a serial programming method. Commands, addresses, and data are transmitted to and from the device on two pins after programming mode is entered. Serial programming allows easy implementation of In-System Programming of the P87LPC760 in an application board. Details of In-System Programming can be found in application note AN466.

The P87LPC760 contains three signature bytes that can be read and used by an EPROM programming system to identify the device. The signature bytes designate the device as an P87LPC760 manufactured by Philips. The signature bytes may be read by the user program at addresses FC30h, FC31h and FC60h with the MOVC instruction, using the DPTR register for addressing.

A special user data area is also available for access via the MOVC instruction at addresses FCE0h through FCFFh. This "customer code" space is programmed in the same manner as the main code EPROM and may be used to store a serial number, manufacturing date, or other application information.

32-Byte Customer Code Space

A small supplemental EPROM space is reserved for use by the customer in order to identify code revisions, store checksums, add a serial number to each device, or any other desired use. This area exists in the code memory space from addresses FCE0h through FCFFh. Code execution from this space is not supported, but it may be read as data through the use of the MOVC instruction with the appropriate addresses. The memory may be programmed at the same time as the rest of the code memory and UCFG bytes are programmed.

System Configuration Bytes

A number of user configurable features of the P87LPC760 must be defined at power up and therefore cannot be set by the program after start of execution. Those features are configured through the use of two EPROM bytes that are programmed in the same manner as the EPROM program space. The contents of the two configuration bytes, UCFG1 and UCFG2, are shown in Figures 39 and 40. The values of these bytes may be read by the program through the use of the MOVX instruction at the addresses shown in the figure.

UCFG1	UCFG1 Address: FD00h Unprogrammed Value: FFh												
			7	6	5	4	3	2	1	0			
			WDTE	RPD	PRHI	BOV	CLKR	FOSC2	FOSC1	FOSC0			
						•							
BIT		SYM	BOL	FUNCT	ION								
UCF	UCFG1.7 WDTE Watchdog timer enable. When programmed (0), disables the watchdog timer. The timer may still be used to generate an interrupt.												
UCFG1.6 RPD Reset pin disable. When 1 disables the reset function of pin P1.5, allowing it to be used as an input only port pin.													
UCF	G1.5	PR	RHI	Port res	set high. W	/hen 1, ports	s reset to a	a high state	e. When 0,	ports rese	t to a low state.		
UCF	G1.4	BC	DV	Browno detect	out voltage voltage is 3	select. Whe 3.8V. This is	en 1, the b described	rownout d	etect voltag wer Monito	ge is 2.5V. ring Functi	When 0, the brownout ons section.		
UCF	G1.3	CL	KR	Clock r taking this div	ate select. 12 CPU clo ision applie	When 0, the ocks to comp es to periphe	e CPU cloo plete as in eral timing	ck rate is o the standa as well.	divided by 2 ard 80C51.	2. This resu For full ba	ults in machine cycles ackward compatibility,		
UCF	G1.2–0	FOSC2-	-FSOC0	CPU os other th	scillator typ an those s	e select. Se shown belov	e Oscillato v should no	or section ot be used	for addition I. They are	al informa reserved f	tion. Combinations or future use.		
		FOSC2-	-FOSC0	<u>Oscilla</u>	or Configu	ration							
		1 1	1	Externa	al clock inp	ut on X1 (de	efault settir	ng for an u	Inprogramn	ned part).			
		0 1	1	Interna	RC oscilla	ator, 6 MHz.	For tolera	nce, see A	AC Electrica	al Characte	eristics table.		
		0 1	0	Low fre	quency cry	/stal, 20 kH	z to 100 kł	Hz.					
		0 0) 1	Medium	n frequenc	y crystal or	resonator,	100 kHz t	o 4 MHz.				
		0 0	0 0	High fre	equency cr	ystal or reso	onator, 4 N	1Hz to 20 I	MHz.				
											SU01477		

Figure 39. EPROM System Configuration Byte 1 (UCFG1)



Figure 40. EPROM System Configuration Byte 2 (UCFG2)

Security Bits

When neither of the security bits are programmed, the code in the EPROM can be verified. When only security bit 1 is programmed, all

further programming of the EPROM is disabled. At that point, only security bit 2 may still be programmed. When both security bits are programmed, EPROM verify is also disabled.

Table 11. EPROM Security Bits

SB2	SB1	Protection Description
1	1	Both security bits unprogrammed. No program security features enabled. EPROM is programmable and verifiable.
1	0	Only security bit 1 programmed. Further EPROM programming is disabled. Security bit 2 may still be programmed.
0	1	Only security bit 2 programmed. This combination is not supported.
0	0	Both security bits programmed. All EPROM verification and programming are disabled.

P87LPC760

ABSOLUTE MAXIMUM RATINGS

PARAMETER	RATING	UNIT
Operating temperature under bias	–55 to +125	°C
Storage temperature range	–65 to +150	°C
Voltage on RST/V _{PP} pin to V _{SS}	0 to +11.0	V
Voltage on any other pin to V_{SS}	–0.5 to V _{DD} +0.5V	V
Maximum I _{OL} per I/O pin	20	mA
Power dissipation (based on package heat transfer, not device power consumption)	1.5	W

NOTES:

1. Stresses above those listed under Absolute Maximum Ratings may cause permanent damage to the device. This is a stress rating only and functional operation of the device at these or any conditions other than those described in the AC and DC Electrical Characteristics section of this specification are not implied.

2. This product includes circuitry specifically designed for the protection of its internal devices from the damaging effects of excessive static charge. Nonetheless, it is suggested that conventional precautions be taken to avoid applying greater than the rated maximum.

3. Parameters are valid over operating temperature range unless otherwise specified. All voltages are with respect to VSS unless otherwise noted.

DC ELECTRICAL CHARACTERISTICS

V_{DD} = 2.7 V to 6.0 V unless otherwise specified; T_{amb} = 0 °C to +70 °C, unless otherwise specified.

SYMPOL	DADAMETED	TEST CONDITIONS		LINIT		
STMBOL	PARAMETER	TEST CONDITIONS	MIN	TYP ^{1,2}	MAX	UNIT
1	Power supply surrent operating	5.0 V, 20 MHz ¹¹	-	15	25	mA
'DD	Power supply current, operating	3.0 V, 10 MHz ¹¹	-	4	7	mA
1	Bower supply surrent exercting BC Occ	5.0 V, 6 MHz ¹¹	-	4	-	mA
'RC	Power supply current, operating RC Osc.	3.0 V, 6 MHz ¹¹	-	2	-	mA
	Bower auguly current Idle mode	5.0 V, 20 MHz ¹¹	-	6	10	mA
'ID	Fower supply current, fale filode	3.0 V, 10 MHz ¹¹	-	2	4	mA
1	Rower supply surrent Rower Down mode	5.0 V ¹¹	-	1	10	μΑ
PD	Power supply current, Power Down mode	3.0 V ¹¹	-	1	5	μΑ
V _{RAM}	RAM keep-alive voltage		1.5	-	-	V
Ma	Input low voltage (TTL input)	4.0 V < V _{DD} < 6.0 V	-0.5	-	0.2 V _{DD} -0.1	V
VIL	input low voltage (11 E input)	2.7 V < V _{DD} < 4.0 V	-0.5	-	0.7	V
V _{IL1}	Negative going threshold (Schmitt input)		-0.5	-	0.3 V _{DD}	V
V _{IH}	Input high voltage (TTL input)		0.2 V _{DD} +0.9	-	V _{DD} +0.5	V
V _{IH1}	Positive going threshold (Schmitt input)		0.7V _{DD}	-	V _{DD} +0.5	V
HYS	Hysteresis voltage		-	0.2 V _{DD}	-	V
V _{OL}	Output low voltage all ports ^{5, 9}	I _{OL} = 3.2 mA, V _{DD} = 2.7 V	-	-	0.4	V
V _{OL1}	Output low voltage all ports ^{5, 9}	I _{OL} = 20 mA, V _{DD} = 2.7 V	-	-	1.0	V
Vau	Output high voltage, all parts ³	$I_{OH} = -20 \ \mu A, \ V_{DD} = 2.7 \ V$	V _{DD} -0.7	-	-	V
⊻он	Output high voltage, an ports	$I_{OH} = -30 \ \mu A, \ V_{DD} = 4.5 \ V$	V _{DD} -0.7	-	-	V
V _{OH1}	Output high voltage, all ports ⁴	$I_{OH} = -1.0 \text{ mA}, V_{DD} = 2.7 \text{ V}$	V _{DD} -0.7	-	-	V
C _{IO}	Input/Output pin capacitance ¹⁰		-	-	15	pF
١ _{١L}	Logical 0 input current, all ports ⁸	V _{IN} = 0.4 V	-	-	-50	μΑ
ILI	Input leakage current, all ports ⁷	$V_{IN} = V_{IL} \text{ or } V_{IH}$	-	-	±2	μΑ
	Logical 1 to 0 transition surrant all parts 3 f	$V_{IN} = 1.5 \text{ V} \text{ at } V_{DD} = 3.0 \text{ V}$	-30	-	-250	μΑ
ITL	Logical 1 to 0 transition current, all ports ^o , o	$V_{IN} = 2.0 \text{ V} \text{ at } V_{DD} = 5.5 \text{ V}$	-150	-	-650	μΑ
R _{RST}	Internal reset pull-up resistor		40	-	225	kΩ
VBOLOW	Brownout trip voltage with BOV = 1^{12}		2.35	-	2.69	V
V _{BOHI}	Brownout trip voltage with BOV = 0		3.45	-	3.99	V
V _{REF}	Reference voltage		1.11	1.26	1.41	V

NOTES:

Typical ratings are not guaranteed. The values listed are at room temperature, 5 V.

See other Figures for details. 2.

3. Ports in quasi-bidirectional mode with weak pull-up (applies to all port pins with pull-ups). Does not apply to open drain pins.

4. Ports in PUSH-PULL mode. Does not apply to open drain pins.

5. In all output modes except high impedance mode.

6. Port pins source a transition current when used in quasi-bidirectional mode and externally driven from 1 to 0. This current is highest when VIN is approximately 2 V.

Measured with port in high impedance mode. Parameter is guaranteed but not tested at cold temperature. 7.

Measured with port in quasi-bidirectional mode. 8.

9. Under steady state (non-transient) conditions, I_{OL} must be externally limited as follows: 20 mA

Maximum IOL per port pin:

Maximum total IOL for all outputs: 80 mA Maximum total IOH for all outputs: 5 mA

If IOL exceeds the test condition, VOL may exceed the related specification. Pins are not guaranteed to sink current greater than the listed test conditions

10. Pin capacitance is characterized but not tested.

11. The IDD, IDD, and IPD specifications are measured using an external clock with the following functions disabled: comparators, brownout

detect, and watchdog timer. For V_{DD} = 3 V, LPEP = 1. Refer to the appropriate figures on the following pages for additional current drawn by each of these functions and detailed graphs for other frequency and voltage combinations.

12. Devices initially operating at V_{DD} = 2.7 V or above, and at f_{OSC} = 10 MHz or less, are guaranteed to continue to execute instructions

correctly at the brownout trip point. Initial power-on operation below V_{DD} = 2.7 V is not guaranteed. 13. Devices initially operating at V_{DD} = 4.0 V or above and at f_{OSC} = 20 MHz or less are guaranteed to continue to execute instructions correctly at the brownout trip point. Initial power-on operation below V_{DD} = 4.0 V and f_{OSC} > 10 MHz is not guaranteed.

2002 Mar 07

COMPARATOR ELECTRICAL CHARACTERISTICS

 V_{DD} = 3.0 V to 6.0 V unless otherwise specified; T_{amb} = 0 °C to +70 °C, unless otherwise specified.

SYMPOL	DADAMETED	TEST CONDITIONS				
STMBOL	PARAMETER	TEST CONDITIONS	MIN	TYP	MAX	
V _{IO}	Offset voltage comparator inputs ¹		-	-	±10	mV
V _{CR}	Common mode range comparator inputs		0	-	V _{DD} -0.3	V
CMRR	Common mode rejection ratio ¹		-	-	-50	dB
	Response time		-	250	500	ns
	Comparator enable to output valid		-	-	10	μs
۱ _{IL}	Input leakage current, comparator	$0 < V_{IN} < V_{DD}$	_	-	±10	μA

NOTE:

1. This parameter is guaranteed by characterization, but not tested in production.

AC ELECTRICAL CHARACTERISTICS

 T_{amb} = 0 °C to +70 °C, V_{DD} = 2.7 V to 6.0 V unless otherwise specified; V_{SS} = 0 V^{1, 2, 3}

SYMPOL	FIGURE	DADAMETED	LIM	LINUT		
STWBUL	FIGURE	PARAMETER	MIN	MAX	UNIT	
External Cl	ock					
f _C	42	Oscillator frequency (V_{DD} = 4.0 V to 6.0 V)		0	20	MHz
f _C	42	Oscillator frequency (V_{DD} = 2.7 V to 6.0 V)		0	10	MHz
t _C	42	Clock period and CPU timing cycle		1/f _C	-	ns
f _{CLCX}	42	Clock low-time ¹	f _{OSC} = 20 MHz	20	-	ns
f _{CLCX}	42		f _{OSC} = 10 MHz	40	-	ns
f _{CHCX}	42	Clock high-time ¹	f _{OSC} = 20 MHz	20	-	ns
f _{CHCX}	42		40	-	ns	
Internal RC	Oscillator					
f _{CCAL}		On-chip RC oscillator calibration ²	f _{RCOSC} = 6 MHz	-1	+1	%
f _{CTOL}		On-chip RC oscillator, 0 °C to +50 °C ^{3,4} tol.	f _{RCOSC} = 6 MHz	-2.5	+2.5	%
f _{CTOL}		On-chip RC oscillator, 0 °C to +70 °C ³ tol.	f _{RCOSC} = 6 MHz	-5 ⁵	+2.5	%
Shift Regis	ter					
t _{XLXL}	41	Serial port clock cycle time	6t _C	-	ns	
t _{QVXH}	41	Output data setup to clock rising edge	5t _C – 133	-	ns	
t _{XHQX}	41	Output data hold after clock rising edge	1t _C - 80	-	ns	
t _{XHDV}	41	Input data setup to clock rising edge		_	5t _C – 133	ns
t _{XHDX}	41	Input data hold after clock rising edge		0	-	ns

NOTES:

1. Applies only to an external clock source, not when a crystal is connected to the X1 and X2 pins.

2. Tested at $V_{DD} = 5.0$ V and room temperature.

3. These parameters are characterized but not tested.

4. +/- 2.5° % accuracy enables serial communication over the UART with the internal Oscillator.

5. Min frequency at hot temperature.



Figure 41. Shift Register Mode Timing



Figure 42. External Clock Timing



Figure 43. Typical ldd versus frequency (low frequency oscillator, 25 $^\circ \rm C)$



Figure 44. Typical Idd versus frequency (medium frequency oscillator, 25 °C)

P87LPC760

Low power, low price, low pin count (14 pin) microcontroller with 1 kbyte OTP



Figure 45. Typical ldd versus frequency (high frequency oscillator, 25 °C)



Figure 46. Typical Active Idd versus frequency (external clock, 25 °C, LPEP=0)



Figure 47. Typical Active Idd versus frequency (external clock, 25 °C, LPEP=1)



Figure 48. Typical Idle Idd versus frequency (external clock, 25 °C, LPEP=1)



Figure 49. Typical Idle Idd versus frequency (external clock, 25 $^{\circ}\text{C}$, LPEP=0)



P87LPC760

0.254

0.01

8.3 0.39

0.33

2.2

0.087



mm	4.2	0.51	3.2	1.73 1.13	0.53 0.38	0.36 0.23	19.50 18.55	6.48 6.20	2.54	7.62	3.60 3.05	8.25 7.80
inches	0.17	0.020	0.13	0.068 0.044	0.021 0.015	0.014 0.009	0.77 0.73	0.26 0.24	0.10	0.30	0.14 0.12	0.32 0.31

Note

1. Plastic or metal protrusions of 0.25 mm maximum per side are not included.

OUTLINE		REFEF	RENCES	EUROPEAN	
VERSION	IEC	JEDEC	EIAJ	PROJECTION	ISSUE DATE
SOT27-1	050G04	MO-001	SC-501-14		-95-03-11 99-12-27

REVISION HISTORY

Date	CPCN	Description
2002 Mar 07	9397 750 09532	Initial release

Philips Semiconductors

Low power, low price, low pin count (14 pin) microcontroller with 1 kbyte OTP

P87LPC760



Purchase of Philips I²C components conveys a license under the Philips' I²C patent to use the components in the I²C system provided the system conforms to the I²C specifications defined by Philips. This specification can be ordered using the code 9398 393 40011.

Data sheet status

Data sheet status ^[1]	Product status ^[2]	Definitions
Objective data	Development	This data sheet contains data from the objective specification for product development. Philips Semiconductors reserves the right to change the specification in any manner without notice.
Preliminary data	Qualification	This data sheet contains data from the preliminary specification. Supplementary data will be published at a later date. Philips Semiconductors reserves the right to change the specification without notice, in order to improve the design and supply the best possible product.
Product data	Production	This data sheet contains data from the product specification. Philips Semiconductors reserves the right to make changes at any time in order to improve the design, manufacturing and supply. Changes will be communicated according to the Customer Product/Process Change Notification (CPCN) procedure SNW-SQ-650A.

[1] Please consult the most recently issued data sheet before initiating or completing a design.

[2] The product status of the device(s) described in this data sheet may have changed since this data sheet was published. The latest information is available on the Internet at URL http://www.semiconductors.philips.com.

Definitions

Short-form specification — The data in a short-form specification is extracted from a full data sheet with the same type number and title. For detailed information see the relevant data sheet or data handbook.

Limiting values definition — Limiting values given are in accordance with the Absolute Maximum Rating System (IEC 60134). Stress above one or more of the limiting values may cause permanent damage to the device. These are stress ratings only and operation of the device at these or at any other conditions above those given in the Characteristics sections of the specification is not implied. Exposure to limiting values for extended periods may affect device reliability.

Application information — Applications that are described herein for any of these products are for illustrative purposes only. Philips Semiconductors make no representation or warranty that such applications will be suitable for the specified use without further testing or modification.

Disclaimers

Life support — These products are not designed for use in life support appliances, devices or systems where malfunction of these products can reasonably be expected to result in personal injury. Philips Semiconductors customers using or selling these products for use in such applications do so at their own risk and agree to fully indemnify Philips Semiconductors for any damages resulting from such application.

Right to make changes — Philips Semiconductors reserves the right to make changes, without notice, in the products, including circuits, standard cells, and/or software, described or contained herein in order to improve design and/or performance. Philips Semiconductors assumes no responsibility or liability for the use of any of these products, conveys no license or title under any patent, copyright, or mask work right to these products, and makes no representations or warranties that these products are free from patent, copyright, or mask work right infringement, unless otherwise specified.

Contact information

For additional information please visit http://www.semiconductors.philips.com. Fax: +31 40 27 24825

sales.addresses@www.semiconductors.philips.com

For sales offices addresses send e-mail to:

825

Document order number:

Date of release: 03-02

9397 750 09532

Let's make things better.



PHILIPS

© Koninklijke Philips Electronics N.V. 2002

All rights reserved. Printed in U.S.A.