PTN3360B

Enhanced performance HDMI/DVI level shifter

Rev. 02 — 8 October 2009

Product data sheet

1. General description

The PTN3360B is a high-speed level shifter device which converts four lanes of low-swing AC-coupled differential input signals to DVI v1.0 and HDMI v1.3a compliant open-drain current-steering differential output signals, up to 2.5 Gbit/s per lane. Each of these lanes provides a level-shifting differential buffer to translate from low-swing AC-coupled differential signaling on the source side, to TMDS-type DC-coupled differential current-mode signaling terminated into 50 Ω to 3.3 V on the sink side. Additionally, the PTN3360B provides a single-ended active buffer for voltage translation of the HPD signal from 5 V on the sink side to 3.3 V on the source side and provides a channel for level shifting of the DDC channel (consisting of a clock and a data line) between 3.3 V source-side and 5 V sink-side. The DDC channel is implemented using pass-gate technology providing level shifting as well as disablement (isolation between source and sink) of the clock and data lines.

The low-swing AC-coupled differential input signals to the PTN3360B typically come from a display source with multi-mode I/O, which supports multiple display standards, e.g., DisplayPort, HDMI and DVI. While the input differential signals are configured to carry DVI or HDMI coded data, they do not comply with the electrical requirements of the DVI v1.0 or HDMI v1.3a specification. By using PTN3360B, chip set vendors are able to implement such reconfigurable I/Os on multi-mode display source devices, allowing the support of multiple display standards while keeping the number of chip set I/O pins low. See Figure 1.


The PTN3360B main high-speed differential lanes feature low-swing self-biasing differential inputs which are compliant to the electrical specifications of *DisplayPort Standard v1.1* and/or *PCI Express Standard v1.1*, and open-drain current-steering differential outputs compliant to DVI v1.0 and HDMI v1.3a electrical specifications. The I²C-bus channel level-translates the DDC signals between 3.3 V (source) and 5.0 V (sink).

The PTN3360B is a fully featured HDMI as well as DVI level shifter. It is functionally equivalent to PTN3300A but provides higher speed performance and higher ESD robustness. The PTN3360B is also equivalent to PTN3360A with the exception that PTN3360B provides non-inverting level shifting on the HPD channel.

PTN3360B is powered from a single 3.3 V power supply consuming a small amount of power (120 mW typ.) and is offered in a 48-terminal HVQFN48 package.



Enhanced performance HDMI/DVI level shifter



Remark: TMDS clock and data lanes can be assigned arbitrarily and interchangeably to D[4:1].

Fig 1. Typical application system diagram

Enhanced performance HDMI/DVI level shifter

2. Features

2.1 High-speed TMDS level shifting

- Converts four lanes of low-swing AC-coupled differential input signals to DVI v1.0 and HDMI v1.3a compliant open-drain current-steering differential output signals
- TMDS level shifting operation up to 2.5 Gbit/s per lane (250 MHz character clock)
- Integrated 50 Ω termination resistors for self-biasing differential inputs
- Back-current safe outputs to disallow current when device power is off and monitor is on
- Disable feature to turn off TMDS inputs and outputs and to enter low-power state

2.2 DDC level shifting

- Integrated DDC level shifting (3.3 V source to 5 V sink side)
- 0 Hz to 400 kHz I²C-bus clock frequency
- Back-power safe sink-side terminals to disallow backdrive current when power is off or when DDC is not enabled

2.3 HPD level shifting

- HPD non-inverting level shift from 5 V on the sink side to 3.3 V on the source side, or from 0 V on the sink side to 0 V on the source side
- Integrated 200 k Ω pull-down resistor on HPD sink input guarantees 'input LOW' when no display is plugged in
- Back-power safe design on HPD_SINK to disallow backdrive current when power is off

2.4 General

- Power supply 3.3 V ± 10 %
- ESD resilience to 8 kV HBM, 500 V CDM
- Power-saving modes (using output enable)
- Back-current-safe design on all sink-side main link, DDC and HPD terminals
- Transparent operation: no re-timing or software configuration required

3. Ordering information


Table 1. Ordering information

Type number	Package	ckage							
	Name	Description	Version						
PTN3360BBS	HVQFN48	plastic thermal enhanced very thin quad flat package; no leads; 48 terminals; body $7\times7\times0.85~\text{mm}$	SOT619-1						

PTN3360B_2 © NXP B.V. 2009. All rights reserved.

Enhanced performance HDMI/DVI level shifter


4. Functional diagram



Enhanced performance HDMI/DVI level shifter

5. Pinning information

5.1 Pinning



pins must be connected to supply ground for proper device operation. For enhanced thermal, electrical, and board level performance, the exposed pad needs to be soldered to the board using a corresponding thermal pad on the board and for proper heat conduction through the board, thermal vias need to be incorporated in the PCB in the thermal pad region.

Fig 3. Pin configuration for HVQFN48

Enhanced performance HDMI/DVI level shifter

5.2 Pin description

Table 2. Pin description

Symbol	Pin	Туре	Description
OE_N, IN	_Dx and OUT_Dx sig	gnals	
OE_N	25	3.3 V low-voltage CMOS single-ended	Output Enable and power saving function for high-speed differential level shifter path.
		input	When OE_N = HIGH:
			IN_Dx termination = high-impedance
			OUT_Dx outputs = high-impedance; zero output current
			When OE_N = LOW:
			IN_Dx termination = 50Ω
			OUT_Dx outputs = active
IN_D4+	48	Self-biasing differential input	Low-swing differential input from display source with PCI Express electrical signalling. IN_D4+ makes a differential pair with IN_D4 The input to this pin must be AC coupled externally.
IN_D4-	47	Self-biasing differential input	Low-swing differential input from display source with PCI Express electrical signalling. IN_D4- makes a differential pair with IN_D4+. The input to this pin must be AC coupled externally.
IN_D3+	45	Self-biasing differential input	Low-swing differential input from display source with PCI Express electrical signalling. IN_D3+ makes a differential pair with IN_D3 The input to this pin must be AC coupled externally.
IN_D3-	44	Self-biasing differential input	Low-swing differential input from display source with PCI Express electrical signalling. IN_D3- makes a differential pair with IN_D3+. The input to this pin must be AC coupled externally.
IN_D2+	42	Self-biasing differential input	Low-swing differential input from display source with PCI Express electrical signalling. IN_D2+ makes a differential pair with IN_D2 The input to this pin must be AC coupled externally.
IN_D2-	41	Self-biasing differential input	Low-swing differential input from display source with PCI Express electrical signalling. IN_D2- makes a differential pair with IN_D2+. The input to this pin must be AC coupled externally.
IN_D1+	39	Self-biasing differential input	Low-swing differential input from display source with PCI Express electrical signalling. IN_D1+ makes a differential pair with IN_D1 The input to this pin must be AC coupled externally.
IN_D1-	38	Self-biasing differential input	Low-swing differential input from display source with PCI Express electrical signalling. IN_D1- makes a differential pair with IN_D1+. The input to this pin must be AC coupled externally.
OUT_D4+	- 13	TMDS differential output	HDMI compliant TMDS output. OUT_D4+ makes a differential pair with OUT_D4 OUT_D4+ is in phase with IN_D4+.
OUT_D4-	- 14	TMDS differential output	HDMI compliant TMDS output. OUT_D4- makes a differential pair with OUT_D4+. OUT_D4- is in phase with IN_D4
OUT_D3+	- 16	TMDS differential output	HDMI compliant TMDS output. OUT_D3+ makes a differential pair with OUT_D3 OUT_D3+ is in phase with IN_D3+.
OUT_D3-	- 17	TMDS differential output	HDMI compliant TMDS output. OUT_D3- makes a differential pair with OUT_D3+. OUT_D3- is in phase with IN_D3
OUT_D2+		TMDS differential output	HDMI compliant TMDS output. OUT_D2+ makes a differential pair with OUT_D2 OUT_D2+ is in phase with IN_D2+.
OUT_D2-	- 20	TMDS differential output	HDMI compliant TMDS output. OUT_D2- makes a differential pair with OUT_D2+. OUT_D2- is in phase with IN_D2

Enhanced performance HDMI/DVI level shifter

Table 2. Pin description ... continued

Symbol	Pin	Туре	Description
OUT_D1+	22	TMDS differential output	HDMI compliant TMDS output. OUT_D1+ makes a differential pair with OUT_D1 OUT_D1+ is in phase with IN_D1+.
OUT_D1-	23	TMDS differential output	HDMI compliant TMDS output. OUT_D1– makes a differential pair with OUT_D1+. OUT_D1– is in phase with IN_D1–.
HPD and DDC sig	gnals		
HPD_SINK	30	5 V CMOS single-ended input	0 V to 5 V (nominal) input signal. This signal comes from the DVI or HDMI sink. A HIGH value indicates that the sink is connected; a LOW value indicates that the sink is disconnected. HPD_SINK is pulled down by an integrated 200 $k\Omega$ pull-down resistor.
HPD_SOURCE	7	3.3 V CMOS single-ended output	0 V to 3.3 V (nominal) output signal. This is level-shifted non-inverted version of the HPD_SINK signal.
SCL_SOURCE	9	single-ended 3.3 V open-drain DDC I/O	$3.3\ \mbox{V}$ source-side DDC clock I/O. Pulled up by external termination to $3.3\ \mbox{V}.$
SDA_SOURCE	8	single-ended 3.3 V open-drain DDC I/O	$3.3\ \mbox{V}$ source-side DDC data I/O. Pulled up by external termination to $3.3\ \mbox{V}.$
SCL_SINK	28	single-ended 5 V open-drain DDC I/O	5 V sink-side DDC clock I/O. Pulled up by external termination to 5 V.
SDA_SINK	29	single-ended 5 V open-drain DDC I/O	5 V sink-side DDC data I/O. Pulled up by external termination to 5 V.
DDC_EN	32	3.3 V CMOS input	Enables the DDC buffer and level shifter.
			When DDC_EN = LOW, buffer/level shifter is disabled.
			When DDC_EN = HIGH, buffer and level shifter are enabled.
Supply and grou	nd		
V_{DD}	2, 11, 15, 21, 26, 33, 40, 46	3.3 V DC supply	Supply voltage; 3.3 V \pm 10 %.
V_{CC}	-		
GND[1]	1, 5, 12, 18, 24, 27, 31, 36, 37, 43	ground	Supply ground. All GND pins must be connected to ground for proper operation.
Feature control s	signals		
REXT	6	analog I/O	Current sense port used to provide an accurate current reference for the differential outputs OUT_Dx. For best output voltage swing accuracy, use of a 10 k Ω resistor (1 % tolerance) from this terminal to GND is recommended. May also be left open-circuit or tied to either V_DD or GND. See Section 6.2 for details.
Miscellaneous			
n.c.	3, 4, 10, 34, 35	no connection to the die	Not connected. May be left open-circuit or tied to GND or $\rm V_{\rm DD}$ either directly or via a resistor.

^[1] HVQFN48 package supply ground is connected to both GND pins and exposed center pad. GND pins must be connected to supply ground for proper device operation. For enhanced thermal, electrical, and board level performance, the exposed pad needs to be soldered to the board using a corresponding thermal pad on the board and for proper heat conduction through the board, thermal vias need to be incorporated in the PCB in the thermal pad region.

Enhanced performance HDMI/DVI level shifter

6. Functional description

Refer to Figure 2 "Functional diagram of PTN3360B".

The PTN3360B level shifts four lanes of low-swing AC-coupled differential input signals to DVI and HDMI compliant open-drain current-steering differential output signals, up to 2.5 Gbit/s per lane. It has integrated 50 Ω termination resistors for AC-coupled differential input signals. An enable signal OE_N can be used to turn off the TMDS inputs and outputs, thereby minimizing power consumption. The TMDS outputs, HPD_SINK input and DDC_SINK I/Os are back-power safe to disallow current flow from a powered sink while the PTN3360B is unpowered.

The PTN3360B's DDC channel provides passive level shifting, allowing 3.3 V source-side termination and 5 V sink-side termination. The PTN3360B offers back-power safe sink-side I/Os to disallow backdrive current from the DDC clock and data lines when power is off or when DDC is not enabled. An enable signal DCC_EN enables the DDC level shifter block.

The PTN3360B also provides voltage translation for the Hot Plug Detect (HPD) signal from 0 V to 5 V on the sink side, non-inverting and level-shifting to 0 V/3.3 V on the source side.

The PTN3360B does not re-time any data. It contains no state machines. No inputs or outputs of the device are latched or clocked. Because the PTN3360B acts as a transparent level shifter, no reset is required.

6.1 Enable and disable features

PTN3360B offers different ways to enable or disable functionality, using the Output Enable (OE_N) and DDC Enable (DDC_EN) inputs. Whenever the PTN3360B is disabled, the device will be in Standby mode and power consumption will be minimal; otherwise the PTN3360B will be in Active mode and power consumption will be nominal. These two inputs each affect the operation of PTN3360B differently: OE_N affects only the TMDS channels, and DDC_EN affects only the DDC channel. HPD_SINK does not affect either of the channels. The following sections and truth table describe their detailed operation.

6.1.1 Hot plug detect

The HPD channel of PTN3360B functions as a level-shifting buffer to pass the HPD logic signal from the display sink device (via input HPD_SINK) on to the display source device (via output HPD_SOURCE).

The output logic state of HPD_SOURCE output always follows the logic state of input HPD_SINK, regardless of whether the device is in Active or Standby mode.

Enhanced performance HDMI/DVI level shifter

6.1.2 Output Enable function (OE_N)

When input OE_N is asserted (active LOW), the IN_Dx and OUT_Dx signals are fully functional. Input termination resistors are enabled and the internal bias circuits are turned on.

When OE_N is de-asserted (inactive HIGH), the OUT_Dx outputs are in a high-impedance state and drive zero output current. The IN_Dx input buffers are disabled and IN_Dx termination is disabled. Power consumption is minimized.

Remark: Note that OE_N has no influence on the HPD_SINK input, HPD_SOURCE output, or the SCL and SDA level shifters. OE_N only affects the high-speed TMDS channel.

6.1.3 DDC channel enable function (DDC_EN)

The DDC_EN pin is active HIGH and can be used to isolate a badly behaved slave. When DDC_EN is LOW, the DDC channel is turned off. The DDC_EN input should never change state during an I²C-bus operation. Note that disabling DDC_EN during a bus operation will hang the bus, while enabling DDC_EN during bus traffic would corrupt the I²C-bus operation. Hence, DDC_EN should only be toggled while the bus is idle. (See I²C-bus specification).

Enhanced performance HDMI/DVI level shifter

6.1.4 Enable/disable truth table

Table 3. HPD_SINK, OE_N and DDC_EN enabling truth table

Inputs			Channels					
HPD_SINK	OE_N [1]	DDC_EN	IN_Dx	OUT_Dx ^[3]	DDC[4]	HPD_SOURCE[5]		
LOW	LOW	LOW	50 Ω termination to $V_{RX(bias)}$	enabled	high-impedance	LOW	Active; DDC disabled	
LOW	LOW	HIGH	$50~\Omega~termination \\ to~V_{RX(bias)}$	enabled	SDA_SINK connected to SDA_SOURCE and SCL_SINK connected to SCL_SOURCE	LOW	Active; DDC enabled	
LOW	HIGH	LOW	high-impedance	high-impedance; zero output current	high-impedance	LOW	Standby	
LOW	HIGH	HIGH	high-impedance	high-impedance; zero output current	SDA_SINK connected to SDA_SOURCE and SCL_SINK connected to SCL_SOURCE	LOW	Standby DDC enabled	
HIGH	LOW	LOW	50 Ω termination to $V_{RX(bias)}$	enabled	high-impedance	HIGH	Active; DDC disabled	
HIGH	LOW	HIGH	50 Ω termination to $V_{RX(bias)}$	enabled	SDA_SINK connected to SDA_SOURCE and SCL_SINK connected to SCL_SOURCE	HIGH	Active; DDC enabled	
HIGH	HIGH	LOW	high-impedance	high-impedance; zero output current	high-impedance	HIGH	Standby	
HIGH	HIGH	HIGH	high-impedance	high-impedance; zero output current	SDA_SINK connected to SDA_SOURCE and SCL_SINK connected to SCL_SOURCE	HIGH	Standby, DDC enabled	

^[1] A HIGH level on input OE_N disables only the TMDS channels.

^[2] A LOW level on input DDC_EN disables only the DDC channel.

^[3] OUT_Dx channels 'enabled' means outputs OUT_Dx toggling in accordance with IN_Dx differential input voltage switching.

^[4] DDC channel 'enabled' means SDA_SINK is connected to SDA_SOURCE and SCL_SINK is connected to SCL_SOURCE.

^[5] The HPD_SOURCE output logic state always follows the HPD_SINK input logic state.

Enhanced performance HDMI/DVI level shifter

6.2 Analog current reference

The REXT pin (pin 6) is an analog current sense port used to provide an accurate current reference for the differential outputs OUT_Dx. For best output voltage swing accuracy, use of a 10 k Ω resistor (1 % tolerance) connected between this terminal and GND is recommended.

If an external 10 k Ω \pm 1 % resistor is not used, this pin can be left open-circuit, or connected to GND or V_{DD}, either directly (0 Ω) or using pull-up or pull-down resistors of value less than 10 k Ω . In any of these cases, the output will function normally but at reduced accuracy over voltage and temperature of the following parameters: output levels (V_{OL}), differential output voltage swing, and rise and fall time accuracy.

6.3 Backdrive current protection

The PTN3360B is designed for backdrive prevention on all sink-side TMDS outputs, sink-side DDC I/Os and the HPD_SINK input. This supports user scenarios where the display is connected and powered, but the PTN3360B is unpowered. In these cases, the PTN3360B will sink no more than a negligible amount of leakage current, and will block the display (sink) termination network from driving the power supply of the PTN3360B or that of the inactive DVI or HDMI source.

Enhanced performance HDMI/DVI level shifter

7. Limiting values

Table 4. Limiting values

In accordance with the Absolute Maximum Rating System (IEC 60134).

Symbol	Parameter	Conditions	Min	Max	Unit
V_{DD}	supply voltage		-0.3	+4.6	V
VI	input voltage	3.3 V CMOS inputs	-0.3	$V_{DD} + 0.5$	V
		5.0 V CMOS inputs	-0.3	6.0	V
T _{stg}	storage temperature		-65	+150	°C
V_{ESD}	electrostatic discharge	HBM	<u>[1]</u> -	8000	V
	voltage	CDM	[2] _	500	V

^[1] Human Body Model: ANSI/EOS/ESD-S5.1-1994, standard for ESD sensitivity testing, Human Body Model - Component level; Electrostatic Discharge Association, Rome, NY, USA.

8. Recommended operating conditions

Table 5. Recommended operating conditions

Symbol	Parameter	Conditions		Min	Тур	Max	Unit
V_{DD}	supply voltage			3.0	3.3	3.6	V
VI	input voltage	3.3 V CMOS inputs		0	-	3.6	V
		5.0 V CMOS inputs		0	-	5.5	V
$V_{I(AV)}$	average input voltage	IN_Dn+, IN_Dn- inputs	<u>[1]</u>	-	0	-	V
R _{ref(ext)}	external reference resistance ^[2]	connected between pin REXT (pin 6) and GND		-	10 ± 1 %	-	kΩ
T _{amb}	ambient temperature	operating in free air		-40	-	+85	°C

^[1] Input signals to these pins must be AC-coupled.

8.1 Current consumption

Table 6. Current consumption

Symbol	Parameter	Conditions	Min	Тур	Max	Unit
I _{DD}	supply current	OE_N = 0; Active mode	10	35	50	mA
		OE_N = 1 and DDC_EN = 0; Standby mode	-	0.8	1.5	mA

PTN3360B_2 © NXP B.V. 2009. All rights reserved.

 ^[2] Charged-Device Model: ANSI/EOS/ESD-S5.3-1-1999, standard for ESD sensitivity testing, Charged-Device Model - Component level; Electrostatic Discharge Association, Rome, NY, USA.

^[2] Operation without external reference resistor is possible but will result in reduced output voltage swing accuracy. For details, see Section 6.2.

Enhanced performance HDMI/DVI level shifter

9. Characteristics

9.1 Differential inputs

Table 7. Differential input characteristics for IN_Dx signals

Symbol	Parameter	Conditions		Min	Тур	Max	Unit
UI	unit interval ^[1]		[2]	360	-	4000	ps
$V_{RX_DIFFp-p}$	differential input peak-to-peak voltage		[3]	0.175	-	1.200	V
T _{RX_EYE}	receiver eye time	minimum eye width at IN_Dx input pair		8.0	-	-	UI
$V_{i(cm)M(AC)}\\$	peak common-mode input voltage (AC)	includes all frequencies above 30 kHz	<u>[4]</u>	-	-	100	mV
Z _{RX_DC}	DC input impedance			40	50	60	Ω
V _{RX(bias)}	bias receiver voltage		[5]	1.0	1.2	1.4	V
$Z_{I(se)}$	single-ended input impedance	inputs in high-impedance state	[6]	100	-	-	kΩ

^[1] UI (unit interval) = t_{bit} (bit time).

^[2] UI is determined by the display mode. Nominal bit rate ranges from 250 Mbit/s to 2.5 Gbit/s per lane. Nominal UI at 2.5 Gbit/s = 400 ps. 360 ps = 400 ps - 10 %.

^[3] $V_{RX_DIFFp-p} = 2 \times |V_{RX_D+} - V_{RX_D-}|$. Applies to IN_Dx signals.

 $[\]begin{split} [4] \quad & V_{i(cm)M(AC)} = |V_{RX_D+} + V_{RX_D-}| \: / \: 2 - V_{RX(cm)}. \\ & V_{RX(cm)} = DC \: (avg) \: \text{of} \: |V_{RX_D+} + V_{RX_D-}| \: / \: 2. \end{split}$

^[5] Intended to limit power-up stress on chip set's PCIe output buffers.

^[6] Differential inputs will switch to a high-impedance state when OE_N is HIGH.

Enhanced performance HDMI/DVI level shifter

9.2 Differential outputs

The level shifter's differential outputs are designed to meet HDMI version 1.3 and DVI version 1.0 specifications.

Table 8. Differential output characteristics for OUT_Dx signals

Symbol	Parameter	Conditions		Min	Тур	Max	Unit
V _{OH(se)}	single-ended HIGH-level output voltage		<u>[1]</u>	$V_{TT} - 0.01$	V_{TT}	V _{TT} + 0.01	V
V _{OL(se)}	single-ended LOW-level output voltage		[2]	V _{TT} – 0.60	V _{TT} – 0.50	$V_{TT} - 0.40$	V
$\Delta V_{O(se)}$	single-ended output voltage variation	logic 1 and logic 0 state applied respectively to differential inputs IN_Dn; R _{ref(ext)} connected; see Table 5	[3]	400	500	600	mV
l _{OZ}	OFF-state output current	single-ended		-	-	10	μΑ
t _r	rise time	20 % to 80 %	<u>[4]</u>	75	-	160	ps
t _f	fall time	80 % to 20 %	<u>[4]</u>	75	-	160	ps
t _{sk}	skew time	intra-pair	<u>[5]</u>	-	-	10	ps
		inter-pair	<u>[6]</u>	-	-	250	ps
t _{jit}	jitter time	jitter contribution	<u>[7]</u>	-	-	7.4	ps

^[1] V_{TT} is the DC termination voltage in the HDMI or DVI sink. V_{TT} is nominally 3.3 V.

- [2] The open-drain output pulls down from V_{TT} .
- [3] Swing down from TMDS termination voltage (3.3 V \pm 10 %).
- [4] Maximum rise/fall time at 2.5 Gbit/s = 400 ps. 360 ps = 400 ps 10 %.
- [5] This differential skew budget is in addition to the skew presented between IN_D+ and IN_D- paired input pins.
- [6] This lane-to-lane skew budget is in addition to skew between differential input pairs.
- [7] Jitter budget for differential signals as they pass through the level shifter.

9.3 HPD_SINK input, HPD_SOURCE output

Table 9. HPD characteristics

Symbol	Parameter	Conditions		Min	Тур	Max	Unit
V_{IH}	HIGH-level input voltage	HPD_SINK	<u>[1]</u>	2.0	5.0	5.3	V
V_{IL}	LOW-level input voltage	HPD_SINK		0	-	0.8	V
I_{LI}	input leakage current	HPD_SINK	[2]	-	-	10	μΑ
V_{OH}	HIGH-level output voltage	HPD_SOURCE		2.5	-	V_{DD}	V
V_{OL}	LOW-level output voltage	HPD_SOURCE		0	-	0.2	V
t _{PD}	propagation delay	from HPD_SINK to HPD_SOURCE; 50 % to 50 %	[3]	-	-	200	ns
t _t	transition time	HPD_SOURCE rise/fall; 10 % to 90 %	<u>[4]</u>	1	-	20	ns
R_{pd}	pull-down resistance	HPD_SINK input pull-down resistor	[5]	100	200	300	kΩ

^[1] Low-speed input changes state on cable plug/unplug.

PTN3360B_2 © NXP B.V. 2009. All rights reserved.

^[2] Measured with HPD_SINK at V_{IH} maximum and V_{IL} minimum.

^[3] Time from HPD_SINK changing state to HPD_SOURCE changing state. Includes HPD_SOURCE rise/fall time.

^[4] Time required to transition from V_{OH} to V_{OL} or from V_{OL} to V_{OH} .

^[5] Guarantees HPD_SINK is LOW when no display is plugged in.

Enhanced performance HDMI/DVI level shifter

9.4 OE_N, DDC_EN inputs

Table 10. OE_N, DDC_EN and DDET input characteristics

Symbol	Parameter	Conditions	Min	Тур	Max	Unit
V_{IH}	HIGH-level input voltage		2.0	-		V
V_{IL}	LOW-level input voltage		-	-	0.8	V
I _{LI}	input leakage current	OE_N pin	[1] _	-	10	μΑ

^[1] Measured with input at V_{IH} maximum and V_{IL} minimum.

9.5 DDC characteristics

Table 11. DDC characteristics

Symbol	Parameter	Conditions	Min	Тур	Max	Unit
f _{clk}	clock frequency	SCL_SOURCE, SDA_SOURCE, SCL_SINK, SDA_SINK	-	-	400	kHz
ON state	(DDC_EN = HIGH)					
R _{ON}	ON resistance	pass gate in ON state; $I_O = 15$ mA; $V_O = 0.4$ V	-	7	30	Ω
$V_{O(sw)}$	switch output voltage	source side; $V_I = 3.3 \text{ V}$; $I_O = -100 \mu\text{A}$	1.7	2.1	2.5	V
		sink side; V_I = 5.0 V; I_O = -100 μA	1.7	2.1	2.5	V
C _{io}	input/output capacitance	$V_1 = 3.3 \text{ V}$	-	5	10	pF
OFF state	e (DDC_EN = LOW)					
I _{LI}	input leakage current	source side; $0 \text{ V} < \text{V}_{\text{I}} < 3.3 \text{ V}$	-10	-	+10	μΑ
		sink side; $0 \text{ V} < \text{V}_{\text{I}} < 5.0 \text{ V}$	-10	-	+10	μΑ
C _{io}	input/output capacitance	$V_1 = 3.3 \text{ V}$	-	1	5	pF

Enhanced performance HDMI/DVI level shifter

10. Package outline

HVQFN48: plastic thermal enhanced very thin quad flat package; no leads; 48 terminals; body 7 x 7 x 0.85 mm

SOT619-1




Fig 4. Package outline SOT619-1 (HVQFN48)

Enhanced performance HDMI/DVI level shifter

11. Soldering of SMD packages

This text provides a very brief insight into a complex technology. A more in-depth account of soldering ICs can be found in Application Note *AN10365 "Surface mount reflow soldering description"*.

11.1 Introduction to soldering

Soldering is one of the most common methods through which packages are attached to Printed Circuit Boards (PCBs), to form electrical circuits. The soldered joint provides both the mechanical and the electrical connection. There is no single soldering method that is ideal for all IC packages. Wave soldering is often preferred when through-hole and Surface Mount Devices (SMDs) are mixed on one printed wiring board; however, it is not suitable for fine pitch SMDs. Reflow soldering is ideal for the small pitches and high densities that come with increased miniaturization.

11.2 Wave and reflow soldering

Wave soldering is a joining technology in which the joints are made by solder coming from a standing wave of liquid solder. The wave soldering process is suitable for the following:

- Through-hole components
- Leaded or leadless SMDs, which are glued to the surface of the printed circuit board

Not all SMDs can be wave soldered. Packages with solder balls, and some leadless packages which have solder lands underneath the body, cannot be wave soldered. Also, leaded SMDs with leads having a pitch smaller than ~0.6 mm cannot be wave soldered, due to an increased probability of bridging.

The reflow soldering process involves applying solder paste to a board, followed by component placement and exposure to a temperature profile. Leaded packages, packages with solder balls, and leadless packages are all reflow solderable.

Key characteristics in both wave and reflow soldering are:

- Board specifications, including the board finish, solder masks and vias
- · Package footprints, including solder thieves and orientation
- The moisture sensitivity level of the packages
- Package placement
- Inspection and repair
- Lead-free soldering versus SnPb soldering

11.3 Wave soldering

Key characteristics in wave soldering are:

- Process issues, such as application of adhesive and flux, clinching of leads, board transport, the solder wave parameters, and the time during which components are exposed to the wave
- Solder bath specifications, including temperature and impurities

Enhanced performance HDMI/DVI level shifter

11.4 Reflow soldering

Key characteristics in reflow soldering are:

- Lead-free versus SnPb soldering; note that a lead-free reflow process usually leads to higher minimum peak temperatures (see <u>Figure 5</u>) than a SnPb process, thus reducing the process window
- Solder paste printing issues including smearing, release, and adjusting the process window for a mix of large and small components on one board
- Reflow temperature profile; this profile includes preheat, reflow (in which the board is heated to the peak temperature) and cooling down. It is imperative that the peak temperature is high enough for the solder to make reliable solder joints (a solder paste characteristic). In addition, the peak temperature must be low enough that the packages and/or boards are not damaged. The peak temperature of the package depends on package thickness and volume and is classified in accordance with Table 12 and 13

Table 12. SnPb eutectic process (from J-STD-020C)

Package thickness (mm)	Package reflow temperature (°C) Volume (mm³)	
	< 350	≥ 350
< 2.5	235	220
≥ 2.5	220	220


Table 13. Lead-free process (from J-STD-020C)

Package thickness (mm)	Package reflow temperature (°C)		
	Volume (mm³)		
	< 350	350 to 2000	> 2000
< 1.6	260	260	260
1.6 to 2.5	260	250	245
> 2.5	250	245	245

Moisture sensitivity precautions, as indicated on the packing, must be respected at all times.

Studies have shown that small packages reach higher temperatures during reflow soldering, see Figure 5.

Enhanced performance HDMI/DVI level shifter



For further information on temperature profiles, refer to Application Note *AN10365* "Surface mount reflow soldering description".

12. Abbreviations

Table 14. Abbreviations

Acronym	Description
CDM	Charged-Device Model
DDC	Data Display Channel
DVI	Digital Visual Interface
ESD	ElectroStatic Discharge
НВМ	Human Body Model
HDMI	High-Definition Multimedia Interface
HPD	Hot Plug Detect
I ² C-bus	Inter-IC bus
I/O	Input/Output
TMDS	Transition Minimized Differential Signaling

Enhanced performance HDMI/DVI level shifter

13. Revision history

Table 15. Revision history

OE_N is LOW." to " when OE_N is HIGH."						
Modifications: • Section 6 "Functional description": - 3 rd paragraph: 1 st sentence re-written; deleted 2 nd and 3 rd sentences. - 5 th paragraph, 2 nd sentence: deleted phrase "except for the DDC/l²C-bus block" • Table 7 "Differential input characteristics for IN_Dx signals", Table note [6]: changed from ". OE_N is LOW." to " when OE_N is HIGH." • Table 8 "Differential output characteristics for OUT_Dx signals", Table note [7]: deleted sentence	Document ID	Release date	Data sheet status	Change notice	Supersedes	
 3rd paragraph: 1st sentence re-written; deleted 2nd and 3rd sentences. 5th paragraph, 2nd sentence: deleted phrase "except for the DDC/I²C-bus block" Table 7 "Differential input characteristics for IN_Dx signals", Table note [6]: changed from ". OE_N is LOW." to " when OE_N is HIGH." Table 8 "Differential output characteristics for OUT_Dx signals", Table note [7]: deleted sentence 	PTN3360B_2	20091008	Product data sheet	-	PTN3360B_1	
sentence	Modifications:	 3rd paragraph: 1st sentence re-written; deleted 2nd and 3rd sentences. 5th paragraph, 2nd sentence: deleted phrase "except for the DDC/I²C-bus block" Table 7 "Differential input characteristics for IN_Dx signals", Table note [6]: changed from " when 				
PTN3360B_1 20090504 Product data sheet		 <u>Table 8 "Differential output characteristics for OUT_Dx signals"</u>, <u>Table note [7]</u>: deleted second sentence 				
	PTN3360B_1	20090504	Product data sheet	-	-	

Enhanced performance HDMI/DVI level shifter

14. Legal information

14.1 Data sheet status

Document status[1][2]	Product status[3]	Definition
Objective [short] data sheet	Development	This document contains data from the objective specification for product development.
Preliminary [short] data sheet	Qualification	This document contains data from the preliminary specification.
Product [short] data sheet	Production	This document contains the product specification.

- [1] Please consult the most recently issued document before initiating or completing a design.
- [2] The term 'short data sheet' is explained in section "Definitions"
- [3] The product status of device(s) described in this document may have changed since this document was published and may differ in case of multiple devices. The latest product status information is available on the Internet at URL http://www.nxp.com.

14.2 Definitions

Draft — The document is a draft version only. The content is still under internal review and subject to formal approval, which may result in modifications or additions. NXP Semiconductors does not give any representations or warranties as to the accuracy or completeness of information included herein and shall have no liability for the consequences of use of such information.

Short data sheet — A short data sheet is an extract from a full data sheet with the same product type number(s) and title. A short data sheet is intended for quick reference only and should not be relied upon to contain detailed and full information. For detailed and full information see the relevant full data sheet, which is available on request via the local NXP Semiconductors sales office. In case of any inconsistency or conflict with the short data sheet, the full data sheet shall prevail.

14.3 Disclaimers

General — Information in this document is believed to be accurate and reliable. However, NXP Semiconductors does not give any representations or warranties, expressed or implied, as to the accuracy or completeness of such information and shall have no liability for the consequences of use of such information.

Right to make changes — NXP Semiconductors reserves the right to make changes to information published in this document, including without limitation specifications and product descriptions, at any time and without notice. This document supersedes and replaces all information supplied prior to the publication hereof.

Suitability for use — NXP Semiconductors products are not designed, authorized or warranted to be suitable for use in medical, military, aircraft, space or life support equipment, nor in applications where failure or malfunction of an NXP Semiconductors product can reasonably be expected to result in personal injury, death or severe property or environmental damage. NXP Semiconductors accepts no liability for inclusion and/or use of NXP Semiconductors products in such equipment or applications and therefore such inclusion and/or use is at the customer's own risk.

Applications — Applications that are described herein for any of these products are for illustrative purposes only. NXP Semiconductors makes no representation or warranty that such applications will be suitable for the specified use without further testing or modification.

Limiting values — Stress above one or more limiting values (as defined in the Absolute Maximum Ratings System of IEC 60134) may cause permanent damage to the device. Limiting values are stress ratings only and operation of the device at these or any other conditions above those given in the Characteristics sections of this document is not implied. Exposure to limiting values for extended periods may affect device reliability.

Terms and conditions of sale — NXP Semiconductors products are sold subject to the general terms and conditions of commercial sale, as published at http://www.nxp.com/profile/terms, including those pertaining to warranty, intellectual property rights infringement and limitation of liability, unless explicitly otherwise agreed to in writing by NXP Semiconductors. In case of any inconsistency or conflict between information in this document and such terms and conditions, the latter will prevail.

No offer to sell or license — Nothing in this document may be interpreted or construed as an offer to sell products that is open for acceptance or the grant, conveyance or implication of any license under any copyrights, patents or other industrial or intellectual property rights.

Export control — This document as well as the item(s) described herein may be subject to export control regulations. Export might require a prior authorization from national authorities.

14.4 Licenses

Purchase of NXP ICs with HDMI technology

Use of an NXP IC with HDMI technology in equipment that complies with the HDMI standard requires a license from HDMI Licensing LLC, 1060 E. Arques Avenue Suite 100, Sunnyvale CA 94085, USA, e-mail: admin@hdmi.org.

14.5 Trademarks

Notice: All referenced brands, product names, service names and trademarks are the property of their respective owners.

15. Contact information

For more information, please visit: http://www.nxp.com

For sales office addresses, please send an email to: salesaddresses@nxp.com

PTN3360B_2 © NXP B.V. 2009. All rights reserved.

PTN3360B NXP Semiconductors


Enhanced performance HDMI/DVI level shifter

16. Contents

1	General description	1
2	Features	3
2.1	High-speed TMDS level shifting	
2.2	DDC level shifting	
2.3	HPD level shifting	
2.4	General	
3	Ordering information	
4	Functional diagram	4
5	Pinning information	5
5.1	Pinning	
5.2	Pin description	6
6	Functional description	
6.1	Enable and disable features	
6.1.1	Hot plug detect	
6.1.2	Output Enable function (OE_N)	
6.1.3	DDC channel enable function (DDC_EN)	
6.1.4	Enable/disable truth table	
6.2 6.3	Analog current reference	
o.s 7	·	
	Limiting values	
8	Recommended operating conditions	
8.1	Current consumption	
9	Characteristics	
9.1	Differential inputs	
9.2	Differential outputs	
9.3 9.4	HPD_SINK input, HPD_SOURCE output OE_N, DDC_EN inputs	
9. 4 9.5	DDC characteristics	
10	Package outline	
11	Soldering of SMD packages	
11 11.1	Introduction to soldering	
11.1 11.2	Wave and reflow soldering	
11.3	Wave soldering	
11.4	Reflow soldering	
12	Abbreviations	
13	Revision history	
14	Legal information	
14.1	Data sheet status	
14.2	Definitions	
14.3	Disclaimers	
14.4	Licenses	
14.5	Trademarks	
15	Contact information	. 21
16	Contents	. 22

Please be aware that important notices concerning this document and the product(s) described herein, have been included in section 'Legal information'.





All rights reserved.