

# **PCA8565**

# Real time clock/calendar Rev. 4 — 5 December 2014

**Product data sheet** 

#### **General description** 1.

The PCA8565 is a CMOS<sup>1</sup> real time clock and calendar optimized for low power consumption. A programmable clock output, interrupt output and voltage-low detector are also provided. All address and data are transferred serially via a two-line bidirectional I<sup>2</sup>C-bus. Maximum bus speed is 400 kbit/s. The built-in word address register is incremented automatically after each written or read data byte.

For a selection of NXP Real-Time Clocks, see Table 36 on page 40

#### **Features and benefits** 2.

- AEC-Q100 compliant (PCA8565TS) for automotive applications
- Provides year, month, day, weekday, hours, minutes and seconds based on a 32.768 kHz quartz crystal
- Clock operating voltage: 0.9 V to 5.5 V at room temperature
- Extended operating temperature range: -40 °C to +125 °C
- Low current; typical 0.65 μA at V<sub>DD</sub> = 3.0 V and T<sub>amb</sub> = 25 °C
- 400 kHz two-wire I<sup>2</sup>C-bus interface (at V<sub>DD</sub> = 1.8 V to 5.5 V)
- Programmable clock output for peripheral devices (32.768 kHz, 1.024 kHz, 32 Hz and 1 Hz)
- Alarm and timer functions
- Internal power-on reset
- I<sup>2</sup>C-bus slave address: read A3h and write A2h
- Open-drain interrupt pin
- One integrated oscillator capacitor

### **Applications**

- Automotive
- Industrial
- Other applications that require a wide operating temperature range

The definition of the abbreviations and acronyms used in this data sheet can be found in Section 22.



#### Real time clock/calendar

# 4. Ordering information

Table 1. Ordering information

Type number			
	Name	Description	Version
PCA8565TS	TSSOP8	plastic thin shrink small outline package; 8 leads; body width 3 mm	SOT505-1

### 4.1 Ordering options

#### Table 2. Ordering options

Product type number	Orderable part number	Sales item (12NC)	Delivery form	IC revision
PCA8565TS/1	PCA8565TS/1,118	935272132118	tape and reel, 13 inch	1
PCA8565TS/S410/1	PCA8565TS/S410/1,5	935273247518	tape and reel, 13 inch, dry pack	1


### 5. Marking

#### Table 3. Marking codes

Type number	Marking code
PCA8565TS	8565

Real time clock/calendar


### 6. Block diagram



Real time clock/calendar

### 7. Pinning information

### 7.1 Pinning



### 7.2 Pin description

#### Table 4. Pin description

Input or input/output pins must always be at a defined level ( $V_{SS}$  or  $V_{DD}$ ) unless otherwise specified.

Symbol Pin PCA8565TS		Description				
OSCI	1	oscillator input				
OSCO	2	scillator output				
ĪNT	3	interrupt output (open-drain; active LOW)				
$V_{SS}$	4	ground				
SDA	5	serial data I/O				
SCL	6	serial clock input				
CLKOUT	7	clock output, open-drain				
$V_{DD}$	8	positive supply voltage				

Real time clock/calendar

### 8. Functional description

The PCA8565 contains sixteen 8-bit registers with an auto-incrementing address register, an on-chip 32.768 kHz oscillator with one integrated capacitor, a frequency divider which provides the source clock for the Real Time Clock (RTC), a programmable clock output, a timer, an alarm, a voltage-low detector and a 400 kHz I<sup>2</sup>C-bus interface.

All 16 registers are designed as addressable 8-bit registers although not all bits are implemented:

- The first two registers (memory address 00h and 01h) are used as control and status registers
- The registers at memory addresses 02h through 08h are used as counters for the clock function (seconds up to years counters)
- Address locations 09h through 0Ch contain alarm registers which define the conditions for an alarm
- The register at address 0Dh controls the CLKOUT output frequency
- At address 0Eh is the timer control register and address 0Fh contains the timer value

The arrays SECONDS, MINUTES, HOURS, DAYS, WEEKDAYS, MONTHS, YEARS as well as the bit fields MINUTE\_ALARM, HOUR\_ALARM, DAY\_ALARM and WEEKDAY\_ALARM are all coded in Binary Coded Decimal (BCD) format.

When one of the RTC registers is written or read the contents of all time counters are frozen. This prevents faulty writing or reading of the clock or calendar during a carry condition (see Section 9.5.3).

#### Real time clock/calendar

### 8.1 Register overview

Table 5. Register overview and control bits default values

Bit positions labeled as - are not implemented. Bit positions labeled as N should always be written with logic 0. Reset values are shown in <u>Table 8</u>.

Address	Register name	Bit							
		7	6	5	4	3	2	1	0
Control reg	isters	,		'					
00h	Control_1	TEST1	N	STOP	N	TESTC	N	N	N
01h	Control_2	N	N	N	TI_TP	AF	TF	AIE	TIE
Time and d	ate registers	,			•				
02h	Seconds	VL	VL SECONDS (0 to 59)						
03h	Minutes	-	MINUTE	S (0 to 59)					
04h	Hours	-	- HOURS (0 to 23)						
05h	Days	-	-	DAYS (1 to 31)					
06h	Weekdays	-	-	-	-	-	WEEKDA	YS (0 to 6	)
07h	Months_century	С	-	-	MONTHS	6 (1 to 12)			
08h	Years	YEARS	(0 to 99)	'					
Alarm regis	sters								
09h	Minute_alarm	AE_M	MINUTE	_ALARM (0	to 59)				
0Ah	Hour_alarm	AE_H	-	HOUR_A	LARM (0 to	23)			
0Bh	Day_alarm	AE_D	-	DAY_ALA	ARM (1 to 3	31)			
0Ch	Weekday_alarm	AE_W	-	-	-	-	WEEKDA	Y_ALARN	l (0 to 6)
CLKOUT co	ontrol register			1	1	1	1		
0Dh	CLKOUT_control	FE	-	-	-	-	-	FD	
Timer regis	ters		1		1	1	-	1	
0Eh	Timer_control	TE	-	-	-	-	-	TD	
0Fh	Timer	COUNTI	DOWN_TIM	1ER					

#### Real time clock/calendar

### 8.2 Control registers

### 8.2.1 Register Control\_1

Table 6. Register Control\_1 (address 00h) bits description

		-	
Bit	Symbol	Value	Description
7	TEST1	0[1]	normal mode
		1	EXT_CLK test mode
6	N	0[2]	default value
5	STOP	0[1]	RTC source clock runs
		1	all RTC divider chain flip-flops are asynchronously set to logic 0;
			the RTC clock is stopped (CLKOUT at 32.768 kHz is still available)
4	N	0[2]	default value
3	TESTC	0	power-on reset override facility is disabled;
			set to logic 0 for normal operation
		1 <u>[1]</u>	power-on reset override may be enabled
2 to 0	N	000[2]	default value

<sup>[1]</sup> Default value.

#### 8.2.2 Register Control\_2

Table 7. Register Control 2 (address 01h) bits description

Bit	Symbol	Value	Description
7 to 5	N	000[1]	default value
4	4 TI_TP		INT is active when TF is active (subject to the status of TIE)
			INT pulses active according to <u>Table 29</u> (subject to the status of TIE);
			Remark: note that if AF and AIE are active then INT will be permanently active
3	3 AF		alarm flag inactive
		1	alarm flag active
2	TF	0[2]	timer flag inactive
		1	timer flag active
1	AIE	0[2]	alarm interrupt disabled
			alarm interrupt enabled
0	) TIE		timer interrupt disabled
		1	timer interrupt enabled

<sup>[1]</sup> Bits labeled as N should always be written with logic 0.

<sup>[2]</sup> Bits labeled as N should always be written with logic 0.

<sup>[2]</sup> Default value.

Real time clock/calendar

#### 8.3 Reset

The PCA8565 includes an internal reset circuit which is active whenever the oscillator is stopped. In the reset state the I<sup>2</sup>C-bus logic is initialized including the address pointer. All other registers are set according to <u>Table 8</u>.

Table 8. Register reset values[1]

Address	Register name	Bit							
		7	6	5	4	3	2	1	0
00h	Control_1	0	0	0	0	1	0	0	0
01h	Control_2	Х	х	0	0	0	0	0	0
02h	Seconds	1	х	Х	Х	х	Х	х	х
03h	Minutes	1	х	Х	Х	х	Х	х	х
04h	Hours	х	х	х	х	х	х	х	х
05h	Days	х	Х	х	Х	х	х	Х	х
06h	Weekdays	х	х	х	х	х	х	х	х
07h	Months_century	х	х	х	х	х	х	х	х
08h	Years	х	х	х	х	х	х	х	х
09h	Minute_alarm	1	х	х	х	х	х	х	х
0Ah	Hour_alarm	1	х	х	х	х	х	х	х
0Bh	Day_alarm	1	х	х	х	х	х	х	х
0Ch	Weekday_alarm	1	х	х	х	х	х	х	х
0Dh	CLKOUT_control	1	х	х	х	х	х	0	0
0Eh	Timer_control	0	х	х	х	х	х	1	1
0Fh	Timer	х	Х	х	Х	х	х	Х	х


<sup>[1]</sup> Registers labeled 'x' are undefined at power-on and unchanged by subsequent resets.

#### 8.3.1 Power-On Reset (POR) override

The POR duration is directly related to the crystal oscillator start-up time. Due to the long start-up times experienced by these types of circuits, a mechanism has been built in to disable the POR and hence speed up on-board test of the device. The setting of this mode requires that the I<sup>2</sup>C-bus pins, SDA and SCL, be toggled in a specific order as shown in Figure 3. All timings are required minimums.

Once the override mode has been entered, the device immediately stops being reset and normal operation may commence i.e. entry into the EXT\_CLK test mode via I<sup>2</sup>C-bus access. The override mode may be cleared by writing a logic 0 to TESTC. TESTC must be set to logic 1 before re-entry into the override mode is possible. Setting TESTC to logic 0 during normal operation has no effect except to prevent entry into the POR override mode.

Real time clock/calendar



#### 8.4 Time and date registers

The majority of the registers are coded in the BCD format to simplify application use.

#### 8.4.1 Register Seconds

Table 9. Register Seconds (address 02h) bits description

Bit	Symbol	Value	Place value	Description
7	VL	0	-	clock integrity is guaranteed
		1[1]	-	integrity of the clock information is not guaranteed
6 to 4	SECONDS	0 to 5	ten's place	actual seconds coded in BCD format
3 to 0		0 to 9	unit place	

<sup>[1]</sup> Start-up value.

Table 10. Seconds coded in BCD format


Seconds value in	Upper-dig	it (ten's pla	ace)	Digit (unit place)			
decimal	Bit 6	Bit 5	Bit 4	Bit 3	Bit 2	Bit 1	Bit 0
00	0	0	0	0	0	0	0
01	0	0	0	0	0	0	1
02	0	0	0	0	0	1	0
:							
09	0	0	0	1	0	0	1
10	0	0	1	0	0	0	0
:							
58	1	0	1	1	0	0	0
59	1	0	1	1	0	0	1

#### 8.4.1.1 Voltage-low detector

The PCA8565 has an on-chip voltage-low detector. When  $V_{DD}$  drops below  $V_{low}$ , bit VL in the Seconds register is set to indicate that the integrity of the clock information is no longer guaranteed. The VL flag is cleared by command.

Bit VL is intended to detect the situation when  $V_{DD}$  is decreasing slowly, for example under battery operation. Should  $V_{DD}$  reach  $V_{low}$  before power is re-asserted then bit VL is set. This indicates that the time may be corrupt (see Figure 4).

#### Real time clock/calendar



#### 8.4.2 Register Minutes

Table 11. Register Minutes (address 03h) bits description

Bit	Symbol	Value	Place value	Description
7	-	-	-	unused
6 to 4	MINUTES	0 to 5	ten's place	actual minutes coded in BCD format
3 to 0		0 to 9	unit place	

#### 8.4.3 Register Hours

Table 12. Register Hours (address 04h) bits description

Bit	Symbol	Value	Place value	Description
7 to 6	-	-	-	unused
5 to 4	HOURS	0 to 2	ten's place	actual hours coded in BCD format
3 to 0		0 to 9	unit place	

#### 8.4.4 Register Days

Table 13. Register Days (address 05h) bits description

Bit	Symbol	Value	Place value	Description
7 to 6	-	-	-	unused
5 to 4	DAYS[1]	0 to 3	ten's place	actual day coded in BCD format
3 to 0		0 to 9	unit place	

<sup>[1]</sup> The PCA8565 compensates for leap years by adding a 29th day to February if the year counter contains a value which is exactly divisible by 4, including the year 00.

### 8.4.5 Register Weekdays

Table 14. Register Weekdays (address 06h) bits description

Bit	Symbol	Value	Description	
7 to 3	-	-	unused	
2 to 0	WEEKDAYS	0 to 6	actual weekday values, see <u>Table 15</u>	

Table 15. Weekday assignments

Day[1]	Bit					
	2	1	0			
Sunday	0	0	0			
Monday	0	0	1			
Tuesday	0	1	0			
Wednesday	0	1	1			
Thursday	1	0	0			
Friday	1	0	1			
Saturday	1	1	0			

<sup>[1]</sup> Definition may be re-assigned by the user.

### 8.4.6 Register Months\_century

Table 16. Register Months\_century (address 07h) bits description

Bit	Symbol	Value	Place value	Description
7	C[1]	0[2]	-	indicates the century is x
		1	-	indicates the century is x + 1
6 to 5	-	-	-	unused
4	MONTHS	0 to 1	ten's place	actual month coded in BCD format, see Table 17
3 to 0		0 to 9	unit place	

<sup>[1]</sup> This bit may be re-assigned by the user.

Table 17. Month assignments coded in BCD format

Month	Upper-digit (ten's place)	Digit (unit place)					
	Bit 4	Bit 3	Bit 2	Bit 1	Bit 0		
January	0	0	0	0	1		
February	0	0	0	1	0		
March	0	0	0	1	1		
April	0	0	1	0	0		
May	0	0	1	0	1		
June	0	0	1	1	0		
July	0	0	1	1	1		
August	0	1	0	0	0		
September	0	1	0	0	1		
October	1	0	0	0	0		
November	1	0	0	0	1		
December	1	0	0	1	0		

<sup>[2]</sup> This bit is toggled when the years register overflows from 99 to 00.

Real time clock/calendar


#### 8.4.7 Register Years

Table 18. Register Years (08h) bits description

Bit	Symbol	Value	Place value	Description
7 to 4	YEARS	0 to 9	ten's place	actual year coded in BCD format
3 to 0		0 to 9	unit place	

#### 8.5 Setting and reading the time

Figure 5 shows the data flow and data dependencies starting from the 1 Hz clock tick.



During read/write operations, the time counting circuits (memory locations 02h through 08h) are blocked.


#### This prevents

- Faulty reading of the clock and calendar during a carry condition
- Incrementing the time registers, during the read cycle

After this read/write access is completed, the time circuit is released again and any pending request to increment the time counters that occurred during the read access is serviced. A maximum of 1 request can be stored; therefore, all accesses must be completed within 1 second (see Figure 6).

As a consequence of this method, it is very important to make a read or write access in one go, that is, setting or reading seconds through to years should be made in one single access. Failing to comply with this method could result in the time becoming corrupted.

#### Real time clock/calendar



As an example, if the time (seconds through to hours) is set in one access and then in a second access the date is set, it is possible that the time may increment between the two accesses. A similar problem exists when reading. A roll over may occur between reads thus giving the minutes from one moment and the hours from the next.

Recommended method for reading the time:

- 1. Send a START condition and the slave address for write (A2h).
- 2. Set the address pointer to registers Seconds (02h).
- 3. Send a RESTART condition or STOP followed by START.
- 4. Send the slave address for read (A3h).
- 5. Read the register Seconds.
- 6. Read the register Minutes.
- 7. Read the register Hours.
- 8. Read the register Days.
- 9. Read the register Weekdays.
- 10. Read the register Months\_century.
- 11. Read the register Years.
- 12. Send a STOP condition.


#### 8.6 Alarm registers

When one or more of the alarm registers are loaded with a valid minute, hour, day or weekday and its corresponding bit alarm enable (AE\_x) is logic 0, then that information is compared with the actual minute, hour, day and weekday.

When all enabled comparisons first match, the Alarm Flag (AF) is set. AF will remain set until cleared by command. Once AF has been cleared it is only set again when the time increments to match the alarm condition once more. (For clearing the AF, see Section 8.9.1.1 on page 18.)

Alarm registers which have their bit AE\_x at logic 1 are ignored.

#### Real time clock/calendar



#### 8.6.1 Register Minute\_alarm

Table 19. Register Minute\_alarm (address 09h) bits description

Bit	Symbol	Value	Place value	Description
7	AE_M	0	-	minute alarm is enabled
		1[1]	-	minute alarm is disabled
6 to 4	MINUTE_ALARM	0 to 5	ten's place	minute alarm information coded in BCD
3 to 0		0 to 9	unit place	format

<sup>[1]</sup> Default value.

#### 8.6.2 Register Hour\_alarm

Table 20. Register Hour\_alarm (address 0Ah) bits description

Bit	Symbol	Value	Place value	Description
7	AE_H	0	-	hour alarm is enabled
		1[1]	-	hour alarm is disabled
6	-	-	-	unused
5 to 4	HOUR_ALARM	0 to 2	ten's place	hour alarm information coded in BCD
3 to 0		0 to 9	unit place	format

<sup>[1]</sup> Default value.

#### Real time clock/calendar

#### 8.6.3 Register Day\_alarm

Table 21. Register Day\_alarm (address 0Bh) bits description

Bit	Symbol	Value	Place value	Description
7	AE_D	0	-	day alarm is enabled
		1[1]	-	day alarm is disabled
6	-	-	-	unused
5 to 4	DAY_ALARM	0 to 3	ten's place	day alarm information coded in BCD
3 to 0		0 to 9	unit place	format

<sup>[1]</sup> Default value.

#### 8.6.4 Register Weekday\_alarm

Table 22. Register Weekday\_alarm (address 0Ch) bits description

Bit	Symbol	Value	Description
7	AE_W	0	weekday alarm is enabled
		1[1]	weekday alarm is disabled
6 to 3	-	-	unused
2 to 0	WEEKDAY_ALARM	0 to 6	weekday alarm information coded in BCD format

<sup>[1]</sup> Default value.

#### 8.7 Timer functions

The 8-bit countdown timer at address 0Fh is controlled by the timer control register at address 0Eh. The timer control register determines one of 4 source clock frequencies for the timer (4.096 kHz, 64 Hz, 1 Hz, or  $^{1}/_{60}$  Hz) and enables or disables the timer. The timer counts down from a software-loaded 8-bit binary value. At the end of every countdown, the timer sets the timer flag (TF) in the register Control\_status\_2. The TF may only be cleared by command. The asserted TF can be used to generate an interrupt (on pin INT). The interrupt may be generated as a pulsed signal every countdown period or as a permanently active signal which follows the state of TF. Bit TI\_TP is used to control this mode selection. When reading the timer, the current countdown value is returned.

#### 8.7.1 Register Timer\_control

The timer register is an 8-bit binary countdown timer. It is enabled and disabled via the bit TE in register Timer\_control. The source clock for the timer is also selected by the TD[1:0] in register Timer\_control. Other timer properties such as interrupt generation are controlled via register Control\_2.

#### Real time clock/calendar

Table 4	table 25. Register Timer_control (address UEn) bits description				
Bit	Symbol	Value	Description		
7	TE	0[1]	timer is disabled		
		1	timer is enabled		
6 to 2	-	-	unused		
1 to 0	TD[1:0]		timer source clock frequency select[2]		
		00	4.096 kHz		
		01	64 Hz		
		10	1 Hz		
		11[2]	1/ <sub>60</sub> Hz		

Table 23. Register Timer\_control (address 0Eh) bits description

#### 8.7.2 Register Countdown\_Timer

Table 24. Timer (address 0Fh) bits description

Bit	Symbol	Value	Description
7 to 0	COUNTDOWN_TIMER	00h to FFh	countdown period in seconds:
			$CountdownPeriod = \frac{n}{SourceClockFrequency}$
			where n is the countdown value

Table 25. Timer register bits value range

Bit										
7	6	5	4	3	2	1	0			
128	64	32	16	8	4	2	1			

The timer register is an 8-bit binary countdown timer. It is enabled or disabled via the Timer\_control register. The source clock for the timer is also selected by the Timer\_control register. Other timer properties such as single or periodic interrupt generation are controlled via the register Control\_status\_2 (address 01h).

For accurate read back of the count down value, it is recommended to read the register twice and check for consistent results, since it is not possible to freeze the countdown timer counter during read back.

#### 8.8 Register CLKOUT\_control and clock output

A programmable square wave is available at pin CLKOUT. Operation is controlled by the CLKOUT\_control register at address 0Dh. Frequencies of 32.768 kHz (default), 1.024 kHz, 32 Hz and 1 Hz can be generated for use as a system clock, microcontroller clock, input to a charge pump, or for calibration of the oscillator. CLKOUT is an open-drain output and enabled at power-on. If disabled it becomes high-impedance.

<sup>[1]</sup> Default value.

<sup>[2]</sup> These bits determine the source clock for the countdown timer; when not in use, TD[1:0] should be set to  $\frac{1}{60}$  Hz for power saving.

#### Real time clock/calendar


10010 1	in the glotter of Enter		(addition of the document
Bit	Symbol	Value	Description
7	FE	0	the CLKOUT output is inhibited and CLKOUT output is set to high-impedance
		1[1]	the CLKOUT output is activated
6 to 2	-	-	unused
1 to 0	FD[1:0]		frequency output at pin CLKOUT
		00[1]	32.768 kHz
		01	1.024 kHz
		10	32 Hz
		11	1 Hz

Table 26. Register CLKOUT\_control (address 0Dh) bits description

#### 8.9 Interrupt output


#### 8.9.1 Bits TF and AF

When an alarm occurs, AF is set to 1. Similarly, at the end of a timer countdown, TF is set to 1. These bits maintain their value until overwritten by command. If both timer and alarm interrupts are required in the application, the source of the interrupt is determined by reading these bits.



<sup>[1]</sup> Default value.

Real time clock/calendar



#### 8.9.1.1 Clearing the alarm flag (AF)

Table 28 shows an example for clearing bit AF but leaving bit TF unaffected. Clearing the flags is made by a write command; therefore bits 7, 6, 4, 1 and 0 must be written with their previous values. Repeatedly re-writing these bits has no influence on the functional behavior.

To prevent the timer flags being overwritten while clearing AF, a logical AND is performed during a write access. Writing a logic 1 will cause the flag to maintain its value, whereas writing a logic 0 will cause the flag to be reset.

Table 27. Flag location in register Control\_2

Register	Bit									
	7	6	5	4	3	2	1	0		
Control_2	-	-	-	-	AF	TF	-	-		

The following table shows what instruction must be sent to clear bit AF. In this example bit TF is unaffected.

Table 28. Example to clear only AF (bit 3) in register Control\_2

Register	Bit							
	7	6	5	4	3	2	1	0
Control_2	-	-	-	-	0	1	-	-

#### 8.9.2 Bits TIE and AIE

These bits activate or deactivate the generation of an interrupt when TF or AF is asserted respectively. The interrupt is the logical OR of these two conditions when both AIE and TIE are set.

Real time clock/calendar

#### 8.9.3 Countdown timer interrupts

The pulse generator for the countdown timer interrupt uses an internal clock and is dependent on the selected source clock for the countdown timer and on the countdown value n. As a consequence, the width of the interrupt pulse varies (see Table 29).

Table 29. INT operation (bit TI\_TP = 1)

Source clock (Hz)	INT period (s)						
	n = 1[1]	n > 1					
4096	1/8192	1/4096					
64	1/ <sub>128</sub>	1/64					
1	1/64	1/64					
1/60	1/64	1/64					

<sup>[1]</sup> n = loaded countdown value. Timer stopped when n = 0.

#### 8.10 External clock (EXT\_CLK) test mode

A test mode is available which allows for on-board testing. In such a mode it is possible to set up test conditions and control the operation of the RTC.

The test mode is entered by setting bit TEST1 in register Control\_1. Then pin CLKOUT becomes an input. The test mode replaces the internal 64 Hz signal with the signal applied to pin CLKOUT. Every 64 positive edges applied to pin CLKOUT will then generate an increment of one second.

The signal applied to pin CLKOUT should have a minimum pulse width of 300 ns and a maximum period of 1000 ns. The internal 64 Hz clock, now sourced from CLKOUT, is divided down to 1 Hz by a 2<sup>6</sup> divide chain called a prescaler. The prescaler can be set into a known state by using bit STOP. When bit STOP is set, the prescaler is reset to 0 (STOP must be cleared before the prescaler can operate again).

From a STOP condition, the first 1 second increment will take place after 32 positive edges on CLKOUT. Thereafter, every 64 positive edges will cause a 1 second increment.

**Remark:** Entry into EXT\_CLK test mode is not synchronized to the internal 64 Hz clock. When entering the test mode, no assumption as to the state of the prescaler can be made.

#### Operation example:


- 1. Set EXT\_CLK test mode (Control\_1, bit TEST1 = 1).
- 2. Set STOP (Control 1, bit STOP = 1).
- 3. Clear STOP (Control\_1, bit STOP = 0).
- 4. Set time registers to desired value.
- 5. Apply 32 clock pulses to CLKOUT.
- 6. Read time registers to see the first change.
- 7. Apply 64 clock pulses to CLKOUT.
- 8. Read time registers to see the second change.

Repeat 7 and 8 for additional increments.

Real time clock/calendar


#### 8.11 STOP bit function

The function of the STOP bit is to allow for accurate starting of the time circuits. The STOP bit function will cause the upper part of the prescaler ( $F_2$  to  $F_{14}$ ) to be held in reset and thus no 1 Hz ticks will be generated (see <u>Figure 10</u>). The time circuits can then be set and will not increment until the STOP bit is released (see <u>Figure 11</u> and <u>Table 30</u>).



The STOP bit function will not affect the output of 32.768 kHz but will stop 1.024 kHz, 32 Hz and 1 Hz.

The lower two stages of the prescaler ( $F_0$  and  $F_1$ ) are not reset and because the  $I^2$ C-bus is asynchronous to the crystal oscillator, the accuracy of re-starting the time circuits will be between zero and one 8.192 kHz cycle (see Figure 11).



#### Real time clock/calendar

Table 30. First increment of time circuits after STOP bit release

Bit	Prescaler bits	[1]	1 Hz tick	Time	Comment
STOP	F <sub>0</sub> F <sub>1</sub> -F <sub>2</sub> to F <sub>14</sub>			hh:mm:ss	
Clock is	running normally				
0	01-0 0001 1101 0100			12:45:12	prescaler counting normally
STOP bit	is activated by user.	F <sub>0</sub> F <sub>1</sub> a	re not reset	t and values ca	nnot be predicted externally
1	XX-0 0000 0000 0000			12:45:12	prescaler is reset; time circuits are frozen
New time	e is set by user				
1	XX-0 0000 0000 0000			08:00:00	prescaler is reset; time circuits are frozen
STOP bit	is released by user				
0	XX-0 0000 0000 0000			08:00:00	prescaler is now running
	XX-1 0000 0000 0000	35 s		08:00:00	-
	XX-0 1000 0000 0000	5079		08:00:00	-
	XX-1 1000 0000 0000	0.507813 to 0.507935 s	🌴	08:00:00	-
	:	7813		:	:
	11-1 1111 1111 1110	0.50	<u> </u>	08:00:00	-
	00-0 0000 0000 0001		<u> </u>	08:00:01	0 to 1 transition of F <sub>14</sub> increments the time circuits
	10-0 0000 0000 0001			08:00:01	-
	:			:	:
	11-1 1111 1111 1111	s 000		08:00:01	-
	00-0 0000 0000 0000	1.000000 s		08:00:01	-
	10-0 0000 0000 0000	_		08:00:01	-
	:			:	-
	11-1 1111 1111 1110			08:00:01	-
	00-0 0000 0000 0001		<u>'</u>	08:00:02	0 to 1 transition of F <sub>14</sub> increments the time circuits
			<b> </b> 013aaa076		

#### [1] $F_0$ is clocked at 32.768 kHz.

The first increment of the time circuits is between 0.507813 s and 0.507935 s after STOP bit is released. The uncertainty is caused by the prescaler bits  $F_0$  and  $F_1$  not being reset (see <u>Table 30</u>) and the unknown state of the 32 kHz clock.


Real time clock/calendar

### 9. Characteristics of the I<sup>2</sup>C-bus

The I<sup>2</sup>C-bus is for bidirectional, two-line communication between different ICs or modules. The two lines are a Serial Data Line (SDA) and a Serial CLock line (SCL). Both lines must be connected to a positive supply via a pull-up resistor. Data transfer may be initiated only when the bus is not busy.


#### 9.1 Bit transfer

One data bit is transferred during each clock pulse. The data on the SDA line must remain stable during the HIGH period of the clock pulse as changes in the data line at this time will be interpreted as a control signal (see Figure 12).



#### 9.2 START and STOP conditions


Both data and clock lines remain HIGH when the bus is not busy. A HIGH-to-LOW transition of the data line, while the clock is HIGH is defined as the START condition (S). A LOW-to-HIGH transition of the data line while the clock is HIGH is defined as the STOP condition (P), see Figure 13.



#### 9.3 System configuration

A device generating a message is a transmitter, a device receiving a message is the receiver. The device that controls the message is the master and the devices which are controlled by the master are the slaves (see <a href="Figure 14">Figure 14</a>).

Real time clock/calendar




#### 9.4 Acknowledge

The number of data bytes transferred between the START and STOP conditions from transmitter to receiver is unlimited. Each byte of eight bits is followed by an acknowledge cycle.

- A slave receiver, which is addressed, must generate an acknowledge after the reception of each byte.
- A master receiver must generate an acknowledge after the reception of each byte that has been clocked out of the slave transmitter.
- The device that acknowledges must pull-down the SDA line during the acknowledge clock pulse, so that the SDA line is stable LOW during the HIGH period of the acknowledge related clock pulse (set-up and hold times must be taken into consideration).
- A master receiver must signal an end of data to the transmitter by not generating an
  acknowledge on the last byte that has been clocked out of the slave. In this event, the
  transmitter must leave the data line HIGH to enable the master to generate a STOP
  condition.

Acknowledgement on the I<sup>2</sup>C-bus is shown in Figure 15.



Real time clock/calendar


### 9.5 I<sup>2</sup>C-bus protocol

#### 9.5.1 Addressing

Before any data is transmitted on the  $I^2C$ -bus, the device which should respond is addressed first. The addressing is always carried out with the first byte transmitted after the start procedure.


The PCA8565 acts as a slave receiver or slave transmitter. Therefore the clock signal SCL is only an input signal, but the data signal SDA is a bidirectional line.

The PCA8565 slave address is shown in Figure 16.





#### 9.5.2 Clock and calendar read/write cycles

The I<sup>2</sup>C-bus configuration for the different PCA8565 read and write cycles is shown in <u>Figure 17</u>, <u>Figure 18</u> and <u>Figure 19</u>. The word address is a 4-bit value that defines which register is to be accessed next. The upper four bits of the word address are not used.



#### Real time clock/calendar






#### 9.5.3 Interface watchdog timer

During read/write operations, the time counting circuits are frozen. To prevent a situation where the accessing device becomes locked and does not clear the interface, the PCA8565 has a built in watchdog timer. Should the interface be active for more than 1 s from the time a valid slave address is transmitted, then the PCA8565 will automatically clear the interface and allow the time counting circuits to continue counting. Under a correct data transfer, the watchdog timer is stopped on receipt of a START or STOP condition.

The watchdog is implemented to prevent the excessive loss of time due to interface access failure e.g. if main power is removed from a battery backed-up system during an interface access.


Each time the watchdog period is exceeded, 1 s will be lost from the time counters. The watchdog will trigger between 1 s and 2 s after receiving a valid slave address.

#### Real time clock/calendar



Real time clock/calendar

### 10. Internal circuitry



### 11. Safety notes

#### CAUTION



This device is sensitive to ElectroStatic Discharge (ESD). Observe precautions for handling electrostatic sensitive devices.

Such precautions are described in the ANSI/ESD S20.20, IEC/ST 61340-5, JESD625-A or equivalent standards.

Real time clock/calendar

### 12. Limiting values

Table 31. Limiting values

In accordance with the Absolute Maximum Rating System (IEC 60134).

Symbol	Parameter	Conditions		Min	Max	Unit
$V_{DD}$	supply voltage			-0.5	+6.5	V
I <sub>SS</sub>	ground supply current			-50	+50	mA
I <sub>DD</sub>	supply current			-50	+50	mA
VI	input voltage			-0.5	+6.5	V
I <sub>I</sub>	input current			-10	+10	mΑ
Io	output current			-10	+10	mΑ
P <sub>tot</sub>	total power dissipation			-	300	mW
V <sub>ESD</sub>	electrostatic discharge	НВМ	[1]	-	±3000	V
	voltage	CDM	[2]	-	±1100	V
I <sub>lu</sub>	latch-up current		[3]	-	250	mΑ
T <sub>stg</sub>	storage temperature		[4]	-65	+150	°C
T <sub>amb</sub>	ambient temperature			-40	+125	°C

<sup>[1]</sup> Pass level; Human Body Model (HBM) according to Ref. 6 "JESD22-A114".

<sup>[2]</sup> Pass level; Charged-Device Model (CDM), according to Ref. 7 "JESD22-C101".

<sup>[3]</sup> Pass level; latch-up testing, according to Ref. 8 "JESD78".

<sup>[4]</sup> According to the store and transport requirements (see Ref. 14 "UM10569") the devices have to be stored at a temperature of +8  $^{\circ}$ C to +45  $^{\circ}$ C and a humidity of 25  $^{\circ}$ 6 to 75  $^{\circ}$ 8.

Real time clock/calendar

### 13. Static characteristics

#### Table 32. Static characteristics

 $V_{DD} = 1.8 \text{ V to } 5.5 \text{ V}; V_{SS} = 0 \text{ V}; T_{amb} = -40 ^{\circ}\text{C} \text{ to } +125 ^{\circ}\text{C}; f_{osc} = 32.768 \text{ kHz}; quartz R_s = 40 \text{ k}\Omega; C_L = 8 \text{ pF}; unless otherwise specified.}$ 

Symbol	Parameter	Conditions	Min	Тур	Max	Unit
Supplies						
$V_{DD}$	supply voltage		1.8	-	5.5	V
	pplies  D supply voltage  W low voltage	for clock data integrity	$V_{low}$	-	5.5	V
V <sub>low</sub>	low voltage	for low voltage detection	-	0.9	1.7	V
I <sub>DD</sub>	supply current	interface active				
		f <sub>SCL</sub> = 400 kHz	-	-	820	μΑ
		f <sub>SCL</sub> = 100 kHz	-	-	220	μΑ
		interface inactive (f <sub>SCL</sub> = 0 Hz); T <sub>amb</sub> = 25 °C [1]				
		CLKOUT disabled				
		V <sub>DD</sub> = 5.0 V	-	750	1500	nA
		V <sub>DD</sub> = 4.0 V	-	700	1400	nA
		V <sub>DD</sub> = 3.0 V	-	650	1300	nA
		V <sub>DD</sub> = 2.0 V	-	600	1200	nA
		$V_{DD} = 5.0 \text{ V}; T_{amb} = 125 \text{ °C}$ [2]	-	750	5000	nA
		CLKOUT enabled at 32 kHz				
		V <sub>DD</sub> = 5.0 V	-	1000	2000	nA
		V <sub>DD</sub> = 4.0 V	-	900	1800	nA
		V <sub>DD</sub> = 3.0 V	-	800	1600	nA
		V <sub>DD</sub> = 2.0 V	-	700	1400	nA
		$V_{DD} = 5.0 \text{ V;} T_{amb} = 125 \text{ °C}$ [2]	-	1000	6000	nA
Inputs						
V <sub>IL</sub>	LOW-level input voltage		$V_{SS}-0.3$	-	$0.3V_{DD}$	V
$V_{IH}$	HIGH-level input voltage	on pins SCL and SDA	0.7V <sub>DD</sub>	-	5.5	V
		on pin OSCI	$0.7V_{DD}$	-	$V_{DD} + 0.3$	V
I <sub>LI</sub>	input leakage current	on pins SCL and SDA; $V_I = V_{DD}$ or $V_{SS}$	-1	0	+1	μΑ
Ci	input capacitance	[3]	-	-	7	рF


#### Real time clock/calendar

Table 32. Static characteristics ... continued

 $V_{DD}$  = 1.8 V to 5.5 V;  $V_{SS}$  = 0 V;  $T_{amb}$  = -40 °C to +125 °C;  $f_{OSC}$  = 32.768 kHz; quartz  $R_s$  = 40 k $\Omega$ ;  $C_L$  = 8 pF; unless otherwise specified.


Symbol	puts	Conditions	Min	Тур	Max	Unit
Outputs			,	,		
I <sub>OL</sub>	LOW-level output current	output sink current				
		V <sub>OL</sub> = 0.4 V; V <sub>DD</sub> = 5 V				
	on pin SDA	3	-	-	mA	
		on pin ĪNT	1	-	-	mA
		$V_O = V_{DD}$ or $V_{SS}$			'	'
		on pin CLKOUT	1	-	-	mA
I <sub>LO</sub>	output leakage current		-1	0	+1	μΑ

- [1] Timer source clock =  $\frac{1}{60}$  Hz, level of pins SCL and SDA is  $V_{DD}$  or  $V_{SS}$ .
- [2] Worst case is at high temperature and high supply voltage.
- [3] Tested on sample basis.



 $T_{amb}$  = 25 °C; Timer = 1 minute; CLKOUT disabled.


Fig 22.  $I_{DD}$  as a function of  $V_{DD}$ 



 $T_{amb}$  = 25 °C; Timer = 1 minute; CLKOUT = 32 kHz.

Fig 23.  $I_{DD}$  as a function of  $V_{DD}$ 

#### Real time clock/calendar



Real time clock/calendar

### 14. Dynamic characteristics

#### Table 33. Dynamic characteristics

 $V_{DD}=1.8~V~to~5.5~V;~V_{SS}=0~V;~T_{amb}=-40~^{\circ}C~to~+125~^{\circ}C;~f_{osc}=32.768~kHz;~quartz~R_s=40~k\Omega;~C_L=8~pF;~unless~otherwise~specified.$ 

Symbol	Parameter	Conditions	Min	Тур	Max	Unit
Oscillator			1			
C <sub>L(itg)</sub>	integrated load capacitance	[1]	15	25	35	pF
$\Delta f_{\rm osc}/f_{\rm osc}$	relative oscillator frequency variation	$\Delta V_{DD} = 200 \text{ mV};$ $T_{amb} = 25 \text{ °C}$	-	0.2	-	ppm
Quartz cry	stal parameters (f = 32.768 kHz)		1	<u> </u>	-	
R <sub>s</sub>	series resistance		-	-	100	kΩ
C <sub>L</sub>	load capacitance		-	10	-	pF
C <sub>trim</sub>	trimmer capacitance		5	-	25	pF
CLKOUT o	utput		1	<u> </u>	-	
$\delta$ CLKOUT	duty cycle on pin CLKOUT	[2]	-	50	-	%
I <sup>2</sup> C-bus tim	ning characteristics	[3][4]				
f <sub>SCL</sub>	SCL clock frequency	<u>[5]</u>	-	-	400	kHz
t <sub>HD;STA</sub>	hold time (repeated) START condition		0.6	-	-	μS
t <sub>SU;STA</sub>	set-up time for a repeated START condition		0.6	-	-	μS
t <sub>LOW</sub>	LOW period of the SCL clock		1.3	-	-	μS
t <sub>HIGH</sub>	HIGH period of the SCL clock		0.6	-	-	μS
t <sub>r</sub>	rise time of both SDA and SCL signals		-	-	0.3	μS
t <sub>f</sub>	fall time of both SDA and SCL signals		-	-	0.3	μS
t <sub>SU;DAT</sub>	data set-up time		100	-	-	ns
t <sub>HD;DAT</sub>	data hold time		0	-	-	ns
t <sub>BUF</sub>	bus free time between a STOP and START condition		4.7	-	-	μS
t <sub>SU;STO</sub>	set-up time for STOP condition		0.6	-	-	μS
t <sub>SP</sub>	pulse width of spikes that must be suppressed by the input filter		-	-	50	ns
C <sub>b</sub>	capacitive load for each bus line		-	-	400	pF

<sup>[1]</sup> Integrated load capacitance,  $C_{L(itg)}$ , is a calculation of  $C_{OSCI}$  and  $C_{OSCO}$  in series.  $C_{L(itg)} = \frac{(C_{OSCI} \cdot C_{OSCO})}{(C_{OSCI} + C_{OSCO})}$ 


<sup>[2]</sup> For  $f_{CLKOUT} = 1.024 \text{ kHz}$ , 32 Hz and 1 Hz.

<sup>[3]</sup> All timing values are valid within the operating supply voltage at ambient temperature and referenced to V<sub>IL</sub> and V<sub>IH</sub> with an input voltage swing of V<sub>SS</sub> to V<sub>DD</sub>.


<sup>[4]</sup> A detailed description of the I<sup>2</sup>C-bus specification is given in the document Ref. 12 "UM10204".

<sup>[5]</sup> I<sup>2</sup>C-bus access time between two STARTs or between a START and a STOP condition to this device must be less than one second.

#### Real time clock/calendar



# 15. Application information



Real time clock/calendar

#### 15.1 Quartz frequency adjustment

#### 15.1.1 Method 1: fixed OSCI capacitor

By evaluating the average capacitance necessary for the application layout, a fixed capacitor can be used. The frequency is best measured via the 32.768 kHz signal available after power-on at pin CLKOUT. The frequency tolerance depends on the quartz crystal tolerance, the capacitor tolerance and the device-to-device tolerance (on average  $\Delta f/f = \pm 5 \times 10^{-6}$ ). Average deviations of  $\pm 5$  minutes per year can be easily achieved.

#### 15.1.2 Method 2: OSCI trimmer

Using the 32.768 kHz signal available after power-on at pin CLKOUT, fast setting of a trimmer is possible.

#### 15.1.3 Method 3: OSCO output

Direct measurement of OSCO out (allowing for test probe capacitance).

#### 16. Test information

#### 16.1 Quality information

This product has been qualified in accordance with the Automotive Electronics Council (AEC) standard *Q100 - Failure mechanism based stress test qualification for integrated circuits*, and is suitable for use in automotive applications.


**PCA8565 NXP Semiconductors** 

Real time clock/calendar

### 17. Package outline

TSSOP8: plastic thin shrink small outline package; 8 leads; body width 3 mm

SOT505-1



UNIT	A max.	A <sub>1</sub>	A <sub>2</sub>	А3	bp	С	D <sup>(1)</sup>	E <sup>(2)</sup>	е	HE	L	Lp	v	w	у	Z <sup>(1)</sup>	θ
mm	1.1	0.15 0.05	0.95 0.80	0.25	0.45 0.25	0.28 0.15	3.1 2.9	3.1 2.9	0.65	5.1 4.7	0.94	0.7 0.4	0.1	0.1	0.1	0.70 0.35	6° 0°

#### Notes

- 1. Plastic or metal protrusions of 0.15 mm maximum per side are not included.
- 2. Plastic or metal protrusions of 0.25 mm maximum per side are not included.

	OUTLINE		REFER	EUROPEAN	ISSUE DATE			
	VERSION	IEC	JEDEC	JEITA		PROJECTION	ISSUE DATE	
	SOT505-1						<del>99-04-09</del> 03-02-18	
_					1		L.	-

Fig 28. Package outline SOT505-1 (TSSOP8) of PCA8565TS

All information provided in this document is subject to legal disclaimers.

© NXP Semiconductors N.V. 2014. All rights reserved.

Real time clock/calendar

### 18. Handling information

All input and output pins are protected against ElectroStatic Discharge (ESD) under normal handling. When handling Metal-Oxide Semiconductor (MOS) devices ensure that all normal precautions are taken as described in *JESD625-A*, *IEC 61340-5* or equivalent standards.

Real time clock/calendar

## 19. Packing information

## 19.1 Tape and reel information

For tape and reel packing information, please see Ref. 10 "SOT505-1\_118" and Ref. 11 "SOT505-1\_518" on page 42

## 20. Soldering of SMD packages

This text provides a very brief insight into a complex technology. A more in-depth account of soldering ICs can be found in Application Note *AN10365* "Surface mount reflow soldering description".

## 20.1 Introduction to soldering

Soldering is one of the most common methods through which packages are attached to Printed Circuit Boards (PCBs), to form electrical circuits. The soldered joint provides both the mechanical and the electrical connection. There is no single soldering method that is ideal for all IC packages. Wave soldering is often preferred when through-hole and Surface Mount Devices (SMDs) are mixed on one printed wiring board; however, it is not suitable for fine pitch SMDs. Reflow soldering is ideal for the small pitches and high densities that come with increased miniaturization.

## 20.2 Wave and reflow soldering

Wave soldering is a joining technology in which the joints are made by solder coming from a standing wave of liquid solder. The wave soldering process is suitable for the following:

- Through-hole components
- Leaded or leadless SMDs, which are glued to the surface of the printed circuit board

Not all SMDs can be wave soldered. Packages with solder balls, and some leadless packages which have solder lands underneath the body, cannot be wave soldered. Also, leaded SMDs with leads having a pitch smaller than ~0.6 mm cannot be wave soldered, due to an increased probability of bridging.

The reflow soldering process involves applying solder paste to a board, followed by component placement and exposure to a temperature profile. Leaded packages, packages with solder balls, and leadless packages are all reflow solderable.

Key characteristics in both wave and reflow soldering are:

- · Board specifications, including the board finish, solder masks and vias
- · Package footprints, including solder thieves and orientation
- The moisture sensitivity level of the packages
- Package placement
- Inspection and repair
- Lead-free soldering versus SnPb soldering

## 20.3 Wave soldering

Key characteristics in wave soldering are:

- Process issues, such as application of adhesive and flux, clinching of leads, board transport, the solder wave parameters, and the time during which components are exposed to the wave
- Solder bath specifications, including temperature and impurities

## 20.4 Reflow soldering

Key characteristics in reflow soldering are:

- Lead-free versus SnPb soldering; note that a lead-free reflow process usually leads to higher minimum peak temperatures (see <u>Figure 29</u>) than a SnPb process, thus reducing the process window
- Solder paste printing issues including smearing, release, and adjusting the process window for a mix of large and small components on one board
- Reflow temperature profile; this profile includes preheat, reflow (in which the board is heated to the peak temperature) and cooling down. It is imperative that the peak temperature is high enough for the solder to make reliable solder joints (a solder paste characteristic). In addition, the peak temperature must be low enough that the packages and/or boards are not damaged. The peak temperature of the package depends on package thickness and volume and is classified in accordance with Table 34 and 35

Table 34. SnPb eutectic process (from J-STD-020D)

Package thickness (mm)	Package reflow temperature (°C)				
	Volume (mm³)				
	< 350	≥ 350			
< 2.5	235	220			
≥ 2.5	220	220			


Table 35. Lead-free process (from J-STD-020D)

Package thickness (mm)	Package reflow temperature (°C)						
	Volume (mm³)						
	< 350	350 to 2000	> 2000				
< 1.6	260	260	260				
1.6 to 2.5	260	250	245				
> 2.5	250	245	245				

Moisture sensitivity precautions, as indicated on the packing, must be respected at all times.

Studies have shown that small packages reach higher temperatures during reflow soldering, see Figure 29.

#### Real time clock/calendar



For further information on temperature profiles, refer to Application Note *AN10365* "Surface mount reflow soldering description".

**NXP Semiconductors** 

## 21.1 Real-Time Clock selection

Table 36. Selection of Real-Time Clocks

Type name	Alarm, Timer, Watchdog	Interrupt output	Interface	I <sub>DD</sub> , typical (nA)	Battery backup	Timestamp, tamper input	AEC-Q100 compliant	Special features	Packages
PCF8563	Х	1	I <sup>2</sup> C	250	-	-	-	-	SO8, TSSOP8, HVSON10
PCF8564A	X	1	I <sup>2</sup> C	250	-	-	-	integrated oscillator caps	WLCSP
PCA8565	Х	1	I <sup>2</sup> C	600	-	-	grade 1	high robustness, T <sub>amb</sub> = -40 °C to 125 °C	TSSOP8, HVSON10
PCA8565A	Х	1	I <sup>2</sup> C	600	-	-	-	integrated oscillator caps, T <sub>amb</sub> = -40 °C to 125 °C	WLCSP
PCF85063	-	1	I <sup>2</sup> C	220	-	-	-	basic functions only, no alarm	HXSON8
PCF85063A	X	1	I <sup>2</sup> C	220	-	-	-	tiny package	SO8, DFN2626-10
PCF85063B	Х	1	SPI	220	-	-	-	tiny package	DFN2626-10
PCF85263A	X	2	I <sup>2</sup> C	230	X	Х	-	time stamp, battery backup, stopwatch ½100 s	SO8, TSSOP10, TSSOP8, DFN2626-10
PCF85263B	Х	2	SPI	230	Х	Х	-	time stamp, battery backup, stopwatch ½100s	TSSOP10, DFN2626-10
PCF85363A	X	2	I <sup>2</sup> C	230	X	Х	-	time stamp, battery backup, stopwatch ½100s, 64 Byte RAM	TSSOP10, DFN2626-10
PCF85363B	X	2	SPI	230	X	Х	-	time stamp, battery backup, stopwatch ½100s, 64 Byte RAM	TSSOP10, DFN2626-10
PCF8523	Х	2	I <sup>2</sup> C	150	X	-	-	lowest power 150 nA in operation, FM+ 1 MHz	SO8, HVSON8, TSSOP14, WLCSP
PCF2123	Х	1	SPI	100	-	-	-	lowest power 100 nA in operation	TSSOP14, HVQFN16
PCF2127	X	1	I <sup>2</sup> C and SPI	500	Х	Х	-	temperature compensated, quartz built in, calibrated, 512 Byte RAM	SO16

Туре	name	Alarm, Timer, Watchdog	Interrupt output	Interface	I <sub>DD</sub> , typical (nA)	Battery backup	Timestamp, tamper input	AEC-Q100 compliant	Special features	Packages
PCF2	2127A	X	1	I <sup>2</sup> C and SPI	500	X	X	-	temperature compensated, quartz built in, calibrated, 512 Byte RAM	SO20
PCF2	2129	Х	1	I <sup>2</sup> C and SPI	500	Х	Х	-	temperature compensated, quartz built in, calibrated	SO16
PCF2	2129A	X	1	I <sup>2</sup> C and SPI	500	Х	Х	-	temperature compensated, quartz built in, calibrated	SO20
PCA2	2129	Х	1	I <sup>2</sup> C and SPI	500	Х	Х	grade 3	temperature compensated, quartz built in, calibrated	SO16
PCA2	21125	X	1	SPI	820	-	-	grade 1	high robustness, T <sub>amb</sub> = -40 °C to 125 °C	TSSOP14

## 22. Abbreviations

Table 37. Abbreviations

Acronym	Description
BCD	Binary Coded Decimal
CDM	Charged-Device Model
CMOS	Complementary Metal Oxide Semiconductor
НВМ	Human Body Model
I <sup>2</sup> C	Inter-Integrated Circuit
IC	Integrated Circuit
MSB	Most Significant Bit
MSL	Moisture Sensitivity Level
PCB	Printed-Circuit Board
POR	Power-On Reset
RC	Resistance and Capacitance
RTC	Real Time Clock
SMD	Surface Mount Device

## 23. References

- [1] AN10365 Surface mount reflow soldering description
- [2] AN10853 ESD and EMC sensitivity of IC
- [3] IEC 60134 Rating systems for electronic tubes and valves and analogous semiconductor devices
- [4] IEC 61340-5 Protection of electronic devices from electrostatic phenomena
- [5] IPC/JEDEC J-STD-020D Moisture/Reflow Sensitivity Classification for Nonhermetic Solid State Surface Mount Devices
- [6] JESD22-A114 Electrostatic Discharge (ESD) Sensitivity Testing Human Body Model (HBM)
- [7] JESD22-C101 Field-Induced Charged-Device Model Test Method for Electrostatic-Discharge-Withstand Thresholds of Microelectronic Components
- [8] JESD78 IC Latch-Up Test
- [9] **JESD625-A** Requirements for Handling Electrostatic-Discharge-Sensitive (ESDS) Devices
- [10] SOT505-1\_118 TSSOP8; Reel pack; SMD, 13", packing information
- [11] SOT505-1\_518 TSSOP8; Reel dry pack; SMD, 13", packing information
- [12] UM10204 I<sup>2</sup>C-bus specification and user manual
- [13] UM10301 User Manual for NXP Real Time Clocks PCF85x3, PCA8565 and PCF2123, PCA2125
- [14] UM10569 Store and transport requirements

Real time clock/calendar

## 24. Revision history

#### Table 38. Revision history

Document ID	Release date	Data sheet status	Change notice	Supersedes
PCA8565 v.4	20141205	Product data sheet	-	PCA8565 v.3
Modifications:	Corrected F	igure 27		
PCA8565 v.3	20140901	Product data sheet	-	PCA8565 v.2
PCA8565 v.2	20090616	Product data sheet	-	PCA8565 v.1
PCA8565 v.1	20030331	Product data sheet	-	-

Real time clock/calendar

## 25. Legal information

#### 25.1 Data sheet status

Document status[1][2]	Product status[3]	Definition
Objective [short] data sheet	Development	This document contains data from the objective specification for product development.
Preliminary [short] data sheet	Qualification	This document contains data from the preliminary specification.
Product [short] data sheet	Production	This document contains the product specification.

- [1] Please consult the most recently issued document before initiating or completing a design.
- [2] The term 'short data sheet' is explained in section "Definitions"
- [3] The product status of device(s) described in this document may have changed since this document was published and may differ in case of multiple devices. The latest product status information is available on the Internet at URL http://www.nxp.com.

#### 25.2 Definitions

Draft — The document is a draft version only. The content is still under internal review and subject to formal approval, which may result in modifications or additions. NXP Semiconductors does not give any representations or warranties as to the accuracy or completeness of information included herein and shall have no liability for the consequences of use of such information.

Short data sheet — A short data sheet is an extract from a full data sheet with the same product type number(s) and title. A short data sheet is intended for quick reference only and should not be relied upon to contain detailed and full information. For detailed and full information see the relevant full data sheet, which is available on request via the local NXP Semiconductors sales office. In case of any inconsistency or conflict with the short data sheet, the full data sheet shall prevail.

**Product specification** — The information and data provided in a Product data sheet shall define the specification of the product as agreed between NXP Semiconductors and its customer, unless NXP Semiconductors and customer have explicitly agreed otherwise in writing. In no event however, shall an agreement be valid in which the NXP Semiconductors product is deemed to offer functions and qualities beyond those described in the Product data sheet.

#### 25.3 Disclaimers

Limited warranty and liability — Information in this document is believed to be accurate and reliable. However, NXP Semiconductors does not give any representations or warranties, expressed or implied, as to the accuracy or completeness of such information and shall have no liability for the consequences of use of such information. NXP Semiconductors takes no responsibility for the content in this document if provided by an information source outside of NXP Semiconductors.

In no event shall NXP Semiconductors be liable for any indirect, incidental, punitive, special or consequential damages (including - without limitation - lost profits, lost savings, business interruption, costs related to the removal or replacement of any products or rework charges) whether or not such damages are based on tort (including negligence), warranty, breach of contract or any other legal theory.

Notwithstanding any damages that customer might incur for any reason whatsoever, NXP Semiconductors' aggregate and cumulative liability towards customer for the products described herein shall be limited in accordance with the *Terms and conditions of commercial sale* of NXP Semiconductors.

Right to make changes — NXP Semiconductors reserves the right to make changes to information published in this document, including without limitation specifications and product descriptions, at any time and without notice. This document supersedes and replaces all information supplied prior to the publication hereof.

Suitability for use in automotive applications — This NXP Semiconductors product has been qualified for use in automotive applications. Unless otherwise agreed in writing, the product is not designed, authorized or warranted to be suitable for use in life support, life-critical or safety-critical systems or equipment, nor in applications where failure or malfunction of an NXP Semiconductors product can reasonably be expected to result in personal injury, death or severe property or environmental damage. NXP Semiconductors and its suppliers accept no liability for inclusion and/or use of NXP Semiconductors products in such equipment or applications and therefore such inclusion and/or use is at the customer's own

**Applications** — Applications that are described herein for any of these products are for illustrative purposes only. NXP Semiconductors makes no representation or warranty that such applications will be suitable for the specified use without further testing or modification.

Customers are responsible for the design and operation of their applications and products using NXP Semiconductors products, and NXP Semiconductors accepts no liability for any assistance with applications or customer product design. It is customer's sole responsibility to determine whether the NXP Semiconductors product is suitable and fit for the customer's applications and products planned, as well as for the planned application and use of customer's third party customer(s). Customers should provide appropriate design and operating safeguards to minimize the risks associated with their applications and products.

NXP Semiconductors does not accept any liability related to any default, damage, costs or problem which is based on any weakness or default in the customer's applications or products, or the application or use by customer's third party customer(s). Customer is responsible for doing all necessary testing for the customer's applications and products using NXP Semiconductors products in order to avoid a default of the applications and the products or of the application or use by customer's third party customer(s). NXP does not accept any liability in this respect.

Limiting values — Stress above one or more limiting values (as defined in the Absolute Maximum Ratings System of IEC 60134) will cause permanent damage to the device. Limiting values are stress ratings only and (proper) operation of the device at these or any other conditions above those given in the Recommended operating conditions section (if present) or the Characteristics sections of this document is not warranted. Constant or repeated exposure to limiting values will permanently and irreversibly affect the quality and reliability of the device.

Terms and conditions of commercial sale — NXP Semiconductors products are sold subject to the general terms and conditions of commercial sale, as published at <a href="http://www.nxp.com/profile/terms">http://www.nxp.com/profile/terms</a>, unless otherwise agreed in a valid written individual agreement. In case an individual agreement is concluded only the terms and conditions of the respective agreement shall apply. NXP Semiconductors hereby expressly objects to applying the customer's general terms and conditions with regard to the purchase of NXP Semiconductors products by customer.

PCA8565

#### Real time clock/calendar

No offer to sell or license — Nothing in this document may be interpreted or construed as an offer to sell products that is open for acceptance or the grant, conveyance or implication of any license under any copyrights, patents or other industrial or intellectual property rights.

**Export control** — This document as well as the item(s) described herein may be subject to export control regulations. Export might require a prior authorization from competent authorities.

**Translations** — A non-English (translated) version of a document is for reference only. The English version shall prevail in case of any discrepancy between the translated and English versions.

#### 25.4 Trademarks

Notice: All referenced brands, product names, service names and trademarks are the property of their respective owners.

I<sup>2</sup>C-bus — logo is a trademark of NXP Semiconductors N.V.

## 26. Contact information

For more information, please visit: http://www.nxp.com

For sales office addresses, please send an email to: salesaddresses@nxp.com

## Real time clock/calendar

## 27. Tables

Table 1.	Ordering information	
Table 2.	Ordering options	2
Table 3.	Marking codes	
Table 4.	Pin description	4
Table 5.	Register overview and control bits default	
	values	6
Table 6.	Register Control_1 (address 00h) bits	
	description	7
Table 7.	Register Control_2 (address 01h) bits	
	description	7
Table 8.	Register reset values[1]	8
Table 9.	Register Seconds (address 02h) bits	
	description	
Table 10.		9
Table 11.	Register Minutes (address 03h) bits	
	description	
Table 12.	Register Hours (address 04h) bits description	.10
Table 13.	Register Days (address 05h) bits description	10
Table 14.	Register Weekdays (address 06h) bits	
	description	10
Table 15.	Weekday assignments	11
Table 16.	Register Months_century (address 07h)	
	bits description	11
Table 17.	Month assignments coded in BCD format .	
Table 18.	· / /	12
Table 19.	Register Minute_alarm (address 09h)	
	bits description	14
Table 20.	Register Hour_alarm (address 0Ah)	
	bits description	14
Table 21.	Register Day_alarm (address 0Bh)	
	bits description	15
Table 22.	Register Weekday_alarm (address 0Ch)	
	bits description	15
Table 23.	Register Timer_control (address 0Eh)	
	bits description	
Table 24.	, ,	
Table 25.		16
Table 26.	Register CLKOUT_control (address 0Dh)	
	bits description	
Table 27.	Flag location in register Control_2	18
Table 28.	Example to clear only AF (bit 3) in register	
	<u>Control_2</u>	
Table 29.	INT operation (bit TI_TP = 1)	19
Table 30.	First increment of time circuits after STOP	
	bit release	
Table 31.	Limiting values	
Table 32.	Static characteristics	
Table 33.	Dynamic characteristics	32
Table 34.	SnPb eutectic process (from J-STD-020D) .	38
Table 35.	Lead-free process (from J-STD-020D)	
Table 36.	Selection of Real-Time Clocks	
Table 37.	Abbreviations	
Table 38.	Revision history	43

## Real time clock/calendar

# 28. Figures

Fig 1.	Block diagram of PCA8565	3
Fig 2.	Pin configuration of PCA8565TS (TSSOP8)	
Fig 3.	POR override sequence	9
Fig 4.	Voltage-low detection	.10
Fig 5.	Data flow for the time function	.12
Fig 6.	Access time for read/write operations	.13
Fig 7.	Alarm function block diagram	.14
Fig 8.	AF timing	
Fig 9.	Interrupt scheme	.18
Fig 10.	STOP bit functional diagram	.20
Fig 11.	STOP bit release timing	.20
Fig 12.	Bit transfer	
Fig 13.	Definition of START and STOP conditions	.22
Fig 14.	System configuration	
Fig 15.	Acknowledgement on the I <sup>2</sup> C-bus	.23
Fig 16.	Slave address	.24
Fig 17.	Master transmits to slave receiver (write mode)	.24
Fig 18.	Master reads after setting word address (write	
	word address; read data)	.25
Fig 19.	Master reads slave immediately after first byte	
	(read mode)	
Fig 20.	Interface watchdog timer	
Fig 21.	Device diode protection diagram of PCA8565	.27
Fig 22.	I <sub>DD</sub> as a function of V <sub>DD</sub>	
Fig 23.	I <sub>DD</sub> as a function of V <sub>DD</sub>	.30
Fig 24.	I <sub>DD</sub> as a function of temperature	.31
Fig 25.	Frequency deviation as a function of $V_{\text{DD}}$	.31
Fig 26.	I <sup>2</sup> C-bus timing waveforms	.33
Fig 27.	Application diagram of PCA8565	.33
Fig 28.	Package outline SOT505-1 (TSSOP8) of	
	PCA8565TS	.35
Fig 29.	Temperature profiles for large and small	
	components	.39

#### Real time clock/calendar

## 29. Contents

1	General description	. 1	9.3	System configuration	
2	Features and benefits	. 1	9.4	Acknowledge	23
3	Applications		9.5	I <sup>2</sup> C-bus protocol	24
4	Ordering information		9.5.1	Addressing	
<b>4</b> .1	_		9.5.2	Clock and calendar read/write cycles	
	Ordering options		9.5.3	Interface watchdog timer	25
5	Marking		10	Internal circuitry	27
6	Block diagram		11	Safety notes	27
7	Pinning information	. 4	12	Limiting values	28
7.1	Pinning		13	Static characteristics	
7.2	Pin description		14	Dynamic characteristics	
8	Functional description	. 5	15		
8.1	Register overview	. 6	-	Application information	
8.2	Control registers		15.1 15.1.1	Quartz frequency adjustment	
8.2.1	Register Control_1	. 7	_	Method 1: fixed OSCI capacitor	
8.2.2	Register Control_2	. 7	15.1.2	Method 2: OSCI trimmer	
8.3	Reset		15.1.3	Method 3: OSCO output	
8.3.1	Power-On Reset (POR) override	. 8	16	Test information	
8.4	Time and date registers		16.1	Quality information	34
8.4.1	Register Seconds		17	Package outline	35
8.4.1.1	Voltage-low detector		18	Handling information	36
8.4.2	Register Minutes		19	Packing information	
8.4.3	Register Hours		19.1	Tape and reel information	
8.4.4	Register Days		20	Soldering of SMD packages	
8.4.5	Register Weekdays		-		
8.4.6	Register Months_century		20.1	Introduction to soldering	
8.4.7	Register Years		20.2	Wave and reflow soldering	
8.5	Setting and reading the time		20.3	Wave soldering	
8.6	Alarm registers		20.4	Reflow soldering	
8.6.1	Register Minute_alarm		21	Appendix	
8.6.2	Register Hour_alarm		21.1	Real-Time Clock selection	40
8.6.3	Register Day_alarm		22	Abbreviations	42
8.6.4	Register Weekday_alarm		23	References	42
8.7	Timer functions		24	Revision history	43
8.7.1	Register Timer_control		25	Legal information	
8.7.2	Register Countdown_Timer		25.1	Data sheet status	
8.8	Register CLKOUT_control and clock output		25.1	Definitions	
8.9 8.9.1	Interrupt output		25.2	Disclaimers	
8.9.1.1		18	25.4	Trademarks	
8.9.2	Clearing the alarm flag (AF)				
8.9.3	Countdown timer interrupts		26	Contact information	
8.10	External clock (EXT_CLK) test mode		27	Tables	
8.11	STOP bit function		28	Figures	
	Characteristics of the I <sup>2</sup> C-bus		29	Contents	48
9					
9.1	Bit transfer				
9.2	START and STOP conditions	22			

Please be aware that important notices concerning this document and the product(s) described herein, have been included in section 'Legal information'.

© NXP Semiconductors N.V. 2014.

All rights reserved.

For more information, please visit: http://www.nxp.com For sales office addresses, please send an email to: salesaddresses@nxp.com

Date of release: 5 December 2014