SC16C752 Dual UART with 64-byte FIFO Rev. 04 — 20 June 2003

Product data

1. Description

The SC16C752 is a dual universal asynchronous receiver/transmitter (UART) with 64-byte FIFOs, automatic hardware/software flow control, and data rates up to 5 Mbits/s (3.3 V and 5 V). The SC16C752 offers enhanced features. It has a transmission control register (TCR) that stores receiver FIFO threshold levels to start/stop transmission during hardware and software flow control. With the FIFO RDY register, the software gets the status of TXRDY/RXRDY for all four ports in one access. On-chip status registers provide the user with error indications, operational status, and modem interface control. System interrupts may be tailored to meet user requirements. An internal loop-back capability allows on-board diagnostics.

The UART transmits data, sent to it over the peripheral 8-bit bus, on the TX signal and receives characters on the RX signal. Characters can be programmed to be 5, 6, 7, or 8 bits. The UART has a 64-byte receive FIFO and transmit FIFO and can be programmed to interrupt at different trigger levels. The UART generates its own desired baud rate based upon a programmable divisor and its input clock. It can transmit even, odd, or no parity and 1, 1.5, or 2 stop bits. The receiver can detect break, idle, or framing errors, FIFO overflow, and parity errors. The transmitter can detect FIFO underflow. The UART also contains a software interface for modem control operations, and has software flow control and hardware flow control capabilities.

The SC16C752 is available in a plastic LQFP48 package.

2. Features

- Pin compatible with SC16C2550 with additional enhancements
- Up to 5 Mbits/s baud rate (at 3.3 V and 5 V; at 2.5 V maximum baud rate is 3 Mbits/s)
- 64-byte transmit FIFO
- 64-byte receive FIFO with error flags
- Programmable and selectable transmit and receive FIFO trigger levels for DMA and interrupt generation
- Software/hardware flow control
 - Programmable Xon/Xoff characters
 - Programmable auto-RTS and auto-CTS
- Optional data flow resume by Xon any character
- DMA signalling capability for both received and transmitted data
- Supports 5 V, 3.3 V and 2.5 V operation
- Software selectable baud rate generator
- Prescaler provides additional divide-by-4 function



SC16C752


- Fast databus access time
- Programmable sleep mode
- Programmable serial interface characteristics
 - 5, 6, 7, or 8-bit characters
 - Even, odd, or no parity bit generation and detection
 - 1, 1.5, or 2 stop bit generation
- False start bit detection
- Complete status reporting capabilities in both normal and sleep mode
- Line break generation and detection
- Internal test and loop-back capabilities
- Fully prioritized interrupt system controls
- Modem control functions (CTS, RTS, DSR, DTR, RI, and CD).

3. Ordering information

Table 1:Ordering information


Type number	Package	Package							
	Name	Description	Version						
SC16C752IB48	LQFP48	plastic low profile quad flat package; 48 leads; body $7 \times 7 \times 1.4$ mm	SOT313-2						

4. Block diagram



5. Pinning information

5.1 Pinning



5.2 Pin description

Table 2: Pin d	lescriptio	n	
Symbol	Pin	Туре	Description
A0	28	I	Address 0 select bit. Internal registers address selection.
A1	27	I	Address 1 select bit. Internal registers address selection.
A2	26	I	Address 2 select bit. Internal registers address selection.
CDA, CDB	40, 16	1	Carrier Detect (Active-LOW). These inputs are associated with individual UART channels A and B. A logic LOW on these pins indicates that a carrier has been detected by the modem for that channel. The state of these inputs is reflected in the modem status register (MSR).
CSA, CSB	10, 11	1	Chip Select (Active-LOW). These pins enable data transfers between the user CPU and the SC16C752 for the channel(s) addressed. Individual UART sections (A, B) are addressed by providing a logic LOW on the respective \overline{CSA} and \overline{CSB} pins.

Table 2: Pin description...continued Symbol Pin Type Description CTSA, CTSB 38, 23 L Clear to Send (Active-LOW). These inputs are associated with individual UART channels A and B. A logic 0 (LOW) on the CTS pins indicates the modem or data set is ready to accept transmit data from the SC16C752. Status can be tested by reading MSR[4]. These pins only affect the transmit and receive operations when Auto-CTS function is enabled via the Enhanced Feature Register EFR[7] for hardware flow control operation. 44-48, I/O D0-D4, Data bus (bi-directional). These pins are the 8-bit, 3-state data bus for transferring D5-D7 1-3 information to or from the controlling CPU. D0 is the least significant bit and the first data bit in a transmit or receive serial data stream. DSRA, DSRB 39, 20 Data Set Ready (Active-LOW). These inputs are associated with individual UART I channels A and B. A logic 0 (LOW) on these pins indicates the modem or data set is powered-on and is ready for data exchange with the UART. The state of these inputs is reflected in the modem status register (MSR). DTRA, DTRB Data Terminal Ready (Active-LOW). These outputs are associated with individual 34, 35 0 UART channels A and B. A logic 0 (LOW) on these pins indicates that the SC16C752 is powered-on and ready. These pins can be controlled via the modem control register. Writing a logic 1 to MCR[0] will set the DTR output to logic 0 (LOW), enabling the modem. The output of these pins will be a logic 1 after writing a logic 0 to MCR[0], or after a reset. GND 17 L Signal and power ground. INTA, INTB 30, 29 0 Interrupt A and B (Active-HIGH). These pins provide individual channel interrupts INTA and INTB. INTA and INTB are enabled when MCR[3] is set to a logic 1, interrupt sources are enabled in the interrupt enable register (IER). Interrupt conditions include: receiver errors, available receiver buffer data, available transmit buffer space, or when a modem status flag is detected. INTA, INTB are in the high-impedance state after reset. IOR 19 I Input/Output Read strobe (Active-LOW). A HIGH-to-LOW transition on IOR will load the contents of an internal register defined by address bits A0-A2 onto the SC16C752 data bus (D0-D7) for access by external CPU. ĪOW I Input/Output Write strobe (Active-LOW). A LOW-to-HIGH transition on IOW will 15 transfer the contents of the data bus (D0-D7) from the external CPU to an internal register that is defined by address bits A0-A2 and \overline{CSA} and \overline{CSB} . NC Not connected. 12, 24, 25, 37 OPA, OPB 32, 9 0 User defined outputs. This function is associated with individual channels A and B. The state of these pins is defined by the user through the software settings of MCR[3]. INTA-INTB are set to active mode and OPA-OPB to a logic 0 when MCR[3] is set to a logic 1. INTA-INTB are set to the 3-State mode and OPA-OPB to a logic 1 when MCR[3] is set to a logic 0. The output of these two pins is HIGH after reset. RESET 36 I Reset. This pin will reset the internal registers and all the outputs. The UART transmitter output and the receiver input will be disabled during reset time. RESET is an active-HIGH input. RIA, RIB 41, 21 Ring Indicator (Active-LOW). These inputs are associated with individual UART I channels, A and B. A logic 0 on these pins indicates the modem has received a ringing signal from the telephone line. A LOW-to-HIGH transition on these input pins generates a modem status interrupt, if enabled. The state of these inputs is reflected in the modem status register (MSR).

Table 2:

Dual UART with 64-byte FIFO

Symbol	Pin	Туре	Description
RTSA, RTSB	33, 22	0	Request to Send (Active-LOW). These outputs are associated with individual UART channels, A and B. A logic 0 on the RTS pin indicates the transmitter has data ready and waiting to send. Writing a logic 1 in the modem control register MCR[1] will set this pin to a logic 0, indicating data is available. After a reset these pins are set to a logic 1. These pins only affect the transmit and receive operations when Auto-RTS function is enabled via the Enhanced Feature Register (EFR[6]) for hardware flow control operation.
RXA, RXB	5, 4	I	Receive data input. These inputs are associated with individual serial channel data to the SC16C752. During the local loop-back mode, these RX input pins are disabled and TX data is connected to the UART RX input internally.
RXRDYA, RXRDYB	31, 18	0	Receive Ready (Active-LOW). RXRDYA or RXRDYB goes LOW when the trigger level has been reached or the FIFO has at least one character. It goes HIGH when the RX FIFO is empty.
TXA, TXB	7, 8	0	Transmit data A, B. These outputs are associated with individual serial transmit channel data from the SC16C752. During the local loop-back mode, the TX output pin is disabled and TX data is internally connected to the UART RX input.
TXRDYA, TXRDYB	43, 6	0	Transmit Ready (Active-LOW). TXRDYA or TXRDYB go LOW when there are at least a trigger level number of spaces available or when the FIFO is empty. It goes HIGH when the FIFO is full or not empty.
V _{CC}	42	I	Power supply input.
XTAL1	13	I	Crystal or external clock input. Functions as a crystal input or as an external clock input. A crystal can be connected between XTAL1 and XTAL2 to form an internal oscillator circuit (see Figure 12). Alternatively, an external clock can be connected to this pin to provide custom data rates.
XTAL2	14	0	Output of the crystal oscillator or buffered clock. (See also XTAL1.) XTAL2 is used as a crystal oscillator output or a buffered clock output.

Pin description...continued

Functional description 6.

The SC16C752 UART is pin-compatible with the SC16C2550 UART. It provides more enhanced features. All additional features are provided through a special enhanced feature register.

The UART will perform serial-to-parallel conversion on data characters received from peripheral devices or modems, and parallel-to-parallel conversion on data characters transmitted by the processor. The complete status of each channel of the SC16C752 UART can be read at any time during functional operation by the processor.

The SC16C752 can be placed in an alternate mode (FIFO mode) relieving the processor of excessive software overhead by buffering received/transmitted characters. Both the receiver and transmitter FIFOs can store up to 64 bytes (including three additional bits of error status per byte for the receiver FIFO) and have selectable or programmable trigger levels. Primary outputs RXRDY and TXRDY allow signalling of DMA transfers.

The SC16C752 has selectable hardware flow control and software flow control. Hardware flow control significantly reduces software overhead and increases system efficiency by automatically controlling serial data flow using the $\overline{\text{RTS}}$ output and $\overline{\text{CTS}}$ input signals. Software flow control automatically controls data flow by using programmable Xon/Xoff characters.

The UART includes a programmable baud rate generator that can divide the timing reference clock input by a divisor between 1 and $(2^{16} - 1)$.

6.1 Trigger levels

The SC16C752 provides independent selectable and programmable trigger levels for both receiver and transmitter DMA and interrupt generation. After reset, both transmitter and receiver FIFOs are disabled and so, in effect, the trigger level is the default value of one byte. The selectable trigger levels are available via the FCR. The programmable trigger levels are available via the TLR.


6.2 Hardware flow control

Hardware flow control is comprised of Auto- $\overline{\text{CTS}}$ and Auto- $\overline{\text{RTS}}$. Auto- $\overline{\text{CTS}}$ and Auto- $\overline{\text{RTS}}$ can be enabled/disabled independently by programming EFR[7:6].

With Auto- $\overline{\text{CTS}}$, $\overline{\text{CTS}}$ must be active before the UART can transmit data.


Auto- $\overline{\text{RTS}}$ only activates the $\overline{\text{RTS}}$ output when there is enough room in the FIFO to receive data and de-activates the $\overline{\text{RTS}}$ output when the RX FIFO is sufficiently full. The halt and resume trigger levels in the TCR determine the levels at which $\overline{\text{RTS}}$ is activated/deactivated.

If both Auto- $\overline{\text{CTS}}$ and Auto- $\overline{\text{RTS}}$ are enabled, when $\overline{\text{RTS}}$ is connected to $\overline{\text{CTS}}$, data transmission does not occur unless the receiver FIFO has empty space. Thus, overrun errors are eliminated during hardware flow control. If not enabled, overrun errors occur if the transmit data rate exceeds the receive FIFO servicing latency.




6.2.1 Auto-RTS

Auto-RTS data flow control originates in the receiver block (see Figure 1 "Block diagram." on page 3). Figure 4 shows RTS functional timing. The receiver FIFO trigger levels used in Auto-RTS are stored in the TCR. RTS is active if the RX FIFO level is below the halt trigger level in TCR[3:0]. When the receiver FIFO halt trigger level is reached, RTS is deasserted. The sending device (e.g., another UART) may send an additional byte after the trigger level is reached (assuming the sending UART has another byte to send) because it may not recognize the deassertion of RTS until it has begun sending the additional byte. RTS is automatically reasserted once the receiver FIFO reaches the resume trigger level programmed via TCR[7:4]. This reassertion allows the sending device to resume transmission.



6.2.2 Auto-CTS

The transmitter circuitry checks $\overline{\text{CTS}}$ before sending the next data byte. When $\overline{\text{CTS}}$ is active, the transmitter sends the next byte. To stop the transmitter from sending the following byte, $\overline{\text{CTS}}$ must be deasserted before the middle of the last stop bit that is currently being sent. The auto- $\overline{\text{CTS}}$ function reduces interrupts to the host system. When flow control is enabled, $\overline{\text{CTS}}$ level changes do not trigger host interrupts because the device automatically controls its own transmitter. Without auto- $\overline{\text{CTS}}$, the transmitter sends any data present in the transmit FIFO and a receiver overrun error may result.



6.3 Software flow control

Software flow control is enabled through the enhanced feature register and the modem control register. Different combinations of software flow control can be enabled by setting different combinations of EFR[3:0]. Table 3 shows software flow control options.

EFR[3]	EFR[2]	EFR[1]	EFR[0]	TX, RX software flow controls			
0	0	Х	Х	no transmit flow control			
1	0	Х	Х	transmit Xon1, Xoff1			
0	1	Х	Х	transmit Xon2, Xoff2			
1	1	Х	Х	transmit Xon1, Xon2, Xoff1, Xoff2			
Х	Х	0	0	no receive flow control			
Х	Х	1	0	receiver compared Xon1, Xoff1			
Х	Х	0	1	receiver compares Xon2, Xoff2			
1	0	1	1	transmit Xon1, Xoff1			
				receiver compares Xon1 and Xon2, Xoff1 and Xoff2			
0	1	1	1	transmit Xon2, Xoff2			
				receiver compares Xon1 and Xon2, Xoff1 and Xoff2			
1	1	1	1	transmit Xon1, Xon2, Xoff1, Xoff2			
				receiver compares Xon1 and Xon2, Xoff1 and Xoff2			

 Table 3:
 Software flow control options (EFR[0:3])

Remark: When using software flow control, the Xon/Xoff characters cannot be used for data characters.

There are two other enhanced features relating to software flow control:

- Xon Any function (MCR[5]): Operation will resume after receiving any character after recognizing the Xoff character. It is possible that an Xon1 character is recognized as an Xon Any character, which could cause an Xon2 character to be written to the RX FIFO.
- Special character (EFR[5]): Incoming data is compared to Xoff2. Detection of the special character sets the Xoff interrupt (IIR[4]) but does not halt transmission. The Xoff interrupt is cleared by a read of the IIR. The special character is transferred to the RX FIFO.

6.3.1 RX

When software flow control operation is enabled, the SC16C752 will compare incoming data with Xoff1,2 programmed characters (in certain cases, Xoff1 and Xoff2 must be received sequentially). When the correct Xoff character are received, transmission is halted after completing transmission of the current character. Xoff detection also sets IIR[4] (if enabled via IER[5]) and causes INT to go HIGH.

To resume transmission, an Xon1,2 character must be received (in certain cases Xon1 and Xon2 must be received sequentially). When the correct Xon characters are received, IIR[4] is cleared, and the Xoff interrupt disappears.

6.3.2 TX


Xoff1/2 character is transmitted when the RX FIFO has passed the HALT trigger level programmed in TCR[3:0].

Xon1/2 character is transmitted when the RX FIFO reaches the RESUME trigger level programmed in TCR[7:4].

The transmission of Xoff/Xon(s) follows the exact same protocol as transmission of an ordinary byte from the FIFO. This means that even if the word length is set to be 5, 6, or 7 characters, then the 5, 6, or 7 least significant bits of Xoff1,2/Xon1,2 will be transmitted. (Note that the transmission of 5, 6, or 7 bits of a character is seldom done, but this functionality is included to maintain compatibility with earlier designs.)

It is assumed that software flow control and hardware flow control will never be enabled simultaneously. Figure 6 shows an example of software flow control.

6.3.3 Software flow control example



Assumptions: UART1 is transmitting a large text file to UART2. Both UARTs are using software flow control with single character Xoff (0F) and Xon (0D) tokens. Both have Xoff threshold (TCR[3:0] = F) set to 60, and Xon threshold (TCR[7:4] = 8) set to 32. Both have the interrupt receive threshold (TLR[7:4] = D) set to 52.

UART 1 begins transmission and sends 52 characters, at which point UART2 will generate an interrupt to its processor to service the RCV FIFO, but assume the interrupt latency is fairly long. UART1 will continue sending characters until a total of

9397 750 11635

60 characters have been sent. At this time, UART2 will transmit a 0F to UART1, informing UART1 to halt transmission. UART1 will likely send the 61st character while UART2 is sending the Xoff character. Now UART2 is serviced and the processor reads enough data out of the RX FIFO that the level drops to 32. UART2 will now send a 0D to UART1, informing UART1 to resume transmission.

6.4 Reset

Table 4 summarizes the state of register after reset.

Table 4: Register reset functions								
Register	Reset control	Reset state						
Interrupt enable register	RESET	All bits cleared.						
Interrupt identification register	RESET	Bit 0 is set. All other bits cleared.						
FIFO control register	RESET	All bits cleared.						
Line control register	RESET	Reset to 00011101 (1D hex).						
Modem control register	RESET	All bits cleared.						
Line status register	RESET	Bits 5 and 6 set. All other bits cleared.						
Modem status register	RESET	Bits 0-3 cleared. Bits 4-7 input signals.						
Enhanced feature register	RESET	All bits cleared.						
Receiver holding register	RESET	Pointer logic cleared.						
Transmitter holding register	RESET	Pointer logic cleared.						
Transmission control register	RESET	All bits cleared.						
Trigger level register	RESET	All bits cleared.						

[1] Registers DLL, DLH, SPR, Xon1, Xon2, Xoff1, Xoff2 are not reset by the top-level reset signal RESET, i.e., they hold their initialization values during reset.

Table 5 summarizes the state of registers after reset.

Table 5: Signal RESET functions

Signal	Reset control	Reset state
ТΧ	RESET	high
RTS	RESET	high
DTR	RESET	high
RXRDY	RESET	high
TXRDY	RESET	low

6.5 Interrupts

The SC16C752 has interrupt generation and prioritization (six prioritized levels of interrupts) capability. The interrupt enable register (IER) enables each of the six types of interrupts and the INT signal in response to an interrupt generation. The IER can also disable the interrupt system by clearing bits 0-3, 5-7. When an interrupt is generated, the IIR indicates that an interrupt is pending and provides the type of interrupt through IIR[5;0]. Table 6 summarizes the interrupt control functions.


Priority	Independent to see a		
level	Interrupt type	Interrupt source	Interrupt reset method
None	none	none	none
1	receiver line status	OE, FE, PE, or BI errors occur in characters in the RX FIFO	FE, PE, BI: all erroneous characters are read from the RX FIFO.
			OE: read LSR
2	RX time-out	stale data in RX FIFO	read RHR
2	RHR interrupt	DRDY (data ready)	read RHR
		(FIFO disable)	
		RX FIFO above trigger level	
		(FIFO enable)	
3	THR interrupt	TFE (THR empty)	read IIR or a write to the THR
		(FIFO disable)	
		TX FIFO passes above trigger level	
		(FIFO enable)	
4	modem status	MSR[3:0] = 0	read MSR
5	Xoff interrupt	receive Xoff character(s)/special character	receive Xon character(s)/Read of IIR
6	CTS, RTS	$\overline{\text{RTS}}$ pin or $\overline{\text{CTS}}$ pin change state from active (LOW) to inactive (HIGH)	read IIR
	1 2 2 3 3 4 5	1receiver line status2RX time-out2RHR interrupt3THR interrupt4modem status5Xoff interrupt	1 receiver line status OE, FE, PE, or BI errors occur in characters in the RX FIFO 2 RX time-out stale data in RX FIFO 2 RHR interrupt DRDY (data ready) (FIFO disable) RX FIFO above trigger level (FIFO enable) 3 THR interrupt TFE (THR empty) (FIFO disable) TX FIFO passes above trigger level (FIFO enable) 4 modem status MSR[3:0] = 0 5 Xoff interrupt RTS pin or CTS pin change state from

It is important to note that for the framing error, parity error, and break conditions, LSR[7] generates the interrupt. LSR[7] is set when there is an error anywhere in the RX FIFO, and is cleared only when there are no more errors remaining in the FIFO. LSR[4:2] always represent the error status for the received character at the top of the RX FIFO. Reading the RX FIFO updates LSR[4:2] to the appropriate status for the new character at the top of the FIFO. If the RX FIFO is empty, then LSR[4:2] are all zeros.

For the Xoff interrupt, if an Xoff flow character detection caused the interrupt, the interrupt is cleared by an Xon flow character detection. If a special character detection caused the interrupt, the interrupt is cleared by a read of the LSR.


6.5.1 Interrupt mode operation

In interrupt mode (if any bit of IER[3:0] is 1) the processor is informed of the status of the receiver and transmitter by an interrupt signal, INT. Therefore, it is not necessary to continuously poll the line status register (LSR) to see if any interrupt needs to be serviced. Figure 7 shows interrupt mode operation.



6.5.2 Polled mode operation

In polled mode (IER[3:0] = 0000) the status of the receiver and transmitter can be checked by polling the line status register (LSR). This mode is an alternative to the FIFO interrupt mode of operation where the status of the receiver and transmitter is automatically known by means of interrupts sent to the CPU. Figure 8 shows FIFO polled mode operation.




6.6 DMA operation

There are two modes of DMA operation, DMA mode 0 or DMA mode 1, selected by FCR[3].

In DMA mode 0 or FIFO disable (FCR[0] = 0) DMA occurs in single character transfers. In DMA mode 1, multi-character (or block) DMA transfers are managed to relieve the processor for longer periods of time.

6.6.1 Single DMA transfers (DMA mode 0/FIFO disable)

Figure 9 shows TXRDY and RXRDY in DMA mode 0/FIFO disable.




Transmitter: When empty, the TXRDY signal becomes active. TXRDY will go inactive after one character has been loaded into it.

Receiver: RXRDY is active when there is at least one character in the FIFO. It becomes inactive when the receiver is empty.

6.6.2 Block DMA transfers (DMA mode 1)

Figure 10 shows TXRDY and RXRDY in DMA mode 1.



Transmitter: TXRDY is active when there is a trigger level number of spaces available. It becomes inactive when the FIFO is full.

Receiver: RXRDY becomes active when the trigger level has been reached, or when a time-out interrupt occurs. It will go inactive when the FIFO is empty or an error in the RX FIFO is flagged by LSR[7].

6.7 Sleep mode

Sleep mode is an enhanced feature of the SC16C752 UART. It is enabled when EFR[4], the enhanced functions bit, is set **and** when IER[4] is set. Sleep mode is entered when:

- The serial data input line, RX, is idle (see Section 6.8 "Break and time-out conditions").
- The TX FIFO and TX shift register are empty.
- There are no interrupts pending except THR and time-out interrupts.

Remark: Sleep mode will not be entered if there is data in the RX FIFO.

In sleep mode, the UART clock and baud rate clock are stopped. Since most registers are clocked using these clocks, the power consumption is greatly reduced. The UART will wake up when any change is detected on the RX line, when there is any change in the state of the modem input pins, or if data is written to the TX FIFO.

Remark: Writing to the divisor latches, DLL and DLH, to set the baud clock, must not be done during sleep mode. Therefore, it is advisable to disable sleep mode using IER[4] before writing to DLL or DLH.

6.8 Break and time-out conditions

An RX idle condition is detected when the receiver line, RX, has been HIGH for 4 character time. The receiver line is sampled midway through each bit.

When a break condition occurs, the TX line is pulled LOW. A break condition is activated by setting LCR[6].

6.9 **Programmable baud rate generator**

The SC16C752 UART contains a programmable baud generator that takes any clock input and divides it by a divisor in the range between 1 and $(2^{16} - 1)$. An additional divide-by-4 prescaler is also available and can be selected by MCR[7], as shown in Figure 11. The output frequency of the baud rate generator is 16× the baud rate. The formula for the divisor is:


divisor = $\frac{\left(\frac{\text{XTAL1 crystal input frequency}}{\text{prescaler}}\right)}{(\text{desired baud rate} \times 16)}$

Where:

prescaler = 1, when MCR[7] is set to 0 after reset (divide-by-1 clock selected) prescaler = 4, when MCR[7] is set to 1 after reset (divide-by-4 clock selected).

Remark: The default value of prescaler after reset is divide-by-1.

Figure 11 shows the internal prescaler and baud rate generator circuitry.



DLL and DLH must be written to in order to program the baud rate. DLL and DLH are the least significant and most significant byte of the baud rate divisor. If DLL and DLH are both zero, the UART is effectively disabled, as no baud clock will be generated.

Remark: The programmable baud rate generator is provided to select both the transmit and receive clock rates.

Table 7 and Table 8 show the baud rate and divisor correlation for crystal with frequency 1.8432 MHz and 3.072 MHz, respectively.

Figure 12 shows the crystal clock circuit reference.


Dual UART with 64-byte FIFO

Desired baud rate	Divisor used to generate $16 \times clock$	Percent error difference between desired and actual
50	2304	
75	1536	
110	1047	0.026
134.5	857	0.058
150	768	
300	384	
600	192	
1200	96	
1800	64	
2000	58	0.69
2400	48	
3600	32	
4800	24	
7200	16	
9600	12	
19200	6	
38400	3	
56000	2	2.86

Table 7: Baud rates using a 1.8432 MHz crystal

Table 8:Baud rates using a 3.072 MHz crystal

Divisor used to generate $16 \times clock$	Percent error difference between desired and actual
2304	
2560	
1745	0.026
1428	0.034
1280	
640	
320	
160	
107	0.312
96	
80	
53	0.628
40	
27	1.23
20	
10	
5	
	16 × clock 2304 2560 1745 1428 1280 640 320 160 107 96 80 53 40 27 20 10



7. Register descriptions

Each register is selected using address lines A0, A1, A2, and in some cases, bits from other registers. The programming combinations for register selection are shown in Table 9.

A2	A1	A0	Read mode	Write mode
0	0	0	receive holding register (RHR)	transmit holding register (THR)
0	0	1	interrupt enable register (IER)	interrupt enable register
0	1	0	interrupt identification register (IIR)	FIFO control register (FCR)
0	1	1	line control register (LCR)	line control register
1	0	0	modem control register (MCR) ^[1]	modem control register ^[1]
1	0	1	line status register (LSR)	
1	1	0	modem status register (MSR)	
1	1	1	scratchpad register (SPR)	scratchpad register
0	0	0	divisor latch LSB (DLL) ^{[2], [3]}	divisor latch LSB ^{[2], [3]}
0	0	1	divisor latch MSB (DLH) ^{[2], [3]}	divisor latch MSB ^{[2], [3]}
0	1	0	enhanced feature register (EFR) ^{[2], [4]}	enhanced feature register ^{[2], [4]}
1	0	0	Xon1 word ^{[2], [4]}	Xon1 word ^{[2], [4]}
1	0	1	Xon2 word ^{[2], [4]}	Xon2 word ^{[2], [4]}
1	1	0	Xoff1 word ^{[2], [4]}	Xoff1 word ^{[2], [4]}
1	1	1	Xoff2 word ^{[2], [4]}	Xoff2 word ^{[2], [4]}
1	1	0	transmission control register (TCR) ^{[2], [5]}	transmission control register ^{[2], [5]}
1	1	1	trigger level register (TLR) ^{[2], [5]}	trigger level register ^{[2], [5]}
1	1	1	FIFO ready register ^{[2], [6]}	

Table 9: Register map - read/write properties

[1] MCR[7] can only be modified when EFR[4] is set.

[2] Accessed by a combination of address pins and register bits.

[3] Accessible only when LCR[7] is logic 1.

[4] Accessible only when LCR is set to 10111111 (8hBF).

[5] Accessible only when EFR[4] = 1 and MCR[6] = 1, i.e., EFR[4] and MCR[6] are read/write enables.

[6] Accessible only when \overline{CSA} or $\overline{CSB} = 0$, MCR[2] = 1, and loop-back is disabled (MCR[4] = 0).

Table 10 lists and describes the SC16C752 internal registers.

Table 10: SC16C752 internal registers

Shaded bits are only accessible when EFR[4] is set.

A2	A1	A0	Register	Bit 7	Bit 6	Bit 5	Bit 4	Bit 3	Bit 2	Bit 1	Bit 0	Read/ Write
Ger	hera	l Reg	gister Set ^{[1}	j								
0	0	0	RHR	bit 7	bit 6	bit 5	bit 4	bit 3	bit 2	bit 1	bit 0	R
0	0	0	THR	bit 7	bit 6	bit 5	bit 4	bit 3	bit 2	bit 1	bit 0	W
0	0	1	IER	0/CTS interrupt enable ^[2]	0/RTS interrupt enable ^[2]	0/Xoff ^[2]	0/X sleep mode ^[2]	modem status interrupt	receive line status interrupt	THR empty interrupt	Rx data available interrupt	R/W
0	1	0	FCR	RX trigger level (MSB)	RX trigger level (LSB)	0/TX trigger level (MSB) ^[2]	0/TX trigger level (LSB) ^[2]	DMA mode select	TX FIFO reset	RX FIFO reset	FIFO enable	W
0	1	0	IIR	FCR[0]	FCR[0]	0/CTS, RTS	0/Xoff	interrupt priority bit 2	interrupt priority bit 1	interrupt priority bit 0	interrupt status	R
0	1	1	LCR	DLAB	break control bit	set parity	parity type select	parity enable	number of stop bits	word length bit 1	word length bit 0	R/W
1	0	0	MCR	1× or 1×/4 clock	TCR and TLR enable	0/Xon Any	0/enable loop-back	IRQ enable OP	FIFO ready enable	RTS	DTR	R/W
1	0	1	LSR	0/error in RX FIFO	THR and TSR empty	THR empty	break interrupt	framing error	parity error	overrun error	data in receiver	R
1	1	0	MSR	CD	RI	DSR	CTS	ΔCD	ΔRI	ΔDSR	∆CTS	R
1	1	1	SPR	bit 7	bit 6	bit 5	bit 4	bit 3	bit 2	bit 1	bit 0	R/W
1	1	0	TCR	bit 7	bit 6	bit 5	bit 4	bit 3	bit 2	bit 1	bit 0	R/W
1	1	1	TLR	bit 7	bit 6	bit 5	bit 4	bit 3	bit 2	bit 1	bit 0	R/W
1	1	1	FIFO Rdy	0	0	RX FIFO B status	RX FIFO A status	0	0	TX FIFO B status	TX FIFO A status	R
Spe	ecial	Reg	ister Set ^[3]]								
0	0	0	DLL	bit 7	bit 6	bit 5	bit 4	bit 3	bit 2	bit 1	bit 0	R/W
0	0	1	DLH	bit 15	bit 14	bit 13	bit 12	bit 11	bit 10	bit 9	bit 8	R/W
Enł	nanc	ed F	Register Se	et ^[4]								
0	1	0	EFR	Auto CTS	Auto RTS	Special character detect	Enable enhanced functions [2]	software flow control bit 3	software flow control bit 2	software flow control bit 1	software flow control bit 0	R/W
1	0	0	Xon1	bit 7	bit 6	bit 5	bit 4	bit 3	bit 2	bit 1	bit 0	R/W
1	0	1	Xon2	bit 7	bit 6	bit 5	bit 4	bit 3	bit 2	bit 1	bit 0	R/W
1	1	0	Xoff1	bit 7	bit 6	bit 5	bit 4	bit 3	bit 2	bit 1	bit 0	R/W
1	1	1	Xoff2	bit 7	bit 6	bit 5	bit 4	bit 3	bit 2	bit 1	bit 0	R/W

[1] These registers are accessible only when LCR[7] = 0.

[2] The shaded bits in the above table can only be modified if register bit EFR[4] is enabled, i.e., if enhanced functions are enabled.

9397 750 11635

- [3] The Special Register set is accessible only when LCR[7] is set to a logic 1.
- [4] Enhanced Feature Register; Xon-1,2 and Xoff-1,2 are accessible only when LCR is set to 'BF_{Hex}'.

Remark: Refer to the notes under Table 9 for more register access information.

7.1 Receiver holding register (RHR)

The receiver section consists of the receiver holding register (RHR) and the receiver shift register (RSR). The RHR is actually a 64-byte FIFO. The RSR receives serial data from the RX terminal. The data is converted to parallel data and moved to the RHR. The receiver section is controlled by the line control register. If the FIFO is disabled, location zero of the FIFO is used to store the characters.

Remark: In this case, characters are overwritten if overflow occurs.

If overflow occurs, characters are lost. The RHR also stores the error status bits associated with each character.

7.2 Transmit holding register (THR)

The transmitter section consists of the transmit holding register (THR) and the transmit shift register (TSR). The THR is actually a 64-byte FIFO. The THR receives data and shifts it into the TSR, where it is converted to serial data and moved out on the TX terminal. If the FIFO is disabled, the FIFO is still used to store the byte. Characters are lost if overflow occurs.

7.3 FIFO control register (FCR)

This is a write-only register that is used for enabling the FIFOs, clearing the FIFOs, setting transmitter and receiver trigger levels, and selecting the type of DMA signalling. Table 11 shows FIFO control register bit settings.

Table 11: FIFO Control Register bits desc	escription
---	------------

Bit	Symbol	Description
7-6	FCR[7]	RCVR trigger. Sets the trigger level for the RX FIFO.
	(MSB),	00 - 8 characters
	FCR[6] (LSB)	01 - 16 characters
	(LSD)	10 - 56 characters
		11 - 60 characters
5-4	FCR[5]	TX trigger. Sets the trigger level for the TX FIFO.
	(MSB),	00 - 8 spaces
	FCR[4] (LSB)	01 - 16 spaces
	(200)	10 - 32 spaces
		11 - 56 spaces
		FCR[5-4] can only be modified and enabled when EFR[4] is set. This is because the transmit trigger level is regarded as an enhanced function.
3	FCR[3]	DMA mode select.
		Logic 0 = Set DMA mode '0'
		Logic 1 = Set DMA mode '1'
2	FCR[2]	Reset TX FIFO.
		Logic 0 = No FIFO transmit reset (normal default condition).
		Logic 1 = Clears the contents of the transmit FIFO and resets the FIFO counter logic (the transmit shift register is not cleared or altered). This bit will return to a logic 0 after clearing the FIFO.
1	FCR[1]	Reset RX FIFO.
		Logic 0 = No FIFO receive reset (normal default condition).
		Logic 1 = Clears the contents of the receive FIFO and resets the FIFO counter logic (the receive shift register is not cleared or altered). This bit will return to a logic 0 after clearing the FIFO.
0	FCR[0]	FIFO enable.
		Logic 0 = Disable the transmit and receive FIFO (normal default condition).
		Logic 1 = Enable the transmit and receive FIFO.

7.4 Line control register (LCR)

This register controls the data communication format. The word length, number of stop bits, and parity type are selected by writing the appropriate bits to the LCR. Table 12 shows the line control register bit settings.

Table	12: Line Co	ontrol Register bits description					
Bit	Symbol	Description					
7	LCR[7]	Divisor latch enable.					
		Logic 0 = Divisor latch disabled (normal default condition).					
		Logic 1 = Divisor latch enabled.					
6	LCR[6]	Break control bit. When enabled, the Break control bit causes a break condition to be transmitted (the TX output is forced to a logic 0 state). This condition exists until disabled by setting LCR[6] to a logic 0.					
		Logic 0 = no TX break condition (normal default condition).					
		Logic 1 = forces the transmitter output (TX) to a logic 0 to alert the communication terminal to a line break condition.					
5	LCR[5]	Set parity. LCR[5] selects the forced parity format (if LCR[3] = 1).					
		Logic 0 = parity is not forced (normal default condition).					
		LCR[5] = logic 1 and LCR[4] = logic 0: parity bit is forced to a logical 1 for the transmit and receive data.					
		LCR[5] = logic 1 and LCR[4] = logic 1: parity bit is forced to a logical 0 for the transmit and receive data.					
4	LCR[4]	Parity type select.					
		Logic 0 = ODD Parity is generated (if LCR[3] = 1).					
		Logic 1 = EVEN Parity is generated (if LCR[3] = 1).					
3	LCR[3]	Parity enable.					
		Logic 0 = no parity (normal default condition).					
		Logic 1 = a parity bit is generated during transmission and the receiver checks for received parity.					
2	LCR[2]	Number of Stop bits. Specifies the number of stop bits.					
		0 - 1 stop bit (word length = 5, 6, 7, 8)					
		1 - 1.5 stop bits (word length = 5)					
		1 = 2 stop bits (word length = 6, 7, 8)					
1-0	LCR[1-0]	Word length bits 1, 0. These two bits specify the word length to be transmitted or received.					
		00 - 5 bits					
		01 - 6 bits					
		10 - 7 bits					
		11 - 8 bits					

7.5 Line status register (LSR)

Table 13 shows the line status register bit settings.

Bit	Symbol	Description				
7 LSR[7]		FIFO data error.				
		Logic 0 = No error (normal default condition).				
		Logic 1 = At least one parity error, framing error, or break indication is in the receiver FIFO. This bit is cleared when no more errors are present in the FIFO.				
6	LSR[6]	THR and TSR empty. This bit is the Transmit Empty indicator.				
		Logic 0 = Transmitter hold and shift registers are not empty.				
		Logic 1 = Transmitter hold and shift registers are empty.				
5	LSR[5]	THR empty. This bit is the Transmit Holding Register Empty indicator.				
		Logic 0 = Transmit hold register is not empty.				
		Logic 1 = Transmit hold register is empty. The processor can now load up to 64 bytes of data into the THR if the TX FIFO is enabled.				
4	LSR[4]	Break interrupt.				
		Logic 0 = No break condition (normal default condition).				
		Logic 1 = A break condition occurred and associated byte is 00, i.e., RX was LOW for one character time frame.				
3	LSR[3]	Framing error.				
		Logic 0 = No framing error in data being read from RX FIFO (normal default condition).				
		Logic 1 = Framing error occurred in data being read from RX FIFO, i.e received data did not have a valid stop bit.				
2	LSR[2]	Parity error.				
		Logic 0 = No parity error (normal default condition).				
		Logic 1 = Parity error in data being read from RX FIFO.				
1	LSR[1]	Overrun error.				
		Logic 0 = No overrun error (normal default condition).				
		Logic 1 = Overrun error has occurred.				
0	LSR[0]	Data in receiver.				
		Logic 0 = No data in receive FIFO (normal default condition).				
		Logic 1 = At least one character in the RX FIFO.				

When the LSR is read, LSR[4:2] reflect the error bits (BI, FE, PE) of the character at the top of the RX FIFO (next character to be read). The LSR[4:2] registers do not physically exist, as the data read from the RX FIFO is output directly onto the output data bus, DI[4:2], when the LSR is read. Therefore, errors in a character are identified by reading the LSR and then reading the RHR.

LSR[7] is set when there is an error anywhere in the RX FIFO, and is cleared only when there are no more errors remaining in the FIFO.

Reading the LSR does not cause an increment of the RX FIFO read pointer. The RX FIFO read pointer is incremented by reading the RHR.

Remark: The three error bits (parity, framing, break) may not be updated correctly in the first read of the LSR when the input clock (XTAL1) is running faster than 36 MHz. However, the second read is always correct. It is strongly recommended that when using this device with a clock faster than 36 MHz, that the LSR be read twice and only the second read be used for decision making. All other bits in the LSR are correct on all reads.

7.6 Modem control register (MCR)

The MCR controls the interface with the mode, data set, or peripheral device that is emulating the modem. Table 14 shows modem control register bit settings.

6	MCR[7] ^[1] MCR[6] ^[1] MCR[5] ^[1]	Clock select. Logic 0 = Divide-by-1 clock input. Logic 1 = Divide-by-4 clock input. TCR and TLR enable. Logic 0 = no action. Logic 1 = Enable access to the TCR and TLR registers.
		Logic 1 = Divide-by-4 clock input. TCR and TLR enable. Logic 0 = no action.
		TCR and TLR enable. Logic 0 = no action.
		Logic $0 = no$ action.
5	MCR[5] ^[1]	
5	MCR[5] ^[1]	Logic 1 = Enable access to the TCR and TLR registers.
5	MCR[5] [1]	
		Xon Any.
		Logic 0 = Disable Xon Any function.
		Logic 1 = Enable Xon Any function.
4	MCR[4]	Enable loop-back.
		Logic 0 = Normal operating mode.
		Logic 1 = Enable local loop-back mode (internal). In this mode the MCR[3:0] signals are looped back into MSR[7:4] and the TX output is looped back to the RX input internally.
3	MCR[3]	IRQ enable OP.
		Logic 0 = Forces INTA-INTB outputs to the 3-State mode and OP output to HIGH state.
		Logic 1 = Forces the INTA-INTB outputs to the active state and OP output to LOW state. In loop-back mode, controls MSR[7].
2	MCR[2]	FIFO Ready enable.
		Logic 0 = Disable the FIFO Rdy register.
		Logic 1 = Enable the FIFO Rdy register. In loop-back mode, controls MSR[6].
1	MCR[1]	RTS
		Logic 0 = Force \overline{RTS} output to inactive (HIGH).
		Logic 1 = Force $\overline{\text{RTS}}$ output to active (LOW). In loop-back mode, controls MSR[4]. If Auto- $\overline{\text{RTS}}$ is enabled, the $\overline{\text{RTS}}$ output is controlled by hardware flow control.
0	MCR[0]	DTR
		Logic 0 = Force $\overline{\text{DTR}}$ output to inactive (HIGH).
		Logic 1 = Force $\overline{\text{DTR}}$ output to active (LOW). In loop-back mode, controls MSR[5].

Table 14: Modem Control Register bits description

[1] MCR[7:5] can only be modified when EFR[4] is set, i.e., EFR[4] is a write enable.

7.7 Modem status register (MSR)

This 8-bit register provides information about the current state of the control lines from the mode, data set, or peripheral device to the processor. It also indicates when a control input from the modem changes state. Table 15 shows modem status register bit settings per channel.

Table 15:	Modem	Status	Register	hits	description
Table 15.	wouem	Jialus	register	DILS	uescription

		-
Bit	Symbol	Description
7	MSR[7]	CD (Active-HIGH, logical 1). This bit is the complement of the $\overline{\text{CD}}$ input during normal mode. During internal loop-back mode, it is equivalent to MCR[3].
6	MSR[6]	RI (Active-HIGH, logical 1). This bit is the complement of the \overline{RI} input during normal mode. During internal loop-back mode, it is equivalent to MCR[2].
5	MSR[5]	DSR (Active-HIGH, logical 1). This bit is the complement of the $\overline{\text{DSR}}$ input during normal mode. During internal loop-back mode, it is equivalent MCR[0].
4	MSR[4]	CTS (Active-HIGH, logical 1). This bit is the complement of the $\overline{\text{CTS}}$ input during normal mode. During internal loop-back mode, it is equivalent to MCR[1].
3	MSR[3]	Δ CD. Indicates that $\overline{\text{CD}}$ input (or MCR[3] in loop-back mode) has changed state. Cleared on a read.
2	MSR[2]	ΔRI . Indicates that \overline{RI} input (or MCR[2] in loop-back mode) has changed state from LOW to HIGH. Cleared on a read.
1	MSR[1]	ΔDSR . Indicates that \overline{DSR} input (or MCR[0] in loop-back mode) has changed state. Cleared on a read.
0	MSR[0]	Δ CTS. Indicates that CTS input (or MCR[1] in loop-back mode) has changed state. Cleared on a read.

[1] The primary inputs RI, CD, CTS, DSR are all Active-LOW, but their registered equivalents in the MSR and MCR (in loop-back) registers are Active-HIGH.

7.8 Interrupt enable register (IER)

The interrupt enable register (IER) enables each of the six types of interrupt, receiver error, RHR interrupt, THR interrupt, Xoff received, or CTS/RTS change of state from LOW to HIGH. The INT output signal is activated in response to interrupt generation. Table 16 shows interrupt enable register bit settings.

 Table 16:
 Interrupt Enable Register bits description

Bit	Symbol	Description
7	IER[7] ^[1]	CTS interrupt enable.
		Logic 0 = Disable the \overline{CTS} interrupt (normal default condition).
		Logic 1 = Enable the \overline{CTS} interrupt.
6	IER[6] ^[1]	RTS interrupt enable.
		Logic 0 = Disable the $\overline{\text{RTS}}$ interrupt (normal default condition).
		Logic 1 = Enable the $\overline{\text{RTS}}$ interrupt.
5	IER[5] ^[1]	Xoff interrupt.
		Logic 0 = Disable the Xoff interrupt (normal default condition).
		Logic 1 = Enable the Xoff interrupt.

© Koninklijke Philips Electronics N.V. 2003. All rights reserved

Dual UART with 64-byte FIFO

lable	16: Interi	rupt Enable Register bits descriptioncontinued						
Bit	Symbol	Description						
4 IER[4] ^[1]		Sleep mode.						
		Logic 0 = Disable sleep mode (normal default condition).						
		Logic 1 = Enable sleep mode. See Section 6.7 "Sleep mode" for details.						
3	IER[3]	Modem Status Interrupt.						
		Logic 0 = Disable the modem status register interrupt (normal default condition).						
		Logic 1 = Enable the modem status register interrupt.						
2	IER[2]	Receive Line Status interrupt.						
		Logic 0 = Disable the receiver line status interrupt (normal default condition).						
		Logic 1 = Enable the receiver line status interrupt.						
1	IER[1]	Transmit Holding Register interrupt.						
		Logic 0 = Disable the THR interrupt (normal default condition).						
		Logic 1 = Enable the THR interrupt.						
0	IER[0]	Receive Holding Register interrupt.						
		Logic 0 = Disable the RHR interrupt (normal default condition).						
		Logic 1 = Enable the RHR interrupt.						

 Table 16:
 Interrupt Enable Register bits description...continued

[1] IER[7:4] can only be modified if EFR[4] is set, i.e., EFR[4] is a write enable. Re-enabling IER[1] will not cause a new interrupt if the THR is below the threshold.

7.9 Interrupt identification register (IIR)

The IIR is a read-only 8-bit register which provides the source of the interrupt in a prioritized manner. Table 17 shows interrupt identification register bit settings.

Bit	Symbol	Description			
7-6	IIR[7:6]	Mirror the contents of FCR[0].			
5	IIR[5]	RTS/CTS LOW-to-HIGH change of state.			
4	IIR[4]	1 = Xoff/Special character has been detected.			
3-1	IIR[3:1]	3-bit encoded interrupt. See Table 18.			
0	IIR[0]	Interrupt status.			
		Logic 0 = An interrupt is pending.			
		Logic 1 = No interrupt is pending.			

Table 17: Interrupt Identification Register bits description

The interrupt priority list is shown in Table 18.

Dual UART with 64-byte FIFO

Table 18:	Interru	ipt priori	ty list				
Priority level	lir[5]	IIR[4]	IIR[3]	IIR[2]	IIR[1]	IIR[0]	Source of the interrupt
1	0	0	0	1	1	0	Receiver Line Status error
2	0	0	1	1	0	0	Receiver time-out interrupt
2	0	0	0	1	0	0	RHR interrupt
3	0	0	0	0	1	0	THR interrupt
4	0	0	0	0	0	0	Modem interrupt
5	0	1	0	0	0	0	Received Xoff signal/ special character
6	1	0	0	0	0	0	CTS, RTS change of state from active (LOW) to inactive (HIGH)

7.10 Enhanced feature register (EFR)

This 8-bit register enables or disables the enhanced features of the UART. Table 19 shows the enhanced feature register bit settings.

Bit	Symbol	Description
7	EFR[7]	CTS flow control enable.
		Logic $0 = \overline{CTS}$ flow control is disabled (normal default condition).
		Logic 1 = \overline{CTS} flow control is enabled. Transmission will stop when a HIGH signal is detected on the \overline{CTS} pin.
6	EFR[6]	RTS flow control enable.
		Logic 0 = \overline{RTS} flow control is disabled (normal default condition).
		Logic 1 = $\overline{\text{RTS}}$ flow control is enabled. The $\overline{\text{RTS}}$ pin goes HIGH when the receiver FIFO HALT trigger level TCR[3:0] is reached, and goes LOW when the receiver FIFO RESUME transmission trigger level TCR[7:4] is reached.
5	EFR[5]	Special character detect.
		Logic 0 = Special character detect disabled (normal default condition).
		Logic 1 = Special character detect enabled. Received data is compared with Xoff-2 data. If a match occurs, the received data is transferred to FIFO and IIR[4] is set to a logical 1 to indicate a special character has been detected.
4	EFR[4]	Enhanced functions enable bit.
		Logic 0 = Disables enhanced functions and writing to IER[7:4], FCR[5:4], MCR[7:5].
		Logic 1 = Enables the enhanced function IER[7:4], FCR[5:4], and MCR[7:5] can be modified, i.e., this bit is therefore a write enable.
3-0	EFR[3:0]	Combinations of software flow control can be selected by programming these bits. See Table 3 "Software flow control options (EFR[0:3])" on page 9.

Table 19: Enhanced Feature Register bits description

7.11 Divisor latches (DLL, DLH)

These are two 8-bit registers which store the 16-bit divisor for generation of the baud clock in the baud rate generator. DLH stores the most significant part of the divisor. DLL stores the least significant part of the divisor.

Note that DLL and DLH can only be written to before sleep mode is enabled, i.e., before IER[4] is set.

7.12 Transmission control register (TCR)

This 8-bit register is used to store the RX FIFO threshold levels to stop/start transmission during hardware/software flow control. Table 20 shows transmission control register bit settings.

Bit	Symbol	Description
7-4	TCR[7:4]	RX FIFO trigger level to resume transmission (0-60).
3-0	TCR[3:0]	RX FIFO trigger level to halt transmission (0-60).

TCR trigger levels are available from 0-60 bytes with a granularity of four.

Remark: TCR can only be written to when EFR[4] = 1 and MCR[6] = 1. The programmer must program the TCR such that TCR[3:0] > TCR[7:4]. There is no built-in hardware check to make sure this condition is met. Also, the TCR must be programmed with this condition before Auto- \overline{RTS} or software flow control is enabled to avoid spurious operation of the device.

7.13 Trigger level register (TLR)

This 8-bit register is pulsed to store the transmit and received FIFO trigger levels used for DMA and interrupt generation. Trigger levels from 4-60 can be programmed with a granularity of 4. Table 21 shows trigger level register bit settings.

Table 21: Trigger Level Register bits description

Bit	Symbol	Description
7-4	TLR[7:4]	RX FIFO trigger levels (4-60), number of characters available.
3-0	TLR[3:0]	TX FIFO trigger levels (4-60), number of spaces available.

Remark: TLR can only be written to when EFR[4] = 1 and MCR[6] = 1. If TLR[3:0] or TLR[7:4] are logical 0, the selectable trigger levels via the FIFO control register (FCR) are used for the transmit and receive FIFO trigger levels. Trigger levels from 4-60 bytes are available with a granularity of four. The TLR should be programmed for N_{4}^{\prime} , where N is the desired trigger level.

When the trigger level setting in TLR is zero, the SC16C752 uses the trigger level setting defined in FCR. If TLR has non-zero trigger level value, the trigger level defined in FCR is discarded. This applies to both transmit FIFO and receive FIFO trigger level setting.

When TLR is used for RX trigger level control, ICR[7:6] should be left at the default state, i.e., '00'.

7.14 FIFO ready register

The FIFO ready register provides real-time status of the transmit and receive FIFOs of both channels.

Table	Table 22: FIFO Ready Register bits description					
Bit	Symbol	Description				
7-6	FIFO Rdy[7:6]	Unused; always 0.				
5	FIFO Rdy[5]	RX FIFO B status. Related to DMA.				
4	FIFO Rdy[4]	RX FIFO A status. Related to DMA.				
3-2	FIFO Rdy[3:2]	Unused; always 0.				
1	FIFO Rdy[1]	TX FIFO B status. Related to DMA.				
0	FIFO Rdy[0]	TX FIFO A status. Related to DMA.				

Table 22: FIFO Ready Register bits description

The FIFO Rdy register is a read-only register that can be accessed when any of the two UARTs is selected \overline{CSA} or $\overline{CSB} = 0$, MCR[2] (FIFO Rdy Enable) is a logic 1, and loop-back is disabled. The address is 111.

8. Programmer's guide

The base set of registers that is used during high-speed data transfer have a straightforward access method. The extended function registers require special access bits to be decoded along with the address lines. The following guide will help with programming these registers. Note that the descriptions below are for individual register access. Some streamlining through interleaving can be obtained when programming all the registers.

Table 23:	Register	programming	guide
-----------	----------	-------------	-------

Table 23: Register programming guid	
Command	Actions
Set baud rate to VALUE1, VALUE2	Read LCR (03), save in temp
	Set LCR (03) to 80
	Set DLL (00) to VALUE1
	SET DLM (01) to VALUE2
	Set LCR (03) to temp
Set Xoff-1, Xon-1 to VALUE1, VALUE2	Read LCR (03), save in temp
	Set LCR (03) to BF
	Set Xoff-1 (06) to VALUE1
	SET Xon-1 (04) to VALUE2
	Set LCR (03) to temp
Set Xoff-2, Xon-2 to VALUE1, VALUE2	Read LCR (03), save in temp
	Set LCR (03) to BF
	Set Xoff-2 (07) to VALUE1
	SET Xon-2 (05) to VALUE2
	Set LCR (03) to temp
Set software flow control mode to	Read LCR (03), save in temp
VALUE	Set LCR (03) to BF
	Set EFR (02) to VALUE
	Set LCR (03) to temp
Set flow control threshold to VALUE	Read LCR (03), save in temp1
	Set LCR (03) to BF
	Read EFR (02), save in temp2
	Set EFR (02) to 10 + temp2
	Set LCR (03) to 00
	Read MCR (04), save in temp3
	Set MCR (04) to 40 + temp3
	Set TCR (06) to VALUE
	Set I CR (04) to temp3
	Set LCR (03) to BF
	Set EFR (02) to temp2
	Set LCR (03) to temp1

Command	Actions
Set TX FIFO and RX FIFO thresholds	Read LCR (03), save in temp1
to VALUE	Set LCR (03) to BF
	Read EFR (02), save in temp2
	Set EFR (02) to 10 + temp2
	Set LCR (03) to 00
	Read MCR (04), save in temp3
	Set MCR (04) to 40 + temp3
	Set TLR (07) to VALUE
	Set MCR (04) to temp3
	Set LCR (03) to BF
	Set EFR (02) to temp2
	Set LCR (03) to temp1
Read FIFO Rdy register	Read MCR (04), save in temp1
	Set temp2 = temp1 \times EF ^[1]
	Set MCR (04) = 40 + temp2
	Read FFR (07), save in temp2
	Pass temp2 back to host
	Set MCR (04) to temp1
Set prescaler value to divide-by-1	Read LCR (03), save in temp1
	Set LCR (03) to BF
	Read EFR (02), save in temp2
	Set EFR (02) to 10 + temp2
	Set LCR (03) to 00
	Read MCR (04), save in temp3
	Set MCR (04) to temp $3 \times 7F^{[1]}$
	Set LCR (03) to BF
	Set EFR (02) to temp2
	Set LCR (03) to temp1
Set prescaler value to divide-by-4	Read LCR (03), save in temp1
	Set LCR (03) to BF
	Read EFR (02), save in temp2
	Set EFR (02) to 10 + temp2
	Set LCR (03) to 00
	Read MCR (04), save in temp3
	Set MCR (04) to temp3 + 80
	Set LCR (03) to BF
	Set EFR (02) to temp2

Table 23: Register programming guide...continued

[1] \times sign here means bit-AND.

9. Limiting values

Table 24: Limiting values

In accordance with the Absolute Maximum Rating System (IEC 60134).

		•••			
Symbol	Parameter	Conditions	Min	Мах	Unit
V _{CC}	supply voltage		-	7	V
VI	input voltage		-0.3	V _{CC} + 0.3	V
Vo	output voltage		-0.3	V _{CC} + 0.3	V
T _{amb}	operating ambient temperature	in free-air	-40	+85	°C
T _{stg}	storage temperature		-65	+150	°C

[1] Stresses beyond those listed under Limiting values may cause permanent damage to the device. These are stress ratings only, and functional operation of the device at these or any other conditions beyond those indicated under "recommended operating conditions" is not implied. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.

10. Static characteristics

Table 25: DC electrical characteristics

Symbol	Parameter	Conditions		2.5 V			3.3 V and 5 V			Unit
				Min	Nom	Max	Min	Nom	Max	
V _{CC}	supply voltage			V _{CC} – 10%	V _{CC}	V _{CC} + 10%	V _{CC} – 10%	V _{CC}	V _{CC} + 10%	V
VI	input voltage			0	-	V _{CC}	0	-	V _{CC}	V
V _{IH}	HIGH-level input voltage		[1]	1.6	-	V _{CC}	2.0	-	V _{CC}	V
V _{IL}	LOW-level input voltage		[1]	-	-	0.65	-	-	0.8	V
Vo	output voltage		[2]	0	-	V _{CC}	0	-	V _{CC}	V
V _{OH}	HIGH-level output voltage	$I_{OH} = -8 \text{ mA}$	[4]	-	-	-	2.0	-	-	V
		$I_{OH} = -4 \text{ mA}$	[5]	-	-	-	2.0	-	-	V
		$I_{OH} = -800 \ \mu A$	[4]	1.85	-	-	-	-	-	V
		$I_{OH} = -400 \ \mu A$	[5]	1.85	-	-	-	-	-	V
V _{OL}	LOW-level output voltage ^[7]	$I_{OL} = 8 \text{ mA}$	[4]	-	-	-	-	-	0.4	V
		$I_{OL} = 4 \text{ mA}$	[5]	-	-	-	-	-	0.4	V
		$I_{OL} = 2 \text{ mA}$	[4]	-	-	0.4	-	-	-	V
		I _{OL} = 1.6 mA	[5]	-	-	0.4	-	-	-	V
Ci	input capacitance			-	-	18	-	-	18	pF
T _{amb}	operating ambient temperature			-40	25	85	-40	25	85	°C
Tj	junction temperature		[3]	0	25	125	0	25	125	°C
	clock speed		[8]	-	-	50	-	-	80	MHz
	clock duty cycle			-	50	-	-	50	-	%
I _{CC}	supply current	f = 5 MHz	[6]	-	-	3.5	-	-	4.5	mΑ

 $V_{CC} = 2.5 V$, 3.3 V ±10% or 5 V ±10%.

[1] Meets TTL levels, $V_{IO(min)} = 2 V$ and $V_{IH(max)} = 0.8 V$ on non-hysteresis inputs.

[2] Applies for external output buffers.

9397 750 11635

SC16C752

- [3] These junction temperatures reflect simulated conditions. Absolute maximum junction temperature is 150 °C. The customer is responsible for verifying junction temperature.
- [4] These parameters apply for D7-D0.
- [5] These parameters apply for DTRA, DTRB, INIA, INTB, RTSA, RTSB, RXRDYA, RXRDYB, TXRDYA, TXRDYB, TXA, TXB.
- [6] Measurement condition, normal operation other than sleep mode:
 V_{CC} = 3.3 V; T_{amb} = 25 °C. Full duplex serial activity on all two serial (UART) channels at the clock frequency specified in the recommended operating conditions with divisor of 1.
- [7] Except x_2 , $V_{OL} = 1 V$ typical.
- [8] Applies to external clock; crystal oscillator max. 24 MHz.

11. Dynamic characteristics

Table 26: AC electrical characteristics

 T_{amb} = -40 °C to +85 °C; V_{CC} = 2.5 V, 3.3 V ± 10% or 5 V ± 10%, unless specified otherwise.

Symbol	Parameter	Conditions			2.5 V		/ and 5 V	Unit
				Min	Max	Min	Max	
t _{d1}	IOR delay from chip select			10	-	0	-	ns
t _{d2}	read cycle delay	25 pF load		20	-	20	-	ns
t _{d3}	delay from IOR to data	25 pF load		-	77	-	26	ns
t _{d4}	data disable time	25 pF load		-	15	-	15	ns
t _{d5}	IOW delay from chip select			10	-	10	-	ns
t _{d6}	write cycle delay		[1]	25	-	25	-	ns
t _{d7}	delay from IOW to output	25 pF load		-	100	-	33	ns
t _{d8}	delay to set interrupt from modem input	25 pF load		-	100	-	24	ns
t _{d9}	delay to reset interrupt from $\overline{\text{IOR}}$	25 pF load		-	100	-	24	ns
t _{d10}	delay from stop to set interrupt			-	1	-	1	R _{clk} baud rate
t _{d11}	delay from IOR to reset interrupt	25 pF load		-	100	-	29	ns
t _{d12}	delay from start to set interrupt			-	100	-	100	ns
t _{d13}	delay from $\overline{\text{IOW}}$ to transmit start			8	24	8	24	R _{clk} baud rate
t _{d14}	delay from $\overline{\text{IOW}}$ to reset interrupt			-	100	-	70	ns
t _{d15}	delay from stop to set RXRDY			-	1	-	1	R _{clk} baud rate
t _{d16}	delay from IOR to reset RXRDY			-	100	-	75	ns
t _{d17}	delay from IOW to set TXRDY			-	100	-	70	ns
t _{d18}	delay from start to reset TXRDY			-	16	-	16	R _{clk} baud rate
t _{d19}	delay between successive assertion of $\overline{\text{IOW}}$ and $\overline{\text{IOR}}$			-	20	-	20	ns
t _{h1}	chip select hold time from IOR			0	-	0	-	ns
t _{h2}	chip select hold time from IOW			0	-	0	-	ns
t _{h3}	data hold time			15	-	15	-	ns
t _{h4}	address hold time			0	-	0	-	ns
t _{h5}	hold time from XTAL1 clock HIGH-to-LOW transition to IOW or IOR release			20	-	20	-	ns

Table 26: AC electrical characteristics...continued

 T_{amb} = -40 °C to +85 °C; V_{CC} = 2.5 V, 3.3 V ± 10% or 5 V ± 10%, unless specified otherwise.

Symbol	Parameter	Conditions		2.5 V		3.3 V and 5 V		Unit
				Min	Max	Min	Max	
t _{p1} , t _{p2}	clock cycle period			10	-	6	-	ns
t _{p3}	clock speed	[3]	-	48	-	80	MHz
t _(RESET)	RESET pulse width			200	-	200	-	ns
t _{su1}	address set-up time			0	-	0	-	ns
t _{su2}	data set-up time			16	-	16	-	ns
t _{su3}	set-up time from IOW or IOR assertion to XTAL1 clock LOW-to-HIGH transition			20	-	20	-	ns
t _{w1}	IOR strobe width			77	-	30	-	ns
t _{w2}	IOW strobe width	[2	2]	30	-	30	-	ns

[1] When in **both** DMA mode 0 **and** FIFO enable mode, the write cycle delay should be larger than one x₁ clock cycle.

[2]
$$\overline{\text{IOW}} \text{strobe}_{max} = \frac{1}{2(\text{Baudrate}_{max})}$$


= 333 ns (for Baudrate_{max} = 1.5 Mbits/s)

= 1 μ s (for Baudrate_{max} = 460.8 kbits/s)

= 4 μ s (for Baudrate_{max} = 115.2 kbits/s)


[3] Applies to external clock; crystal oscillator max 24 MHz.


11.1 Timing diagrams




SC16C752

Dual UART with 64-byte FIFO






SC16C752





Dual UART with 64-byte FIFO

SC16C752




SC16C752 Dual UART with 64-byte FIFO






Dual UART with 64-byte FIFO


SC16C752





Dual UART with 64-byte FIFO

SC16C752



12. Package outline




Fig 23. LQFP48 package outline (SOT313-2).

13. Soldering

13.1 Introduction to soldering surface mount packages

This text gives a very brief insight to a complex technology. A more in-depth account of soldering ICs can be found in our *Data Handbook IC26; Integrated Circuit Packages* (document order number 9398 652 90011).

There is no soldering method that is ideal for all IC packages. Wave soldering can still be used for certain surface mount ICs, but it is not suitable for fine pitch SMDs. In these situations reflow soldering is recommended. In these situations reflow soldering is recommended.

13.2 Reflow soldering

Reflow soldering requires solder paste (a suspension of fine solder particles, flux and binding agent) to be applied to the printed-circuit board by screen printing, stencilling or pressure-syringe dispensing before package placement. Driven by legislation and environmental forces the worldwide use of lead-free solder pastes is increasing.

Several methods exist for reflowing; for example, convection or convection/infrared heating in a conveyor type oven. Throughput times (preheating, soldering and cooling) vary between 100 and 200 seconds depending on heating method.

Typical reflow peak temperatures range from 215 to 270 °C depending on solder paste material. The top-surface temperature of the packages should preferably be kept:

- below 220 °C (SnPb process) or below 245 °C (Pb-free process)
 - for all BGA and SSOP-T packages
 - for packages with a thickness \geq 2.5 mm
 - for packages with a thickness < 2.5 mm and a volume ≥ 350 mm³ so called thick/large packages.
- below 235 °C (SnPb process) or below 260 °C (Pb-free process) for packages with a thickness < 2.5 mm and a volume < 350 mm³ so called small/thin packages.

Moisture sensitivity precautions, as indicated on packing, must be respected at all times.

13.3 Wave soldering

Conventional single wave soldering is not recommended for surface mount devices (SMDs) or printed-circuit boards with a high component density, as solder bridging and non-wetting can present major problems.

To overcome these problems the double-wave soldering method was specifically developed.

If wave soldering is used the following conditions must be observed for optimal results:

• Use a double-wave soldering method comprising a turbulent wave with high upward pressure followed by a smooth laminar wave.

© Koninklijke Philips Electronics N.V. 2003. All rights reserved.

9397 750 11635

- For packages with leads on two sides and a pitch (e):
 - larger than or equal to 1.27 mm, the footprint longitudinal axis is preferred to be parallel to the transport direction of the printed-circuit board;
 - smaller than 1.27 mm, the footprint longitudinal axis must be parallel to the transport direction of the printed-circuit board.

The footprint must incorporate solder thieves at the downstream end.

• For packages with leads on four sides, the footprint must be placed at a 45° angle to the transport direction of the printed-circuit board. The footprint must incorporate solder thieves downstream and at the side corners.

During placement and before soldering, the package must be fixed with a droplet of adhesive. The adhesive can be applied by screen printing, pin transfer or syringe dispensing. The package can be soldered after the adhesive is cured.

Typical dwell time of the leads in the wave ranges from 3 to 4 seconds at 250 °C or 265 °C, depending on solder material applied, SnPb or Pb-free respectively.

A mildly-activated flux will eliminate the need for removal of corrosive residues in most applications.

13.4 Manual soldering

Fix the component by first soldering two diagonally-opposite end leads. Use a low voltage (24 V or less) soldering iron applied to the flat part of the lead. Contact time must be limited to 10 seconds at up to $300 \,^{\circ}$ C.

When using a dedicated tool, all other leads can be soldered in one operation within 2 to 5 seconds between 270 and 320 $^\circ$ C.

13.5 Package related soldering information

Table 27:	Suitability of surface mount IC packages for wave and reflow soldering
	methods

Package ^[1]	Soldering method				
	Wave	Reflow ^[2]			
BGA, LBGA, LFBGA, SQFP, SSOP-T ^[3] , TFBGA, VFBGA	not suitable	suitable			
DHVQFN, HBCC, HBGA, HLQFP, HSQFP, HSOP, HTQFP, HTSSOP, HVQFN, HVSON, SMS	not suitable ^[4]	suitable			
PLCC ^[5] , SO, SOJ	suitable	suitable			
LQFP, QFP, TQFP	not recommended ^{[5][6]}	suitable			
SSOP, TSSOP, VSO, VSSOP	not recommended ^[7]	suitable			

[1] For more detailed information on the BGA packages refer to the *(LF)BGA Application Note* (AN01026); order a copy from your Philips Semiconductors sales office.

[2] All surface mount (SMD) packages are moisture sensitive. Depending upon the moisture content, the maximum temperature (with respect to time) and body size of the package, there is a risk that internal or external package cracks may occur due to vaporization of the moisture in them (the so called popcorn effect). For details, refer to the Drypack information in the *Data Handbook IC26; Integrated Circuit Packages; Section: Packing Methods.*

SC16C752

- [3] These transparent plastic packages are extremely sensitive to reflow soldering conditions and must on no account be processed through more than one soldering cycle or subjected to infrared reflow soldering with peak temperature exceeding 217 °C ± 10 °C measured in the atmosphere of the reflow oven. The package body peak temperature must be kept as low as possible.
- [4] These packages are not suitable for wave soldering. On versions with the heatsink on the bottom side, the solder cannot penetrate between the printed-circuit board and the heatsink. On versions with the heatsink on the top side, the solder might be deposited on the heatsink surface.
- [5] If wave soldering is considered, then the package must be placed at a 45° angle to the solder wave direction. The package footprint must incorporate solder thieves downstream and at the side corners.
- [6] Wave soldering is suitable for LQFP, QFP and TQFP packages with a pitch (e) larger than 0.8 mm; it is definitely not suitable for packages with a pitch (e) equal to or smaller than 0.65 mm.
- [7] Wave soldering is suitable for SSOP and TSSOP packages with a pitch (e) equal to or larger than 0.65 mm; it is definitely not suitable for packages with a pitch (e) equal to or smaller than 0.5 mm.

14. Revision history

Table 28:Revision history

Rev	Date	CPCN	Description	
04	20030620	-	Product data (9397 750 11635); ECN 853-2379 30031 of 16 June 2003.	
			Modifications:	
			 Figure 12 "Crystal oscillator connections." on page 18: capacitors' values changed and added connection with resistor. 	
03	20030313	-	Product data (9397 750 11196); ECN 853-2379 29623 of 10 March 2003.	
02	20021216	-	Product data (9397 750 10811); ECN 853-2379 29261 of 06 December 2002.	
01	20020910	-	Product data (9397 750 09575); ECN 853-2379 28891 of 10 September 2002.	

15. Data sheet status

Level	Data sheet status ^[1]	Product status ^{[2][3]}	Definition
I	Objective data	Development	This data sheet contains data from the objective specification for product development. Philips Semiconductors reserves the right to change the specification in any manner without notice.
II	Preliminary data	Qualification	This data sheet contains data from the preliminary specification. Supplementary data will be published at a later date. Philips Semiconductors reserves the right to change the specification without notice, in order to improve the design and supply the best possible product.
III	Product data	Production	This data sheet contains data from the product specification. Philips Semiconductors reserves the right to make changes at any time in order to improve the design, manufacturing and supply. Relevant changes will be communicated via a Customer Product/Process Change Notification (CPCN).

[1] Please consult the most recently issued data sheet before initiating or completing a design.

[2] The product status of the device(s) described in this data sheet may have changed since this data sheet was published. The latest information is available on the Internet at URL http://www.semiconductors.philips.com.

[3] For data sheets describing multiple type numbers, the highest-level product status determines the data sheet status.

16. Definitions

Short-form specification — The data in a short-form specification is extracted from a full data sheet with the same type number and title. For detailed information see the relevant data sheet or data handbook.

Limiting values definition — Limiting values given are in accordance with the Absolute Maximum Rating System (IEC 60134). Stress above one or more of the limiting values may cause permanent damage to the device. These are stress ratings only and operation of the device at these or at any other conditions above those given in the Characteristics sections of the specification is not implied. Exposure to limiting values for extended periods may affect device reliability.

Application information — Applications that are described herein for any of these products are for illustrative purposes only. Philips Semiconductors make no representation or warranty that such applications will be suitable for the specified use without further testing or modification.

17. Disclaimers

Life support — These products are not designed for use in life support appliances, devices, or systems where malfunction of these products can reasonably be expected to result in personal injury. Philips Semiconductors customers using or selling these products for use in such applications do so at their own risk and agree to fully indemnify Philips Semiconductors for any damages resulting from such application.

Right to make changes — Philips Semiconductors reserves the right to make changes in the products - including circuits, standard cells, and/or software - described or contained herein in order to improve design and/or performance. When the product is in full production (status 'Production'), relevant changes will be communicated via a Customer Product/Process Change Notification (CPCN). Philips Semiconductors assumes no responsibility or liability for the use of any of these products, conveys no licence or title under any patent, copyright, or mask work right to these products are free from patent, copyright, or mask work right infringement, unless otherwise specified.

Contact information

For additional information, please visit http://www.semiconductors.philips.com. For sales office addresses, send e-mail to: sales.addresses@www.semiconductors.philips.com.

Fax: +31 40 27 24825

© Koninklijke Philips Electronics N.V. 2003. All rights reserved

9397 750 11635

Dual UART with 64-byte FIFO

Contents

1	Description 1
2	Features 1
3	Ordering information 2
4	Block diagram 3
5	Pinning information 4
5.1	Pinning
5.2	Pin description 4
6	Functional description6
6.1	Trigger levels
6.2	Hardware flow control
6.2.1	Auto-RTS 8
6.2.2	Auto-CTS 8
6.3	Software flow control 9
6.3.1	RX
6.3.2	TX 10
6.3.3	Software flow control example
6.4	Reset 11
6.5	Interrupts 12
6.5.1	Interrupt mode operation
6.5.2	Polled mode operation 13
6.6	DMA operation 14
6.6.1	Single DMA transfers (DMA mode 0/FIFO
	disable)
6.6.2	Block DMA transfers (DMA mode 1) 15
6.7	Sleep mode
6.8	Break and time-out conditions
6.9	Programmable baud rate generator 16
7	Register descriptions 18
7.1	Receiver holding register (RHR)
7.2	Transmit holding register (THR)
7.3	FIFO control register (FCR) 21
7.4	Line control register (LCR) 22
7.5	Line status register (LSR)
7.6	Modem control register (MCR) 24
7.7	Modem status register (MSR)
7.8	Interrupt enable register (IER)
7.9	Interrupt identification register (IIR)
7.10	Enhanced feature register (EFR)
7.11	Divisor latches (DLL, DLH)
7.12	Transmission control register (TCR) 28
7.13	Trigger level register (TLR)
7.14	FIFO ready register
8	Programmer's guide 30

9	Limiting values	32
10	Static characteristics	32
11	Dynamic characteristics	33
11.1	Timing diagrams	34
12	Package outline	42
13	Soldering	43
13.1	Introduction to soldering surface mount	
	packages	43
13.2	Reflow soldering	43
13.3	Wave soldering.	43
13.4	Manual soldering	44
13.5	Package related soldering information	44
14	Revision history	45
15	Data sheet status	46
16	Definitions	46
17	Disclaimers	46

© Koninklijke Philips Electronics N.V. 2003. Printed in the U.S.A

All rights are reserved. Reproduction in whole or in part is prohibited without the prior written consent of the copyright owner.

The information presented in this document does not form part of any quotation or contract, is believed to be accurate and reliable and may be changed without notice. No liability will be accepted by the publisher for any consequence of its use. Publication thereof does not convey nor imply any license under patent- or other industrial or intellectual property rights.



Let's make things better.