# SC16C850V

1.8 V single UART, 5 Mbit/s (max.) with 128-byte FIFOs, infrared (IrDA), and XScale VLIO bus interface

Rev. 5 — 19 January 2011

**Product data sheet** 

## 1. General description

The SC16C850V is a 1.8 V, low power single channel Universal Asynchronous Receiver and Transmitter (UART) used for serial data communications. Its principal function is to convert parallel data into serial data and vice versa. The UART can handle serial data rates up to 5 Mbit/s. SC16C850V can be programmed to operate in extended mode where additional advanced UART features are available (see Section 6.2). The SC16C850V family UART provides enhanced UART functions with 128-byte FIFOs, modem control interface and IrDA encoder/decoder. On-board status registers provide the user with error indications and operational status. System interrupts and modem control features may be tailored by software to meet specific user requirements. An internal loopback capability allows on-board diagnostics. Independent programmable baud rate generators are provided to select transmit and receive baud rates.

The SC16C850V with Intel XScale processor VLIO interface operates at 1.8 V and is available in the HVQFN32 package.

#### 2. Features and benefits

- Single channel high performance UART
- 1.8 V operation
- Advanced package: HVQFN32
- Up to 5 Mbit/s data rate at 1.8 V
- 128-byte transmit FIFO to reduce the bandwidth requirement of the external CPU
- 128-byte receive FIFO with error flags to reduce the bandwidth requirement of the external CPU
- 128 programmable Receive and Transmit FIFO interrupt trigger levels
- 128 Receive and Transmit FIFO reporting levels (level counters)
- Automatic software (Xon/Xoff) and hardware (RTS/CTS or DTR/DSR) flow control
- Programmable Xon/Xoff characters
- 128 programmable hardware and software trigger levels
- Automatic 9-bit mode (RS-485) address detection
- Automatic RS-485 driver turn-around with programmable delay
- UART software reset
- High resolution clock prescaler, from 0 to 15 with granularity of <sup>1</sup>/<sub>16</sub> to allow non-standard UART clock to be used
- Industrial temperature range (–40 °C to +85 °C)
- Software compatible with industry standard SC16C650B
- Software selectable baud rate generator



## Single UART with 128-byte FIFOs, IrDA, and XScale VLIO bus interface

- Supports IrDA version 1.0 (up to 115.2 kbit/s)
- Standard modem interface or infrared IrDA encoder/decoder interface
- Enhanced Sleep mode and low power feature
- Modem control functions (CTS, RTS, DSR, DTR, RI, CD)
- Independent transmitter and receiver enable/disable
- Pb-free, RoHS compliant package offered


## 3. Ordering information

Table 1. Ordering information

Type number	Package	Package						
	Name	Description	Version					
SC16C850VIBS	HVQFN32	plastic thermal enhanced very thin quad flat package; no leads; 32 terminals; body $5\times5\times0.85$ mm	SOT617-1					

## Single UART with 128-byte FIFOs, IrDA, and XScale VLIO bus interface


## 4. Block diagram



## Single UART with 128-byte FIFOs, IrDA, and XScale VLIO bus interface

# 5. Pinning information

#### 5.1 Pinning



## 5.2 Pin description

Table 2. Pin description

Symbol	Pin	Туре	Description							
AD0	29	I/O	Address and Data bus (bidirectional). These pins are the 8-bit multiplexed data bus and							
AD1	30		address bus for transferring information to or from the controlling CPU. AD0 is the least significant bit and is address A0 during the address cycle, and AD7 is the most significant bit and is address A7 during the address cycle.							
AD2	31									
AD3	32									
AD4	1									
AD5	3									
AD6	4									
AD7	5									
CD	26	I	<b>Carrier Detect (active LOW).</b> A logic 0 on this pin indicates that a carrier has been detected by the modem for that channel. Status can be tested by reading MSR[7].							
CS	8	I	<b>Chip Select (active LOW).</b> This pin enables the data transfers between the host and the SC16C850V.							
CTS	24	I	Clear to Send (active LOW). A logic 0 on the CTS pin indicates the modem or data set is ready to accept transmit data from the SC16C850V. Status can be tested by reading MSR[4].							
DSR	25	I	<b>Data Set Ready (active LOW).</b> A logic 0 on this pin indicates the modem or data set is powered-on and is ready for data exchange with the UART. Status can be tested by reading MSR[5].							
DTR	22	0	<b>Data Terminal Ready (active LOW).</b> A logic 0 on this pin indicates that the SC16C850V is powered-on and ready. This pin can be controlled via the Modem Control Register. Writing a logic 1 to MCR[0] will set the DTR output to logic 0, enabling the modem. This pin will be a logic 1 after writing a logic 0 to MCR[0], or after a reset.							

#### Single UART with 128-byte FIFOs, IrDA, and XScale VLIO bus interface

Table 2. Pin description ...continued

Table 2.	Pin descriptioncontinued					
Symbol	Pin	Type	Description			
INT	20	0	<b>Interrupt output.</b> The output state is defined by the user through the software setting of MCR[5]. INT is set to the active mode when MCR[5] is set to a logic 0. INT is set to the open-source mode when MCR[3] is set to a logic 1. See <u>Table 19</u> .			
ĪOR	14	I	<b>Read strobe (active LOW).</b> A HIGH to LOW transition on this signal starts the read cycle. The SC16C850V reads a byte from the internal register and puts the byte on the data bus for the host to retrieve.			
ĪOW	12	1	<b>Write strobe (active LOW).</b> A HIGH to LOW transition on this signal starts the write cycle, and a LOW to HIGH transition transfers the data on the data bus to the internal register.			
LLA	19	I	<b>Latch Lower Address (active LOW).</b> A logic LOW on this pin puts the VLIO interface in the address phase of the transaction, where the lower 8 bits of the VLIO (specifying the UART register and the channel address) are loaded into the address latch of the device through the AD7 to AD0 bus. A logic HIGH puts the VLIO interface in the data phase where data can are transferred between the host and the UART.			
LOWPWR	9	l	<b>Low Power.</b> When asserted (active HIGH), the device immediately goes into low-power mode. The oscillator is shut-off and some host interface pins are isolated from the host's bus to reduce power consumption. The device only returns to normal mode when the LOWPWR pin is de-asserted. On the negative edge of a de-asserting LOWPWR signal, the device is automatically reset and all registers return to their default reset states. This pin has an internal pull-down resistor, therefore, it can be left unconnected.			
n.c.	2, 15, 16, 17, 18	-	not connected			
RESET	23	I	Master reset (active LOW). A reset pulse will reset the internal registers and all the outputs. The SC16C850V transmitter outputs and receiver inputs will be disabled during reset time. (See Section 7.23 "SC16C850V external reset condition and software reset" for initialization details.)			
RI	27	I	<b>Ring Indicator (active LOW).</b> A logic 0 on this pin indicates the modem has received a ringing signal from the telephone line. A logic 1 transition on this input pin will generate an interrupt is modem status interrupt is enabled. Status can be tested by reading MCR[6].			
RTS	21	0	<b>Request to Send (active LOW).</b> A logic 0 on the $\overline{RTS}$ pin indicates the transmitter has data ready and waiting to send. Writing a logic 1 in the modem control register MCR[1] will set this pin to a logic 0, indicating data is available. After a reset this pin will be set to a logic 1.			
RX	6	I	<b>UART receive data.</b> The RX signal will be a logic 1 during reset, idle (no data), or when not receiving data. During the local Loopback mode, the RX input pin is disabled and TX data is connected to the UART RX input internally.			
TX	7	0	<b>UART transmit data.</b> The TX signal will be a logic 1 during reset, idle (no data), or when the transmitter is disabled. During the local Loopback mode, the TX output pin is disabled and TX data is internally connected to the UART RX input.			
$V_{DD}$	28	I	Power supply input.			
V <sub>SS</sub>	13 <mark>[1]</mark>	I	Signal and power ground.			
XTAL1	10	I	<b>Crystal or external clock input.</b> Functions as a crystal input or as an external clock input. A crystal can be connected between this pin and XTAL2 to form an internal oscillator circuit. Alternatively, an external clock can be connected to this pin to provide custom data rates (see Section 6.9 "Programmable baud rate generator"). See Figure 4.			
XTAL2	11	0	Output of the crystal oscillator or buffered clock. Crystal oscillator output or buffered clock output. Should be left open if an external clock is connected to XTAL1.			

<sup>[1]</sup> HVQFN32 package die supply ground is connected to both V<sub>SS</sub> pin and exposed center pad. V<sub>SS</sub> pin must be connected to supply ground for proper device operation. For enhanced thermal, electrical, and board level performance, the exposed pad needs to be soldered to the board using a corresponding thermal pad on the board and for proper heat conduction through the board, thermal vias need to be incorporated in the printed-circuit board in the thermal pad region.

#### Single UART with 128-byte FIFOs, IrDA, and XScale VLIO bus interface

## 6. Functional description

The SC16C850V provides serial asynchronous receive data synchronization, parallel-to-serial and serial-to-parallel data conversions for both the transmitter and receiver sections. These functions are necessary for converting the serial data stream into parallel data that is required with digital data systems. Synchronization for the serial data stream is accomplished by adding start and stop bits to the transmit data to form a data character (character orientated protocol). Data integrity is ensured by attaching a parity bit to the data character. The parity bit is checked by the receiver for any transmission bit errors. The electronic circuitry to provide all these functions is fairly complex, especially when manufactured on a single integrated silicon chip. The SC16C850V represents such an integration with greatly enhanced features. The SC16C850V is fabricated with an advanced CMOS process.

The SC16C850V is an upward solution to the SC16C650B with a VLIO interface that provides a single UART capability with 128 bytes of transmit and receive FIFO memory, instead of 32 bytes for the SC16C650B. The SC16C850V is designed to work with high speed modems and shared network environments that require fast data processing time. Increased performance is realized in the SC16C850V by the transmit and receive FIFOs. This allows the external processor to handle more networking tasks within a given time. In addition, the four selectable receive and transmit FIFO trigger interrupt levels are provided in normal mode, or 128 programmable levels are provided in extended mode for maximum data throughput performance especially when operating in a multi-channel environment (see <a href="Section 6.2" Extended mode (128-byte FIFO)">Section 6.2 "Extended mode (128-byte FIFO)"</a>). The FIFO memory greatly reduces the bandwidth requirement of the external controlling CPU, and increases performance.

A low power pin (LOWPWR) is provided to further reduce power consumption by isolating the host interface bus.

The SC16C850V is capable of operation up to 5 Mbit/s with an external 80 MHz clock. With a crystal is capable of operation up to 1.5 Mbit/s.

The rich feature set of the SC16C850V is available through internal registers. These features are: selectable and programmable receive and transmit FIFO trigger levels, selectable TX and RX baud rates, and modem interface controls (all standard features). Following a power-on reset an external reset or a software reset, the SC16C850V is software compatible with the previous generation SC16C650B.

#### 6.1 UART selection

The UART provides the user with the capability to bidirectionally transfer information between a CPU and an external serial device. The  $\overline{\text{CS}}$  pin together with addresses A6 and A7 determine if the UART is being accessed; see Table 3.

**Table 3. Serial port selection** H = HIGH; L = LOW; X = Don't care.

Chip Select	Function
$\overline{CS} = H, A7 = X, A6 = X$	device not selected
<del>CS</del> = L, A7 = L, A6 = L	UART selected
<del>CS</del> = L, A7 = L, A6 = H	device not selected
CS = L, A7 = H, A6 = X	device not selected

SC16C850V

All information provided in this document is subject to legal disclaimers.

© NXP B.V. 2011. All rights reserved.

#### Single UART with 128-byte FIFOs, IrDA, and XScale VLIO bus interface

## 6.2 Extended mode (128-byte FIFO)

The device is in the extended mode when any of these four registers contains any value other than 0: FLWCNTH, FLWCNTL, TXINTLVL, RXINTLVL.

## 6.3 Internal registers

The SC16C850V provides a set of 25 internal registers for monitoring and controlling the functions of the UART. These registers are shown in Table 4.

Table 4. Internal registers decoding

Iabi	<b>-</b>	IIIICI	nai registers decoding							
А3	<b>A2</b>	<b>A</b> 1	Read mode	Write mode						
Gen	General register set (THR/RHR, IER/ISR, MCR/MSR, FCR, LSR, SPR)[1]									
0	0	0	Receive Holding Register	Transmit Holding Register						
0	0	1	Interrupt Enable Register	Interrupt Enable Register						
0	1	0	Interrupt Status Register	FIFO Control Register						
0	1	1	Line Control Register	Line Control Register						
1	0	0	Modem Control Register	Modem Control Register						
1	0	1	Line Status Register	Extra Feature Control Register (EFCR)						
1	1	0	Modem Status Register	n/a						
1	1	1	Scratchpad Register	Scratchpad Register						
Bau	d rate	regis	ster set (DLL/DLM)[2]							
0	0	0	LSB of Divisor Latch	LSB of Divisor Latch						
0	0	1	MSB of Divisor Latch	MSB of Divisor Latch						
Sec	ond s	pecia	register set (TXLVLCNT/RXLVLCNT)[3	<u> </u>						
0	1	1	Transmit FIFO Level Count	n/a						
1	0	0	Receive FIFO Level Count	n/a						
Enh	anced	d regis	ster set (EFR, Xon1/Xon2, Xoff1/Xoff2)	<u>[4]</u>						
0	1	0	Enhanced Feature Register	Enhanced Feature Register						
1	0	0	Xon1 word	Xon1 word						
1	0	1	Xon2 word	Xon2 word						
1	1	0	Xoff1 word	Xoff1 word						
1	1	1	Xoff2 word	Xoff2 word						
Firs	t extra	a feati	ure register set (TXINTLVL/RXINTLVL,	FLWCNTH/FLWCNTL) <u></u> 티						
0	1	0	Transmit FIFO Interrupt Level	Transmit FIFO Interrupt Level						
1	0	0	Receive FIFO Interrupt Level	Receive FIFO Interrupt Level						
1	1	0	Flow Control Count High	Flow Control Count High						
1	1	1	Flow Control Count Low	Flow Control Count Low						
Sec	ond e	xtra f	eature register set (CLKPRES, RS485T	IME, AFCR2, AFCR1)[6]						
0	1	0	Clock Prescaler	Clock Prescaler						
1	0	0	RS-485 turn-around Timer	RS-485 turn-around Timer						
1	1	0	Additional Feature Control Register 2	Additional Feature Control Register 2						
1	1	1	Additional Feature Control Register 1	Additional Feature Control Register 1						

<sup>[1]</sup> These registers are accessible only when LCR[7] is a logic 0.

<sup>[2]</sup> These registers are accessible only when LCR[7] is a logic 1.

#### Single UART with 128-byte FIFOs, IrDA, and XScale VLIO bus interface

- [3] Second special registers are accessible only when EFCR[0] = 1.
- [4] Enhanced Feature Registers are only accessible when LCR = 0xBF.
- [5] First extra feature registers are only accessible when EFCR[2:1] = 01b.
- [6] Second extra feature registers are only accessible when EFCR[2:1] = 10b.

#### 6.4 FIFO operation

#### 6.4.1 32-byte FIFO mode

When all four of these registers (TXINTLVL, RXINTLVL, FLWCNTH, FLWCNTL) in the First Extra Register Set are empty (0x00) the transmit and receive trigger levels are set by FCR[7:4]. In this mode the transmit and receive trigger levels are backward compatible to the SC16C650B (see <u>Table 5</u>), and the FIFO sizes are 32 entries. The transmit and receive data FIFOs are enabled by the FIFO Control Register bit 0 (FCR[0]). It should be noted that the user can set the transmit trigger levels by writing to the FCR, but activation will not take place until EFR[4] is set to a logic 1. The receiver FIFO section includes a time-out function to ensure data is delivered to the external CPU (see <u>Section 6.8</u>). Please refer to <u>Table 10</u> and <u>Table 11</u> for the setting of FCR[7:4].

Table 5. Interrupt trigger level and Flow control mechanism

FCR[7:6]	FCR[5:4]	INT pin activ	ation	Negate RTS or	Assert RTS or send Xon	
		RX	TX	send Xoff		
00	00	8	16	8	0	
01	01	16	8	16	7	
10	10	24	24	24	15	
11	11	28	30	28	23	

#### 6.4.2 128-byte FIFO mode

When either TXINTLVL, RXINTLVL, FLWCNTH or FLWCNTL in the First Extra Register Set contains any value other than 0x00, the transmit and receive trigger levels are set by TXINTLVL and RXINTLVL registers. TXINTLVL sets the trigger levels for the transmit FIFO, and the transmit trigger levels can be set to any value between 1 and 128 with granularity of 1. RXINTLVL sets the trigger levels for the receive FIFO, the receive trigger levels can be set to any value between 1 and 128 with granularity of 1.

When the effective FIFO size changes (that is, when FCR[0] toggles or when the combined content of TXINTLVL, RXINTLVL, FLWCNTH and FLWCNTL changes between equal and unequal to 0x00), both RX FIFO and TX FIFO will be reset (data in the FIFO will be lost).

#### 6.5 Hardware flow control

When automatic hardware flow control is enabled, the  $\overline{\text{RTS}}$  pin for local buffer overflows. Automatic hardware flow control is selected by setting EFR[6] (RTS) and EFR[7] (CTS) to a logic 1. If  $\overline{\text{CTS}}$  transitions from a logic 0 to a logic 1 indicating a flow control request, ISR[5] will be set to a logic 1 (if enabled via IER[7:6]), and the SC16C850V will suspend TX transmissions as soon as the stop bit of the character in process is shifted out. Transmission is resumed after the  $\overline{\text{CTS}}$  input returns to a logic 0, indicating more data may be sent.

#### Single UART with 128-byte FIFOs, IrDA, and XScale VLIO bus interface

When AFCR1[2] is set to 1, then the function of  $\overline{CTS}$  pin is mapped to the  $\overline{DSR}$  pin, and the function of  $\overline{RTS}$  is mapped to  $\overline{DTR}$  pin.  $\overline{DSR}$  and  $\overline{DTR}$  pins will behave as described above for  $\overline{CTS}$  and  $\overline{RTS}$ .

With the automatic hardware flow control function enabled, an interrupt is generated when the receive FIFO reaches the programmed trigger level. The  $\overline{\text{RTS}}$  (or  $\overline{\text{DTR}}$ ) pin will not be forced to a logic 1 (RTS off) until the receive FIFO reaches the next trigger level. However, the  $\overline{\text{RTS}}$  (or  $\overline{\text{DTR}}$ ) pin will return to a logic 0 after the receive buffer (FIFO) is unloaded to the next trigger level below the programmed trigger level. Under the above described conditions, the SC16C850V will continue to accept data until the receive FIFO is full.

When TXINTLVL, RXINTLVL, FLWCNTH and FLWCNTL in the First Extra Register Set are all zeroes, the hardware and software flow control trigger levels are set by FCR[7:4]; see Table 5.

When either TXINTLVL, RXINTLVL, FLWCNTH or FLWCNTL in the First Extra Register Set contains any value other than 0x00, the hardware and software flow control trigger levels are set by FLWCNTH and FLWCNTL. The content in FLWCNTH determines how many bytes are in the receive FIFO before RTS (or DTR) is de-asserted or Xoff is sent. The content of FLWCNTL determines how many bytes are in the receive FIFO before RTS (or DTR) is asserted, or Xon is sent.

In 128-byte FIFO mode, hardware and software flow control trigger levels can be set to any value between 1 and 128 in granularity of 1. The value of FLWCNTH should always be greater than FLWCNTL. The UART does not check for this condition automatically, and if this condition is not met spurious operation of the device might occur. When using FLWCNTH and FWLCNTL, these registers must be initialized to the proper values before hardware or software flow control is enabled via the EFR register.

#### 6.6 Software flow control

When software flow control is enabled, the SC16C850V compares one or two sequentially received data characters with the programmed Xon or Xoff character value(s). If the received character(s) match the programmed Xoff values, the SC16C850V will halt transmission (TX) as soon as the current character(s) has completed transmission. When a match occurs, ISR bit 4 will be set (if enabled via IER[5]) and the interrupt output pin (if receive interrupt is enabled) will be activated. Following a suspension due to a match of the Xoff characters' values, the SC16C850V will monitor the receive data stream for a match to the Xon1/Xon2 character value(s). If a match is found, the SC16C850V will resume operation and clear the flags (ISR[4]).

Reset initially sets the contents of the Xon/Xoff 8-bit flow control registers to a logic 0. Following reset, the user can write any Xon/Xoff value desired for software flow control. Different conditions can be set to detect Xon/Xoff characters and suspend/resume transmissions (see <a href="Table 24">Table 24</a>). When double 8-bit Xon/Xoff characters are selected, the SC16C850V compares two consecutive receive characters with two software flow control 8-bit values (Xon1, Xon2, Xoff1, Xoff2) and controls TX transmissions accordingly. Under the above described flow control mechanisms, flow control characters are not placed (stacked) in the receive FIFO. When using software flow control, the Xon/Xoff characters cannot be used for data transfer.

#### Single UART with 128-byte FIFOs, IrDA, and XScale VLIO bus interface

In the event that the receive buffer is overfilling, the SC16C850V automatically sends an Xoff character (when enabled) via the serial TX output to the remote UART. The SC16C850V sends the Xoff1/Xoff2 characters as soon as the number of received data in the receive FIFO passes the programmed trigger level. To clear this condition, the SC16C850V will transmit the programmed Xon1/Xon2 characters as soon as the number of characters in the receive FIFO drops below the programmed trigger level.

## 6.7 Special character detect

A special character detect feature is provided to detect an 8-bit character when EFR[5] is set. When an 8-bit character is detected, it will be placed on the user-accessible data stack along with normal incoming RX data. This condition is selected in conjunction with EFR[3:0] (see <u>Table 24</u>). Note that software flow control should be turned off when using this special mode by setting EFR[3:0] to all zeroes.

The SC16C850V compares each incoming receive character with Xoff2 data. If a match occurs, the received data will be transferred to the FIFO, and ISR[4] will be set to indicate detection of a special character. Although <u>Table 7 "SC16C850V internal registers"</u> shows Xon1, Xon2, Xoff1, Xoff2 with eight bits of character information, the actual number of bits is dependent on the programmed word length. Line Control Register bits LCR[1:0] define the number of character bits, that is, either 5 bits, 6 bits, 7 bits or 8 bits. The word length selected by LCR[1:0] also determine the number of bits that will be used for the special character comparison. Bit 0 in the Xon1, Xon2, Xoff1, Xoff2 registers corresponds with the LSB bit for the received character.

#### 6.8 Interrupt priority and time-out interrupts

The interrupts are enabled by IER[7:0]. Care must be taken when handling these interrupts. Following a reset, if Interrupt Enable Register (IER) bit 1 = 1, the SC16C850V will issue a Transmit Holding Register interrupt. This interrupt must be serviced prior to continuing operations. The ISR indicates the current singular highest priority interrupt only. A condition can exist where a higher priority interrupt masks the lower priority interrupt(s) (see <u>Table 12</u>). Only after servicing the higher pending interrupt will the lower priority interrupt(s) be reflected in the status register. Servicing the interrupt without investigating further interrupt conditions can result in data errors.

Receive Data Ready and Receive Time Out have the same interrupt priority (when enabled by IER[0]), and it is important to serve these interrupts correctly. The receiver issues an interrupt after the number of characters have reached the programmed trigger level. In this case, the SC16C850V FIFO may hold more characters than the programmed trigger level. Following the removal of a data byte, the user should re-check LSR[0] to see if there are any additional characters. A Receive Time Out will not occur if the receive FIFO is empty. The time-out counter is reset at the center of each stop bit received or each time the Receive Holding Register (RHR) is read. The actual time-out value is 4 character time, including data information length, start bit, parity bit, and the size of stop bit, that is,  $1 \times 1.5 \times$ 

#### Single UART with 128-byte FIFOs, IrDA, and XScale VLIO bus interface

## 6.9 Programmable baud rate generator

The SC16C850V UART contains a programmable rational baud rate generator that takes any clock input and divides it by a divisor in the range between 1 and  $(2^{16} - 1)$ . The SC16C850V offers the capability of dividing the input frequency by rational divisor. The fractional part of the divisor is controlled by the CLKPRES register in the First Extra Register Set.

band rate = 
$$\frac{f_{XTAL1}}{MCR[7] \times \left[16 \times \left(N + \frac{M}{16}\right)\right]}$$
 (1)

where:


N is the integer part of the divisor in DLL and DLM registers;

M is the fractional part of the divisor in CLKPRES register;

f<sub>XTAL1</sub> is the clock frequency at XTAL1 pin.

Prescaler = 1 when MCR[7] is set to 0.

Prescaler = 4 when MCR[7] is set to 1.




A single baud rate generator is provided for the transmitter and receiver. The programmable Baud Rate Generator is capable of operating with a frequency of up to 80 MHz. To obtain maximum data rate, it is necessary to use full rail swing on the clock input. The SC16C850V can be configured for internal or external clock operation. For internal clock operation, an industry standard crystal is connected externally between the XTAL1 and XTAL2 pins (see Figure 4). Alternatively, an external clock can be connected to the XTAL1 pin (see Figure 5) to clock the internal baud rate generator for standard or custom rates (see Table 6).

The generator divides the input  $16 \times$  clock by any divisor from 1 to  $(2^{16} - 1)$ . The SC16C850V divides the basic external clock by 16. The baud rate is configured via the CLKPRES, DLL and DLM internal register functions. Customized baud rates can be achieved by selecting the proper divisor values for the MSB and LSB sections of baud rate generator.

Programming the baud rate generator registers CLKPRES, DLM (MSB) and DLL (LSB) provides a user capability for selecting the desired final baud rate. The example in <u>Table 6</u> shows the selectable baud rate table available when using a 1.8432 MHz external clock input with MCR[7] is 0, and CLKPRES = 0x00.

## Single UART with 128-byte FIFOs, IrDA, and XScale VLIO bus interface






Table 6. Baud rate generator programming table using a 1.8432 MHz clock with MCR[7] = 0 and CLKPRE[3:0] = 0

Output baud rate (bit/s)	Output 16× clock divisor (decimal)	Output 16× clock divisor (hexadecimal)	DLM program value (hexadecimal)	DLL program value (hexadecimal)
50	2304	900	09	00
75	1536	600	06	00
110	1047	417	04	17
150	768	300	03	00
300	384	180	01	80
600	192	C0	00	C0
1.2 k	96	60	00	60
2.4 k	48	30	00	30
3.6 k	32	20	00	20
4.8 k	24	18	00	18
7.2 k	16	10	00	10
9.6 k	12	0C	00	0C
19.2 k	6	06	00	06
38.4 k	3	03	00	03
57.6 k	2	02	00	02
115.2 k	1	01	00	01


#### Single UART with 128-byte FIFOs, IrDA, and XScale VLIO bus interface

#### 6.10 Loopback mode

The internal loopback capability allows on-board diagnostics. In the Loopback mode, the normal modem interface pins are disconnected and reconfigured for loopback internally (see Figure 6). MCR[3:0] register bits are used for controlling loopback diagnostic testing. In the Loopback mode, the transmitter output (TX) and the receiver input (RX) are disconnected from their associated interface pins, and instead are connected together internally. The CTS, DSR, CD, and RI are disconnected from their normal modem control inputs pins, and instead are connected internally to RTS, DTR, MCR[3] (OP2) and MCR[2] (OP1). Loopback test data is entered into the transmit holding register via the user data bus interface, AD[7:0]. The transmit UART serializes the data and passes the serial data to the receive UART via the internal loopback connection. The receive UART converts the serial data back into parallel data that is then made available at the user data interface AD[7:0]. The user optionally compares the received data to the initial transmitted data for verifying error-free operation of the UART TX/RX circuits.

In this mode, the receiver and transmitter interrupts are fully operational. The modem control interrupts are also operational.

#### Single UART with 128-byte FIFOs, IrDA, and XScale VLIO bus interface



#### Single UART with 128-byte FIFOs, IrDA, and XScale VLIO bus interface

## 6.11 Sleep mode

Sleep mode is an enhanced feature of the SC16C850V UART. It is enabled when EFR[4], the enhanced functions bit, is set **and** when IER[4] bit is also set.

## 6.11.1 Conditions to enter Sleep mode

Sleep mode is entered when:

- · Modem input pins are not toggling.
- The serial data input line, RX, is idle for 4 character time (logic HIGH) and AFCR1[4] is 0. When AFCR1[4] is 1, the device will go to sleep regardless of the state of the RX pin (see Section 7.21 for the description of AFCR1 bit 4).
- The TX FIFO and TX shift register are empty.
- There are no interrupts pending.
- The RX FIFO is empty.

In Sleep mode, the UART clock and baud rate clock are stopped. Since most registers are clocked using these clocks, the power consumption is greatly reduced.

**Remark:** Writing to the divisor latches, DLL and DLM, to set the baud clock, must not be done during Sleep mode. Therefore, it is advisable to disable Sleep mode using IER[4] before writing to DLL or DLM.

#### 6.11.2 Conditions to resume normal operation

SC16C850V resumes normal operation by any of the following:

- · Receives a start bit on RX pin.
- Data is loaded into transmit FIFO.
- A change of state on any of the modem input pins.

If the device is awakened by one of the conditions described above, it will return to the Sleep mode automatically after all the conditions described in <u>Section 6.11.1</u> are met. The device will stay in Sleep mode until it is disabled by setting any channel's IER bit 4 to a logic 0.

When the SC16C850V is in Sleep mode and the host interface bus (AD7 to AD0,  $\overline{\text{IOW}}$ ,  $\overline{\text{IOR}}$ ,  $\overline{\text{CS}}$ ) remains in steady state, either HIGH or LOW, the sleep current will be in the microampere range as specified in <u>Table 36 "Static characteristics"</u>. If any of these signals is toggling or floating then the sleep current will be higher.

#### 6.12 Low power feature

A low power feature is provided by the SC16C850V to prevent the switching of the host data bus from influencing the sleep current. When the pin LOWPWR is activated (logic HIGH), the device immediately and unconditionally goes into Low Power mode. All clocks are stopped and most host interface pins are isolated to reduce power consumption. The device only returns to normal mode when the LOWPWR pin is de-asserted. The pin can be left unconnected because it has an internal pull-down resistor.

#### Single UART with 128-byte FIFOs, IrDA, and XScale VLIO bus interface

#### **6.13 RS-485 Features**

#### 6.13.1 Auto RS-485 RTS control

Normally the RTS pin is controlled by MCR bit 1, or if hardware flow control is enabled, the logic state of the RTS pin is controlled by the hardware flow control circuitry. EFCR2 register bit 4 will take the precedence over the other two modes; once this bit is set, the transmitter will control the state of the RTS pin. The transmitter automatically asserts the RTS pin (logic 0) once the host writes data to the transmit FIFO, and de-asserts the RTS pin (logic 1) once the last bit of the data has been transmitted.

To use the auto RS-485 RTS mode, the software would have to disable the hardware flow control function.

#### 6.13.2 RS-485 RTS inversion

EFCR2 bit 5 reverses the polarity of the  $\overline{RTS}$  pin if the UART is in auto RS-485  $\overline{RTS}$  mode.

When the transmitter has data to be sent, it will de-assert the RTS pin (logic 1), and when the last bit of the data has been sent out, the transmitter asserts the RTS pin (logic 0).

#### 6.13.3 Auto 9-bit mode (RS-485)

EFCR2 bit 0 is used to enable the 9-bit mode (Multi-drop or RS-485 mode). In this mode of operation, a 'master' station transmits an address character followed by data characters for the addressed 'slave' stations. The slave stations examine the received data and interrupt the controller if the received character is an address character (parity bit = 1).

To use the auto 9-bit mode the software would have to disable the hardware and software flow control functions.

#### 6.13.3.1 Normal Multi-drop mode

The 9-bit Mode in EFCR (bit 0) is enabled, but not Special Character Detect (EFR bit 5). The receiver is set to Force Parity 0 (LCR[5:3] = 111) in order to detect address bytes. With the receiver initially disabled, it ignores all the data bytes (parity bit = 0) until an address byte is received (parity bit = 1). This address byte will cause the UART to set the parity error. The UART will generate a line status interrupt (IER bit 2 must be set to '1' at this time), and at the same time puts this address byte in the RX FIFO. After the controller examines the byte it must make a decision whether or not to enable the receiver; it should enable the receiver if the address byte addresses its ID address, and must not enable the receiver if the address byte does not address its ID address.

If the controller enables the receiver, the receiver will receive the subsequent data until being disabled by the controller after the controller has received a complete message from the 'master' station. If the controller does not disable the receiver after receiving a message from the 'master' station, the receiver will generate a parity error upon receiving another address byte. The controller then determines if the address byte addresses its ID address, if it is not, the controller then can disable the receiver. If the address byte addresses the 'slave' ID address, the controller take no further action, the receiver will receive the subsequent data.

#### Single UART with 128-byte FIFOs, IrDA, and XScale VLIO bus interface

#### 6.13.3.2 Auto address detection

If Special Character Detect is enabled (EFR[5] is set and the Xoff2 register contains the address byte), the receiver will try to detect an address byte that matches the programmed character in the Xoff2 register. If the received byte is a data byte or an address byte that does not match the programmed character in the Xoff2 register, the receiver will discard these data. Upon receiving an address byte that matches the Xoff2 character, the receiver will be automatically enabled if not already enabled, and the address character is pushed into the RX FIFO along with the parity bit (in place of the parity error bit). The receiver also generates a line status interrupt (IER[2] must be set to logic 1 at this time). The receiver will then receive the subsequent data from the 'master' station until being disabled by the controller after having received a message from the 'master' station.

If another address byte is received and this address byte does not match Xoff2 character, the receiver will be automatically disabled and the address byte is ignored. If the address byte matches Xoff2 character, the receiver will put this byte in the RX FIFO along with the parity bit in the parity error bit (LSR bit 2).

## 7. Register descriptions

<u>Table 7</u> details the assigned bit functions for the SC16C850V internal registers. The assigned bit functions are more fully defined in <u>Section 7.1</u> through <u>Section 7.23</u>.

Single UART with 128-byte FIFOs, IrDA, and XScale VLIO bus interface

**NXP Semiconductors** 

_													
<b>A3</b>	<b>A2</b>	<b>A</b> 1	Register	Default[1]	Bit 7	Bit 6	Bit 5	Bit 4	Bit 3	Bit 2	Bit 1	Bit 0	R/W
Gen	eral	Regis	ster Set[2]										
0	0	0	RHR	XX	bit 7	bit 6	bit 5	bit 4	bit 3	bit 2	bit 1	bit 0	R
0	0	0	THR	XX	bit 7	bit 6	bit 5	bit 4	bit 3	bit 2	bit 1	bit 0	W
0	0	1	IER	00	CTS interrupt[3]	RTS interrupt[3]	Xoff interrupt[3]	Sleep mode <sup>[3]</sup>	modem status interrupt	receive line status interrupt	transmit holding register interrupt	receive holding register	R/W
0	1	0	FCR	00	RCVR trigger (MSB)	RCVR trigger (LSB)	TX trigger (MSB)[3]	TX trigger (LSB)[3]	reserved	XMIT FIFO reset	RCVR FIFO reset	FIFOs enable	W
0	1	0	ISR	01	FIFOs enabled	FIFOs enabled	INT priority bit 4	INT priority bit 3	INT priority bit 2	INT priority bit 1	INT priority bit 0	INT status	R
0	1	1	LCR	00	divisor latch enable	set break	set parity	even parity	parity enable	stop bits	word length bit 1	word length bit 0	R/W
1	0	0	MCR	00	clock select[3]	IrDA enable	INT type	loopback	OP2	OP1	RTS	DTR	R/W
1	0	1	LSR	60	FIFO data error	THR and TSR empty	THR empty	break interrupt	framing error	parity error	overrun error	receive data ready	R
1	0	1	EFCR	00	reserved	reserved	reserved	reserved	reserved	Enable extra feature bit-1	Enable extra feature bit-0	Enable TXLVLCNT/ RXLVLCNT	W
1	1	0	MSR	X0	CD	RI	DSR	CTS	$\Delta \overline{CD}$	$\Delta \overline{RI}$	ΔDSR	ΔCTS	R
1	1	1	SPR	FF	bit 7	bit 6	bit 5	bit 4	bit 3	bit 2	bit 1	bit 0	R/W
Spe	cial I	Regis	ter Set[4]										
0	0	0	DLL	XX	bit 7	bit 6	bit 5	bit 4	bit 3	bit 2	bit 1	bit 0	R/W
0	0	1	DLM	XX	bit 15	bit 14	bit 13	bit 12	bit 11	bit 10	bit 9	bit 8	R/W
Sec	ond	Spec	ial Register Se	et[5]									
0	1	1	TXLVLCNT	00	bit 7	bit 6	bit 5	bit 4	bit 3	bit 2	bit 1	bit 0	R
1	0	0	RXLVLCNT	00	bit 7	bit 6	bit 5	bit 4	bit 3	bit 2	bit 1	bit 0	R

DTR/DSR

Re
×
5
_
9
ي
7
Ξ
<u>a</u>
2
N
2
$\equiv$

Product data sheet

1	
3	
- 1	
:	
- 1	
- 13	

SC1	Table 7.		SC16C850V internal registerscontinued											
6C850	А3	<b>A2</b>	<b>A1</b>	Register	Default[1]	Bit 7	Bit 6	Bit 5	Bit 4	Bit 3	Bit 2	Bit 1	Bit 0	R/W
Enhanced Register Set[6]														
	0	1	0	EFR	00	Auto CTS	Auto RTS	special character select	Enable IER[7:4], ISR[5:4], FCR[5:4], MCR[7:5]	Cont-3 Tx, Rx Control	Cont-2 Tx, Rx Control	Cont-1 Tx, Rx Control	Cont-0 Tx, Rx Control	R/W
	1	0	0	Xon1	00	bit 7	bit 6	bit 5	bit 4	bit 3	bit 2	bit 1	bit 0	R/W
	1	0	1	Xon2	00	bit 15	bit 14	bit 13	bit 12	bit 11	bit 10	bit 9	bit 8	R/W
	1	1	0	Xoff1	00	bit 7	bit 6	bit 5	bit 4	bit 3	bit 2	bit 1	bit 0	R/W
	1	1	1	Xoff2	00	bit 15	bit 14	bit 13	bit 12	bit 11	bit 10	bit 9	bit 8	R/W
₽	Firs	t Ext	ra Re	egister Set[7]										
inform	0	1	0	TXINTLVL	0x00	bit 7	bit 6	bit 5	bit 4	bit 3	bit 2	bit 1	bit 0	R/W
ation p	1	0	0	RXINTLVL	0x00	bit 7	bit 6	bit 5	bit 4	bit 3	bit 2	bit 1	bit 0	R/W
rovideo	1	1	0	FLWCNTH	0x00	bit 7	bit 6	bit 5	bit 4	bit 3	bit 2	bit 1	bit 0	R/W
in this	1	1	1	FLWCNTL	0x00	bit 7	bit 6	bit 5	bit 4	bit 3	bit 2	bit 1	bit 0	R/W
docur	Second Extra Register Set <sup>[8]</sup>													
nent is	0	1	0	CLKPRES		reserved	reserved	reserved	reserved	bit 3	bit 2	bit 1	bit 0	R/W
subjec	1	0	0	RS485TIME	0x00	bit 7	bit 6	bit 5	bit 4	bit 3	bit 2	bit 1	bit 0	R/W
t to legal disclaim	1	1	0	AFCR2	0x00	reserved	reserved	RS485 RTS invert	Auto RS485 RTS	RS485 RTS/DTR	transmitter disable	receiver disable	9-bit enable	R/W
iers.	1	1	1	AFCR1	0x00	reserved	reserved	reserved	sleep RX LOW	reserved	RTS/CTS mapped to	software reset	TSR interrupt	R/W

- [1] The value shown represents the register's initialized hexadecimal value; X = not applicable.
- Accessible only when LCR[7] is logic 0, and EFCR[2:1] are logic 0.
- This bit is only accessible when EFR[4] is set.
- Baud rate registers accessible only when LCR[7] is logic 1.
- Second Special Registers are accessible only when EFCR[0] = 1, and EFCR[2:1] are logic 0.
- [6] Enhanced Feature Register, Xon1/Xon2 and Xoff1/Xoff2 are accessible only when LCR is set to 0xBF, and EFCR[2:1] are logic 0.
- First Extra Register Set is only accessible when EFCR[2:1] = 01b.
- Second Extra Register Set is only accessible when EFCR[2:1] = 10b.

#### Single UART with 128-byte FIFOs, IrDA, and XScale VLIO bus interface

## 7.1 Transmit (THR) and Receive (RHR) Holding Registers

The serial transmitter section consists of an 8-bit Transmit Hold Register (THR) and Transmit Shift Register (TSR). The status of the THR is provided in the Line Status Register (LSR). Writing to the THR transfers the contents of the data bus (AD7 to AD0) to the transmit FIFO. The THR empty flag in the LSR will be set to a logic 1 when the transmit FIFO is empty or when data is transferred to the TSR.

The serial receive section also contains an 8-bit Receive Holding Register (RHR) and a Receive Serial Shift Register (RSR). Receive data is removed from the SC16C850V receive FIFO by reading the RHR. The receive section provides a mechanism to prevent false starts. On the falling edge of a start or false start bit, an internal receiver counter starts counting clocks at the  $16\times$  clock rate. After  $7\frac{1}{2}$  clocks, the start bit time should be shifted to the center of the start bit. At this time the start bit is sampled, and if it is still a logic 0 it is validated. Evaluating the start bit in this manner prevents the receiver from assembling a false character. Receiver status codes will be posted in the LSR.

## 7.2 Interrupt Enable Register (IER)

The Interrupt Enable Register (IER) masks the interrupts from receiver ready, transmitter empty, line status and modem status registers. These interrupts would normally be seen on the INT output pin.

Table 8. Interrupt Enable Register bits description

Bit	Symbol	Description
7	IER[7]	CTS interrupt.  logic $0 = \text{disable the CTS interrupt (normal default condition)}$ logic $1 = \text{enable the CTS interrupt}$ . The SC16C850V issues an interrupt when the $\overline{\text{CTS}}$ pin transitions from a logic 0 to a logic 1.
6	IER[6]	RTS interrupt.  logic $0 = \text{disable the RTS}$ interrupt (normal default condition)  logic $1 = \text{enable the RTS}$ interrupt. The SC16C850V issues an interrupt when the $\overline{\text{RTS}}$ pin transitions from a logic 0 to a logic 1.
5	IER[5]	Xoff interrupt.  logic 0 = disable the software flow control, receive Xoff interrupt (normal default condition)  logic 1 = enable the receive Xoff interrupt
4	IER[4]	Sleep mode.  logic 0 = disable Sleep mode (normal default condition)  logic 1 = enable Sleep mode
3	IER[3]	Modem Status Interrupt. This interrupt will be issued whenever there is a modem status change as reflected in MSR[3:0].  logic 0 = disable the modem status register interrupt (normal default condition)  logic 1 = enable the modem status register interrupt
2	IER[2]	Receive Line Status interrupt. This interrupt will be issued whenever a receive data error condition exists as reflected in LSR[4:1].  logic 0 = disable the receiver line status interrupt (normal default condition)  logic 1 = enable the receiver line status interrupt

#### Single UART with 128-byte FIFOs, IrDA, and XScale VLIO bus interface

Table 8. Interrupt Enable Register bits description ...continued

Bit	Symbol	Description
	Cy.11501	2000 Ipiloti
1	IER[1]	Transmit Holding Register interrupt. In the non-FIFO mode, this interrupt will be issued whenever the THR is empty, and is associated with LSR[5]. In the FIFO modes, this interrupt will be issued whenever the FIFO is empty.
		logic 0 = disable the Transmit Holding Register Empty (TXRDY) interrupt (normal default condition)
		logic 1 = enable the TXRDY (ISR level 3) interrupt
0	IER[0]	Receive Holding Register. In the non-FIFO mode, this interrupt will be issued when the RHR has data, or is cleared when the RHR is empty. In the FIFO mode, this interrupt will be issued when the FIFO has reached the programmed trigger level or is cleared when the FIFO drops below the trigger level.
		logic 0 = disable the receiver ready (ISR level 2, RXRDY) interrupt (normal default condition)
		logic 1 = enable the RXRDY (ISR level 2) interrupt

## 7.2.1 IER versus transmit/receive FIFO interrupt mode operation

When the receive FIFO is enabled (FCR[0] = logic 1), and receive interrupts (IER[0] = logic 1) are enabled, the receive interrupts and register status will reflect the following:

- The receive RXRDY interrupt (Level 2 ISR interrupt) is issued to the external CPU
  when the receive FIFO has reached the programmed trigger level. It will be cleared
  when the receive FIFO drops below the programmed trigger level.
- Receive FIFO status will also be reflected in the user accessible ISR register when
  the receive FIFO trigger level is reached. Both the ISR register receive status bit and
  the interrupt will be cleared when the FIFO drops below the trigger level.
- The receive data ready bit (LSR[0]) is set as soon as a character is transferred from the shift register (RSR) to the receive FIFO. It is reset when the FIFO is empty.
- When the Transmit FIFO and interrupts are enabled, an interrupt is generated when
  the transmit FIFO is empty due to the unloading of the data by the TSR and UART for
  transmission via the transmission media. The interrupt is cleared either by reading the
  ISR, or by loading the THR with new data characters.

#### 7.2.2 IER versus receive/transmit FIFO polled mode operation

When FCR[0] = logic 1, setting IER[3:0] = zeroes puts the SC16C850V in the FIFO polled mode of operation. In this mode, interrupts are not generated and the user must poll the LSR register for TX and/or RX data status. Since the receiver and transmitter have separate bits in the LSR either or both can be used in the polled mode by selecting respective transmit or receive control bit(s).

- LSR[0] will be a logic 1 as long as there is one byte in the receive FIFO.
- LSR[4:1] will provide the type of receive errors, or a receive break, if encountered.
- LSR[5] will indicate when the transmit FIFO is empty.
- LSR[6] will indicate when both the transmit FIFO and transmit shift register are empty.
- LSR[7] will show if any FIFO data errors occurred.

#### Single UART with 128-byte FIFOs, IrDA, and XScale VLIO bus interface

## 7.3 FIFO Control Register (FCR)

This register is used to enable the FIFOs, clear the FIFOs and set the receive FIFO trigger levels.

#### 7.3.1 FIFO mode

Table 9. FIFO Control Register bits description

Bit	Symbol	Description
7:6	FCR[7:6]	Receive trigger level in 32-byte FIFO mode.[1]
		These bits are used to set the trigger level for receive FIFO interrupt and flow control. The SC16C850V will issue a receive ready interrupt when the number of characters in the receive FIFO reaches the selected trigger level. Refer to Table 10.
5:4	FCR[5:4]	Transmit trigger level in 32-byte FIFO mode.[2]
		These bits are used to set the trigger level for the transmit FIFO interrupt and flow control. The SC16C850V will issue a transmit empty interrupt when the number of characters in FIFO drops below the selected trigger level. Refer to Table 11.
3	FCR[3]	reserved
2	FCR[2]	XMIT FIFO reset.
		logic 0 = no FIFO transmit reset (normal default condition)
		logic 1 = clears the contents of the transmit FIFO and resets the FIFO counter logic. This bit will return to a logic 0 after clearing the FIFO.
1	FCR[1]	RCVR FIFO reset.
		logic 0 = no FIFO receive reset (normal default condition)
		logic 1 = clears the contents of the receive FIFO and resets the FIFO counter logic. This bit will return to a logic 0 after clearing the FIFO.
0	FCR[0]	FIFO enable.
		logic 0 = disable the transmit and receive FIFO (normal default condition)
		logic 1 = enable the transmit and receive FIFO

<sup>[1]</sup> For 128-byte FIFO mode, refer to Section 7.16, Section 7.17, Section 7.18.

Table 10. RCVR trigger levels

FCR[7]	FCR[6]	RX FIFO trigger level in 32-byte FIFO mode[1]
0	0	8 bytes
0	1	16 bytes
1	0	24 bytes
1	1	28 bytes

<sup>[1]</sup> When RXINTLVL or TXINTLVL or FLWCNTH or FLWCNTL contains any value other than 0x00, receive and transmit trigger levels are set by RXINTLVL, TXINTLVL; see Section 6.4 "FIFO operation".

<sup>[2]</sup> For 128-byte FIFO mode, refer to Section 7.15, Section 7.17, Section 7.18.

#### Single UART with 128-byte FIFOs, IrDA, and XScale VLIO bus interface

Table 11. TX FIFO trigger levels

FCR[5]	FCR[4]	TX FIFO trigger level in 32-byte FIFO mode[1]
0	0	16 bytes
0	1	8 bytes
1	0	24 bytes
1	1	30 bytes

<sup>[1]</sup> When RXINTLVL or TXINTLVL or FLWCNTH or FLWCNTL contains any value other than 0x00, receive and transmit trigger levels are set by RXINTLVL, TXINTLVL; see Section 6.4 "FIFO operation".

### 7.4 Interrupt Status Register (ISR)

The SC16C850V provides six levels of prioritized interrupts to minimize external software interaction. The Interrupt Status Register (ISR) provides the user with six interrupt status bits. Performing a read cycle on the ISR will provide the user with the highest pending interrupt level to be serviced. No other interrupts are acknowledged until the pending interrupt is serviced. A lower level interrupt may be seen after servicing the higher level interrupt and re-reading the interrupt status bits. Table 12 "Interrupt source" shows the data values (bits 5:0) for the six prioritized interrupt levels and the interrupt sources associated with each of these interrupt levels.

Table 12. Interrupt source

Priority level	ISR[5]	ISR[4]	ISR[3]	ISR[2]	ISR[1]	ISR[0]	Source of the interrupt
1	0	0	0	1	1	0	LSR (Receiver Line Status Register)
2	0	0	0	1	0	0	RXRDY (Received Data Ready)
2	0	0	1	1	0	0	RXRDY (Receive Data time-out)
3	0	0	0	0	1	0	TXRDY (Transmitter Holding Register Empty)
4	0	0	0	0	0	0	MSR (Modem Status Register)
5	0	1	0	0	0	0	RXRDY (Received Xoff signal)/ Special character
6	1	0	0	0	0	0	CTS, RTS change of state

Table 13. Interrupt Status Register bits description

Bit	Symbol	Description
7:6	ISR[7:6]	FIFOs enabled. These bits are set to a logic 0 when the FIFOs are not being used in the non-FIFO mode. They are set to a logic 1 when the FIFOs are enabled in the SC16C850V mode.
		logic 0 or cleared = default condition
5:4	ISR[5:4]	INT priority bits 4:3. These bits are enabled when EFR[4] is set to a logic 1. ISR[4] indicates that matching Xoff character(s) have been detected. ISR[5] indicates that CTS, RTS have been generated. Note that once set to a logic 1, the ISR[4] bit will stay a logic 1 until Xon character(s) are received. logic 0 or cleared = default condition
3:1	ISR[3:1]	INT priority bits 2:0. These bits indicate the source for a pending interrupt at interrupt priority levels 1, 2, and 3 (see <u>Table 12</u> ).
		logic 0 or cleared = default condition

#### Single UART with 128-byte FIFOs, IrDA, and XScale VLIO bus interface

Table 13. Interrupt Status Register bits description ...continued

Bit	Symbol	Description
0	ISR[0]	INT status.
		logic 0 = an interrupt is pending and the ISR contents may be used as a pointer to the appropriate interrupt service routine
		logic 1 = no interrupt pending (normal default condition)

## 7.5 Line Control Register (LCR)

The Line Control Register is used to specify the asynchronous data communication format. The word length, the number of stop bits, and the parity are selected by writing the appropriate bits in this register.

Table 14. Line Control Register bits description

Bit	Symbol	Description
7	LCR[7]	Divisor latch enable. The internal baud rate counter latch and Enhanced Feature mode enable.
		logic 0 = divisor latch disabled (normal default condition)
		logic 1 = divisor latch enabled
6	LCR[6]	Set break. When enabled, the Break control bit causes a break condition to be transmitted (the TX output is forced to a logic 0 state). This condition exists until disabled by setting LCR[6] to a logic 0.
		logic 0 = no TX break condition (normal default condition)
		logic 1 = forces the transmitter output (TX) to a logic 0 for alerting the remote receiver to a line break condition
5:3	LCR[5:3]	Programs the parity conditions (see <u>Table 15</u> ).
2	LCR[2]	Stop bits. The length of stop bit is specified by this bit in conjunction with the programmed word length (see <u>Table 16</u> ).
		logic 0 or cleared = default condition
1:0	LCR[1:0]	Word length bits 1, 0. These two bits specify the word length to be transmitted or received (see <u>Table 17</u> ).
		logic 0 or cleared = default condition

Table 15. LCR[5:3] parity selection

LCR[5]	LCR[4]	LCR[3]	Parity selection
X	Χ	0	no parity
X	0	1	odd parity
0	1	1	even parity
0	0	1	forced parity '1'
1	1	1	forced parity '0'

Table 16. LCR[2] stop bit length

LCR[2]	Word length (bits)	Stop bit length (bit times)
0	5, 6, 7, 8	1
1	5	11/2
1	6, 7, 8	2

## Single UART with 128-byte FIFOs, IrDA, and XScale VLIO bus interface

Table 17. LCR[1:0] word length

LCR[1]	LCR[0]	Word length (bits)
0	0	5
0	1	6
1	0	7
1	1	8

## 7.6 Modem Control Register (MCR)

This register controls the interface with the modem or a peripheral device.

Table 18. Modem Control Register bits description

Table Bit	Symbol	em Control Register bits description  Description
	_	
7	MCR[7]	Clock select
		logic 0 = divide-by-1 clock input
		logic 1 = divide-by-4 clock input
6	MCR[6]	IR enable (see Figure 14).
		logic 0 = enable the standard modem receive and transmit input/output interface (normal default condition)
		logic 1 = enable infrared IrDA receive and transmit inputs/outputs. While in this mode, the TX/RX output/inputs are routed to the infrared encoder/decoder. The data input and output levels will conform to the IrDA infrared interface requirement. As such, while in this mode, the infrared TX output will be a logic 0 during idle data conditions.
5	MCR[5]	Interrupt type.
		logic 0 = CMOS output
		logic 1 = open-source. A 300 $\Omega$ to 500 $\Omega$ pull-down resistor is required.
4	MCR[4]	Loopback. Enable the local Loopback mode (diagnostics). In this mode the transmitter output (TX) and the receiver input (RX), CTS, DSR, CD, and RI are disconnected from the SC16C850V I/O pins. Internally the modem data and control pins are connected into a loopback data configuration (see Figure 6). In this mode, the receiver and transmitter interrupts remain fully operational. The Modem Control Interrupts are also operational, but the interrupts' sources are switched to the lower four bits of the Modem Control. Interrupts continue to be controlled by the IER register.
		logic 0 = disable Loopback mode (normal default condition)
		logic 1 = enable local Loopback mode (diagnostics)
3	MCR[3]	OP2. This bit is used for internal Loopback mode only. In Loopback mode, this bit is used to write the state of the modem CD interface signal.
2	MCR[2]	OP1. This bit is used for internal Loopback mode only. In Loopback mode, this bit is used to write the state of the modem RI interface signal.
1	MCR[1]	RTS
		logic $0 = \text{force } \overline{\text{RTS}}$ output to a logic 1 (normal default condition)
		logic 1 = force $\overline{RTS}$ output to a logic 0
0	MCR[0]	DTR
		logic $0 = \text{force } \overline{\text{DTR}}$ output to a logic 1 (normal default condition)
		logic 1 = force $\overline{DTR}$ output to a logic 0
		10g.0 1 - 10.00 D TT output to a logic o

SC16C850V **NXP Semiconductors** 

## Single UART with 128-byte FIFOs, IrDA, and XScale VLIO bus interface

Table 19. Interrupt output control

MCR[5]	INT output	
0	active	
1	open-source	

## 7.7 Line Status Register (LSR)

This register provides the status of data transfers between the SC16C850V and the CPU.

Table	Table 20. Line Status Register bits description			
Bit	Symbol	Description		
7	LSR[7]	FIFO data error.		
		logic 0 = no error (normal default condition)		
		logic 1 = at least one parity error, framing error or break indication is in the current FIFO data. This bit is cleared when there are no remaining error flags associated with the remaining data in the FIFO.		
6	LSR[6]	THR and TSR empty. This bit is the Transmit Empty indicator. This bit is set to a logic 1 whenever the transmit holding register and the transmit shift register are both empty. It is reset to logic 0 whenever either the THR or TSR contains a data character. In the FIFO mode, this bit is set to logic 1 whenever the transmit FIFO and transmit shift register are both empty.		
5	LSR[5]	THR empty. This bit is the Transmit Holding Register Empty indicator. This bit indicates that the UART is ready to accept a new character for transmission. In addition, this bit causes the UART to issue an interrupt to CPU when the THR interrupt enable is set. The THR bit is set to a logic 1 when a character is transferred from the transmit holding register into the transmitter shift register. The bit is reset to a logic 0 concurrently with the loading of the transmitter holding register by the CPU. In the FIFO mode, this bit is set when the transmit FIFO is empty; it is cleared when at least 1 byte is written to the transmit FIFO.		
4	LSR[4]	Break interrupt.		
		logic 0 = no break condition (normal default condition)		
		logic 1 = the receiver received a break signal (RX was a logic 0 for one character frame time). In the FIFO mode, only one break character is loaded into the FIFO.		
3	LSR[3]	Framing error.		
		logic 0 = no framing error (normal default condition)		
		logic 1 = framing error. The receive character did not have a valid stop bit(s). In the FIFO mode, this error is associated with the character at the top of the FIFO.		
2	LSR[2]	Parity error.		
		logic 0 = no parity error (normal default condition		
		logic 1 = parity error. The receive character does not have correct parity information and is suspect. In the FIFO mode, this error is associated with the character at the top of the FIFO.		
1	LSR[1]	Overrun error.		
		logic 0 = no overrun error (normal default condition)		
		logic 1 = overrun error. A data overrun error occurred in the Receive Shift Register. This happens when additional data arrives while the FIFO is full. In this case, the previous data in the shift register is overwritten. Note that under this condition, the data byte in the Receive Shift Register is not transferred into the FIFO, therefore the data in the FIFO is not corrupted by the error.		

## Single UART with 128-byte FIFOs, IrDA, and XScale VLIO bus interface

 Table 20.
 Line Status Register bits description ...continued

Bit	Symbol	Description
0	LSR[0]	Receive data ready.
		logic 0 = no data in Receive Holding Register or FIFO (normal default condition)
		logic 1 = data has been received and is saved in the Receive Holding Register or FIFO

## 7.8 Modem Status Register (MSR)

This register shares the same address as EFCR register. This is a read-only register and it provides the current state of the control interface signals from the modem, or other peripheral device to which the SC16C850V is connected. Four bits of this register are used to indicate the changed information. These bits are set to a logic 1 whenever a control input from the modem changes state. These bits are set to a logic 0 whenever the CPU reads this register.

When write, the data will be written to EFCR register.

Table 21. Modem Status Register bits description

Bit	Symbol	Description	
7	MSR[7]	CD. During normal operation, this bit is the complement of the $\overline{\text{CD}}$ input. Reading this bit in the loopback mode produces the state of MCR[3] ( $\overline{\text{OP2}}$ ).	
6	MSR[6]	RI. During normal operation, this bit is the complement of the $\overline{\text{RI}}$ input. Reading this bit in the loopback mode produces the state of MCR[2] ( $\overline{\text{OP1}}$ ).	
5	MSR[5]	DSR. During normal operation, this bit is the complement of the $\overline{\rm DSR}$ input. During the loopback mode, this bit is equivalent to MCR[0] ( $\overline{\rm DTR}$ ).	
4	MSR[4]	CTS. During normal operation, this bit is the complement of the $\overline{\text{CTS}}$ input. During the loopback mode, this bit is equivalent to MCR[1] ( $\overline{\text{RTS}}$ ).	
3	MSR[3]	Δ <del>CD</del> [1]	
		logic $0 = no \overline{CD}$ change (normal default condition)	
		logic 1 = the $\overline{\text{CD}}$ input to the SC16C850V has changed state since the last time it was read. A modem Status Interrupt will be generated.	
2	MSR[2]	Δ <del>R</del> I [1]	
		logic $0 = no \overline{RI}$ change (normal default condition)	
		logic 1 = the $\overline{RI}$ input to the SC16C850V has changed from a logic 0 to a logic 1. A modem Status Interrupt will be generated.	
1	MSR[1]	ΔDSR [1]	
		logic $0 = no \overline{DSR}$ change (normal default condition)	
		logic 1 = the $\overline{\text{DSR}}$ input to the SC16C850V has changed state since the last time it was read. A modem Status Interrupt will be generated.	
0	MSR[0]	ΔCTS [1]	
		logic $0 = no \overline{CTS}$ change (normal default condition)	
		logic 1 = the $\overline{\text{CTS}}$ input to the SC16C850V has changed state since the last time it was read. A modem Status Interrupt will be generated.	

<sup>[1]</sup> Whenever any MSR bit 3:0 is set to logic 1, a Modem Status Interrupt will be generated.

#### Single UART with 128-byte FIFOs, IrDA, and XScale VLIO bus interface

## 7.9 Extra Feature Control Register (EFCR)

This is a write-only register, and it allows the software access to these registers: First Extra Register Set, Second Extra Register Set, Transmit FIFO Level Counter (TXLVLCNT), and Receive FIFO Level Counter (RXLVLCNT).

Table 22. Extra Feature Control Register bits description

Bit	Symbol	Description	
7:3	EFCR[7:3]	reserved	
2:1	EFCR[2:1]	Enable Extra Feature Control bits	
		00 = General Register Set is accessible	
		01 = First Extra Register Set is accessible	
		10 = Second Extra Register Set is accessible	
		11 = reserved	
0	EFCR[0]	Enable TXLVLCNT and RXLVLCNT access	
		0 = TXLVLCNT and RXLVLCNT are disabled	
		1 = TXLVLCNT and RXLVLCNT are enabled and can be read	

**Remark:** EFCR[2:1] has higher priority than EFCR[0]. TXLVLCNT and RXLVLCNT can only be accessed if EFCR[2:1] are zeroes.

#### 7.10 Scratchpad Register (SPR)

The SC16C850V provides a temporary data register to store 8 bits of user information.

## 7.11 Division Latch (DLL and DLM)

These are two 8-bit registers which store the 16-bit divisor for generation of the baud clock in the baud rate generator. DLM stores the most significant part of the divisor. DLL stores the least significant part of the divisor.

#### 7.12 Transmit FIFO Level Count (TXLVLCNT)

This register is a read-only register. It reports the number of spaces available in the transmit FIFO.

#### 7.13 Receive FIFO Level Count (RXLVLCNT)

This register is a read-only register. It reports the fill level of the receive FIFO (the number of characters in the RXFIFO).

## Single UART with 128-byte FIFOs, IrDA, and XScale VLIO bus interface

## 7.14 Enhanced Feature Register (EFR)

Enhanced features are enabled or disabled using this register.

Bit 0 through bit 4 provide single or dual character software flow control selection. When the Xon1 and Xon2 and/or Xoff1 and Xoff2 modes are selected, the double 8-bit words are concatenated into two sequential numbers.

Table 23. Enhanced Feature Register bits description

Bit	Symbol	Description
7	EFR[7]	Automatic CTS flow control.
		logic 0 = automatic CTS flow control is disabled (normal default condition)
		<u>logic</u> 1 = enable automatic CTS flow control. Transmission will stop when CTS goes to a logical 1. Transmission will resume when the $\overline{\text{CTS}}$ signal returns to a logical 0.
6	EFR[6]	Automatic RTS flow control. Automatic RTS may be used for hardware flow control by enabling EFR[6]. When Auto-RTS is selected, an interrupt will be generated when the receive FIFO is filled to the programmed trigger level and RTS will go to a logic 1 at the next trigger level. RTS will return to a logic 0 when data is unloaded below the next lower trigger level (programmed trigger level 1). The state of this register bit changes with the status of the hardware flow control. RTS functions normally when hardware flow control is disabled.
		logic 0 = automatic RTS flow control is disabled (normal default condition)
		logic 1 = enable automatic RTS flow control
5	EFR[5]	Special Character Detect.
		logic 0 = special character detect disabled (normal default condition)
		logic 1 = special character detect enabled. The SC16C850V compares each incoming receive character with Xoff2 data. If a match exists, the received data will be transferred to FIFO and ISR[4] will be set to indicate detection of special character. Bit-0 in the X-registers corresponds with the LSB bit for the receive character. When this feature is enabled, the normal software flow control must be disabled (EFR[3:0] must be set to a logic 0).
4	EFR[4]	Enhanced function control bit. The content of IER[7:4], ISR[5:4], FCR[5:4], and MCR[7:5] can be modified and latched. After modifying any bits in the enhanced registers, EFR[4] can be set to a logic 0 to latch the new values. This feature prevents existing software from altering or overwriting the SC16C850V enhanced functions.
		logic 0 = disable/latch enhanced features[1]
		logic 1 = enables the enhanced functions[1]. When this bit is set to a logic 1, all enhanced features of the SC16C850V are enabled and user settings stored during a reset will be restored.
3:0	EFR[3:0]	Cont-3:0 Tx, Rx control. Logic 0 or cleared is the default condition.  Combinations of software flow control can be selected by programming these bits. See <a href="Table 24">Table 24</a> .

<sup>[1]</sup> Enhanced function control bits: IER[7:4], ISR[5:4], FCR[5:4] and MCR[7:5].

#### Single UART with 128-byte FIFOs, IrDA, and XScale VLIO bus interface

Table 24. Software flow control functions[1]

Cont-3	Cont-2	Cont-1	Cont-0	TX, RX software flow controls
0	0	Χ	Χ	No transmit flow control
1	0	Χ	Χ	Transmit Xon1/Xoff1
0	1	Χ	Χ	Transmit Xon2/Xoff2
1	1	Χ	Χ	Transmit Xon1 and Xon2/Xoff1 and Xoff2
X	Χ	0	0	No receive flow control
X	Χ	1	0	Receiver compares Xon1/Xoff1
X	Χ	0	1	Receiver compares Xon2/Xoff2
1	0	1	1	Transmit Xon1/Xoff1
				Receiver compares Xon1 or Xon2, Xoff1 or Xoff2
0	1	1	1	Transmit Xon2/Xoff2
				Receiver compares Xon1 or Xon2, Xoff1 or Xoff2
1	1	1	1	Transmit Xon1 and Xon2, Xoff1 and Xoff2
				Receiver compares Xon1 and Xon2, Xoff1 and Xoff2

<sup>[1]</sup> When using a software flow control the Xon/Xoff characters cannot be used for data transfer.

## 7.15 Transmit Interrupt Level register (TXINTLVL)

This 8-bit register is used store the transmit FIFO trigger levels used for interrupt generation. Trigger levels from 1 to 128 can be programmed with a granularity of 1. Table 25 shows trigger level register bit settings.

Table 25. TXINTLVL register bits description

Bit	Symbol	Description
7:0	TXINTLVL[7:0]	This register stores the programmable transmit interrupt trigger levels for 128-byte FIFO mode. [1]
		0x00 = trigger level is set to 1
		0x01 = trigger level is set to 1
		0x80 = trigger level is set to 128

<sup>[1]</sup> For 32-byte FIFO mode, refer to Section 7.3 "FIFO Control Register (FCR)".

## 7.16 Receive Interrupt Level register (RXINTLVL)

This 8-bit register is used store the receive FIFO trigger levels used for interrupt generation. Trigger levels from 1 to 128 can be programmed with a granularity of 1. Table 26 shows trigger level register bit settings.

Table 26. RXINTLVL register bits description

Bit	Symbol	Description
7:0	RXINTLVL[7:0]	This register stores the programmable receive interrupt trigger levels for 128-byte FIFO mode. [1]
		0x00 = trigger level is set to 1
		0x01 = trigger level is set to 1
		0x80 = trigger level is set to 128

SC16C850V

#### Single UART with 128-byte FIFOs, IrDA, and XScale VLIO bus interface

[1] For 32-byte FIFO mode, refer to Section 7.3 "FIFO Control Register (FCR)".

## 7.17 Flow Control Trigger Level High (FLWCNTH)

This 8-bit register is used to store the receive FIFO high threshold levels to start/stop transmission during hardware/software flow control. <u>Table 27</u> shows transmission control register bit settings; see <u>Section 6.5</u>.

Table 27. FLWCNTH register bits description

Bit	Symbol	Description
7:0	FLWCNTH[7:0]	This register stores the programmable HIGH threshold level for hardware and software flow control for 128-byte FIFO mode.[1]
		0x00 = trigger level is set to 1
		0x01 = trigger level is set to 1
		0x80 = trigger level is set to 128

<sup>[1]</sup> For 32-byte FIFO mode, refer to Section 7.3 "FIFO Control Register (FCR)".

## 7.18 Flow Control Trigger Level Low (FLWCNTL)

This 8-bit register is used to store the receive FIFO low threshold levels to start/stop transmission during hardware/software flow control. <u>Table 28</u> shows transmission control register bit settings; see <u>Section 6.5</u>.

Table 28. FLWCNTL register bits description

Bit	Symbol	Description
		This register stores the programmable LOW threshold level for hardware and software flow control for 128-byte FIFO mode.[1]
		0x00 = trigger level is set to 1
		0x01 = trigger level is set to 1
		0x80 = trigger level is set to 128

<sup>[1]</sup> For 32-byte FIFO mode, refer to Section 7.3 "FIFO Control Register (FCR)".

## 7.19 Clock prescaler (CLKPRES)

This register hold values for the clock prescaler.

Table 29. Clock prescaler register description

Bit	Symbol	Description
7:4	CLKPRES[7:4]	reserved
3:0	CLKPRES[3:0]	clock prescaler value; reset to 0

## Single UART with 128-byte FIFOs, IrDA, and XScale VLIO bus interface

## 7.20 RS-485 turn-around time delay (RS485TIME)

The value in this register controls the <u>turn-around</u> time of the external line transceiver in bit time. In automatic 9-bit mode, the RTS or DTR pin is used to control the direction of the line driver, after the last bit of data has been shifted out of the transmit shift register the UART will count down the value in this register. When the count value reaches zero, the UART will assert the RTS or DTR pin (logic 0) to turn the external RS-485 transceiver around for receiving.

Table 30. RS-485 programmable turn-around time register

Bit	Symbol	Description
7:0	RS485TIME[7:0]	External RS-485 transceiver turn-around time delay. The value represents the bit time at the programmed baud rate.

## 7.21 Advanced Feature Control Register 1 (AFCR1)

Table 31. Advanced Feature Control Register 1 bits description

Bit	Symbol	Description					
7:5	AFCR1[7:5]	reserved					
4	AFCR1[4]	CR1[4] Sleep RXIow. Program RX input to be edge-sensitive or level-sensitive.					
		logic 0 = RX input is level sensitive. If RX pin is LOW, the UART will not go to sleep. Once the UART is in Sleep mode, it will wake up if RX pin goes LOW.					
		logic 1 = RX input is edge sensitive. UART will go to sleep even if RX pin is LOW, and will wake up when RX pin toggles.					
3	AFCR1[3]	reserved					
2	AFCR1[2]	RTS/CTS mapped to DTR/DSR. Switch the function of RTS/CTS to DTR/DSR.					
		logic 0 = RTS and CTS signals are used for hardware flow control					
		logic 1 = DTR and DSR signals are used for hardware flow control. RTS and CTS retain their functionality.					
1	AFCR1[1]	SReset. Software reset. A write to this bit will reset the UART. Once the UART is reset this bit is automatically set to logic 0.[1]					
0	AFCR1[0]	TSR interrupt. Select TSR interrupt mode.					
		logic 0 = transmit empty interrupt occurs when transmit FIFO falls below the trigger level or becomes empty.					
		logic 1 = transmit empty interrupt occurs when transmit FIFO fall below the trigger level, or becomes empty and the last stop bit has been shift out the transmit shift register.					

<sup>[1]</sup> It takes 4 XTAL1 clocks to reset the device.

## Single UART with 128-byte FIFOs, IrDA, and XScale VLIO bus interface

# 7.22 Advanced Feature Control Register 2 (AFCR2)

Table 32. Advanced Feature Control Register 2 bits description

Symbol	Description
AFCR2[7:6]	reserved
AFCR2[5]	RTSInvert. Invert RTS or DTR signal in auto 9-bit mode.
	logic 0 = RTS or DTR is set to 0 by the UART during transmission, and to 1 during reception
	logic 1 = RTS or DTR is set to 1 by the UART during transmission, and to 0 during reception
AFCR2[4]	RTSCon. Enable the transmitter to control RTS or DTR signal in auto 9-bit mode.
	logic 0 = transmitter does not control RTS or DTR signal
	logic 1 = transmitter controls RTS or DTR signal
AFCR2[3]	RS485 RTS/DTR. Select RTS or DTR pin to control the external transceiver.
	logic $0 = \overline{RTS}$ pin is used to control the external transceiver
	logic 1 = $\overline{DTR}$ pin is used to control the external transceiver
AFCR2[2]	TXDisable. Disable transmitter.
	logic 0 = transmitter is enabled
	logic 1 = transmitter is disabled
AFCR2[1]	RXDisable. Disable receiver.
	logic 0 = receiver is enabled
	logic 1 = receiver is disabled
AFCR2[0]	9-bitMode. Enable 9-bit mode or Multidrop (RS-485) mode.
	logic 0 = normal RS-232 mode
	logic 1 = enable 9-bit mode
	AFCR2[7:6] AFCR2[5]  AFCR2[4]  AFCR2[3]  AFCR2[2]

## Single UART with 128-byte FIFOs, IrDA, and XScale VLIO bus interface

## 7.23 SC16C850V external reset condition and software reset

These two reset methods are identical and will reset the internal registers as indicated in Table 33.

Table 33. Reset state for registers

Table co. Tree	or state for registers
Register	Reset state
IER	IER[7:0] = 0
FCR	FCR[7:0] = 0
ISR	ISR[7:1] = 0; ISR[0] = 1
LCR	LCR[7:0] = 0
MCR	MCR[7:0] = 0
LSR	LSR[7] = 0; LSR[6:5] = 1; LSR[4:0] = 0
MSR	MSR[7:4] = input signals; MSR[3:0] = 0
EFCR	EFCR[7:0] = 0
SPR	SPR[7:0] = 1
DLL	undefined
DLM	undefined
TXLVLCNT	TXLVLCNT[7:0] = 0
RXLVLCNT	RXLVLCNT[7:0] = 0
EFR	EFR[7:0] = 0
Xon1	Undefined
Xon2	Undefined
Xoff1	Undefined
Xoff2	Undefined
TXINTLVL	TXINTLVL[7:0] = 0
RXINTLVL	RXINTLVL[7:0] = 0
FLWCNTH	FLWCNTH[7:0] = 0
FLWCNTL	FLWCNTL[7:0] = 0
CLKPRES	CLKPRES[7:0] = 0
RS485TIME	RS485TIME[7:0] = 0
AFCR2	AFCR2[7:0] = 0
AFCR1	AFCR1[7:0] = 0

Table 34. Reset state for outputs

Output R	Reset state
	ogic 1
	ogic 1
DTR lo	ogic 1
INT 3	3-state condition

## Single UART with 128-byte FIFOs, IrDA, and XScale VLIO bus interface

## 8. Limiting values

Table 35. Limiting values

In accordance with the Absolute Maximum Rating System (IEC 60134).

Symbol	Parameter	Conditions		Min	Max	Unit
$V_{DD}$	supply voltage			-	2.5	V
V <sub>n</sub>	voltage on any other pin		[1]	$V_{SS} - 0.3$	$V_{DD} + 0.3$	V
T <sub>amb</sub>	ambient temperature	operating in free air		-40	+85	°C
T <sub>stg</sub>	storage temperature			-65	+150	°C
P <sub>tot</sub> /pack	total power dissipation per package			-	500	mW

<sup>[1]</sup> V<sub>n</sub> should not exceed 2.5 V.

## 9. Static characteristics

Table 36. Static characteristics

 $T_{amb} = -40$  °C to +85 °C;  $V_{DD} = 1.65$  V to 1.95 V; unless otherwise specified.

Symbol	Parameter	Conditions	Min	Тур	Max	Unit
$V_{\text{IL}(\text{clk})}$	clock LOW-level input voltage	XTAL1 pin	-	-	0.25	V
V <sub>IH(clk)</sub>	clock HIGH-level input voltage	XTAL1 pin	1.35	-	-	V
$V_{IL}$	LOW-level input voltage	except XTAL1 clock, LOWPWR pin	-	-	0.45	V
		LOWPWR pin	<u>[1]</u> _	-	0.45	V
$V_{IH}$	HIGH-level input voltage	except XTAL1 clock, LOWPWR pin	1.35	-	-	V
		LOWPWR pin	1.35	-	-	V
$V_{OL}$	LOW-level output voltage	$I_{OL} = 2 \text{ mA}$	[2] _	-	0.35	V
$V_{OH}$	HIGH-level output voltage	$I_{OH} = -800 \ \mu A$	<sup>[2]</sup> 1.45	-	-	V
I <sub>LIL</sub>	LOW-level input leakage current		-	-	1	μΑ
I <sub>LIH</sub>	HIGH-level input leakage current		-	-	1	μΑ
I <sub>L(clk)</sub>	clock leakage current	LOW-level	-	-	30	μΑ
		HIGH-level	-	-	30	μΑ
$I_{DD}$	supply current	f = 5 MHz	-	-	2	mA
I <sub>DD(sleep)</sub>	sleep mode supply current		[3] _	-	5	μΑ
$I_{DD(Ip)}$	low-power mode supply current		[4] -	-	5	μΑ
C <sub>i</sub>	input capacitance		_	-	5	pF

<sup>[1]</sup> Hysteresis input.

<sup>[2]</sup> Except XTAL2.

<sup>[3]</sup> Sleep current might be higher if there is any activity on the UART data bus during Sleep mode.

<sup>[4]</sup> Activate by LOWPWR pin.

## Single UART with 128-byte FIFOs, IrDA, and XScale VLIO bus interface

# 10. Dynamic characteristics

Table 37. Dynamic characteristics

 $T_{amb} = -40$  °C to +85 °C;  $V_{DD} = 1.65$  V to 1.95 V; unless otherwise specified.

Symbol	Parameter	Conditions		Min	Тур	Max	Unit
f <sub>XTAL1</sub>	frequency on pin XTAL1		<u>[1]</u>	-	-	80	MHz
t <sub>d(CS-LLAH)</sub>	delay time from CS to LLA HIGH			10	-	-	ns
t <sub>su(A-LLAH)</sub>	set-up time from address to LLA HIGH			5	-	-	ns
t <sub>w(LLA)</sub>	LLA pulse width time			10	-	-	ns
t <sub>h(LLAH-A)</sub>	address hold time after LLA HIGH			10	-	-	ns
t <sub>d(IOW)</sub>	IOW delay time			10	-	-	ns
t <sub>d(IOR-DV)</sub>	delay time from IOR to data valid	25 pF load		-	-	40	ns
$t_{w(IOR)}$	IOR pulse width time			20	-	-	ns
t <sub>d(LLAH-IORL)</sub>	delay time from LLA HIGH to IOR LOW			10	-	-	ns
$t_{w(IOW)}$	IOW pulse width time			10	-	-	ns
t <sub>h(IOWH-D)</sub>	data input hold time after IOW HIGH			5	-	-	ns
t <sub>d(LLAH-IOWL)</sub>	delay time from LLA HIGH to IOW LOW			10	-	-	ns
t <sub>su(D-IOWH)</sub>	set-up time from data input to IOW HIGH			5	-	-	ns
t <sub>d(IOR)</sub>	IOR delay time			10	-	-	ns
$t_{\text{dis}(\text{IOR-QZ})}$	disable time from $\overline{\text{IOR}}$ to high-impedance data output [2]	25 pF load		-	-	20	ns
$t_{d(IOW-Q)}$	delay time from IOW to data output	25 pF load		-	-	50	ns
t <sub>d(modem-INT)</sub>	delay time from modem to INT	25 pF load		-	-	50	ns
t <sub>d(IOR-INTL)</sub>	delay time from IOR to INT LOW	25 pF load		-	-	50	ns
$t_{WH}$	pulse width HIGH			6	-	-	ns
t <sub>WL</sub>	pulse width LOW			6	-	-	ns
t <sub>w(clk)</sub>	clock pulse width			12.5	-	-	ns
t <sub>d(stop-INT)</sub>	delay time from stop to INT	25 pF load	[3]	-	-	1T <sub>RCLK</sub>	S
t <sub>d(start-INT)</sub>	delay time from start to INT	25 pF load	[3]	-	-	1T <sub>RCLK</sub>	S
t <sub>d(IOW-TX)</sub>	delay time from $\overline{\text{IOW}}$ to TX		[3]	8T <sub>RCLK</sub>	-	24T <sub>RCLK</sub>	S
t <sub>d(IOW-INTL)</sub>	delay time from $\overline{\text{IOW}}$ to INT LOW	25 pF load		-	-	50	ns
$t_{w(RESET\_N)}$	pulse width on pin RESET			10	-	-	ns


<sup>[1]</sup> External clock only; maximum crystal frequency is 24 MHz.


<sup>[2] 10 %</sup> of the data bus output voltage level.

<sup>[3]</sup> RCLK is an internal frequency and it is equal to 16 times the baud rate.


## Single UART with 128-byte FIFOs, IrDA, and XScale VLIO bus interface


# 10.1 Timing diagrams







## Single UART with 128-byte FIFOs, IrDA, and XScale VLIO bus interface






# Single UART with 128-byte FIFOs, IrDA, and XScale VLIO bus interface





## Single UART with 128-byte FIFOs, IrDA, and XScale VLIO bus interface






Fig 14. Infrared receive timing

### Single UART with 128-byte FIFOs, IrDA, and XScale VLIO bus interface

# 11. Package outline

HVQFN32: plastic thermal enhanced very thin quad flat package; no leads; 32 terminals; body  $5 \times 5 \times 0.85 \text{ mm}$ 

SOT617-1




Fig 15. Package outline SOT617-1 (HVQFN32)

16C850V All information provided in this document is subject to legal disclaimers.

© NXP B.V. 2011. All rights reserved.

#### Single UART with 128-byte FIFOs, IrDA, and XScale VLIO bus interface

# 12. Soldering of SMD packages

This text provides a very brief insight into a complex technology. A more in-depth account of soldering ICs can be found in Application Note *AN10365* "Surface mount reflow soldering description".

### 12.1 Introduction to soldering

Soldering is one of the most common methods through which packages are attached to Printed Circuit Boards (PCBs), to form electrical circuits. The soldered joint provides both the mechanical and the electrical connection. There is no single soldering method that is ideal for all IC packages. Wave soldering is often preferred when through-hole and Surface Mount Devices (SMDs) are mixed on one printed wiring board; however, it is not suitable for fine pitch SMDs. Reflow soldering is ideal for the small pitches and high densities that come with increased miniaturization.

### 12.2 Wave and reflow soldering

Wave soldering is a joining technology in which the joints are made by solder coming from a standing wave of liquid solder. The wave soldering process is suitable for the following:

- Through-hole components
- · Leaded or leadless SMDs, which are glued to the surface of the printed circuit board

Not all SMDs can be wave soldered. Packages with solder balls, and some leadless packages which have solder lands underneath the body, cannot be wave soldered. Also, leaded SMDs with leads having a pitch smaller than ~0.6 mm cannot be wave soldered, due to an increased probability of bridging.

The reflow soldering process involves applying solder paste to a board, followed by component placement and exposure to a temperature profile. Leaded packages, packages with solder balls, and leadless packages are all reflow solderable.

Key characteristics in both wave and reflow soldering are:

- · Board specifications, including the board finish, solder masks and vias
- · Package footprints, including solder thieves and orientation
- The moisture sensitivity level of the packages
- Package placement
- Inspection and repair
- Lead-free soldering versus SnPb soldering

### 12.3 Wave soldering

Key characteristics in wave soldering are:

- Process issues, such as application of adhesive and flux, clinching of leads, board transport, the solder wave parameters, and the time during which components are exposed to the wave
- Solder bath specifications, including temperature and impurities

SC16C850\

#### Single UART with 128-byte FIFOs, IrDA, and XScale VLIO bus interface

## 12.4 Reflow soldering

Key characteristics in reflow soldering are:

- Lead-free versus SnPb soldering; note that a lead-free reflow process usually leads to higher minimum peak temperatures (see <u>Figure 16</u>) than a SnPb process, thus reducing the process window
- Solder paste printing issues including smearing, release, and adjusting the process window for a mix of large and small components on one board
- Reflow temperature profile; this profile includes preheat, reflow (in which the board is heated to the peak temperature) and cooling down. It is imperative that the peak temperature is high enough for the solder to make reliable solder joints (a solder paste characteristic). In addition, the peak temperature must be low enough that the packages and/or boards are not damaged. The peak temperature of the package depends on package thickness and volume and is classified in accordance with Table 38 and 39

Table 38. SnPb eutectic process (from J-STD-020C)

Package thickness (mm)	Package reflow temperature (°C)		
	Volume (mm³)		
	< 350	≥ 350	
< 2.5	235	220	
≥ 2.5	220	220	


Table 39. Lead-free process (from J-STD-020C)

Package thickness (mm)	Package reflow temperature (°C)  Volume (mm³)			
	< 350	350 to 2000	> 2000	
< 1.6	260	260	260	
1.6 to 2.5	260	250	245	
> 2.5	250	245	245	

Moisture sensitivity precautions, as indicated on the packing, must be respected at all times.

Studies have shown that small packages reach higher temperatures during reflow soldering, see Figure 16.

# Single UART with 128-byte FIFOs, IrDA, and XScale VLIO bus interface



For further information on temperature profiles, refer to Application Note *AN10365* "Surface mount reflow soldering description".

# 13. Abbreviations

Table 40. Abbreviations

Description
Central Processing Unit
First In, First Out
Infrared Data Association
Integrated Service Digital Network
Least Significant Bit
Most Significant Bit
Restriction of Hazardous Substances directive
Universal Asynchronous Receiver/Transmitter
Variable Latency Input/Output

## Single UART with 128-byte FIFOs, IrDA, and XScale VLIO bus interface

# 14. Revision history

### Table 41. Revision history

Document ID	Release date	Data sheet status	Change notice	Supersedes
SC16C850V v.5	20110119	Product data sheet	-	SC16C850V v.4
Modifications:	<ul> <li>Table 36 "Static characteristics":</li> <li>V<sub>IL(clk)</sub> specification: added condition "XTAL1 pin"</li> <li>V<sub>IH(clk)</sub> specification: added condition "XTAL1 pin"</li> <li>V<sub>IL</sub> specification split for condition "LOWPWR pin".</li> <li>V<sub>IH</sub> specification split for condition "LOWPWR pin".</li> <li>Added (new) Table note [1].</li> </ul>			
SC16C850V v.4	20080114	Product data sheet	-	SC16C850V v.3
SC16C850V v.3	20070924	Product data sheet	-	SC16C850V v.2
SC16C850V v.2	20070413	Product data sheet	-	SC16C850V v.1
SC16C850V v.1	20061107	Objective data sheet	-	-

#### Single UART with 128-byte FIFOs, IrDA, and XScale VLIO bus interface

# 15. Legal information

#### 15.1 Data sheet status

Document status[1][2]	Product status[3]	Definition
Objective [short] data sheet	Development	This document contains data from the objective specification for product development.
Preliminary [short] data sheet	Qualification	This document contains data from the preliminary specification.
Product [short] data sheet	Production	This document contains the product specification.

- [1] Please consult the most recently issued document before initiating or completing a design.
- [2] The term 'short data sheet' is explained in section "Definitions"
- [3] The product status of device(s) described in this document may have changed since this document was published and may differ in case of multiple devices. The latest product status information is available on the Internet at URL http://www.nxp.com.

#### 15.2 Definitions

Draft — The document is a draft version only. The content is still under internal review and subject to formal approval, which may result in modifications or additions. NXP Semiconductors does not give any representations or warranties as to the accuracy or completeness of information included herein and shall have no liability for the consequences of use of such information.

Short data sheet — A short data sheet is an extract from a full data sheet with the same product type number(s) and title. A short data sheet is intended for quick reference only and should not be relied upon to contain detailed and full information. For detailed and full information see the relevant full data sheet, which is available on request via the local NXP Semiconductors sales office. In case of any inconsistency or conflict with the short data sheet, the full data sheet shall prevail.

**Product specification** — The information and data provided in a Product data sheet shall define the specification of the product as agreed between NXP Semiconductors and its customer, unless NXP Semiconductors and customer have explicitly agreed otherwise in writing. In no event however, shall an agreement be valid in which the NXP Semiconductors product is deemed to offer functions and qualities beyond those described in the Product data sheet.

#### 15.3 Disclaimers

Limited warranty and liability — Information in this document is believed to be accurate and reliable. However, NXP Semiconductors does not give any representations or warranties, expressed or implied, as to the accuracy or completeness of such information and shall have no liability for the consequences of use of such information.

In no event shall NXP Semiconductors be liable for any indirect, incidental, punitive, special or consequential damages (including - without limitation - lost profits, lost savings, business interruption, costs related to the removal or replacement of any products or rework charges) whether or not such damages are based on tort (including negligence), warranty, breach of contract or any other legal theory.

Notwithstanding any damages that customer might incur for any reason whatsoever, NXP Semiconductors' aggregate and cumulative liability towards customer for the products described herein shall be limited in accordance with the *Terms and conditions of commercial sale* of NXP Semiconductors.

Right to make changes — NXP Semiconductors reserves the right to make changes to information published in this document, including without limitation specifications and product descriptions, at any time and without notice. This document supersedes and replaces all information supplied prior to the publication hereof.

**Suitability for use** — NXP Semiconductors products are not designed, authorized or warranted to be suitable for use in life support, life-critical or safety-critical systems or equipment, nor in applications where failure or

malfunction of an NXP Semiconductors product can reasonably be expected to result in personal injury, death or severe property or environmental damage. NXP Semiconductors accepts no liability for inclusion and/or use of NXP Semiconductors products in such equipment or applications and therefore such inclusion and/or use is at the customer's own risk.

**Applications** — Applications that are described herein for any of these products are for illustrative purposes only. NXP Semiconductors makes no representation or warranty that such applications will be suitable for the specified use without further testing or modification.

Customers are responsible for the design and operation of their applications and products using NXP Semiconductors products, and NXP Semiconductors accepts no liability for any assistance with applications or customer product design. It is customer's sole responsibility to determine whether the NXP Semiconductors product is suitable and fit for the customer's applications and products planned, as well as for the planned application and use of customer's third party customer(s). Customers should provide appropriate design and operating safeguards to minimize the risks associated with their applications and products.

NXP Semiconductors does not accept any liability related to any default, damage, costs or problem which is based on any weakness or default in the customer's applications or products, or the application or use by customer's third party customer(s). Customer is responsible for doing all necessary testing for the customer's applications and products using NXP Semiconductors products in order to avoid a default of the applications and the products or of the application or use by customer's third party customer(s). NXP does not accept any liability in this respect.

Limiting values — Stress above one or more limiting values (as defined in the Absolute Maximum Ratings System of IEC 60134) will cause permanent damage to the device. Limiting values are stress ratings only and (proper) operation of the device at these or any other conditions above those given in the Recommended operating conditions section (if present) or the Characteristics sections of this document is not warranted. Constant or repeated exposure to limiting values will permanently and irreversibly affect the quality and reliability of the device.

Terms and conditions of commercial sale — NXP Semiconductors products are sold subject to the general terms and conditions of commercial sale, as published at <a href="http://www.nxp.com/profile/terms">http://www.nxp.com/profile/terms</a>, unless otherwise agreed in a valid written individual agreement. In case an individual agreement is concluded only the terms and conditions of the respective agreement shall apply. NXP Semiconductors hereby expressly objects to applying the customer's general terms and conditions with regard to the purchase of NXP Semiconductors products by customer.

No offer to sell or license — Nothing in this document may be interpreted or construed as an offer to sell products that is open for acceptance or the grant, conveyance or implication of any license under any copyrights, patents or other industrial or intellectual property rights.

**Export control** — This document as well as the item(s) described herein may be subject to export control regulations. Export might require a prior authorization from national authorities.

SC16C850V

All information provided in this document is subject to legal disclaimers.

© NXP B.V. 2011. All rights reserved.

### Single UART with 128-byte FIFOs, IrDA, and XScale VLIO bus interface

Non-automotive qualified products — Unless this data sheet expressly states that this specific NXP Semiconductors product is automotive qualified, the product is not suitable for automotive use. It is neither qualified nor tested in accordance with automotive testing or application requirements. NXP Semiconductors accepts no liability for inclusion and/or use of non-automotive qualified products in automotive equipment or applications.

In the event that customer uses the product for design-in and use in automotive applications to automotive specifications and standards, customer (a) shall use the product without NXP Semiconductors' warranty of the product for such automotive applications, use and specifications, and (b) whenever customer uses the product for automotive applications beyond

NXP Semiconductors' specifications such use shall be solely at customer's own risk, and (c) customer fully indemnifies NXP Semiconductors for any liability, damages or failed product claims resulting from customer design and use of the product for automotive applications beyond NXP Semiconductors' standard warranty and NXP Semiconductors' product specifications.

#### 15.4 Trademarks

Notice: All referenced brands, product names, service names and trademarks are the property of their respective owners.

### 16. Contact information

For more information, please visit: http://www.nxp.com

For sales office addresses, please send an email to: salesaddresses@nxp.com

SC16C850V **NXP Semiconductors** 

# Single UART with 128-byte FIFOs, IrDA, and XScale VLIO bus interface

# 17. Contents

1	General description	. 1	7.11	Division Latch (DLL and DLM)	
2	Features and benefits	. 1	7.12	Transmit FIFO Level Count (TXLVLCNT)	
3	Ordering information	. 2	7.13	Receive FIFO Level Count (RXLVLCNT)	
4	Block diagram		7.14	Enhanced Feature Register (EFR)	29
5	Pinning information		7.15	Transmit Interrupt Level register (TXINTLVL)	30
	_		7.16	Receive Interrupt Level register (RXINTLVL).	30
5.1	Pinning		7.17	Flow Control Trigger Level High (FLWCNTH)	31
5.2	Pin description		7.18	Flow Control Trigger Level Low (FLWCNTL).	
6	Functional description		7.19	, ,	31
6.1	UART selection		7.20	RS-485 turn-around time delay (RS485TIME)	32
6.2	Extended mode (128-byte FIFO)		7.21	Advanced Feature Control Register 1	
6.3	Internal registers		<b>-</b> 00	(AFCR1)	32
6.4	FIFO operation		7.22	Advanced Feature Control Register 2	
6.4.1	32-byte FIFO mode			(AFCR2)	33
6.4.2	128-byte FIFO mode		7.23	SC16C850V external reset condition	
6.5	Hardware flow control			and software reset	
6.6	Software flow control		8	Limiting values	
6.7	Special character detect		9	Static characteristics	35
6.8	Interrupt priority and time-out interrupts		10	Dynamic characteristics	36
6.9	Programmable baud rate generator		10.1	Timing diagrams	37
6.10	Loopback mode		11	Package outline	
6.11 6.11.1	Sleep mode		12	Soldering of SMD packages	
6.11.2	·		12.1	Introduction to soldering	
6.11.2 6.12	Conditions to resume normal operation Low power feature		12.1	Wave and reflow soldering	
6.13	RS-485 Features		12.2	Wave soldering	
6.13.1	Auto RS-485 RTS control		12.3	Reflow soldering	
6.13.1	RS-485 RTS inversion		13		
6.13.3	Auto 9-bit mode (RS-485)			Abbreviations	
6.13.3.1			14	Revision history	
6.13.3.2			15	Legal information	46
7	Register descriptions		15.1	Data sheet status	
		17	15.2	Definitions	46
7.1	Transmit (THR) and Receive (RHR) Holding	20	15.3	Disclaimers	46
7.2	Registers		15.4	Trademarks	47
7.2 7.2.1	Interrupt Enable Register (IER)	20	16	Contact information	47
1.2.1	interrupt mode operation	21	17	Contents	48
7.2.2	IER versus receive/transmit FIFO	<b>4</b> 1			
1.2.2	polled mode operation	21			
7.3	FIFO Control Register (FCR)				
7.3.1	FIFO mode				
7.3.1 7.4	Interrupt Status Register (ISR)				
7. <del>4</del> 7.5	Line Control Register (LCR)				
7.6	Modem Control Register (MCR)				
7.0 7.7	Line Status Register (LSR)				
7.8	Modem Status Register (MSR)				
7.9	Extra Feature Control Register (EFCR)				
7.3 7.10	Scratchpad Register (SPR)				

Please be aware that important notices concerning this document and the product(s) described herein, have been included in section 'Legal information'.

© NXP B.V. 2011.

All rights reserved.

For more information, please visit: http://www.nxp.com For sales office addresses, please send an email to: salesaddresses@nxp.com

Date of release: 19 January 2011 Document identifier: SC16C850V