

UM11170 TEA1936xDB1556 27 W compact power supply demo board Rev. 1.03 — 7 January 2019 User manual COMPANY PUBLIC

Document information

Information	Content
Keywords	TEA1936xDB1556, TEA1936x, TEA1999, adapter, switched-mode power supply (SMPS), synchronous rectifier
Abstract	This user manual describes the performance, technical data, and the connections of the TEA1936xDB1556 demo board. The TEA1936xDB1556 demo board operates at mains voltages from 90 V (AC) up to 264 V (AC) with an output voltage from 3 V, 5 V, and 12 V (DC) at a maximum output current of 3 A.



Revision history

Revision history		
Rev	Date	Description
v.1	20181220	first issue

1 Introduction

WARNING

Lethal voltage and fire ignition hazard




The non-insulated high voltages that are present when operating this product, constitute a risk of electric shock, personal injury, death and/ or ignition of fire. This product is intended for evaluation purposes only. It shall be operated in a designated test area by personnel qualified according to local requirements and labor laws to work with non-insulated mains voltages and high-voltage circuits. This product shall never be operated unattended.

This user manual describes the operation of the TEA1936xDB1556 demo board featuring the quasi-resonant (QR) controller TEA19361 and the synchronous rectifier controller (SR) TEA1999.

The TEA1936xDB1556 demo board is designed for delivering a maximum output power of 27 W at a maximum current of 3 A. Output voltages can be chosen from 3 V, 5 V, and 12 V using a soldering jumper.

The TEA1936xDB1556 provides an effective solution with a low output current ripple and high efficiency for SMPS adapter applications.



1.1 Key features

- · Soldering jumper can set the output voltage
- · Functionality user-configurable end of line
- Best-in-class energy efficiency meeting all DOE & EU CoC requirements
- Small size due to high near-full digital integration level and high W/CI power density
- · Best in class thermal management
- Safe solution with extensive set of hardware-integrated protection features
- Complete one-stop-shop solution from NXP Semiconductors, minimizing development time and research and development costs

1.2 Applications

Mobile adapter with DC cable for:

Notebooks


The new adapter platform of NXP Semiconductors helps designers of notebook adapters to maximize power output for smallest form-factor and with lowest bill of materials.

The result is a cost-effective design that meets the requirements published by Energy Star, the Department of Energy (DoE) in the United States, the Ecodesign Directive of the European Union, the European Code of Conduct, and other guidelines.

2 Safety warning

The demo board is connected to the mains voltage. Avoid touching the board while it is connected to the mains voltage and when it is in operation. When used in uncontrolled, non-laboratory environments, an isolated housing is obligatory. Galvanic isolation from the mains phase using a fixed or variable transformer is always recommended.

Figure 2 shows the symbols on how to recognize these devices.



3 Specifications

Table 1. TEA1936xDB1556 specifications

When operating at 230 V (AC)

Symbol	Parameter	Value
V _{mains}	AC mains voltage	90 V (AC) up to 264 V (AC)
P _{out(max)}	maximum output power	27 W
f _{mains}	mains frequency	50 Hz and 60 Hz
P _{out} / P _{in}	efficiency	> 91 % at P _{out(max)}
V _{out}	output voltage ^[1]	3 V, 5 V, and 12 V (DC)
I _{out(max)}	maximum output current	3 A
V _{ripple(burst)}	output voltage ripple at burst mode	100 mV _{pp} at cable end
V _{ripple(full)}	output voltage ripple at continuous switching	80 mV _{pp} at cable end
EMI _C	conductive EMI	-3 dB
CMN	common-mode noise	< 2 V _{pp}
ESD	electrostatic discharge	± 15 kV through air
		± 8 kV via contact


TEA1936xDB1556 27 W compact power supply demo board

4 Board photographs



TEA1936xDB1556 27 W compact power supply demo board






UM11170 User manual COMPANY PUBLIC © NXP B.V. 2019. All rights reserved.

5 Board connections

The TEA1936xDB1556 demo board is a universal mains supplied application. Its output is the 2-pin header. The default setting for V_{out} is 3 V (DC).



6 Performance

6.1 Efficiency

Table 2. Efficiency at 3 V output (PCB end)

Load	Efficiency at 115 V (AC) (%)	Efficiency at 230 V (AC) (%)
10 % (0.3 A)	88.1	83.4
25 % (0.75 A)	88.9	85.3
50 % (1.5 A)	89.4	86.7
75 % (2.25 A)	89.8	87.2
100 % (3 A)	89.6	88.6
4-point average	89.4	86.9


Table 3. Efficiency at 5 V output (PCB end)

Load	Efficiency at 115 V (AC) (%)	Efficiency at 230 V (AC) (%)
10 % (0.3 A)	89.7	86.5
25 % (0.75 A)	90.4	87.9
50 % (1.5 A)	91.0	89.0
75 % (2.25 A)	91.1	89.6
100 % (3 A)	90.7	90.7
4-point average	90.8	89.3

Table 4. Efficiency at 12 V output (PCB end)

Load	Efficiency at 115 V (AC) (%)	Efficiency at 230 V (AC) (%)
10 % (0.3 A)	87.8	85.5
25 % (0.75 A)	90.4	88.7
50 % (1.5 A)	91.5	90.5
75 % (2.25 A)	91.8	91.6
100 % (3 A)	91.6	92.2
4-point average	91.3	90.7

TEA1936xDB1556 27 W compact power supply demo board



6.2 Electromagnetic interference (EMI)


TEA1936xDB1556 27 W compact power supply demo board

Tracel:	EN55022Q		
Trace2:	EN55022A		
Trace3:			
TRACE	FREQUENCY	LEVEL dBµV	DELTA LIMIT di
l Quasi Peak	706 kHz	52.62 N	-3.37
2 Average	354 kHz	45.27 L1	-3.59
2 Average	710 kHz	41.86 L1	-4.13
l Quasi Peak	954 kHz	51.52 L1	-4.47
l Quasi Peak	358 kHz	52.93 N	-5.83
1 Quasi Peak	474 kHz	49.63 N	-6.80
2 Average	474 kHz	39.01 L1	-7.42
2 Average	950 kHz	38.29 L1	-7.71
1 Quasi Peak	150 kHz	57.58 Ll	-8.41
2 Average	1.066 MHz	36.22 L1	-9.77
2 Average	1.538 MHz	35.96 L1	-10.03
2 Average	238 kHz	41.24 L1	-10.92
1 Quasi Peak	214 kHz	51.77 L1	-11.27
l Quasi Peak	262 kHz	49.80 N	-11.56
l Quasi Peak	2.142 MHz	43.89 L1	-12.10
1 Quasi Peak	962 kHz	39.28 N	-16.71
1 Quasi Peak	1.674 MHz	38.89 N	-17.11
1 Quasi Peak	1.558 MHz	38.23 L1	-17.76
			aaa-0325

UM11170

7 Schematic

The schematic of the TEA1936xDB1556 comprises the quasi-resonant controller TEA19361 and the synchronous rectifier controller TEA1999.



8 Bill of materials (BOM)

Reference	Description and values	Part number	Manufacturer
C1	capacitor; 15 μF; 20 %; 400 V; ALU; THT	EKM156M2G F16RR	Samxon
C3	capacitor; 10 μF; 20 %; 100 V; ALU; THT	100YXJ10M 5X11	Rubycon
C4	capacitor; 820 μF; 20 %; 16 V; ALU; THT	827AVG016 MFBJ	Illinois Capacitor Inc
C5	capacitor; 100 nF; 10 %; 50 V; X7R; 0402	C1005X7R1 H104K050BB	ТDК
C6; C41	capacitor; 4.7 µF; 10 %; 16 V; X5R; 0603	C1608X5R1 C475K080A C	ТDК
C10	capacitor; 1 μF; 10 %; 16 V; X7R; 0603	-	-
C12	capacitor; 680 pF; 10 %; 630 V; X7R; 1206	C1206C681K BRAC	KEMET
C14; C17	capacitor; 1 nF; 10 %; 50 V; X7R; 0603	-	-
C15	capacitor; 470 nF; 10 %; 50 V; X7R; 0603	C1608X7R1 H474K	ТDК
C19	capacitor; 22 pF; 5 %; 50 V; C0G; 0603	-	-
C20	capacitor; 470 pF; 10 %; 100 V; X7R; 0603	-	-
C22	capacitor; 6.8 nF; 10 %; 630 V; X7R; 0805; NM	C0805C682K BRACTU	KEMET
C29; C33	capacitor; 15 μF; 20 %; 400 V; ALU; THT	EKM156M2G F16RR	Samxon
C30	capacitor; 820 μF; 20 %; 16 V; ALU; THT	827AVG016 MFBJ	Illinois Capacitor Inc
C36	capacitor; 10 μF; 20 %; 35 V; ALU; THT	UVR1V100M DD6TP	Nichicon Corp
C38	capacitor; 10 nF; 10 %; 50 V; X7R; 0402	-	-
C39	capacitor; 6.8 pF; 5 %; 50°V; C0G; 0603; NM	-	-
CY1	capacitor; 100 pF; 10 %; 250 V (AC); B; THT; X1/Y2	DE2B3KY10 1KA2BM01F	Murata
D1	TVS; unidirectional; 16 V; maximum 15.4 A at 26.0 V	PTVS16VS1 UR	NeXPeria USA Inc
D3	diode; 1 kV; 2 A	S2M	Fairchild
D4	diode; 300 V; 250 mA	BAS521	NeXPeria USA Inc
D5	diode; 100 V; 250 mA	BAS316	NXP Semiconductors
D15	diode; 200 V; 250 mA	BAS321	NeXPeria USA Inc
D16; D18	diode; not mounted; 1 kV; 1 A	S1ML	Taiwan Semiconductor
D21; D22; D23; D24	diode; 1 kV; 2 A	SA2M-E3-61 T	Vishay

NXP Semiconductors

UM11170


TEA1936xDB1556 27 W compact power supply demo board

Reference	Description and values	Part number	Manufacturer
D26	diode; 300 V; 250 mA	BAS521	NeXPeria USA Inc
F1	fuse; slow blow; 250 V (AC); 2 A	MCPMP2A2 50V	Multicomp
FB2	fbead; 0.009 Ω; 6 A; 0805	BLM21PG22 0SH1	Murata
J3	header; terminal block; 1 × 2-way; 5.08 mm	1508060000	Weidmüller
L1	inductor; CM; EE7.0; Cu = 0.27 mm; 18T:18T	inductor; common mode	NXP Semiconductors
L3	inductor; 120 μH; 850 mA	TEA19363DB ⁻ (L3) / 744772121	靴 を Semiconductors/Würth Elektronik
Q1	MOSFET-N; 700 V; 6 A	TSM70N750 CP	Taiwan Semiconductor
Q2	MOSFET-N; 60 V; 100 A	BSC028N06 NS	Infineon
R5	resistor; 10 Ω; 1 %; 63 mW; 0603	-	-
R7	resistor; 442 kΩ; 1 %; 660 mW; 500 V; 1206	ERJP08F44 23V	Panasonic
R8	resistor; 5.1 kΩ; 1 %; 63 mW; 0402	-	-
R9; R21	resistor; 1 kΩ; 1 %; 63 mW; 0402	-	-
R13	resistor; 10 Ω; 1 %; 250 mW; 1206	-	-
R15	resistor; 2.2 kΩ; 1 %; 63 mW; 0603	-	-
R16	resistor; 100 Ω; 1 %; 100 mW; 0603	-	-
R17	resistor; 4.7 Ω; 1 %; 100 mW; 0603	-	-
R18	resistor; 0.62 Ω; 1 %; 250 mW; 0805	ERJS6QFR6 2V	Panasonic
R19	resistor; 0.56 Ω; 1 %; 250 mW; 0805	ERJS6QFR5 6V	Panasonic
R22	resistor; 5.1 kΩ; 1 %; 63 mW; 0603	-	-
R24; R56; R64	resistor; 84.5 kΩ; 1 %; 660 mW; 500 V; 1206	ERJP08F84 52V	Panasonic
R25	resistor; 110 kΩ; 1 %; 63 mW; 0603	-	-
R29	resistor; not mounted; 1 k Ω ; 1 %; 63 mW; 0603	-	-
R50	resistor; 430 Ω; 1 %; 100 mW; 0402	ERJ2RKF43 00X	Panasonic
R53	resistor; 162 kΩ; 1 %; 63 mW; 0402	-	-
R54; R65	resistor; 43 kΩ; 1 %; 63 mW; 0402	-	-
R55	resistor; 150 Ω; 1 %; 100 mW; 0402	ERJ2RKF15 00X	Panasonic
R66	resistor; 8.66 kΩ; 1 %; 63 mW; 0402	-	-
R67; R68	resistor; jumper; not mounted; 0 $\Omega;$ 63 mW; 0603	-	-

Reference	Description and values	Part number	Manufacturer
R69	resistor; jumper; 0 Ω; 63 mW; 0603	-	-
RT1	ICL; 5 Ω; 25 %; 1 A; 6 mm	SL05 5R001- A	Ametherm
RT2	resistor; NTC; 100 kΩ; 5 %; 100 mW; 4190 K	NTCLE100E 3104JB0	Vishay
T1	transformer; RM7; 780 μH	TR1077	NXP Semiconductors
U2	Synchronous Rectifier Controller; TEA1999	TEA1999	NXP Semiconductors
U10	SMPS Controller; TEA19361	TEA19361	NXP Semiconductors
U11	adjustable voltage regulator; 1 %; 100 mA	NCP431ACS NT1G	ON Semiconductors
U3	optocoupler; NPN; 70 V; 50 mA	TCLT1008	Vishay

TEA1936xDB1556 27 W compact power supply demo board

9 Board layout



TEA1936xDB1556 27 W compact power supply demo board

10 Abbreviations

Table 6. Abbreviations			
Acronym	Description		
CMN	common-mode noise		
EMI	electromagnetic interference		
ESD	electrostatic discharge		
QR	quasi-resonant		
SMPS	switched-mode power supply		
SR	synchronous rectifier/rectification		

TEA1936xDB1556 27 W compact power supply demo board

11 Legal information

11.1 Definitions

Draft — The document is a draft version only. The content is still under internal review and subject to formal approval, which may result in modifications or additions. NXP Semiconductors does not give any representations or warranties as to the accuracy or completeness of information included herein and shall have no liability for the consequences of use of such information.

11.2 Disclaimers

Limited warranty and liability - Information in this document is believed to be accurate and reliable. However, NXP Semiconductors does not give any representations or warranties, expressed or implied, as to the accuracy or completeness of such information and shall have no liability for the consequences of use of such information. NXP Semiconductors takes no responsibility for the content in this document if provided by an information source outside of NXP Semiconductors. In no event shall NXP Semiconductors be liable for any indirect, incidental, punitive, special or consequential damages (including - without limitation - lost profits, lost savings, business interruption, costs related to the removal or replacement of any products or rework charges) whether or not such damages are based on tort (including negligence), warranty, breach of contract or any other legal theory. Notwithstanding any damages that customer might incur for any reason whatsoever, NXP Semiconductors' aggregate and cumulative liability towards customer for the products described herein shall be limited in accordance with the Terms and conditions of commercial sale of NXP Semiconductors.

Right to make changes — NXP Semiconductors reserves the right to make changes to information published in this document, including without limitation specifications and product descriptions, at any time and without notice. This document supersedes and replaces all information supplied prior to the publication hereof.

Suitability for use — NXP Semiconductors products are not designed, authorized or warranted to be suitable for use in life support, life-critical or safety-critical systems or equipment, nor in applications where failure or malfunction of an NXP Semiconductors product can reasonably be expected to result in personal injury, death or severe property or environmental damage. NXP Semiconductors and its suppliers accept no liability for inclusion and/or use of NXP Semiconductors products in such equipment or applications and therefore such inclusion and/or use is at the customer's own risk.

Applications — Applications that are described herein for any of these products are for illustrative purposes only. NXP Semiconductors makes no representation or warranty that such applications will be suitable for the specified use without further testing or modification. Customers are responsible for the design and operation of their applications and products using NXP Semiconductors products, and NXP Semiconductors accepts no liability for any assistance with applications or customer product design. It is customer's sole responsibility to determine whether the NXP Semiconductors product is suitable and fit for the customer's applications and products planned, as well as for the planned application and use of customer's third party customer(s). Customers should provide appropriate design and operating safeguards to minimize the risks associated with their applications and products. NXP Semiconductors does not accept any liability related to any default, damage, costs or problem which is based on any weakness or default in the customer's applications or products, or the application or use by customer's third party customer(s). Customer is responsible for doing all necessary testing for the customer's applications and products using NXP Semiconductors products in order to avoid a default of the applications and the products or of the application or use by customer's third party customer(s). NXP does not accept any liability in this respect.

Limiting values — Stress above one or more limiting values (as defined in the Absolute Maximum Ratings System of IEC 60134) will cause permanent damage to the device. Limiting values are stress ratings only and (proper) operation of the device at these or any other conditions above those given in the Recommended operating conditions section (if present) or the Characteristics sections of this document is not warranted. Constant or repeated exposure to limiting values will permanently and irreversibly affect the quality and reliability of the device.

Terms and conditions of commercial sale — NXP Semiconductors products are sold subject to the general terms and conditions of commercial sale, as published at http://www.nxp.com/profile/terms, unless otherwise agreed in a valid written individual agreement. In case an individual agreement is concluded only the terms and conditions of the respective agreement shall apply. NXP Semiconductors hereby expressly objects to applying the customer's general terms and conditions with regard to the purchase of NXP Semiconductors products by customer.

No offer to sell or license — Nothing in this document may be interpreted or construed as an offer to sell products that is open for acceptance or the grant, conveyance or implication of any license under any copyrights, patents or other industrial or intellectual property rights.

Quick reference data — The Quick reference data is an extract of the product data given in the Limiting values and Characteristics sections of this document, and as such is not complete, exhaustive or legally binding.

Export control — This document as well as the item(s) described herein may be subject to export control regulations. Export might require a prior authorization from competent authorities.

Non-automotive qualified products - Unless this data sheet expressly states that this specific NXP Semiconductors product is automotive qualified, the product is not suitable for automotive use. It is neither qualified nor tested in accordance with automotive testing or application requirements. NXP Semiconductors accepts no liability for inclusion and/or use of nonautomotive qualified products in automotive equipment or applications. In the event that customer uses the product for design-in and use in automotive applications to automotive specifications and standards, customer (a) shall use the product without NXP Semiconductors' warranty of the product for such automotive applications, use and specifications, and (b) whenever customer uses the product for automotive applications beyond NXP Semiconductors' specifications such use shall be solely at customer's own risk, and (c) customer fully indemnifies NXP Semiconductors for any liability, damages or failed product claims resulting from customer design and use of the product for automotive applications beyond NXP Semiconductors' standard warranty and NXP Semiconductors' product specifications.

Translations — A non-English (translated) version of a document is for reference only. The English version shall prevail in case of any discrepancy between the translated and English versions.

Security — While NXP Semiconductors has implemented advanced security features, all products may be subject to unidentified vulnerabilities. Customers are responsible for the design and operation of their applications and products to reduce the effect of these vulnerabilities on customer's applications and products, and NXP Semiconductors accepts no liability for any vulnerability that is discovered. Customers should implement appropriate design and operating safeguards to minimize the risks associated with their applications and products.

11.3 Trademarks

Notice: All referenced brands, product names, service names and trademarks are the property of their respective owners.

GreenChip — is a trademark of NXP B.V.

NXP Semiconductors

UM11170

TEA1936xDB1556 27 W compact power supply demo board

Contents

1	Introduction	3
1.1	Key features	4
1.2	Applications	4
2	Safety warning	4
3	Specifications	5
4	Board photographs	6
5	Board connections	
6	Performance	9
6.1	Efficiency	9
6.2	Electromagnetic interference (EMI)	
7	Schematic	
8	Bill of materials (BOM)	
9	Board layout	
10	Abbreviations	
11	Legal information	

Please be aware that important notices concerning this document and the product(s) described herein, have been included in section 'Legal information'.

© NXP B.V. 2019.

All rights reserved.

For more information, please visit: http://www.nxp.com For sales office addresses, please send an email to: salesaddresses@nxp.com

Date of release: 7 January 2019 Document identifier: UM11170