



V	DE Test Report			
Report No.				
VDE File No.	5016540-4970-0008/294957			
Date of issue	2022-10-18			
Laboratory	VDE Testing and Certification Institute	е		
Address	Merianstrasse 28 63069 Offenbach/Main; Germany			
Testing location/ address	VDE Testing and Certification Institute Merianstrasse 28 63069 Offenbach/Main; Germany	е		
Applicant's name	NXP Semiconductors Czech Republic	s.r.o.		
Applicant's address	1. Maje 1009; 756 61 Roznov pod Ra	dhoste	m; Cze	ch Republic
Applied standard(s)	DIN EN 60730-1 (VDE 0631-1):2021- DIN EN 60335-1 (VDE 0700-1):2020- EN 60730-1:2016+A1:2019 EN 60335-1:2012+AC+A11+A13+A1- EN 60335-1:2012/A15:2021 IEC 60730-1:2013/AMD1:2015 IEC 60730-1:2013/AMD2:2020 IEC 60335-1:2010 IEC 60335-1:2010/AMD1:2013 IEC 60335-1:2010/AMD2:2016	-08;	14:2019	)
Test item description	Peripherals/Common for Micro contro CM0+/CM33/CM4/CM7 core	ollers wi	ith	
Trade Mark	NP			
Type reference(s)	File Name			Revision
	iec60730b_clock.c			4.2
	iec60730b_invariable_memory.c			4.2
	iec60730b_dio.c			4.2
	iec60730b_dio_ext.c			4.3
	iec60730b_aio.c			4.3
	lec60730b_tsi.c			4.2
	IEC60730B_M0_COM_IAR_v4_3.a*			4.3
	IEC60730B_M0_COM_KEIL_v4_3.lib	)*		4.3
	IEC60730B_M4_M7_COM_IAR_v4_3	3.a*		4.3
	IEC60730B_M4_M7_COM_KEIL_v4_	3.lib*		4.3
	IEC60730B_M33_COM_IAR_v4_3.a*	k		4.3
Report No : 294957-TI 2-1	D	age	1	of 28

 Report No.:
 294957-TL2-1
 Page
 1
 of
 28

#### Disclaimer:

This test report contains the result of a singular investigation carried out on the product submitted. A sample of this product was tested to found the accordance with the thereafter listed standards or clauses of standards resp.

The test report does not entitle for the use of a VDE Certification Mark and considers solely the requirements of the specifications mentioned below.

Whenever reference is made to this test report towards third party, this test report shall be made available on the very spot in full length.





	1				4 0 111 4	4.0
	_		30B_M33_COM_			4.3
	_		30B_M33_NDSP			4.3
			30B_M33_NDSP			4.3
	libl	EC60	0730B_M0_COM	_MCUX	_v4_3.a*	4.3
	libl	EC60	D730B_M4_M7_C	OM_MO	CUX_v4_3.a*	4.3
	libl	EC60	4.3			
	libl	EC60	0730B_M33_NDS	SP_COM	1_MCUX_v4_3.a*	4.3
Remark:	-R	evisio	ne files marked with * are object code files. evision number of .c source files is stated in the h the files.			
Test sample condition		$\boxtimes$	Non-damaged s	ample		
			nark:	*/*		
Sample entry date			2-10-17			
Date (s) of performance of tests			2-10-17 2-10-17 to 2022-1	10 <b>-</b> 18		
Date (3) of performance of tests		202	2 10 17 10 2022	10 10		
Tested by  Name, Signature  Function  Verified by  Name, Signature	:	(Auth	childbach norization of test report ting engineer	rt)	Jadin de	
Name, Signature  Function  Verified by	:	(Auth	norization of test reporting engineer		Tas	
Name, Signature  Function  Verified by  Name, Signature	:	(Auth	ting engineer		Tas	
Name, Signature  Function  Verified by  Name, Signature	:	(Auth Tesi K. T Teci NXF 1. M	ting engineer  as  hnical Certificatio	n Office	Tas	
Name, Signature  Function  Verified by  Name, Signature  Function	:	(Auth Tesi K. T Teci NXF 1. M	ting engineer  as  hnical Certificatio  Semiconductors laje 1009; 756 61	n Office	r ; Republic s.r.o.	
Name, Signature  Function  Verified by  Name, Signature  Function	:	(Auth Tesi K. T Teci NXF 1. M	ting engineer  as  hnical Certificatio  Semiconductors laje 1009; 756 61	n Office	r ; Republic s.r.o.	
Name, Signature  Function  Verified by  Name, Signature  Function  Factory(ies)	:	(Auth Tesi K. T Teci NXF 1. M	ting engineer  as  hnical Certificatio  Semiconductors laje 1009; 756 61	n Office	r ; Republic s.r.o.	
Name, Signature  Function  Verified by  Name, Signature  Function  Factory(ies)  Possible test case verdicts:	ect :	(Auth Tes: K. T Tec: NXF 1. M CZE	ting engineer  as  hnical Certificatio  Semiconductors laje 1009; 756 61	n Office	r ; Republic s.r.o.	

Report No.:	294957-TL2-1	Page	2	of	28
-------------	--------------	------	---	----	----





Final Verdict:	$\boxtimes$	Р	F
Remark :::	*/*		

Environmental conditions (if applicable)	Ambient temperature	Atmospheric pressure	Relative humidity
Rated values:	15-35 °C	860-1060 hPa	30-60 %
Verified values:	N/A	Range confirmed by: Deutscher Wetterdienst (Meteorological service)	N/A

#### **General Remarks:**

#### **Conformity statement:**

The VDE decision rule for the statement of conformity is in accordance with IEC Guide 115:2021 procedure 2

#### **General Remarks:**

All self-diagnostic routines are executable after reset and during runtime.

The files referenced under this test report are also suitable for device families with CM0+/CM33/CM4/CM7 core referenced under VDE folders:

- 5016540-4970-0002 for features for devices with ARM CM4 or CM7 core with its actual test report.
- 5016540-4970-0004 for features for devices with ARM CM0+ core with its actual test report.
- 5016540-4970-0005 for features for devices with ARM CM33 core with its actual test report.

#### **Special Details:**

The files referenced under this test report support the following cores in reference to the devices as shown by the table below:

CPU Core	List of Device Families
CM0	K32L2Ax, K32L2Bx, LPC51U68x, LPC80x, LPC82x, LPC84x, LPC86x, MKV1x, MKExx, MKLxx, MKE1xZ, MK32W0x, MKW3x, K32L3Ax,
CM33	LPC55xx, LPC55Sxx, MIMXRT118x,
CM4, CM7	MK2xFxx, MIMXRT117x, MIMX8MNxx, MIMX8MMxx, MIMXRT10xx, MKV3x, MKV4x, MKV5x, MKE1xF, LPC540x, LPC54S0x, MIMXRT116x, K32L3Ax

The file "iec60730b\_aio.c" cannot be used for the devices MIMX8MNxx, MIMX8MMxx.

The file "iec60730b dio.c" cannot be used for the device MIMXRT118x.

The file "iec60730b tsi.c" can be used for the device MKE1xZ only.

The file "iec60730b\_invariable\_memory.c" can be used only for devices with HW CRC module.

Report No.:	294957-TL2-1	Page	3	of	28
-------------	--------------	------	---	----	----





#### Naming conventions for object code files:

- Standard IEC60730 (In case of IAR and KEIL) or libIEC60730 (In case of MCUXpresso)
- Library class compliance according to the IEC60730 standard B
- The MCU core for which, the library was compiled M0, or M4\_M7 or M33
- Library for common peripheral tests COM
- The type of compiler/IDE IAR or KEIL or MCUX
- Identification of the library version v4.3
- File extension differs between IDEs that were used for compilation \*.a (in case of IAR and MCUXpresso) or \*.lib (in case of KEIL)

IEC60730B\_M0\_COM\_IAR\_v4\_3.a

#### Additional rule for CM33 cores without DSP support:

For devices without DSP/FPU is necessary use library with \*\_NDSP\_\* name:

The object code files revision 4.3 can be verified by its SHA-256 Hash-Tag shown by an example on next page as follows:

Report No.: 294957-TL2-1 Page 4 of 28





File Name:	SHA-256 Hash-Tag:
IEC60730B_M0_COM_IAR_v4_3.a	3FAD662CAC926D6FE9C57EF09E68BEEF16B89F302670C38D27843D35AC8B80FA
IEC60730B_M0_COM_KEIL_v4_3.lib	E9BD4EE40BDD2A045B489A4B7A644575197A76D6A287C6CD07CF9370E4A9C56C
libIEC60730B_M0_COM_MCUX_v4_3.a	55D5134FB6500B8E40F10057DD25B1C8148DC659EED58AFB975CF6DA99F49283
IEC60730B_M4_M7_COM_IAR_v4_3.a	BC0FDC45A1369BD0AF0845C9CDA654B2A3F76CEBDA745FC31F94DC10E0D43F5A
IEC60730B_M4_M7_COM_KEIL_v4_3.lib	CD5373AB67A6BCCDC6B6AB24DE0877E726A740FF7E9C93FCA9EB56CEA4279E31
libIEC60730B_M4_M7_COM_MCUX_v4_3.a	D6944371FD9F0949967BF43AFC3EA5B9A5F09FC5C332FF8163799AE89E636986
IEC60730B_M33_COM_IAR_v4_3.a	9C6FD634E2BB8EDAD273CA49A60BCDD0C3F37A2619B15C49F7E8E1ADC5BE28C9
IEC60730B_M33_COM_KEIL_v4_3.lib	D562F7C27887BBF523D4F1C9FEE4A9C10A411DF59F132CB278F4C49C030E15D7
libIEC60730B_M33_COM_MCUX_v4_3.a	9079499F9E078874AA2727518D87986EE92D50247180C3BC8E6C8FC14EFB8DF8
IEC60730B_M33_NDSP_COM_IAR_v4_3.a	1D3E2A50748A3AFB7BC9AB2E04202E9BFF55BB27166C303F3DD01693A442C7B9
IEC60730B_M33_NDSP_COM_KEIL_v4_3.lib	04FBBA80170788E0C0737B6716F1D6AC3B950967915553FF8649D0208168547C
libIEC60730B_M33_NDSP_COM_MCUX_v4_3.a	EFE5D63B65A9095D11C811384568E953F74C6CC866DFA0BF60A8DCEDB250DE48





1. Download from internet a utility like "MDS\_and\_SHA\_Checksum\_Utility.exe" via the following link: <a href="https://download.cnet.com/MD5-SHA-Checksum-Utility/3000-2092\_4-10911445.html">https://download.cnet.com/MD5-SHA-Checksum-Utility/3000-2092\_4-10911445.html</a>. (Another example is the link <a href="https://www.nirsoft.net/utils/hash\_my\_files.html">https://www.nirsoft.net/utils/hash\_my\_files.html</a>. Click to "Download HashMyFiles".)

2. Start the utility.



Delete the hooks for "MDS", "SHA-1" and SHA-512 (see red arrows).

Report No.: 294957-TL2-1 Page 6 of 28





3. In the windows file explorer mark the downloaded object code file and move it the line "File" (see red arrow).



The "SHA-256" Hash-Tag for this file will be generated directly (see green arrow).

4. Copy the corresponding Hash-Tag from this test report and insert it to the line "Hash" (see red arrow).



Report No.: 294957-TL2-1 Page 7 of 28





5. Now press the button "Verify". If both Hash-Tags are identically the window below will pop up.



Report No.: 294957-TL2-1 Page 8 of 28





#### **Performed Tests**

01	IEC 60335-1 (An		1		ManaPa
Clause	Requirement + Test	Result – Rema	Ark		Verdic
R	ANNEX R (NORMATIVE) (60335-1) SOFTWARE EVALUATION				
	Programmable electronic circuits requiring software incorporating measures to control the fault/error conditions specified in table R.1 or R.2 validated in accordance with the requirements of this annex	Self-test routin class R.1	es for soft	ware of	P
R.1	Programmable electronic circuits using softwa	are			_
	Programmable electronic circuits requiring software incorporating measures to control the fault/error conditions specified in table R.1 or R.2 constructed so that the software does not impair compliance with the requirements of this standard				P
R.2	Requirements for the architecture				_
	Programmable electronic circuits requiring software incorporating measures to control the fault/error conditions specified in table R.1 or R.2 use measures to control and avoid software-related faults/errors in safety-related data and safety-related segments of the software				P
R.2.1.1	Programmable electronic circuits requiring so control the fault/error conditions specified in ta structures:				_
	- single channel with periodic self-test and monitoring				N/A
	- dual channel (homogenous) with comparison				N/A
	- dual channel (diverse) with comparison				N/A
	Programmable electronic circuits requiring so control the fault/error conditions specified in tastructures:				_
	- single channel with functional test				Р
	- single channel with periodic self-test				Р
	- dual channel without comparison				N/A
R.2.2	Measures to control faults/errors				_
R.2.2.1	When redundant memory with comparison				N/A
Report No.:	294957-TL2-1		Page	9 0	f 28

#### Disclaimer:

This test report contains the result of a singular investigation carried out on the product submitted. A sample of this product was tested to found the accordance with the thereafter listed standards or clauses of standards resp.

The test report does not entitle for the use of a VDE Certification Mark and considers solely the requirements of the specifications mentioned below. Whenever reference is made to this test report towards third party, this test report shall be made available on the very spot in full length.





	is provided on two gross of the same		
	is provided on two areas of the same component, the data in one area is stored in a different format from that in the other area		
R.2.2.2	Programmable electronic circuits with functions requiring software incorporating measures to control the fault/error conditions specified in table R.2 and that use dual channel structures with comparison, have additional fault/error detection means for any fault/errors not detected by the comparison		N/A
R.2.2.3	For programmable electronic circuits with functions requiring software incorporating measures to control the fault/error conditions specified in table R.1 or R.2, means are provided for the recognition and control of errors in transmissions to external safety-related data paths		N/A
R.2.2.4	For programmable electronic circuits with functions requiring software incorporating measures to control the fault/error conditions specified in table R.1 or R.2, the programmable electronic circuits incorporate measures to address the fault/errors in safety-related segments and data indicated in table R.1 and R.2 as appropriate		Р
R.2.2.5	For programmable electronic circuits with functions requiring software incorporating measures to control the fault/error conditions specified in table R.1 or R.2, detection of a fault/error occur before compliance with clause 19 is impaired	Self-test routines only; compliance to clause 19 has to be insured by the user of the self-test routines	N/A
R.2.2.6	The software is referenced to relevant parts of the operating sequence and the associated hardware functions		Р
R.2.2.7	Labels used for memory locations are unique		Р
R.2.2.8	The software is protected from user alteration of safety-related segments and data		Р
R.2.2.9	Software and safety-related hardware under its control is initialized and terminates before compliance with clause 19 is impaired	Self-test routines only; compliance to clause 19 has to be insured by the user of the self-test routines	N/A
R.3	Measures to avoid errors	•	_
R.3.1	General		_

Report No.: 294957-TL2-1	Page	10	of	28
--------------------------	------	----	----	----





	For programmable electronic circuits with functions requiring software incorporating measures to control the fault/error conditions specified in table R.1 or R.2, the following measures to avoid systematic fault in the software are applied				
	or R.2, the following measures to avoid system  Software that incorporates measures used to control the fault/error conditions specified in table R.2 is inherently acceptable for software required to control the fault/error conditions specified in table R.1	Class R.1 only	N/A		
R.3.2	Specification		_		
R.3.2.1	Software safety requirements:	Software Id: 4.2, 4.3	Р		
	The specification of the software safety requirements includes the descriptions listed		Р		
R.3.2.2	Software architecture		_		
R.3.2.2.1	The specification of the software architecture includes the aspects listed  - techniques and measures to control software faults/errors (refer to R.2.2);  - interactions between hardware and software;  - partitioning into modules and their allocation to the specified safety functions;  - hierarchy and call structure of the modules (control flow);  - interrupt handling;  - data flow and restrictions on data access;  - architecture and storage of data;  - time-based dependencies of sequences and data	IEC60730B_Library_User_ Guide_CM0_v4_3.pdf Revision 0  IEC60730B_Library_User_ Guide_CM4_CM7_v4_3.pdf Revision 0  IEC60730B_Library_User_ Guide_CM33_v4_3.pdf Revision 0	Р		
R.3.2.2.2	The architecture specification is validated against the specification of the software safety requirements by static analysis		Р		
R.3.2.3	Module design and coding		_		
R.3.2.3.1	Based on the architecture design, software is suitably refined into modules		Р		
	Software module design and coding is implemented in a way that is traceable to the software architecture and requirements		Р		
R.3.2.3.2	Software code is structured		Р		
R.3.2.3.3	Coded software is validated against the module specification by static analysis		Р		
	The module specification is validated against the architecture specification by static analysis	Reviews and source code walk through	Р		
R.3.3.3	Software validation		_		
	The software is validated with reference to the requirements of the software safety		Р		





requi	rements specification	
Com	pliance is checked by simulation of:	_
- inpu	ut signals present during normal ation	Р
- anti	cipated occurrences	Р
- und	lesired conditions requiring system n	Р





	IEC 60730-1 (So	ftware)	
Clause	Requirement + Test	Result - Remark	Verdict
H.6	Classification, additions		_
H.6.18	Class of control function (A, B,C)		
H.7	Information in addition to Table 1 provided:		_
	66 - Software sequence documentation; clause: H.11.12.2.9; method: X	Self-diagnostiv modules acc. Table R.1/H.1 only	N/A
	67 - Program documentation; clause: H.11.12.2.9, H.11.12.2.12; method: X		Р
	68 - Software fault analysis; clause: H.11.12, H.27.1.1.4; method: X		Р
	69 - Software class(es) and structure; clause: H.11.12.2, H.11.12.3, H.27.1.2.2.1, H.27.1.2.3.1; method: D		Р
	70 - Analytical measures and fault/error control techniques employed; clause: H.11.12.1.2, H.11.12.2.2, H.11.12.2.4; method: X		Р
	71 - Software fault/error detection time(s) for controls with software Classes B or C; clause: H.2.17.10, H.11.12.2.6; method: X		Р
	72 - Control response(s) in case of detected fault/error; clause: H.11.12.2.7; method: X		Р
	93 – Maximum number of reset actions within a time period; clause H.11.12.4.3.6, H.11.12.4.3.4; method: D		N/A
	94 – Number of remote reset actions; clause H.17.1.4.3; method: X		N/A
	m – Controls with software classes B or C had information provided for safety-related segments of the software. Information on the non-safety related segments was sufficient to establish that they did not influence safety-related segments		N/A
	n – Software sequence was documented and, together with the operating sequence, included a description of the control system philosophy, the control flow, data flow and the timings		N/A

Report No.:   294957-1L2-1   Page   13   of	Report No.:	294957-TL2-1	Page	13	of	28
---	-------------	--------------	------	----	----	----





	o - Safety-related data and safety-related segments of the software sequence, the malfunction of which could result in non-compliance with the requirements of Clauses 17, 25, 26 and 27, are identified	P
	- Included the operating sequence	N/A
	Software fault analysis was related to the hardware fault analysis in Clause H.27	N/A
	q - Programming documentation was supplied in a programming design language declared by the manufacturer	Р
	r – Different software classes applied to different control functions	N/A
	s - Measures declared are chosen by manufacturer from the requirements of Clauses H.11.12.1.2 to H.11.12.2.4 inclusive	N/A
H.11	Constructional requirements	_
H.11.12	Controls using software	_
	Controls using software were so constructed that the software did not impair control compliance with the requirements of this standard	Р
H.11.12.1	Requirements for the architecture	_
H.11.12.1 .1	Control functions with software class B or C use measures to control and avoid software-related faults/errors in safety-related data and safety-related segments of the software, as detailed in H.11.12.1.2 to H.11.12.3 inclusive	Р
H.11.12.1	Control functions with software class C have one of the following structures:	_
	<ul><li>single channel with periodic self-test and monitoring (H.2.16.7)</li></ul>	N/A
	- dual channel (homogenous) with comparison (H.2.16.3)	N/A
	- dual channel (diverse) with comparison (H.2.16.2)	N/A
	Control functions with software class B have one of the following structures:	_
	- single channel with functional test (H.2.16.5)	Р
	- single channel with periodic self-test (H.2.16.6)	Р

Report No.:   294957-TL2-1   Page   14   of	Report No.:	294957-TL2-1	Page	14	of	28
---	-------------	--------------	------	----	----	----





	- dual channel without comparison (H.2.16.1)	N/A
H.11.12.1 .3	Other structure permitted with equivalent level of safety to those in H.11.12.1.2	N/A
H.11.12.2	Measures to control faults/errors	_
H.11.12.2 .1	Redundant memory with comparison provided on two areas of the same component: data stored in different formats	N/A
H.11.12.2 .2	Software class C using dual channel structures with comparison: additional fault/error detection means	N/A
H.11.12.2 .3	Software class B or C: means for recognition and control of errors in transmission to external safety-related data paths: Means took into account errors of data, addressing, transmission timing and sequence of protocol	N/A
H.11.12.2 .4	Software class B or C: within the control, measures are taken to address the fault/errors in safety-related segments and data indicated in Table H.1 and identified in Table 1 requirement 68.	Р
H.11.12.2 .5	Measures others than those specified in H.11.12.2.4 utilized to satisfy the requirements listed in Table H.1	N/A
H.11.12.2 .6	Software fault/error detection:	_
	<ul><li>occur not later than declared time(s), Table 1,</li><li>requirement 71</li></ul>	Р
	acceptability of declared time(s): evaluated during fault analysis of the control	Р
H.11.12.2 .7	For controls with functions, classified as Class B or C, detection of fault/error:	_
	- results in the response declared in Table 1, requirement 72	Р
	<ul> <li>for Class C: independent means capable of performing this response provided</li> </ul>	N/A
H.11.12.2 .8	Class C, dual channel structure, loss of dual channel capability: deemed to be an error	N/A
H.11.12.2 .9	Software referenced:	_





- to relevant parts of the operating sequence	Р
- to the associated hardware functions	Р
Labels used for memory locations are unique	Р
Software protected from user alteration of safety- related segments and data	Р
Software and safety-related hardware under its control is initialized to and terminates at a declared state, Table 1, requirement 66	Р
Measures to avoid errors	_
For controls with software class B or C the measures shown in Figure H.1 to avoid systematic faults are applied	Р
Other methods utilized that incorporate disciplined and structured processes including design and test phases	N/A
Specification	_
Software safety requirements	_
The specification of the software safety requirements includes:	_
A description of each safety related function to be implemented, including its response time(s):     - functions related to the application including	Р
their related software classes	
and management of software or hardware faults	
A description of interfaces between software and hardware	Р
A description of interfaces between any safety and non-safety related functions	N/A
Software architecture	_
The description of software architecture include the following aspects:	_
Techniques and measures to control software faults/errors (refer to H.11.12.2)	Р
	Labels used for memory locations are unique  Software protected from user alteration of safety-related segments and data  Software and safety-related hardware under its control is initialized to and terminates at a declared state, Table 1, requirement 66





	Interactions between hardware and software	Р
	Partitioning into modules and their allocation to the specified safety functions	Р
	Hierarchy and call structure of the modules (control flow)	Р
	Interrupt handling	Р
	Data flow and restrictions on data access	Р
	Architecture and storage of data	Р
	Time based dependencies of sequences and data	Р
H.11.12.3 .2.2.2	The architecture specification is verified against the specification of the software safety requirements by static analysis	Р
H.11.12.3 .2.3	Module design and coding	_
H.11.12.3 .2.3.1	Software is suitably refined into modules. Software module design and coding are implemented in a way that is traceable to the software architecture and requirements. The module design specified:	Р
	- function(s)	Р
	- interfaces to other modules	N/A
	- data	Р
H.11.12.3 .2.3.2	Software code is structured	Р
H.11.12.3 .2.3.3	Coded software is verified against the module specification, and the module specification is verified against the architecture specification by static analysis	Р
H.11.12.3 .2.4	Design and coding standards	Р
	Program design and coding standards is used during software design and maintenance	Р
	Coding standards :	_
	- specified programming practice	Р
	proscribed unsafe language features	Р

Report No.:   294957-1L2-1   Fage   17   01   2		Report No.:	294957-TL2-1	Page	17	of	28
---	--	-------------	--------------	------	----	----	----





	specify procedures for source code documentation	Р
	- specify data naming conventions	Р
H.11.12.3 .3	Testing	_
H.11.12.3 .3.1	Module design (software system design, software module design and coding)	_
H.11.12.3 .3.1.1	A test concept with suitable test cases is defined based on the module design specification.	Р
H.11.12.3 .3.1.2	Each software module is tested as specified within the test concept	Р
H.11.12.3 .3.1.3	Test cases, test data and test results are documented	Р
H.11.12.3 .3.1.4	Code verification of a software module by static means includes such techniques as software inspections, walk-throughs, static analysis and formal proof	Р
	Code verification of a software module by dynamic means includes functional testing, white-box testing and statistical testing	Р
H.11.12.3 .3.2	Software integration testing	_
H.11.12.3 .3.2.1	A test concept with suitable test cases is defined based on the architecture design specification	Р
H.11.12.3 .3.2.2	The software is tested as specified within the test concept	Р
H.11.12.3 .3.2.3	Test cases, test data and test results are documented	Р
H.11.12.3 .3.3	Software validation	_
H.11.12.3 .3.3.1	A validation concept with suitable test cases is defined based on the software safety requirements specification	Р
H.11.12.3 .3.3.2	The software is validated with reference to the requirements of the software safety requirements specification as specified within the validation concept	Р
	The software is exercised by simulation or stimulation of:	_

Report No.:   294957-TL2-1   Page   18   of   28
--





	input signals present during normal operation	Р					
	anticipated occurrences	Р					
	undesired conditions requiring system action	Р					
H.11.12.3 .3.3.4	Test cases, test data and test results are documented	Р					
H.11.12.3 .4	Other Items						
H.11.12.3 .4.1	Equipment used for software design, verification and maintenance was qualified appropriately and demonstrated to be suitable for purpose in manifold applications						
H.11.12.3 .4.2	Management of software versions: All versions are uniquely identified for traceability	Р					
H.11.12.3 .4.3	Software modification	_					
H.11.12.3 .4.3.1	Software modifications are based on a modification request which details the following:	N/A					
	the hazards which may be affected	N/A					
	the proposed change	N/A					
	the reasons for change	N/A					
H.11.12.3 .4.3.2	An analysis is carried out to determine the impact of the proposed modification on functional safety.	N/A					
H.11.12.3 .4.3.3	A detailed specification for the modification is generated including the necessary activities for verification and validation, such as a definition of suitable test cases	N/A					
H.11.12.3 .4.3.4	The modification is carried out as planned	N/A					
H.11.12.3 .4.3.5	The assessment of the modification is carried out based on the specified verification and validation activities.	N/A					
H.11.12.3 .4.3.6	All details of modification activities are documented	N/A					
H.11.12.3 .5	For class C control functions: One of the						

Report No.:   294957-1L2-1   Page   19   Of		Report No.:	294957-TL2-1	Page	19	of	28
---	--	-------------	--------------	------	----	----	----





H.11.12.4	Remotely actuated control functions	_
H.11.12.4 .1.1	Data Exchange – General – Remotely actuated control functions are connected to separate, independent devices, which may themselves contain control functions or provide other information and any data exchange between these devices does not compromise the integrity of class B control function or class C control function.	N/A
H.11.12.4 .1.2	Type of data - Message types for data exchange in a control function or functions are allocated to class A control function, class B control function or class C control function. The safety or protective relevance or influence, message types or data exchange are allocated only to class B control function or class C control functions, see Table H.10.	N/A
H.11.12.4 .1.3.1	Communication of Safety Related Data – Transmission – Safety relevant data is transmitted authentically concerning:	N/A
	- data corruption	N/A
	- address corruption	N/A
	- wrong timing or sequence	N/A
	Data variation or corrupted data did not lead to an unsafe state	N/A
	Before transmitted data was used it was ensured that data corruption, address corruption and wrong timing or sequence are addressed using the measures as given in Annex H.	N/A
	The following failure modes are addressed:	_
	<ul><li>permanent "auto-sending" or repetition,</li></ul>	N/A
	- interruption of data transfer	N/A
H.11.12.4 .1.3.2	Access to data exchange - All types of access to class B control function or class C control function related data exchange systems is clearly restricted	N/A
	Adequate hardware/software measures are taken to ensure no unauthorized access to the control functions (class B and C; operating data, configuration parameters and/or software modules)	N/A

Report No.:	294957-TL2-1	Page	20	of	28
кероп по	294937-1LZ-1	rage	20	OI I	Ĺ





H.11.12.4 .1.3.3	For class B and class C software revisions the requirements of H.11.12.3 and hardware configuration management are applied and the control maintains its protective functions		N/A			
H.11.12.4 .1.4						
H.11.12.4	Leantral tunetions done not load to a hazardous					
H.11.12.4 .3.1	Remote reset action is manually initiated.		N/A			
	Reset functionality initiated by a hand-held device required at least two manual actions to activate		N/A			
H.11.12.4 .3.2	Reset functions are capable of resetting the system as intended		N/A			
H.11.12.4 .3.3	Unintended resets from safe state do not occur.		N/A			
H.11.12.4 .3.4	Any fault of the reset function does not cause the control or controlled function to result in a hazardous condition, and was evaluated for its Class B classification		N/A			
H.11.12.4 .3.5	For reset functions initiated by manual action not in visible sight of the appliance, the following additional requirements apply:		N/A			
	<ul> <li>the actual status and relevant information of the process under control is visible to the user before, during and after the reset action;</li> </ul>		N/A			
	the maximum number of reset actions within a time period is declared. Following this, any further reset is denied unless the appliance is physically checked		N/A			
H.11.12.4 .3.6	The reset function is evaluated on the final application.		N/A			
	Manual switching of a thermostat or device with similar function that activates a reset is declared by the manufacturer and is suitable in the final application.		N/A			
H.27.1.2	Protection against internal faults to ensure functional	al safety	_			

Report No.:	294957-TL2-1	Page	21	of	28
report No	254557 TEZ T	i age	41	Oi	-





H.27.1.2. 1	Design and construction requirements		_			
H.27.1.2. 1.1	Fault avoidance and fault tolerance					
	Controls incorporating control functions of class B or C are designed according to H.27.1.2 taking into account the failure modes of Cl. H.11.12 for software		Р			
	Systematic errors are avoided		Р			
	Random faults are dealt with by a proper system configuration		Р			
	Functional analysis of the application resulted in a structured design with:		Р			
	<ul><li>Control flow</li></ul>		Р			
	<ul><li>Data flow</li></ul>		Р			
	Time related functions required by the application		Р			
	For custom-chips special attention was made to minimize systematic errors		N/A			
	System configuration was failsafe or:		N/A			
	Incorporated components with direct safety-critical functions guarded by safeguards that cause a completely independent safety shut-down in accordance to H.11.12 software class B or C		N/A			
	- safeguards are built into hardware and,		N/A			
	- safeguards are supplemented by software		N/A			
	Time slot monitoring is sensitive to both an upper and a lower limit of the time interval.		N/A			
	Faults resulting in a shift of the upper and/or lower limit are taken into account.		N/A			
	In a class C control function when a single fault in a primary safeguard can render the safeguard inoperative, a secondary safeguard is provided		N/A			
	The reaction time of the secondary safeguard is in accordance with Clause H.27.1.2.3.		N/A			
H.27.1.2. 1.2	Documentation		_			

Report No.:	294957-TL2-1	Page	22	of	28
Report No	294957-1L2-1	Page	22	OI	ı





	The documentation was based on H.11.12.3.2	Р
	The functional analysis of the control and the safety related programs under its control are documented in a clear hierarchical way in accordance with the safety philosophy and the program requirements.	Р
	Documentation provided for assessment included:	_
	A description of the system philosophy, the control flow, data flow and timings.	Р
	A clear description of the safety philosophy of the system with all safeguards and safety functions clearly indicated. Sufficient design information is provided to enable the safety functions or safeguards to be assessed	Ф
	Documentation for any software within the system	Р
	Programming documentation is supplied in a programming design language declared by the manufacturer	Р
	Safety related data and safety related segments of the operating sequence are identified and classified according to H.11.12.3	Р
	There is a clear relationship between the various parts of the documentation	Р
H.27.1.2. 2	Class B control function	_
H.27.1.2. 2.1	Design and construction requirements	_
	Software complies with software class B	Р
H.27.1.2. 3	Class C control function	_
H.27.1.2. 3.1	Design and construction requirements	_
	Software complies with software class C	N/A
H.27.1.2. 5	Circuit and construction evaluation	_
H.27.1.2. 5.3	Assessment	N/A

Report No.: 294957-TL2-1	Page	23	of	28
--------------------------	------	----	----	----





Only the safety related software (software class B and C) as identified according to H.27.1.2.1.2 were subjected to further assessment





Component 1)	Fault/error	Acceptable measures 2) 3) 4)	Definitions	Document reference	Document reference	Verdict
				for applied measure	for applied test	
1.CPU						_
1.1 Register	Stuck at	Functional test, or	H.2.16.5			N/A
		periodic self- test using either:	H.2.16.6			N/A
		<ul> <li>static</li> <li>memory test, or</li> </ul>	H.2.19.6			N/A
		<ul><li>word</li><li>protection with</li><li>single bit</li><li>redundancy</li></ul>	H.2.19.8.2			N/A
1.2 Void						_
1.3 Programme counter	Stuck at	Functional test, or	H.2.16.5			N/A
		periodic self- test, or	H.2.16.6			N/A
		independent time-slot monitoring, or	H.2.18.10.4			N/A
		logical monitoring of the programme sequence	H.2.18.10.2			N/A
2. Interrupt	No interrupt	Functional test; or	H.2.16.5			
handling and execution	or too frequent interrupt	time-slot monitoring	H.2.18.10.4			N/A
3. Clock	Wrong frequency (for quartz synchroniz	Frequency monitoring, or	H.2.18.10.1	IEC60730B_Library_U Guide_CM0_v4_3.pdf Revision 0	ser_	
	ed clock: harmonics/ subharmon			IEC60730B_Library_U Guide_CM4_CM7_v4_ Revision 0		N/A
	ics only)			IEC60730B_Library_U Guide_CM33_v4_3.pd Revision 0		
		time slot monitoring	H.2.18.10.4			N/A
4. Memory						_
4.1 Invariable memory	All single bit faults	Periodic modified checksum; or	H.2.19.3.1	IEC60730B_Library_U Guide_CM0_v4_3.pdf Revision 0		
				IEC60730B_Library_U Guide_CM4_CM7_v4_ Revision 0		Р
				IEC60730B_Library_U Guide_CM33_v4_3.pd Revision 0		
		multiple checksum, or	H.2.19.3.2			N/A
		word protection	H.2.19.8.2			N/A

Page

25 of 28

VDE\_Test\_Report\_e\_Rev3\_2021-01-21\_dom

Report No.: 294957-TL2-1





		with single bit redundancy		
4.2 Variable	DC fault	Periodic static memory test, or	H.2.19.6	N/A
memory		word protection with single bit redundancy	H.2.19.8.2	N/A
4.3 Addressing (relevant to variable and invariable memory)	Stuck at	Word protection with single bit parity including the address	H.2.19.18.2	N/A
5.Internal data path	Communicat	ion interface		_
5.1 Data	Stuck at	Word protection with single bit redundancy	H.2.19.8.2	N/A
5.2 Addressing	Wrong address	Word protection with single bit redundancy including the address	H.2.19.8.2	N/A
6 External communication	Communicat	ion interface not sa	fety relevant	_
6.1 Data	Hamming distance 3	Word protection with multi-bit redundancy, or CRC – single word, or	H.2.19.8.1 H.2.19.4.1	N/A
		transfer redundancy, or	H.2.18.2.2	N/A
0.01/ :1		protocol test	H.2.18.14	N/A
6.2 Void		T		_
6.3 Timing	Wrong point in time	Time-slot monitoring, or scheduled transmission	H.2.18.10.4 H.2.18.18	N/A
		Time-slot and logical monitoring, or	H.2.18.10.3	N/A
		comparison of redundant communication channels by either:		_
		<ul><li>reciprocal comparison</li></ul>	H.2.18.15	N/A
		independen t hardware comparator	H.2.18.3	N/A
	Wrong sequence	Logical monitoring, or	H.2.18.10.2	N/A
		time-slot monitoring, or	H.2.18.10.4	N/A
		scheduled transmission (same options as for wrong point in time)	H.2.18.18	N/A

 Report No.:
 294957-TL2-1
 Page
 26
 of
 28





7. Input/output					_
7.1 Digital I/O	Fault conditions specified in 19.11.2	Plausibility check	H.2.18.13	IEC60730B_Library_User_ Guide_CM0_v4_3.pdf Revision 0  IEC60730B_Library_User_ Guide_CM4_CM7_v4_3.pdf Revision 0  IEC60730B_Library_User_ Guide_CM33_v4_3.pdf Revision 0	Р
7.2 Analog I/O				TOURS OF THE PROPERTY OF THE P	
7.2.1 A/D- and D/A- converter	Fault conditions specified in 19.11.2	Plausibility check	H.2.18.13	IEC60730B_Library_User_ Guide_CM0_v4_3.pdf Revision 0  IEC60730B_Library_User_ Guide_CM4_CM7_v4_3.pdf Revision 0  IEC60730B_Library_User_ Guide_CM33_v4_3.pdf Revision 0	Р
7.2.2 Analog multiplexer	Wrong addressing	Plausibility check	H.2.18.13	IEC60730B_Library_User_ Guide_CM0_v4_3.pdf Revision 0  IEC60730B_Library_User_ Guide_CM4_CM7_v4_3.pdf Revision 0  IEC60730B_Library_User_ Guide_CM33_v4_3.pdf Revision 0	Р
8. Void					_
9 Custom chips. ASIC, GAL, Gate array	Any output outside the static and dynamic functional specificatio n	Periodic self- test	H.2.16.6		N/A

Additional measures	Details	Reference
Watch-Dog reset and Watch-Dog clock test	Functional test after power on reset for reset execution and timing	IEC60730B_Library_User_Guide_CM0_v4_3.pdf IEC60730B_Library_User_Guide_CM4_CM7_v4_3.pdf IEC60730B_Library_User_Guide_CM33_v4_3.pdf iec60730b_wdog.c / use in all devices
Remarks: files can b	e used for all devices, file av	railable as source code, not part of object code

Report No.:   294957-TL2-1   Page   27   of   2	Report No.:	294957-TL2-1	Page	27	of	28
---	-------------	--------------	------	----	----	----





Supplementary information:		
The self-diagnostic routines mention	oned below are foreseen for followin	g measures of table R.1 / H.1:
File Name	Measure	To be used in
iec60730b_clock.c	3.0 Clock	all devices
iec60730b_invariable_memory.c	4.1 Invariable memory	devices with HW CRC module
iec60730b_dio.c	7.1 Digital I/O	all devices, except MIMXRT118x
iec60730b_dio_ext.c	7.1 Digital I/O	all devices
iec60730b_aio.c	7.2.1 A/D- and D/A- converter	all devices, except MIMX8MNxx, MIMX8MMxx
iec60730b_tsi.c	7.2.1 A/D- and D/A- converter	MKE1xZ only
Remark: */*	•	

#### Photo documentation:

For photo documentation see VDE folders:

- 5016540-4970-0002 for devices with ARM CM4 or CM7 core with its actual test report.
- 5016540-4970-0004 for devices with ARM CM0+ core with its actual test report.
- 5016540-4970-0005 for devices with ARM CM33 core with its actual test report.

#### Testing and measuring equipment:

For testing and measuring equipment see VDE folders:

- 5016540-4970-0002 for devices with ARM CM4 or CM7 core with its actual test report.
- 5016540-4970-0004 for devices with ARM CM0+ core with its actual test report.
- 5016540-4970-0005 for devices with ARM CM33 core with its actual test report.

#### And:

IAR C/C++ Compiler for ARM Software9.30.1.50054IAR Assembler for ARM9.30.1.50054IAR ELF Linker for ARM9.30.1.50054J-Link Software and Documentation Packv7.70d

Internal testing tools

Hardware J-Link Base

Board name	Revision	Family mask
LPCXpresso860-MAX	REV X1	LPC86x
X-MIMXRT1180-EVK	REV X3	MIMXRT118x

### **End of Test Report**

Report No.: 294957-TL2-1	Page	28	of	28
--------------------------	------	----	----	----