

DSP56603

16-bit Digital Signal Processor User's Manual

Motorola, Incorporated Semiconductor Products Sector DSP Division 6501 William Cannon Drive West Austin, TX 78735-8598



This document (and other documents) can be viewed on the World Wide Web at http://www.motorola-dsp.com.

This manual is one of a set of three documents. You need the following manuals to have complete product information: Family Manual, User's Manual, and Technical Data.

OnCETM is a trademark of Motorola, Inc.

© MOTOROLA INC., 1996

Order this document by **DSP56603UM/AD**

Motorola reserves the right to make changes without further notice to any products herein to improve reliability, function, or design. Motorola does not assume any liability arising out of the application or use of any product or circuit described herein; neither does it convey any license under its patent rights nor the rights of others. Motorola products are not authorized for use as components in life support devices or systems intended for surgical implant into the body or intended to support or sustain life. Buyer agrees to notify Motorola of any such intended end use whereupon Motorola shall determine availability and suitability of its product or products for the use intended. Motorola and are registered trademarks of Motorola, Inc. Motorola, Inc. is an Equal Employment Opportunity / Affirmative Action Employer.



TABLE OF CONTENTS

1.1 INTRODUCTION	1-3 1-4 1-6
1.2 MANUAL ORGANIZATION	1-4 1-6
	1-6
1.3 MANUAL CONVENTIONS	
1.4 DSP56600 CORE DESCRIPTION	
1.5 DSP56600 CORE FUNCTIONAL BLOCKS	1-6
1.5.1 Data ALU	1-7
1.5.1.1 Data ALU Registers	1-7
1.5.1.2 Multiplier-Accumulator (MAC)	1-7
1.5.2 Address Generation Unit	1-8
1.5.3 Program Control Unit	1-9
1.5.4 Program Patch Logic	1-9
1.5.5 PLL and Clock Oscillator	I-10
1.5.6 Expansion Port (Port A)	I-10
1.5.7 JTAG Test Access Port and On-Chip Emulation (OnCE) Mod	dule
1-11	
1.5.8 On-Chip Memory	I-11
1.6 INTERNAL BUSES	
1.7 DSP56603 ARCHITECTURE OVERVIEW	
1.7.1 GPIO Functionality	
1.7.2 Host Interface (HI08)	
1.7.3 Synchronous Serial Interface (SSI)	
1.7.4 Triple Timer	I-15
CECTION 2 CIONAL/CONNECTION DESCRIPTION	2.4
SECTION 2 SIGNAL/CONNECTION DESCRIPTION	
2.3 GROUND	2-0
2.5 INTERRUPT AND MODE CONTROL	
2.6 EXPANSION PORT (PORT A)	
2.7 HOST INTERFACE (HI08)	



2.7.1	Host Port Usage Considerations	2-12
2.7.2	Host Port Configuration	
2.8	SYNCHRONOUS SERIAL INTERFACE 0 (SSI0)	2-18
2.9	SYNCHRONOUS SERIAL INTERFACE 1 (SSI1)	
2.10	GENERAL PURPOSE I/O, GPIO	2-24
2.11	TRIPLE TIMER	2-25
2.12	JTAG/ONCE INTERFACE	2-26
SECTIO	ON 3 MEMORY MAPS	3-1
3.1	INTRODUCTION	3-3
3.2	DSP56603 MEMORY MAP DESCRIPTION	3-3
3.2.1	On-Chip Program Memory	3-4
3.2.2	On-Chip X Data Memory	3-4
3.2.3	On-Chip Y Data Memory	
3.3	MEMORY-MAPPED I/O REGISTERS	3-5
SECTIO	N 4 CORE CONFIGURATION	4-1
4.1	INTRODUCTION	
4.2	DSP56600 CORE-SPECIFIC ATTRIBUTES	4-3
4.2.1	Program Patch Detector JUMP Targets	4-3
4.2.2	Operating Mode Register (OMR)	
4.2.2.1	Chip Operating Mode Bits—Bits 0–3	
4.2.2.2	External Bus Disable (EDB)—Bit 4	
4.2.2.3	PC Relative Logic Disable (PCD)—Bit 5	
4.2.2.4	Stop Delay (SD)—Bit 6	
4.2.2.5	XY Select for Stack Extension (XY)—Bit 8	
4.2.2.6	Extended Stack Underflow Flag (EUN)—Bit 9	
4.2.2.7	Extended Stack Overflow Flag (EOV)—Bit 10	
4.2.2.8	Extended Stack Wrap Flag (WR)—Bit 11	
4.2.2.9	Extended Stack Enable (EN)—Bit 12	
4.2.2.10	,	
4.2.2.11	\	
4.2.2.12	(, , , ,	
4.2.3	Status Register (SR)	
4.2.4	Device Identification Register (IDR)	
4.2.5	Bus Control Register (BCR)	4-8



4.3	BOOTSTRAP PROGRAM	4-9
4.4	CHIP OPERATING MODES	4-9
4.4.1	Expanded Mode (Mode 0)	. 4-10
4.4.2	Normal Mode (Modes 1–7)	
4.4.2.1	Mode 1—Reserved	
4.4.2.2	Mode 2—Bootstrap from 68338	. 4-11
4.4.2.3	Mode 3—Bootstrap from 24-Bit Memory	. 4-11
4.4.2.4	Mode 4—Bootstrap from 8-Bit Memory	. 4-11
4.4.2.5	Mode 5—Bootstrap from ISA Bus	
4.4.2.6	Mode 6—Bootstrap from 68HC11	
4.4.2.7	Mode 7—Reserved	
4.5	INTERRUPTS	. 4-11
4.5.1	Interrupt Priority Levels	. 4-14
4.5.2	Interrupt Sources Priorities within an IPL	
4.6	PHASE LOCK LOOP	. 4-17
4.6.1	PLL Control Register 0 (PCTL0)	. 4-17
4.6.1.1	Multiplication Factor Bits (MF0–MF11)—Bits 0–11	. 4-17
4.6.1.2	Predivider Factor Bits PD0-PD3-Bits 12-15	. 4-18
4.6.2	PLL Control Register 1 (PCTL1)	. 4-18
4.6.2.1	Division Factor Bits (DF2–DF0)—Bits 0–2	. 4-19
4.6.2.2	Crystal Range Bit (XTLR)—Bit 3	. 4-19
4.6.2.3	Crystal Disable Bit (XTLD)—Bit 4	. 4-19
4.6.2.4	Stop Processing State Bit (PSTP)–Bit 5	. 4-20
4.6.2.5	PLL Enable Bit (PEN)—Bit 6	. 4-20
4.6.2.6	Clock Output Disable Bit (COD)—Bit 7	. 4-20
4.6.2.7	Predivider Factor Bits PD4–PD6—Bits 9–11	. 4-20
4.6.2.8	Reserved Bits 8, 12–15	. 4-20
SECTIO	N 5 EXTERNAL MEMORY INTERFACE (PORT A) .	5-1
5.1	INTRODUCTION	
5.2	EXPANSION PORT SIGNAL DESCRIPTION	
5.2.1	Address Bus—A0–A15	5-3
5.2.2	Data Bus—D0–D23	
5.2.3	Memory Chip Select—MCS	
5.2.4	Read Enable—RD	
5.2.5	Write Enable—WR	5-4



5.2.6	Address Trace—AT	5-4
5.3	Expansion Port Operation	5-4
5.3.1	Static RAM Support	
5.3.2	Expansion Port Disable	
5.4	PORT A CONTROL AND DATA TRANSFER	
5.4.1	Bus Control Register (BCR)	5-7
5.4.1.1	Expansion Bus Memory Wait—Bits 0-4	
5.4.1.2	Reserved Bits—Bits 5–15	
5.4.2	Bus Switch Program Memory Register (BPMR)	5-8
5.4.2.1	BPMR Mapping	
5.4.2.2	24-bit Access to BPMR	
5.4.2.3	16-bit Access to BPMR	5-9
5.4.2.4	BPMR Usage Typical Examples	5-9
5.5	PROGRAM ADDRESS TRACING MODE	
SECTIO	N 6 GPIO	6-1
6.1	INTRODUCTION	
6.2	GPIO CONFIGURATION	
6.3	PORT CONTROL REGISTER (PCR)	
6.4	PORT DIRECTION REGISTER (PRR)	6-5
6.5	PORT DATA REGISTER (PDR)	6-6
SECTIO	, ,	
7.1	INTRODUCTION	
7.2	INTERFACE	
7.2.1	DSP Side	7-3
7.2.2	Host Side	7-4
7.3	HI08 HOST PORT	
7.4	HOST INTERFACE—DSP PROGRAMMER'S MODEL	
7.4.1	HI08 Control Register (HCR)	
7.4.1.1	Host Receive Interrupt Enable (HRIE)—Bit 0	7-9
7.4.1.2	Host Transmit Interrupt Enable (HTIE)—Bit 1	7-9
7.4.1.3	Host Command Interrupt Enable (HCIE)—Bit 2	7-9
7.4.1.4	Host Flags 2 and 3 (HF2–HF3)—Bits 3–4	. 7-10
7.4.1.5	Reserved Bits—Bits 5–15	. 7-10
7.4.2	HI08 Status Register (HSR)	. 7-10





7.4.2.1	Host Receive Data Full (HRDF)—Bit 0	7-10
7.4.2.2	Host Transmit Data Empty (HTDE)—Bit 1	
7.4.2.3	Host Command Pending (HCP)—Bit 2	7-11
7.4.2.4	Host Flags 0 and 1 (HF0-HF1)—Bits 3-4	7-11
7.4.2.5	Reserved Bits—Bits 5–15	7-11
7.4.3	HI08 Port Control Register (HPCR)	7-12
7.4.3.1	Host GPIO Port Enable (HGEN)—Bit 0	7-12
7.4.3.2	Host Address Line 8 Enable (HA8EN)—Bit 1	7-12
7.4.3.3	Host Address Line 9 Enable (HA9EN)—Bit 2	7-12
7.4.3.4	Host Chip Select Enable (HCSEN)—Bit 3	
7.4.3.5	Host Request Enable (HREN)—Bit 4	7-13
7.4.3.6	Host Acknowledge Enable (HAEN)—Bit 5	7-13
7.4.3.7	Host Enable (HEN)—Bit 6	7-13
7.4.3.8	Reserved Bit—Bit 7	7-13
7.4.3.9	Host Request Open Drain (HROD)—Bit 8	7-14
7.4.3.10	Host Data Strobe Polarity (HDSP)—Bit 9	7-14
7.4.3.11	Host Address Strobe Polarity (HASP)—Bit 10	7-14
7.4.3.12	Host Multiplexed Bus (HMUX)—Bit 11	
7.4.3.13	Host Dual Data Strobe (HDDS)—Bit 12	7-14
7.4.3.14	Host Chip Select Polarity (HCSP)—Bit 13	
7.4.3.15	Host Request Polarity (HRP)—Bit 14	7-15
7.4.3.16	Host Acknowledge Polarity (HAP)—Bit 15	7-16
7.4.4	HI08 Data Direction Register (HDDR)	
7.4.5	HI08 Data Register (HDR)	
7.4.6	HI08 Base Address Register (HBAR)	
7.4.7	HI08 Receive Data Register (HRX)	
7.4.8	HI08 Transmit Data Register (HTX)	
7.4.9	DSP Side Registers After Reset	
7.4.10	HI08 DSP Core Interrupts	
7.5	HI08—EXTERNAL HOST PROGRAMMER'S MODEL	
7.5.1	Interface Control Register (ICR)	
7.5.1.1	Receive Request Enable (RREQ)—Bit 0	
7.5.1.2	Transmit Request Enable (TREQ)–Bit 1	
7.5.1.3	Double Host Request (HDRQ)—Bit 2	
7.5.1.4	Host Flag 0 (HF0)—Bit 3	
7.5.1.5	Host Flag 1 (HF1)—Bit 4	7-24



7.5.1.6	Host Little Endian (HLEND)—Bit 5	7-24
7.5.1.7	Initialize Bit (INIT)—Bit 7	7-24
7.5.1.8	Reserved Bit—Bit 6	
7.5.2	Command Vector Register (CVR)	7-25
7.5.2.1	Host Vector (HV)—Bits 0–6	
7.5.2.2	Host Command Bit (HC)—Bit 7	7-26
7.5.3	Interface Status Register (ISR)	7-26
7.5.3.1	Receive Data Register Full (RXDF)—Bit 0	7-26
7.5.3.2	Transmit Data Register Empty (TXDE)—Bit 1	
7.5.3.3	Transmitter Ready (TRDY)—Bit 2	7-27
7.5.3.4	Host Flag 2 (HF2)—Bit 3	7-27
7.5.3.5	Host Flag 3 (HF3)–Bit 4	7-27
7.5.3.6	Reserved Bits-Bits 5 and 6	7-27
7.5.3.7	ISR Host Request (HREQ)—Bit 7	7-27
7.5.4	Interrupt Vector Register (IVR)	
7.5.5	Receive Byte Registers (RXH, RXL)	7-29
7.5.6	Transmit Byte Registers (TXH, TXL)	7-29
7.5.7	Host Side Registers After Reset	7-29
7.6	GENERAL PURPOSE I/O	7-30
7.6.1	Servicing the Host Interface	7-31
7.6.2	HI08 Host Processor Data Transfer	7-31
7.6.3	Polling	7-31
7.6.4	Servicing Interrupts	7-32
SECTIO	N 8 SYNCHRONOUS SERIAL INTERFACE	8-1
8.1	INTRODUCTION	
8.2	SSI DATA AND CONTROL PINS	8-4
8.2.1	Serial Control 0 (SC0)	8-4
8.2.2	Serial Control 1 (SC1)	8-4
8.2.3	Serial Control 2 (SC2)	8-5
8.2.4	Serial Clock (SCK)	
8.2.5	Serial Receive Data (SRD)	8-6
8.2.6	Serial Transmit Data (STD)	
8.3	SSI PROGRAMMING MODEL	
8.3.1	SSI Control Register A (CRA)	
8.3.1.1	Prescale Modulus Select (PM0-PM7)—Bits 0-7.	8-8



8.3.1.2	Frame Rate Divider Control (DC4–DC0)—Bits 8–12	8-8
8.3.1.3	Word Length Control (WL0-WL1)—Bits 13-14	8-8
8.3.1.4	Prescaler Range (PSR)—Bit 15	
8.3.2	SSI Control Register B (CRB)	
8.3.2.1	Serial Output Flag 0 (OF0)—Bit 0	. 8-10
8.3.2.2	Serial Output Flag 1 (OF1)—Bit 1	
8.3.2.3	Reserved Bits 2–7	
8.3.2.4	Transmit Enable (TE)—Bit 8	. 8-10
8.3.2.5	Receive Enable (RE)—Bit 9	
8.3.2.6	Transmit Interrupt Enable (TIE)—Bit 10	. 8-12
8.3.2.7	Receive Interrupt Enable (RIE)—Bit 11	. 8-12
8.3.2.8	Transmit Last Slot Interrupt Enable (TLIE)—Bit 12	. 8-12
8.3.2.9	Receive Last Slot Interrupt Enable (RLIE)—Bit 13	. 8-13
8.3.2.10	Transmit Exception Interrupt Enable (TEIE)—Bit 14.	. 8-13
8.3.2.11	Receive Exception Interrupt Enable (REIE)—Bit 15.	. 8-13
8.3.3	SSI Control Register C (CRC)	. 8-13
8.3.3.1	Asynchronous /Synchronous (SYN)—Bit 0	. 8-14
8.3.3.2	SSI Mode Select (MOD)—Bit 1	. 8-14
8.3.3.3	Serial Control 0 Direction (SCD0)—Bit 2	. 8-14
8.3.3.4	Serial Control 1 Direction (SCD1) —Bit 3	. 8-14
8.3.3.5	Serial Control 2 Direction (SCD2)—Bit 4	. 8-14
8.3.3.6	Clock Source Direction (SCKD)—Bit 5	
8.3.3.7	Clock Polarity (CKP)—Bit 6	. 8-15
8.3.3.8	Shift Direction (SHFD)—Bit 7	. 8-15
8.3.3.9	Reserved Bits 8–11	. 8-15
8.3.3.10	Frame Sync Length (FSL0–FSL1)—Bits 12–13	
8.3.3.11	Frame Sync Relative Timing (FSR)—Bit 14	. 8-16
8.3.3.12	Frame Sync Polarity (FSP)—Bit 15	. 8-16
8.3.4	SSI Status Register (SSISR)	. 8-16
8.3.4.1	Serial Input Flag 0 (IF0)—Bit 0	. 8-17
8.3.4.2	Serial Input Flag 1 (IF1)—Bit 1	. 8-17
8.3.4.3	Transmit Frame Sync Flag (TFS)—Bit 2	. 8-17
8.3.4.4	Receive Frame Sync Flag (RFS)—Bit 3	. 8-18
8.3.4.5	Transmitter Underrun Error Flag (TUE)—Bit 4	. 8-18
8.3.4.6	Receiver Overrun Error Flag (ROE)—Bit 5	. 8-18
8.3.4.7	Transmit Data Register Empty (TDE)—Bit 6	. 8-18



8.3.4.8	Receive Data Register Full (RDF)—Bit 7	8-19
8.3.4.9	Reserved Bits 8–15	8-19
8.3.5	Receive Shift Register	8-19
8.3.6	Receive Data Register (RX)	8-19
8.3.7	Transmit Shift Register	8-19
8.3.8	Transmit Data Register (TX)	8-20
8.3.9	Time Slot Register (TSR)	8-20
8.3.10	Port Control Register (PCR)	8-20
8.3.10.1	Port Control (PC0–PC5)—Bits 0–5	
8.3.10.2	Port Enable (PEN)—Bit 7	8-21
8.3.10.3	Reserved Bits—Bits 6, 8–15	8-21
8.3.11	Port Direction Register (PRR)	8-21
8.3.12	Port Data Register (PDR)	8-22
8.4	OPERATING MODES	8-23
8.4.1	SSI Exceptions	
8.4.2	Operating Modes-Normal, Network, and On-Demand	
8.4.2.1	Operating Mode Selection	8-25
8.4.2.2	Synchronous/Asynchronous Operating Modes	
8.4.2.3	Frame Sync Selection	8-26
8.4.2.4	Shift Direction Selection	8-27
8.4.3	Serial I/O Flags	8-27
SECTIO	N 9 TRIPLE TIMER MODULE	. 9-1
9.1	INTRODUCTION	. 9-3
9.2	TRIPLE TIMER MODULE ARCHITECTURE	. 9-3
9.3	TIMER ARCHITECTURE	
9.4	TRIPLE TIMER MODULE PROGRAMMING MODEL	
9.4.1	Timer Prescaler Load Register (TPLR)	. 9-7
9.4.1.1	Prescaler Preload Value Bits (PL0-PL13)—Bits 0-13	3. 9-7
9.4.1.2	Prescaler Source Bits (PS0–PS1)—Bits 14–15	
9.4.2	Timer Prescaler Count Register (TPCR)	. 9-8
9.4.2.1	Prescaler Counter Value Bits	
	(PC0–PC13)—Bits 0–13	
9.4.2.2	Reserved Bits (Bits 14–15)	
9.4.3	Timer Count Register (TCR)	
9.4.4	Timer Load Register (TLR)	. 9-8



9.4.5	Timer Compare Register (TCPR)	9-9
9.4.6	Timer Control/Status Register (TCSR)	
9.4.6.1	Timer Enable Bit (TE)—Bit 0	9-9
9.4.6.2	Timer Overflow Interrupt Enable Bit (TOIE)—Bit 1	9-9
9.4.6.3	Timer Compare Interrupt Enable Bit (TCIE)-Bit 2	9-9
9.4.6.4	Timer Control Bits (TC0–TC3)—Bits 4–7	. 9-10
9.4.6.5	Inverter Bit (INV)—Bit 8	. 9-11
9.4.6.6	Timer Reload Mode Bit (TRM)—Bit 9	. 9-11
9.4.6.7	Direction Bit (DIR)—Bit 10	. 9-11
9.4.6.8	Data Input Bit (DI)—Bit 11	. 9-12
9.4.6.9	Data Output Bit (DO)—Bit 12	. 9-12
9.4.6.10	Timer Overflow Flag Bit (TOF)—Bit 13	. 9-12
9.4.6.11	Timer Compare Flag Bit (TCF)—Bit 14	. 9-12
9.4.6.12	Prescaled Clock Enable Bit (PCE)—Bit 15	. 9-12
9.4.6.13		
9.5	TIMER MODES OF OPERATION	. 9-13
9.5.1	Timer Modes	. 9-14
9.5.1.1	Mode 0—Timer Mode, No Output (Internal Clock)	. 9-14
9.5.1.2	Mode 1—Timer Mode, Output Pulse Enable	
	(Internal Clock)	. 9-15
9.5.1.3	Mode 2—Timer Mode, Output Toggle Enable	
	(Internal Clock)	. 9-15
9.5.1.4	Mode 3—Timer Mode, Event Counter	
	(External Clock)	. 9-15
9.5.2	Measurement Modes	
9.5.2.1	Mode 4—Pulse Width Measurement Mode	. 9-16
9.5.2.2	Mode 5—Period Measurement Mode	. 9-16
9.5.2.3	Mode 6—Capture Mode	. 9-17
9.5.3	PWM Mode	. 9-17
9.5.3.1	Mode 7—Pulse Width Modulation Mode, Output	
	Toggle Enable (Internal Clock)	
9.5.4	Watchdog Modes	. 9-18
9.5.4.1	Mode 9—Watchdog Mode, Output Pulse Enable	
	(Internal Clock)	. 9-18
9.5.4.2	Mode 10—Watchdog Mode, Output Toggle Enable	
	(Internal Clock)	. 9-19



9.5.5	Reserved Modes	. 9-19
9.5.6	Timer Behavior During WAIT and STOP Instructions	. 9-19
SECTIO	N 10 ON-CHIP EMULATION MODULE	. 10-1
10.1	INTRODUCTION	. 10-3
10.2	ONCE MODULE PINS	. 10-3
10.3	ONCE CONTROLLER	. 10-5
10.3.1	OnCE Command Register (OCR)	. 10-5
10.3.1.1	Register Select Bits (RS4–RS0)—Bits 0–4	
10.3.1.2	Exit Command Bit (EX)—Bit 5	. 10-7
10.3.1.3	GO Command Bit (GO)—Bit 6	. 10-7
10.3.1.4	Read/Write Command Bit (R/W)—Bit 7	. 10-8
10.3.2	OnCE Decoder (ODEC)	. 10-8
10.3.3	OnCE Status and Control Register (OSCR)	. 10-8
10.3.3.1	Trace Mode Enable Bit (TME)—Bit 0	. 10-9
10.3.3.2	Interrupt Mode Enable Bit (IME)—Bit 1	. 10-9
10.3.3.3	Software Debug Occurrence Bit (SWO)—Bit 2	. 10-9
10.3.3.4	Memory Breakpoint Occurrence Bit (MBO)—Bit 3	. 10-9
10.3.3.5	Trace Occurrence Bit (TO)—Bit 4	. 10-9
10.3.3.6	Reserved Bit 5	
10.3.3.7	Core Status Bits (OS0–OS1)—Bits 6-7	. 10-9
10.3.3.8	Reserved Bits 8–23	
10.4	ONCE MEMORY BREAKPOINT LOGIC	
10.4.1	OnCE Memory Address Latch (OMAL)	
10.4.2	OnCE Memory Limit Register 0 (OMLR0)	
10.4.3	OnCE Memory Address Comparator 0 (OMAC0)	
10.4.4	OnCE Memory Limit Register 1 (OMLR1)	
10.4.5	OnCE Memory Address Comparator 1 (OMAC1)	
10.4.6	OnCE Breakpoint Control Register (OBCR)	10-12
10.4.6.1	Memory Breakpoint Select Bits	
	(MBS0–MBS1)—Bits 0–1	10-13
10.4.6.2	•	
	(RW00–RW01)—Bits 2–3	10-13
10.4.6.3		
	(CC00–CC01)—Bits 4–5	10-13





10.4.6.4		
	(RW10–RW11)—Bits 6–7	10-14
10.4.6.5		
	(CC10–CC11)—Bits 8–9	10-14
10.4.6.6	Breakpoint 0 and 1 Event Select Bits	
	(BT0-BT1)—Bits 10-11	10-15
10.4.6.7		
10.4.7	OnCE Memory Breakpoint Counter (OMBC)	10-15
10.5	ONCE TRACE LOGIC	10-15
10.6	METHODS OF ENTERING THE DEBUG MODE	10-17
10.6.1	External Debug Request During RESET Assertion	10-17
10.6.2	External Debug Request During Normal Activity	
10.6.3	Executing the JTAG DEBUG_REQUEST Instruction	10-18
10.6.4	External Debug Request During Stop	10-18
10.6.5	External Debug Request During Wait	
10.6.6	Software Request During Normal Activity	10-19
10.6.7	Enabling Trace Mode	
10.6.8	Enabling Memory Breakpoints	
10.7	PIPELINE INFORMATION AND OGDB REGISTER	
10.7.1	OnCE PDB Register (OPDBR)	10-20
10.7.2	OnCE PIL Register (OPILR)	10-20
10.7.3	OnCE GDB Register (OGDBR)	10-21
10.8	TRACE BUFFER	
10.8.1	OnCE PAB Register for Fetch (OPABFR)	10-21
10.8.2	PAB Register for Decode (OPABDR)	10-21
10.8.3	OnCE PAB Register for Execute (OPABEX)	10-22
10.8.4	Trace Buffer	
10.9	ONCE COMMANDS AND SERIAL PROTOCOL	10-24
10.10	TARGET SITE DEBUG SYSTEM REQUIREMENTS	10-25
10.11	EXAMPLES OF USING THE ONCE	10-25
10.11.1	Checking Whether the Chip has Entered the Debug	
	Mode	10-25
10.11.2	Polling the JTAG Instruction Shift Register	10-26
10.11.3	Saving Pipeline Information	10-26
10.11.4	Reading the Trace Buffer	10-26
10.11.5	Displaying a Specified Register	10-27



10.11.6 Displaying X Memory Area Starting at Address \$xxxx . 1	0-28
10.11.7 Returning from Debug Mode to Normal Mode to	
Current Program	0-29
10.11.8 Returning from Debug Mode to Normal Mode to a	
New Program	0-30
10.12 EXAMPLES OF JTAG AND ONCE INTERACTION 1	0-30
SECTION 11 JTAG PORT	11-1
11.1 INTRODUCTION	11-3
11.2 JTAG PINS	11-5
11.2.1 Test Clock (TCK)	
11.2.2 Test Mode Select (TMS)	
11.2.3 Test Data Input (TDI)	
11.2.4 Test Data Output (TDO)	
11.2.5 Test Reset (TRST)	
11.3 TAP CONTROLLER	
11.3.1 Boundary Scan Register	
11.3.2 Instruction Register	
11.3.2.1 EXTEST (B[3:0] = 0000)	
11.3.2.2 SAMPLE/PRELOAD (B[3:0] = 0001)	
11.3.2.3 IDCODE (B[3:0] = 0010)	
11.3.2.4 CLAMP (B[3:0] = 0011)	
11.3.2.5 HI-Z (B[3:0] = 0100)	
11.3.2.6 ENABLE_ONCE(B[3:0] = 0110)	
11.3.2.7 DEBUG_REQUEST(B[3:0] = 0111)	
11.3.2.8 BYPASS (B[3:0] = 1111)	
11.4 DSP56600 RESTRICTIONS	
APPENDIX A BOOTSTRAP PROGRAM	. A-1
A.1 DSP56603 BOOTSTRAP LISTING	. A-3
ADDENDIN D. VIIO FOLIATEO	.
APPENDIX B X I/O EQUATES	
B.1 DSP56603 X I/O EQUATES	
B.2 DSP56603 INTERRUPT EQUATES	B-10





APPE	ENDIX C	PROGRAMMER'S REFERENCE	
C.1	INTRO	DUCTION	
C.2	INSTRI	UCTION SET SUMMARY	
C.3	INTERI	RUPT, VECTOR, AND ADDRESS TABI	_ES C-14
$C \Lambda$	PROGI	PAMMER'S SHEETS	C-23









LIST OF FIGURES

Figure 1-1	DSP56603 Block Diagram
Figure 2-1	DSP56603 Signals Identified by Functional Group 2-4
Figure 3-1	DSP56603 Memory Map
Figure 4-1	Operating Mode Register (OMR) Programming Model 4-4
Figure 4-2	Status Register Programming Model
Figure 4-3	DSP Device ID (IDR) Register for DSP56603 4-8
Figure 4-4	Interrupt Priority Registers IPR-C and IPR-P 4-14
Figure 4-5	PLL Control Register 0 (PCTL0) Programming Model 4-17
Figure 4-6	PLL Control Register 1 (PCTL1) Programming Model 4-18
Figure 5-1	Static RAM Connection Diagram 5-5
Figure 5-2	Bus Operation, One Wait State—SRAM Access 5-6
Figure 5-3	Bus Control Register Programming Model 5-7
Figure 5-4	BPMR Register
Figure 5-5	Possible Address Tracing Configuration Diagram 5-12
Figure 6-1	GPIO Programming Model 6-4
Figure 7-1	HI08 Block Diagram7-7
Figure 7-2	Host Control Register Programming Model
Figure 7-3	Host Status Register (HSR) Programming Model 7-10
Figure 7-4	Host Port Control Register (HPCR) Programming Model 7-12
Figure 7-5	Single and Dual Strobe Bus Modes



Figure 7-6	Host Data Direction Register (HDDR) Programming Model 7-16
Figure 7-7	Host Data Register (HDR) Programming Model7-17
Figure 7-8	Self Chip Select Logic
Figure 7-9	Host Base Address Register (HBAR) Programming Model 7-18
Figure 7-10	HSR–HCR Operation
Figure 7-11	Interface Control Register Programming Model7-22
Figure 7-12	Command Vector Register (CVR)
Figure 7-13	Interface Status Register Programming Model7-26
Figure 7-14	Interrupt Vector Register (IVR)7-28
Figure 7-15	HI08 Host Request Structure
Figure 8-1	SSI Block Diagram
Figure 8-2	SSI Control Register A Programming Model 8-8
Figure 8-3	SSI Control Register B Programming Model 8-9
Figure 8-4	SSI Control Register C Programming Model 8-14
Figure 8-5	SSI Status Register Programming Model 8-17
Figure 8-6	SSI Port Control Register Programming Model 8-21
Figure 8-7	SSI GPIO Direction Control Register Programming Model 8-22
Figure 8-8	SSI GPIO Data Register Programming Model 8-23
Figure 9-1	Triple Timer Module Block Diagram9-4
Figure 9-2	16-bit Timer Module Block Diagram9-5
Figure 9-3	Triple Timers Programming Model9-6
Figure 10-1	OnCE Module Block Diagram10-3





Figure 10-2	OnCE Module Multiprocessor Configuration
Figure 10-3	OnCE Controller Block Diagram
Figure 10-4	OnCE Command Register
Figure 10-5	OnCE Status and Control Register (OSCR) 10-8
Figure 10-6	OnCE Memory Breakpoint Logic 0
Figure 10-7	OnCE Breakpoint Control Register (OBCR) 10-12
Figure 10-8	OnCE Trace Logic Block Diagram 10-16
Figure 10-9	OnCE Pipeline Information and GDB Registers 10-20
Figure 10-10	OnCE Trace Buffer
Figure 11-1	TAP Block Diagram
Figure 11-2	TAP Controller State Machine11-6
Figure 11-3	JTAG Instruction Register
Figure 11-4	JTAG ID Register 11-10
Figure 11-5	Bypass Register









LIST OF TABLES

Table 1-1	High True / Low True Signal Conventions 1-5
Table 2-1	Functional Group Signal Allocations 2-3
Table 2-2	Power Inputs
Table 2-3	Grounds
Table 2-4	Clock and PLL Signals
Table 2-5	Interrupt and Mode Control Signals
Table 2-6	Expansion Port, Port A Signals
Table 2-7	Host Port Usage Considerations
Table 2-8	Host Interface Signals
Table 2-9	Synchronous Serial Interface 0 (SSI0) 2-18
Table 2-10	Synchronous Serial Interface 1 (SSI1) 2-21
Table 2-11	General Purpose I/O (GPIO)2-24
Table 2-12	Triple Timer Signals
Table 2-13	JTAG Interface/On-Chip Emulation Module (OnCE) Signals 2-26
Table 3-1	Switch Mode Memory Configuration
Table 3-2	Internal I/O Memory Map
Table 4-1	Patch JUMP Targets
Table 4-2	DSP566603 Reset Addresses
Table 4-3	Interrupt Sources
Table 4-4	Interrupt Priority Level Bits



Table 4-5	External Interrupt Trigger Mode Bits
Table 4-6	Interrupt Source Priorities within an IPL4-15
Table 4-7	Multiplication Factor Bits MF0–MF114-18
Table 4-8	Division Factor Bits
Table 6-1	PCR and PRR Bits Functionality 6-5
Table 7-1	Summary of HI08 Pins and Operating Modes
Table 7-2	Strobe Signals Support Pins7-6
Table 7-3	Host Request Support Pins
Table 7-4	HI08 Interrupt Request Priority Order7-9
Table 7-5	HDR and HDDR Bits Functionality7-17
Table 7-6	DSP Side Registers after Reset7-19
Table 7-7	HI08 Host Side Register Map7-22
Table 7-8	TREQ and HREQ Modes (HDRQ = 0)7-23
Table 7-9	TREQ and HREQ Modes (HDRQ = 1)7-23
Table 7-10	INIT Commands
Table 7-11	Host Side Registers After Reset
Table 8-1	SSI Clock Sources
Table 8-2	SSI Word Length Selection 8-9
Table 8-3	Mode and Pin Definition Table
Table 8-4	FSL1 and FSL0 Encoding
Table 8-5	PCR and PRR Register Bits Functionality 8-22
Table 9-1	PS Bit Functionality





Table 9-2	TC Bit Functionality 9-10
Table 9-3	Timer Mode Summary 9-13
Table 10-1	OnCE Register Select Encoding
Table 10-2	EX Bit Definition
Table 10-3	GO Bit Definition
Table 10-4	R/W Bit Definition
Table 10-5	Core Status Bits Description
Table 10-6	Memory Breakpoint 0 and 1 Select Table
Table 10-7	Breakpoint 0 Read/Write Select Table
Table 10-8	Breakpoint 0 Condition Select Table
Table 10-9	Breakpoint 1 Read/Write Select Table
Table 10-10	Breakpoint 1 Condition Select Table
Table 10-11	Breakpoint 0 and 1 Event Select Table
Table 10-12	TMS Sequencing for DEBUG_REQUEST
Table 10-13	TMS Sequencing for ENABLE_ONCE 10-32
Table 10-14	TMS Sequencing for Reading Pipeline Registers 10-32
Table 11-1	JTAG Instructions
Table 11-2	DSP56603 Boundary Scan Register (BSR) Bit Definitions 11-13
Table C-1	Program Word and Timing Symbols
Table C-2	Condition Code Register (CCR) Symbols
Table C-3	Condition Code Register Notation
Table C-4	Instruction Set Summary



Table C-5	Interrupt Sources	.C-14
Table C-6	Interrupt Source Priorities within an IPL	.C-16
Table C-7	Internal I/O Memory Map	.C-17
Table C-8	List of Programmer's Sheets	.C-23






LIST OF EXAMPLES

Example 1-1	Sample Code Listing
Example 5-1	Move from P Source Address to P Destination Address 5-9
Example 5-2	Bootstrap through External EPROM 5-9
Example 5-3	Pass Program Memory Words to the OGDB Register 5-10
Example A-1	DSP56603 Bootstrap Listing
Example B-1	DSP56603 X I/O Equates
Example B-2	DSP56603 Interrupt Equates





SECTION 1 OVERVIEW





1.1	INTRODUCTION
1.2	MANUAL ORGANIZATION
1.3	MANUAL CONVENTIONS
1.4	DSP56600 CORE DESCRIPTION 1-6
1.5	DSP56600 CORE FUNCTIONAL BLOCKS 1-6
1.6	INTERNAL BUSES
1.7	DSP56603 ARCHITECTURE OVERVIEW 1-13



Introduction

1.1 INTRODUCTION

This manual describes the DSP56603 16-bit Digital Signal Processor (DSP), its memory and operating modes, and its peripheral modules. This manual is intended to be used with the *DSP56600 Family Manual (DSP56600FM/AD)*, which describes the Central Processing Unit (CPU), programming models, and instruction set details. *DSP56603 Technical Data (DSP56603/D)* provides electrical specifications, timing, pinout, and packaging descriptions on the DSP56603. These documents, as well as Motorola's DSP development tools, can be obtained through a local Motorola Semiconductor Sales Office or authorized distributor.

To receive the latest information, access the Motorola DSP home page located at the address listed on the back cover of this document.

The DSP56603 is a member of the DSP56600 core-based family of programmable CMOS DSPs. This general purpose DSP combines processing power with configuration flexibility, making it an excellent cost-effective solution for signal processing and control functions.

1.2 MANUAL ORGANIZATION

This manual is arranged in the following sections:

- **Section 1—Overview** provides a brief overview of the DSP56603, describes the structure of this document, and lists other documentation necessary to use this chip.
- Section 2—Signal/Connection Description provides a description of the signals
 present on the pins of the DSP56603, and how these signals are grouped into
 the various interfaces.
- Section 3—Memory Maps describes the on-chip memory, structures, registers, and interfaces.
- **Section 4—Core Configuration** describes the registers that must be programmed to properly configure the DSP56600 core when using the DSP56603.
- **Section 5—External Memory Interface (Port A)** describes the external memory interface, which is also referred to as Port A.
- **Section 6—GPIO** describes the dedicated General Purpose Input/Output (GPIO) interface, and the alternate GPIO functionality provided on certain on-chip interfaces.

Manual Conventions

, v crview

- Section 7— Host Interface (HI08) describes the 8-bit HI08 Host Interface.
- **Section 8—Synchronous Serial Interface** describes the 16-bit Synchronous Serial Interface (SSI), which communicates with devices such as codecs, other DSPs, microprocessors, and peripherals, to provide the primary data input path. The SSI is a part of Port C.
- Section 9—Triple Timer Module describes the three internal timer/counter devices.
- Section 10—On-Chip Emulation Module describes the On-Chip Emulation (OnCETM) module, which is accessed through the Joint Test Action Group (JTAG) port.
- Section 11—JTAG Port describes the specifics of the JTAG port on the DSP56603.
- Appendix A—Bootstrap Program provides a listing of the bootstrap code used to start or reset the DSP56603.
- Appendix B—X I/O Equates lists the Input/Output equates for the DSP56603.
- Appendix C—Programmer's Reference provides programming references and master programming sheets used to program the DSP56603 registers.
- Glossary provides a listing of terms used in this manual.
- **Index** provides a cross-reference to topics in this manual.

1.3 MANUAL CONVENTIONS

The following conventions are used in this manual:

 Bits within registers are always listed from Most Significant Bit (MSB) to Least Significant Bit (LSB).

Note: Other manuals may use the opposite convention, with bits listed from LSB to MSB.

- Bits within a register are indicated AA[n:0] when more than one bit is involved in a description. For purposes of description, the bits are presented as if they are contiguous within a register. However, this is not always the case. Refer to the programming model diagrams or to the programmer's sheets to see the exact location of bits within a register.
- When a bit is described as "set," its value is 1. When a bit is described as "cleared," its value is 0.



Manual Conventions

- Pins or signals that are asserted low (made active when pulled to ground) have an overbar over their name; for example, the \$\overline{SS0}\$ pin is asserted low.
- Hex values are indicated with a dollar sign (\$) preceding the hex value as follows: \$FFFF is the X memory address for the Interrupt Priority Register—Core (IPR-C).
- Code examples are displayed in a monospaced font, as shown in Example 1-1.

Example 1-1 Sample Code Listing

BFSET	#\$0007,X:PCC; Configure:	line 1
	; MISOO, MOSIO, SCKO for SPI master	line 2
	; ~SSO as PC3 for GPIO	line 3

- Pins or signals listed in code examples that are asserted low have a tilde in front of their names. In the previous example, line 3 refers to the $\overline{SS0}$ pin (shown as $\sim SS0$).
- The word "assert" means that a high true (active high) signal is pulled high to V_{CC} or that a low true (active low) signal is pulled low to ground. The word "deassert" means that a high true signal is pulled low to ground or that a low true signal is pulled high to V_{CC} . See **Table 1-1**.

Table 1-1 High True / Low True Signal Conventions

Signal/Symbol	Logic State	Signal State	Voltage
PIN	True	Asserted	Ground ¹
PIN	False	Deasserted	$V_{\rm CC}^{\ 2}$
PIN	True	Asserted	V_{CC}
PIN	False	Deasserted	Ground

Notes: 1. Ground is an acceptable low voltage level. See the appropriate data sheet for the range of acceptable low voltage levels (typically a TTL logic low).

- 2. V_{CC} is an acceptable high voltage level. See the appropriate data sheet for the range of acceptable high voltage levels (typically a TTL logic high).
- The word "reset" is used in three different contexts in this manual. There is a reset pin that is always written as "RESET", a reset instruction that is always written as "RESET", and the word reset that refers to the reset function and is written in lower case with a leading capital letter as grammar dictates. The word "pin" is a generic term for any pin on the chip.



DSP56600 Core Description

1.4 DSP56600 CORE DESCRIPTION

The DSP56600 core is based on the DSP56300 core, with a number of power-saving, performance-enhancing, and cost-reducing features implemented. With its seven-stage instruction pipeline, the DSP56600 core is capable of executing an instruction on every clock cycle. A standard interface between the DSP56600 core and the on-chip memory and peripherals supports many memory and peripheral configurations. Complete details of the DSP56600 core are provided in the *DSP56600 Family Manual (DSP56600FM/AD)*.

The following are some of the features of the DSP56600 core:

- 60 Million Instructions Per Second (MIPS) with a 60 MHz clock at 2.7 V
- Fully pipelined 16 × 16-bit parallel Multiplier-Accumulator (MAC)
- 40-bit parallel barrel shifter
- Highly parallel instruction set with unique DSP addressing modes
- Code compatible with the 56300 core
- Position Independent Code (PIC) support
- Nested hardware DO loops
- Fast auto-return interrupts
- · On-chip support for software patching and enhancements
- On-chip Phase Lock Loop (PLL)
- Real-time trace capability via External Address Bus
- On-Chip Emulation (OnCE) module
- JTAG port

1.5 DSP56600 CORE FUNCTIONAL BLOCKS

The DSP56600 core provides the following functional blocks:

- Data Arithmetic Logic Unit (Data ALU)
- Address Generation Unit (AGU)
- Program Control Unit (PCU)
- Program Patch Logic

1-6



DSP56600 Core Functional Blocks

- PLL and Clock Oscillator
- Expansion Port (Port A)
- JTAG Test Access Port and On-Chip Emulation (OnCE) module
- Memory

In addition, the DSP56603 provides a set of on-chip peripherals, described in **DSP56603 Architecture Overview** on page 1-13.

1.5.1 Data ALU

The Data ALU performs all the arithmetic and logical operations on data operands in the DSP56600 core. The components of the Data ALU are as follows:

- Four 16-bit input general purpose registers: X1, X0, Y1, and Y0
- A parallel, fully pipelined Multiplier-Accumulator unit (MAC)
- Six Data ALU registers (A2, A1, A0, B2, B1, and B0) that are concatenated into two general purpose, 40-bit accumulators, A and B
- An accumulator shifter that is an asynchronous parallel shifter with a 40-bit input and a 40-bit output
- · A Bit Field Unit (BFU) with a 40-bit barrel shifter
- Two data bus shifter/limiter circuits

1.5.1.1 Data ALU Registers

The Data ALU registers can be read or written over the X Data Bus (XDB) and the Y Data Bus (YDB) as 16- or 32-bit operands. The source operands for the Data ALU, which can be 16, 32, or 40 bits, always originate from Data ALU registers. The results of all Data ALU operations are stored in an accumulator.

All the Data ALU operations are performed in 2 clock cycles in pipeline fashion so that a new instruction can be initiated in every clock, yielding an effective execution rate of one instruction per clock cycle. The destination of every arithmetic operation can be used as a source operand for the immediate following operation without penalty.

1.5.1.2 Multiplier-Accumulator (MAC)

The Multiplier-Accumulator (MAC) unit comprises the main arithmetic processing unit of the DSP56600 core and performs all of the calculations on data operands. In the case of arithmetic instructions, the unit accepts as many as three input operands



DSP56600 Core Functional Blocks

and outputs one 40-bit result of the following form, Extension:Most Significant Product:Least Significant Product (EXT:MSP:LSP).

The multiplier executes 16-bit \times 16-bit, parallel, fractional multiplies, between two's-complement signed, unsigned, or mixed operands. The 32-bit product is right-justified and added to the 40-bit contents of either the A or B accumulator. A 40-bit result can be stored as a 16-bit operand. The LSP can either be truncated or rounded into the MSP. Rounding is performed if specified.

1.5.2 Address Generation Unit

The AGU performs the effective address calculations using integer arithmetic necessary to address data operands in memory and contains the registers used to generate the addresses. It implements four types of arithmetic: linear, modulo, multiple wrap-around modulo, and reverse-carry. The AGU operates in parallel with other chip resources to minimize address-generation overhead.

The AGU is divided into two halves, each with its own Address Arithmetic Logic Unit (Address ALU). Each Address ALU has four sets of register triplets, and each register triplet is composed of an address register, an offset register, and a modifier register. The two Address ALUs are identical. Each contains a 16-bit full adder (called an offset adder).

A second full adder (called a modulo adder) adds the summed result of the first full adder to a modulo value that is stored in its respective modifier register. A third full adder (called a reverse-carry adder) is also provided.

The offset adder and the reverse-carry adder are in parallel and share common inputs. The only difference between them is that the carry propagates in opposite directions. Test logic determines which of the three summed results of the full adders is output.

Each Address ALU can update one address register from its respective address register file during 1 instruction cycle. The contents of the associated modifier register specifies the type of arithmetic to be used in the address register update calculation. The modifier value is decoded in the Address ALU.



DSP56600 Core Functional Blocks

1.5.3 Program Control Unit

The Program Control Unit (PCU) performs instruction prefetch, instruction decoding, hardware DO loop control, and exception processing. The PCU implements a seven-stage pipeline and controls the different processing states of the DSP56600 core. The PCU consists of three hardware blocks:

- Program Decode Controller (PDC)
- Program Address Generator (PAG)
- Program Interrupt Controller (PIC)

The PDC decodes the 24-bit instruction loaded into the instruction latch and generates all signals necessary for pipeline control. The PAG contains all the hardware needed for program address generation, system stack, and loop control. The PIC arbitrates among all interrupt requests (internal interrupts, as well as the five external requests IRQA, IRQB, IRQC, IRQD, and NMI), and generates the appropriate interrupt vector address.

The PCU implements its functions using the following registers:

- PC—Program Counter register
- SR—Status Register
- LA—Loop Address register
- LC—Loop Counter register
- VBA—Vector Base Address register
- SZ—Size register
- SP—Stack Pointer
- OMR—Operating Mode Register
- SC—Stack Counter register

The PCU also includes a hardware System Stack (SS).

1.5.4 Program Patch Logic

The Program Patch Logic (PPL) block provides the DSP56600 core user a way to fix the program code in the on-chip ROM without generating a new mask. Implementing the code correction is done by replacing a piece of ROM-based code

Overview

Freescale Semiconductor, Inc.

DSP56600 Core Functional Blocks

with a patch program stored in RAM. The PPL consists of four Patch Address Registers (PAR1–PAR4) and four patch address comparators. Each PAR points to a starting location in the ROM code where the program flow is to be changed. The PC register in the PCU is compared to each PAR. When an address of a fetched instruction is identical to an address stored in one of the PARs, the Program Data Bus (PDB) is forced to a corresponding JMP instruction, replacing the instruction that otherwise would have been fetched from the ROM.

1.5.5 PLL and Clock Oscillator

The DSP56600 core features a Phase Lock Loop (PLL) clock oscillator in its central processing module. The PLL allows the processor to operate at a high internal clock frequency using a low frequency clock input, a feature that offers two immediate benefits:

- A lower frequency clock input reduces the overall electromagnetic interference generated by a system.
- The ability to oscillate at different frequencies reduces costs by eliminating the need to add additional oscillators to a system.

The clock generator in the DSP56600 core is composed of two main blocks: the PLL, which performs clock input division, frequency multiplication, and skew elimination; and the Clock Generator (CLKGEN), which performs low power division and clock pulse generation.

1.5.6 Expansion Port (Port A)

Port A is the memory expansion port used for both program and data memory. It provides an easy to use, low part-count connection with fast or slow static memories and with I/O devices. The Port A data bus is 24 bits wide with a separate 16-bit address bus capable of a sustained rate of one memory access per two clock cycles. External memory can be as large as $64~\rm K \times 24$ -bit program memory space, depending on chip configuration. An internal wait state generator can be programmed to insert as many as thirty-one wait states if access to slower memory or I/O device is required. For power-sensitive applications and applications that do not require external memory, Port A can be fully disabled.



Internal Buses

1.5.7 JTAG Test Access Port and On-Chip Emulation (OnCE) Module

The DSP56600 core provides a dedicated user-accessible Test Access Port (TAP) that is fully compatible with the *IEEE 1149.1 Standard Test Access Port and Boundary Scan Architecture*. Problems associated with testing high density circuit boards have led to development of this standard under the sponsorship of the Test Technology Committee of IEEE and the Joint Test Action Group (JTAG). The DSP56600 core implementation supports circuit-board test strategies based on this standard.

The test logic includes a TAP consisting of four dedicated signal pins, a 16-state controller, and three test data registers. A boundary scan register links all device signal pins into a single shift register. The test logic, implemented utilizing static logic design, is independent of the device system logic. More information on the JTAG port is provided in **Section 11**, **JTAG Port**.

The On-Chip Emulation (OnCE) module provides a means of interacting with the DSP56600 core and its peripherals non-intrusively so that a user can examine registers, memory, or on-chip peripherals. This facilitates hardware and software development on the DSP56600 core processor. OnCE module functions are provided through the JTAG TAP pins. More information on the OnCE module is provided in **Section 10, On-Chip Emulation Module**.

1.5.8 On-Chip Memory

The memory space of the DSP56600 core is partitioned into program memory space, X data memory space, and Y data memory space. The data memory space is divided into X data memory and to Y data memory in order to work with the two Address ALUs and to feed two operands simultaneously to the Data ALU. Memory space includes internal RAM and ROM and can be expanded off-chip under software control. More information on the internal memory is provided in **Section 3**, **Memory Maps**.

1.6 INTERNAL BUSES

To provide data exchange between these blocks, the following buses are implemented:

• Peripheral I/O Expansion Bus (PIO_EB) to peripherals



Internal Buses

- Program Memory Expansion Bus (PM_EB) to Program ROM
- X Memory Expansion Bus (XM_EB) to X Memory
- Y Memory Expansion Bus (YM_EB) to Y Memory
- Global Data Bus (GDB) between Program Control Unit and other core structures
- Program Data Bus (PDB) for carrying program data throughout the core
- X Memory Data Bus (XDB) for carrying X data throughout the core
- Y Memory Data Bus (YDB) for carrying Y data throughout the core
- Program Address Bus (PAB) for carrying program memory addresses throughout the core
- X Memory Address Bus (XAB) for carrying X memory addresses throughout the core
- Y Memory Address Bus (YAB) for carrying Y memory addresses throughout the core

With the exception of the Program Data Bus (PDB), all internal buses on the DSP56600 family members are 16-bit buses. The PDB is a 24-bit bus. **Figure 1-1** provides a block diagram of the DSP56603.



DSP56603 Architecture Overview




Figure 1-1 DSP56603 Block Diagram

1.7 DSP56603 ARCHITECTURE OVERVIEW

The DSP56603 is designed to perform a wide variety of fixed-point digital signal processing functions. In addition to the core features previously discussed, the DSP56603 provides the following peripherals:

- Three dedicated General Purpose I/O (GPIO) pins
- As many as thirty-one additional user-configurable GPIO pins
- 8-bit parallel Host Interface (HI08) to external hosts
- Dual Synchronous Serial Interface (SSI)
- Triple timer module



DSP56603 Architecture Overview

- Memory Switch mode
- Four external interrupt/mode control lines

1.7.1 GPIO Functionality

The General Purpose I/O (GPIO) port consists of three bidirectional pins, each pin separately controlled. Functionality is controlled by three memory-mapped registers. GPIO functionality is also available on the HI08, SSI, and timer pins when these pins are not otherwise being used by their peripherals. The techniques for register programming for all GPIO functionality is very similar between these interfaces. A maximum of thirty-four GPIO pins can be configured.

1.7.2 Host Interface (HI08)

The Host Interface (HI08) is a byte-wide, full-duplex, double-buffered, parallel port that can be connected directly to the data bus of a host processor. The HI08 supports a variety of buses, and provides connection with a number of industry-standard DSPs, microcomputers, and microprocessors without requiring any additional logic.

The DSP core views the HI08 as a memory-mapped peripheral occupying eight 16-bit words in data memory space. The DSP can use the HI08 as a memory-mapped peripheral, using either standard polled or interrupt programming techniques. Separate transmit and receive data registers are double-buffered to allow the DSP and host processor to efficiently transfer data at high speed. Memory mapping allows DSP core communication with the HI08 registers to be accomplished using standard instructions and addressing modes.

1.7.3 Synchronous Serial Interface (SSI)

The DSP56603 provides two independent and identical Synchronous Serial Interfaces (SSI). Each SSI provides a full-duplex serial port for communication with a variety of serial devices, including one or more industry-standard codecs, other DSPs, microprocessors, and peripherals that implement the Motorola SPI. The SSI consists of independent transmitter and receiver sections and a common SSI clock generator.



Overview

DSP56603 Architecture Overview

The capabilities of the SSI include:

- Independent (asynchronous) or shared (synchronous) transmit and receive sections with separate or shared internal/external clocks and frame syncs
- Normal mode operation using frame sync
- Network mode operation with as many as 32 time slots
- Programmable word length (8, 12, or 16 bits)
- Program options for frame synchronization and clock generation

1.7.4 Triple Timer

The triple timer module is composed of a common 14-bit prescaler and three independent and identical general purpose 16-bit timer/event counters, each one having its own memory-mapped register set.

Each timer can use internal or external clocking and can interrupt the DSP after a specified number of events (clocks) or can signal an external device after counting internal events. Each timer connects to the external world through one bidirectional pin. When this pin is configured as an input, the timer can function as an external event counter or measures external pulse width/signal period. When the pin is used as an output, the timer can function as either a timer, a watchdog, or a Pulse Width Modulator (PWM).






DSP56603 Architecture Overview



SECTION 2 SIGNAL/CONNECTION DESCRIPTION



Signal/Connection Description

2.1	INTRODUCTION	-3
2.2	POWER	-5
2.3	GROUND	-6
2.4	CLOCK AND PHASE LOCK LOOP	-7
2.5	INTERRUPT AND MODE CONTROL	-8
2.6	EXPANSION PORT (PORT A)	11
2.7	HOST INTERFACE (HI08)	12
2.8	SYNCHRONOUS SERIAL INTERFACE 0 (SSI0)2-	18
2.9	SYNCHRONOUS SERIAL INTERFACE 1 (SSI1) 2-2	21
2.10	GENERAL PURPOSE I/O, GPIO	24
2.11	TRIPLE TIMER	25
2 12	ITAG/ONCE INTERFACE 2-4	26



Introduction

2.1 INTRODUCTION

The input and output signals of the DSP56603 are organized into functional groups, as shown in Table 2-1 and as illustrated in Figure 2-1. In Table 2-2 through **Table 2-13**, each table row describes the signal or signals present on a pin.


The DSP56603 operates from a 3 V supply; however, some of the inputs can tolerate 5 V. A special notice for this feature is added to the signal descriptions of those inputs.

Table 2-1 Functional Group Signal Allocations

Functional Group	Number of Signals	Detailed Description	
Power (V _{CC})		19	Table 2-2
Ground (GND)		19	Table 2-3
PLL and Clock Signals		5	Table 2-4
Interrupt and Mode Control		5	Table 2-5
External Memory Port	Address Bus	16	Table 2-6
(also referred to as Port A)	Data Bus	24	
	Bus Control	4	
Host Interface (HI08)	Port B (GPIO)	16	Table 2-8
Synchronous Serial Interface 0 (SSI0)	Port C (GPIO)	6	Table 2-9
Synchronous Serial Interface 1 (SSI1)	Port D (GPIO)	6	Table 2-10
General Purpose Input/Output (GPI	3	Table 2-11	
Triple Timer	3	Table 2-12	
JTAG Interface/On-Chip Emulation	(OnCE) Module	6	Table 2-13



Introduction



Note: 1. The HI08 port supports a non-multiplexed or a multiplexed bus, single or double Data Strobe (DS), and single or double Host Request (HR) configurations. Since each these modes is configured independently, any combination of these modes is possible. The HI08 signals can also be configured alternately as GPIO signals (PB0–PB15).

- 2. The SSI0 and SSI1 signals can be configured alternatively as Port C GPIO signals (PC0–PC5) and Port D GPIO signals (PD0–PD5), respectively.
- 3. TIO0-TIO2 can be configured alternatively as GPIO signals.

Figure 2-1 DSP56603 Signals Identified by Functional Group





2.2 **POWER**

 Table 2-2
 Power Inputs

Signal Name (number of pins)	Signal Description		
V _{CCA} (3)	Address Bus Power — V_{CCA} is an isolated power for sections of address bus I/O drivers, and must be tied externally to all other chip power inputs, except for the V_{CCQL} input. The user must provide adequate external decoupling capacitors.		
V _{CCC} (1)	Bus Control Power — V_{CCC} is an isolated power for the bus control I/O drivers, and must be tied to all other chip power inputs externally, except for the V_{CCQL} input. The user must provide adequate external decoupling capacitors.		
V _{CCD} (4)	$\begin{array}{ c c c c c c c c c c c c c c c c c c c$		
V _{CCH} (1)	$\label{eq:host Power-V} \textbf{Host Power-} V_{CCH} \ \text{is an isolated power for the HI08 logic, and must be tied to all other chip power inputs externally, except for the V_{CCQL} input. The user must provide adequate external decoupling capacitors.}$		
V _{CCP} (1)	PLL Power — V_{CCP} is V_{CC} dedicated for Phase Lock Loop (PLL) use. The voltage should be well-regulated and the input should be provided with an extremely low impedance path to the V_{CC} power rail.		
V _{CCQH} (3)			
	The voltage supplied to these inputs should equal the voltage supplied to I/O power inputs V_{CCA} , V_{CCC} , V_{CCD} , V_{CCH} , and V_{CCS} .		
V _{CCQL} (4)	Quiet Power Low Voltage —V _{CCQL} is an isolated power for the CPU logic, and should not be tied to the other chip power inputs. The user must provide adequate external decoupling capacitors.		
	The voltage supplied to these inputs should be equal to or lower than the voltage supplied to the V_{CCQH} inputs. The user can lower the voltage supplied to V_{CCQL} as long as it meets the MIPS requirements of the application, thus lowering the chip's overall power consumption.		



Ground

Table 2-2 Power Inputs (Continued)

Signal Name (number of pins)	Signal Description		
V _{CCS} (2)	SSI, GPIO, and Timers Power — V_{CCS} is a isolated power for the SSIs, GPIO, and Timers logic, and must be tied to all other chip power inputs externally, except for the V_{CCQL} input. The user must provide adequate external decoupling capacitors.		

2.3 **GROUND**

Table 2-3 Grounds

Signal Name (number of pins)	Signal Description
GND _A (4)	Address Bus Ground — GND_A is an isolated ground for sections of address bus I/O drivers, and must be tied externally to all other chip ground connections. The user must provide adequate external decoupling capacitors.
GND _C (2)	Bus Control Ground — GND_C is an isolated ground for the bus control I/O drivers, and must be tied externally to all other chip ground connections. The user must provide adequate external decoupling capacitors.
GND _D (4)	Data Bus Ground — GND_D is an isolated ground for sections of the data bus I/O drivers, and must be tied externally to all other chip ground connections. The user must provide adequate external decoupling capacitors.
GND _H (1)	Host Ground —GND _H is an isolated ground for the HI08 I/O drivers, and must be tied externally to all other chip ground connections. The user must provide adequate external decoupling capacitors.
GND _P (1)	PLL Ground —GND _P is ground dedicated for PLL use, and should be provided with an extremely low impedance path to ground. V_{CCP} should be bypassed to GND _P with a 0.1 μF capacitor located as close as possible to the chip package.
GND _{P1} (1)	PLL Ground 1 — GND_{P1} is ground dedicated for PLL use, and should be provided with an extremely low impedance path to ground.

Table 2-3 Grounds (Continued)

Signal Name (number of pins)	Signal Description
GND _Q (4)	$ \begin{array}{c} \textbf{Quiet Ground} - \text{GND}_Q \text{ is an isolated ground for the CPU logic, and} \\ \text{must be tied externally to all other chip ground connections. The user} \\ \text{must provide adequate external decoupling capacitors.} \end{array} $
GND _S (2)	SSIs, GPIO, and Timers Ground—GNDS is an isolated ground for the SSIs, GPIO, and Timers logic, and must be tied externally to all other chip ground connections. The user must provide adequate external decoupling capacitors.

CLOCK AND PHASE LOCK LOOP 2.4

Table 2-4 Clock and PLL Signals

Signal Name	Signal Type	State During Reset	Signal Description
EXTAL	Input	Input	External Clock/Crystal Input—EXTAL interfaces the internal crystal oscillator input to an external crystal or an external clock.
XTAL	Output	Chip- driven	Crystal Output—XTAL connects the internal crystal oscillator output to an external crystal. If an external clock is used, leave XTAL unconnected.
PCAP	Input	Indeter- minate	$\begin{array}{c} \textbf{PLL Capacitor} - PCAP \text{ is an input connecting an off-chip capacitor to the PLL filter. Connect one capacitor terminal to PCAP and the other terminal to V_{CCP}. \end{array}$
			If the PLL is not used, PCAP may be tied to V_{CC} , GND, or left floating.
CLKOUT	Output	Chip- driven	Clock Output—CLKOUT provides an output clock synchronized to the internal core clock phase. When the PLL is enabled, the Division Factor (DF) equals one, and the Multiplication Factor (MF) is less than or equal to four, CLKOUT is also synchronized to EXTAL When the PLL is disabled, the CLKOUT frequency is half the
			frequency of EXTAL.



Signal/Connection Description

Interrupt And Mode Control

Table 2-4 Clock and PLL Signals (Continued)

Signal Name	Signal Type	State During Reset	Signal Description
PINIT/ NMI	Input	Input	PLL Initial/Non-Maskable Interrupt—During assertion of RESET, the value of PINIT/NMI is written into the PLL Enable (PEN) bit of the PLL control register, determining whether the PLL is enabled or disabled. After RESET deassertion and during normal instruction processing, the PINIT/NMI Schmitt-trigger input is a negative-edge-triggered Non-Maskable Interrupt (NMI) request internally synchronized to CLKOUT. This input can tolerate 5 V.

2.5 INTERRUPT AND MODE CONTROL

 Table 2-5
 Interrupt and Mode Control Signals

Signal Name	Signal Type	State During Reset	Signal Description
RESET	Input	Input	Reset—RESET is an active low, Schmitt-trigger input. Deassertion of the RESET signal is internally synchronized to the clock out (CLKOUT). When asserted, the chip is placed in the Reset state and the internal phase generator is reset. The Schmitt-trigger input allows a slowly rising input, such as a capacitor charging, to reliably reset the chip. If the RESET signal is deasserted synchronous to CLKOUT, exact start-up timing is guaranteed, allowing multiple processors to start up synchronously and operate together. When the RESET signal is deasserted, the initial chip operating mode is latched from the MODA, MODB, MODC, and MODD inputs. This input can tolerate 5 V.



Signal/Connection Description

Interrupt And Mode Control

 Table 2-5
 Interrupt and Mode Control Signals (Continued)

Signal Name	Signal Type	State During Reset	Signal Description
MODA/ IRQA	Input	Input	Mode Select A/External Interrupt Request A—MODA/IRQA is an active low Schmitt-trigger input, internally synchronized to CLKOUT. MODA/IRQA selects the initial chip operating mode during hardware reset and becomes a level-sensitive or negative-edge-triggered, maskable interrupt request input during normal instruction processing. MODA, MODB, MODC, and MODD select one of sixteen initial chip operating modes latched into the Operating Mode Register (OMR) when the RESET signal is deasserted. If IRQA is asserted synchronous to CLKOUT, multiple processors can be resynchronized using the WAIT instruction and asserting IRQA to exit the Wait state. If the processor is in the Stop standby state and IRQA is asserted, the processor exits the Stop state.
MODB/ IRQB	Input	Input	This input can tolerate 5 V. Mode Select B/External Interrupt Request B—MODB/IRQB is an active low Schmitt-trigger input, internally synchronized to CLKOUT. MODB/IRQB selects the initial chip operating mode during hardware reset and becomes a level-sensitive or negative-edge-triggered, maskable interrupt request input during normal instruction processing. MODA, MODB, MODC, and MODD select one of sixteen initial chip operating modes latched into the OMR register when the RESET signal is deasserted. If IRQB is asserted synchronous to CLKOUT, multiple processors can be resynchronized using the WAIT instruction and asserting IRQB to exit the Wait state. This input can tolerate 5 V.



Signal/Connection Description

Interrupt And Mode Control

 Table 2-5
 Interrupt and Mode Control Signals (Continued)

Signal Name	Signal Type	State During Reset	Signal Description
MODC/ IRQC	Input	Input	Mode Select C/External Interrupt Request C—MODC/IRQCn is an active low Schmitt-trigger input, internally synchronized to CLKOUT. MODC/IRQC selects the initial chip operating mode during hardware reset and becomes a level-sensitive or negative-edge-triggered, maskable interrupt request input during normal instruction processing. MODA, MODB, MODC, and MODD select one of sixteen initial chip operating modes latched into the OMR register when the RESET signal is deasserted. If IRQC is asserted synchronous to CLKOUT, multiple processors can be resynchronized using the WAIT instruction and asserting IRQC to exit the Wait state.
			This input can tolerate 5 V.
MODD/ IRQD	Input	Input	Mode Select D/External Interrupt Request D MODD/IRQD is an active low Schmitt-trigger input, internally synchronized to CLKOUT. MODD/IRQD selects the initial chip operating mode during hardware reset and becomes a level-sensitive or negative-edge-triggered, maskable interrupt request input during normal instruction processing. MODA, MODB, MODC, and MODD select one of sixteen initial chip operating modes, latched into OMR when the RESET signal is deasserted. If IRQD is asserted synchronous to CLKOUT, multiple processors can be re-synchronized using the WAIT instruction and asserting IRQD to exit the Wait state. This input can tolerate 5 V.



Signal/Connection Description

·

2.6 EXPANSION PORT (PORT A)

 Table 2-6
 Expansion Port, Port A Signals

Signal Name	Signal Type	State During Reset	Signal Description
A0-A15	Output	Set according to chip operating mode ¹	Address Bus—These active high outputs specify the address for external program memory accesses. To minimize power dissipation, A0–A15 do not change state when external memory spaces are not being accessed.
D0-D23	Input/ Output	Tri-stated	Data Bus —These active high, bidirectional input/outputs provide the bidirectional data bus for external program memory accesses. D0–D23 are tri-stated when no external bus activity occurs, and during hardware reset.
MCS	Output	Pulled high internally	Memory Chip Select—This signal is an active low output, and is asserted when an external memory access occurs. MCS is deasserted during hardware reset.
RD	Output	Pulled high internally	Read Enable —This signal is an active low output. \overline{RD} is asserted to read external memory on the data bus (D0–D23). \overline{RD} is deasserted during hardware reset.
WR	Output	Pulled high internally	Write Enable—This signal is an active low output. \overline{WR} is asserted to write external memory on the data bus (D0–D23). \overline{WR} is deasserted during hardware reset.
ĀT	Output	Pulled high internally	Address Tracing—This signal is an active low output. \overline{AT} is asserted (for half of a clock cycle) whenever a new address is driven on the address bus (A0–A15) in the Program Address Tracing mode. The new address is either a reflection of internal fetch or internal program space move instruction or an external address driven for an external access. \overline{AT} is deasserted during hardware reset.

Note: 1. The A0–A15 pins are asserted according to the selected chip operating mode, as determined by the values on the MODA–MODD pins. Each mode has a different reset address. A0–A15 are latched to the value of that reset address minus 1. For example, if the reset address for a selected operating mode is \$0800, the address bus is asserted to \$07FF.



Signal/Connection Description

Host Interface (HI08)

2.7 HOST INTERFACE (HI08)

The HI08 provides a fast 8-bit port that can be connected directly to the host bus. The HI08 supports a variety of standard buses, and can be directly connected to a number of industry standard microcomputers, microprocessors, DSPs, and DMA hardware.

2.7.1 Host Port Usage Considerations

Careful synchronization is required when reading multiple-bit registers that are written by another asynchronous system. This is a common problem when two asynchronous systems are connected (as they are in the Host port). The considerations for proper operation are discussed in the following table:

Table 2-7 Host Port Usage Considerations

Action	Description
Asynchronous read of receive byte registers	When reading the receive byte registers, Receive High (RXH) register or Receive Low (RXL) register, the Host Interface programmer should use interrupts or poll the Receive Register Data Full (RXDF) flag, which indicates that data is available. This assures that the data in the receive byte registers is valid.
Asynchronous write to transmit byte registers	The host interface programmer should not write to the transmit byte registers, Transmit High (TXH) register or Transmit Low (TXL) register, unless the Transmit Register Data Empty (TXDE) bit is set, which indicates that the transmit byte registers are empty. This guarantees that the transmit byte registers transfer valid data to the Host Receive (HRX) register.
Asynchronous write to host vector	The Host Interface programmer should change the Host Vector (HV) register only when the Host Command (HC) bit is clear. This guarantees that the DSP interrupt control logic receives a stable vector.

2.7.2 Host Port Configuration

The signal functions associated with the HI08 vary according to the configuration determined by the HI08 Port Control Register (HPCR). Refer to **Section 7**, **Host Interface (HI08)**, for detailed descriptions of this and the other configuration registers used with the HI08.





Signal/Connection Description

Table 2-8 Host Interface Signals

Signal Name	Signal Type	State During Reset	Signal Description
HAD0- HAD7	Bi-directional	Discon- nected internally	Host Data Bus—When the HI08 is programmed to interface a non-multiplexed host bus and the HI function is selected, these signals are lines 0–7 of the Host Data bidirectional tri-state bus (HD0–HD7).
	Bi-directional		Host Address and Data Bus—When the HI08 is programmed to interface a multiplexed host bus and the HI function is selected, these signals are lines 0–7 of the Host Address/Data multiplexed bidirectional tri-state bus (HAD0–HAD7).
	Input or Output		Port B 0–7 —When the HI08 is configured as GPIO through the HI08 Port Control Register (HPCR), these signals are individually programmed as inputs or outputs through the HI08 Data Direction Register (HDDR).
			When configured as an input, this pin can tolerate 5 V. This pin is electrically disconnected internally during Stop mode.
HA0/HAS	Input	Discon- nected internally	Host Address Input 0—When the HI08 is programmed to interface a non-multiplexed host bus and the HI function is selected, this signal is line 0 of the Host Address input bus (HA0).
	Input		Host Address Strobe—When the HI08 is programmed to interface a multiplexed host bus and the HI function is selected, this signal is the Host Address Strobe (HAS) Schmitt-trigger input. The polarity of the address strobe is programmable.
	Input or Output		Port B 8—When the HI08 is configured as GPIO through the HPCR, this signal is individually programmed as an input or output through the HDDR.
			When configured as an input, this pin can tolerate 5 V. This pin is electrically disconnected internally during Stop mode.



Signal/Connection Description

Table 2-8 Host Interface Signals (Continued)

Signal Name	Signal Type	State During	Signal Description
	Jighai Type	Reset	Signal Description
HA1/HA8	Input	Discon- nected internally	Host Address Input 1—When the HI08 is programmed to interface a non-multiplexed host bus and the HI function is selected, this signal is line one of the Host Address input bus (HA1).
	Input		Host Address 8 —When the HI08 is programmed to interface a multiplexed host bus and the HI function is selected, this signal is line eight of the input Host Address bus (HA8).
	Input or Output		Port B 9 —When the HI08 is configured as GPIO through the HPCR, this signal is individually programmed as an input or output through the HDDR.
			When configured as an input, this pin can tolerate 5 V. This pin is electrically disconnected internally during Stop mode.
HA2/HA9	Input	Discon- nected internally	Host Address Input 2—When the HI08 is programmed to interface a non-multiplexed host bus and the HI function is selected, this signal is line two of the Host Address input bus (HA2).
	Input		Host Address 9—When the HI08 is programmed to interface a multiplexed host bus and the HI function is selected, this signal is line nine of the input Host Address bus (HA9).
	Input or Output		Port B 10 —When the HI08 is configured as GPIO through the HPCR, this signal is individually programmed as an input or output through the HDDR.
			When configured as an input, this pin can tolerate 5 V. This pin is electrically disconnected internally during Stop mode.





Signal/Connection Description

 Table 2-8
 Host Interface Signals (Continued)

Signal Name	Signal Type	State During Reset	Signal Description
HRW/HRD	Input	Discon- nected internally	Host Read/Write—When the HI08 is programmed to interface a single-data-strobe host bus and the HI function is selected, this signal is the Read/Write input (HRW).
	Input		Host Read Data—When the HI08 is programmed to interface a double-data-strobe host bus and the HI function is selected, this signal is the Read Data strobe Schmitt-trigger input (HRD). The polarity of the data strobe is programmable.
	Input or Output		Port B 11 —When the HI08 is configured as GPIO through the HPCR, this signal is individually programmed as an input or output through the HDDR.
			When configured as an input, this pin can tolerate 5 V. This pin is electrically disconnected internally during Stop mode.
HDS/HWR	Input	Discon- nected internally	Host Data Strobe—When the HI08 is programmed to interface a single-data-strobe host bus and the HI function is selected, this signal is the Host Data Strobe Schmitt-trigger input (HDS). The polarity of the data strobe is programmable.
	Input		Host Write Enable—When the HI08 is programmed to interface a double-data-strobe host bus and the HI function is selected, this signal is the Write Data Strobe Schmitt-trigger input (HWR). The polarity of the data strobe is programmable.
	Input or Output		Port B 12 —When the HI08 is configured as GPIO through the HPCR, this signal is individually programmed as an input or output through the HDDR.
			When configured as an input, this pin can tolerate 5 V. This pin is electrically disconnected internally during Stop mode.



Signal/Connection Description

Table 2-8 Host Interface Signals (Continued)

Tuble 2 0 1105t Interface Signals (Continued)					
Signal Name	Signal Type	State During Reset	Signal Description		
HCS/HA10	Input	Discon- nected internally	Host Chip Select—When the HI08 is programmed to interface a non-multiplexed host bus and the HI function is selected, this signal is the Host Chip Select input (HCS). The polarity of the chip select is programmable.		
	Input		Host Address 10—When the HI08 is programmed to interface a multiplexed host bus and the HI function is selected, this signal is line 10 of the input Host Address bus (HA10).		
	Input or Output		Port B 13 —When the HI08 is configured as GPIO through the HPCR, this signal is individually programmed as an input or output through the HDDR.		
			When configured as an input, this pin can tolerate 5 V. This pin is electrically disconnected internally during Stop mode.		
HREQ/HTRQ	Output	Discon- nected internally	Host Request—When the HI08 is programmed to interface a single host request host bus and the HI function is selected, this signal is the Host Request output (HREQ). The polarity of the host request is programmable. The host request can be programmed as a driven or open-drain output.		
	Output		Transmit Host Request —When the HI08 is programmed to interface a double host request host bus and the HI function is selected, this signal is the Transmit Host Request output (HTRQ). The polarity of the host request is programmable. The host request can be programmed as a driven or open-drain output.		
	Input or Output		Port B 14 —When the HI08 is programmed to interface a multiplexed host bus and the signal is configured as GPIO through the HPCR, this signal is individually programmed as an input or output through the HDDR.		
			When configured as an input, this pin can tolerate 5 V. This pin is electrically disconnected internally during Stop mode.		





Signal/Connection Description

 Table 2-8
 Host Interface Signals (Continued)

Signal Name	Signal Type	State During Reset	Signal Description
HACK/ HRRQ	Input	Discon- nected internally	Host Acknowledge —When the HI08 is programmed to interface a single host request host bus and the HI function is selected, this signal is the Host Acknowledge Schmitt-trigger input (HACK). The polarity of the host acknowledge is programmable.
	Output		Receive Host Request—When the HI08 is programmed to interface a double host request host bus and the HI function is selected, this signal is the Receive Host Request output (HRRQ). The polarity of the host request is programmable. The host request can be programmed as a driven or open-drain output.
	Input or Output		Port B 15—When the HI08 is configured as GPIO through the HPCR, this signal is individually programmed as an input or output through the HDDR. When configured as an input, this pin can tolerate 5 V. This pin is electrically disconnected internally during Stop mode.



Signal/Connection Description

Synchronous Serial Interface 0 (SSI0)

2.8 SYNCHRONOUS SERIAL INTERFACE 0 (SSI0)

Two identical Synchronous Serial Interfaces (SSI0 and SSI1) provide a full-duplex serial port for serial communication with a variety of serial devices including one or more industry-standard codecs, other DSPs, or microprocessors. When either SSI port is disabled, it can be used for General Purpose I/O (GPIO).

 Table 2-9
 Synchronous Serial Interface 0 (SSI0)

Signal Name	Signal Type	State During Reset	Signal Description
SC00	Input or Output	Input	Serial Control Signal 0 —The function of SC00 is determined by the selection of either Synchronous or Asynchronous mode. For Asynchronous mode, this signal is used for the receive clock I/O (Schmitt-trigger input). For Synchronous mode, this signal is used for or for Serial I/O Flag 0.
	Input or Output		Port C 0 —When configured as PC0, signal direction is controlled through the SSI0 Port Direction Control Register (PRRC). The signal can be configured as SSI signal SC00 through the SSI0 Port Control Register (PCRC).
			When configured as an input, this pin can tolerate 5 V. This pin is electrically disconnected internally during Stop mode.
SC01	Input or Output	Input	Serial Control Signal 1 —The function of SC00 is determined by the selection of either Synchronous or Asynchronous mode. For Asynchronous mode, this signal is used for the receive clock I/O (Schmitt-trigger input). For Synchronous mode, this signal is used for Serial I/O Flag 1.
	Input or Output		Port C 1 —When configured as PC1, signal direction is controlled through the PRRC register. The signal can be configured as an SSI signal SC01 through the PCRC register.
			When configured as an input, this pin can tolerate 5 V. This pin is electrically disconnected internally during Stop mode.





Signal/Connection Description

Synchronous Serial Interface 0 (SSI0)

Table 2-9 Synchronous Serial Interface 0 (SSI0) (Continued)

Signal Name	Signal Type	State During Reset	Signal Description
SC02	Input or Output	Input	Serial Control Signal 2—SC02 is the frame sync for both the transmitter and receiver in Synchronous mode, and for the transmitter only in Asynchronous mode. When configured as an output, this signal is the internally generated frame sync signal. When configured as an input, this signal receives an external frame sync signal for the transmitter (and the receiver in synchronous operation).
	Input or Output		Port C 2 —When configured as PC2, signal direction is controlled through the PRRC register. The signal can be configured as an SSI signal SC02 through the PCRC register.
			When configured as an input, this pin can tolerate 5 V. This pin is electrically disconnected internally during Stop mode.
SCK0	Input or Output	Input	Serial Clock—SCK0 is a bidirectional Schmitt-trigger input signal providing the serial bit rate clock for the SSI interface. The SCK0 is a clock input or output used by both the transmitter and receiver in Synchronous modes, or by the transmitter in Asynchronous modes.
			Although an external serial clock can be independent of and asynchronous to the DSP system clock, it must exceed the minimum clock cycle time of 6T (i.e., the system clock frequency must be at least three times the external SSI clock frequency). The SSI needs at least three DSP phases inside each half of the serial clock.
	Input or Output		Port C 3 —When configured as PC3, signal direction is controlled through the PRRC register. The signal can be configured as an SSI signal SCK0 through the PCRC register.
			When configured as an input, this pin can tolerate 5 V. This pin is electrically disconnected internally during Stop mode.



Signal/Connection Description

Synchronous Serial Interface 0 (SSI0)

 Table 2-9
 Synchronous Serial Interface 0 (SSI0) (Continued)

Signal Name	Signal Type	State During Reset	Signal Description
SRD0	Input	Input	Serial Receive Data —SRD0 receives serial data and transfers the data to the SSI receive shift register. SRD0 is an input when data is being received.
	Input or Output		Port C 4 —When configured as PC4, signal directions is controlled through the PRRC register. The signal can be configured as an SSI signal SRD0 through the PCRC register.
			When configured as an input, this pin can tolerate 5 V. This pin is electrically disconnected internally during Stop mode.
STD0	Output	Input	Serial Transmit Data —STD0 is used for transmitting data from the serial transmit shift register. STD0 is an output when data is being transmitted.
	Input or Output		Port C 5 —When configured as PC5, signal directions is controlled through the PRRC register. The signal can be configured as an SSI signal STD0 through the PCRC register.
			When configured as an input, this pin can tolerate 5 V. This pin is electrically disconnected internally during Stop mode.





Signal/Connection Description

Synchronous Serial Interface 1 (SSI1)

2.9 SYNCHRONOUS SERIAL INTERFACE 1 (SSI1)

 Table 2-10
 Synchronous Serial Interface 1 (SSI1)

Signal Name	Signal Type	State During Reset	Signal Description
SC10	Input or Output	Input	Serial Control Signal 0 —The function of SC10 is determined by the selection of either Synchronous or Asynchronous mode. For Asynchronous mode, this signal is used for the receive clock I/O (Schmitt-trigger input). For Synchronous mode, this signal is used for or for Serial I/O Flag 0.
	Input or Output		Port D 0 —When configured as PD0, signal direction is controlled through the SSI1 Port Direction Control Register (PRRD). The signal can be configured as SSI signal SC10 through the SSI1 Port Control Register (PCRD).
			When configured as an input, this pin can tolerate 5 V. This pin is electrically disconnected internally during Stop mode.
SC11	Input or Output	Input	Serial Control Signal 1 —The function of SC11 is determined by the selection of either Synchronous or Asynchronous mode. For Asynchronous mode, this signal is used for the receive clock I/O (Schmitt-trigger input). For Synchronous mode, this signal is used for Serial I/O Flag 1.
	Input or Output		Port D 1 —When configured as PD1, signal direction is controlled through the PRRD register. The signal can be configured as an SSI signal SC11 through the PCRD register.
			When configured as an input, this pin can tolerate 5 V. This pin is electrically disconnected internally during Stop mode.



Signal/Connection Description

Synchronous Serial Interface 1 (SSI1)

 Table 2-10
 Synchronous Serial Interface 1 (SSI1) (Continued)

Signal Name	Signal Type	State During Reset	Signal Description
SC12	Input or Output	Input	Serial Control Signal 2—SC12 is used for frame sync I/O. SC12 is the frame sync for both the transmitter and receiver in Synchronous mode, and for the transmitter only in Asynchronous mode. When configured as an output, this signal is the internally generated frame sync signal. When configured as an input, this signal receives an external frame sync signal for the transmitter (and the receiver in synchronous operation).
	Input or Output		Port D 2 —When configured as PD2, signal direction is controlled through the PRRD register. The signal can be configured as an SSI signal SC12 through the PCRD register.
			When configured as an input, this pin can tolerate 5 V. This pin is electrically disconnected internally during Stop mode.
SCK1	Input or Output	Input	Serial Clock—SCK1 is a bidirectional Schmitt-trigger input signal providing the serial bit rate clock for the SSI interface. The SCK1 is a clock input or output used by both the transmitter and receiver in Synchronous modes, or by the transmitter in Asynchronous modes.
			Although an external serial clock can be independent of and asynchronous to the DSP system clock, it must exceed the minimum clock cycle time of 6T (i.e., the system clock frequency must be at least three times the external SSI clock frequency). The SSI needs at least three DSP phases inside each half of the serial clock.
	Input or Output		Port D 3 —When configured as PD3, signal direction is controlled through the PRRD register. The signal can be configured as an SSI signal SCK1 through the PCRD register.
			When configured as an input, this pin can tolerate 5 V. This pin is electrically disconnected internally during Stop mode.





Signal/Connection Description

Synchronous Serial Interface 1 (SSI1)

 Table 2-10
 Synchronous Serial Interface 1 (SSI1) (Continued)

Signal Name	Signal Type	State During Reset	Signal Description
SRD1	Input	Input	Serial Receive Data —SRD1 receives serial data and transfers the data to the SSI Receive Shift Register.
	Input or Output		Port D 4 —When configured as PD4, signal direction is controlled through the PRRD register. The signal can be configured as an SSI signal SRD1 through the PCRD register.
			When configured as an input, this pin can tolerate 5 V. This pin is electrically disconnected internally during Stop mode.
STD1	Input	Input	Serial Transmit Data —STD1 is used for transmitting data from the SSI Transmit Shift Register.
	Input or Output		Port D 5 —When configured as PD5, signal direction is controlled through the PRRD register. The signal can be configured as an SSI signal STD1 through the PCRD register.
			When configured as an input, this pin can tolerate 5 V. This pin is electrically disconnected internally during Stop mode.



Signal/Connection Description

General Purpose I/O, GPIO

2.10 GENERAL PURPOSE I/O, GPIO

Three dedicated General Purpose Input/Output (GPIO) signals are provided on the DSP56603. Each is reconfigurable as input, output, or tri-state. These signals are exclusively defined as GPIO, and do not offer additional functionality.

Table 2-11 General Purpose I/O (GPIO)

Signal Name	Signal Type	State During Reset	Signal Description	
GPIO0	Input or Output	Input	General Purpose I/O 0—When a GPIO signal is used as input, the logic state is reflected to an internal register and can be read by the software. When a GPIO signal is used as output, the logic state is controlled by the software. This input can tolerate 5 V. This pin is electrically disconnected internally during Stop mode.	
GPIO1	Input or Output	Input	General Purpose I/O 1—When a GPIO signal is used as input, the logic state is reflected to an internal register and can be read by the software. When a GPIO signal is used as output, the logic state is controlled by the software. This input can tolerate 5 V. This pin is electrically disconnected internally during Stop mode.	
GPIO2	Input or Output	Input	General Purpose I/O 2—When a GPIO signal is used as input, the logic state is reflected to an internal register and can be read by the software. When a GPIO signal is used as output, the logic state is controlled by the software. This input can tolerate 5 V. This pin is electrically disconnected internally during Stop mode.	





Triple Timer

TRIPLE TIMER 2.11

Three identical and independent timers are implemented. The three timers can use internal or external clocking and can interrupt the DSP after a specified number of events (clocks), or can signal an external device after counting a specific number of internal events. When a timer port is disabled, it can be used for General Purpose I/O (GPIO).

Table 2-12 Triple Timer Signals

Signal Name	Signal Type	State During Reset	Signal Description	
TIO0	Input or Output	GPIO Input	00 1 1	
	Input or		When TIO0 is not used by the timer module, it can be used for GPIO.	
	Output		When configured as an input, this pin can tolerate 5 V. This pin is electrically disconnected internally during Stop mode.	
TIO1	Input or Output	GPIO Input	Timer 1 Schmitt-Trigger Input/Output —When TIO1 is used as an input, the timer module functions as an external event counter or measures external pulse width or signal period. When TIO1 is used as an output, the timer module functions as a timer and TIO1 provides the timer pulse.	
	Input or		When TIO1 is not used by the timer module, it can be used for GPIO.	
	Output		When configured as an input, this pin can tolerate 5 V. This pin is electrically disconnected internally during Stop mode.	
TIO2	Input or Output	GPIO Input	Timer 2 Schmitt-Trigger Input/Output —When TIO2 is used as an input, the timer module functions as an external event counter or measures external pulse width or signal period. When TIO2 is used as an output, the timer module functions as a timer and TIO2 provides the timer pulse.	
	Input or		When TIO2 is not used by the timer module, it can be used for GPIO.	
	Output		When configured as an input, this pin can tolerate 5 V. This pin is electrically disconnected internally during Stop mode.	



Signal/Connection Description

JTAG/OnCE Interface

2.12 JTAG/ONCE INTERFACE


 Table 2-13
 JTAG Interface/On-Chip Emulation Module (OnCE) Signals

Signal Name	Signal Type	State During Reset	Signal Description	
TCK	Input	Input	Test Clock —TCK is a test clock input signal used to synchronize the JTAG test logic. The TCK pin can be tri-stated.	
			This input can tolerate 5 V.	
TDI	Input	Input	Test Data Input — TDI is a test data serial input signal used for test instructions and data. TDI is sampled on the rising edge of the TCK signal and has an internal pull-up resistor.	
			This input can tolerate 5 V.	
TDO	Output	Tri- stated	Test Data Output — TDO is a test data serial output signal used for test instructions and data. TDO is tri-stateable and is actively driven in the shift-IR and shift-DR controller states. TDO changes on the falling edge of the TCK signal.	
TMS	Input	Input	Test Mode Select — TMS is an input signal used to sequence the test controller's state machine. TMS is sampled on the rising edge of the TCK signal and has an internal pull-up resistor.	
			This input can tolerate 5 V.	
TRST	Input	Input	Test Reset—TRST is an active-low Schmitt-trigger input signal used to asynchronously initialize the test controller. TRST has an internal pull-up resistor. TRST must be asserted after power up.	
			This input can tolerate 5 V.	
DE	Bi-directional	Input	Debug Event — \overline{DE} is an open-drain bidirectional active-low signal providing, as an input, a means of entering the Debug mode of operation from an external command controller, and as an output, a means of acknowledging that the chip has entered the Debug mode. The \overline{DE} has an internal pull-up resistor.	
			When this pin is an input, it can tolerate 5 V.	

dsp









3.1	INTRODUCTION	3-3
3.2	DSP56603 MEMORY MAP DESCRIPTION	3-3
3 3	MEMORY-MAPPED I/O REGISTERS	3-5



Introduction

Memory Maps

3.1 INTRODUCTION

This section describes in detail the on-chip memories and the internal peripheral memory map of the DSP56603.

3.2 **DSP56603 MEMORY MAP DESCRIPTION**

The three independent memory spaces of DSP56603: Program, X data, and Y data, are shown in Figure 3-1.




Figure 3-1 DSP56603 Memory Map

A special function, called Switch mode, allows switching a portion of Program RAM for use as X and Y data RAM. The Memory Switch mode (MS) bit in the Operating Mode Register (OMR) controls Switch mode. See Memory Switch Mode Bit (MS)—Bit 14 on page 4-6 for more information.



DSP56603 Memory Map Description

Table 3-1 shows the available memory spaces when Switch Mode is activated.

 Table 3-1
 Switch Mode Memory Configuration

Memory Space	Switch Mode Off	Switch Mode On
Program RAM	16.5 K × 24-bit	11.5 K × 24-bit
X RAM	8 K × 16-bit	10.5 K × 16-bit
Y RAM	8 K × 16-bit	10.5 K × 16-bit

In addition to the Program RAM, X data RAM, and Y data RAM, a $3~{\rm K} \times 24$ -bit bootstrap ROM is provided on the DSP56603. The contents of this ROM are listed in **Appendix A, Bootstrap Program**.

3.2.1 On-Chip Program Memory

The on-chip Program RAM consists of two blocks of memory. A 24-bit-wide, high-speed, static memory occupies the lowest 512 locations (\$0000–\$01FF) in the P memory space. The on-chip Program RAM is organized in two banks, with 256 locations in each bank.

In addition, a 24-bit-wide block of Program RAM occupies the locations \$1000–\$4FFF. This Program RAM is organized in 44 banks, with 256 locations in each bank. When Switch mode is active, the upper 5 K of this memory (at addresses \$3C00–\$4FFF) is reassigned as X and Y data RAM. A 3 K \times 24-bit bootstrap ROM occupies the locations (\$0400–\$0FFF). No user Program ROM is provided.

Note: The P memory space located at locations \$0200–\$03FF is reserved and should not be accessed.

3.2.2 On-Chip X Data Memory

The on-chip X data RAM is a 16-bit-wide, internal, static memory occupying the lowest 8192 locations (\$0000–\$1FFF) in X memory space. The on-chip X data RAM is organized in 32 banks, with 256 locations in each bank. No X data ROM is provided. When Switch mode is active, an additional 2.5 K of X data RAM, located at \$2000–\$29FF, is accessible. This Switch mode X data RAM is organized in 10 banks, with 256 locations in each bank.



reescale Sellicolladetol, Ilici

Memory-Mapped I/O Registers

Memory Maps

The on-chip peripheral registers and some of the core registers occupy the top 128 locations of the X data memory (\$FF80-\$FFF). This area is referred to as X I/O space. It can be accessed by the MOVE and the MOVEP instructions, as well as by bit-oriented instructions (such as the BCHG, BCLR, BSET, BTST, BRCLR, BRSET, BSCLR, BSSET, JCLR, JSET, JSCLR, and JSSET instructions).

Note: The X memory space located at locations \$2A00–FF7F is reserved and

should not be accessed.

3.2.3 On-Chip Y Data Memory

The on-chip Y data RAM is a 16-bit-wide, internal, static memory occupying the lowest 8192 locations (\$0000–\$1FFF) in Y memory space. The on-chip Y data RAM is organized in 32 banks, with 256 locations in each bank. No Y data ROM is provided. When Switch mode is active, an additional 2.5 K of Y data RAM, located at \$2000–\$29FF, is accessible. This Switch mode Y data RAM is organized in 10 banks, with 256 locations in each bank.

Note: The Y memory space located at locations \$2A00–FFFF is reserved and

should not be accessed.

3.3 MEMORY-MAPPED I/O REGISTERS

All the DSP56603 on-chip peripherals are mapped on the internal X-I/O space, the top 128 locations of the X data memory space. The specific addresses for every on-chip peripheral register or peripheral-mapped register are shown in **Table 3-2**.

Table 3-2 Internal I/O Memory Map

Peripheral	Address	Register Name	
PIC	\$FFFF	IPR-C—Interrupt Priority Register—Core	
	\$FFFE	IPR-P—Interrupt Priority Register—Peripheral	
PLL	\$FFFD	PCTL0—PLL Control Register	
	\$FFFC	PCTL1—PLL Control Register	
OnCE	\$FFFB	OGDB—OnCE GDB Register	



Memory-Mapped I/O Registers

Table 3-2 Internal I/O Memory Map (Continued)

Peripheral	l Address Register Name				
Тепристи	ridaress	190gister runne			
BIU	\$FFFA	BCR—Bus Control Register			
	\$FFF9	IDR—ID Register			
Patch	\$FFF8	PAR0—Patch 0 Register			
	\$FFF7	PAR1—Patch 1 Register			
	\$FFF6	PAR2—Patch 2 Register			
	\$FFF5	PAR3—Patch 3 Register			
BPMR	\$FFF4	BPMRG—Bus Switch Program Memory Register (24 bits)			
	\$FFF3	BPMRL—Bus Switch Program Memory Register Low(16 bits)			
	\$FFF2	BPMRH—Bus Switch Program Memory Register High (16 bits)			
Reserved	\$FFF1	Reserved			
	•				
	\$FFCA				
HI08	\$FFC9	HDR—HI08 Data Register			
	\$FFC8	HDDR—HI08 Data Direction Register			
	\$FFC7	HTX—HI08 Transmit Data Register			
	\$FFC6	HRX—HI08 Receive Data Register			
	\$FFC5	HBAR —HI08 Base Address Register			
	\$FFC4	HPCR—HI08 Port Control Register			
	\$FFC3	HSR—HI08 Status Register			
	\$FFC2	HCR—HI08 Control Register			
Reserved	\$FFC1	Reserved			
	\$FFC0				





Memory Maps

Memory-Mapped I/O Registers

Table 3-2 Internal I/O Memory Map (Continued)

Peripheral	Address	Register Name		
SSI0	\$FFBF	PCRC—SSI 0 Port Control Register		
	\$FFBE	PRRC—SSI 0 GPIO Direction Register		
	\$FFBD	PDRC—SSI 0 GPIO Data Register		
SSI0	\$FFBC	TX0—SSI 0 Transmit Data Register		
	\$FFBB	TSR0—SSI 0 Time Slot Register		
	\$FFBA	RX0—SSI 0 Receive Data Register		
	\$FFB9	SSISR0—SSI 0 Status Register		
	\$FFB8	CRC0—SSI 0 Control Register C		
	\$FFB7	CRB0—SSI 0 Control Register B		
	\$FFB6	CRA0—SSI 0 Control Register A		
Reserved	\$FFB5	Reserved		
	•			
	\$FFB0			
SSI1	\$FFAF	PCRD—SSI 1 Port Control Register		
	\$FFAE	PRRD—SSI 1 GPIO Direction Register		
	\$FFAD	PDRD—SSI 1 GPIO Data Register		
	\$FFAC	TX1—SSI 1 Transmit Data Register		
	\$FFAB	TSR1—SSI 1 Time Slot Register		
	\$FFAA	RX1—SSI 1 Receive Data Register		
	\$FFA9	SSISR1—SSI 1 Status Register		
	\$FFA8	CRC1—SSI 1 Control Register C		
	\$FFA7	CRB1—SSI 1 Control Register B		
	\$FFA6	CRA1—SSI 1 Control Register A		



Memory-Mapped I/O Registers


Table 3-2 Internal I/O Memory Map (Continued)

Dania basal	Douinhoual Adduses Degister Nome					
Peripheral	Address	Register Name				
Reserved	\$FFA5	Reserved				
	•					
	\$FFA0					
GPIO	\$FF9F	PCRE—GPIO Control Register				
	\$FF9E	PRRE—GPIO Direction Register				
	\$FF9D	PDRE—GPIO Data Register				
Triple	\$FF8F	TCSR0—Timer 0 Control/Status Register				
Timer	\$FF8E	TLR0—Timer 0 Load Register				
	\$FF8D	TCPR0—Timer 0 Compare Register				
	\$FF8C	TCR0—Timer 0 Count Register				
\$FF8B TCSR1—Timer 1 Control/Status Register \$FF8A TLR1—Timer 1 Load Register \$FF89 TCPR1—Timer 1 Compare Register		TCSR1—Timer 1 Control/Status Register				
		TLR1—Timer 1 Load Register				
		TCPR1—Timer 1 Compare Register				
	\$FF88	TCR1—Timer 1 Count Register				
	\$FF87	TCSR2—Timer 2 Control/Status Register				
	\$FF86	TLR2—Timer 2 Load Register				
	\$FF85	TCPR2—Timer 2 Compare Register				
	\$FF84	TCR2—Timer 2 Count Register				
	\$FF83	TPLR—Timer Prescaler Load Register				
	\$FF82	TPCR—Timer Prescaler Count Register				
Reserved	\$FF81	Reserved				
	\$FF80					





SECTION 4 CORE CONFIGURATION





4.1	INTRODUCTION	4-3
4.2	DSP56600 CORE-SPECIFIC ATTRIBUTES	4-3
4.3	BOOTSTRAP PROGRAM	4-9
4.4	CHIP OPERATING MODES	4-9
4.5	INTERRUPTS	. 4-11
4 6	PHASE LOCK LOOP.	. 4-17





Core Configuration

Introduction

4.1 INTRODUCTION

This section contains the core configuration details specific to the DSP56603, including descriptions of the reset operation, operating modes, interrupt vectors and registers, and Phase Lock Loop (PLL).

Configuration requires programming the following functional blocks:

- Core operational control
- Program patch detection
- Core and peripheral interrupts
- **Bus** control
- PLL control

After establishing control of these core functions, the peripherals can successfully be programmed. The DSP56603 peripherals and their programming specifics are described in subsequent sections of this document.

DSP56600 CORE-SPECIFIC ATTRIBUTES 4.2

The following paragraphs describe important core configuration details for the DSP56603.

Program Patch Detector JUMP Targets 4.2.1

Table 4-1 on page 4-4 lists the various JUMP targets for each of the four Patch Address Registers (PARs). The user can download the correct piece of code to the target location for the patch program to be executed properly. For more information on the Program Patch Logic, see Section 6, Program Patch Logic, in the DSP56600 Family Manual (DSP56600FM/AD).

Go to: www.freescale.com




DSP56600 Core-Specific Attributes

 Table 4-1
 Patch JUMP Targets

Patch Register	Patch JUMP Target
PAR0	\$0000
PAR1	\$0008
PAR2	\$0010
PAR3	\$0018

4.2.2 Operating Mode Register (OMR)

The Operating Mode Register (OMR) is a 16-bit read/write register that controls the operating mode of the DSP56603 and provides status flags on its operation. The OMR is partitioned into two bytes. The least significant byte of the OMR (bits 7–0) is the Chip Operating Mode (COM) byte, which determines the operating mode of the chip. The most significant byte of the OMR (bits 15–8) is the Extended Chip Operating Mode (EOM) byte, which provides operating mode control and operating mode flags. The OMR is affected only by processor reset and by instructions that directly reference it, such as the ANDI and ORI instructions, and instructions that specify OMR as a destination, such as the MOVEC instruction. The OMR is shown in **Figure 4-1**.



^{*} Indicates reserved bits, written as 0 for future compatibility

AA0716

Figure 4-1 Operating Mode Register (OMR) Programming Model

4.2.2.1 Chip Operating Mode Bits—Bits 0–3

The Chip Operating Mode bits (MD,MC, MB, and MA) indicate the operating mode of the DSP56603. On processor reset, these bits are loaded from the external mode select pins, MODD, MODC, MODB, and MODA, respectively. After the DSP56603 leaves the Reset state, MD, MC, MB, and MA can be changed under program control.



Core Configuration

DSP56600 Core-Specific Attributes

4.2.2.2 External Bus Disable (EDB)—Bit 4

The External Bus Disable (EBD) control bit is used to disable the external bus controller, in order to reduce the power consumption when external memories are not used. When the EBD bit is set, the external bus controller is disabled and external memory cannot be accessed. When the EBD bit is cleared, the external bus controller is enabled and external access to memory can be performed. The EBD bit is cleared on hardware reset.

4.2.2.3 PC Relative Logic Disable (PCD)—Bit 5

The PC Relative Disable (PCD) control bit is used when PC-relative instructions (Bcc, BRA, LRA, DO, DO FOREVER, BSR, BScc, BRSET, BRCLR, BSSET, or BSCLR) are not in use, in order to reduce the power consumption when PC-relative instructions are not needed. When the PCD bit is set, the use of any PC-relative instruction causes undetermined results. When the PCD bit is cleared, PC-relative instructions operate correctly. In addition, when the PCD bit is set and then cleared, the use of PC-relative instructions is allowed only after seven instructions are executed. (This allows the instruction pipeline to clear.) The PCD bit is cleared on hardware reset.

4.2.2.4 Stop Delay (SD)—Bit 6

The Stop Delay (SD) control bit enables providing a long or short delay when exiting the Stop state. The STOP instruction causes the DSP56600 core to indefinitely suspend processing in the middle of the STOP instruction. When the SD bit is set, a short delay of 16 clock cycles is inserted when exiting the Stop state before continuing the instruction cycle. When the SD bit is cleared, a short delay of 128 K clock cycles is inserted before continuing the instruction cycle. The long delay allows a clock stabilization period for the internal clock to begin oscillating and to stabilize. When a stable external clock is used, the shorter delay allows faster start-up of the DSP56600 core. Note that when the PSTP bit (in the PCTL1 register) is set, it overrides the SD bit and forces wake-up with no delay. The SD bit is cleared during processor reset.

4.2.2.5 XY Select for Stack Extension (XY)—Bit 8

The XY Select (XY) control bit for the stack extension determines whether the extension is mapped onto the X memory space or onto the Y memory space. When the XY bit is set, the stack extension is mapped to the Y memory space. When the XY bit is cleared, the stack extension is mapped onto the X memory space. The XY bit is cleared by hardware reset.

4.2.2.6 Extended Stack Underflow Flag (EUN)—Bit 9

The Extended Stack Underflow (EUN) flag bit is set when a stack underflow occurs in the Stack Extended mode. The Extended Stack Underflow is generated when the SP equals 0 and an additional pull operation is requested while the Extended mode is enabled by the SEN bit. The EUN bit is a "sticky bit" (i.e., the only way to clear this bit is by hardware reset or by an explicit MOVE operation to the OMR). The



DSP56600 Core-Specific Attributes

transition of the EUN bit from 0 to 1 causes an Interrupt Priority Level (IPL) Level 3 Stack Error interrupt. The EUN bit is cleared by hardware reset.

4.2.2.7 Extended Stack Overflow Flag (EOV)—Bit 10

The Extended Stack Overflow (EOV) flag bit is set when a stack overflow occurs in the Stack Extended mode. The Extended Stack Overflow is generated when SP equals SZ and an additional push operation is requested while the Extended mode is enabled by the SEN bit. The EOV bit is a "sticky bit" (i.e., the only way to clear this bit is by hardware reset or by an explicit MOVE operation to the OMR). The transition of the extended stack overflow flag from 0 to 1 causes an IPL 3 Stack Error interrupt. The EOV bit is cleared by hardware reset.

4.2.2.8 Extended Stack Wrap Flag (WR)—Bit 11

The Extended Stack Wrap (WR) flag bit is set when it is first recognized that a copy from the on-chip hardware stack to the stack extension memory is needed. This flag can be used during the debugging phase of the software as means of evaluating and increasing the speed of the software implemented algorithms. The WR bit is a "sticky bit" (i.e., the only way to clear this bit is by hardware reset or by an explicit MOVE operation to the OMR). The WR bit is cleared by hardware reset.

4.2.2.9 Extended Stack Enable (EN)—Bit 12

The Extended Stack Enable (EN) control bit is used to enable or to disable the stack extension in the data memory. When the EN bit is set, the extension is enabled. When the EN bit is cleared, the extension is disabled. The EN bit is cleared by hardware reset.

4.2.2.10 Memory Switch Mode Bit (MS)—Bit 14

The Memory Switch Mode (MS) control bit is used to enable Switch mode. When the MS bit is set, Switch mode shifts a portion of program memory to X data and Y data memory. When the MS bit is cleared, Switch mode is disabled and the default memory map is used. **Section 3, Memory Maps**, provides more information of the size of memory space that is switched. The MS bit is cleared by hardware reset.

4.2.2.11 Address Trace Enable (ATE)—Bit 15

The Address Trace Enable (ATE) bit is used for debugging purposes where internal activity should be traceable via a logic analyzer. When this bit is set, the Address Trace mode is enabled and the external address bus reflects the internal program address bus for every program fetch. When this bit is cleared, normal operation resumes and the external address bus is activated only when the program address is in the external address space. The ATE bit is cleared by hardware reset.



Core Configuration

DSP56600 Core-Specific Attributes

4.2.2.12 Reserved Bits (Bit 7, 13)

Bits 7 and 13 are reserved for future expansion. They are read as 0 and should be written with 0 for future compatibility.

4.2.3 Status Register (SR)

The Status Register (SR) is a 16-bit register that consists of an 8-bit Condition Code Register (CCR) and an 8-bit Mode Register (MR). The SR is stacked when program looping is initialized, when a JSR is performed, or when interrupts occur, except for no-overhead fast interrupts. The SR format is shown in **Figure 4-2**.




Figure 4-2 Status Register Programming Model

Understanding the interaction between the SR and the DSP56600 family instruction set is vital to understanding how to program the DSP56600 family chips. The *DSP56600 Family Manual (DSP56600FM/AD)* provides complete information on the SR. A brief description is provided in the following paragraphs.

The CCR is a special-purpose control register that defines the results of previous arithmetic computations. The CCR bits are affected by Data ALU operations, parallel move operations, and by instructions that directly reference the CCR (such as ORI and ANDI instructions) or by an instruction that specifies the SR as its destination, such as the MOVEC instruction. Parallel move operations only affect the S and L bits of the CCR. During processor reset, all CCR bits are cleared.




DSP56600 Core-Specific Attributes

The MR is a special-purpose control register that defines the current system state of the processor. The MR bits are affected by processor reset, exception processing, DO, DO FOREVER, ENDDO, BRKcc, RTI, and TRAP instructions, and by instructions that directly reference the MR (such as the ANDI and ORI instructions), or an instruction that specifies the SR as its destination, such as the MOVEC instruction. During processor reset, the interrupt mask bits of the MR are set, and all the other bits are cleared.

4.2.4 Device Identification Register (IDR)

The Device Identification Register (IDR) is a 16-bit read-only factory-programmed register used to identify the different DSP56600 core-based family members. This register specifies the derivative number and revision number. This information may be used in testing or by software. This memory-mapped register is located at \$FFF9. **Figure 4-3** shows the IDR configuration, with data filled for the DSP56603.



^{*} Indicates reserved bits, read as 0 and should be written with 0 for future compatibility

AA0717

Figure 4-3 DSP Device ID (IDR) Register for DSP56603

The Derivative Number (bits 11:0) for the DSP56603 are 011000000011. The Revision Number (bits 15:12) for the DSP56603 first silicon is 0000. The ID register value for DSP56603 first silicon is \$0603.

4.2.5 Bus Control Register (BCR)

The Bus Control Register (BCR) specifies the number of wait states provided when using the external memory bus (also known as Port A) to access external memory. The BCR allows specifying from 1 to 31 wait states. For bootstrapping, the maximum number of wait states (31) is specified by default, and can be changed under user control after bootstrapping is completed. **Section 5**, **External Memory Interface (Port A)**, provides complete details on BCR configuration.



Core Configuration

Bootstrap Program

4.3 BOOTSTRAP PROGRAM

On the DSP56603, the bootstrap program is located at P:\$0400-\$0FFF. This bootstrap program is factory-programmed and cannot be altered for customer requirements. However, a number of the bootstrap modes allow using an external location, such as an EPROM or other memory, for bootstrapping. The bootstrap program tests the MA, MB, and MC bits in the OMR to determine the bootstrap mode, and then boots from the specified port. For purposes of bootstrapping on the DSP56603, the MD bit is a "don't care" bit. For a complete listing of the bootstrap code, see **Appendix A**, **Bootstrap Program**.

4.4 CHIP OPERATING MODES

The DSP56603 operating modes determine the start-up procedure location when the chip leaves the Reset state. On processor reset, the values present on the MODA, MODB, MODC, and MODD pins are loaded into the MA, MB. MC, and MD bits of the OMR. For more information on the OMR, see **Operating Mode Register (OMR)** on page 4-4. The bootstrap code for the DSP56603 uses the reset addresses listed in **Table 4-2** to select its reset vectors and operating modes.

Table 4-2 DSP566603 Reset Addresses

Mode	MODD	MODC	MODB	MODA	Reset Vector	Description
0	0	0	0	0	P:\$8000	Expanded Mode (Unused)
1	0	0	0	1	P:\$0400	Reserved
2	0	0	1	0	P:\$0400	Bootstrap from 68338
3	0	0	1	1	P:\$0400	Bootstrap from external 24-bit slow memory
4	0	1	0	0	P:\$0400	Bootstrap from external 8-bit slow memory
5	0	1	0	1	P:\$0400	Bootstrap from ISA bus
6	0	1	1	0	P:\$0400	Bootstrap from 68HC11
7	0	1	1	1	P:\$0400	Reserved
8	1	0	0	0	P:\$8000	Expanded Mode (Unused)



Chip Operating Modes

Freescale Semiconductor, Inc.

Table 4-2 DSP566603 Reset Addresses

Mode	MODD	MODC	MODB	MODA	Reset Vector	Description
9	1	0	0	1	P:\$0400	Reserved
10	1	0	1	0	P:\$0400	Bootstrap from 68338
11	1	0	1	1	P:\$0400	Bootstrap from external 24-bit slow memory
12	1	1	0	0	P:\$0400	Bootstrap from external 8-bit slow memory
13	1	1	0	1	P:\$0400	Bootstrap from ISA bus
14	1	1	1	0	P:\$0400	Bootstrap from 68HC11
15	1	1	1	1	P:\$0400	Reserved
Note: Modes 8–15 are identical to Modes 0–7.						

The DSP56603 has a mode select pin, the MODD pin, which adds an additional eight operating modes for the DSP56603, Modes 8–15. These modes are identical to Modes 0–7. The value on the MODD pin is latched into the MD mode select bit, which functions as a "don't care" bit for mode selection.

4.4.1 Expanded Mode (Mode 0)

In Expanded mode, the DSP56603 starts to fetch instructions beginning with the address P:\$8000 from an external Static RAM (SRAM) with 31 wait states.

4.4.2 Normal Mode (Modes 1–7)

In Normal mode, the DSP56603 starts to fetch instructions beginning with the address P:\$0400 in the internal bootstrap ROM. The code programmed into the Program ROM tests MODA, MODB, and MODC bits in the OMR to determine the exact operating mode. For bootstrapping on the DSP56603, the value on the MODD pin is ignored, and the MD bit is a "don't care" bit. Following completion of bootstrapping, instructions are fetched from the location determined by the values on the MODA, MODB, and MODC pins.





Core Configuration

Interrupts

4.4.2.1 Mode 1—Reserved

This mode is reserved. If this mode is selected, the DSP56603 enters an error state and is placed in a low-power mode. Asserting $\overline{\text{RESET}}$ causes the chip to exit the error state and perform a fresh bootstrap.

4.4.2.2 Mode 2—Bootstrap from 68338

Mode 2 allows loading program instructions from an MC68338 microcontroller using the HI08.

4.4.2.3 Mode 3—Bootstrap from 24-Bit Memory

Mode 3 allows loading program instructions from external 24-bit slow memory using Port A.

4.4.2.4 Mode 4—Bootstrap from 8-Bit Memory

Mode 4 allows loading program instructions from external 8-bit slow memory using Port A.

4.4.2.5 Mode 5—Bootstrap from ISA Bus

Mode 5 allows loading program instructions from an ISA bus using the HI08.

4.4.2.6 Mode 6—Bootstrap from 68HC11

Mode 6 allows loading program instructions from an MC68HC11 microcontroller using the HI08.

4.4.2.7 Mode 7—Reserved

This mode is reserved. It allows loading the typ2 power consumption benchmark test from the internal Program ROM. For more information on this benchmark application, see the *DSP56603 Technical Data sheet (DSP56603/D)*.

4.5 INTERRUPTS

The interrupt starting address for each interrupt source is shown in **Table 4-3**. These addresses are located in the 256 locations of program memory pointed to by the VBA (Vector Base Address) register in the Program Control Unit (PCU).

On the DSP56603, only 46 of the 128 vector addresses are used for specific interrupt sources. The remaining 82 are reserved and may be used for Host Non-maskable Interrupts (NMI), Interrupt Priority Level (IPL) = 3, or for Host Command interrupt, IPL = 0-2. If it is known that certain interrupts will not be used at all, those interrupt



Interrupts

vector locations can be used for program or data storage, but this is not recommended.

 Table 4-3
 Interrupt Sources

Interrupt Starting Address	IPL	Interrupt Source			
VBA:\$00	3	Hardware RESET			
VBA:\$02	3	Stack Error			
VBA:\$04	3	Illegal Instruction			
VBA:\$06	3	Debug Request Interrupt			
VBA:\$08	3	Trap			
VBA:\$0A	3	Reserved			
VBA:\$0C	3	Reserved			
VBA:\$0E	3	Reserved			
VBA:\$10	0-2	ĪRQĀ			
VBA:\$12	0-2	ĪRQB			
VBA:\$14	0-2	ĪRQC			
VBA:\$16	0-2	ĪRQD			
VBA:\$18	0-2	Reserved			
VBA:\$1A	0-2	Reserved			
VBA:\$1C	0-2	Reserved			
VBA:\$1E	0-2	Reserved			
VBA:\$20	0-2	Reserved			
VBA:\$22	0-2	Reserved			
VBA:\$24	0–2	Timer 0 Compare			
VBA:\$26	0-2	Timer 0 Overflow			
VBA:\$28	0-2	Timer 1 Compare			
VBA:\$2A	0-2	Timer 1 Overflow			



Core Configuration

Interrupts

 Table 4-3
 Interrupt Sources (Continued)

reescale Semiconductor, Inc.

Interrupt Starting Address	IPL	Interrupt Source	
VBA:\$2C	0–2	Timer 2 Compare	
VBA:\$2E	0-2	Timer 2 Overflow	
VBA:\$30	0-2	SSI0 Receive Data	
VBA:\$32	0-2	SSI0 Receive Data With Exception Status	
VBA:\$34	0-2	SSI0 Receive Last Slot	
VBA:\$36	0-2	SSI0 Transmit Data	
VBA:\$38	0-2	SSI0 Transmit Data with Exception Status	
VBA:\$3A	0-2	SSI0 Transmit Last Slot	
VBA:\$3C	0-2	Reserved	
VBA:\$3E	0-2	Reserved	
VBA:\$40	0-2	SSI1 Receive Data	
VBA:\$42	0-2	SSI1 Receive Data With Exception Status	
VBA:\$44	0-2	SSI1 Receive Last Slot	
VBA:\$46	0-2	SSI1 Transmit Data	
VBA:\$48	0-2	SSI1 Transmit Data with Exception Status	
VBA:\$4A	0-2	SSI0 Transmit Last Slot	
VBA:\$4C	0-2	Reserved	
VBA:\$4E	0–2	Reserved	
VBA:\$60	0-2	Host Receive Data Full	
VBA:\$62	0–2	Host Transmit Data Empty	
VBA:\$64	0-2	Default Host Command	
VBA:\$66	0–2	Reserved	



Interrupts


Table 4-3 Interrupt Sources (Continued)

Interrupt Starting Address	IPL	Interrupt Source
	•	
	•	
•	•	·
VBA:\$FE		Reserved

Note: Any interrupt starting address (including reserved addresses) can be used for Host command interrupt (IPL 0–2).

4.5.1 Interrupt Priority Levels

The DSP56603 provides two Interrupt Priority Registers, IPR-C and IPR-P. The IPR-C is dedicated for DSP56600 core interrupt sources. The IPR-P is dedicated for peripheral interrupt sources. The IPR-C and IPR-P are shown in **Figure 4-4**. **Table 4-4** and **Table 4-5** define the IPL bits in these registers.



^{*} Indicates reserved bits, read as 0 and should be written with 0 for future compatibility

AA0711

Figure 4-4 Interrupt Priority Registers IPR-C and IPR-P



Interrupts

Core Configuration

Table 4-4 Interrupt Priority Level Bits

IPL Bits		Interrupts	Interrupt
xxL1	xxL0	Enabled	Priority Level
0	0	No	_
0	1	Yes	0
1	0	Yes	1
1	1	Yes	2

Table 4-5 External Interrupt Trigger Mode Bits

IxL2	Trigger Mode
0	Level
1	Negative Edge

4.5.2 **Interrupt Sources Priorities within an IPL**

If more than one interrupt request is pending when an instruction is executed, the interrupt source with the highest priority level is serviced first. When multiple interrupt requests having the same IPL are pending, a second fixed-priority structure within that IPL determines the order in which each interrupt source is serviced. The fixed priority of interrupt sources within an IPL is shown in Table 4-6.

Table 4-6 Interrupt Source Priorities within an IPL

Priority	Interrupt Source						
Level 3 (Non-Maskable)							
Highest	Hardware RESET						
	Stack Error						
	Illegal Instruction						
	Debug Request Interrupt						
Lowest	Trap						



Interrupts

Freescale Semiconductor, Inc.

 Table 4-6
 Interrupt Source Priorities within an IPL (Continued)

Priority	Interrupt Source						
Levels 0, 1, 2 (Maskable)							
Highest	IRQA (External Interrupt)						
	IRQB (External Interrupt)						
	IRQC (External Interrupt)						
	Host Command Interrupt						
	Host Transmit Data Full						
	Host Receive Data Empty						
	SSI0 RX Data with Exception Interrupt						
	SSI0 RX Data Interrupt						
	SSI0 Receive Last Slot Interrupt						
	SSI0 TX Data with Exception Interrupt						
	SSI0 Transmit Last Slot Interrupt						
	SSI0 TX Data Interrupt						
	SSI1 RX Data with Exception Interrupt						
	SSI1 RX Data Interrupt						
	SSI1 Receive Last Slot Interrupt						
	SSI1 TX Data with Exception Interrupt						
	SSI1 Transmit Last Slot Interrupt						
	SSI1 TX Data Interrupt						
	Timer 0 Overflow Interrupt						
	Timer 0 Compare Interrupt						
	Timer 1 Overflow Interrupt						
	Timer 1 Compare Interrupt						
	Timer 2 Overflow Interrupt						
Lowest	Timer 2 Compare Interrupt						



Phase Lock Loop

Core Configuration

4.6 PHASE LOCK LOOP

The Phase Lock Loop (PLL) allows the processor to operate at a high internal clock frequency using a low frequency clock input, a feature that offers two immediate benefits:

- Lower frequency clock input reduces the overall electromagnetic interference generated by a system.
- The ability to oscillate at different frequencies reduces costs by eliminating the need to add additional oscillators to a system.

For more information on the PLL, see Section 8, PLL and Clock Generator, in the DSP56600 Family Manual (DSP56600FM/AD).

PLL Control Register 0 (PCTL0) 4.6.1

The PLL Control Register 0 (PCTL0) is an X I/O-mapped 16-bit read/write register used to direct the operation of the on-chip PLL. Figure 4-5 shows the programming model for the PCTL0 register.

PCTL0—X:\$FFFD	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
PLL Control	PD	PD	PD	PD	MF											
Register 0	3	2	1	0	11	10	9	8	7	6	5	4	3	2	1	0
Reset = \$0000													ш			ш
Read/Write																

^{*} Indicates reserved bits, read as 0 and should be written with 0 for future compatibility AA0713

Figure 4-5 PLL Control Register 0 (PCTL0) Programming Model

4.6.1.1 Multiplication Factor Bits (MF0-MF11)—Bits 0-11

The Multiplication Factor bits (MF0–MF11) define the Multiplication Factor (MF) that is applied to the PLL input frequency. The MF0-MF11 bits are cleared during hardware reset, which corresponds to an MF of 1. **Table 4-7** shows how to program the MF0-MF11 bits.



Phase Lock Loop

Freescale Semiconductor, Inc.

 Table 4-7
 Multiplication Factor Bits MF0-MF11

MF[11:0]	Multiplication Factor (MF)
\$000	1
\$001	2
\$002	3
•	
•	•
•	•
\$FFE	4095
\$FFF	4096

4.6.1.2 Predivider Factor Bits PD0-PD3—Bits 12-15

The Predivider Factor bits (PD0–PD3) in the PCTL0 register are combined with the PD4–PD6 bits in the PCTL1 register to define the Predivider Factor (PDF) that is applied to the PLL input frequency. The PD0–PD6 bits are cleared during hardware reset, which corresponds to a PDF of 1.

4.6.2 PLL Control Register 1 (PCTL1)

The PLL Control Register 1 (PCTL1) is an X I/O-mapped 16-bit read/write register that gives additional control functions for the PLL. **Figure 4-6** shows the programming model for the PCTL1 register.

PCTL1—X:\$FFFD	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
PLL Control					PD	PD	PD		COD	PEN	PS	XT	ХТ	DF	DF	DF
Register 1	*	*	*	*	6	5	4	*			TP	LD	LR	2	1	0
Reset = \$0000 l		<u> </u>					<u> </u>	<u> </u>					<u> </u>	<u> </u>		
Read/Write																

^{*} Indicates reserved bits, read as 0 and should be written with 0 for future compatibility

AA0714

Figure 4-6 PLL Control Register 1 (PCTL1) Programming Model



Phase Lock Loop

Core Configuration

4.6.2.1 Division Factor Bits (DF2-DF0)—Bits 0-2

The Division Factor bits (DF2–DF0) define the Division Factor (DF) of the low power divider. These bits specify any power-of-two Division Factor in the range from 2^0 to 2⁷. **Table 4-8** shows the programming of the DF bits. Changing the value of the DF bits does not cause a loss of lock condition. Whenever possible, changes of the operating frequency of the chip (e.g., to enter a low power mode) should be made by changing the value of the DF2-DF0 bits, rather than by changing the MF0-MF11 bits.

The DF2-DF0 bits are cleared by hardware reset, setting the DF to divide by 1.

DF[2:0]	Division Factor DF
000	20
001	21
010	2 ²
011	2 ³
100	2 ⁴
101	2 ⁵
110	26
111	27

Table 4-8 Division Factor Bits

4.6.2.2 Crystal Range Bit (XTLR)—Bit 3

The Crystal Range (XTLR) bit controls the on-chip crystal oscillator transconductance. If the external crystal frequency is less than 200 kHz, this bit should be set in order to decrease the transconductance of the input amplifier, otherwise the internal clocks may not be stable. If the external crystal frequency is greater than 200 kHz, this bit should be cleared in order to have the full transconductance, otherwise the crystal oscillator may not function at all. Changing the XTLR bit while the PLL is active causes a loss of PLL lock and a reinitialization of the lock process. The XTLR bit is cleared during hardware reset.

4.6.2.3 Crystal Disable Bit (XTLD)—Bit 4

The XTAL Disable (XTLD) bit controls the on-chip crystal oscillator XTAL output. When the XTLD bit is set, the on-chip oscillator output is disabled. When the XTLD bit is cleared, the on-chip crystal oscillator output can be used. The XTLD bit is set during hardware reset.



Phase Lock Loop

4.6.2.4 Stop Processing State Bit (PSTP)–Bit 5

The Stop Processing State (PSTP) bit controls the behavior of the PLL and of the on-chip crystal oscillator during the Stop processing state. When the PSTP bit is set, the PLL and the on-chip crystal oscillator remain operating while the chip is in the Stop state. When the PSTP bit is cleared, the PLL and the on-chip crystal oscillator are disabled when the chip enters the Stop state. For minimum power consumption during the Stop state at the cost of longer recovery time, the PSTP bit should be cleared. To enable rapid recovery when exiting the Stop state, at the cost of higher power consumption, the PSTP bit should be set. The PSTP bit is cleared by hardware reset.

4.6.2.5 PLL Enable Bit (PEN)—Bit 6

The PLL Enable (PEN) bit enables the PLL operation. When the PEN bit is set, the PLL is enabled and the internal clocks are derived from the PLL VCO output. When the PEN bit is cleared, the PLL is disabled and the internal clocks are derived directly from the clock connected to the EXTAL pin. When the PLL is disabled, the VCO is not operating. This helps minimize power consumption. The PEN bit can be set or cleared by software any time during the chip operation. During hardware reset, this bit receives the value of the PLL's PINIT pin.

4.6.2.6 Clock Output Disable Bit (COD)—Bit 7

The Clock Output Disable (COD) bit controls the output buffer of the clock at the CLKOUT pin. When the COD bit is set, the CLKOUT pin is held high. When the COD bit is cleared, the CLKOUT pin is acctive, providing a 50% duty cycle clock synchronized to the internal core clock. If the CLKOUT pin is not connected to external circuits, the COD bit should be set, disabling clock output and minimizing RFI noise and power dissipation. CLKOUT oscillates in all operating states except the Stop state. The COD bit is cleared by hardware reset.

4.6.2.7 Predivider Factor Bits PD4–PD6—Bits 9–11

The Predivider Factor bits PD4–PD6 are used with the PD0–PD3 bits in the PCTL0 register to define the PDF that is applied to the PLL input frequency.


4.6.2.8 Reserved Bits 8, 12–15

These bits are reserved and are read as 0. They should be written with 0 to ensure future compatibility.





SECTION 5 EXTERNAL MEMORY INTERFACE (PORT A)





External Memory Interface (Port A)

5.1	INTRODUCTION	5-3
5.2	EXPANSION PORT SIGNAL DESCRIPTION	5-3
5.3	EXPANSION PORT OPERATION	5-4
5.4	PORT A CONTROL AND DATA TRANSFER	5-7
5.5	PROGRAM ADDRESS TRACING MODE	5-11

External Memory Interface (Port A)

Introduction

5.1 INTRODUCTION

This section describes the External Memory Interface, also referred to as Port A, and describes some of the memory transfer and trace modes associated with this interface. Port A is used for program and data memory expansion. It provides an easy to use, low part-count connection with fast or slow static memories and with I/O devices.

Port A provides a 24-bit data bus and a 16-bit address bus capable of a sustained rate of one memory access per 2 clock cycles. External memory can be as large as $64~\mathrm{K} \times 24$ -bit program memory space, depending on chip configuration. An internal wait state generator can be programmed to insert as many as 31 wait states if access to slower memory or I/O device is required.

5.2 EXPANSION PORT SIGNAL DESCRIPTION

Port A provides the following pins on the DSP56603.

5.2.1 Address Bus—A0–A15

These active high outputs specify the address for external program memory accesses. To minimize power dissipation, A0–A15 do not change state when external memory spaces are not being accessed. A0–A15 are pulled high during hardware reset.

5.2.2 Data Bus—D0–D23

These active high, bidirectional input/outputs provide the data bus for external program memory accesses. D0–D23 are tri-stated when no external bus activity occurs, and during hardware reset.

5.2.3 Memory Chip Select—MCS

The Memory Chip Select (\overline{MCS}) signal is an active low output, and is asserted when an external memory access occurs. \overline{MCS} is deasserted during hardware reset.



External Memory Interface (Port A)

Expansion Port Operation

5.2.4 Read Enable—RD

The Read Enable (\overline{RD}) signal is an active low output. \overline{RD} is asserted to read external memory on the data bus (D0–D23). \overline{RD} is deasserted during hardware reset.

5.2.5 Write Enable—WR

The Write Enable (\overline{WR}) signal is an active low output. \overline{WR} is asserted to write external memory on the data bus (D0–D23). \overline{WR} is deasserted during hardware reset.

5.2.6 Address Trace—AT

The Address Trace (\overline{AT}) signal is an active low output. \overline{AT} is asserted (for half of a clock cycle) whenever a new address is driven on the address bus (A0-A15) in the Program Address Tracing mode. The new address is either a reflection of internal fetch or internal program space move instruction or an external address driven for an external access. \overline{AT} is deasserted during hardware reset.

5.3 EXPANSION PORT OPERATION

The external bus timing is defined by the operation of the Address Bus, Data Bus, and Bus Control pins. The DSP56600 core external ports are designed to interface with high-speed Static RAM (SRAM) and peripheral devices with SRAM-based timing, as well as with slower memory devices.

5.3.1 Static RAM Support

External bus timing is controlled by the Bus Control Register (BCR). Insertion of wait states is controlled by the BCR to provide constant bus access timing. The number of wait states for each external access is determined by the BCR.

The external memory address is defined by the address bus. The Memory Chip Select signal \overline{MCS} is used to generate a chip select signal for the external memory device. This chip select signal changes the mode of the memory device from low power Standby mode to Active mode and begins the access. This allows slower memories to be used, since the \overline{MCS} signal is address-based rather than read or write



External Memory Interface (Port A)

Expansion Port Operation

AA0719

enable-based. SRAMs can be easily interfaced to the DSP56600 core bus timing. Because of the SRAM requirement to keep the address stable during the entire bus cycle, at least 1 wait state must be inserted to the bus operation. **Figure 5-1** shows a possible SRAM configuration for the DSP56603.




Figure 5-1 Static RAM Connection Diagram

Write Access

- 1. A0-A15 and \overline{MCS} are asserted in the middle of CLKOUT low phase.
- 2. \overline{WR} is asserted with the rising edge of CLKOUT (for a single wait state access).
- 3. Data is driven in the middle of CLKOUT low phase.

An SRAM access is performed in one of the following ways:

Read Access

- 1. A0–A15 and \overline{MCS} are asserted in the middle of CLKOUT low phase.
- 2. $\overline{\text{RD}}$ is asserted with the rising edge of CLKOUT.
- 3. Data is sampled in the middle of CLKOUT last high phase of the external access.

Wait states postpone the disappearance of the external address, thereby increasing memory access time. In any case, SRAM access requires at least 1 wait state. **Figure 5-2** shows the memory bus operation using 1 wait state. For detailed timing specifications, see the *DSP56603 Technical Data Sheet (DSP56603/D*).

Go to: www.freescale.com



External Memory Interface (Port A)

Expansion Port Operation




Figure 5-2 Bus Operation, One Wait State—SRAM Access

Note:

The assertion of the \overline{WR} signal depends on the number of wait states programmed in the BCR. If a single wait state is programmed in the BCR, the \overline{WR} signal is asserted with the rising edge of CLKOUT. If the number of wait states programmed is 2 or 3, \overline{WR} assertion is delayed by half cycle of CLKOUT. If the number of wait states programmed is four or more, \overline{WR} assertion is delayed by a full cycle of CLKOUT. This feature enables the connection of slow external devices that require long address setup time before write assertion in order to prevent false write.



External Memory Interface (Port A)

Port A Control and Data Transfer

5.3.2 Expansion Port Disable

Because the DSP56603 provides internal memory, not all applications will require using Port A. In this case, Port A can be disabled completely by the user, resulting in a significant reduction in power consumption.


Port A can be disabled by setting the EBD bit in the Operating Mode Register (OMR). When this bit is set, the Port A controller is disabled. External memory should not be accessed, otherwise improper operation may result.

5.4 PORT A CONTROL AND DATA TRANSFER

Two registers are used by Port A for control and program memory data transfer. The Bus Control Register (BCR), provides control functions for Port A. The Bus Switch Program Memory Register (BPMR) gives data transfer, and provides a special function that allows the use of 24-bit program memory accesses.

5.4.1 Bus Control Register (BCR)

Port A control is provided by the Bus Control Register (BCR). The BCR is a 16-bit read/write register used to control the external bus activity and Bus Interface Unit operation. **Figure 5-3** shows the BCR programming model.



^{*} Indicates reserved bits, read as 0 and should be written with 0 for future compatibility

AA0720

Figure 5-3 Bus Control Register Programming Model

5.4.1.1 Expansion Bus Memory Wait—Bits 0–4

The Expansion Bus Memory Wait (BMW0–BWM4) control bits define the number of wait states inserted in each external SRAM access. The range of programmable wait states is from 0 to 31. These bits should not all be cleared, because SRAM memory access requires at least one wait state.



External Memory Interface (Port A)

Port A Control and Data Transfer

When selecting 4 to 7 wait states, one additional wait state is inserted at the end of the access. When selecting 8 or more wait states, two additional wait states are inserted at the end of the access. These trailing wait states increase the data hold time and the memory release time and do not increase the memory access time.

The BMW bits are set to b11111 (\$001F) during hardware reset, providing the maximum value of 31 wait states.

5.4.1.2 Reserved Bits—Bits 5–15

Bits 5 through 15 in the BCR are reserved. These bits should be written as 0 to ensure future compatibility.

5.4.2 Bus Switch Program Memory Register (BPMR)

The Bus Switch Program Memory Register (BPMR) is a 24-bit X I/O-mapped read/write register. An access to the BPMR can be either a 24-bit access or a 16-bit access. The BPMR is mapped as a 24-bit register in address BPMRG and as a pair of 16-bit registers designated as BPMR Low (BPMRL) and BPMR High (BPMRH).

The internal and external program memories consist of 24-bit wide words. The access to a program memory word is required in any instruction fetch and in program memory move instructions. In the latter case, the BPMR is used to interface between the internal and external program memory spaces and the rest of the DSP56600 core, which mostly consists of 16-bit components. Each move from a 16-bit source to a 24-bit destination is extended by the eight lower bits of the BPMRH. Each move from a 24-bit source to a 16-bit destination truncates the 24-bit source and moves only its sixteen Least Significant Bits (LSBs). Using the BPMR is the only way to access the eight Most Significant Bits (MSBs) of any program memory address, external or internal, which is essential for many applications.

For example, when using a system configuration operating mode, a hardware reset causes the DSP56600 core to jump to the mask-programmed internal program memory location and execute the code fetched from this location. This code usually includes a set of program memory move instructions that load the program code to the required destination and then execute it. Access to the eight MSBs of each 24-bit program word is available only by using the BPMR.

5.4.2.1 BPMR Mapping

The BPMR is mapped as a 24-bit register in address BPMRG and as a pair of 16-bit registers in addresses x:BPMRL and x:BPMRH, respectively. The top eight bits of the BPMRH are reserved. **Figure 5-4** shows the BPMRL, BPMRH, and BPMRG registers.





External Memory Interface (Port A)

Port A Control and Data Transfer




Figure 5-4 BPMR Register

5.4.2.2 24-bit Access to BPMR

A 24-bit access to BPMR is done by move instruction between the BPMR and any program memory word, as shown in **Example 5-1**.

Example 5-1 Move from P Source Address to P Destination Address

; move from P	source address	s to P destination address
BPMRG	equ	\$FFF4
	movep	p:(r0), x:BPMRG
	movep	x:BPMRG, p:\$5

5.4.2.3 16-bit Access to BPMR

A 16-bit access to the BPMR is done either to its sixteen LSBs, which are mapped to the BPMRL, or to its eight MSBs, which are mapped to the BPMRH. In both cases it is not treated as a special access but as a regular 16-bit X I/O access. Reading the BPMRH clears the sixteen MSBs of the 24-bit destination or the eight MSBs of the 16-bit destination, depending on the destination's width.

5.4.2.4 BPMR Usage Typical Examples

A typical usage of the BPMR is for bootstrapping through External EPROM or through the HI08 interface. The following code, when loaded to an External EPROM hardware reset location can load any required Program RAM segment. **Example 5-2** shows the part of it that uses the BPMR.

Example 5-2 Bootstrap through External EPROM

BPMRG	equ	\$FFF4
BPMRL	equ	\$FFF3



External Memory Interface (Port A)

Port A Control and Data Transfer

Example 5-2 Bootstrap through External EPROM

```
BPMRH
                   $FFF2
             equ
; This is part of the routine that loads from external EPROM.
; The external EPROM is 8 bit wide.
      do #2,_LOOP1
                                ; Read the 16 LSB part of the instruction.
      movem p:(r2)+,a2
                                ; Get the 8 LSB from ext. P mem.
      asr #8,a,a
                                ; Shift 8 bit data into Al.
LOOP1
                                ; Go get another byte.
      movep al,x:BPMRL
                                ; Store the 16 LSB part in BPMRL.
      movep p:(r2)+,x:BPMRH
                                ; Get the 8 MSB part and store it in BPMRH.
      movep x:BPMRG,p:(r0)+
                                ; Store 24 Bit result in P mem.
```

A common debugging process requires the content of a segment of program memory code to be delivered to the external command controller. This information should be passed through the OnCE Global Data Bus (OGDB) register. The only way to pass the eight MSBs of each 24-bit program word to the OGDB register is to use the BPMR. **Example 5-3** shows how the OGDB register is loaded by a 24-bit program memory word. For more information on using the OnCE functionality, see **Section 10**, **On-Chip Emulation Module**.

Example 5-3 Pass Program Memory Words to the OGDB Register

BPMRG	equ	\$FFF4	
BPMRL	equ	\$FFF3	
BPMRH	equ	\$FFF2	
OGDB	equ	\$FFFB	
;=======	======	=========	=======================================
move	p:(r2)+	-,x:BPMRG	; Read the 24 bit data and store in BPMR.
move	x:BPMRI	,x0	; Store the 16 LSB part in x0.
move	x0,x:00	GDB	; Pass the 16 LSB part to OGDB.
move	movep x:BPMRH,y0		; Store the 8 MSB part in y0.
move	movep y0,x:OGDB		; Pass the 8 MSB part to OGDB.



External Memory Interface (Port A)

Program Address Tracing Mode

5.5 PROGRAM ADDRESS TRACING MODE

The Address Tracing (AT) mode provides a means of software development in addition to the On-Chip Emulation (OnCE) circuitry. Section 10, On-Chip Emulation Module, provides more information. When the AT mode is enabled by setting the ATE bit in the OMR, the DSP56600 core reflects the addresses of internal fetches and program space moves (MOVEM) to the Address Bus (A0–A15), if the Address Bus is not needed by the DSP56600 core for external accesses. When an AT cycle is performed (e.g., as an internal access reflected to the Address Bus), the $\overline{\text{RD}}$ and $\overline{\text{WR}}$ strobes and the $\overline{\text{MCS}}$ signal are not asserted. This assures that no external device is erroneously activated. The $\overline{\text{AT}}$ signal indicates that a new address is on the Address Bus, either of an AT cycle or of an external access. The user can sample the Address Bus and the $\overline{\text{MCS}}$ signal with the falling edge of the $\overline{\text{AT}}$ signal and sort between the AT cycles and the external accesses according to the sampled value of $\overline{\text{MCS}}$.

Note:

The trace capability of the AT mechanism differs from the OnCE trace buffer capability. The AT mechanism provides information on fetches, not on program flow. For example, in the AT mechanism, fetches for a jump that is not taken are sampled, although the program flow has not gone that way. Any software that interprets this information must take such aspects into account to function properly.

Figure 5-5 shows a possible configuration. For detailed timing information, see the *DSP56603 Technical Data (DSP56603/D)*.



External Memory Interface (Port A)

Program Address Tracing Mode





Figure 5-5 Possible Address Tracing Configuration Diagram





SECTION 6 GPIO





6.1	INTRODUCTION	6-3
6.2	GPIO CONFIGURATION	6-3
6.3	PORT CONTROL REGISTER (PCR)	6-5
6.4	PORT DIRECTION REGISTER (PRR)	6-5
6.5	PORT DATA REGISTER (PDR)	6-6



Introduction

6.1 INTRODUCTION

The General Purpose I/O (GPIO) port consists of three bidirectional pins, each pin separately controlled. Functionality is controlled by the following three registers:

- Port Control Register (PCR)
- Port Direction Control Register (PRR)
- Port Data Register (PDR)

These registers are described in this section.

6.2 GPIO CONFIGURATION

The dedicated GPIO port on the DSP56603 supports three bidirectional pins. GPIO functionality is also available on some of the HI08, SSI, and timer pins when these pins are not otherwise being used by their peripherals. The following registers are provided for control of the three dedicated GPIO pins:

- PCR—GPIO Port Control Register
- PRR— GPIO Port Direction Control Register
- PDR—GPIO Port Data Register

On the peripherals that can be configured for GPIO, the following registers are used:

- HI08 (Port B)
 - HPCR—Host Port Control Register
 - HDDR—Host Data Direction Register
 - HDR—Host Data Register
- SSI (Ports C and D)
 - PCRC—GPIO Port C Control Register (GPIO on SSI0)
 - PRRC— GPIO Port C Direction Control Register (GPIO on SSI0)
 - PDRC—GPIO Port C Data Register (GPIO on SSI0)
 - PCRD—GPIO Port D Control Register (GPIO on SSI1)
 - PRRD— GPIO Port D Direction Control Register (GPIO on SSI1)
 - PDRD—GPIO Port D Data Register (GPIO on SSI1)




GPIO Configuration

- Timer (Port E)
 - TCSR0—Timer Control/Status Register (GPIO on the TIO0 pin)
 - TCSR1—Timer Control/Status Register (GPIO on the TIO1 pin)
 - TCSR2—Timer Control/Status Register (GPIO on the TIO2 pin)

These registers are discussed in more detail in their respective sections.

The dedicated GPIO programming model is shown in **Figure 6-1**.



^{*} Indicates reserved bits, read as 0 and should be written with 0 for future compatibility

AA0701

Figure 6-1 GPIO Programming Model





GPIO

Port Control Register (PCR)

6.3 PORT CONTROL REGISTER (PCR)

The 16-bit read/write Port Control Register (PCR) controls the functionality of GPIO pins. Each of the PC bits controls the functionality of the corresponding port pin. When a PC bit is set, the corresponding port pin is tri-stated or GPIO output with open drain defined by the direction control bit. When a PC bit is cleared, the corresponding port pin is configured as GPIO pin.

Although the PCR has sixteen bits, only the bottom three bits are used. Hardware and software reset clear all PCR bits.

6.4 PORT DIRECTION REGISTER (PRR)

The 16-bit read/write Port Direction Register (PRR) controls the direction of GPIO pins. When a port pin is configured as GPIO (its corresponding PC bit in the PCR is cleared), the PDC bit controls the port pin direction. When the PDC bit is set, its corresponding GPIO port pin is configured as output. When the PDC bit is cleared, the GPIO port pin is configured as input.

When the PC bit is set and the PDC bit is cleared, the corresponding port pin is tri-stated. When both the PC bit and the PDC bit are set, the corresponding port pin is configured for open-drain GPIO output. Although the PRR has sixteen bits, only the bottom three bits are used. Hardware and software reset clear all PRR bits.

The following table describes the port pin configurations.

Table 6-1 PCR and PRR Bits Functionality

PC Bit	PDC Bit	Port Pin Function
0	0	GPIO Input
0	1	GPIO Output
1	0	tri-stated
1	1	GPIO Output as open drain



Port Data Register (PDR)


6.5 PORT DATA REGISTER (PDR)

The 16-bit read/write Port Data Register (PDR) is used to read or write data to and from GPIO pins. The PD bits are used to read or write data from and to the corresponding port pins if they are configured as GPIO (by the PC bits in the PCR register). If a port pin is configured as a GPIO input, then the corresponding PD bit reflects the value present on this pin. If a port pin is configured as a GPIO output, then the value written into the corresponding PD bit is reflected on the this pin.





SECTION 7 HOST INTERFACE (HI08)





7.1	INTRODUCTION
7.2	INTERFACE 7-3
	HI08 HOST PORT7-6
7.4	HOST INTERFACE—DSP PROGRAMMER'S MODEL 7-8
7.5	HI08—EXTERNAL HOST PROGRAMMER'S MODEL 7-21
7.6	GENERAL PURPOSE I/O



Host Interface (HI08)

Introduction

7.1 INTRODUCTION

The Host Interface (HI08) is a byte-wide, full-duplex, double-buffered, parallel port that can be connected directly to the data bus of a host processor. The HI08 supports a variety of buses, and provides connection with a number of industry-standard DSPs, microcomputers, and microprocessors without requiring any additional logic.

Because the host bus can operate asynchronously to the DSP core clock, the HI08 registers are divided into two banks. The Host side bank is accessible to the external host, and the DSP side bank is accessible to the DSP core.

The HI08 supports two classes of interfaces:

- Host processor/MCU connection interface
- General Purpose Input/Output (GPIO) port

Unused HI08 port pins can be configured as GPIO pins.

7.2 INTERFACE

The following section describes the HI08 interface from the DSP side and from the host side.

DSP Side 7.2.1

- Eight internal X I/O-mapped locations
- 16-bit data word
- **Transfer modes**
 - DSP to host
 - Host to DSP
 - Host command
- Handshaking protocols
 - Software polled
 - Interrupt driven
 - Core DMA accesses



Interface

- Instructions
 - Memory-mapped registers allow the standard MOVE instruction to be used.
 - Special MOVEP instruction provides for I/O service capability using fast interrupts.
 - Bit addressing instructions (e.g., BCHG, BCLR, BSET, BTST, JCLR, JSET, JSSET) simplify I/O service routines.

7.2.2 Host Side

- Signals (16 pins)
 - HAD[7:0] Host HD7-HD0 data bus or Host multiplexed Address/Data bus HAD0-HAD7
 - HAS/HA0 Address Strobe (HAS) or Host Address line HA0
 - HA8/HA1 Host Address line HA8 or Host Address line HA1
 - HA9/HA2 Host Address line HA9 or Host Address line HA2
 - HRW/HRD Read Write select (HRW) or Read strobe (HRD)
 - HDS/HWR Data Strobe (HDS) or Write strobe (HWR)
 - HCS/HA10 Host Chip Select (HCS) or Host Address line HA10
 - HREQ/HTRQ Host Request (HREQ) or Host Transmit Request (HTRQ)
 - HACK/HRRQ Host Acknowledge (HACK) or Host Receive Request (HRRQ)
- Mapping
 - Consecutive byte locations
 - Memory or I/O-mapped peripheral for microprocessors, microcontrollers, etc.
- 8-bit data word
- Transfer modes
 - Mixed 8- and 16-bit data transfers
 - DSP to host
 - Host to DSP





Host Interface (HI08)

Interface

- Host Command
- Handshaking protocols
 - Software polled
 - Interrupt-driven
- Dedicated interrupts
 - Separate interrupt lines for each interrupt source
 - Special host commands force DSP core interrupts under host processor control, which are useful for:
 - Realtime production diagnostics
 - · Debugging window for program development
 - Host control protocols
- Interface Capabilities
 - Interface with no additional logic to:
 - Motorola HC11
 - Hitachi H8
 - 8051 family
 - Thomson P6 family.
 - Interface with minimal additional logic to:
 - ISA bus
 - Motorola 68K family
 - Intel X86 family



HI08 Host Port

7.3 HI08 HOST PORT

This section provides a brief description of the HI08 pins and their functions. In addition to HI08 functionality, every HI08 pin can be programmed as a GPIO pin when not used for HI08.

 Table 7-1
 Summary of HI08 Pins and Operating Modes

HI08 Port Pin	Multiplexed Address/data bus Mode	Non Multiplexed Bus Mode	GPIO Mode
HAD0-HAD7	HAD0-HAD7	HD0-HD7	PB0-PB7
HA0/ HAS	HAS/ HAS	HA0	PB8
HA1/HA8-HA2/HA9	HA8-HA9	HA1-HA2	PB9-PB10
HCS/HA10	HA10	HCS/ HCS	PB13

Table 7-2 Strobe Signals Support Pins

HI08 Port Pin	Single Strobe Bus	Dual Strobe Bus	GPIO Mode
HRW/ HRD	HRW	HRD	PB11
HDS/HWR	HDS/ HDS	HWR	PB12

 Table 7-3
 Host Request Support Pins

HI08 Port Pin	Vector Required	No Vector Required	GPIO Mode
HREQ/HTRQ	HREQ/ HREQ	HTRQ/ HTRQ	PB14
HACK/HRRQ	HACK/ HACK	HRRQ/HRRQ	PB15





HI08 Host Port




Figure 7-1 HI08 Block Diagram

Figure 7-1 shows the registers in the HI08. The top row of registers (HCR, HSR, HDDR, HDR, HBAR, HPCR, HTX, and HRX) can be accessed the DSP core, and the bottom row of registers (ISR, ICR, CVR, IVR, RXH, RXL, TXH, and TXL) can be accessed by the host processor.

AA0722



Host Interface—DSP Programmer's Model

7.4 HOST INTERFACE—DSP PROGRAMMER'S MODEL

The DSP56600 core views the HI08 as a memory-mapped peripheral occupying eight 16-bit words in data memory space. The DSP can use the HI08 as a normal memory-mapped peripheral, using either standard polled or interrupt programming techniques. Separate transmit and receive data registers are double-buffered to allow the DSP and host processor to efficiently transfer data at high speed. Memory mapping allows DSP core communication with the HI08 registers to be accomplished using standard instructions and addressing modes. In addition, the MOVEP instruction allows HI08-to-memory and memory-to-HI08 data transfers without going through an intermediate register. Both hardware and software reset disable the HI08 and change the HI08 to GPIO with all pins disconnected.

The HI08 provides the following registers:

- HCR—HI08 Control Register
- HSR—HI08 Status Register
- HTX—HI08 Data Transmit Register
- HRX—HI08 Data Receive Register
- HBAR—HI08 Base Address Register
- HPCR—HI08 Port Control Register
- HDDR—HI08 GPIO Data Direction Register
- HDR—HI08 GPIO Data Register

These registers can be accessed by the DSP core. They cannot be accessed by the external host.

7.4.1 HI08 Control Register (HCR)

The HI08 Control Register (HCR) is 16-bit read/write control register used by the DSP core to control the HI08 operating mode. Reserved bits are read as 0 and should be written with 0 to ensure future compatibility. **Figure 7-2** shows the programming model of the HCR. The initialization values for the HCR bits are described in **DSP Side Registers After Reset** on page 7-19. The HCR bits are described in the following paragraphs.



Host Interface (HI08)

Host Interface—DSP Programmer's Model

HCR—X:\$FFC2	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
Host Control Register	*	*	*	*	*	*	*	*	*	*	*	HF3	HF2	HCIE	HTIE	HRIE
Reset = \$0000 ^t Read/Write							•					•				

^{*} Indicates reserved bits, read as 0 and should be written with 0 for future compatibility

AA0723

Figure 7-2 Host Control Register Programming Model

7.4.1.1 Host Receive Interrupt Enable (HRIE)—Bit 0

The Host Receive Interrupt Enable (HRIE) bit is used to enable a DSP core interrupt when the Host Receive Data Full (HRDF) status bit in the Host Status Register (HSR) is set. When the HRIE bit is cleared, HRDF interrupts are disabled. When the HRIE bit is set, a Host Receive Data Interrupt request occurs if the HRDF bit is also set. The HRIE bit is cleared on hardware reset.

7.4.1.2 Host Transmit Interrupt Enable (HTIE)—Bit 1

The Host Transmit Interrupt Enable (HTIE) bit is used to enable a DSP core interrupt when the Host Transmit Data Empty (HTDE) status bit in the HSR is set. When the HTIE bit is cleared, HTDE interrupts are disabled. When the HTIE bit is set, a Host Transmit Data Interrupt request occurs when the HTDE bit is set. The HTIE bit is cleared on hardware reset.

7.4.1.3 Host Command Interrupt Enable (HCIE)—Bit 2

The Host Command Interrupt Enable (HCIE) bit is used to enable a DSP core interrupt when the HCP status bit in the HSR is set. When the HCIE bit is cleared, HCP interrupts are disabled. When the HCIE bit is set, a Host Command Interrupt request occurs if HCP is set. The interrupt address is determined by the host Command Vector Register (CVR). The HCIE cleared is set on hardware reset.

Note: Host interrupt request priorities: If more than one interrupt request source is asserted and enabled (e.g., HRDF = 1, HCP = 1, HRIE = 1, and HCIE = 1), the HI08 generates interrupt requests according to **Table 7-4**.

Table 7-4 HI08 Interrupt Request Priority Order

Priority	Interrupt Source
Highest	Host Command (HCP = 1)
	Transmit Data (HTDE = 1)
Lowest	Receive Data (HRDF = 1)



Host Intertace (HI08)

Freescale Semiconductor, Inc.

Host Interface—DSP Programmer's Model

7.4.1.4 Host Flags 2 and 3 (HF2–HF3)—Bits 3–4

The Host Flag 2 and Host Flag 3 (HF2 and HF3) bits are used as general purpose flags for DSP-to-host communication. HF2 and HF3 may be set or cleared by the DSP core. HF2 and HF3 are reflected in the ISR on the host side such that if they are modified by the DSP software, the host processor can read the modified values by reading the ISR.

These two flags are not designated for any specific purpose but are general purpose flags. They can be used individually or as encoded pairs in a simple DSP-to-host communication protocol, implemented in both the DSP and the host processor software.

7.4.1.5 Reserved Bits—Bits 5–15

Bits 5–15 in the HCR are reserved bits and are read as 0. They should be written with 0 to ensure future compatibility.

7.4.2 HI08 Status Register (HSR)

The HI08 Status Register (HSR) is a 16-bit read-only status register used by the DSP to read the status and flags of the HI08. It cannot be directly accessed by the host processor. Reserved bits are read as 0s. The value of the HSR after reset is \$0002. All bits are cleared except for the Host Transmit Data Empty (HTDE) bit, which is set. The HSR bits are described in the following paragraphs.

HSR—X:\$FFFC	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0	
Host Status Register	*	*	*	*	*	*	*	*	*	*	*	HF1	HF0	НСР	HT DE	HR DF	
Reset = \$0002 ^l																	l
•																	
Read/Write																	

^{*} Indicates reserved bits, read as 0 and should be written with 0 for future compatibility

AA0724

Figure 7-3 Host Status Register (HSR) Programming Model

7.4.2.1 Host Receive Data Full (HRDF)—Bit 0

The Host Receive Data Full (HRDF) flag bit indicates that the Host Receive Data (HRX) register contains data from the host processor. The HRDF bit is set when data is transferred from the TXH:TXL registers to the HRX register. The HRDF bit is cleared when the HRX register is read by the DSP core. When the HRDF bit is set, the HI08 generates a receive data full DMA request. The HRDF bit can also be cleared by





Host Interface (HI08)

Host Interface—DSP Programmer's Model

the host processor using the initialize function. The HRDF bit is cleared on hardware reset.

7.4.2.2 Host Transmit Data Empty (HTDE)—Bit 1

The Host Transmit Data Empty (HTDE) flag bit indicates that the Host Transmit Data (HTX) register is empty and can be written by the DSP core. The HTDE bit is set when the HTX register is transferred to the RXH:RXL registers, and cleared when HTX is written by the DSP core. When the HTDE bit is set, the HI08 generates a Transmit Data Full DMA request. HTDE can also be set by the host processor using the initialize function. The HTDE bit is set on hardware reset.

7.4.2.3 Host Command Pending (HCP)—Bit 2

The Host Command Pending (HCP) flag bit reflects the status of the HC bit in the Command Vector Register (CVR), indicating that a host command interrupt is pending. The HCP bit is set when the HC bit is set, and both bits are cleared by the HI08 hardware when the interrupt request is serviced by the DSP core. The host also can clear the HC bit, which clears the HCP bit as well. The HCP bit is cleared on hardware reset.

7.4.2.4 Host Flags 0 and 1 (HF0–HF1)—Bits 3–4

The Host Flag bits (HF0 and HF1) are used as a general purpose flags for host-to-DSP communication. The HF0 and HF1 bits can be set or cleared by the host. These bits reflect the status of host flags HF0 and HF1 in the ICR on the host side.

These two flags are not designated for any specific purpose but are general purpose flags. They can be used individually or as encoded pairs in a simple host-to-DSP communication protocol, implemented in both the DSP and the host processor software. The HF0 and HP1 bits are cleared on hardware reset.

7.4.2.5 Reserved Bits—Bits 5–15

Bits 5–15 in the HSR are reserved bits and are read as 0. They should be written with 0 to ensure future compatibility.



Host Interface—DSP Programmer's Model

7.4.3 HI08 Port Control Register (HPCR)

The Host Port Control Register (HPCR) is 16-bit read/write control register used by the DSP to control the HI08 operating mode. The HPCR bits are cleared on hardware reset.

HPCR—X:\$FFC4	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
Host Port Control	HAP	HRP		3 H	HM		D E	HR OD		HEN	HA EN	HR EN	HCS EN	HAS EN	HA8 EN	HG EN
Register Reset = \$0000			SP	DS	UX	SP	SP	OD	*		LIN	LIN	LIN	LIN	LIN	LIN
Reset = \$0000																
Read/Write																

^{*} Indicates reserved bits, read as 0 and should be written with 0 for future compatibility

AA0725

Figure 7-4 Host Port Control Register (HPCR) Programming Model

Note:

In order to assure proper operation, the HPCR bits HAP, HRP, HCSP, HDDS, HMUX, HASP, HDSP, HROD, HAEN, and HREN should be changed only when the HEN bit is set to 0. Also, the HPCR bits should not all be written at the same time. Set the HEN bit only after the other bits have been written.

7.4.3.1 Host GPIO Port Enable (HGEN)—Bit 0

The Host GPIO Port Enable (HGEN) bit controls the GPIO port functionality of the HI08 pins. When the HGEN bit is set, pins that are configured as GPIO are enabled. When this bit is cleared, pins that are configured as GPIO are disconnected. Outputs are tri-stated, and inputs are electrically disconnected. Pins configured as HI08 are not affected. The HGEN bit is cleared on hardware reset.

7.4.3.2 Host Address Line 8 Enable (HA8EN)—Bit 1

The Host Address Line 8 Enable (HA8EN) bit allows using the HA8/A1 pin for Host Address line 8 (HA8). When the HA8EN bit is set and the HI08 is used in Multiplexed Bus mode, then the HA8/A1 pin is used as HA8. When the HA8EN bit is cleared and the HI08 is used in Multiplexed Bus mode, then HA8/A1 is used as a GPIO pin according to the value of HDDR and HDR. When the HI08 is not in the Multiplexed Bus mode (HMUX = 0), the HA8EN bit is ignored. The HA8EN bit is cleared on hardware reset.

7.4.3.3 Host Address Line 9 Enable (HA9EN)—Bit 2

When the Host Address Line 9 Enable (HA9EN) bit is set and the HI08 is used in Multiplexed Bus mode, the HA9/A2 pin is used as Host Address line 9 (HA9). When the HA9EN bit is cleared and the HI08 is used in Multiplexed Bus mode, then the HA9/A2 pin is configured as GPIO pin according to the value of HDDR and HDR.



Host Interface (HI08)

Host Interface—DSP Programmer's Model

When the HI08 is not in the Multiplexed Bus mode (HMUX = 0), the HA9EN bit is ignored. The HA9EN bit is cleared on hardware reset.

7.4.3.4 Host Chip Select Enable (HCSEN)—Bit 3

When the Host Chip Select Enable (HCSEN) bit is set, then HCS/A10 is used as Host Chip Select (HCS) in the Non-Multiplexed Bus mode (HMUX = 0), and as address line 10 (HA10) in the Multiplexed Bus mode (HMUX = 1). When this bit is cleared, the HCS/A10 pin is configured as GPIO pin according to the value of HDDR and HDR. The HCSEN bit is cleared on hardware reset.

7.4.3.5 Host Request Enable (HREN)—Bit 4

The Host Request Enable (HREN) bit controls the host request pins. In the Single Host Request mode (HDRQ = 0 in the host-side Interface Control Register (ICR)), if HREN is set, HREQ/TRQ is configured as the host request (HREQ) output. When the HREN bit is cleared, HREQ/TRQ and HACK/RRQ are configured as GPIO pins according to the value of HDDR and HDR.

In the Double Host Request mode (HDRQ = 1 in the ICR), if HREN is set, HREQ/TRQ is configured as the Host Transmit Request (HTRQ) output and HACK/RRQ as the Host Receive Request (HRRQ) output. When the HREN bit is cleared, HREQ/TRQ and HACK/RRQ are configured as GPIO pins according to the value of HDDR and HDR. The HREN bit is cleared on hardware reset.

7.4.3.6 Host Acknowledge Enable (HAEN)—Bit 5

The Host Acknowledge Enable (HAEN) bit controls the HACK pin. In the Single Host Request mode (HDRQ = 0 in the ICR), if HAEN is set and HREN is set HACK/RRQ is configured as the Host Acknowledge (HACK) input. When either the HAEN bit or the HREN bit is cleared, the HACK/RRQ pin is configured as a GPIO pin according to the value of HDDR and HDR. In the Double Host Request mode (HDRQ = 1 in the ICR), HAEN is ignored. The HAEN bit is cleared on hardware reset.

7.4.3.7 Host Enable (HEN)—Bit 6

The Host Enable (HEN) bit allows controls the HI08 functionality. When the HEN bit is set, the HI08 operates as the Host Interface. When the HEN bit is cleared, the HI08 is not active, and all the HI08 pins are configured as GPIO pins according to the value of the HDDR and HDR. The HEN bit is cleared on hardware reset.

7.4.3.8 Reserved Bit—Bit 7

Bit 7in the HSR is a reserved bit and is read as 0. This bit should be written with 0 to ensure future compatibility.



Host Interface—DSP Programmer's Model

7.4.3.9 Host Request Open Drain (HROD)—Bit 8

The Host Request Open Drain (HROD) bit controls the output drive of the host request pins. In the Single Host Request mode (HDRQ = 0 in ICR), if HROD is cleared and host requests are enabled (HREN = 1 and HEN = 1 in the Host Port Control Register (HPCR)), the HREQ pin is always driven. When the HROD bit is set and host requests are enabled, the HREQ pin is an open drain output.

In the Double Host Request mode (HDRQ = 1 in the ICR), if HROD is cleared and host requests are enabled (HREN = 1 and HEN = 1 in the HPCR), the HTRQ and HRRQ pins are always driven. When the HROD bit is set and host requests are enabled, the HTRQ and HRRQ pins are open drain outputs. The HROD bit is cleared on hardware reset.

7.4.3.10 Host Data Strobe Polarity (HDSP)—Bit 9

When the Host Data Strobe Polarity (HDSP) bit is set, the data strobe pins HDS or HRD and HWR are configured as active high inputs, and data is transferred when the data strobe is high. When the HDSP bit is cleared, the data strobe pins are configured as active low inputs, and data is transferred when the data strobe is low. The HDSP bit is cleared on hardware reset.

7.4.3.11 Host Address Strobe Polarity (HASP)—Bit 10

When the Host Address Strobe Polarity (HASP) bit is cleared, the Address Strobe (HAS) pin is an active low input, and the address on the host address/data bus is sampled when the HAS pin is low. When the HASP bit is set, HAS is an active high address strobe input, and the address on the host address/data bus is sampled when the HAS pin is high. The HASP bit is cleared on hardware reset.

7.4.3.12 Host Multiplexed Bus (HMUX)—Bit 11

When the Host Multiplexed Bus (HMUX) bit is set, the HI08 latches the lower portion of a multiplexed Address/Data bus. In this mode the internal address lines of the host registers are taken from the internal latch. When the HMUX bit is cleared, it indicates that the HI08 is connected to a non-multiplexed type of bus, and the address lines are taken from the HI08 input pins. The HMUX bit is cleared on hardware reset.

7.4.3.13 Host Dual Data Strobe (HDDS)—Bit 12


When the Host Dual Data Strobe (HDDS) bit is set, the HI08 operates in the Dual Strobe Bus mode (i.e., a bus with separated Read and Write data strobes). When the HDDS bit is cleared, the HI08 operates in the Single Strobe Bus mode (i.e., a host bus with a single Data Strobe signal). See **Figure 7-5** for a description on the two types of buses. The HDDS bit is cleared on hardware reset.





Host Interface (HI08)

Host Interface—DSP Programmer's Model



In Dual Strobe Bus mode, there are special RD and WR signals that both qualify the access as being a read or a write access, respectively.

AA0726

Figure 7-5 Single and Dual Strobe Bus Modes

7.4.3.14 Host Chip Select Polarity (HCSP)—Bit 13

The Host Chip Select Polarity (HCSP) bit configures the polarity of the Host Chip Select (HCS) pin. When the HCS pin is asserted, the HI08 is selected. When the HCSP bit is set, the HCS pin is configured as an active high input and the HI08 is selected when the HCS pin is pulled high. When the HCSP bit is cleared, the HCS pin is configured as an active low input, and the HI08 is selected when the HCS pin is low. The HCSP bit is cleared on hardware reset.

7.4.3.15 Host Request Polarity (HRP)—Bit 14

The Host Request Polarity (HRP) bit controls the polarity of the Host Request (HREQ) pin. In the Single Host Request mode (the HDRQ bit in the ICR is cleared), if the HRP bit is cleared and host requests are enabled (the HREN and HEN bits in the HPCR are set), the HREQ pin is an active low output. When the HRP bit is set and host requests are enabled, the HREQ pin is active high.

In the Double Host Request mode (the HDRQ bit in the ICR is set), if HRP is cleared and host requests are enabled (the HREN and HEN bits in the HPCR are set), the HTRQ and HRRQ pins are active low outputs. When the HRP bit is set and host requests are enabled, the HTRQ and HRRQ pins are active high outputs.



Host Interface—DSP Programmer's Model

The HRP bit is cleared on hardware reset.

7.4.3.16 Host Acknowledge Polarity (HAP)—Bit 15

The Host Acknowledge Polarity (HAP) bit controls the polarity of the Host Acknowledge (HACK) pin. When the HAP bit is set, the HACK pin is configured as an active high input, and the HI08 outputs the contents of the IVR when the HACK pin is asserted high. When the HAP bit is cleared, the HACK pin is configured as an active low input, and the HI08 drives the contents of the IVR onto the host bus when the HACK pin is low. The HAP bit is cleared on hardware reset.

7.4.4 HI08 Data Direction Register (HDDR)

The HI08 Data Direction Register (HDDR) controls the direction of each of the HI08 pins configured as GPIO. Note that even when the HI08 is used as the Host Interface, some of its pins can be configured as GPIO pins and the direction of these pins is controlled by this register. For full information regarding all the configuration options, see **General Purpose I/O** on page 7-30.

When the DRxx bit is set, the corresponding HI08 pin is configured as an output pin. When the DRxx bit is cleared, the corresponding HI08 pin is configured as an input pin.




Figure 7-6 Host Data Direction Register (HDDR) Programming Model

7.4.5 HI08 Data Register (HDR)

The HI08 Data Register (HDR) holds the data value of the corresponding bits of the HI08 pins that are configured as GPIO pins. The bit Dxx functionality depends on the corresponding HDDR bit. See **Table 7-5**. The HDR cannot be accessed by the host processor.



Host Interface (HI08)

Host Interface—DSP Programmer's Model




Figure 7-7 Host Data Register (HDR) Programming Model

Table 7-5 HDR and HDDR Bits Functionality

HDDR	HDR										
DRxx	Dxx										
Бил	GPIO pin	Non-GPIO pin									
0	Read-only bit. The value read is the binary value of the pin. The corresponding pin is configured as an input.	Read-only bit. The bit does not contain significant data.									
1	Read/write bit. The value written is the value read. The corresponding pin is configured as an output, and is driven with the data written to Dxx.	Read/write bit. The value written is the value read.									

7.4.6 HI08 Base Address Register (HBAR)

The HI08 Base Address Register (HBAR) is used in Multiplexed Bus modes. This register selects the base address for the host side registers. The address from the host is compared with the base address as programmed in the HBAR, and the internal chip select is generated if a match is found. The mechanism that uses this register is shown in **Figure 7-8**. Bits 0–7 provide the base address. Bits 8–15 in the HBAR are reserved bits and are read as 0. They should be written with 0 to ensure future compatibility.



Host Interface—DSP Programmer's Model




Figure 7-8 Self Chip Select Logic

HBAR—X:\$FFC5	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
Host Base								*	ВА							
Address Register	*	*	*	*	*	*	*		10	9	8	7	6	5	4	3
Reset = \$0080 I															,	

^{*} Indicates reserved bits, read as 0 and should be written with 0 for future compatibility

AA0730

Figure 7-9 Host Base Address Register (HBAR) Programming Model

7.4.7 HI08 Receive Data Register (HRX)

The HI08 Receive Data (HRX) register is used for host-to-DSP data transfers. The HRX register is viewed as a 16-bit read-only register by the DSP core. The HRX register is loaded with 16-bit data from the transmit data registers (TXH:TXL) on the host side when both the transmit data register empty TXDE (host side) and DSP Host Receive Data Full (HRDF) bits are cleared. This transfer operation sets TXDE and HRDF. The HRX register contains valid data when the HRDF bit is set. Reading HRX clears HRDF. The DSP may program the HRIE bit to cause a Host Receive Data interrupt when HRDF is set.

Host Interface (HI08)

Host Interface—DSP Programmer's Model

7.4.8 HI08 Transmit Data Register (HTX)

The HI08 Transmit Data (HTX) register is used for DSP-to-host data transfers. The HTX register is viewed as a 16-bit write-only register by the DSP core. Writing the HTX register clears the HTDE bit in the HSR. The DSP can program the HTIE bit to cause a Host Transmit Data interrupt when HTDE is set. The HTX register is transferred as 16-bit data to the receive byte registers (RXH:RXL) if both the HTDE bit (DSP side) and Receive Data Full (RXDF) status bits (host side) are cleared. This transfer operation sets RXDF and HTDE. Data should not be written to the HTX until HTDE is set to prevent the previous data from being overwritten.

7.4.9 **DSP Side Registers After Reset**

Table 7-6 shows the results of the four reset types on the bits in each of the HI08 registers accessible by the DSP core.

Table 7-6 DSP Side Registers after Reset

Reset Type					
STOP Reset ⁴					
_					
_					
_					
0					
1					
0					
_					
_					
_					
empty					
empty					

- Note: 1. Caused by \overline{RESET} signal
 - Caused by executing the RESET instruction
 - Caused by clearing the HEN bit in the HPCR
 - Caused by executing the STOP instruction



Host Intertace (HI08)

Host Interface—DSP Programmer's Model

7.4.10 HI08 DSP Core Interrupts

The HI08 may request interrupt service from either the DSP core or the host processor. The DSP core interrupts are internal and do not require the use of an external interrupt pin (see **Figure 7-10**). When the appropriate interrupt enable bit in the HCR is set, an interrupt condition caused by the host processor sets the appropriate bit in the HSR, which generates an interrupt request to the DSP core. The DSP core acknowledges interrupts caused by the host processor by jumping to the appropriate interrupt service routine. The three possible interrupts are:

- Receive data register full
- Transmit data register empty
- Host command

The host command can access any interrupt vector in the interrupt vector table, although it has a set of vectors reserved for host command use. The DSP interrupt service routine must read or write the appropriate HI08 register (e.g., by clearing the HRDF or HTDE bit) to clear the interrupt. In the case of host command interrupts, the interrupt acknowledge from the DSP core Program Controller Unit (PCU) clears the pending interrupt condition.




Figure 7-10 HSR-HCR Operation



Host Interface (HI08)

HI08—External Host Programmer's Model

7.5 HI08—EXTERNAL HOST PROGRAMMER'S MODEL

The HI08 appears to the host processor as eight byte-wide registers. The host can access the HI08 asynchronously by using polling techniques or interrupt-based techniques. Separate transmit and receive data registers are double buffered to allow the DSP core and host processor to transfer data efficiently at high speed.

The HI08 appears to the host processor as a memory-mapped peripheral occupying eight bytes in the host processor address space (see **Table 7-7**). These registers can be viewed as a control register (ICR), a status register (ISR), two data registers (RXH/TXH and RXL/TXL), and two vector registers (IVR and CVR). The CVR is a special command register that is used by the host processor to issue commands to the DSP. These registers can be accessed only by the host processor.

Host processors can use standard host processor instructions (e.g., byte move) and addressing modes to communicate with the HI08 registers. The HI08 registers are addressed so that 8-bit host processors can use 8/16-bit load and store instructions for data transfers. The HREQ/HTRQ and HACK/HRRQ handshake flags are provided for polled or interrupt-driven data transfers with the host processor. Because the DSP interrupt response is sufficiently fast, most host microprocessors can load or store data at their maximum programmed I/O instruction rate without testing the handshake flags for each transfer. If full handshake is not needed, the host processor can treat the DSP as a fast device, and data can be transferred between the host processor and the DSP at the fastest host processor data rate.

One of the most innovative features of the host interface is the host command feature. With this feature, the host processor can issue vectored interrupt requests to the DSP core. The host can select any of 128 DSP interrupt routines to be executed by writing a vector address register in the HI08. This flexibility allows the host programmer to execute as many as 128 pre-programmed functions inside the DSP core. For example, host interrupts can allow the host processor to read or write DSP registers (X, Y, or program memory locations), force interrupt handlers (e.g., SSI, SCI, \overline{IRQA} , \overline{IRQB} interrupt routines), and perform control and debugging operations if interrupt routines are implemented in the DSP to perform these tasks.

Note:

Users should be aware that when the DSP core enters the Stop mode, the HI08 pins are electrically disconnected internally, thus disabling the HI08 until the core leaves Stop mode. While the HI08 configuration remains unchanged while in Stop mode, the core cannot be restarted via the HI08 interface.

Do not issue a STOP command to the DSP via the HI08 unless some other mechanism for exiting Stop mode is provided.



HI08—External Host Programmer's Model

Table 7-7 HI08 Host Side Register Map

Host Address	"Big Endian" HLEND = 0	"Little Endian" HLEND = 1	
0	ICR	ICR	Interface Control
1	CVR	CVR	Command Vector
2	ISR	ISR	Interface Status
3	IVR	IVR	Interrupt Vector
4	00000000	00000000	Unused
5	00000000	00000000	Unused
6	RXH/TXH	RXL/TXL	Receive/Transmit
7	RXL/TXL	RXH/TXH	Bytes
	‡	‡	
	Host Data Bus H0-H7	Host Data Bus H0-H7	

7.5.1 Interface Control Register (ICR)

The Interface Control Register (ICR) is an 8-bit read/write control register used by the host processor to control the HI08 interrupts and flags. The ICR cannot be accessed by the DSP core. The ICR is a read/write register, which allows the use of bit manipulation instructions on control register bits. The control bits are described in the following paragraphs. **Figure 7-11** shows the programming model of the ICR.

7-22



Host Interface (HI08)

HI08—External Host Programmer's Model

ICR
Interface Control
Register
Reset = \$00
Read/Write

_	7	6	5	4	3	2	1	0
	INIT	*	HB END	HF1	HF0	HD RQ	TR EQ	RR EQ

^{*} Indicates reserved bits, read as 0 and should be written with 0 for future compatibility

JAS0007

Figure 7-11 Interface Control Register Programming Model

7.5.1.1 Receive Request Enable (RREQ)—Bit 0

The Receive Request Enable (RREQ) bit is used to control the HREQ pin for host receive data transfers. The RREQ bit is used to enable host requests via the host request (HREQ or HRRQ) pin when the Receive Data register Full (RXDF) status bit in the ISR is set. When the RREQ bit is cleared, RXDF interrupts are disabled. When the RREQ bit is set, the host request pin (HREQ or HRRQ) is asserted if RXDF is set. The RREQ bit is cleared on hardware reset.

7.5.1.2 Transmit Request Enable (TREQ)—Bit 1

The Transmit Request Enable (TREQ) bit is used to enable host requests via the host request (HREQ or HTRQ) pin when the Transmit Data Register Empty (TXDE) status bit in the ISR is set. When the TREQ bit is cleared, TXDE interrupts are disabled. When the TREQ bit is set, the host request pin is asserted if TXDE is set. The TREQ bit is cleared on hardware reset.

Table 7-8 and **Table 7-8** summarize the effect of RREQ and TREQ on the HREQ pin.

Table 7-8 TREQ and HREQ Modes (HDRQ = 0)

TREQ	RREQ	HREQ Pin
0	0	No Interrupts (Polling)
0	1	RXDF Request (Interrupt)
1	0	TXDE Request (Interrupt)
1	1	RXDF and TXDE Request (Interrupts)

Table 7-9 TREQ and HREQ Modes (HDRQ = 1)

TREQ	RREQ	HTRQ Pin	HRRQ Pin
0	0	No Interrupts (Polling)	No Interrupts (Polling)



HI08—External Host Programmer's Model

Table 7-9 TREQ and HREQ Modes (HDRQ = 1)

TREQ	RREQ	HTRQ Pin	HRRQ Pin
0	1	No Interrupts (Polling)	RXDF Request (Interrupt)
1	0	TXDE Request (Interrupt)	No Interrupts (Polling)
1	1	TXDE Request (Interrupt)	RXDF Request (Interrupt)

7.5.1.3 Double Host Request (HDRQ)—Bit 2

When the Double Host Request (HDRQ) bit is set, the HREQ/TRQ pin is configured as HTRQ, and the HACK/RRQ pin is configured as HRRQ. When the HDRQ bit is cleared, the HREQ/TRQ pin is configured as HREQ, and the HACK/RRQ is configured as HACK. The HDRQ bit is cleared on hardware reset.

7.5.1.4 Host Flag 0 (HF0)—Bit 3

The Host Flag 0 (HF0) bit is used as a general purpose flag for host-to-DSP communication. HF0 can be set or cleared by the host processor, but cannot be changed by the DSP core. HF0 is reflected in the HSR on the DSP side of the HI08. The HF0 bit is cleared on hardware reset.

7.5.1.5 Host Flag 1 (HF1)—Bit 4

The Host Flag 1 (HF1) bit is used as a general purpose flag for host-to-DSP communication. The HF1 bit can be set or cleared by the host processor, but cannot be changed by the DSP core. The HF1 bit is reflected in the HSR on the DSP side of the HI08. The HF1 bit is cleared on hardware reset.

7.5.1.6 Host Little Endian (HLEND)—Bit 5

The Host Little Endian (HLEND) bit allows the HI08 to be accessed by the host in "Little Endian" or "Big Endian" data order. When the HLEND bit in the ICR is set, the HI08 can be accessed by the host in "Little Endian" order. The RXH/TXH is located at address \$7 and RXL/TXL at \$6. When the HLEND bit is cleared, the HI08 can be accessed by the host in "Big Endian" host data order. The RXH/TXH is located at address \$6 and RXL/TXL at \$7. The HLEND bit is cleared on hardware reset.

7.5.1.7 Initialize Bit (INIT)—Bit 7

The Initialize (INIT) bit is used by the host processor to force initialization of the HI08 hardware. Initialization consists of configuring the HI08 transmit and receive control bits. Using the INIT bit to initialize the HI08 hardware may or may not be necessary, depending on the software design of the interface.





Host Interface (HI08)

HI08—External Host Programmer's Model

The type of initialization done when the INIT bit is set depends on the state of TREQ and RREQ in the HI08. The INIT command, which is local to the HI08, is designed to conveniently configure the HI08 into the desired data transfer mode. The commands are described in **Table 7-10**. The host sets the INIT bit, which causes the HI08 hardware to execute the INIT command. The interface hardware clears the INIT bit when the command has been executed.

Table 7-10	INIT	Commands
-------------------	------	----------


TREQ	RREQ	After INIT Execution	Transfer Direction Initialized
0	0	INIT = 0	None
0	1	INIT = 0; RXDF = 0; HTDE = 1	DSP to Host
1	0	INIT = 0; $TXDE = 1$; $HRDF = 0$	Host to DSP
1	1	INIT = 0; RXDF = 0; HTDE = 1; $TXDE = 1; HRDF = 0$	Host to/from DSP

7.5.1.8 Reserved Bit—Bit 6

Bit 6 is reserved and should be written as 0 to ensure future compatibility.

7.5.2 Command Vector Register (CVR)

The Command Vector Register (CVR) is used by the host processor to cause the DSP core to execute an interrupt. The host command feature is independent of any of the data transfer mechanisms in the HI08. It can be used to cause any of the 128 possible interrupt routines in the DSP core to be executed.



AA0732

Figure 7-12 Command Vector Register (CVR)

7.5.2.1 Host Vector (HV)—Bits 0–6

The seven HV bits select the host command interrupt address to be used by the host command interrupt logic. When the host command interrupt is recognized by the



HI08—External Host Programmer's Model

DSP interrupt control logic, the address of the interrupt routine taken is 2 • HV. The host can write HC and HV in the same write cycle.


The host processor can select any of the 128 possible interrupt routine starting addresses in the DSP by writing the interrupt routine address divided by 2 into HV[6:0]. This means that the host processor can force any of the existing interrupt handlers (SSI, SCI, IRQA, IRQB, etc.) and can use any of the reserved or otherwise unused addresses provided they have been pre-programmed in the DSP. The HV[6:0] bits are set to \$32 (vector location \$0064) by hardware, software, individual, and Stop resets.

7.5.2.2 Host Command Bit (HC)—Bit 7

The Host Command (HC) bit is used by the host processor to handshake the execution of host command interrupts. Normally, the host processor sets HC = 1 to request the host command interrupt from the DSP core. When the host command interrupt is acknowledged by the DSP core, the HC bit is cleared by the HI08 hardware. The host processor can read the state of the HC bit to determine when the host command has been accepted. After writing HC = 1 to the CVR, the host must not write to the CVR again until the HC bit is cleared by the HI08 hardware. Setting the HC bit causes host command pending (HCP) to be set in the HSR. The host can write both the HC and the HV bits in the same write cycle if desired.

7.5.3 Interface Status Register (ISR)

The Interface Status Register (ISR) is an 8-bit read-only status register used by the host processor to interrogate the status and flags of the HI08. The host processor can write this address without affecting the internal state of the HI08, which is useful if the user desires to access all of the HI08 registers by stepping through the HI08 addresses. The ISR can be accessed by the DSP core. The status bits are described in the following paragraphs.



^{*} Indicates reserved bits, read as 0 and should be written with 0 for future compatibility

AA0733

Figure 7-13 Interface Status Register Programming Model





Host Interface (HI08)

HI08—External Host Programmer's Model

7.5.3.1 Receive Data Register Full (RXDF)—Bit 0

The Receive Data Register Full (RXDF) flag bit indicates that the receive byte registers (RXH and RXL) contain data from the DSP core and can be read by the host processor. The RXDF bit is set when the HTX is transferred to the receive byte registers. RXDF is cleared when the receive data (RXL or RXH according to HLEND bit) register is read by the host processor. RXDF can be cleared by the host processor using the initialize function. RXDF may be used to assert the external HREQ pin if the RREQ bit is set. Regardless of whether the RXDF interrupt is enabled, RXDF provides valid status so that polling techniques may be used by the host processor.

Transmit Data Register Empty (TXDE)—Bit 1 7.5.3.2

The Transmit Data Register Empty (TXDE) bit indicates that the transmit byte registers (TXH, and TXL) are empty and can be written by the host processor. TXDE is set when the transmit byte registers are transferred to the HRX register. TXDE is cleared when the transmit (TXL or TXH according to HLEND bit) register is written by the host processor. TXDE can be set by the host processor using the initialize feature. TXDE may be used to assert the external HREQ pin if the TREQ bit is set. Regardless of whether the TXDE interrupt is enabled, TXDE provides valid status so that polling techniques may be used by the host processor.

7.5.3.3 Transmitter Ready (TRDY)—Bit 2

The Transmitter Ready (TRDY) flag bit indicates that TXH, TXL, and the HRX registers are empty.

TRDY=TXDE ● HRDF

When the TRDY bit is set, the data that the host processor writes to the TXH and TXL registers is immediately transferred to the DSP side of the HI08. This has many applications. For example, if the host processor issues a host command which causes the DSP core to read the HRX, the host processor can be guaranteed that the data it just transferred to the HI08 is what is being received by the DSP core.

7.5.3.4 Host Flag 2 (HF2)—Bit 3

The Host Flag 2 (HF2) bit in the ISR indicates the state of host flag 2 in the HCR on the DSP side. The HF2 bit can only be changed by the DSP (see Host Flags 2 and 3 (HF2-HF3)—Bits 3-4 on page 7-10).

7.5.3.5 Host Flag 3 (HF3)-Bit 4

The Host Flag 3 (HF3) bit in the ISR indicates the state of host flag 3 in the HCR on the DSP side. The HF3 bit can only be changed by the DSP (see Host Flags 2 and 3 (HF2-HF3)—Bits 3-4 on page 7-10).



Host Intertace (HI08)

Freescale Semiconductor, Inc.

HI08—External Host Programmer's Model

7.5.3.6 Reserved Bits-Bits 5 and 6

Bits 5 and 6 in the ISR are reserved bits and are read as 0. They should be written with 0 to ensure future compatibility.

7.5.3.7 ISR Host Request (HREQ)—Bit 7

The ISR Host Request (HREQ) bit indicates the status of the external host request output pin (HREQ) if the HDRQ bit is cleared; or the external transmit and receive request output pins (HTRQ and HRRQ, respectively) if HDRQ is set.

When the HDRQ bit is cleared: If the HREQ status bit is cleared, it indicates that the Host Request pin (HREQ) is deasserted and no host processor interrupts are being requested. If the HREQ status bit is set, it means that the Host Request pin (HREQ) is asserted, indicating that the DSP is interrupting the host processor.

When the HDRQ bit is set: If the HREQ status bit is cleared, it indicates that the HTRQ and HRRQ pins are deasserted and no host processor interrupts are being requested. When the HREQ status bit is set, it means that the HTRQ pin or HRRQ pin is asserted, indicating that the DSP is interrupting the host processor.

The HREQ bit may be set from either or both of two sources—the receive byte registers are full or the transmit byte registers are empty. These conditions are indicated by the ISR RXDF and TXDE status bits, respectively. If the interrupt source has been enabled by the associated request enable bit in the ICR, HREQ is set if one or more of the two enabled interrupt sources is set.

7.5.4 Interrupt Vector Register (IVR)

The Interrupt Vector Register (IVR) is an 8-bit read/write register that typically contains the interrupt vector number used with MC68000 family processor vectored interrupts. Only the host processor can read and write this register. The contents of IVR are placed on the Host Data Bus (H0–H7) when both the HREQ and HACK pins are asserted. The contents of this register are initialized to a pre-defined value by a hardware or software reset, which corresponds to the uninitialized interrupt vector in the MC68000 family.



Host Interface (HI08)

HI08—External Host Programmer's Model

IVR	7	6	5	4	3	2	1	0
Interrupt Vector	IV7	IV6	IV5	IV4	IV3	IV2	IV1	IV0
Register Reset = \$0F								
Read/Write								

^{*} Indicates reserved bits, read as 0 and should be written with 0 for future compatibility

AA0734

Figure 7-14 Interrupt Vector Register (IVR)

7.5.5 Receive Byte Registers (RXH, RXL)

The receive byte registers are viewed as two 8-bit read-only registers by the host processor. These registers are called Receive High (RXH) and Receive Low (RXL). These two registers receive data from the high byte, and low byte, respectively, of the HTX register and are selected by two external host address inputs (HA1 and HA0) during a host processor read operation. The receive byte registers contain valid data when the Receive Data register Full (RXDF) bit is set. The host processor may program the RREQ bit to assert the external HREQ pin when RXDF is set. This informs the host processor that the receive byte registers are full. Reading the data register at host address \$7 clears the RXDF bit. When the HLEND bit in the ICR is cleared, the RXH is located at address \$6 and RXL at \$7. When the HLEND bit in the ICR is set, the RXH is located at address \$7 and RXL at \$6.

7.5.6 Transmit Byte Registers (TXH, TXL)

The transmit byte registers are viewed as two 8-bit write-only registers by the host processor. These registers are called Transmit High (TXH) and Transmit Low (TXL). These two registers send data to the high byte and low byte, respectively, of the HRX register and are selected by two external host address inputs (HA1 and HA0) during a host processor write operation. Data can be written into the transmit byte registers when the Transmit Data register Empty (TXDE) bit is set. The host processor can program the TREQ bit to assert the external HREQ pin when TXDE is set. This informs the host processor that the transmit byte registers are empty. Writing the data register at host address \$7 clears the TXDE bit. When the HLEND bit in the ICR is cleared, the TXH is located at address \$6 and TXL at \$7. When the HLEND bit in the ICR is set, the TXH is located at address \$7 and TXL at \$6. The transmit byte registers are transferred as 16-bit data to the HRX register when both TXDE and the HRDF bit are cleared. This transfer operation sets TXDE and HRDF.



Host Interface (HI08)
General Purpose I/O

7.5.7 Host Side Registers After Reset

Table 7-11 shows the result of the four kinds of reset on bits in each of the HI08 registers seen by the host processor. The hardware reset is caused by asserting the \overline{RESET} pin; the software reset is caused by executing the RESET instruction; the individual reset is caused by clearing the HEN bit in the HPCR; and the Stop reset is caused by executing the STOP instruction.

 Table 7-11
 Host Side Registers After Reset

Dogiston	Dogiston	Reset Type					
Register Name	Register Data	Hardware Reset	Software Reset	Individual Reset	Reset		
ICR	All bits	0	0	_	_		
CVR	HC	0	0	0	0		
	HV[6:0]	\$2A	\$2A	_	_		
ISR	HREQ	0	0	1 if TREQ is set, 0 if TREQ is cleared	1 if TREQ is set, 0 if TREQ is cleared		
	HF[3:2]	0	0	_	_		
	TRDY	1	1	1	1		
	TXDE	1	1	1	1		
	RXDF	0	0	0	0		
IVR	IV[7:0]	\$0F	\$0F	_	_		
RX	RXH: RXL	empty	empty	empty	empty		
TX	TXH: TXL	empty	empty	empty	empty		

7.6 GENERAL PURPOSE I/O

When configured as General Purpose I/O (GPIO), the HI08 is viewed by the DSP core as memory-mapped registers that control as many as sixteen I/O pins. The software and hardware resets configure the HI08 interface as GPIO with all sixteen pins disconnected, by clearing all DSP-side control registers. External circuitry connected to these pins may need external pull-up or pull-down resistors until the pins are configured for operation. These registers are the HI08 Port Control Register (HPCR), the HI08 Data Direction Register (HDDR), and the HI08 Data Register (HDR). Selection between GPIO and HI08 functionality is made by clearing bits 6–1 in the HPCR for GPIO, or setting these bits for HI08 functionality. The HDDR configures each corresponding pin in the HDR, as an input pin if the HDDR bit is





Host Interface (HI08)

General Purpose I/O

cleared or as an output pin if the HDDR bit is set (see HI08 Data Direction Register (HDDR) on page 7-16 and HI08 Data Register (HDR) on page 7-16).

7.6.1 **Servicing the Host Interface**

The HI08 can be serviced by using one of the following protocols:

- Polling
- Interrupts

From the host processor viewpoint, the service consists of making a data transfer since this is the only way to reset the appropriate status bits.

7.6.2 HI08 Host Processor Data Transfer

The HI08 looks like Static RAM to the host processor. To transfer data with the HI08, the host processor must do the following:

- 1. Assert the HI08 address to select the register to be read or written.
- 2. Select the direction of the data transfer.
- 3. Strobe the data transfer.

7.6.3 **Polling**

In the Polling mode of operation, the HREQ pin is not connected to the host processor and HACK must be deasserted to insure IVR data is not being driven on H0-H7 when other registers are being polled. (HACK can also be configured as a GPIO pin if the HACK function is not required. See HI08 Port Control Register (**HPCR**) on page 7-12.)

The host processor first performs a data read transfer to read the ISR (see **Figure 7-15**) to determine, whether:

1. RXDF = 1 indicates the Receive Data register is full, and a data read should be performed.



Host Intertace (HI08) General Purpose I/O

- 2. TXDE = 1 indicates the Transmit Data register is empty, and a data write can be performed.
- 3. TRDY = 1 indicates the Transmit Data register is empty and that the Receive Data register on the DSP side is also empty so that the data written by the host processor can be transferred directly to the DSP side.
- 4. HF2 HF3 \neq 0 may indicate an application-specific state within the DSP core has been reached, which requires action on the part of the host processor.
- 5. When HREQ = 1, the HREQ pin has been asserted, and one of the previous four conditions exists.

Generally, after the appropriate data transfer has been made, the corresponding status bit is updated to reflect the transfer.

If the host processor has issued a command to the DSP by writing the CVR and setting the HC bit, it can read the HC bit in the CVR to determine when the command has been accepted by the interrupt controller in the DSP core. When the command has been accepted for execution, the HC bit is cleared by the interrupt controller in the DSP core.

7.6.4 Servicing Interrupts

When HREQ is connected to the host processor interrupt input, the HI08 can request service from the host processor by asserting HREQ. HREQ is asserted when TXDE = 1 and/or RXDF = 1 and the corresponding enable bit (TREQ or RREQ, respectively) is set. This is depicted in **Figure 7-15**.




Figure 7-15 HI08 Host Request Structure



Host Interface (HI08)

General Purpose I/O

Generally, servicing the interrupt starts with reading the ISR to determine which DSP flag has generated the interrupt. The host processor interrupt service routine must read or write the appropriate HI08 register to clear the interrupt. HREQ is deasserted when the enabled request is cleared or masked.

The host processor interrupts are external and use the HREQ pin. HREQ is normally connected to the host processor maskable interrupt input. The host processor acknowledges host interrupts by executing an interrupt service routine. The two LSBs (RXDF and TXDE) of the ISR may be tested by the host processor to determine the interrupt source (see **Figure 7-15**). The host processor interrupt service routine must read or write the appropriate HI08 register to clear the interrupt. HREQ is deasserted when one of the following occurs:

- The enabled request is cleared or masked.
- The DSP is reset.

In the case where the host processor is a member of the MC680XX family, servicing the interrupt starts by asserting \overline{HREQ} to interrupt the processor. The host processor then acknowledges the interrupt by asserting \overline{HACK} . When \overline{HREQ} and \overline{HACK} are simultaneously asserted, the contents of the IVR are placed on the host data bus. This vector tells the host processor which routine to use to service the \overline{HREQ} interrupt.






General Purpose I/O



SECTION 8 SYNCHRONOUS SERIAL INTERFACE





Synchronous Serial Interface

8.1	INTRODUCTION	8-3
8.2	SSI DATA AND CONTROL PINS	8-4
8.3	SSI PROGRAMMING MODEL	8-7
8 4	OPERATING MODES	8-23



Synchronous Serial Interface

8.1 INTRODUCTION

This section presents the Synchronous Serial Interface (SSI) and discusses its architecture, programming model, operating modes, and initialization. The capabilities of the SSI include:

- Independent (asynchronous) or shared (synchronous) transmit and receive sections with separate or shared internal/external clocks and frame syncs
- Normal mode operation using frame sync
- Network mode operation with as many as 32 time slots
- Programmable word length (8, 12, or 16 bits)
- Program options for frame synchronization and clock generation

The DSP56603 provides two independent and identical SSIs. (For simplicity, a single SSI is described in this section.) Each SSI provides a full-duplex serial port for communication with a variety of serial devices, including one or more industry-standard codecs, other DSPs, microprocessors, and peripherals that implement the Motorola SPI. The SSI consists of independent transmitter and receiver sections and a common SSI clock generator. SSI pins can also be configured for use as General Purpose I/O (GPIO) pins when not used by the SSI. **Figure 8-1** shows a block diagram of the SSI.




Figure 8-1 SSI Block Diagram



Synchronous Serial Interface

SSI Data and Control Pins

8.2 SSI DATA AND CONTROL PINS

Each SSI provides the following signal connections:

- SC0—Serial Control Pin 0
- SC1—Serial Control Pin 1
- SC2—Serial Control Pin 2
- SCK—Serial Clock Pin
- SRD—Serial Receive Data Pin
- STD—Serial Transmit Data Pin

8.2.1 Serial Control 0 (SC0)

The function of the Serial Control 0 (SC0) pin is determined by the selection of either Synchronous or Asynchronous mode (see **Table 8-3** on page 8-11). In Asynchronous mode, this pin is used for the receive clock I/O. In Synchronous mode, this pin is used for Serial I/O Flag 0. A typical application of flag I/O would be multiple device selection for addressing in codec systems. When this pin is configured as a serial flag pin, its direction is determined by the SCD0 bit in the SSI Control Register C (CRC) (see **Serial Control 0 Direction (SCD0)**—**Bit 2** on page 8-14). When configured as an output, this pin functions either as Serial Output Flag 0, based on control bit OF0 in the SSI Control Register B (CRB), or as a receive shift register clock output. When configured as an input, this pin is used either as Serial Input Flag 0, which controls the IF1 flag bit in the SSI Status register (SSISR), or as a receive shift register clock input.

The SC0 pin can be programmed as a GPIO pin (PC0 on SSI0, and PD0 on SSI1) when the SSI SC0 function is not being used.

8.2.2 Serial Control 1 (SC1)

The function of the Serial Control 1 (SC1) pin is determined by the selection of either Synchronous or Asynchronous mode (see **Table 8-3** on page 8-11). In Asynchronous mode (such as a single codec with asynchronous transmit and receive), this pin provides the receiver frame sync I/O. In Synchronous mode, this pin is used for Serial I/O Flag 1 and operates like the previously described SC0. The SC0 and SC1 pins provide independent serial I/O flags, but can be used together for multiple





Synchronous Serial Interface

SSI Data and Control Pins

serial device selection. The SC0 and SC1 pins can be used unencoded to select either one or two codecs, or can be decoded externally to select as many as four codecs. If this pin is configured as a serial flag pin, its direction is determined by the SCD1 bit in the CRC (see **Serial Control 1 Direction (SCD1)** —**Bit 3** on page 8-14). When configured as an output, this pin provides either Serial Output Flag 1 (based on control bit OF1) or the receive frame sync signal. When configured as an input, this pin can be used as Serial Input Flag 1, which controls the IF1 flag bit in the SSI Status Register (SSISR), or as a receive frame sync from an external source.

The SC1 pin can be programmed as a GPIO pin (PC1 on SSI0, or PD1 on SSI1) when the SSI SC1 function is not being used.

8.2.3 Serial Control 2 (SC2)

The Serial Control 2 (SC2) pin is used for frame sync I/O. The SC2 pin provides frame synchronization for both the transmitter and receiver in Synchronous mode, and frame synchronization for the transmitter only in Asynchronous mode (see **Table 8-3** on page 8-11). The direction of this pin is determined by the SCD2 bit in the CRC (described in **Serial Control 2 Direction (SCD2)**—**Bit 4** on page 8-14). When configured as an output, this pin provides the internally generated frame sync signal. When configured as an input, this pin receives an external frame sync signal for the transmitter and the receiver in Synchronous mode, and for the transmitter only in Asynchronous mode.

The SC2 pin can be programmed as a GPIO pin (PC2 on SSI0, or PD2 on SSI1) when the SSI SC2 function is not being used.

8.2.4 Serial Clock (SCK)

The Serial Clock (SCK) pin is a bidirectional pin that provides the serial bit rate clock for the SSI. The SCK pin is a clock input or output used by the transmitter and receiver in Synchronous mode, or by only the transmitter in Asynchronous mode (see **Table 8-1**).



Synchronous Serial Interface

SSI Data and Control Pins

Table 8-1 SSI Clock Sources

SYN	SCKD	SCD0	Receive Clock Source	Receive Clock Out	Transmit Clock Source	Transmit Clock Out
			Asynch	ronous Clock		
0	0	0	EXT, SC0	_	EXT, SCK	_
0	0	1	INT	SC0	EXT, SCK	_
0	1	0	EXT, SC0	_	INT	SCK
0	1	1	INT	SC0	INT	SCK
			Synchi	onous Clock		
1	0	d.c.	EXT, SCK	_	EXT, SCK	_
1	1	d.c.	INT	SCK	INT	SCK

The SCK pin can be programmed as a GPIO pin (PC3 on SSI0, and PD3 on SSI1) when the SSI SCK function is not being used.

Note:

Although an external serial clock can be independent of and asynchronous to the DSP system clock, it must exceed the minimum clock cycle time of 6T (i.e., the system clock frequency must be at least three times the external SSI clock frequency). The SSI needs at least three DSP phases (DSP phase equals T) inside each half of the serial clock.

8.2.5 Serial Receive Data (SRD)

The Serial Receive Data (SRD) pin receives serial data and transfers the data to the Receive Shift Register. The SRD pin can be programmed as a GPIO pin (PC4 on SSI0, and PD4 on SSI1) when the SSI SRD function is not being used.

8.2.6 Serial Transmit Data (STD)

The Serial Transmit Data (STD) pin is used for transmitting data from the Transmit Shift Register. The STD pin is an output when data is being transmitted from the Transmit Shift Register. When using an internally generated bit clock, the STD pin is tri-stated after transmitting the last data bit when another data word does not follow





Synchronous Serial Interface

SSI Programming Model

immediately. If a data word follows immediately (within a full clock cycle), the STD pin is not tri-stated. The STD pin can be programmed as a GPIO pin (PC5 on SSI0, and PD5 on SSI1) when the SSI STD function is not being used.

8.3 SSI PROGRAMMING MODEL

The SSI contains the following registers:

- Interface control registers
 - CRA—Control Register A
 - CRB—Control Register B
 - CRC—Control Register C
- SSISR—SSI Status Register
- Data registers
 - TX—Transmit Data Register
 - RX—Receive Data Register
- Time Slot Register
- GPIO port registers
 - PCR—Port Control Register
 - PRR—Port Direction Register
 - PDR—Port Data Register

The following paragraphs describe the SSI registers.

Note: The registers described in this section represent one SSI. The DSP56603 chip has two identical SSIs. When programming the SSI, the user must ensure that the correct set of registers is used for the desired SSI.

8.3.1 SSI Control Register A (CRA)

The SSI Control Register A (CRA) is one of three 16-bit read/write control registers used to direct the operation of the SSI. The CRA controls the SSI clock generator bit and frame sync rates, word length, and number of words per frame for the serial



Synchronous Serial Interface

SSI Programming Model

data. **Figure 8-2** shows the programming model for the CRA. Hardware and software reset clear all the bits in the CRA.

CRA0—X:\$FFB6	15	14	13	12	11	10	9	- 8	7	6	5	4	3	2	1	0	
CRA1—X:\$FFA6	PSR	WL1	WLO	DC4	DC3	DC2	DC1	DC0	PM7	PM6	PM5	PM4	РМ3	PM2	PM1	PM0	
SSI Control																	
Register A																	
Reset = \$0000																	
Read/Write																ΔΔ073	6

Figure 8-2 SSI Control Register A Programming Model

8.3.1.1 Prescale Modulus Select (PM0–PM7)—Bits 0–7

The Prescale Modulus Select (PM0–PM7) bits specify the divide ratio of the prescale divider in the SSI clock generator. A divide ratio from 1 to 256 (PM[7:0] = 0 to \$FF) can be selected. The bit clock output is available on the SCK pin or the SC0 pin. The bit clock output is also available internally for use as the bit clock to shift the Transmit Shift Register and the Receive Shift Register. Careful choice of the crystal oscillator frequency and the prescaler modulus allows the industry-standard codec master clock frequencies of 2.048 MHz, 1.544 MHz, and 1.536 MHz to be generated. Hardware and software reset clear the PM0–PM7 bits.

8.3.1.2 Frame Rate Divider Control (DC4–DC0)—Bits 8–12

The Frame Rate Divider Control (DC4–DC0) bits control the divide ratio for the programmable frame rate dividers used to generate the frame clocks. In Network mode, this ratio can be interpreted as the number of words per frame minus one. In Normal mode, this ratio determines the word transfer rate. The divide ratio ranges from 1 to 32 (DC[4:0] = 00000 to 11111) for Normal mode, and from 2 to 32 (DC[4:0] = 00001 to 11111) for Network mode.

In Network mode, a divide ratio of 1 (DC[4:0] = 00000) is a special case (On-Demand mode). In Normal mode, a divide ratio of 1 (DC[4:0] = 00000) provides continuous periodic data word transfers. In this case, a bit-length sync must be used. Hardware and software reset clear the DC4–DC0 bits.

8.3.1.3 Word Length Control (WL0–WL1)—Bits 13–14

The Word Length Control (WL0 and WL1) bits are used to select the length of the data words being transferred via the SSI. Word lengths of 8, 12, or 16 bits can be selected according to the assignment described in **Table 8-2**. Hardware and software reset clear the WL1 and WL0 bits.



SSI Programming Model

Synchronous Serial Interface

Table 8-2 SSI Word Length Selection

WL1	WLO	Number of Bits Per Word
0	0	8
0	1	12
1	0	16
1	1	Reserved

8.3.1.4 Prescaler Range (PSR)—Bit 15

The Prescaler Range (PSR) bit controls a fixed divide-by-eight prescaler in series with the variable prescaler. This bit extends the prescaler range for those cases where a slower bit clock is desired. The minimum internally generated bit clock frequency is:


fosc/2/8/256 = fosc/4096

The maximum internally generated bit clock frequency is fosc/4. When the PSR bit is set, the fixed prescaler is bypassed. When the PSR bit is cleared, the fixed divide-by-eight prescaler is used. Hardware and software reset clear the PSR bit.

Note: The combination PSR = 1 and PM[7:0] = \$00 is reserved, and may cause synchronization problems if used.

8.3.2 SSI Control Register B (CRB)

The SSI Control Register B (CRB) is one of three 16-bit read/write control registers used to direct the operation of the SSI. The CRB controls the serial output flag, the SSI interrupts enables, and transmitter and receiver enable. The CRB bits are described in the following paragraphs. **Figure 8-3** shows the programming model for the CRB. Hardware and software reset clear all the bits in the CRB.



Read/Write

AA0737

Figure 8-3 SSI Control Register B Programming Model

^{*} Indicates reserved bits, read as 0 and should be written with 0 for future compatibility



Synchronous Serial Interface

SSI Programming Model

8.3.2.1 Serial Output Flag 0 (OF0)—Bit 0

When the SSI is in the Synchronous mode (the SYN bit in the CRC is set) the SC0 pin is configured as Serial I/O Flag 0. When the SCD0 bit in the CRC is set, the SC0 pin is an output, and data present in the OF0 bit is written to the SC0 pin either at the beginning of the frame in Normal mode, or at the beginning of the next time slot in Network mode. Hardware and software reset clear the OF0 bit.

8.3.2.2 Serial Output Flag 1 (OF1)—Bit 1

When the SSI is in the Synchronous mode (the SYN bit in the CRC is set) the SC1 pin is configured as Serial I/O Flag 1. When the SCD1 bit in the CRC is set, the SC1 pin is an output, and data present in the OF1 bit is written to the SC1 pin either at the beginning of the frame in Normal mode, or at the beginning of the next time slot in Network mode. Hardware and software reset clear the OF1 bit. Hardware and software reset clear the OF1 bit.

The normal sequence for setting output flags when transmitting data is:

- 1. Wait for the TDE bit to be set, indicating the TX register is empty.
- 2. Write the OF0 and OF1 bits flags.
- 3. Write the transmit data to the TX register.

The OF0 and OF1 bits are double-buffered so that the flag states appear on the pins when the TX data is transferred to the transmit shift register (i.e., the flags are synchronous with the data).

Note: The optional serial output pins timing (SC0 and SC1) are controlled by the frame timing and are not affected by the TE or RE bits.

8.3.2.3 Reserved Bits 2–7

Bits 2-7 in the CRB are reserved bits. They read as 0 and must be written with 0 for future compatibility.

8.3.2.4 Transmit Enable (TE)—Bit 8

The Transmit Enable (TE) bit enables the transfer of data from the Transmit Data (TX) register to the Transmit Shift Register. When the TE bit is set and a frame sync is detected, the transmit portion of the SSI is enabled for that frame. When the TE bit is cleared, the transmitter is disabled after completing transmission of data currently in the Transmit Shift Register. The STD output pin is tri-stated, and any data present in the TX register is not transmitted. Data can be written to the TX register when the TE bit is cleared, but no data is transferred to the Transmit Shift Register.

The Normal mode transmit enable sequence is to write data to the TX register (or Transmit Shift Register) before setting the TE bit. The normal transmit disable





Synchronous Serial Interface

SSI Programming Model

sequence is to clear the TE, TIE, and TEIE bits after the TDE flag bit in the SSI Status Register (SSISR) is set.

In the Network mode, the operation of clearing and then resetting the TE bit disables the transmitter after completing transmission of the current data word until the beginning of the next frame. During that time period, the STD pin remains in the high-impedance state. Hardware reset and software reset clear the TE bit.

The On-Demand mode transmit enable sequence can be the same as the Normal mode, or TE can be left enabled.

Note: The TE bit does not affect the generation of frame sync or output flags.

 Table 8-3
 Mode and Pin Definition Table

C	ontrol B	its	SSI Pins											
SYN	TE	RE	SC0	SC1	SC2	SCK	STD	SRD						
0	0	0	_	_	_	_	—	_						
0	0	1	RXC	FSR	_	_	_	RD						
0	1	0	_	_	FST	TXC	TD	_						
0	1	1	RXC	FSR	FST	TXC	TD	RD						
1	0	0	F0/U	F1/U	FS	XC	_	_						
1	0	1	F0/U	F1/U	FS	XC	_	RD						
1	1	0	F0/U	F1/U	FS	XC	TD	_						
1	1	1	F0/U	F1/U	FS	XC	TD	RD						
Legen	d:		1		•									
TXC RXC	Receive	nitter Cl er Clock			FS	(Synchrono	r/Receiver F ous Operatio							
XC			eceiver Clo	ck	TD	Transmit D								
FST			Operation)		RD F0/U	Receive Da								
FSR		er Frame	ame Sync		F1/U	Flag 1 / Unused								
rok	Receiv	ci riaili	Sylic		— —	Flag 1 / Unused Unused (can be used as GPIO pin)								

Note: A pin can be used for GPIO if its corresponding bit in the Port Control Register is cleared.



Synchronous Serial Interface

SSI Programming Model

8.3.2.5 Receive Enable (RE)—Bit 9

The Receive Enable (RE) bit controls the receive portion of the SSI. When the RE bit is set, the receive portion of the SSI is enabled. When the RE bit is cleared, the receiver is disabled by inhibiting data transfer into the Receive Data (RX) register. If data is being received while the RE bit is cleared, the remainder of the word is shifted in and transferred to the RX register. The RE bit must be set in the Normal mode and On-Demand mode to receive data. In Network mode, the operation of clearing RE and then resetting it disables the receiver after reception of the current data word until the beginning of the next data frame. Hardware and software reset clear the RE bit.

Note: The RE bit does not affect the generation of a frame sync.

8.3.2.6 Transmit Interrupt Enable (TIE)—Bit 10

The Transmit Interrupt Enable (TIE) control bit enables transmit interrupts. When the TIE control bit and the TDE flag bit in the SSISR are set, the DSP is interrupted. When the TIE bit is cleared, the transmit interrupt is disabled. Writing to the TX register or to the Transmit Shift Register clears the TDE bit, thus clearing the interrupt.

Transmit interrupts with exception have higher priority than normal transmit data interrupts. Therefore, if an exception occurs (the TUE bit is set) and the TEIE bit is set, the SSI requests an SSI Transmit Data with Exception interrupt from the interrupt controller. Hardware and software reset clear the TIE bit.

8.3.2.7 Receive Interrupt Enable (RIE)—Bit 11

The Receive Interrupt Enable (RIE) bit enables the receive interrupt. When the RIE bit is set, the DSP is interrupted when the RDF bit in the SSISR is set. When the RIE bit is cleared, this interrupt is disabled. Reading the RX register clears the RDF bit, thus clearing the pending interrupt.

Receive interrupts with exception have higher priority than normal receive data interrupts. Therefore, if an exception occurs (the ROE bit is set) and REIE is set, the SSI requests an SSI Receive Data with Exception interrupt from the interrupt controller. Hardware and software reset clear the RIE bit.

8.3.2.8 Transmit Last Slot Interrupt Enable (TLIE)—Bit 12

The Transmit Last Slot Interrupt Enable (TLIE) control bit enables an interrupt at the beginning of last slot of a frame in Network mode. When the TLIE bit is set, the DSP is interrupted at the start of the last slot in a frame in Network mode. When the TLIE bit is cleared, the Transmit Last Slot interrupt is disabled. The TLIE function is disabled when DC[4:0] = \$0 (On-Demand mode). Hardware and software reset clear the TLIE bit. The use of the Transmit Last Slot interrupt is described in **SSI Exceptions** on page 8-24.



Synchronous Serial Interface

SSI Programming Model

8.3.2.9 Receive Last Slot Interrupt Enable (RLIE)—Bit 13

The Receive Last Slot Interrupt Enable (RLIE) control bit enables an interrupt after the last slot of a frame ended in Network mode only. When the RLIE bit is set, the DSP is interrupted after the last slot in a frame has ended. When the RLIE bit is cleared, the Receive Last Slot interrupt is disabled. The RLIE bit is disabled when DC[4:0] = \$0 (On-Demand mode). Hardware and software reset clear the RLIE bit. The use of the Receive Last Slot interrupt is described in **SSI Exceptions** on page 8-24.

Transmit Exception Interrupt Enable (TEIE)—Bit 14 8.3.2.10

When the Transmit Exception Interrupt Enable (TEIE) control bit is set, the DSP is interrupted when both the TDE and TUE bits in the SSISR are set. When the TEIE bit is cleared, this interrupt is disabled. Reading the SSISR followed by writing to the transmitter data registers clears the TUE bit, thus clearing the pending interrupt. Hardware and software reset clear the TEIE bit.

Receive Exception Interrupt Enable (REIE)—Bit 15 8.3.2.11

When the Receive Exception Interrupt Enable (REIE) control bit is set, the DSP is interrupted when both the RDF and ROE bits in the SSISR are set. When the REIE bit is cleared, this interrupt is disabled. Reading the SSISR followed by reading the receive data register clears the ROE bit, thus clearing the pending interrupt. Hardware and software reset clear the REIE bit.

SSI Control Register C (CRC) 8.3.3

The SSI Control Register C (CRC) is one of three 16-bit read/write control registers used to direct the operation of the SSI. The CRC controls the SSI multifunction pins, SC2, SC1, and SC0, which can be used as clock inputs or outputs, frame synchronization pins or serial I/O flag pins. The direction control bits for the serial control pins are in the CRC. Operating modes are also selected in this register. Hardware and software reset clear all the bits in the CRC. The SSI CRC bits are described in the following paragraphs. Figure 8-4 shows the programming model for the CRC. Hardware and software reset clear all the bits in the CRC.

Go to: www.freescale.com



chronous Serial Interface

SSI Programming Model

Read/Write

CRC0—X:\$FFB8	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
CRC1—X:\$FFA8	FSP	FSR	FS	FS	*	*	*	*	SH	СКР	SC	SC	SC	sc	MOD	SYN
SSI Control			L1	L0					FD		KD	D2	D1	D0		
Register C															ш	
Reset = $$0000$																

^{*} Indicates reserved bits, read as 0 and should be written with 0 for future compatibility

AA0738

Figure 8-4 SSI Control Register C Programming Model

8.3.3.1 Asynchronous /Synchronous (SYN)—Bit 0

The Asynchronous/Synchronous (SYN) control bit selects whether the receive and transmit functions of the SSI occur synchronously or asynchronously with respect to each other. When the SYN bit is set, Synchronous mode is chosen and the transmit and receive sections use common clock and frame sync signals. When the SYN bit is cleared, Asynchronous mode is chosen and separate clock and frame sync signals are used for the transmit and receive sections. Hardware reset and software reset clear the SYN bit.

8.3.3.2 SSI Mode Select (MOD)—Bit 1

The SSI Mode Select (MOD) control bit selects the operational mode of the SSI. When the MOD bit is cleared, Normal mode is selected. When the MOD bit is set, Network mode is selected. In Normal mode, the Frame Rate Divider Control (DC4–DC0) bits determine the word transfer rate. One word can be transferred per frame sync during the frame sync time slot. In Network mode, a word can be transferred during every time slot. Hardware and software reset clear the MOD bit.

8.3.3.3 Serial Control 0 Direction (SCD0)—Bit 2

The Serial Control 0 Direction (SCD0) control bit selects the direction of the SC0 pin. When the SCD0 bit is set, the SC0 pin is an output. When the SCD0 bit is cleared, the SC0 pin is an input. Hardware and software reset clear the SCD0 bit.

8.3.3.4 Serial Control 1 Direction (SCD1) —Bit 3

The Serial Control 1 Direction (SCD1) control bit selects the direction of the SC1 pin. When the SCD1 bit is cleared, the SC1 pin is an input. When the SCD bit 1 is set, the SC1 pin is an output. Hardware and software reset clear the SCD1 bit.

8.3.3.5 Serial Control 2 Direction (SCD2)—Bit 4

The Serial Control 2 Direction (SCD2) control bit selects the direction of the SC2 pin. When the SCD2 bit is cleared, the SC2 pin is an input. When the SCD2 bit is set, the SC2 pin is an output. Hardware and software reset clear the SCD2 bit.





Synchronous Serial Interface

SSI Programming Model

8.3.3.6 Clock Source Direction (SCKD)—Bit 5

The Clock Source Direction (SCKD) control bit selects the source of the clock signal used to clock the Transmit Shift register in the Asynchronous mode and the Transmit Shift register and the Receive Shift register in the Synchronous mode. When the SCKD bit is set in Asynchronous mode, the internal clock source becomes the bit clock for the Transmit Shift register and word length divider, and is the output on the SCK pin. When the SCKD bit is cleared, the clock source is external, the internal clock generator is disconnected from the SCK pin, and an external clock source can drive the SCK pin. Hardware and software reset clear the SCKD bit.

8.3.3.7 Clock Polarity (CKP)—Bit 6

The Clock Polarity (CKP) control bit controls on which bit the clock edge data and frame sync are clocked out and latched in. When the CKP bit is cleared, the data and the frame sync are clocked out on the rising edge of the transmit bit clock and latched in on the falling edge of the receive bit clock. When the CKP bit is set, the falling edge of the transmit clock is used to clock the data out and frame sync, and the rising edge of the receive clock is used to latch the data and frame sync in. Hardware and software reset clear the CKP bit.

8.3.3.8 Shift Direction (SHFD)—Bit 7

The Shift Direction (SHFD) control bit causes the Transmit Shift register to shift data out MSB first when SHFD is cleared, and LSB first when SHFD is set to 1. Received data is shifted in MSB first when SHFD is cleared or LSB first when SHFD equals 1. Hardware and software reset clear the SHFD bit.

8.3.3.9 Reserved Bits 8–11

Bits 8–11 in the CRC are reserved bits. They are read as 0 and should be written with 0 to ensure future compatibility.

8.3.3.10 Frame Sync Length (FSL0–FSL1)—Bits 12–13

The Frame Sync Length (FSL1–FSL0) control bits select the length of frame sync to be generated or recognized. If FSL1 and FSL0 are both cleared, a word-length frame sync is selected for both TX and RX that is the length of the data word defined by bits WL1 and WL0. If the FSL1 bit is set and the FSL0 bit is cleared, a 1-bit clock period frame sync is selected for both TX and RX. When the FSL0 bit is set, the TX and RX frame syncs are different lengths. The FSL0 bit is ignored when the SYN bit is set. Encoding of the FSL1 and FSL0 bits is described in **Table 8-4**. Hardware reset and software reset clear FSL0 and FSL1.



Synchronous Serial Interface

SSI Programming Model

Table 8-4 FSL1 and FSL0 Encoding

FSL1	FSL0	Frame Sync Length
0	0	Word-length bit clock for both TX/RX
0	1	One-bit clock for TX and Word-length bit clock for RX
1	0	One-bit clock for both TX/RX
1	1	One-bit clock for RX and Word-length bit clock for TX

8.3.3.11 Frame Sync Relative Timing (FSR)—Bit 14

The Frame Sync Relative Timing (FSR) control bit determines the relative timing of the receive and transmit frame sync signal as referred to the serial data lines, for a word length frame sync only. When the FSR bit is set, the word length frame sync occurs one serial clock cycle earlier (i.e., together with the last bit of the previous data word). When the FSR bit is cleared, the word length frame sync occurs together with the first bit of the data word of the first slot. Hardware reset and software reset clear the FSR bit.

8.3.3.12 Frame Sync Polarity (FSP)—Bit 15

The Frame Sync Polarity (FSP) bit determines the polarity of the receive and transmit frame sync signals. When FSP is set, the frame sync signal polarity is negative (that is, the frame start is signaled by the low level of the frame sync pin). When the FSP bit is cleared, the frame sync signal polarity is positive (i.e., the frame start is signaled by the high level of the frame sync pin). Hardware reset and software reset clear the FSP bit.

8.3.4 SSI Status Register (SSISR)

The SSI Status Register (SSISR) is an 8-bit read-only status register used by the DSP to read the status and serial input flags of the SSI. When the SSISR is read to the internal data bus, the register contents occupy the low-order byte of the data bus, and the remaining bits are read as 0. The status bits are described in the following paragraphs. **Figure 8-5** shows the programming model for the SSISR.



Synchronous Serial Interface

SSI Programming Model

SSISR0-X:\$FFB9	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
SSISR1—X:\$FFA9	*	*	*	*	*	*	*	*	RDF	TDE	ROE	TUE	RFS	TFS	IF1	IF0
SSI Status Register																
Reset = \$0040 ^l													l			ш
Read/Write																

^{*} Indicates reserved bits, read as 0 and should be written with 0 for future compatibility

AA0739

Figure 8-5 SSI Status Register Programming Model

8.3.4.1 Serial Input Flag 0 (IF0)—Bit 0

The SSI latches data present on the SC0 pin during reception of the first received bit after frame sync is detected. The IF0 bit is updated with this data when the Receive Shift Register is transferred into the RX register. The IF0 bit is enabled only when the SC0 pin is programmed as SSI in the PCR, the SYN bit is set, and the SCD0 bit (in the CRC) is cleared, indicating that SC0 is an input flag and the Synchronous mode is selected. Otherwise, the IF0 bit reads as a 0 when it is not enabled. Hardware, software, SSI individual, and STOP reset clear IF0.

8.3.4.2 Serial Input Flag 1 (IF1)—Bit 1

The SSI latches data present on the SC1 pin during reception of the first received bit after frame sync is detected. The IF1 bit is updated with this data when the Receive Shift Register is transferred into the RX register. The IF1 bit is enabled only when the SC1 pin is programmed as SSI in the PCR, the SYN bit is set, and the SCD1 bit (in the CRC) is cleared, indicating that SC1 is an input flag and Synchronous mode is selected. Otherwise, the IF1 bit is read as 0 when it is not enabled. Hardware, software, SSI individual, and STOP reset clear the IF1 bit.

8.3.4.3 Transmit Frame Sync Flag (TFS)—Bit 2

The Transmit Frame Sync Flag (TFS) bit indicates whether a transmit frame synch has occurred in the current time slot. The TFS bit is set at the start of the first time slot in the frame, and cleared during all other time slots. In Network mode, data written to a transmit data register during the time slot when the TFS bit is set is transmitted (if the transmitter is enabled) during the second time slot in the frame. The TFS bit is useful in Network mode to identify the start of a frame. The TFS bit is cleared by hardware, software, SSI individual, or STOP reset. The TFS bit is valid only if the transmitter is enabled (the TE bit in the CRB is set).

Note: In Normal mode, the TFS bit is always read as 1 when transmitting data because there is only one time slot per frame—the "frame sync" time slot.



Synchronous Serial Interface

SSI Programming Model

8.3.4.4 Receive Frame Sync Flag (RFS)—Bit 3

When set, the Receive Frame Sync Flag (RFS) bit indicates that a receive frame sync occurred during reception of the word in the serial receive data register. This indicates that the data word is from the first time slot in the frame. In Network mode, when the RFS bit is cleared and a word is received, it indicates that the frame sync did not occur during reception of that word.

The RFS bit is cleared by hardware, software, SSI individual, or STOP reset. The RFS bit is valid only if the receiver is enabled by setting the RE bit in the CRB.

Note: In Normal mode, the RFS bit is always read as 1 when reading data because there is only one time slot per frame— the "frame sync" time slot.

8.3.4.5 Transmitter Underrun Error Flag (TUE)—Bit 4

The Transmitter Underrun Error Flag (TUE) bit indicates whether a transmit underrun error has occurred. The TUE bit is set when the Transmit Shift Register is empty (no new data is available to be transmitted) and a transmit time slot occurs. When a transmit underrun error occurs, the previous data, which is still present in the TX register that was not written, is retransmitted.

In Normal mode, a frame contains only one transmit time. In Network mode, a frame can contain as many as 32 transmit time slots.

If the TEIE bit is set, a DSP Transmit Underrun Error Interrupt request is issued when the TUE bit is set. Hardware, software, SSI individual, and STOP reset clear the TUE bit. The TUE bit is also cleared by reading the SSISR with this bit set, followed by writing to the transmit data registers or to TSR.

8.3.4.6 Receiver Overrun Error Flag (ROE)—Bit 5

The Receiver Overrun Error Flag (ROE) bit indicates that a receive overrun error has occurred. The ROE bit is set when the Receive Shift Register is filled and ready to transfer to the RX register and RX is already full (i.e., RDF = 1). If the REIE bit is set, a DSP Receiver Overrun Error Interrupt request is issued when the ROE bit is set. Hardware, software, SSI individual, and STOP reset clear the ROE bit. The ROE bit is also cleared by reading the SSISR with this bit set, followed by reading the RX register.

8.3.4.7 Transmit Data Register Empty (TDE)—Bit 6

The Transmit Data Register Empty (TDE) bit is set when the contents of the Transmit Data (TX) register is transferred to the Transmit Shift Register. This bit is also set for a TSR disabled time slot period in Network mode (as if data were being transmitted after the TSR was written). When set, the TDE bit indicates that data should be written to the TX register or to the Time Slot Register (TSR). The TDE bit is cleared





Synchronous Serial Interface

SSI Programming Model

when the DSP writes to the transmit data register, or when the DSP writes to the TSR to disable transmission of the next time slot. If the TIE bit is set, a DSP transmit data interrupt request is issued when the TDE bit is set. Hardware, software, SSI individual, and STOP reset set the TDE bit.

8.3.4.8 Receive Data Register Full (RDF)—Bit 7

The Receive Data Register Full (RDF) bit is set when the contents of the receive shift register are transferred to the receive data register. The RDF bit is cleared when the DSP reads the SSI Receive Data Register (RX) or cleared by hardware, software, SSI individual, or STOP reset. If the RIE bit (in the CRB) is set, a DSP receive data interrupt request is issued when the RDF bit is set.

8.3.4.9 Reserved Bits 8–15

Bits 8–15 are reserved for future use. They are read as 0 and should be written with 0 for future compatibility.

8.3.5 Receive Shift Register

The Receive Shift Register is a 16-bit shift register that receives the incoming data from the SRD pin. Data is shifted in by the selected bit clock (internal or external) when the associated frame sync I/O is asserted. Data is received LSB first if the SHFD bit (in the CRC) is set, and MSB first if the SHFD bit is cleared. Data is transferred to the Receive Data Register after 8, 12, or 16 serial clock cycles are counted, depending on the Word Length (WL1–0) bits in the CRA.

8.3.6 Receive Data Register (RX)

The Receive Data Register (RX) is a 16-bit read-only register that accepts data from the Receive Shift Register as it becomes full. The data read occupies the most significant portion of the RX register. The unused bits (least significant portion) are read as 0. If the associated interrupt is enabled, the DSP is interrupted whenever the RX register becomes full.

8.3.7 Transmit Shift Register

The Transmit Shift Register is a 16-bit shift register that contain the data being transmitted. Data is shifted out to the Serial Transmit Data (STD) pin by the selected bit clock (internal or external) when the associated frame sync I/O is asserted. The



Synchronous Serial Interface

SSI Programming Model

number of bits shifted out before the Transmit Shift Register is considered empty and can be written to again can be 8, 12, or 16 bits, depending on the Word Length (WL1–0) bits in the CRA. The data to be transmitted occupies the most significant portion of the shift register. The unused portion of the register is ignored. Data is shifted out of this register LSB first if the SHFD bit (in the CRC) is set, and MSB first if the SHFD bit is cleared. (This is the same direction as the Receive Shift Register.)

8.3.8 Transmit Data Register (TX)

The Transmit Data (TX) register is a 16-bit write-only register. Data to be transmitted is written into this register and is automatically transferred to the transmit shift register. The data written (8, 12 or 16 bits) should occupy the most significant portion of the TX. The unused bits (least significant portion) of the TX register are don't care bits. If the TEIE bit has been enabled, the DSP is interrupted when the TX register becomes empty.

8.3.9 Time Slot Register (TSR)

The Time Slot Register (TSR) is effectively a null data register that is used when the data is not to be transmitted in the available transmit time slot. For the purposes of timing, the TSR is a write-only register that behaves like an alternative transmit data register, except that, rather than transmitting data, the transmit data pin is in the high-impedance state for that time slot.

8.3.10 Port Control Register (PCR)

The Port Control Register (PCR) is a 16-bit read/write register that controls the functionality of the SSI GPIO pins. The PCRC is associated with SSI0. The PCRD is associated with SSI1. Figure 8-6 shows the programming model for the PCR. Hardware and software reset clear all PCR bits.



Read/Write

Freescale Semiconductor, Inc.

Synchronous Serial Interface

SSI Programming Model

PCRC—X:\$FFBF	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
PCRD—X:\$FFAF	*	*	*	*	*	*	*	*	PEN	*	PC5	PC4	PC3	PC2	PC1	PC0
SSI Port Control																
Register ^l								<u> </u>			L			<u> </u>		
Reset = \$0000																

^{*} Indicates reserved bits, read as 0 and should be written with 0 for future compatibility

AA0740

Figure 8-6 SSI Port Control Register Programming Model

8.3.10.1 Port Control (PC0–PC5)—Bits 0–5

The Port Control (PC0–PC5) bits control the functionality of a corresponding port pin. When a PC bit is set, the corresponding port pin is configured as a SSI pin. When a PC bit is cleared, the corresponding port pin is configured as GPIO pin.

8.3.10.2 Port Enable (PEN)—Bit 7

When the Port Enable (PEN) control bit is set, all SSI pins are activated as defined by all other settings. When the PEN bit is cleared, all SSI pins are tri-stated, ignoring all other settings.

8.3.10.3 Reserved Bits—Bits 6, 8–15

Bit 6 and bits 8–15 are reserved. They are read as 0 and should be written as 0 to ensure future compatibility.

8.3.11 Port Direction Register (PRR)

The Port Direction Register (PRR) is a 16-bit read/write register that controls the direction of SSI GPIO pins. The PRRC is associated with SSI0. The PRRD is associated with SSI1. When a port pin is configured as GPIO, the PDC bit controls the port pin direction. When the PDC bit is set, the GPIO port pin is configured as output. When the PDC bit is cleared the GPIO port pin is configured as input. Hardware and software reset clear all PRR bits.



Synchronous Serial Interface

SSI Programming Model

Read/Write

PRRC—X:\$FFBE	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
PRRD—X:\$FFAE	*	*	*	*	*	*	*	*	*	*	PD	PD	PD	PD	PD	PD
SSI GPIO Direction											PD C5	C4	C3	C2		C0
Control Register																
Reset - \$0000																

^{*} Indicates reserved bits, read as 0 and should be written with 0 for future compatibility

Figure 8-7 SSI GPIO Direction Control Register Programming Model

Table 8-5 describes the port pin configurations.

Table 8-5 PCR and PRR Register Bits Functionality

PC	PDC	Port Pin Function
1	0 or 1	SSI
0	0	GPIO input
0	1	GPIO output

Note: When the PEN bit in the PCR is cleared, the port is disabled and all the pins are at high impedance regardless of the values of the PC and PDC bits.

8.3.12 Port Data Register (PDR)

The read/write 16-bit Port Data Register (PDR) is used to read or write data to or from the SSI GPIO pins. The PDRC is associated with SSI0, and the PDRD is associated with SSI1. Bits PD[5:0] are used to read or write data to or from the corresponding port pins if they are configured as GPIO (by PC[5:0] bits in the PCR). If a port pin is configured as a GPIO input, then the corresponding PD bit reflects the value present on this pin. If a port pin is configured as a GPIO output, then the value written into the corresponding PD bit is reflected on the this pin. Hardware and software reset clear all PDR bits.

Synchronous Serial Interface

Operating Modes

Data Register Reset = \$0000 Read/Write

Figure 8-8 SSI GPIO Data Register Programming Model

8.4 OPERATING MODES

SSI operating modes are selected by the SSI Control Registers CRA, CRB, and CRC. The main operating modes are described in the following paragraphs.

Hardware or software reset clears the Port Control Register (PCR) and the Port Direction Control Register (PRR), which configure all SSI pins to be at high impedance. The SSI is reset while all SSI pins are programmed as GPIO and is active only when at least one of the SSI I/O pins is programmed as an SSI pin.

The correct way to initialize the SSI is as follows:

- 1. Hardware, software, SSI individual, or STOP reset
- 2. Program SSI control according to the desired functionality

During program execution, the PC[5:0] bits in the PCR can be cleared, causing the SSI to stop serial activity and enter the individual reset state. All status bits of the interface are then set to their reset state. However, the contents of CRA, CRB, and CRC are not affected. This procedure allows the DSP program to reset each interface separately from the other internal peripherals. During individual reset, internal DMA accesses to the data registers of the SSI are not valid and any data read will not be valid.

To ensure proper operation of the interface, the DSP program must reset the SSI before changing any of its control registers except for the CRB.

^{*} Indicates reserved bits, read as 0 and should be written with 0 for future compatibility

AA0742



Operating Modes

8.4.1 SSI Exceptions

The SSI can generate the following exceptions, ordered from the highest to the lowest priority:

- 1. SSI Receive Data with Exception Status—This exception occurs when the receive exception interrupt is enabled, the receive data register is full, and a receiver overrun error has occurred. ROE is cleared by first reading the SSISR and then reading RX.
- 2. SSI Receive Data—This exception occurs when the receive interrupt is enabled, the receive data register is full, and no receive error conditions exist. Reading RX clears the pending interrupt. This error-free interrupt can use a fast interrupt service routine for minimum overhead.
- 3. SSI Receive Last Slot Interrupt—This exception occurs after the last slot of the frame ended (in Network mode only). The Receive Last Slot interrupt can be used to reconfigure the DMA channels and reassignment of data memory pointers. Using the Receive Last Slot interrupt guarantees that the previous frame was serviced with the previous setting and the new frame is to be serviced with the new setting without synchronization problems. Note that the maximum Receive Last Slot interrupt service time should not exceed N 1 SSI bits service time (where N is the number of bits in a slot).
- 4. SSI Transmit Data with Exception Status—This exception occurs when the transmit exception interrupt is enabled, the transmit data register is empty, and a transmitter underrun error has occurred. TUE is cleared by first reading the SSISR and then writing to the transmit data register, or to the TSR to clear the pending interrupt.
- 5. SSI Transmit Last Slot Interrupt—This exception occurs at the start of the last slot of the frame in Network mode. The Transmit Last slot interrupt can be used to reconfigure the DMA channels and reassignment of data memory pointers. Using the Transmit last slot interrupt guarantees that the previous frame was serviced with the previous setting and the new frame is to be serviced with the new setting without synchronization problems. Note that the maximum Transmit last slot interrupt service time should not exceed N 1 SSI bits service time (Where N is the number of bits in a slot).
- 6. SSI Transmit Data—This exception occurs when the transmit interrupt is enabled, and the transmit data register is empty, and no transmitter error conditions exist. Writing to the TX registers or to the TSR clears this interrupt. This error-free interrupt can use a fast interrupt service routine for minimum overhead.



Synchronous Serial Interface

Operating Modes

8.4.2 Operating Modes-Normal, Network, and On-Demand

The SSI has three basic operating modes and many data/operation formats. These modes can be programmed by several bits in the SSI control registers.

The data/operation formats available to the SSI are selected by setting or clearing control bits in the CRA and CRC. These control bits are DC4–DC0, WL1, WL0, MOD, SYN, FSL1, FSL0, FSR, FSP, CKP, and SHFD.

8.4.2.1 Operating Mode Selection

Selecting between the Normal mode and Network mode is accomplished by clearing or setting the MOD bit in the CRC. In Normal mode, the SSI functions with one data word of I/O per frame. In Network mode, two to 32 time slots per frame can be selected. During each frame, 0 to 32 data words of I/O can be received or transmitted. In either case, the transfers are periodic. Normal mode is typically used to transfer data to or from a single device. Network mode is typically used in Time Division Multiplexed (TDM) networks of codecs or DSPs with multiple words per frame.

Setting the MOD bit in the CRC, as for Network mode, and setting the frame rate divider to 0 (DC[4:0] = 00000) selects the On-Demand mode. This special case does not generate a periodic frame sync. Instead, a frame sync pulse is generated only when data is available to transmit. The frame sync signal indicates the first time slot in the frame. The On-Demand mode requires that the transmit frame sync be internal (output) and the receive frame sync be external (input). Therefore, for simplex operation, the Synchronous mode could be used; however, for full-duplex operation, the Asynchronous mode must be used. Data transmission that is data driven is enabled by writing data into the TX register. Although the SSI is double-buffered, only one word can be written to the TX register, even if the transmit shift register is empty. The receive and transmit interrupts function as usual using the TDE and RDF flag bits. However, transmit underruns are impossible for on-demand transmission and are disabled. This mode is useful for interfacing to codecs that require a continuous clock.

8.4.2.2 Synchronous/Asynchronous Operating Modes

The transmit and receive sections of this interface can be synchronous or asynchronous—the transmitter and receiver can use common clock and synchronization signals (Synchronous mode) or they can have their own separate clock and sync signals (Asynchronous mode). The SYN bit in the CRC selects synchronous or asynchronous operation. Since the SSI is designed to operate either synchronously or asynchronously, separate receive and transmit interrupts are provided.



Synchronous Serial Interface

Operating Modes

When the SYN bit is cleared, the Asynchronous mode is selected and the SSI TX and RX clocks and frame sync sources are independent. When the SYN bit is set, the SSI TX and RX clocks and frame sync come from the same source (either external or internal).

Data clock and frame sync signals can be generated internally by the DSP or can be obtained from external sources. If internally generated, the SSI clock generator is used to derive bit clock and frame sync signals from the DSP internal system clock. The SSI clock generator consists of a selectable fixed prescaler and a programmable prescaler for bit rate clock generation and also a programmable frame-rate divider and a word-length divider for frame-rate sync-signal generation.

8.4.2.3 Frame Sync Selection

The transmitter and receiver can operate independently of each other. The transmitter can have either a bit-long or word-long frame-sync signal format, and the receiver can have the same or opposite format. The selection is made by programming the FSL0 and FSL1 bits in the CRC.

- 1. If the FSL1 bit is cleared, the RX frame sync is asserted during the entire data transfer period. This frame sync length is compatible with Motorola codecs, SPI serial peripherals, serial A/D and D/A converters, shift registers, and telecommunication PCM serial I/O.
- 2. If FSL1 is set, the RX frame sync pulse is active for one bit clock immediately before the data transfer period. This frame sync length is compatible with Intel and National components, codecs, and telecommunication PCM serial I/O.

The ability to mix frame sync lengths is useful in configuring systems in which data is received from one type device (e.g., codec) and transmitted to a different type device.

The FSL0 bit controls whether RX and TX have the same frame sync length. If FSL0 equals 0, RX and TX have the same frame sync length, which is selected by FSL1. If FSL0 equals 1, RX and TX have different frame sync lengths, which are selected by FSL1. FSL0 is ignored when the SYN bit is set.

The FSR bit controls the relative timing of the word length frame sync as referred to the data word. When the FSR bit is cleared, the word length frame sync is generated (or expected) with the first bit of the data word. When the FSR bit is set, the word length frame sync is generated (or expected) with the last bit of the previous word. The FSR bit is ignored when a bit length frame sync is selected.



Synchronous Serial Interface

Operating Modes

The FSP bit controls the polarity of the frame sync. When FSP is cleared the polarity of the frame sync is positive (i.e., the frame sync signal is asserted high). When FSP is set the polarity of the frame sync is negative (i.e., the frame sync is asserted low.)

The SSI receiver looks for a receive frame sync leading edge (or trailing edge, if FSP is set) only when the previous frame is completed. If the frame sync goes high before the frame is completed (or before the last bit of the frame is received in the case of a bit frame sync or a word length frame sync with FSR set), the current frame sync is not recognized, and the receiver is internally disabled until the next frame sync. Frames do not have to be adjacent—that is, a new frame sync does not have to immediately follow the previous frame. Gaps of arbitrary periods can occur between frames. The transmitter is tri-stated during these gaps.

8.4.2.4 Shift Direction Selection

Some data formats, such as those used by codecs, specify MSB first. Other data formats, such as the AES-EBU digital audio, specify LSB first. To interface with devices from both systems, the shift registers in the SSI are bidirectional. The MSB/LSB selection is made by programming the SHFD bit in the CRC.

When the SHFD bit is cleared, data is shifted into the Receive Shift Register and shifted out of the Transmit Shift Register MSB first. If the SHFD bit is set, data is shifted into the Receive Shift Register and shifted out of the Transmit Shift Register LSB first.

8.4.3 Serial I/O Flags

Two SSI pins (SC1 and SC0) are available as serial I/O flags. Their operation is controlled by the SYN, SCD0, and SCD1 bits in the CRC. The control bits (OF1 and OF0) and status bits (IF1 and IF0) are double-buffered to and from the SC1 and SC0 pins. Double buffering the flags keeps them synchronized with TX and RX registers.

The flags are available in the Synchronous mode only (when the SYN bit is set). Each flag can be separately programmed. When flag 0 is enabled, its direction is selected by SCD0, SCD0 = 1 as output and SCD0 = 0 as input. In the same way when flag1 is enabled, its direction is selected by SCD1, SCD1 = 1 as output and SCD1 = 0 as input.

When programmed as input, the SC0 and SC1 pins are latched at the same time as the first bit of the receive data word is sampled. Since the input is latched, the signal on the input flag pins SC0 and SC1 can change without affecting the input flag until the first bit of the next receive data word. When the received data word is latched by the RX register, the latched values are then latched by the IF0 and IF1 bits (in the SSISR) and can be read by software.



Synchronous Serial Interface


Operating Modes

When programmed as output, the SC0 and SC1 pins are driven by the value from the OF0 and OF1 bits (in the CRB) and latched when the contents of the TX register is transferred to the transmit shift register. The values on the SC0 and SC1 pins are stable from the same time the first bit of the transmit data word is transmitted until the first bit of the next transmit data word is transmitted. Software can change the values of the OF0 and OF1 bits (in the CRB), thus controlling the SC0 and SC1 pin values for each transmitted word.





SECTION 9 TRIPLE TIMER MODULE





9.1	INTRODUCTION9-3
9.2	TRIPLE TIMER MODULE ARCHITECTURE 9-3
9.3	TIMER ARCHITECTURE 9-4
9.4	TRIPLE TIMER MODULE PROGRAMMING MODEL 9-6
9.5	TIMER MODES OF OPERATION 9-13





Introduction

Triple Timer Module

9.1 INTRODUCTION

This section describes the triple timer module, composed of a common 14-bit prescaler and three independent and identical general purpose 16-bit timer/event counters, each with its own memory-mapped register set.

Each timer can use internal or external clocking and can interrupt the DSP after a specified number of events (clocks) or can signal an external device after counting internal events. Each timer connects to the external world through one bidirectional pin, TIO. When the TIO pin is configured as an input, the timer functions as an external event counter or measures external pulse width/signal period. When the TIO pin is used as an output, the timer functions as either a timer, a watchdog, or a Pulse Width Modulator (PWM). When the TIO pin is not used by the timer, it can be configured as a General Purpose I/O (GPIO) pin.

9.2 TRIPLE TIMER MODULE ARCHITECTURE

The triple timer module includes a 16-bit Timer Prescaler Load Register (TPLR), a 16-bit Timer Prescaler Count Register (TPCR), a 14-bit Prescaler Counter, and three timers. Each one of the three timers can use the Prescaler Clock as its clock source.

The Timer Prescaler Load Register (TPLR) is a 16-bit read/write register that controls the Prescaler Divide Factor and the source for the prescaler input clock. The Timer Prescaler Count Register (TPCR) is a 16-bit read-only register that reflects the current value in the prescaler counter. The register bits are described in the following paragraphs. The 14-bit Prescaler Counter is decremented on each rising edge of the prescaler input clock pulse. The counter is enabled when at least one of the three timers is both enabled and is using the prescaler output as its source. Figure 9-1 shows a block diagram of the triple timer module.



Timer Architecture




Figure 9-1 Triple Timer Module Block Diagram

9.3 TIMER ARCHITECTURE

Figure 9-2 shows a block diagram of a timer. It includes a 16-bit counter, a 16-bit read/write Timer Control and Status Register (TCSR), a 16-bit read only Timer Count Register (TCR), a 16-bit write only Timer Load Register (TLR), a 16-bit read/write Timer Compare Register (TCPR), and logic for clock selection and interrupt generation. The DSP views each timer as a memory-mapped peripheral occupying four 16-bit words in the X data memory space. The user can use standard polled or interrupt programming techniques. The programming model is shown in **Figure 9-3** on page 9-6.





Triple Timer Module

Timer Architecture





Figure 9-2 16-bit Timer Module Block Diagram



Triple Timer Module Programming Model

9.4 TRIPLE TIMER MODULE PROGRAMMING MODEL

The registers comprising the Triple Timer Module are shown in **Figure 9-3**.



AA0745

Figure 9-3 Triple Timers Programming Model



Triple Timer Module

Triple Timer Module Programming Model

9.4.1 Timer Prescaler Load Register (TPLR)

The Timer Prescaler Load Register (TPLR) is a 16-bit read/write register that controls the prescaler divide factor and the source for the prescaler input clock. The control bits are described in the following paragraphs.

9.4.1.1 Prescaler Preload Value Bits (PL0-PL13)—Bits 0-13

The Prescaler Preload Value bits (PL0-PL13) contain the prescaler preload value. This preload value is loaded into the prescaler counter whenever either the counter reaches the value of 0 or the counter switches state from disabled to enabled. For PL[13:0] = N, the prescaler counts N + 1 source clock cycles before generating a prescaled clock pulse. Therefore, the prescaler divide factor is preload value + 1.

The PL0-PL13 bits are cleared by hardware and software reset.

9.4.1.2 Prescaler Source Bits (PS0-PS1)—Bits 14-15

The Prescaler Source (PS0–PS1) bits control the source of the prescaler clock. Table 9-1 summarizes the functionality of the PS bits. The DSP internal clock CLK divided by two is selected when the PS0-PS1 bits are cleared. The other combinations select one of the TIO pins as the source clock for the prescaler, regardless of the operating mode of the selected timer.

PS1	PS0	Prescaler Clock Source
0	0	DSP internal clock (CLK) divided by two
0	1	TIO0
1	0	TIO1
1	1	TIO2

Table 9-1 PS Bit Functionality

Notes:

- 1. If the prescaler source clock is external, the prescaler counter is incremented by the transitions on the TIO pin. The external clock is internally synchronized to the internal clock and its frequency should be lower than the DSP internal clock (CLK) divided by 4.
- 2. To ensure proper functionality, the PS0-PS1 bits should be changed only when the prescaler counter is disabled.

Go to: www.freescale.com

The PS0-PS1 bits are cleared by hardware and software reset.



Triple Timer Module Programming Model

9.4.2 Timer Prescaler Count Register (TPCR)

The Timer Prescaler Count Register (TPCR) is a 16-bit read-only register that reflects the current value in the prescaler counter. The register bits are described in the following paragraphs.

9.4.2.1 Prescaler Counter Value Bits (PC0–PC13)—Bits 0–13

The Prescaler Counter Value (PC0–PC13) bits contain the current value in the prescaler counter.

9.4.2.2 Reserved Bits (Bits 14–15)

These reserved bits are read as 0.

9.4.3 Timer Count Register (TCR)

The Timer Count Register (TCR) is a 16-bit read-only register. In Timer and Watchdog modes, the counter contents can be read at any time by reading the TCR. In Measurement modes, the TCR is loaded with the current value of the counter on the appropriate edge of the input signal and its value can be read to determine the width, period, or delay of the leading edge of the input signal (incoming on the TIO pin).

9.4.4 Timer Load Register (TLR)

The Timer Load Register (TLR) is a 16-bit write-only register. In all modes, the counter is preloaded with the TLR value after the Timer Enable (TE) bit in the TCSR is set and a first event occurs.

In Timer modes, if the Timer Reload Mode (TRM) bit is set, the counter is reloaded each time after it has reached the value contained by the Timer Compare Register (TCR) and the new event occurs. In Measurement modes, if the TRM bit is set, the counter is reloaded with the TLR value on each appropriate edge of the input signal, after the Timer Enable (TE) bit is set. In Pulse Width Modulation (PWM) modes, if the TRM bit is set, the counter is reloaded each time after it has overflowed and the new event occurs. In Watchdog modes, if the TRM bit is set, the counter is reloaded each time after it has reached the value contained by the Timer Compare Register and the new event occurs. In this mode, the counter is also reloaded whenever the TLR is written with a new value while the TE bit is set. In all modes, if the TRM bit is cleared, the counter operates as free running counter.



Triple Timer Module

Triple Timer Module Programming Model

9.4.5 Timer Compare Register (TCPR)

The Timer Compare Register (TCPR) is a 16-bit read/write register that contains the value to be compared to the counter value. The counter value is compared against the value in the TCPR on every timer clock after the Timer Enable (TE) bit is set. When the compare matches, the TCF bit is set. If interrupts are enabled (the TCIE bit is set), an interrupt is also generated. In Measurement modes, the TCPR is ignored.

9.4.6 Timer Control/Status Register (TCSR)

The Timer Control/Status Register (TCSR) is a 16-bit read/write register that controls the timer and reflects its status. The control and status bits are described in the following paragraphs (see **Figure 9-3** on page 9-6).

9.4.6.1 Timer Enable Bit (TE)—Bit 0

The Timer Enable (TE) bit is used to enable or disable the timer. Setting the TE bit (TE = 1) enables the timer and clears the Timer Count Register (TCR). The counter starts counting according to the mode defined by TC[3:0]. Clearing the TE bit disables the timer. The TE bit is cleared by hardware and software reset.

Note:

When all the three timers are disabled and not in GPIO mode, all three TIO pins are tristated. In order to prevent undesired spikes on the TIO pins (when switching from tri-state into active state), external pull-up or pull down resistors should be tied to the TIO pins.

9.4.6.2 Timer Overflow Interrupt Enable Bit (TOIE)—Bit 1

The Timer Overflow Interrupt Enable (TOIE) bit is used to enable the timer overflow interrupts. The overflow interrupt is generated after the counter wraparound occurs; that is, the counter value changes from \$FFFF to \$0000 when a new event occurs. Setting the TOIE bit enables the overflow interrupts. When the TOIE bit is cleared, the overflow interrupts are disabled. The TOIE bit is cleared by hardware and software reset.

9.4.6.3 Timer Compare Interrupt Enable Bit (TCIE)—Bit 2

The Timer Compare Interrupt Enable (TCIE) bit is used to enable the timer compare interrupts. The compare interrupt is generated after the counter matches the compare register in the Timer, PWM, or Watchdog modes. If the TCPR is loaded with N, an interrupt occurs after (N-M+1) events, where M is TLR value. Setting the TCIE bit enables the compare interrupts. When the TCIE bit is cleared, the compare interrupts are disabled. The TCIE bit is cleared by hardware and software reset.



Triple Timer Module Programming Model

9.4.6.4 Timer Control Bits (TC0–TC3)—Bits 4–7

The four Timer Control (TC0–TC3) bits control the source of the timer clock, the behavior of the TIO pin and the Timer mode of operation. **Table 9-2** summarizes the functionality of the TC bits. A detailed description of the timer operating modes is given in **Timer Modes of Operation** on page 9-13. The TC0–TC3 bits are cleared by hardware and software reset. To ensure proper functionality, the TC0–TC3 bits should be changed only when the timer is disabled

Note:

If the clock is external, the counter is incremented by transitions on the TIO pin. The external clock is internally synchronized to the internal clock and its frequency should be lower than the internal operating frequency divided by 4 (CLK/4).

Table 9-2 TC Bit Functionality

TC3	TC2	TC1	TC0	TIO	Clock	Mode
0	0	0	0	GPIO	Internal	Timer GPIO
0	0	0	1	Output	Internal	Timer Pulse
0	0	1	0	Output	Internal	Timer Toggle
0	0	1	1	Input	External	Event Counter
0	1	0	0	Input	Internal	Input Width
0	1	0	1	Input	Internal	Input Period
0	1	1	0	Input	Internal	Capture
0	1	1	1	Output	Internal	Pulse Width Modulation(PWM)
1	0	0	0	_	_	Reserved
1	0	0	1	Output	Internal	Watchdog Pulse
1	0	1	0	Output	Internal	Watchdog Toggle
1	0	1	1	_	_	Reserved
1	1	0	0	_	_	Reserved
1	1	0	1	_	_	Reserved
1	1	1	0	_	_	Reserved
1	1	1	1	Output	Internal	Timer Pulse



Triple Timer Module

Triple Timer Module Programming Model

9.4.6.5 Inverter Bit (INV)—Bit 8

The Inverter (INV) bit affects the polarity of the external incoming signal on the TIO pin when TIO is programmed as input, and affects the polarity of the pulse generated on the TIO pin when TIO is programmed as output. In the Timer modes, if the INV bit is set, the 1 to 0 transitions on the TIO input pin increment the counter. If TIO is programmed as input and the INV bit is cleared, the 0 to 1 transitions on the TIO input pin increment the counter. In the Input Width mode, the INV bit determines whether the high pulse or the low pulse is measured. In the Input Period mode, the INV bit determines whether the period is measured between rising or falling edges. If TIO is programmed as output and the INV bit is set, the pulse generated by the timer is inverted. If the INV bit is cleared, the pulse generated by the timer is of positive polarity;. The INV bit is cleared by hardware and software reset.

Notes: 1. The INV bit affects both the timer and the GPIO modes of operation.

- 2. To ensure proper functionality, the INV bit should be changed only when the timer is disabled or in GPIO mode of operation.
- **3.** When the TIO is used as input to the prescaler, the polarity of the prescaler source clock is not affected by the corresponding INV bit.

9.4.6.6 Timer Reload Mode Bit (TRM)—Bit 9

The Timer Reload Mode (TRM) control bit determines the counter preload operation. In Timer and Watchdog modes the counter is preloaded with the TLR value after the TE bit is set and a first event occurs. If the TRM bit is set, the counter is reloaded each time it reaches the value contained by the Timer Compare Register and the new event occurs. In PWM mode, the counter is reloaded each time counter wraparound occurs (overflow) and the new event occurs. In Measurement modes, the counter is preloaded with the TLR value (if TRM = 1) on each appropriate edge of the input signal after the TE bit is set. If TRM is cleared, the counter operates as a free-running counter, incrementing on each incoming event. The TRM bit is cleared by hardware and software reset.

9.4.6.7 Direction Bit (DIR)—Bit 10

The Direction (DIR) control bit determines the behavior of the TIO pin when used as a GPIO pin. When the DIR bit is set, the TIO pin is an output. When the DIR bit is cleared, the TIO pin is an input. The TIO pin can be used as a GPIO pin only when TC0-TC3 are all cleared. If one or more of TC0-TC3 is not cleared, the GPIO function is disabled and the DIR bit has no effect. The DIR bit is cleared by hardware and software reset.



Triple Timer Module Programming Model

9.4.6.8 Data Input Bit (DI)—Bit 11

The Data Input (DI) bit reflects the value of TIO pin according to the INV bit. Reading the DI bit reads the TIO pin if INV = 0, or the inverted TIO pin if INV = 1.

9.4.6.9 Data Output Bit (DO)—Bit 12

The Data Output (DO) bit writes data to the TIO pin. When the GPIO mode is enabled (TC0–TC3 are all cleared) and DIR = 1, the TIO pin acts as data output. Writing the DO bit writes the data to the TIO pin. If the INV bit is set, the data on the TIO pin is inverted. When GPIO mode is disabled, writing the DO bit has no effect. The DO bit is cleared by hardware and software reset.

9.4.6.10 Timer Overflow Flag Bit (TOF)—Bit 13

The Timer Overflow Flag (TOF) bit, when set, indicates that counter wraparound has occurred. The Timer Overflow Flag bit is cleared when writing a one into the TOF bit. Writing a 0 into the TOF bit has no effect. The bit is also cleared when the timer overflow interrupt is serviced (timer overflow interrupt acknowledge). The TOF bit is cleared by hardware and software reset, by the STOP instruction, and also by timer disabling (TE = 0).

9.4.6.11 Timer Compare Flag Bit (TCF)—Bit 14

In the Timer, PWM, and Watchdog modes, the Timer Compare Flag (TCF) bit when set indicates that (N - M + 1) events are counted, where N is the value in the compare register and M is TLR value. In the Measurement modes, the TCF bit when set indicates that the measurement has been completed. The Timer Compare Flag bit is cleared when writing a 1 into the TCF bit. Writing a 0 into the TCF bit has no effect. The bit is cleared also when the Timer Compare interrupt is serviced (timer compare interrupt acknowledge). The TCF bit is cleared by hardware and software reset, the STOP instruction, and also by timer disabling (TE = 0).

Notes:

- 1. Writing a 0 in the TOF or TCF bit can be done with the Bit Test and Clear (BCLR) instruction. The state of the tested bit is stored in the Carry bit of the Status Register (SR).
- 2. TOF and TCF are cleared by writing logic 1 to the specific bit. In order to assure that only the desired bit is cleared, the programmer should not use the BSET command. The proper way to clear these bits is to write a logic 1 to the flag to be cleared and 0 to the other flag, using the MOVEP instruction.

9.4.6.12 Prescaled Clock Enable Bit (PCE)—Bit 15

The Prescaled Clock Enable (PCE) bit is used to select the prescaled clock as the timer source clock. When PCE is cleared the timer uses either internal (CLK/2) or external (TIO) source clock as determined by the timer operating mode. When PCE is set, the





Triple Timer Module

Timer Modes of Operation

prescaler output is used as the timer source clock for the counter regardless of the timer operating mode.

The PCE bit is cleared by hardware and software reset.

Notes:

- **1.** To ensure proper functionality, the PCE bit should be changed only when the timer is disabled.
- **2.** The source clock for the prescaler is determined only by the Prescaler Source bits (PS0–PS1) of the TPLR. Therefore, a timer can be clocked by prescaled clock derived from the TIO of another timer.

9.4.6.13 Reserved Bit 3

Bit 3 of the TCSR is reserved. It is read as 0 and should be written with 0 for future compatibility.

9.5 TIMER MODES OF OPERATION

The DSP56603 timers have the following four modes of operation:

- Timer
- Measurement
- Pulse Width Modulation
- Watchdog

Table 9-3 summarizes these modes, and the following paragraphs describe these modes in detail.

Table 9-3 Timer Mode Summary

Mode	Mode Description	Mode Type	TC[3:0]
0	Timer Mode, No Output (Internal Clock)	Timer	0000
1	Timer Mode, Output Pulse Enable (Internal Clock)	Timer	0001
2	Timer Mode, Output Toggle Enable (Internal Clock)	Timer	0010
3	Timer Mode, Output Toggle Enable (External Clock)	Timer	0011
4	Pulse Width Measurement Mode	Measurement	0100



Timer Modes of Operation

Table 9-3 Timer Mode Summary (Continued)

Mode	Mode Description	Mode Type	TC[3:0]
5	Period Measurement Mode	Measurement	0101
6	Capture Mode	Measurement	0110
7	Pulse Width Modulation Mode, Output Toggle Enable	PWM	0111
8	(reserved)	(reserved)	1000
9	Watchdog Mode, Output Pulse Enable (Internal Clock)	Watchdog	1001
10	Watchdog Mode, Output Toggle Enable (Internal Clock)	Watchdog	1010
11	(reserved)	(reserved)	1011
12	(reserved)	(reserved)	1100
13	(reserved)	(reserved)	1101
14	(reserved)	(reserved)	1110
15	(reserved)	(reserved)	1111

9.5.1 Timer Modes

Timer modes allow using the timers to measure the duration of an event.

9.5.1.1 Mode 0—Timer Mode, No Output (Internal Clock)

This mode is selected when TC[3:0] is set to 0000. In this mode, the counter is cleared after the TE bit is set and loaded with the TLR value on the first timer pulse derived either from the DSP clock divided by two (CLK/2) or from the prescaled clock input. The following timer pulses increment the counter. When the counter matches the value contained by the TCPR, the TCF bit in TCSR is set and, if the TCIE is set, a compare interrupt is generated. At the next timer pulse, the counter is loaded with TLR value (if TRM is set) and the count is resumed. If TRM is cleared, the counter continues to be incremented on each timer pulse. If counter wraparound occurs, the TOF bit is set, and if the TOIE is set, an overflow interrupt is generated. This process is repeated until the timer is disabled (the TE bit is cleared). The counter contents can be read at any time by reading the TCR.



Triple Timer Module

Timer Modes of Operation

9.5.1.2 Mode 1—Timer Mode, Output Pulse Enable (Internal Clock)

This mode is selected when TC[3:0] is set to 0001. In this mode, the counter is cleared after the TE bit is set and loaded with the TLR value on the first timer pulse derived either from the DSP clock divided by two (CLK/2) or from the prescaled clock input. The following timer pulses increment the counter. When the counter matches the value contained by the TCPR, the TCF bit in TCSR is set, and if the TCIE is set, a compare interrupt is generated. At the next timer pulse, the counter is loaded with TLR value (if TRM is set) and the count is resumed. If TRM is cleared, the counter continues to be incremented on each timer pulse. This process is repeated until the timer is disabled (TE = 0). Each time the counter matches the TCPR value, a pulse is output on the TIO pin with the width equal to timer clock period. The pulse polarity is determined by the INV bit. If counter wraparound occurs, the TOF bit is set, and if the TOIE is set, an overflow interrupt is generated. The counter contents can be read at any time by reading the TCR.

Note: After the TE bit is set, the TIO pin output value is set equal to the INV bit to guarantee the correct first pin transition.

9.5.1.3 Mode 2—Timer Mode, Output Toggle Enable (Internal Clock)

This mode is selected when TC[3:0] is set to 0010. In this mode, the counter is cleared after the TE bit is set and loaded with the TLR value on the first timer pulse derived either from the DSP clock divided by two (CLK/2) or from the prescaled clock input. The following timer pulses increment the counter. When the counter matches the value of the TCPR, the TIO output pin is toggled, the TCF bit in TCSR is set, and if the TCIE bit is set, a compare interrupt is generated. At the next timer pulse, the counter is loaded with TLR value (if TRM is set) and the count is resumed. If TRM is cleared, the counter continues to be incremented on each timer pulse. This process is repeated until the timer is disabled (TE = 0). The TIO polarity is determined by the INV bit. On the first match, the TIO output is set if the INV bit is cleared, or cleared if the INV bit is set. If counter wraparound occurs, the TOF bit is set, and if the TOIE bit is set, an overflow interrupt is generated. The counter contents can be read at any time by reading the TCR.

Note: After the TE bit is set, the TIO pin output value is set equal to the INV bit to guarantee the correct first pin transition.

9.5.1.4 Mode 3—Timer Mode, Event Counter (External Clock)

This mode is selected when TC[3:0] is set to 0011. In this mode, the counter is cleared after the TE bit is set and loaded with the TLR value on the first transition on the source clock, which can be either the TIO input pin or the prescaled clock input. The following transitions increment the counter. When the counter matches the value contained by TCPR, the TCF bit in the TCSR is set. If the TCIE bit is set, a compare interrupt is generated. At the next transition, the counter is loaded with TLR value if



Timer Modes of Operation

the TRM bit is set, and the count is resumed. If the TRM bit is cleared, the counter continues to be incremented with each transition of the source clock. This process is repeated until the timer is disabled. The INV bit determines whether 0-to-1 transitions (the INV bit is cleared) or 1-to-0 transitions (the INV bit is set) increment the counter. If counter wraparound occurs, the TOF bit is set, and if the TOIE bit is set, an overflow interrupt is generated. The counter contents can be read at any time by reading the TCR. The external clock is internally synchronized to the internal clock and its frequency should be lower than the DSP internal clock (CLK) divided by four.

9.5.2 Measurement Modes

Since the measurement modes use the internal clock to increment the counter, but use the external signal for gating the count, synchronization is needed. The synchronization process can affect the measurement exactness by as much as a single selected internal or prescaled clock cycle.

9.5.2.1 Mode 4—Pulse Width Measurement Mode

The Pulse Width Measurement mode is selected when TC[3:0] is set to 0100. In this mode, the counter is cleared after the TE bit is set. After the first appropriate transition (as defined by the INV bit) occurring on the TIO input pin, the counter is loaded with the TLR value on the first timer pulse derived either from the DSP internal clock (CLK) divided by two or from the prescaled clock input. Each subsequent timer pulse increments the counter.

When the first edge of opposite polarity occurs on TIO, the counter stops, the TCF bit in TCSR is set, and if the TCIE bit is set, a compare interrupt is generated. The contents of the counter is loaded into the TCR and the user's program can read its value that represents the widths of the TIO pulse. On the first timer pulse following the next transition that occurs on TIO input pin, the counter is loaded with the value in TLR (if TRM is set), and the count is resumed. If the TRM bit is cleared, the counter continues to be incremented on each timer pulse. This process is repeated until the timer is disabled. If counter wraparound occurs, the TOF bit is set. If the TOIE bit is set, an overflow interrupt is generated. In this mode, TIO acts as a gating signal for the internal timer clock. The INV bit determines whether the counting is enabled when TIO is low (the INV bit is set) or TIO is high (the INV bit is cleared).

9.5.2.2 Mode 5—Period Measurement Mode

The Period Measurement mode is selected when TC[3:0] is set to 0101. In this mode, the counter is cleared after the TE bit is set. After the first appropriate transition (as defined by the INV bit) occurring on the TIO input pin, it is loaded with the TLR value on the first timer pulse derived either from the DSP internal clock (CLK)



Triple Timer Module

Timer Modes of Operation

divided by two or from the prescaled clock input. Each subsequent timer pulse increments the counter.

On each following transition of the same polarity that occurs on TIO, the TCF bit in the TCSR is set. If the TCIE bit is set, a compare interrupt is generated. The contents of the counter is loaded in the TCR. The user's program can then read its value and the value in the TCR to determine the distance between TIO edges. On the next timer pulse, the counter is loaded with the value in the TLR (if the TRM bit is set) and the count is resumed. If the TRM bit is cleared, the counter continues to be incremented on each timer pulse, accumulating measurements results. This process is repeated until the timer is disabled. If counter wraparound occurs, the TOF bit is set. If the TOIE bit is set, an overflow interrupt is generated. The INV bit determines whether the period is measured between consecutive 1 to 0 transitions of TIO (the INV bit is set) or between consecutive 0 to 1 transitions of TIO (the INV bit is cleared).

9.5.2.3 Mode 6—Capture Mode

The Capture mode is selected when TC[3:0] is set to 0110. In this mode, the counter is cleared after the TE bit is set and loaded with the TLR value on the first timer pulse derived either from the DSP clock divided by two (CLK/2) or from the prescaled clock input. The following timer pulses increment the counter. If counter wraparound occurs, the TOF bit is set, and if the TOIE is set, an overflow interrupt is generated. At the first transition of external clock, the TCF bit in TCSR is set, and if the TCIE bit is set, a compare interrupt is generated. The contents of the counter are loaded into the TCR and the user's program can read the value that represents the delay of the leading detected edge in relation to the setting of the TE bit. The counting is stopped. The INV bit determines whether the period is measured between the setting of TE bit and the transitions of TIO from 0 to 1 (the INV bit is cleared) or from 1 to 0 (the INV bit is set).

9.5.3 PWM Mode

One form of Pulse Width Modulation mode is provided, and is designated Mode 7.

9.5.3.1 Mode 7—Pulse Width Modulation Mode, Output Toggle Enable (Internal Clock)

The Pulse Width Modulation mode, Output Toggle Enable mode, is selected when TC[3:0] is set to 0111. In this mode, the counter is cleared after the TE bit is set and loaded with the TLR value on the first timer pulse derived either from the DSP clock divided by two (CLK/2) or from the prescaled clock input. The following timer pulses increment the counter. When the counter matches the value of the TCPR, the TIO output pin is toggled, the TCF bit in TCSR is set, and if the TCIE bit is set, a compare interrupt is generated and the count is continued. When counter



Timer Modes of Operation

Triple Timer Module

wraparound occurs, the TIO output pin is toggled, the TOF bit in TCSR is set, and if the TOIE is set, an overflow interrupt is generated. At the next timer pulse, the counter is loaded with TLR value (if the TRM bit is set) and the count is resumed. If TRM is cleared, the counter continues to be incremented on each timer pulse. This process is repeated until the timer is disabled. The TIO polarity is determined by the INV bit. On the first transaction, the TIO output is set if the INV bit is cleared, or cleared if the INV bit is set. The counter contents can be read at any time by reading the TCR.

The value in the TLR determines the output period (\$FFFF - TLR + 1). The value in the TCPR determines the duty cycle of the output signal (\$FFFF - TCPR + 1 vs. \$FFFF - TLR + 1). Therefore, to ensure correct functionality, the values in TLR and TCPR should not be the same.

Note: After the timer is enabled, the TIO pin output value is set equal to the INV

bit to guarantee the correct first pin transition.

9.5.4 Watchdog Modes

9.5.4.1 Mode 9—Watchdog Mode, Output Pulse Enable (Internal Clock) The Watchdog Mode, Output Pulse Enable mode is selected when TC[3:0] is set to 1001. In this mode, the counter is cleared after the TE bit is set and loaded with the TLR value on the first timer pulse derived either from the DSP clock divided by two (CLK/2) or from the prescaled clock input. The following timer pulses increment the counter. When the counter matches the value of the TCPR, the TCF bit in TCSR is set, and if the TCIE bit is set, a compare interrupt is generated and the count is continued. At the next timer pulse, the counter is loaded with TLR value (if TRM is set) and the count is resumed. If the TRM bit is cleared, the counter continues to be incremented on each timer pulse. This process is repeated until the timer is disabled. The counter is reloaded whenever the TLR is written with a new value while the timer is enabled. When counter wraparound occurs, the TOF bit in the TCSR is set, and if the TOIE bit is set, an overflow interrupt is generated. At the same time, a pulse is output on the TIO pin with the width equal to the timer clock period. The pulse polarity is

Note: In this mode, the internal hardware preserves the TIO value and direction

determined by the INV bit. The counter contents can be read at any time by reading

for an additional 2.5 internal clock cycles after reset was activated. This ensures a valid length reset when the TIO is used as input to the RESET

pin.

9-18

the TCR.



Timer Modes of Operation

Triple Timer Module

9.5.4.2 Mode 10—Watchdog Mode, Output Toggle Enable (Internal Clock)

The Watchdog Mode, Output Toggle Enable mode is selected when TC[3:0] is set to 1010. In this mode, the counter is cleared after the TE bit is set and loaded with the TLR value on the first timer pulse derived either from the DSP clock divided by two (CLK/2) or from the prescaled clock input. The following timer pulses increment the counter. When the counter matches the value of the TCPR, the TCF bit in TCSR is set, and if the TCIE bit is set, a compare interrupt is generated and the count is continued. At the next timer pulse, the counter is loaded with the TLR value (if the TRM bit is set) and the count is resumed. If the TRM bit is cleared, the counter continues to be incremented on each timer pulse. This process is repeated until the timer is disabled. The counter is reloaded whenever the TLR is written with a new value while the timer is enabled. When counter wraparound occurs, the TIO output pin is toggled, the TOF bit in the TCSR is set, and if the TOIE is set, an overflow interrupt is generated. The TIO polarity is determined by the INV bit. On the first transaction, the TIO output is set if the INV bit is cleared, or cleared if the INV bit is set. The counter contents can be read at any time by reading the TCR.

Notes:

- **1.** After the timer is enabled, the TIO pin output value is set equal to INV bit to guarantee the correct first pin transition.
- 2. In this mode, the internal hardware preserves the TIO value and direction for an additional 2.5 internal clock cycles after reset is activated, ensuring a valid length reset when the TIO is used as input to the RESET pin.

9.5.5 Reserved Modes

Timer modes 8, 11, 12, 13, 14 and 15 are reserved.

9.5.6 Timer Behavior During WAIT and STOP Instructions

The timer clocks are active during the execution of the WAIT instruction. Thus, timer activity continues undisturbed. On reaching the final event, if the timer interrupt is enabled, an interrupt is generated and the processor leaves the Wait state and services the interrupt. The timer clocks are disabled during the execution of the STOP instruction. Thus, timer activity is stopped. In Stop mode, the TIO pins are electrically disconnected internally. If a TIO pin is used as an input, changes that occur while in Stop mode are ignored. To ensure proper operation, disable the timer before executing the STOP instruction.






Timer Modes of Operation



SECTION 10 ON-CHIP EMULATION MODULE



On-Chip Emulation Module

10.1	INTRODUCTION10-3
10.2	ONCE MODULE PINS
10.3	ONCE CONTROLLER
10.4	ONCE MEMORY BREAKPOINT LOGIC 10-10
10.5	ONCE TRACE LOGIC
10.6	METHODS OF ENTERING THE DEBUG MODE 10-17
10.7	PIPELINE INFORMATION AND OGDB REGISTER 10-19
10.8	TRACE BUFFER
10.9	ONCE COMMANDS AND SERIAL PROTOCOL 10-24
10.10	TARGET SITE DEBUG SYSTEM REQUIREMENTS 10-25
10.11	EXAMPLES OF USING THE ONCE
10 12	EXAMPLES OF JTAG AND ONCE INTERACTION 10-30



On-Chip Emulation Module

Introduction

10.1 INTRODUCTION

The DSP56600 core On-Chip Emulation (OnCE™) module provides a means of interacting with the DSP56600 core and its peripherals non-intrusively so that a user can examine registers, memory, or on-chip peripherals, thus facilitating hardware and software development on the DSP56600 core processor. To achieve this, special circuits and dedicated pins on the DSP56600 core are defined to avoid sacrificing any user-accessible on-chip resource. The OnCE module resources can be accessed only after executing the JTAG instruction ENABLE_ONCE (these resources are accessible even when the chip is operating in Normal mode). See Section 12, JTAG Port, for a description of the JTAG functionality and its relation to the OnCE. Figure 10-1 shows the block diagram of the OnCE module.




Figure 10-1 OnCE Module Block Diagram

10.2 Once Module PINS

The OnCE module controller functionality is accessed through the JTAG Test Access Port (TAP). There are no dedicated OnCE module pins for clock, data in, or data out. The JTAG pins TCK, TDI, and TDO are used to shift in and out data and instructions. See JTAG Pins on page 11-5 for the description of the JTAG pins. To facilitate emulation-specific functions, one additional pin, called \overline{DE} , is provided on the DSP56603.

OnCE Module Pins

The bidirectional open drain Debug Event pin (\overline{DE}) provides a fast means of entering the Debug mode of operation from an external command controller (when input) as well as a fast means of acknowledging the entering of the Debug mode of operation to an external command controller (when output). The assertion of this pin by a command controller causes the DSP56600 core to finish the current instruction being executed, save the instruction pipeline information, enter the Debug mode, and wait for commands to be entered from the TDI line. If the $\overline{\rm DE}$ pin is used to enter the Debug mode, then it must be deasserted after the OnCE port responds with an acknowledge and before sending the first OnCE command. The assertion of this pin by the DSP56600 core indicates that the DSP has entered the Debug mode and is waiting for commands to be entered from the TDI line. The $\overline{\rm DE}$ pin also facilitates multiple processor connections, as shown in Figure 10-2.




Figure 10-2 OnCE Module Multiprocessor Configuration

In this way, the user can stop all the devices in the system when one of the devices enters the Debug mode. The user can also stop all the devices synchronously by asserting the \overline{DE} line.



On-Chip Emulation Module

10.3 **OnCE CONTROLLER**

The OnCE controller contains the following blocks: OnCE Command Register (OCR), OnCE Decoder, and the status/control register. Figure 10-3 illustrates a block diagram of the OnCE controller.




Figure 10-3 OnCE Controller Block Diagram

10.3.1 **OnCE Command Register (OCR)**

The OnCE Command Register (OCR) is an 8-bit shift register that receives its serial data from the TDI pin. It holds the 8-bit commands to be used as input for the OnCE Decoder. The OCR is shown in **Figure 10-4**.




Figure 10-4 OnCE Command Register



On-Chip Emulation Module

OnCE Controller

10.3.1.1 Register Select Bits (RS4–RS0)—Bits 0–4

The Register Select bits define which register is source/destination for the read/write operation. **Table 10-1** shows the OnCE register addresses.

Table 10-1 OnCE Register Select Encoding

RS[4:0]	Register Selected
00000	OnCE Status and Control Register (OSCR)
00001	Memory Breakpoint Counter (OMBC)
00010	Breakpoint Control Register (OBCR)
00011	Reserved Address
00100	Reserved Address
00101	Memory Limit Register 0 (OMLR0)
00110	Memory Limit Register 1 (OMLR1)
00111	Reserved Address
01000	Reserved Address
01001	GDB Register (OGDBR)
01010	PDB Register (OPDBR)
01011	PIL Register (OPILR)
01100	PDB GO-TO Register (for GO TO command)
01101	Trace Counter (OTC)
01110	Reserved Address
01111	PAB Register for Fetch (OPABFR)
10000	PAB Register for Decode (OPABDR)
10001	PAB Register for Execute (OPABEX)
10010	Trace Buffer and Increment Pointer
10011	Reserved Address
101xx	Reserved Address
11xx0	Reserved Address



OnCE Controller

On-Chip Emulation Module

Table 10-1 OnCE Register Select Encoding (Continued)

RS[4:0]	Register Selected	
11x0x	Reserved Address	
110xx	Reserved Address	
11111	No Register Selected	

10.3.1.2 Exit Command Bit (EX)—Bit 5

If the EX bit is set, leave Debug mode and resume normal operation. The EXIT command is executed only if the GO command is issued, and the operation is write to OPDBR or read/write to "No Register Selected". Otherwise the EX bit is ignored. **Table 10-2** shows the definition of the EX bit.

Table 10-2 EX Bit Definition

EX	Action
0	Remain in Debug mode
1	Leave Debug mode

GO Command Bit (GO)—Bit 6 10.3.1.3

If the GO bit is set, execute the instruction that resides in the PIL register. To execute the instruction, the core leaves the Debug mode. The core returns to the Debug mode immediately after executing the instruction if the EX bit is cleared. The core goes on to normal operation if the EX bit is set. The GO command is executed only if the operation is write to OPDBR or read/write to "No Register Selected". Otherwise, the GO bit is ignored. **Table 10-3** shows the definition of the GO bit.

Table 10-3 GO Bit Definition

GO	Action
0	Inactive—no action taken
1	Execute instruction in PIL



On-Chip Emulation Module

OnCE Controller

10.3.1.4 Read/Write Command Bit (R/W)—Bit 7

The R/\overline{W} bit specifies the direction of data transfer. **Table 10-4** shows the definition of the R/\overline{W} bit.

Table 10-4 R/\overline{W} Bit Definition


R/W	Action
0	Write the data associated with the command into the register specified by RS4–RS0.
1	Read the data contained in the register specified by RS4–RS0.

10.3.2 OnCE Decoder (ODEC)

The OnCE Decoder (ODEC) supervises the entire OnCE module activity. It receives as input the 8-bit command from the OCR, a signal from JTAG Controller (indicating that 8/24 bits have been received and update of the selected data register must be performed), and a signal indicating that the core was halted. The ODEC generates all the strobes required for reading and writing the selected OnCE registers.

10.3.3 OnCE Status and Control Register (OSCR)

The OnCE Status and Control Register (OSCR) is a 24-bit register used to enable the Trace mode of operation and to indicate the cause of entering the Debug mode. The control bits are read/write while the status bits are read-only. The OSCR bits are cleared on hardware reset. The OSCR is shown in **Figure 10-5**.



^{*} Indicates reserved bits, written as 0 for future compatibility

AA0705

Figure 10-5 OnCE Status and Control Register (OSCR)



On-Chip Emulation Module

OnCE Controller

10.3.3.1 Trace Mode Enable Bit (TME)—Bit 0

The Trace Mode Enable (TME) control bit, when set, enables the Trace mode of operation.

10.3.3.2 Interrupt Mode Enable Bit (IME)—Bit 1

The Interrupt Mode Enable (IME) control bit, when set, causes the chip to execute a vectored interrupt to the address VBA:\$06 instead of entering the Debug mode.

Software Debug Occurrence Bit (SWO)—Bit 2 10.3.3.3

The Software Debug Occurrence (SWO) bit is a read-only status bit that is set when the Debug mode of operation is entered because of the execution of the DEBUG or DEBUGcc instruction with condition true. This bit is cleared when leaving the Debug mode.

10.3.3.4 Memory Breakpoint Occurrence Bit (MBO)—Bit 3

The Memory Breakpoint Occurrence (MBO) bit is a read-only status bit that is set when the Debug mode of operation is entered because a memory breakpoint has been encountered. This bit is cleared when leaving the Debug mode.

10.3.3.5 Trace Occurrence Bit (TO)—Bit 4

The Trace Occurrence (TO) bit is a read-only status bit that is set when the Debug mode of operation is entered when the Trace Counter is zero while Trace mode is enabled. This bit is cleared when leaving the Debug mode.

Reserved Bit 5 10.3.3.6

Bit 5 is reserved for future use. It is read as 0 and should be written with 0 for future compatibility.

10.3.3.7 Core Status Bits (OS0–OS1)—Bits 6-7

The Core Status (OS0,OS1) bits are read-only status bits that provide core status information. By examining the status bits, the user can determine whether the chip has entered the Debug mode. Examining SWO, MBO, and TO identifies the cause of entering the Debug mode. The user can also examine these bits and determine the cause why the chip has not entered the Debug mode after debug event assertion (\overline{DE}) or as a result of the execution of the JTAG DEBUG_REQUEST instruction (core waiting for the bus, STOP or WAIT instruction, etc.). These bits are also reflected in the JTAG Instruction shift Register (IR), which allows the polling of the core status information at the JTAG level. This is useful when the DSP56600 core executes the STOP instruction (and therefore there are no clocks) to allow the reading of OSCR. See **Table 10-5** for the definition of the OS0-OS1 bits.

Go to: www.freescale.com



On-Chip Emulation Module

OnCE Memory Breakpoint Logic

Table 10-5 Core Status Bits Description

OS1	OS0	Description
0	0	DSP56600 core is executing instructions
0	1	DSP56600 core is in Wait or Stop mode
1	0	DSP56600 core is waiting for bus
1	1	DSP56600 core is in Debug mode

10.3.3.8 Reserved Bits 8–23

Bits 8–23 are reserved for future use. They are read as 0 and should be written with 0 for future compatibility.

10.4 OnCE MEMORY BREAKPOINT LOGIC

Memory breakpoints can be set on program memory or data memory locations. In addition, the breakpoint does not have to be in a specific memory address, but within an approximate address range of where the program may be executing. This significantly increases the programmer's ability to monitor what the program is doing in real-time. The breakpoint logic, described in **Figure 10-6**, contains a latch for the addresses, registers that store the upper and lower address limit, address comparators, and a breakpoint counter.





On-Chip Emulation Module

OnCE Memory Breakpoint Logic




Figure 10-6 OnCE Memory Breakpoint Logic 0

Address comparators are useful in determining where a program may be getting lost or when data is being written where it should not be written. They are also useful in halting a program at a specific point to examine/change registers or memory. Using address comparators to set breakpoints enables the user to set breakpoints in RAM or ROM and while in any operating mode. Memory accesses are monitored according to the contents of the OBCR as specified in OnCE Breakpoint Control Register (**OBCR**) on page 10-12.

10.4.1 **OnCE Memory Address Latch (OMAL)**

The OnCE Memory Address Latch (OMAL) is a 16-bit register that latches the PAB, XAB or YAB on every instruction cycle according to the MBS1-MBS0 bits in OBCR.



OnCE Memory Breakpoint Logic

On-Chip Emulation Module

10.4.2 OnCE Memory Limit Register 0 (OMLR0)

The OnCE Memory Limit Register 0 (OMLR0) is a 16-bit register that stores the memory breakpoint limit. Before enabling breakpoints, OMLR0 must be loaded by the external command controller. OMLR0 can be read or written through the TAP.

10.4.3 OnCE Memory Address Comparator 0 (OMAC0)

The OnCE Memory Address Comparator 0 (OMAC0) compares the current memory address (stored in OMAL0) with the OMLR0 contents.

OnCE Memory Limit Register 1 (OMLR1) 10.4.4


The OnCE Memory Limit Register 1 (OMLR1) is a 16-bit register that stores the memory breakpoint limit. OMLR1 can be read or written through the TAP. Before enabling breakpoints, OMLR1 must be loaded by the external command controller.

OnCE Memory Address Comparator 1 (OMAC1) 10.4.5

The OnCE Memory Address Comparator 1 (OMAC1) compares the current memory address (stored in OMAL0) with the OMLR1 contents.

OnCE Breakpoint Control Register (OBCR) 10.4.6

The OnCE Breakpoint Control Register (OBCR) is a 16-bit register used to define the memory breakpoint events. OBCR can be read or written through the JTAG TAP. All the bits of the OBCR are cleared on hardware reset. The OBCR is described in **Figure 10-7**.



* Indicates reserved bits, written as 0 for future compatibility

AA0707



On-Chip Emulation Module

OnCE Memory Breakpoint Logic

10.4.6.1 Memory Breakpoint Select Bits (MBS0-MBS1)—Bits 0-1

The Memory Breakpoint Select bits (MBS0-MBS1) enable memory breakpoints 0 and 1, allowing them to occur when a memory access is performed on P, X, or Y space access is performed. See **Table 10-6** for the definition of the MBS0-MBS1 bits.

Table 10-6 Memory Breakpoint 0 and 1 Select Table

MBS1	MBS0	Description	
0	0	Reserved	
0	1	Breakpoint on P access	
1	0	Breakpoint on X access	
1	1	Breakpoint on Y access	

10.4.6.2 Breakpoint 0 Read/Write Select Bits (RW00-RW01)—Bits 2-3 The Breakpoint 0 Read/Write Select bits (RW00–RW01) define the memory breakpoints 0 to occur when a memory address accesses is performed for read, write or both. See Table 10-7 for the definition of the RW00-RW01 bits.

Table 10-7 Breakpoint 0 Read/Write Select Table

RW01	RW00	Description	
0	0	Breakpoint disabled	
0	1	Breakpoint on write access	
1	0	Breakpoint on read access	
1	1	Breakpoint on read or write access	

Breakpoint 0 Condition Code Select Bits (CC00-CC01)—Bits 4-5 10.4.6.3 The Breakpoint 0 Condition Code Select bits (CC00-CC01) define the condition of the comparison between the current Memory Address (OMAL0) and the Memory Limit Register 0 (OMLR0). See **Table 10-8** for the definition of the CC00–CC01 bits.

Go to: www.freescale.com



On-Chip Emulation Module

OnCE Memory Breakpoint Logic

 Table 10-8
 Breakpoint 0 Condition Select Table

CC01	CC00	Description	
0	0	Breakpoint on not equal	
0	1	Breakpoint on equal	
1	0	Breakpoint on less than	
1	1	Breakpoint on greater than	

10.4.6.4 Breakpoint1 Read/Write Select Bits (RW10–RW11)—Bits 6–7 The Breakpoint1 Read/Write Select (RW10–RW11) bits control define memory breakpoints 1 to occur when a memory address accesses is performed for read, write or both. See **Table 10-9** for the definition of the RW10–RW11 bits.

Table 10-9 Breakpoint 1 Read/Write Select Table

RW11	RW10	Description	
0	0	Breakpoint disabled	
0	1	Breakpoint on write access	
1	0	Breakpoint on read access	
1	1	Breakpoint read or write access	

10.4.6.5 Breakpoint1 Condition Code Select Bits (CC10–CC11)—Bits 8–9 The Breakpoint1 Condition Code Select bits (CC10–CC11) define the condition of the comparison between the current memory address (OMAL0) and the OnCE Memory Limit Register 1 (OMLR1). See **Table 10-10** for the definition of the CC10–CC11 bits.

 Table 10-10
 Breakpoint 1 Condition Select Table

CC11	CC10	Description	
0	0	Breakpoint on not equal	
0	1	Breakpoint on equal	
1	0	Breakpoint on less than	
1	1	Breakpoint on greater than	



On-Chip Emulation Module

OnCE Trace Logic

10.4.6.6 Breakpoint 0 and 1 Event Select Bits (BT0-BT1)—Bits 10-11

The Breakpoint 0 and 1 Event Select bits (BT0-BT1) define the sequence between breakpoint 0 and 1. If the condition defined by BT0-BT1 is met, then the Breakpoint Counter (OMBC) is decremented. See **Table 10-11** for the definition of the BT0-BT1 bits.

BT1	ВТ0	Description
0	0	Breakpoint 0 and Breakpoint 1
0	1	Breakpoint 0 or Breakpoint 1
1	0	Breakpoint 1 after Breakpoint 0

Breakpoint 0 after Breakpoint 1

 Table 10-11
 Breakpoint 0 and 1 Event Select Table

10.4.6.7 Reserved Bits 12–15

1

1

Bits 12–15 are reserved for future use. They are read as 0 and should be written with 0 for future compatibility.

10.4.7 OnCE Memory Breakpoint Counter (OMBC)

The OnCE Memory Breakpoint Counter (OMBC) is a 16-bit counter that is loaded with a value equal to the number of times minus one that a memory access event should occur before a memory breakpoint is declared. The memory access event is specified by the OBCR and by the memory limit registers. On each occurrence of the memory access event, the breakpoint counter is decremented. When the counter reaches 0 and a new occurrence takes place, the chip enters the Debug mode. The OMBC can be read or written through the TAP. Every time that the limit register is changed, or a different breakpoint event is selected in the OBCR, the breakpoint counter must be written afterwards. This ensures that the OnCE breakpoint logic is reset and that no previous events can affect the new breakpoint event selected. The breakpoint counter is cleared by hardware reset.

10.5 OnCE TRACE LOGIC

Using the OnCE Trace Logic, execution of instructions in single or multiple steps is possible. The OnCE Trace Logic causes the chip to enter the Debug mode of operation after the execution of one or more instructions and wait for OnCE



On-Chip Emulation Module

OnCE Trace Logic

commands from the debug serial port. The OnCE Trace Logic block diagram is shown in **Figure 10-8**.




Figure 10-8 OnCE Trace Logic Block Diagram

The Trace mode has a counter associated with it so that more than one instruction can be executed before returning back to the Debug mode of operation. The objective of the counter is to allow the user to take multiple instruction steps real-time before entering the Debug mode. This feature helps the software developer debug sections of code that do not have a normal flow or are getting hung up in infinite loops. The Trace Counter also enables the user to count the number of instructions executed in a code segment.

The OnCE Trace Counter (OTC) is a 16-bit counter that can be read or written through the TAP. If N instructions are to be executed before entering the Debug mode, the Trace Counter should be loaded with N-1. The Trace Counter is cleared by hardware reset.

To enable the Trace mode of operation, do the following:

- 1. Load the counter with a value.
- 2. Set the program counter to the start location of the instruction(s) to be executed real-time.
- 3. Set the TME bit in the OSCR.
- 4. Cause the DSP56600 core to exit the Debug mode by executing the appropriate command issued by the external command controller.



On-Chip Emulation Module

Methods of Entering the Debug Mode

Upon exiting the Debug mode, the counter is decremented after each execution of an instruction. Interrupts are serviceable and all instructions executed, including fast interrupt services and the execution of each repeated instruction, cause the Trace Counter to be decremented. Upon decrementing to 0, the DSP56600 core re-enters the Debug mode, the Trace Occurrence bit (TO) in the OSCR register is set, the core Status bits OS[1:0] are set to 11, and the $\overline{\rm DE}$ pin is asserted to indicate that the DSP56600 core has entered Debug mode and is requesting service.

10.6 METHODS OF ENTERING THE DEBUG MODE

Entering the Debug mode is acknowledged by the chip by setting the Core Status bits OS1 and OS0 and asserting the $\overline{\rm DE}$ line. This informs the external command controller that the chip has entered the Debug mode and is waiting for commands. The DSP56600 core can disable the OnCE module if the ROM Security option is implemented. If the ROM Security is implemented, the OnCE module remains inactive until a write operation to the OGDBR is executed by the DSP56600 core.

10.6.1 External Debug Request During RESET Assertion

Holding the \overline{DE} line asserted during the assertion of \overline{RESET} causes the chip to enter the Debug mode. After receiving the acknowledge, the external command controller must negate the \overline{DE} line before sending the first command.

Note: In this case, the chip does not execute any instruction before entering the

Debug mode.

10.6.2 External Debug Request During Normal Activity

Holding the \overline{DE} line asserted during normal chip activity causes the chip to finish the execution of the current instruction and then enter the Debug mode. After receiving the acknowledge, the external command controller must negate the \overline{DE} line before sending the first command. This process is the same for any newly fetched instruction, including instructions fetched by the interrupt processing or instructions that will be aborted by the interrupt processing.

Note: In this case the chip completes the execution of the current instruction and stops after the newly fetched instruction enters the instruction latch.



On-Chip Emulation Module

Methods of Entering the Debug Mode

10.6.3 Executing the JTAG DEBUG_REQUEST Instruction

Executing the JTAG instruction DEBUG_REQUEST asserts an internal debug request signal. Consequently, the chip finishes the execution of the current instruction and stops after the newly fetched instruction enters the instruction latch. After entering the Debug mode, the Core Status bits OS1 and OS0 are set and the $\overline{\rm DE}$ line is asserted, thus acknowledging the external command controller that the Debug mode of operation has been entered.

10.6.4 External Debug Request During Stop

Executing the JTAG instruction DEBUG_REQUEST (or asserting \overline{DE}) while the chip is in the Stop state (i. e., has executed a STOP instruction) causes the chip to exit the Stop state and enter the Debug mode. After receiving the acknowledge, the external command controller must negate \overline{DE} before sending the first command.

Note: In this case, the chip completes the execution of the STOP instruction and

halts after the next instruction enters the instruction latch.

10.6.5 External Debug Request During Wait

Executing the JTAG instruction DEBUG_REQUEST (or asserting \overline{DE}) while the chip is in the Wait state (i. e., has executed a WAIT instruction) causes the chip to exit the Wait state and enter the Debug mode. After receiving the acknowledge, the external command controller must negate \overline{DE} before sending the first command.

Note: In this case, the chip completes the execution of the WAIT instruction and

halts after the next instruction enters the instruction latch.



On-Chip Emulation Module

Pipeline Information and OGDB Register

10.6.6 Software Request During Normal Activity

Upon executing the DSP56600 core instruction DEBUG (or DEBUGcc when the specified condition is true), the chip enters the Debug mode after the instruction following the DEBUG instruction has entered the instruction latch.

10.6.7 Enabling Trace Mode

When the Trace mode mechanism is enabled and the Trace Counter is greater than zero, the Trace Counter is decremented after each instruction execution. Execution of an instruction when the value in the Trace Counter is 0 causes the chip to enter the Debug mode after completing the execution of the instruction. Only instructions actually executed cause the Trace Counter to decrement. An aborted instruction does not decrement the Trace Counter and does not cause the chip to enter the Debug mode.

10.6.8 Enabling Memory Breakpoints

When the memory breakpoint mechanism is enabled with a Breakpoint Counter value of 0, the chip enters the Debug mode after completing the execution of the instruction that caused the memory breakpoint to occur. In case of breakpoints on executed Program memory fetches, the breakpoint is acknowledged immediately after the execution of the fetched instruction. In case of breakpoints on accesses to X, Y, or P memory spaces by MOVE instructions, the breakpoint is acknowledged after the completion of the instruction following the instruction that accessed the specified address.

10.7 PIPELINE INFORMATION AND OGDB REGISTER

To restore the pipeline and to resume normal chip activity upon returning from the Debug mode, a number of on-chip registers store the chip pipeline status. **Figure 10-9** shows the block diagram of the Pipeline Information Registers, with the exception of the PAB registers, which are shown in **Figure 10-10** on page 10-23.

On-Chip Emulation Module

Pipeline Information and OGDB Register




Figure 10-9 OnCE Pipeline Information and GDB Registers

10.7.1 OnCE PDB Register (OPDBR)

The OnCE Program Data Bus Register (OPDBR) is a 24-bit latch that stores the value of the Program Data Bus generated by the last program memory access of the core before the Debug mode is entered. The OPDBR register can be read or written through the TAP. This register is affected by the operations performed during the Debug mode and must be restored by the external command controller when returning to Normal mode.

10.7.2 OnCE PIL Register (OPILR)

The OnCE PIL Register (OPILR) is a 24-bit latch that stores the value of the Instruction Latch before the Debug mode is entered. OPILR can only be read through the TAP.

Note:

Since the Instruction Latch is affected by the operations performed during the Debug mode, it must be restored by the external command controller when returning to Normal mode. Since there is no direct write access to the Instruction Latch, the task of restoring is accomplished by writing to OPDBR with no-GO and no-EX. In this case, the data written on PDB is transferred into the Instruction Latch.





Trace Buffer

On-Chip Emulation Module

10.7.3 OnCE GDB Register (OGDBR)

The OnCE GDB Register (OGDBR) is a 16-bit latch that can only be read through the TAP. The OGDBR is not actually required from a pipeline status restore point of view, but is required as a means of passing information between the chip and the external command controller. The OGDBR is mapped on the X internal I/O space at address \$FFFC. Whenever the external command controller needs the contents of a register or memory location, it forces the chip to execute an instruction that brings that information to the OGDBR. Then the contents of the OGDBR are delivered serially to the external command controller by the command "READ GDB REGISTER".

TRACE BUFFER 10.8

To ease debugging activity and keep track of program flow, the DSP56600 core provides a number of on-chip dedicated resources. There are three read-only PAB registers that give pipeline information when the Debug mode is entered, and a Trace buffer that stores the address of the last instruction that was executed, as well as the addresses of the last eight change of flow instructions.

OnCE PAB Register for Fetch (OPABFR) 10.8.1

The OnCE PAB Register for Fetch Register (OPABFR) is a 16-bit register that stores the address of the last instruction whose fetch was started before the Debug mode was entered. The OPABFR can only be read through the TAP. This register is not affected by the operations performed during the Debug mode.

10.8.2 PAB Register for Decode (OPABDR)

The OnCE PAB Register for Decode Register (OPABDR) is a 16-bit register that stores the address of the instruction currently on the PDB. This is the instruction whose fetch was completed before the chip has entered the Debug mode. The OPABDR can only be read through the TAP. This register is not affected by the operations performed during the Debug mode.



Trace Buffer

10.8.3 OnCE PAB Register for Execute (OPABEX)

The OnCE PAB Register for Execute (OPABEX) is a 16-bit register that stores the address of the instruction currently in the Instruction Latch. This is the instruction that would have been decoded and executed if the chip had not entered the Debug mode. The OPABEX register can be read only through the TAP. This register is not affected by the operations performed during the Debug mode.

10.8.4 Trace Buffer

The Trace buffer stores the addresses of the last eight change of flow instructions that were executed, as well as the address of the last executed instruction. The Trace buffer is implemented as a circular buffer containing eight 17-bit registers and one 4-bit counter. All the registers have the same address, but any read access to the Trace buffer address causes the counter to increment, thus pointing to the next Trace buffer register. The registers are serially available to the external command controller through their common Trace buffer address. **Figure 10-10** shows the block diagram of the Trace buffer. The Trace buffer is not affected by the operations performed during the Debug mode except for the Trace buffer pointer increment when reading the Trace buffer. When entering the Debug mode, the Trace buffer counter is pointing to the Trace buffer register containing the address of the last executed instructions. The first Trace buffer read obtains the oldest address and the following Trace buffer reads get the other addresses from the oldest to the newest, in order of execution.



On-Chip Emulation Module

Trace Buffer




Figure 10-10 OnCE Trace Buffer

Notes: 1. To ensure Trace buffer coherence, a complete set of eight reads of the Trace buffer must be performed. This is necessary because each read increments the Trace buffer pointer, thus pointing to the next location. After eight reads, the pointer indicates the same location as before starting the read procedure.



On-Chip Emulation Module

OnCE Commands and Serial Protocol

2. On any change of flow instruction, the Trace buffer stores both the address of the change of flow instruction, as well as the address of the target of the change of flow instruction. In the case of conditional change of flows, the address of the change of flow instruction is always stored (regardless of the fact that the change of flow is true or false), but if the conditional change of flow is false (that is, not taken) the address of the target is not stored. In order to facilitate the program trace reconstruction every Trace buffer location has an additional "invalid bit" (the 25th bit). If a conditional change of flow instruction has a "condition false", the "invalid bit" is set, thus marking this instruction as "not taken". Therefore, it is imperative to read seventeen bits of data when reading the eight Trace buffer registers. Since data is read LSB first, the "invalid bit" is the first bit to be read.

10.9 OnCE COMMANDS AND SERIAL PROTOCOL

To permit an efficient means of communication between the external command controller and the DSP56603, the following protocol is adopted. Before starting any debugging activity, the external command controller waits for an acknowledge on the $\overline{\rm DE}$ line indicating that the chip has entered the Debug mode (optionally the external command controller can poll the OS1 and OS0 bits in the JTAG instruction shift register). The external command controller communicates with the chip by sending 8-bit commands that can be accompanied by 24 bits of data. Both commands and data are sent or received least significant bit first. After sending a command, the external command controller waits for the DSP56603 to acknowledge execution of the command. The external command controller sends a new command only after the chip has acknowledged execution of the previous command.

The OnCE commands are classified as follows:

- Read commands (when the chip delivers the required data)
- Write commands (when the chip receives data and writes the data in one of the OnCE registers)
- Commands that do not have data transfers associated with them

The commands are 8 bits long and have the format shown in **Figure 10-4** on page 10-5.

On-Chip Emulation Module

Target Site Debug System Requirements

10.10 TARGET SITE DEBUG SYSTEM REQUIREMENTS

A typical debug environment consists of a target system where the DSP56600 core-based device resides in the user defined hardware. The TAP interfaces to the external command controller through a 14-pin connector that provides connections for the five JTAG port lines, one OnCE module control line, a ground, a $\overline{\text{RESET}}$ line, and .a target power input line. The $\overline{\text{RESET}}$ line is optional and is only used to reset the DSP56600 core-based device and its associated circuitry. The external command controller acts as the medium between the DSP56600 core target system and a host computer. The external command controller circuit acts as a JTAG TAP driver and host computer command interpreter. The controller issues commands based on the host computer inputs from a user interface program that communicates with the user.

10.11 EXAMPLES OF USING THE OnCE

All the following examples of debugging procedures assume that the DSP is the only device in the JTAG chain. If the chain has more than one device, the other devices can be forced to execute the JTAG BYPASS instruction such as their effect in the serial stream will be one bit per additional device. The select-DR, select-IR, update-DR, and shift-DR events refer to bringing the JTAG TAP in the corresponding state. Please refer to Section 11, JTAG, for a detailed description of the JTAG protocol.

10.11.1 Checking Whether the Chip has Entered the Debug Mode

There are two methods to verify that the chip has entered the Debug mode:

- 1. Every time the chip enters the Debug mode, a pulse is generated on the \overline{DE} pin. A pulse is also generated every time the chip acknowledges the execution of an instruction while in Debug mode. An external command controller can connect the \overline{DE} line to an interrupt pin in order to sense the acknowledge.
- 2. An external command controller can poll the JTAG instruction shift register for the status bits OS[1:0]. When the chip is in Debug mode, these bits are set to the value 11.

Note: In the following paragraphs, "ACK" denotes the operation performed by the command controller to see if the Debug mode has been entered, either by sensing \overline{DE} or by polling the JTAG instruction shift register.



Examples of Using the OnCE

On-Chip Emulation Module

10.11.2 Polling the JTAG Instruction Shift Register

To poll the core status bits in the JTAG Instruction Shift register, do the following:

- 1. Select shift-IR. Passing through capture-IR loads the core status bits into the instruction shift register.
- 2. Shift in ENABLE_ONCE. While shifting in the new instruction, the captured status information is shifted out. Pass through update-IR.
- 3. Return to Run-Test/Idle.

The external command controller can analyze the information shifted out and detect whether the chip has entered the Debug mode.

Note: JTAG compliance requires a preamble of "01" prior to shifting out status information.

10.11.3 Saving Pipeline Information

The debugging activity is accomplished by means of DSP56600 core instructions supplied from the external command controller. Therefore, the current state of the DSP56600 core pipeline must be saved prior to starting the debug activity, and the state must be restored prior to returning to the Normal mode of operation. Following is the description of the saving procedure (assume that ENABLE_ONCE has been executed and Debug mode has been entered and verified, as described in **Checking Whether the Chip has Entered the Debug Mode** on page 10-25):

- 1. Select shift-DR. Shift in the "Read PDB". Pass through update-DR.
- 2. Select shift-DR. Shift out the 24-bit OPDB register. Pass through update-DR.
- 3. Select shift-DR. Shift in the "Read PIL". Pass through update-DR.
- 4. Select shift-DR. Shift out the 24-bit OPILR register. Pass through update-DR.

Note that there is no need to verify acknowledge between steps 1 and 2, as well as 3 and 4, because completion is guaranteed by design.

10.11.4 Reading the Trace Buffer

An optional step during debugging activity is reading the information associated with the Trace buffer in order to enable an external program to reconstruct the full trace of the executed program. Following is the description of the read Trace buffer



On-Chip Emulation Module

Examples of Using the OnCE

procedure (assume that all actions described in **Saving Pipeline Information** have been executed):

- 1. Select shift-DR. Shift in the "Read PABFR". Pass through update-DR.
- 2. Select shift-DR. Shift out the 16-bit OPABFR register. Pass through update-DR.
- 3. Select shift-DR. Shift in the "Read PABDR". Pass through update-DR.
- 4. Select shift-DR. Shift out the 16 bit OPABDR register. Pass through update-DR.
- 5. Select shift-DR. Shift in the "Read PABEX". Pass through update-DR.
- Select shift-DR. Shift out the 16-bit OPABEX register. Pass through update-DR.
- 7. Select shift-DR. Shift in the "Read FIFO". Pass through update-DR.
- 8. Select shift-DR. Shift out the 17-bit FIFO register. Pass through update-DR.
- 9. Repeat steps 7 and 8 for the entire FIFO (8 times).

Note: The user must read the entire FIFO, since each read increments the FIFO pointer, thus pointing to the next FIFO location. At the end of this procedure, the FIFO pointer points back to the beginning of the FIFO.

The information that has been read by the external command controller now contains the address of the newly fetched instruction, the address of the instruction currently on the PDB, the address of the instruction currently on the instruction latch, as well as the addresses of the last eight instructions that have been executed and are change of flow. A user program can now reconstruct the flow of a full trace based on this information and on the original source code of the currently running program.

10.11.5 Displaying a Specified Register

The DSP56600 must be in Debug mode and all actions described in **Saving Pipeline Information** on page 10-26 have been executed. The sequence of actions is:

- 1. Select shift-DR. Shift in the "Write PDB with GO no-EX". Pass through update-DR.
- 2. Select shift-DR. Shift in the 24-bit opcode: "MOVE reg, X:OGDB". Pass through update-DR to actually write OPDBR and thus begin executing the MOVE instruction.
- 3. Wait for DSP to reenter Debug mode (wait for \overline{DE} or poll core status).



Examples of Using the OnCE

4. Select shift-DR and shift in "READ GDB REGISTER". Pass through

update-DR (this selects OGDBR as the data register for read).

5. Select shift-DR. Shift out the OGDBR contents. Pass through update-DR. Wait for next command.

10.11.6 Displaying X Memory Area Starting at Address \$xxxx

The DSP56600 must be in Debug mode and all actions described in **Saving Pipeline Information** on page 10-26 must have been executed. Since R0 is used as pointer for the memory, R0 is saved first. The sequence of actions is:

- 1. Select shift-DR. Shift in the "Write PDB with GO no-EX". Pass through update-DR.
- 2. Select shift-DR. Shift in the 24-bit opcode: "MOVE R0, X:OGDB". Pass through update-DR to actually write OPDBR and begin executing the MOVE instruction.
- 3. Wait for DSP to reenter Debug mode (wait for \overline{DE} or poll core status).
- 4. Select shift-DR and shift in "READ GDB REGISTER". Pass through update-DR (this selects OGDBR as the data register for read).
- 5. Select shift-DR. Shift out the OGDBR contents. Pass through update-DR. R0 is now saved.
- 6. Select shift-DR. Shift in the "Write PDB with no-GO no-EX". Pass through update-DR.
- 7. Select shift-DR. Shift in the 24-bit opcode: "MOVE #\$xxxx,R0". Pass through update-DR to actually write OPDBR.
- 8. Select shift-DR. Shift in the "Write PDB with GO no-EX". Pass through update-DR.
- 9. Select shift-DR. Shift in the second word of the 24-bit opcode: "MOVE #\$xxxx,R0" (the \$xxxx field). Pass through update-DR to actually write OPDBR and execute the instruction. R0 is loaded with the base address of the memory block to be read.
- 10. Wait for DSP to reenter Debug mode (wait for \overline{DE} or poll core status).
- 11. Select shift-DR. Shift in the "Write PDB with GO no-EX". Pass through update-DR.



On-Chip Emulation Module

Examples of Using the OnCE

- 12. Select shift-DR. Shift in the 24-bit opcode: "MOVE X:(R0)+, X:OGDB". Pass through update-DR to actually write OPDBR and begin executing the MOVE instruction.
- 13. Wait for DSP to reenter Debug mode (wait for \overline{DE} or poll core status).
- 14. Select shift-DR and shift in "READ GDB REGISTER". Pass through update-DR (this selects OGDBR as the data register for read).
- 15. Select shift-DR. Shift out the OGDBR contents. Pass through update-DR. The memory contents of address \$xxxx is read.
- 16. Select shift-DR. Shift in the "NO SELECT with GO no-EX". Pass through update-DR. This re-executes the same "MOVE X:(R0)+, X:OGDB" instruction.
- 17. Repeat from step 14 to complete the reading of the entire block. When finished, restore the original value of R0.

Note: Polling for status through the JTAG instruction register is preferable to reading the OnCE Status Register through the DR path.

10.11.7 Returning from Debug Mode to Normal Mode to Current Program

In this case, the user has finished examining the current state of the machine, changed some of the registers, and wishes to return and continue execution of its program from the point where it stopped. Therefore, the user must restore the pipeline of the machine end enable normal instruction execution. The sequence of actions is:

- 1. Select shift-DR. Shift in the "Write PDB with no-GO no-EX". Pass through update-DR.
- 2. Select shift-DR. Shift in the 24 bits of saved PIL (instruction latch value). Pass through update-DR to actually write the Instruction Latch.
- 3. Select shift-DR. Shift in the "Write PDB with GO and EX". Pass through update-DR.
- 4. Select shift-DR. Shift in the 24 bits of saved PDB. Pass through update-DR to actually write the PDB. At the same time the internally saved value of the PAB is driven back from the PABFR register onto the PAB, the ODEC releases the chip from Debug mode and the normal flow of execution is continued.



On-Chip Emulation Module

Examples of JTAG and OnCE interaction

10.11.8 Returning from Debug Mode to Normal Mode to a New Program

In this case, the user has finished examining the current state of the machine, changed some of the registers, and wishes to start the execution of a new program (the GOTO command). Therefore, the user must force a "change of flow" to the starting address of the new program (\$xxxx). The sequence of actions is:

- 1. Select shift-DR. Shift in the "Write PDB with no-GO no-EX". Pass through update-DR.
- 1. Select shift-DR. Shift in the 24-bit "\$0AF080", which is the opcode of the JUMP instruction. Pass through update-DR to actually write the Instruction Latch.
- 2. Select shift-DR. Shift in the "Write PDB-GO-TO with GO and EX". Pass through update-DR.
- 3. Select shift-DR. Shift in the 16 bits of "\$xxxx". Pass through update-DR to actually write the PDB. At this time the ODEC releases the chip from Debug mode and the execution is started from the address \$xxxx.

Note: If the Debug mode is entered during a DO LOOP, REP instruction, or other special cases such as interrupt processing, STOP, WAIT, or conditional branching, the user must first reset the DSP56600 before proceeding with the execution of the new program.

10.12 EXAMPLES OF JTAG AND ONCE INTERACTION

This subsection lists the details of the JTAG port/OnCE module interaction and TMS sequencing required to achieve the communication described in **Examples of Using the OnCE** on page 10-25.

The external command controller can force the DSP56600 into Debug mode by executing the JTAG instruction DEBUG_REQUEST. In order to check that the DSP56600 has entered the Debug mode, the external command controller must poll the status by reading the OS[1:0] bits in the JTAG instruction shift register. After executing the JTAG instructions DEBUG_REQUEST and ENABLE_ONCE and after the core status was polled to verify that the chip is in Debug mode, the pipeline saving procedure must take place. The TMS sequencing for this procedure is depicted in **Table 10-12**. The sequencing of enabling the OnCE module is described in **Table 10-13** on page 10-32.





On-Chip Emulation Module

Examples of JTAG and OnCE interaction

Table 10-12 TMS Sequencing for DEBUG_REQUEST

Step	TMS	JTAG Port	OnCE Module	Note	
a	0	Run-Test/Idle	Idle		
b	1	Select-DR-Scan	Idle		
С	1	Select-IR-Scan	Idle		
d	0	Capture-IR	Idle	The status is sampled in the shifter.	
e	0	Shift-IR	Idle	The four bits of the JTAG DEBUG_REQUEST (0111) are	
	••••			shifted in while status is	
e	0	Shift-IR	Idle	shifted out.	
f	1	Exit1-IR	Idle		
g	1	Update-IR	Idle	The debug request is generated.	
h	1	Select-DR-Scan	Idle		
i	1	Select-IR-Scan	Idle		
j	0	Capture-IR	Idle	The status is sampled in the shifter.	
k	0	Shift-IR	Idle	The four bits of the JTAG DEBUG_REQUEST (0111) are	
	••••			shifted in while status is	
k	0	Shift-IR	Idle	shifted out.	
l	1	Exit1-IR	Idle		
m	1	Update-IR	Idle		
n	0	Run-Test/Idle	Idle	This step is repeated, enabling an external command controller to	
				poll the status.	
n	0	Run-Test/Idle	Idle		

In "step n" the external command controller verifies that the OS[1:0] bits have the value 11, indicating that the chip has entered the Debug mode. If the chip has not yet entered the Debug mode, the external command controller goes to "step b", "step c" etc. until the Debug mode is acknowledged.



Examples of JTAG and OnCE interaction

 Table 10-13
 TMS Sequencing for ENABLE_ONCE

Step	TMS	JTAG Port	OnCE Module	Note
a	1	Test-Logic-Reset	Idle	
b	0	Run-Test/Idle	Idle	
С	1	Select-DR-Scan	Idle	
d	1	Select-IR-Scan	Idle	
e	0	Capture-IR	Idle	The core status bits are captured.
f	0	Shift-IR	Idle	The four bits of the JTAG
g	0	Shift-IR	Idle	ENABLE_ONCE instruction (0110) are shifted into the JTAG
h	0	Shift-IR	Idle	instruction register while status is shifted out.
i	0	Shift-IR	Idle	
j	1	Exit1-IR	Idle	
k	1	Update-IR	Idle	The OnCE module is enabled.
l	0	Run-Test/Idle	Idle	This step can be repeated, enabling an external command controller to
			poll the status.	
l	0	Run-Test/Idle	Idle	

 Table 10-14
 TMS Sequencing for Reading Pipeline Registers

Step	TMS	JTAG Port	OnCE Module	Note
a	0	Run-Test/Idle	Idle	
b	1	Select-DR-Scan	Idle	
С	0	Capture-DR	Idle	
d	0	Shift-DR	Idle	The eight bits of the OnCE command "Read PIL"
	•••••			(10001011) are shifted in.
d	0	Shift-DR	Idle	





On-Chip Emulation Module

Examples of JTAG and OnCE interaction

 Table 10-14
 TMS Sequencing for Reading Pipeline Registers (Continued)

Step	TMS	JTAG Port	OnCE Module	Note
e	1	Exit1-DR	Idle	
f	1	Update-DR	Execute "Read PIL"	The PIL value is loaded in the shifter.
g	1	Select-DR-Scan	Idle	
h	0	Capture-DR	Idle	
i	0	Shift-DR	Idle	The 24 bits of the PIL are
	•••••			shifted out (24 steps).
i	0	Shift-DR	Idle	
j	1	Exit1-DR	Idle	
k	1	Update-DR	Idle	
1	1	Select-DR-Scan	Idle	
m	0	Capture-DR	Idle	
n	0	Shift-DR	Idle	The eight bits of the OnCE
				command "Read PDB" (10001010) are shifted in
n	0	Shift-DR	Idle	
О	1	Exit1-DR	Idle	
p	1	Update-DR	Execute "Read PDB"	PDB value is loaded in shifter
q	1	Select-DR-Scan	Idle	
r	0	Capture-DR	Idle	
S	0	Shift-DR	Idle	The 24 bits of the PDB are
				shifted out (24 steps).
s	0	Shift-DR	Idle	
t	1	Exit1-DR	Idle	
u	1	Update-DR	Idle	



On-Chip Emulation Module

Examples of JTAG and OnCE interaction

 Table 10-14
 TMS Sequencing for Reading Pipeline Registers (Continued)

Step	TMS	JTAG Port	OnCE Module	Note
V	0	Run-Test/Idle	Idle	This step can be repeated, enabling an external
				command controller to
v	0	Run-Test/Idle	Idle	analyze the information.


During "step v" the external command controller stores the pipeline information and afterwards it can proceed with the debug activities as requested by the user.







SECTION 11 JTAG PORT





11.1	INTRODUCTION	11-3
11.2	JTAG PINS	11-5
11.3	TAP CONTROLLER	11-6
11 4	DSP56600 RESTRICTIONS	11-12



JTAG Port

Introduction

11.1 INTRODUCTION

The DSP56600 core provides a dedicated user-accessible Test Access Port (TAP) that is fully compatible with the IEEE 1149.1 Standard Test Access Port and Boundary Scan Architecture. Problems associated with testing high density circuit boards have led to development of this proposed standard under the sponsorship of the Test Technology Committee of IEEE and the Joint Test Action Group (JTAG). The DSP56600 core implementation supports circuit-board test strategies based on this standard.

The test logic includes a TAP that consists of five dedicated signal pins, a 16-state controller, and three test data registers. A Boundary Scan Register (BSR) links all device signal pins into a single shift register. The test logic, implemented utilizing static logic design, is independent of the device system logic. The DSP56600 core implementation provides the following capabilities:

- Perform boundary scan operations to test circuit-board electrical continuity (EXTEST).
- Bypass the DSP56600 core for a given circuit-board test by effectively reducing the BSR to a single cell (BYPASS).
- Sample the DSP56600 core-based device system pins during operation and transparently shift out the result in the BSR. Preload values to output pins prior to invoking the EXTEST instruction (SAMPLE/PRELOAD).
- Disable the output drive to pins during circuit-board testing (HI-Z).
- Provide a means of accessing the On-Chip Emulation (OnCE) controller and circuits to control a target system (ENABLE_ONCE).
- Provide a means of entering the Debug mode of operation (DEBUG_REQUEST).
- Query identification information (manufacturer, part number and version) from an DSP56600 core-based device (IDCODE).
- Force test data onto the outputs of an DSP56600 core-based device while replacing its boundary-scan register in the serial data path with a single bit register (CLAMP).

This section, which includes aspects of the JTAG implementation that are specific to the DSP56600 core, is intended to be used with the supporting IEEE 1149.1 document. The discussion includes those items required by the standard to be defined and, in certain cases, provides additional information specific to the DSP56600 core implementation. For internal details and applications of the standard,



Introduction

refer to the IEEE 1149.1 document. **Figure 11-1** shows a block diagram of the TAP port.




Figure 11-1 TAP Block Diagram



JTAG Port

JTAG Pins

11.2 **JTAG PINS**

As described in the IEEE 1149.1 document, the JTAG port requires a minimum of four pins to support TDI, TDO, TCK, and TMS signals. The DSP56600 family also provides the optional \overline{TRST} pin. On the DSP56603, the Debug Event (\overline{DE}) signal is provided for use by the OnCE module, and is described in Section 10, On-Chip **Emulation Module**. The pin functions are described in the following paragraphs.

Test Clock (TCK) 11.2.1

The Test Clock Input (TCK) pin is used to synchronize the test logic.

Test Mode Select (TMS) 11.2.2

The Test Mode Select Input (TMS) pin is used to sequence the test controller's state machine. The TMS is sampled on the rising edge of TCK and it has an internal pullup resistor.

11.2.3 Test Data Input (TDI)

Serial test instruction and data are received through the Test Data Input (TDI) pin. TDI is sampled on the rising edge of TCK and it has an internal pullup resistor.

Test Data Output (TDO) 11.2.4

The Test Data Output (TDO) pin is the serial output for test instructions and data. TDO is tri-stateable and is actively driven in the Shift-IR and Shift-DR controller states. TDO changes on the falling edge of TCK.

Test Reset (TRST) 11.2.5

The Test Reset Input (TRST) pin is used to asynchronously initialize the test controller. The TRST pin has an internal pullup resistor.

TAP Controller

11.3 TAP CONTROLLER

The TAP controller is responsible for interpreting the sequence of logical values on the TMS signal. It is a synchronous state machine that controls the operation of the JTAG logic. The state machine is shown in **Figure 11-2**. The TAP controller responds to changes at the TMS and TCK signals. Transitions from one state to another occur on the rising edge of TCK. The value shown adjacent to each state transition represents the value of the TMS signal sampled on the rising edge of TCK signal. For a description of the TAP controller states, please refer to *IEEE 1149.1 Standard Test Access Port and Boundary Scan Architecture*.




Figure 11-2 TAP Controller State Machine

11-6



TAP Controller

JTAG Port

11.3.1 **Boundary Scan Register**

The Boundary Scan Register (BSR) in the DSP56603 JTAG implementation contains bits for all device signal and clock pins and associated control signals. All DSP56603 bidirectional pins have a single register bit in the BSR for pin data, and are controlled by an associated control bit in the BSR. The DSP56603 BSR bit definitions are described in **Table 11-2** on page 11-13.

11.3.2 Instruction Register

The DSP56603 JTAG implementation includes the three mandatory public instructions (EXTEST, SAMPLE/PRELOAD, and BYPASS), and also supports the optional CLAMP instruction defined by IEEE 1149.1. The HI-Z public instruction provides the capability for disabling all device output drivers. The ENABLE_ONCE public instruction enables the JTAG port to communicate with the OnCE circuitry. The DEBUG_REQUEST public instruction enables the JTAG port to force the DSP56600 core into the Debug mode of operation. The DSP56600 core includes a 4-bit instruction register without parity consisting of a shift register with four parallel outputs. Data is transferred from the shift register to the parallel outputs during the Update-IR controller state. Figure 11-3 shows the JTAG Instruction Register.




Figure 11-3 JTAG Instruction Register

The four bits are used to decode the eight unique instructions shown in **Table 11-1**. All other encodings are reserved for future enhancements and are decoded as BYPASS.



TAP Controller

Table 11-1 JTAG Instructions

	Co	ode		Instruction	
В3	B2	B1	В0		
0	0	0	0	EXTEST	
0	0	0	1	SAMPLE/PRELOAD	
0	0	1	0	IDCODE	
0	0	1	1	CLAMP	
0	1	0	0	HI-Z	
0	1	0	1	RESERVED	
0	1	1	0	ENABLE_ONCE	
0	1	1	1	DEBUG_REQUEST	
1	0	X	Х	(Reserved)	
1	1	0	х	(Reserved)	
1	1	1	0	(Reserved)	
1	1	1	1	BYPASS	

The parallel output of the instruction register is reset to 0010 in the Test-Logic-Reset controller state, which is equivalent to the IDCODE instruction.

During the Capture-IR controller state, the parallel inputs to the instruction shift register are loaded with 01 in the least significant bits as required by the standard. The two most significant bits are loaded with the values of the core status bits OS1 and OS0 from the OnCE controller. See **Section 10**, **On-Chip Emulation Module**, for a description of the status bits.



TAP Controller

JTAG Port

11.3.2.1 EXTEST (B[3:0] = 0000)

The external test (EXTEST) instruction selects the BSR. EXTEST also asserts internal reset for the DSP56600 core system logic to force a predictable internal state while performing external boundary scan operations.

By using the TAP, the BSR is capable of the following:

- Scanning user-defined values into the output buffers
- Capturing values presented to input pins
- Controlling the direction of bidirectional pins
- Controlling the output drive of tri-stateable output pins

For more details on the function and use of the EXTEST instruction, please refer to the IEEE 1149.1 document.

SAMPLE/PRELOAD (B[3:0] = 0001) 11.3.2.2

The SAMPLE/PRELOAD instruction provides two separate functions. First, it provides a means to obtain a snapshot of system data and control signals. The snapshot occurs on the rising edge of TCK in the Capture-DR controller state. The data can be observed by shifting it transparently through the BSR.

Note: Since there is no internal synchronization between the JTAG clock (TCK) and the system clock (CLK), the user must provide some form of external synchronization to achieve meaningful results.

The second function of the SAMPLE/PRELOAD instruction is to initialize the BSR output cells prior to selection of EXTEST. This initialization ensures that known data appears on the outputs when entering the EXTEST instruction.

11.3.2.3 IDCODE (B[3:0] = 0010)

The IDCODE instruction selects the ID register. This instruction is provided as a public instruction to allow the manufacturer, part number, and version of a component to be determined through the TAP. Figure 11-4 shows the ID register configuration.



TAP Controller

31 28	3 ₁ 27 22	21 17	, 16 12	11 1	0
Version Information	n Cu	stomer Part Nui	Manufacturer Identity	1	
	Design Center Number	Core Number	Chip Derivative Number		
00000	000110	00001	nnnn	00000001110	1

AA0718

Figure 11-4 JTAG ID Register

One application of the ID register is to distinguish the manufacturer(s) of components on a board when multiple sourcing is used. As more components emerge which conform to the IEEE 1149.1 standard, it is desirable to allow for a system diagnostic controller unit to blindly interrogate a board design in order to determine the type of each component in each location. This information is also available for factory process monitoring and for failure mode analysis of assembled boards.

Motorola's Manufacturer Identity is 00000001110. The Customer Part Number consists of two parts: Motorola Design Center Number (bits 27:22) and a sequence number (bits 21:12). The sequence number is divided into two parts: Core Number (bits 21:17) and Chip Derivative Number (bits 16:12). Motorola Semiconductor IsraeL (MSIL) Design Center Number is 000110 and DSP56600 core number is 00001.

Once the IDCODE instruction is decoded, it selects the ID register, which is a 32-bit data register. Since the Bypass register loads a logic 0 at the start of a scan cycle, whereas the ID register loads a logic 1 into its least significant bit, examination of the first bit of data shifted out of a component during a test data scan sequence immediate following exit from Test-Logic-Reset controller state shows whether such a register is included in the design. When the IDCODE instruction is selected, the operation of the test logic has no effect on the operation of the on-chip system logic as required by the IEEE 1149.1 standard.

11.3.2.4 CLAMP (B[3:0] = 0011)

The CLAMP instruction is not included in the IEEE 1149.1 standard. It is provided as a public instruction that selects the 1-bit Bypass register as the serial path between TDI and TDO while allowing signals driven from the component pins to be determined from the BSR. During testing of ICs on PCB, it may be necessary to place static guarding values on signals that control operation of logic not involved in the test. The EXTEST instruction could be used for this purpose, but since it selects the



TAP Controller

JTAG Port

Boundary Scan Register the required guarding signals would be loaded as part of the complete serial data stream shifted in, both at the start of the test and each time a new test pattern is entered. Since the CLAMP instruction allows guarding values to be applied using the boundary-scan register of the appropriate ICs while selecting their Bypass registers, it allows much faster testing than does the EXTEST instruction. Data in the boundary scan cell remains unchanged until a new instruction is shifted in or the JTAG state machine is set to its reset state. The CLAMP instruction also asserts internal reset for the DSP56600 core system logic to force a predictable internal state while performing external boundary scan operations.

HI-Z (B[3:0] = 0100)11.3.2.5

The HI-Z instruction is not included in the IEEE 1149.1 standard. It is provided as a manufacturer's optional public instruction to prevent having to backdrive the output pins during circuit-board testing. When HI-Z is invoked, all output drivers, including the two-state drivers, are turned off (i.e., high impedance). The instruction selects the Bypass register. The HI-Z instruction also asserts internal reset for the DSP56600 core system logic to force a predictable internal state while performing external boundary scan operations

11.3.2.6 $ENABLE_ONCE(B[3:0] = 0110)$

The ENABLE_ONCE instruction is not included in the IEEE 1149.1 standard. It is provided as a public instruction to allow the user to perform system debug functions. When the ENABLE_ONCE instruction is decoded the TDI and TDO pins are connected directly to the OnCE registers. The particular OnCE register connected between TDI and TDO at a given time is selected by the OnCE controller depending on the OnCE instruction being currently executed. All communication with the OnCE controller is done through the Select-DR-Scan path of the JTAG TAP Controller. See Section 10, On-Chip Emulation (OnCE), for more information.

11.3.2.7 $DEBUG_REQUEST(B[3:0] = 0111)$

The DEBUG_REQUEST instruction is not included in the IEEE 1149.1 standard. It is provided as a public instruction to allow the user to generate a debug request signal to the DSP56600 core. When the DEBUG_REQUEST instruction is decoded, the TDI and TDO pins are connected to the Instruction Registers. Due to the fact that in the Capture-IR state of the TAP the OnCE status bits are captured in the Instruction shift register, the external JTAG controller must continue to shift in the DEBUG_REQUEST instruction while polling the status bits that are shifted out until the Debug mode of operation is entered (acknowledged by the combination 11 on OS1-OS0). After the acknowledgment of the Debug mode is received, the external JTAG controller must issue the ENABLE_ONCE instruction to allow the user to perform system debug functions.



DSP56600 Restrictions

11.3.2.8 BYPASS (B[3:0] = 1111)

The BYPASS instruction selects the single-bit Bypass register as shown in **Figure 11-5**. This creates a shift register path from TDI to the Bypass register, and finally to TDO, circumventing the BSR. This instruction is used to enhance test efficiency when a component other than the DSP56600 core-based device becomes the device under test. When the Bypass register is selected by the current instruction, the shift-register stage is set to a logic 0 on the rising edge of TCK in the Capture-DR controller state. Therefore, the first bit shifted out after selecting the Bypass register is always a logic 0.




Figure 11-5 Bypass Register

11.4 DSP56600 RESTRICTIONS

The control afforded by the output enable signals using the BSR and the EXTEST instruction requires a compatible circuit-board test environment to avoid device-destructive configurations. The user must avoid situations in which the DSP56600 core output drivers are enabled into actively driven networks. In addition, the EXTEST instruction can be performed only after power-up or regular hardware reset while EXTAL was provided. Then during the execution of EXTEST, EXTAL can remain inactive.

There are two constraints related to the JTAG interface. First, the TCK input does not include an internal pullup resistor and should not be left unconnected. The second constraint is to ensure that the JTAG test logic is kept transparent to the system logic by forcing the TAP into the Test-Logic-Reset controller state, using either of two methods. During power-up, \overline{TRST} must be externally asserted to force the TAP controller into this state. After power-up is concluded, TMS must be sampled as a logic 1 for five consecutive TCK rising edges. If TMS either remains unconnected or is connected to V_{CC} , then the TAP controller cannot leave the Test-Logic-Reset state, regardless of the state of TCK.



JTAG Port

DSP56600 Restrictions

The DSP56600 core features a low-power Stop mode, which is invoked using the STOP instruction. The interaction of the JTAG interface with low-power Stop mode is as follows:

- The TAP controller must be in the Test-Logic-Reset state to either enter or remain in the low-power Stop mode. Leaving the TAP controller Test-Logic-Reset state negates the ability to achieve low-power, but does not otherwise affect device functionality.
- 2. The TCK input is not blocked in low-power Stop mode. To consume minimal power, the TCK input should be externally connected to V_{CC} or GND.
- 3. The TMS and TDI pins include on-chip pullup resistors. In low-power Stop mode, these two pins should remain either unconnected or connected to $V_{\rm CC}$ to achieve minimal power consumption.

Since during Stop mode all DSP56603 core clocks are disabled, the JTAG interface provides the means of polling the device status (sampled in the Capture-IR state).

Table 11-2 DSP56603 Boundary Scan Register (BSR) Bit Definitions

Bit #	Cell Type	Pin Name	Pin Type	BSR Cell Type
0	BC_1	MODA	Input	Data
1	BC_1	MODB	Input	Data
2	BC_1	MODC	Input	Data
3	BC_1	MODD	Input	Data
4	BC_6	D23	Input/Output	Data
5	BC_6	D22	Input/Output	Data
6	BC_6	D21	Input/Output	Data
7	BC_6	D20	Input/Output	Data
8	BC_6	D19	Input/Output	Data
9	BC_6	D18	Input/Output	Data
10	BC_6	D17	Input/Output	Data
11	BC_6	D16	Input/Output	Data



DSP56600 Restrictions

Table 11-2 DSP56603 Boundary Scan Register (BSR) Bit Definitions (Continued)

Bit #	Cell Type	Pin Name	Pin Type	BSR Cell Type
12	BC_6	D15	Input/Output	Data
13	BC_1	D[23:12]	_	Control
14	BC_6	D14	Input/Output	Data
15	BC_6	D13	Input/Output	Data
16	BC_6	D12	Input/Output	Data
17	BC_6	D11	Input/Output	Data
18	BC_6	D10	Input/Output	Data
19	BC_6	D9	Input/Output	Data
20	BC_6	D8	Input/Output	Data
21	BC_6	D7	Input/Output	Data
22	BC_6	D6	Input/Output	Data
23	BC_6	D5	Input/Output	Data
24	BC_6	D4	Input/Output	Data
25	BC_6	D3	Input/Output	Data
26	BC_1	D[11:0]	_	Control
27	BC_6	D2	Input/Output	Data
28	BC_6	D1	Input/Output	Data
29	BC_6	D0	Input/Output	Data
30	BC_2	A15	Output 2	Data
31	BC_2	A14	Output 2	Data
32	BC_2	A13	Output 2	Data
33	BC_2	A12	Output 2	Data
34	BC_2	A11	Output 2	Data
35	BC_2	A10	Output 2	Data



JTAG Port

DSP56600 Restrictions

 Table 11-2
 DSP56603 Boundary Scan Register (BSR) Bit Definitions (Continued)

Bit #	Cell Type	Pin Name	Pin Type	BSR Cell Type
36	BC_2	A9	Output 2	Data
37	BC_2	A8	Output 2	Data
38	BC_2	A7	Output 2	Data
39	BC_2	A6	Output 2	Data
40	BC_2	A5	Output 2	Data
41	BC_2	A4	Output 2	Data
42	BC_2	A3	Output 2	Data
43	BC_2	A2	Output 2	Data
44	BC_2	A1	Output 2	Data
45	BC_2	A0	Output 2	Data
46	BC_2	MCS	Output	Data
47	BC_2	RD	Output	Data
48	BC_2	WR	Output	Data
49	BC_2	ĀT	Output	Data
50	BC_2	CLKOUT	Output	Data
51	BC_1	EXTAL	Input	Data
52	BC_1	RESET	Input	Data
53	BC_1	HAD0	_	Control
54	BC_6	HAD0	Input/Output	Data
55	BC_1	HAD1	_	Control
56	BC_6	HAD1	Input/Output	Data
57	BC_1	HAD2	_	Control
58	BC_6	HAD2	Input/Output	Data
59	BC_1	HAD3	_	Control

Go to: www.freescale.com



DSP56600 Restrictions

Freescale Semiconductor, Inc.

 Table 11-2
 DSP56603 Boundary Scan Register (BSR) Bit Definitions (Continued)

Bit #	Cell Type	Pin Name	Pin Type	BSR Cell Type
60	BC_6	HAD3	Input/Output	Data
61	BC_1	HAD4	_	Control
62	BC_6	HAD4	Input/Output	Data
63	BC_1	HAD5	_	Control
64	BC_6	HAD5	Input/Output	Data
65	BC_1	HAD6	_	Control
66	BC_6	HAD6	Input/Output	Data
67	BC_1	HAD7	_	Control
68	BC_6	HAD7	Input/Output	Data
69	BC_1	HAS/A0	_	Control
70	BC_6	HAS/A0	Input/Output	Data
71	BC_1	HA8/A1	_	Control
72	BC_6	HA8/A1	Input/Output	Data
73	BC_1	HA9/A2	_	Control
74	BC_6	HA9/A2	Input/Output	Data
75	BC_1	HCS/A10	_	Control
76	BC_6	HCS/A10	Input/Output	Data
77	BC_1	TIO0	_	Control
78	BC_6	TIO0	Input/Output	Data
79	BC_1	TIO1	_	Control
80	BC_6	TIO1	Input/Output	Data
81	BC_1	TIO2		Control
82	BC_6	TIO2	Input/Output	Data
83	BC_1	HREQ/TRQ	_	Control





JTAG Port

DSP56600 Restrictions

Table 11-2 DSP56603 Boundary Scan Register (BSR) Bit Definitions (Continued)

Bit #	Cell Type	Pin Name	Pin Type	BSR Cell Type
84	BC_6	HREQ/TRQ	Input/Output	Data
85	BC_1	HACK/RRQ	_	Control
86	BC_6	HACK/RRQ	Input/Output	Data
87	BC_1	HRW/RD	_	Control
88	BC_6	HRW/RD	Input/Output	Data
89	BC_1	HDS/WR	_	Control
90	BC_6	HDS/WR	Input/Output	Data
91	BC_1	SCK0	_	Control
92	BC_6	SCK0	Input/Output	Data
93	BC_1	SCK1	_	Control
94	BC_6	SCK1	Input/Output	Data
95	BC_1	GPIO2	_	Control
96	BC_6	GPIO2	Input/Output	Data
97	BC_1	GPIO1	_	Control
98	BC_6	GPIO1	Input/Output	Data
99	BC_1	GPIO0	_	Control
100	BC_6	GPIO0	Input/Output	Data
101	BC_1	SC00	_	Control
102	BC_6	SC00	Input/Output	Data
103	BC_1	SC10	_	Control
104	BC_6	SC10	Input/Output	Data
105	BC_1	STD0	_	Control
106	BC_6	STD0	Input/Output	Data
107	BC_1	SRD0	_	Control



DSP56600 Restrictions

 Table 11-2
 DSP56603 Boundary Scan Register (BSR) Bit Definitions (Continued)


Bit #	Cell Type	Pin Name	Pin Type	BSR Cell Type
108	BC_6	SRD0	Input/Output	Data
109	BC_1	PINIT	_	Control
110	BC_6	PINIT	Input/Output	Data
111	BC_1	DE	_	Control
112	BC_6	DE	Input/Output	Data
113	BC_1	SC01	_	Control
114	BC_6	SC01	Input/Output	Data
115	BC_1	SC02	_	Control
116	BC_6	SC02	Input/Output	Data
117	BC_1	STD1	_	Control
118	BC_6	STD1	Input/Output	Data
119	BC_1	SRD1	_	Control
120	BC_6	SRD1	Input/Output	Data
121	BC_1	SC11	_	Control
122	BC_6	SC11	Input/Output	Data
123	BC_1	SC12	_	Control







APPENDIX A BOOTSTRAP PROGRAM





A.1	DSP56603 BOOTSTRAP LISTING	Δ-3
A. I	- DOI 30003 DOO FOTINAL EIGTING	1





Bootstrap Program

DSP56603 Bootstrap Listing

A.1 DSP56603 BOOTSTRAP LISTING

The bootstrap source code listing provided in **Example A-1** is programmed into the DSP56603 chip at the factory. Use this listing to develop external ROM programming for DSP56603 applications.

Notes:

- 1. This example for the DSP56603 does not take advantage of the functionality provided by the MD bit.
- **2.** When compiling source code, the correct X I/O equate and interrupt equate files (specified by ioequ.asm and intequ.asm) must be used. Listings for these files are provided in Appendix B, X I/O Equates.

Example A-1 DSP56603 Bootstrap Listing

```
; BOOTSTRAP CODE FOR DSP56603 - (C) Copyright 1996 Motorola Inc.
       include
                      "ioequ.asm"
       include
                      "intequ.asm"
; Written April 21, 1996
; reset addresses:
                   mode 0 $8000 (external)
                   mode 8 $0000 (internal pram)
                   mode 1-7 $0400 (internal prom)
                   mode 9-F $0400 (internal prom)
              $8000
EXTERN equ
       org
              p:$400
       move
              omr,a
       and
              #<$7,a
       move
              #j_table,r0
       move
              a,n0
       move
              p:(r0+n0),r0
              (r0)
       jmp
j_table
                             ; jump table starting address
                             ; mode 0
       dc
              ERROR
                             ; If MC:MB:MA=000, goto error (should reset to external)
```



Bootstrap Program

Freescale Semiconductor, Inc.

DSP56603 Bootstrap Listing

Example A-1 DSP56603 Bootstrap Listing (Continued)

```
; mode 1 (reserved mode)
       dc
              ERROR
                           ; If MC:MB:MA=001, goto error (reserved mode)
                           ; If MC:MB:MA=010, go load from 68338 (hi08)
       dc
             HOSTLD68338
                           ; mode 3
              ERAMLDS
                           ; If MC:MB:MA=011, go load from external slow (31 ws)
       dc
                           ; 24 bit memory
                           ; mode 4
      dc
              EPROMLDS
                           ; If MC:MB:MA=100, go load from external slow (31 ws)
                           ; 8 bit memory
                           ; mode 5
      dc
              ISAHOSTLD
                           ; If MC:MB:MA=101, go load from ISA (hi08)
                           ; mode 6
             HC11HOSTLD
                           ; If MC:MB:MA=110, go load from HC11 (hi08)
      dc
                           ; mode 7
       dc
                           ; If MC:MB:MA=111, go to typ2 current consumption test
; This routine loads a program through the HIO8 host port
; The program is downloaded from the host MCU with the following rules:
; 1) 2 bytes - Define the program length.
; 2) 2 bytes - Define the address to which to start loading the program to.
; 3) 2 bytes - Define the address to jump to after program is loaded
; 4) 4n bytes (while n is any integer number)
; The program words will be stored in contiguous PRAM memory locations starting
; at the specified starting address.
; After reading the program words, program execution starts from the same address
; where loading started.
; The host MCU may terminate the loading process by setting the HF1=0 and HF0=1.
; When the downloading is terminated, the program will start execution of the
; loaded program
; from the specified starting address.
; The HI08 boot ROM program enables the following busses to download programs
; through the HI08 port:
      1 - ISA
      2 - HC11
       3 - 68338
```





Bootstrap Program

DSP56603 Bootstrap Listing

```
HOSTI-D68338
                             ; boot from 68338 host processor
       movep #%000000100110000,x:M HPCR; Configure the following conditions:
                             ; HAP = 0 Negative host acknowledge
                             ; HRP = 0 Negative host request
                             ; HCSP = 0 Negative chip select input
                             ; HD/HS = 0 Single strobe bus (R/W~ and DS strobes)
                             ; HMUX = 0 Non multiplexed bus
                             ; HASP = 0 (address strobe polarity has no
                             ; meaning in non-multiplexed bus)
                             ; HDSP = 0 Negative data strobes polarity
                             ; HROD = 1 Host request is open-drain
                             ; spare = 0 Set this bit to 0 for future compatibility
                             ; HEN = 0 When the HPCR register is
                             ; modified HEN should be cleared
                             ; HAEN = 1 Host acknowledge is enabled
                             ; HREN = 1 Host requests are enabled
                             ; HCSEN = 0 Host chip select input disabled
                             ; HA9EN = 0 (address 9 enable bit has no meaning in
                             ; non-multiplexed bus)
                             ; HA8EN = 0 (address 8 enable bit has no meaning in
                             ; non-multiplexed bus)
                             ; HGEN = 0 Host GPIO pins are disabled
              HI08CON
       jmp
TSAHOSTI D
                             ; boot from ISA bus
              #%0101000000011000,x:M_HPCR
                             ; Configure the following conditions:
                             ; HAP = 0 Negative host acknowledge
                             ; HRP = 1 Positive host request
                             ; HCSP = 0 Negative chip select input
                             ; HD/HS = 1 Dual strobes bus (RD and WR strobes)
                             ; HMUX = 0 Non multiplexed bus
                             ; HASP = 0 (address strobe polarity has no meaning in
                             ; non-multiplexed bus)
                             ; HDSP = 0 Negative data strobes polarity
                             ; HROD = 0 Host request is active when enabled
                             ; spare = 0 Set this to 0 for future compatibility
                             ; HEN = 0 Clear HEN when the HPCR register is modified
                             ; HAEN = 0 Host acknowledge is disabled
                             ; HREN = 1 Host requests are enabled
                             ; HCSEN = 1 Host chip select input enabled
                             ; HA9EN = 0 (address 9 enable bit has no meaning in
                             ; non-multiplexed bus)
                             ; HA8EN = 0 (address 8 enable bit has no meaning in
                             ; non-multiplexed bus)
                             ; HGEN = 0 Host GPIO pins are disabled
              HI08CONT
       jmp
```

A-6



Bootstrap Program

Freescale Semiconductor, Inc.

DSP56603 Bootstrap Listing

```
HC11HOSTLD
                             ; boot from 68HC11 processor
       movep #%000001000011000,x:M_HPCR
                             ; Configure the following conditions:
                             ; HAP = 0 Negative host acknowledge
                             ; HRP = 0 Negative host request
                             ; HCSP = 0 Negative chip select input
                             ; HD/HS = 0 Single strobe bus (R/W\sim and DS strobes)
                             ; HMUX = 0 Non multiplexed bus
                             ; HASP = 0 (address strobe polarity has no meaning in
                             ; non-multiplexed bus)
                             ; HDSP = 1 Negative data strobes polarity
                             ; HROD = 0 Host request is active when enabled
                             ; spare = 0 Set this bit to 0 for future compatibility
                             ; HEN = 0 Clear HEN when the HPCR register is modified
                             ; HAEN = 0 Host acknowledge is disabled
                             ; HREN = 1 Host requests are enabled
                             ; HCSEN = 1 Host chip select input enabled
                             ; HA9EN = 0 (address 9 enable bit has no meaning in
                             ; non-multiplexed bus)
                             ; HA8EN = 0 (address 8 enable bit has no meaning in
                             ; non-multiplexed bus)
                             ; HGEN = 0 Host GPIO pins are disabled
HI08CONT
       bset
               #M_HEN,x:M_HPCR
                             ; Enable HI08 to operate as host interface (set HEN=1)
       jclr
               #M_HRDF,x:M_HSR,*
                             ; wait for the program length to be written
              x:M_HRX,a0
                             ; download length in a0
       movep
       jclr
              #M_HRDF,x:M_HSR,*
                             ; wait for the program starting address to be written
              x:M_HRX,r0
       movep
                             ; destination starting address in r0
       jclr
              #M_HRDF,x:M_HSR,*
                             ; wait for the program address to jump to
                             ; after program is loaded
       movep
              x:M_HRX,r1
                             ; target branch address in rl
       nop
       do
              a0,HI08LOOP
                             ; set a loop with the downloaded length counts
HI08LL
              #M_HRDF,x:M_HSR,HI08NW
       jset
                             ; If new word was loaded then jump to read that word
               #M_HF0,x:M_HSR,HI08LL
       jclr
                             ; If HF0=0 then continue with the downloading
       enddo
                             ; Must terminate the do loop
              HI08LOOP
       jmp
```

Semiconductor, Inc.



Freescale Semiconductor, Inc.

Bootstrap Program

DSP56603 Bootstrap Listing

```
MI08NM
      movep x:M_HRX,x:M_BPMRL
                         ; low 16 bits of the 24-bit program word
HI08LL1
      jset
             #M_HRDF,x:M_HSR,HI08NW1
                         ; If new word was loaded then jump to read that word
      jclr
             #M_HF0,x:M_HSR,HI08LL1
                         ; If HF0=0 then continue with the downloading
      enddo
                         ; Must terminate the do loop
      jmp
            HI08LOOP
HI08NW1
            x:M_HRX,x:M_BPMRH
      movep
                         ; high 8 bits of the 24-bit program word
            x:M_BPMRG,p:(r0)+
                          ; Move the new word into its destination location
                         ; in the program RAM
      nop
      nop
      nop
HI08LOOP
; This routine loads from external slow (31 ws) 24 bit memory.
ERAMLDS
       move#EXTERN,r2
                         ; r2 = address of external EPROM
      movem p:(r2)+,r0
                       ; read starting address to load to r0
      movem p:(r2)+,r7
                         ; read number of words to load to r7
      movem p:(r2)+,r1
                         ; read starting address to jump to after loading, into r1
      r7, ERAMLDSLOOP
do
                         ; read program words
       movepp:(r2)+,x:M_BPMRG
                          ; Get 24 bit word from ext. P mem.
       movepx:M_BPMRG,p:(r0)+
                         ; Store 24-bit word in P ram.
      nop
      nop
      nop
ERAMLDSLOOP
                         ; and go get another 24-bit word.
            FINISH
                         ; Boot from EPROM done
```



Freescale Semiconductor, Inc.

DSP56603 Bootstrap Listing

```
; This routine loads from external slow (31 ws) 8 bit EPROM.
EPROMLDS
       move #EXTERN,r2
                            ; r2 = address of external EPROM
do #4,_LOOP8
                            ; read number of words and starting address to load to
        movem p:(r2)+,a2
                            ; Get the 8 LSB from ext. P mem.
        asr #8,a,a
                            ; Shift 8 bit data into Al
       nop
       nop
_LOOP8
                            ; starting address for load
       move al,r0
       move a0,r7
                            ; a0 holds the number of words
                            ; read starting address to jump to after loading
do #2,_LOOP9
       movem p:(r2)+,a2
                            ; Get the 8 LSB from ext. P mem.
                            ; Shift 8 bit data into Al
       asr #8,a,a
       nop
       nop
LOOP9
                            ; save it in r1
       move al,rl
       nop
       move al,rl
                            ; save it in r1
do r7,_LOOP10
                            ; read program words
       do #2,_LOOP11
                           ; get lower 16 bits of each 24-bit instruction
       movem p:(r2)+,a2
                           ; Get the 8 LSB from ext. P mem.
       asr #8,a,a
                            ; Shift 8 bit data into Al
       nop
       nop
_LOOP11
                            ; Go get another byte.
       movep al,x:M_BPMRL ; Store 16-bit result in BPMRL
       movem p:(r2)+,a1
                            ; Get the 8 LSB from ext. P mem.
       movep al,x:M_BPMRH ; Store 16-bit result in BPMRL
       movep x:M_BPMRG,p:(r0)+
                             ; Store 24-bit result in P mem.
       nop
       nop
_LOOP10
                             ; and go get another 24-bit word.
                             ; Boot from EPROM done
; This is the exit handler that returns execution to normal
; expanded mode and jumps to the RESET vector.
        andi #$0,ccr
                            ; Clear CCR as if RESET to 0.
        jmp (r1)
                            ; Then go to starting Prog address.
```





DSP56603 Bootstrap Listing

```
TYP2
               #px,r0
       move
               #0,r1
       move
       do
               #64,pxe
                               ; copy x data to xram
               p:(r0)+,x0
       move
               x0,x:(r1)+
       move
       nop
       nop
pxe
               #py,r0
       move
       move
               #0,r1
               #64,pye
                              ; copy y data to Y ram
       do
       move
               p:(r0)+,x0
               x0,y:(r1)+
       move
       nop
       nop
pye
       bset
               #7,x:M_PCTL1 ; CLKOUT disable
               #4,x:M_PCTL1 ; XTAL disable
       bset
               #$10,omr
                              ;set EDB
       ori
       ori
               #$20,omr
                              ;set PCD
               #$0,r0
       move
               #$0,r4
       move
               #$3f,m0
       move
               #$3f,m4
       move
       clr
       clr
               #$0,x0
       move
               #$0,x1
       move
       move
               #$0,y0
               #$0,y1
       move
loop
               forever,_end
       do
               x0,y0,a
                              x:(r0)+,x1
                                             y:(r4)+,y1
       mac
               x1,y1,a
                              x:(r0)+,x0
                                             y:(r4)+,y0
       mac
       add
       mac
               x0,y0,ax:(r0)+,x1
       mac
               x1,y1,a
                                 y:(r4)+,y0
               b1,x:$ff
       move
_end
рх
       dc
               $2EB9
       dc
               $F2FE
       dc
               $6A5F
       dc
               $6CAC
               $FD75
               $10A
       dc
```



Freescale Semiconductor, Inc.

DSP56603 Bootstrap Listing

	Example A-1	DSP56603 Bootstrap Listing (Continued)
dc	\$6D7B	
dc	\$A798	
dc	\$FBF1	
dc	\$63D6	
dc	\$6657	
dc	\$A544	
dc	\$662D	
dc	\$E762	
dc	\$F0F3	
dc	\$F1B0	
dc	\$829	
dc	\$F7AE	
dc	\$A94F	
dc	\$78DC	
dc	\$2DE5	
dc	\$E0BA	
dc	\$AB6B	
dc	\$26C8	
dc	\$361	
dc	\$6E86	
dc	\$7347	
dc	\$E774	
dc	\$349D	
dc	\$ED12	
dc	\$FCE3	
dc	\$26E0	
dc	\$7D99	
dc	\$A85E	
dc	\$A43F	
dc	\$B10C	
dc	\$A55	
dc	\$EC6A	
dc	\$255B	
dc	\$F1F8	
dc	\$26D1	
dc	\$6536	
dc	\$BC37	
dc	\$35A4	
dc	\$F0D	
dc	\$BEC2	
dc	\$E4D3	
dc	\$E810	
dc	\$F09	
dc	\$E50E	
dc	\$FB2F	
dc	\$753C	
dc	\$62C5	
dc	\$641A	
dc	\$3B4B	



Bootstrap Program

DSP56603 Bootstrap Listing

		Lampie 11 1	D51 00000	Dootstrap Els
	dc	\$A928		
	dc	\$6641		
	dc	\$A7E6		
	dc	\$2127		
	dc	\$2FD4		
	dc	\$57D		
	dc	\$3C72		
	dc	\$8C3		
	dc	\$7540		
ру				
	dc	\$6DA		
	dc	\$F70B		
	dc	\$39E8		
	dc	\$E801		
	dc	\$66A6		
	dc	\$F8E7		
	dc	\$EC94		
	dc	\$233D		
	dc	\$2732		
	dc	\$3C83		
	dc	\$3E00		
	dc	\$B639		
	dc	\$A47E		
	dc	\$FDDF		
	dc	\$A2C		
	dc	\$7CF5		
	dc	\$6A8A		
	dc	\$B8FB		
	dc	\$ED18		
	dc	\$F371		
	dc	\$A556		
	dc	\$E9D7		
	dc	\$A2C4		
	dc	\$35AD		
	dc	\$E0E2		
	dc	\$2C73		
	dc	\$2730		
	dc	\$7FA9		
	dc	\$292E		
	dc	\$3CCF		
	dc	\$A65C		
	dc	\$6D65		
	dc	\$A3A		
	dc	\$B6EB		
	dc	\$AC48		
	dc	\$7AE1		
	dc	\$3006		
	dc	\$F6C7		
	dc	\$64F4		



Freescale Semiconductor, Inc.

DSP56603 Bootstrap Listing

Example A-1 DSP56603 Bootstrap Listing (Continued)


```
dc
               $E41D
       dc
               $2692
       dc
               $3863
       dc
               $BC60
       dc
               $A519
               $39DE
       dc
               $F7BF
       dc
       dc
               $3E8C
       dc
               $79D5
       dc
               $F5EA
       dc
               $30DB
               $B778
       dc
       dc
               $FE51
       dc
               $A6B6
       dc
               $FFB7
       dc
               $F324
       dc
               $2E8D
       dc
               $7842
       dc
               $E053
               $FD90
       dc
       dc
               $2689
       dc
               $B68E
               $2EAF
       dc
       dc
               $62BC
       dc
               $A245
ERROR
       bset
               #7,x:M_PCTL1
                               ; ClockOut disable
               #4,x:M_PCTL1 ; XTAL disable
       bset
       bclr
               #6,x:M_PCTL1 ; PLL Disable
               #$10,omr
                               ;set EDB
       ori
               #$20,omr
                               ;set PCD
       ori
       nop
       nop
       nop
       nop
       nop
       stop
       nop
       nop
       nop
```

dsp





APPENDIX B X I/O EQUATES





B.1	DSP56603 X I/O EQUATES	B-3
B.2	DSP56603 INTERRUPT EQUATES	B-10



DSP56603 X I/O Equates

X I/O Equates

B.1 DSP56603 X I/O EQUATES

Example B-1 provides X I/O equates for the DSP56603. If bootstrap code is developed for the DSP56603 (for external bootstrap loading), this listing should be enclosed in a file titled ioequ.asm for inclusion in the bootstrap executable.

Example B-1 DSP56603 X I/O Equates

```
EQUATES for DSP56603 I/O registers and ports
     Reference: DSP56603 Specifications Revision 0.1
     1st update: June 20 1996 (creation,
                               copied from DSP56602 and modified) by Zvika R.
     Last update:
 page 132,55,0,0,0
        opt mex
DSP56603
             EQU
ioequ
       ident
               1,0
       EQUATES for I/O Port Programming
       Register Addresses
       EQU
                          ; Host Port GPIO Data Direction Register
M_HDDR
               $FFC8
        EQU
                $FFC9
                            ; Host Port GPIO Data Register
M_HDR
M_PCRC
       EOU
                $FFBF
                            ; SSIO Port Control Register
M_PRRC
       EQU
                $FFBE
                             ; SSIO GPIO Direction Register
M_PDRC EQU
                $FFBD
                             ; SSIO GPIO Data Register
M_PCRD
       EQU
                $FFAF
                            ; SSI1 Port Control register
                             ; SSI1 GPIO Direction Data Register
M_PRRD
       EOU
                $FFAE
M_PDRD
        EOU
                $FFAD
                             ; SSI1 GPIO Data Register
                             ; GPIO Control Register
M_PCRE
       EQU
                $FF9F
M_PRRE
       EQU
                $FF9E
                             ; GPIO Direction Register
M_PDRE
                             ; GPIO Data Register
        EOU
                $FF9D
                             ; OnCE GDB Register
M_OGDB
        EQU
                $FFFB
```



DSP56603 X I/O Equates

```
EQUATES for Host Interface
       Register Addresses
M HCR
        EQU
             $FFC2
                             ; Host Control Register
                $FFC3
                             ; Host Status Register
M HSR
        EQU
                             ; Host Polarity Control Register
M HPCR EQU
                $FFC4
M HBAR
       EQU
             $FFC5
                             ; Host Base Address Register
             $FFC6
                             ; Host Receive Register
M_HRX
        EQU
M_HTX
                $FFC7
                             ; Host Transmit Register
       HCR Bits Definition
M HRIE
       EQU
             $0
                             ; Host Receive Interrupt Enable
M_HTIE
                             ; Host Transmit Interrupt Enable
       EQU
               $1
M HCIE
       EQU
               $2
                              ; Host Command Interrupt Enable
M_HF2
        EQU
               $3
                             ; Host Flag 2
M HF3
       EQU
               $4
                              ; Host Flag 3
       HSR Bits Definition
M HRDF
       EQU
               $0
                             ; Host Receive Data Full
M HTDE
        EQU
               $1
                             ; Host Receive Data Empty
M_HCP
        EQU
              $2
                              ; Host Command Pending
M_HF0
             $3
                              ; Host Flag 0
        EQU
M_HF1
        EQU
                              ; Host Flag 1
       HPCR Bits Definition
M HGEN
                              ; Host Port GPIO Enable
M_HA8EN EQU
               $1
                              ; Host Address 8 Enable
M_HA9EN EQU
               $2
                              ; Host Address 9 Enable
M_HCSEN EQU
               $3
                              ; Host Chip Select Enable
M HREN
        EQU
               $4
                              ; Host Request Enable
M HAEN EQU
                             ; Host Acknowledge Enable
             $5
M HEN
        EQU
               $6
                              ; Host Enable
M_HOD
        EQU
               $8
                              ; Host Request Open Drain Mode
M HDSP
                              ; Host Data Strobe Polarity
       EQU
               $9
M_HASP
                              ; Host Address Strobe Polarity
                              ; Host Multiplexed Bus select
M HMUX
        EQU
               $В
M HD HS EQU
               $C
                              ; Host Double/Single Strobe select
M_HCSP
        EQU
               $D
                              ; Host Chip Select Polarity
M HRP
                              ; Host Request Polarity
        EQU
               $E
M_HAP
        EQU
               $F
                              ; Host Acknowledge Polarity
```



X I/O Equates

DSP56603 X I/O Equates

```
EQUATES for Synchronous Serial Interface (SSI)
       Register Addresses of SSIO
M_TX0
        EQU
               $FFBC ; SSIO Transmit Data Register
                            ; SSIO Time Slot Register
                $FFBB
M_TSR0
        EQU
                            ; SSIO Receive Data Register
M_RX0
        EQU
                $FFBA
M_SSISR0 EQU
               $FFB9
                            ; SSIO Status Register
                            ; SSIO Control Register C
M_CRC0
       EQU
               $FFB8
M_CRB0 EQU
               $FFB7
                            ; SSIO Control Register B
M CRAO EQU
               $FFB6
                            ; SSIO Control Register A
       Register Addresses of SSI1
        EQU
               $FFAC ; SSI1 Transmit Data Register 0
M TX1
M_TSR1 EQU
               $FFAB
                           ; SSI1 Time Slot Register
M_RX1
        EQU
             $FFAA
                            ; SSI1 Receive Data Register
                            ; SSI1 Status Register
M_SSISR1 EQU
              $FFA9
M_CRC1 EQU
               $FFA8
                            ; SSI1 Control Register C
M_CRB1 EQU
                $FFA7
                            ; SSI1 Control Register B
                            ; SSI1 Control Register A
M_CRA1 EQU
                $FFA6
       SSI Control Register A Bit Flags
M_PSR
        EQU
                               ; Prescaler Range
M_DC
        EQU
                $1F00
                               ; Frame Rate Divider Control Mask (DC0-DC7)
                $6000
                               ; Word Length Control Mask (WL0-WL7)
M WL
        EQU
       SSI Control Register B Bit Flags
M_OF
        EQU
                $3
                               ; Serial Output Flag Mask
M_OF0
        EQU
                0
                               ; Serial Output Flag 0
M OF1
        EQU
                1
                               ; Serial Output Flag 1
M_SSTE EQU
                               ; SSI Transmit Enable
               8
M_SSRE EQU
               9
                               ; SSI Receive Enable
             10
                               ; SSI Transmit Interrupt Enable
M_SSTIE EQU
M_SSRIE EQU
                               ; SSI Receive Interrupt Enable
              12
M_STLIE EQU
                              ; SSI Transmit Last Slot Interrupt Enable
M_SRLIE EQU
                13
                              ; SSI Receive Last Slot Interrupt Enable
M_STEIE EQU
                14
                              ; SSI Transmit Error Interrupt Enable
                              ; SSI Receive Error Interrupt Enable
M_SREIE EQU
```



DSP56603 X I/O Equates

				• • • • • • • • • • • • • • • • • • • •
;	SSI Cont	trol Register	C Bit	Flags
M_SYN	EQU	0	;	Sync/Async Control
M_MOD	EQU	1	;	SSI Mode Select
M_SCD	EQU	\$1C	;	Serial Control Direction Mask
M_SCD0	EQU	2	;	Serial Control O Direction
M_SCD1	EQU	3	;	Serial Control 1 Direction
M_SCD2	EQU	4	;	Serial Control 2 Direction
M_SCKD	EQU	5	;	Clock Source Direction
M_CKP	EQU	6	;	Clock Polarity
M_SHFD	EQU	7	;	Shift Direction
M_FSL	EQU	\$3000		Frame Sync Length Mask (FSL0-FSL1)
M_FSL0	EQU	12	;	Frame Sync Length 0
M_FSL1	EQU	13	;	Frame Sync Length 1
M_FSR	EQU	14	;	Frame Sync Relative Timing
M_FSP	EQU	15	;	Frame Sync Polarity
	CCT Ctot	-ua Dogiator I	o:+ ⊡].	200
; M TE		tus Register I		
M_IF	EQU	\$3 0		Serial Input Flag Mask Serial Input Flag 0
	EQU	1 2		Serial Input Flag 1 Transmit Frame Sync Flag
M_TFS M RFS				Receive Frame Sync Flag
_	~			Transmitter Underrun Error FLaq
M_TUE				
M_ROE				Receiver Overrun Error Flag
M_TDE				Transmit Data Register Empty
M_RDF	EQU	7	,	Receive Data Register Full
;				
;	EQUATES	for Exception	n Proce	essing
;				
;	Register	r Addresses		
M_IPRC	EQU	\$FFFF	; Ir	nterrupt Priority Register Core
M_IPRP	EQU			nterrupt Priority Register Peripheral
;				
;	EQUATES	for Timers		
;				
		7.11	C	20
;		r Addresses of		
M_TCSR0				IMERO Control/Status Register
M_TLR0				IMERO Load Register
M_TCPR0				IMERO Compare Register
M_TCR0	EQU	\$FF8C	; T	IMERO Count Register





X I/O Equates

DSP56603 X I/O Equates

; Register Addresses of TIMER1	
	Control/Status Register
	Load Register
	Compare Register
	Count Register
; Register Addresses of TIMER2	
M_TCSR2 EQU \$FF87 ; TIMER2	Control/Status Register
M_TLR2 EQU \$FF86 ; TIMER2	Load Register
M_TCPR2 EQU \$FF85 ; TIMER2	Compare Register
M_TCR2 EQU \$FF84 ; TIMER2	Count Register
M_TPLR EQU \$FF83 ; TIMER E	Prescaler Load Register
M_TPCR EQU \$FF82 ; TIMER E	Prescaler Count Register
. Minney Control / Otator Davietas Di	
; Timer Control/Status Register Bi	
_ ~ ~ ~	r Enable
	r Overflow Interrupt Enable
	r Compare Interrupt Enable
	r Control Mask (TC0-TC3)
	rter Bit
= ~-	r Restart Mode
_ ~ ~ .	ction Bit
M_DI EQU 11 ; Data	-
	Output
_	r Overflow Flag
	r Compare Flag
M_PCE EQU 15 ; Preso	caler Clock Enable
; Timer Prescaler Register Bit Fla	ags
_	caler Source Mask
_ ~ ~	caler Source 0
_ ~	caler Source 1
_	
; Timer Control Bits	
	r Control 0
_ ~	
	r Control 1
M_TC2 EQU 6 ; Timer	r Control 1 r Control 2



DSP56603 X I/O Equates

```
EQUATES for Phase Lock Loop (PLL)
      Register Addresses of PLL
           $FFFD ; PLL Control Register 0
M_PCTLO EQU
                        ; PLL Control Register 1
M_PCTL1 EQU
             $FFFC
      PLL Control Register 0 (PCTL0)
           $FFF
                        ; Multiplication Factor Bits Mask (MF0-MF11)
M MF
       EOU
       EQU $F000
                         ; PreDivider Factor Bits Mask (PD3-PD0)
M PD
M_PD03 EQU
             $F000
                         ; PreDivider Factor Bits Mask (PD3-PD0)
      PLL Control Register 1 (PCTL1)
M_PD46 EQU $0E00 ; PreDivider Factor Bits Mask (PD6-PD4)
M DF
      EQU
             $7
                         ; Division Factor Bits Mask (DF0-DF2)
M_XTLR EQU
             3
                         ; XTAL Range Select Bit
M_XTLD EQU 4
                         ; XTAL Disable Bit
                         ; STOP Processing State Bit
M_PSTP EQU 5
           6
M_PEN EQU
                          ; PLL Enable Bit
M_PCOD EQU
                          ; PLL Clock Output Disable Bit
;-----
      EQUATES for BIU
;-----
      Register Addresses of BIU
           $FFFA ; Bus Control Register
M BCR EQU
M_IDR
      EQU
             $FFF9
                        ; ID Register
      Register Addresses of PATCH
M_PAO EQU $FFF8
                    ; Patch Address Register 0
M_PA1 EQU
                        ; Patch Address Register 1
             $FFF7
M_PA2 EQU $FFF6
                        ; Patch Address Register 2
M_PA3 EQU $FFF5
                        ; Patch Address Register 3
      Register Addresses of BPMR
                        ; BPMRG Register
M_BPMRG EQU
           $FFF4
M_BPMRL EQU
             $FFF3
                        ; BPMRL Register
M_BPMRH EQU
           $FFF2
                        ; BPMRH Register
      Bus Control Register
M_BMW EQU $1F
                        ; Memory Wait Control Mask (BMW0-BMW4)
```



X I/O Equates

DSP56603 X I/O Equates

;	EQUATES	for	SR and	OMR	
,					
;	Control	and	Status	Bits	in SR
M_C	EQU	0		;	Carry
M_V	EQU	1		;	Overflow
M_Z	EQU	2		;	Zero
M_N	EQU	3		;	Negative
M_U	EQU	4		;	Unnormalized
M_E	EQU	5		;	Extension
M_L	EQU	6		;	Limit
M_S	EQU	7		;	Scaling Bit
M_I0	EQU	8		;	Interrupt Mask Bit 0
M_I1	EQU	9		;	Interrupt Mask Bit 1
M_S0	EQU	10		;	Scaling Mode Bit 0
M_S1	EQU	11		;	Scaling Mode Bit 1
M_FV	EQU	12		;	DO-Forever Flag
M_SM	EQU	13		;	Arithmetic Saturation
M_RM	EQU	14		;	Rounding Mode
M_LF	EQU	15		;	DO-Loop Flag
;	Control	and	Status	Rits	in OMR
M MA	EQU	0	Бсасав	DICB	; Operating Mode A
M_MB	EQU	1			; Operating Mode B
M_MC	EQU	2			; Operating Mode C
M MD	EQU	3			; Operating Mode D
M EBD	EQU	4			; External Bus Disable Bit in OMR
M_PCD	EQU	5			; PC Relative Logic Disable
M SD	EQU	6			; Stop Delay
M_XYS	EQU	8			; Stack Extension Space Select
M_EUN	EQU	9			; Extended Stack Underflow Flag
M_EOV	EQU	10			; Extended Stack Overflow Flag
_ M_WRP	EQU	11			; Extended Stack Wrap Flag
M_SEN	EQU	12			; Stack Extended Enable
M_MS	EQU	14			; Memory Switch Mode
M_ATE	EQU	15			; Address Tracing Enable Bit in OMR.



DSP56603 Interrupt Equates

B.2 DSP56603 INTERRUPT EQUATES

Example B-2 provides interrupt equates for the DSP56603. If bootstrap code is developed for the DSP56603 (for external bootstrap loading), this listing should be enclosed in a file titled intequ.asm for inclusion in the bootstrap executable.

Example B-2 DSP56603 Interrupt Equates

```
EQUATES for DSP56603 Interrupts
     Reference: DSP56603 Specifications Revision 0.1
     1st update: June 20 1996 (creation,
                             copied from DSP56602 and modified) by Zvika R.
     Last update:
page
       132,55,0,0,0
       opt
              mex
; DSP56603
              EOU
                      1
intequ
      ident 1,0
        if
               @DEF(I_VEC)
        ; leave user definition as is.
        else
I_VEC
        equ
               $0
        endif
; Non-Maskable interrupts
I_VEC+$02 ; Stack Error
I_STACK EQU
I_ILL
       EQU
              I_VEC+$04 ; Illegal Instruction
       EQU
            I_VEC+$06 ; Debug Request
I_DBG
I_TRAP EQU
              I_VEC+$08 ; Trap
              I_VEC+$0A ; Non Maskable Interrupt
I_NMI
       EQU
```





X I/O Equates

DSP56603 Interrupt Equates

Example B-2 DSP56603 Interrupt Equates (Continued)

•		
; Interrupt R	_	
	I_VEC+\$10	
I_INQD EQU	I_VEC+\$12 I_VEC+\$14	: IROC
	I_VEC+\$14	
;; Timer Inter		
	-	
I_TIMOC EQU	I_VEC+\$24	; TIMER 0 Compare
I_TIMOOF EQU	I_VEC+\$26	; TIMER 0 Overflow
		; TIMER 1 Compare
I_TIM1OF EQU	I_VEC+\$2A	; TIMER 1 Overflow
I_TIM2C EQU	I_VEC+\$2C	; TIMER 2 Compare
I_TIM2OF EQU		; TIMER 2 Overflow
:		
, ; SSI Interru		
	-	
		; SSIO Receive Data
		; SSIO Receive Data with Exception Status
_ ~ I_SIORLS EQU		; SSIO Receive Last Slot
_ ~ I_SIOTD EQU		; SSIO Transmit Data
I_SIOTDE EQU		; SSIO Transmit Data with Exception Status
I_SIOTLS EQU		; SSIO Transmit Last Slot
I_SI1RD EQU		; SSI1 Receive Data
_ ~ I_SI1RDE EQU		; SSI1 Receive Data with Exception Status
I_SI1RLS EQU		; SSI1 Receive Last Slot
I_SI1TD EQU		; SSI1 Transmit Data
I_SI1TDE EQU		; SSI1 Transmit Data with Exception Status
I_SI1TLS EQU	I_VEC+\$4A	; SSI1 Transmit Last Slot
;		
, ; HOST Interr		
;		
I_HRDF EQU	I_VEC+\$60	; Host Receive Data Full
I_HTDE EQU	I_VEC+\$62	; Host Transmit Data Empty
I_HC EQU	I_VEC+\$64	; Default Host Command
;		
; INTERRUPT E	NDING ADDRESS	
;		; Last address of interrupt vector space
	T_4TC, ALL	. Last address of interrupt vector space

dsp




DSP56603 Interrupt Equates





APPENDIX C PROGRAMMER'S REFERENCE





Programmer's Reterence

C.1	INTRODUCTION	C- 3
C.2	INSTRUCTION SET SUMMARY	C -3
C.3	INTERRUPT, VECTOR, AND ADDRESS TABLES	. C-14
C.4	PROGRAMMER'S SHEETS	C-23



C.1 INTRODUCTION

The following pages provide a set of reference tables and programming sheets that are intended to simplify programming the DSP56603. The programming sheets provide room to write in the value of each bit and the hexadecimal value for each register. The programmer can photocopy these sheets.

C.2 INSTRUCTION SET SUMMARY

The following tables provide a brief summary of the instruction set for the DSP56603. Table C-1, Table C-2, and Table C-3 provide a key to the abbreviations in Table C-4, the instruction set summary table. For complete instruction set details, see Appendix A of the DSP56600 Family Manual (DSP56600FM/AD).

Table C-1 Program Word and Timing Symbols

Column	Description and Symbols				
P	Parallel Move				
	P	Parallel Move			
	N	No Parallel Move			
	_	Not Applicable			
Т	Instruction	tion Clock Cycle Counts (Add one cycle for each symbol in column)			
	U	Pre-Update			
	A	Long Absolute			
	I	Long Immediate			

Table C-2 Condition Code Register (CCR) Symbols

Symbol	Description
S	Scaling bit indicating data growth is detected
L	Limit bit indicating arithmetic overflow and/or data limiting
E	Extension bit indicating if the integer portion is in use
U	Unnormalized bit indicating if the result is unnormalized
N	Negative bit indicating if Bit 35 (or 31) of the result is set



 Table C-2
 Condition Code Register (CCR) Symbols (Continued)

Symbol	Description		
Z	Zero bit indicating if the result equals 0		
V	Overflow bit indicating if arithmetic overflow has occurred in the result		
С	Carry bit indicating if a carry or borrow occurred in the result		

 Table C-3
 Condition Code Register Notation

Notation	Description
*	Bit is set or cleared according to the standard definition by the result of the operation
_	Bit is not affected by the operation
0	Bit is always cleared by the operation
1	Bit is always set by the operation
U	Undefined
?	Bit is set or cleared according to the special computation definition by the result of the operation

Table C-4 Instruction Set Summary

Mnemonic	onic Syntax P T		T				C	CR			
Minemonic	Syntax	P	1	S	L	E	U	N	Z	V	C
ABS	ABS D	P		*	*	*	*	*	*	*	_
ADC	ADC S,D	P		*	*	*	*	*	*	*	*
ADD	ADD S,D	P		*	*	*	*	*	*	*	*
	ADD #iiiiii,D	_	2	*	*	*	*	*	*	*	*
	ADD #iii,D	_	1	*	*	*	*	*	*	*	*
ADDL	ADDL S,D	P		*	*	*	*	*	*	?	*
ADDR	ADDR S,D	P		*	*	*	*	*	*	*	*
AND	AND S,D	P		*	_	_	_	?	?	0	_
	AND #iiiiii,D	_	2	*	_	_	_	?	?	0	_



 Table C-4
 Instruction Set Summary (Continued)

Mnemonic	Symtox	P T		CCR									
Milemonic	Syntax	r	1	S	L	E	U	N	Z	V	С		
AND	AND #iii,D	_	1	*	_		_	?	?	0			
ANDI	ANDI EE	_	3	?	?	?	?	?	?	?	?		
ASL	ASL S,D	P		*	*	*	*	*	*	?	?		
	ASL #ii,S,D	_	1	*	*	*	*	*	*	?	?		
	ASL sss,S,D	_	1	*	*	*	*	*	*	?	?		
ASR	ASR S,D	P		*	*	*	*	*	*	0	?		
	ASR sss,S,D	_	1	*	*	*	*	*	*	0	?		
	ASR #ii,S,D	_	1	*	*	*	*	*	*	0	?		
Всс	Bcc (PC + Rn)	_	4	_	_	_	_	_	_	_	_		
	Bcc (PC + aa)	_	4	_	_		_	_	_	_	_		
BCHG	BCHG #bbbb , S: <aa></aa>	_	2	?	?	?	?	?	?	?	?		
	BCHG #bbbb , S: <ea></ea>	_	2 + U + A	?	?	?	?	?	?	?	?		
	BCHG #bbbb , S: <pp></pp>	_	2	?	?	?	?	?	?	?	?		
	BCHG #bbbb , S: <qq></qq>	_	2	?	?	?	?	?	?	?	?		
	BCHG #bbbb, DDDDDD	_	2	?	?	?	?	?	?	?	?		
BCLR	BCLR #bbbb , S: <pp></pp>	_	2	?	?	?	?	?	?	?	?		
	BCLR #bbbb , S: <ea></ea>	_	2 + U + A	?	?	?	?	?	?	?	?		
	BCLR #bbbb , S: <aa></aa>	_	2	?	?	?	?	?	?	?	?		
	BCLR #bbbb , S: <qq></qq>	_	2	?	?	?	?	?	?	?	?		
	BCLR #bbbb , DDDDDD	_	2	?	?	?	?	?	?	?	?		
BRA	BRA (PC + Rn)	_	4	_	_	_	_	_	_	_	_		
	BRA (PC + aa)	_	4	_	_		_	_	_	_	_		
BRKcc	BRKcc	_	5	_	_	_	_	_	_	_	_		

Go to: www.freescale.com



Table C-4 Instruction Set Summary (Continued)

Manamania	Comton	P T					C	CR			
Mnemonic	Syntax	P	1	S	L	E	U	N	Z	V	С
BScc	BScc (PC + Rn)	_	4	_	_	_	_	_	_	_	_
	BScc (PC + aa)	_	4	_	_	_	_	_	_	_	_
BSET	BSET #bbbb,S: <pp></pp>	_	2	?	?	?	?	?	?	?	?
	BSET #bbbb, S: <ea></ea>	_	2 + U + A	?	?	?	?	?	?	?	?
	BSET #bbbb, S: <aa></aa>	_	2	?	?	?	?	?	?	?	?
	BSET #bbbb , DDDDDD		2	?	?	?	?	?	?	?	?
	BSET #bbbb , S: <qq></qq>	_	2	?	?	?	?	?	?	?	?
BSR	BSR (PC + Rn)	_	4	_	_	_	_	_	_	_	_
	BSR (PC + aa)	_	4	_	_	_	_	_	_	_	_
BTST	BTST #bbbb,S: <pp></pp>	_	2	*	*	_	_	_	_	_	?
	BTST #bbb ,S: <ea></ea>		2 + U + A	*	*	_	_	_	_	_	?
	BTST #bbbb,S: <aa></aa>	_	2	*	*	_	_	_	_	_	?
	BTST #bbbb , DDDDDD	_	2	*	*	_	_	_	_	_	?
	BTST #bbbb,S: <qq></qq>	_	2	*	*	_	_	_	_	_	?
CLB	CLB S,D	_	1	_	_	_	_	?	?	0	
CLR	CLR D	P		*	*	0	1	0	1	0	_
CMP	CMP S1,S2	P		*	*	*	*	*	*	*	*
	CMP #iiiiii,D	_	2	*	*	*	*	*	*	*	*
	CMP #iii,D	_	1	*	*	*	*	*	*	*	*
CMPM	CMPM S1,S2	P		*	*	*	*	*	*	*	*
CMPU	CMPU ggg,D	_	1	_	_	_	_	*	?	0	*
DEBUG	DEBUG	_	1	_	_	_	_	_	_	_	_
DEBUGcc	DEBUGcc		5	_	_	_	_	_	_	_	_





Management	C4	P	Т	CCR											
Mnemonic	Syntax	P	1	S	L	E	U	N	Z	V	C				
DEC	DEC	1-	1	_	*	*	*	*	*	*	*				
DIV	DIV		1	_	?	_	_	_	_	?	?				
DMAC	DMAC S1,S2,D (ss,su,uu)	N	1	_	*	*	*	*	*	*	_				
DO	DO #xxx,aaaa		5	?	?	_	_	_	_	_	_				
	DO DDDDDD,aaaa		5	?	?	_	_	_	_	_	_				
	DO S: <ea>,aaaa</ea>		5 + U	?	?	_	_	_	_	_	_				
	DO S: <aa>,aaaa</aa>		5	?	?	_	_	_	_	_	_				
DO FOREVER	DO FOREVER, (aaaa)	_	4	-			_	_	_	_					
ENDDO	ENDDO		1	_	_	_	_	_	_	_	_				
EOR	EOR S,D	P		*	*	_	_	?	?	0	_				
	EOR #iiiiii,D		2	*	*	_	_	?	?	0	_				
	EOR #iii,D		1	*	*	_	_	?	?	0	_				
EXTRACT	EXTRACT SSS,s,D		1	_	_	*	*	*	*	0	0				
	EXTRACT #iiii,s,D		2	_	_	*	*	*	*	0	0				
EXTRACTU	EXTRACTU SSS,s,D		1	_	_	*	*	*	*	0	0				
	EXTRACTU #iiii,s,D		2	_	_	*	*	*	*	0	0				
IFcc	IFcc		1	_	_	_	_	_	_	_	_				
IFcc(.U)	IFcc(.U)			?	?	?	?	?	?	?	?				
ILLEGAL	ILLEGAL		5	_	_	_	_	_	_	_	_				
INC	INC D		1	_	*	*	*	*	*	*	*				
INSERT	INSERT SSS,qqq,D		1	_	_	*	*	*	*	0	0				
	INSERT #iiii,qqq,D		2	_	_	*	*	*	*	0	0				

Go to: www.freescale.com

C-8



Freescale Semiconductor, Inc.

Table C-4 Instruction Set Summary (Continued)

Marania	C4	P	Т				C	CR			
Mnemonic	Syntax	P	1	S	L	E	U	N	Z	V	С
Jcc	Jcc aa	_	4		_	_	_	_	_	_	_
	Jcc ea	_	4	_	_	_	_	_	_	_	_
JCLR	JCLR #bbbb,S: <ea>,aaaa</ea>	_	4 + U	*	*	_	_	_	_	_	_
	JCLR #bbbb,S: <pp>,aaaa</pp>	_	4	*	*	_	_	_	_	_	
	JCLR #bbbb ,S: <aa>,aaaa</aa>	_	4	*	*	_	_	_	_	_	_
	JCLR #bbbb,DDDDDD,aaaa	_	4	*	*	_	_	_	_	_	
	JCLR #bbbb, S: <qq>,aaaa</qq>	_	4	*	*	_	_	_	_	_	_
JMP	JMP aa	_	3	_		_	_	_	_	_	_
	JMP ea	_	3 + U + A	_		_	_	_	_	_	_
JScc	JScc aa	_	4	_	_	_	_	_	_	_	_
	JScc ea	_	4	_		_	_	_	_	_	_
JSCLR	JSCLR #bbbb,S: <pp>,aaaa</pp>	_	4	*	*	_	_	_	_	_	_
	JSCLR #bbbb , S: <ea>,aaaa</ea>	_	4 + U	*	*	_	_	_	_	_	_
	JSCLR #bbbb , S: <aa>,aaaa</aa>	_	4	*	*	_	_	_	_	_	_
	JSCLR #bbbb, DDDDDD,aaaa	_	4	*	*	_	_	_	_	_	
	JSCLR #bbbb , S: <qq>,aaaa</qq>	_	4	*	*	_	_	_	_	_	_
JSET	JSET #bbbb , S: <pp>,aaaa</pp>	_	4	*	*	_	_	_	_	_	
	JSET #bbbb , S: <ea>,aaaa</ea>	_	4 + U	*	*	_	_	_	_	_	_
	JSET #bbbb , S: <aa>,aaaa</aa>	_	4	*	*	_	_	_	_	_	_
	JSET #bbbb, DDDDDD,aaaa	-	4	*	*	_	_	_	_	_	_
	JSET #bbbb , S: <qq>,aaaa</qq>	-	4	*	*	_	_	_	_	_	
JSR	JSR aa	-	3	_	_	_	_	_	_	_	_
	JSR ea	-	3 + U + A	_	_	_	_	_	_	_	_



 Table C-4
 Instruction Set Summary (Continued)

Mnemonic	C4	P					C	CR			
Minemonic	Syntax	r	Т	S	L	E	U	N	Z	V	C
JSSET	JSSET #bbbb,S: <pp>,aaaa</pp>	_	4	*	*	_	_	_	_	_	
	JSSET #bbbb,S: <ea>,aaaa</ea>	_	4 + U	*	*	_	_	_	_	_	_
	JSSET #bbbb,S: <aa>,aaaa</aa>	_	4	*	*	_	_	_	_	_	_
	JSSET #bbbb, DDDDDD,aaaa	_	4	*	*	_	_	_	_	_	_
	JSSET #bbbb,S: <qq>,aaaa</qq>	_	4	*	*	_	_	_	_	_	_
LRA	LRA (PC + Rn) → 0DDDDD	_	3	_	_	_	_	_	_	_	_
	LRA (PC + aaaa) → 0DDDDD	_	3	-	_	_	_	_	_	_	_
LSL	LSL D	P		*	*	_	_	?	?	0	?
	LSL sss,D	_	1	*	*	_	_	?	?	0	?
	LSL #ii,D	_	1	*	*	_	_	?	?	0	?
LSR	LSR D	P		*	*	_	_	?	?	0	?
	LSR #ii,D	_	1	*	*	_	_	?	?	0	?
	LSR sss,D	_	1	*	*	_	_	?	?	0	?
LUA, LEA	LUA ea \rightarrow 0DDDDD	_	3	-	_	_	_	_	_	_	_
	LUA (Rn + aa) → 01DDDD	_	3	_	_	_	_	_	_	_	_
MAC	MAC ± 2**s,QQ,d	_	1	*	*	*	*	*	*	*	_
	MAC S1,S2,D	_	1	*	*	*	*	*	*	*	_
MAC (su,uu)	MAC S1,S2,D	N	1	-	*	*	*	*	*	*	
MACI	MACI ± #iiiiii,QQ,D	_	2	-	*	*	*	*	*	*	_
MACR	MACR ±2**s,QQ,d	_	1	*	*	*	*	*	*	*	_
MACRI	MACRI ± #iiiiii,QQ,D	-	2	-	*	*	*	*	*	*	_
MAX	MAX A,B	P	1	*	*	_	_	-	_	_	?



Table C-4 Instruction Set Summary (Continued)

Manamania	Syntax P T										
Mnemonic	Syntax	P	1	S	L	E	U	N	Z	V	С
MAXM	MAXM A,B	P	1	*	*	_	_	_	_	_	?
MERGE	MERGE SSS,D	_	1	_	_	_	_	?	?	0	_
MOVE	No Parallel Data Move (DALU)	N	1		_		_	_	_	_	_
	MOVE #xx→DDDDD	-	1	_	_		_	_	_	_	_
	MOVE ddddd→DDDDD	-	1	*	*	_	_	_	_	_	_
	U move	1-	1	_	_	_	_	_	_	_	_
	MOVE S: <ea>,DDDDD</ea>	-	1+U+A+I	*	*		_	_	_	_	_
	MOVE S: <aa>,DDDDD</aa>	_	1	*	*	_	_	_	_	_	_
	MOVE S: <rn +="" aa="">,DDDD</rn>	_	2	*	*	_	_	_	_	_	_
	MOVE S: <rn +="" aaaa="">,DDDDDD</rn>	-	3	*	*	_	_	_	_	_	_
	MOVE d →X Y: <ea>,YY</ea>	_	1+U+A+I	*	*	_	_	_	_	_	_
	MOVE X: <ea>,XX & d→Y</ea>	_	1+U+A+I	*	*	_	_	_	_	_	_
	$\overrightarrow{MOVE A \rightarrow X: X0 A}$	1-	1 + U	*	*	_	_	_	_	_	_
	$MOVE B \rightarrow X: \langle ea \rangle X0 B$	1-	1 + U	*	*	_	_	_	_	_	_
	MOVE Y0 → A A Y: <ea></ea>	<u> </u>	1 + U	*	*	_	_	_	_	_	_
	MOVE Y0 → B B Y: <ea></ea>	_	1 + U	*	*	_	_	_	-	_	_
	MOVE L: <ea>,LLL</ea>	1-	1 + U + A	*	*	_	_	_	_	_	_
	MOVE L: <aa>,LLL</aa>	_	1	*	*		_		_	_	_
	MOVE X: <ea>,XX & Y:<ea>,YY</ea></ea>	-	1	*	*			_	_	_	_
MOVEC	MOVEC #xx → 1DDDDD	-	1	?	?	?	?	?	?	?	?
	MOVEC S: <ea>,1DDDDD</ea>	-	1+U+A+I	?	?	?	?	?	?	?	?
	MOVEC S: <aa>,1DDDDD</aa>	1-	1	?	?	?	?	?	?	?	?



Table C-4 Instruction Set Summary (Continued)

Mnemonic	Crimtor	P	Т				C	CR			
Willemonic	Syntax	r	1	S	L	E	U	N	Z	V	С
MOVEC	MOVEC DDDDDD, 1ddddd	_	1	?	?	?	?	?	?	?	?
MOVEM	MOVEM P: <ea>,DDDDDD</ea>	-	6 + U + A	?	?	?	?	?	?	?	?
	MOVEM P: <aa>,DDDDDD</aa>	-	6	?	?	?	?	?	?	?	?
MOVEP	MOVEP S: <pp>,s:<ea></ea></pp>	-	2 + U + A	?	?	?	?	?	?	?	?
	MOVEP S: <pp>,P:<ea></ea></pp>	_	6 + U + A	?	?	?	?	?	?	?	?
	MOVEP S: <pp>,DDDDDD</pp>	-	1	?	?	?	?	?	?	?	?
	MOVEP X: <qq>,s:<ea></ea></qq>	-	2 + U + A	?	?	?	?	?	?	?	?
	MOVEP Y: <qq>,s:<ea></ea></qq>	_	2 + U + A	?	?	?	?	?	?	?	?
	MOVEP X: <qq>,DDDDDD</qq>	_	1	?	?	?	?	?	?	?	?
	MOVEP Y: <qq>,DDDDDD</qq>	-	1	?	?	?	?	?	?	?	?
	MOVEP S: <qq>,P:<ea></ea></qq>	_	6 + U + A	?	?	?	?	?	?	?	?
MPY	MPY ± 2**s,QQ,d	-	1	*	*	*	*	*	*	*	_
MPY(su,uu)	MPY S1,S2,D (su,uu)	-	1	_	*	*	*	*	*	*	_
MPYI	MPYI ± #iiiiii,QQ,D	-	2	_	*	*	*	*	*	*	_
MPYR	MPYR ± 2**s,QQ,d	-	1	*	*	*	*	*	*	*	_
MPYRI	MPYRI ± #iiiiii,QQ,D	-	2	_	*	*	*	*	*	*	_
NEG	NEG D	P		*	*	*	*	*	*	*	_
NOP	NOP	_	1	_	_	_	_	_	_	_	_
NORMF	NORMF SSS,D	-	1	_	*	*	*	*	*	?	_
NOT	NOT D	P		*	*	_	_	?	?	0	_
OR	OR SD	P		*	*	_	_	?	?	0	_
	OR #iiiiii,D	-	2	*	*	_	_	?	?	0	_
	OR #iii,D	_	1	*	*	_	_	?	?	0	_



Table C-4 Instruction Set Summary (Continued)

	~ .	Syntax P T					C	CR			
Mnemonic	Syntax	P	T	S	L	E	U	N	Z	V	C
ORI	ORI EE	_	3	?	?	?	?	?	?	?	?
REP	REP #xxx	_	5	*	*	_	_	_	_	_	_
	REP DDDDDD	_	5	*	*	_	_	_	_	_	_
	REP S: <ea></ea>	_	5 + U	*	*	_	_	_	_	_	_
	REP S: <aa></aa>	_	5	*	*	_	_	_	_	_	_
RESET	RESET	_	7	_	_	_	_	_	_	_	_
RND	RND D	P		*	*	*	*	*	*	*	_
ROL	ROL D	P		*	*	_	_	?	?	0	?
ROR	ROR D	P		*	*	_	_	?	?	0	?
RTI	RTI	_	3	?	?	?	?	?	?	?	?
RTS	RTS	-	3	_	_	_	_	_	_	_	_
SBC	SBC S,D	P		*	*	*	*	*	*	*	*
STOP	STOP	_	10	_	_	_	_	_	_	_	_
SUB	SUB S,D	P		*	*	*	*	*	*	*	*
	SUB #iiiiii,D	_	2	*	*	*	*	*	*	*	*
	SUB #iii,D	_	1	*	*	*	*	*	*	*	*
SUBL	SUBL S,D	P		*	*	*	*	*	*	?	*
SUBR	SUBR S,D	P		*	*	*	*	*	*	*	*
Tcc	$\operatorname{Tcc} JJJ \to D \operatorname{ttt} \operatorname{TTT}$	_	1	_	_	_	_	_	_	_	_
	$TccJJJ \to D$	_	1	_	_	_	_	_	_	_	_
	$Tcc\;ttt\toTTT$	_	1	_	_	_	_	_	_	_	_
TFR	TFR S,D	P		*	*	_	_	_	_	_	_
TRAP	TRAP	_	9	_	_	_	_	_	_	_	_

C-12





 Table C-4
 Instruction Set Summary (Continued)

Mnemonic	Syntax	P	Т				C	CR			
Milemonic	Syntax	-	1	S	L	E	U	N	Z	V	C
TRAPcc	TRAPcc	_	9	_	_	_	_	_	_	_	
TST	TST S	P		*	*	*	*	*	*	0	_
VSL	VSL S,i,L:ea	_	1 + U + A	_	_	_	_		_	_	_
WAIT	WAIT	_	10	_	_		_			_	_



C.3 INTERRUPT, VECTOR, AND ADDRESS TABLES

Table C-5 Interrupt Sources

Interrupt Starting Address	IPL	Interrupt Source
VBA:\$00	3	Hardware RESET
VBA:\$02	3	Stack Error
VBA:\$04	3	Illegal Instruction
VBA:\$06	3	Debug Request Interrupt
VBA:\$08	3	Trap
VBA:\$0A	3	Reserved
VBA:\$0C	3	Reserved
VBA:\$0E	3	Reserved
VBA:\$10	0-2	ĪRQĀ
VBA:\$12	0-2	ĪRQB
VBA:\$14	0-2	ĪRQC
VBA:\$16	0-2	ĪRQD
VBA:\$18	0-2	Reserved
VBA:\$1A	0-2	Reserved
VBA:\$1C	0-2	Reserved
VBA:\$1E	0-2	Reserved
VBA:\$20	0-2	Reserved
VBA:\$22	0-2	Reserved
VBA:\$24	0-2	Timer 0 Compare
VBA:\$26	0-2	Timer 0 Overflow
VBA:\$28	0-2	Timer 1 Compare
VBA:\$2A	0-2	Timer 1 Overflow
VBA:\$2C	0-2	Timer 2 Compare



 Table C-5
 Interrupt Sources (Continued)

Interrupt Starting Address	IPL	Interrupt Source
VBA:\$2E	0–2	Timer 2 Overflow
VBA:\$30	0-2	SSI0 Receive Data
VBA:\$32	0-2	SSI0 Receive Data With Exception Status
VBA:\$34	0-2	SSI0 Receive last slot
VBA:\$36	0-2	SSI0 Transmit Data
VBA:\$38	0-2	SSI0 Transmit Data with Exception Status
VBA:\$3A	0-2	SSI0 Transmit Last Slot
VBA:\$3C	0-2	Reserved
VBA:\$3E	0-2	Reserved
VBA:\$40	0-2	SSI1 Receive Data
VBA:\$42	0-2	SSI1 Receive Data With Exception Status
VBA:\$44	0-2	SSI1 Receive Last Slot
VBA:\$46	0-2	SSI1 Transmit Data
VBA:\$48	0-2	SSI1 Transmit Data with Exception Status
VBA:\$4A	0-2	SSI0 Transmit Last Slot
VBA:\$4C	0-2	Reserved
VBA:\$4E	0-2	Reserved
VBA:\$60	0-2	Host Receive Data Full
VBA:\$62	0-2	Host Transmit Data Empty
VBA:\$64	0-2	Default Host Command
VBA:\$66	0-2	Reserved
VBA:\$FE		Reserved



Table C-6 Interrupt Source Priorities within an IPL

Priority	Interrupt Source
Level 3 (Nonmaskable)	
Highest	Hardware RESET
	Stack Error
	Illegal Instruction
	Debug Request Interrupt
Lowest	Trap
Levels 0, 1, 2 (Maskable)	
Highest	IRQA (External Interrupt)
	IRQB (External Interrupt)
	IRQC (External Interrupt)
	IRQD (External Interrupt)
	Host Command Interrupt
	Host Transmit Data Full
	Host Receive Data Empty
	SSI0 RX Data with Exception Interrupt
	SSI0 RX Data Interrupt
	SSI0 Receive Last Slot Interrupt
	SSI0 TX Data with Exception Interrupt
	SSI0 Transmit Last Slot Interrupt
	SSI0 TX Data Interrupt
	SSI1 RX Data with Exception Interrupt
	SSI1 RX Data Interrupt
	SSI1 Receive Last Slot Interrupt
	SSI1 TX Data with Exception Interrupt



 Table C-6
 Interrupt Source Priorities within an IPL (Continued)

Priority	Interrupt Source						
	SSI1 Transmit Last Slot Interrupt						
	SSI1 TX Data Interrupt						
	Timer 0 Overflow Interrupt						
	Timer 0 Compare Interrupt						
	Timer 1 Overflow Interrupt						
	Timer 1 Compare Interrupt						
	Timer 2 Overflow Interrupt						
Lowest	Timer 2 Compare Interrupt						

Table C-7 Internal I/O Memory Map

Peripheral	Address	Register Name	Reset Value	
PIC	\$FFFF	IPR-C—Interrupt Priority Register—Core	\$0000	
	\$FFFE	IPR-P—Interrupt Priority Register—Peripheral	\$0000	
PLL	\$FFFD	PCTL0—PLL Control Register	\$0000	
	\$FFFC	PCTL1—PLL Control Register	\$0000	
OnCE	\$FFFB	OGDB—OnCE GDB Register	\$0000	
BIU	\$FFFA	BCR—Bus Control Register	\$001F	
	\$FFF9	IDR—ID Register	\$0603	
Patch	\$FFF8	PAR0—Patch 0 Register	\$FEFD	
	\$FFF7	PAR1—Patch 1 Register	\$F7FF	
	\$FFF6	PAR2—Patch 2 Register	\$7FEE	
	\$FFF5	PAR3—Patch 3 Register	\$BBF3	
BPMR	\$FFF4	BPMRG—Bus Switch Program Memory Register (24 bits)	\$2600	



Table C-7 Internal I/O Memory Map (Continued)

Peripheral	Address	Register Name	Reset Value
BPMR	\$FFF3	BPMRL—Bus Switch Program Memory Register Low(16 bits)	\$2600
	\$FFF2	BPMRH—Bus Switch Program Memory Register High (16 bits)	\$0000
Reserved	\$FFF1	Reserved	uninitialized
	\$FFF0	Reserved	uninitialized
	\$FFEF	Reserved	uninitialized
	\$FFEE	Reserved	uninitialized
	\$FFED	Reserved	uninitialized
	\$FFEC	Reserved	uninitialized
	\$FFEB	Reserved	uninitialized
	\$FFEA	Reserved	uninitialized
	\$FFE9	Reserved	uninitialized
	\$FFE8	Reserved	uninitialized
	\$FFE7	Reserved	uninitialized
	\$FFE6	Reserved	uninitialized
	\$FFE5	Reserved	uninitialized
	\$FFE4	Reserved	uninitialized
	\$FFE3	Reserved	uninitialized
	\$FFE2	Reserved	uninitialized
	\$FFE1	Reserved	uninitialized
	\$FFE0	Reserved	uninitialized
	\$FFDF	Reserved	uninitialized
	\$FFDE	Reserved	uninitialized
	\$FFDD	Reserved	uninitialized





Peripheral	Address	Register Name	Reset Value
Reserved	\$FFDC	Reserved	uninitialized
	\$FFDB	Reserved	uninitialized
	\$FFDA	Reserved	uninitialized
	\$FFD9	Reserved	uninitialized
	\$FFD8	Reserved	uninitialized
	\$FFD7	Reserved	uninitialized
	\$FFD6	Reserved	uninitialized
	\$FFD5	Reserved	uninitialized
	\$FFD4	Reserved	uninitialized
	\$FFD3	Reserved	uninitialized
	\$FFD2	Reserved	uninitialized
	\$FFD1	Reserved	uninitialized
	\$FFD0	Reserved	uninitialized
	\$FFCF	Reserved	\$0000
	\$FFCE	Reserved	\$0000
	\$FFCD	Reserved	\$0000
	\$FFCC	Reserved	\$0000
	\$FFCB	Reserved	\$0000
	\$FFCA	Reserved	\$0000
HI08	\$FFC9	HDR—HI08 Data Register	\$3FE2
	\$FFC8	HDDR—HI08 Data Direction Register	\$0000
	\$FFC7	HTX—HI08 Transmit Data Register	\$0000
	\$FFC6	HRX—HI08 Receive Data Register	\$0000
	\$FFC5	HBAR —HI08 Base Address Register	\$0080



Table C-7 Internal I/O Memory Map (Continued)

Peripheral	Address	Register Name	Reset Value
HI08	\$FFC4	HPCR—HI08 Port Control Register	\$0000
	\$FFC3	HSR—HI08 Status Register	\$0002
	\$FFC2	HCR—HI08 Control Register	\$0000
Reserved	\$FFC1	Reserved	\$0000
	\$FFC0	Reserved	\$0000
SSI0	\$FFBF	PCRC—SSI 0 Port Control Register	\$0000
	\$FFBE	PRRC—SSI 0 GPIO Direction Register	\$0000
	\$FFBD	PDRC—SSI 0 GPIO Data Register	\$0000
	\$FFBC	TX0—SSI 0 Transmit Data Register	\$0000
	\$FFBB	TSR0—SSI 0 Time Slot Register	\$0000
	\$FFBA	RX0—SSI 0 Receive Data Register	\$FFFF
	\$FFB9	SSISR0—SSI 0 Status Register	\$0040
	\$FFB8	CRC0—SSI 0 Control Register C	\$0000
	\$FFB7	CRB0—SSI 0 Control Register B	\$0000
	\$FFB6	CRA0—SSI 0 Control Register A	\$0000
Reserved	\$FFB5	Reserved	\$0000
	\$FFB4	Reserved	\$0000
	\$FFB3	Reserved	\$0000
	\$FFB2	Reserved	\$0000
	\$FFB1	Reserved	\$0000
	\$FFB0	Reserved	\$0000
SSI1	\$FFAF	PCRD—SSI 1 Port Control Register	\$0000
	\$FFAE	PRRD—SSI 1 GPIO Direction Register	\$0000
	\$FFAD	PDRD—SSI 1 GPIO Data Register	\$0000



Table C-7 Internal I/O Memory Map (Continued)

Peripheral	Address	Register Name	Reset Value
SSI1	\$FFAC	TX1—SSI 1 Transmit Data Register	\$0000
	\$FFAB	TSR1—SSI 1 Time Slot Register	\$0000
	\$FFAA	RX1—SSI 1 Receive Data Register	\$FFFF
	\$FFA9	SSISR1—SSI 1 Status Register	\$0040
	\$FFA8	CRC1—SSI 1 Control Register C	\$0000
	\$FFA7	CRB1—SSI 1 Control Register B	\$0000
	\$FFA6	CRA1—SSI 1 Control Register A	\$0000
Reserved	\$FFA5	Reserved	\$0000
	\$FFA4	Reserved	\$0000
	\$FFA3 Reserved		\$0000
	\$FFA2	Reserved	\$0000
\$FFA1		Reserved	\$0000
	\$FFA0	Reserved	\$0000
GPIO	\$FF9F	PCRE—GPIO Control Register	\$0000
	\$FF9E	PRRE—GPIO Direction Register	\$0800
	\$FF9D	PDRE—GPIO Data Register	\$0007
Triple	\$FF8F	TCSR0—Timer 0 Control/Status Register	\$0000
Timer	\$FF8E	TLR0—Timer 0 Load Register	\$0000
	\$FF8D	TCPR0—Timer 0 Compare Register	\$0000
	\$FF8C	TCR0—Timer 0 Count Register	\$0000
	\$FF8B	TCSR1—Timer 1 Control/Status Register	\$0800
	\$FF8A	TLR1—Timer 1 Load Register	\$0000
	\$FF89	TCPR1—Timer 1 Compare Register	\$0000
	\$FF88	TCR1—Timer 1 Count Register	\$0000



Table C-7 Internal I/O Memory Map (Continued)

Peripheral	Address	Register Name	Reset Value
Triple	\$FF87	TCSR2—Timer 2 Control/Status Register	\$0800
Timer	\$FF86	TLR2—Timer 2 Load Register	\$0000
	\$FF85	TCPR2—Timer 2 Compare Register	\$0000
	\$FF84	TCR2—Timer 2 Count Register	\$0000
	\$FF83	TPLR—Timer Prescaler Load Register	\$0000
	\$FF82	TPCR—Timer Prescaler Count Register	\$0000
Reserved	\$FF81	Reserved	\$0000
	\$FF80	Reserved	\$0000



C.4 PROGRAMMER'S SHEETS

The following pages provide programmer's sheets that are intended to simplify programming the various registers in the DSP56603. The programmer's sheets provide room to write in the value of each bit and the hexadecimal value for each register. The programmer can photocopy these sheets.

The programmer's sheets are provided in the same order as the sections in this document. **Table C-8** lists the sets of programmer's sheets, the registers described in the sheets, and the pages in this appendix where the sheets are located.

Table C-8 List of Programmer's Sheets

Type of Register	Register	Page		
CPU	JTAG Instruction Register	C-26		
CPU	JTAG Bypass Register	C-26		
CPU	JTAG ID Register	C-26		
CPU	OMR—Operating Mode Register	C-27		
CPU	SR—Status Register	C-28		
CPU	IPR-C—Interrupt Priority Register (Core)	C-29		
CPU	IPR-P—Interrupt Priority Register (Peripheral)	C-30		
CPU	BCR— Bus Control Register	C-31		
CPU	IDR—Identification Register	C-31		
CPU	PATn—Patch Registers	C-32		
CPU	BPMRG—Bus Switch Program Memory Register	C-33		
CPU	BPMRL—Bus Switch Program Memory Register Low	C-33		
CPU	BPMRH—Bus Switch Program Memory Register High	C-33		
PLL	PCTL0—PLL Control Register 0			
PLL	PCTL1—PLL Control Register 1			
HI08	HSR—HI08 Status Register	C-35		
HI08	HCR—HI08 Control Register	C-35		



 Table C-8
 List of Programmer's Sheets (Continued) (Continued)

Type of Register	Register	Page		
HI08	HPCR—HI08 Port Control Register	C-36		
HI08	HDDR—HI08 Data Direction Register	C-37		
HI08	HDR—HI08 Data Register	C-37		
HI08	HRX—HI08 Receive Data Register	C-37		
HI08	HTX—HI08 Transmit Data Register	C-37		
HI08	HBAR—HI08 Base Address Register	C-37		
HI08	ICR—Interface Control Register	C-38		
HI08	ISR—Interface Status Register	C-38		
HI08	CVR—Control Vector Register	C-39		
HI08	IVR—Interrupt Vector Register	C-39		
SSI0	CRA0—SSI0 Control Register A	C-40		
SSI0	CRB0—SSI0 Control Register B	C-40		
SSI0	CRC0—SSI0 Control Register C	C-41		
SSI0	SSISR0—SSI0 Status Register	C-42		
SSI0	RX0—SSI0 Receive Register	C-42		
SSI0	TSR0—SSI0 Time Slot Register	C-42		
SSI0	TX0—SSI0 Transmit Register	C-42		
SSI0	PCRC—SSI0 Port C Control Register	C-43		
SSI0	PDRC—SSI0 Port C Data Register	C-43		
SSI0	PRRC—SSI0 Port C Data Direction Register	C-43		
SSI1	CRA1—SSI1 Control Register A	C-44		
SSI1	CRB1—SSI1 Control Register B			
SSI1	CRC1—SSI1 Control Register C	C-45		
SSI1	SSISR1—SSI1 Status Register	C-46		



Table C-8 List of Programmer's Sheets (Continued) (Continued)

Type of Register	pe of Register Register				
SSI1	RX1—SSI1 Receive Register	C-46			
SSI1	TSR1—SSI1 Time Slot Register	C-46			
SSI1	TX1—SSI1 Transmit Register	C-46			
SSI1	PCRD—SSI1 Port D Control Register	C-47			
SSI1	PDRD—SSI1 Port D Data Register	C-47			
SSI1	PRRD—SSI1 Port D Data Direction Register	C-47			
GPIO	PCR—GPIO Port Control Register	C-48			
GPIO	PDR—GPIO Port Data Register	C-48			
GPIO	PRR—GPIO Port Data Direction Register	C-48			
Timers	TPLR—Timer Prescaler Load Register	C-49			
Timers	TPCR—Timer Prescaler Count Register	C-49			
Timer0	TCSR0—Timer 0 Control/Status Register	C-50			
Timer0	TLR0—Timer 0 Load Register	C-50			
Timer0	TCPR0—Timer 0 Compare Register	C-50			
Timer0	TCR0—Timer 0 Count Register	C-50			
Timer1	TCSR1—Timer 1 Control/Status Register	C-51			
Timer1	TLR1—Timer 1 Load Register	C-51			
Timer1	TCPR1—Timer 1 Compare Register	C-51			
Timer1	TCR1—Timer 1 Count Register	C-51			
Timer2	TCSR2—Timer 2 Control/Status Register				
Timer2	TLR2—Timer 2 Load Register	C-52			
Timer2	TCPR2—Timer 2 Compare Register	C-52			
Timer2	TCR2—Timer 2 Count Register	C-52			





Application:										_		e: gram				
										_	-10	gram			neet 1	of 8
CPU			JΤ		Reg Rese	ictioi giste t = \$2 Write	r 2 —		1 B1	0 B0			Re	Regi eset	ister	0
JTAG ID Register Read Only	31 MSK 7	30 MSK 6	29 MSK 5	28 MSK 4	27 MSK 3	26 MSK 2	25 MSK 1	24 MSK 0	23 INV 7	22 INV 6	21 INV 5	20 INV 4	19 INV 3	18 INV 2	17 INV 1	16 INV 0
	15 MSK 7	14 MSK 6	13 MSK 5	12 MSK 4	11 MSK 3	10 MSK 2	9 MSK 1	8 MSK 0	7 INV 7	6 INV 6	5 INV 5	4 INV 4	3 INV 3	2 INV 2	1 INV 1	0 INV 0






Programmer's Reference

CPU

МС	МВ	MA	Mode	Reset Vector				
0	0	0	0—Extended	\$0400				
0	0	1	1—Normal	\$0800				
0	1	0	2—Normal	\$0800				
0	1	1	3—Normal	\$0800				
1	0	0	4—Normal	\$0800				
1	0	1	5—Normal	\$0800				
1	1	0	6—Normal	\$0800				
1	1	1	7—Normal	\$0800				
	Setting MD bit has no effect on DSP56603.							

XYS	Description											
0	Stack extension mapped to X memory											
1	Stack extension mapped to Y memory											



0

EOM

Extended Operating

Mode Register

	0	128 K	clock	Cy	/cle	delay								
	1	16 clo	ock cy	cle	del	ay								
	PCD)		De	scr	iption								
	0	PC ı	elativ	e ir	nstru	uctions	s enab	led						
	1	PC i	elativ	e ir	nstri	uctions	s disal	oled						
			EBD Description											
			0		External bus									
					CO	ontroller enabled								
			1		External bus controller disabled									
			4		CO	ntrolle	r disar	olea						
						-								
	_					V								
	\	\	₩		_	`								
7	6	5	4	_	3	2	1	0						
*	SD	PCD	EBD	N	/ID	MC	MB	MA						
0														
				ı										

COM

Chip Operating

Mode Register

Description

* = Reserved, Program as 0

Reset = \$0300 Read/Write



plica	ation	<u>:</u>								te:				
									Pro	gram	mer:		neet 3	
(<u>ن ا</u>													
		Carry _												
	C	verflow -												
		– Zero – legative												
Uı	nnor	malized -												
	Ex	tension –												
		Limit – Scaling –							1					
-						_								
I1	10	Exceptions			s Maske	d								
0	0	IPL 0, 1, 2, 3	3	None IPL 0		4								
1	0	IPL 1, 2, 3		IPL 0, 1		-								
1	1	IPL 3		IPL 0, 1, 2		\dashv								
S 1	S0	Rounding		Scaling M										
		Bit												
0	0	15	No scaling			1								
0	1	16		n—1 bit arith										
1	0	14	(reserved)	-1 bit arithme	elic ieit si	IIIL								
)O F	-OR	EVER Flaç												
SM		rithmetic Sa		ode										
0		vergent round		la ata d										
1	Auto	matic 32-bit s	saturation se	elected										
RM		Rounding I												
0		ergent round												
1		s-complemer	nt rounding		\downarrow		\downarrow							
DO I	Loop	Flag	→ ↓	\downarrow \downarrow	ئے	\neg	<u>`</u>	\psi	↓ ↓	\forall	\downarrow	¥	\downarrow	
Sta	atus	Register (SR)	15 14 LF RM	13 12 SM FV		10 9	8 10		6 5 L E	4 U	3 N	2 Z	1 V	
R		t = \$0300												L
	Re	ad/Write												

MR Mode Register CCR Condition Code Register





Programmer's Reference

Application:	Date:
	Programmer:
	Sheet 4 of 8



IAL2	IAL1	IAL0	IRQ A Mode	Trigger Mode
0	0	0	IRQ A disabled, no IPL	Level-Triggered
0	0	1	IRQ A enabled, IPL = 0	Level-Triggered
0	1	0	IRQ A enabled, IPL = 1	Level-Triggered
0	1	1	IRQ A enabled, IPL = 2	Level-Triggered
1	0	0	IRQ A disabled, no IPL	Negative-Edge Triggered
1	0	1	IRQ A enabled, IPL = 0	Negative-Edge Triggered
1	1	0	IRQ A enabled, IPL = 1	Negative-Edge Triggered
1	1	1	IRQ A enabled, IPL = 2	Negative-Edge Triggered

IBL2	IBL1	IBL0	IRQ B Mode	Trigger Mode
0	0	0	IRQ B disabled, no IPL	Level-Triggered
0	0	1	IRQ B enabled, IPL = 0	Level-Triggered
0	1	0	IRQ B enabled, IPL = 1	Level-Triggered
0	1	1	IRQ B enabled, IPL = 2	Level-Triggered
1	0	0	IRQ B disabled, no IPL	Negative-Edge Triggered
1	0	1	IRQ B enabled, IPL = 0	Negative-Edge Triggered
1	1	0	IRQ B enabled, IPL = 1	Negative-Edge Triggered
1	1	1	IRQ B enabled, IPL = 2	Negative-Edge Triggered

ICL2	ICL1	ICL0	IRQ C Mode	Trigger Mode
0	0	0	IRQ C disabled, no IPL	Level-Triggered
0	0	1	IRQ C enabled, IPL = 0	Level-Triggered
0	1	0	IRQ C enabled, IPL = 1	Level-Triggered
0	1	1	IRQ C enabled, IPL = 2	Level-Triggered
1	0	0	IRQ C disabled, no IPL	Negative-Edge Triggered
1	0	1	IRQ C enabled, IPL = 0	Negative-Edge Triggered
1	1	0	IRQ C enabled, IPL = 1	Negative-Edge Triggered
1	1	1	IRQ C enabled, IPL = 2	Negative-Edge Triggered

IDL2	IDL1	IDL0	IRQ D Mode	Trigger Mode
0	0	0	IRQ D disabled, no IPL	Level-Triggered
0	0	1	IRQ D enabled, IPL = 0	Level-Triggered
0	1	0	IRQ D enabled, IPL = 1	Level-Triggered
0	1	1	IRQ D enabled, IPL = 2	Level-Triggered
1	0	0	IRQ D disabled, no IPL	Negative-Edge Triggered
1	0	1	IRQ D enabled, IPL = 0	Negative-Edge Triggered
1	1	0	IRQ D enabled, IPL = 1	Negative-Edge Triggered
1	1	1	IRQ D enabled, IPL = 2	Negative-Edge Triggered

11 8 5 14 13 12 10 9 6 4 3 0 Interrupt Priority IDL2 IDL1 IDL0 ICL1 ICL0 IBL2 IBL1 IAL1 ICL2 IBL0 IAL2 IAL0 Register-Core (IPR-C) 0 0 0 X:\$FFFF \$0 Reset = \$0000

* = Reserved, Program as 0



Application:_	Date:	
	Programmer:_	
	5 –	Sheet 5 of 8

																		Sh	eet 5 d	of 8
Г	\overline{C}	OI I											Г			HIO	8 IPL			
L	<u>Uг</u>	U											Н	HPL1 HPL0 Mode						
														0	0	Inter	rupts	disable	ed	
		Γ				SSI1 I	PL							0	1	Inter	rupts	enable	d, IPL	. = 0
			S1L1	S1L) N	Mode								1	0	Inter	rupts	enable	d, IPL	. = 1
			0	0	I	nterrup	ts dis	abled						1	1	Inter	rupts	enable	d, IPL	_= 2
			0	1	I	nterrup	ts ena	abled,	IPL =	0										
			1	0	I	nterrup	ts ena	abled,	IPL =	1					SSI0	IPL				
			1	1	I	nterrup	ts ena	abled,	IPL = 2	2		SOL	.1 S	0L0	Mode					
												0		0 Interrupts disabled						
l			Tin	ner IP	<u> </u>			\neg				0		1	Interrupts enabled, IPL = 0				0	
	TPL1	TPLO	_		_			\dashv				1		0	Interrupts enabled, IPL = 1				1	
	0	0		rrupts	dis	abled						1		1	Interru	pts en	abled	, IPL =	2	
	0	1	_			abled, I	PI = ()												
	1	0	_			abled, I		-		_						1				
	1	1	_			abled, I														
											'				'	Y		Y		_
					15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
_	anister Berinberg							*	*	*	TPL1	TPL0	*	*	S1L1	S1L0	S0L1	S0L0	HPL1	HPL0
Re	egister–Peripheral 0 0 0 0						0	0	0			0	0							
	X:\$FFFE \$0 Reset = \$0000								-				-			•				


^{* =} Reserved, Program as 0





Programmer's Reference

Application:_	Date:	
	Programmer:_	
_	<u> </u>	Sheet 6 of 8



^{* =} Reserved, Program as 0

	Revision							Device Number								
	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
DSP56603 Identification Register (IDR)	0	0	0	0	0	1	1	0	0	0	0	0	0	0	1	1
X:\$FFF9 Read-Only		\$	0			\$(6			\$	0			,	\$3	



Applicati	on:											Da	te:				
												Pro	gran	nmer			
															S	heet 7	of 8
С	PU																
		15	14	13	12	11	10	9	8	_I 7	6	5	4	3	2	1	0
Patch	Register 0 (PAR0)	PAR 15	PAR 14	PAR 13	PAR 12	PAR 11	PAR 10	PAR 9	PAR 8	PAR 7	PAR 6	PAR 5	PAR 4	PAR 3	PAR 2	PAR 1	PAR 0
Res	X:\$FFF8 et = \$FEFD		•	•									•				
		15	14	13	12		10	9	8		6	5	4	3	2	1	0
Patch	Register 1 (PAR1) X:\$FFF7	PAR 15	PAR 14	PAR 13	PAR 12	PAR 11	PAR 10	PAR 9	PAR 8	PAR 7	PAR 6	PAR 5	PAR 4	PAR 3	PAR 2	PAR 1	PAR 0
Res	set = \$F7FF																
		15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
Patch	Register 2 (PAR2)	PAR 15	PAR 14	PAR 13	PAR 12	PAR 11	PAR 10	PAR 9	PAR 8	PAR 7	PAR 6	PAR 5	PAR 4	PAR 3	PAR 2	PAR 1	PAR 0
Res	X:\$FFF6 et = \$7FEE																
		15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
Patch	Register 3 (PAR3)	PAR 15	PAR 14	PAR 13	PAR 12	PAR 11	PAR 10	PAR 9	PAR 8	PAR 7	PAR 6	PAR 5	PAR 4	PAR 3	PAR 2	PAR 1	PAR 0
Res	X:\$FFF5 et = \$BBF3		•	•	•						•		•				





Programmer's Reference

Application:_	Date:	
_	Programmer:_	
	_	Sheet 8 of 8

CDII

	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
Bus Switch Program Memory Register (BPMRG)	G15	BPMR G14	BPMR G13	BPMR G12	BPMR G11	BPMR G10	BPMR G9	BPMR G8	BPMR G7	BPMR G6	BPMR G5	BPMR G4	BPMR G3	BPMR G2	BPMR G1	BPMR G0
X:\$FFF4 Reset = \$0000																

5 6 4 1	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
Bus Switch Program Memory Register Low	L15	BPMR L14	BPMR L13	BPMR L12	BPMR L11	BPMR L10	BPMR L9	BPMR L8	BPMR L7	BPMR L6	BPMR L5	BPMR L4	BPMR L3	BPMR L2	BPMR L1	BPMR L0
(BPMRL) X:\$FFF3 Reset = \$0000				l			<u> </u>								l	

	15	14	13	12	11	10	9	8	7	6	5	4	₁ 3	2	1	0
Bus Switch Program Memory Register High	*	*	*	*	*	*	*	*	BPMR H7	BPMR H6	BPMR H5	BPMR H4	BPMR H3	BPMR H2	BPMR H1	BPMR H0
(BPMRH) X:\$FFF2 Reset = \$0000		4	60			\$	0					•				

^{* =} Reserved, Program as 0



Programmer's Reference

Freescale Semiconductor, Inc.

Application:_ Programmer:__ Sheet 1 of 1 Predivider Factor Use with PD4-PD6 in PCTL1 **Multiplication Factor** 15 14 12 9 2 0 13 11 10 6 5 3 PD3 PD2 PD1 PD0 MF11 MF10 MF9 MF8 MF7 MF6 MF5 MF4 MF3 MF2 MF1 MF0 **PLL Control** Register 0 (PCTL0) X:\$FFFD Reset = \$0000 **PSTP** Description **XTLD** Description PLL disabled during Stop state 0 0 XTAL output enabled PLL operates during Stop state XTAL output disabled (XTAL pin pulled high) PEN Description 0 PLL disabled **XTLR** Description 1 PLL enabled Use for external crystal frequency above 200 KHz COD Description Use for external crystal 0 PLL disabled during Stop state frequency below 200 KHz PLL operates during Stop state **Division Factor Predivider Factor** Use with PD0-PD3 in PCTL0 11 0 15 14 13 12 10 8 PD6 PD5 PD4 COD PEN PSTP XTLD DF2 DF1 DF0 **PLL Control** Register 1 (PCTL1) 0 0 0 0 X:\$FFFC \$0 Reset = \$0000 * = Reserved, Program as 0






Programmer's Reference

Application	າ:										_	Date	e:				
												Prog	gram	mer:			
															Sh	eet 1	of 5
HI	<u> </u>											HRDF		Des	scripti	on	
	00											0	HR	X regis	ter is	not ful	ı
												1	HR	X regis	ter is	full	Į.
НСР	De	escrip	otion						Γ	HTDE	<u> </u>		Des	criptic	n		1
0	Host Comma pending (HC									0	Н	RX reg					1
1	Host Comma				rea)					1	Н	TX reg	ister is	s empt	.y		
'	pending (HC																
	HF0, I	4F1															
	General purp	ose f			-									٦			
Values re	eflect HF0, HF1	in IC	R on h	nost si	de.									¥			
		15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
	II08 Status [ster (HSR)	*	*	*	*	*	*	*	*	*	*	*	HF1	HF0	HCP	HT DE	HR DF
og.	X:\$FFC3	0	0	0	0	0	0	0	0	0	0	0					
	et = \$0002 Read-Only		\$	0			\$	0									
•						l											
										HRIE			De	script	ion		
										0	Ho	st Rec	eive D	ata In	terrupt	disab	led
										1	Hos	st Rec	eive D	ata In	terrupt	enab	led
								Г	HTIE			Do	script	ion		\neg	
HCIE		locor	iption			٦		F	0	Hos	t Trar	nsmit E			t disal	oled	
0	Host Commai				ed				1			nsmit [
1	Host Comma					_				-						T	
	HF2 General pu	, HF3 irpose											,	1			
Values	reflect HF2, H				side									<u> </u>	\downarrow	\downarrow	\downarrow
н	08 Control	15 *	14	13	12	11	10	9	8 *	7	6 *	5	4 HF3	3	2 HCIE	1	0
	ter (HCR)	0	0	0	0	0	0	0	0	0	0	0	пгэ	пг∠	HOIL	ППЕ	IUKIE
_	X:\$FFC2				U		U	U				<u> </u>					
	et = \$0000 Read/Write		\$	0			\$	0			\$	0					
•		* = R	leser	ved.	Proa	ram a	as 0			•							
				- /	- 3												

Date: Application:_ Programmer:__








Programmer's Reference

Register (HDDR) X:\$FFC8 Reset = \$0000 Read/Write 15	Application:										_	Dat	e:				
HI08 Data Direction Register (HDDR) X:\$FFC8 Reset = \$0000 Read/Write											_	Pro	gram	mer:			
HI08 Data Direction Register (HDDR) X:\$FFC8 Reset = \$0000 Read/Write HI08 Data Register (HDR) X:\$FFC9 Reset = \$0000 Read/Write HI08 Boata Register (HDR) X:\$FFC6 Reset = \$0000 Read/Write HI08 Boata Register (HDR) X:\$FFC6 Reset = \$0000 Read/Write HI08 Receive Data Register (HRX) X:\$FFC6 Reset = \$0000 Read/Write HI08 Receive Data Register (HRX) X:\$FFC6 Reset = \$0000 Read/Write HI08 Receive Data Register (HRX) X:\$FFC6 Reset = \$0000 Read/Write HI08 Transmit Data Register (HTX) X:\$FFC6 Reset = \$0000 Read-Only HI08 Transmit Data Register (HTX) X:\$FFC6 Reset = \$0000 Read-Only HI08 Transmit Data Register (HTX) X:\$FFC6 Reset = \$0000 Read-Only HI08 Transmit Data Register (HTX) X:\$FFC6 Reset = \$0000 Read-Only HI08 Transmit Data Register (HTX) X:\$FFC6 Reset = \$0000 Read-Only HI08 Transmit Data Register (HTX) X:\$FFC6 Reset = \$0000 Read-Only HI08 Transmit Data Register (HTX) X:\$FFC6 Reset = \$0000 Read-Only HI08 Transmit Data Register (HTX) X:\$FFC6 Reset = \$0000 Read-Only HI08 Base Address * * * * * * * * * * * * * * * * * *																eet 3	of 5
HI08 Data Direction Register (HDDR) X:\$FFC8 Reset = \$0000 Read/Write HI08 Data Register (HDR) X:\$FFC9 Reset = \$0000 Read/Write HI08 Boata Register (HDR) X:\$FFC6 Reset = \$0000 Read/Write HI08 Boata Register (HDR) X:\$FFC6 Reset = \$0000 Read/Write HI08 Receive Data Register (HRX) X:\$FFC6 Reset = \$0000 Read/Write HI08 Receive Data Register (HRX) X:\$FFC6 Reset = \$0000 Read/Write HI08 Receive Data Register (HRX) X:\$FFC6 Reset = \$0000 Read/Write HI08 Transmit Data Register (HTX) X:\$FFC6 Reset = \$0000 Read-Only HI08 Transmit Data Register (HTX) X:\$FFC6 Reset = \$0000 Read-Only HI08 Transmit Data Register (HTX) X:\$FFC6 Reset = \$0000 Read-Only HI08 Transmit Data Register (HTX) X:\$FFC6 Reset = \$0000 Read-Only HI08 Transmit Data Register (HTX) X:\$FFC6 Reset = \$0000 Read-Only HI08 Transmit Data Register (HTX) X:\$FFC6 Reset = \$0000 Read-Only HI08 Transmit Data Register (HTX) X:\$FFC6 Reset = \$0000 Read-Only HI08 Transmit Data Register (HTX) X:\$FFC6 Reset = \$0000 Read-Only HI08 Base Address * * * * * * * * * * * * * * * * * *	Шло									Γ	DRn	.		Desc	rintio	n	
HI08 Data Direction Register (HDDR) X:\$FFC8 Reset = \$00000 Read/Write 15	ПІОО									ŀ			n used		•		
HI08 Data Direction Register (HDDR)											1						
HI08 Data Direction Register (HDDR)		15	1.1	12	12	. 11	10	۵	0	. 7	6	5	4	. 2	2	1	
Reset = \$0000 Read/Write	HI08 Data Direction											_					
Reset = \$0000 Read/Write																	
HI08 Data Register (HDR) X:\$FFC9 Reset = \$0000 Read-Only	·																<u> </u>
HI08 Data Register (HDR) X:\$FFC9 Reset = \$0000 Read/Write 15	Read/Write																
HI08 Data Register (HDR) X:\$FFC9 Reset = \$0000 Read/Write 15																	
HI08 Data Register (HDR) X:\$FFC9 Reset = \$0000 Read/Write 15																	
HI08 Data Register (HDR) X:\$FFC9 Reset = \$0000 Read/Write 15		15	14	13	12 .	11	10	9	8 .	7	6	5	4 .	3	2	1	0
X:\$FFC9 Reset = \$0000 Read/Write																	
HI08 Receive Data Register (HRX) X:\$FFC6 Reset = \$0000 Read-Only 15																	
Third Transmit Data Register (HTX) X:\$FFC7 Reset = \$0000 Write-Only Third Thir	-	ļ		·		J	J										
HI08 Receive Data Register (HRX) X:\$FFC6 Reset = \$0000 Read-Only HI08 Transmit Data Register (HTX) X:\$FFC7 Reset = \$0000 Write-Only HI08 Base Address * * * * * * * * * * * * * * * * * *																	
HI08 Receive Data Register (HRX) X:\$FFC6 Reset = \$0000 Read-Only 15																	
HI08 Receive Data Register (HRX) X:\$FFC6 Reset = \$0000 Read-Only HI08 Transmit Data Register (HTX) X:\$FFC7 Reset = \$0000 Write-Only HI08 Base Address * * * * * * * * * * * * * * * * * *		15	14	13	12 ı	11	10	9	8	ı 7	6	5	4 1	3	2	1	0
X:\$FFC6 Reset = \$0000 Read-Only HI08 Transmit Data Register (HTX) X:\$FFC7 Reset = \$0000 Write-Only 15			Data							-			_		1		
Reset = \$0000 Read-Only HI08 Transmit Data Register (HTX) X:\$FFC7 Reset = \$0000 Write-Only HI08 Base Address	• • •																
Read-Only	-																
HI08 Transmit Data Register (HTX) X:\$FFC7 Reset = \$0000 Write-Only 15 14 13 12 11 10 9 8 7 6 5 4 3 2 1 0 HI08 Base Address * * * * * * * * * * * * * * * * * *																	
HI08 Transmit Data Register (HTX) X:\$FFC7 Reset = \$0000 Write-Only 15 14 13 12 11 10 9 8 7 6 5 4 3 2 1 0 HI08 Base Address * * * * * * * * * * * * * * * * * *																	
HI08 Transmit Data Register (HTX) X:\$FFC7 Reset = \$0000 Write-Only 15 14 13 12 11 10 9 8 7 6 5 4 3 2 1 0 HI08 Base Address * * * * * * * * * * * * * * * * * *		15	1.1	12	10	. 11	10	0	0	. 7	6	_	4	. 9	2	1	0
X:\$FFC7 Reset = \$0000 Write-Only 15 14 13 12 11 10 9 8 7 6 5 4 3 2 1 0 HI08 Base Address * * * * * * * * * * * * * * * * * *	HI08 Transmit Data																
Reset = \$0000 Write-Only 15 14 13 12 11 10 9 8 7 6 5 4 3 2 1 0 HI08 Base Address * * * * * * * * * * BA10 BA9 BA8 BA7 BA6 BA5 BA4 BA3	• , ,																
Write-Only 15 14 13 12 11 10 9 8 7 6 5 4 3 2 1 0 HI08 Base Address * * * * * * * * * * * * * * * * * *				<u> </u>							ļ .						
HI08 Base Address * * * * * * * * BA10 BA9 BA8 BA7 BA6 BA5 BA4 BA3	Write-Only																
HI08 Base Address * * * * * * * * * BA10 BA9 BA8 BA7 BA6 BA5 BA4 BA3																	
		15	14	13	12	11	10	9	8	_ 7	6	5	4	3	2	_1	0
	HI08 Base Address Register (HBAR)		*	*	*	*			*	BA10	BA9	BA8	BA7	BA6	BA5	BA4	BA3
X:\$FFC5 0 0 0 0 0 0 0 0 0 0	• • • • • • • • • • • • • • • • • • • •	0	0	0	0	0	0	0	0								
Reset = \$0080 \$0 \$0	Reset = \$0080		\$(D			\$(D									
Read/Write	Read/Write																
* = Reserved, Program as 0	*	* = R	eserv	/ed, F	Progr	am a	s 0										



Application:	Date:
	Programmer:



C-38



Semiconductor, Inc.



Freescale Semiconductor, Inc.

Programmer's Reference

Application	า:			Date:	
				Programmer:_	
					Sheet 5 of 5
HI	80]			
	НС	Description		HV0-HV6	
	0	No host command pending	Eq	uals VBA register interr	upt vector ÷ 2

				1			1VU–H	V6		
0	No host command pending			Equ	als VE	3A reg	ister ir	nterrup	ot vect	or ÷ 2
1	Host command is pending		\forall							$\overline{}$
			7	6	5	4	3	2	1	0
		egister (CVR)	HC	HV6	HV5	HV4	HV3	HV2	HV1	HV0
		Reset = \$32 Read/Write								

IV0-IV7 Contains interrupt vector for MC68000 family 6 5 4 3 2 0 IV7 IV6 IV5 IV4 IV3 IV2 IV1 IV0 **Interrupt Vector** Register (IVR) Reset = \$0FRead/Write




Register A (CRA0) X:\$FFB6 Reset = \$0000 Read/Write TLIE Description 0 (Bit is cleared) 1 TX Underrun Occurred TEIE Description 0 (Bit is cleared) 1 TX Underrun Occurred TEIE Description 0 (Bit is cleared) 1 TX Underrun Occurred TEIE Description 0 (Bit is cleared) 1 TX Underrun Occurred TEIE Description 0 (Bit is cleared) 1 TX Underrun Occurred TEIE Description 0 Transmit Interrupt disabled 1 Receive enabled TE Description 0 Receive disabled 1 Receive enabled TE Description 0 Transmit disabled 1 TX Underrun Occurred TE Description 0 Transmit disabled 1 TX Underrun Occurred TE Description 0 Transmit disabled 1 Transmit enabled	Application:										Da	ate:				
WL1											Pr	ograr	nmer	:		
SSI 0 Control 7 6 5 4 3 2 1 0 15 14 13 12 11 10 9 Prescale Modulus Bits Prescale A (CRAO) Table Prescale Modulus Bits Prescale Modulus Prescale Modulus Prescale Modulus Prescale Modu														S	heet	1 of 4
SSI 0 Control 7 6 5 4 3 2 1 0 15 14 13 12 11 10 9 Prescale Modulus Bits Dinary encoded Dinary enco	9910	WI	L1	WL0	1	Descri	ption				romo	Poto I	Divido	r Dito	_	
1	3310	0)	0	8 bits	per wo	ord			Ľ						
1		0)	1	12 bit	s per w	ord									
SSI 0 Control Register A (CRA0) X:\$FFB6 Reset = \$0000 Read/Write REIE Description 0 (Bit is cleared) 1 TX Underrun Occurred 2 TEIE Description 0 (Bit is cleared) 1 TX Underrun Occurred 1 TX Underrun Occurred 2 TEIE Description 0 (Bit is cleared) 1 TX Underrun Occurred 1 TX Underrun Occurred 1 TX Underrun Occurred 2 TEIE Description 0 (Bit is cleared) 1 TX Underrun Occurred 2 TEIE Description 0 (Bit is cleared) 1 TX Underrun Occurred 2 TEIE Description 0 (Bit is cleared) 1 TX Underrun Occurred 2 TEIE Description 0 (Bit is cleared) 1 TX Underrun Occurred 2 TEIE Description 0 (Bit is cleared) 1 TX Underrun Occurred 2 TEIE Description 0 (Bit is cleared) 2 TEIE Description 3 TEIE Description 3 TEIE Description 3 TEIE Description 4 TEIE Description 5 TEIE TILIE		1		0			ord		_							
SSI 0 Control PSR WL1 WL0 DC4 DC3 DC2 DC1 DC0 PM7 PM6 PM6 PM4 PM3 PM2 PM1		1		1	(reser	ved)										
SSI 0 Control Register A (CRA0)			\downarrow			▼						۱	V	-		
Tile Description 0 (Bit is cleared) 1 TX Underrun Occurred 1	001.0.0	7	5	4	1 3	2	1	0	15	14	13	12	 11	10	9	8
X:\$FFB6 Reset = \$0000 Read/Write TLIE		PSR W	L1 WL	0 DC4	DC3	DC2	DC1	DC0	PM7	PM6	PM5	PM4	PM3	PM2	PM1	PM0
TLIE Description 0 (Bit is cleared) 1 TX Underrun Occurred 1 Receive Interrupt disabled 1 TX Underrun Occurred 1 Receive enabled 1 TX Underrun Occurred 1 Receive enabled 1 TX Underrun Occurred 1 TX	X:\$FFB6															
TLIE Description 0 (Bit is cleared) 1 TX Underrun Occurred 1 Receive Interrupt disabled 1 Transmit Interrupt disabled 1 Receive enabled 1 Receive enabled 1 Receive enabled 1 Receive enabled 1 Transmit disabled 1 Transmit disabled 1 Transmit disabled 1 Transmit disabled 1 Transmit enabled Serial Output Flaten Serial Output	Reset = \$0000 Read/Write															
0	itoaa, viito								<u> </u>							
O																
1 TX Underrun Occurred			TLIE		Desc	ription				F	RIE		Des	criptio	on	
TIE Description 0 (Bit is cleared) 1 TX Underrun Occurred 1 Transmit Interrupt disabled 1 TX Underrun Occurred 1 Transmit Interrupt enabled 1 TX Underrun Occurred 1 Receive enabled 1 Receive enabled 1 Receive enabled 1 Receive enabled 1 TX Underrun Occurred 1 Transmit disabled 1 TX Underrun Occurred 1 Transmit disabled 1 Transmit disabled 1 Transmit disabled 1 Transmit disabled 1 Transmit enabled 1 Tr			0	(Bit is	cleared	l)		r			0	Rece	ive Inte	errupt	disabl	ed
0			1	TX Un	derrun	Occur	red	ᅰ			1	Rece	ive Inte	errupt	enabl	ed
1 TX Underrun Occurred		RLIE		Desc	ription					-	ΓIE		Des	cripti	on	
TEIE Description 0 (Bit is cleared) 1 TX Underrun Occurred REIE Description 0 (Bit is cleared) 1 Receive enabled TE Description 0 Transmit disabled 1 Tx Underrun Occurred Serial Output Flag Serial		0	(Bit is	cleared	d)						0	Trans	smit Int	terrupt	disab	led
O (Bit is cleared)		1	TX Ur	nderrun	Occur	red					1	Trans	smit Int	terrupt	enab	led
1 TX Underrun Occurred 1 Receive enabled TE Description 0 (Bit is cleared) 1 TX Underrun Occurred 1 Transmit disabled 1 Tx Underrun Occurred 1 Transmit enabled Serial Output Flate Serial Output Flate Table Ta	TEIE	Des	criptio	n							RE		Des	cription	on	
REIE Description 0 (Bit is cleared) 1 TX Underrun Occurred	0 (Bit	is cleare	ed)								0	Rece	ive dis	abled		
0 (Bit is cleared) 1 TX Underrun Occurred Serial Output Flat Ser	1 TX	Underrur	n Occu	rred							1	Rece	ive en	abled		
1 TX Underrun Occurred Serial Output Flag Se	REIE Descr	iption									TE		Des	scripti	on	
SSI 0 Control Register B (CRB0) X:\$FFB7 Reset = \$0000	0 (Bit is cleared)										0	Tran	smit di	sabled	ł	
SSI 0 Control Register B (CRB0) X:\$FFB7 Reset = \$0000	1 TX Underrun	Occurred									1	Trans	smit er	nabled		
SSI 0 Control Reje Tele RLIE TLIE RE TE * * * * * * * * * OF1 Register B (CRB0) X:\$FFB7 Reset = \$0000 CRB0 CR]							Seria	al Out	put F	lags
SSI 0 Control Reje Tele RLIE TLIE RE TE * * * * * * * * * OF1 Register B (CRB0) X:\$FFB7 Reset = \$0000 CRB0 CR		↓ ▼	\ \	, ↓	↓		$\overline{\ }$								_	V_
Register B (CRB0) X:\$FFB7 Reset = \$0000	SSI 0 Control										_		 		1	OF0
Reset = \$0000	Register B (CRB0)	KLIL 1	LIE KL	1116	. KIE	''=	KE	'=							J OF 1	OFU
1/6361 - \$0000						1			"			"	"	U		
Read/Write	Reset = \$0000 Read/Write									\$	0					

* = Reserved, Program as 0





Application:_______ Date:______
Programmer:______





Applicati	ion:											Dat	te:				
												Pro	orar	nmer			
													, g. a.			Sheet :	3 of 4
S	SI0																
ROE	Descri	iption				TUE		Desc	riptio	on		TFS		De	escrip	tion	
0	(Bit is cleared))		_	ı	0	(Bit	t is clea	red)			0	No	Fram	e Syn	C	
1	RX Overrun O	ccurre	ed			1	TX	Under	un O	ccurre	d	1	TX	Fram	e Syn	с Осс	urred
TDE	Descri (Bit is cleared)										F	RFS 0	No Fr	Desc	riptic Sync	n	
1	TX Data Regis	ster En	npty									1	RX Fı	rame S	Sync C	Occurr	ed
RDF	Descri	ption		7									\neg		ſſ	Se	rial
0	(Bit is cleared)	•		<u> </u>											L	Input	Flags
1	RX Data Regis	ster ha	s data	a								\downarrow				_	Y
		15	14	13	12		10	9	8	1 7	6	5	4	3	2	<u>, 1</u>	0
S	SSI 0 Status		*	*	*	*	*	*	*	RDF	TDE	ROE	TUE	RFS	TFS	IF1	IF0
Regist	er (SSISR0) X:\$FFB9		0	0	0	0	0	0	0								
Re	set = \$0040		\$	0			,	\$0									
		* = R	Reser	ved,	Prog	gram	as 0										
	_	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
	0 Receive ster (RX0) X:\$FFBA			Н	ligh	Byte						L	ow E	Byte			
i	Read-Only																
	Г	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
X:\$FFBB					my	Regis	ster,	Writt	en C	Ourin	g In	active	Tim	e Slo	ots		
١	Write-Only																
	_	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
	SSI 0 Transmit Register (TX0) X:\$FFBC					Byte						L	ow I	Byte			
,	Write-Only																

* = Reserved, Program as 0

Application:										_	Dat	e:				
											Pro	gram	nmer:			
														Sł	neet 4	of 4
CCIO				Γ	PEN		D	escrip	tion		1 [PCn	р	escri	otion	٦
SSI0				F	0	SS		tri-stat			1	0		is GF		=
				+	1			enable			1	1	_	is SS		-
				L					1						•	
									\downarrow					<u> </u>		
	15	14	13	12	11	10	9	8	, ,	6	5	4	3	2	1	0
SSI 0 Port C Control	*	*	*	*	*	*	*	*	PEN	*	PC5	PC4	PC3	PC2	PC1	PC0
Register (PCRC) X:\$FFBF	0	0	0	0	0	0	0	0		0						
Reset = \$0000		\$	0				\$0							_		_
Read/Write													l			
											PE)n	Des	criptio	n	
											C) F	Pin is ii	nput		
											1	F	Pin is c	utput		
													1	1		
	15	14	13	12	11	10	9	8	7	6	5	4		2	1	0
SSI 0 Port C Data	*	*	*	*	*	*	*	*	*	*	PD5	PD4	PD3	PD2	PD1	PD0
Register (PDRC) X:\$FFBD	0	0	0	0	0	0	0	0	0	0						
Reset = \$0000		•		l .		¢.										
Read/Write		\$	<u> </u>			\$	<u> </u>									
00100 10	15	14	13	12	ı 11	10	9	8	7	6	5	4	ı 3	2	1	0
SSI 0 Port C Data Direction	*	*	*	*	*	*	*	*	*	*	PDC5		PDC3			PDC0
Register (PRRC)	0	0	0	0	0	0	0	0	0	0						
X:\$FFBE				<u> </u>												<u> </u>
Reset = \$0000		\$	0			\$	0									
Read/Write													L			

* = Reserved, Program as 0



Programmer's Reterence

Application:														te: ogran				
														ogran			heet	
	14		,	WL1	V	VL0	-	Descri	ption									
SSI			F	0		0		per wo				F	rame bir	Rate I nary ei				
				0		1	12 bit	s per v	vord									
				1		0	16 bit	s per v	vord									
				1		1	(reser	ved)					Presc	ale Mo				
				,				Ţ					, DII	nary C	licoaci	<u> </u>		
	1	0	15	14	13	12	11	10	9	8								
SSI 1 Register A	Conti	rol	7 PSR	6 WL1	5' WL0	DC4	DC3	DC2	DC1	DC0	PM7	PM6	PM5	PM4	PM3	PM2	PM1	PM0
	X:\$FF																	
Reset	= \$00 ad/Wr	00		•						•		•		•				
				TLI	-	(Dit in a		ription	1				RIE	Dani		criptic		
				TL I	((Bit is c	leared	i)					RIE 0 1		Des	errupt	disabl	
		[ВП	0	(TX Und	leared	l) Occur					0		ive Inte	errupt errupt	disabl enable	
			RLI	0 1	-	TX Und	leared lerrun ription	l) Occur					0 1 TIE	Recei	ive Inte	errupt errupt cripti	disabl enable	ed
			RLI 0 1	0 1 E (E	Bit is	TX Und	leared lerrun ription	Occur					0	Recei	ive Inte	errupt errupt cription	disablenable on t disab	ed
	TEIE		0	0 1 E (E	Bit is	Desc Cleared derrun	leared lerrun ription	Occur					0 1 TIE 0	Recei	Des	errupt errupt cription	disable enable on the disable tenable tenable tenable disable disable tenable disable tenable disable	ed
	TEIE 0	(Bit	0	0 1 E (E	Bit is	Desc Cleared derrun	leared lerrun ription	Occur					0 1 TIE 0 1	Trans Trans	Des	errupt errupt ecriptic terrupt terrupt	disable enable on the disable tenable tenable tenable disable disable tenable disable tenable disable	ed
		•	0 1 De	0 1 E (E	Bit is	Desc cleared derrun	leared lerrun ription	Occur					0 1 TIE 0 1	Trans Trans Rece	Des	errupt errupt ecriptic terrupt terrupt ecriptic	disable enable on the disable tenable tenable tenable disable disable tenable disable tenable disable	ed
REIE	0	TΧ l	0 1 De	0 1 1 E (E T escriptared)	Bit is	Desc cleared derrun	leared lerrun ription	Occur					0 1 TIE 0 1	Trans Trans Rece	Des mit Interpretation Des ive dis ive en	errupt errupt ecriptic terrupt terrupt ecriptic	on t disab t enab	ed
REIE 0 (Bi	0 1 De	TX (escrip	0 1 Dois clear	0 1 E (E Tescripe ared)	Bit is	Desc cleared derrun	leared lerrun ription	Occur					0 1 TIE 0 1 RE 0	Trans Trans Rece	Des mit Interpretation Des ive dis ive en	errupt errupt ceriptic terrupt terrupt abled abled scriptic	disable enable on transfer disable transfer on	ed
REIE 0 (Bi	0 1	TX (escrip	0 1 Dois clear	0 1 E (E Tescripe ared)	Bit is	Desc cleared derrun	leared lerrun ription	Occur					0 1 TIE 0 1 RE 0 1	Trans Trans Rece Rece Trans	Des	errupt errupt terrupt terrupt terrupt abled abled scriptic	on t disab t enab on	ed
REIE 0 (Bi	0 1 De	TX (escrip	0 1 Dois clear	0 1 E (E Tescripe ared)	Bit is	Desc cleared derrun	leared lerrun ription	Occur					0 1 TIE 0 1 RE 0 1 TE	Trans Trans Rece Rece Trans	Des smit Interpretation Des ive districted Des ive endismit en	errupt errupt terrupt terrupt terrupt abled abled scriptic	on t disable enable ena	eled sled sled

14

TEIE RLIE

15

SSI1 Control REIE

X:\$FFA7 Reset = \$0000

Read/Write

Register B (CRB1)

13

12 | 11

RIE

TLIE

* = Reserved, Program as 0

10

TIE

RE

8

TE

0

0

\$0

0

0

0

0

0,

OF0

OF1






Programmer's Reference

Sheet 2 of 4 SCKD Description External clock source 1 Internal clock source SCD2 Description CKP SC2 pin is input Description Data clocked out on rising edge of TX 1 SC2 pin is output 0 clock, latched in on falling edge of RX clock SCD1 Description Data clocked out on falling edge of TX clock, latched in on rising edge of RX clock SC1 pin is input 0 1 SC1 pin is output **SHFD** Description SCD0 Description 0 Data shifted out MSB first SC0 pin is input Data shifted out LSB first 1 1 SC0 pin is output FSL1 FSL₀ Description MOD Description WL bit clock for both TX and RX Normal mode selected 0 One-bit clock for TX WL bit clock for RX Network mode selected One-bit clock for both TX and RX 1 SYN Description WL bit clock for TX Asynchronous mode One-bit clock for RX selected **FSR** Description Synchronous mode Frame synch occurs with selected 0 first bit of current word Frame synch occurs with last bit of previous word **FSP** Description Positive frame synch Negative frame synch 15 13 12 11 10 9 8 FSR FSL1 FSL0 SHFD CKP SCKD SCD2 SCD1 SCD0 MOD SYN SSI 1 Control Register C (CRC1) 0 0 0 0 X:\$FFA8 \$0 Reset = \$0000* = Reserved, Program as 0

MOTOROLA



Application:	_ Date:
	_ Programmer:



Application:										_	Date	e:				
										_	Pro	gram	mer:			
											·				eet 4	of 4
				Г							, c					7
SSI1					PEN	-		escrip			╡╞	PCn		escrip		
				-	0	_		tri-state			4 F	0		is GP		1
				L	1	55	I pins	enable	a T			1	PIF	is SS	ı pın	
													1	Į.		
CCI 4 Dowt D Comfrol	15	14	13	12	11	10	9	8	, †	6	5	4	3	2	1	0
SSI 1 Port D Control Register (PCRD)	*	*	*	*	*	*	*	*	PEN	*	PC5	PC4	PC3	PC2	PC1	PC0
X:\$FFAF	0	0	0	0	0	0	0	0		0						
Reset = \$0000		\$	0	ı		•	60				1	1			ı	
Read/Write																
											PE		Des Pin is i	criptic	n	
											1	l F	Pin is o	output		
													,	ļ		
											_					
SSI 1 Port D Data	15 *	14	13	12	11 *	10	9	8	7	6 *	5 PD5	4 PD4	DD3	2 PD2	1 PD1	O PD0
Register (PDRD)											FD3	PD4	PD3	PD2	PDI	PDU
X:\$FFAD	0	0	0	0	0	0	0	0	0	0						
Reset = \$0000 Read/Write		\$	0			\$	0									
0014 Dans D	15	14	13	12	ı 11	10	9	8	. 7	6	5	4	ı 3	2	1	0
SSI 1 Port D Data Direction	*	*	*	*	*	*	*	*	*	*	PDC5				PDC1	PDC0
Register (PRRD)	0	0	0	0	0	0	0	0	0	0						
X:\$FFAE						•		L								
Reset = \$0000		\$	<u> </u>			\$	<u> </u>									
Read/Write	* = R	Reser	ved.	Prog	ram a	as O										



Application:	Date:
	Programmer:
	Sheet 1 of 1

GPIO

CDIO Dort Control	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
GPIO Port Control	*	*	*	*	*	*	*	*	*	*	*	*	*	PC2	PC1	PC0
Register (PCR) X:\$FF9F	0	0	0	0	0	0	0	0	0	0	0	0	0			
Reset = \$0000 Read/Write		\$	0	•		\$	60			\$	60			•		

PCn	PDCn	Port Pin Function
0	0	GPIO input
0	1	GPIO output
1	0	tri-stated
1	1	GPIO output, open-drain

	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
GPIO Port Direction	*	*	*	*	*	*	*	*	*	*	*	*	*	PDC2	PDC1	PDC0
Register (PRR)	0	0	0	0	0	0	0	0	0	0	0	0	0			
X:\$FF9E Reset = \$0000		\$	0			\$	0			\$(0	•		•		
Read/Write																

	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
GPIO Port Data		*	*	*	*	*	*	*	*	*	*	*	*	PD2	PD1	PD0
Register (PDR) X:\$FF9D	0	0	0	0	0	0	0	0	0	0	0	0	0			
Reset = \$0007 Read/Write		\$	0			\$	0			\$	0					

^{* =} Reserved, Program as 0






Freescale Semiconductor, Inc.

Programmer's Reference

Application:_	Date:	
	Programmer:_	
	<u> </u>	01



* = Reserved, Program as 0



Applic	ation:											Date	e:				
• •												Prod	gram	mer:			
													J			eet 4 c	of 4
									I IN	1/			Dos	criptio	n .		
Ш	imer0									0	Timer	increm				sitions	
										1	Timer						
TRM	Description								-		rter Bit						
0	Timer is free-runnin			DIR		cription					rmation			0 011 p			
1	Timer reloads when value is reached	TCR	.		TIO pi TIO pi						TCIE			Descr	iption		
TOF	Description	1	[·	110 рі		T			F	0	Time	r Com	pare l	nterru	pt disa	bled
	Description (bit is cleared)				Data lı						1	Time	er Com	pare	Interru	pt ena	bled
-	Timer Overflow deter	cted		-	DI)—B page 9						TOIE			Desci	iption		
		╗	Į			\top					0	Time				pt disa	bled
TCF	Description			ata O							1	-				pt enal	
0	(bit is cleared)		-	age 9									_ ['		
1	Timer has reached value in TCR									Γ,	Timer N	/lode	7	TE	De	scripti	ion
										ď	Control	Bits		0		er disal	
PCE	Description										ee Tab n page			1	Time	er enab	oled
1	Prescaler disabled									L	ii page	3-10	J L			\neg	\top
1	Prescaler enabled	\forall	\forall	\	₩	\forall	\forall	\forall	¥	_			$\overline{}$		\	\forall	\forall
	mer 0 Control/	15 PCE	14 TCF	13 TOF	12 DO	11 DI	10 DIR	9 TRM	8 INV	7 TC3	6 TC2	5 TC1	4 TC0	3	2 TCIE	1 TOIE	0 TE
S	tatus Register	PCE	ICF	TOF	ВО	וט	DIK	I KIVI	IINV	103	102	101	100		ICIE	TOIL	IE
	(TCSR0) X:\$FF8F													0			
	Reset = \$0000																
	Read/Write L	15	14	13	12	11	10	9	8		6	5	4	. 3	2	1	0
	Timer 0 Load	13	14	13	12	11			0	<u> </u>	Т		-	3	<u> </u>		
R	Register (TLR0)																
Reset	X:\$FF8E = Uninitialized																
10001	Write-Only																
		15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
	ner 0 Compare																
ĸe	gister (TCPR0) X:\$FF8D																
Reset	= Uninitialized																
	Read/Write	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
	Timer 0 Count	.,	• •				.,			†	T			<u> </u>	_ <u> </u>	\Box	
R	egister (TCR0)																
	X:\$FF8C]			l				1]		I		
	Reset = \$0000 Read-Only																
	-	= R	eser	ved,	Progi	am a	as 0										



Semiconductor, Inc.



Freescale Semiconductor, Inc.

Programmer's Reference

Application:	Date:
	Programmer:

Sheet 4 of 4 INV Description imer1 0 Timer increments on rising transitions Timer increments on falling transitions TRM Description See Inverter Bit (INV)-Bit 8 on page 9-11 for DIR Description 0 Timer is free-running more information. TIO pin is input Timer reloads when TCR TCIE Description value is reached TIO pin is output Timer Compare Interrupt disabled **TOF** Description See Data Input Timer Compare Interrupt enabled 0 (bit is cleared) Bit (DI)-Bit 11 Timer Overflow detected on page 9-12 1 TOIE Description 0 Timer Overflow Interrupt disabled **TCF** Description See Data Output Timer Overflow Interrupt enabled 1 Bit (DO)-Bit 12 (bit is cleared) on page 9-12 Timer has reached value in TCR **Timer Mode** Description **Control Bits** Timer disabled PCE Description See Table 9-2 Timer enabled on page 9-10 Prescaler disabled Prescaler enabled 14 13 12 11 10 0 5 Timer 1 Control/_ TCF TOF DO DI DIR TRM INV TC3 TC2 TC1 TC0 TCIE TOIE TE Status Register (TCSR1) 0 X:\$FF8B Reset = \$0000Read/Write 12₁ 10 13 11 Timer 1 Load Register (TLR1) X:\$FF8A Reset = Uninitialized Write-Only 15 14 13 12₁ 11 10 9 8 7 6 5 4 2 0 3 **Timer 1 Compare** Register (TCPR1) X:\$FF89 Reset = Uninitialized Read/Write 15 14 13 12 9 8 4 0 11 10 5 **Timer 1 Count** Register (TCR1) X:\$FF88 Reset = \$0000Read-Only * = Reserved, Program as 0



Programmer's Reference

Application:										_	Date	:				
											Prog	ramr	ner.			
											1 109	Iuiii		She	eet 4 o	f 4
									\I\/				!4!			
Timer2									VV	Timor	incron		cripti		ncition	_
THICIZ	12							1	Timer increments on rising transitions Timer increments on falling transitions							
TRM Description	on															
0 Timer is free-running		DIR Description						See Inverter Bit (INV)—Bit 8 on page 9-11 for more information.								
1 Timer reloads when value is reached	TCR	R 0 TIO pin is input 1 TIO pin is output							TCIE Description							
TOF Description								\blacksquare	0 Timer Compare Interrupt disal						abled	
0 (bit is cleared)	See Data Input								1	Time	er Com	npare	Interru	upt ena	bled	
1 Timer Overflow detect	ected Bit (DI)—Bit 11 on page 9-12								TOIE Description							
TCF Description	1 [See C	Data C	utput	1					0	Time	er Ove	rflow	Interru	ıpt disa	bled
0 (bit is cleared)		Bit (C	00)—	Bit 12						1	Time	er Ove	rflow	Interru	ıpt ena	bled
1 Timer has reached] L	on p	page 9	9-12]							Пl				
value in TCR										imer M ontrol			TE		escript	
PCE Description									_	e Tabl			1		er disa er enal	
0 Prescaler disabled	7								or	n page	9-10		'	111116	=1 enai	l
1 Prescaler enabled	\	Ų .	Ų .	\downarrow	Ų .	Ų .	\downarrow									Ų .
	15	14	13	12	11	10	9	8	7	6	5	4	3	<u>2</u>	1	ŏ
Status Register	CE	TCF	TOF	DO	DI	DIR	TRM	INV	TC3	TC2	TC1	TC0	*	TCIE	TOIE	TE
(TCSR2) X:\$FF87													0			
Reset = \$0000																
Read/Write └─																
Timer 2 Load ☐	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
Register (TLR2)																
X:\$FF86_																
Reset = Uninitialized Write-Only																
	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
Timer 2 Compare																
Register (TCPR2) X:\$FF85																
Reset = Uninitialized				•												
Read/Write	15	14	13	12	11	10	9	8	7	6	5	4	3	2	1	0
Timer 2 Count																
Register (TCR2)																
X:\$FF84							ıl				ļ			L		
Read-Only																
*.	_ D	ocor	hav	Prog	ram 1	ac Λ										



INDEX

A	BT0-BT1 bits 10-15
	Bus Control Ground signal (GND _C) 2-6
A0-A15 signals 2-11	Bus Control Power signal (V _{CCC}) 2-5
adder	Bus Control Register (BCR) 4-8, 5-7
modulo 1-8	Bus Switch Program Memory Register
offset 1-8	(BPMR) 5-8
reverse-carry 1-8	buses
Address Bus Ground signal (GND _A) 2-6	internal 1-11
Address Bus Power signal (V_{CCA}) 2-5	BYPASS instruction 11-12
Address Bus signals (A0–A15) 2-11	
Address Bus—A0–A15 5-3	C
address generation unit 1-8	-
Address Trace Enable bit (ATE) 4-6	CC00-CC01 bits 10-13
	CC10-CC11 bits 10-14
Address Trace signal (AT) 2-11, 5-4	CCR register 4-7
Address Tracing (AT) mode 5-11	Chip Operating Mode bits (MD,MC, MB, and
AGU 1-8	MA) 4-4
Asynchronous/Synchronous bit (SYN) 8-14	Chip Operating Modes 4-9
AT mode 5-11	CKP bit 8-15
AT signal 2-11, 5-4	CLAMP instruction 11-10
ATE bit 4-6	CLKOUT signal 2-7
В	Clock Output Disable bit (COD) 4-20
В	Clock Output signal (CLKOUT) 2-7
BA3-BA10 bits 7-17	Clock Polarity bit (CKP) 8-15
	Clock signals 2-7
Base Address bits (BA3–BA10) 7-17	Clock Source Direction bit (SCKD) 8-15
BCR register 4-8, 5-7	
bits 0-4—Expansion Bus Memory Wait bits	COD bit 4-20
(BMW0-BMW4) 5-7	Command Vector Register (CVR) 7-25
reserved bits—bits 5–15 5-8	Condition Code Register (CCR) 4-7
BMPR register 5-8	configuration
BMW0-BMW4 bits 5-7	GPIO 6-3
Boundary Scan Register (BSR) 11-7	Core Status bits (OS0–OS1) 10-9
BPMR register	CRA register 8-7
16-bit access 5-9	bits 0-7—Prescale Modulus Select bits
24-bit access 5-9	(PM0-PM7) 8-8
mapping 5-8	bits 8–12—Frame Rate Divider Control bits
typical usage 5-9	(DC4-DC0) 8-8
Breakpoint 0 and 1 Event bits (BT0-BT1) 10-15	bits 13–14—Word Length Control bits
Breakpoint 0 Condition Code Select bits	(WL0-WL1) 8-8
(CC00–CC01) 10-13	bit 15—Prescaler Range bit (PSR) 8-9
Breakpoint 0 Read/Write Select bits	CRB register
(RW00–RW01) 10-13	bit 0—Serial Output Flag 0 bit (OF0) 8-10
Breakpoint 1 Condition Code Select bits	bit 1—Serial Output Flag 1 bit (OF1) 8-10
(CC10-CC11) 10-14	bit 8—Transmit Enable bit (TE) 8-10
Breakpoint 1 Read/Write Select bits	bit 9—Receive Enable bit (RE) 8-12
(RW10-RW11) 10-14	bit 10—Transmit Interrupt Enable bit
BSR bit definitions 11-13	(TIE) 8-12
BSR register 11-7	





D

bit 11—Receive Interrupt Enable bit
(RIE) 8-12
bit 12—Transmit Last Slot Interrupt Enable
bit (TLIE) 8-12
bit 13—Receive Last Slot Interrupt Enable bit
(RLIE) 8-13
bit 14—Transmit Exception Interrupt Enable
bit (TEIE) 8-13
bit 15—Receive Exception Interrupt Enable
bit (REIE) 8-13
reserved bits—bits 2-7 8-10
CRC register
bit 0—Asynchronous/Synchronous bit
(SYN) 8-14
bit 1—SSI Mode Select bit (MOD) 8-14
bit 2—Serial Control 0 Direction bit
(SCD0) 8-14
bit 3—Serial Control 1 Direction bit
(SCD1) 8-14
bit 4—Serial Control 2 Direction bit
(SCD2) 8-14
bit 5—Clock Source Direction bit
(SCKD) 8-15
bit 6—Clock Polarity bit (CKP) 8-15
bit 7—Shift Direction bit (SHFD) 8-15
bits 12-13—Frame Sync Length bits
(FSL1-FSL0) 8-15
bit 14—Frame Sync Relative Timing bit
(FSR) 8-16
bit 15—Frame Sync Polarity bit (FSP) 8-16
reserved bits—bits 8–11 8-15
Crystal Output signal (XTAL) 2-7
Crystal Range bit (XTLR) 4-19
CVR register 7-25
bits 0–6—Host Vector bits (HV0–HV6) 7-25
hit 7—Host Command hit (HC) 7-26

D

D0–D23 signals 2-11 data ALU 1-7 Data Bus Ground signal (GND_D) 2-6 Data Bus Power signal (V_{CCD}) 2-5 Data Bus Power signal (V_{CCH}) 2-5 Data Bus signals (A0–A15) 2-11 Data Bus—D0–D23 5-3 Data Input bit (DI) 9-12 Data Output bit (DO) 9-12 DC4–DC0 bits 8-8

DE signal 2-26, 10-4 Debug Event signal (DE signal) 2-26, 10-4 Debug mode in OnCE module 10-17 DEBUG_REQUEST instruction 11-11 executing during Stop state 10-18 executing during Wait state 10-18 executing in OnCE module 10-18 Device Identification Register (IDR) 4-8 DF2-DF0 bits 4-19 DI bit 9-12 **DIR bit 9-11** Direction bit (DIR) 9-11 Division Factor bits (DF2-DF0) 4-19 DO bit 9-12 Double Host Request bit (HDRQ) 7-24

Ε

EBD bit 4-5 EN bit 4-6 **ENABLE ONCE instruction 11-11** EOV bit 4-6 EUN bit 4-5 EX bit 10-7 Exit Command bit (EX) 10-7 Expanded Mode (Mode 0) 4-10 **Expansion Bus Memory Wait bits** (BMW0-BMW4) 5-7 **Expansion Port signals 2-11** Expansion Port, Port A pins 2-11 EXTAL signal 2-7 Extended Stack Enable bit (EN) 4-6 Extended Stack Overflow bit (EOV) 4-6 Extended Stack Underflow bit (EUN) 4-5 Extended Stack Wrap bit (WR) 4-6 External Bus Disable bit (EBD) 4-5 External Clock/Crystal Input signal (EXTAL) 2-7 **EXTEST instruction 11-9**

F

Frame Rate Divider Control bits (DC4–DC0) 8-8 Frame Sync Length bits (FSL1–FSL0) 8-15 Frame Sync Polarity bit (FSP) 8-16 Frame Sync Relative Timing bit (FSR) 8-16 FSL1–FSL0 bits 8-15 FSP bit 8-16 FSR bit 8-16





Freescale Semiconductor, Inc.

General Purpose I/O (GPIO) port 6-3 General Purpose I/O 0 signal (GPI00) 2-24 General Purpose I/O 1 signal (GPI01) 2-24 General Purpose I/O 2 signal (GPI02) 2-24 General Purpose I/O 3 signal (GPI02) 2-24 General Purpose I/O 5 signals 2-24 General Purpose I/O 5 signals 2-24 Global Data Bus 1-12 GND _A signal 2-6 GND _C signal 2-6 GND _C signal 2-6 GND _D signal 2-7 GND _S signal 2-7 GND _S signal 2-7 GPIO0 signal 2-24 GPI01 signal 2-24 GPI02 signal 2-24 GPIO1 1-14 Configuration 6-3 in H108 7-30 GPIO signals 2-24 GPIO signals 2-14 HA0 signal 2-16 HA0 signal 2-16 HA0 signal 2-16 HA1 signal 2-14 HA8 signal 2-14 HIOS Command Interrupt Enable bit (HTIE) 7-9 bit 2—Host Command Interrupt Enable bit (HTIE) 7-9 bit 2—Host Command Interrupt Enable bit (HTIE) 7-9 bit 2—Host Command Interrupt Enable bit (HCIE) 7-9 bit 3 2—Host Command Interrupt Enable bit (HCIE) 7-9 bit 3 2—Host Command Interrupt Enable bit (HCIE) 7-9 bits 3—Host Command Interrupt Enable bit (HCIE) 7-9 bits 3—Host Command Interrupt Enable bit (HCIE) 7-9 bits 3—Host Flag 2 and 3 bits (HF2, HF3) t-10 reserved bits—bits 5-15 7-10 HCS signal 2-16 HCSEN bit 7-13 HDS signal 2-16 HDDR register 7-16 HDDS bit 7-14 HDR register 7-16 HDDF reserved bits—bits 5-15 7-10 HES bit 7-14 HDR register 7-16 HCSEN bit 7-12 HDS signal 2-16 HCSEN bit 7-13 HDDR reserved bits—bits 5-15 7-10 HCS signal 2-16 HCSEN bit 7-14 HF2 bit 7-15 HDDR reserved bits—bits 6-15 7-10 HCS signal 2-16 HCSEN bit 7-14 HDS bit 1—Host Command Interrupt Enable bit (HCIE) 7-9 bits 3—Host Plag 2 and 3 bits (HF2, HF3) 7-10 reserved bits—bits—bits 6-15 7-10 HCS bits 3—HF3 bit 7-15 HDDR register 9-16 HCSEN bit 7-14 HDS bit 7-14	G	bit 0—Host Receive Interrupt Enable bit (HRIE) 7-9
General Purpose I/O 1 signal (GPI00) 2-24 General Purpose I/O 2 signal (GPI00) 2-24 General Purpose I/O 3 signal 2-24 General Purpose I/O 3 signal 2-24 GNDA signal 2-6 GNDC signal 2-6 GNDC signal 2-6 GNDD signal 2-7 GNDS signal 2-24 GPI01 signal 2-24 GPI02 signal 2-24 GPI03 signal 2-24 GPI04 signal 2-14 Configuration 6-3 in H108 7-30 GPIO signals 2-24 Ground signals 2-6 H H H H H H H H H H H H H H H H H H H	General Purpose I/O (GPIO) port 6-3	· · · · · · · · · · · · · · · · · · ·
General Purpose I/O 2 signal (GPI01) 2-24 General Purpose I/O 2 signal (GPI02) 2-24 General Purpose I/O 3 signals 2-24 Global Data Bus 1-12 Global Data Bus 1-12 GND _A signal 2-6 GND _C signal 2-6 GND _D signal 2-7 GND _D signal 2-7 GND _D signal 2-7 GO Command bit (GO) 10-7 GPI00 signal 2-24 GPI01 signal 2-24 GPI01 signal 2-24 GPI01 signal 2-24 GPI02 signal 2-24 GPI02 signal 2-24 GPI03 signal 2-24 GPI04 GPI05 signal 2-24 GPI06 signal 2-24 GPI07 signal 2-24 GPI08 signal 2-24 GPI09 signal 2-25 GPI09 signal 2-26 GPI09 signal 2-26 GPI09 signal 2-27 GPI09 signal 2-29 GPI09 signal 2-20 GPI09 signal (FI09 signal (FI09 signal (FI09 signal (FI08 signal (FI09 signal (FI08 signal signal (FI09 signal (FI		
General Purpose I/O 2 signals (GPl02) 2-24 General Purpose I/O 2 signals 2-24 General Purpose I/O signals 2-24 General Purpose I/O signals 2-24 Gibsal Data Bus 1-12 GND, signal 2-6 GND _C signal 2-7 GND _C signal 2-14 GPI01 signal 2-24 GPI02 signal 2-24 GPI03 signal 2-24 GPI03 signal 2-24 GPI04 GPI07 signal 2-24 GPI08 signal 2-24 GPI0		
General Purpose I/O signals 2-24 Global Data Bus 1-12 Global Data Bus 1-12 GND ₂ signal 2-6 GND ₂ signal 2-6 GND ₃ signal 2-6 GND ₅ signal 2-6 GND ₅ signal 2-6 GND ₆ signal 2-6 GND ₇ signal 2-6 GND ₈ signal 2-7 GND ₈ signal 2-7 GND ₈ signal 2-7 GND ₉ signal 2-7 GND ₉ signal 2-7 GO Command bit (GO) 10-7 GP100 signal 2-24 GP101 signal 2-24 GP102 signal 2-24 GP102 signal 2-24 GP103 signal 2-24 GP101 signal 2-24 GP102 signal 2-24 GP103 signal 2-24 GP105 signal 2-24 GP106 signal 2-24 GP107 signal 2-24 GP108 signal 2-14 HEN bit 7-13 HF1 bit 7-24 GP109 signal 2-24 Ground signals 2-6 HF2 bit 7-27 HGEN bit 7-12 HA8 signal 2-14 HA8 signal 2-14 HA8 signal 2-14 HA8 signal 2-14 HA9 signal 2-14 HA9 signal 2-14 HA9 signal 2-14 HA9 signal 2-17 HA9 signal 2-17 HA9 signal 2-17 HAD0-HAD7 signals 2-13 HAEN bit 7-12 HACK signal 2-17 HABO-HAD7 signals 2-13 HAP bit 7-16 HBAR register 7-17 bits 0-7-Base Address bits (BA3-BA10) 7-17 reserved bits—bits 5-15 7-17 HC bit 7-26 HCE bit 7-9 HOST Point Signal (HAB) 2-14 HOST Address Bus signals (HAD0) 2-13 HOST Point 10 signal (HAA0) 2-14 HOST Address Input 1 signal (HAO1) 2-16		•
HF3) 7-10		
GND _A signal 2-6 GND _C signal 2-6 GND _D signal 2-7 GND _S signal 2-14 GPI00 signal 2-24 GPI01 signal 2-24 GPI02 signal 2-24 GPI01 signal 2-24 GPI02 signal 2-24 GPI03 signal 2-24 GPI04 GPI05 signal 2-24 GPI05 signal 2-24 GPI06 signal 2-24 GPI07 signal 2-24 GPI08 signal 2-24 GPI08 signal 2-24 GPI09		
GND _C signal 2-6 GND _D signal 2-7 GND _D signal 2-14 GPI00 signal 2-24 GPI00 signal 2-24 GPI01 signal 2-24 GPI02 signal 2-24 GPI02 signal 2-24 GPI03 signal 2-24 GPI0 signal 2-14 GPI0 signal 2-15 HF1 bit 7-27 GPI0 signal 2-16 HF2 bit 7-27 GPI0 signal 2-16 HF2 bit 7-27 GPI0 signal 2-16 HF2 bit 7-27 GPI0 signal 2-16 HF3 bit 7-12 HI08 HA0 signal 2-13 HA1 signal 2-14 HA10 signal 2-14 HA3 signal 2-14 HA8 signal 2-14 HA8 signal 2-14 HA8 signal 2-14 HA9 signal 2-14 HA9 signal 2-14 HA9 signal 2-14 HA9 signal 2-17 HADD-HAD7 signals 2-13 HAEN bit 7-12 HADD-HAD7 signals 2-13 HAEN bit 7-16 HACK signal 2-13 HAP bit 7-16 HAP bit 7-17 HOS Address Bits signal (HAB) 2-14 HOS Address Bipal (HAB) 2-14 HOS Address Input 1 signal (HAD) 2-13 HOS Address Input 1 signal (HAD) 2-14 HOS Address Input 1 signal (HAD) 2-14 HOS Address Input 1 signal (HAD) 2-16 HOS Address Input 1 signal (HAD) 2-16 HOS Address Input 1 signal (HAD) 2-16		•
GND _D signal 2-6 GND _H signal 2-6 GND _D signal 2-6 GND _Q signal 2-7 GND _S signal 2-17 GND _S signal 2-18 GND _M signal 2-24 GND _S signal 2-15 GPI00 signal 2-24 GPI01 signal 2-24 GPI01 signal 2-24 GPI02 signal 2-24 GPI02 signal 2-24 GPI03 signal 2-24 GPI04 signal 2-14 HNB _S signal 2-14 HNB _S signal 2-14 HNB _S signal 2-13 HA1 signal 2-14 HA10 signal 2-16 HA2 signal 2-14 HA3 signal 2-14 HA3 signal 2-14 HA4BSN bit 7-12 HA9 signal 2-14 HA9 Signal 2-14 HA9 Signal 2-17 HAS signal 2-17 HAB Signal 2-17 HAB Signal 2-18 HASP bit 7-12 HADO-HAD7 signals 2-13 HAEN bit 7-13 HAP bit 7-13 HAP bit 7-13 HABAR register 7-17 bits 0-7—Base Address bits (BA3-BA10 7-17 reserved bits—bits 5-15 7-17 HC bit 7-26 HCIE bit 7-9 Host Address Input 10 signal (HA0) 2-13 HOSt Address Input 10 signal (HA0) 2-14 HOSt Address Input 10 signal (HA0) 2-16	•	
GND _H signal 2-6 GND _D signal 2-6 GND _D signal 2-7 GND _D signal 2-14 GND _D signal 2-24 GPI00 signal 2-24 GPI01 signal 2-24 GPI02 signal 2-24 GPI02 signal 2-24 GPI02 signal 2-24 GPI03 signal 2-24 GPI04 HF0 bit 7-13 GPI0 1-14 Configuration 6-3 In HI08 7-30 GPIO signals 2-24 GPIO signals 2-24 GPIO signals 2-24 GPIO signals 2-24 GPIO signals 2-14 HF0 bit 7-27 GROCH GPIO signals 2-16 HF1 bit 7-27 GROCH GPIO signals 2-16 HF2 bit 7-27 GROCH GPIO signals 2-16 HF3 bit 7-12 HI08 HA0 signal 2-13 HA1 signal 2-14 HA10 signal 2-16 HA2 signal 2-14 HA3 signal 2-14 HA8 signal 2-14 HA8 signal 2-14 HA8 signal 2-14 HA8 signal 2-14 HA9 signal 2-15 HA9 signal 2-17 HAD0-HAD7 signals 2-13 HACK signal 2-17 HAD0-HAD7 signals 2-13 HAEN bit 7-12 HI08 Status Register (HDR) 7-16 HAP bit 7-16 HAP bit 7-16 HAP bit 7-16 HAR signal 2-13 HASP bit 7-14 HBAR register 7-17 bits 0-7—Base Address bits (BA3-BA10) 7-17 Host Address signal (HAB) 2-14 HCB bit 7-26 HCE bit 7-9 HOST Address signal (HAB) 2-14 HOST Address signals (HAD0) -HAD7) 2-13 HOST Address signals (HAD0) -14 HOST Address sipnut 0 signal (HAO1) 2-16 HOST Address input 10 signal (HAO1) 2-16 HOST Address input 10 signal (HAO1) 2-16		
GNDp signal 2-6 GNDq signal 2-7 GNDg signal 2-7 GO Command bit (GO) 10-7 GP100 signal 2-24 GP100 signal 2-24 GP101 signal 2-25 GP101 signal 2-24 GP101 signal 2-26 GP101 signal 2-26 GP101 signal 2-26 GP101 signal 2-27 GP101 signal 2-26 GP101 signal 2-26 GP101 signal 2-26 GP101 signal 2-27 GP101 signal 2-26 GP101 signal 2-27 GP101 signal 2-26 GP101 signal 2-26 GP101 signal 2-27 GP101 signal 2-26 GP101 signal 2-26 GP101 signal 2-27 GP101 signal 2-26 GP101 signal 2-16 HP101 signa		
GNDQ signal 2-7 GNDg signal 2-7 GNDg signal 2-7 GNDg signal 2-7 GNDg signal 2-7 GP100 signal 2-24 GP101 signal 2-24 GP101 signal 2-24 GP101 signal 2-24 GP102 signal 2-24 GP103 signal 2-24 GP101 signal 2-21 GP101 signal 2-22 GP101 signal 2-23 HP2 bit 7-24 HP3 bit 7-27 HP3 bit 7-24 HP3 signal 2-13 HP3 signal 2-14 HP3 signal 2-	11 0	
GND _S signal 2-7 GO Command bit (GO) 10-7 GO Command bit (GO) 10-7 GO Command bit (GO) 10-7 GP100 signal 2-24 GP101 signal 2-24 GP102 signal 2-24 GP102 signal 2-24 GP102 signal 2-24 GP102 signal 2-24 GP103 signal 2-24 GP104 GP105 signal 2-24 GP105 signal 2-24 GP106 signal 2-24 GP107 signal 2-24 GP108 signal 2-24 GP109 signal 2-26 HF2 bit 7-27 HF2 bit 7-27 HF2 bit 7-27 HF2 bit 7-27 HF3 bit 7-27 HF3 bit 7-27 HF3 bit 7-12 HF3 bit 7-12 HF3 bit 7-12 HF3 bit 7-13 HF3 bit 7-13 HF3 bit 7-13 HF3 bit 7-13 HF3 bit 7-14 HF3 bit 7-15 HF3 bit 7-15 HF3 bit 7-16 HF2 bit 7-16 HF3 b		
GO Command bit (GO) 10-7 GP100 signal 2-24 GP101 signal 2-24 GP102 signal 2-24 HDS pit 7-14 GP102 signal 2-24 GP103 signal 2-24 GP101 signal 2-24 HEN bit 7-13 GP10 1-14 CONFIGURATION C		
GP100 signal 2-24 GP101 signal 2-24 GP101 signal 2-24 GP101 signal 2-24 GP102 signal 2-24 HEN bit 7-13 GP10 1-14 configuration 6-3 in H108 7-30 GP10 signals 2-24 GP10 signals 2-26 HF2 bit 7-27 GP10 signals 2-26 HF2 bit 7-27 HF2 bit 7-27 HF3 bits 7-10 HF3 bit 7-27 HF2 bit 7-27 HF3 bits 7-10 HF3 bit 7-12 HI08 Gata transfer 7-31 polling 7-31 servicing interrupts 7-32 servicing interrupts 7-32 HI08 Dasa Address Register (HBAR) 7-17 HI08 Control Register (HCR 7-8 HI08 Data Register (HDR) 7-16 HA9 signal 2-14 HI08 Data Register (HDR) 7-16 HI08 Data Register (HDR) 7-16 HI08 Data Register (HDR) 7-16 HI08 signals 2-13 HI08 Status Register (HSR) 7-10 HI08 signals 2-13 HI08 Status Register (HSR) 7-10 HI08 Transmit Data Register (HTX) 7-19 HI-Z instruction 11-11 HI-Z instruct		
GP101 signal 2-24 GP102 signal 2-24 GP102 signal 2-24 GP102 signal 2-24 GP10 1-14 Configuration 6-3		
GP102 signal 2-24 GP10 1-14	9	<u> </u>
GPIO 1-14	9	
configuration 6-3 in HI08 7-30 HF1 bits 7-11 in HI08 7-30 HF2 bit 7-24 GPIO signals 2-24 HF2 bit 7-27 Ground signals 2-6 HF2, HF3 bits 7-10 HF3 bit 7-27 H HA0 signal 2-13 HGEN bit 7-12 HI08 HA1 signal 2-14 HI08 HA1 signal 2-16 servicing interrupts 7-32 servicing interrupts 7-32 HA2 signal 2-14 HI08 Base Address Register (HBAR) 7-17 HA8 signal 2-14 HI08 Control Register (HCR 7-8 HA8EN bit 7-12 HI08 Data Direction Register (HDDR) 7-16 HA9EN bit 7-12 HI08 Receive Data Register (HDR) 7-16 HA9EN bit 7-12 HI08 Receive Data Register (HRX) 7-18 HACK signal 2-17 HI08 signals 2-13 HI08 Status Register (HSR) 7-10 HAPD bit 7-16 HI08 Transmit Data Register (HTX) 7-19 HAP bit 7-16 HI08 Transmit Data Register (HTX) 7-19 HASP bit 7-14 HOSE Signal 2-13 HI08 Status Register (HSR) 7-10 HASP bit 7-14 HOSE Signal 2-13 HI08 Status Register (HSR) 7-10 HASP bit 7-14 HOSE Signal 2-13 HI08 Status Register (HSR) 7-10 HASP bit 7-14 HOSE Signal 2-13 HI08 Transmit Data Register (HTX) 7-19 HASP bit 7-14 HOSE Acknowledge Polarity bit (HAP) 7-13 HBAR register 7-17 Host Acknowledge Fnable bit (HAEN) 7-13 HBAR register 7-17 Host Acknowledge Fnable bit (HAEN) 7-13 HBAR register 7-17 Host Acknowledge signal (HAO) 2-17 reserved bits—bits 5-15 7-17 Host Address 8 signal (HAB) 2-14 HC bit 7-9 Host Address Bus signals (HADO) 2-13 HCP bit 7-11 Host Address Input 1 signal (HAO1) 2-14 HCR register Host Address Input 10 signal (HAO1) 2-16	9	_
in HI08 7-30 GPIO signals 2-24 GPIO signals 2-24 Ground signals 2-6 HF2 bit 7-27 Ground signals 2-6 HF2 bit 7-27 HF3 bits 7-10 HF3 bit 7-12 HI08 HA0 signal 2-13 HA1 signal 2-14 HA10 signal 2-16 HA2 signal 2-14 HA3 signal 2-14 HA8 signal 2-14 HA8 signal 2-14 HA8 signal 2-14 HA9 Signal 2-14 HO8 Data Direction Register (HBAR) 7-17 HA9 Data Direction Register (HDR) 7-16 HA9 Data Direction Register (HDR) 7-16 HA9EN bit 7-12 HI08 Data Register (HDR) 7-16 HO8 Data Register (HRX) 7-18 HO8 Data Register (HRX) 7-18 HO9 Data Register (HSR) 7-10 HI08 Signals 2-13 HI08 Status Register (HSR) 7-10 HAP bit 7-13 HAD bit 7-13 HAP bit 7-14 HAS signal 2-13 HMUX bit 7-14 HAS signal 2-13 HMUX bit 7-14 HAS register 7-17 bits 0-7—Base Address bits (BA3-BA10) 7-17 reserved bits—bits 5-15 7-17 HC bit 7-26 HO5 Address 8 signal (HA8) 2-14 HO5 Address 9 signal (HA0) 2-13 HCP bit 7-11 HO5 Address Input 0 signal (HA01) 2-16 HO5 Address Input 10 signal (HA01) 2-16		
GPIO signals 2-24 Ground signals 2-6 HF2, HF3 bits 7-10 HF3 bit 7-27 HGEN bit 7-12 HH08 HA0 signal 2-13 HA1 signal 2-14 HA10 signal 2-16 HA2 signal 2-16 HA3 signal 2-14 HA8 signal 2-14 HA8 signal 2-14 HA8 signal 2-14 HA9 signal 2-14 HA9 signal 2-14 HB8 Base Address Register (HBAR) 7-17 HA8 signal 2-14 HB9 Data Direction Register (HDDR) 7-16 HA9 signal 2-14 HB9 Data Register (HDR) 7-16 HA99EN bit 7-12 HB08 Data Register (HDR) 7-16 HA99EN bit 7-12 HB08 Data Register (HDR) 7-16 HB08 Signals 2-13 HB08 Status Register (HSR) 7-10 HB08 Status Register (HSR) 7-10 HB08 Transmit Data Register (HTX) 7-19 HAP bit 7-16 HB4 HB5 Transmit Data Register (HTX) 7-19 HB4 Signal 2-13 HB4 Fregister 7-17 bits 0-7—Base Address bits (BA3-BA10) 7-17 reserved bits—bits 5-15 7-17 HC bit 7-26 HO8 Address Bus signals (HAB) 2-14 HCS register HO8 Address Input 1 signal (HA01) 2-16 HO8 Address Input 10 signal (HA01) 2-16	9	
HF2, HF3 bits 7-10		
HF3 bit 7-27 HGEN bit 7-12 HI08 HA0 signal 2-13 HA1 signal 2-14 HA10 signal 2-16 HA2 signal 2-16 HA2 signal 2-14 HA8 signal 2-14 HA9 bit 7-12 HA9 signal 2-14 HA9 bit 7-12 HA9 signal 2-17 HA9 signal 2-17 HANDO-HAD7 signals 2-13 HADNO-HAD7 signals 2-13 HAEN bit 7-13 HAEN bit 7-16 HAFD bit 7-16 HOST Acknowledge Enable bit (HAFN) 7-16 HOST Acknowledge signal (HAFN) 2-17 HOST Acknowledge signal (HAFN) 2-17 HOST Address 8 signal (HAFN) 2-14 HOST Address 9 signal (HAFN) 2-13 HCF bit 7-26 HOST Address Input 10 signal (HA01) 2-13 HCF bit 7-11 HOST Address Input 10 signal (HA01) 2-16	9	
HAO signal 2-13 HA1 signal 2-14 HA10 signal 2-15 HA1 signal 2-16 HA2 signal 2-16 HA2 signal 2-14 HA8 signal 2-14 HA8 signal 2-14 HA8 signal 2-14 HA8 signal 2-14 HA9 signal 2-14 HA9 signal 2-14 HA9 signal 2-14 HA9EN bit 7-12 HA9 signal 2-17 HA9 signal 2-17 HAD0-HAD7 signals 2-13 HAD0-HAD7 signals 2-13 HAP bit 7-16 HAP bit 7-16 HARF wire reset signal (RESET) 2-8 HAS signal 2-13 HASP bit 7-14 HASP bit 7-14 HASP bit 7-15 HASP bit 7-16 HASP bit 7-17 BISP bit 7-18 HASP bit 7-18 HASP bit 7-19 HASP bit 7-19 HASP bit 7-16 HASP bit 7-17 BISP bit 7-18 HASP bit 7-18 HASP bit 7-18 HASP bit 7-19 HASP bit 7-14 HASP bit 7-16 HASP bit 7-17 BISP bit 3-17 BISP bit 3-18 BISP bit 3-18 BISP bit 3-18 BISP bit 3-19 B	Ground signals 2-0	
HA0 signal 2-13 HA1 signal 2-14 HA10 signal 2-16 HA2 signal 2-16 HA2 signal 2-14 HA8 signal 2-14 HA8 signal 2-14 HA8 signal 2-14 HA9 signal 2-14 HB9 Base Address Register (HBAR) 7-17 HA9 signal 2-14 HB9 Base Address Register (HDR) 7-16 HA9 signal 2-14 HB9 Base Address Register (HDR) 7-16 HA9 signal 2-14 HB9 Base Address Register (HDR) 7-16 HB9 Base Address Register (HDR) 7-16 HB9 Base Address Bits HB9 Base Address Bits Base Address Bits Bits Address Bits Signal (HAB) 2-14 HBAR register 7-17 Bits 0-7—Base Address bits Base Address Bits Signal (HA8) 2-14 HC bit 7-26 HCE bit 7-9 HOS Base Address Input 10 signal (HA01) 2-16 HCE pit 7-11 HCR register HCR 7-31 HCB Base Address Input 10 signal (HA01) 2-16 HCE bit 7-11 HCR register HOS Base Address Input 10 signal (HA01) 2-16	H	
HA0 signal 2-13	•	
HA1 signal 2-14	HA0 signal 2-13	
HA10 signal 2-16 HA2 signal 2-14 HA8 signal 2-14 HA8 signal 2-14 HA9 signal 2-14 HA9 signal 2-14 HI08 Data Direction Register (HDDR) 7-16 HA9 signal 2-17 HA9 signal 2-17 HAD0-HAD7 signals 2-13 HAD0-HAD7 signals 2-13 HAP bit 7-16 HA9 bit 7-16 HAS signal 2-17 HAS signal 2-18 HI08 Receive Data Register (HRX) 7-18 HI08 Status Register (HSR) 7-10 HAEN bit 7-13 HI08 Transmit Data Register (HTX) 7-19 HAP bit 7-16 HI-Z instruction 11-11 HASP bit 7-14 HASP bit 7-14 HASP bit 7-14 HASP bit 7-14 HASP cister 7-17 bits 0-7—Base Address bits (BA3-BA10) 7-17 reserved bits—bits 5-15 7-17 HOST Address 8 signal (HA8) 2-14 HC bit 7-26 Host Address Bus signals (HAD0-HAD7) 2-13 HCP bit 7-11 HOST Address Input 0 signal (HA01) 2-14 Host Address Input 1 signal (HA01) 2-14 Host Address Input 10 signal (HA01) 2-16	=	
HA2 signal 2-14 HI08 Base Address Register (HBAR) 7-17 HA8 signal 2-14 HI08 Control Register (HCR 7-8 HA8EN bit 7-12 HI08 Data Direction Register (HDDR) 7-16 HA9 signal 2-14 HI08 Data Register (HDR) 7-16 HA9EN bit 7-12 HI08 Receive Data Register (HRX) 7-18 HACK signal 2-17 HI08 signals 2-13 HAD0-HAD7 signals 2-13 HI08 Status Register (HSR) 7-10 HAEN bit 7-13 HI08 Transmit Data Register (HTX) 7-19 HAP bit 7-16 HI-Z instruction 11-11 Hardware reset signal (RESET) 2-8 HLEND bit 7-24 HAS signal 2-13 HMUX bit 7-14 HASP bit 7-14 Host Acknowledge Enable bit (HAEN) 7-13 HBAR register 7-17 Host Acknowledge Polarity bit (HAP) 7-16 bits 0-7—Base Address bits (BA3-BA10) 7-17 Host Address 8 signal (HA8) 2-14 HC bit 7-26 Host Address Bus signals (HA8) 2-14 HC bit 7-9 Host Address Input 0 signal (HA0) 2-13 HCP bit 7-11 Host Address Input 1 signal (HA01) 2-14 HCR register Host Address Input 10 signal (HA10) 2-16		• •
HA8 signal 2-14 HI08 Control Register (HCR 7-8 HA8EN bit 7-12 HI08 Data Direction Register (HDDR) 7-16 HA9 signal 2-14 HI08 Data Register (HDR) 7-16 HA9EN bit 7-12 HI08 Receive Data Register (HRX) 7-18 HACK signal 2-17 HI08 signals 2-13 HAD0-HAD7 signals 2-13 HI08 Status Register (HSR) 7-10 HAEN bit 7-13 HI08 Transmit Data Register (HTX) 7-19 HAP bit 7-16 HI-Z instruction 11-11 Hardware reset signal (RESET) 2-8 HLEND bit 7-24 HAS signal 2-13 HMUX bit 7-14 HASP bit 7-14 Host Acknowledge Enable bit (HAEN) 7-13 HBAR register 7-17 Host Acknowledge Polarity bit (HAP) 7-16 bits 0-7—Base Address bits (BA3-BA10) 7-17 Host Address 8 signal (HAR) 2-14 reserved bits—bits 5-15 7-17 Host Address 9 signal (HA8) 2-14 HC bit 7-26 Host Address Bus signals (HAD0-HAD7) 2-13 HCIE bit 7-9 Host Address Input 0 signal (HA0) 2-13 HCP bit 7-11 Host Address Input 1 signal (HA01) 2-14 HCR register Host Address Input 10 signal (HA10) 2-16	_	· .
HA8EN bit 7-12 HA9 signal 2-14 HA9 signal 2-14 HA9EN bit 7-12 HA0EN bit 7-12 HAD0-HAD7 signals 2-13 HAD0-HAD7 signals 2-13 HAD0-HAD7 signals 2-13 HAP bit 7-13 HAP bit 7-16 HA9 bit 7-16 HA9 bit 7-16 HARW bit 7-16 HARW bit 7-16 HARW bit 7-16 HARW bit 7-16 HAP bit 7-16 HARW bit 7-14 HASP bit 7-17 Bits 0-7—Base Address bits (BA3-BA10) 7-17 Feserved bits—bits 5-15 7-17 HOST Address 8 signal (HA8) 2-14 HC bit 7-26 HOST Address 9 signal (HA8) 2-14 HOST Address 9 signal (HA8) 2-13 HOST Address 9 lignal (HA0) 2-13 HOST Address Input 0 signal (HA0) 2-14 HOST Address Input 1 signal (HA01) 2-14 HOST Address Input 10 signal (HA01) 2-16		9
HA9 signal 2-14 HA9EN bit 7-12 HACK signal 2-17 HAD0-HAD7 signals 2-13 HAD0-HAD7 signals 2-13 HAP bit 7-16 HAFEN bit 7-16 HAFEN bit 7-16 HAFEN bit 7-16 HAFEN bit 7-17 HAP bit 7-16 HAFEN bit 7-17 HAFEN bit 7-18 HAFEN bit 7-18 HAFEN bit 7-19 HAFEN bit 7-19 HAFEN bit 7-14 HAFEN bit 7-14 HAFEN bit 7-14 HAFEN bit 7-14 HAFEN bit 7-15 HAFEN bit 7-17 BAFEN CACHOLOGY BASABALOD 7-17 FENSION BIT SIGNAL	HA8EN bit 7-12	<u> </u>
HA9EN bit 7-12 HACK signal 2-17 HAD0-HAD7 signals 2-13 HAD0-HAD7 signals 2-13 HI08 Status Register (HSR) 7-10 HAEN bit 7-13 HAP bit 7-16 HAFN bit 7-16 HAFN bit 7-16 HAS signal 2-13 HI08 Transmit Data Register (HTX) 7-19 HAP bit 7-16 HI-Z instruction 11-11 HARD bit 7-24 HAS signal 2-13 HMUX bit 7-14 HOST Acknowledge Enable bit (HAEN) 7-13 HBAR register 7-17 bits 0-7—Base Address bits (BA3-BA10) 7-17 reserved bits—bits 5-15 7-17 HOST Address 8 signal (HA8) 2-14 HCB bit 7-26 HOST Address Bus signals (HAD0-HAD7) 2-13 HCIE bit 7-9 HOST Address Input 0 signal (HA01) 2-14 HCR register HOST Address Input 10 signal (HA01) 2-16	HA9 signal 2-14	
HACK signal 2-17 HAD0-HAD7 signals 2-13 HAD0-HAD7 signals 2-13 HI08 Status Register (HSR) 7-10 HAEN bit 7-13 HAP bit 7-16 HI-Z instruction 11-11 Hardware reset signal (RESET) 2-8 HAS signal 2-13 HMUX bit 7-14 HASP bit 7-14 HBAR register 7-17 bits 0-7—Base Address bits (BA3-BA10) 7-17 reserved bits—bits 5-15 7-17 HC bit 7-26 HCIE bit 7-9 HCP bit 7-11 HCR register HI08 signals 2-13 HI08 Status Register (HSR) 7-10 HI08 Transmit Data Register (HTX) 7-19 HI08 Transmit Data Register (HTX) 7-19 HI08 Status Register (HSR) 7-10 HO8 Transmit Data Register (HTX) 7-19 HI08 Status Register (HSR) 7-10 HO8 Transmit Data Register (HTX) 7-19 HI08 Status Register (HSR) 7-10 HO8 Transmit Data Register (HTX) 7-19 HI08 Status Register (HSR) 7-10 HO8 Transmit Data Register (HTX) 7-19 HI08 Status Register (HSR) 7-10 HO8 Transmit Data Register (HSR) 7-10 HI08 Status Register (HSR) 7-10 HO8 Transmit Data Register (HSR) 7-10 HI08 Status Register (HSR) 7-10 HO8 Transmit Data Register (HSR) 7-10 HI08 Status Register (HSR) 7-10 HO8 Transmit Data Register (HSR) 7-10 HI08 Status Register (HSR) 7-10 HO8 Transmit Data Register (HTX) 7-19 HI08 Transmit Data Register (HTX) 7-19 HI08 Transmit Data Register (HTX) 7-19 HI08 Transmit Data Register (HTX) 7-19 HID8 Transmit Data Registe		9
HAD0-HAD7 signals 2-13 HAEN bit 7-13 HAEN bit 7-16 HAP bit 7-16 HI-Z instruction 11-11 Hardware reset signal (RESET) 2-8 HAS7 signal 2-13 HAS9 bit 7-14 HAS9 bit 7-14 HBAR register 7-17 bits 0-7—Base Address bits (BA3-BA10) 7-17 reserved bits—bits 5-15 7-17 HC bit 7-26 HCIE bit 7-9 HCP bit 7-11 HCR register HI08 Status Register (HSR) 7-10 HI08 Transmit Data Register (HTX) 7-19 HI-Z instruction 11-11 HLEND bit 7-24 HLEND bit 7-24 HAS9 bit 7-14 Host Acknowledge Enable bit (HAEN) 7-13 Host Acknowledge Polarity bit (HAP) 7-16 Host Address 8 signal (HAO) 2-17 Host Address 9 signal (HA8) 2-14 Host Address Bus signals (HAD0-HAD7) 2-13 HOST Address Input 0 signal (HA0) 2-13 HOST Address Input 1 signal (HA01) 2-14 Host Address Input 10 signal (HA01) 2-16	HACK signal 2-17	9
HAEN bit 7-13 HAP bit 7-16 HAP bit 7-16 HI-Z instruction 11-11 Hardware reset signal (RESET) 2-8 HAS signal 2-13 HMUX bit 7-14 HASP bit 7-14 HASP bit 7-14 HBAR register 7-17 bits 0-7—Base Address bits (BA3-BA10) 7-17 reserved bits—bits 5-15 7-17 HC bit 7-26 HCIE bit 7-9 HCP bit 7-11 HCR register HI08 Transmit Data Register (HTX) 7-19 HI-Z instruction 11-11 HLEND bit 7-24 HLEND bit 7-24 HMUX bit 7-14 Host Acknowledge Enable bit (HAEN) 7-13 Host Acknowledge Polarity bit (HAP) 7-16 Host Address 8 signal (HAB) 2-17 Host Address 9 signal (HA8) 2-14 Host Address Bus signals (HAD0-HAD7) 2-13 HOST Address Input 0 signal (HA0) 2-13 Host Address Input 1 signal (HA01) 2-14 Host Address Input 10 signal (HA01) 2-16	<u>o</u>	
HAP bit 7-16 Hardware reset signal (RESET) 2-8 HAS signal 2-13 HASP bit 7-14 HASP bit 7-14 HBAR register 7-17 bits 0-7—Base Address bits (BA3-BA10) 7-17 reserved bits—bits 5-15 7-17 HC bit 7-26 HCIE bit 7-9 HCP bit 7-11 HASP bit 7-16 HI-Z instruction 11-11 HLEND bit 7-24 HMUX bit 7-14 HOST Acknowledge Enable bit (HAEN) 7-13 Host Acknowledge Polarity bit (HAP) 7-16 Host Acknowledge signal (HAP) 2-17 Host Address 8 signal (HA8) 2-14 Host Address 9 signal (HA8) 2-14 Host Address Bus signals (HAD0-HAD7) 2-13 HOST Address Input 0 signal (HA0) 2-14 Host Address Input 1 signal (HA01) 2-14 Host Address Input 10 signal (HA01) 2-16		9
Hardware reset signal (RESET) 2-8 HAS signal 2-13 HASP bit 7-14 HASP bit 7-14 HBAR register 7-17 bits 0-7—Base Address bits (BA3-BA10) 7-17 reserved bits—bits 5-15 7-17 HC bit 7-26 HCIE bit 7-9 HCP bit 7-11 HCR register HLEND bit 7-24 HMUX bit 7-24 HMUX bit 7-14 Host Acknowledge Enable bit (HAEN) 7-13 Host Acknowledge Polarity bit (HAP) 7-16 Host Acknowledge signal (HACK) 2-17 Host Address 8 signal (HA8) 2-14 Host Address 9 signal (HA8) 2-14 Host Address Bus signals (HAD0-HAD7) 2-13 Host Address Input 0 signal (HA0) 2-13 Host Address Input 1 signal (HA01) 2-14 Host Address Input 10 signal (HA01) 2-16		
HAS signal 2-13 HMUX bit 7-14 HASP bit 7-14 HBAR register 7-17 bits 0-7—Base Address bits (BA3-BA10) 7-17 reserved bits—bits 5-15 7-17 HC bit 7-26 HCIE bit 7-9 HCP bit 7-11 HCR register HMUX bit 7-14 Host Acknowledge Enable bit (HAEN) 7-13 Host Acknowledge signal (HAEN) 2-17 Host Address 8 signal (HA8) 2-14 Host Address 9 signal (HA8) 2-14 Host Address Bus signals (HAD0-HAD7) 2-13 Host Address Input 0 signal (HA0) 2-13 Host Address Input 1 signal (HA01) 2-14 Host Address Input 10 signal (HA01) 2-16		
HASP bit 7-14 HBAR register 7-17 bits 0-7—Base Address bits (BA3-BA10) 7-17 reserved bits—bits 5-15 7-17 HC bit 7-26 HCIE bit 7-9 HCP bit 7-11 HOST Acknowledge Enable bit (HAEN) 7-13 Host Acknowledge signal (HAECK) 2-17 Host Address 8 signal (HA8) 2-14 Host Address 9 signal (HA8) 2-14 Host Address Bus signals (HAD0-HAD7) 2-13 HOST Address Input 0 signal (HA0) 2-13 Host Address Input 1 signal (HA01) 2-14 Host Address Input 10 signal (HA01) 2-16		
HBAR register 7-17 bits 0-7—Base Address bits (BA3-BA10) 7-17 reserved bits—bits 5-15 7-17 HOST Acknowledge Polarity bit (HAP) 7-16 Host Acknowledge signal (HACK) 2-17 Host Address 8 signal (HA8) 2-14 HC bit 7-26 HCIE bit 7-9 HOST Acknowledge Polarity bit (HAP) 7-16 Host Address 8 signal (HA8) 2-14 Host Address 9 signal (HA8) 2-14 Host Address Bus signals (HAD0-HAD7) 2-13 HCP bit 7-11 Host Address Input 0 signal (HA0) 2-13 HCP register Host Address Input 1 signal (HA01) 2-14 HCR register		
bits 0–7—Base Address bits (BA3–BA10) 7-17 Host Address 8 signal (HA8) 2-14 Host Address 9 signal (HA8) 2-14 HC bit 7-26 HCIE bit 7-9 HCP bit 7-11 HCR register Host Address Input 0 signal (HA0) 2-13 HCR register Host Address Input 1 signal (HA01) 2-14 Host Address Input 10 signal (HA01) 2-16		
(BA3-BA10) 7-17 Host Address 8 signal (HA8) 2-14 reserved bits—bits 5-15 7-17 Host Address 9 signal (HA8) 2-14 HC bit 7-26 Host Address Bus signals (HAD0-HAD7) 2-13 HCIE bit 7-9 Host Address Input 0 signal (HA0) 2-13 HCP bit 7-11 Host Address Input 1 signal (HA01) 2-14 HCR register Host Address Input 10 signal (HA10) 2-16		
reserved bits—bits 5–15 7-17 HOST Address 9 signal (HA8) 2-14 HC bit 7-26 HOST Address Bus signals (HAD0–HAD7) 2-13 HCIE bit 7-9 HOST Address Input 0 signal (HA0) 2-13 HCP bit 7-11 HOST Address Input 1 signal (HA01) 2-14 HCR register HOST Address Input 10 signal (HA10) 2-16		
HC bit 7-26 HOSt Address Bus signals (HAD0-HAD7) 2-13 HCIE bit 7-9 HOSt Address Input 0 signal (HA0) 2-13 HCP bit 7-11 HCR register Host Address Input 1 signal (HA01) 2-14 HCR register Host Address Input 10 signal (HA10) 2-16		
HCIE bit 7-9 Host Address Input 0 signal (HA0) 2-13 HCP bit 7-11 Host Address Input 1 signal (HA01) 2-14 HCR register Host Address Input 10 signal (HA10) 2-16		
HCP bit 7-11 Host Address Input 1 signal (HA01) 2-14 HCR register Host Address Input 10 signal (HA10) 2-16		
HCR register Host Address Input 10 signal (HA10) 2-16		
	0	

G



Н

bit 0—Host GPIO Port Enable bit (HGEN) 7-12 bit 1—Host Address Line 8 bit (HA8EN) 7-12 bit 2—Host Address Line 9 bit (HA9EN) 7-12 HTRQ signal 2-16 HTX register 7-19 (HA9EN) 7-12 HV0-HV6 bits 7-25	Host Address Line 8 Enable bit (HA8EN) 7-12 Host Address Strobe Polarity bit (HASP) 7-14 Host Address Strobe signal (HAS) 2-13 Host Chip Select Enable bit (HCSEN) 7-13 Host Chip Select Enable bit (HCSEN) 7-15 Host Chip Select Signal (HCS) 2-16 Host Command bit (HC) 7-26 Host Command bit (HC) 7-26 Host Command Interrupt Enable bit (HCIE) 7-9 Host Command Pending bit (HCP) 7-11 Host Data Strobe Polarity bit (HDSP) 7-14 Host Data Strobe signal (HDS) 2-15 Host Dual Data Strobe bit (HDDS) 7-14 Host Data Strobe bit (HEN) 7-13 Host Flag 0 and 1 bits (HF0, HF1) 7-11 Host Flag 0 bit (HF0) 7-24 Host Flag 1 bit (HF1) 7-24 Host Flag 2 and 3 bits (HF2, HF3) 7-10 Host Flag 2 bit (HF3) 7-27 Host GPIO Port Enable bit (HGEN) 7-12 Host Ground signal (GND _H) 2-6 Host Interface (HI08) 7-3 Host Interface (HI08) 7-3 Host Little Endian bit (HLEND) 7-24 Host Port Control Register (HPCR) 7-12 host Port Control Register (HPCR) 7-12 host Read Data signal (HRD) 2-15 Host Read Data Full bit (HRDF) 7-10 Host Request Enable bit (HREN) 7-13 Host Request Open Drain bit (HREN) 7-13 Host Request Polarity bit (HREN) 7-15 Host Request Signal (HREQ) 2-16 Host Transmit Interrupt Enable bit (HTIE) 7-9 Host Vector bits (HV0-HV6) 7-25 Host Write Enable Strobe signal (HWR) 2-15	bit 3—Host Chip Select Enable bit (HCSEN) 7-13 bit 4—Host Request Enable bit (HREN) 7-13 bit 5—Host Acknowledge Enable bit (HAEN) 7-13 bit 6—Host Enable bit (HEN) 7-13 bit 8—Host Request Open Drain bit (HROD) 7-14 bit 9—Host Data Strobe Polarity bit (HDSP) 7-14 bit 10—Host Address Strobe Polarity bit (HASP) 7-14 bit 11—Host Multiplexed Bus bit (HMUX) 7-14 bit 12—Host Dual Data Strobe bit (HDDS) 7-14 bit 13—Host Chip Select Polarity bit (HCSP) 7-15 bit 14—Host Request Polarity bit (HRP) 7-15 bit 15—Host Acknowledge Polarity bit (HAP) 7-16 reserved bit—bit 7 7-13 HRD signal 2-15 HRDF bit 7-10 HREN bit 7-13 HREQ signal 2-16 HRIE bit 7-9 HROD bit 7-14 HRP bit 7-15 HRRQ signal 2-17 HRW signal 2-15 HRX register bit 0—Host Receive Data Full bit (HRDF) 7-10 bit 1—Host Transmit Data Empty bit (HTDE) 7-11 bit 2—Host Command Pending bit (HCP) 7-11 bits 3, 4—Host Flag 0 and 1 bits (HF0,
Host Request Open Drain bit (HROD) 7-14 Host Request Polarity bit (HRP) 7-15 Host Request signal (HREQ) 2-16 Host Transmit Data Empty bit (HTDE) 7-11 Host Transmit Interrupt Enable bit (HTIE) 7-9 Host Write Enable Strobe signal (HWR) 2-15 HPCR register bit 0—Host GPIO Port Enable bit (HGEN) 7-12 HTDE bit 7-11 bit 1—Host Address Line 8 bit (HA8EN) 7-12 HTDE bit 7-19 (HA9EN) 7-12 HV0-HV6 bits 7-25 HIDE bit 1—Host Receive Data Full bit (HRDF) 7-10 bit 1—Host Transmit Data Empty bit (HRDF) 7-11 bit 2—Host Command Pending bit (HCP) 7-11 bits 3, 4—Host Flag 0 and 1 bits (HF0, HF1) 7-11 reserved bits—bits 5–15 7-11 HTDE bit 7-11 HTDE bit 7-11 HTDE bit 7-11 HTDE bit 7-9 HTRQ signal 2-16 HTX register 7-19 HTX register 7-19 HV0-HV6 bits 7-25	Host Receive Interrupt Enable bit (HRIE) 7-9	HRX register 7-18
Host Request signal (HREQ) 2-16 Host Transmit Data Empty bit (HTDE) 7-11 Host Transmit Interrupt Enable bit (HTIE) 7-9 Host Vector bits (HV0–HV6) 7-25 Host Write Enable Strobe signal (HWR) 2-15 HPCR register bit 0—Host GPIO Port Enable bit (HGEN) 7-12 HTDE bit 7-9 (HA8EN) 7-12 HTRQ signal 2-16 HTX register 7-19 (HA9EN) 7-12 Ht Designal (HWEQ) 2-16 HIDE bit 1—Host Transmit Data Empty bit (HTDE) 7-11 (HTDE) 7-11 bit 2—Host Command Pending bit (HCP) 7-11 bit 3, 4—Host Flag 0 and 1 bits (HF0, HF1) 7-11 reserved bits—bits 5–15 7-11 HTDE bit 7-9 HTRQ signal 2-16 HTX register 7-19 HV0–HV6 bits 7-25	Host Request Open Drain bit (HROD) 7-14	bit 0—Host Receive Data Full bit
Host Transmit Interrupt Enable bit (HTIE) 7-9 Host Vector bits (HV0–HV6) 7-25 Host Write Enable Strobe signal (HWR) 2-15 HPCR register bit 0—Host GPIO Port Enable bit (HGEN) 7-12 HTDE bit 7-11 bit 1—Host Address Line 8 bit (HA8EN) 7-12 HTRQ signal 2-16 bit 2—Host Address Line 9 bit (HA9EN) 7-12 HTX register 7-19 (HA9EN) 7-12 HTX register 7-25	Host Request signal (HREQ) 2-16	bit 1—Host Transmit Data Empty bit
bit 0—Host GPIO Port Enable bit (HGEN) 7-12 bit 1—Host Address Line 8 bit (HA8EN) 7-12 bit 2—Host Address Line 9 bit (HA9EN) 7-12 HTRQ signal 2-16 HTX register 7-19 (HA9EN) 7-12 HV0-HV6 bits 7-25	Host Transmit Interrupt Enable bit (HTIE) 7-9 Host Vector bits (HV0-HV6) 7-25 Host Write Enable Strobe signal (HWR) 2-15	bit 2—Host Command Pending bit (HCP) 7-11 bits 3, 4—Host Flag 0 and 1 bits (HF0,
(HA8EN) 7-12 HTRQ signal 2-16 bit 2—Host Address Line 9 bit HTX register 7-19 (HA9EN) 7-12 HV0–HV6 bits 7-25	bit 0—Host GPIO Port Enable bit (HGEN) 7-12	reserved bits—bits 5–15 7-11 HTDE bit 7-11
11VV V SIGNAL 7-17	(HA8EN) 7-12 bit 2—Host Address Line 9 bit	HTRQ signal 2-16 HTX register 7-19





•	•
ICR register 7-22 bit 0—Receive Request Enable bit (RREQ) 7-23 bit 1—Transmit Request Enable bit (TREQ) 7-23 bit 2—Double Host Request bit (HDRQ) 7-24 bit 3—Host Flag 0 bit (HF0) 7-24 bit 4—Host Flag 1 bit (HF1) 7-24 bit 5—Host Little Endian bit (HLEND) 7-24 bit 7—Initialize bit (INIT) 7-24 reserved bit—bit 6 7-25 IDCODE instruction 11-9 IDR register 4-8 IF0 bit 8-17 IF1 bit 8-17 IME bit 10-9 INIT bit 7-24 Initialize bit (INIT) 7-24 input and output signals 2-3 Interface Control Register (ICR) 7-22 Interface Status Register (ISR) 7-26	Joint Test Action Group (JTAG) 11-3 JTAG 1-11 JTAG instructions BYPASS instruction 11-12 CLAMP instruction 11-10 DEBUG_REQUEST instruction 11-11 ENABLE_ONCE instruction 11-11 EXTEST instruction 11-9 HI-Z instruction 11-1 IDCODE instruction 11-9 SAMPLE/PRELOAD instruction 11-9 JTAG/OnCE Interface signals 2-26 Debug Event signal (DE signal) 2-26, 10-4 Test Clock signal (TCK) 2-26 Test Data Input signal (TDI) 2-26 Test Data Output signal (TDO) 2-26 Test Mode Select signal (TMS) 2-26 Test Reset signal (TRST) 2-26
internal buses 1-11 Interrupt 10-9	LA register 1-9 LC register 1-9
Interrupt And Mode Control pins 2-8	Loop Address register (LA) 1-9
Interrupt Control signals 2-8	Loop Counter register (LC) 1-9
Interrupt Mode Enable bit (IME) 10-9	М
Interrupt Priority Levels 4-14	IVI
Interrupt Priority Register—Core (IPR-C) 4-14 Interrupt Priority Register—Peripheral (IPR-P) 4-14 interrupt starting address 4-11 Interrupt Vector Register (IVR) 7-28 INV bit 9-11 Inverter bit (INV) 9-11	MAC 1-7 MBO bit 10-9 MBS0-MBS1 bits 10-13 MCS signal 2-11, 5-3 MD,MC, MB, and MA bits 4-4 memory on-chip 1-11
IPR-C register 4-14	Memory Breakpoint Occurrence bit (MBO) 10-9
IPR-P register 4-14 ISR Host Request bit (HREQ) 7-27	Memory Breakpoint Select bits
ISR register 7-26	(MBS0–MBS1) 10-13
bit 0—Receive Data Register Full bit (RXDF) 7-26	memory breakpoints enabling 10-19 Memory Chip Select signal (MCS) 2-11, 5-3
bit 1—Transmit Data Register Empty bit (TXDE) 7-27	memory map description 3-3
bit 2—Transmitter Ready bit (TRDY) 7-27	Memory Switch Mode bit (MS) 4-6
bit 3—Host Flag 2 bit (HF2) 7-27	memory-mapped I/O registers 3-5
bit 4—Host Flag 3 bit (HF3) 7-27	MF0-MF11 bits 4-17 MOD bit 8-14
bit 7—ISR Host Request bit (HREQ) 7-27	MODA/IRQA signal 2-9
reserved bits—bits 5, 6 7-27 IVR register 7-28	MODB/ IRQB signal 2-9 MODC/ IRQC signal 2-10



Ν

MODD/IRQD signal 2-10	OMAC1 comparator 10-12
Mode Control signals 2-8	OMAL register 10-11
Mode Register (MR) 4-7	OMBC counter 10-15
Mode Select A/External Interrupt Request A	OMLR0 register 10-12
signal (MODA/ IRQA) 2-9	OMLR1 register 10-12
Mode Select B/External Interrupt Request B	OMR register 1-9
signal (MODA/ IRQB) 2-9	bits 0-3—Chip Operating Mode bits
Mode Select C/External Interrupt Request C	(MD,MC, MB, and MA) 4-4
signal (MODC/ $\overline{\text{IRQC}}$) 2-10	bit 4—External Bus Disable bit (EBD) 4-5
Mode Select D/External Interrupt Request D	bit 5—PC Relative Disable bit (PCD) 4-5
signal (MODD/ IRQD) 2-10	bit 6—Stop Delay bit (SD) 4-5
modulo adder 1-8	bit 8—XY Select bit (XY) 4-5
MR register 4-7	bit 9—Extended Stack Underflow bit
MS bit 4-6	(EUN) 4-5
Multiplication Factor bits (MF0-MF11) 4-17	bit 10—Extended Stack Overflow bit
multiplier-accumulator 1-7	(EOV) 4-6
-	bit 11—Extended Stack Wrap bit (WR) 4-6
N	bit 12—Extended Stack Enable bit (EN) 4-6
	bit 14—Memory Switch Mode bit (MS) 4-6
Normal mode 4-10	bit 15—Address Trace Enable bit (ATE) 4-6
0	reserved bits—bit 7, 13 4-7
0	OnCE Breakpoint Control Register (OBCR) 10-12
OPCP register 10.19	OnCE Command Register (OCR) 10-5
OBCR register 10-12	OnCE commands 10-24
bits 0–1—Memory Breakpoint Select bits (MBS0–MBS1) 10-13	OnCE controller 10-5
bits 2–3—Breakpoint 0 Read/Write Select	OnCE Decoder (ODEC) 10-8
bits (RW00–RW01) 10-13	OnCE GDB Register (OGDBR) 10-21
bits 4-5—Breakpoint 0 Condition Code	OnCE Global Data Bus register (OGDB) 5-10
Select bits (CC00–CC01) 10-13	OnCE Memory Address Comparator 0
bits 6-7—Breakpoint 1 Read/Write Select	(OMAC0) 10-12
bits (RW10–RW11) 10-14	OnCE Memory Address Comparator 1
bits 8-9—Breakpoint 1 Condition Code	(OMAC1) 10-12
Select bits (CC10–CC11) 10-14	OnCE Memory Address Latch register
bits 10–11—Breakpoint 0 and 1 Event Select	(OMAL) 10-11
bits (BT0-BT1) 10-15	OnCE Memory Breakpoint Counter
reserved bits—bits 12–15 10-15	(OMBC) 10-15
OCR register	OnCE Memory Limit Register 0 (OMLR0) 10-12
bits 0-4—Register Select bits (RS0-RS4) 10-6	OnCE Memory Limit Register 1 (OMLR1) 10-12
bit 5—Exit Command bit (EX) 10-7	OnCE module 1-11, 10-3
bit 6—GO Command bit (GO) 10-7	checking for Debug mode 10-25
bit 7—Read/Write Command bit	displaying a specified register 10-27
(R/\overline{W}) 10-8	displaying X data memory 10-28
ODEC 10-8	interaction with JTAG port 10-30
OF0 bit 8-10	polling the JTAG Instruction Shift
OF1 bit 8-10	register 10-26
offset adder 1-8	reading the Trace buffer 10-26
OGDB register 5-10	returning to Normal mode 10-29
OGDBR register 10-21	saving pipeline information 10-26
OMAC0 comparator 10-12	







OnCE PAB Register for Decode Register	PB9 signal 2-14
(OPABDR) 10-21	PC bits 6-5
OnCE PAB Register for Execute (OPABEX) 10-22	PC register 1-9
OnCE PAB Register for Fetch Register	PC Relative Disable bit (PCD) 4-5
(OPABFR) 10-21	PC0 signal 2-18
OnCE PIL Register (OPILR) 10-20	PC0-PC13 bits 9-8
OnCE Program Data Bus Register	PC0-PC5 bits 8-21
(OPDBR) 10-20	PC1 signal 2-18
OnCE Status and Control Register (OSCR) 10-8	PC2 signal 2-19
OnCE Trace Counter (OTC) 10-17	PC3 signal 2-19
OnCE trace logic 10-15	PC4 signal 2-20
OnCE/JTAG Interface pins 2-26	PC5 signal 2-20
On-Chip Emulation (OnCE) module 1-11	PCAP signal 2-7
On-Chip Emulation module 10-3	PCD bit 4-5
on-chip memory 1-11	PCE bit 9-12
on-chip program memory 3-4	PCR register 6-5
on-chip X data memory 3-4	bits 0-3—Port Control bits (PC) 6-5
on-chip Y data memory 3-5	reserved bits—bits 4-15 6-5
OPABDR register 10-21	PCRC register 8-20
OPABEX register 10-22	bits 0–5—Port Control bits (PC0–PC5) 8-21
OPABFR register 10-21	bit 7—Port Enable bit (PEN) 8-21
OPDBR register 10-20	reserved bits—bit 6, bits 8–15 8-21
Operating Mode Register (OMR) 1-9, 4-4	PCRD register 8-20
OPILR register 10-20	bits 0–5—Port Control bits (PC0–PC5) 8-21
OS0-OS1 bits 10-9	bit 7—Port Enable bit (PEN) 8-21
OSCR register 10-8	reserved bits—bit 6, bits 8–15 8-21
bit 0—Trace Mode Enable bit (TME) 10-9	PCTL0 register
bit 1—Interrupt Mode Enable bit (IME) 10-9	bits 0-11—Multiplication Factor bits
bit 2—Software Debug Occurrence bit	$(MF0-MF11)^{2}4-17$
(SWO) 10-9	bits 12–15—Predivider Factor bits
bit 3—Memory Breakpoint Occurrence bit	(PD0-PD3) 4-18
(MBO) 10-9	PCTL1 register 4-18
bit 4—Trace Occurrence bit (TO) 10-9	bits 0-2—Division Factor bits
bit 5—reserved bit 10-9	(DF2-DF0) 4-19
bits 6-7—Core Status bits (OS0-OS1) 10-9	bit 3—Crystal Range (XTLR) bit 4-19
reserved bits—bits 8-23 10-10	bit 4—XTAL Disable bit (XTLD) 4-19
OTC counter 10-17	bit 5—Stop Processing State bit (PSTP) 4-20
_	bit 6—PLL Enable bit (PEN) 4-20
P	bit 7—Clock Output Disable bit (COD) 4-20
	bits 9–11—Predivider Factor bits
PAB 1-12	(PD4-PD6) 4-20
PAG 1-9	reserved bits—bit 8, bits 12-15 4-20
PAR register 4-3	PCU 1-9
Patch Address Register (PAR) 4-3	PD bits 6-6
PB10 signal 2-14	PD0 signal 2-21
PB11 signal 2-15	PD0-PD3 bits 4-18

PB12 signal 2-15

PB13 signal 2-16

PB14 signal 2-16

PB15 signal 2-17

PB8 signal 2-13

Р

PD1 signal 2-21

PD2 signal 2-22

PD3 signal 2-22

PD4 signal 2-23

PD4-PD6 bits 4-20



Freescale Semiconductor, Inc.

Q

Inc.	
OF,	
duct	
onoc	
emic	
S	
ale	
esc	
Fre	

PD5 signal 2-23	Port Control Register (PCR) 6-5
PDB 1-12	Port D Control Register (PCRD) 8-20
PDC 1-9	Port D Data Register (PDRD) 8-22
PDC bits 6-5	Port D Direction Register (PRRD) 8-21
PDR register 6-6	Port D GPIO signal
bits 0-3—Port Data bits (PD) 6-6	PD0 2-21
PDRC register 8-22	PD1 2-21
PDRD register 8-22	PD2 2-22
PEN bit 4-20, 8-21	
•	PD3 2-22
Phase Lock Loop (PLL) 1-10, 4-17	PD4 2-23
PIC 1-9	PD5 2-23
PINIT/NMI signal 2-8	Port Data bits (PD0–PD3) 6-6
PL0-PL13 bits 9-7	Port Data Register (PDR) 6-6
PLL 1-10	Port Direction Control bits (PDC0-PDC3) 6-5
PLL Capacitor signal (PCAP) 2-7	Port Direction Register (PRR) 6-5
PLL Control Register 0 (PCTL0) 4-17	Port Enable bit (PEN) 8-21
PLL Control Register 1 (PCTL1) 4-18	Power & Ground pins 2-5
PLL Enable bit (PEN) 4-20	Power signals 2-5
PLL Ground signal (GND _P) 2-6	PPL 1-9
PLL Initial /Non-Maskable Interrupt signal	Predivider Factor bits (PD0-PD3) 4-18
$(PINIT/\overline{NMI})$ 2-8	Predivider Factor bits (PD4-PD6) 4-20
PLL Power signal (V _{CCP}) 2-5	Prescale Modulus Select bits (PM0-PM7) 8-8
PLL signals 2-7	Prescaled Clock Enable bit (PCE) 9-12
PM0-PM7 bits 8-8	Prescaler Counter Value bits (PC0–PC13) 9-8
Port A 1-10	Prescaler Preload Value bits (PL0–PL13) 9-7
	Prescaler Preload Value bits (PS0–PS1) 9-7
controlling 5-7	
disabling 5-7	Prescaler Range bit (PSR) 8-9
Port A signals 2-11	Program Address Bus (PAB) 1-12
Port B GPIO signal	Program Address Generator (PAG) 1-9
PB10 2-14	Program Control Unit (PCU) 1-9
PB11 2-15	Program Counter register (PC) 1-9
PB12 2-15	Program Data Bus (PDB) 1-12
PB13 2-16	Program Decode Controller (PDC) 1-9
PB14 2-16	Program Interrupt Controller (PIC) 1-9
PB15 2-17	program memory 3-4
PB8 2-13	Program Patch Logic (PPL) 1-9
PB9 2-14	PRR register 6-5
Port C Control Register (PCRC) 8-20	bits 0-3—Port Direction Control bits
Port C Data Register (PDRC) 8-22	(PDC) 6-5
Port C Direction Register (PRRC) 8-21	reserved bits—bits 4–15 6-5
Port C GPIO signal	PRRC register 8-21
PC0 2-18	PRRD register 8-21
PC1 2-18	PS0-PS1 bits 9-7
PC2 2-19	PSR bit 8-9
PC3 2-19	PSTP bit 4-20
PC4 2-20	Q
PC5 2-20	· ·
Port Control bits (PC0–PC3) 6-5	Ouist Cround signal (CND) 2.7
Port Control bits (PC0–PC5) 8-21	Quiet Ground signal (GND _Q) 2-7



Quiet Power High Voltage signal (V _{CCQH}) 2-5	in OSCR register
Quiet Power Low Voltage signal (V _{CCQL}) 2-5	bit 5, bits 8–23 10-9
_	in PCR register
R	bits 4–15 6-5
- 	in PCRC register
R/\overline{W} bit 10-8	bit 6, bits 8–15 8-21
RD signal 2-11, 5-4	in PCRD register
RDF bit 8-19	bit 6, bits 8–15 8-21
RE bit 8-12	in PCTL1 register
Read Enable signal (RD) 2-11, 5-4	bit 8, bits 12-15 4-20
Read/Write Command bit (R/\overline{W}) 10-8	in PDR register
Receive Data Register (RX) 8-19	bits 4–15 6-6
Receive Data Register Full bit (RDF) 8-19	in PRR register
Receive Data Register Full bit (RXDF) 7-26	bits 4–15 6-5
Receive Enable bit (RE) 8-12	in SSISR register
Receive Exception Interrupt Enable bit	bits 8–15 8-19
(REIE) 8-13	in TCSR register
Receive Frame Sync Flag bit (RFS) 8-18	bit 3 9-13
Receive High register (RXH) 7-29	in TPCR register
Receive Host Request signal (HRRQ) 2-17	bits 14–15 9-8
Receive Interrupt Enable bit (RIE) 8-12	RESET signal 2-8
Receive Last Slot Interrupt Enable bit (RLIE) 8-13	reverse-carry adder 1-8
Receive Low register (RXL) 7-29	RFS bit 8-18
Receive Request Enable bit (RREQ) 7-23	RIE bit 8-12
Receive Shift Register 8-19	RLIE bit 8-13
Receiver Overrun Error Flag bit (ROE) 8-18	ROE bit 8-18
Register Select bits (RS0–RS4) 10-6	RREQ bit 7-23
REIE bit 8-13	RS0-RS4 bits 10-6
reserved bits	RW00–RW01 bits 10-13
in BCR register	RW10-RW11 bits 10-14
bits 5–15 5-8	RX register 8-19
in CRB register	RXDF bit 7-26
bits 2–7 8-10	RXH register 7-29
in CRC register	RXL register 7-29
bits 8–11 8-15	17121081561 1 20
in HBAR register	S
bits 5–15 7-17	
in HCR register	SAMPLE/PRELOAD instruction 11-9
bits 5–15 7-10	SC register 1-9
in HPC register	SC0 signal 8-4, 8-5
bit 7 7-13	SC00 signal 2-18
in HSR register	SC01 signal 2-18
bits 5–15 7-11	SC02 signal 2-19
in ICR register	SC1 signal 8-4
bit 6 7-25	SC10 signal 2-21
in ISR register	SC11 signal 2-21
bits 5–6 7-27	SC12 signal 2-22
in OBCR register	SCD0 bit 8-14
bits 12–15 10-15	SCD1 bit 8-14
in OMR register	SCD2 bit 8-14
bit 7, bit 13 4-7	SCK signal 8-5
·	U



S

SCK0 signal 2-19	Serial Control 2 signal (SC02) 2-19
SCK1 signal 2-22	Serial Receive Data signal (SRD0) 2-20
SCKD bit 8-15	Serial Transmit Data signal (STD0) 2-20
SD bit 4-5	signals 2-18
Serial Clock signal (SCK) 8-5	SSI0 signals 2-18
Serial Control 0 Direction bit (SCD0) 8-14	SSI1
Serial Control 0 signal (SC0) 8-4, 8-5	Serial Clock signal (SCK1) 2-22
Serial Control 1 Direction bit (SCD1) 8-14	Serial Control 0 signal (SC10) 2-21
Serial Control 1 signal (SC0) 8-4	Serial Control 1 signal (SC11) 2-21
Serial Control 2 Direction bit (SCD2) 8-14	Serial Control 2 signal (SC12) 2-22
Serial Input Flag 0 bit (IF0) 8-17	Serial Control 2 signal (SC12) 2-22 Serial Receive Data signal (SRD1) 2-23
	<u> </u>
Serial Input Flag 1 bit (IF1) 8-17	Serial Transmit Data signal (STD1) 2-23
Serial Output Flag 0 bit (OF0) 8-10	signals 2-21
Serial Output Flag 1 bit (OF1) 8-10	SSI1 signals 2-21
serial protocol	SSISR register 8-16
in OnCE module 10-24	bit 0—Serial Input Flag 0 bit (IF0) 8-17
Serial Receive Data signal (SRD) 8-6	bit 1—Serial Input Flag 1 bit (IF1) 8-17
Serial Transmit Data signal (STD) 8-6	bit 2—Transmit Frame Sync Flag bit
SHFD bit 8-15	(TFS) 8-17
Shift Direction bit (SHFD) 8-15	bit 3—Receive Frame Sync Flag bit
Size register (SZ) 1-9	(RFS) 8-18
Software Debug Occurrence bit (SWO) 10-9	bit 4—Transmitter Underrun Error Flag bit
SP 1-9	(TUE) 8-18
SR register 1-9, 4-7	bit 5—Receiver Overrun Error Flag bit
SRAM	(ROE) 8-18
read access 5-5	bit 6—Transmit Data Register Empty bit
write access 5-5	(TDE) 8-18
SRD signal 8-6	bit 7—Receive Data Register Full bit
SRD0 signal 2-20	(RDF) 8-19
SRD1 signal 2-20	reserved bits—bits 8–15 8-19
SS 1-9	
SSI 1-14	Stack Counter register (SC) 1-9
	Stack Pointer (SP) 1-9 Status Pagintan (SP) 1-0 4-7
Asynchronous mode 8-25	Status Register (SR) 1-9, 4-7
frame sync selection 8-26	STD signal 8-6
operating mode selection 8-25	STD0 signal 2-20
operating modes 8-23	STD1 signal 2-23
shift direction selection 8-27	Stop Delay bit (SD) 4-5
Synchronous mode 8-25	Stop Processing State bit (PSTP) 4-20
SSI Control Register A (CRA) 8-7	Switch Mode 3-4
SSI exceptions 8-24	Switch mode 3-3
SSI Mode Select bit (MOD) 8-14	SWO bit 10-9
SSI Status Register (SSISR) 8-16	SYN bit 8-14
SSI, GPIO, and Timers Ground signal	Synchronous Serial Interface (SSI) 1-14
(GND _S) 2-7	Synchronous Serial Interface 0 signals 2-18
SSI, GPIO, and Timers Power signal (V _{CCS}) 2-6	Synchronous Serial Interface 0 signals (SSI0) 2-18
SSI0	Synchronous Serial interface 1 signals 2-21
Serial Clock signal (SCK0) 2-19	Synchronous Serial Interface 1 signals (SSI1) 2-21
Serial Control 0 signal (SC00) 2-18	System Stack (SS) 1-9
Serial Control 1 signal (SC00) 2-18	SZ register 1-9
501101 Collifor 1 5181101 (5001) & 10	52 105 15 CT 1 0





T	Timer 1 I/O signal (TI01) 2-25
TIA D 4 44	Timer 2 I/O signal (TI02) 2-25
TAP 1-11	timer architecture 9-4
TAP controller 11-6	Timer Compare Flag bit (TCF) 9-12
TC0-TC3 bits 9-10	Timer Compare Interrupt Enable bit (TCIE) 9-9
TCF bit 9-12	Timer Compare Register (TCPR) 9-9
TCIE bit 9-9	Timer Control bits (TC0–TC3) 9-10
TCK pin 11-5	Timer Control/Status Register (TCSR) 9-9
TCK signal 2-26	Timer Enable bit (TE) 9-9
TCPR register 9-9	Timer Load Register (TLR) 9-8
TCSR register 9-9	timer modes
bit 0—Timer Enable bit (TE) 9-9	measurement modes 9-16
bit 1—Timer Overflow Interrupt Enable bit	PWM mode 9-17
(TOIE) 9-9	reserved modes 9-19
bit 2—Timer Compare Interrupt Enable bit	timer modes 9-14
(TCIE) 9-9	watchdog modes 9-18
bits 4-7—Timer Control bits (TC0-TC3) 9-10	Timer Overflow Flag bit (TOF) 9-12
bit 8—Inverter bit (INV) 9-11	Timer Overflow Interrupt Enable bit (TOIE) 9-9
bit 9—Timer Reload Mode bit (TRM) 9-11	Timer Prescaler Load Register (TPLR) 9-7
bit 10—Direction bit (DIR) 9-11	Timer Reload Mode bit (TRM) 9-11
bit 11—Data Input bit (DI) 9-12	TIO1 signal 2-25
bit 12—Data Output bit (DO) 9-12	TLIE bit 8-12
bit 13—Timer Overflow Flag bit (TOF) 9-12	TLR register 9-8
bit 14—Timer Compare Flag bit (TCF) 9-12	TME bit 10-9
bit 15—Prescaled Clock Enable bit	TMS pin 11-5
(PCE) 9-12	TMS signal 2-26
reserved bit—bit 3 9-13	TO bit 10-9
TDE bit 8-18	TOF bit 9-12
TDI pin 11-5	TOIE bit 9-9
TDI signal 2-26	TPCR register
TDO pin 11-5	bits 0-13—Prescaler Counter Value bits
TDO signal 2-26	(PC0-PC13) 9-8
TE bit 8-10, 9-9	reserved bits—bits 14-15 9-8
TEIE bit 8-13	TPLR register 9-7
Test Access Port (TAP) 1-11, 11-3	bits 0-13—Prescaler Preload Value bits
Test Clock Input pin (TCK) 11-5	(PL0-PL13) 9-7
Test Clock signal (TCK) 2-26	bits 14–15—Prescaler Source bits
Test Data Input pin (TDI) 11-5	(PS0-PS1) 9-7
Test Data Input signal (TDI) 2-26	Trace buffer 10-22
Test Data Output pin (TDO) 11-5	Trace mode
Test Data Output signal (TDO) 2-26	enabling 10-19
Test Mode Select Input pin (TMS) 11-5	in OnCE module 10-16
Test Mode Select signal (TMS) 2-26	Trace Mode Enable bit (TME) 10-9
Test Reset Input pin (TRST) 11-5	Trace Occurrence bit (TO) 10-9
Test Reset signal (TRST signal) 2-26	Transmit Data register (TX) 8-20
TFS bit 8-17	Transmit Data Register Empty bit (TDE) 8-18
	Transmit Data Register Empty bit (TDE) 7-17 Transmit Data Register Empty bit (TXDE) 7-27
TI00 signal 2-25	Transmit Enable bit (TE) 8-10
TIO2 signal 2-25	
TIE bit 8-12 Time Slat Posiston (TSP) 8-20	Transmit Exception Interrupt Enable bit (TEIE) 8-13
Time Slot Register (TSR) 8-20	
Timer 0 I/O signal (TI00) 2-25	Transmit Frame Sync Flag bit (TFS) 8-17

T





Transmit High register (TXH) 7-29 Transmit Host Request signal (HTRQ) 2-16 Transmit Interrupt Enable bit (TIE) 8-12 Transmit Last Slot Interrupt Enable bit (TLIE) 8-12 Transmit Low register (TXL) 7-29 Transmit Request Enable bit (TREQ) 7-23 Transmit Shift Register 8-19 Transmitter Ready bit (TRDY) 7-27 Transmitter Underrun Error Flag bit (TUE) 8-18 TRDY bit 7-27 TREQ bit 7-23 triple timer module 1-15 Triple Timer signals 2-25 TRM bit 9-11 TRST pin 11-5 TRST signal 2-26 TSR register 8-20 **TUE bit 8-18** TX register 8-20 TXDE bit 7-27 TXH register 7-29

X Memory Expansion Bus 1-12 XAB 1-12 XDB 1-12 XTAL Disable bit (XTLD) 4-19 XTAL signal 2-7 XTLD bit 4-19 XTLR bit 4-19 XY Select bit (XY) 4-5

Y data memory 3-5 Y Memory Address Bus (YAB) 1-12 Y Memory Data Bus (YDB) 1-12 Y Memory Expansion Bus 1-12 YAB 1-12 YDB 1-12

TXL register 7-29

VBA register 1-9, 4-11

V_{CCA} signal 2-5 V_{CCC} signal 2-5 V_{CCD} signal 2-5 V_{CCH} signal 2-5 V_{CCP} signal 2-5 V_{CCQH} signal 2-5 V_{CCQL} signal 2-5 V_{CCS} signal 2-6 Vector Base Address register (VBA) 1-9, 4-11

W

WL0-WL1 bits 8-8 Word Length Control bits (WL0-WL1) 8-8 WR bit 4-6 WR signal 2-11, 5-4 Write Enable signal (\overline{WR}) 2-11, 5-4

X

X data memory 3-4 X Memory Address Bus (XAB) 1-12 X Memory Data Bus (XDB) 1-12

		V/	
	7		
	4		

0\	/F	R۱	VI	F۱	N
\smile	, _		•		

MEMORY MAPS

CORE CONFIGURATION 4

EXTERNAL MEMORY INTERFACE (PORT A) 5

> **GPIO** 6

HOST INTERFACE (HI08)

SYNCHRONOUS SERIAL INTERFACE 8

> TRIPLE TIMER MODULE 9

ON-CHIP EMULATION MODULE 10

> **JTAG PORT** 11

BOOTSTRAP PROGRAM A

> X I/O EQUATES В

PROGRAMMER'S REFERENCE C

INDEX

1	OVERVIEW
2	SIGNAL/CONNECTION DESCRIPTION
3	MEMORY MAPS
4	CORE CONFIGURATION
5	EXTERNAL MEMORY INTERFACE (PORT A)
6	GPIO
7	HOST INTERFACE (HI08)
8	SYNCHRONOUS SERIAL INTERFACE
9	TRIPLE TIMER MODULE
10	ON-CHIP EMULATION MODULE
11	JTAG PORT
Α	BOOTSTRAP PROGRAM
В	X I/O EQUATES
С	PROGRAMMER'S REFERENCE
	INDEX

For More Information On This Product, Go to: www.freescale.com