# **UM10345** P89LPC970/971/972 User manual Rev. 4 — 1 July 2010

**User manual** 

#### **Document information**

Info	Content
Keywords	P89LPC970/971/972
Abstract	Technical information for the P89LPC970/971/972 device



#### P89LPC970/971/972 User manual

#### **Revision history**

Rev	Date	Description
4	20100701	<ul> <li><u>Table 8 "Clock control register (CLKCON - address FFDEh) bit description</u>: updated XTALWD description</li> </ul>
		<ul> <li><u>Table 90 "Watchdog input clock selection"</u>: updated text</li> </ul>
		<ul> <li><u>Section 2.3 "Crystal oscillator option"</u>: updated text</li> </ul>
		<ul> <li><u>Section 15.1 "Watchdog function"</u>: updated text</li> </ul>
		<ul> <li><u>Section 15.3 "Watchdog clock source"</u>: updated text</li> </ul>
		<ul> <li><u>Section 15.5 "Power-down operation"</u>: updated text</li> </ul>
3	20100428	<ul> <li>Figure 1 "TSSOP20 pin configuration": corrected figure</li> </ul>
		<ul> <li>Figure 2 "P89LPC972 DIP20 pin configuration": corrected figure</li> </ul>
		<ul> <li>Figure 3 "Logic symbol": corrected figure</li> </ul>
2	20091216	<ul> <li>Table 99 "Flash User Configuration Byte 1 (UCFG1) bit allocation": corrected values for bits 3, 4 and 5</li> </ul>
		<ul> <li>Section 5.4 "Regulators": removed sentence "Before set LPMOD to select"</li> </ul>
		<ul> <li>Section 6 "Reset": removed note</li> </ul>
		<ul> <li>Section 8.3 "Mode 2: 16-bit PWM mode": updated third bullet</li> </ul>
1	20091023	Initial version
1	20091023	•

## **Contact information**

For more information, please visit: <u>http://www.nxp.com</u>

For sales office addresses, please send an email to: salesaddresses@nxp.com


UM10345


User manual

## 1. Introduction

The P89LPC970/971/972 is a single-chip microcontroller, available in low cost packages, based on a high performance processor architecture that executes instructions in two to four clocks, six times the rate of standard 80C51 devices. Many system-level functions have been incorporated into the P89LPC970/971/972 in order to reduce component count, board space, and system cost.

#### **1.1** Pin configuration





## 1.2 Pin description

Symbol	Pin	Туре	Description								
	DIP20, TSSOP20										
P0.0 to P0.7		I/O	<b>Port 0:</b> Port 0 is an 8-bit I/O port with a user-configurable output type. During reset Port 0 latches are configured in the input only mode with the internal pull-up disabled. The operation of Port 0 pins as inputs and outputs depends upon the port configuration selected. Each port pin is configured independently. Refer to <u>Section</u> 4.1 "Port configurations" for details.								
			The Keypad Interrupt feature operates with Port 0 pins.								
			All pins have Schmitt trigger inputs.								
			Port 0 also provides various special functions as described below:								
P0.0/CMP2/KBI0/	1	I/O	<b>P0.0</b> — Port 0 bit 0.								
SPICLK		0	CMP2 — Comparator 2 output								
		I	KBI0 — Keyboard input 0.								
		I/O	<b>SPICLK</b> — SPI clock. When configured as master, this pin is output; when configured as slave, this pin is input. (Pin Remap)								
P0.1/CIN2B/ <bi1< td=""><td>20</td><td>I/O</td><td><b>P0.1</b> — Port 0 bit 1.</td></bi1<>	20	I/O	<b>P0.1</b> — Port 0 bit 1.								
		I	CIN2B — Comparator 2 positive input B.								
		I	KBI1 — Keyboard input 1.								
P0.2/CIN2A/	19	I/O	<b>P0.2</b> — Port 0 bit 2.								
KBI2		I	CIN2A — Comparator 2 positive input A.								
		I	KBI2 — Keyboard input 2.								
P0.3/CIN1B/	18	I/O	P0.3 — Port 0 bit 3. High current source.								
KBI3/T2		I	CIN1B — Comparator 1 positive input B.								
		I	KBI3 — Keyboard input 3.								
		I/O	T2 — Timer/counter 2 external count input or overflow output.								
P0.4/CIN1A/	17	I/O	P0.4 — Port 0 bit 4. High current source.								
KBI4		I	CIN1A — Comparator 1 positive input A.								
		I	KBI4 — Keyboard input 4.								
P0.5/CMPREF/	16	I/O	P0.5 — Port 0 bit 5. High current source.								
KBI5/T3		I	<b>CMPREF</b> — Comparator reference (negative) input.								
		I	KBI5 — Keyboard input 5.								
	-	I/O	T3 — Timer/counter 3 external count input or overflow output.								

Symbol	Pin	Туре	Description
	DIP20, TSSOP20	_	
P0.6/CMP1/KBI6	14	I/O	P0.6 — Port 0 bit 6. High current source.
		0	CMP1 — Comparator 1 output.
		I	KBI6 — Keyboard input 6.
P0.7/KBI7/T1	13	I/O	P0.7 — Port 0 bit 7. High current source.
		I/O	T1 — Timer/counter 1 external count input or overflow output.
		I	KBI7 — Keyboard input 7.
P1.0 to P1.7		I/O, I [1]	<b>Port 1:</b> Port 1 is an 8-bit I/O port with a user-configurable output type, except for three pins as noted below. During reset Port 1 latches are configured in the input only mode with the internal pull-up disabled. The operation of the configurable Port 1 pins as inputs and outputs depends upon the port configuration selected. Each of the configurable port pins are programmed independently. Refer to <u>Section 4.1 "Port configurations"</u> for details. P1.2 to P1.3 are open drain when used as outputs. P1.5 is input only.
			All pins have Schmitt trigger inputs.
			Port 1 also provides various special functions as described below:
P1.0/TXD	12	I/O	<b>P1.0</b> — Port 1 bit 0.
		0	<b>TXD</b> — Transmitter output for serial port.
91.1/RXD/T2EX	11	I/O	<b>P1.1</b> — Port 1 bit 1.
		I	<b>RXD</b> — Receiver input for serial port.
		I	<b>T2EX</b> — Timer/counter 2 external capture input.
P1.2/SCL/T0	10	I/O	<b>P1.2</b> — Port 1 bit 2 (open-drain when used as output).
		I/O	<b>T0</b> — Timer/counter 0 external count input or overflow output. (open-drain when used as output.)
		I/O	<b>SCL</b> — I <sup>2</sup> C-bus serial clock input/output.
P1.3/INT0/SDA/	9	I/O	P1.3 — Port 1 bit 3 (open-drain when used as output).
T4		I	INTO — External interrupt 0 input.
		I/O	<b>SDA</b> — I <sup>2</sup> C-bus serial data input/output.
		I/O	T4 — Timer/counter 4 external count input or overflow output.
P1.4/INT1/T4EX/	8	I/O	P1.4 — Port 1 bit 4. High current source.
SS		I	INT1 — External interrupt 1 input.
		I	<b>T4EX</b> — Timer/counter 4 external capture input.
			<b>SS</b> — SPI Slave select. (Pin Remap)
P1.5/RST	4	I	P1.5 — Port 1 bit 5 (input only).
		I	<b>RST</b> — External Reset input during power-on or if selected via UCFG1. When functioning as a reset input, a LOW on this pin resets the microcontroller, causing I/O ports and peripherals to take on their default states, and the processor begins execution at address 0. Also used during a power-on sequence to force ISP mode.
P1.6/MISO	3	I/O	P1.6 — Port 1 bit 6. High current source.
		I/O	<b>MISO</b> — SPI master in slave out. When configured as master, this pin is input, when configured as slave, this pin is output. (Pin Remap)

## Table 1. Pin description ...continued

Table 1. Pin des	scriptionc	ontinued	
Symbol	Pin	Туре	Description
	DIP20, TSSOP20		
P1.7/T3EX/MOSI	2	I/O	P1.7 — Port 1 bit 7. High current source.
		I	T3EX — Timer/counter 3 external capture input.
		I/O	<b>MOSI</b> — SPI master out slave in. When configured as master, this pin is output; when configured as slave, this pin is input. (Pin Remap)
P3.0 to P3.1		I/O	<b>Port 3:</b> Port 3 is a 2-bit I/O port with a user-configurable output type. During reset Port 3 latches are configured in the input only mode with the internal pull-up disabled. The operation of Port 3 pins as inputs and outputs depends upon the port configuration selected. Each port pin is configured independently. Refer to <u>Section 4.1 "Port configurations</u> " for details.
			All pins have Schmitt trigger inputs.
			Port 3 also provides various special functions as described below:
P3.0/XTAL2/	7	I/O	<b>P3.0</b> — Port 3 bit 0.
CLKOUT		0	<b>XTAL2</b> — Output from the oscillator amplifier (when a crystal oscillator option is selected via the flash configuration.
		0	<b>CLKOUT</b> — CPU clock divided by 2 when enabled via SFR bit (ENCLK -TRIM.6). It can be used if the CPU clock is the internal RC oscillator, watchdog oscillator or external clock input, except when XTAL1/XTAL2 are used to generate clock source for the RTC/system timer.
P3.1/XTAL1	6	I/O	<b>P3.1</b> — Port 3 bit 1.
		I	<b>XTAL1</b> — Input to the oscillator circuit and internal clock generator circuits (when selected via the flash configuration). It can be a port pin if internal RC oscillator or watchdog oscillator is used as the CPU clock source, <b>and</b> if XTAL1/XTAL2 are not used to generate the clock for the RTC/system timer.
V <sub>SS</sub>	5	I	Ground: 0 V reference.
V <sub>DD</sub>	15	I	<b>Power supply:</b> This is the power supply voltage for normal operation as well as Idle and Power-down modes.


[1] Input/output for P1.0 to P1.4, P1.6, P1.7. Input for P1.5.

User manual

**UM10345** 

P89LPC970/971/972 User manual





P89LPC970/971/972 ACCELERATED 2-CLOCK 80C51 CPU ► TXD 2 kB/4 kB/8 kB UART RXD CODE FLASH internal bus → SCL 256-BYTE I<sup>2</sup>C-BUS DATA RAM → SDA ► SPICLK<sup>(1)</sup> PORT 3 → MOSI<sup>(1)</sup> P3[1:0] SPI **CONFIGURABLE I/Os** → MISO<sup>(1)</sup> → SS(1) PORT 1 P1[7:0] REAL-TIME CLOCK/ CONFIGURABLE I/Os SYSTEM TIMER PORT 0 P0[7:0] TIMER 0 → T0 CONFIGURABLE I/Os + T1 TIMER 1 T2 KEYPAD T2EX TIMER 2 INTERRUPT T3 T3EX TIMER 3 TIMER 4 T4 WATCHDOG TIMER T4EX AND OSCILLATOR CMP2 CIN2B CIN2A CIN2A CMP1 ANALOG PROGRAMMABLE CPU COMPARATORS OSCILLATOR DIVIDER CIN1A CIN1B clock **ON-CHIP RC** XTAL1 CRYSTAL POWER MANAGEMENT CONFIGURABLE OSCILLATOR OR (POWER-ON RESET, OSCILLATOR WITH CLOCK RESONATOR XTAL2 BROWNOUT RESET. DOUBLER **REGULATORS**) 002aae550 (1) For pin remap Fig 4. **Block diagram** 

## 1.4 Block diagram

## 1.5 Special function registers

**Remark:** SFR accesses are restricted in the following ways:

- User must not attempt to access any SFR locations not defined.
- Accesses to any defined SFR locations must be strictly for the functions for the SFRs.
- SFR bits labeled '-', '0' or '1' can **only** be written and read as follows:
  - '-' Unless otherwise specified, must be written with '0', but can return any value when read (even if it was written with '0'). It is a reserved bit and may be used in future derivatives.
  - '0' **must** be written with '0', and will return a '0' when read.
  - '1' **must** be written with '1', and will return a '1' when read.

Name	Description	SFR addr.	Bit function	ns and addr	esses						Reset value	
			MSB							LSB	Hex	Binary
		Bit address	E7	<b>E6</b>	E5	E4	E3	E2	E1	E0		
ACC*	Accumulator	E0H									00	0000 000
AUXR1	Auxiliary function register	A2H	CLKLP	EBRR	ENT1	ENT0	SRST	0	-	DPS	00	0000 00x
		Bit address	F7	F6	F5	F4	F3	F2	F1	F0		
B*	B register	F0H									00	0000 000
BRGR0 <sup>[2]</sup>	Baud rate generator 0 rate low	BEH									00	0000 000
BRGR1 <sup>[2]</sup>	Baud rate generator 0 rate high	BFH									00	0000 000
BRGCON	Baud rate generator 0 control	BDH	-	-	-	-	-	-	SBRGS	BRGEN	00[2]	xxxx xx0(
CMP1	Comparator 1 control register	ACH	-	-	CE1	CP1	CN1	OE1	CO1	CMF1	00[1]	xx00 000
CMP2	Comparator 2 control register	ADH	-	-	CE2	CP2	CN2	OE2	CO2	CMF2	00[1]	xx00 000
DIVM	CPU clock divide-by-M control	95H									00	0000 000
DPTR	Data pointer (2 bytes)											
DPH	Data pointer high	83H									00	0000 000
DPL	Data pointer Iow	82H									00	0000 000
FMADRH	Program flash address high	E7H									00	0000 000
FMADRL	Program flash address low	E6H									00	0000 000

Name	Description	SFR addr.	Bit functio	ns and addr	esses						Reset	value
			MSB							LSB	Hex	Binary
FMCC	N Program flash control (Read)		BUSY	-	-	-	HVA	HVE	SV	OI	70	0111 000
	Program flash control (Write)		FMCMD.7	FMCMD.6	FMCMD.5	FMCMD.4	FMCMD.3	FMCMD.2	FMCMD.1	FMCMD.0		
FMDA	TA Program flash data	E5H									00	0000 000
I2ADF	l <sup>2</sup> C-bus slave address register	DBH	I2ADR.6	I2ADR.5	I2ADR.4	I2ADR.3	I2ADR.2	I2ADR.1	I2ADR.0	GC	00	0000 000
		Bit address	DF	DE	DD	DC	DB	DA	D9	D8		
I2CON	I* I <sup>2</sup> C-bus contro register	D8H	-	I2EN	STA	STO	SI	AA	-	CRSEL	00	x000 00x0
I2DAT	l <sup>2</sup> C-bus data register	DAH										
I2SCL	H Serial clock generator/SCI duty cycle register high	DDH -									00	0000 000
I2SCL	L Serial clock generator/SCI duty cycle register low	DCH									00	0000 000
I2STA	<ul> <li>I<sup>2</sup>C-bus status register</li> </ul>	5 D9H	STA.4	STA.3	STA.2	STA.1	STA.0	0	0	0	F8	1111 100
		Bit address	AF	AE	AD	AC	AB	AA	A9	<b>A</b> 8		
IEN0*	Interrupt enable 0	A8H	EA	EWDRT	EBO	ES/ESR	ET1	EX1	ET0	EX0	00	000 000
		Bit address	EF	EE	ED	EC	EB	EA	E9	E8		
IEN1*	Interrupt enable 1	E8H	-	EST	-	EXTIM	ESPI	EC	EKBI	EI2C	00 <u>[1]</u>	00x0 000
		Bit address	BF	BE	BD	BC	BB	BA	B9	<b>B</b> 8		
IP0*	Interrupt priority 0	B8H	-	PWDRT	PBO	PS/PSR	PT1	PX1	PT0	PX0	00[1]	x000 000

P89LPC970/971/972 User manual

UM10345

Name	Description	SFR addr.	7. Bit functions and addresses									
			MSB							LSB	Hex	Binary
IP0H	Interrupt priority 0 high	B7H	-	PWDRTH	PBOH	PSH/ PSRH	PT1H	PX1H	PT0H	PX0H	00[1]	x000 000
		Bit address	FF	FE	FD	FC	FB	FA	F9	F8		
IP1*	Interrupt priority 1	F8H	-	PST	-	PXTIM	PSPI	PC	PKBI	PI2C	00[1]	00x0 000
IP1H	Interrupt priority 1 high	F7H	-	PSTH	-	PXTIMH	PSPIH	PCH	PKBIH	PI2CH	00[1]	00x0 000
KBCON	Keypad control register	94H	-	-	-	-	-	-	PATN _SEL	KBIF	00[1]	xxxx xx00
KBMASK	Keypad interrupt mask register	86H									00	0000 0000
KBPATN	Keypad pattern register	93H									FF	1111 111
		Bit address	87	86	85	84	83	82	81	80		
P0*	Port 0	80H	T1/KB7	CMP1 /KB6	CMPREF /KB5/T3	CIN1A /KB4	CIN1B /KB3/T2	CIN2A /KB2	CIN2B /KB1	CMP2 /KB0	[1]	
		Bit address	97	96	95	94	93	92	91	90		
P1*	Port 1	90H	T3EX	-	RST	INT1/T4E X	INT0/SDA/ T4	T0/SCL	RXD/T2E X	TXD	[1]	
		Bit address	B7	<b>B6</b>	B5	B4	<b>B</b> 3	B2	B1	<b>B</b> 0		
P3*	Port 3	B0H	-	-	-	-	-	-	XTAL1	XTAL2	<u>[1]</u>	
P0M1	Port 0 output mode 1	84H	(P0M1.7)	(P0M1.6)	(P0M1.5)	(P0M1.4)	(P0M1.3)	(P0M1.2)	(P0M1.1)	(P0M1.0)	FF <u>[1]</u>	1111 111
P0M2	Port 0 output mode 2	85H	(P0M2.7)	(P0M2.6)	(P0M2.5)	(P0M2.4)	(P0M2.3)	(P0M2.2)	(P0M2.1)	(P0M2.0)	00[1]	0000 000
P1M1	Port 1 output mode 1	91H	(P1M1.7)	(P1M1.6)	-	(P1M1.4)	(P1M1.3)	(P1M1.2)	(P1M1.1)	(P1M1.0)	D3[1]	11x1 xx1
P1M2	Port 1 output mode 2	92H	(P1M2.7)	(P1M2.6)	-	(P1M2.4)	(P1M2.3)	(P1M2.2)	(P1M2.1)	(P1M2.0)	00[1]	00x0 xx0

Name	Description	SFR addr.	Bit functio	ns and addr	resses						Reset	value
			MSB							LSB	Hex	Binary
P3M1	Port 3 output mode 1	B1H	-	-	-	-	-	-	(P3M1.1)	(P3M1.0)	03 <mark>[1]</mark>	xxxx xx11
P3M2	Port 3 output mode 2	B2H	-	-	-	-	-	-	(P3M2.1)	(P3M2.0)	00[1]	xxxx xx00
PCON	Power control register	87H	SMOD1	SMOD0	-	BOI	GF1	GF0	PMOD1	PMOD0	00	0000 0000
PCONA	Power control register A	B5H	RTCPD	-	VCPD	-	I2PD	SPPD	SPD	-	00[1]	0000 0000
PINCON	Pin Remap control register	CFH	-	-	-	-	-	-	SPI	-	00[1]	0000 0000
PMUCO	N Power Management Unit control register	FAH	LPMOD	-	-	-	-	-	-	HCOK		0xxx xxx1
		Bit address	D7	D6	D5	D4	D3	D2	D1	D0		
PSW*	Program status word	D0H	CY	AC	F0	RS1	RS0	OV	F1	Р	00	0000 0000
PT0AD	Port 0 digital input disable	F6H	-	-	PT0AD.5	PT0AD.4	PT0AD.3	PT0AD.2	PT0AD.1	-	00	xx00 000x
PWMD2	H PWM Free Cycle Register 2 High Byte	AEH									00	0000 0000
PWMD2	L PWM Free Cycle Register 2 Low Byte	AFH									00	0000 0000
PWMD3	H PWM Free Cycle Register 3 High Byte	E9H									00	0000 0000
PWMD3	L PWM Free Cycle Register 3 Low Byte	EAH									00	0000 0000
PWMD4	H PWM Free Cycle Register 4 High Byte	AAH									00	0000 0000

13 of 129

Rev. 4 — 1 July 2010

Name	Description	SFR addr.	Bit function	ons and add	resses						Reset value	
			MSB							LSB	Hex	Binary
PWMD4L	PWM Free Cycle Register 4 Low Byte	ABH									00	0000 0000
RCAP2H	Capture Register 2 High Byte	FCH									00	0000 0000
RCAP2L	Capture Register 2 Low Byte	FBH									00	0000 0000
RCAP3H	Capture Register 3 High Byte	ECH									00	0000 0000
RCAP3L	Capture Register 3 Low Byte	EBH									00	0000 0000
RCAP4H	Capture Register 4 High Byte	CAH									00	0000 0000
RCAP4L	Capture Register 4 Low Byte	C9H									00	0000 0000
RSTSRC	Reset source register	DFH	-	BOIF	BORF	POF	R_KB	R_WD	R_SF	R_EX	[3]	
RTCCON	RTC control	D1H	RTCF	RTCS1	RTCS0	-	-	-	ERTC	RTCEN	60 <u>[1][6]</u>	011x xx00
RTCH	RTC register high	D2H									00 <u>[6]</u>	0000 0000
RTCL	RTC register low	D3H									00[6]	0000 0000
SADDR	Serial port address register	A9H									00	0000 0000
SADEN	Serial port address enable	B9H									00	0000 0000

14 of 129

Name	Description	SFR addr.										Reset value	
			MSB							LSB	Hex	Binary	
SBUF	Serial Port data buffer register	99H									xx	XXXX XXXX	
		Bit address	9F	9E	9D	9C	9B	9 <b>A</b>	99	98			
SCON*	Serial port control	98H	SM0/FE	SM1	SM2	REN	TB8	RB8	TI	RI	00	000 000	
SSTAT	Serial port extended status register	BAH	DBMOD	INTLO	CIDIS	DBISEL	FE	BR	OE	STINT	00	0000 000	
SP	Stack pointer	81H									07	0000 011	
SPCTL	SPI control register	E2H	SSIG	SPEN	DORD	MSTR	CPOL	CPHA	SPR1	SPR0	04	0000 010	
SPSTAT	SPI status register	E1H	SPIF	WCOL	-	-	-	-	-	-	00	00xx xxx	
SPDAT	SPI data register	E3H									00	0000 000	
TAMOD	Timer 0 and 1 auxiliary mode	8FH	-	-	-	T1M2	-	-	-	T0M2	00	xxx0 xxx	
		Bit address	8F	8E	8D	8C	8B	<b>8A</b>	89	88			
TCON*	Timer 0 and 1 control	88H	TF1	TR1	TF0	TR0	IE1	IT1	IE0	IT0	00	000 000	
TH0	Timer 0 high	8CH									00	0000 000	
TH1	Timer 1 high	8DH									00	0000 000	
TL0	Timer 0 low	8AH									00	0000 000	
TL1	Timer 1 low	8BH									00	0000 000	
TMOD	Timer 0 and 1 mode	89H	T1GATE	T1C/T	T1M1	T1M0	TOGATE	T0C/T	T0M1	TOMO	00	0000 000	
T2CON	Timer/Counter 2 Control	FFH	PSEL2	ENT2	TIEN2	PWM2	EXEN2	TR2	C/NT2	CP/NRL2	00	0000 000	
TH2	Timer/Counter 2 High Byte	FEH									00	0000 000	
TL2	Timer/Counter 2 Low Byte	FDH									00	0000 000	

P89LPC970/971/972 User manual UM10345

Rev. 4 — 1 July 2010

UM10345 User manual

#### Table 2. **Special function registers**

\* indicates SFRs that are bit addressable.

Name	Description	SFR addr.	Bit function	Reset value								
			MSB							LSB	Hex	Binary
T3CON	Timer/Counter 3 Control	EFH	PSEL3	ENT3	TIEN3	PWM3	EXEN3	TR3	C/NT3	CP/NRL3	00	0000 0000
TH3	Timer/Counter 3 High Byte	EEH									00	0000 0000
TL3	Timer/Counter 3 Low Byte	EDH									00	0000 0000
T4CON	Timer/Counter 2 Control	CDH	PSEL4	ENT4	TIEN4	PWM4	EXEN4	TR4	C/NT4	CP/NRL4	00	0000 0000
TH4	Timer/Counter 4 High Byte	ССН									00	0000 0000
TL4	Timer/Counter 4 Low Byte	CBH									00	0000 0000
TINTF	Timer/Counter s 2/3/4 Overflow and External Flags	CEH	-	-	TF4	EXF4	TF3	EXF3	TF2	EXF2	00	0000 0000
TRIM	Internal oscillator trim register	96H	RCCLK	ENCLK	TRIM.5	TRIM.4	TRIM.3	TRIM.2	TRIM.1	TRIM.0	<u>[5][6]</u>	
WDCON	Watchdog control register	A7H	PRE2	PRE1	PRE0	-	-	WDRUN	WDTOF	WDCLK	<u>[4][6]</u>	
WDL	Watchdog load	C1H									FF	1111 1111
WFEED1	Watchdog feed 1	C2H										
WFEED2	Watchdog feed 2	СЗН										

All ports are in input only (high-impedance) state after power-up. [1]

BRGR1 and BRGR0 must only be written if BRGEN in BRGCON SFR is logic 0. If any are written while BRGEN = 1, the result is unpredictable. [2]

© NXP B.V. 2010. All rights res [3] The RSTSRC register reflects the cause of the UM10345 reset except BOIF bit. Upon a power-up reset, all reset source flags are cleared except POF and BOF; the power-on reset value is x011 0000.

[4] After reset, the value is 1110 01x1, i.e., PRE2 to PRE0 are all logic 1, WDRUN = 1 and WDCLK = 1. WDTOF bit is logic 1 after watchdog reset and is logic 0 after power-on reset. Other resets will not affect WDTOF.

On power-on reset and watchdog reset, the TRIM SFR is initialized with a factory preprogrammed value. Other resets will not cause initialization of the TRIM register. [5]

[6] The only reset sources that affect these SFRs are power-on reset and watchdog reset.

User manual

UM10345

16 of 129

ervec

#### Table 3. Extended special function registers<sup>[1]</sup>

10345	Name	Description	SFR addr.	Bit functions and addresses						Reset value			
				MSB							LSB	Hex	Binary
	BODCFG	BOD configuration register	FFC8H	-	-	-	-	-	BOICFG2	BOICFG1	BOICFG0	[2]	
	CLKCON	CLOCK Control register	FFDEH	CLKOK	-	WDMOD	XTALWD	CLKDBL	FOSC2	FOSC1	FOSC0	[2]	1000 xxxx
All information provided in this	CMPREF	Comparator reference register	FFCBH	-	REFS5	REFS4	REFS3	-	REFS2	REFS1	REFS0	00	0000 0000
	RTCDATH	Real-time clock data register high	FFBFH									00	0000 0000
	RTCDATL	Real-time clock data register low	FFBEH									00	0000 0000


[1] Extended SFRs are physically located on-chip but logically located in external data memory address space (XDATA). The MOVX A, @DPTR and MOVX @DPTR, A instructions are used to access these extended SFRs.

[2] The BOICFG2/1/0 will be copied from UCFG1.5 to UCFG1.3 when power-on reset.

[3] CLKCON register reset value comes from UCFG1. The reset value of CLKCON.2 to CLKCON.0 come from UCFG1.2 to UCFG1.0 and reset value of CLKDBL bit comes from UCFG1.7.

User manual

ovided in this document is subject to legal disclaimer Rev. 4 — 1 July 2010



#### 1.6 Memory organization

Fig 5. P89LPC970/971/972 memory map

The various P89LPC970/971/972 memory spaces are as follows:

**DATA** — 128 bytes of internal data memory space (00h:7Fh) accessed via direct or indirect addressing, using instruction other than MOVX and MOVC. All or part of the Stack may be in this area.

**IDATA** — Indirect Data. 256 bytes of internal data memory space (00h:FFh) accessed via indirect addressing using instructions other than MOVX and MOVC. All or part of the Stack may be in this area. This area includes the DATA area and the 128 bytes immediately above it.

**SFR** — Special Function Registers. Selected CPU registers and peripheral control and status registers, accessible only via direct addressing.

**XDATA** — 'External' Data or Auxiliary RAM. Duplicates the classic 80C51 64 kB memory space addressed via the MOVX instruction using the DPTR, R0, or R1. All or part of this space could be implemented on-chip.

**CODE** — 64 kB of Code memory space, accessed as part of program execution and via the MOVC instruction. The P89LPC970/971/972 has 4 kB/8 kB of on-chip Code memory.

Table 4.	Data RAM arrangement	
Туре	Data RAM	Size (bytes)
DATA	Directly and indirectly addressable memory	128
IDATA	Indirectly addressable memory	256
XDATA	Auxiliary ('External Data') on-chip memory that is accessed using the MOVX instructions	256

## 2. Clocks

#### 2.1 Enhanced CPU

The P89LPC970/971/972 uses an enhanced 80C51 CPU which runs at six times the speed of standard 80C51 devices. A machine cycle consists of two CPU clock cycles, and most instructions execute in one or two machine cycles.

#### 2.2 Clock definitions

The P89LPC970/971/972 device has several internal clocks as defined below:

**OSCCLK** — Input to the DIVM clock divider. OSCCLK is selected from one of four clock sources and can also be optionally divided to a slower frequency (see <u>Figure 7</u> and <u>Section 2.10 "CPU Clock (CCLK) modification: DIVM register"</u>). **Note:** f<sub>osc</sub> is defined as the OSCCLK frequency.

**CCLK** — CPU clock; output of the DIVM clock divider. There are two CCLK cycles per machine cycle, and most instructions are executed in one to two machine cycles (two or four CCLK cycles).

**RCCLK** — The internal 7.373 MHz RC oscillator output. The clock doubler option, when enabled, provides an output frequency of 14.746 MHz.

PCLK — Clock for the various peripheral devices and is <sup>CCLK</sup>/<sub>2</sub>.

#### 2.2.1 Oscillator Clock (OSCCLK)

The P89LPC970/971/972 provides several user-selectable oscillator options in generating the CPU clock. This allows optimization for a range of needs from high precision to lowest possible cost. These options are configured when the flash is programmed and include an on-chip watchdog oscillator, an on-chip RC oscillator, an oscillator using an external crystal, or an external clock source.

#### 2.3 Crystal oscillator option

The crystal oscillator can be optimized for low, medium, or high frequency crystals covering a range from 20 kHz to 18 MHz. It can be the clock source of OSCCLK and RTC. The low speed oscillator option can be the clock source of WDT.

#### 2.3.1 Low speed oscillator option

This option supports an external crystal in the range of 20 kHz to 100 kHz. Ceramic resonators are also supported in this configuration.

#### 2.3.2 Medium speed oscillator option

This option supports an external crystal in the range of 100 kHz to 4 MHz. Ceramic resonators are also supported in this configuration.

#### 2.3.3 High speed oscillator option

This option supports an external crystal in the range of 4 MHz to 18 MHz. Ceramic resonators are also supported in this configuration.

#### 2.4 Clock output

The P89LPC970/971/972 supports a user-selectable clock output function on the XTAL2 / CLKOUT pin when the crystal oscillator is not being used. This condition occurs if a different clock source has been selected (on-chip RC oscillator, watchdog oscillator, external clock input on X1) and if the Real-time Clock and Watchdog Timer are not using the crystal oscillator as their clock source. This allows external devices to synchronize to the P89LPC970/971/972. This output is enabled by the ENCLK bit in the TRIM register.

The frequency of this clock output is  $\frac{1}{2}$  that of the CCLK. If the clock output is not needed in Idle mode, it may be turned off prior to entering Idle, saving additional power. Note: on reset, the TRIM SFR is initialized with a factory preprogrammed value. Therefore when setting or clearing the ENCLK bit, the user should retain the contents of other bits of the TRIM register. This can be done by reading the contents of the TRIM register (into the ACC for example), modifying bit 6, and writing this result back into the TRIM register. Alternatively, the 'ANL direct' or 'ORL direct' instructions can be used to clear or set bit 6 of the TRIM register.

#### 2.5 On-chip RC oscillator option

The P89LPC970/971/972 has a 6-bit TRIM register that can be used to tune the frequency of the RC oscillator. During reset, the TRIM value is initialized to a factory pre-programmed value to adjust the oscillator frequency to 7.373 MHz  $\pm$  1 % at room temperature. (Note: the initial value is better than 1 %; please refer to the *P89LPC970/971/972 data sheet* for behavior over temperature). End user applications can write to the TRIM register to adjust the on-chip RC oscillator to other frequencies. Increasing the TRIM value will decrease the oscillator frequency. When the clock doubler option is enabled (UCFG2.7 = 1), the output frequency is doubled. If CCLK is 8 MHz or slower, the CLKLP SFR bit (AUXR1.7) can be set to logic 1 to reduce power consumption. On reset, CLKLP is logic 0 allowing highest performance access. This bit can then be set in software if CCLK is running at 8 MHz or slower. When clock doubler option is enabled, BOE0 to BOE2 bits (UCFG1[3:5]) are required to hold the device in reset at power-up until V<sub>DD</sub> has reached its specified level.

Bit	7	6	5	4	3	2	1	0
Symbol	RCCLK	ENCLK	TRIM.5	TRIM.4	TRIM.3	TRIM.2	TRIM.1	TRIM.0
Reset	0	0	Bits 5:0 loa	Bits 5:0 loaded with factory stored value during reset.				

#### Table 5. On-chip RC oscillator trim register (TRIM - address 96h) bit allocation

Table 6.	On-chip RC oscillator	trim register (TRIM - address 96h) bit description
Bit	Symbol	Description
0	TRIM.0	Trim value. Determines the frequency of the internal RC oscillator. During reset,
1	TRIM.1	these bits are loaded with a stored factory calibration value. When writing to either bit 6 or bit 7 of this register, care should be taken to preserve the current TRIM value
2	TRIM.2	by reading this register, modifying bits 6 or 7 as required, and writing the result to
3	TRIM.3	this register.
4	TRIM.4	
5	TRIM.5	
6	ENCLK	when = 1, <sup>CCLK</sup> <sup>1</sup> 2 is output on the XTAL2 pin provided the crystal oscillator is not being used.
7	RCCLK	when = 1, selects the RC Oscillator output as the CPU clock (CCLK). This allows for fast switching between any clock source and the internal RC oscillator without needing to go through a reset cycle.


#### On ohis PC assillator trim register (TPIM address 06h) hit description

#### 2.6 Watchdog oscillator option


The watchdog has a separate oscillator which provide two option: 400 kHz and 25 kHz. It is calibrated to ± 10 % at 400 kHz. The oscillator can be used to save power when a high clock frequency is not needed.

#### 2.7 External clock input option

In this configuration, the processor clock is derived from an external source driving the XTAL1 / P3.1 pin. The rate may be from 0 Hz up to 18 MHz. The XTAL2 / P3.0 pin may be used as a standard port pin or a clock output. When using an oscillator frequency above 12 Mhz, BOE0 to BOE2 bits (UCFG1[3:5]) are required to hold the device in reset at power-up until V<sub>DD</sub> has reached its specified level.



#### P89LPC970/971/972 User manual



#### 2.8 Clock source switching on the fly

P89LPC970/971/972 can implement clock switching on any sources of watchdog oscillator, 7/14MHz IRC oscillator, crystal oscillator and external clock input during code is running. CLKOK bit in register CLKCON is read only and used to indicate the clock switch status. When CLKOK is '0', clock switch is processing, not completed. When CLKOK is '1', clock switch is completed. When start new clock source switch, CLKOK is cleared automatically. Notice that when CLKOK is '0', Writing to CLKCON register is not allowed. During reset, CLKCON register value comes from UCFG1. The reset value of CLKCON.2 to CLKCON.0 comes from UCFG1.2 to UCFG1.0 and reset value of CLKDBL bit comes from UCFG1.7.

		••••••••••••••••••••••••••••••••••••••	(					
Bit	7	6	5	4	3	2	1	0
Symbol	CLKOK	-	WDMOD	XTALWD	CLKDBL	FOSC2	FOSC1	FOSC0
Reset	1	0	0	0	х	х	х	х

#### Table 7. Clock control register (CLKCON - address FEDEh) bit allocation

#### Table 8. Clock control register (CLKCON - address FFDEh) bit description

10010 01	••••••••••••••••••••••••••••••••••••••	
Bit	Symbol	Description
2:0	FOSC2, FOSC1, FOSC0	CPU oscillator type selection for clock switch. See <u>Section 2</u> for additional information. Combinations other than those shown in <u>Table 9</u> are reserved for future use and should not be used.
3	CLKDBL	Clock doubler option for clock switch. When set, doubles the output frequency of the internal RC oscillator.
4	XTALWD	Low speed external crystal oscillator as the clock source of watchdog timer. When = 0, disable the external crystal oscillator as the clock source of watchdog timer.
5	WDMOD	When WDCLK=1 and XTALWD=0, WDMOD is used to select watchdog clock input from 400 k oscillator or 25 k oscillator. If WDMOD=0, 400 kHz watchdog oscillator is selected. If WDMOD=1, 25 kHz watchdog oscillator is selected.
6	-	reserved
7	CLKOK	Clock switch completed flag. When = 1, clock switch is completed. When =0, clock switch is processing and writing to register CLKCON is not allowed.
UM10345		All information provided in this document is subject to legal disclaimers. © NXP B.V. 2010. All rights reserved.

Table 9.	Oscillator type selection for clock switch
FOSC[2:0]	Oscillator configuration
111	External clock input on XTAL1.
100	Watchdog Oscillator, nominal 400 kHz or 25 kHz.
011	Internal RC oscillator, 7.373 MHz ± 1 %.
010	Low frequency crystal, 20 kHz to 100 kHz.
001	Medium frequency crystal or resonator, 100 kHz to 4 MHz.
000	High frequency crystal or resonator, 4 MHz to 18 MHz.

#### 2.9 Oscillator Clock (OSCCLK) wake-up delay

The P89LPC970/971/972 has an internal wake-up timer that delays the clock until it stabilizes depending on the clock source used. If the clock source is any of the three crystal selections (low, medium and high frequencies) the delay is 1024 OSCCLK cycles plus 60  $\mu$ s to 100  $\mu$ s. If the clock source is the internal RC oscillator, the delay is 200  $\mu$ s to 300  $\mu$ s. If the clock source is watchdog oscillator or external clock, the delay is 32 OSCCLK cycles.

#### 2.10 CPU Clock (CCLK) modification: DIVM register

The OSCCLK frequency can be divided down, by an integer, up to 510 times by configuring a dividing register, DIVM, to provide CCLK. This produces the CCLK frequency using the following formula:

CCLK frequency =  $f_{osc} / (2N)$ 

Where: fosc is the frequency of OSCCLK, N is the value of DIVM.

Since N ranges from 0 to 255, the CCLK frequency can be in the range of  $f_{osc}$  to  $f_{osc}/510$ . (for N = 0, CCLK =  $f_{osc}$ ).

This feature makes it possible to temporarily run the CPU at a lower rate, reducing power consumption. By dividing the clock, the CPU can retain the ability to respond to events other than those that can cause interrupts (i.e. events that allow exiting the Idle mode) by executing its normal program at a lower rate. This can often result in lower power consumption than in Idle mode. This can allow bypassing the oscillator start-up time in cases where Power-down mode would otherwise be used. The value of DIVM may be changed by the program at any time without interrupting code execution.

#### 2.11 Low power select

The P89LPC970/971/972 is designed to run at 18 MHz (CCLK) maximum. However, if CCLK is 8 MHz or slower, the CLKLP SFR bit (AUXR1.7) can be set to a logic 1 to lower the power consumption further. On any reset, CLKLP is logic 0 allowing highest performance. This bit can then be set in software if CCLK is running at 8 MHz or slower.

#### 3. Interrupts

The P89LPC970/971/972 uses a four priority level interrupt structure. This allows great flexibility in controlling the handling of the P89LPC970/971/972's 15 interrupt sources.

Each interrupt source can be individually enabled or disabled by setting or clearing a bit in the interrupt enable registers IEN0 or IEN1. The IEN0 register also contains a global enable bit, EA, which enables all interrupts.

Each interrupt source can be individually programmed to one of four priority levels by setting or clearing bits in the interrupt priority registers IP0, IP0H, IP1, and IP1H. An interrupt service routine in progress can be interrupted by a higher priority interrupt, but not by another interrupt of the same or lower priority. The highest priority interrupt service cannot be interrupted by any other interrupt source. If two requests of different priority levels are received simultaneously, the request of higher priority level is serviced.

If requests of the same priority level are pending at the start of an instruction cycle, an internal polling sequence determines which request is serviced. This is called the arbitration ranking. Note that the arbitration ranking is only used for pending requests of the same priority level. <u>Table 11</u> summarizes the interrupt sources, flag bits, vector addresses, enable bits, priority bits, arbitration ranking, and whether each interrupt may wake-up the CPU from a Power-down mode.

#### 3.1 Interrupt priority structure

Priority bits		
IPxH	IPx	Interrupt priority level
0	0	Level 0 (lowest priority)
0	1	Level 1
1	0	Level 2
1	1	Level 3

#### Table 10.Interrupt priority level

There are four SFRs associated with the four interrupt levels: IP0, IP0H, IP1, IP1H. Every interrupt has two bits in IPx and IPxH (x = 0, 1) and can therefore be assigned to one of four levels, as shown in <u>Table 11</u>.

The P89LPC970/971/972 has two external interrupt inputs in addition to the Keypad Interrupt function. The two interrupt inputs are identical to those present on the standard 80C51 microcontrollers.

These external interrupts can be programmed to be level-triggered or edge-triggered by clearing or setting bit IT1 or IT0 in Register TCON. If ITn = 0, external interrupt n is triggered by a low level detected at the INTn pin. If ITn = 1, external interrupt n is edge triggered. In this mode if consecutive samples of the INTn pin show a high level in one cycle and a low level in the next cycle, interrupt request flag IEn in TCON is set, causing an interrupt request.

Since the external interrupt pins are sampled once each machine cycle, an input high or low level should be held for at least one machine cycle to ensure proper sampling. If the external interrupt is edge-triggered, the external source has to hold the request pin high for at least one machine cycle, and then hold it low for at least one machine cycle. This is to ensure that the transition is detected and that interrupt request flag IEn is set. IEn is automatically cleared by the CPU when the service routine is called. If the external interrupt is level-triggered, the external source must hold the request active until the requested interrupt is generated. If the external interrupt is still asserted when the interrupt service routine is completed, another interrupt will be generated. It is not necessary to clear the interrupt flag IEn when the interrupt is level sensitive, it simply tracks the input pin level.

If an external interrupt has been programmed as level-triggered and is enabled when the P89LPC970/971/972 is put into Power-down mode or Idle mode, the interrupt occurrence will cause the processor to wake-up and resume operation. Refer to <u>Section 5.3 "Power</u> reduction modes" for details. Note: the external interrupt must be programmed as level-triggered to wake-up from Power-down mode.


#### 3.2 External Interrupt pin glitch suppression

Most of the P89LPC970/971/972 pins have glitch suppression circuits to reject short glitches (please refer to the *P89LPC970/971/972 data sheet, Dynamic characteristics* for glitch filter specifications). However, pins SDA/INT0/P1.3 and SCL/T0/P1.2 do not have the glitch suppression circuits. Therefore, INT1 has glitch suppression while INT0 does not.

Description	Interrupt flag bit(s)	Vector address	Interrupt enable bit(s)	Interrupt priority	Arbitration ranking	Power- down wake-up
External interrupt 0	IE0	0003h	EX0 (IEN0.0)	IP0H.0, IP0.0	1 (highest)	Yes
Timer 0 interrupt	TF0	000Bh	ET0 (IEN0.1)	IP0H.1, IP0.1	4	No
External interrupt 1	IE1	0013h	EX1 (IEN0.2)	IP0H.2, IP0.2	7	Yes
Timer 1 interrupt	TF1	001Bh	ET1 (IEN0.3)	IP0H.3, IP0.3	10	No
Serial port Tx and Rx	TI and RI	0023h	ES/ESR (IEN0.4)	IP0H.4, IP0.4	13	No
Serial port Rx	RI					
Brownout detect	BOIF	002Bh	EBO (IEN0.5)	IP0H.5, IP0.5	2	Yes
Watchdog timer/Real-time clock	WDOVF/RTCF	0053h	EWDRT (IEN0.6)	IP0H.6, IP0.6	3	Yes
I <sup>2</sup> C interrupt	SI	0033h	EI2C (IEN1.0)	IP1H.0, IP1.0	5	No
KBI interrupt	KBIF	003Bh	EKBI (IEN1.1)	IP1H.1, IP1.1	8	Yes
Comparators 1 and 2 interrupts	CMF1/CMF2	0043h	EC (IEN1.2)	IP1H.2, IP1.2	11	Yes
SPI interrupt	SPIF	004Bh	ESPI (IEN1.3)	IP1H.3, IP1.3	14	No
Timer 2/3/4	TF2,EXF2	005Bh	EXTIM(IEN1.4)	IP1H.4, IP1.4	6	No
	TF3,EXF3					
	TF4,EXF4					
Serial port Tx	TI	006Bh	EST (IEN1.6)	IP1H.6, IP1.6	12	No

#### Table 11. Summary of interrupts

#### P89LPC970/971/972 User manual



## 4. I/O ports

The P89LPC970/971/972 has four I/O ports: Port 0, Port 1 and Port 3. Ports 0, 1 are 8-bit ports, and Port 3 is a 2-bit port. The exact number of I/O pins available depends upon the clock and reset options chosen (see Table 12).

 Table 12.
 Number of I/O pins available

Clock source	Reset option	Number of I/O pins
On-chip oscillator or watchdog	No external reset (except during power up)	18
oscillator	External RST pin supported	17

Clock source	Reset option	Number of I/O pins
External clock input	No external reset (except during power up)	17
	External RST pin supported	16
Low/medium/high speed oscillator	No external reset (except during power up)	16
(external crystal or resonator)	External RST pin supported	15

#### Table 12. Number of I/O pins available ...continued

#### 4.1 Port configurations

All but three I/O port pins on the P89LPC970/971/972 may be configured by software to one of four types on a pin-by-pin basis, as shown in <u>Table 13</u>. These are: quasi-bidirectional (standard 80C51 port outputs), push-pull, open drain, and input-only. Two configuration registers for each port select the output type for each port pin.

P1.5 (RST) can only be an input and cannot be configured.

P1.2 (SCL/T0) and P1.3 (SDA/INT0) may only be configured to be either input-only or open drain.

PxM1.y	PxM2.y	Port output mode	
0	0	Quasi-bidirectional	
0	1	Push-pull	
1	0	Input only (high-impedance)	
1	1	Open drain	

Table 13. Port output configuration settings

#### 4.2 Quasi-bidirectional output configuration

Quasi-bidirectional outputs can be used both as an input and output without the need to reconfigure the port. This is possible because when the port outputs a logic high, it is weakly driven, allowing an external device to pull the pin low. When the pin is driven low, it is driven strongly and able to sink a large current. There are three pull-up transistors in the quasi-bidirectional output that serve different purposes.

One of these pull-ups, called the 'very weak' pull-up, is turned on whenever the port latch for the pin contains a logic 1. This very weak pull-up sources a very small current that will pull the pin high if it is left floating.

A second pull-up, called the 'weak' pull-up, is turned on when the port latch for the pin contains a logic 1 and the pin itself is also at a logic 1 level. This pull-up provides the primary source current for a quasi-bidirectional pin that is outputting a 1. If this pin is pulled low by an external device, the weak pull-up turns off, and only the very weak pull-up remains on. In order to pull the pin low under these conditions, the external device has to sink enough current to overpower the weak pull-up and pull the port pin below its input threshold voltage.

The third pull-up is referred to as the 'strong' pull-up. This pull-up is used to speed up low-to-high transitions on a quasi-bidirectional port pin when the port latch changes from a logic 0 to a logic 1. When this occurs, the strong pull-up turns on for two CPU clocks quickly pulling the port pin high.


UM10345

The quasi-bidirectional port configuration is shown in Figure 9.

Although the P89LPC970/971/972 is a 3 V device most of the pins are 5 V-tolerant. If 5 V is applied to a pin configured in quasi-bidirectional mode, there will be a current flowing from the pin to  $V_{DD}$  causing extra power consumption. Therefore, applying 5 V to pins configured in quasi-bidirectional mode is discouraged.

A quasi-bidirectional port pin has a Schmitt-triggered input that also has a glitch suppression circuit

(Please refer to the *P89LPC970/971/972 data sheet, Dynamic characteristics* for glitch filter specifications).




#### 4.3 Open drain output configuration

The open drain output configuration turns off all pull-ups and only drives the pull-down transistor of the port pin when the port latch contains a logic 0. To be used as a logic output, a port configured in this manner must have an external pull-up, typically a resistor tied to  $V_{DD}$ . The pull-down for this mode is the same as for the quasi-bidirectional mode.

The open drain port configuration is shown in Figure 10.

An open drain port pin has a Schmitt-triggered input that also has a glitch suppression circuit.


Please refer to the *P89LPC970/971/972 data sheet, Dynamic characteristics* for glitch filter specifications.



#### 4.4 Input-only configuration

The input port configuration is shown in <u>Figure 11</u>. It is a Schmitt-triggered input that also has a glitch suppression circuit.

(Please refer to the *P89LPC970/971/972 data sheet, Dynamic characteristics* for glitch filter specifications).



## 4.5 Push-pull output configuration


The push-pull output configuration has the same pull-down structure as both the open drain and the quasi-bidirectional output modes, but provides a continuous strong pull-up when the port latch contains a logic 1. The push-pull mode may be used when more source current is needed from a port output.

The push-pull port configuration is shown in Figure 12.

A push-pull port pin has a Schmitt-triggered input that also has a glitch suppression circuit.

(Please refer to the *P89LPC970/971/972 data sheet, Dynamic characteristics* for glitch filter specifications).

#### P89LPC970/971/972 User manual



#### 4.6 Port 0 and Analog Comparator functions

The P89LPC970/971/972 incorporates two Analog Comparators. In order to give the best analog performance and minimize power consumption, pins that are being used for analog functions must have both the digital outputs and digital inputs disabled.

Digital outputs are disabled by putting the port pins into the input-only mode as described in the Port Configurations section (see Figure 11).

Digital inputs on Port 0 may be disabled through the use of the PT0AD register. Bits 1 through 5 in this register correspond to pins P0.1 through P0.5 of Port 0, respectively. Setting the corresponding bit in PT0AD disables that pin's digital input. Port bits that have their digital inputs disabled will be read as 0 by any instruction that accesses the port.

On any reset, PT0AD bits 1 through 5 default to logic 0s to enable the digital functions.

#### 4.7 Additional port features

After power-up, all pins are in Input-Only mode. Please note that this is different from the LPC76x series of devices.

- After power-up, all I/O pins except P1.5, may be configured by software.
- Pin P1.5 is input only. Pins P1.2 and P1.3 are configurable for either input-only or open drain.

Every output on the P89LPC970/971/972 has been designed to sink typical LED drive current. However, there is a maximum total output current for all ports which must not be exceeded. Please refer to the *P89LPC970/971/972 data sheet* for detailed specifications.

All ports pins that can function as an output have slew rate controlled outputs to limit noise generated by quickly switching output signals. The slew rate is factory-set to approximately 10 ns rise and fall times.

Table 14.	Port outpu	ut configuration		
Port pin	Configurat	tion SFR bits		
	PxM1.y	PxM2.y	Alternate usage	Notes
P0.0	P0M1.0	P0M2.0	KBI0, CMP2, SPICLK <sup>[1]</sup>	
P0.1	P0M1.1	P0M2.1	KBI1, CIN2B,	Refer to Section 4.6 "Port 0 and
P0.2	P0M1.2	P0M2.2	KBI2, CIN2A,	Analog Comparator functions" for usage as analog inputs.
P0.3	P0M1.3	P0M2.3	KBI3, CIN1B, T2	usage as analog inputs.
P0.4	P0M1.4	P0M2.4	KBI4, CIN1A	
P0.5	P0M1.5	P0M2.5	KBI5, CMPREF, T3	
P0.6	P0M1.6	P0M2.6	KBI6, CMP1	
P0.7	P0M1.7	P0M2.7	KBI7, T1	
P1.0	P1M1.0	P1M2.0	TXD	
P1.1	P1M1.1	P1M2.1	RXD, T2EX	
P1.2	P1M1.2	P1M2.2	T0, SCL	Input-only or open-drain
P1.3	P1M1.3	P1M2.3	ĪNTO, SDA, T4	input-only or open-drain
P1.4	P1M1.4	P1M2.4	INT1,T4EX, SS <sup>[1]</sup>	
P1.5	P1M1.5	P1M2.5	RST	
P1.6	P1M1.6	P1M2.6	MISO <sup>[1]</sup>	
P1.7	P1M1.7	P1M2.7	T3EX, MOSI <sup>[1]</sup>	
P3.0	P3M1.0	P3M2.0	CLKOUT, XTAL2	
P3.1	P3M1.1	P3M2.1	XTAL1	

Table 14.	Port	output	configuration
		output	configuration

[1] For Pin Remap

#### 4.8 Pin Remap

This feature allows the functions of UART/I2C/SPI to be remapped to other pins. Configuration register controls the multiplexers to allow connection between the pins and the on chip peripherals.

UART/I2C/SPI, each has two options of pin configuration: primary pin map and alternative pin map. Please refer to Table 15 for SPI/I2C/UART pin configuration. PINCON register is used to configure the pin remap function. SPI, I2C, UART can be configured separately. Setting the corresponding bit in PINCON register will use the alternative pin map and otherwise use the primary pin map. After reset, UART/I2C/SPI chooses the primary pin map as default. User can adjust to the alternative pin map through configuring PINCON register according to the application. Refer to Table 16 and Table 17 for details.

#### Table 15. SPI/I2C/UART Pin Remap

Peripherals	Function	Primary Pin out	Alternative Pin out
SPI	SPICLK	-	P0.0
	MOSI	-	P1.7
	MISO	-	P1.6
	SS	-	P1.4

Table 15. SPI/I2C/UART PIN Remap						
Peripherals	Function	Primary Pin out	Alternative Pin out			
I2C	SDA	P1.3	-			
	SCL	P1.2	-			
UART	TXD	P1.0	-			
	RXD	P1.1	-			

#### able 15. SPI/I2C/UART Pin Remap

#### Table 16. Pin remap Control register (PINCON - address CFh) bit allocation

Bit	7	6	5	4	3	2	1	0	
Symbol	-	-	-	-	-	-	SPI	-	
Reset	х	х	х	х	х	х	0	х	

#### Table 17. Pin remap Control register (PINCON - address CFh) bit description

Bit	Symbol	Description
0	-	Reserved
1	SPI	When = 0, does not have SPI pinout; when = 1, SPI for alternative pin map is selected.
2	-	When = 0, UART for primary pin map is selected; when = 1, UART for alternative pin map is selected.
3:7	-	Reserved

#### 5. Power management

The P89LPC970/971/972 support a variety of power management features.

Power-on detect and brownout detect are designed to prevent incorrect operation during initial power-up and power loss or reduction during operation.

The P89LPC970/971/972 support three different power reduction modes: Idle mode, Power-down mode, and total Power-down mode. In addition, individual on-chip peripherals can be disabled to eliminate unnecessary dynamic power use in any peripherals that are not required for the application.

Integrated PMU automatically adjusts internal regulators to minimize power consumption during idle mode, Power-down mode and total Power-down mode. In addition, the power consumption can be further reduced in normal or idle mode through configuring regulators mode according to the applications.

#### 5.1 Brownout detection

The brownout detect function determines if the power supply voltage drops below a certain level. Enhanced brownout detection has 3 independent functions: BOD reset, BOD interrupt and BOD FLASH.

These 3 functions are disabled in Power-down mode and Total Power-down mode. In normal or idle mode, BOD reset and BOD flash are always on and can not be disabled in software. BOD interrupt will generate an interrupt and can be enabled or disabled in software.

BOD reset and BOD interrupt, each has 6 levels. BOE0 to BOE2 (UCFG1[3:5]) are used as trip point configuration bits of BOD reset. BOICFG0 to BOICFG2 in register BODCFG are used as trip point configuration bits of BOD interrupt. BOD reset voltage should be lower than BOD interrupt trip point. <u>Table 18</u> and <u>Table 19</u> give BOD trip points configuration.

In Power-down mode (PMOD1/PMOD0 = '10') or total Power-down mode (PMOD1/PMOD0 = '11'), the circuitry for the Brownout Detection is disabled for lowest power consumption. When PMOD1/PMOD0 is not equal to '10' or '11', BOD reset is always on and BOD interrupt is enabled by setting BOI (PCON.4) bit. Please refer <u>Table 20</u> for BOD reset and BOD interrupt configuration. BOF bit (RSTSRC.5), BOD reset flag is default as '0' and is set when BOD reset is tripped. BOIF bit (RSTSRC.6), BOD interrupt flag is default as '0' and is set when BOD interrupt is tripped.

BOD FLASH is used for flash program/erase protection. BOD FLASH is always on, except in power-down or total power down mode (PCON.1=1). It can not be disabled in software. BOD FLASH has only 1 trip voltage level of 2.4 V. When voltage supply is lower than 2.4 V, the BOD FLASH is tripped and flash program/erase is blocked.

If brownout detection works, the brownout condition occurs when  $V_{DD}$  falls below the brownout falling trip voltage and is negated when  $V_{DD}$  rises above the brownout rising trip voltage.

For correct activation of brownout detect, the  $V_{DD}$  rise and fall times must be observed. Please see the data sheet for specifications.

BOE2 (UCFG1.5)	BOE1 (UCFG1.4)	BOE0 (UCFG1.3)	B	OD Reset
			Fall	Rise
0	0	0	reserved	reserved
0	0	1	reserved	reserved
0	1	0	2.25V	2.4V
0	1	1	2.55V	2.7V
1	0	0	2.85V	3.0V
1	0	1	3.15V	3.3V
1	1	0	3.85V	4V
1	1	1	4.05V	4.2V

#### Table 18. BOD reset trip points configuration

#### Table 19. BOD interrupt trip points configuration

BOICFG2 (BODCFG.2)	BOICFG1 (BODCFG.1)	BOICFG0 (BODCFG.0)	BOD Interrupt	
			Fall	Rise
0	0	0	reserved	reserved
0	0	1	reserved	reserved
0	1	0	2.55V	2.7V
0	1	1	2.85V	3.0V
1	0	0	3.0V	3.15V

#### UM10345

.

Table 19.	BOD	interrupt trip p	oints configuration	
BOICFG2		BOICFG1	BOICFG0	BOD Interr
	<b>^</b>			

BOICFG2 (BODCFG.2)	(BODCFG1)	BOICEGO (BODCEG.0)	BOD Interrupt	
			Fall	Rise
1	0	1	3.45V	3.6V
1	1	0	4.15V	4.3V
1	1	1	4.35V	4.5V

#### Table 20. BOD Reset and BOD interrupt configuration

PMOD1/PMOD0 (PCON[1:0])	BOI (PCON.4)	EBO (IEN0.5)	EA (IEN0.7)	BOD Reset	BOD Interrupt
'10' (power-down) or '11' (total power-down)	X	X	x	Ν	Ν
'00' or '01' (normal	0	Х	Х	Y	Ν
or idle mode)	1	0	Х	Y	Ν
		1	0	Y	Ν
		1	1	Y	Y

#### 5.2 Power-on detection

The Power-on detect has a function similar to the brownout detect, but is designed to work as power comes up initially to ensure that the device is reset from Power-on. The POF flag in the RSTSRC register is set to indicate an initial power-up condition. The POF flag will remain set until cleared by software.

#### 5.3 Power reduction modes

The P89LPC970/971/972 supports three different power reduction modes as determined by SFR bits PCON[1:0] (see <u>Table 21</u>).

Table 21.	Power reduction modes									
PMOD1 (PCON.1)	PMOD0 (PCON.0)	Description								
0	0	Normal mode	(default) - no	power reduct	ion.					
0	1	Idle mode. The Idle mode leaves peripherals running in order to allow them to activate th processor when an interrupt is generated. Any enabled interrupt source or reset may term mode.								
1	0	Power-down mode:								
		The Power-down mode stops the oscillator in order to minimize power consumption. Brownout detection circuitry is disabled.								
		The P89LPC970/971/972 exits Power-down mode via any reset, or certain interrupts - external pins INT0/INT1, keyboard, Real-time Clock/System Timer), watchdog, and comparator trips. Waking up by reset is only enabled if the corresponding reset is enabled, and waking up by interrupt is only enabled if the corresponding interrupt is enabled and the EA SFR bit (IEN0.7) is set. External interrupts should be programmed to level-triggered mode to be used to exit Power-down mode.								
		In Power-dowr	In Power-down mode the internal RC oscillator is disabled unless both the RC oscillator has been selected as the system clock AND the RTC is enabled.							
		In Power-down mode, the power supply voltage may be reduced to the RAM keep-alive voltage VRAM. This retains the RAM contents at the point where Power-down mode was entered. SFR contents are not guaranteed after $V_{DD}$ has been lowered to VRAM, therefore it is recommended wake-up the processor via Reset in this situation. $V_{DD}$ must be raised to within the operating ran before the Power-down mode is exited.								
		When the processor wakes up from Power-down mode, it will start the oscillator immediately an begin execution when the oscillator is stable. Oscillator stability is determined by counting 1024 CPU clocks after start-up when one of the crystal oscillator configurations is used, or 200 $\mu$ s to 300 $\mu$ s after start-up for the internal RC, or 32 OSCCLK cycles after start-up for external clock input.								
		Some chip functions continue to operate and draw power during Power-down mode, increat total power used during power-down. These include:								
		<ul> <li>Watchdog Timer when watchdog oscillator or crystal oscillator is selected as the clock source</li> </ul>								
	<ul> <li>Comparators (Note: Comparators can be powered down separately with PCONA. logic 1 and comparators disabled);</li> </ul>							IA.5 set to		
		<ul> <li>Real-time Clock/System Timer (and the crystal oscillator circuitry if this block is using it, RTCPD, i.e., PCONA.7 is logic 1).</li> </ul>								
1	1	The total Powe analog compa					wnout detectior or.	i circuitry and		
		The following are the wake-up options supported:								
	<ul> <li>Watchdog Timer when watchdog oscillator or crystal oscillator is selected as the clock Could generate Interrupt or Reset, either one can wake up the device.</li> </ul>							e clock source.		
		<ul> <li>External interrupts INT0/INT1 (when programmed to level-triggered mode).</li> </ul>								
		Keyboard Interrupt								
			Clock/Syster e., PCONA.7		the crystal os	cillator circuitr	y if this block is	using it, unless		
Table 22.	Power Con	trol register (P	CON - addre	ss 87h) bit a	llocation					
Bit	7	6	5	4	3	2	1	0		
Symbol	SMOD1	SMOD0	-	BOI	GF1	GF0	PMOD1	PMOD0		
	-									

UM10345

Reset

0

0

0

0

0

0

0

-

Bit	Symbol	Description			
0	PMOD0	Power Reduction Mode (see Section 5.3)			
1	PMOD1				
2	GF0	General Purpose Flag 0. May be read or written by user software, but has no effect on operation			
3	GF1	General Purpose Flag 1. May be read or written by user software, but has no effect on operation			
4	BOI	Brownout Detect Interrupt Enable. When logic 1, Brownout Detection will generate a interrupt.			
5	-	Reserved.			
6	SMOD0	Framing Error Location:			
		<ul> <li>When logic 0, bit 7 of SCON is accessed as SM0 for the UART.</li> </ul>			
		<ul> <li>When logic 1, bit 7 of SCON is accessed as the framing error status (FE) for the UART</li> </ul>			
7	SMOD1	Double Baud Rate bit for the serial port (UART) when Timer 1 is used as the baud rate source. When logic 1, the Timer 1 overflow rate is supplied to the UART. When logic 0, the Timer 1 overflow rate is divided by two before being supplied to the UART. (See <u>Section 10</u> )			

#### Table 23. Power Control register (PCON - address 87h) bit description

Table 24.	Power Control register A (PCONA - address B5h) bit allocation								
Bit	7	6	5	4	3	2	1	0	
Symbol	RTCPD	-	VCPD	-	I2PD	SPPD	SPD	-	
Reset	0	х	0	х	0	0	0	х	

#### Table 25. Power Control register A (PCONA - address B5h) bit description

Bit	Symbol	Description
0	-	Reserved
1	SPD	Serial Port (UART) power-down: When logic 1, the internal clock to the UART is disabled. Note that in either Power-down mode or Total Power-down mode, the UART clock will be disabled regardless of this bit.
2	SPPD	SPI power-down: When logic 1, the internal clock to the SPI is disabled. Note that in either Power-down mode or Total Power-down mode, the SPI clock will be disabled regardless of this bit.
3	I2PD	I <sup>2</sup> C power-down: When logic 1, the internal clock to the I <sup>2</sup> C-bus is disabled. Note that in either Power-down mode or Total Power-down mode, the I <sup>2</sup> C clock will be disabled regardless of this bit.
4	-	Reserved
5	VCPD	Analog Voltage Comparators power-down: When logic 1, the voltage comparators are powered down. User must disable the voltage comparators prior to setting this bit.
6	-	Reserved
7	RTCPD	Real-time Clock power-down: When logic 1, the internal clock to the Real-time Clock is disabled.

## 5.4 Regulators

Internal regulators can be adjusted automatically to minimize power consumption during different power reduction modes. In normal or idle modes, power consumption can be further reduced by configuring PMUCON register.

In normal or idle mode, regulators have two operation modes: high speed mode and low current mode.

The regulators can be configured to low current mode to reduce the power consumption.

After power-on-reset, internal regulators enter high speed mode as default. PMUCON register is used to configure the regulators' operation modes. LPMOD bit is used to select the regulators' mode and HCOK bit is used to indicate whether the switch completed or not. When switching back to high speed mode, first clear LPMOD bit to select high speed mode, then check HCOK bit. If HCOK bit turns to '1', it means the switch was completed.

#### Table 26. PMU Control register (PMUCON - address FAh) bit allocation

Bit	7	6	5	4	3	2	1	0
Symbol	LPMOD	-	-	-	-	-	-	HCOK
Reset	0	х	х	Х	X	х	Х	1

#### Table 27. PMU control register (PMUCON - address FAh) bit description

Bit	Symbol	Description
0	HCOK	Regulators mode flag. HCOK bit is set when the switch from low current mode to high speed mode is completed. It is cleared when switching to low current mode. This bit can be reset only by POR reset.
1:6	-	Reserved
7	LPMOD	Low current mode control. When cleared, high speed mode is selected; when set, low current mode is selected.

# 6. Reset

The P1.5/RST pin can function as either an active low reset input or as a digital input, P1.5. The RPE (Reset Pin Enable) bit in UCFG1, when set to 1, enables the external reset input function on P1.5. When cleared, P1.5 may be used as an input pin.

**Remark:** During a power-on sequence, The RPE selection is overridden and this pin will always functions as a reset input. An external circuit connected to this pin should not hold this pin low during a Power-on sequence as this will keep the device in reset. After power-on this input will function either as an external reset input or as a digital input as defined by the RPE bit. Only a power-on reset will temporarily override the selection defined by RPE bit. Other sources of reset will not override the RPE bit.


Reset can be triggered from the following sources:

- External reset pin (during power-on or if user configured via UCFG1);
- Power-on detect;
- Brownout detect;
- Watchdog timer;
- Software reset;

• UART break character detect reset.

For every reset source, there is a flag in the Reset Register, RSTSRC. The user can read this register to determine the most recent reset source. These flag bits can be cleared in software by writing a '0' to the corresponding bit. More than one flag bit may be set:

- During a power-on reset, both POF and BOF are set but the other flag bits are cleared.
- A watchdog reset is similar to a power-on reset, both POF and BOF are set but the other flag bits are cleared.
- For any other reset, previously set flag bits that have not been cleared will remain set.



#### Table 28. Reset Sources register (RSTSRC - address DFh) bit allocation

Bit	7	6	5	4	3	2	1	0
Symbol	-	BOIF	BOF	POF	R_BK	R_WD	R_SF	R_EX
Reset <sup>[1]</sup>	Х	0	1	1	0	0	0	0

[1] The value shown is for a power-on reset. Other reset sources will set their corresponding bits.

#### Table 29. Reset Sources register (RSTSRC - address DFh) bit description

Bit	Symbol	Description
0	R_EX	external reset Flag. When this bit is logic 1, it indicates external pin reset. Cleared by software by writing a logic 0 to the bit or a Power-on reset. If RST is still asserted after the Power-on reset is over, R_EX will be set.
1	R_SF	software reset Flag. Cleared by software by writing a logic 0 to the bit or a Power-on reset
2	R_WD	Watchdog Timer reset flag. Cleared by software by writing a logic 0 to the bit or a Power-on reset.(NOTE: UCFG2.7 must be = 1)
3	R_BK	break detect reset. If a break detect occurs and EBRR (AUXR1.6) is set to logic 1, a system reset will occur. This bit is set to indicate that the system reset is caused by a break detect. Cleared by software by writing a logic 0 to the bit or on a Power-on reset.
4	POF	Power-on Detect Flag. When Power-on Detect is activated, the POF flag is set to indicate an initial power-up condition. The POF flag will remain set until cleared by software by writing a logic 0 to the bit. (Note: On a Power-on reset, both BOF and this bit will be set while the other flag bits are cleared.)

Bit	Symbol	Description
5	BOF	BOD Reset Flag. When BOD Reset is activated, this bit is set. It will remain set until cleared by software by writing a logic 0 to the bit. (Note: On a Power-on reset, both POF and this bit will be set while the other flag bits are cleared.)
6	BOIF	BOD Interrupt Flag. When BOD Interrupt is activated, this bit is set. It will remain set until cleared by software by writing a logic 0 to the bit.
7	-	reserved

#### Table 29. Reset Sources register (RSTSRC - address DFh) bit description ... continued

### 6.1 Reset vector

Following reset, the P89LPC970/971/972 will fetch instructions from either address 0000h or the Boot address. The Boot address is formed by using the Boot Vector as the high byte of the address and the low byte of the address = 00h. The Boot address will be used if a UART break reset occurs or the non-volatile Boot Status bit (BOOTSTAT.0) = 1, or the device has been forced into ISP mode. Otherwise, instructions will be fetched from address 0000H.

# 7. Timers 0 and 1

The P89LPC970/971/972 has two general-purpose counter/timers which are upward compatible with the 80C51 Timer 0 and Timer 1. Both can be configured to operate either as timers or event counters (see <u>Table 31</u>). An option to automatically toggle the Tx pin upon timer overflow has been added.

In the 'Timer' function, the timer is incremented every PCLK.

In the 'Counter' function, the register is incremented in response to a 1-to-0 transition on its corresponding external input pin (T0 or T1). The external input is sampled once during every machine cycle. When the pin is high during one cycle and low in the next cycle, the count is incremented. The new count value appears in the register during the cycle following the one in which the transition was detected. Since it takes two machine cycles (four CPU clocks) to recognize a 1-to-0 transition, the maximum count rate is  $\frac{1}{4}$  of the CPU clock frequency. There are no restrictions on the duty cycle of the external input signal, but to ensure that a given level is sampled at least once before it changes, it should be held for at least one full machine cycle.

The 'Timer' or 'Counter' function is selected by control bits  $TnC/\overline{T}$  (x = 0 and 1 for Timers 0 and 1 respectively) in the Special Function Register TMOD. Timer 0 and Timer 1 have five operating modes (modes 0, 1, 2, 3 and 6), which are selected by bit-pairs (TnM1, TnM0) in TMOD and TnM2 in TAMOD. Modes 0, 1, 2 and 6 are the same for both Timers/Counters. Mode 3 is different. The operating modes are described later in this section.

Bit	7	6	5	4	3	2	1	0
Symbol	T1GATE	T1C/T	T1M1	T1M0	TOGATE	T0C/T	T0M1	T0M0
Reset	0	0	0	0	0	0	0	0

#### Table 30. Timer/Counter Mode register (TMOD - address 89h) bit allocation

UM10345

Bit	Symbol	Description
0	T0M0	Mode Select for Timer 0. These bits are used with the T0M2 bit in the TAMOD register to determine the
1	T0M1	Timer 0 mode (see <u>Table 33</u> ).
2	T0C/T	Timer or Counter selector for Timer 0. Cleared for Timer operation (input from CCLK). Set for Counter operation (input from T0 input pin).
3	TOGATE	Gating control for Timer 0. When set, Timer/Counter is enabled only while the INT0 pin is high and the TR0 control pin is set. When cleared, Timer 0 is enabled when the TR0 control bit is set.
4	T1M0	Mode Select for Timer 1. These bits are used with the T1M2 bit in the TAMOD register to determine the
5	T1M1	Timer 1 mode (see <u>Table 33</u> ).
6	T1C/T	Timer or Counter Selector for Timer 1. Cleared for Timer operation (input from CCLK). Set for Counter operation (input from T1 input pin).
7	T1GATE	Gating control for Timer 1. When set, Timer/Counter is enabled only while the INT1 pin is high and the TR1 control pin is set. When cleared, Timer 1 is enabled when the TR1 control bit is set.

### Table 31. Timer/Counter Mode register (TMOD - address 89h) bit description

Table 32. Timer/Counter Auxiliary M	Node register (TAMOD - address 8Fh) bit allocatior	۱
-------------------------------------	--	---

Bit	7	6	5	4	3	2	1	0
Symbol		-	-	T1M2	-	-	-	T0M2
Reset	х	х	х	0	х	X	х	0

#### Table 33. Timer/Counter Auxiliary Mode register (TAMOD - address 8Fh) bit description

Bit	Symbol	Description
0	T0M2	Mode Select for Timer 0. These bits are used with the T0M2 bit in the TAMOD register to determine the Timer 0 mode (see <u>Table 33</u> ).
1:3	-	reserved
4	T1M2	Mode Select for Timer 1. These bits are used with the T1M2 bit in the TAMOD register to determine the Timer 1 mode (see <u>Table 33</u> ).
		The following timer modes are selected by timer mode bits TnM[2:0]:
		000 — 8048 Timer 'TLn' serves as 5-bit prescaler. (Mode 0)
		001 — 16-bit Timer/Counter 'THn' and 'TLn' are cascaded; there is no prescaler.(Mode 1)
		<b>010</b> — 8-bit auto-reload Timer/Counter. THn holds a value which is loaded into TLn when it overflows. (Mode 2)
		<b>011</b> — Timer 0 is a dual 8-bit Timer/Counter in this mode. TL0 is an 8-bit Timer/Counter controlled by the standard Timer 0 control bits. TH0 is an 8-bit timer only, controlled by the Timer 1 control bits (see text). Timer 1 in this mode is stopped. (Mode 3)
		100 — Reserved. User must not configure to this mode.
		101 — Reserved. User must not configure to this mode.
		110 — PWM mode (see <u>Section 7.5</u> ).
		111 — Reserved. User must not configure to this mode.
5:7	-	reserved

## 7.1 Mode 0

Putting either Timer into Mode 0 makes it look like an 8048 Timer, which is an 8-bit Counter with a divide-by-32 prescaler. Figure 14 shows Mode 0 operation.

In this mode, the Timer register is configured as a 13-bit register. As the count rolls over from all 1s to all 0s, it sets the Timer interrupt flag TFn. The count input is enabled to the Timer when TRn = 1 and either TnGATE = 0 or INTn = 1. (Setting TnGATE = 1 allows the Timer to be controlled by external input INTn, to facilitate pulse width measurements). TRn is a control bit in the Special Function Register TCON (Table 35). The TnGATE bit is in the TMOD register.

The 13-bit register consists of all 8 bits of THn and the lower 5 bits of TLn. The upper 3 bits of TLn are indeterminate and should be ignored. Setting the run flag (TRn) does not clear the registers.

Mode 0 operation is the same for Timer 0 and Timer 1. See Figure 14. There are two different GATE bits, one for Timer 1 (TMOD.7) and one for Timer 0 (TMOD.3).

## 7.2 Mode 1

Mode 1 is the same as Mode 0, except that all 16 bits of the timer register (THn and TLn) are used. See Figure 15.

## 7.3 Mode 2

Mode 2 configures the Timer register as an 8-bit Counter (TLn) with automatic reload, as shown in <u>Figure 16</u>. Overflow from TLn not only sets TFn, but also reloads TLn with the contents of THn, which must be preset by software. The reload leaves THn unchanged. Mode 2 operation is the same for Timer 0 and Timer 1.

## 7.4 Mode 3

When Timer 1 is in Mode 3 it is stopped. The effect is the same as setting TR1 = 0.

Timer 0 in Mode 3 establishes TL0 and TH0 as two separate 8-bit counters. The logic for Mode 3 on Timer 0 is shown in Figure 17. TL0 uses the Timer 0 control bits: T0C/T, T0GATE, TR0, INT0, and TF0. TH0 is locked into a timer function (counting machine cycles) and takes over the use of TR1 and TF1 from Timer 1. Thus, TH0 now controls the 'Timer 1' interrupt.

Mode 3 is provided for applications that require an extra 8-bit timer. With Timer 0 in Mode 3, an P89LPC970/971/972 device can look like it has three Timer/Counters.

Note: When Timer 0 is in Mode 3, Timer 1 can be turned on and off by switching it into and out of its own Mode 3. It can still be used by the serial port as a baud rate generator, or in any application not requiring an interrupt.

## 7.5 Mode 6

In this mode, the corresponding timer can be changed to a PWM with a full period of 256 timer clocks (see Figure 18). Its structure is similar to mode 2, except that:


- TFn (n = 0 and 1 for Timers 0 and 1 respectively) is set and cleared in hardware;
- The low period of the TFn is in THn, and should be between 1 and 254, and;
- The high period of the TFn is always 256–THn.
- Loading THn with 00h will force the Tx pin high, loading THn with FFh will force the Tx pin low.


Note that interrupt can still be enabled on the low to high transition of TFn, and that TFn can still be cleared in software like in any other modes.


Table 34.	Timer/Cou	Timer/Counter Control register (TCON) - address 88h) bit allocation							
Bit	7	6	5	4	3	2	1	0	
Symbol	TF1	TR1	TF0	TR0	IE1	IT1	IE0	IT0	
Reset	0	0	0	0	0	0	0	0	


### Table 35. Timer/Counter Control register (TCON - address 88h) bit description

Bit	Symbol	Description
0	IT0	Interrupt 0 Type control bit. Set/cleared by software to specify falling edge/low level triggered external interrupts.
1	IE0	Interrupt 0 Edge flag. Set by hardware when external interrupt 0 edge is detected. Cleared by hardware when the interrupt is processed, or by software.
2	IT1	Interrupt 1 Type control bit. Set/cleared by software to specify falling edge/low level triggered external interrupts.
3	IE1	Interrupt 1 Edge flag. Set by hardware when external interrupt 1 edge is detected. Cleared by hardware when the interrupt is processed, or by software.
4	TR0	Timer 0 Run control bit. Set/cleared by software to turn Timer/Counter 0 on/off.
5	TF0	Timer 0 overflow flag. Set by hardware on Timer/Counter overflow. Cleared by hardware when the processor vectors to the interrupt routine, or by software. (except in mode 6, where it is cleared in hardware)
6	TR1	Timer 1 Run control bit. Set/cleared by software to turn Timer/Counter 1 on/off
7	TF1	Timer 1 overflow flag. Set by hardware on Timer/Counter overflow. Cleared by hardware when the interrupt is processed, or by software (except in mode 6, see above, when it is cleared in hardware).










UM10345



## 7.6 Timer overflow toggle output

Timers 0 and 1 can be configured to automatically toggle a port output whenever a timer overflow occurs. The same device pins that are used for the T0 and T1 count inputs and PWM outputs are also used for the timer toggle outputs. This function is enabled by control bits ENT0 and ENT1 in the AUXR1 register, and apply to Timer 0 and Timer 1 respectively. The port outputs will be a logic 1 prior to the first timer overflow when this mode is turned on. In order for this mode to function, the C/T bit must be cleared selecting PCLK as the clock source for the timer.

# 8. Timers 2, 3 and 4

The P89LPC970/971/972 has three external 16-bit timers/counters. All can be configured to operate either as timers or event counters. An option to automatically toggle the Tx pin upon timer overflow has been added.

In the 'Timer' function, the timer is incremented every PCLK.

In the 'Counter' function, the register is incremented in response to a 1-to-0 transition on its corresponding count input pin (T2/T3/T4). The count input is sampled once during every machine cycle. When the pin is high during one cycle and low in the next cycle, the count is incremented. The new count value appears in the register during the cycle following the one in which the transition was detected. Since it takes two machine cycles (four CPU clocks) to recognize a 1-to-0 transition, the maximum count rate is  $\frac{1}{4}$  of the CPU clock frequency. There are no restrictions on the duty cycle of the count input signal, but to ensure that a given level is sampled at least once before it changes, it should be held for at least one full machine cycle.

Only external Timer 2/3/4 has the external input pin TxEX(x=2, 3 or 4). When EXENx = 1, a 1-to-0 transition on this pin can trigger a reload or capture event.

Timer 2, Timer 3 and Timer 4 have three operating modes, which are selected by PWMx(TxCON.4), C/NTx(TxCON.1) and CP/NRLx(TxCON.0) in TxCON (where x = 2, 3 or 4 for Timers 2, 3 or 4 respectively).

Table 36.	Timer/Counter x Control (TxCON - where x = 2, 3 or 4) bit allocation	1
-----------	--	---

Bit	7	6	5	4	3	2	1	0
Symbol	PSELx	ENTx	TIENx	PWMx	EXENx	TRx	C/NTx	CP/NRLx
Reset	0	0	0	0	0	0	0	0

© NXP B.V. 2010. All rights reserved.

Bit	Symbol	Description
0	CP/NRLx	Capture/Reload control. When set, captures occur on 1-to-0 transitions of TxEX (if EXENx is set). When cleared, auto-reloads are performed on timer overflows or on negative transitions of TxEX (if EXENx is set).
1	C/NTx	Timer/Counter select. Cleared for Timer operation (input from PCLK). Set for Counter operation (input from Tx input pin).
2	TRx	Timer x Run control bit. Set/cleared by software to turn Timer/Counter x on/off.
3	EXENx	When set, a falling edge on TxEX will trigger a capture or auto-reload.
4	PWMx	PWM control bit. When set, PWM function of corresponding channel is enabled, at the same time, Tx pin outputs as a PWM output pin. Before enable PWM function, timer function and auto-reload function must be selected.
5	TIENx	Timer x interrupt enable.
6	ENTx	Enable Tx pin output in 16-bit auto reload mode or PWM mode. When set, if 16-bit auto reload timer or PWM mode is selected, Tx pin will be toggled upon the counter overflow.
7	PSELx	Tx pin output polarity selection. When 0, Tx pin outputs original polarity; when 1, Tx pin outputs inversed polarity.

### Table 37. Timer/Counter x Control (TxCON - where x = 2, 3 or 4) bit description

Table 38.	Timer/Co	imer/Counters Overflow and External Flags (TINTF, address CEh) bit allocation						
Bit	7	6	5	4	3	2	1	0
Symbol		-	TF4	EXF4	TF3	EXF3	TF2	EXF2
Reset	х	х	0	0	0	0	0	0

### Table 39. Timer/Counters Overflow and External Flags (TINTF, address CEh) bit description

Bit	Symbol	Description
0	EXF2	Timer 2 external flag. This bit is set when a capture or reload is triggered by a negative transition on T2EX and EXEN2 is set. If the Timer 2 interrupt is enabled, setting this bit will cause an interrupt to the Xtimer vector.
1	TF2	Timer 2 overflow flag. Set by hardware when Timer/Counter 2 overflows. If the Timer 2 interrupt is enabled, setting this bit will cause an interrupt to the Xtimer vector. This bit is not cleared by hardware when the processor calls the interrupt service routine.
2	EXF3	Timer 3 external flag. This bit is set when a capture or reload is triggered by a negative transition on T3EX and EXEN3 is set. If the Timer 3 interrupt is enabled, setting this bit will cause an interrupt to the Xtimer vector.
3	TF3	Timer 3 overflow flag. Set by hardware when Timer/Counter 3 overflows. If the Timer 3 interrupt is enabled, setting this bit will cause an interrupt to the Xtimer vector. This bit is not cleared by hardware when the processor calls the interrupt service routine.
4	EXF4	Timer 4 external flag. This bit is set when a capture or reload is triggered by a negative transition on T4EX and EXEN4 is set. If the Timer 4 interrupt is enabled, setting this bit will cause an interrupt to the Xtimer vector.
5	TF4	Timer 4 overflow flag. Set by hardware when Timer/Counter 4 overflows. If the Timer 4 interrupt is enabled, setting this bit will cause an interrupt to the Xtimer vector. This bit is not cleared by hardware when the processor calls the interrupt service routine.
6:7	-	Reserved

Label	Description	Address	Reset Value
TH2	Timer/Counter 2 High Byte	FEH	00
TL2	Timer/Counter 2 Low Byte	FDH	00
RCAP2H	Capture Register 2 High Byte	FCH	00
RCAP2L	Capture Register 2 Low Byte	FBH	00
PWMD2H	PWM Free Cycle Register 2 High Byte	AEH	00
PWMD2L	PWM Free Cycle Register 2 Low Byte	AFH	00
TH3	Timer/Counter 3 High Byte	EEH	00
TL3	Timer/Counter 3 Low Byte	EDH	00
RCAP3H	Capture Register 3 High Byte	ECH	00
RCAP3L	Capture Register 3 Low Byte	EBH	00
PWMD3H	PWM Free Cycle Register 3 High Byte	E9H	00
PWMD3L	PWM Free Cycle Register 3 Low Byte	EAH	00
TH4	Timer/Counter 4 High Byte	CCH	00
TL4	Timer/Counter 4 Low Byte	СВН	00
RCAP4H	Capture Register 4 High Byte	CAH	00
RCAP4L	Capture Register 4 Low Byte	С9Н	00
PWMD4H	PWM Free Cycle Register 4 High Byte	AAH	00
PWMD4L	PWM Free Cycle Register 4 Low Byte	ABH	00

#### Table 40. Data register map

### 8.1 Mode 0: 16-bit Timer/Counter with Auto-reload

Mode 0 configures Timer x as a 16-bit Timer/Counter with auto-reload, as shown in Figure 19. (Where x = 2, 3, 4)


In this mode, Timer x can be configured as either a timer or counter via C/NTx in TxCON and then programmed to count up. (Where x = 2, 3, 4)

There are two options to trigger the auto-reload that can be selected by EXENx bit (TxCON.3).

When EXENx is cleared, Timer x counts up to 0FFFFH and sets the TFx bit upon overflow. This causes the Timer x registers to be reloaded with the 16-bit value in RCAPxL and RCAPxH, which are preset by software.

When EXENx is set, the 16-bit reload can be triggered by not only the overflow of Timer x but also a 1-to-0 transition at input TxEX. This transition also sets the EXFx bit. It takes two consecutive machine cycles to recognize falling edge on TxEX and another one machine cycle to set EXFx.

The Timer x interrupt, if enabled, can be generated when TFx or EXFx is set.



## 8.2 Mode 1: 16-bit Timer/Counter with Input Capture

Mode 1 configures Timer x as a 16-bit Timer/Counter with input capture, as shown in Figure 20. (Where x = 2, 3, 4)


In this mode, there are also two options selected by EXENx bit (TxCON.3).

If EXENx is cleared, Timer x is a 16-bit timer/counter (selected by C/NTx in TxCON). When overflow occurs, TFx bit in the TINTF register will be set. The Timer x interrupt, if enabled, can be generated when TFx or EXFx is set.

If EXENx is set, when a 1- to -0 transition occurs at external input TxEX, the current value in the Timer x register TLx:THx is captured to the corresponding 16-bit register RCAPxL:RCAPxH. In addition, the transition at TxEX will set EXFx bit in TINTF. EXFx bit, like TFx bit, can generate an interrupt (which vectors to the same location as Timer x overflow interrupt). The Timer x interrupt service routine can check TFx and EXFx to determine which event causes the interrupt.

In this mode, TLx and THx registers keep on counting 1-to-0 transitions at Tx pin or PCLK, regardless of whether the capture event happens or not. Since the contents of RCAPxL:RCAPxH register are not protected, once Timer x interrupt is generated, the value in register RCAPxL:RCAPxH should be read before new capture event on TxEX pin occurs. Otherwise, the next falling edge on TxEX pin will initiate the capture of the current value from TLx:THx to RCAPxL:RCAPxH and corrupt the captured contents of the previously interrupt.

UM10345



### 8.3 Mode 2: 16-bit PWM mode

In PWM mode, the corresponding timer can be configured as a PWM generator. And the RCAPxH and RCAPxL registers are also used as PWM duty cycle Registers. The duty cycle of the PWM waveform can be adjusted through the following formula:

Duty Cycle = RCAPxH:RCAPxL / (RCAPxH:RCAPxL + PWMDxH:PWMDxL)(1)


In addition, PWM output has a polarity control function. When control register bit PSELx is set, PWM will output an inversed waveform.


Figure 21 illustrates the Tx pin output when timer x operating in PWM mode.

Its structure is similar to auto-reload mode, except that:

- TFx (where x = 2, 3 or 4) is set and cleared in hardware;
- The high period of the TFx is in RCAPxH:RCAPxL, and the low period of TFx is PWMDxH:PWMDxL. They should be between 1 and 65536;
- Only loading RCAPxH:RCAPxL with 0000h will force the Tx pin low, and only loading PWMDxH:PWMDxL with 0000h will force the Tx pin high. Loading both RCAPxH:RCAPxL and PWMDxH:PWMDxL with 0000h will force the Tx pin high.

Note that interrupt can still be enabled on the low to high transition of TFx and TFx can be cleared in software like in other modes.





## 8.4 Timer overflow toggle output

Timer x (where x = 2, 3 or 4) can be configured to automatically toggle a port output whenever a timer overflow occurs. The same device pins that are used for the Tx counter inputs and PWM outputs are also used for the timer toggle outputs. This function is enabled by control bits ENTx in TxCON. The port outputs will be a logic '1' prior to the first timer overflow when this mode is turned on. In order to enable this mode, the C/NTx must be cleared, selecting PCLK as the clock source for the timer.

# 9. Real-time clock system timer

The P89LPC970/971/972 has a simple Real-time Clock/System Timer that allows a user to continue running an accurate timer while the rest of the device is powered down. The Real-time Clock can be an interrupt or a wake-up source (see Figure 23).

The Real-time Clock is a 23-bit down counter. The clock source for this counter can be either the CPU clock (CCLK) or the XTAL1-2 oscillator. There are five SFRs used for the RTC:

**RTCCON** — Real-time Clock control.

**RTCH** — Real-time Clock counter reload high (bits 22 to 15).

**RTCL** — Real-time Clock counter reload low (bits 14 to 7).

**RTCDATH** — Real-time clock data register high.


**RTCDATL** — Real-time Clock data register low.

© NXP B.V. 2010. All rights reserved.

UM10345

The Real-time clock system timer can be enabled by setting the RTCEN (RTCCON.0) bit. The Real-time Clock is a 23-bit down counter (initialized to all 0's when RTCEN = 0) that is comprised of a 7-bit prescaler and a 16-bit loadable down counter. When RTCEN is written with logic 1, the counter is first loaded with (RTCH, RTCL, '111111') and will count down. When it reaches all 0's, the counter will be reloaded again with (RTCH, RTCL, '111111') and a flag - RTCF (RTCCON.7) - will be set.

The 16-bit counter portion of the RTC is readable by reading the RTCDATH and RTCDATL registers.



## 9.1 Real-time clock source

RTCS1/RTCS0 (RTCCON[6:5]) are used to select the clock source for the RTC if either the Internal RC oscillator or the internal WD oscillator is used as the CPU clock. If the internal crystal oscillator or the external clock input on XTAL1 is used as the CPU clock, then the RTC will use CCLK as its clock source.

# 9.2 Changing RTCS1/RTCS0

RTCS1/RTCS0 cannot be changed if the RTC is currently enabled (RTCCON.0 = 1). Setting RTCEN and updating RTCS1/RTCS0 may be done in a single write to RTCCON. However, if RTCEN = 1, this bit must first be cleared before updating RTCS1/RTCS0.

## 9.3 Real-time clock interrupt/wake-up

If ERTC (RTCCON.1), EWDRT (IEN1.0.6) and EA (IEN0.7) are set to logic 1, RTCF can be used as an interrupt source. This interrupt vector is shared with the watchdog timer. It can also be a source to wake-up the device.

### 9.3.1 Real-time clock read back

Users can read RTCDATH and RTCDATL registers and get the 16-bit counter portion of the RTC.

# 9.4 Reset sources affecting the Real-time clock

Only power-on reset and watchdog reset will reset the Real-time Clock and its associated SFRs to their default state.

FOSC2:0	RCCLK	RTCS1:0	RTC clock source	CPU clock source	
000	0	00	High frequency crystal	High frequency crystal	
		01		/DIVM	
		10			
		11	High frequency crystal /DIVM		
	1 00 High frequency crystal	Internal RC oscillator			
		01			
		10			
		11	Internal RC oscillator		
001	0	00	Medium frequency crystal	Medium frequency crysta	
		01		/DIVM	
		10			
		11	Medium frequency crystal /DIVM		
	1	00	Medium frequency crystal	Internal RC oscillator	
		01			
		10			
		11	Internal RC oscillator		
010	0	00	Low frequency crystal	Low frequency crystal	
		01		/DIVM	
		10			
		11	Low frequency crystal /DIV		
	1	00	Low frequency crystal	Internal RC oscillator	
		01			
		10			
		11	Internal RC oscillator		

 Table 41.
 Real-time Clock/System Timer clock sources

OSC2:0	RCCLK	RTCS1:0	RTC clock source	CPU clock source	
011	0	00	High frequency crystal	Internal RC oscillator	
		01	Medium frequency crystal	/DIVM	
		10	Low frequency crystal		
		11	Internal RC oscillator /DIVM		
	1	00	High frequency crystal	Internal RC oscillator	
		01	Medium frequency crystal		
		10	Low frequency crystal		
		11	Internal RC oscillator		
100	0	00	High frequency crystal	Watchdog oscillator	
		01	Medium frequency crystal	/DIVM	
		10	Low frequency crystal		
		11	Watchdog oscillator /DIVM		
	1	00	High frequency crystal	Internal RC oscillator	
		01	Medium frequency crystal		
		10	Low frequency crystal		
		11	Internal RC oscillator		
101	х	xx	undefined	undefined	
110	х	xx	undefined	undefined	
111	0	00	External clock input	External clock input	
		01		/DIVM	
		10			
		11	External clock input /DIVM		
	1	00	External clock input	Internal RC oscillator	
		01			
		10			
		11	Internal RC oscillator		

### Table 41. Real-time Clock/System Timer clock sources ...continued

### Table 42. Real-time Clock Control register (RTCCON - address D1h) bit allocation

Bit	7	6	5	4	3	2	1	0
Symbol	RTCF	RTCS1	RTCS0	-	-	-	ERTC	RTCEN
Reset	0	1	1	х	х	х	0	0

Table 12	Pool time Clock Control register (P		hit description
Table 45.	Real-time Clock Control register (R	address Ding	bit description

Bit	Symbol	Description
0	RTCEN	Real-time Clock enable. The Real-time Clock will be enabled if this bit is logic 1. Note that this bit will not power-down the Real-time Clock. The RTCPD bit (PCONA.7) if set, will power-down and disable this block regardless of RTCEN.
1	ERTC	Real-time Clock interrupt enable. The Real-time Clock shares the same interrupt as the watchdog timer. Note that if the user configuration bit WDTE (UCFG2.7) is logic 0, the watchdog timer can be enabled to generate an interrupt. Users can read the RTCF (RTCCON.7) bit to determine whether the Real-time Clock caused the interrupt.
2:4	-	reserved
5	RTCS0	Real-time Clock source select (see Table 41).
6	RTCS1	
7	RTCF	Real-time Clock Flag. This bit is set to logic 1 when the 23-bit Real-time Clock reaches a count of logic 0. It can be cleared in software.

# **10. UART**

The P89LPC970/971/972 has an enhanced UART that is compatible with the conventional 80C51 UART except that Timer 2 overflow cannot be used as a baud rate source. The P89LPC970/971/972 does include an independent Baud Rate Generator. The baud rate can be selected from the oscillator (divided by a constant), Timer 1 overflow, or the independent Baud Rate Generator. In addition to the baud rate generation, enhancements over the standard 80C51 UART include Framing Error detection, break detect, automatic address recognition, selectable double buffering and several interrupt options.

The UART can be operated in 4 modes, as described in the following sections.

### 10.1 Mode 0

Serial data enters and exits through RXD. TXD outputs the shift clock. 8 bits are transmitted or received, LSB first. The baud rate is fixed at  $\frac{1}{16}$  of the CPU clock frequency.

## 10.2 Mode 1

10 bits are transmitted (through TXD) or received (through RXD): a start bit (logic 0), 8 data bits (LSB first), and a stop bit (logic 1). When data is received, the stop bit is stored in RB8 in Special Function Register SCON. The baud rate is variable and is determined by the Timer 1 overflow rate or the Baud Rate Generator (see <u>Section 10.6 "Baud Rate</u> <u>generator and selection"</u>).

### 10.3 Mode 2

11 bits are transmitted (through TXD) or received (through RXD): start bit (logic 0), 8 data bits (LSB first), a programmable 9th data bit, and a stop bit (logic 1). When data is transmitted, the 9th data bit (TB8 in SCON) can be assigned the value of 0 or 1. Or, for

example, the parity bit (P, in the PSW) could be moved into TB8. When data is received, the 9th data bit goes into RB8 in Special Function Register SCON and the stop bit is not saved. The baud rate is programmable to either  $1/_{16}$  or  $1/_{32}$  of the CCLK frequency, as determined by the SMOD1 bit in PCON.

## 10.4 Mode 3

11 bits are transmitted (through TXD) or received (through RXD): a start bit (logic 0), 8 data bits (LSB first), a programmable 9th data bit, and a stop bit (logic 1). Mode 3 is the same as Mode 2 in all respects except baud rate. The baud rate in Mode 3 is variable and is determined by the Timer 1 overflow rate or the Baud Rate Generator (see <u>Section 10.6</u> "Baud Rate generator and selection").

In all four modes, transmission is initiated by any instruction that uses SBUF as a destination register. Reception is initiated in Mode 0 by the condition RI = 0 and REN = 1. Reception is initiated in the other modes by the incoming start bit if REN = 1.

## 10.5 SFR space

The UART SFRs are at the following locations:

Register	Description	SFR location
PCON	Power Control	87H
SCON	Serial Port (UART) Control	98H
SBUF	Serial Port (UART) Data Buffer	99H
SADDR	Serial Port (UART) Address	A9H
SADEN	Serial Port (UART) Address Enable	B9H
SSTAT	Serial Port (UART) Status	BAH
BRGR1	Baud Rate Generator Rate High Byte	BFH
BRGR0	Baud Rate Generator Rate Low Byte	BEH
BRGCON	Baud Rate Generator Control	BDH

#### Table 44.UART SFR addresses

### **10.6 Baud Rate generator and selection**

The P89LPC970/971/972 enhanced UART has an independent Baud Rate Generator. The baud rate is determined by a value programmed into the BRGR1 and BRGR0 SFRs. The UART can use either Timer 1 or the baud rate generator output as determined by BRGCON[2:1] (see Figure 24). Note that Timer T1 is further divided by 2 if the SMOD1 bit (PCON.7) is set. The independent Baud Rate Generator uses CCLK.

## 10.7 Updating the BRGR1 and BRGR0 SFRs

The baud rate SFRs, BRGR1 and BRGR0 must only be loaded when the Baud Rate Generator is disabled (the BRGEN bit in the BRGCON register is logic 0). This avoids the loading of an interim value to the baud rate generator. (CAUTION: If either BRGR0 or BRGR1 is written when BRGEN = 1, the result is unpredictable.)

Table 45.	UART	baud	rate	generation
-----------	------	------	------	------------


SCON.7 (SM0)	SCON.6 (SM1)	PCON.7 (SMOD1)	BRGCON.1 (SBRGS)	Receive/transmit baud rate for UART
0	0	Х	х	CCLK <sub>16</sub>
0	1	0	0	CCLK (256-TH1)64
		1	0	CCLK (256-TH1)32
		Х	1	CCLK (BRGR1,BRGR0)+16)
1	0	0	Х	CCLK <sub>32</sub>
		1	Х	CCLK <sub>16</sub>
1	1	0	0	CCLK (256-TH1)64
		1	0	CCLK (256-TH1)32
		Х	1	CCLK <sub>(BRGR1,BRGR0)+16)</sub>

#### Table 46. Baud Rate Generator Control register (BRGCON - address BDh) bit allocation

Bit	7	6	5	4	3	2	1	0
Symbol		-	-	-	-	-	SBRGS	BRGEN
Reset	х	х	х	х	х	х	0	0

#### Table 47. Baud Rate Generator Control register (BRGCON - address BDh) bit description

Bit	Symbol	Description
0	BRGEN	Baud Rate Generator Enable. Enables the baud rate generator. BRGR1 and BRGR0 can only be written when $BRGEN = 0$ .
1	SBRGS	Select Baud Rate Generator as the source for baud rates to UART in modes 1 and 3 (see Table 45 for details)
2:7	-	reserved



### 10.8 Framing error

A Framing error occurs when the stop bit is sensed as a logic 0. A Framing error is reported in the status register (SSTAT). In addition, if SMOD0 (PCON.6) is 1, framing errors can be made available in SCON.7. If SMOD0 is 0, SCON.7 is SM0. It is recommended that SM0 and SM1 (SCON[7:6]) are programmed when SMOD0 is logic 0.

## 10.9 Break detect

A break detect is reported in the status register (SSTAT). A break is detected when any 11 consecutive bits are sensed low. Since a break condition also satisfies the requirements for a framing error, a break condition will also result in reporting a framing error. Once a

break condition has been detected, the UART will go into an idle state and remain in this idle state until a stop bit has been received. The break detect can be used to reset the device and force the device into ISP mode by setting the EBRR bit (AUXR1.6)

 Table 48.
 Serial Port Control register (SCON - address 98h) bit allocation

			-	-		-			
Bit	7	6	5	4	3	2	1	0	
Symbol	SM0/FE	SM1	SM2	REN	TB8	RB8	ΤI	RI	
Reset	х	х	х	х	х	х	0	0	

### Table 49. Serial Port Control register (SCON - address 98h) bit description

Bit	Symbol	Description
0	RI	Receive interrupt flag. Set by hardware at the end of the 8th bit time in Mode 0, or approximately halfway through the stop bit time in Mode 1. For Mode 2 or Mode 3, if SMOD0, it is set near the middle of the 9th data bit (bit 8). If SMOD0 = 1, it is set near the middle of the stop bit (see SM2 - SCON.5 - for exceptions). Must be cleared by software.
1	TI	Transmit interrupt flag. Set by hardware at the end of the 8th bit time in Mode 0, or at the stop bit (see description of INTLO bit in SSTAT register) in the other modes. Must be cleared by software.
2	RB8	The 9th data bit that was received in Modes 2 and 3. In Mode 1 (SM2 must be 0), RB8 is the stop bit that was received. In Mode 0, RB8 is undefined.
3	TB8	The 9th data bit that will be transmitted in Modes 2 and 3. Set or clear by software as desired.
4	REN	Enables serial reception. Set by software to enable reception. Clear by software to disable reception.
5	SM2	Enables the multiprocessor communication feature in Modes 2 and 3. In Mode 2 or 3, if SM2 is set to 1, then RI will not be activated if the received 9th data bit (RB8) is 0. In Mode 0, SM2 should be 0. In Mode 1, SM2 must be 0.
6	SM1	With SM0 defines the serial port mode, see Table 50.
7	SM0/FE	The use of this bit is determined by SMOD0 in the PCON register. If $SMOD0 = 0$ , this bit is read and written as SM0, which with SM1, defines the serial port mode. If $SMOD0 = 1$ , this bit is read and written as FE (Framing Error). FE is set by the receiver when an invalid stop bit is detected. Once set, this bit cannot be cleared by valid frames but is cleared by software. (Note: UART mode bits SM0 and SM1 should be programmed when SMOD0 is logic 0 - default mode on any reset.)

#### Table 50.Serial Port modes

SM0, SM1	UART mode	UART baud rate
00	Mode 0: shift register	<sup>CCLK</sup> •16 (default mode on any reset)
01	Mode 1: 8-bit UART	Variable (see <u>Table 45</u> )
10	Mode 2: 9-bit UART	CCLK <sub>92</sub> Or CCLK <sub>96</sub>
11	Mode 3: 9-bit UART	Variable (see <u>Table 45</u> )

### Table 51. Serial Port Status register (SSTAT - address BAh) bit allocation

Bit	7	6	5	4	3	2	1	0
Symbol	DBMOD	INTLO	CIDIS	DBISEL	FE	BR	OE	STINT
Reset	х	х	х	х	х	х	0	0


Table 52.	Serial Port Status register (	SSTAT - address BAh	) bit description
	ochari on otatas register (	OOTAT UUUICSS DAT	

Bit	Symbol	Description
0	STINT	Status Interrupt Enable. When set = 1, FE, BR, or OE can cause an interrupt. The interrupt used (vector address 0023h) is shared with RI (CIDIS = 1) or the combined TI/RI (CIDIS = 0). When cleared = 0, FE, BR, OE cannot cause an interrupt. (Note: FE, BR, or OE is often accompanied by a RI, which will generate an interrupt regardless of the state of STINT). Note that BR can cause a break detect reset if EBRR (AUXR1.6) is set to logic 1.
1	OE	Overrun Error flag is set if a new character is received in the receiver buffer while it is still full (before the software has read the previous character from the buffer), i.e., when bit 8 of a new byte is received while RI in SCON is still set. Cleared by software.
2	BR	Break Detect flag. A break is detected when any 11 consecutive bits are sensed low. Cleared by software.
3	FE	Framing error flag is set when the receiver fails to see a valid STOP bit at the end of the frame. Cleared by software.
4	DBISEL	Double buffering transmit interrupt select. Used only if double buffering is enabled. This bit controls the number of interrupts that can occur when double buffering is enabled. When set, one transmit interrupt is generated after each character written to SBUF, and there is also one more transmit interrupt generated at the beginning (INTLO = 0) or the end (INTLO = 1) of the STOP bit of the last character sent (i.e., no more data in buffer). This last interrupt can be used to indicate that all transmit operations are over. When cleared = 0, only one transmit interrupt is generated per character written to SBUF. Must be logic 0 when double buffering is disabled. Note that except for the first character written (when buffer is empty), the location of the transmit interrupt is generated immediately after SBUF is written.
5	CIDIS	Combined Interrupt Disable. When set = 1, Rx and Tx interrupts are separate. When cleared = 0, the UART uses a combined Tx/Rx interrupt (like a conventional $80C51$ UART). This bit is reset to logic 0 to select combined interrupts.
6	INTLO	Transmit interrupt position. When cleared = 0, the Tx interrupt is issued at the beginning of the stop bit. When set = 1, the Tx interrupt is issued at end of the stop bit. Must be logic 0 for mode 0. Note that in the case of single buffering, if the Tx interrupt occurs at the end of a STOP bit, a gap may exist before the next start bit.
7	DBMOD	Double buffering mode. When set = 1 enables double buffering. Must be logic 0 for UART mode 0. In order to be compatible with existing 80C51 devices, this bit is reset to logic 0 to disable double buffering.

### 10.10 More about UART Mode 0

In Mode 0, a write to SBUF will initiate a transmission. At the end of the transmission, TI (SCON.1) is set, which must be cleared in software. Double buffering must be disabled in this mode.


Reception is initiated by clearing RI (SCON.0). Synchronous serial transfer occurs and RI will be set again at the end of the transfer. When RI is cleared, the reception of the next character will begin. Refer to Figure 25



## 10.11 More about UART Mode 1

Reception is initiated by detecting a 1-to-0 transition on RxD. RxD is sampled at a rate 16 times the programmed baud rate. When a transition is detected, the divide-by-16 counter is immediately reset. Each bit time is thus divided into 16 counter states. At the 7th, 8th, and 9th counter states, the bit detector samples the value of RxD. The value accepted is the value that was seen in at least 2 of the 3 samples. This is done for noise rejection. If the value accepted during the first bit time is not 0, the receive circuits are reset and the receiver goes back to looking for another 1-to-0 transition. This provides rejection of false start bits. If the start bit proves valid, it is shifted into the input shift register, and reception of the rest of the frame will proceed.


The signal to load SBUF and RB8, and to set RI, will be generated if, and only if, the following conditions are met at the time the final shift pulse is generated: RI = 0 and either SM2 = 0 or the received stop bit = 1. If either of these two conditions is not met, the received frame is lost. If both conditions are met, the stop bit goes into RB8, the 8 data bits go into SBUF, and RI is activated.



## 10.12 More about UART Modes 2 and 3

Reception is the same as in Mode 1.

The signal to load SBUF and RB8, and to set RI, will be generated if, and only if, the following conditions are met at the time the final shift pulse is generated. (a) RI = 0, and (b) Either SM2 = 0, or the received 9th data bit = 1. If either of these conditions is not met, the received frame is lost, and RI is not set. If both conditions are met, the received 9th data bit goes into RB8, and the first 8 data bits go into SBUF.



# 10.13 Framing error and RI in Modes 2 and 3 with SM2 = 1

If SM2 = 1 in modes 2 and 3, RI and FE behaves as in the following table.

Mode	PCON.6 (SMOD0)	RB8	RI	FE
2	0	0	No RI when RB8 = 0	Occurs during STOP bit
		1	Similar to Figure 27, with SMOD0 = 0, RI occurs during RB8, one bit before FE	Occurs during STOP bit
3	1	0	No RI when RB8 = 0	Will NOT occur
		1	Similar to Figure 27, with SMOD0 = 1, RI occurs during STOP bit	Occurs during STOP bit

### Table 53.FE and RI when SM2 = 1 in Modes 2 and 3

## 10.14 Break detect

A break is detected when 11 consecutive bits are sensed low and is reported in the status register (SSTAT). For Mode 1, this consists of the start bit, 8 data bits, and two stop bit times. For Modes 2 and 3, this consists of the start bit, 9 data bits, and one stop bit. The break detect bit is cleared in software or by a reset. The break detect can be used to reset the device and force the device into ISP mode. This occurs if the UART is enabled and the the EBRR bit (AUXR1.6) is set and a break occurs.

## 10.15 Double buffering

The UART has a transmit double buffer that allows buffering of the next character to be written to SBUF while the first character is being transmitted. Double buffering allows transmission of a string of characters with only one stop bit between any two characters, provided the next character is written between the start bit and the stop bit of the previous character.

Double buffering can be disabled. If disabled (DBMOD, i.e. SSTAT.7 = 0), the UART is compatible with the conventional 80C51 UART. If enabled, the UART allows writing to SnBUF while the previous data is being shifted out.

## **10.16** Double buffering in different modes

Double buffering is only allowed in Modes 1, 2 and 3. When operated in Mode 0, double buffering must be disabled (DBMOD = 0).

## 10.17 Transmit interrupts with double buffering enabled (Modes 1, 2, and 3)

Unlike the conventional UART, when double buffering is enabled, the Tx interrupt is generated when the double buffer is ready to receive new data. The following occurs during a transmission (assuming eight data bits):


- 1. The double buffer is empty initially.
- 2. The CPU writes to SBUF.
- 3. The SBUF data is loaded to the shift register and a Tx interrupt is generated immediately.
- 4. If there is more data, go to 6, else continue.
- 5. If there is no more data, then:
  - If DBISEL is logic 0, no more interrupts will occur.

UM10345

- If DBISEL is logic 1 and INTLO is logic 0, a Tx interrupt will occur at the beginning of the STOP bit of the data currently in the shifter (which is also the last data).
- If DBISEL is logic 1 and INTLO is logic 1, a Tx interrupt will occur at the end of the STOP bit of the data currently in the shifter (which is also the last data).
- Note that if DBISEL is logic 1 and the CPU is writing to SBUF when the STOP bit of the last data is shifted out, there can be an uncertainty of whether a Tx interrupt is generated already with the UART not knowing whether there is any more data following.
- 6. If there is more data, the CPU writes to SBUF again. Then:

Go to 3.

- If INTLO is logic 0, the new data will be loaded and a Tx interrupt will occur at the beginning of the STOP bit of the data currently in the shifter.
- If INTLO is logic 1, the new data will be loaded and a Tx interrupt will occur at the end of the STOP bit of the data currently in the shifter.



## 10.18 The 9th bit (bit 8) in double buffering (Modes 1, 2, and 3)

If double buffering is disabled (DBMOD, i.e. SSTAT.7 = 0), TB8 can be written before or after SBUF is written, provided TB8 is updated before that TB8 is shifted out. TB8 must not be changed again until after TB8 shifting has been completed, as indicated by the Tx interrupt.

### UM10345

If double buffering is enabled, TB8 MUST be updated before SBUF is written, as TB8 will be double-buffered together with SBUF data. The operation described in the <u>Section</u> <u>10.17 "Transmit interrupts with double buffering enabled (Modes 1, 2, and 3)"</u> becomes as follows:

- 1. The double buffer is empty initially.
- 2. The CPU writes to TB8.
- 3. The CPU writes to SBUF.
- 4. The SBUF/TB8 data is loaded to the shift register and a Tx interrupt is generated immediately.
- 5. If there is more data, go to 7, else continue on 6.
- 6. If there is no more data, then:
  - If DBISEL is logic 0, no more interrupt will occur.
  - If DBISEL is logic 1 and INTLO is logic 0, a Tx interrupt will occur at the beginning of the STOP bit of the data currently in the shifter (which is also the last data).
  - If DBISEL is logic 1 and INTLO is logic 1, a Tx interrupt will occur at the end of the STOP bit of the data currently in the shifter (which is also the last data).
- 7. If there is more data, the CPU writes to TB8 again.
- 8. The CPU writes to SBUF again. Then:
  - If INTLO is logic 0, the new data will be loaded and a Tx interrupt will occur at the beginning of the STOP bit of the data currently in the shifter.
  - If INTLO is logic 1, the new data will be loaded and a Tx interrupt will occur at the end of the STOP bit of the data currently in the shifter.
- 9. Go to 4.
- 10. Note that if DBISEL is logic 1 and the CPU is writing to SBUF when the STOP bit of the last data is shifted out, there can be an uncertainty of whether a Tx interrupt is generated already with the UART not knowing whether there is any more data following.

## **10.19** Multiprocessor communications

UART modes 2 and 3 have a special provision for multiprocessor communications. In these modes, 9 data bits are received or transmitted. When data is received, the 9th bit is stored in RB8. The UART can be programmed such that when the stop bit is received, the serial port interrupt will be activated only if RB8 = 1. This feature is enabled by setting bit SM2 in SCON. One way to use this feature in multiprocessor systems is as follows:

When the master processor wants to transmit a block of data to one of several slaves, it first sends out an address byte which identifies the target slave. An address byte differs from a data byte in that the 9th bit is 1 in an address byte and 0 in a data byte. With SM2 = 1, no slave will be interrupted by a data byte. An address byte, however, will interrupt all slaves, so that each slave can examine the received byte and see if it is being addressed. The addressed slave will clear its SM2 bit and prepare to receive the data bytes that follow. The slaves that weren't being addressed leave their SM2 bits set and go on about their business, ignoring the subsequent data bytes.

Note that SM2 has no effect in Mode 0, and must be logic 0 in Mode 1.

62 of 129

## 10.20 Automatic address recognition

Automatic address recognition is a feature which allows the UART to recognize certain addresses in the serial bit stream by using hardware to make the comparisons. This feature saves a great deal of software overhead by eliminating the need for the software to examine every serial address which passes by the serial port. This feature is enabled by setting the SM2 bit in SCON. In the 9 bit UART modes (mode 2 and mode 3), the Receive Interrupt flag (RI) will be automatically set when the received byte contains either the 'Given' address or the 'Broadcast' address. The 9 bit mode requires that the 9th information bit is a 1 to indicate that the received information is an address and not data.

Using the Automatic Address Recognition feature allows a master to selectively communicate with one or more slaves by invoking the Given slave address or addresses. All of the slaves may be contacted by using the Broadcast address. Two special Function Registers are used to define the slave's address, SADDR, and the address mask, SADEN. SADEN is used to define which bits in the SADDR are to be used and which bits are 'don't care'. The SADEN mask can be logically ANDed with the SADDR to create the 'Given' address which the master will use for addressing each of the slaves. Use of the Given address allows multiple slaves to be recognized while excluding others. The following examples will help to show the versatility of this scheme:

### Table 54.Slave 0/1 examples

Example 1			Example 2		
Slave 0	SADDR	= 1100 0000	Slave 1	SADDR	= 1100 0000
	SADEN	= 1111 1101		SADEN	= 1111 1110
	Given	= 1100 00X0		Given	= 1100 000X

In the above example SADDR is the same and the SADEN data is used to differentiate between the two slaves. Slave 0 requires a 0 in bit 0 and it ignores bit 1. Slave 1 requires a 0 in bit 1 and bit 0 is ignored. A unique address for Slave 0 would be 1100 0010 since slave 1 requires a 0 in bit 1. A unique address for slave 1 would be 1100 0001 since a 1 in bit 0 will exclude slave 0. Both slaves can be selected at the same time by an address which has bit 0 = 0 (for slave 0) and bit 1 = 0 (for slave 1). Thus, both could be addressed with 1100 0000.

In a more complex system the following could be used to select slaves 1 and 2 while excluding slave 0:

### Table 55. Slave 0/1/2 examples

Example 1			Example	Example 2				Example 3			
Slave 0	SADDR	=	1100 0000	Slave 1	SADDR	=	1110 0000	Slave 2	SADDR	= .	1100 0000
	SADEN	=	1111 1001		SADEN	=	1111 1010		SADEN	=	1111 1100
	Given	=	1100 0XX0		Given	=	1110 0X0X		Given	=	1110 00XX

In the above example the differentiation among the 3 slaves is in the lower 3 address bits. Slave 0 requires that bit 0 = 0 and it can be uniquely addressed by 1110 0110. Slave 1 requires that bit 1 = 0 and it can be uniquely addressed by 1110 and 0101. Slave 2 requires that bit 2 = 0 and its unique address is 1110 0011. To select Slaves 0 and 1 and exclude Slave 2 use address 1110 0100, since it is necessary to make bit 2 = 1 to exclude slave 2. The Broadcast Address for each slave is created by taking the logical OR of SADDR and SADEN. Zeros in this result are treated as don't-cares. In most cases, interpreting the don't-cares as ones, the broadcast address will be FF hexadecimal. Upon reset SADDR and SADEN are loaded with 0s. This produces a given address of all 'don't cares' as well as a Broadcast address of all 'don't cares'. This effectively disables the Automatic Addressing mode and allows the microcontroller to use standard UART drivers which do not make use of this feature.

# 11. I<sup>2</sup>C interface


The I<sup>2</sup>C-bus uses two wires, serial clock (SCL) and serial data (SDA) to transfer information between devices connected to the bus, and has the following features:

- Bidirectional data transfer between masters and slaves
- Multimaster bus (no central master)
- Arbitration between simultaneously transmitting masters without corruption of serial data on the bus
- Serial clock synchronization allows devices with different bit rates to communicate via one serial bus
- Serial clock synchronization can be used as a handshake mechanism to suspend and resume serial transfer
- The I<sup>2</sup>C-bus may be used for test and diagnostic purposes

A typical I<sup>2</sup>C-bus configuration is shown in <u>Figure 29</u>. Depending on the state of the direction bit (R/W), two types of data transfers are possible on the I<sup>2</sup>C-bus:

- Data transfer from a master transmitter to a slave receiver. The first byte transmitted by the master is the slave address. Next follows a number of data bytes. The slave returns an acknowledge bit after each received byte.
- Data transfer from a slave transmitter to a master receiver. The first byte (the slave address) is transmitted by the master. The slave then returns an acknowledge bit. Next follows the data bytes transmitted by the slave to the master. The master returns an acknowledge bit after all received bytes other than the last byte. At the end of the last received byte, a 'not acknowledge' is returned. The master device generates all of the serial clock pulses and the START and STOP conditions. A transfer is ended with a STOP condition or with a repeated START condition. Since a repeated START condition is also the beginning of the next serial transfer, the l<sup>2</sup>C-bus will not be released.

The P89LPC970/971/972 device provides a byte-oriented I<sup>2</sup>C interface. It has four operation modes: Master Transmitter Mode, Master Receiver Mode, Slave Transmitter Mode and Slave Receiver Mode.



The P89LPC970/971/972 CPU interfaces with the I<sup>2</sup>C-bus through six Special Function Registers (SFRs): I2CON (I<sup>2</sup>C Control Register), I2DAT (I<sup>2</sup>C Data Register), I2STAT (I<sup>2</sup>C Status Register), I2ADR (I<sup>2</sup>C Slave Address Register), I2SCLH (SCL Duty Cycle Register High Byte), and I2SCLL (SCL Duty Cycle Register Low Byte).

## 11.1 I<sup>2</sup>C data register

I2DAT register contains the data to be transmitted or the data received. The CPU can read and write to this 8-bit register while it is not in the process of shifting a byte. Thus this register should only be accessed when the SI bit is set. Data in I2DAT remains stable as long as the SI bit is set. Data in I2DAT is always shifted from right to left: the first bit to be transmitted is the MSB (bit 7), and after a byte has been received, the first bit of received data is located at the MSB of I2DAT.

Table 56.	I <sup>2</sup> C data register (	I2DAT - address	DAh) bit allocation
-----------	----------------------------------	-----------------	---------------------

Bit	7	6	5	4	3	2	1	0
Symbol	I2DAT.7	I2DAT.6	I2DAT.5	I2DAT.4	I2DAT.3	I2DAT.2	I2DAT.1	I2DAT.0
Reset	0	0	0	0	0	0	0	0

## 11.2 I<sup>2</sup>C slave address register

I2ADR register is readable and writable, and is only used when the I<sup>2</sup>C interface is set to slave mode. In master mode, this register has no effect. The LSB of I2ADR is general call bit. When this bit is set, the general call address (00h) is recognized.

Table 57.	I <sup>2</sup> C slave address register (I2ADR - address DBh) bit allocation
-----------	--

Bit	7	6	5	4	3	2	1	0
Symbol	I2ADR.6	I2ADR.5	I2ADR.4	I2ADR.3	I2ADR.2	I2ADR.1	I2ADR.0	GC
Reset	0	0	0	0	0	0	0	0

#### Table 58. I<sup>2</sup>C slave address register (I2ADR - address DBh) bit description

Bit	Symbol	Description
0	GC	General call bit. When set, the general call address (00H) is recognized, otherwise it is ignored.
1:7	I2ADR1:7	7 bit own slave address. When in master mode, the contents of this register has no effect.

**User manual** 

## 11.3 I<sup>2</sup>C control register

The CPU can read and write this register. There are two bits are affected by hardware: the SI bit and the STO bit. The SI bit is set by hardware and the STO bit is cleared by hardware.

CRSEL determines the SCL source when the I<sup>2</sup>C-bus is in master mode. In slave mode this bit is ignored and the bus will automatically synchronize with any clock frequency up to 400 kHz from the master I<sup>2</sup>C device. When CRSEL = 1, the I<sup>2</sup>C interface uses the Timer 1 overflow rate divided by 2 for the I<sup>2</sup>C clock rate. Timer 1 should be programmed by the user in 8 bit auto-reload mode (Mode 2).

Data rate of  $I^2C$ -bus = Timer overflow rate / 2 = PCLK / (2\*(256-reload value)).

If  $f_{osc} = 12$  MHz, reload value is 0 to 255, so I<sup>2</sup>C data rate range is 11.72 Kbit/sec to 3000 Kbit/sec.

When CRSEL = 0, the  $I^2C$  interface uses the internal clock generator based on the value of I2SCLL and I2CSCLH register. The duty cycle does not need to be 50 %.

The STA bit is START flag. Setting this bit causes the I<sup>2</sup>C interface to enter master mode and attempt transmitting a START condition or transmitting a repeated START condition when it is already in master mode.

The STO bit is STOP flag. Setting this bit causes the I<sup>2</sup>C interface to transmit a STOP condition in master mode, or recovering from an error condition in slave mode.

If the STA and STO are both set, then a STOP condition is transmitted to the I<sup>2</sup>C-bus if it is in master mode, and transmits a START condition afterwards. If it is in slave mode, an internal STOP condition will be generated, but it is not transmitted to the bus.

### Table 59. I<sup>2</sup>C Control register (I2CON - address D8h) bit allocation

Bit         7         6         5         4         3         2         1         0           Symbol         -         I2EN         STA         STO         SI         AA         -         CRSEL           Reset         x         0         0         0         0         x         0			•	•					
	Bit	7	6	5	4	3	2	1	0
Reset x 0 0 0 0 0 x 0	Symbol	-	I2EN	STA	STO	SI	AA	-	CRSEL
	Reset	х	0	0	0	0	0	х	0

#### Table 60. I<sup>2</sup>C Control register (I2CON - address D8h) bit description

Bit	Symbol	Description
0	CRSEL	SCL clock selection. When set = 1, Timer 1 overflow generates SCL, when cleared = 0, the internal SCL generator is used base on values of I2SCLH and I2SCLL.
1	-	reserved
2	AA	The Assert Acknowledge Flag. When set to 1, an acknowledge (low level to SDA) will be returned during the acknowledge clock pulse on the SCL line on the following situations:
		(1)The 'own slave address' has been received. (2)The general call address has been received while the general call bit (GC) in I2ADR is set. (3) A data byte has been received while the I <sup>2</sup> C interface is in the Master Receiver Mode. (4)A data byte has been received while the I <sup>2</sup> C interface is in the addressed Slave Receiver Mode. When cleared to 0, an not acknowledge (high level to SDA) will be returned during the acknowledge clock pulse on the SCL line on the following situations: (1) A data byte has been received while the I <sup>2</sup> C interface is in the Master Receiver Mode. (2) A data byte has been received while the I <sup>2</sup> C interface is in the Master Receiver Slave Receiver Mode.

Bit	Symbol	Description
3	SI	$I^2C$ Interrupt Flag. This bit is set when one of the 25 possible $I^2C$ states is entered. When EA bit and El2C (IEN1.0) bit are both set, an interrupt is requested when SI is set. Must be cleared by software by writing 0 to this bit.
4	STO	STOP Flag. STO = 1: In master mode, a STOP condition is transmitted to the $I^2C$ -bus. When the bus detects the STOP condition, it will clear STO bit automatically. In slave mode, setting this bit can recover from an error condition. In this case, no STOP condition is transmitted to the bus. The hardware behaves as if a STOP condition has been received and it switches to 'not addressed' Slave Receiver Mode. The STO flag is cleared by hardware automatically.
5	STA	Start Flag. STA = 1: $l^2C$ -bus enters master mode, checks the bus and generates a START condition if the bus is free. If the bus is not free, it waits for a STOP condition (which will free the bus) and generates a START condition after a delay of a half clock period of the internal clock generator. When the $l^2C$ interface is already in master mode and some data is transmitted or received, it transmits a repeated START condition. STA may be set at any time, it may also be set when the $l^2C$ interface is in an addressed slave mode. STA = 0: no START condition or repeated START condition will be generated.
6	I2EN	$\rm I^2C$ Interface Enable. When set, enables the $\rm I^2C$ interface. When clear, the $\rm I^2C$ function is disabled.
7	-	reserved

#### Table 60. I<sup>2</sup>C Control register (I2CON - address D8h) bit description ... continued

## 11.4 I<sup>2</sup>C Status register

This is a read-only register. It contains the status code of the  $I^2C$  interface. The least three bits are always 0. There are 26 possible status codes. When the code is F8H, there is no relevant information available and SI bit is not set. All other 25 status codes correspond to defined  $I^2C$  states. When any of these states entered, the SI bit will be set. Refer to Table 66 to Table 69 for details.

			. (					
Bit	7	6	5	4	3	2	1	0
Symbol	STA.4	STA.3	STA.2	STA.1	STA.0	0	0	0
Reset	0	0	0	0	0	0	0	0

Table 61.	I <sup>2</sup> C Status register (I	2STAT - address	D9h) bit allocation
-----------	-------------------------------------	-----------------	---------------------

Table 62. I<sup>2</sup>C Status register (I2STAT - address D9h) bit description

Bit	Symbol	Description
0:2	-	Reserved, are always set to 0.
3:7	STA[0:4]	I <sup>2</sup> C Status code.

## 11.5 I<sup>2</sup>C SCL duty cycle registers I2SCLH and I2SCLL

When the internal SCL generator is selected for the I<sup>2</sup>C interface by setting CRSEL = 0 in the I2CON register, the user must set values for registers I2SCLL and I2SCLH to select the data rate. I2SCLH defines the number of PCLK cycles for SCL = high, I2SCLL defines the number of PCLK cycles for SCL = low. The frequency is determined by the following formula:

Bit Frequency =  $f_{PCLK} / (2^*(I2SCLH + I2SCLL))$ 

Where f<sub>PCLK</sub> is the frequency of PCLK.

UM10345

The values for I2SCLL and I2SCLH do not have to be the same; the user can give different duty cycles for SCL by setting these two registers. However, the value of the register must ensure that the data rate is in the I<sup>2</sup>C data rate range of 0 to 400 kHz. Thus the values of I2SCLL and I2SCLH have some restrictions and values for both registers greater than three PCLKs are recommended.

		Bit data rate	Bit data rate (Kbit/sec) at f <sub>osc</sub>				
I2SCLL+ I2SCLH	CRSEL	7.373 MHz	3.6865 MHz	1.8433 MHz	12 MHz	6 MHz	
6	0	-	307	154	-	-	
7	0	-	263	132	-	-	
8	0	-	230	115	-	375	
9	0	-	205	102	-	333	
10	0	369	184	92	-	300	
15	0	246	123	61	400	200	
25	0	147	74	37	240	120	
30	0	123	61	31	200	100	
50	0	74	37	18	120	60	
60	0	61	31	15	100	50	
100	0	37	18	9	60	30	
150	0	25	12	6	40	20	
200	0	18	9	5	30	15	
-	1	3.6 Kbps to 922 Kbps Timer 1 in mode 2	1.8 Kbps to 461 Kbps Timer 1 in mode 2	0.9 Kbps to 230 Kbps Timer 1 in mode 2	5.86 Kbps to 1500 Kbps Timer 1 in mode 2	2.93 Kbps to 750 Kbps Timer 1 in mode 2	

### Table 63. I<sup>2</sup>C clock rates selection

## 11.6 I<sup>2</sup>C operation modes

### 11.6.1 Master Transmitter mode

In this mode data is transmitted from master to slave. Before the Master Transmitter mode can be entered, I2CON must be initialized as follows:

Table 64.	I <sup>2</sup> C Control	register	(I2CON ·	address	<b>D8h)</b>
-----------	--------------------------	----------	----------	---------	-------------


		-	•		-			
Bit	7	6	5	4	3	2	1	0
	-	I2EN	STA	STO	SI	AA	-	CRSEL
value	-	1	0	0	0	х	-	bit rate

CRSEL defines the bit rate. I2EN must be set to 1 to enable the I<sup>2</sup>C function. If the AA bit is 0, it will not acknowledge its own slave address or the general call address in the event of another device becoming master of the bus and it can not enter slave mode. STA, STO, and SI bits must be cleared to 0.

The first byte transmitted contains the slave address of the receiving device (7 bits) and the data direction bit. In this case, the data direction bit (R/W) will be logic 0 indicating a write. Data is transmitted 8 bits at a time. After each byte is transmitted, an acknowledge bit is received. START and STOP conditions are output to indicate the beginning and the end of a serial transfer.

The I<sup>2</sup>C-bus will enter Master Transmitter Mode by setting the STA bit. The I<sup>2</sup>C logic will send the START condition as soon as the bus is free. After the START condition is transmitted, the SI bit is set, and the status code in I2STAT should be 08h. This status code must be used to vector to an interrupt service routine where the user should load the slave address to I2DAT (Data Register) and data direction bit (SLA+W). The SI bit must be cleared before the data transfer can continue.


When the slave address and R/W bit have been transmitted and an acknowledgment bit has been received, the SI bit is set again, and the possible status codes are 18h, 20h, or 38h for the master mode or 68h, 78h, or 0B0h if the slave mode was enabled (setting AA = Logic 1). The appropriate action to be taken for each of these status codes is shown in Table 66.




### 11.6.2 Master Receiver mode

In the Master Receiver Mode, data is received from a slave transmitter. The transfer started in the same manner as in the Master Transmitter Mode. When the START condition has been transmitted, the interrupt service routine must load the slave address and the data direction bit to I<sup>2</sup>C Data Register (I2DAT). The SI bit must be cleared before the data transfer can continue.

When the slave address and data direction bit have been transmitted and an acknowledge bit has been received, the SI bit is set, and the Status Register will show the status code. For master mode, the possible status codes are 40H, 48H, or 38H. For slave mode, the possible status codes are 68H, 78H, or B0H. Refer to <u>Table 68</u> for details.



After a repeated START condition, I<sup>2</sup>C-bus may switch to the Master Transmitter Mode.



### 11.6.3 Slave Receiver mode


In the Slave Receiver Mode, data bytes are received from a master transmitter. To initialize the Slave Receiver Mode, the user should write the slave address to the Slave Address Register (I2ADR) and the I<sup>2</sup>C Control Register (I2CON) should be configured as follows:

Table 65.	I <sup>2</sup> C Control register (I2CON - address D8h)
-----------	---

Bit	7	6	5	4	3	2	1	0
	-	I2EN	STA	STO	SI	AA	-	CRSEL
value	-	1	0	0	0	1	-	-


CRSEL is not used for slave mode. I2EN must be set = 1 to enable  $I^2C$  function. AA bit must be set = 1 to acknowledge its own slave address or the general call address. STA, STO and SI are cleared to 0.


After I2ADR and I2CON are initialized, the interface waits until it is addressed by its own address or general address followed by the data direction bit which is 0(W). If the direction bit is 1(R), it will enter Slave Transmitter Mode. After the address and the direction bit have been received, the SI bit is set and a valid status code can be read from the Status Register(I2STAT). Refer to <u>Table 69</u> for the status codes and actions.



### 11.6.4 Slave Transmitter mode

The first byte is received and handled as in the Slave Receiver Mode. However, in this mode, the direction bit will indicate that the transfer direction is reversed. Serial data is transmitted via P1.3/SDA while the serial clock is input through P1.2/SCL. START and STOP conditions are recognized as the beginning and end of a serial transfer. In a given application, the I<sup>2</sup>C-bus may operate as a master and as a slave. In the slave mode, the I<sup>2</sup>C hardware looks for its own slave address and the general call address. If one of these addresses is detected, an interrupt is requested. When the microcontrollers wishes to become the bus master, the hardware waits until the bus is free before the master mode is entered so that a possible slave action is not interrupted. If bus arbitration is lost in the master mode, the I<sup>2</sup>C-bus switches to the slave mode immediately and can detect its own slave address in the same serial transfer.





Status code Status of the I <sup>2</sup> C		Application softwa	are res	Next action taken by I <sup>2</sup> C				
I2STAT)	hardware	to/from I2DAT	to I2C	ON			hardware	
			STA	STO	SI	AA		
)8H	A START condition has been transmitted	Load SLA+W	x	0	0	x	SLA+W will be transmitted; ACK bit will be received	
0H	A repeat START condition has been transmitted	Load SLA+W or Load SLA+R	x	0	0	x	As above; SLA+W will be transmitted; I <sup>2</sup> C-bus switches to Master Receiver Mode	
8h	SLA+W has been transmitted; ACK	Load data byte or	0	0	0	x	Data byte will be transmitted; ACK bit will be received	
	has been received	no I2DAT action or	1	0	0	x	Repeated START will be transmitted;	
		no I2DAT action or	0	1	0	x	STOP condition will be transmitted; STO flag will be reset	
		no I2DAT action	1	1	0	x	STOP condition followed by a START condition will be transmitted; STO flag will be reset.	
20h	SLA+W has been transmitted;	Load data byte or	0	0	0	x	Data byte will be transmitted; ACK bit will be received	
	NOT-ACK has been received	no I2DAT action or	1	0	0	x	Repeated START will be transmitted;	
		no I2DAT action or	0	1	0	x	STOP condition will be transmitted; STO flag will be reset	
		no I2DAT action	1	1	0	X	STOP condition followed by a START condition will be transmitted; STO flag will be reset	
:8h	Data byte in I2DAT has been	Load data byte or	0	0	0	x	Data byte will be transmitted; ACK bit will be received	
	transmitted; ACK has been received	no I2DAT action or	1	0	0	x	Repeated START will be transmitted;	
		no I2DAT action or	0	1	0	x	STOP condition will be transmitted; STO flag will be reset	
		no I2DAT action	1	1	0	x	STOP condition followed by a START condition will be transmitted; STO flag will be reset	

### Table 66. Master Transmitter mode

Status code	Status of the I <sup>2</sup> C	Application softw	are res	sponse			Next action taken by I <sup>2</sup> C
(I2STAT)	hardware	to/from I2DAT	to I2C	ON			hardware
			STA	STO	SI	AA	
30h	Data byte in I2DAT has been	Load data byte or	0	0	0	x	Data byte will be transmitted; ACK bit will be received
	transmitted, NOT ACK has been received	no I2DAT action or	1	0	0	x	Repeated START will be transmitted;
		no I2DAT action or	0	1	0	x	STOP condition will be transmitted; STO flag will be reset
		no I2DAT action	1	1	0	x	STOP condition followed by a START condition will be transmitted. STO flag will be reset.
38H	Arbitration lost in SLA+R/W or data	No I2DAT action or	0	0	0	x	I <sup>2</sup> C-bus will be released; not addressed slave will be entered
	bytes	No I2DAT action	1	0	0	x	A START condition will be transmitted when the bus becomes free.

#### Table 66. Master Transmitter mode ... continued

#### Table 67.Master Receiver mode

Status code	Status of the I <sup>2</sup> C	Application softw	are re	spons	Next action taken by I <sup>2</sup> C hardware			
(I2STAT)	hardware	to/from I2DAT	to 120	CON			-	
			STA	STO	SI	STA	-	
08H	A START condition has been transmitted	Load SLA+R	x	0	0	x	SLA+R will be transmitted; ACK bit will be received	
10H	A repeat START	Load SLA+R or	х	0	0	x	As above	
	condition has been transmitted	Load SLA+W					SLA+W will be transmitted; I <sup>2</sup> C-bus will be switched to Master Transmitter Mode	
38H	Arbitration lost in NOT ACK bit	no I2DAT action or	0	0	0	x	I <sup>2</sup> C-bus will be released; it will enter a slave mode	
		no I2DAT action	1	0	0	x	A START condition will be transmitted when the bus becomes free	
40h	SLA+R has been transmitted; ACK	no I2DAT action or	0	0	0	0	Data byte will be received; NOT ACK bit will be returned	
	has been received	no I2DAT action or	0	0	0	1	Data byte will be received; ACK bit will be returned	
48h	SLA+R has been transmitted; NOT	No I2DAT action or	1	0	0	x	Repeated START will be transmitted	
	ACK has been received	no I2DAT action or	0	1	0	x	STOP condition will be transmitted; STO flag will be reset	
		no I2DAT action or	1	1	0	x	STOP condition followed by a START condition will be transmitted; STO flag will be reset	

Status code	Status of the I <sup>2</sup> C	Application softw	are re	spons	Next action taken by I <sup>2</sup> C hardware		
(I2STAT)	hardware	to/from I2DAT	to I20	CON			
			STA	STO	SI	STA	
50h	Data byte has been received;	Read data byte	0	0	0	0	Data byte will be received; NOT ACK bit will be returned
	ACK has been returned	read data byte	0	0	0	1	Data byte will be received; ACK bit will be returned
58h	Data byte has	Read data byte or	1	0	0	х	Repeated START will be transmitted;
	been received; NACK has been	read data byte or	0	1	0	x	STOP condition will be transmitted; STO flag will be reset
	returned	read data byte	1	1	0	x	STOP condition followed by a START condition will be transmitted; STO flag will be reset

#### Table 67. Master Receiver mode ... continued

#### Table 68. Slave Receiver mode

Status code	Status of the I <sup>2</sup> C	Application softw	are res	sponse	Next action taken by I <sup>2</sup> C hardware		
(I2STAT)	hardware	to/from I2DAT	to I20	ON			
			STA	STO	SI	AA	_
60H	Own SLA+W has been received;	no I2DAT action or	х	0	0	0	Data byte will be received and NOT ACK will be returned
	ACK has been received	no I2DAT action	x	0	0	1	Data byte will be received and ACK will be returned
SLA mas SLA rece	Arbitration lost in SLA+R/Was	No I2DAT action or	x	0	0	0	Data byte will be received and NOT ACK will be returned
	master; Own SLA+W has been received, ACK returned	no I2DAT action	x	0	0	1	Data byte will be received and ACK will be returned
70H	General call address(00H) has	No I2DAT action or	x	0	0	0	Data byte will be received and NOT ACK will be returned
	been received, ACK has been returned	no I2DAT action	x	0	0	1	Data byte will be received and ACK will be returned
78H	Arbitration lost in SLA+R/W as	no I2DAT action or	x	0	0	0	Data byte will be received and NOT ACK will be returned
	master; General call address has been received, ACK bit has been returned	no I2DAT action	x	0	0	1	Data byte will be received and ACK will be returned
80H	Previously addressed with	Read data byte or	x	0	0	0	Data byte will be received and NOT ACK will be returned
	own SLA address; Data has been received; ACK has been returned	read data byte	x	0	0	1	Data byte will be received; ACK bit will be returned

Status code	Status of the I <sup>2</sup> C	Application softw	are re	sponse		Next action taken by I <sup>2</sup> C hardware	
(I2STAT)	hardware	to/from I2DAT	to 120	CON			
			STA	STO	SI	AA	
88H	Previously addressed with own SLA address;	Read data byte or	0	0	0	0	Switched to not addressed SLA mode; no recognition of own SLA or general address
	Data has been received; NACK has been returned	read data byte or	0	0	0	1	Switched to not addressed SLA mode; Own SLA will be recognized; general call address will be recognized if I2ADR.0 = 1
		read data byte or	1	0	0	0	Switched to not addressed SLA mode; no recognition of own SLA or General call address. A START condition will be transmitted when the bus becomes free
		read data byte	1	0	0	1	Switched to not addressed SLA mode; Own slave address will be recognized; General call address will be recognized if I2ADR.0 = 1. A START condition will be transmitted when the bus becomes free.
90H	Previously addressed with	Read data byte or	х	0	0	0	Data byte will be received and NOT ACK will be returned
	General call; Data has been received; ACK has been returned	read data byte	x	0	0	1	Data byte will be received and ACK will be returned
98H	Previously addressed with General call; Data	Read data byte	0	0	0	0	Switched to not addressed SLA mode; no recognition of own SLA or General call address
	has been received; NACK has been returned	read data byte	0	0	0	1	Switched to not addressed SLA mode; Own slave address will be recognized; General call address will be recognized if I2ADR.0 = 1.
		read data byte	1	0	0	0	Switched to not addressed SLA mode; no recognition of own SLA or General call address. A START condition will be transmitted when the bus becomes free.
		read data byte	1	0	0	1	Switched to not addressed SLA mode; Own slave address will be recognized; General call address will be recognized if I2ADR.0 = 1. A START condition will be transmitted when the bus becomes free.

#### Table 68. Slave Receiver mode ...continued

Status code	Status of the I <sup>2</sup> C	Application softw	vare re	sponse	Next action taken by I <sup>2</sup> C hardware		
(I2STAT)	hardware	to/from I2DAT	to 120	CON			_
			STA	STO	SI	AA	_
АОН	A STOP condition or repeated START condition	No I2DAT action	0	0	0	0	Switched to not addressed SLA mode; no recognition of own SLA or General call address
	has been received while still addressed as SLA/REC or SLA/TRX	no I2DAT action	0	0	0	1	Switched to not addressed SLA mode; Own slave address will be recognized; General call address will be recognized if I2ADR.0 = 1.
	SLATINA	no I2DAT action	1	0	0	0	Switched to not addressed SLA mode; no recognition of own SLA or General call address. A START condition will be transmitted when the bus becomes free.
		no I2DAT action	1	0	0	1	Switched to not addressed SLA mode; Own slave address will be recognized; General call address will be recognized if I2ADR.0 = 1. A START condition will be transmitted when the bus becomes free.

#### Table 68. Slave Receiver mode ...continued

#### Table 69.Slave Transmitter mode


Status code	Status of the I <sup>2</sup> C	Application softw	are re	sponse	Next action taken by I <sup>2</sup> C		
(I2STAT)	hardware	to/from I2DAT	to 120	CON			hardware
			STA	STO	SI	AA	_
A8h	Own SLA+R has been received;	Load data byte or	x	0	0	0	Last data byte will be transmitted and ACK bit will be received
	ACK has been returned	load data byte	x	0	0	1	Data byte will be transmitted; ACK will be received
B0h	Arbitration lost in SLA+R/W as	Load data byte or	x	0	0	0	Last data byte will be transmitted and ACK bit will be received
	master; Own SLA+R has been received, ACK has been returned	load data byte	x	0	0	1	Data byte will be transmitted; ACK bit will be received
B8H	Data byte in I2DAT has been	Load data byte or	x	0	0	0	Last data byte will be transmitted and ACK bit will be received
	transmitted; ACK has been received	load data byte	x	0	0	1	Data byte will be transmitted; ACK will be received

Status code	Status of the I <sup>2</sup> C	Application softw	are re	sponse	•		Next action taken by I <sup>2</sup> C hardware
(I2STAT)	hardware	to/from I2DAT	to 120	CON			
			STA	STO	SI	AA	_
COH	Data byte in I2DAT has been transmitted;	No I2DAT action or	0	0	0	0	Switched to not addressed SLA mode; no recognition of own SLA o General call address.
	NACK has been received	no I2DAT action or	0	0	0	1	Switched to not addressed SLA mode; Own slave address will be recognized; General call address will be recognized if I2ADR.0 = 1.
		no I2DAT action or	1	0	0	0	Switched to not addressed SLA mode; no recognition of own SLA o General call address. A START condition will be transmitted when the bus becomes free.
		no I2DAT action	1	0	0	1	Switched to not addressed SLA mode; Own slave address will be recognized; General call address will be recognized if I2ADR.0 = 1. A START condition will be transmitted when the bus becomes free.
C8H	Last data byte in I2DAT has been transmitted	No I2DAT action or	0	0	0	0	Switched to not addressed SLA mode; no recognition of own SLA o General call address.
	(AA = 0); ACK has been received	no I2DAT action or	0	0	0	1	Switched to not addressed SLA mode; Own slave address will be recognized; General call address will be recognized if I2ADR.0 = 1.
		no I2DAT action or	1	0	0	0	Switched to not addressed SLA mode; no recognition of own SLA of General call address. A START condition will be transmitted when the bus becomes free.
		no I2DAT action	1	0	0	1	Switched to not addressed SLA mode; Own slave address will be recognized; General call address will be recognized if I2ADR.0 = 1. A START condition will be transmitte when the bus becomes free.

### Table 69. Slave Transmitter mode ...continued

# 12. Serial Peripheral Interface (SPI) (Pin Remap)

The P89LPC970/971/972 provides another high-speed serial communication interface, the SPI interface. SPI is a full-duplex, high-speed, synchronous communication bus with two operation modes: Master mode and Slave mode. Up to 3 Mbit/s can be supported in either Master or Slave mode. It has a Transfer Completion Flag and Write Collision Flag Protection.



The SPI interface has four pins: SPICLK, MOSI, MISO and  $\overline{SS}$ :

- SPICLK, MOSI and MISO are typically tied together between two or more SPI devices. Data flows from master to slave on the MOSI (Master Out Slave In) pin and flows from slave to master on the MISO (Master In Slave Out) pin. The SPICLK signal is output in the master mode and is input in the slave mode. If the SPI system is disabled, i.e. SPEN (SPCTL.6) = 0 (reset value), these pins are configured for port functions.
- SS is the optional slave select pin. In a typical configuration, an SPI master asserts one of its port pins to select one SPI device as the current slave. An SPI slave device uses its SS pin to determine whether it is selected. The SS is ignored if any of the following conditions are true:
  - If the SPI system is disabled, i.e. SPEN (SPCTL.6) = 0 (reset value)
  - If the SPI is configured as a master, i.e., MSTR (SPCTL.4) = 1, and P2.4 is configured as an output (via the P2M1.4 and P2M2.4 SFR bits);
  - If the SS pin is ignored, i.e. SSIG (SPCTL.7) bit = 1, this pin is configured for port functions.

Note that even if the SPI is configured as a master (MSTR = 1), it can still be converted to a slave by driving the  $\overline{SS}$  pin low (if P2.4 is configured as input and SSIG = 0). Should this happen, the SPIF bit (SPSTAT.7) will be set (see Section 12.4 "Mode change on SS")

Typical connections are shown in Figure 37 to Figure 39.

#### Table 70. SPI Control register (SPCTL - address E2h) bit allocation

		0			,			
Bit	7	6	5	4	3	2	1	0
Symbol	SSIG	SPEN	DORD	MSTR	CPOL	CPHA	SPR1	SPR0
Reset	0	0	0	0	0	1	0	0

Bit	Symbol	Description
0	SPR0	SPI Clock Rate Select
1	SPR1	SPR1, SPR0:
		00 — <sup>CCLK</sup> <sup>4</sup>
		01 — <sup>CCLK</sup> <sub>16</sub>
		10 — <sup>CCLK</sup> <sub>64</sub>
		11 — <sup>CCLK</sup> <sub>128</sub>
2	CPHA	SPI Clock PHAse select (see Figure 40 to Figure 43):
		1 — Data is driven on the leading edge of SPICLK, and is sampled on the trailing edge.
		<b>0</b> — Data is driven when $\overline{SS}$ is low (SSIG = 0) and changes on the trailing edge of SPICLK, and is sampled on the leading edge. (Note: If SSIG = 1, the operation is not defined.
3	CPOL	SPI Clock POLarity (see Figure 40 to Figure 43):
		1 — SPICLK is high when idle. The leading edge of SPICLK is the falling edge and the trailing edge is the rising edge.
		<b>0</b> — SPICLK is low when idle. The leading edge of SPICLK is the rising edge and the trailing edge is the falling edge.
4	MSTR	Master/Slave mode Select (see Table 75).
5	DORD	SPI Data ORDer.
		1 — The LSB of the data word is transmitted first.
		0 — The MSB of the data word is transmitted first.
6	SPEN	SPI Enable.
		1 — The SPI is enabled.
		0 — The SPI is disabled and all SPI pins will be port pins.
7	SSIG	SS IGnore.
		1 — MSTR (bit 4) decides whether the device is a master or slave.
		<b>0</b> — The $\overline{SS}$ pin decides whether the device is master or slave. The $\overline{SS}$ pin can be used as a port pin (see <u>Table 75</u> ).

 Table 71.
 SPI Control register (SPCTL - address E2h) bit description

Table 72.	SPI Status register (SPSTAT - address E1h) bit allocation
-----------	---

		0	•		,				
Bit	7	6	5	4	3	2	1	0	
Symbol	SPIF	WCOL	-	-	-	-	-	-	
Reset	0	0	х	х	х	х	х	х	

#### Table 73. SPI Status register (SPSTAT - address E1h) bit description

Bit	Symbol	Description
0:5	-	reserved
6	WCOL	SPI Write Collision Flag. The WCOL bit is set if the SPI data register, SPDAT, is written during a data transfer (see <u>Section 12.5 "Write collision</u> "). The WCOL flag is cleared in software by writing a logic 1 to this bit.
7	SPIF	SPI Transfer Completion Flag. When a serial transfer finishes, the SPIF bit is set and an interrupt is generated if both the ESPI (IEN1.3) bit and the EA bit are set. If SS is an input and is driven low when SPI is in master mode, and SSIG = 0, this bit will also be set (see <u>Section 12.4 "Mode change on SS</u> "). The SPIF flag is cleared in software by writing a logic 1 to this bit.




 Table 74.
 SPI Data register (SPDAT - address E3h) bit allocation

In <u>Figure 37</u>, SSIG (SPCTL.7) for the slave is logic 0, and  $\overline{SS}$  is used to select the slave. The SPI master can use any port pin (including P2.4/SS) to drive the SS pin.




Figure 38 shows a case where two devices are connected to each other and either device can be a master or a slave. When no SPI operation is occurring, both can be configured as masters (MSTR = 1) with SSIG cleared to 0 and P2.4 (SS) configured in quasi-bidirectional mode. When a device initiates a transfer, it can configure P2.4 as an output and drive it low, forcing a mode change in the other device (see Section 12.4 "Mode change on SS") to slave.




Fig 39. SPI single master multiple slaves configuration

In Figure 39, SSIG (SPCTL.7) bits for the slaves are logic 0, and the slaves are selected by the corresponding  $\overline{SS}$  signals. The SPI master can use any port pin (including P2.4/SS) to drive the SS pins.

### 12.1 Configuring the SPI

Table 75 shows configuration for the master/slave modes as well as usages and directions for the modes.

SPEN	SSIG	SS Pin	MSTR	Master or Slave Mode	MISO	MOSI	SPICLK	Remarks
0	x	P2.4[1]	x	SPI Disabled	P2.3 <sup>[1]</sup>	P2.2 <sup>[1]</sup>	P2.5 <sup>[1]</sup>	SPI disabled. P2.2, P2.3, P2.4, P2.5 are used as port pins.
1	0	0	0	Slave	output	input	input	Selected as slave.
1	0	1	0	Slave	Hi-Z	input	input	Not selected. MISO is high-impedance to avoid bus contention.
1	0	0	1 (-> 0)[2]	Slave	output	input	input	P2.4/ $\overline{SS}$ is configured as an input or quasi-bidirectional pin. SSIG is 0. Selected externally as slave if $\overline{SS}$ is selected and is driven low. The MSTR bit will be cleared to logic 0 when $\overline{SS}$ becomes low.

Table 75. SPI master and slave selection

SPEN	SSIG	SS Pin	MSTR	Master or Slave Mode	MISO	MOSI	SPICLK	Remarks
1	0	1	1	Master (idle)	input	Hi-Z	Hi-Z	MOSI and SPICLK are at high-impedance to avoid bus contention when the MAster is idle. The application must pull-up or pull-down SPICLK (depending on CPOL - SPCTL.3) to avoid a floating SPICLK.
				Master (active)		output	output	MOSI and SPICLK are push-pull when the Master is active.
1	1	P2.4[1]	0	Slave	output	input	input	
1	1	P2.4[1]	1	Master	input	output	output	

#### Table 75. SPI master and slave selection ... continued

[1] Selected as a port function

[2] The MSTR bit changes to logic 0 automatically when SS becomes low in input mode and SSIG is logic 0.

### 12.2 Additional considerations for a slave

When CPHA equals zero, SSIG must be logic 0 and the SS pin must be negated and reasserted between each successive serial byte. If the SPDAT register is written while SS is active (low), a write collision error results. The operation is undefined if CPHA is logic 0 and SSIG is logic 1.

When CPHA equals one, SSIG may be set to logic 1. If SSIG = 0, the  $\overline{SS}$  pin may remain active low between successive transfers (can be tied low at all times). This format is sometimes preferred in systems having a single fixed master and a single slave driving the MISO data line.

### 12.3 Additional considerations for a master

In SPI, transfers are always initiated by the master. If the SPI is enabled (SPEN = 1) and selected as master, writing to the SPI data register by the master starts the SPI clock generator and data transfer. The data will start to appear on MOSI about one half SPI bit-time to one SPI bit-time after data is written to SPDAT.

Note that the master can select a slave by driving the  $\overline{SS}$  pin of the corresponding device low. Data written to the SPDAT register of the master is shifted out of the MOSI pin of the master to the MOSI pin of the slave, at the same time the data in SPDAT register in slave side is shifted out on MISO pin to the MISO pin of the master.

After shifting one byte, the SPI clock generator stops, setting the transfer completion flag (SPIF) and an interrupt will be created if the SPI interrupt is enabled (ESPI, or IEN1.3 = 1). The two shift registers in the master CPU and slave CPU can be considered as one distributed 16-bit circular shift register. When data is shifted from the master to the slave, data is also shifted in the opposite direction simultaneously. This means that during one shift cycle, data in the master and the slave are interchanged.

# 12.4 Mode change on SS

If SPEN = 1, SSIG = 0 and MSTR = 1, the SPI is enabled in master mode. The  $\overline{SS}$  pin can be configured as an input (P2M2.4, P2M1.4 = 00) or quasi-bidirectional (P2M2.4, P2M1.4 = 01). In this case, another master can drive this pin low to select this device as an SPI

slave and start sending data to it. To avoid bus contention, the SPI becomes a slave. As a result of the SPI becoming a slave, the MOSI and SPICLK pins are forced to be an input and MISO becomes an output.

The SPIF flag in SPSTAT is set, and if the SPI interrupt is enabled, an SPI interrupt will occur.

User software should always check the MSTR bit. If this bit is cleared by a slave select and the user wants to continue to use the SPI as a master, the user must set the MSTR bit again, otherwise it will stay in slave mode.

### 12.5 Write collision

The SPI is single buffered in the transmit direction and double buffered in the receive direction. New data for transmission can not be written to the shift register until the previous transaction is complete. The WCOL (SPSTAT.6) bit is set to indicate data collision when the data register is written during transmission. In this case, the data currently being transmitted will continue to be transmitted, but the new data, i.e., the one causing the collision, will be lost.


While write collision is detected for both a master or a slave, it is uncommon for a master because the master has full control of the transfer in progress. The slave, however, has no control over when the master will initiate a transfer and therefore collision can occur.


For receiving data, received data is transferred into a parallel read data buffer so that the shift register is free to accept a second character. However, the received character must be read from the Data Register before the next character has been completely shifted in. Otherwise. the previous data is lost.


WCOL can be cleared in software by writing a logic 1 to the bit.


### 12.6 Data mode

Clock Phase Bit (CPHA) allows the user to set the edges for sampling and changing data. The Clock Polarity bit, CPOL, allows the user to set the clock polarity. Figure 40 to Figure 43 show the different settings of Clock Phase bit CPHA.









### 12.7 SPI clock prescaler select

The SPI clock prescaler selection uses the SPR1-SPR0 bits in the SPCTL register (see Table 71).

# 13. Analog comparators

Two analog comparators are provided on the P89LPC970/971/972. Input and output options allow use of the comparators in a number of different configurations. Comparator operation is such that the output is a logic 1 (which may be read in a register and/or routed to a pin) when the positive input (one of two selectable pins) is greater than the negative input (selectable from a pin or an internal reference voltage). Otherwise the output is a zero. Each comparator may be configured to cause an interrupt when the output value changes.

### 13.1 Comparator configuration

Each comparator has a control register, CMP1 for comparator 1 and CMP2 for comparator 2. The control registers are identical and are shown in <u>Table 77</u>.

The overall connections to both comparators are shown in <u>Figure 44</u>. There are eight possible configurations for each comparator, as determined by the control bits in the corresponding CMPn register: CPn, CNn, and OEn. These configurations are shown in <u>Figure 45</u>.

<u>UM103</u>45


When each comparator is first enabled, the comparator output and interrupt flag are not guaranteed to be stable for 10 microseconds. The corresponding comparator interrupt should not be enabled during that time, and the comparator interrupt flag must be cleared before the interrupt is enabled in order to prevent an immediate interrupt service.

 Table 76.
 Comparator Control register (CMP1 - address ACh, CMP2 - address ADh) bit allocation

Bit	7	6	5	4	3	2	1	0
Symbol	-	-	CEn	CPn	CNn	OEn	COn	CMFn
Reset	х	х	0	0	0	0	0	0

# Table 77. Comparator Control register (CMP1 - address ACh, CMP2 - address ADh) bit description

Bit	Symbol	Description
0	CMFn	Comparator interrupt flag. This bit is set by hardware whenever the comparator output COn changes state. This bit will cause a hardware interrupt if enabled. Cleared by software.
1	COn	Comparator output, synchronized to the CPU clock to allow reading by software.
2	OEn	Output enable. When logic 1, the comparator output is connected to the CMPn pin if the comparator is enabled (CEn = 1). This output is asynchronous to the CPU clock.
3	CNn	Comparator negative input select. When logic 0, the comparator reference pin CMPREF is selected as the negative comparator input. When logic 1, the internal comparator reference, $V_{\text{REF}}$ , is selected as the negative comparator input.
4	CPn	Comparator positive input select. When logic 0, CINnA is selected as the positive comparator input. When logic 1, CINnB is selected as the positive comparator input.
5	CEn	Comparator enable. When set, the corresponding comparator function is enabled. Comparator output is stable 10 microseconds after CEn is set.
6:7	-	reserved



### 13.2 Selectable internal reference voltage

An internal reference voltage generator may be used to supply a default reference when a single comparator input pin is used. The user may program one of eight different values for the internal reference voltage using the Comparator Reference register (CMPREF). Each of the two comparators may use a different reference voltage. Please refer to the *P89LPC970/971/972 data sheet* for specifications.

#### Table 78. Comparator Reference register (CMPREF - address FFCBh) bit allocation

			•	•		,		
Bit	7	6	5	4	3	2	1	0
Symbol	-	REFS5	REFS4	REFS3	-	REFS2	REFS1	REFS0
Reset	х	0	0	0	х	0	0	0

#### Table 79. Comparator Reference register (CMPREF - address FFCBh) bit description

Bit	Symbol	Description
2:0	REFS2:0	Reference Select for Comparator 1. These bits are used to select the internal reference voltage for Comparator 1.
		The following references for Comparator 1 are selected by reference bits REFS[2:0]:
		000 Bandgap voltage, Vref(bg), nominally 1.23 V
		001 Vref_trip1, 0.875 V <sub>DD</sub> .
		010 Vref_trip2, 0.750 V <sub>DD</sub> .
		011 Vref_trip3, 0.625 V <sub>DD</sub> .
		100 Vref_trip4, 0.500V <sub>DD</sub> .
		101 Vref_trip5, 0.375 V <sub>DD</sub> .
		110 Vref_trip6, 0.250 V <sub>DD</sub> .
		111 Vref_trip7, 0.125 V <sub>DD</sub> .
3	-	Beserved

3 - Reserved

lable	e /9. Co	mparator Reference register (CMPREF - address FFCBh) bit description
Bit	Symbol	Description
6:4 REFS5:3		Reference Select for Comparator 2. These bits are used to select the internal reference voltage for Comparator 2.
		The following references for Comparator 2 are selected by reference bits REFS[5:3]:
		000 Bandgap voltage, Vref(bg), nominally 1.23 V
		001 Vref_trip1, 0.875 V <sub>DD</sub> .
		010 Vref_trip2, 0.750 V <sub>DD</sub> .
		011 Vref_trip3, 0.625 V <sub>DD</sub> .
		100 Vref_trip4, 0.500 V <sub>DD</sub> .
		101 Vref_trip5, 0.375 V <sub>DD</sub> .
		110 Vref_trip6, 0.250 V <sub>DD</sub> .
		111 Vref_trip7, 0.125 V <sub>DD</sub> .
7	-	Reserved

### **13.3 Comparator input pins**

Comparator input and reference pins maybe be used as either digital I/O or as inputs to the comparator. However, when selected as comparator input signals in CMPn lower voltage limits apply. Please refer to the *P89LPC970/971/972 data sheet* for specifications.

### **13.4 Comparator interrupt**

Each comparator has an interrupt flag CMFn contained in its configuration register. This flag is set whenever the comparator output changes state. The flag may be polled by software or may be used to generate an interrupt. The two comparators use one common interrupt vector. The interrupt will be generated when the interrupt enable bit EC in the IEN1 register is set and the interrupt system is enabled via the EA bit in the IEN0 register. If both comparators enable interrupts, after entering the interrupt service routine, the user will need to read the flags to determine which comparator caused the interrupt.


When a comparator is disabled the comparator's output, COx, goes high. If the comparator output was low and then is disabled, the resulting transition of the comparator output from a low to high state will set the comparator flag, CMFx. This will cause an interrupt if the comparator interrupt is enabled. The user should therefore disable the comparator interrupt prior to disabling the comparator. Additionally, the user should clear the comparator flag, CMFx, after disabling the comparator.

### 13.5 Comparators and power reduction modes

Either or both comparators may remain enabled when Power-down mode or Idle mode is activated, but both comparators are disabled automatically in Total Power-down mode.

If a comparator interrupt is enabled (except in Total Power-down mode), a change of the comparator output state will generate an interrupt and wake-up the processor. If the comparator output to a pin is enabled, the pin should be configured in the push-pull mode in order to obtain fast switching times while in Power-down mode. The reason is that with the oscillator stopped, the temporary strong pull-up that normally occurs during switching on a quasi-bidirectional port pin does not take place.

Comparators consume power in Power-down mode and Idle mode, as well as in the normal operating mode. This should be taken into consideration when system power consumption is an issue. To minimize power consumption, the user can power-down the comparators by disabling the comparators and setting PCONA.5 to logic 1, or simply putting the device in Total Power-down mode.



### **13.6** Comparators configuration example

The code shown below is an example of initializing one comparator. Comparator 1 is configured to use the CIN1A and CMPREF inputs, outputs the comparator result to the CMP1 pin, and generates an interrupt when the comparator output changes.

CMPINIT:

MOV PTOAD,#030h	;Disable digital INPUTS on CIN1A, CMPREF.
ANL POM2,#0CFh	;Disable digital OUTPUTS on pins that are used
ORL P0M1,#030h	;for analog functions: CIN1A, CMPREF.
MOV CMP1,#024h	;Turn on comparator 1 and set up for:
	;Positive input on CIN1A.
	;Negative input from CMPREF
pin.	
	;Output to CMP1 pin enabled.
CALL delay10us	;Output to CMP1 pin enabled. ;The comparator needs at least 10 microseconds
CALL delay10us before use.	
1	
before use.	;The comparator needs at least 10 microseconds
before use. ANL CMP1,#0FEh	;The comparator needs at least 10 microseconds ;Clear comparator 1 interrupt flag.

**User manual** 

The interrupt routine used for the comparator must clear the interrupt flag (CMF1 in this case) before returning

# 14. Keypad interrupt (KBI)

The Keypad Interrupt function is intended primarily to allow a single interrupt to be generated when Port 0 is equal to or not equal to a certain pattern. This function can be used for bus address recognition or keypad recognition. The port can be configured via SFRs for different tasks.

There are three SFRs used for this function. The Keypad Interrupt Mask Register (KBMASK) is used to define which input pins connected to Port 0 are enabled to trigger the interrupt. The Keypad Pattern Register (KBPATN) is used to define a pattern that is compared to the value of Port 0. The Keypad Interrupt Flag (KBIF) in the Keypad Interrupt Control Register (KBCON) is set when the condition is matched while the Keypad Interrupt function is active. An interrupt will be generated if it has been enabled by setting the EKBI bit in IEN1 register and EA = 1. The PATN\_SEL bit in the Keypad Interrupt Control Register (KBCON) is used to define equal or not-equal for the comparison.

In order to use the Keypad Interrupt as an original KBI function like in the 87LPC76x series, the user needs to set KBPATN = 0FFH and PATN\_SEL = 0 (not equal), then any key connected to Port0 which is enabled by KBMASK register is will cause the hardware to set KBIF = 1 and generate an interrupt if it has been enabled. The interrupt may be used to wake-up the CPU from Idle or Power-down modes. This feature is particularly useful in handheld, battery powered systems that need to carefully manage power consumption yet also need to be convenient to use.

In order to set the flag and cause an interrupt, the pattern on Port 0 must be held longer than 6 CCLKs

Table 80.	Keypad Patterr	n register (KBPATN	- address 93h) bit allocation
-----------	----------------	--------------------	-------------------------------

Bit	7	6	5	4	3	2	1	0
Symbol	KBPATN.7	KBPATN.6	KBPATN.5	KBPATN.4	KBPATN.3	KBPATN.2	KBPATN.1	KBPATN.0
Reset	1	1	1	1	1	1	1	1

#### Table 81. Keypad Pattern register (KBPATN - address 93h) bit description

х

			• •						
Bit Sym	bol	Access	Descripti	on					
0:7 KBP	ATN.7:0	R/W	Pattern bi	t 0 - bit 7					
Table 82.         Keypad Control register (KBCON - address 94h) bit allocation									
					, , , , , , , , , , , , , , , , , , , ,				
Bit	7	6		5	4	3	2	1	0

х

Reset

х

х

0

0

х

х

Bit	Symbol	Access	Description
0	KBIF	R/W	Keypad Interrupt Flag. Set when Port 0 matches user defined conditions specified in KBPATN, KBMASK, and PATN_SEL. Needs to be cleared by software by writing logic 0.
1	PATN_SEL	R/W	Pattern Matching Polarity selection. When set, Port 0 has to be equal to the user-defined Pattern in KBPATN to generate the interrupt. When clear, Port 0 has to be not equal to the value of KBPATN register to generate the interrupt.
2:7	-	-	reserved

#### Table 83. Keypad Control register (KBCON - address 94h) bit description

Table 84.	Keypad Intern	Keypad Interrupt Mask register (KBMASK - address 86h) bit allocation							
Bit	7	6	5	4	3	2	1	0	
Symbol	KBMASK.7	KBMASK.6	KBMASK.5	KBMASK.4	KBMASK.3	KBMASK.2	KBMASK.1	KBMASK.0	
Reset	0	0	0	0	0	0	0	0	

#### Table 85. Keypad Interrupt Mask register (KBMASK - address 86h) bit description

<ul> <li>KBMASK.0 When set, enables P0.0 as a cause of a Keypad Interrupt.</li> <li>KBMASK.1 When set, enables P0.1 as a cause of a Keypad Interrupt.</li> <li>KBMASK.2 When set, enables P0.2 as a cause of a Keypad Interrupt.</li> <li>KBMASK.3 When set, enables P0.3 as a cause of a Keypad Interrupt.</li> <li>KBMASK.4 When set, enables P0.4 as a cause of a Keypad Interrupt.</li> <li>KBMASK.5 When set, enables P0.5 as a cause of a Keypad Interrupt.</li> <li>KBMASK.6 When set, enables P0.6 as a cause of a Keypad Interrupt.</li> <li>KBMASK.7 When set, enables P0.7 as a cause of a Keypad Interrupt.</li> </ul>	Bit	Symbol	Description
<ul> <li>KBMASK.2 When set, enables P0.2 as a cause of a Keypad Interrupt.</li> <li>KBMASK.3 When set, enables P0.3 as a cause of a Keypad Interrupt.</li> <li>KBMASK.4 When set, enables P0.4 as a cause of a Keypad Interrupt.</li> <li>KBMASK.5 When set, enables P0.5 as a cause of a Keypad Interrupt.</li> <li>KBMASK.6 When set, enables P0.6 as a cause of a Keypad Interrupt.</li> </ul>	0	KBMASK.0	When set, enables P0.0 as a cause of a Keypad Interrupt.
<ul> <li>KBMASK.3 When set, enables P0.3 as a cause of a Keypad Interrupt.</li> <li>KBMASK.4 When set, enables P0.4 as a cause of a Keypad Interrupt.</li> <li>KBMASK.5 When set, enables P0.5 as a cause of a Keypad Interrupt.</li> <li>KBMASK.6 When set, enables P0.6 as a cause of a Keypad Interrupt.</li> </ul>	1	KBMASK.1	When set, enables P0.1 as a cause of a Keypad Interrupt.
<ul> <li>KBMASK.4 When set, enables P0.4 as a cause of a Keypad Interrupt.</li> <li>KBMASK.5 When set, enables P0.5 as a cause of a Keypad Interrupt.</li> <li>KBMASK.6 When set, enables P0.6 as a cause of a Keypad Interrupt.</li> </ul>	2	KBMASK.2	When set, enables P0.2 as a cause of a Keypad Interrupt.
<ul> <li>5 KBMASK.5 When set, enables P0.5 as a cause of a Keypad Interrupt.</li> <li>6 KBMASK.6 When set, enables P0.6 as a cause of a Keypad Interrupt.</li> </ul>	3	KBMASK.3	When set, enables P0.3 as a cause of a Keypad Interrupt.
6 KBMASK.6 When set, enables P0.6 as a cause of a Keypad Interrupt.	4	KBMASK.4	When set, enables P0.4 as a cause of a Keypad Interrupt.
	5	KBMASK.5	When set, enables P0.5 as a cause of a Keypad Interrupt.
7 KBMASK.7 When set, enables P0.7 as a cause of a Keypad Interrupt.	6	KBMASK.6	When set, enables P0.6 as a cause of a Keypad Interrupt.
	7	KBMASK.7	When set, enables P0.7 as a cause of a Keypad Interrupt.

[1] The Keypad Interrupt must be enabled in order for the settings of the KBMASK register to be effective.

# 15. Watchdog timer (WDT)

The watchdog timer subsystem protects the system from incorrect code execution by causing a system reset when it underflows as a result of a failure of software to feed the timer prior to the timer reaching its terminal count. The watchdog timer can only be reset by a power-on reset.

### 15.1 Watchdog function

The user has the ability using the WDCON, CLKCON and UCFG1 registers to control the run /stop condition of the WDT, the clock source for the WDT, the prescaler value, and whether the WDT is enabled to reset the device on underflow. In addition, there is a safety mechanism which forces the WDT to be enabled by values programmed into UCFG1 either through IAP or a commercial programmer.

The WDTE bit (UCFG2.7), if set, enables the WDT to reset the device on underflow. Following reset, the WDT will be running regardless of the state of the WDTE bit.

The WDRUN bit (WDCON.2) can be set to start the WDT and cleared to stop the WDT. Following reset this bit will be set and the WDT will be running. All writes to WDCON need to be followed by a feed sequence (see <u>Section 15.2</u>). Additional bits in WDCON allow the user to select the clock source for the WDT and the prescaler.

When the timer is not enabled to reset the device on underflow, the WDT can be used in 'timer mode' and be enabled to produce an interrupt (IEN0.6) if desired.

The Watchdog Safety Enable bit, WDSE (UCFG2.1) along with WDTE, is designed to force certain operating conditions at power-up. Refer to <u>Table 86</u> for details.


Figure 48 shows the watchdog timer in watchdog mode. It consists of a programmable 13-bit prescaler, and an 8-bit down counter. The down counter is clocked (decremented) by a tap taken from the prescaler. The clock source for the prescaler is either PCLK, low speed crystal oscillator or the watchdog oscillator selected by the WDCLK bit in the WDCON register and XTALWD bit in the CLKCON register. (Note that switching of the clock sources will not take effect immediately - see Section 15.3).


The watchdog asserts the watchdog reset when the watchdog count underflows and the watchdog reset is enabled. When the watchdog reset is enabled, writing to WDL or WDCON must be followed by a feed sequence for the new values to take effect.

If a watchdog reset occurs, its behavior is similar to power on reset. Both POF and BOF are cleared.

#### Table 86.Watchdog timer configuration

WDTE	WDSE	FUNCTION
0	x	The watchdog reset is disabled. The timer can be used as an internal timer and can be used to generate an interrupt. WDSE has no effect.
1	0	The watchdog reset is enabled. The user can set WDCLK to choose the clock source.
1	1	<ul> <li>The watchdog reset is enabled, along with additional safety features:</li> <li>1. WDCLK is forced to 1 (using watchdog oscillator)</li> <li>2. WDCON and WDL register can only be written once</li> <li>3. WDPLIN is forced to 1</li> </ul>





UM10345

### 15.2 Feed sequence

The watchdog timer control register and the 8-bit down counter (See Figure 47) are not directly loaded by the user. The user writes to the WDCON and the WDL SFRs. At the end of a feed sequence, the values in the WDCON and WDL SFRs are loaded to the control register and the 8-bit down counter. Before the feed sequence, any new values written to these two SFRs will not take effect. To avoid a watchdog reset, the watchdog timer needs to be fed (via a special sequence of software action called the feed sequence) prior to reaching an underflow.

To feed the watchdog, two write instructions must be sequentially executed successfully. Between the two write instructions, SFR reads are allowed, but writes are not allowed. The instructions should move A5H to the WFEED1 register and then 5AH to the WFEED2 register. An incorrect feed sequence will cause an immediate watchdog reset. The program sequence to feed the watchdog timer is as follows:

```
CLR EA ;disable interrupt
MOV WFEED1,#0A5h ;do watchdog feed part 1
MOV WFEED2,#05Ah ;do watchdog feed part 2
SETB EA ;enable interrupt
```

This sequence assumes that the P89LPC970/971/972 interrupt system is enabled and there is a possibility of an interrupt request occurring during the feed sequence. If an interrupt was allowed to be serviced and the service routine contained any SFR writes, it would trigger a watchdog reset. If it is known that no interrupt could occur during the feed sequence, the instructions to disable and re-enable interrupts may be removed.

In watchdog mode (WDTE = 1), writing the WDCON register must be IMMEDIATELY followed by a feed sequence to load the WDL to the 8-bit down counter, and the WDCON to the shadow register. If writing to the WDCON register is not immediately followed by the feed sequence, a watchdog reset will occur.

For example: setting WDRUN = 1:

MOV ACC,WDCON ;get WDCON
SETB ACC.2 ;set WD\_RUN=1
MOV WDL,#0FFh ;New count to be loaded to 8-bit down counter
 CLR EA ;disable interrupt
MOV WDCON,ACC ;write back to WDCON (after the watchdog is enabled, a feed
must occur ; immediately)
MOV WFEED1,#0A5h ;do watchdog feed part 1
MOV WFEED2,#05Ah ;do watchdog feed part 2
 SETB EA ;enable interrupt

In timer mode (WDTE = 0), WDCON is loaded to the control register every CCLK cycle (no feed sequence is required to load the control register), but a feed sequence is required to load from the WDL SFR to the 8-bit down counter before a time-out occurs.

The number of watchdog clocks before timing out is calculated by the following equations:

$$tclks = (2^{(5+PRE)})(WDL+1)+1$$
 (1)

where:

**User manual** 

PRE is the value of prescaler (PRE2 to PRE0) which can be the range 0 to 7, and; WDL is the value of watchdog load register which can be the range of 0 to 255.

The minimum number of tclks is:

$$tclks = (2^{(5+0)})(0+1) + 1 = 33$$
 (2)

The maximum number of tclks is:

$$tclks = (2^{(5+7)})(255+1) + 1 = 1048577$$
(3)

Table 89 shows sample P89LPC970/971/972 timeout values.

Table 87.	Watchdog	Watchdog Timer Control register (WDCON - address A7h) bit allocation								
Bit	7	6	5	4	3	2	1	0		
Symbol	PRE2	PRE1	PRE0	-	-	WDRUN	WDTOF	WDCLK		
Reset	1	1	1	х	х	1	1/0	1		

#### Table 88. Watchdog Timer Control register (WDCON - address A7h) bit description

Bit	Symbol	Description
0	WDCLK	Watchdog input clock select. When set, the watchdog oscillator is selected. When cleared, PCLK is selected. (If the CPU is powered down, the watchdog is disabled if WDCLK = 0, see Section 15.5). (Note: If both WDTE and WDSE are set to 1, this bit is forced to 1.) Refer to Section 15.3 for details.
1	WDTOF	Watchdog Timer Time-Out Flag. This bit is set when the 8-bit down counter underflows. In watchdog mode, a feed sequence will clear this bit. It can also be cleared by writing a logic 0 to this bit in software.
2	WDRUN	Watchdog Run Control. The watchdog timer is started when WDRUN = 1 and stopped when WDRUN = 0. This bit is forced to 1 (watchdog running) and cannot be cleared to zero if both WDTE and WDSE are set to 1.
3:4	-	reserved
5	PRE0	
6	PRE1	Clock Prescaler Tap Select. Refer to Table 89 for details.
7	PRE2	

#### Table 89. Watchdog timeout values

PRE2 to PRE0		<b>Timeout Period</b>	Watchdog Clock Source				
	decimal)	(in watchdog clock cycles)	25 KHz Watchdog Oscillator Clock (Nominal)	400 KHz Watchdog Oscillator Clock (Nominal)	12 MHz CCLK (6 MHz <sup>CCLK</sup> 2 Watchdog Clock)		
000	0	33	1.32 ms	82.5 μs	5.50 μs		
	255	8,193	328.0 ms	20.5 ms	1.37 ms		
001	0	65	2.6 ms	162.5 μs	10.8 μs		
	255	16,385	656.0 ms	41.0 ms	2.73 ms		
010	0	129	5.16 μs	322.5 μs	21.5 μs		
	255	32,769	1.31 s	81.9 ms	5.46 ms		
011	0	257	10.28 ms	642.5 μs	42.8 μs		
	255	65,537	2.62 s	163.8 ms	10.9 ms		

PRE2 to PRE0		Timeout Period		Watchdog Clock Source				
	decimal)	(in watchdog clock cycles)	25 KHz Watchdog Oscillator Clock (Nominal)	400 KHz Watchdog Oscillator Clock (Nominal)	12 MHz CCLK (6 MHz <sup>CCLK</sup> % Watchdog Clock)			
100	0	513	20.48 ms	1.28 ms	85.5 μs			
	255	131,073	5.24 s	327.7 ms	21.8 ms			
101	0	1,025	40.96 ms	2.56 ms	170.8 μs			
	255	262,145	10.48 s	655.4 ms	43.7 ms			
110	0	2,049	81.92 ms	5.12 ms	341.5 μs			
	255	524,289	20.96 s	1.31 s	87.4 ms			
111	0	4097	163.2 ms	10.2 ms	682.8 μs			
	255	1,048,577	41.92 s	2.62 s	174.8 ms			

### Table 89. Watchdog timeout values

### 15.3 Watchdog clock source

The watchdog timer system has an on-chip oscillator which provides two options: 400 kHz and 25 kHz. Lower power consumption of watchdog timer can be realized by selecting 25 kHz option. The watchdog timer can be clocked from the 400 kHz/25 kHz watchdog oscillator, PCLK or low speed crystal oscillator (refer to Figure 46) by configuring the WDCLK bit in the Watchdog Control Register WDCON, XTALWD bit and WDMOD bit in CLKCON register. When the watchdog feature is enabled, the timer must be fed regularly by software in order to prevent it from resetting the CPU.

#### Table 90. Watchdog input clock selection


WDMOD(CLKCON.5)	WDCLK(WDCON.0)	XTALWD(CLKCON.4)	Watchdog input clock selection
0	1	0	400kHz watchdog oscillator
1	1	0	25kHz watchdog oscillator
X	0	0	PCLK
X	Х	1	Low speed crystal oscillator

WDCLK bit is used to switch between watchdog oscillator and PCLK. XTALWD bit is used to switch between watchdog oscillator/PCLK and low speed crystal oscillator. WDMOD bit is used to switch the watchdog oscillator between 400 kHz and 25 kHz. After changing clock source, switching of the clock source will not immediately take effect. As shown in Figure 48, the selection is loaded after a watchdog feed sequence. In addition, due to clock synchronization logic, it can take two old clock cycles before the old clock source is deselected, and then an additional two new clock cycles before the new clock source is selected.

Since the prescaler starts counting immediately after a feed, switching clocks can cause some inaccuracy in the prescaler count. The inaccuracy could be as much as 2 old clock source counts plus 2 new clock cycles.

**Note:** When switching clocks, it is important that the old clock source is left enabled for two clock cycles after the feed completes. Otherwise, the watchdog may become disabled when the old clock source is disabled. For example, suppose PCLK (WCLK = 0) is the current clock source. After WCLK is set to logic 1, the program should wait at least two PCLK cycles (4 CCLKs) after the feed completes before going into Power-down mode.


Otherwise, the watchdog could become disabled when CCLK turns off. The watchdog oscillator will never become selected as the clock source unless CCLK is turned on again first.



### 15.4 Watchdog Timer in Timer mode

Figure 48 shows the Watchdog Timer in Timer Mode. In this mode, any changes to WDCON are written to the shadow register after one watchdog clock cycle. A watchdog underflow will set the WDTOF bit. If IEN0.6 is set, the watchdog underflow is enabled to cause an interrupt. WDTOF is cleared by writing a logic 0 to this bit in software. When an underflow occurs, the contents of WDL is reloaded into the down counter and the watchdog timer immediately begins to count down again.

A feed is necessary to cause WDL to be loaded into the down counter before an underflow occurs. Incorrect feeds are ignored in this mode.



### 15.5 Power-down operation

The WDT oscillator or low speed crystal oscillator will continue to run in power-down, consuming approximately 50  $\mu$ A, as long as the corresponding oscillator is selected as the clock source for the WDT. If either of the two oscillators is selected, the other one will be stopped in power-down. Selecting PCLK as the WDT source will result in the WDT oscillator going into power-down with the rest of the device (see Section 15.3). Power-down mode will also prevent PCLK from running and therefore the watchdog is effectively disabled.

### 15.6 Periodic wake-up from power-down without an external oscillator

Without using an external oscillator source, the power consumption required in order to have a periodic wake-up is determined by the power consumption of the internal oscillator source used to produce the wake-up. The Real-time clock running from the internal RC oscillator can be used. The power consumption of this oscillator is approximately 300  $\mu$ A. Instead, if the WDT is used to generate interrupts the current is reduced to approximately 50  $\mu$ A. Whenever the WDT underflows, the device will wake-up. When wake-up, WDMOD bit is cleared and watchdog oscillator is 400 kHz.

# **16. Additional features**

The AUXR1 register contains several special purpose control bits that relate to several chip features. AUXR1 is described in Table 92

Table 91.         AUXR1 register (address A2h) bit allocation	
---	--

				-				
Bit	7	6	5	4	3	2	1	0
Symbol	CLKLP	EBRR	ENT1	ENT0	SRST	0	-	DPS
Reset	0	0	0	0	0	0	х	0

Bit	Symbol	Description
0	DPS	Data Pointer Select. Chooses one of two Data Pointers.
1	-	Not used. Allowable to set to a logic 1.
2	0	This bit contains a hard-wired 0. Allows toggling of the DPS bit by incrementing AUXR1, without interfering with other bits in the register.
3	SRST	Software Reset. When set by software, resets the P89LPC970/971/972 as if a hardware reset occurred.
4	ENT0	When set the P1.2 pin is toggled whenever Timer 0 overflows. The output frequency is therefore one half of the Timer 0 overflow rate. Refer to <u>Section 7</u> <u>"Timers 0 and 1"</u> for details.
5	ENT1	When set, the P0.7 pin is toggled whenever Timer 1 overflows. The output frequency is therefore one half of the Timer 1 overflow rate. Refer to <u>Section 7</u> <u>"Timers 0 and 1"</u> for details.
6	EBRR	UART Break Detect Reset Enable. If logic 1, UART Break Detect will cause a chip reset and force the device into ISP mode.
7	CLKLP	Clock Low Power Select. When set, reduces power consumption in the clock circuits. Can be used when the clock frequency is 8 MHz or less. After reset this bit is cleared to support up to 12 MHz operation.

#### Table 92. AUXR1 register (address A2h) bit description

### 16.1 Software reset

The SRST bit in AUXR1 gives software the opportunity to reset the processor completely, as if an external reset or watchdog reset had occurred. If a value is written to AUXR1 that contains a 1 at bit position 3, all SFRs will be initialized and execution will resume at program address 0000. Care should be taken when writing to AUXR1 to avoid accidental software resets.

### **16.2 Dual Data Pointers**

The dual Data Pointers (DPTR) adds to the ways in which the processor can specify the address used with certain instructions. The DPS bit in the AUXR1 register selects one of the two Data Pointers. The DPTR that is not currently selected is not accessible to software unless the DPS bit is toggled.

Specific instructions affected by the Data Pointer selection are:

**INC DPTR** — Increments the Data Pointer by 1

JMP@A+DPTR — Jump indirect relative to DPTR value

MOV DPTR, #data16 — Load the Data Pointer with a 16-bit constant

**MOVC A**, **@A+DPTR** — Move code byte relative to DPTR to the accumulator

MOVX A, @DPTR - Move accumulator to data memory relative to DPTR

MOVX @DPTR, A - Move from data memory relative to DPTR to the accumulator

Also, any instruction that reads or manipulates the DPH and DPL registers (the upper and lower bytes of the current DPTR) will be affected by the setting of DPS. The MOVX instructions have limited application for the P89LPC970/971/972 since the part does not have an external data bus. However, they may be used to access Flash configuration information (see Flash Configuration section) or auxiliary data (XDATA) memory.

Bit 2 of AUXR1 is permanently wired as a logic 0. This is so that the DPS bit may be toggled (thereby switching Data Pointers) simply by incrementing the AUXR1 register, without the possibility of inadvertently altering other bits in the register.

# 17. Flash memory

### 17.1 General description

The P89LPC970/971/972 Flash memory provides in-circuit electrical erasure and programming. The Flash can be read and written as bytes. The Sector and Page Erase functions can erase any Flash sector (1 kB) or page (64 bytes). The Chip Erase operation will erase the entire program memory. Five Flash programming methods are available. On-chip erase and write timing generation contribute to a user-friendly programming interface. The P89LPC970/971/972 Flash reliably stores memory contents even after 100,000 erase and program cycles. The cell is designed to optimize the erase and programming mechanisms. P89LPC970/971/972 uses V<sub>DD</sub> as the supply voltage to perform the Program/Erase algorithms. When voltage supply is lower than 2.4V, the BOD FLASH is tripped and flash erase/program is blocked.

### 17.2 Features

- Parallel programming with industry-standard commercial programmers
- In-Circuit serial Programming (ICP) with industry-standard commercial programmers.
- IAP-Lite allows individual and multiple bytes of code memory to be used for data storage and programmed under control of the end application.
- Internal fixed boot ROM, containing low-level In-Application Programming (IAP) routines that can be called from the end application (in addition to IAP-Lite).
- Default serial loader providing In-System Programming (ISP) via the serial port, located in upper end of user program memory.
- Boot vector allows user provided Flash loader code to reside anywhere in the Flash memory space, providing flexibility to the user.
- Programming and erase over the full operating voltage range
- Read/Programming/Erase using ISP, IAP or IAP-Lite
- Any flash program operation in 2 ms (4 ms for erase/program)
- · Programmable security for the code in the Flash for each sector
- > 100,000 typical erase/program cycles for each byte
- 10-year minimum data retention

# 17.3 Flash programming and erase

The P89LPC970/971/972 program memory consists of two/four/eight 1 kB sectors. Each sector can be further divided into 64-byte pages. In addition to sector erase and page erase, a 64-byte page register is included which allows from 1 to 64 bytes of a given page to be programmed at the same time, substantially reducing overall programming time. Five methods of programming this device are available.

• Parallel programming with industry-standard commercial programmers.

- In-Circuit serial Programming (ICP) with industry-standard commercial programmers.
- IAP-Lite allows individual and multiple bytes of code memory to be used for data storage and programmed under control of the end application.
- Internal fixed boot ROM, containing low-level In-Application Programming (IAP) routines that can be called from the end application (in addition to IAP-Lite).
- A factory-provided default serial loader, located in upper end of user program memory, providing In-System Programming (ISP) via the serial port.
- Note: Flash erase/program will be blocked if BOD FLASH is detected (Vdd<2.4 V).

### 17.4 Using Flash as data storage: IAP-Lite

The Flash code memory array of this device supports IAP-Lite in addition to standard IAP functions. Any byte in a non-secured sector of the code memory array may be read using the MOVC instruction and thus is suitable for use as non-volatile data storage. IAP-Lite provides an erase-program function that makes it easy for one or more bytes within a page to be erased and programmed in a single operation without the need to erase or program any other bytes in the page. IAP-Lite is performed in the application under the control of the microcontroller's firmware using four SFRs and an internal 64-byte 'page register' to facilitate erasing and programing within unsecured sectors. These SFRs are:

- FMCON (Flash Control Register). When read, this is the status register. When written, this is a command register. Note that the status bits are cleared to logic 0s when the command is written.
- FMADRL, FMADRH (Flash memory address low, Flash memory address high). Used to specify the byte address within the page register or specify the page within user code memory
- FMDATA (Flash Data Register). Accepts data to be loaded into the page register.

The page register consists of 64 bytes and an update flag for each byte. When a LOAD command is issued to FMCON the page register contents and all of the update flags will be cleared. When FMDATA is written, the value written to FMDATA will be stored in the page register at the location specified by the lower 6 bits of FMADRL. In addition, the update flag for that location will be set. FMADRL will auto-increment to the next location. Auto-increment after writing to the last byte in the page register will 'wrap-around' to the first byte in the page register, but will not affect FMADRL[7:6]. Bytes loaded into the page register do not have to be continuous. Any byte location can be loaded into the page register by changing the contents of FMADRL prior to writing to FMDATA. However, each location in the page register can only be written once following each LOAD command. Attempts to write to a page register location more than once should be avoided.

FMADRH and FMADRL[7:6] are used to select a page of code memory for the erase-program function. When the erase-program command is written to FMCON, the locations within the code memory page that correspond to updated locations in the page register, will have their contents erased and programmed with the contents of their corresponding locations in the page register. Only the bytes that were loaded into the page register will be erased and programmed in the user code array. Other bytes within the user code memory will not be affected.

Writing the erase-program command (68H) to FMCON will start the erase-program process and place the CPU in a program-idle state. The CPU will remain in this idle state until the erase-program cycle is either completed or terminated by an interrupt. When the program-idle state is exited FMCON will contain status information for the cycle.

If an interrupt occurs during an erase/programming cycle, the erase/programming cycle will be aborted and the OI flag (Operation Interrupted) in FMCON will be set. If the application permits interrupts during erasing-programming the user code should check the OI flag (FMCON.0) after each erase-programming operation to see if the operation was aborted. If the operation was aborted, the user's code will need to repeat the process starting with loading the page register.

The erase-program cycle takes 4 ms (2 ms for erase, 2 ms for programming) to complete, regardless of the number of bytes that were loaded into the page register.

Erasing-programming of a single byte (or multiple bytes) in code memory is accomplished using the following steps:

- Write the LOAD command (00H) to FMCON. The LOAD command will clear all locations in the page register and their corresponding update flags.
- Write the address within the page register to FMADRL. Since the loading the page register uses FMADRL[5:0], and since the erase-program command uses FMADRH and FMADRL[7:6], the user can write the byte location within the page register (FMADRL[5:0]) and the code memory page address (FMADRH and FMADRL[7:6]) at this time.
- Write the data to be programmed to FMDATA. This will increment FMADRL pointing to the next byte in the page register.
- Write the address of the next byte to be programmed to FMADRL, if desired. (Not needed for contiguous bytes since FMADRL is auto-incremented). All bytes to be programmed must be within the same page.
- Write the data for the next byte to be programmed to FMDATA.
- Repeat writing of FMADRL and/or FMDATA until all desired bytes have been loaded into the page register.
- Write the page address in user code memory to FMADRH and FMADRL[7:6], if not previously included when writing the page register address to FMADRL[5:0].
- Write the erase-program command (68H) to FMCON, starting the erase-program cycle.
- Read FMCON to check status. If aborted, repeat starting with the LOAD command.

#### Table 93. Flash Memory Control register (FMCON - address E4h) bit allocation

Bit	7	6	5	4	3	2	1	0
Symbol (R)	-	-	-	-	HVA	HVE	SV	OI
Symbol (W)	FMCMD.7	FMCMD.6	FMCMD.5	FMCMD.4	FMCMD.3	FMCMD.2	FMCMD.1	FMCMD.0
Reset	0	0	0	0	0	0	0	0

Bit	Symbol	Access	Description
0	OI	R	Operation interrupted. Set when cycle aborted due to an interrupt or reset.
	FMCMD.0	W	Command byte bit 0.
1	SV	R	Security violation. Set when an attempt is made to program, erase, or CRC a secured sector or page.
	FMCMD.1	W	Command byte bit 1
2	HVE	R	High voltage error. Set when an error occurs in the high voltage generator.
	FMCMD.2	W	Command byte bit 2.
3	HVA	R	High voltage abort. Set if either an interrupt or BOD FLASH is detected during a program or erase cycle.
	FMCMD.3	W	Command byte bit 3.
4:7	-	R	reserved.
4	FMCMD.4	W	Command byte bit 4.
5	FMCMD.5	W	Command byte bit 5.
6	FMCMD.6	W	Command byte bit 6.
7	FMCMD.7	W	Command byte bit 7.

#### Table 94. Flash Memory Control register (FMCON - address E4h) bit description

An assembly language routine to load the page register and perform an erase/program operation is shown below.

;******	* * * * * * * * *	* * * * * * * * * * * * * * * *	* * * * * * * * * * * * * * * * * *
;* pgi	m user co	de *	
;******	* * * * * * * * *	*****	* * * * * * * * * * * * * * * * * *
;*			*
;* Input	s:	*	
;*R3 = n	umber of	am (byte) *	
;*R4 = p	age addre	*	
;*R5 = p	age addre	ess LSB(byte)	*
;*R7 = p	ointer to	o data buffer in	n RAM(byte) *
;* Outpu	ts:		*
;*R7 = s	tatus (by	rte)	*
-		no error, set on	
• * * * * * * * * /	* * * * * * * * *	**************	* * * * * * * * * * * * * * * * * * *
LOAD	EQU	00H	
ΕP	EQU	68H	
PGM USER	:		
_	MOV	FMCON, #LOAD	;load command, clears page register
	MOV	FMADRH,R4	;get high address
	MOV	FMADRL,R5	;get low address
MOV	A,R7	;	
	MOV	R0,A	;get pointer into RO
LOAD_PA	GE:		
	MOV	FMDAT,@R0	;write data to page register
	INC	RO	;point to next byte
	DJNZ	R3,LOAD_PAGE	;do until count is zero
	MOV	FMCON, #EP	;else erase & program the page

User manual

	MOV	R7,FMCON	;copy status for return
	MOV	A,R7	;read status
	ANL	A,#0FH	;save only four lower bits
	JNZ	BAD	;
	CLR	С	;clear error flag if good
	RET		;and return
BAD:			
	SETB	С	;set error flag
	RET		;and return

A C-language routine to load the page register and perform an erase/program operation is shown below.

```
#include <REG972.H>
unsigned char idata dbytes[64]; // data buffer
unsigned char Fm_stat; // status result
bit PGM USER (unsigned char, unsigned char);
bit prog_fail;
void main ()
{
     prog_fail=PGM_USER(0x1F,0xC0);
}
bit PGM_USER (unsigned char page_hi, unsigned char page_lo)
            {
                      #define LOAD0x00// clear page register, enable loading
                      #define EP0x68// erase & program page
                      unsigned char i;// loop count
            FMCON = LOAD; //load command, clears page reg
            FMADRH = page hi; //
            FMADRL = page lo; //write my page address to addr regs
             for(i=0;i<64;i=i+1)</pre>
                 {
                                  FMDATA = dbytes[i];
                  }
            FMCON = EP; //erase & prog page command
            Fm_stat = FMCON; //read the result status
            if ((Fm stat & 0x0F)!=0) prog fail=1; else prog fail=0;
            return(prog_fail);
     }
```

### 17.5 In-circuit programming (ICP)

In-Circuit Programming is a method intended to allow commercial programmers to program and erase these devices without removing the microcontroller from the system. The In-Circuit Programming facility consists of a series of internal hardware resources to facilitate remote programming of the P89LPC970/971/972 through a two-wire serial interface. NXP has made in-circuit programming in an embedded application possible with a minimum of additional expense in components and circuit board area. The ICP function

uses five pins ( $V_{DD}$ ,  $V_{SS}$ , P0.5, P0.4, and RST). Only a small connector needs to be available to interface your application to an external programmer in order to use this feature.

### 17.6 ISP and IAP capabilities of the P89LPC970/971/972

An In-Application Programming (IAP) interface is provided to allow the end user's application to erase and reprogram the user code memory. In addition, erasing and reprogramming of user-programmable bytes including UCFG1, UCFG2, the Boot Status Bit, and the Boot Vector is supported. As shipped from the factory, the upper 512 bytes of user code space contains a serial In-System Programming (ISP) loader allowing for the device to be programmed in circuit through the serial port. This ISP boot loader will, in turn, call low-level routines through the same common entry point that can be used by the end-user application.

### 17.7 Boot ROM

When the microcontroller contains a a 256 byte Boot ROM that is separate from the user's Flash program memory. This Boot ROM contains routines which handle all of the low level details needed to erase and program the user Flash memory. A user program simply calls a common entry point in the Boot ROM with appropriate parameters to accomplish the desired operation. Boot ROM operations include operations such as erase sector, erase page, program page, CRC, program security bit, etc. The Boot ROM occupies the program memory space at the top of the address space from FF00 to FFFFh, thereby not conflicting with the user program memory space. This function is in addition to the IAP-Lite feature.

### 17.8 Power on reset code execution

The P89LPC970/971/972 contains two special Flash elements: the BOOT VECTOR and the Boot Status Bit. Following reset, the P89LPC970/971/972 examines the contents of the Boot Status Bit. If the Boot Status Bit is set to zero, power-up execution starts at location 0000H, which is the normal start address of the user's application code. When the Boot Status Bit is set to one, the contents of the Boot Vector is used as the high byte of the execution address and the low byte is set to 00H.

The factory default settings for this device is shown in Table 95, below.

The factory pre-programmed boot loader can be erased by the user. Users who wish to use this loader should take cautions to avoid erasing the last 1 kB sector on the device. Instead, the page erase function can be used to erase the eight 64-byte pages located in this sector. A custom boot loader can be written with the Boot Vector set to the custom boot loader, if desired.


Product	Flash size	End address	Signature bytes		Sector	Page	Pre-programmed	Default Boot	
			Mfg id	ld 1	ld 2	size	size	serial loader	vector
P89LPC970	$2 \ kB \times 8$	07FFh	15h	DDh	40h	$1 \ kB \times 8$	$64\times8$	0600h to 07FFh	07h
P89LPC971	$4 \text{ kB} \times 8$	0FFFh	15h	DDh	41h	$1 \text{ kB} \times 8$	64  imes 8	0E00h to 0FFFh	0Fh
P89LPC972	$8 \text{ kB} \times 8$	1FFFh	15h	DDh	42h	$1 \text{ kB} \times 8$	64  imes 8	1E00h to 1FFFh	1Fh

#### Table 95. Boot loader address and default Boot vector

### 17.9 Hardware activation of Boot Loader

The boot loader can also be executed by forcing the device into ISP mode during a power-on sequence (see Figure 49). This is accomplished by powering up the device with the reset pin initially held low and holding the pin low for a fixed time after V<sub>DD</sub> rises to its normal operating value. This is followed by three, and only three, properly timed low-going pulses. Fewer or more than three pulses will result in the device not entering ISP mode. Timing specifications may be found in the data sheet for this device.

This has the same effect as having a non-zero status bit. This allows an application to be built that will normally execute the user code but can be manually forced into ISP operation. If the factory default setting for the Boot Vector is changed, it will no longer point to the factory pre-programmed ISP boot loader code. If this happens, the only way it is possible to change the contents of the Boot Vector is through the parallel or ICP programming method, provided that the end user application does not contain a customized loader that provides for erasing and reprogramming of the Boot Vector and Boot Status Bit. After programming the Flash, the status byte should be programmed to zero in order to allow execution of the user's application code beginning at address 0000H.



### 17.10 In-system programming (ISP)

In-System Programming is performed without removing the microcontroller from the system. The In-System Programming facility consists of a series of internal hardware resources coupled with internal firmware to facilitate remote programming of the P89LPC970/971/972 through the serial port. This firmware is provided by NXP and embedded within each P89LPC970/971/972 device. The NXP In-System Programming facility has made in-circuit programming in an embedded application possible with a minimum of additional expense in components and circuit board area. The ISP function uses five pins (V<sub>DD</sub>, V<sub>SS</sub>, TXD0, RXD0, and RST). Only a small connector needs to be available to interface your application to an external circuit in order to use this feature.

### 17.11 Using the In-system programming (ISP)

The ISP feature allows for a wide range of baud rates to be used in your application, independent of the oscillator frequency. It is also adaptable to a wide range of oscillator frequencies. This is accomplished by measuring the bit-time of a single bit in a received character. This information is then used to program the baud rate in terms of timer counts based on the oscillator frequency. The ISP feature requires that an initial character (an uppercase U) be sent to the P89LPC970/971/972 to establish the baud rate. The ISP firmware provides auto-echo of received characters. Once baud rate initialization has

been performed, the ISP firmware will only accept Intel Hex-type records. Intel Hex records consist of ASCII characters used to represent hexadecimal values and are summarized below:

#### :NNAAAARRDD..DDCC<crlf>

In the Intel Hex record, the 'NN' represents the number of data bytes in the record. The P89LPC970/971/972 will accept up to 64 (40H) data bytes. The 'AAAA' string represents the address of the first byte in the record. If there are zero bytes in the record, this field is often set to 0000. The 'RR' string indicates the record type. A record type of '00' is a data record. A record type of '01' indicates the end-of-file mark. In this application, additional record types will be added to indicate either commands or data for the ISP facility. The maximum number of data bytes in a record is limited to 64 (decimal). ISP commands are summarized in Table 96. As a record is received by the P89LPC970/971/972, the information in the record is stored internally and a checksum calculation is performed. The operation indicated by the record type is not performed until the entire record has been received. Should an error occur in the checksum, the P89LPC970/971/972 will send an 'X' out the serial port indicating a checksum error. If the checksum calculation is found to match the checksum in the record will be indicated by transmitting a '.' character out the serial port.

**User manual** 

-	
Record type	Command/data function
00	Program User Code Memory Page
	: nnaaaa00ddddcc
	Where:
	nn = number of bytes to program; aaaa = page address; dddd= data bytes; cc
	= checksum;
	Example:10000000102030405006070809DC3
01	Read Version Id
	: 00xxxx01cc
	Where: xxxx = required field but value is a 'don't care'; cc = checksum
	Example: 0000001FF
02	Miscellaneous Write Functions
	:02xxxx02ssddcc
	Where: xxxx = required field but value is a 'don't care'; ss= subfunction code; dd= data; cc= checksum
	Subfunction codes:
	00= UCFG1
	01= UCFG2
	02= Boot Vector
	03= Status Byte
	04= reserved
	05= reserved
	06= reserved
	07= reserved
	08= Security Byte 0
	09= Security Byte 1
	0A= Security Byte 2
	0B= Security Byte 3
	0C= Security Byte 4
	0D= Security Byte 5
	0E= Security Byte 6
	0F= Security Byte 7
	10= Clear Configuration Protection
	Example::020000020347B2

 Table 96.
 In-system Programming (ISP) hex record formats

Table 96. In-sy	ystem Programming (ISP) hex record formatscontinued
Record type	Command/data function
03	Miscellaneous Read Functions
	: 01xxxx03sscc
	Where xxxx = required field but value is a 'don't care'; ss= subfunction code; cc = checksum
	Subfunction codes:
	00= UCFG1
	01= UCFG2
	02= Boot Vector
	03= Status Byte
	04= reserved
	05= reserved
	06= reserved
	07= reserved
	08= Security Byte 0
	09= Security Byte 1
	0A= Security Byte 2
	0B= Security Byte 3
	0C= Security Byte 4
	0D= Security Byte 5
	0E= Security Byte 6
	0F= Security Byte 7
	10= Manufacturer Id
	11= Device Id
	12= Derivative Id
	Example: 0100000312EA
04	Erase Sector/Page
	: 03xxxx04ssaaaacc
	Where: xxxx = required field but value is a 'don't care'; aaaa = sector/page address; ss= 01 erase sector; ss = 00 erase page; cc = checksum
	Example :0300004010000F8
05	Read Sector CRC
	: 01xxxx05aacc
	Where: xxxx = required field but value is a 'don't care'; aa= sector address high byte; cc= checksum
	Example: 0100000504F6

 Table 96.
 In-system Programming (ISP) hex record formats ...continued

UM10345

P89LPC970/971/972 User manual

Record type	Command/data function
06	Read Global CRC
	: 00xxxx06cc
	Where: xxxx = required field but value is a 'don't care'; cc= checksum
	Example: 0000006FA
07	Direct Load of Baud Rate
	: 02xxxx07HHLLcc
	Where: xxxx = required field but value is a 'don't care'; HH= high byte of timer; LL = low byte of timer; cc = checksum
	Example: 02000007FFFF9
08	Reset MCU
	: 00xxxx08cc
	Where: xxxx = required field but value is a 'don't care'; cc = checksum
	Example: 0000008F8

#### Table 96. In-system Programming (ISP) hex record formats ...continued

# 17.12 In-application programming (IAP)

Several In-Application Programming (IAP) calls are available for use by an application program to permit selective erasing and programming of Flash sectors, pages, security bits, configuration bytes, and device id. All calls are made through a common interface, PGM\_MTP. The programming functions are selected by setting up the microcontroller's registers before making a call to PGM\_MTP at FF03H. The IAP calls are shown in Table 98.

# 17.13 IAP authorization key

IAP functions which write or erase code memory require an authorization key be set by the calling routine prior to performing the IAP function call. This authorization key is set by writing 96H to RAM location FFH. The following example was written using the Keil C compiler. The methods used to access a specific physical address in memory may vary with other compilers.

```
#include <ABSACC.H> /* enable absolute memory access */
#define key DBYTE[0xFF] /* force key to be at address 0xFF */
short (*pgm_mtp) (void) = 0xFF00; /* set pointer to IAP entry point */;
key = 0x96; /* set the authorization key */
pgm_mtp (); /* execute the IAP function call */
```

After the function call is processed by the IAP routine, the authorization key will be cleared. Thus it is necessary for the authorization key to be set prior to EACH call to PGM\_MTP that requires a key. If an IAP routine that requires an authorization key is called without a valid authorization key present, the MCU will perform a reset.

# 17.14 Flash write enable

This device has hardware write enable protection. This protection applies to both ISP and IAP modes and applies to both the user code memory space and the user configuration bytes (UCFG1, UCFG2, BOOTVEC, and BOOTSTAT). This protection does not apply to ICP or parallel programmer modes. If the Activate Write Enable (AWE) bit in BOOTSTAT.7

is a logic 0, an internal Write Enable (WE) flag is forced set and writes to the flash memory and configuration bytes are enabled. If the Active Write Enable (AWE) bit is a logic 1, then the state of the internal WE flag can be controlled by the user.

The WE flag is SET by writing the Set Write Enable (08H) command to FMCON followed by a key value (96H) to FMDATA:

```
FMCON = 0x08;
FMDATA = 0x96;
```

The WE flag is CLEARED by writing the Clear Write Enable (0BH) command to FMCON followed by a key value (96H) to FMDATA, or by a reset:

```
FMCON = 0x0B;
FMDATA = 0x96;
```

The ISP function in this device sets the WE flag prior to calling the IAP routines. The IAP function in this device executes a Clear Write Enable command following any write operation. If the Write Enable function is active, user code which calls IAP routines will need to set the Write Enable flag prior to each IAP write function call.

# 17.15 Configuration byte protection

In addition to the hardware write enable protection, described above, the 'configuration bytes' may be separately write protected. These configuration bytes include UCFG1, UCFG2, BOOTVEC, and BOOTSTAT. This protection applies to both ISP and IAP modes and does not apply to ICP or parallel programmer modes.

If the Configuration Write Protect bit (CWP) in BOOTSTAT.6 is a logic 1, writes to the configuration bytes are disabled. If the Configuration Write Protect bit (CWP) is a logic 0, writes to the configuration bytes are enabled. The CWP bit is set by programming the BOOTSTAT register. This bit is cleared by using the Clear Configuration Protection (CCP) command in IAP or ISP.

The Clear Configuration Protection command can be disabled in ISP or IAP mode by programming the Disable Clear Configuration Protection bit (DCCP) in BOOTSTAT.7 to a logic 1. When DCCP is set, the CCP command may still be used in ICP or parallel programming modes. This bit is cleared by writing the Clear Configuration Protection (CCP) command in either ICP or parallel programming modes.

# 17.16 IAP error status

It is not possible to use the Flash memory as the source of program instructions while programming or erasing this same Flash memory. During an IAP erase, program, or CRC the CPU enters a program-idle state. The CPU will remain in this program-idle state until the erase, program, or CRC cycle is completed. These cycles are self timed. When the cycle is completed, code execution resumes. If an interrupt occurs during an erase, programming or CRC cycle, the erase, programming, or CRC cycle will be aborted so that the Flash memory can be used as the source of instructions to service the interrupt. An IAP error condition will be flagged by setting the carry flag and status information returned. The status information returned is shown in Table 97. If the application permits interrupts during erasing, programming, or CRC cycles, the user code should check the carry flag after each erase, programming, or CRC operation to see if an error occurred. If the operation was aborted, the user's code will need to repeat the operation.

### Table 97. IAP error status

Bit	Flag	Description
0	OI	Operation Interrupted. Indicates that an operation was aborted due to an interrupt occurring during a program or erase cycle.
1	SV	Security Violation. Set if program or erase operation fails due to security settings. Cycle is aborted. Memory contents are unchanged. CRC output is invalid.
2	HVE	High Voltage Error. Set if error detected in high voltage generation circuits. Cycle is aborted. Memory contents may be corrupted.
3	VE	Verify error. Set during IAP programming of user code if the contents of the programmed address does not agree with the intended programmed value. IAP uses the MOVC instruction to perform this verify. Attempts to program user code that is MOVC protected can be programmed but will generate this error after the programming cycle has been completed.
4 to 7	-	unused; reads as a logic 0

IAP function	IAP call parameters
Program User Code Page (requires 'key')	Input parameters: ACC = 00h R3= number of bytes to program R4= page address (MSB) R5= page address (LSB) R7= pointer to data buffer in RAM F1= 0h = use IDATA Return parameter(s): R7= status Carry= set on error, clear on no error
Read Version Id	Input parameters: ACC = 01h Return parameter(s): R7=IAP version id
Misc. Write (requires 'key')	Input parameters: ACC = 02h R5= data to write R7= register address 00= UCFG1 01= UCFG2 02= Boot Vector 03= Status Byte 04 to 07 = reserved 08= Security Byte 0 09= Security Byte 1 0A= Security Byte 1 0A= Security Byte 2 0B= Security Byte 3 0C= Security Byte 4 0D= Security Byte 5 0E= Security Byte 6 0F= Security Byte 7 10 = Clear Configuration Protection Return parameter(s): R7= status Carry= set on error, clear on no error

# Table 98. IAP function calls

IAP function	IAP call parameters
Misc. Read	Input parameters:
	ACC = 03h
	R7= register address
	00= UCFG1
	01= UCFG2
	02= Boot Vector
	03= Status Byte
	04 to 07 = reserved
	08= Security Byte 0
	09= Security Byte 1
	0A= Security Byte 2
	0B= Security Byte 3
	0C= Security Byte 4
	0D= Security Byte 5
	0E= Security Byte 6
	0F= Security Byte 7
	Return parameter(s):
	R7= register data if no error, else error status
	Carry= set on error, clear on no error
Erase Sector/Page	Input parameters:
(requires 'key')	ACC = 04h
	R4= address (MSB)
	R5= address (LSB)
	R7= 00H (erase page) or 01H (erase sector)
	Return parameter(s):
	R7= data
	Carry= set on error, clear on no error

#### Table 98. IAP function calls ...continued

Table 98. IAP function c	allscontinued				
IAP function	IAP call parameters				
Read Sector CRC	Input parameters:				
	ACC = 05h				
	R7= sector address				
	Return parameter(s):				
	R4= CRC bits 31:24				
	R5= CRC bits 23:16				
	R6= CRC bits 15:8				
	R7= CRC bits 7:0 (if no error)				
	R7= error status (if error)				
	Carry= set on error, clear on no error				
Read Global CRC	Input parameters:				
	ACC = 06h				
	Return parameter(s):				
	R4= CRC bits 31:24				
	R5= CRC bits 23:16				
	R6= CRC bits 15:8				
	R7= CRC bits 7:0 (if no error)				
	R7= error status (if error)				
	Carry= set on error, clear on no error				
Read User Code	Input parameters:				
	ACC = 07h				
	R4= address (MSB)				
	R5= address (LSB)				
	Return parameter(s):				
	R7= data				

# 

# 17.17 User configuration bytes

A number of user-configurable features of the P89LPC970/971/972 must be defined at power-up and therefore cannot be set by the program after start of execution. These features are configured through the use of an Flash byte UCFG1 and UCFG2 shown in Table 100 and Table 103.

Table 99.	Flash User	Configuration	Byte 1	(UCFG1) bit allocation
-----------	------------	---------------	--------	------------------------

Bit	7	6	5	4	3	2	1	0
Symbol	CLKDBL	RPE	BOE2	BOE1	BOE0	FOSC2	FOSC1	FOSC0
Unprogrammed value	0	1	0	1	0	0	1	1

#### Table 100. Flash User Configuration Byte 1 (UCFG1) bit description

Bit	Symbol	Description
0	FOSC0	CPU oscillator type select. See Section 2 "Clocks" for additional information. Combinations other than those
1	FOSC1	shown in Table 101 are reserved for future use and should not be used.
2	FOSC2	

UM10345

UM10345

P89LPC970/971/972 User manual

Bit	Symbol	Description			
3	BOE0	Brownout Detect Configuration (see Section 5.1 "Brownout detection")			
4	BOE1				
5	BOE2				
6	RPE	Reset pin enable. When set = 1, enables the reset function of pin P1.5. When cleared, P1.5 may be used as an input pin. NOTE: During a power-up sequence, the RPE selection is overridden and this pin will always functions as a reset input. After power-up the pin will function as defined by the RPE bit. Only a power-up reset will temporarily override the selection defined by RPE bit. Other sources of reset will not override the RPE bit.			
7	CLKDBL	Clock doubler. When set, doubles the output frequency of the internal RC oscillator.			

#### Table 100. Flash User Configuration Byte 1 (UCFG1) bit description ... continued

#### Table 101. Oscillator type selection

FOSC[2:0]	Oscillator configuration
111	External clock input on XTAL1.
100	Watchdog Oscillator, nominal 400 kHz /25 kHz.
011	Internal RC oscillator, 7.373 MHz ± 1 %.
010	Low frequency crystal, 20 kHz to 100 kHz.
001	Medium frequency crystal or resonator, 100 kHz to 4 MHz.
000	High frequency crystal or resonator, 4 MHz to 18 MHz.

#### Table 102. Flash User Configuration Byte 2 (UCFG2) bit allocation

		•		,				
Bit	7	6	5	4	3	2	1	0
Symbol	WDTE	-	-	-	-	-	WDSE	-
Unprogrammed value	0	х	x	x	x	x	0	х

#### Table 103. Flash User Configuration Byte 2 (UCFG2) bit description

Bit	Symbol	Description
0	-	Not used.
1	WDSE	Watchdog Safety Enable bit. Refer to Table 86 "Watchdog timer configuration" for details.
2:6	-	Not used.
7	WDTE	Watchdog timer reset enable. When set = 1, enables the watchdog timer reset. When cleared = 0, disables the watchdog timer reset. The timer may still be used to generate an interrupt. Refer to <u>Table 86 "Watchdog timer configuration</u> " for details.

# 17.18 User security bytes

This device has three security bits associated with each of its eight sectors, as shown in Table 104

Table 104	Sector Security	v Bytes	(SECx)	) bit allocation

	-	,						
Bit	7	6	5	4	3	2	1	0
Symbol	-	-	-	-	-	EDISx	SPEDISx	MOVCDISx
Unprogrammed value	0	0	0	0	0	0	0	0

#### Table 105. Sector Security Bytes (SECx) bit description

Bit	Symbol	Description
0	MOVCDISx	MOVC Disable. Disables the MOVC command for sector x. Any MOVC that attempts to read a byte in a MOVC protected sector will return invalid data. This bit can only be erased when sector x is erased.
1	SPEDISx	Sector Program Erase Disable x. Disables program or erase of all or part of sector x. This bit and sector x are erased by either a sector erase command (ISP, IAP, commercial programmer) or a 'global' erase command (commercial programmer).
2	EDISx	Erase Disable ISP. Disables the ability to perform an erase of sector x in ISP or IAP mode. When programmed, this bit and sector x can only be erased by a 'global' erase command using a commercial programmer. This bit and sector x CANNOT be erased in ISP or IAP modes.
3:7	-	reserved

#### Table 106. Effects of Security Bits

EDISx	SPEDISx	MOVCDISx	Effects on Programming
0	0	0	None.
0	0	1	Security violation flag set for sector CRC calculation for the specific sector. Security violation flag set for global CRC calculation if any MOVCDISx bit is set. Cycle aborted. Memory contents unchanged. CRC invalid. Program/erase commands will not result in a security violation.
0	1	x	Security violation flag set for program commands or an erase page command. Cycle aborted. Memory contents unchanged. Sector erase and global erase are allowed.
1	x	x	Security violation flag set for program commands or an erase page command. Cycle aborted. Memory contents unchanged. Global erase is allowed.

# 17.19 Boot Vector register

#### Table 107. Boot Vector (BOOTVEC) bit allocation

Bit	7	6	5	4	3	2	1	0
Symbol	-	-	-	BOOTV4	BOOTV3	BOOTV2	BOOTV1	BOOTV0
Factory default value	0	0	0	1	1	1	1	1

## Table 108. Boot Vector (BOOTVEC) bit description

Bit	Symbol	Description
0:4	BOOTV[0:4]	Boot vector. If the Boot Vector is selected as the reset address, the P89LPC970/971/972 will start execution at an address comprised of 00h in the lower eight bits and this BOOTVEC as the upper eight bits after a reset.
5:7	-	reserved

# 17.20 Boot status register

Table 109. Boot Status (BOOTSTAT) bit allocation								
Bit	7	6	5	4	3	2	1	0
Symbol	DCCP	CWP	AWP	-	-	-	-	BSB
Factory default value	0	0	0	0	0	0	0	1

# Table 109. Boot Status (BOOTSTAT) bit allocation

## Table 110. Boot Status (BOOTSTAT) bit description

Bit	Symbol	Description
0	BSB	Boot Status Bit. If programmed to logic 1, the P89LPC970/971/972 will always start execution at an address comprised of 00H in the lower eight bits and BOOTVEC as the upper bits after a reset. (See <u>Section 6.1 "Reset vector"</u> ).
1:4	-	reserved
5	AWP	Activate Write Protection bit. When this bit is cleared, the internal Write Enable flag is forced to the set state, thus writes to the flash memory are always enabled. When this bit is set, the Write Enable internal flag can be set or cleared using the Set Write Enable (SWE) or Clear Write Enable (CWE) commands.
6	CWP	Configuration Write Protect bit. Protects inadvertent writes to the user programmable configuration bytes (UCFG1, UCFG2, BOOTVEC, and BOOTSTAT). If programmed to a logic 1, the writes to these registers are disabled. If programmed to a logic 0, writes to these registers are enabled.
		This bit is set by programming the BOOTSTAT register. This bit is cleared by writing the Clear Configuration Protection (CCP) command to FMCON followed by writing 96H to FMDATA.
7	DCCP	Disable Clear Configuration Protection command. If Programmed to '1', the Clear Configuration Protection (CCP) command is disabled during ISP or IAP modes. This command can still be used in ICP or parallel programmer modes. If programmed to '0', the CCP command can be used in all programming modes. This bit is set by programming the BOOTSTAT register. This bit is cleared by writing the Clear Configuration Protection (CCP) command in either ICP or parallel programmer modes.

# 18. Instruction set

## Table 111. Instruction set summary

Mnemonic	Description	Bytes	Cycles	Hex code
	ARITHMETIC			
ADD A,Rn	Add register to A	1	1	28 to 2F
ADD A,dir	Add direct byte to A	2	1	25
ADD A,@Ri	Add indirect memory to A	1	1	26 to 27
ADD A,#data	Add immediate to A	2	1	24
ADDC A,Rn	Add register to A with carry	1	1	38 to 3F
ADDC A,dir	Add direct byte to A with carry	2	1	35
ADDC A,@Ri	Add indirect memory to A with carry	1	1	36 to 37
ADDC A,#data	Add immediate to A with carry	2	1	34
SUBB A,Rn	Subtract register from A with borrow	1	1	98 to 9F
SUBB A,dir	Subtract direct byte from A with borrow	2	1	95
SUBB A, @ Ri	Subtract indirect memory from A with borrow	1	1	96 to 97
SUBB A,#data	Subtract immediate from A with borrow	2	1	94
INC A	Increment A	1	1	04
INC Rn	Increment register	1	1	08 to 0F
INC dir	Increment direct byte	2	1	05
INC @Ri	Increment indirect memory	1	1	06 to 07
DEC A	Decrement A	1	1	14
DEC Rn	Decrement register	1	1	18 to 1F
DEC dir	Decrement direct byte	2	1	15
DEC @Ri	Decrement indirect memory	1	1	16 to 17
INC DPTR	Increment data pointer	1	2	A3
MUL AB	Multiply A by B	1	4	A4
DIV AB	Divide A by B	1	4	84
DA A	Decimal Adjust A	1	1	D4
	LOGICAL			
ANL A,Rn	AND register to A	1	1	58 to 5F
ANL A,dir	AND direct byte to A	2	1	55
ANL A,@Ri	AND indirect memory to A	1	1	56 to 57
ANL A,#data	AND immediate to A	2	1	54
ANL dir,A	AND A to direct byte	2	1	52
ANL dir,#data	AND immediate to direct byte	3	2	53
ORL A,Rn	OR register to A	1	1	48 to 4F
ORL A,dir	OR direct byte to A	2	1	45
ORL A,@Ri	OR indirect memory to A	1	1	46 to 47
ORL A,#data	OR immediate to A	2	1	44
ORL dir,A	OR A to direct byte	2	1	42
ORL dir,#data	OR immediate to direct byte	3	2	43

Mnemonic XRL A,Rn

	P89LPC	970/971/972	User manual
continued			
Description	Bytes	Cycles	Hex code
Exclusive-OR register to A	1	1	68 to 6F
Exclusive-OR direct byte to A	2	1	65
Exclusive-OR indirect memory to A	1	1	66 to 67

**UM10345** 

## Table 111. Instruction set summary

XRL A,dir	Exclusive-OR direct byte to A	2	1	65
XRL A, @Ri	Exclusive-OR indirect memory to A	1	1	66 to 67
XRL A,#data	Exclusive-OR immediate to A	2	1	64
XRL dir,A	Exclusive-OR A to direct byte	2	1	62
XRL dir,#data	Exclusive-OR immediate to direct byte	3	2	63
CLR A	Clear A	1	1	E4
CPL A	Complement A	1	1	F4
SWAP A	Swap Nibbles of A	1	1	C4
RL A	Rotate A left	1	1	23
RLC A	Rotate A left through carry	1	1	33
Rotate A right	RR A	1	1	03
RRC A	Rotate A right through carry	1	1	13
	DATA TRANSFER			
MOV A,Rn	Move register to A	1	1	E8 to EF
MOV A,dir	Move direct byte to A	2	1	E5
Move indirect memory to A	MOV A,@Ri	1	1	E6 to E7
MOV A,#data	Move immediate to A	2	1	74
MOV Rn,A	Move A to register	1	1	F8 to FF
MOV Rn,dir	Move direct byte to register	2	2	A8 to AF
MOV Rn,#data	Move immediate to register	2	1	78 to 7F
MOV dir,A	Move A to direct byte	2	1	F5
MOV dir,Rn	Move register to direct byte	2	2	88 to 8F
MOV dir,dir	Move direct byte to direct byte	3	2	85
MOV dir,@Ri	Move indirect memory to direct byte	2	2	86 to 87
MOV dir,#data	Move immediate to direct byte	3	2	75
MOV @Ri,A	Move A to indirect memory	1	1	F6 to F7
MOV @Ri,dir	Move direct byte to indirect memory	2	2	A6 to A7
MOV @Ri,#data	Move immediate to indirect memory	2	1	76 to 77
MOV DPTR,#data	Move immediate to data pointer	3	2	90
MOVC A,@A+DPTR	Move code byte relative DPTR to A	1	2	93
MOVC A,@A+PC	Move code byte relative PC to A	1	2	94
MOVX A,@Ri	Move external data(A8) to A	1	2	E2 to E3
MOVX A,@DPTR	Move external data(A16) to A	1	2	E0
MOVX @Ri,A	Move A to external data(A8)	1	2	F2 to F3
MOVX @DPTR,A	Move A to external data(A16)	1	2	F0
PUSH dir	Push direct byte onto stack	2	2	C0
POP dir	Pop direct byte from stack	2	2	D0
XCH A,Rn	Exchange A and register	1	1	C8 to CF
XCH A,dir	Exchange A and direct byte	2	1	C5
XCH A,@Ri	Exchange A and indirect memory	1	1	C6 to C7
UM10345	All information provided in this document is subject to legal disclaimers.		©N	XP B.V. 2010. All rights reserve

UM10345

All information provided in this document is subject to legal disclaimers.

Mnemonic	Description	Bytes	Cycles	Hex code
XCHD A,@Ri	Exchange A and indirect memory nibble	1	1	D6 to D7
	BOOLEAN			
Mnemonic	Description	Bytes	Cycles	Hex code
CLR C	Clear carry	1	1	C3
CLR bit	Clear direct bit	2	1	C2
SETB C	Set carry	1	1	D3
SETB bit	Set direct bit	2	1	D2
CPL C	Complement carry	1	1	B3
CPL bit	Complement direct bit	2	1	B2
ANL C,bit	AND direct bit to carry	2	2	82
ANL C,/bit	AND direct bit inverse to carry	2	2	B0
ORL C,bit	OR direct bit to carry	2	2	72
ORL C,/bit	OR direct bit inverse to carry	2	2	A0
MOV C,bit	Move direct bit to carry	2	1	A2
MOV bit,C	Move carry to direct bit	2	2	92
	BRANCHING			
ACALL addr 11	Absolute jump to subroutine	2	2	116F1
LCALL addr 16	Long jump to subroutine	3	2	12
RET	Return from subroutine	1	2	22
RETI	Return from interrupt	1	2	32
AJMP addr 11	Absolute jump unconditional	2	2	016E1
LJMP addr 16	Long jump unconditional	3	2	02
SJMP rel	Short jump (relative address)	2	2	80
JC rel	Jump on carry = 1	2	2	40
JNC rel	Jump on carry = 0	2	2	50
JB bit,rel	Jump on direct bit = 1	3	2	20
JNB bit,rel	Jump on direct bit = 0	3	2	30
JBC bit,rel	Jump on direct bit = 1 and clear	3	2	10
JMP @A+DPTR	Jump indirect relative DPTR	1	2	73
JZ rel	Jump on accumulator = 0	2	2	60
JNZ rel	Jump on accumulator $\neq 0$	2	2	70
CJNE A,dir,rel	Compare A, direct jne relative	3	2	B5
CJNE A,#d,rel	Compare A, immediate jne relative	3	2	B4
CJNE Rn,#d,rel	Compare register, immediate jne relative	3	2	B8 to BF
CJNE @Ri,#d,rel	Compare indirect, immediate jne relative	3	2	B6 to B7
DJNZ Rn,rel	Decrement register, jnz relative	2	2	D8 to DF
DJNZ dir,rel	Decrement direct byte, jnz relative	3	2	D5
•	MISCELLANEOUS			
	MISOLLEANLOOS			

### Table 111. Instruction set summary ... continued

UM10345

# 19. Legal information

# **19.1 Definitions**

**Draft** — The document is a draft version only. The content is still under internal review and subject to formal approval, which may result in modifications or additions. NXP Semiconductors does not give any representations or warranties as to the accuracy or completeness of information included herein and shall have no liability for the consequences of use of such information.

# 19.2 Disclaimers

Limited warranty and liability — Information in this document is believed to be accurate and reliable. However, NXP Semiconductors does not give any representations or warranties, expressed or implied, as to the accuracy or completeness of such information and shall have no liability for the consequences of use of such information.

In no event shall NXP Semiconductors be liable for any indirect, incidental, punitive, special or consequential damages (including - without limitation - lost profits, lost savings, business interruption, costs related to the removal or replacement of any products or rework charges) whether or not such damages are based on tort (including negligence), warranty, breach of contract or any other legal theory.

Notwithstanding any damages that customer might incur for any reason whatsoever, NXP Semiconductors' aggregate and cumulative liability towards customer for the products described herein shall be limited in accordance with the *Terms and conditions of commercial sale* of NXP Semiconductors.

**Right to make changes** — NXP Semiconductors reserves the right to make changes to information published in this document, including without limitation specifications and product descriptions, at any time and without notice. This document supersedes and replaces all information supplied prior to the publication hereof.

Suitability for use — NXP Semiconductors products are not designed, authorized or warranted to be suitable for use in life support, life-critical or safety-critical systems or equipment, nor in applications where failure or malfunction of an NXP Semiconductors product can reasonably be expected to result in personal injury, death or severe property or environmental damage. NXP Semiconductors accepts no liability for inclusion and/or use of NXP Semiconductors products in such equipment or applications and therefore such inclusion and/or use is at the customer's own risk.

**Applications** — Applications that are described herein for any of these products are for illustrative purposes only. NXP Semiconductors makes no representation or warranty that such applications will be suitable for the specified use without further testing or modification.

Customers are responsible for the design and operation of their applications and products using NXP Semiconductors products, and NXP Semiconductors accepts no liability for any assistance with applications or customer product design. It is customer's sole responsibility to determine whether the NXP Semiconductors product is suitable and fit for the customer's applications and products planned, as well as for the planned application and use of customer's third party customer(s). Customers should provide appropriate design and operating safeguards to minimize the risks associated with their applications and products.

NXP Semiconductors does not accept any liability related to any default, damage, costs or problem which is based on any weakness or default in the customer's applications or products, or the application or use by customer's third party customer(s). Customer is responsible for doing all necessary testing for the customer's applications and products using NXP Semiconductors products in order to avoid a default of the applications and the products or of the application or use by customer's third party customer(s). NXP does not accept any liability in this respect.

**Export control** — This document as well as the item(s) described herein may be subject to export control regulations. Export might require a prior authorization from national authorities.

# 19.3 Trademarks

Notice: All referenced brands, product names, service names and trademarks are the property of their respective owners.

**User manual** 

# 20. Tables

Table 1.	Pin description4
Table 2.	Special function registers
Table 3.	Extended special function registers <sup>[1]</sup> 17
Table 4.	Data RAM arrangement
Table 5.	On-chip RC oscillator trim register (TRIM -
Table 5.	
Table C	address 96h) bit allocation20 On-chip RC oscillator trim register (TRIM -
Table 6.	
<b>T</b> -1-1- <b>7</b>	address 96h) bit description
Table 7.	Clock control register (CLKCON - address
<b>-</b>	FFDEh) bit allocation
Table 8.	Clock control register (CLKCON - address
	FFDEh) bit description
Table 9.	Oscillator type selection for clock switch23
Table 10.	Interrupt priority level
Table 11.	Summary of interrupts
Table 12.	Number of I/O pins available
Table 13.	Port output configuration settings27
Table 14.	Port output configuration
Table 15.	SPI/I2C/UART Pin Remap
Table 16.	Pin remap Control register (PINCON - address
	CFh) bit allocation
Table 17.	Pin remap Control register (PINCON - address
	CFh) bit description
Table 18.	BOD reset trip points configuration
Table 19.	BOD interrupt trip points configuration
Table 13.	BOD Reset and BOD interrupt configuration
	Power reduction modes
Table 21.	
Table 22.	Power Control register (PCON - address 87h) bit
T-1-1- 00	allocation
Table 23.	Power Control register (PCON - address 87h) bit
<b>-</b>	description
Table 24.	Power Control register A (PCONA - address B5h)
	bit allocation
Table 25.	Power Control register A (PCONA - address B5h)
	bit description
Table 26.	PMU Control register (PMUCON - address FAh)
	bit allocation
Table 27.	PMU control register (PMUCON - address FAh) bit
	description
Table 28.	Reset Sources register (RSTSRC - address DFh)
	bit allocation
Table 29.	Reset Sources register (RSTSRC - address DFh)
	bit description
Table 30.	Timer/Counter Mode register (TMOD - address
	89h) bit allocation
Table 31.	Timer/Counter Mode register (TMOD - address
	89h) bit description
Table 32.	Timer/Counter Auxiliary Mode register (TAMOD -
	address 8Fh) bit allocation
Table 33.	Timer/Counter Auxiliary Mode register (TAMOD -
	address 8Fh) bit description
Table 34	Timer/Counter Control register (TCON) - address
10010 07.	88h) bit allocation
Table 35	Timer/Counter Control register (TCON - address
10010 00.	88h) bit description
Table 26	Timer/Counter x Control (TxCON - where $x = 2, 3$
10018 30.	$\frac{1}{1000} = \frac{1}{1000} = 1$
UM10345	All information provided in this docu

	or 4) bit allocation
Table 37.	Timer/Counter x Control (TxCON - where $x = 2, 3$
Table 38.	or 4) bit description
Table So.	(TINTF, address CEh) bit allocation
Table 39.	
	(TINTF, address CEh) bit description
Table 40.	
Table 41.	Real-time Clock/System Timer clock sources . 51
Table 42.	
	address D1h) bit allocation52
Table 43.	
<b>-</b>	address D1h) bit description53
Table 44.	
	UART baud rate generation
Table 46.	Baud Rate Generator Control register (BRGCON - address BDh) bit allocation
Table 47.	Baud Rate Generator Control register (BRGCON
	- address BDh) bit description
Table 48.	
	bit allocation
Table 49.	Serial Port Control register (SCON - address 98h)
	bit description
Table 50.	
Table 51.	
	bit allocation
Table 52.	
Table CO	bit description
Table 53. Table 54.	
Table 54.	•
Table 55.	•
	allocation
Table 57.	
	bit allocation
Table 58.	I <sup>2</sup> C slave address register (I2ADR - address DBh)
	bit description65
Table 59.	
	allocation
Table 60.	I <sup>2</sup> C Control register (I2CON - address D8h) bit
Table 61	description
Table 61.	I <sup>2</sup> C Status register (I2STAT - address D9h) bit allocation
Table 62.	I <sup>2</sup> C Status register (I2STAT - address D9h) bit
	description
Table 63.	I <sup>2</sup> C clock rates selection
Table 64.	I <sup>2</sup> C Control register (I2CON - address D8h) 68
Table 65.	I <sup>2</sup> C Control register (I2CON - address D8h)70
Table 66.	Master Transmitter mode
Table 67.	Master Receiver mode74
Table 68.	Slave Receiver mode75
	Slave Transmitter mode
Table 70.	SPI Control register (SPCTL - address E2h) bit
Table 74	allocation
Table 71.	
	description

Table	72.	SPI Status register (SPSTAT - address E1h) bit
		allocation
Table	73.	SPI Status register (SPSTAT - address E1h) bit
		description
Table	74.	SPI Data register (SPDAT - address E3h) bit
		allocation
Table	75	SPI master and slave selection
	-	Comparator Control register (CMP1 - address
Table	70.	ACh, CMP2 - address ADh) bit allocation89
Tabla	77	
Table	11.	Comparator Control register (CMP1 - address
		ACh, CMP2 - address ADh) bit description89
Table	78.	Comparator Reference register (CMPREF -
		address FFCBh) bit allocation
Table	79.	Comparator Reference register (CMPREF -
		address FFCBh) bit description
Table	80.	Keypad Pattern register (KBPATN - address 93h)
		bit allocation
Table	81	Keypad Pattern register (KBPATN - address 93h)
Table	01.	bit description
Table	02	Keypad Control register (KBCON - address 94h)
Table	02.	
<b>-</b>	~~	bit allocation
Table	83.	Keypad Control register (KBCON - address 94h)
		bit description94
Table	84.	Keypad Interrupt Mask register (KBMASK -
		address 86h) bit allocation
Table	85.	Keypad Interrupt Mask register (KBMASK -
		address 86h) bit description
Table	86.	Watchdog timer configuration
Table		Watchdog Timer Control register (WDCON -
100.0	••••	address A7h) bit allocation
Table	88	Watchdog Timer Control register (WDCON -
Table	00.	address A7h) bit description
Table	00	
Table		Watchdog timeout values
Table		Watchdog input clock selection
Table		AUXR1 register (address A2h) bit allocation .100
Table	92.	AUXR1 register (address A2h) bit
		description
Table	93.	Flash Memory Control register (FMCON - address
		E4h) bit allocation
Table	94.	Flash Memory Control register (FMCON - address
100.0	•	E4h) bit description
Table	95	Boot loader address and default Boot vector 107
Table		
Table	90.	
<b>-</b>	~7	formats
		IAP error status
		IAP function calls
Table	99.	Flash User Configuration Byte 1 (UCFG1) bit
		allocation
Table	100.	Flash User Configuration Byte 1 (UCFG1) bit
		description
Table	101.	Oscillator type selection
		Flash User Configuration Byte 2 (UCFG2) bit
		allocation
Table	102	Flash User Configuration Byte 2 (UCFG2) bit
Table	100.	
Toble	104	description
		Sector Security Bytes (SECx) bit allocation . 118
	105.	Sector Security Bytes (SECx) bit description 119
Table	106.	Effects of Security Bits119

Table 107. Boot Vector (BOOTVEC) bit allocation 119	
Table 108. Boot Vector (BOOTVEC) bit description 119       119	
Table 109. Boot Status (BOOTSTAT) bit allocation 119	
Table 110. Boot Status (BOOTSTAT) bit description 120	
Table 111. Instruction set summary    121	

# 21. Figures

Fig 1.	TSSOP20 pin configuration
Fig 2.	P89LPC972 DIP20 pin configuration
Fig 3.	Logic symbol
Fig 4.	Block diagram
Fig 5.	P89LPC970/971/972 memory map
Fig 6.	Using the crystal oscillator
Fig 7.	Block diagram of oscillator control
•	
Fig 8.	Interrupt sources, interrupt enables, and power-down wake-up sources
Fig 9.	Quasi-bidirectional output
Fig 10.	Open drain output
Fig 11.	Input only
Fig 12.	Push-pull output
Fig 13.	Block diagram of reset
Fig 14.	Timer/counter 0 or 1 in Mode 0 (13-bit counter) .42
Fig 15.	Timer/counter 0 or 1 in mode 1 (16-bit counter) .43
Fig 16.	Timer/counter 0 or 1 in Mode 2 (8-bit
<b>F</b> : 47	auto-reload)
Fig 17.	Timer/counter 0 Mode 3 (two 8-bit counters)43
Fig 18.	Timer/counter 0 or 1 in mode 6 (PWM
<b>F</b> in <b>10</b>	auto-reload)
Fig 19.	16-bit Timer/Counter Auto-reload Mode47
Fig 20.	16-bit Timer/Counter Input Capture Mode 48
Fig 21.	16-bit PWM Mode
Fig 22.	PWM signal output
Fig 23.	Real-time clock/system timer block diagram 50
Fig 24.	Baud rate generation for UART (Modes 1, 3)55
Fig 25.	Serial Port Mode 0 (double buffering must be
<b>F</b> ' 00	disabled)
Fig 26.	Serial Port Mode 1 (only single transmit buffering
	case is shown)
Fig 27.	Serial Port Mode 2 or 3 (only single transmit buffering case is shown)
Eig 29	Transmission with and without double buffering .61
Fig 28.	
Fig 29.	I <sup>2</sup> C-bus configuration
Fig 30.	Format in the Master Transmitter mode69 Format of Master Receiver mode70
Fig 31.	A Master Receiver switches to Master Transmitter
Fig 32.	after sending Repeated Start
Fig 33.	Format of Slave Receiver mode
Fig 34.	Format of Slave Transmitter mode
Fig 35.	I <sup>2</sup> C serial interface block diagram
Fig 36.	SPI block diagram
-	
Fig 37.	SPI single master single slave configuration 81
Fig 38.	SPI dual device configuration, where either can be a
<b>Fi</b> a 20	master or a slave
Fig 39.	SPI single master multiple slaves configuration82 SPI slave transfer format with CPHA = $085$
Fig 40.	
Fig 41.	SPI slave transfer format with CPHA = $186$
Fig 42.	SPI master transfer format with CPHA = 087 SPI master transfer format with CPHA = 188
Fig 43.	
Fig 44.	Comparator input and output connections90
Fig 45.	Comparator configurations. (Suppose PGA1 is disabled, or gain = 1)92
Fig 16	
Fig 46. Fig 47.	Watchdog Prescaler

UM10345

# 22. Contents

1	Introduction	<b>. 3</b> 7.
1.1	Pin configuration	. 3 7.
1.2	Pin description	. 4 7.
1.3	Logic symbols	. 7 7.
1.4	Block diagram	.8 <b>8</b>
1.5	Special function registers	
1.6	Memory organization	18 8.
2	Clocks	19
2.1	Enhanced CPU	19 8.
2.2	Clock definitions	
2.2.1	Oscillator Clock (OSCCLK)	
2.3	Crystal oscillator option	
2.3.1	Low speed oscillator option	
2.3.2	Medium speed oscillator option	
2.3.3	High speed oscillator option	
2.4	Clock output	
2.5	On-chip RC oscillator option	
2.6	Watchdog oscillator option	11
2.7	External clock input option	
2.8 2.9	Clock source switching on the fly	11
2.9	Oscillator Clock (OSCCLK) wake-up delay CPU Clock (CCLK) modification: DIVM	
2.10	register	23 10
2.11	Low power select	23 11
3	Interrupts	
-	-	
3.1 3.2	Interrupt priority structure	
-	External Interrupt pin glitch suppression	
4	I/O ports	
4.1	Port configurations	
4.2	Quasi-bidirectional output configuration	
4.3	Open drain output configuration	
4.4 4.5	Input-only configuration	
4.5 4.6	Push-pull output configuration	
4.0	Additional port features.	00
4.8	Pin Remap	
<del>5</del>	Power management.	
<b>5</b> .1	Brownout detection	52
5.1 5.2	Power-on detection.	
5.2 5.3	Power reduction modes	
5.3 5.4	Regulators	-
	-	01
6	Reset	31
6.1	Reset vector	39 11
7	Timers 0 and 1	<b>39</b> 11
7.1	Mode 0	1
7.2	Mode 1	41

7.3	Mode 2	41
7.4	Mode 3	41
7.5	Mode 6	41
7.6	Timer overflow toggle output	44
8	Timers 2, 3 and 4	44
8.1	Mode 0: 16-bit Timer/Counter with Auto-reload	d 46
8.2	Mode 1: 16-bit Timer/Counter with Input	
	Capture	47
8.3	Mode 2: 16-bit PWM mode	48
8.4	Timer overflow toggle output	49
9	Real-time clock system timer	49
9.1	Real-time clock source	50
9.2	Changing RTCS1/RTCS0	50
9.3	Real-time clock interrupt/wake-up	50
9.3.1	Real-time clock read back	51
9.4	Reset sources affecting the Real-time clock .	51
10	UART	53
10.1	Mode 0	53
10.2	Mode 1	53
10.3	Mode 2	53
10.4	Mode 3	54
10.5	SFR space	54
10.6	Baud Rate generator and selection	54
10.7	Updating the BRGR1 and BRGR0 SFRs	54
10.8	Framing error	55
10.9	Break detect	55
10.10	More about UART Mode 0	57
10.11	More about UART Mode 1	58
10.12	More about UART Modes 2 and 3	59
10.13	Framing error and RI in Modes 2 and 3 with	
40.44	SM2 = 1	59
10.14	Break detect.	60
10.15 10.16	Double buffering.	60 60
10.18	Double buffering in different modes Transmit interrupts with double buffering enab	
10.17	(Modes 1, 2, and 3)	60
10.18	The 9th bit (bit 8) in double buffering (Modes 1	
10.10	and 3)	, <u>2</u> , 61
10.19	Multiprocessor communications.	62
10.10	Automatic address recognition.	63
	-	
11	I <sup>2</sup> C interface	64 67
11.1 11.2	I <sup>2</sup> C data register	65
11.2	I <sup>2</sup> C slave address register	65
11.3	I <sup>2</sup> C control register I <sup>2</sup> C Status register	66 67
11.4	I <sup>2</sup> C SCL duty cycle registers I2SCLH and	07
11.5	I2SCLL	67
	1200LL	07

# continued >>

11.6	I <sup>2</sup> C operation modes 68
11.6.1	Master Transmitter mode 68
11.6.2	Master Receiver mode 69
11.6.3	Slave Receiver mode
11.6.4	Slave Transmitter mode
12	Serial Peripheral Interface (SPI) (Pin Remap) 78
12.1	Configuring the SPI 82
12.2	Additional considerations for a slave 83
12.3	Additional considerations for a master 83
12.4	Mode change on <u>SS</u> 83
12.5	Write collision 84
12.6	Data mode 84
12.7	SPI clock prescaler select
13	Analog comparators 88
13.1	Comparator configuration
13.2	Selectable internal reference voltage
13.3	Comparator input pins 91
13.4	Comparator interrupt
13.5	Comparators and power reduction modes 91
13.6	Comparators configuration example
14	Keypad interrupt (KBI) 93
15	Watchdog timer (WDT) 94
15.1	Watchdog function
15.2	Feed sequence
15.3	Watchdog clock source
15.4	Watchdog Timer in Timer mode 99
15.5	Power-down operation 100
15.6	Periodic wake-up from power-down without an
	external oscillator 100
16	Additional features 100
16.1	Software reset
16.2	Dual Data Pointers 101
17	Flash memory 102
17.1	General description 102
17.2	Features
17.3	Flash programming and erase 102
17.4	Using Flash as data storage: IAP-Lite 103
17.5	In-circuit programming (ICP)
17.6	ISP and IAP capabilities of the
	P89LPC970/971/972 107
17.7	Boot ROM 107
17.8	Power on reset code execution 107
17.9	Hardware activation of Boot Loader 108
17.10	In-system programming (ISP)
17.11	Using the In-system programming (ISP) 108
17.12	In-application programming (IAP) 112
17.13	IAP authorization key 112
17.14	Flash write enable 112
17.15	Configuration byte protection 113

17.16	IAP error status 113
17.17	User configuration bytes 117
17.18	User security bytes 118
17.19	Boot Vector register 119
17.20	Boot status register 119
18	Instruction set 121
19	Legal information 124
19.1	Definitions 124
10.1	
19.2	Disclaimers 124
19.2	Disclaimers 124
19.2 19.3	Disclaimers

Please be aware that important notices concerning this document and the product(s) described herein, have been included in section 'Legal information'.

#### © NXP B.V. 2010.

For more information, please visit: http://www.nxp.com For sales office addresses, please send an email to: salesaddresses@nxp.com

Date of release: 1 July 2010 Document identifier: UM10345

All rights reserved.