



TE21-5101

Test Report Date: 20-Nov-2020 Page: 1 of 18 No.: ETR20B02241

SHINKO ELECTRIC INDUSTRIES CO., LTD. 80 OSHIMADA-MACHI, NAGANO-SHI, 381-2287 JAPAN

The following sample(s) was/were submitted and identified by/on behalf of the applicant as:

Sample Submitted By SHINKO ELECTRIC INDUSTRIES CO., LTD.

Sample Name Ag PLATING

Use For BASE MATERIAL: Copper & 42-ALLOY

Sample Receiving Date 13-Nov-2020

Testing Period 13-Nov-2020 to 20-Nov-2020

Test Requested (1) As specified by client, with reference to RoHS 2011/65/EU Annex II and

> amending Directive (EU) 2015/863 to determine Cadmium, Lead, Mercury, Cr(VI), PBBs, PBDEs, DBP, BBP, DEHP, DIBP contents in the

submitted sample(s).

(2) Please refer to next pages for the other item(s).

Test Results Please refer to following pages.

Conclusion (1) Based on the performed tests on submitted sample(s), the test results

of Cadmium, Lead, Mercury, Cr(VI), PBBs, PBDEs, DBP, BBP, DEHP, DIBP

comply with the limits as set by RoHS Directive (EU) 2015/863

amending Annex II to Directive 2011/65/EU.

Chang Manage Te Signed for and on behalf SĞS TAIWAN LTD. Chemical Laboratory - Taipei





No.: ETR20B02241 Date: 20-Nov-2020 Page: 2 of 18

SHINKO ELECTRIC INDUSTRIES CO., LTD.
80 OSHIMADA-MACHI, NAGANO-SHI, 381-2287 JAPAN

TEST PART DESCRIPTION

No.1 : SILVER-WHITE METAL SHEET

Test Result(s)

Test Item(s)	Method	Unit	MDL	Result	Limit
				No.1	
Cadmium (Cd) (CAS No.: 7440-43-9)	With reference to IEC 62321-5: 2013, analysis was performed by	mg/kg	2	n.d.	100
Lead (Pb) (CAS No.: 7439-92-1)	ICP-OES.	mg/kg	2	n.d.	1000
Mercury (Hg) (CAS No.: 7439-97-6)	With reference to IEC 62321-4: 2013+ AM D1: 2017, analysis was performed by ICP-OES.	mg/kg	2	n.d.	1000
Chromium VI (CrVI) (CAS No.: 18540-29-9) (#2)	With reference to IEC 62321-7-1: 2015, analysis was performed by UV-VIS.	μg/cm²	0.1	n.d.	-8
Hexavalent Chromium Cr(VI) (CAS No.: 18540-29-9)	With reference to IEC 62321-7-2: 2017, analysis was performed by UV-VIS.	mg/kg	8	n.d.	-
Monobromobiphenyl		mg/kg	5	n.d.	-
Dibromobiphenyl		mg/kg	5	n.d.	=3
Tribromobiphenyl		mg/kg	5	n.d.	=:
Tetrabromobiphenyl		mg/kg	5	n.d.	
Pentabromobiphenyl	With reference to IEC 62321-6:	mg/kg	5	n.d.	=
Hexabromobiphenyl	2015, analysis was performed by	mg/kg	5	n.d.	1
Heptabromobiphenyl	GC/MS.	mg/kg	5	n.d.	æ
Octabromobiphenyl		mg/kg	5	n.d.	12 0
Nonabromobiphenyl		mg/kg	5	n.d.	-7
Decabromobiphenyl		mg/kg	5	n.d.	-
Sum of PBBs		mg/kg	-	n.d.	1000



No.: ETR20B02241 Date: 20-Nov-2020 Page: 3 of 18

SHINKO ELECTRIC INDUSTRIES CO., LTD.
80 OSHIMADA-MACHI, NAGANO-SHI, 381-2287 JAPAN

Test Item(s)	Method	Unit	M DL	Result	Limit
				No.1	
Monobromodiphenyl ether		mg/kg	5	n.d.	-
Dibromodiphenyl ether		mg/kg	5	n.d.	-
Tribromodiphenyl ether		mg/kg	5	n.d.	-
Tetrabromodiphenyl ether		mg/kg	5	n.d.	-
Pentabromodiphenyl ether	With reference to IEC 62321-6:	mg/kg	5	n.d.	-
Hexabromodiphenyl ether	2015, analysis was performed by	mg/kg	5	n.d.	-
Heptabromodiphenyl ether	GC/MS.	mg/kg	5	n.d.	-
Octabromodiphenyl ether		mg/kg	5	n.d.	-
Nonabromodiphenyl ether		mg/kg	5	n.d.	-
Decabromodiphenyl ether		mg/kg	5	n.d.	-
Sum of PBDEs		mg/kg	ı	n.d.	1000
Fluorine (F) (CAS No.: 14762-94-8)	With reference to BS EN 14582: 2016, analysis was performed by IC.	mg/kg	50	n.d.	-
Chlorine (CI) (CAS No.: 22537-15-1)	With reference to BS EN 14582: 2016, analysis was performed by IC.	mg/kg	50	n.d.	-
Bromine (Br) (CAS No.: 10097-32-2)	With reference to BS EN 14582: 2016, analysis was performed by IC.	mg/kg	50	n.d.	-
Iodine (I) (CAS No.: 14362-44-8)	With reference to BS EN 14582: 2016, analysis was performed by IC.	mg/kg	50	n.d.	-
PFOS and its salts (CAS No.: 1763-23-1 and its salts)	With reference to CEN/TS 15968: 2010, analysis was performed by LC/MS/MS.	mg/kg	0.01	n.d.	-
PFOA and its salts (CAS No.: 335-67-1 and its salts)	With reference to CEN/TS 15968: 2010, analysis was performed by LC/MS/MS.	mg/kg	0.01	n.d.	-
Polyvinyl chloride (PVC)	With reference to ASTM E1252: 2013, analysis was performed by FT-IR and Flame Test.	**	-	Negative	-
Antimony (Sb) (CAS No.: 7440-36- 0)	With reference to US EPA 3052: 1996, analysis was performed by ICP-OES.	mg/kg	2	n.d.	-



Port No.: ETR20B02241 Date: 20-Nov-2020 **Page: 4 of 18**

SHINKO ELECTRIC INDUSTRIES CO., LTD.
80 OSHIMADA-MACHI, NAGANO-SHI, 381-2287 JAPAN

Test Item(s)	Method	Unit	MDL	Result	Limit
				No.1	
Beryllium (Be) (CAS No.: 7440-41-7)	With reference to US EPA 3052: 1996, analysis was performed by ICP-OES.	mg/kg	2	n.d.	-
Arsenic (As) (CAS No.: 7440-38-2)	With reference to US EPA 3052: 1996, analysis was performed by ICP-OES.	mg/kg	2	n.d.	-
Butyl benzyl phthalate (BBP) (CAS No.: 85-68-7)	With reference to IEC 62321-8: 2017, analysis was performed by GC/MS.	mg/kg	50	n.d.	1000
Dibutyl phthalate (DBP) (CAS No.: 84-74-2)	With reference to IEC 62321-8: 2017, analysis was performed by GC/MS.	mg/kg	50	n.d.	1000
Di-(2-ethylhexyl) phthalate (DEHP) (CAS No.: 117-81-7)	With reference to IEC 62321-8: 2017, analysis was performed by GC/MS.	mg/kg	50	n.d.	1000
Diisobutyl phthalate (DIBP) (CAS No.: 84-69-5)	With reference to IEC 62321-8: 2017, analysis was performed by GC/MS.	mg/kg	50	n.d.	1000
Diisodecyl phthalate (DIDP) (CAS No.: 26761-40-0, 68515-49-1)	With reference to IEC 62321-8: 2017, analysis was performed by GC/MS.	mg/kg	50	n.d.	1
Diisononyl phthalate (DINP) (CAS No.: 28553-12-0, 68515-48-0)	With reference to IEC 62321-8: 2017, analysis was performed by GC/MS.	mg/kg	50	n.d.	-
Di-n-octyl phthalate (DNOP) (CAS No.: 117-84-0)	With reference to IEC 62321-8: 2017, analysis was performed by GC/MS.	mg/kg	50	n.d.	-
Di-n-pentyl phthalate (DNPP) (CAS No.: 131-18-0)	With reference to IEC 62321-8: 2017, analysis was performed by GC/MS.	mg/kg	50	n.d.	-
Diisopentyl phthalate (DIPP) (CAS No.: 605-50-5)	With reference to IEC 62321-8: 2017, analysis was performed by GC/MS.	mg/kg	50	n.d.	-
Di-n-hexyl phthalate (CAS No.: 84-75-3)	With reference to IEC 62321-8: 2017, analysis was performed by GC/MS.	mg/kg	50	n.d.	-



Page: 5 of 18 No.: ETR20B02241 Date: 20-Nov-2020

SHINKO ELECTRIC INDUSTRIES CO., LTD. 80 OSHIMADA-MACHI, NAGANO-SHI, 381-2287 JAPAN

Test Item(s)	Method	Unit	M DL	Result No.1	Limit
Bis(2-methoxyethyl) phthalate (DMEP) (CAS No.: 117-82-8)	With reference to IEC 62321-8: 2017, analysis was performed by GC/MS.	mg/kg	50	n.d.	3 0
1,2-Benzenedicarboxylic acid, di- C6-8-branched alkyl esters, C7-rich (DIHP) (CAS No.: 71888-89-6)	With reference to IEC 62321-8: 2017, analysis was performed by GC/MS.	mg/kg	50	n.d.	EX.
1,2-Benzenedicarboxylic acid, di- C7-11-branched and linear alkyl esters (DHNUP) (CAS No.: 68515- 42-4)	With reference to IEC 62321-8: 2017, analysis was performed by GC/MS.	mg/kg	50	n.d.	100
Hexabromocyclododecane (HBCDD) and all major diastereoisomers identified (α -HBCDD, β -HBCDD, γ -HBCDD) (CAS No.: 25637-99-4, 3194-55-6 (134237-51-7, 134237-50-6, 134237-52-8))	With reference to IEC 62321: 2008, analysis was performed by GC/MS.	mg/kg	5	n.d.	L.
Polychlorinated biphenyls (PCBs)	With reference to US EPA 3550C: 2007, analysis was performed by GC/MS.	mg/kg	0.5	n.d.	15
Polychlorinated naphthalene (PCNs)	With reference to US EPA 3550C: 2007, analysis was performed by GC/MS.	mg/kg	5	n.d.	¥
Polychlorinated terphenyls (PCTs)	With reference to US EPA 3550C: 2007, analysis was performed by GC/MS.	mg/kg	0.5	n.d.	= 3
Short Chain Chlorinated Paraffins(C10-C13) (SCCP) (CAS No.: 85535-84-8)	With reference to US EPA 3550C: 2007, analysis was performed by GC/MS.	mg/kg	100	n.d.	3
Tributyl tin (TBT)	With reference to ISO 17353: 2004, analysis was performed by GC/FPD.	mg/kg	0.03	n.d.	-
Bis(tributyltin) oxide (TBTO) (CAS No.: 56-35-9)	Calculated from the result of Tributyl Tin (TBT).	mg/kg	0.03 🛦	n.d.	-



No.: ETR20B02241 Date: 20-Nov-2020 Page: 6 of 18

SHINKO ELECTRIC INDUSTRIES CO., LTD. 80 OSHIMADA-MACHI, NAGANO-SHI, 381-2287 JAPAN

Test Item(s)	Method	Unit	MDL	Result	Limit
				No.1	
Triphenyl tin (TPhT)	With reference to ISO 17353: 2004, analysis was performed by GC/FPD.	mg/kg	0.03	n.d.	B
Dibutyl tin (DBT)	With reference to ISO 17353: 2004, analysis was performed by GC/FPD.	mg/kg	0.03	n.d.	6 8
Dioctyl tin (DOT)	With reference to ISO 17353: 2004, analysis was performed by GC/FPD.	mg/kg	0.03	n.d.	ë
4-Tert-butylphenol (CAS No.: 98- 54-4)	With reference to RSTS-EE- SVHC-007, analysis was performed by GC/MS.	mg/kg	500	n.d.	•

Note:

- 1. mg/kg = ppm ; 0.1wt% = 1000ppm
- 2. MDL = Method Detection Limit
- 3. n.d. = Not Detected (Less than MDL)
- 4. "-" = Not Regulated
- 5. **= Qualitative analysis (No Unit)
- 6. Negative = Undetectable ; Positive = Detectable
- 7. PFOS and its salts including:
 - CAS No.: 29081-56-9, 2795-39-3, 29457-72-5, 70225-14-8, 56773-42-3, 251099-16-8, 307-35-7.
- 8. PFOA and its salts including:
 - CAS No.: 3825-26-1, 335-95-5, 2395-00-8, 335-93-3, 335-66-0.
- 9. (#2) =
 - a. The sample is positive for Cr(VI) if the Cr(VI) concentration is greater than 0.13 $\mu g/cm^2$. The sample coating is considered to contain Cr(VI).
 - b. The sample is negative for Cr(VI) if Cr(VI) is n.d. (concentration less than 0.10 μ g/cm²). The coating is considered a non-Cr(VI) based coating
 - c. The result between $0.10 \,\mu g/cm^2$ and $0.13 \,\mu g/cm^2$ is considered to be inconclusive unavoidable coating variations may influence the determination.



No.: ETR20B02241 Date: 20-Nov-2020 Page: 7 of 18

SHINKO ELECTRIC INDUSTRIES CO., LTD.
80 OSHIMADA-MACHI, NAGANO-SHI, 381-2287 JAPAN

10. ▲ : The MDL was evaluated for element / tested substance.

Conversion Formula : $AX = A \times F$

AX	Α	F	
Bis(tributyltin)oxide (TBTO)	Tributyl Tin	1.024	

Parameter Conversion Table: https://eecloud.sgs.com/Region_TW/DocDownload.aspx#otherDoc

11. The statement of compliance conformity is based on comparison of testing results and limits.




No.: ETR20B02241 Date: 20-Nov-2020 Page: 8 of 18

SHINKO ELECTRIC INDUSTRIES CO., LTD. 80 OSHIMADA-MACHI, NAGANO-SHI, 381-2287 JAPAN

Analytical flow chart of Heavy Metal

These samples were dissolved totally by pre-conditioning method according to below flow chart.

(Cr6+ test method excluded)






No.: ETR20B02241 Date: 20-Nov-2020 Page: 9 of 18

SHINKO ELECTRIC INDUSTRIES CO., LTD. 80 OSHIMADA-MACHI, NAGANO-SHI, 381-2287 JAPAN

Analytical flow chart - PBBs / PBDEs






No.: ETR20B02241 Date: 20-Nov-2020

SHINKO ELECTRIC INDUSTRIES CO., LTD. 80 OSHIMADA-MACHI, NAGANO-SHI, 381-2287 JAPAN

Analytical flow chart - Halogen



This document is issued by the Company subject to its General Conditions of Service printed overleaf, available on request or accessible at https://www.sgs.com.tw/terms-of-service. Attention is drawn to the limitation of liability, indemnification and jurisdiction issues defined therein. Any holder of this document is advised that information contained hereon reflects the Company's findings at the time of its intervention only and within the limits of client's instruction, if any. The Company's sole responsibility is to its Client and this document does not exonerate parties to a transaction from exercising all their rights and obligations under the transaction documents. This document cannot be reproduced, except in full, without prior written approval of the Company. Any unauthorized alteration, forgery or falsification of the content or appearance of this document is unlawful and offenders may be prosecuted to the fullest extent of the law. Unless otherwise stated the results shown in this test report refer only to the sample(s) tested.


Page: 10 of 18



No.: ETR20B02241 Date: 20-Nov-2020

SHINKO ELECTRIC INDUSTRIES CO., LTD. 80 OSHIMADA-MACHI, NAGANO-SHI, 381-2287 JAPAN

Analytical flow chart - PFOA/PFOS



This document is issued by the Company subject to its General Conditions of Service printed overleaf, available on request or accessible at https://www.sgs.com.tw/terms-of-service. Attention is drawn to the limitation of liability, indemnification and jurisdiction issues defined therein. Any holder of this document is advised that information contained hereon reflects the Company's findings at the time of its intervention only and within the limits of client's instruction, if any. The Company's sole responsibility is to its Client and this document does not exonerate parties to a transaction from exercising all their rights and obligations under the transaction documents. This document cannot be reproduced, except in full, without prior written approval of the Company. Any unauthorized alteration, forgery or falsification of the content or appearance of this document is unlawful and offenders may be prosecuted to the fullest extent of the law. Unless otherwise stated the results shown in this test report refer only to the sample(s) tested.


Page: 11 of 18



No.: ETR20B02241 Date: 20-Nov-2020 Page: 12 of 18

SHINKO ELECTRIC INDUSTRIES CO., LTD. 80 OSHIMADA-MACHI, NAGANO-SHI, 381-2287 JAPAN

Analysis flow chart - PVC






No.: ETR20B02241 Date: 20-Nov-2020 Page: 13 of 18

SHINKO ELECTRIC INDUSTRIES CO., LTD. 80 OSHIMADA-MACHI, NAGANO-SHI, 381-2287 JAPAN

Analytical flow chart of Heavy Metal

These samples were dissolved totally by pre-conditioning method according to below flow chart.

[Reference method: US EPA 3051 \ US EPA 3052]



* US EPA 3051 method does not add HF.




No.: ETR20B02241 Date: 20-Nov-2020 Page: 14 of 18

SHINKO ELECTRIC INDUSTRIES CO., LTD. 80 OSHIMADA-MACHI, NAGANO-SHI, 381-2287 JAPAN

Analytical flow chart - Phthalate

[Test method: IEC 62321-8]






No.: ETR20B02241 Date: 20-Nov-2020 Page: 15 of 18

SHINKO ELECTRIC INDUSTRIES CO., LTD. 80 OSHIMADA-MACHI, NAGANO-SHI, 381-2287 JAPAN

Analytical flow chart - HBCDD






No.: ETR20B02241 Date: 20-Nov-2020 Page: 16 of 18

SHINKO ELECTRIC INDUSTRIES CO., LTD. 80 OSHIMADA-MACHI, NAGANO-SHI, 381-2287 JAPAN

Analytical flow chart

* Apply to: PCBs, PCNs, PCTs, Mirex, Chlorinated Paraffins, DBBT






No.: ETR20B02241 Date: 20-Nov-2020 Page: 17 of 18

SHINKO ELECTRIC INDUSTRIES CO., LTD. 80 OSHIMADA-MACHI, NAGANO-SHI, 381-2287 JAPAN

Analytical flow chart - Organic-Tin





No.: ETR20B02241 Date: 20-Nov-2020

SHINKO ELECTRIC INDUSTRIES CO., LTD.
80 OSHIMADA-MACHI, NAGANO-SHI, 381-2287 JAPAN

*The tested sample / part is marked by an arrow if it's shown on the photo. *

ETR20B02241



** End of Report **

This document is issued by the Company subject to its General Conditions of Service printed overleaf, available on request or accessible at https://www.sgs.com.tw/terms-of-service. Attention is drawn to the limitation of liability, indemnification and jurisdiction issues defined therein. Any holder of this document is advised that information contained hereon reflects the Company's findings at the time of its intervention only and within the limits of client's instruction, if any. The Company's sole responsibility is to its Client and this document does not exonerate parties to a transaction from exercising all their rights and obligations under the transaction documents. This document cannot be reproduced, except in full, without prior written approval of the Company. Any unauthorized alteration, forgery or falsification of the content or appearance of this document is unlawful and offenders may be prosecuted to the fullest extent of the law. Unless otherwise stated the results shown in this test report refer only to the sample(s) tested.

Page: 18 of 18